

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331849-940

Luminaire Tested: **S122RDIW-S1005D710U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331849-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D710U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5929.0 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55	50
2	92	85	79	75	86	80	75	70	69	66	62	60	57	55	51	49	48	43
3	85	76	69	63	79	71	65	60	62	58	54	54	51	48	46	44	42	38
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37	34
5	72	61	53	48	67	57	51	45	51	45	41	44	40	37	38	35	33	30
6	67	55	47	42	62	52	45	40	46	41	36	41	36	33	35	32	29	27
7	62	50	43	37	58	48	41	36	42	37	33	37	33	30	33	29	27	24
8	58	46	39	33	54	44	37	32	39	33	29	34	30	27	30	27	24	22
9	54	42	35	30	51	40	34	29	36	31	27	32	28	24	28	25	22	20
10	51	39	32	27	48	37	31	26	33	28	24	30	25	22	26	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31752	31752	31752	31752
5°	35462	31951	28329	31951
10°	39346	31727	24556	31727
15°	41279	31263	19348	31263
20°	35787	30574	16744	30574
25°	23469	29630	14949	29630
30°	15797	28486	13530	28486
35°	12796	27045	12203	27045
40°	11377	25478	11291	25478
45°	10298	23640	10079	23640
50°	9372	21815	9339	21815
55°	8811	19792	8695	19792
60°	7369	17938	7282	17938
65°	6212	16290	7049	16290
70°	5740	14549	6647	14549
75°	5371	12664	6138	12664
80°	4956	10423	5467	10423
85°	4557	8225	4798	8225



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	3.1
10°-20°	519.5	8.8
20°-30°	669.4	11.3
30°-40°	636.1	10.7
40°-50°	544.9	9.2
50°-60°	415.0	7.0
60°-70°	262.3	4.4
70°-80°	131.0	2.2
80°-90°	36.2	0.6
90°-100°	28.8	0.5
100°-110°	105.5	1.8
110°-120°	282.1	4.8
120°-130°	465.6	7.9
130°-140°	495.2	8.4
140°-150°	460.3	7.8
150°-160°	370.1	6.2
160°-170°	238.5	4.0
170°-180°	82.1	1.4
0°-30°	1375.3	23.2
0°-40°	2011.4	33.9
0°-60°	2971.3	50.1
0°-90°	3400.9	57.4
90°-120°	416.4	7.0
90°-150°	1837.6	31.0
90°-180°	2528.0	42.6
0°-180°	5929.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1967	1967	1967	1967	1967	
5°	2188	1971	1748	1971	2188	216
15°	2470	1870	1158	1870	2470	666
25°	1317	1663	839	1663	1317	625
35°	649	1372	619	1372	649	415
45°	451	1035	441	1035	451	349
55°	313	703	309	703	313	275
65°	163	426	184	426	163	166
75°	86	203	98	203	86	91
85°	25	44	26	44	25	27
90°	17	1	17	1	17	9
95°	27	41	27	41	27	25
105°	47	190	47	190	47	49
115°	51	359	51	359	51	128
125°	534	508	534	508	534	462
135°	649	628	649	628	649	500
145°	740	728	740	728	740	463
155°	803	802	803	802	803	370
165°	843	845	843	845	843	238
175°	860	865	860	865	860	82
180°	863	863	863	863	863	



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	2046.4	2048.1	2049.7	2045.9	2045.9	2042.6	2035.5	2030.0	2014.7	2012.5	2012.5
5°	2188.0	2186.7	2189.3	2180.5	2168.2	2165.4	2152.5	2135.4	2117.6	2097.8	2093.7
7.5°	2328.8	2326.7	2321.2	2319.8	2310.3	2289.6	2268.8	2246.5	2217.0	2188.2	2173.6
10°	2399.9	2422.4	2408.7	2384.8	2389.6	2357.5	2340.4	2311.0	2286.4	2243.4	2233.8
12.5°	2469.8	2478.7	2474.3	2460.8	2454.6	2432.3	2409.2	2383.7	2338.3	2299.6	2266.0
15°	2469.5	2482.5	2485.9	2481.8	2485.3	2483.9	2471.6	2450.4	2410.7	2368.4	2331.5
17.5°	2287.2	2296.2	2318.6	2333.8	2353.0	2393.4	2413.3	2421.2	2415.3	2391.1	2365.1
20°	2082.8	2067.7	2130.6	2162.8	2190.0	2258.3	2317.1	2339.7	2375.9	2375.3	2368.4
22.5°	1793.1	1796.6	1856.2	1894.4	1974.2	2042.5	2109.4	2194.3	2264.4	2310.7	2337.8
25°	1317.4	1343.5	1402.8	1454.8	1543.6	1670.7	1786.2	1920.1	2046.6	2146.3	2241.3
27.5°	989.4	991.4	1038.5	1086.5	1139.2	1243.4	1388.8	1548.7	1728.9	1877.7	2048.7
30°	847.3	843.2	863.0	892.4	937.5	1018.2	1127.5	1284.7	1464.4	1688.5	1888.0
32.5°	746.7	747.0	761.9	783.6	821.1	875.5	950.4	1078.0	1247.9	1468.2	1702.2
35°	649.2	648.5	659.4	675.1	690.8	725.7	776.9	843.9	960.7	1166.4	1405.6
37.5°	579.2	582.2	587.5	597.4	614.7	634.1	664.9	709.8	793.1	914.7	1115.7
40°	539.8	541.2	548.7	556.9	567.1	582.2	607.4	643.7	704.5	801.6	948.4
42.5°	503.7	505.2	510.4	518.1	526.2	541.2	562.1	593.4	642.7	718.5	839.6
45°	451.0	451.0	455.8	459.2	468.1	481.7	498.8	524.8	558.9	615.0	695.6
47.5°	401.5	401.6	404.8	410.7	416.3	427.0	443.7	464.9	489.8	533.2	602.0
50°	373.1	373.8	375.9	380.6	384.1	393.6	406.6	425.0	451.0	484.5	541.9
52.5°	350.2	349.7	352.3	354.4	356.7	363.6	373.3	389.5	412.7	441.8	489.4
55°	313.0	310.2	314.3	317.7	319.8	322.5	328.0	338.2	358.0	382.6	418.2
57.5°	266.5	265.4	268.3	271.4	277.9	285.3	289.9	296.4	306.7	324.3	359.5
60°	228.2	228.2	234.3	236.4	244.0	253.5	263.1	268.6	278.8	290.4	316.4
62.5°	194.3	194.9	197.8	199.8	204.0	215.8	229.2	241.2	250.9	262.0	279.2
65°	162.6	164.0	164.0	165.3	168.1	170.9	176.3	185.8	203.0	218.6	231.7
67.5°	138.0	138.5	138.8	140.2	140.9	143.9	146.1	150.3	154.3	169.2	185.3
70°	121.6	123.7	123.0	124.4	125.0	126.4	129.1	131.2	137.3	140.8	150.3
72.5°	106.3	107.8	107.7	108.5	110.3	110.6	112.7	114.8	118.8	121.6	126.8
75°	86.1	85.4	86.1	87.5	88.2	88.8	88.8	91.6	93.6	96.3	99.8
77.5°	66.4	67.1	67.0	67.1	67.2	68.5	68.3	69.6	71.6	72.9	74.6
80°	53.3	53.9	53.3	53.9	54.7	55.4	54.7	55.4	57.4	58.8	58.8
82.5°	41.3	41.4	41.8	42.0	42.1	42.3	43.2	43.3	44.9	44.6	45.1
85°	24.6	23.9	23.9	23.9	24.6	25.3	24.6	24.6	25.3	25.3	25.3
87.5°	12.1	12.6	12.6	12.5	12.5	12.3	12.2	12.6	11.9	12.3	11.6
90°	16.9	16.6	16.3	16.1	15.8	15.2	14.5	13.9	13.2	12.5	11.4
92.5°	16.9	16.7	16.5	16.3	16.2	16.0	15.6	15.2	14.8	14.4	13.9
95°	26.8	27.0	27.1	27.3	27.4	27.1	26.4	25.8	25.1	24.3	23.4
97.5°	35.8	35.7	35.5	35.3	35.1	34.8	34.2	33.7	33.2	32.5	30.3
100°	41.8	41.6	41.3	41.0	40.8	40.0	38.9	37.8	36.6	35.6	33.3
102.5°	44.9	44.4	44.1	43.7	43.2	42.4	40.9	39.5	38.0	36.6	56.3
105°	47.4	46.9	46.4	45.7	45.2	44.1	42.6	41.1	39.6	38.1	76.0
107.5°	48.8	48.2	47.7	47.2	46.6	47.1	48.7	50.2	51.7	53.3	98.7
110°	49.3	48.8	48.2	47.6	47.1	53.8	67.6	81.5	95.4	109.2	149.4



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	49.8	49.4	49.0	48.5	48.1	73.1	123.8	174.3	225.0	275.5	285.4
115°	51.2	61.2	71.2	81.1	91.1	128.2	192.4	256.7	320.9	385.1	381.7
117.5°	209.0	241.8	274.6	307.5	340.3	364.4	380.0	395.6	411.1	426.6	424.2
120°	380.8	399.5	418.2	436.9	455.7	464.2	462.5	460.9	459.2	457.5	455.0
122.5°	475.2	478.8	482.4	486.1	489.7	491.1	490.0	489.0	488.0	487.1	484.3
125°	533.7	533.3	532.9	532.4	532.1	531.4	530.4	529.4	528.4	527.4	524.9
127.5°	570.7	570.6	570.5	570.4	570.3	569.6	568.2	566.8	565.3	563.9	562.0
130°	593.7	593.8	594.0	594.1	594.2	593.5	592.0	590.5	589.0	587.5	585.9
132.5°	616.2	616.3	616.4	616.5	616.7	616.1	614.8	613.5	612.2	610.9	609.4
135°	648.6	648.9	649.2	649.4	649.7	649.2	647.7	646.4	645.0	643.6	642.4
137.5°	678.1	678.7	679.1	679.6	680.1	679.7	678.2	676.9	675.6	674.2	672.8
140°	696.7	697.3	698.0	698.7	699.5	699.2	697.9	696.7	695.4	694.2	692.6
142.5°	714.6	715.3	716.0	716.8	717.4	717.2	716.0	714.9	713.8	712.7	710.9
145°	739.8	740.4	741.1	741.8	742.5	742.3	741.4	740.4	739.5	738.5	736.1
147.5°	761.8	762.4	763.0	763.6	764.2	764.1	763.4	762.7	762.0	761.2	758.8
150°	775.3	776.0	776.7	777.4	778.1	778.0	777.2	776.3	775.5	774.7	772.5
152.5°	786.8	787.7	788.6	789.5	790.5	790.5	789.7	788.8	788.0	787.2	785.1
155°	802.8	803.9	805.0	806.1	807.2	807.4	806.6	805.7	804.9	804.1	802.4
157.5°	817.3	818.5	819.6	820.6	821.7	821.8	820.8	819.9	818.9	818.0	816.8
160°	825.9	826.9	827.8	828.8	829.7	829.8	829.0	828.1	827.3	826.5	825.6
162.5°	832.9	834.0	835.3	836.4	837.7	837.8	836.8	835.9	834.9	834.0	833.3
165°	843.4	844.4	845.3	846.2	847.2	847.2	846.2	845.3	844.4	843.4	842.9
167.5°	850.0	851.2	852.5	853.7	855.0	855.1	854.2	853.2	852.2	851.2	850.9
170°	854.0	855.2	856.5	857.7	859.0	859.1	858.1	857.2	856.2	855.2	855.0
172.5°	856.9	858.2	859.4	860.7	861.9	862.1	861.1	860.1	859.2	858.2	857.9
175°	859.6	860.9	862.4	863.7	865.1	865.3	864.3	863.4	862.5	861.5	861.2
177.5°	861.2	862.2	863.2	864.2	865.2	865.3	864.5	863.8	863.0	862.2	862.1
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	2013.7	2009.2	2005.5	1995.6	1990.7	1979.7	1978.1	1977.5	1963.4	1949.6	1945.8
5°	2082.8	2071.8	2055.5	2036.3	2016.5	1996.0	1982.4	1971.4	1944.0	1918.1	1903.1
7.5°	2152.5	2129.0	2100.7	2064.5	2034.3	2000.4	1975.2	1952.7	1913.9	1876.7	1851.6
10°	2204.4	2166.1	2128.5	2078.7	2039.7	2001.4	1966.0	1935.2	1891.4	1842.3	1807.4
12.5°	2236.7	2194.6	2142.8	2094.0	2043.5	1994.9	1947.3	1907.8	1856.5	1805.6	1764.2
15°	2280.3	2235.2	2172.3	2102.6	2037.6	1974.2	1919.5	1870.3	1803.3	1742.5	1691.9
17.5°	2316.0	2253.9	2186.4	2105.8	2030.6	1949.8	1879.5	1816.6	1742.0	1668.7	1609.1
20°	2327.4	2265.9	2188.0	2107.4	2018.6	1923.6	1847.7	1779.4	1699.4	1619.4	1551.1
22.5°	2320.3	2272.4	2185.9	2089.4	1998.3	1899.0	1813.3	1734.0	1645.3	1563.7	1484.4
25°	2272.1	2255.7	2173.6	2068.4	1964.5	1849.1	1750.0	1663.2	1562.1	1474.6	1388.5
27.5°	2159.5	2194.9	2144.1	2032.0	1916.6	1792.8	1681.4	1582.6	1477.7	1379.2	1293.4
30°	2051.4	2132.6	2110.8	2006.9	1877.8	1756.1	1631.1	1527.9	1415.9	1314.7	1230.0
32.5°	1903.2	2037.6	2058.9	1971.9	1838.4	1704.8	1573.7	1471.1	1354.1	1247.5	1164.9
35°	1667.3	1868.2	1960.4	1905.1	1771.2	1627.0	1491.7	1372.1	1254.5	1149.3	1067.4
37.5°	1385.9	1659.6	1813.3	1817.2	1694.3	1544.4	1397.0	1278.3	1158.0	1054.6	966.0
40°	1203.4	1499.9	1700.1	1744.5	1640.7	1478.7	1329.7	1208.8	1091.3	990.2	888.3
42.5°	1039.4	1334.8	1580.9	1658.1	1575.7	1414.8	1265.2	1138.8	1024.6	928.9	824.9
45°	840.5	1098.8	1370.0	1508.1	1462.3	1313.3	1155.5	1035.3	927.9	845.3	745.5
47.5°	709.0	891.1	1153.6	1340.2	1339.4	1203.5	1048.2	933.0	833.5	756.0	675.3
50°	634.1	792.6	1014.8	1226.5	1244.3	1130.2	982.6	868.5	775.6	694.3	629.4
52.5°	566.9	697.5	897.2	1100.3	1150.8	1052.0	908.8	803.4	713.3	638.5	582.9
55°	479.0	580.1	731.8	921.8	998.4	928.6	801.6	703.1	630.0	567.1	519.3
57.5°	405.2	481.1	602.8	755.7	844.9	801.0	696.2	616.3	553.7	496.8	459.1
60°	358.7	420.9	524.1	651.9	750.3	719.5	630.0	555.5	502.2	453.1	417.5
62.5°	315.0	368.5	456.9	560.6	650.8	638.1	565.0	502.5	455.8	411.0	380.8
65°	253.5	292.5	361.5	442.8	515.2	521.4	468.8	426.4	384.7	349.2	322.5
67.5°	201.9	227.3	275.9	344.4	398.7	418.0	385.9	353.6	320.5	293.0	269.9
70°	170.1	190.6	226.1	281.5	331.4	351.9	333.5	308.2	279.5	256.9	237.1
72.5°	137.9	157.8	184.0	224.7	267.4	289.6	283.2	265.0	241.7	223.0	204.3
75°	103.9	110.0	127.8	155.2	188.6	207.8	212.5	203.0	184.5	170.1	159.2
77.5°	76.8	80.5	89.0	103.3	125.2	142.2	149.3	148.1	135.5	127.1	116.8
80°	61.5	63.6	67.7	73.8	90.2	107.3	112.1	112.1	103.2	99.8	89.5
82.5°	46.7	48.2	50.7	54.1	61.8	76.7	82.0	83.1	77.5	72.9	64.9
85°	26.7	25.9	27.4	29.4	30.8	34.9	43.1	44.4	43.1	37.5	35.5
87.5°	11.3	11.7	11.4	10.6	10.9	11.1	13.6	16.0	14.1	12.8	11.9
90°	10.3	9.2	8.0	6.7	5.2	3.7	2.1	0.6	2.1	3.7	5.2
92.5°	13.4	12.8	12.3	12.0	12.2	12.3	12.5	12.6	12.5	12.3	12.2
95°	22.4	21.4	20.4	22.3	26.8	31.4	36.0	40.6	36.0	31.4	26.8
97.5°	28.1	25.9	23.6	28.9	41.8	54.8	67.6	80.5	67.6	54.8	41.8
100°	30.9	28.5	26.1	34.5	53.5	72.5	91.5	110.5	91.5	72.5	53.5
102.5°	76.1	95.8	115.5	127.3	131.3	135.4	139.5	143.5	139.5	135.4	131.3
105°	113.8	151.7	189.6	206.4	202.2	198.1	193.9	189.8	193.9	198.1	202.2
107.5°	144.2	189.6	235.0	256.0	252.6	249.3	245.9	242.5	245.9	249.3	252.6
110°	189.4	229.5	269.6	288.2	285.3	282.4	279.5	276.5	279.5	282.4	285.3



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	295.3	305.2	315.1	318.8	316.2	313.7	311.1	308.5	311.1	313.7	316.2
115°	378.3	374.8	371.3	368.4	366.0	363.6	361.3	358.9	361.3	363.6	366.0
117.5°	421.9	419.5	417.1	414.6	411.9	409.3	406.6	404.0	406.6	409.3	411.9
120°	452.5	450.0	447.5	445.3	443.2	441.1	439.1	436.9	439.1	441.1	443.2
122.5°	481.6	478.8	476.2	473.7	471.5	469.3	467.2	464.9	467.2	469.3	471.5
125°	522.2	519.6	516.9	514.7	512.9	511.1	509.3	507.5	509.3	511.1	512.9
127.5°	560.0	558.0	556.1	554.1	552.1	550.1	548.0	546.1	548.0	550.1	552.1
130°	584.3	582.8	581.3	579.4	577.2	575.0	572.7	570.5	572.7	575.0	577.2
132.5°	607.8	606.3	604.8	603.1	601.2	599.3	597.4	595.6	597.4	599.3	601.2
135°	641.1	639.9	638.6	636.9	634.6	632.4	630.2	628.0	630.2	632.4	634.6
137.5°	671.4	669.9	668.5	667.0	665.5	664.0	662.4	660.8	662.4	664.0	665.5
140°	691.1	689.6	688.0	686.7	685.6	684.5	683.4	682.3	683.4	684.5	685.6
142.5°	709.2	707.4	705.6	704.3	703.3	702.3	701.2	700.3	701.2	702.3	703.3
145°	733.8	731.4	729.1	727.9	728.1	728.3	728.3	728.5	728.3	728.3	728.1
147.5°	756.5	754.2	751.9	751.0	751.5	752.1	752.6	753.0	752.6	752.1	751.5
150°	770.3	768.0	765.8	765.2	766.2	767.1	768.1	769.1	768.1	767.1	766.2
152.5°	782.9	780.9	778.7	778.2	779.3	780.4	781.5	782.6	781.5	780.4	779.3
155°	800.7	799.1	797.4	797.2	798.4	799.7	800.9	802.2	800.9	799.7	798.4
157.5°	815.6	814.5	813.3	813.3	814.3	815.4	816.5	817.5	816.5	815.4	814.3
160°	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	825.6	824.8	824.0
162.5°	832.6	831.8	831.1	831.2	832.0	832.9	833.7	834.5	833.7	832.9	832.0
165°	842.5	842.1	841.7	841.9	842.8	843.6	844.4	845.3	844.4	843.6	842.8
167.5°	850.4	850.1	849.7	849.9	850.7	851.6	852.4	853.2	852.4	851.6	850.7
170°	854.7	854.3	854.1	854.3	855.2	856.0	856.8	857.7	856.8	856.0	855.2
172.5°	857.6	857.4	857.1	857.4	858.2	859.1	859.9	860.7	859.9	859.1	858.2
175°	860.9	860.6	860.3	860.7	861.7	862.6	863.6	864.6	863.6	862.6	861.7
177.5°	862.0	861.8	861.7	862.1	862.9	863.6	864.4	865.2	864.4	863.6	862.9
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1938.8	1934.9	1927.8	1916.8	1910.3	1898.8	1891.1	1895.5	1896.7	1895.5	1894.4
5°	1886.7	1872.3	1852.5	1833.4	1815.6	1796.4	1785.6	1780.7	1771.2	1765.7	1763.0
7.5°	1823.6	1798.9	1770.9	1737.6	1709.2	1679.6	1664.5	1656.9	1637.4	1626.7	1617.4
10°	1776.6	1737.7	1709.7	1666.0	1639.3	1600.4	1573.7	1574.4	1547.7	1532.7	1521.8
12.5°	1724.7	1681.9	1635.3	1596.0	1559.0	1527.7	1495.5	1482.6	1454.3	1439.8	1410.2
15°	1638.6	1588.8	1539.5	1486.2	1448.7	1400.2	1353.7	1297.0	1251.2	1211.6	1200.6
17.5°	1544.6	1482.8	1433.5	1370.9	1306.5	1224.9	1171.1	1138.2	1110.5	1089.7	1074.1
20°	1480.1	1417.2	1364.6	1270.3	1183.5	1128.2	1088.5	1063.3	1034.6	1012.0	999.7
22.5°	1412.3	1346.7	1275.0	1169.7	1102.1	1057.7	1022.3	993.3	973.8	956.3	945.0
25°	1316.1	1244.3	1126.1	1053.6	999.0	952.5	927.9	910.2	889.7	865.8	854.9
27.5°	1214.4	1100.3	1015.4	961.5	909.4	879.1	857.0	830.5	812.2	801.4	790.1
30°	1138.4	1024.3	958.1	899.3	862.4	828.8	802.9	787.9	770.1	751.6	744.1
32.5°	1053.6	962.5	899.0	850.1	812.6	784.1	763.6	739.2	726.4	715.1	699.3
35°	948.4	879.4	821.4	781.8	746.2	723.0	699.0	684.7	661.5	651.9	645.8
37.5°	859.3	799.5	756.2	714.3	686.2	660.5	645.9	623.0	613.0	599.7	586.7
40°	809.0	750.3	708.6	674.4	643.0	623.8	605.4	587.0	571.9	565.8	550.1
42.5°	757.7	709.8	668.2	630.7	609.7	589.4	566.1	552.5	537.0	527.0	517.3
45°	686.7	644.4	608.9	578.1	554.8	533.7	518.6	496.1	487.2	467.4	459.2
47.5°	624.5	585.1	551.2	521.9	499.3	485.4	463.4	445.8	431.6	419.5	408.9
50°	580.1	547.3	514.5	488.6	468.1	448.3	425.7	416.8	394.9	388.8	382.6
52.5°	539.7	508.5	478.5	453.1	432.6	413.3	393.4	381.8	367.1	361.0	356.4
55°	483.1	453.1	424.4	401.8	381.3	361.5	349.2	334.8	328.0	323.2	317.7
57.5°	426.2	399.2	377.2	354.4	333.8	318.0	303.8	295.2	288.1	281.8	275.3
60°	390.2	364.2	344.4	323.2	302.0	289.0	278.1	267.9	259.7	250.1	247.4
62.5°	351.9	329.2	311.0	290.4	272.0	260.1	249.7	240.0	230.2	216.2	212.4
65°	299.3	281.5	262.4	245.3	228.9	217.3	202.2	191.4	187.3	185.8	185.2
67.5°	251.7	235.0	218.6	201.0	186.1	175.3	167.7	166.0	163.2	162.4	160.4
70°	220.1	204.3	187.9	171.5	157.2	155.2	152.4	149.6	146.2	144.9	143.5
72.5°	191.6	175.3	158.9	145.8	139.6	137.1	134.4	131.6	129.3	128.0	127.1
75°	147.0	131.9	120.9	116.2	112.7	110.7	106.6	104.5	103.2	101.1	100.4
77.5°	105.8	97.3	92.3	89.3	85.7	83.5	81.1	79.1	77.7	77.2	76.2
80°	80.6	76.5	73.1	69.0	67.7	64.9	64.2	62.2	62.9	60.8	60.8
82.5°	62.6	57.4	54.6	52.6	51.3	49.0	48.4	47.4	47.5	46.0	46.0
85°	32.1	30.8	29.4	28.0	28.0	25.9	26.7	25.9	25.9	24.6	23.9
87.5°	11.8	11.4	10.6	10.8	11.1	10.7	10.9	10.4	10.5	10.7	10.3
90°	6.7	8.0	9.2	10.3	11.4	12.5	13.2	13.9	14.5	15.2	15.8
92.5°	12.0	12.3	12.8	13.4	13.9	14.4	14.8	15.2	15.6	16.0	16.2
95°	22.3	20.4	21.4	22.4	23.4	24.3	25.1	25.8	26.4	27.1	27.4
97.5°	28.9	23.6	25.9	28.1	30.3	32.5	33.2	33.7	34.2	34.8	35.1
100°	34.5	26.1	28.5	30.9	33.3	35.6	36.6	37.8	38.9	40.0	40.8
102.5°	127.3	115.5	95.8	76.1	56.3	36.6	38.0	39.5	40.9	42.4	43.2
105°	206.4	189.6	151.7	113.8	76.0	38.1	39.6	41.1	42.6	44.1	45.2
107.5°	256.0	235.0	189.6	144.2	98.7	53.3	51.7	50.2	48.7	47.1	46.6
110°	288.2	269.6	229.5	189.4	149.4	109.2	95.4	81.5	67.6	53.8	47.1



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	318.8	315.1	305.2	295.3	285.4	275.5	225.0	174.3	123.8	73.1	48.1
115°	368.4	371.3	374.8	378.3	381.7	385.1	320.9	256.7	192.4	128.2	91.1
117.5°	414.6	417.1	419.5	421.9	424.2	426.6	411.1	395.6	380.0	364.4	340.3
120°	445.3	447.5	450.0	452.5	455.0	457.5	459.2	460.9	462.5	464.2	455.7
122.5°	473.7	476.2	478.8	481.6	484.3	487.1	488.0	489.0	490.0	491.1	489.7
125°	514.7	516.9	519.6	522.2	524.9	527.4	528.4	529.4	530.4	531.4	532.1
127.5°	554.1	556.1	558.0	560.0	562.0	563.9	565.3	566.8	568.2	569.6	570.3
130°	579.4	581.3	582.8	584.3	585.9	587.5	589.0	590.5	592.0	593.5	594.2
132.5°	603.1	604.8	606.3	607.8	609.4	610.9	612.2	613.5	614.8	616.1	616.7
135°	636.9	638.6	639.9	641.1	642.4	643.6	645.0	646.4	647.7	649.2	649.7
137.5°	667.0	668.5	669.9	671.4	672.8	674.2	675.6	676.9	678.2	679.7	680.1
140°	686.7	688.0	689.6	691.1	692.6	694.2	695.4	696.7	697.9	699.2	699.5
142.5°	704.3	705.6	707.4	709.2	710.9	712.7	713.8	714.9	716.0	717.2	717.4
145°	727.9	729.1	731.4	733.8	736.1	738.5	739.5	740.4	741.4	742.3	742.5
147.5°	751.0	751.9	754.2	756.5	758.8	761.2	762.0	762.7	763.4	764.1	764.2
150°	765.2	765.8	768.0	770.3	772.5	774.7	775.5	776.3	777.2	778.0	778.1
152.5°	778.2	778.7	780.9	782.9	785.1	787.2	788.0	788.8	789.7	790.5	790.5
155°	797.2	797.4	799.1	800.7	802.4	804.1	804.9	805.7	806.6	807.4	807.2
157.5°	813.3	813.3	814.5	815.6	816.8	818.0	818.9	819.9	820.8	821.8	821.7
160°	823.1	823.1	824.0	824.8	825.6	826.5	827.3	828.1	829.0	829.8	829.7
162.5°	831.2	831.1	831.8	832.6	833.3	834.0	834.9	835.9	836.8	837.8	837.7
165°	841.9	841.7	842.1	842.5	842.9	843.4	844.4	845.3	846.2	847.2	847.2
167.5°	849.9	849.7	850.1	850.4	850.9	851.2	852.2	853.2	854.2	855.1	855.0
170°	854.3	854.1	854.3	854.7	855.0	855.2	856.2	857.2	858.1	859.1	859.0
172.5°	857.4	857.1	857.4	857.6	857.9	858.2	859.2	860.1	861.1	862.1	861.9
175°	860.7	860.3	860.6	860.9	861.2	861.5	862.5	863.4	864.3	865.3	865.1
177.5°	862.1	861.7	861.8	862.0	862.1	862.2	863.0	863.8	864.5	865.3	865.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1888.5	1889.5	1887.9	1889.0	1887.9	1889.5	1888.5	1894.4	1895.5	1896.7	1895.5
5°	1759.5	1751.3	1750.0	1747.9	1750.0	1751.3	1759.5	1763.0	1765.7	1771.2	1780.7
7.5°	1605.7	1604.5	1601.1	1596.3	1601.1	1604.5	1605.7	1617.4	1626.7	1637.4	1656.9
10°	1506.7	1503.3	1502.6	1497.8	1502.6	1503.3	1506.7	1521.8	1532.7	1547.7	1574.4
12.5°	1390.8	1368.9	1366.5	1354.6	1366.5	1368.9	1390.8	1410.2	1439.8	1454.3	1482.6
15°	1184.2	1180.1	1166.4	1157.5	1166.4	1180.1	1184.2	1200.6	1211.6	1251.2	1297.0
17.5°	1066.1	1052.8	1048.5	1046.6	1048.5	1052.8	1066.1	1074.1	1089.7	1110.5	1138.2
20°	990.2	977.9	975.8	974.5	975.8	977.9	990.2	999.7	1012.0	1034.6	1063.3
22.5°	937.6	924.8	919.4	915.3	919.4	924.8	937.6	945.0	956.3	973.8	993.3
25°	848.0	843.2	840.5	839.1	840.5	843.2	848.0	854.9	865.8	889.7	910.2
27.5°	777.9	767.4	765.4	761.8	765.4	767.4	777.9	790.1	801.4	812.2	830.5
30°	738.0	734.6	729.8	725.7	729.8	734.6	738.0	744.1	751.6	770.1	787.9
32.5°	691.0	688.1	683.9	682.0	683.9	688.1	691.0	699.3	715.1	726.4	739.2
35°	638.9	629.4	625.3	619.1	625.3	629.4	638.9	645.8	651.9	661.5	684.7
37.5°	583.8	578.8	573.0	575.1	573.0	578.8	583.8	586.7	599.7	613.0	623.0
40°	541.2	537.8	536.5	535.7	536.5	537.8	541.2	550.1	565.8	571.9	587.0
42.5°	507.3	497.8	494.3	494.2	494.3	497.8	507.3	517.3	527.0	537.0	552.5
45°	455.8	446.9	440.8	441.4	440.8	446.9	455.8	459.2	467.4	487.2	496.1
47.5°	403.1	402.8	399.0	400.1	399.0	402.8	403.1	408.9	419.5	431.6	445.8
50°	377.9	373.8	371.0	371.8	371.0	373.8	377.9	382.6	388.8	394.9	416.8
52.5°	353.8	350.3	348.1	351.0	348.1	350.3	353.8	356.4	361.0	367.1	381.8
55°	314.3	310.2	309.5	308.9	309.5	310.2	314.3	317.7	323.2	328.0	334.8
57.5°	270.2	267.4	263.3	261.5	263.3	267.4	270.2	275.3	281.8	288.1	295.2
60°	238.4	233.0	226.1	225.5	226.1	233.0	238.4	247.4	250.1	259.7	267.9
62.5°	209.5	208.4	207.1	206.9	207.1	208.4	209.5	212.4	216.2	230.2	240.0
65°	183.8	183.2	183.8	184.5	183.8	183.2	183.8	185.2	185.8	187.3	191.4
67.5°	160.2	158.9	157.7	158.3	157.7	158.9	160.2	160.4	162.4	163.2	166.0
70°	142.1	141.4	140.8	140.8	140.8	141.4	142.1	143.5	144.9	146.2	149.6
72.5°	124.7	124.5	123.9	123.2	123.9	124.5	124.7	127.1	128.0	129.3	131.6
75°	99.8	98.4	98.4	98.4	98.4	98.4	99.8	100.4	101.1	103.2	104.5
77.5°	76.0	75.3	74.6	74.1	74.6	75.3	76.0	76.2	77.2	77.7	79.1
80°	60.1	59.5	58.8	58.8	58.8	59.5	60.1	60.8	60.8	62.9	62.2
82.5°	45.9	45.2	45.1	44.6	45.1	45.2	45.9	46.0	46.0	47.5	47.4
85°	24.6	25.3	24.6	25.9	24.6	25.3	24.6	23.9	24.6	25.9	25.9
87.5°	10.3	9.8	10.4	9.9	10.4	9.8	10.3	10.3	10.7	10.5	10.4
90°	16.1	16.3	16.6	16.9	16.6	16.3	16.1	15.8	15.2	14.5	13.9
92.5°	16.3	16.5	16.7	16.9	16.7	16.5	16.3	16.2	16.0	15.6	15.2
95°	27.3	27.1	27.0	26.8	27.0	27.1	27.3	27.4	27.1	26.4	25.8
97.5°	35.3	35.5	35.7	35.8	35.7	35.5	35.3	35.1	34.8	34.2	33.7
100°	41.0	41.3	41.6	41.8	41.6	41.3	41.0	40.8	40.0	38.9	37.8
102.5°	43.7	44.1	44.4	44.9	44.4	44.1	43.7	43.2	42.4	40.9	39.5
105°	45.7	46.4	46.9	47.4	46.9	46.4	45.7	45.2	44.1	42.6	41.1
107.5°	47.2	47.7	48.2	48.8	48.2	47.7	47.2	46.6	47.1	48.7	50.2
110°	47.6	48.2	48.8	49.3	48.8	48.2	47.6	47.1	53.8	67.6	81.5



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	48.5	49.0	49.4	49.8	49.4	49.0	48.5	48.1	73.1	123.8	174.3
115°	81.1	71.2	61.2	51.2	61.2	71.2	81.1	91.1	128.2	192.4	256.7
117.5°	307.5	274.6	241.8	209.0	241.8	274.6	307.5	340.3	364.4	380.0	395.6
120°	436.9	418.2	399.5	380.8	399.5	418.2	436.9	455.7	464.2	462.5	460.9
122.5°	486.1	482.4	478.8	475.2	478.8	482.4	486.1	489.7	491.1	490.0	489.0
125°	532.4	532.9	533.3	533.7	533.3	532.9	532.4	532.1	531.4	530.4	529.4
127.5°	570.4	570.5	570.6	570.7	570.6	570.5	570.4	570.3	569.6	568.2	566.8
130°	594.1	594.0	593.8	593.7	593.8	594.0	594.1	594.2	593.5	592.0	590.5
132.5°	616.5	616.4	616.3	616.2	616.3	616.4	616.5	616.7	616.1	614.8	613.5
135°	649.4	649.2	648.9	648.6	648.9	649.2	649.4	649.7	649.2	647.7	646.4
137.5°	679.6	679.1	678.7	678.1	678.7	679.1	679.6	680.1	679.7	678.2	676.9
140°	698.7	698.0	697.3	696.7	697.3	698.0	698.7	699.5	699.2	697.9	696.7
142.5°	716.8	716.0	715.3	714.6	715.3	716.0	716.8	717.4	717.2	716.0	714.9
145°	741.8	741.1	740.4	739.8	740.4	741.1	741.8	742.5	742.3	741.4	740.4
147.5°	763.6	763.0	762.4	761.8	762.4	763.0	763.6	764.2	764.1	763.4	762.7
150°	777.4	776.7	776.0	775.3	776.0	776.7	777.4	778.1	778.0	777.2	776.3
152.5°	789.5	788.6	787.7	786.8	787.7	788.6	789.5	790.5	790.5	789.7	788.8
155°	806.1	805.0	803.9	802.8	803.9	805.0	806.1	807.2	807.4	806.6	805.7
157.5°	820.6	819.6	818.5	817.3	818.5	819.6	820.6	821.7	821.8	820.8	819.9
160°	828.8	827.8	826.9	825.9	826.9	827.8	828.8	829.7	829.8	829.0	828.1
162.5°	836.4	835.3	834.0	832.9	834.0	835.3	836.4	837.7	837.8	836.8	835.9
165°	846.2	845.3	844.4	843.4	844.4	845.3	846.2	847.2	847.2	846.2	845.3
167.5°	853.7	852.5	851.2	850.0	851.2	852.5	853.7	855.0	855.1	854.2	853.2
170°	857.7	856.5	855.2	854.0	855.2	856.5	857.7	859.0	859.1	858.1	857.2
172.5°	860.7	859.4	858.2	856.9	858.2	859.4	860.7	861.9	862.1	861.1	860.1
175°	863.7	862.4	860.9	859.6	860.9	862.4	863.7	865.1	865.3	864.3	863.4
177.5°	864.2	863.2	862.2	861.2	862.2	863.2	864.2	865.2	865.3	864.5	863.8
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1891.1	1898.8	1910.3	1916.8	1927.8	1934.9	1938.8	1945.8	1949.6	1963.4	1977.5
5°	1785.6	1796.4	1815.6	1833.4	1852.5	1872.3	1886.7	1903.1	1918.1	1944.0	1971.4
7.5°	1664.5	1679.6	1709.2	1737.6	1770.9	1798.9	1823.6	1851.6	1876.7	1913.9	1952.7
10°	1573.7	1600.4	1639.3	1666.0	1709.7	1737.7	1776.6	1807.4	1842.3	1891.4	1935.2
12.5°	1495.5	1527.7	1559.0	1596.0	1635.3	1681.9	1724.7	1764.2	1805.6	1856.5	1907.8
15°	1353.7	1400.2	1448.7	1486.2	1539.5	1588.8	1638.6	1691.9	1742.5	1803.3	1870.3
17.5°	1171.1	1224.9	1306.5	1370.9	1433.5	1482.8	1544.6	1609.1	1668.7	1742.0	1816.6
20°	1088.5	1128.2	1183.5	1270.3	1364.6	1417.2	1480.1	1551.1	1619.4	1699.4	1779.4
22.5°	1022.3	1057.7	1102.1	1169.7	1275.0	1346.7	1412.3	1484.4	1563.7	1645.3	1734.0
25°	927.9	952.5	999.0	1053.6	1126.1	1244.3	1316.1	1388.5	1474.6	1562.1	1663.2
27.5°	857.0	879.1	909.4	961.5	1015.4	1100.3	1214.4	1293.4	1379.2	1477.7	1582.6
30°	802.9	828.8	862.4	899.3	958.1	1024.3	1138.4	1230.0	1314.7	1415.9	1527.9
32.5°	763.6	784.1	812.6	850.1	899.0	962.5	1053.6	1164.9	1247.5	1354.1	1471.1
35°	699.0	723.0	746.2	781.8	821.4	879.4	948.4	1067.4	1149.3	1254.5	1372.1
37.5°	645.9	660.5	686.2	714.3	756.2	799.5	859.3	966.0	1054.6	1158.0	1278.3
40°	605.4	623.8	643.0	674.4	708.6	750.3	809.0	888.3	990.2	1091.3	1208.8
42.5°	566.1	589.4	609.7	630.7	668.2	709.8	757.7	824.9	928.9	1024.6	1138.8
45°	518.6	533.7	554.8	578.1	608.9	644.4	686.7	745.5	845.3	927.9	1035.3
47.5°	463.4	485.4	499.3	521.9	551.2	585.1	624.5	675.3	756.0	833.5	933.0
50°	425.7	448.3	468.1	488.6	514.5	547.3	580.1	629.4	694.3	775.6	868.5
52.5°	393.4	413.3	432.6	453.1	478.5	508.5	539.7	582.9	638.5	713.3	803.4
55°	349.2	361.5	381.3	401.8	424.4	453.1	483.1	519.3	567.1	630.0	703.1
57.5°	303.8	318.0	333.8	354.4	377.2	399.2	426.2	459.1	496.8	553.7	616.3
60°	278.1	289.0	302.0	323.2	344.4	364.2	390.2	417.5	453.1	502.2	555.5
62.5°	249.7	260.1	272.0	290.4	311.0	329.2	351.9	380.8	411.0	455.8	502.5
65°	202.2	217.3	228.9	245.3	262.4	281.5	299.3	322.5	349.2	384.7	426.4
67.5°	167.7	175.3	186.1	201.0	218.6	235.0	251.7	269.9	293.0	320.5	353.6
70°	152.4	155.2	157.2	171.5	187.9	204.3	220.1	237.1	256.9	279.5	308.2
72.5°	134.4	137.1	139.6	145.8	158.9	175.3	191.6	204.3	223.0	241.7	265.0
75°	106.6	110.7	112.7	116.2	120.9	131.9	147.0	159.2	170.1	184.5	203.0
77.5°	81.1	83.5	85.7	89.3	92.3	97.3	105.8	116.8	127.1	135.5	148.1
80°	64.2	64.9	67.7	69.0	73.1	76.5	80.6	89.5	99.8	103.2	112.1
82.5°	48.4	49.0	51.3	52.6	54.6	57.4	62.6	64.9	72.9	77.5	83.1
85°	26.7	25.9	28.0	28.0	29.4	30.8	32.1	35.5	37.5	43.1	44.4
87.5°	10.9	10.7	11.1	10.8	10.6	11.4	11.8	11.9	12.8	14.1	16.0
90°	13.2	12.5	11.4	10.3	9.2	8.0	6.7	5.2	3.7	2.1	0.6
92.5°	14.8	14.4	13.9	13.4	12.8	12.3	12.0	12.2	12.3	12.5	12.6
95°	25.1	24.3	23.4	22.4	21.4	20.4	22.3	26.8	31.4	36.0	40.6
97.5°	33.2	32.5	30.3	28.1	25.9	23.6	28.9	41.8	54.8	67.6	80.5
100°	36.6	35.6	33.3	30.9	28.5	26.1	34.5	53.5	72.5	91.5	110.5
102.5°	38.0	36.6	56.3	76.1	95.8	115.5	127.3	131.3	135.4	139.5	143.5
105°	39.6	38.1	76.0	113.8	151.7	189.6	206.4	202.2	198.1	193.9	189.8
107.5°	51.7	53.3	98.7	144.2	189.6	235.0	256.0	252.6	249.3	245.9	242.5
110°	95.4	109.2	149.4	189.4	229.5	269.6	288.2	285.3	282.4	279.5	276.5



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	225.0	275.5	285.4	295.3	305.2	315.1	318.8	316.2	313.7	311.1	308.5
115°	320.9	385.1	381.7	378.3	374.8	371.3	368.4	366.0	363.6	361.3	358.9
117.5°	411.1	426.6	424.2	421.9	419.5	417.1	414.6	411.9	409.3	406.6	404.0
120°	459.2	457.5	455.0	452.5	450.0	447.5	445.3	443.2	441.1	439.1	436.9
122.5°	488.0	487.1	484.3	481.6	478.8	476.2	473.7	471.5	469.3	467.2	464.9
125°	528.4	527.4	524.9	522.2	519.6	516.9	514.7	512.9	511.1	509.3	507.5
127.5°	565.3	563.9	562.0	560.0	558.0	556.1	554.1	552.1	550.1	548.0	546.1
130°	589.0	587.5	585.9	584.3	582.8	581.3	579.4	577.2	575.0	572.7	570.5
132.5°	612.2	610.9	609.4	607.8	606.3	604.8	603.1	601.2	599.3	597.4	595.6
135°	645.0	643.6	642.4	641.1	639.9	638.6	636.9	634.6	632.4	630.2	628.0
137.5°	675.6	674.2	672.8	671.4	669.9	668.5	667.0	665.5	664.0	662.4	660.8
140°	695.4	694.2	692.6	691.1	689.6	688.0	686.7	685.6	684.5	683.4	682.3
142.5°	713.8	712.7	710.9	709.2	707.4	705.6	704.3	703.3	702.3	701.2	700.3
145°	739.5	738.5	736.1	733.8	731.4	729.1	727.9	728.1	728.3	728.3	728.5
147.5°	762.0	761.2	758.8	756.5	754.2	751.9	751.0	751.5	752.1	752.6	753.0
150°	775.5	774.7	772.5	770.3	768.0	765.8	765.2	766.2	767.1	768.1	769.1
152.5°	788.0	787.2	785.1	782.9	780.9	778.7	778.2	779.3	780.4	781.5	782.6
155°	804.9	804.1	802.4	800.7	799.1	797.4	797.2	798.4	799.7	800.9	802.2
157.5°	818.9	818.0	816.8	815.6	814.5	813.3	813.3	814.3	815.4	816.5	817.5
160°	827.3	826.5	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5
162.5°	834.9	834.0	833.3	832.6	831.8	831.1	831.2	832.0	832.9	833.7	834.5
165°	844.4	843.4	842.9	842.5	842.1	841.7	841.9	842.8	843.6	844.4	845.3
167.5°	852.2	851.2	850.9	850.4	850.1	849.7	849.9	850.7	851.6	852.4	853.2
170°	856.2	855.2	855.0	854.7	854.3	854.1	854.3	855.2	856.0	856.8	857.7
172.5°	859.2	858.2	857.9	857.6	857.4	857.1	857.4	858.2	859.1	859.9	860.7
175°	862.5	861.5	861.2	860.9	860.6	860.3	860.7	861.7	862.6	863.6	864.6
177.5°	863.0	862.2	862.1	862.0	861.8	861.7	862.1	862.9	863.6	864.4	865.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	1978.1	1979.7	1990.7	1995.6	2005.5	2009.2	2013.7	2012.5	2012.5	2014.7	2030.0
5°	1982.4	1996.0	2016.5	2036.3	2055.5	2071.8	2082.8	2093.7	2097.8	2117.6	2135.4
7.5°	1975.2	2000.4	2034.3	2064.5	2100.7	2129.0	2152.5	2173.6	2188.2	2217.0	2246.5
10°	1966.0	2001.4	2039.7	2078.7	2128.5	2166.1	2204.4	2233.8	2243.4	2286.4	2311.0
12.5°	1947.3	1994.9	2043.5	2094.0	2142.8	2194.6	2236.7	2266.0	2299.6	2338.3	2383.7
15°	1919.5	1974.2	2037.6	2102.6	2172.3	2235.2	2280.3	2331.5	2368.4	2410.7	2450.4
17.5°	1879.5	1949.8	2030.6	2105.8	2186.4	2253.9	2316.0	2365.1	2391.1	2415.3	2421.2
20°	1847.7	1923.6	2018.6	2107.4	2188.0	2265.9	2327.4	2368.4	2375.3	2375.9	2339.7
22.5°	1813.3	1899.0	1998.3	2089.4	2185.9	2272.4	2320.3	2337.8	2310.7	2264.4	2194.3
25°	1750.0	1849.1	1964.5	2068.4	2173.6	2255.7	2272.1	2241.3	2146.3	2046.6	1920.1
27.5°	1681.4	1792.8	1916.6	2032.0	2144.1	2194.9	2159.5	2048.7	1877.7	1728.9	1548.7
30°	1631.1	1756.1	1877.8	2006.9	2110.8	2132.6	2051.4	1888.0	1688.5	1464.4	1284.7
32.5°	1573.7	1704.8	1838.4	1971.9	2058.9	2037.6	1903.2	1702.2	1468.2	1247.9	1078.0
35°	1491.7	1627.0	1771.2	1905.1	1960.4	1868.2	1667.3	1405.6	1166.4	960.7	843.9
37.5°	1397.0	1544.4	1694.3	1817.2	1813.3	1659.6	1385.9	1115.7	914.7	793.1	709.8
40°	1329.7	1478.7	1640.7	1744.5	1700.1	1499.9	1203.4	948.4	801.6	704.5	643.7
42.5°	1265.2	1414.8	1575.7	1658.1	1580.9	1334.8	1039.4	839.6	718.5	642.7	593.4
45°	1155.5	1313.3	1462.3	1508.1	1370.0	1098.8	840.5	695.6	615.0	558.9	524.8
47.5°	1048.2	1203.5	1339.4	1340.2	1153.6	891.1	709.0	602.0	533.2	489.8	464.9
50°	982.6	1130.2	1244.3	1226.5	1014.8	792.6	634.1	541.9	484.5	451.0	425.0
52.5°	908.8	1052.0	1150.8	1100.3	897.2	697.5	566.9	489.4	441.8	412.7	389.5
55°	801.6	928.6	998.4	921.8	731.8	580.1	479.0	418.2	382.6	358.0	338.2
57.5°	696.2	801.0	844.9	755.7	602.8	481.1	405.2	359.5	324.3	306.7	296.4
60°	630.0	719.5	750.3	651.9	524.1	420.9	358.7	316.4	290.4	278.8	268.6
62.5°	565.0	638.1	650.8	560.6	456.9	368.5	315.0	279.2	262.0	250.9	241.2
65°	468.8	521.4	515.2	442.8	361.5	292.5	253.5	231.7	218.6	203.0	185.8
67.5°	385.9	418.0	398.7	344.4	275.9	227.3	201.9	185.3	169.2	154.3	150.3
70°	333.5	351.9	331.4	281.5	226.1	190.6	170.1	150.3	140.8	137.3	131.2
72.5°	283.2	289.6	267.4	224.7	184.0	157.8	137.9	126.8	121.6	118.8	114.8
75°	212.5	207.8	188.6	155.2	127.8	110.0	103.9	99.8	96.3	93.6	91.6
77.5°	149.3	142.2	125.2	103.3	89.0	80.5	76.8	74.6	72.9	71.6	69.6
80°	112.1	107.3	90.2	73.8	67.7	63.6	61.5	58.8	58.8	57.4	55.4
82.5°	82.0	76.7	61.8	54.1	50.7	48.2	46.7	45.1	44.6	44.9	43.3
85°	43.1	34.9	30.8	29.4	27.4	25.9	26.7	25.3	25.3	25.3	24.6
87.5°	13.6	11.1	10.9	10.6	11.4	11.7	11.3	11.6	12.3	11.9	12.6
90°	2.1	3.7	5.2	6.7	8.0	9.2	10.3	11.4	12.5	13.2	13.9
92.5°	12.5	12.3	12.2	12.0	12.3	12.8	13.4	13.9	14.4	14.8	15.2
95°	36.0	31.4	26.8	22.3	20.4	21.4	22.4	23.4	24.3	25.1	25.8
97.5°	67.6	54.8	41.8	28.9	23.6	25.9	28.1	30.3	32.5	33.2	33.7
100°	91.5	72.5	53.5	34.5	26.1	28.5	30.9	33.3	35.6	36.6	37.8
102.5°	139.5	135.4	131.3	127.3	115.5	95.8	76.1	56.3	36.6	38.0	39.5
105°	193.9	198.1	202.2	206.4	189.6	151.7	113.8	76.0	38.1	39.6	41.1
107.5°	245.9	249.3	252.6	256.0	235.0	189.6	144.2	98.7	53.3	51.7	50.2
110°	279.5	282.4	285.3	288.2	269.6	229.5	189.4	149.4	109.2	95.4	81.5



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	311.1	313.7	316.2	318.8	315.1	305.2	295.3	285.4	275.5	225.0	174.3
115°	361.3	363.6	366.0	368.4	371.3	374.8	378.3	381.7	385.1	320.9	256.7
117.5°	406.6	409.3	411.9	414.6	417.1	419.5	421.9	424.2	426.6	411.1	395.6
120°	439.1	441.1	443.2	445.3	447.5	450.0	452.5	455.0	457.5	459.2	460.9
122.5°	467.2	469.3	471.5	473.7	476.2	478.8	481.6	484.3	487.1	488.0	489.0
125°	509.3	511.1	512.9	514.7	516.9	519.6	522.2	524.9	527.4	528.4	529.4
127.5°	548.0	550.1	552.1	554.1	556.1	558.0	560.0	562.0	563.9	565.3	566.8
130°	572.7	575.0	577.2	579.4	581.3	582.8	584.3	585.9	587.5	589.0	590.5
132.5°	597.4	599.3	601.2	603.1	604.8	606.3	607.8	609.4	610.9	612.2	613.5
135°	630.2	632.4	634.6	636.9	638.6	639.9	641.1	642.4	643.6	645.0	646.4
137.5°	662.4	664.0	665.5	667.0	668.5	669.9	671.4	672.8	674.2	675.6	676.9
140°	683.4	684.5	685.6	686.7	688.0	689.6	691.1	692.6	694.2	695.4	696.7
142.5°	701.2	702.3	703.3	704.3	705.6	707.4	709.2	710.9	712.7	713.8	714.9
145°	728.3	728.3	728.1	727.9	729.1	731.4	733.8	736.1	738.5	739.5	740.4
147.5°	752.6	752.1	751.5	751.0	751.9	754.2	756.5	758.8	761.2	762.0	762.7
150°	768.1	767.1	766.2	765.2	765.8	768.0	770.3	772.5	774.7	775.5	776.3
152.5°	781.5	780.4	779.3	778.2	778.7	780.9	782.9	785.1	787.2	788.0	788.8
155°	800.9	799.7	798.4	797.2	797.4	799.1	800.7	802.4	804.1	804.9	805.7
157.5°	816.5	815.4	814.3	813.3	813.3	814.5	815.6	816.8	818.0	818.9	819.9
160°	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	827.3	828.1
162.5°	833.7	832.9	832.0	831.2	831.1	831.8	832.6	833.3	834.0	834.9	835.9
165°	844.4	843.6	842.8	841.9	841.7	842.1	842.5	842.9	843.4	844.4	845.3
167.5°	852.4	851.6	850.7	849.9	849.7	850.1	850.4	850.9	851.2	852.2	853.2
170°	856.8	856.0	855.2	854.3	854.1	854.3	854.7	855.0	855.2	856.2	857.2
172.5°	859.9	859.1	858.2	857.4	857.1	857.4	857.6	857.9	858.2	859.2	860.1
175°	863.6	862.6	861.7	860.7	860.3	860.6	860.9	861.2	861.5	862.5	863.4
177.5°	864.4	863.6	862.9	862.1	861.7	861.8	862.0	862.1	862.2	863.0	863.8
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6	1966.6
2.5°	2035.5	2042.6	2045.9	2045.9	2049.7	2048.1	2046.4
5°	2152.5	2165.4	2168.2	2180.5	2189.3	2186.7	2188.0
7.5°	2268.8	2289.6	2310.3	2319.8	2321.2	2326.7	2328.8
10°	2340.4	2357.5	2389.6	2384.8	2408.7	2422.4	2399.9
12.5°	2409.2	2432.3	2454.6	2460.8	2474.3	2478.7	2469.8
15°	2471.6	2483.9	2485.3	2481.8	2485.9	2482.5	2469.5
17.5°	2413.3	2393.4	2353.0	2333.8	2318.6	2296.2	2287.2
20°	2317.1	2258.3	2190.0	2162.8	2130.6	2067.7	2082.8
22.5°	2109.4	2042.5	1974.2	1894.4	1856.2	1796.6	1793.1
25°	1786.2	1670.7	1543.6	1454.8	1402.8	1343.5	1317.4
27.5°	1388.8	1243.4	1139.2	1086.5	1038.5	991.4	989.4
30°	1127.5	1018.2	937.5	892.4	863.0	843.2	847.3
32.5°	950.4	875.5	821.1	783.6	761.9	747.0	746.7
35°	776.9	725.7	690.8	675.1	659.4	648.5	649.2
37.5°	664.9	634.1	614.7	597.4	587.5	582.2	579.2
40°	607.4	582.2	567.1	556.9	548.7	541.2	539.8
42.5°	562.1	541.2	526.2	518.1	510.4	505.2	503.7
45°	498.8	481.7	468.1	459.2	455.8	451.0	451.0
47.5°	443.7	427.0	416.3	410.7	404.8	401.6	401.5
50°	406.6	393.6	384.1	380.6	375.9	373.8	373.1
52.5°	373.3	363.6	356.7	354.4	352.3	349.7	350.2
55°	328.0	322.5	319.8	317.7	314.3	310.2	313.0
57.5°	289.9	285.3	277.9	271.4	268.3	265.4	266.5
60°	263.1	253.5	244.0	236.4	234.3	228.2	228.2
62.5°	229.2	215.8	204.0	199.8	197.8	194.9	194.3
65°	176.3	170.9	168.1	165.3	164.0	164.0	162.6
67.5°	146.1	143.9	140.9	140.2	138.8	138.5	138.0
70°	129.1	126.4	125.0	124.4	123.0	123.7	121.6
72.5°	112.7	110.6	110.3	108.5	107.7	107.8	106.3
75°	88.8	88.8	88.2	87.5	86.1	85.4	86.1
77.5°	68.3	68.5	67.2	67.1	67.0	67.1	66.4
80°	54.7	55.4	54.7	53.9	53.3	53.9	53.3
82.5°	43.2	42.3	42.1	42.0	41.8	41.4	41.3
85°	24.6	25.3	24.6	23.9	23.9	23.9	24.6
87.5°	12.2	12.3	12.5	12.5	12.6	12.6	12.1
90°	14.5	15.2	15.8	16.1	16.3	16.6	16.9
92.5°	15.6	16.0	16.2	16.3	16.5	16.7	16.9
95°	26.4	27.1	27.4	27.3	27.1	27.0	26.8
97.5°	34.2	34.8	35.1	35.3	35.5	35.7	35.8
100°	38.9	40.0	40.8	41.0	41.3	41.6	41.8
102.5°	40.9	42.4	43.2	43.7	44.1	44.4	44.9
105°	42.6	44.1	45.2	45.7	46.4	46.9	47.4
107.5°	48.7	47.1	46.6	47.2	47.7	48.2	48.8
110°	67.6	53.8	47.1	47.6	48.2	48.8	49.3



TEST NUMBER: P331849-940

CATALOG NUMBER: S122RDIW-S1005D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	123.8	73.1	48.1	48.5	49.0	49.4	49.8
115°	192.4	128.2	91.1	81.1	71.2	61.2	51.2
117.5°	380.0	364.4	340.3	307.5	274.6	241.8	209.0
120°	462.5	464.2	455.7	436.9	418.2	399.5	380.8
122.5°	490.0	491.1	489.7	486.1	482.4	478.8	475.2
125°	530.4	531.4	532.1	532.4	532.9	533.3	533.7
127.5°	568.2	569.6	570.3	570.4	570.5	570.6	570.7
130°	592.0	593.5	594.2	594.1	594.0	593.8	593.7
132.5°	614.8	616.1	616.7	616.5	616.4	616.3	616.2
135°	647.7	649.2	649.7	649.4	649.2	648.9	648.6
137.5°	678.2	679.7	680.1	679.6	679.1	678.7	678.1
140°	697.9	699.2	699.5	698.7	698.0	697.3	696.7
142.5°	716.0	717.2	717.4	716.8	716.0	715.3	714.6
145°	741.4	742.3	742.5	741.8	741.1	740.4	739.8
147.5°	763.4	764.1	764.2	763.6	763.0	762.4	761.8
150°	777.2	778.0	778.1	777.4	776.7	776.0	775.3
152.5°	789.7	790.5	790.5	789.5	788.6	787.7	786.8
155°	806.6	807.4	807.2	806.1	805.0	803.9	802.8
157.5°	820.8	821.8	821.7	820.6	819.6	818.5	817.3
160°	829.0	829.8	829.7	828.8	827.8	826.9	825.9
162.5°	836.8	837.8	837.7	836.4	835.3	834.0	832.9
165°	846.2	847.2	847.2	846.2	845.3	844.4	843.4
167.5°	854.2	855.1	855.0	853.7	852.5	851.2	850.0
170°	858.1	859.1	859.0	857.7	856.5	855.2	854.0
172.5°	861.1	862.1	861.9	860.7	859.4	858.2	856.9
175°	864.3	865.3	865.1	863.7	862.4	860.9	859.6
177.5°	864.5	865.3	865.2	864.2	863.2	862.2	861.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7

(END OF REPORT)