

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331520-935

Luminaire Tested: **S122DIW-S485D1440U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331520-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S485D1440U935-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6152.9 lumens  
Efficiency: N/A  
Efficacy: 101.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - · - 135°-315°



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	89	86	83	84	80	77	75	64	62	60	48	47	46	34	33	32	26
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28	22
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	12
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13	11
9	48	36	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	10
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13508	13508	13508	13508
5°	15144	13598	12049	13598
10°	17354	13485	10427	13485
15°	19199	13237	9212	13237
20°	18907	12972	8399	12972
25°	17047	12618	7883	12618
30°	14087	12055	7506	12055
35°	10267	11466	7238	11466
40°	8201	10768	7088	10768
45°	7165	9965	6887	9965
50°	6737	9183	6752	9183
55°	6210	8391	6570	8391
60°	5690	7550	6290	7550
65°	5184	6793	6021	6793
70°	4707	6057	5618	6057
75°	4173	5234	4972	5234
80°	3589	4342	3998	4342
85°	3223	3223	2371	3223



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.7	1.3
10°-20°	231.6	3.8
20°-30°	336.2	5.5
30°-40°	354.8	5.8
40°-50°	314.1	5.1
50°-60°	250.7	4.1
60°-70°	170.4	2.8
70°-80°	87.4	1.4
80°-90°	27.2	0.4
90°-100°	97.5	1.6
100°-110°	302.7	4.9
110°-120°	517.4	8.4
120°-130°	680.4	11.1
130°-140°	763.7	12.4
140°-150°	748.8	12.2
150°-160°	628.1	10.2
160°-170°	416.6	6.8
170°-180°	145.6	2.4
0°-30°	647.5	10.5
0°-40°	1002.3	16.3
0°-60°	1567.1	25.5
0°-90°	1852.0	30.1
90°-120°	917.6	14.9
90°-150°	3110.6	50.6
90°-180°	4301.0	69.9
0°-180°	6152.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	837	837	837	837	837	
5°	934	839	743	839	934	93
15°	1149	792	551	792	1149	317
25°	957	708	442	708	957	432
35°	521	582	367	582	521	339
45°	314	436	302	436	314	247
55°	221	298	233	298	221	198
65°	136	178	158	178	136	135
75°	67	84	80	84	67	71
85°	17	17	13	17	17	20
90°	44	1	44	1	44	20
95°	80	68	80	68	80	90
105°	288	279	288	279	288	303
115°	519	519	519	519	519	513
125°	758	755	758	755	758	676
135°	989	977	989	977	989	761
145°	1199	1186	1199	1186	1199	749
155°	1367	1356	1367	1356	1367	629
165°	1477	1476	1477	1476	1477	417
175°	1530	1536	1530	1536	1530	145
180°	1538	1538	1538	1538	1538	



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	875.3	875.6	876.0	871.9	871.4	871.4	867.8	864.7	861.1	856.2	856.7
5°	934.4	938.0	939.3	935.4	929.6	928.9	923.5	914.5	906.1	899.4	894.6
7.5°	1005.0	1006.4	1003.3	998.2	993.9	986.2	976.0	966.0	952.1	939.3	929.8
10°	1058.5	1060.5	1055.0	1047.6	1041.5	1032.5	1017.7	1002.5	984.3	966.6	952.4
12.5°	1099.2	1104.0	1096.9	1096.0	1085.5	1073.2	1055.5	1047.8	1022.1	997.5	982.2
15°	1148.6	1148.2	1148.9	1142.8	1135.1	1133.2	1114.5	1094.2	1057.9	1043.4	1018.3
17.5°	1134.3	1139.2	1141.4	1141.3	1141.2	1140.0	1133.9	1121.2	1102.9	1079.5	1050.6
20°	1100.4	1106.7	1107.8	1115.2	1119.3	1124.8	1127.0	1123.5	1112.2	1092.6	1067.6
22.5°	1047.8	1049.6	1052.7	1064.2	1073.2	1086.9	1094.1	1106.0	1101.6	1092.1	1071.2
25°	956.9	953.7	964.9	970.8	991.6	1013.5	1029.2	1046.6	1062.0	1071.4	1065.3
27.5°	847.7	842.9	859.8	875.1	892.1	915.8	940.3	969.3	993.4	1023.6	1034.0
30°	755.6	758.5	774.6	791.0	816.7	850.2	877.8	909.6	944.1	977.8	1001.3
32.5°	656.3	667.4	677.6	702.7	725.4	762.7	803.2	843.0	886.0	924.3	960.6
35°	520.9	533.7	547.9	566.3	598.1	635.1	674.6	728.3	786.9	839.2	882.4
37.5°	438.4	436.4	444.5	457.8	483.5	513.4	558.9	612.0	680.9	742.4	803.2
40°	389.1	387.8	393.6	405.8	425.4	447.3	487.2	533.7	597.8	673.0	745.4
42.5°	355.1	355.9	359.1	367.7	381.2	399.2	429.0	468.7	527.3	598.1	675.9
45°	313.8	316.1	319.6	323.8	331.5	346.3	363.0	391.3	437.6	496.8	573.3
47.5°	284.1	284.2	287.7	291.4	296.0	304.4	318.1	335.8	368.4	416.6	482.4
50°	268.2	265.9	268.5	271.4	276.2	282.0	291.0	307.7	329.6	368.5	423.4
52.5°	248.7	248.7	251.0	252.1	256.4	262.2	270.4	282.0	301.8	332.3	377.5
55°	220.6	222.2	223.5	225.4	229.3	233.4	239.9	247.6	263.0	285.9	319.3
57.5°	194.2	194.8	196.0	199.7	202.2	206.0	212.1	219.1	229.1	246.1	271.2
60°	176.2	176.2	178.7	180.4	183.6	187.4	192.3	199.1	208.0	221.9	242.1
62.5°	159.7	159.5	160.5	163.2	165.6	169.2	174.0	179.8	188.2	200.5	217.1
65°	135.7	135.1	137.0	137.6	140.2	143.7	147.6	153.7	160.5	169.4	184.3
67.5°	112.5	113.3	114.3	115.5	117.0	120.7	123.3	127.6	133.3	140.8	150.8
70°	99.7	99.7	99.7	100.7	102.5	104.5	107.1	110.6	116.1	122.5	131.5
72.5°	85.2	86.3	87.3	86.8	89.2	90.3	93.4	95.4	100.7	104.8	112.7
75°	66.9	66.9	66.9	68.4	69.5	70.4	72.3	74.3	76.9	82.0	86.2
77.5°	49.9	49.8	50.1	50.5	51.5	52.7	53.2	55.0	57.3	59.8	63.3
80°	38.6	39.3	39.5	40.2	40.2	40.8	41.2	43.4	45.0	46.7	48.9
82.5°	29.9	30.0	30.0	30.1	30.4	30.8	31.6	32.4	32.9	34.3	36.0
85°	17.4	17.0	17.0	17.7	17.4	17.4	18.0	18.7	18.7	18.9	20.0
87.5°	15.5	15.5	15.7	15.3	15.3	15.6	15.7	15.6	15.9	16.3	15.2
90°	44.2	43.8	43.6	43.3	43.0	43.1	43.7	44.3	44.9	45.5	39.1
92.5°	42.0	42.0	41.9	41.8	41.8	41.8	41.6	41.5	41.4	41.2	39.8
95°	80.5	81.0	81.6	82.2	82.7	83.1	83.1	83.1	83.1	83.1	82.5
97.5°	139.4	139.5	139.5	139.6	139.7	139.7	139.7	139.7	139.7	139.7	138.5
100°	177.8	178.1	178.4	178.7	179.0	179.1	179.1	179.1	179.1	179.1	178.2
102.5°	221.4	221.7	222.1	222.3	222.6	222.7	222.4	222.1	222.0	221.7	220.6
105°	288.2	288.2	288.2	288.2	288.2	287.8	287.3	286.7	286.1	285.6	285.0
107.5°	350.9	352.3	353.6	355.0	356.3	356.8	356.6	356.4	356.1	355.9	355.9
110°	399.8	400.6	401.5	402.3	403.2	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.5	447.1	447.8	448.4	449.0	449.7	450.4	451.1	451.8	452.5	452.7
115°	519.2	520.0	520.9	521.8	522.6	523.2	523.5	523.8	524.1	524.4	525.0
117.5°	588.5	589.4	590.2	591.1	591.9	592.8	593.5	594.2	594.9	595.6	597.1
120°	637.3	638.2	639.0	639.9	640.8	641.2	641.2	641.2	641.2	641.2	643.5
122.5°	685.1	685.7	686.4	687.0	687.6	688.3	689.0	689.7	690.3	691.0	692.7
125°	758.0	758.4	758.6	758.9	759.2	759.7	760.6	761.5	762.3	763.2	764.1
127.5°	824.5	825.4	826.3	827.2	828.2	829.1	830.2	831.2	832.2	833.4	834.4
130°	872.3	873.4	874.6	875.7	876.8	877.7	878.3	878.9	879.5	880.0	880.6
132.5°	917.9	918.9	919.8	920.8	921.6	922.7	924.0	925.3	926.5	927.8	927.7
135°	989.1	990.0	990.8	991.7	992.6	993.2	993.4	993.7	994.0	994.3	993.7
137.5°	1053.4	1054.6	1055.8	1057.0	1058.1	1058.8	1059.0	1059.2	1059.5	1059.7	1058.9
140°	1098.1	1099.2	1100.4	1101.6	1102.8	1103.3	1103.3	1103.3	1103.3	1103.3	1101.9
142.5°	1138.6	1139.8	1140.9	1142.1	1143.2	1143.7	1143.5	1143.2	1143.0	1142.8	1141.8
145°	1199.4	1200.5	1201.7	1202.8	1203.9	1204.4	1204.1	1203.9	1203.5	1203.2	1201.5
147.5°	1253.6	1254.7	1255.8	1256.9	1258.0	1258.3	1257.6	1257.0	1256.4	1255.7	1254.6
150°	1288.9	1289.8	1290.6	1291.5	1292.4	1292.4	1291.5	1290.6	1289.8	1288.9	1287.8
152.5°	1322.2	1323.3	1324.3	1325.4	1326.5	1326.5	1325.4	1324.3	1323.3	1322.2	1320.8
155°	1366.8	1367.7	1368.6	1369.4	1370.3	1369.9	1368.6	1367.1	1365.6	1364.2	1363.3
157.5°	1405.2	1406.6	1408.0	1409.4	1410.7	1410.5	1408.5	1406.5	1404.5	1402.7	1402.1
160°	1429.1	1430.3	1431.4	1432.5	1433.7	1433.4	1431.7	1429.9	1428.2	1426.5	1426.2
162.5°	1449.8	1451.3	1452.7	1454.1	1455.4	1455.1	1453.2	1451.2	1449.2	1447.3	1447.0
165°	1477.1	1478.6	1480.1	1481.4	1482.9	1482.6	1480.6	1478.6	1476.5	1474.5	1474.5
167.5°	1499.4	1501.0	1502.4	1504.0	1505.5	1505.2	1503.2	1501.2	1499.2	1497.1	1497.2
170°	1510.9	1512.6	1514.3	1516.0	1517.8	1517.7	1515.6	1513.6	1511.6	1509.6	1509.8
172.5°	1520.3	1522.0	1523.7	1525.4	1527.2	1527.0	1525.0	1522.9	1521.0	1518.9	1519.2
175°	1530.3	1532.1	1533.8	1535.5	1537.3	1537.1	1535.1	1533.1	1531.1	1529.0	1529.7
177.5°	1535.0	1536.4	1537.8	1539.2	1540.6	1540.6	1539.2	1537.8	1536.4	1535.0	1535.5
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	858.5	856.4	855.1	850.6	846.4	842.3	841.0	841.5	835.9	830.5	828.2
5°	892.0	885.5	879.4	870.7	860.5	849.2	843.4	839.0	827.7	815.5	808.4
7.5°	922.0	912.7	901.0	884.7	869.7	852.0	840.7	830.8	814.2	797.0	786.5
10°	940.2	927.6	912.6	892.6	874.3	852.7	837.7	822.5	803.2	782.6	769.8
12.5°	955.9	939.0	924.1	898.5	876.8	849.9	832.0	810.7	790.4	765.9	753.3
15°	993.2	962.1	933.8	904.8	878.1	840.5	820.6	791.9	765.3	735.0	720.6
17.5°	1022.1	987.1	942.5	905.8	874.6	832.9	803.7	769.4	737.8	703.3	683.6
20°	1038.6	998.4	950.5	906.8	869.4	821.9	790.1	755.0	718.0	679.1	657.9
22.5°	1048.4	1006.2	958.7	902.9	859.2	812.9	772.8	734.4	696.9	655.0	632.7
25°	1051.5	1012.9	962.7	899.7	846.3	793.9	745.6	708.3	663.1	623.8	591.3
27.5°	1036.1	1008.5	960.3	893.6	831.5	770.2	716.4	674.2	626.3	583.8	551.0
30°	1017.4	1001.3	954.3	887.4	819.6	753.7	694.6	646.6	599.1	555.9	522.5
32.5°	988.3	984.8	943.6	878.7	807.0	732.9	671.7	623.2	570.5	528.1	496.3
35°	931.2	946.7	920.6	859.2	783.3	703.3	637.0	581.7	527.0	486.5	456.6
37.5°	854.7	893.0	886.2	830.5	751.2	671.0	597.8	540.0	487.9	447.0	417.7
40°	801.9	850.8	857.9	808.7	728.7	646.0	568.5	510.9	460.1	422.8	393.2
42.5°	745.4	802.5	821.9	782.5	704.0	619.7	542.3	482.7	432.4	396.1	369.9
45°	650.5	726.1	761.1	738.6	662.7	576.5	496.8	436.4	390.7	356.6	336.3
47.5°	561.8	644.4	691.6	683.5	616.8	531.5	452.7	394.7	350.3	323.0	304.9
50°	499.0	583.9	640.8	643.4	583.9	499.4	420.3	365.6	324.8	299.4	284.6
52.5°	444.5	525.6	587.6	601.2	547.2	465.9	391.2	336.8	300.8	277.5	264.2
55°	373.3	441.8	510.7	535.7	492.3	415.1	345.9	298.1	264.3	248.2	236.7
57.5°	310.4	367.5	431.0	458.7	432.0	365.9	301.1	259.5	232.1	218.0	209.1
60°	277.2	322.2	378.8	411.9	388.7	329.9	273.3	233.8	211.3	198.7	190.4
62.5°	246.3	286.2	334.0	364.3	351.7	296.2	245.6	210.6	191.2	179.4	173.4
65°	203.2	234.7	271.7	299.7	291.4	249.2	207.8	177.8	162.4	153.1	148.3
67.5°	167.3	190.1	215.8	240.2	233.5	203.6	170.4	147.1	135.5	127.5	124.7
70°	144.7	162.0	184.9	204.5	199.1	174.6	148.3	128.3	118.3	111.6	108.7
72.5°	123.1	137.3	154.8	170.8	167.1	146.8	124.8	109.8	102.1	95.9	93.5
75°	92.9	103.8	114.5	125.1	124.2	108.4	95.5	83.9	77.8	73.0	72.1
77.5°	68.6	74.7	82.0	88.3	86.5	77.5	67.4	60.8	56.3	53.0	52.5
80°	52.4	56.0	61.1	65.6	63.4	59.5	51.5	46.7	43.4	40.2	38.9
82.5°	38.0	41.6	44.6	47.1	45.4	41.8	36.8	33.5	31.6	29.4	28.8
85°	20.0	21.9	23.2	23.8	23.2	20.9	18.7	17.4	15.8	14.8	14.5
87.5°	14.3	13.0	11.7	11.3	9.8	9.1	7.4	5.9	6.4	6.8	7.0
90°	32.7	26.4	20.1	15.2	11.7	8.2	4.7	1.3	4.7	8.2	11.7
92.5°	38.3	36.8	35.3	33.2	30.7	28.2	25.7	23.1	25.7	28.2	30.7
95°	81.9	81.4	80.8	79.0	76.1	73.3	70.3	67.5	70.3	73.3	76.1
97.5°	137.5	136.4	135.3	133.5	131.0	128.4	125.9	123.3	125.9	128.4	131.0
100°	177.4	176.5	175.6	174.1	171.8	169.4	167.1	164.9	167.1	169.4	171.8
102.5°	219.5	218.4	217.3	215.9	214.0	212.2	210.3	208.4	210.3	212.2	214.0
105°	284.4	283.9	283.3	282.5	281.6	280.8	279.9	279.1	279.9	280.8	281.6
107.5°	355.9	355.9	355.9	355.2	354.0	352.8	351.5	350.2	351.5	352.8	354.0
110°	403.7	403.7	403.7	402.8	401.1	399.3	397.6	395.9	397.6	399.3	401.1





TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	453.0	453.1	453.4	452.6	450.9	449.2	447.5	445.7	447.5	449.2	450.9
115°	525.6	526.2	526.7	526.2	524.4	522.6	520.9	519.2	520.9	522.6	524.4
117.5°	598.7	600.4	602.0	601.7	599.3	597.0	594.7	592.5	594.7	597.0	599.3
120°	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2	643.5	645.8	648.2
122.5°	694.3	695.9	697.5	697.0	694.1	691.4	688.6	685.9	688.6	691.4	694.1
125°	765.0	765.9	766.7	765.9	763.2	760.6	758.0	755.4	758.0	760.6	763.2
127.5°	835.4	836.5	837.5	836.4	833.1	829.7	826.5	823.2	826.5	829.7	833.1
130°	881.2	881.8	882.4	880.8	877.0	873.3	869.5	865.7	869.5	873.3	877.0
132.5°	927.6	927.5	927.4	925.7	922.7	919.6	916.6	913.5	916.6	919.6	922.7
135°	993.2	992.6	992.0	990.1	986.9	983.8	980.6	977.4	980.6	983.8	986.9
137.5°	1058.2	1057.5	1056.7	1055.0	1052.4	1049.8	1047.2	1044.7	1047.2	1049.8	1052.4
140°	1100.4	1099.0	1097.5	1095.5	1093.0	1090.4	1087.7	1085.1	1087.7	1090.4	1093.0
142.5°	1140.8	1139.8	1138.8	1137.0	1134.5	1131.9	1129.3	1126.7	1129.3	1131.9	1134.5
145°	1199.8	1198.1	1196.4	1194.5	1192.4	1190.4	1188.4	1186.4	1188.4	1190.4	1192.4
147.5°	1253.4	1252.2	1251.1	1249.3	1246.9	1244.4	1242.0	1239.6	1242.0	1244.4	1246.9
150°	1286.6	1285.5	1284.3	1282.9	1281.2	1279.4	1277.6	1275.9	1277.6	1279.4	1281.2
152.5°	1319.4	1318.0	1316.6	1315.1	1313.3	1311.6	1309.8	1308.1	1309.8	1311.6	1313.3
155°	1362.4	1361.6	1360.7	1359.9	1359.0	1358.1	1357.3	1356.4	1357.3	1358.1	1359.0
157.5°	1401.6	1401.1	1400.6	1400.0	1399.5	1398.9	1398.3	1397.7	1398.3	1398.9	1399.5
160°	1425.9	1425.6	1425.4	1425.0	1424.4	1423.7	1423.2	1422.6	1423.2	1423.7	1424.4
162.5°	1446.7	1446.4	1446.1	1446.0	1445.8	1445.7	1445.6	1445.4	1445.6	1445.7	1445.8
165°	1474.5	1474.5	1474.5	1474.7	1475.0	1475.2	1475.6	1475.8	1475.6	1475.2	1475.0
167.5°	1497.3	1497.3	1497.4	1497.8	1498.7	1499.5	1500.4	1501.2	1500.4	1499.5	1498.7
170°	1510.2	1510.5	1510.7	1511.3	1512.2	1513.0	1513.9	1514.8	1513.9	1513.0	1512.2
172.5°	1519.5	1519.8	1520.1	1520.7	1521.6	1522.4	1523.3	1524.1	1523.3	1522.4	1521.6
175°	1530.2	1530.8	1531.4	1532.1	1532.9	1533.8	1534.6	1535.5	1534.6	1533.8	1532.9
177.5°	1535.9	1536.4	1536.9	1537.5	1538.2	1538.9	1539.6	1540.2	1539.6	1538.9	1538.2
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	825.6	824.1	818.6	815.8	811.2	806.8	804.0	805.3	806.3	805.8	805.0
5°	801.9	795.8	786.5	778.4	772.7	762.1	757.6	755.4	753.4	751.1	748.9
7.5°	773.8	764.1	750.8	739.3	728.5	715.3	707.8	703.3	698.6	693.5	689.1
10°	753.7	740.2	726.1	710.0	697.2	685.2	674.6	667.5	661.1	655.0	650.5
12.5°	732.6	717.0	699.6	677.6	663.4	646.4	644.8	632.3	622.2	618.5	613.2
15°	699.0	677.2	655.0	629.0	617.7	602.3	592.6	583.0	574.3	568.2	566.5
17.5°	660.9	632.6	610.5	591.9	573.4	557.6	548.7	541.0	533.8	525.6	524.6
20°	631.8	607.4	583.3	566.9	547.9	531.8	520.9	513.2	507.0	502.2	498.1
22.5°	604.3	577.6	555.5	537.5	518.8	505.8	497.2	489.8	484.7	479.4	475.4
25°	560.2	539.2	515.1	494.9	479.4	471.1	464.0	457.5	454.3	450.8	446.3
27.5°	521.5	498.3	475.7	460.0	446.4	439.0	434.0	429.6	426.6	424.6	422.0
30°	494.2	470.7	453.1	437.6	426.4	419.0	415.8	413.2	409.7	408.4	407.1
32.5°	468.0	446.9	431.7	418.4	407.6	402.8	399.8	397.5	394.8	393.5	390.9
35°	430.8	413.2	398.4	391.0	382.3	378.2	375.9	372.6	370.1	368.9	368.5
37.5°	396.0	380.6	370.8	361.4	357.7	355.1	352.1	349.8	349.0	348.9	348.5
40°	373.3	360.8	352.1	344.4	342.8	338.9	336.3	334.4	334.4	334.8	334.4
42.5°	352.8	341.5	333.8	327.2	325.3	323.0	320.4	320.3	320.8	321.8	320.8
45°	321.6	313.5	308.1	304.8	301.3	299.0	298.7	299.7	300.0	300.3	301.3
47.5°	292.8	287.5	282.6	279.1	277.5	277.1	276.7	278.4	279.9	280.5	282.0
50°	275.9	269.8	265.6	263.4	262.1	261.4	262.1	264.0	265.3	266.9	267.9
52.5°	256.8	252.5	249.7	247.9	247.4	247.8	247.9	250.1	252.2	252.7	253.2
55°	230.6	227.3	226.7	223.8	225.1	224.7	226.4	227.6	229.5	231.5	231.9
57.5°	204.3	201.7	200.0	200.3	200.6	202.1	203.4	205.7	207.8	209.7	210.0
60°	186.8	185.5	184.6	184.6	185.2	187.2	188.7	191.0	192.3	193.6	194.5
62.5°	170.9	169.6	168.6	169.1	170.8	171.9	173.8	175.0	176.3	177.6	178.1
65°	145.7	145.0	146.0	146.6	147.0	148.5	150.8	151.8	153.1	153.7	155.9
67.5°	122.4	122.6	122.4	123.4	125.2	125.6	127.7	130.0	130.3	131.5	132.9
70°	106.8	107.4	108.1	108.7	110.3	110.9	112.5	113.5	114.8	115.7	116.8
72.5°	92.4	92.5	93.2	93.0	94.4	95.7	97.1	98.1	99.4	100.6	101.5
75°	71.0	71.0	71.7	72.1	73.6	75.3	74.9	75.6	76.9	78.2	78.8
77.5°	51.9	51.2	51.9	52.2	52.7	54.1	54.3	55.3	56.7	56.3	57.0
80°	39.5	38.6	39.5	39.9	39.9	41.5	41.5	42.1	43.0	42.1	43.0
82.5°	28.2	27.8	28.5	28.6	29.1	29.1	29.6	29.8	30.7	30.3	30.7
85°	14.1	13.9	14.1	13.9	14.1	14.5	14.5	14.1	14.1	14.8	13.9
87.5°	7.4	8.1	9.1	10.4	11.5	12.4	12.1	12.0	11.8	11.2	11.2
90°	15.2	20.1	26.4	32.7	39.1	45.5	44.9	44.3	43.7	43.1	43.0
92.5°	33.2	35.3	36.8	38.3	39.8	41.2	41.4	41.5	41.6	41.8	41.8
95°	79.0	80.8	81.4	81.9	82.5	83.1	83.1	83.1	83.1	83.1	82.7
97.5°	133.5	135.3	136.4	137.5	138.5	139.7	139.7	139.7	139.7	139.7	139.7
100°	174.1	175.6	176.5	177.4	178.2	179.1	179.1	179.1	179.1	179.1	179.0
102.5°	215.9	217.3	218.4	219.5	220.6	221.7	222.0	222.1	222.4	222.7	222.6
105°	282.5	283.3	283.9	284.4	285.0	285.6	286.1	286.7	287.3	287.8	288.2
107.5°	355.2	355.9	355.9	355.9	355.9	355.9	356.1	356.4	356.6	356.8	356.3
110°	402.8	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.2



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	452.6	453.4	453.1	453.0	452.7	452.5	451.8	451.1	450.4	449.7	449.0
115°	526.2	526.7	526.2	525.6	525.0	524.4	524.1	523.8	523.5	523.2	522.6
117.5°	601.7	602.0	600.4	598.7	597.1	595.6	594.9	594.2	593.5	592.8	591.9
120°	650.5	650.5	648.2	645.8	643.5	641.2	641.2	641.2	641.2	641.2	640.8
122.5°	697.0	697.5	695.9	694.3	692.7	691.0	690.3	689.7	689.0	688.3	687.6
125°	765.9	766.7	765.9	765.0	764.1	763.2	762.3	761.5	760.6	759.7	759.2
127.5°	836.4	837.5	836.5	835.4	834.4	833.4	832.2	831.2	830.2	829.1	828.2
130°	880.8	882.4	881.8	881.2	880.6	880.0	879.5	878.9	878.3	877.7	876.8
132.5°	925.7	927.4	927.5	927.6	927.7	927.8	926.5	925.3	924.0	922.7	921.6
135°	990.1	992.0	992.6	993.2	993.7	994.3	994.0	993.7	993.4	993.2	992.6
137.5°	1055.0	1056.7	1057.5	1058.2	1058.9	1059.7	1059.5	1059.2	1059.0	1058.8	1058.1
140°	1095.5	1097.5	1099.0	1100.4	1101.9	1103.3	1103.3	1103.3	1103.3	1103.3	1102.8
142.5°	1137.0	1138.8	1139.8	1140.8	1141.8	1142.8	1143.0	1143.2	1143.5	1143.7	1143.2
145°	1194.5	1196.4	1198.1	1199.8	1201.5	1203.2	1203.5	1203.9	1204.1	1204.4	1203.9
147.5°	1249.3	1251.1	1252.2	1253.4	1254.6	1255.7	1256.4	1257.0	1257.6	1258.3	1258.0
150°	1282.9	1284.3	1285.5	1286.6	1287.8	1288.9	1289.8	1290.6	1291.5	1292.4	1292.4
152.5°	1315.1	1316.6	1318.0	1319.4	1320.8	1322.2	1323.3	1324.3	1325.4	1326.5	1326.5
155°	1359.9	1360.7	1361.6	1362.4	1363.3	1364.2	1365.6	1367.1	1368.6	1369.9	1370.3
157.5°	1400.0	1400.6	1401.1	1401.6	1402.1	1402.7	1404.5	1406.5	1408.5	1410.5	1410.7
160°	1425.0	1425.4	1425.6	1425.9	1426.2	1426.5	1428.2	1429.9	1431.7	1433.4	1433.7
162.5°	1446.0	1446.1	1446.4	1446.7	1447.0	1447.3	1449.2	1451.2	1453.2	1455.1	1455.4
165°	1474.7	1474.5	1474.5	1474.5	1474.5	1474.5	1476.5	1478.6	1480.6	1482.6	1482.9
167.5°	1497.8	1497.4	1497.3	1497.3	1497.2	1497.1	1499.2	1501.2	1503.2	1505.2	1505.5
170°	1511.3	1510.7	1510.5	1510.2	1509.8	1509.6	1511.6	1513.6	1515.6	1517.7	1517.8
172.5°	1520.7	1520.1	1519.8	1519.5	1519.2	1518.9	1521.0	1522.9	1525.0	1527.0	1527.2
175°	1532.1	1531.4	1530.8	1530.2	1529.7	1529.0	1531.1	1533.1	1535.1	1537.1	1537.3
177.5°	1537.5	1536.9	1536.4	1535.9	1535.5	1535.0	1536.4	1537.8	1539.2	1540.6	1540.6
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	802.5	801.9	801.9	799.6	801.9	801.9	802.5	805.0	805.8	806.3	805.3
5°	744.4	743.4	741.8	743.4	741.8	743.4	744.4	748.9	751.1	753.4	755.4
7.5°	687.0	683.1	682.5	678.7	682.5	683.1	687.0	689.1	693.5	698.6	703.3
10°	645.1	642.5	642.1	636.0	642.1	642.5	645.1	650.5	655.0	661.1	667.5
12.5°	613.1	606.9	608.2	604.7	608.2	606.9	613.1	613.2	618.5	622.2	632.3
15°	557.8	557.8	556.6	551.1	556.6	557.8	557.8	566.5	568.2	574.3	583.0
17.5°	518.2	517.5	514.4	516.0	514.4	517.5	518.2	524.6	525.6	533.8	541.0
20°	494.6	492.6	488.8	488.8	488.8	492.6	494.6	498.1	502.2	507.0	513.2
22.5°	472.2	472.0	468.0	469.2	468.0	472.0	472.2	475.4	479.4	484.7	489.8
25°	446.0	443.4	441.5	442.5	441.5	443.4	446.0	446.3	450.8	454.3	457.5
27.5°	421.2	419.7	419.7	417.0	419.7	419.7	421.2	422.0	424.6	426.6	429.6
30°	406.7	403.6	404.2	402.6	404.2	403.6	406.7	407.1	408.4	409.7	413.2
32.5°	390.3	389.2	388.5	387.1	388.5	389.2	390.3	390.9	393.5	394.8	397.5
35°	367.8	368.2	366.5	367.2	366.5	368.2	367.8	368.5	368.9	370.1	372.6
37.5°	348.3	349.3	348.5	348.7	348.5	349.3	348.3	348.5	348.9	349.0	349.8
40°	335.4	335.4	335.4	336.3	335.4	335.4	335.4	334.4	334.8	334.4	334.4
42.5°	323.0	322.5	322.0	321.9	322.0	322.5	323.0	320.8	321.8	320.8	320.3
45°	302.0	302.9	303.2	301.6	303.2	302.9	302.0	301.3	300.3	300.0	299.7
47.5°	282.8	282.9	282.8	284.2	282.8	282.9	282.8	282.0	280.5	279.9	278.4
50°	269.5	268.8	269.5	268.8	269.5	268.8	269.5	267.9	266.9	265.3	264.0
52.5°	255.3	255.5	255.0	254.9	255.0	255.5	255.3	253.2	252.7	252.2	250.1
55°	233.2	233.8	233.4	233.4	233.4	233.8	233.2	231.9	231.5	229.5	227.6
57.5°	210.2	210.8	211.2	209.7	211.2	210.8	210.2	210.0	209.7	207.8	205.7
60°	194.2	195.8	195.5	194.8	195.5	195.8	194.2	194.5	193.6	192.3	191.0
62.5°	179.5	180.1	180.0	179.9	180.0	180.1	179.5	178.1	177.6	176.3	175.0
65°	156.9	157.6	156.6	157.6	156.6	157.6	156.9	155.9	153.7	153.1	151.8
67.5°	132.5	132.8	133.5	133.9	133.5	132.8	132.5	132.9	131.5	130.3	130.0
70°	117.4	117.0	118.0	119.0	118.0	117.0	117.4	116.8	115.7	114.8	113.5
72.5°	101.4	102.1	101.8	102.5	101.8	102.1	101.4	101.5	100.6	99.4	98.1
75°	78.2	79.1	78.8	79.7	78.8	79.1	78.2	78.8	78.2	76.9	75.6
77.5°	56.5	56.6	56.5	57.0	56.5	56.6	56.5	57.0	56.3	56.7	55.3
80°	43.0	42.4	41.8	43.0	41.8	42.4	43.0	43.0	42.1	43.0	42.1
82.5°	30.0	30.4	29.7	29.7	29.7	30.4	30.0	30.7	30.3	30.7	29.8
85°	13.9	13.5	12.8	12.8	12.8	13.5	13.9	13.9	14.8	14.1	14.1
87.5°	11.2	11.0	11.1	10.8	11.1	11.0	11.2	11.2	11.2	11.8	12.0
90°	43.3	43.6	43.8	44.2	43.8	43.6	43.3	43.0	43.1	43.7	44.3
92.5°	41.8	41.9	42.0	42.0	42.0	41.9	41.8	41.8	41.8	41.6	41.5
95°	82.2	81.6	81.0	80.5	81.0	81.6	82.2	82.7	83.1	83.1	83.1
97.5°	139.6	139.5	139.5	139.4	139.5	139.5	139.6	139.7	139.7	139.7	139.7
100°	178.7	178.4	178.1	177.8	178.1	178.4	178.7	179.0	179.1	179.1	179.1
102.5°	222.3	222.1	221.7	221.4	221.7	222.1	222.3	222.6	222.7	222.4	222.1
105°	288.2	288.2	288.2	288.2	288.2	288.2	288.2	288.2	287.8	287.3	286.7
107.5°	355.0	353.6	352.3	350.9	352.3	353.6	355.0	356.3	356.8	356.6	356.4
110°	402.3	401.5	400.6	399.8	400.6	401.5	402.3	403.2	403.7	403.7	403.7



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	448.4	447.8	447.1	446.5	447.1	447.8	448.4	449.0	449.7	450.4	451.1
115°	521.8	520.9	520.0	519.2	520.0	520.9	521.8	522.6	523.2	523.5	523.8
117.5°	591.1	590.2	589.4	588.5	589.4	590.2	591.1	591.9	592.8	593.5	594.2
120°	639.9	639.0	638.2	637.3	638.2	639.0	639.9	640.8	641.2	641.2	641.2
122.5°	687.0	686.4	685.7	685.1	685.7	686.4	687.0	687.6	688.3	689.0	689.7
125°	758.9	758.6	758.4	758.0	758.4	758.6	758.9	759.2	759.7	760.6	761.5
127.5°	827.2	826.3	825.4	824.5	825.4	826.3	827.2	828.2	829.1	830.2	831.2
130°	875.7	874.6	873.4	872.3	873.4	874.6	875.7	876.8	877.7	878.3	878.9
132.5°	920.8	919.8	918.9	917.9	918.9	919.8	920.8	921.6	922.7	924.0	925.3
135°	991.7	990.8	990.0	989.1	990.0	990.8	991.7	992.6	993.2	993.4	993.7
137.5°	1057.0	1055.8	1054.6	1053.4	1054.6	1055.8	1057.0	1058.1	1058.8	1059.0	1059.2
140°	1101.6	1100.4	1099.2	1098.1	1099.2	1100.4	1101.6	1102.8	1103.3	1103.3	1103.3
142.5°	1142.1	1140.9	1139.8	1138.6	1139.8	1140.9	1142.1	1143.2	1143.7	1143.5	1143.2
145°	1202.8	1201.7	1200.5	1199.4	1200.5	1201.7	1202.8	1203.9	1204.4	1204.1	1203.9
147.5°	1256.9	1255.8	1254.7	1253.6	1254.7	1255.8	1256.9	1258.0	1258.3	1257.6	1257.0
150°	1291.5	1290.6	1289.8	1288.9	1289.8	1290.6	1291.5	1292.4	1292.4	1291.5	1290.6
152.5°	1325.4	1324.3	1323.3	1322.2	1323.3	1324.3	1325.4	1326.5	1326.5	1325.4	1324.3
155°	1369.4	1368.6	1367.7	1366.8	1367.7	1368.6	1369.4	1370.3	1369.9	1368.6	1367.1
157.5°	1409.4	1408.0	1406.6	1405.2	1406.6	1408.0	1409.4	1410.7	1410.5	1408.5	1406.5
160°	1432.5	1431.4	1430.3	1429.1	1430.3	1431.4	1432.5	1433.7	1433.4	1431.7	1429.9
162.5°	1454.1	1452.7	1451.3	1449.8	1451.3	1452.7	1454.1	1455.4	1455.1	1453.2	1451.2
165°	1481.4	1480.1	1478.6	1477.1	1478.6	1480.1	1481.4	1482.9	1482.6	1480.6	1478.6
167.5°	1504.0	1502.4	1501.0	1499.4	1501.0	1502.4	1504.0	1505.5	1505.2	1503.2	1501.2
170°	1516.0	1514.3	1512.6	1510.9	1512.6	1514.3	1516.0	1517.8	1517.7	1515.6	1513.6
172.5°	1525.4	1523.7	1522.0	1520.3	1522.0	1523.7	1525.4	1527.2	1527.0	1525.0	1522.9
175°	1535.5	1533.8	1532.1	1530.3	1532.1	1533.8	1535.5	1537.3	1537.1	1535.1	1533.1
177.5°	1539.2	1537.8	1536.4	1535.0	1536.4	1537.8	1539.2	1540.6	1540.6	1539.2	1537.8
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	804.0	806.8	811.2	815.8	818.6	824.1	825.6	828.2	830.5	835.9	841.5
5°	757.6	762.1	772.7	778.4	786.5	795.8	801.9	808.4	815.5	827.7	839.0
7.5°	707.8	715.3	728.5	739.3	750.8	764.1	773.8	786.5	797.0	814.2	830.8
10°	674.6	685.2	697.2	710.0	726.1	740.2	753.7	769.8	782.6	803.2	822.5
12.5°	644.8	646.4	663.4	677.6	699.6	717.0	732.6	753.3	765.9	790.4	810.7
15°	592.6	602.3	617.7	629.0	655.0	677.2	699.0	720.6	735.0	765.3	791.9
17.5°	548.7	557.6	573.4	591.9	610.5	632.6	660.9	683.6	703.3	737.8	769.4
20°	520.9	531.8	547.9	566.9	583.3	607.4	631.8	657.9	679.1	718.0	755.0
22.5°	497.2	505.8	518.8	537.5	555.5	577.6	604.3	632.7	655.0	696.9	734.4
25°	464.0	471.1	479.4	494.9	515.1	539.2	560.2	591.3	623.8	663.1	708.3
27.5°	434.0	439.0	446.4	460.0	475.7	498.3	521.5	551.0	583.8	626.3	674.2
30°	415.8	419.0	426.4	437.6	453.1	470.7	494.2	522.5	555.9	599.1	646.6
32.5°	399.8	402.8	407.6	418.4	431.7	446.9	468.0	496.3	528.1	570.5	623.2
35°	375.9	378.2	382.3	391.0	398.4	413.2	430.8	456.6	486.5	527.0	581.7
37.5°	352.1	355.1	357.7	361.4	370.8	380.6	396.0	417.7	447.0	487.9	540.0
40°	336.3	338.9	342.8	344.4	352.1	360.8	373.3	393.2	422.8	460.1	510.9
42.5°	320.4	323.0	325.3	327.2	333.8	341.5	352.8	369.9	396.1	432.4	482.7
45°	298.7	299.0	301.3	304.8	308.1	313.5	321.6	336.3	356.6	390.7	436.4
47.5°	276.7	277.1	277.5	279.1	282.6	287.5	292.8	304.9	323.0	350.3	394.7
50°	262.1	261.4	262.1	263.4	265.6	269.8	275.9	284.6	299.4	324.8	365.6
52.5°	247.9	247.8	247.4	247.9	249.7	252.5	256.8	264.2	277.5	300.8	336.8
55°	226.4	224.7	225.1	223.8	226.7	227.3	230.6	236.7	248.2	264.3	298.1
57.5°	203.4	202.1	200.6	200.3	200.0	201.7	204.3	209.1	218.0	232.1	259.5
60°	188.7	187.2	185.2	184.6	184.6	185.5	186.8	190.4	198.7	211.3	233.8
62.5°	173.8	171.9	170.8	169.1	168.6	169.6	170.9	173.4	179.4	191.2	210.6
65°	150.8	148.5	147.0	146.6	146.0	145.0	145.7	148.3	153.1	162.4	177.8
67.5°	127.7	125.6	125.2	123.4	122.4	122.6	122.4	124.7	127.5	135.5	147.1
70°	112.5	110.9	110.3	108.7	108.1	107.4	106.8	108.7	111.6	118.3	128.3
72.5°	97.1	95.7	94.4	93.0	93.2	92.5	92.4	93.5	95.9	102.1	109.8
75°	74.9	75.3	73.6	72.1	71.7	71.0	71.0	72.1	73.0	77.8	83.9
77.5°	54.3	54.1	52.7	52.2	51.9	51.2	51.9	52.5	53.0	56.3	60.8
80°	41.5	41.5	39.9	39.9	39.5	38.6	39.5	38.9	40.2	43.4	46.7
82.5°	29.6	29.1	29.1	28.6	28.5	27.8	28.2	28.8	29.4	31.6	33.5
85°	14.5	14.5	14.1	13.9	14.1	13.9	14.1	14.5	14.8	15.8	17.4
87.5°	12.1	12.4	11.5	10.4	9.1	8.1	7.4	7.0	6.8	6.4	5.9
90°	44.9	45.5	39.1	32.7	26.4	20.1	15.2	11.7	8.2	4.7	1.3
92.5°	41.4	41.2	39.8	38.3	36.8	35.3	33.2	30.7	28.2	25.7	23.1
95°	83.1	83.1	82.5	81.9	81.4	80.8	79.0	76.1	73.3	70.3	67.5
97.5°	139.7	139.7	138.5	137.5	136.4	135.3	133.5	131.0	128.4	125.9	123.3
100°	179.1	179.1	178.2	177.4	176.5	175.6	174.1	171.8	169.4	167.1	164.9
102.5°	222.0	221.7	220.6	219.5	218.4	217.3	215.9	214.0	212.2	210.3	208.4
105°	286.1	285.6	285.0	284.4	283.9	283.3	282.5	281.6	280.8	279.9	279.1
107.5°	356.1	355.9	355.9	355.9	355.9	355.9	355.2	354.0	352.8	351.5	350.2
110°	403.7	403.7	403.7	403.7	403.7	403.7	402.8	401.1	399.3	397.6	395.9



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	451.8	452.5	452.7	453.0	453.1	453.4	452.6	450.9	449.2	447.5	445.7
115°	524.1	524.4	525.0	525.6	526.2	526.7	526.2	524.4	522.6	520.9	519.2
117.5°	594.9	595.6	597.1	598.7	600.4	602.0	601.7	599.3	597.0	594.7	592.5
120°	641.2	641.2	643.5	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2
122.5°	690.3	691.0	692.7	694.3	695.9	697.5	697.0	694.1	691.4	688.6	685.9
125°	762.3	763.2	764.1	765.0	765.9	766.7	765.9	763.2	760.6	758.0	755.4
127.5°	832.2	833.4	834.4	835.4	836.5	837.5	836.4	833.1	829.7	826.5	823.2
130°	879.5	880.0	880.6	881.2	881.8	882.4	880.8	877.0	873.3	869.5	865.7
132.5°	926.5	927.8	927.7	927.6	927.5	927.4	925.7	922.7	919.6	916.6	913.5
135°	994.0	994.3	993.7	993.2	992.6	992.0	990.1	986.9	983.8	980.6	977.4
137.5°	1059.5	1059.7	1058.9	1058.2	1057.5	1056.7	1055.0	1052.4	1049.8	1047.2	1044.7
140°	1103.3	1103.3	1101.9	1100.4	1099.0	1097.5	1095.5	1093.0	1090.4	1087.7	1085.1
142.5°	1143.0	1142.8	1141.8	1140.8	1139.8	1138.8	1137.0	1134.5	1131.9	1129.3	1126.7
145°	1203.5	1203.2	1201.5	1199.8	1198.1	1196.4	1194.5	1192.4	1190.4	1188.4	1186.4
147.5°	1256.4	1255.7	1254.6	1253.4	1252.2	1251.1	1249.3	1246.9	1244.4	1242.0	1239.6
150°	1289.8	1288.9	1287.8	1286.6	1285.5	1284.3	1282.9	1281.2	1279.4	1277.6	1275.9
152.5°	1323.3	1322.2	1320.8	1319.4	1318.0	1316.6	1315.1	1313.3	1311.6	1309.8	1308.1
155°	1365.6	1364.2	1363.3	1362.4	1361.6	1360.7	1359.9	1359.0	1358.1	1357.3	1356.4
157.5°	1404.5	1402.7	1402.1	1401.6	1401.1	1400.6	1400.0	1399.5	1398.9	1398.3	1397.7
160°	1428.2	1426.5	1426.2	1425.9	1425.6	1425.4	1425.0	1424.4	1423.7	1423.2	1422.6
162.5°	1449.2	1447.3	1447.0	1446.7	1446.4	1446.1	1446.0	1445.8	1445.7	1445.6	1445.4
165°	1476.5	1474.5	1474.5	1474.5	1474.5	1474.5	1474.7	1475.0	1475.2	1475.6	1475.8
167.5°	1499.2	1497.1	1497.2	1497.3	1497.3	1497.4	1497.8	1498.7	1499.5	1500.4	1501.2
170°	1511.6	1509.6	1509.8	1510.2	1510.5	1510.7	1511.3	1512.2	1513.0	1513.9	1514.8
172.5°	1521.0	1518.9	1519.2	1519.5	1519.8	1520.1	1520.7	1521.6	1522.4	1523.3	1524.1
175°	1531.1	1529.0	1529.7	1530.2	1530.8	1531.4	1532.1	1532.9	1533.8	1534.6	1535.5
177.5°	1536.4	1535.0	1535.5	1535.9	1536.4	1536.9	1537.5	1538.2	1538.9	1539.6	1540.2
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	841.0	842.3	846.4	850.6	855.1	856.4	858.5	856.7	856.2	861.1	864.7
5°	843.4	849.2	860.5	870.7	879.4	885.5	892.0	894.6	899.4	906.1	914.5
7.5°	840.7	852.0	869.7	884.7	901.0	912.7	922.0	929.8	939.3	952.1	966.0
10°	837.7	852.7	874.3	892.6	912.6	927.6	940.2	952.4	966.6	984.3	1002.5
12.5°	832.0	849.9	876.8	898.5	924.1	939.0	955.9	982.2	997.5	1022.1	1047.8
15°	820.6	840.5	878.1	904.8	933.8	962.1	993.2	1018.3	1043.4	1057.9	1094.2
17.5°	803.7	832.9	874.6	905.8	942.5	987.1	1022.1	1050.6	1079.5	1102.9	1121.2
20°	790.1	821.9	869.4	906.8	950.5	998.4	1038.6	1067.6	1092.6	1112.2	1123.5
22.5°	772.8	812.9	859.2	902.9	958.7	1006.2	1048.4	1071.2	1092.1	1101.6	1106.0
25°	745.6	793.9	846.3	899.7	962.7	1012.9	1051.5	1065.3	1071.4	1062.0	1046.6
27.5°	716.4	770.2	831.5	893.6	960.3	1008.5	1036.1	1034.0	1023.6	993.4	969.3
30°	694.6	753.7	819.6	887.4	954.3	1001.3	1017.4	1001.3	977.8	944.1	909.6
32.5°	671.7	732.9	807.0	878.7	943.6	984.8	988.3	960.6	924.3	886.0	843.0
35°	637.0	703.3	783.3	859.2	920.6	946.7	931.2	882.4	839.2	786.9	728.3
37.5°	597.8	671.0	751.2	830.5	886.2	893.0	854.7	803.2	742.4	680.9	612.0
40°	568.5	646.0	728.7	808.7	857.9	850.8	801.9	745.4	673.0	597.8	533.7
42.5°	542.3	619.7	704.0	782.5	821.9	802.5	745.4	675.9	598.1	527.3	468.7
45°	496.8	576.5	662.7	738.6	761.1	726.1	650.5	573.3	496.8	437.6	391.3
47.5°	452.7	531.5	616.8	683.5	691.6	644.4	561.8	482.4	416.6	368.4	335.8
50°	420.3	499.4	583.9	643.4	640.8	583.9	499.0	423.4	368.5	329.6	307.7
52.5°	391.2	465.9	547.2	601.2	587.6	525.6	444.5	377.5	332.3	301.8	282.0
55°	345.9	415.1	492.3	535.7	510.7	441.8	373.3	319.3	285.9	263.0	247.6
57.5°	301.1	365.9	432.0	458.7	431.0	367.5	310.4	271.2	246.1	229.1	219.1
60°	273.3	329.9	388.7	411.9	378.8	322.2	277.2	242.1	221.9	208.0	199.1
62.5°	245.6	296.2	351.7	364.3	334.0	286.2	246.3	217.1	200.5	188.2	179.8
65°	207.8	249.2	291.4	299.7	271.7	234.7	203.2	184.3	169.4	160.5	153.7
67.5°	170.4	203.6	233.5	240.2	215.8	190.1	167.3	150.8	140.8	133.3	127.6
70°	148.3	174.6	199.1	204.5	184.9	162.0	144.7	131.5	122.5	116.1	110.6
72.5°	124.8	146.8	167.1	170.8	154.8	137.3	123.1	112.7	104.8	100.7	95.4
75°	95.5	108.4	124.2	125.1	114.5	103.8	92.9	86.2	82.0	76.9	74.3
77.5°	67.4	77.5	86.5	88.3	82.0	74.7	68.6	63.3	59.8	57.3	55.0
80°	51.5	59.5	63.4	65.6	61.1	56.0	52.4	48.9	46.7	45.0	43.4
82.5°	36.8	41.8	45.4	47.1	44.6	41.6	38.0	36.0	34.3	32.9	32.4
85°	18.7	20.9	23.2	23.8	23.2	21.9	20.0	20.0	18.9	18.7	18.7
87.5°	7.4	9.1	9.8	11.3	11.7	13.0	14.3	15.2	16.3	15.9	15.6
90°	4.7	8.2	11.7	15.2	20.1	26.4	32.7	39.1	45.5	44.9	44.3
92.5°	25.7	28.2	30.7	33.2	35.3	36.8	38.3	39.8	41.2	41.4	41.5
95°	70.3	73.3	76.1	79.0	80.8	81.4	81.9	82.5	83.1	83.1	83.1
97.5°	125.9	128.4	131.0	133.5	135.3	136.4	137.5	138.5	139.7	139.7	139.7
100°	167.1	169.4	171.8	174.1	175.6	176.5	177.4	178.2	179.1	179.1	179.1
102.5°	210.3	212.2	214.0	215.9	217.3	218.4	219.5	220.6	221.7	222.0	222.1
105°	279.9	280.8	281.6	282.5	283.3	283.9	284.4	285.0	285.6	286.1	286.7
107.5°	351.5	352.8	354.0	355.2	355.9	355.9	355.9	355.9	355.9	356.1	356.4
110°	397.6	399.3	401.1	402.8	403.7	403.7	403.7	403.7	403.7	403.7	403.7





TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	447.5	449.2	450.9	452.6	453.4	453.1	453.0	452.7	452.5	451.8	451.1
115°	520.9	522.6	524.4	526.2	526.7	526.2	525.6	525.0	524.4	524.1	523.8
117.5°	594.7	597.0	599.3	601.7	602.0	600.4	598.7	597.1	595.6	594.9	594.2
120°	643.5	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2	641.2	641.2
122.5°	688.6	691.4	694.1	697.0	697.5	695.9	694.3	692.7	691.0	690.3	689.7
125°	758.0	760.6	763.2	765.9	766.7	765.9	765.0	764.1	763.2	762.3	761.5
127.5°	826.5	829.7	833.1	836.4	837.5	836.5	835.4	834.4	833.4	832.2	831.2
130°	869.5	873.3	877.0	880.8	882.4	881.8	881.2	880.6	880.0	879.5	878.9
132.5°	916.6	919.6	922.7	925.7	927.4	927.5	927.6	927.7	927.8	926.5	925.3
135°	980.6	983.8	986.9	990.1	992.0	992.6	993.2	993.7	994.3	994.0	993.7
137.5°	1047.2	1049.8	1052.4	1055.0	1056.7	1057.5	1058.2	1058.9	1059.7	1059.5	1059.2
140°	1087.7	1090.4	1093.0	1095.5	1097.5	1099.0	1100.4	1101.9	1103.3	1103.3	1103.3
142.5°	1129.3	1131.9	1134.5	1137.0	1138.8	1139.8	1140.8	1141.8	1142.8	1143.0	1143.2
145°	1188.4	1190.4	1192.4	1194.5	1196.4	1198.1	1199.8	1201.5	1203.2	1203.5	1203.9
147.5°	1242.0	1244.4	1246.9	1249.3	1251.1	1252.2	1253.4	1254.6	1255.7	1256.4	1257.0
150°	1277.6	1279.4	1281.2	1282.9	1284.3	1285.5	1286.6	1287.8	1288.9	1289.8	1290.6
152.5°	1309.8	1311.6	1313.3	1315.1	1316.6	1318.0	1319.4	1320.8	1322.2	1323.3	1324.3
155°	1357.3	1358.1	1359.0	1359.9	1360.7	1361.6	1362.4	1363.3	1364.2	1365.6	1367.1
157.5°	1398.3	1398.9	1399.5	1400.0	1400.6	1401.1	1401.6	1402.1	1402.7	1404.5	1406.5
160°	1423.2	1423.7	1424.4	1425.0	1425.4	1425.6	1425.9	1426.2	1426.5	1428.2	1429.9
162.5°	1445.6	1445.7	1445.8	1446.0	1446.1	1446.4	1446.7	1447.0	1447.3	1449.2	1451.2
165°	1475.6	1475.2	1475.0	1474.7	1474.5	1474.5	1474.5	1474.5	1474.5	1476.5	1478.6
167.5°	1500.4	1499.5	1498.7	1497.8	1497.4	1497.3	1497.3	1497.2	1497.1	1499.2	1501.2
170°	1513.9	1513.0	1512.2	1511.3	1510.7	1510.5	1510.2	1509.8	1509.6	1511.6	1513.6
172.5°	1523.3	1522.4	1521.6	1520.7	1520.1	1519.8	1519.5	1519.2	1518.9	1521.0	1522.9
175°	1534.6	1533.8	1532.9	1532.1	1531.4	1530.8	1530.2	1529.7	1529.0	1531.1	1533.1
177.5°	1539.6	1538.9	1538.2	1537.5	1536.9	1536.4	1535.9	1535.5	1535.0	1536.4	1537.8
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	867.8	871.4	871.4	871.9	876.0	875.6	875.3
5°	923.5	928.9	929.6	935.4	939.3	938.0	934.4
7.5°	976.0	986.2	993.9	998.2	1003.3	1006.4	1005.0
10°	1017.7	1032.5	1041.5	1047.6	1055.0	1060.5	1058.5
12.5°	1055.5	1073.2	1085.5	1096.0	1096.9	1104.0	1099.2
15°	1114.5	1133.2	1135.1	1142.8	1148.9	1148.2	1148.6
17.5°	1133.9	1140.0	1141.2	1141.3	1141.4	1139.2	1134.3
20°	1127.0	1124.8	1119.3	1115.2	1107.8	1106.7	1100.4
22.5°	1094.1	1086.9	1073.2	1064.2	1052.7	1049.6	1047.8
25°	1029.2	1013.5	991.6	970.8	964.9	953.7	956.9
27.5°	940.3	915.8	892.1	875.1	859.8	842.9	847.7
30°	877.8	850.2	816.7	791.0	774.6	758.5	755.6
32.5°	803.2	762.7	725.4	702.7	677.6	667.4	656.3
35°	674.6	635.1	598.1	566.3	547.9	533.7	520.9
37.5°	558.9	513.4	483.5	457.8	444.5	436.4	438.4
40°	487.2	447.3	425.4	405.8	393.6	387.8	389.1
42.5°	429.0	399.2	381.2	367.7	359.1	355.9	355.1
45°	363.0	346.3	331.5	323.8	319.6	316.1	313.8
47.5°	318.1	304.4	296.0	291.4	287.7	284.2	284.1
50°	291.0	282.0	276.2	271.4	268.5	265.9	268.2
52.5°	270.4	262.2	256.4	252.1	251.0	248.7	248.7
55°	239.9	233.4	229.3	225.4	223.5	222.2	220.6
57.5°	212.1	206.0	202.2	199.7	196.0	194.8	194.2
60°	192.3	187.4	183.6	180.4	178.7	176.2	176.2
62.5°	174.0	169.2	165.6	163.2	160.5	159.5	159.7
65°	147.6	143.7	140.2	137.6	137.0	135.1	135.7
67.5°	123.3	120.7	117.0	115.5	114.3	113.3	112.5
70°	107.1	104.5	102.5	100.7	99.7	99.7	99.7
72.5°	93.4	90.3	89.2	86.8	87.3	86.3	85.2
75°	72.3	70.4	69.5	68.4	66.9	66.9	66.9
77.5°	53.2	52.7	51.5	50.5	50.1	49.8	49.9
80°	41.2	40.8	40.2	40.2	39.5	39.3	38.6
82.5°	31.6	30.8	30.4	30.1	30.0	30.0	29.9
85°	18.0	17.4	17.4	17.7	17.0	17.0	17.4
87.5°	15.7	15.6	15.3	15.3	15.7	15.5	15.5
90°	43.7	43.1	43.0	43.3	43.6	43.8	44.2
92.5°	41.6	41.8	41.8	41.8	41.9	42.0	42.0
95°	83.1	83.1	82.7	82.2	81.6	81.0	80.5
97.5°	139.7	139.7	139.7	139.6	139.5	139.5	139.4
100°	179.1	179.1	179.0	178.7	178.4	178.1	177.8
102.5°	222.4	222.7	222.6	222.3	222.1	221.7	221.4
105°	287.3	287.8	288.2	288.2	288.2	288.2	288.2
107.5°	356.6	356.8	356.3	355.0	353.6	352.3	350.9
110°	403.7	403.7	403.2	402.3	401.5	400.6	399.8



TEST NUMBER: P331520-935

CATALOG NUMBER: S122DIW-S485D1440U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	450.4	449.7	449.0	448.4	447.8	447.1	446.5
115°	523.5	523.2	522.6	521.8	520.9	520.0	519.2
117.5°	593.5	592.8	591.9	591.1	590.2	589.4	588.5
120°	641.2	641.2	640.8	639.9	639.0	638.2	637.3
122.5°	689.0	688.3	687.6	687.0	686.4	685.7	685.1
125°	760.6	759.7	759.2	758.9	758.6	758.4	758.0
127.5°	830.2	829.1	828.2	827.2	826.3	825.4	824.5
130°	878.3	877.7	876.8	875.7	874.6	873.4	872.3
132.5°	924.0	922.7	921.6	920.8	919.8	918.9	917.9
135°	993.4	993.2	992.6	991.7	990.8	990.0	989.1
137.5°	1059.0	1058.8	1058.1	1057.0	1055.8	1054.6	1053.4
140°	1103.3	1103.3	1102.8	1101.6	1100.4	1099.2	1098.1
142.5°	1143.5	1143.7	1143.2	1142.1	1140.9	1139.8	1138.6
145°	1204.1	1204.4	1203.9	1202.8	1201.7	1200.5	1199.4
147.5°	1257.6	1258.3	1258.0	1256.9	1255.8	1254.7	1253.6
150°	1291.5	1292.4	1292.4	1291.5	1290.6	1289.8	1288.9
152.5°	1325.4	1326.5	1326.5	1325.4	1324.3	1323.3	1322.2
155°	1368.6	1369.9	1370.3	1369.4	1368.6	1367.7	1366.8
157.5°	1408.5	1410.5	1410.7	1409.4	1408.0	1406.6	1405.2
160°	1431.7	1433.4	1433.7	1432.5	1431.4	1430.3	1429.1
162.5°	1453.2	1455.1	1455.4	1454.1	1452.7	1451.3	1449.8
165°	1480.6	1482.6	1482.9	1481.4	1480.1	1478.6	1477.1
167.5°	1503.2	1505.2	1505.5	1504.0	1502.4	1501.0	1499.4
170°	1515.6	1517.7	1517.8	1516.0	1514.3	1512.6	1510.9
172.5°	1525.0	1527.0	1527.2	1525.4	1523.7	1522.0	1520.3
175°	1535.1	1537.1	1537.3	1535.5	1533.8	1532.1	1530.3
177.5°	1539.2	1540.6	1540.6	1539.2	1537.8	1536.4	1535.0
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2

(END OF REPORT)