

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331855-940

Luminaire Tested: **S122RDIW-S1005D970U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331855-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D970U940-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 970 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6559.5 lumens  
Efficiency: N/A  
Efficacy: 97.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331855-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331855-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	98	94	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26
5	69	58	50	44	63	54	47	41	46	40	36	38	34	31	31	29	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24380	24380	24380
5°	24473	24076	24209
10°	24287	23682	23481
15°	24008	22980	22318
20°	23622	21978	20874
25°	23225	20838	19475
30°	22676	19669	17682
35°	22141	18398	16109
40°	21602	17081	14286
45°	20970	15602	12638
50°	20321	14109	11017
55°	19657	12504	9464
60°	18887	10811	7857
65°	18010	9085	7156
70°	16966	7482	6581
75°	15689	6818	6138
80°	13845	6100	5588
85°	10893	4798	4798



TEST NUMBER: P331855-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.3	2.2
10°-20°	388.1	5.9
20°-30°	545.0	8.3
30°-40°	594.3	9.1
40°-50°	546.4	8.3
50°-60°	429.2	6.5
60°-70°	279.8	4.3
70°-80°	144.3	2.2
80°-90°	40.3	0.6
90°-100°	39.3	0.6
100°-110°	144.0	2.2
110°-120°	385.0	5.9
120°-130°	635.6	9.7
130°-140°	675.9	10.3
140°-150°	628.3	9.6
150°-160°	505.1	7.7
160°-170°	325.5	5.0
170°-180°	112.0	1.7
0°-30°	1074.4	16.4
0°-40°	1668.7	25.4
0°-60°	2644.3	40.3
0°-90°	3108.7	47.4
90°-120°	568.4	8.7
90°-150°	2508.2	38.2
90°-180°	3451.0	52.6
0°-180°	6559.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1510	1510	1510	1510	1510	
5°	1510	1503	1486	1497	1494	143
15°	1436	1419	1375	1350	1335	404
25°	1304	1257	1170	1116	1093	599
35°	1123	1051	933	850	817	703
45°	918	824	683	590	554	709
55°	698	589	444	365	336	624
65°	471	360	238	194	187	467
75°	252	158	109	100	98	266
85°	59	31	26	26	26	69
90°	1	10	17	21	23	5
95°	55	29	33	37	37	68
105°	259	270	52	61	65	277
115°	490	505	526	150	70	482
125°	693	704	720	726	728	617
135°	857	870	878	886	885	662
145°	994	994	1008	1013	1010	622
155°	1095	1088	1097	1102	1096	504
165°	1154	1149	1151	1156	1151	326
175°	1180	1175	1176	1181	1173	112
180°	1178	1178	1178	1178	1178	



TEST NUMBER: P331855-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0
2.5°	1515.6	1514.3	1513.1	1511.9	1510.6	1508.7	1506.0	1503.4	1500.7	1498.1	1500.5
5°	1510.0	1508.5	1507.0	1505.5	1504.0	1501.3	1497.3	1493.3	1489.4	1485.5	1488.2
7.5°	1494.5	1492.6	1490.8	1488.8	1486.9	1483.7	1479.1	1474.4	1469.9	1465.3	1466.1
10°	1481.4	1479.3	1477.1	1475.0	1472.8	1468.7	1462.7	1456.6	1450.5	1444.5	1443.6
12.5°	1465.0	1462.3	1459.7	1457.1	1454.6	1449.3	1441.5	1433.8	1426.0	1418.3	1416.6
15°	1436.3	1432.9	1429.6	1426.2	1422.9	1416.0	1405.8	1395.4	1385.1	1374.8	1369.0
17.5°	1401.0	1395.9	1390.8	1385.7	1380.6	1371.5	1358.2	1345.0	1331.7	1318.5	1311.6
20°	1374.8	1368.7	1362.6	1356.6	1350.5	1339.9	1324.6	1309.5	1294.3	1279.1	1271.5
22.5°	1346.3	1339.5	1332.8	1326.0	1319.1	1307.2	1290.0	1272.9	1255.8	1238.7	1228.9
25°	1303.7	1294.0	1284.2	1274.5	1264.8	1250.0	1229.9	1209.9	1189.8	1169.7	1157.4
27.5°	1252.3	1241.8	1231.2	1220.7	1210.1	1193.5	1170.9	1148.3	1125.7	1103.1	1088.6
30°	1216.3	1204.7	1193.2	1181.6	1170.1	1152.2	1127.8	1103.6	1079.3	1055.0	1039.5
32.5°	1181.2	1167.8	1154.3	1140.9	1127.3	1108.2	1083.4	1058.6	1033.8	1009.1	991.4
35°	1123.3	1107.9	1092.3	1076.8	1061.4	1040.3	1013.5	986.9	960.1	933.4	914.3
37.5°	1065.4	1048.4	1031.4	1014.3	997.4	974.6	946.1	917.7	889.1	860.7	839.6
40°	1024.9	1006.7	988.5	970.3	952.1	928.2	898.8	869.3	839.8	810.4	788.8
42.5°	983.4	964.2	945.0	925.8	906.6	881.8	851.4	820.9	790.5	760.1	737.8
45°	918.4	898.0	877.6	857.3	837.0	810.8	778.9	747.1	715.2	683.3	661.7
47.5°	854.9	833.4	811.8	790.2	768.7	741.5	708.6	675.6	642.7	609.8	588.4
50°	809.0	787.5	765.9	744.3	722.7	695.3	661.9	628.5	595.0	561.7	540.7
52.5°	764.2	741.6	719.2	696.6	674.0	646.5	613.8	581.1	548.4	515.8	495.5
55°	698.3	674.7	650.9	627.2	603.6	575.3	542.5	509.7	477.0	444.2	425.9
57.5°	630.8	606.5	582.2	557.9	533.6	505.7	474.2	442.6	411.2	379.6	362.9
60°	584.9	560.6	536.3	512.0	487.7	459.9	428.6	397.3	366.0	334.8	319.3
62.5°	540.1	515.8	491.5	467.2	442.9	415.8	386.0	356.1	326.4	296.6	281.8
65°	471.4	446.8	422.3	397.7	373.1	347.1	319.8	292.5	265.1	237.8	227.5
67.5°	405.3	380.9	356.5	332.1	307.6	283.1	258.6	234.0	209.4	184.8	180.0
70°	359.4	335.7	312.0	288.4	264.7	242.4	221.4	200.5	179.5	158.5	155.5
72.5°	315.7	292.9	270.3	247.5	224.8	205.0	188.2	171.4	154.5	137.8	135.2
75°	251.5	230.2	208.9	187.7	166.4	150.6	140.3	130.0	119.7	109.3	107.2
77.5°	188.3	169.7	151.1	132.4	113.7	101.9	96.9	91.9	86.9	82.0	80.8
80°	148.9	133.5	118.0	102.5	87.0	77.8	74.7	71.7	68.7	65.6	64.4
82.5°	112.9	100.8	88.7	76.6	64.6	57.4	55.4	53.3	51.3	49.2	48.5
85°	58.8	52.3	46.0	39.6	33.3	29.6	28.7	27.8	26.8	25.9	25.9
87.5°	17.7	16.1	14.6	13.1	11.6	11.0	11.2	11.6	11.9	12.1	12.1
90°	0.9	2.9	5.0	7.1	9.2	11.0	12.5	14.0	15.5	17.0	18.0
92.5°	17.2	17.0	16.9	16.7	16.5	16.8	17.5	18.3	19.0	19.8	20.2
95°	55.4	49.1	42.9	36.6	30.4	27.9	29.2	30.6	31.9	33.3	34.2
97.5°	109.9	92.3	74.7	57.1	39.5	32.2	35.3	38.3	41.4	44.5	45.2
100°	150.8	124.8	98.9	73.0	47.1	35.7	38.9	42.1	45.4	48.6	50.1
102.5°	195.8	190.3	184.9	179.3	173.8	157.7	130.7	103.8	76.9	49.9	51.9
105°	259.0	264.7	270.4	276.1	281.8	258.8	207.1	155.3	103.7	52.0	54.0
107.5°	331.1	335.7	340.3	344.8	349.5	320.7	258.8	196.7	134.7	72.8	70.6
110°	377.5	381.5	385.4	389.4	393.3	368.0	313.3	258.6	203.8	149.1	130.2



TEST NUMBER: P331855-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	421.1	424.6	428.1	431.7	435.2	430.2	416.7	403.1	389.6	376.1	307.0
115°	489.9	493.1	496.4	499.6	502.8	506.8	511.5	516.2	521.0	525.8	438.0
117.5°	551.4	555.1	558.7	562.2	565.9	569.3	572.6	575.8	579.1	582.3	561.1
120°	596.5	599.3	602.1	604.9	607.8	610.9	614.3	617.8	621.2	624.6	626.9
122.5°	634.6	637.6	640.6	643.5	646.6	650.0	653.6	657.4	661.0	664.8	666.1
125°	692.7	695.2	697.7	700.1	702.6	705.6	709.2	712.8	716.4	720.0	721.3
127.5°	745.4	748.1	750.8	753.6	756.3	759.0	761.7	764.4	767.0	769.7	771.7
130°	778.8	781.9	784.9	787.8	790.9	793.4	795.5	797.6	799.7	801.8	803.9
132.5°	812.9	815.5	818.1	820.6	823.1	825.5	827.6	829.6	831.7	833.8	835.6
135°	857.2	860.2	863.3	866.3	869.3	871.6	873.3	875.0	876.7	878.5	880.4
137.5°	902.0	904.1	906.2	908.4	910.4	912.5	914.4	916.3	918.3	920.2	922.1
140°	931.3	932.8	934.3	935.9	937.4	939.1	941.2	943.3	945.4	947.5	949.2
142.5°	955.8	957.2	958.6	959.9	961.3	963.1	965.5	968.0	970.4	972.7	974.3
145°	994.3	994.2	994.0	993.8	993.6	995.1	998.4	1001.6	1004.8	1008.0	1009.3
147.5°	1028.0	1027.2	1026.4	1025.7	1025.0	1026.3	1029.5	1032.6	1035.8	1039.0	1040.0
150°	1049.7	1048.4	1047.0	1045.8	1044.5	1045.3	1048.3	1051.3	1054.4	1057.4	1058.5
152.5°	1068.2	1066.7	1065.1	1063.7	1062.2	1062.9	1065.8	1068.7	1071.6	1074.4	1075.6
155°	1094.9	1093.1	1091.5	1089.8	1088.1	1088.3	1090.7	1092.9	1095.2	1097.4	1098.6
157.5°	1115.9	1114.5	1112.9	1111.5	1110.1	1110.2	1111.8	1113.4	1114.9	1116.5	1117.8
160°	1128.1	1127.0	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1129.3
162.5°	1139.1	1137.9	1136.8	1135.6	1134.5	1134.4	1135.4	1136.4	1137.4	1138.4	1139.6
165°	1153.7	1152.5	1151.4	1150.3	1149.1	1148.9	1149.4	1150.0	1150.6	1151.1	1152.4
167.5°	1164.6	1163.4	1162.3	1161.2	1160.0	1159.8	1160.3	1160.8	1161.4	1161.9	1163.1
170°	1170.7	1169.6	1168.5	1167.3	1166.2	1165.8	1166.2	1166.5	1167.0	1167.3	1168.7
172.5°	1174.8	1173.7	1172.5	1171.4	1170.3	1169.9	1170.3	1170.6	1171.0	1171.4	1172.8
175°	1180.1	1178.8	1177.4	1176.2	1174.8	1174.3	1174.7	1175.1	1175.5	1175.8	1177.1
177.5°	1181.0	1179.9	1178.8	1177.8	1176.7	1176.3	1176.4	1176.5	1176.7	1176.9	1177.9
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331855-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0
2.5°	1502.9	1505.3	1507.8	1508.7	1508.2	1507.8	1507.3	1506.8
5°	1490.9	1493.7	1496.4	1497.3	1496.4	1495.5	1494.6	1493.7
7.5°	1466.8	1467.6	1468.4	1468.0	1466.4	1464.8	1463.3	1461.7
10°	1442.6	1441.7	1440.8	1439.5	1437.6	1435.8	1434.0	1432.2
12.5°	1415.0	1413.3	1411.7	1409.3	1406.3	1403.3	1400.3	1397.2
15°	1363.2	1357.5	1351.7	1347.3	1344.3	1341.2	1338.2	1335.2
17.5°	1304.8	1297.9	1291.0	1285.0	1279.8	1274.5	1269.3	1264.1
20°	1263.9	1256.3	1248.8	1241.6	1234.9	1228.2	1221.6	1214.9
22.5°	1219.1	1209.3	1199.5	1192.1	1187.2	1182.2	1177.2	1172.2
25°	1144.9	1132.5	1120.0	1111.5	1106.9	1102.3	1097.8	1093.2
27.5°	1074.1	1059.5	1045.0	1034.1	1026.9	1019.7	1012.4	1005.2
30°	1024.0	1008.5	993.0	981.2	973.0	964.8	956.6	948.4
32.5°	973.7	956.1	938.3	925.7	918.0	910.3	902.5	894.8
35°	895.1	876.0	856.8	843.9	837.2	830.5	823.9	817.3
37.5°	818.5	797.5	776.3	762.0	754.4	746.7	739.0	731.4
40°	767.2	745.6	724.2	709.4	701.5	693.6	685.7	677.8
42.5°	715.5	693.2	670.9	655.9	648.3	640.6	633.0	625.4
45°	640.2	618.6	597.0	582.6	575.3	568.0	560.7	553.5
47.5°	566.9	545.5	524.0	510.0	503.4	496.8	490.1	483.5
50°	519.8	498.8	477.9	464.1	457.8	451.4	445.1	438.6
52.5°	475.3	455.0	434.9	421.8	415.9	410.0	404.1	398.2
55°	407.7	389.5	371.2	359.3	353.5	347.7	342.0	336.2
57.5°	346.3	329.5	312.8	302.0	297.2	292.3	287.5	282.6
60°	303.8	288.4	272.9	262.7	257.8	253.0	248.1	243.3
62.5°	267.1	252.3	237.6	228.6	225.8	222.8	219.9	217.0
65°	217.1	206.8	196.4	190.8	189.9	189.0	188.2	187.3
67.5°	175.3	170.6	165.8	162.9	162.0	161.0	160.1	159.1
70°	152.5	149.5	146.4	144.3	143.0	141.8	140.6	139.4
72.5°	132.7	130.1	127.5	125.9	125.2	124.5	123.7	123.0
75°	105.0	103.0	100.9	99.6	99.3	99.0	98.7	98.4
77.5°	79.5	78.4	77.1	76.2	75.8	75.3	74.8	74.4
80°	63.1	62.0	60.7	60.1	60.1	60.1	60.1	60.1
82.5°	47.7	47.0	46.3	45.9	45.9	45.9	45.9	45.9
85°	25.9	25.9	25.9	25.9	25.9	25.9	25.9	25.9
87.5°	12.0	11.9	11.9	11.9	12.0	12.1	12.2	12.2
90°	18.9	19.9	20.9	21.5	21.8	22.2	22.6	23.0
92.5°	20.8	21.2	21.8	22.1	22.3	22.6	22.7	23.0
95°	35.1	36.1	37.0	37.4	37.2	37.0	36.8	36.6
97.5°	46.0	46.7	47.5	48.0	48.2	48.4	48.7	48.9
100°	51.6	53.1	54.7	55.6	55.9	56.4	56.7	57.1
102.5°	53.9	55.8	57.8	59.0	59.6	60.1	60.6	61.2
105°	56.2	58.2	60.3	61.7	62.5	63.2	64.0	64.7
107.5°	68.5	66.4	64.3	63.6	64.4	65.1	65.9	66.6
110°	111.2	92.3	73.4	64.3	65.0	65.8	66.5	67.3





TEST NUMBER: P331855-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	237.9	168.9	99.8	65.5	66.2	66.8	67.4	68.0
115°	350.4	262.7	175.0	124.4	110.8	97.1	83.5	69.9
117.5°	539.8	518.7	497.5	464.5	419.6	374.9	330.1	285.3
120°	629.1	631.3	633.6	622.0	596.5	570.9	545.3	519.8
122.5°	667.5	668.9	670.2	668.4	663.4	658.5	653.5	648.6
125°	722.6	724.0	725.3	726.2	726.8	727.4	727.9	728.5
127.5°	773.6	775.5	777.5	778.5	778.6	778.7	778.8	778.9
130°	805.9	808.1	810.1	811.1	810.8	810.7	810.5	810.3
132.5°	837.4	839.2	841.0	841.8	841.5	841.3	841.2	841.0
135°	882.3	884.1	886.0	886.8	886.4	886.0	885.6	885.3
137.5°	923.9	925.8	927.6	928.3	927.6	926.9	926.3	925.7
140°	950.9	952.6	954.3	954.7	953.8	952.8	951.8	950.9
142.5°	975.8	977.4	978.9	979.2	978.3	977.3	976.4	975.4
145°	1010.7	1012.0	1013.3	1013.5	1012.5	1011.6	1010.7	1009.7
147.5°	1041.0	1042.0	1042.9	1043.0	1042.2	1041.4	1040.6	1039.8
150°	1059.7	1060.8	1061.9	1062.0	1061.1	1060.2	1059.2	1058.3
152.5°	1076.7	1077.8	1079.0	1079.0	1077.7	1076.5	1075.2	1074.0
155°	1099.7	1100.8	1102.0	1101.8	1100.3	1098.8	1097.3	1095.7
157.5°	1119.1	1120.4	1121.7	1121.6	1120.1	1118.7	1117.1	1115.7
160°	1130.4	1131.5	1132.7	1132.6	1131.2	1129.9	1128.6	1127.3
162.5°	1140.9	1142.2	1143.5	1143.4	1141.7	1140.1	1138.4	1136.8
165°	1153.8	1155.1	1156.5	1156.5	1155.1	1153.8	1152.4	1151.1
167.5°	1164.5	1165.8	1167.2	1167.0	1165.3	1163.6	1161.9	1160.2
170°	1170.0	1171.3	1172.6	1172.4	1170.7	1169.0	1167.3	1165.6
172.5°	1174.0	1175.4	1176.7	1176.5	1174.8	1173.1	1171.4	1169.7
175°	1178.5	1179.8	1181.2	1180.9	1178.9	1177.1	1175.2	1173.3
177.5°	1179.0	1180.0	1181.1	1181.0	1179.6	1178.2	1176.9	1175.5
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5

(END OF REPORT)