

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331856-940

Luminaire Tested: **S122RDIW-S1005D970U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331856-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D970U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6102.7 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331856-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331856-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70		62	61	59		51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59		55	53	50		46	44	42	38
3	82	73	66	61	76	68	62	57	58	54	50		49	46	43		41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43		44	40	37		37	34	32	28
5	70	58	50	45	64	54	47	42	47	41	37		40	36	33		33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33		36	32	29		30	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29		33	29	26		28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26		30	26	23		26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	23		28	24	21		24	21	18	16
10	48	36	29	25	45	34	28	24	30	25	21		26	22	19		22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24380	24380	24380
5°	24473	24076	24209
10°	24287	23682	23481
15°	24008	22980	22318
20°	23622	21978	20874
25°	23225	20838	19475
30°	22676	19669	17682
35°	22141	18398	16109
40°	21602	17081	14286
45°	20970	15602	12638
50°	20321	14109	11017
55°	19657	12504	9464
60°	18887	10811	7857
65°	18010	9085	7156
70°	16966	7482	6581
75°	15689	6818	6138
80°	13845	6100	5588
85°	10893	4798	4798



TEST NUMBER: P331856-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.3	2.3
10°-20°	388.1	6.4
20°-30°	545.0	8.9
30°-40°	594.3	9.7
40°-50°	546.4	9.0
50°-60°	429.2	7.0
60°-70°	279.8	4.6
70°-80°	144.3	2.4
80°-90°	41.7	0.7
90°-100°	67.8	1.1
100°-110°	210.6	3.5
110°-120°	360.0	5.9
120°-130°	473.5	7.8
130°-140°	531.4	8.7
140°-150°	521.1	8.5
150°-160°	437.0	7.2
160°-170°	289.9	4.7
170°-180°	101.3	1.7
0°-30°	1074.4	17.6
0°-40°	1668.7	27.3
0°-60°	2644.3	43.3
0°-90°	3110.1	51.0
90°-120°	638.5	10.5
90°-150°	2164.4	35.5
90°-180°	2993.0	49.0
0°-180°	6102.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1510	1510	1510	1510	1510	
5°	1510	1503	1486	1497	1494	143
15°	1436	1419	1375	1350	1335	404
25°	1304	1257	1170	1116	1093	599
35°	1123	1051	933	850	817	703
45°	918	824	683	590	554	709
55°	698	589	444	365	336	624
65°	471	360	238	194	187	467
75°	252	158	109	100	98	266
85°	59	31	26	26	26	69
90°	1	12	32	30	31	5
95°	47	56	58	58	56	54
105°	194	197	199	200	200	205
115°	361	366	365	364	361	357
125°	526	533	531	528	527	470
135°	680	690	692	691	688	525
145°	826	832	837	838	835	515
155°	944	946	949	953	951	434
165°	1027	1026	1026	1032	1028	289
175°	1068	1066	1064	1070	1065	101
180°	1070	1070	1070	1070	1070	



TEST NUMBER: P331856-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0
2.5°	1515.6	1514.3	1513.1	1511.9	1510.6	1508.7	1506.0	1503.4	1500.7	1498.1	1500.5
5°	1510.0	1508.5	1507.0	1505.5	1504.0	1501.3	1497.3	1493.3	1489.4	1485.5	1488.2
7.5°	1494.5	1492.6	1490.8	1488.8	1486.9	1483.7	1479.1	1474.4	1469.9	1465.3	1466.1
10°	1481.4	1479.3	1477.1	1475.0	1472.8	1468.7	1462.7	1456.6	1450.5	1444.5	1443.6
12.5°	1465.0	1462.3	1459.7	1457.1	1454.6	1449.3	1441.5	1433.8	1426.0	1418.3	1416.6
15°	1436.3	1432.9	1429.6	1426.2	1422.9	1416.0	1405.8	1395.4	1385.1	1374.8	1369.0
17.5°	1401.0	1395.9	1390.8	1385.7	1380.6	1371.5	1358.2	1345.0	1331.7	1318.5	1311.6
20°	1374.8	1368.7	1362.6	1356.6	1350.5	1339.9	1324.6	1309.5	1294.3	1279.1	1271.5
22.5°	1346.3	1339.5	1332.8	1326.0	1319.1	1307.2	1290.0	1272.9	1255.8	1238.7	1228.9
25°	1303.7	1294.0	1284.2	1274.5	1264.8	1250.0	1229.9	1209.9	1189.8	1169.7	1157.4
27.5°	1252.3	1241.8	1231.2	1220.7	1210.1	1193.5	1170.9	1148.3	1125.7	1103.1	1088.6
30°	1216.3	1204.7	1193.2	1181.6	1170.1	1152.2	1127.8	1103.6	1079.3	1055.0	1039.5
32.5°	1181.2	1167.8	1154.3	1140.9	1127.3	1108.2	1083.4	1058.6	1033.8	1009.1	991.4
35°	1123.3	1107.9	1092.3	1076.8	1061.4	1040.3	1013.5	986.9	960.1	933.4	914.3
37.5°	1065.4	1048.4	1031.4	1014.3	997.4	974.6	946.1	917.7	889.1	860.7	839.6
40°	1024.9	1006.7	988.5	970.3	952.1	928.2	898.8	869.3	839.8	810.4	788.8
42.5°	983.4	964.2	945.0	925.8	906.6	881.8	851.4	820.9	790.5	760.1	737.8
45°	918.4	898.0	877.6	857.3	837.0	810.8	778.9	747.1	715.2	683.3	661.7
47.5°	854.9	833.4	811.8	790.2	768.7	741.5	708.6	675.6	642.7	609.8	588.4
50°	809.0	787.5	765.9	744.3	722.7	695.3	661.9	628.5	595.0	561.7	540.7
52.5°	764.2	741.6	719.2	696.6	674.0	646.5	613.8	581.1	548.4	515.8	495.5
55°	698.3	674.7	650.9	627.2	603.6	575.3	542.5	509.7	477.0	444.2	425.9
57.5°	630.8	606.5	582.2	557.9	533.6	505.7	474.2	442.6	411.2	379.6	362.9
60°	584.9	560.6	536.3	512.0	487.7	459.9	428.6	397.3	366.0	334.8	319.3
62.5°	540.1	515.8	491.5	467.2	442.9	415.8	386.0	356.1	326.4	296.6	281.8
65°	471.4	446.8	422.3	397.7	373.1	347.1	319.8	292.5	265.1	237.8	227.5
67.5°	405.3	380.9	356.5	332.1	307.6	283.1	258.6	234.0	209.4	184.8	180.0
70°	359.4	335.7	312.0	288.4	264.7	242.4	221.4	200.5	179.5	158.5	155.5
72.5°	315.7	292.9	270.3	247.5	224.8	205.0	188.2	171.4	154.5	137.8	135.2
75°	251.5	230.2	208.9	187.7	166.4	150.6	140.3	130.0	119.7	109.3	107.2
77.5°	188.3	169.7	151.1	132.4	113.7	101.9	96.9	91.9	86.9	82.0	80.8
80°	148.9	133.5	118.0	102.5	87.0	77.8	74.7	71.7	68.7	65.6	64.4
82.5°	112.9	100.8	88.7	76.6	64.6	57.4	55.4	53.3	51.3	49.2	48.5
85°	58.8	52.3	46.0	39.6	33.3	29.6	28.7	27.8	26.8	25.9	25.9
87.5°	17.7	16.2	14.7	13.3	11.9	11.5	12.4	13.3	14.2	15.1	14.7
90°	0.9	3.3	5.7	8.1	10.5	13.9	18.4	22.7	27.2	31.6	31.2
92.5°	16.1	17.8	19.6	21.4	23.2	24.5	25.6	26.7	27.6	28.7	28.8
95°	47.0	49.0	51.0	53.0	55.0	56.2	56.6	57.0	57.4	57.8	57.8
97.5°	85.8	87.6	89.3	91.1	92.8	94.2	94.9	95.7	96.4	97.2	97.2
100°	114.7	116.3	117.9	119.5	121.1	122.3	122.8	123.4	124.0	124.7	124.7
102.5°	145.1	146.3	147.6	148.9	150.2	151.2	151.9	152.8	153.5	154.3	154.4
105°	194.2	194.7	195.4	196.0	196.6	197.1	197.5	197.9	198.3	198.7	199.1
107.5°	243.7	244.6	245.4	246.3	247.2	247.6	247.6	247.6	247.6	247.6	247.8
110°	275.4	276.7	277.9	279.1	280.3	280.9	280.9	280.9	280.9	280.9	280.9



TEST NUMBER: P331856-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	310.1	311.4	312.5	313.8	315.0	315.5	315.3	315.1	315.0	314.9	314.3
115°	361.2	362.5	363.6	364.9	366.0	366.5	366.0	365.7	365.2	364.9	364.7
117.5°	412.2	413.8	415.4	417.1	418.7	418.8	417.8	416.6	415.5	414.4	413.9
120°	446.2	447.8	449.4	451.0	452.6	452.6	451.0	449.4	447.8	446.2	446.2
122.5°	477.2	479.2	481.1	483.0	484.9	485.4	484.2	483.1	482.0	480.8	480.4
125°	525.7	527.4	529.2	531.1	532.9	533.5	532.9	532.3	531.6	531.1	530.5
127.5°	572.8	575.1	577.4	579.7	581.9	582.7	582.0	581.3	580.6	579.9	579.1
130°	602.4	605.0	607.6	610.3	612.9	613.9	613.6	613.1	612.8	612.3	612.0
132.5°	635.6	637.8	639.9	642.0	644.2	645.2	645.3	645.4	645.5	645.6	644.7
135°	680.1	682.3	684.5	686.7	688.9	690.2	690.6	691.0	691.4	691.8	691.6
137.5°	726.8	728.7	730.5	732.3	734.1	735.3	735.8	736.3	736.8	737.4	737.2
140°	755.0	756.9	758.7	760.5	762.2	763.7	764.7	765.7	766.7	767.7	767.7
142.5°	784.0	785.8	787.6	789.3	791.2	792.5	793.1	793.8	794.5	795.1	795.3
145°	825.5	826.9	828.3	829.7	831.2	832.4	833.7	834.8	836.1	837.2	837.4
147.5°	862.6	864.2	865.9	867.5	869.2	870.5	871.3	872.1	872.9	873.7	874.1
150°	887.8	889.0	890.2	891.4	892.6	893.7	894.5	895.3	896.1	896.9	897.4
152.5°	910.3	911.4	912.7	913.8	915.1	916.1	917.1	918.0	919.0	920.0	920.7
155°	943.8	944.4	945.0	945.7	946.2	946.8	947.4	948.1	948.6	949.2	950.2
157.5°	972.5	972.9	973.3	973.7	974.1	974.6	974.9	975.3	975.6	976.0	977.3
160°	989.9	990.2	990.7	991.0	991.5	991.8	992.0	992.2	992.4	992.6	993.8
162.5°	1005.8	1005.8	1005.9	1006.0	1006.1	1006.2	1006.5	1006.7	1006.8	1007.0	1008.4
165°	1026.9	1026.7	1026.5	1026.3	1026.1	1026.0	1026.0	1026.0	1026.0	1026.0	1027.4
167.5°	1044.6	1044.0	1043.4	1042.8	1042.2	1041.9	1041.9	1041.8	1041.8	1041.7	1043.1
170°	1054.0	1053.4	1052.8	1052.2	1051.6	1051.2	1051.0	1050.8	1050.6	1050.4	1051.8
172.5°	1060.5	1059.9	1059.3	1058.7	1058.1	1057.7	1057.5	1057.3	1057.1	1056.9	1058.3
175°	1068.4	1067.8	1067.3	1066.7	1066.0	1065.5	1065.1	1064.7	1064.3	1063.9	1065.3
177.5°	1071.7	1071.2	1070.8	1070.2	1069.8	1069.3	1069.1	1068.7	1068.4	1068.1	1069.1
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331856-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0	1510.0
2.5°	1502.9	1505.3	1507.8	1508.7	1508.2	1507.8	1507.3	1506.8
5°	1490.9	1493.7	1496.4	1497.3	1496.4	1495.5	1494.6	1493.7
7.5°	1466.8	1467.6	1468.4	1468.0	1466.4	1464.8	1463.3	1461.7
10°	1442.6	1441.7	1440.8	1439.5	1437.6	1435.8	1434.0	1432.2
12.5°	1415.0	1413.3	1411.7	1409.3	1406.3	1403.3	1400.3	1397.2
15°	1363.2	1357.5	1351.7	1347.3	1344.3	1341.2	1338.2	1335.2
17.5°	1304.8	1297.9	1291.0	1285.0	1279.8	1274.5	1269.3	1264.1
20°	1263.9	1256.3	1248.8	1241.6	1234.9	1228.2	1221.6	1214.9
22.5°	1219.1	1209.3	1199.5	1192.1	1187.2	1182.2	1177.2	1172.2
25°	1144.9	1132.5	1120.0	1111.5	1106.9	1102.3	1097.8	1093.2
27.5°	1074.1	1059.5	1045.0	1034.1	1026.9	1019.7	1012.4	1005.2
30°	1024.0	1008.5	993.0	981.2	973.0	964.8	956.6	948.4
32.5°	973.7	956.1	938.3	925.7	918.0	910.3	902.5	894.8
35°	895.1	876.0	856.8	843.9	837.2	830.5	823.9	817.3
37.5°	818.5	797.5	776.3	762.0	754.4	746.7	739.0	731.4
40°	767.2	745.6	724.2	709.4	701.5	693.6	685.7	677.8
42.5°	715.5	693.2	670.9	655.9	648.3	640.6	633.0	625.4
45°	640.2	618.6	597.0	582.6	575.3	568.0	560.7	553.5
47.5°	566.9	545.5	524.0	510.0	503.4	496.8	490.1	483.5
50°	519.8	498.8	477.9	464.1	457.8	451.4	445.1	438.6
52.5°	475.3	455.0	434.9	421.8	415.9	410.0	404.1	398.2
55°	407.7	389.5	371.2	359.3	353.5	347.7	342.0	336.2
57.5°	346.3	329.5	312.8	302.0	297.2	292.3	287.5	282.6
60°	303.8	288.4	272.9	262.7	257.8	253.0	248.1	243.3
62.5°	267.1	252.3	237.6	228.6	225.8	222.8	219.9	217.0
65°	217.1	206.8	196.4	190.8	189.9	189.0	188.2	187.3
67.5°	175.3	170.6	165.8	162.9	162.0	161.0	160.1	159.1
70°	152.5	149.5	146.4	144.3	143.0	141.8	140.6	139.4
72.5°	132.7	130.1	127.5	125.9	125.2	124.5	123.7	123.0
75°	105.0	103.0	100.9	99.6	99.3	99.0	98.7	98.4
77.5°	79.5	78.4	77.1	76.2	75.8	75.3	74.8	74.4
80°	63.1	62.0	60.7	60.1	60.1	60.1	60.1	60.1
82.5°	47.7	47.0	46.3	45.9	45.9	45.9	45.9	45.9
85°	25.9	25.9	25.9	25.9	25.9	25.9	25.9	25.9
87.5°	14.4	14.1	13.7	13.6	13.6	13.7	13.7	13.8
90°	30.8	30.4	30.0	29.9	30.1	30.3	30.5	30.7
92.5°	28.9	29.0	29.1	29.1	29.2	29.2	29.2	29.2
95°	57.8	57.8	57.8	57.6	57.2	56.8	56.4	56.0
97.5°	97.2	97.2	97.2	97.2	97.1	97.1	97.0	97.0
100°	124.7	124.7	124.7	124.6	124.3	124.1	123.9	123.8
102.5°	154.6	154.7	154.9	154.9	154.7	154.4	154.3	154.1
105°	199.5	199.9	200.3	200.5	200.5	200.5	200.5	200.5
107.5°	248.0	248.2	248.3	247.9	247.0	246.0	245.1	244.2
110°	280.9	280.9	280.9	280.6	280.0	279.4	278.7	278.2



TEST NUMBER: P331856-940

CATALOG NUMBER: S122RDIW-S1005D970U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	313.9	313.4	312.9	312.5	312.0	311.6	311.1	310.7
115°	364.4	364.3	364.1	363.6	363.1	362.5	361.9	361.2
117.5°	413.4	413.0	412.4	411.9	411.3	410.7	410.1	409.5
120°	446.2	446.2	446.2	445.9	445.2	444.7	444.1	443.4
122.5°	479.9	479.4	478.9	478.5	478.0	477.6	477.2	476.7
125°	529.9	529.2	528.7	528.2	528.1	527.9	527.6	527.4
127.5°	578.4	577.7	576.9	576.2	575.6	575.0	574.4	573.7
130°	611.5	611.2	610.7	610.1	609.3	608.5	607.7	606.9
132.5°	643.8	642.9	642.0	641.3	640.7	640.0	639.4	638.7
135°	691.4	691.3	691.0	690.6	690.0	689.4	688.8	688.2
137.5°	737.0	736.9	736.7	736.2	735.4	734.6	733.8	733.0
140°	767.7	767.7	767.7	767.3	766.5	765.7	764.9	764.1
142.5°	795.5	795.7	795.8	795.5	794.7	793.9	793.1	792.3
145°	837.7	837.9	838.0	837.8	837.0	836.2	835.4	834.6
147.5°	874.6	875.0	875.5	875.3	874.6	873.8	873.1	872.3
150°	898.0	898.7	899.3	899.3	898.7	898.0	897.4	896.9
152.5°	921.5	922.3	923.0	923.0	922.3	921.5	920.7	920.0
155°	951.3	952.3	953.2	953.4	952.9	952.3	951.6	951.0
157.5°	978.7	980.1	981.4	981.6	980.7	979.7	978.7	977.8
160°	995.0	996.2	997.4	997.6	996.8	996.0	995.2	994.4
162.5°	1009.8	1011.1	1012.5	1012.7	1011.7	1010.8	1009.8	1008.9
165°	1028.9	1030.2	1031.6	1031.8	1030.8	1029.8	1028.9	1027.8
167.5°	1044.6	1046.0	1047.3	1047.5	1046.5	1045.4	1044.4	1043.4
170°	1053.2	1054.6	1056.1	1056.1	1054.9	1053.7	1052.5	1051.3
172.5°	1059.7	1061.1	1062.5	1062.7	1061.4	1060.2	1059.0	1057.8
175°	1066.8	1068.2	1069.5	1069.7	1068.4	1067.3	1066.0	1064.9
177.5°	1070.1	1070.9	1071.9	1071.9	1070.9	1070.1	1069.1	1068.1
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2

(END OF REPORT)