

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331505-935

Luminaire Tested: **S122DIW-S485D710U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331505-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S485D710U935-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4144.6 lumens  
Efficiency: N/A  
Efficacy: 110.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331505-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331505-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	50	42	36	56	45	38	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10797	10797	10797
5°	10838	10682	10746
10°	10775	10575	10627
15°	10641	10437	10425
20°	10452	10232	10220
25°	10265	9978	9978
30°	10023	9747	9661
35°	9798	9469	9329
40°	9514	9190	9012
45°	9236	8912	8690
50°	8932	8626	8317
55°	8617	8290	7983
60°	8263	7892	7598
65°	7885	7492	7148
70°	7407	7010	6680
75°	6744	6457	6301
80°	5979	5793	5504
85°	4872	4650	4168



TEST NUMBER: P331505-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.9	1.5
10°-20°	176.9	4.3
20°-30°	260.1	6.3
30°-40°	302.1	7.3
40°-50°	301.8	7.3
50°-60°	263.2	6.3
60°-70°	194.6	4.7
70°-80°	110.2	2.7
80°-90°	31.7	0.8
90°-100°	27.8	0.7
100°-110°	101.9	2.5
110°-120°	272.4	6.6
120°-130°	449.6	10.8
130°-140°	478.2	11.5
140°-150°	444.4	10.7
150°-160°	357.3	8.6
160°-170°	230.3	5.6
170°-180°	79.3	1.9
0°-30°	499.9	12.1
0°-40°	802.0	19.4
0°-60°	1366.9	33.0
0°-90°	1703.4	41.1
90°-120°	402.1	9.7
90°-150°	1774.3	42.8
90°-180°	2441.0	58.9
0°-180°	4144.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	669	669	669	669	669	
5°	669	666	659	664	663	63
15°	637	632	624	627	624	179
25°	576	571	560	561	560	265
35°	497	490	480	476	473	310
45°	404	400	390	384	381	312
55°	306	302	294	287	284	274
65°	206	202	196	190	187	204
75°	108	107	104	100	101	115
85°	26	26	25	23	22	30
90°	1	7	12	15	16	3
95°	39	21	24	26	26	48
105°	183	191	37	43	46	196
115°	347	357	372	106	49	341
125°	490	498	509	513	515	437
135°	606	616	622	627	626	468
145°	703	703	713	717	714	440
155°	775	770	776	779	775	357
165°	816	813	814	818	814	230
175°	835	831	832	835	830	79
180°	833	833	833	833	833	



TEST NUMBER: P331505-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7
2.5°	671.8	671.2	670.7	670.1	669.5	668.7	667.4	666.2	664.9	663.6	664.8
5°	668.7	668.1	667.6	667.0	666.5	665.4	663.8	662.3	660.6	659.1	660.2
7.5°	662.8	661.9	661.1	660.1	659.3	658.1	656.4	654.9	653.2	651.6	652.8
10°	657.2	656.2	655.1	654.2	653.2	651.8	650.1	648.4	646.7	645.0	646.1
12.5°	649.5	648.6	647.6	646.8	645.9	644.6	642.9	641.2	639.5	637.7	638.5
15°	636.6	635.8	634.9	634.0	633.2	631.8	629.9	628.1	626.2	624.4	624.9
17.5°	620.1	619.3	618.5	617.6	616.7	615.4	613.5	611.6	609.7	607.8	608.5
20°	608.3	607.4	606.6	605.7	604.9	603.5	601.4	599.4	597.4	595.5	595.9
22.5°	596.5	595.3	594.1	592.9	591.7	590.1	588.2	586.3	584.4	582.6	582.6
25°	576.2	575.0	573.9	572.7	571.6	569.8	567.4	564.9	562.5	560.1	560.3
27.5°	553.0	552.0	551.0	549.9	548.9	547.4	545.5	543.5	541.7	539.8	539.3
30°	537.6	536.4	535.3	534.2	533.0	531.3	529.2	527.1	525.0	522.8	522.4
32.5°	521.1	520.2	519.3	518.3	517.5	515.8	513.6	511.3	509.1	506.9	506.1
35°	497.1	495.6	494.2	492.8	491.4	489.5	487.2	484.9	482.6	480.4	479.5
37.5°	469.9	468.6	467.4	466.1	464.9	463.1	460.8	458.6	456.2	454.0	452.9
40°	451.4	450.2	449.1	448.0	446.9	445.1	442.8	440.6	438.2	436.0	434.7
42.5°	433.4	432.2	431.1	430.0	428.9	427.1	424.8	422.6	420.3	417.9	416.6
45°	404.5	403.5	402.4	401.5	400.5	398.9	396.7	394.6	392.4	390.3	388.7
47.5°	375.7	374.7	373.8	372.8	371.9	370.3	368.1	365.8	363.6	361.4	359.7
50°	355.6	354.9	354.1	353.4	352.8	351.4	349.4	347.4	345.3	343.4	341.4
52.5°	336.0	335.1	334.2	333.2	332.3	330.9	329.0	327.1	325.2	323.3	321.7
55°	306.1	305.2	304.4	303.5	302.6	301.4	299.6	297.9	296.2	294.5	292.8
57.5°	276.0	275.3	274.6	274.0	273.3	272.0	270.1	268.2	266.3	264.4	262.7
60°	255.9	255.4	254.8	254.2	253.7	252.4	250.4	248.3	246.3	244.4	242.8
62.5°	236.3	235.5	234.5	233.6	232.7	231.5	230.0	228.4	226.9	225.3	223.9
65°	206.4	205.5	204.7	203.8	203.0	201.8	200.4	199.0	197.5	196.1	194.8
67.5°	175.9	175.2	174.5	173.8	173.1	172.2	170.9	169.6	168.3	167.0	166.1
70°	156.9	156.4	155.8	155.2	154.6	153.7	152.4	151.1	149.8	148.5	147.6
72.5°	137.3	136.8	136.2	135.6	135.1	134.4	133.5	132.7	131.9	131.0	130.0
75°	108.1	107.7	107.5	107.2	106.9	106.4	105.6	105.0	104.3	103.5	102.6
77.5°	81.8	81.3	80.8	80.3	79.8	79.5	79.2	78.9	78.6	78.4	77.9
80°	64.3	64.1	64.1	63.9	63.7	63.5	63.2	62.9	62.7	62.3	61.9
82.5°	47.9	47.8	47.8	47.8	47.7	47.6	47.4	47.3	47.1	46.9	46.4
85°	26.3	26.3	26.1	25.9	25.8	25.7	25.5	25.4	25.2	25.1	24.6
87.5°	9.4	9.5	9.5	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.4
90°	0.6	2.1	3.5	5.0	6.5	7.7	8.9	9.9	11.0	12.1	12.7
92.5°	12.1	12.1	11.9	11.8	11.6	11.9	12.4	12.9	13.4	13.9	14.3
95°	39.2	34.8	30.3	25.9	21.5	19.7	20.7	21.6	22.6	23.5	24.2
97.5°	77.7	65.3	52.9	40.4	27.9	22.8	25.0	27.1	29.3	31.4	32.0
100°	106.7	88.3	70.0	51.7	33.3	25.2	27.6	29.8	32.1	34.4	35.4
102.5°	138.5	134.7	130.7	126.8	123.0	111.5	92.5	73.4	54.3	35.3	36.7
105°	183.2	187.3	191.3	195.3	199.3	183.0	146.5	109.9	73.4	36.8	38.2
107.5°	234.2	237.5	240.7	243.9	247.2	226.9	183.0	139.2	95.3	51.5	49.9
110°	267.0	269.8	272.7	275.4	278.3	260.3	221.6	182.9	144.2	105.5	92.1



TEST NUMBER: P331505-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	297.9	300.4	302.9	305.3	307.8	304.3	294.7	285.2	275.6	266.0	217.2
115°	346.6	348.9	351.1	353.4	355.7	358.5	361.9	365.2	368.5	371.9	309.9
117.5°	390.1	392.6	395.2	397.7	400.3	402.7	405.0	407.3	409.6	411.9	396.9
120°	421.9	424.0	425.9	427.9	430.0	432.1	434.5	437.0	439.4	441.8	443.4
122.5°	448.9	451.1	453.1	455.3	457.4	459.8	462.4	465.0	467.6	470.3	471.2
125°	490.0	491.8	493.5	495.2	497.0	499.1	501.7	504.2	506.8	509.3	510.2
127.5°	527.3	529.2	531.2	533.0	535.0	536.9	538.8	540.7	542.6	544.5	545.9
130°	550.9	553.0	555.2	557.3	559.5	561.3	562.7	564.2	565.7	567.2	568.7
132.5°	575.1	576.9	578.7	580.5	582.3	583.9	585.4	586.9	588.4	589.9	591.1
135°	606.4	608.5	610.6	612.8	614.9	616.6	617.9	619.1	620.3	621.5	622.8
137.5°	638.1	639.6	641.1	642.6	644.0	645.5	646.9	648.2	649.6	651.0	652.3
140°	658.8	659.9	660.9	662.0	663.1	664.3	665.8	667.3	668.7	670.3	671.5
142.5°	676.1	677.1	678.1	679.1	680.0	681.3	683.0	684.8	686.4	688.1	689.2
145°	703.4	703.3	703.2	703.0	702.8	704.0	706.2	708.5	710.8	713.1	714.0
147.5°	727.1	726.7	726.2	725.7	725.1	726.0	728.2	730.5	732.7	734.9	735.7
150°	742.6	741.7	740.7	739.8	738.8	739.4	741.6	743.7	745.9	748.0	748.8
152.5°	755.6	754.6	753.5	752.4	751.4	751.9	754.0	756.0	758.0	760.1	760.9
155°	774.6	773.4	772.1	770.9	769.7	769.9	771.5	773.1	774.7	776.4	777.1
157.5°	789.4	788.3	787.3	786.3	785.3	785.3	786.4	787.6	788.7	789.8	790.7
160°	798.1	797.2	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1	798.8
162.5°	805.7	804.9	804.2	803.3	802.5	802.5	803.1	803.9	804.6	805.3	806.2
165°	816.1	815.3	814.5	813.7	812.9	812.7	813.1	813.5	813.9	814.3	815.3
167.5°	823.8	823.0	822.3	821.4	820.6	820.4	820.8	821.1	821.6	821.9	822.9
170°	828.2	827.3	826.6	825.8	824.9	824.7	824.9	825.3	825.5	825.8	826.7
172.5°	831.0	830.3	829.5	828.6	827.9	827.6	827.9	828.1	828.4	828.6	829.6
175°	834.8	833.9	832.9	832.0	831.0	830.7	831.0	831.3	831.6	831.8	832.8
177.5°	835.4	834.7	833.9	833.2	832.4	832.1	832.2	832.3	832.4	832.5	833.3
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331505-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7
2.5°	665.9	667.0	668.1	668.7	668.4	668.1	668.0	667.7
5°	661.4	662.5	663.7	664.1	663.8	663.5	663.2	663.0
7.5°	653.9	655.0	656.3	656.6	656.3	656.0	655.7	655.4
10°	647.2	648.4	649.5	649.9	649.5	649.0	648.6	648.2
12.5°	639.4	640.2	640.9	641.2	640.8	640.6	640.2	639.9
15°	625.5	626.1	626.6	626.5	625.9	625.2	624.5	623.7
17.5°	609.1	609.8	610.4	610.4	609.7	609.1	608.4	607.7
20°	596.3	596.8	597.2	597.1	596.5	595.9	595.4	594.8
22.5°	582.7	582.8	582.9	582.8	582.5	582.1	581.8	581.4
25°	560.7	560.9	561.2	561.2	560.9	560.7	560.3	560.1
27.5°	538.9	538.5	538.0	537.5	536.8	536.1	535.5	534.8
30°	521.9	521.5	521.1	520.6	520.0	519.4	518.8	518.2
32.5°	505.3	504.5	503.8	503.1	502.5	502.0	501.4	500.8
35°	478.6	477.8	476.9	476.1	475.4	474.7	474.0	473.3
37.5°	451.9	450.8	449.8	448.8	448.2	447.5	446.8	446.2
40°	433.4	432.1	430.8	429.9	429.3	428.8	428.2	427.6
42.5°	415.2	413.8	412.3	411.3	410.4	409.7	408.9	408.0
45°	387.2	385.6	384.0	383.0	382.4	381.9	381.3	380.6
47.5°	358.1	356.4	354.7	353.5	352.7	351.9	351.0	350.2
50°	339.4	337.3	335.4	334.0	333.3	332.6	331.8	331.1
52.5°	320.0	318.3	316.7	315.4	314.4	313.5	312.5	311.6
55°	291.1	289.4	287.7	286.5	285.7	285.0	284.3	283.6
57.5°	261.1	259.3	257.7	256.6	256.0	255.5	254.9	254.3
60°	241.2	239.6	238.1	237.0	236.6	236.2	235.7	235.3
62.5°	222.4	220.9	219.5	218.5	217.9	217.4	216.9	216.3
65°	193.6	192.3	191.0	189.9	189.2	188.6	187.9	187.1
67.5°	165.1	164.0	163.1	162.3	161.7	161.1	160.6	160.0
70°	146.5	145.5	144.6	143.8	143.2	142.6	142.1	141.5
72.5°	129.1	128.0	127.1	126.3	125.9	125.4	124.9	124.5
75°	101.8	101.0	100.1	99.8	100.1	100.4	100.7	101.0
77.5°	77.5	77.1	76.6	76.2	75.8	75.4	75.0	74.6
80°	61.5	61.0	60.7	60.3	60.0	59.8	59.4	59.2
82.5°	45.9	45.3	44.8	44.4	44.4	44.3	44.3	44.3
85°	24.2	23.8	23.3	23.1	22.9	22.8	22.6	22.5
87.5°	9.2	9.0	8.8	8.6	8.6	8.5	8.4	8.4
90°	13.4	14.0	14.7	15.2	15.5	15.8	16.0	16.3
92.5°	14.7	15.1	15.4	15.7	15.8	15.9	16.1	16.3
95°	24.9	25.5	26.2	26.4	26.3	26.2	26.1	25.9
97.5°	32.5	33.1	33.6	33.9	34.1	34.3	34.4	34.6
100°	36.5	37.5	38.7	39.3	39.6	39.9	40.1	40.4
102.5°	38.1	39.5	40.9	41.8	42.2	42.5	42.9	43.3
105°	39.7	41.2	42.6	43.7	44.2	44.8	45.3	45.8
107.5°	48.5	47.0	45.5	45.0	45.5	46.1	46.6	47.1
110°	78.7	65.3	51.9	45.5	46.0	46.6	47.1	47.6





TEST NUMBER: P331505-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.3	119.5	70.6	46.4	46.8	47.3	47.7	48.1
115°	247.9	185.8	123.8	88.0	78.4	68.7	59.1	49.4
117.5°	381.9	366.9	351.9	328.6	296.9	265.2	233.5	201.8
120°	445.1	446.6	448.2	440.0	421.9	403.8	385.7	367.6
122.5°	472.2	473.1	474.2	472.9	469.3	465.8	462.4	458.8
125°	511.2	512.1	513.1	513.8	514.1	514.5	515.0	515.3
127.5°	547.3	548.6	550.0	550.7	550.8	550.9	551.0	551.0
130°	570.2	571.6	573.1	573.8	573.6	573.5	573.3	573.3
132.5°	592.4	593.7	594.9	595.5	595.3	595.2	595.0	595.0
135°	624.1	625.4	626.8	627.3	627.1	626.8	626.5	626.3
137.5°	653.6	654.9	656.3	656.7	656.2	655.7	655.3	654.8
140°	672.7	673.9	675.1	675.4	674.7	674.0	673.3	672.7
142.5°	690.3	691.4	692.5	692.7	692.1	691.4	690.7	690.0
145°	714.9	715.8	716.8	717.0	716.3	715.6	714.9	714.3
147.5°	736.4	737.1	737.8	737.9	737.3	736.8	736.2	735.6
150°	749.6	750.4	751.2	751.3	750.6	749.9	749.2	748.6
152.5°	761.6	762.5	763.3	763.3	762.3	761.5	760.6	759.7
155°	777.9	778.8	779.5	779.4	778.3	777.3	776.2	775.2
157.5°	791.7	792.6	793.5	793.4	792.4	791.3	790.3	789.2
160°	799.6	800.5	801.2	801.2	800.2	799.3	798.4	797.5
162.5°	807.1	808.0	808.9	808.8	807.6	806.5	805.3	804.2
165°	816.2	817.1	818.0	818.0	817.1	816.2	815.3	814.3
167.5°	823.8	824.8	825.6	825.5	824.3	823.1	821.9	820.7
170°	827.7	828.5	829.5	829.4	828.2	827.0	825.8	824.6
172.5°	830.5	831.5	832.4	832.2	831.0	829.8	828.6	827.4
175°	833.7	834.6	835.5	835.3	834.0	832.7	831.3	830.0
177.5°	834.1	834.7	835.5	835.4	834.5	833.4	832.5	831.6
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0

(END OF REPORT)