

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331544-935

Luminaire Tested: **S122DIW-S675D1240U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331544-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1240U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6227.6 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41						41														
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35						35														
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35	30						30														
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26						26														
4	74	63	56	50	67	58	51	46	48	43	40	39	36	33	31	28	26	22						22														
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20						20														
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18						18														
7	58	46	38	33	53	42	36	31	36	30	27	29	25	22	23	20	18	16						16														
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17	14						14														
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13						13														
10	47	35	28	23	43	32	26	22	27	23	19	23	19	16	18	16	14	12						12														

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	18466	18466	18466	18466
5°	20702	18585	16470	18585
10°	23722	18433	14254	18433
15°	26242	18094	12593	18094
20°	25844	17732	11478	17732
25°	23302	17250	10774	17250
30°	19257	16479	10260	16479
35°	14034	15672	9895	15672
40°	11209	14720	9691	14720
45°	9796	13618	9412	13618
50°	9206	12552	9231	12552
55°	8487	11468	8982	11468
60°	7776	10317	8603	10317
65°	7087	9287	8225	9287
70°	6430	8280	7676	8280
75°	5702	7155	6800	7155
80°	4909	5923	5477	5923
85°	4409	4409	3260	4409



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.9	1.7
10°-20°	316.6	5.1
20°-30°	459.5	7.4
30°-40°	484.9	7.8
40°-50°	429.4	6.9
50°-60°	342.6	5.5
60°-70°	232.9	3.7
70°-80°	119.4	1.9
80°-90°	34.1	0.5
90°-100°	83.8	1.3
100°-110°	260.4	4.2
110°-120°	445.0	7.1
120°-130°	585.3	9.4
130°-140°	656.9	10.5
140°-150°	644.1	10.3
150°-160°	540.2	8.7
160°-170°	358.3	5.8
170°-180°	125.2	2.0
0°-30°	885.1	14.2
0°-40°	1370.0	22.0
0°-60°	2142.0	34.4
0°-90°	2528.4	40.6
90°-120°	789.2	12.7
90°-150°	2675.4	43.0
90°-180°	3699.0	59.4
0°-180°	6227.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1144	1144	1144	1144	1144	
5°	1277	1147	1016	1147	1277	128
15°	1570	1082	753	1082	1570	433
25°	1308	968	605	968	1308	591
35°	712	795	502	795	712	463
45°	429	596	412	596	429	337
55°	302	407	319	407	302	270
65°	186	243	215	243	186	184
75°	91	115	109	115	91	98
85°	24	24	18	24	24	27
90°	38	1	38	1	38	18
95°	69	58	69	58	69	77
105°	248	240	248	240	248	261
115°	447	447	447	447	447	441
125°	652	650	652	650	652	581
135°	851	841	851	841	851	655
145°	1032	1020	1032	1020	1032	644
155°	1176	1167	1176	1167	1176	541
165°	1270	1269	1270	1269	1270	358
175°	1316	1321	1316	1321	1316	125
180°	1323	1323	1323	1323	1323	



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1196.4	1196.7	1197.5	1191.8	1191.1	1191.1	1186.2	1182.0	1177.1	1170.4	1171.0
5°	1277.3	1282.1	1283.8	1278.6	1270.7	1269.8	1262.3	1250.0	1238.5	1229.3	1222.8
7.5°	1373.8	1375.7	1371.4	1364.4	1358.6	1348.1	1334.1	1320.5	1301.4	1283.9	1270.9
10°	1446.9	1449.6	1442.1	1432.0	1423.7	1411.4	1391.1	1370.5	1345.4	1321.2	1301.8
12.5°	1502.4	1509.0	1499.4	1498.1	1483.8	1466.9	1442.8	1432.4	1397.1	1363.4	1342.6
15°	1569.9	1569.5	1570.5	1562.1	1551.5	1548.9	1523.4	1495.7	1446.0	1426.2	1392.0
17.5°	1550.5	1557.1	1560.2	1560.1	1559.9	1558.2	1550.1	1532.6	1507.7	1475.6	1436.0
20°	1504.1	1512.9	1514.2	1524.3	1530.0	1537.5	1540.5	1535.7	1520.4	1493.5	1459.2
22.5°	1432.4	1434.8	1438.9	1454.7	1467.1	1485.7	1495.6	1511.8	1505.9	1492.8	1464.1
25°	1308.0	1303.6	1319.1	1326.9	1355.5	1385.3	1407.0	1430.6	1451.7	1464.5	1456.1
27.5°	1158.7	1152.2	1175.2	1196.2	1219.4	1251.8	1285.4	1325.0	1358.0	1399.2	1413.3
30°	1032.9	1036.8	1058.9	1081.2	1116.4	1162.1	1199.9	1243.5	1290.5	1336.6	1368.6
32.5°	897.2	912.4	926.3	960.6	991.5	1042.6	1097.9	1152.4	1211.0	1263.4	1313.1
35°	712.0	729.6	749.0	774.0	817.5	868.1	922.1	995.5	1075.6	1147.2	1206.1
37.5°	599.3	596.5	607.6	625.7	661.0	701.7	764.0	836.5	930.7	1014.9	1097.9
40°	531.8	530.0	538.0	554.7	581.5	611.4	665.9	729.6	817.1	919.9	1018.8
42.5°	485.4	486.5	490.9	502.7	521.0	545.6	586.4	640.7	720.7	817.6	923.9
45°	429.0	432.0	436.9	442.6	453.1	473.4	496.2	534.9	598.2	679.1	783.7
47.5°	388.4	388.5	393.4	398.4	404.7	416.0	434.7	458.9	503.6	569.5	659.4
50°	366.5	363.5	367.0	370.9	377.5	385.5	397.8	420.6	450.5	503.7	578.9
52.5°	339.8	339.9	343.1	344.6	350.5	358.3	369.6	385.5	412.5	454.1	515.9
55°	301.5	303.7	305.5	308.1	313.4	319.1	327.9	338.5	359.6	390.7	436.4
57.5°	265.4	266.1	267.9	272.9	276.3	281.5	289.9	299.5	313.2	336.3	370.7
60°	240.8	240.8	244.4	246.6	251.0	256.2	262.9	272.1	284.4	303.2	331.0
62.5°	218.3	218.0	219.4	223.0	226.4	231.3	237.9	245.7	257.3	274.1	296.9
65°	185.5	184.6	187.3	188.1	191.7	196.5	201.7	210.1	219.3	231.6	251.8
67.5°	153.9	154.9	156.3	158.0	159.9	165.0	168.5	174.4	182.2	192.4	206.1
70°	136.2	136.2	136.2	137.6	140.2	142.8	146.4	151.2	158.7	167.5	179.8
72.5°	116.6	118.0	119.3	118.6	121.9	123.5	127.7	130.4	137.6	143.2	154.1
75°	91.4	91.4	91.4	93.6	95.0	96.3	98.9	101.5	105.0	112.1	117.8
77.5°	68.2	68.0	68.4	69.0	70.4	72.0	72.8	75.2	78.4	81.6	86.5
80°	52.8	53.6	54.1	54.9	54.9	55.8	56.2	59.3	61.6	63.7	66.8
82.5°	40.8	41.0	41.1	41.2	41.6	42.1	43.2	44.3	45.0	46.8	49.2
85°	23.8	23.3	23.3	24.2	23.8	23.8	24.6	25.5	25.5	25.9	27.2
87.5°	16.7	16.7	17.0	16.6	16.5	16.9	17.0	16.8	17.2	17.7	17.0
90°	38.0	37.7	37.5	37.2	36.9	37.1	37.6	38.1	38.6	39.1	33.6
92.5°	36.2	36.2	36.1	36.0	36.0	35.9	35.8	35.7	35.6	35.5	34.2
95°	69.2	69.7	70.2	70.7	71.2	71.5	71.5	71.5	71.5	71.5	70.9
97.5°	119.9	119.9	120.0	120.0	120.1	120.1	120.1	120.1	120.1	120.1	119.2
100°	152.9	153.2	153.4	153.7	153.9	154.0	154.0	154.0	154.0	154.0	153.3
102.5°	190.5	190.7	191.0	191.2	191.5	191.5	191.3	191.1	190.9	190.7	189.8
105°	247.9	247.9	247.9	247.9	247.9	247.6	247.1	246.6	246.1	245.6	245.1
107.5°	301.9	303.0	304.2	305.3	306.4	306.9	306.7	306.5	306.3	306.1	306.1
110°	343.9	344.6	345.3	346.1	346.8	347.2	347.2	347.2	347.2	347.2	347.2



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	384.0	384.6	385.1	385.6	386.2	386.8	387.4	388.0	388.6	389.2	389.3
115°	446.6	447.3	448.1	448.8	449.5	450.0	450.3	450.6	450.8	451.0	451.5
117.5°	506.2	507.0	507.6	508.4	509.2	509.8	510.4	511.0	511.6	512.2	513.6
120°	548.2	548.9	549.7	550.4	551.1	551.5	551.5	551.5	551.5	551.5	553.5
122.5°	589.3	589.8	590.3	590.9	591.4	592.0	592.6	593.2	593.7	594.3	595.7
125°	651.9	652.2	652.5	652.7	653.0	653.5	654.2	655.0	655.7	656.4	657.2
127.5°	709.1	710.0	710.8	711.5	712.3	713.2	714.0	715.0	715.8	716.7	717.6
130°	750.2	751.2	752.3	753.2	754.2	754.9	755.4	756.0	756.4	756.9	757.4
132.5°	789.5	790.3	791.1	791.9	792.7	793.7	794.7	795.8	796.9	798.0	797.9
135°	850.7	851.4	852.2	852.9	853.7	854.2	854.5	854.7	854.9	855.1	854.7
137.5°	906.1	907.1	908.1	909.0	910.1	910.7	910.9	911.0	911.3	911.5	910.8
140°	944.5	945.5	946.5	947.4	948.5	948.9	948.9	948.9	948.9	948.9	947.7
142.5°	979.3	980.3	981.3	982.3	983.3	983.7	983.5	983.3	983.1	982.9	982.1
145°	1031.6	1032.6	1033.5	1034.6	1035.5	1035.9	1035.7	1035.4	1035.2	1034.9	1033.5
147.5°	1078.2	1079.2	1080.1	1081.1	1082.0	1082.2	1081.7	1081.1	1080.6	1080.0	1079.0
150°	1108.6	1109.3	1110.1	1110.9	1111.6	1111.6	1110.9	1110.1	1109.3	1108.6	1107.6
152.5°	1137.2	1138.2	1139.1	1140.0	1140.9	1140.9	1140.0	1139.1	1138.2	1137.2	1136.0
155°	1175.6	1176.3	1177.1	1177.8	1178.5	1178.3	1177.1	1175.9	1174.6	1173.4	1172.6
157.5°	1208.6	1209.8	1211.0	1212.2	1213.4	1213.1	1211.4	1209.8	1208.1	1206.4	1205.9
160°	1229.2	1230.2	1231.1	1232.2	1233.1	1232.9	1231.4	1229.9	1228.4	1226.9	1226.7
162.5°	1247.1	1248.2	1249.4	1250.6	1251.8	1251.5	1249.8	1248.2	1246.5	1244.8	1244.6
165°	1270.5	1271.7	1273.0	1274.2	1275.4	1275.2	1273.4	1271.7	1270.0	1268.3	1268.3
167.5°	1289.7	1291.0	1292.3	1293.6	1294.9	1294.6	1292.9	1291.2	1289.4	1287.6	1287.7
170°	1299.5	1301.0	1302.5	1304.0	1305.4	1305.4	1303.6	1301.8	1300.1	1298.4	1298.6
172.5°	1307.5	1309.1	1310.5	1312.0	1313.5	1313.4	1311.6	1309.9	1308.2	1306.4	1306.7
175°	1316.2	1317.8	1319.2	1320.7	1322.2	1322.1	1320.3	1318.6	1316.9	1315.1	1315.6
177.5°	1320.3	1321.5	1322.7	1323.9	1325.0	1325.0	1323.9	1322.7	1321.5	1320.3	1320.7
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1173.5	1170.7	1169.0	1162.6	1157.0	1151.4	1149.6	1150.3	1142.6	1135.2	1132.0
5°	1219.3	1210.5	1202.1	1190.2	1176.2	1160.8	1152.9	1146.7	1131.4	1114.7	1105.0
7.5°	1260.2	1247.7	1231.6	1209.2	1188.8	1164.6	1149.2	1135.6	1113.0	1089.5	1075.0
10°	1285.2	1268.0	1247.3	1220.1	1195.1	1165.6	1145.0	1124.3	1097.9	1069.8	1052.2
12.5°	1306.7	1283.5	1263.2	1228.2	1198.6	1161.7	1137.2	1108.1	1080.4	1047.0	1029.8
15°	1357.7	1315.1	1276.3	1236.8	1200.3	1148.9	1121.7	1082.5	1046.0	1004.8	985.0
17.5°	1397.1	1349.3	1288.3	1238.0	1195.5	1138.6	1098.5	1051.7	1008.6	961.3	934.4
20°	1419.7	1364.7	1299.2	1239.5	1188.4	1123.4	1080.0	1032.0	981.5	928.2	899.2
22.5°	1433.0	1375.3	1310.5	1234.2	1174.4	1111.1	1056.4	1003.8	952.6	895.3	864.8
25°	1437.3	1384.5	1316.0	1229.8	1156.8	1085.2	1019.3	968.3	906.3	852.6	808.3
27.5°	1416.3	1378.5	1312.6	1221.5	1136.5	1052.7	979.3	921.5	856.1	797.9	753.3
30°	1390.7	1368.6	1304.5	1213.1	1120.3	1030.3	949.3	883.9	818.8	759.9	714.2
32.5°	1350.9	1346.2	1289.8	1201.1	1103.1	1001.8	918.1	851.9	779.8	721.9	678.4
35°	1272.9	1294.0	1258.4	1174.4	1070.7	961.2	870.7	795.1	720.4	665.0	624.1
37.5°	1168.3	1220.6	1211.3	1135.3	1026.9	917.1	817.2	738.1	666.9	611.1	570.9
40°	1096.1	1163.0	1172.7	1105.4	996.0	883.0	777.1	698.4	629.0	578.0	537.5
42.5°	1018.8	1096.9	1123.4	1069.5	962.2	847.1	741.2	659.7	591.0	541.4	505.6
45°	889.2	992.5	1040.3	1009.6	905.9	788.1	679.1	596.4	534.0	487.4	459.8
47.5°	767.9	880.8	945.2	934.4	843.2	726.5	618.8	539.5	478.7	441.5	416.7
50°	682.2	798.1	876.0	879.5	798.1	682.6	574.5	499.7	443.9	409.2	389.0
52.5°	607.6	718.3	803.2	821.8	747.9	636.9	534.8	460.4	411.2	379.3	361.2
55°	510.3	603.9	697.9	732.3	672.9	567.4	472.9	407.4	361.3	339.3	323.5
57.5°	424.2	502.3	589.2	627.1	590.5	500.2	411.6	354.7	317.3	298.0	285.9
60°	378.8	440.4	517.7	563.0	531.4	451.0	373.6	319.5	288.8	271.6	260.2
62.5°	336.7	391.2	456.6	498.0	480.8	404.9	335.6	287.9	261.3	245.2	237.0
65°	277.8	320.9	371.4	409.7	398.2	340.6	284.0	243.1	222.0	209.2	202.6
67.5°	228.8	259.8	294.9	328.4	319.2	278.4	232.9	201.0	185.3	174.4	170.4
70°	197.8	221.5	252.7	279.6	272.1	238.7	202.6	175.4	161.8	152.5	148.5
72.5°	168.2	187.8	211.5	233.5	228.4	200.7	170.7	150.1	139.6	131.0	127.8
75°	127.0	142.0	156.4	171.0	169.6	148.1	130.5	114.7	106.3	99.8	98.4
77.5°	93.8	102.1	112.0	120.6	118.2	105.9	92.1	83.1	76.9	72.5	71.8
80°	71.6	76.5	83.5	89.6	86.6	81.3	70.3	63.7	59.3	54.9	53.2
82.5°	51.9	56.8	61.0	64.3	62.0	57.1	50.3	45.8	43.1	40.2	39.4
85°	27.2	29.9	31.7	32.5	31.7	28.6	25.5	23.8	21.5	20.2	19.8
87.5°	16.2	15.1	14.0	13.9	12.2	11.6	9.6	7.9	8.2	8.4	8.4
90°	28.2	22.7	17.2	13.0	10.1	7.1	4.1	1.1	4.1	7.1	10.1
92.5°	32.9	31.6	30.3	28.6	26.4	24.3	22.0	19.9	22.0	24.3	26.4
95°	70.4	70.0	69.5	68.0	65.5	63.0	60.5	58.0	60.5	63.0	65.5
97.5°	118.2	117.3	116.3	114.8	112.6	110.5	108.2	106.1	108.2	110.5	112.6
100°	152.6	151.8	151.1	149.7	147.7	145.8	143.8	141.8	143.8	145.8	147.7
102.5°	188.8	187.9	186.9	185.6	184.1	182.4	180.9	179.3	180.9	182.4	184.1
105°	244.6	244.1	243.7	243.0	242.3	241.5	240.7	240.0	240.7	241.5	242.3
107.5°	306.1	306.1	306.1	305.6	304.4	303.4	302.3	301.2	302.3	303.4	304.4
110°	347.2	347.2	347.2	346.5	345.0	343.5	342.0	340.5	342.0	343.5	345.0



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	389.6	389.8	389.9	389.3	387.9	386.3	384.9	383.4	384.9	386.3	387.9
115°	452.0	452.5	453.0	452.5	451.0	449.5	448.1	446.6	448.1	449.5	451.0
117.5°	515.0	516.3	517.8	517.5	515.5	513.5	511.5	509.5	511.5	513.5	515.5
120°	555.5	557.5	559.5	559.5	557.5	555.5	553.5	551.5	553.5	555.5	557.5
122.5°	597.2	598.6	599.9	599.4	597.0	594.7	592.3	589.9	592.3	594.7	597.0
125°	658.0	658.7	659.4	658.7	656.4	654.2	651.9	649.7	651.9	654.2	656.4
127.5°	718.5	719.5	720.3	719.4	716.5	713.7	710.8	708.0	710.8	713.7	716.5
130°	757.9	758.5	758.9	757.5	754.3	751.1	747.9	744.7	747.9	751.1	754.3
132.5°	797.8	797.7	797.6	796.3	793.6	791.0	788.3	785.7	788.3	791.0	793.6
135°	854.2	853.7	853.2	851.6	848.9	846.1	843.3	840.7	843.3	846.1	848.9
137.5°	910.2	909.5	908.9	907.4	905.2	902.9	900.7	898.5	900.7	902.9	905.2
140°	946.5	945.2	944.0	942.3	940.0	937.8	935.6	933.3	935.6	937.8	940.0
142.5°	981.2	980.3	979.5	978.0	975.8	973.5	971.3	969.1	971.3	973.5	975.8
145°	1031.9	1030.4	1029.0	1027.3	1025.6	1023.9	1022.2	1020.4	1022.2	1023.9	1025.6
147.5°	1078.1	1077.0	1076.1	1074.5	1072.5	1070.3	1068.2	1066.2	1068.2	1070.3	1072.5
150°	1106.6	1105.6	1104.7	1103.4	1101.9	1100.4	1098.9	1097.4	1098.9	1100.4	1101.9
152.5°	1134.8	1133.6	1132.4	1131.1	1129.5	1128.1	1126.6	1125.2	1126.6	1128.1	1129.5
155°	1171.8	1171.1	1170.4	1169.7	1168.9	1168.1	1167.4	1166.7	1167.4	1168.1	1168.9
157.5°	1205.5	1205.1	1204.6	1204.1	1203.7	1203.2	1202.6	1202.1	1202.6	1203.2	1203.7
160°	1226.4	1226.2	1226.0	1225.5	1225.1	1224.6	1224.1	1223.6	1224.1	1224.6	1225.1
162.5°	1244.3	1244.1	1243.8	1243.6	1243.5	1243.5	1243.4	1243.2	1243.4	1243.5	1243.5
165°	1268.3	1268.3	1268.3	1268.3	1268.6	1268.9	1269.1	1269.4	1269.1	1268.9	1268.6
167.5°	1287.8	1287.8	1287.9	1288.2	1289.0	1289.8	1290.5	1291.2	1290.5	1289.8	1289.0
170°	1298.9	1299.2	1299.4	1299.9	1300.6	1301.4	1302.1	1302.9	1302.1	1301.4	1300.6
172.5°	1306.9	1307.2	1307.4	1307.9	1308.6	1309.4	1310.2	1310.9	1310.2	1309.4	1308.6
175°	1316.1	1316.6	1317.2	1317.8	1318.4	1319.2	1320.0	1320.7	1320.0	1319.2	1318.4
177.5°	1321.0	1321.5	1321.9	1322.3	1322.9	1323.5	1324.1	1324.7	1324.1	1323.5	1322.9
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1128.5	1126.4	1119.0	1115.2	1108.8	1102.9	1099.0	1100.8	1102.2	1101.5	1100.4
5°	1096.1	1087.8	1075.0	1064.1	1056.2	1041.6	1035.5	1032.4	1029.8	1026.7	1023.6
7.5°	1057.7	1044.5	1026.2	1010.6	995.7	977.8	967.5	961.3	955.0	948.0	941.9
10°	1030.3	1011.8	992.5	970.4	952.9	936.6	922.1	912.5	903.7	895.4	889.2
12.5°	1001.4	980.2	956.2	926.2	906.8	883.6	881.3	864.3	850.6	845.4	838.2
15°	955.5	925.7	895.4	859.7	844.3	823.2	810.0	796.9	785.0	776.6	774.5
17.5°	903.4	864.7	834.6	809.0	783.8	762.2	750.0	739.4	729.7	718.5	717.0
20°	863.7	830.3	797.3	774.9	749.0	726.9	712.0	701.5	693.1	686.6	680.8
22.5°	826.0	789.5	759.3	734.8	709.2	691.5	679.7	669.5	662.5	655.2	649.9
25°	765.7	737.1	704.1	676.4	655.3	643.9	634.2	625.4	621.0	616.2	610.1
27.5°	712.8	681.1	650.2	628.8	610.3	600.1	593.2	587.3	583.2	580.3	576.9
30°	675.5	643.4	619.3	598.2	582.8	572.7	568.3	564.8	560.0	558.2	556.5
32.5°	639.7	610.8	590.1	571.8	557.2	550.5	546.5	543.4	539.6	537.8	534.3
35°	588.9	564.8	544.6	534.4	522.6	516.9	513.8	509.4	505.9	504.1	503.7
37.5°	541.2	520.2	507.0	494.0	489.0	485.4	481.2	478.2	477.2	476.9	476.5
40°	510.3	493.2	481.3	470.7	468.6	463.2	459.8	457.1	457.1	457.5	457.1
42.5°	482.2	466.7	456.3	447.2	444.6	441.4	437.9	437.7	438.5	440.0	438.5
45°	439.5	428.5	421.0	416.6	411.8	408.7	408.3	409.7	410.1	410.5	411.8
47.5°	400.3	393.0	386.2	381.4	379.3	378.8	378.2	380.6	382.6	383.4	385.5
50°	377.1	368.8	363.1	360.0	358.2	357.3	358.2	360.8	362.6	364.8	366.1
52.5°	351.1	345.2	341.2	338.9	338.2	338.7	338.9	341.9	344.7	345.4	346.1
55°	315.1	310.7	309.9	305.9	307.6	307.2	309.4	311.2	313.8	316.4	316.9
57.5°	279.3	275.8	273.4	273.7	274.2	276.2	278.0	281.1	284.0	286.7	287.0
60°	255.4	253.6	252.3	252.3	253.1	255.8	258.0	261.1	262.9	264.6	265.9
62.5°	233.6	231.8	230.5	231.2	233.5	235.1	237.6	239.3	241.0	242.8	243.4
65°	199.1	198.2	199.6	200.4	200.9	203.0	206.1	207.4	209.2	210.1	213.2
67.5°	167.4	167.6	167.4	168.6	171.2	171.7	174.6	177.6	178.0	179.7	181.7
70°	145.9	146.8	147.7	148.5	150.8	151.6	153.9	155.2	156.9	158.3	159.5
72.5°	126.2	126.4	127.3	127.1	129.0	130.9	132.8	134.1	135.8	137.5	138.8
75°	97.1	97.1	98.0	98.4	100.7	102.9	102.4	103.3	105.0	106.8	107.7
77.5°	70.9	70.0	70.9	71.4	72.1	74.0	74.3	75.5	77.5	76.9	77.9
80°	54.1	52.8	54.1	54.5	54.5	56.7	56.7	57.6	58.9	57.6	58.9
82.5°	38.6	38.0	38.9	39.0	39.7	39.8	40.6	40.7	42.0	41.4	42.0
85°	19.4	18.9	19.4	18.9	19.4	19.8	19.8	19.4	19.4	20.2	18.9
87.5°	8.6	9.0	9.8	10.9	11.6	12.4	12.0	11.8	11.7	10.9	10.9
90°	13.0	17.2	22.7	28.2	33.6	39.1	38.6	38.1	37.6	37.1	36.9
92.5°	28.6	30.3	31.6	32.9	34.2	35.5	35.6	35.7	35.8	35.9	36.0
95°	68.0	69.5	70.0	70.4	70.9	71.5	71.5	71.5	71.5	71.5	71.2
97.5°	114.8	116.3	117.3	118.2	119.2	120.1	120.1	120.1	120.1	120.1	120.1
100°	149.7	151.1	151.8	152.6	153.3	154.0	154.0	154.0	154.0	154.0	153.9
102.5°	185.6	186.9	187.9	188.8	189.8	190.7	190.9	191.1	191.3	191.5	191.5
105°	243.0	243.7	244.1	244.6	245.1	245.6	246.1	246.6	247.1	247.6	247.9
107.5°	305.6	306.1	306.1	306.1	306.1	306.1	306.3	306.5	306.7	306.9	306.4
110°	346.5	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	346.8



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	389.3	389.9	389.8	389.6	389.3	389.2	388.6	388.0	387.4	386.8	386.2
115°	452.5	453.0	452.5	452.0	451.5	451.0	450.8	450.6	450.3	450.0	449.5
117.5°	517.5	517.8	516.3	515.0	513.6	512.2	511.6	511.0	510.4	509.8	509.2
120°	559.5	559.5	557.5	555.5	553.5	551.5	551.5	551.5	551.5	551.5	551.1
122.5°	599.4	599.9	598.6	597.2	595.7	594.3	593.7	593.2	592.6	592.0	591.4
125°	658.7	659.4	658.7	658.0	657.2	656.4	655.7	655.0	654.2	653.5	653.0
127.5°	719.4	720.3	719.5	718.5	717.6	716.7	715.8	715.0	714.0	713.2	712.3
130°	757.5	758.9	758.5	757.9	757.4	756.9	756.4	756.0	755.4	754.9	754.2
132.5°	796.3	797.6	797.7	797.8	797.9	798.0	796.9	795.8	794.7	793.7	792.7
135°	851.6	853.2	853.7	854.2	854.7	855.1	854.9	854.7	854.5	854.2	853.7
137.5°	907.4	908.9	909.5	910.2	910.8	911.5	911.3	911.0	910.9	910.7	910.1
140°	942.3	944.0	945.2	946.5	947.7	948.9	948.9	948.9	948.9	948.9	948.5
142.5°	978.0	979.5	980.3	981.2	982.1	982.9	983.1	983.3	983.5	983.7	983.3
145°	1027.3	1029.0	1030.4	1031.9	1033.5	1034.9	1035.2	1035.4	1035.7	1035.9	1035.5
147.5°	1074.5	1076.1	1077.0	1078.1	1079.0	1080.0	1080.6	1081.1	1081.7	1082.2	1082.0
150°	1103.4	1104.7	1105.6	1106.6	1107.6	1108.6	1109.3	1110.1	1110.9	1111.6	1111.6
152.5°	1131.1	1132.4	1133.6	1134.8	1136.0	1137.2	1138.2	1139.1	1140.0	1140.9	1140.9
155°	1169.7	1170.4	1171.1	1171.8	1172.6	1173.4	1174.6	1175.9	1177.1	1178.3	1178.5
157.5°	1204.1	1204.6	1205.1	1205.5	1205.9	1206.4	1208.1	1209.8	1211.4	1213.1	1213.4
160°	1225.5	1226.0	1226.2	1226.4	1226.7	1226.9	1228.4	1229.9	1231.4	1232.9	1233.1
162.5°	1243.6	1243.8	1244.1	1244.3	1244.6	1244.8	1246.5	1248.2	1249.8	1251.5	1251.8
165°	1268.3	1268.3	1268.3	1268.3	1268.3	1268.3	1270.0	1271.7	1273.4	1275.2	1275.4
167.5°	1288.2	1287.9	1287.8	1287.8	1287.7	1287.6	1289.4	1291.2	1292.9	1294.6	1294.9
170°	1299.9	1299.4	1299.2	1298.9	1298.6	1298.4	1300.1	1301.8	1303.6	1305.4	1305.4
172.5°	1307.9	1307.4	1307.2	1306.9	1306.7	1306.4	1308.2	1309.9	1311.6	1313.4	1313.5
175°	1317.8	1317.2	1316.6	1316.1	1315.6	1315.1	1316.9	1318.6	1320.3	1322.1	1322.2
177.5°	1322.3	1321.9	1321.5	1321.0	1320.7	1320.3	1321.5	1322.7	1323.9	1325.0	1325.0
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1096.9	1096.1	1096.1	1093.0	1096.1	1096.1	1096.9	1100.4	1101.5	1102.2	1100.8
5°	1017.5	1016.2	1014.0	1016.2	1014.0	1016.2	1017.5	1023.6	1026.7	1029.8	1032.4
7.5°	939.0	933.8	933.0	927.7	933.0	933.8	939.0	941.9	948.0	955.0	961.3
10°	881.7	878.1	877.7	869.4	877.7	878.1	881.7	889.2	895.4	903.7	912.5
12.5°	838.1	829.7	831.3	826.5	831.3	829.7	838.1	838.2	845.4	850.6	864.3
15°	762.6	762.6	760.8	753.4	760.8	762.6	762.6	774.5	776.6	785.0	796.9
17.5°	708.3	707.5	703.3	705.3	703.3	707.5	708.3	717.0	718.5	729.7	739.4
20°	676.0	673.4	668.0	668.0	668.0	673.4	676.0	680.8	686.6	693.1	701.5
22.5°	645.4	645.2	639.6	641.4	639.6	645.2	645.4	649.9	655.2	662.5	669.5
25°	609.6	606.1	603.5	604.8	603.5	606.1	609.6	610.1	616.2	621.0	625.4
27.5°	575.7	573.8	573.6	570.0	573.6	573.8	575.7	576.9	580.3	583.2	587.3
30°	556.0	551.6	552.5	550.3	552.5	551.6	556.0	556.5	558.2	560.0	564.8
32.5°	533.5	531.9	531.1	529.2	531.1	531.9	533.5	534.3	537.8	539.6	543.4
35°	502.8	503.3	501.1	502.0	501.1	503.3	502.8	503.7	504.1	505.9	509.4
37.5°	476.0	477.4	476.4	476.6	476.4	477.4	476.0	476.5	476.9	477.2	478.2
40°	458.4	458.4	458.4	459.8	458.4	458.4	458.4	457.1	457.5	457.1	457.1
42.5°	441.5	440.8	440.1	440.1	440.1	440.8	441.5	438.5	440.0	438.5	437.7
45°	412.7	414.1	414.5	412.2	414.5	414.1	412.7	411.8	410.5	410.1	409.7
47.5°	386.6	386.8	386.6	388.6	386.6	386.8	386.6	385.5	383.4	382.6	380.6
50°	368.3	367.5	368.3	367.5	368.3	367.5	368.3	366.1	364.8	362.6	360.8
52.5°	349.0	349.1	348.6	348.4	348.6	349.1	349.0	346.1	345.4	344.7	341.9
55°	318.7	319.5	319.1	319.1	319.1	319.5	318.7	316.9	316.4	313.8	311.2
57.5°	287.3	288.1	288.7	286.7	288.7	288.1	287.3	287.0	286.7	284.0	281.1
60°	265.4	267.7	267.3	266.4	267.3	267.7	265.4	265.9	264.6	262.9	261.1
62.5°	245.5	246.2	246.2	246.0	246.2	246.2	245.5	243.4	242.8	241.0	239.3
65°	214.5	215.3	214.0	215.3	214.0	215.3	214.5	213.2	210.1	209.2	207.4
67.5°	181.2	181.4	182.4	183.0	182.4	181.4	181.2	181.7	179.7	178.0	177.6
70°	160.4	160.0	161.3	162.6	161.3	160.0	160.4	159.5	158.3	156.9	155.2
72.5°	138.6	139.6	139.1	140.1	139.1	139.6	138.6	138.8	137.5	135.8	134.1
75°	106.8	108.1	107.7	109.0	107.7	108.1	106.8	107.7	106.8	105.0	103.3
77.5°	77.1	77.3	77.1	77.9	77.1	77.3	77.1	77.9	76.9	77.5	75.5
80°	58.9	58.0	57.2	58.9	57.2	58.0	58.9	58.9	57.6	58.9	57.6
82.5°	41.0	41.5	40.6	40.6	40.6	41.5	41.0	42.0	41.4	42.0	40.7
85°	18.9	18.4	17.6	17.6	17.6	18.4	18.9	18.9	20.2	19.4	19.4
87.5°	10.9	10.7	10.7	10.4	10.7	10.7	10.9	10.9	10.9	11.7	11.8
90°	37.2	37.5	37.7	38.0	37.7	37.5	37.2	36.9	37.1	37.6	38.1
92.5°	36.0	36.1	36.2	36.2	36.2	36.1	36.0	36.0	35.9	35.8	35.7
95°	70.7	70.2	69.7	69.2	69.7	70.2	70.7	71.2	71.5	71.5	71.5
97.5°	120.0	120.0	119.9	119.9	119.9	120.0	120.0	120.1	120.1	120.1	120.1
100°	153.7	153.4	153.2	152.9	153.2	153.4	153.7	153.9	154.0	154.0	154.0
102.5°	191.2	191.0	190.7	190.5	190.7	191.0	191.2	191.5	191.5	191.3	191.1
105°	247.9	247.9	247.9	247.9	247.9	247.9	247.9	247.9	247.6	247.1	246.6
107.5°	305.3	304.2	303.0	301.9	303.0	304.2	305.3	306.4	306.9	306.7	306.5
110°	346.1	345.3	344.6	343.9	344.6	345.3	346.1	346.8	347.2	347.2	347.2



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	385.6	385.1	384.6	384.0	384.6	385.1	385.6	386.2	386.8	387.4	388.0
115°	448.8	448.1	447.3	446.6	447.3	448.1	448.8	449.5	450.0	450.3	450.6
117.5°	508.4	507.6	507.0	506.2	507.0	507.6	508.4	509.2	509.8	510.4	511.0
120°	550.4	549.7	548.9	548.2	548.9	549.7	550.4	551.1	551.5	551.5	551.5
122.5°	590.9	590.3	589.8	589.3	589.8	590.3	590.9	591.4	592.0	592.6	593.2
125°	652.7	652.5	652.2	651.9	652.2	652.5	652.7	653.0	653.5	654.2	655.0
127.5°	711.5	710.8	710.0	709.1	710.0	710.8	711.5	712.3	713.2	714.0	715.0
130°	753.2	752.3	751.2	750.2	751.2	752.3	753.2	754.2	754.9	755.4	756.0
132.5°	791.9	791.1	790.3	789.5	790.3	791.1	791.9	792.7	793.7	794.7	795.8
135°	852.9	852.2	851.4	850.7	851.4	852.2	852.9	853.7	854.2	854.5	854.7
137.5°	909.0	908.1	907.1	906.1	907.1	908.1	909.0	910.1	910.7	910.9	911.0
140°	947.4	946.5	945.5	944.5	945.5	946.5	947.4	948.5	948.9	948.9	948.9
142.5°	982.3	981.3	980.3	979.3	980.3	981.3	982.3	983.3	983.7	983.5	983.3
145°	1034.6	1033.5	1032.6	1031.6	1032.6	1033.5	1034.6	1035.5	1035.9	1035.7	1035.4
147.5°	1081.1	1080.1	1079.2	1078.2	1079.2	1080.1	1081.1	1082.0	1082.2	1081.7	1081.1
150°	1110.9	1110.1	1109.3	1108.6	1109.3	1110.1	1110.9	1111.6	1111.6	1110.9	1110.1
152.5°	1140.0	1139.1	1138.2	1137.2	1138.2	1139.1	1140.0	1140.9	1140.9	1140.0	1139.1
155°	1177.8	1177.1	1176.3	1175.6	1176.3	1177.1	1177.8	1178.5	1178.3	1177.1	1175.9
157.5°	1212.2	1211.0	1209.8	1208.6	1209.8	1211.0	1212.2	1213.4	1213.1	1211.4	1209.8
160°	1232.2	1231.1	1230.2	1229.2	1230.2	1231.1	1232.2	1233.1	1232.9	1231.4	1229.9
162.5°	1250.6	1249.4	1248.2	1247.1	1248.2	1249.4	1250.6	1251.8	1251.5	1249.8	1248.2
165°	1274.2	1273.0	1271.7	1270.5	1271.7	1273.0	1274.2	1275.4	1275.2	1273.4	1271.7
167.5°	1293.6	1292.3	1291.0	1289.7	1291.0	1292.3	1293.6	1294.9	1294.6	1292.9	1291.2
170°	1304.0	1302.5	1301.0	1299.5	1301.0	1302.5	1304.0	1305.4	1305.4	1303.6	1301.8
172.5°	1312.0	1310.5	1309.1	1307.5	1309.1	1310.5	1312.0	1313.5	1313.4	1311.6	1309.9
175°	1320.7	1319.2	1317.8	1316.2	1317.8	1319.2	1320.7	1322.2	1322.1	1320.3	1318.6
177.5°	1323.9	1322.7	1321.5	1320.3	1321.5	1322.7	1323.9	1325.0	1325.0	1323.9	1322.7
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1099.0	1102.9	1108.8	1115.2	1119.0	1126.4	1128.5	1132.0	1135.2	1142.6	1150.3
5°	1035.5	1041.6	1056.2	1064.1	1075.0	1087.8	1096.1	1105.0	1114.7	1131.4	1146.7
7.5°	967.5	977.8	995.7	1010.6	1026.2	1044.5	1057.7	1075.0	1089.5	1113.0	1135.6
10°	922.1	936.6	952.9	970.4	992.5	1011.8	1030.3	1052.2	1069.8	1097.9	1124.3
12.5°	881.3	883.6	906.8	926.2	956.2	980.2	1001.4	1029.8	1047.0	1080.4	1108.1
15°	810.0	823.2	844.3	859.7	895.4	925.7	955.5	985.0	1004.8	1046.0	1082.5
17.5°	750.0	762.2	783.8	809.0	834.6	864.7	903.4	934.4	961.3	1008.6	1051.7
20°	712.0	726.9	749.0	774.9	797.3	830.3	863.7	899.2	928.2	981.5	1032.0
22.5°	679.7	691.5	709.2	734.8	759.3	789.5	826.0	864.8	895.3	952.6	1003.8
25°	634.2	643.9	655.3	676.4	704.1	737.1	765.7	808.3	852.6	906.3	968.3
27.5°	593.2	600.1	610.3	628.8	650.2	681.1	712.8	753.3	797.9	856.1	921.5
30°	568.3	572.7	582.8	598.2	619.3	643.4	675.5	714.2	759.9	818.8	883.9
32.5°	546.5	550.5	557.2	571.8	590.1	610.8	639.7	678.4	721.9	779.8	851.9
35°	513.8	516.9	522.6	534.4	544.6	564.8	588.9	624.1	665.0	720.4	795.1
37.5°	481.2	485.4	489.0	494.0	507.0	520.2	541.2	570.9	611.1	666.9	738.1
40°	459.8	463.2	468.6	470.7	481.3	493.2	510.3	537.5	578.0	629.0	698.4
42.5°	437.9	441.4	444.6	447.2	456.3	466.7	482.2	505.6	541.4	591.0	659.7
45°	408.3	408.7	411.8	416.6	421.0	428.5	439.5	459.8	487.4	534.0	596.4
47.5°	378.2	378.8	379.3	381.4	386.2	393.0	400.3	416.7	441.5	478.7	539.5
50°	358.2	357.3	358.2	360.0	363.1	368.8	377.1	389.0	409.2	443.9	499.7
52.5°	338.9	338.7	338.2	338.9	341.2	345.2	351.1	361.2	379.3	411.2	460.4
55°	309.4	307.2	307.6	305.9	309.9	310.7	315.1	323.5	339.3	361.3	407.4
57.5°	278.0	276.2	274.2	273.7	273.4	275.8	279.3	285.9	298.0	317.3	354.7
60°	258.0	255.8	253.1	252.3	252.3	253.6	255.4	260.2	271.6	288.8	319.5
62.5°	237.6	235.1	233.5	231.2	230.5	231.8	233.6	237.0	245.2	261.3	287.9
65°	206.1	203.0	200.9	200.4	199.6	198.2	199.1	202.6	209.2	222.0	243.1
67.5°	174.6	171.7	171.2	168.6	167.4	167.6	167.4	170.4	174.4	185.3	201.0
70°	153.9	151.6	150.8	148.5	147.7	146.8	145.9	148.5	152.5	161.8	175.4
72.5°	132.8	130.9	129.0	127.1	127.3	126.4	126.2	127.8	131.0	139.6	150.1
75°	102.4	102.9	100.7	98.4	98.0	97.1	97.1	98.4	99.8	106.3	114.7
77.5°	74.3	74.0	72.1	71.4	70.9	70.0	70.9	71.8	72.5	76.9	83.1
80°	56.7	56.7	54.5	54.5	54.1	52.8	54.1	53.2	54.9	59.3	63.7
82.5°	40.6	39.8	39.7	39.0	38.9	38.0	38.6	39.4	40.2	43.1	45.8
85°	19.8	19.8	19.4	18.9	19.4	18.9	19.4	19.8	20.2	21.5	23.8
87.5°	12.0	12.4	11.6	10.9	9.8	9.0	8.6	8.4	8.4	8.2	7.9
90°	38.6	39.1	33.6	28.2	22.7	17.2	13.0	10.1	7.1	4.1	1.1
92.5°	35.6	35.5	34.2	32.9	31.6	30.3	28.6	26.4	24.3	22.0	19.9
95°	71.5	71.5	70.9	70.4	70.0	69.5	68.0	65.5	63.0	60.5	58.0
97.5°	120.1	120.1	119.2	118.2	117.3	116.3	114.8	112.6	110.5	108.2	106.1
100°	154.0	154.0	153.3	152.6	151.8	151.1	149.7	147.7	145.8	143.8	141.8
102.5°	190.9	190.7	189.8	188.8	187.9	186.9	185.6	184.1	182.4	180.9	179.3
105°	246.1	245.6	245.1	244.6	244.1	243.7	243.0	242.3	241.5	240.7	240.0
107.5°	306.3	306.1	306.1	306.1	306.1	306.1	305.6	304.4	303.4	302.3	301.2
110°	347.2	347.2	347.2	347.2	347.2	347.2	346.5	345.0	343.5	342.0	340.5



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	388.6	389.2	389.3	389.6	389.8	389.9	389.3	387.9	386.3	384.9	383.4
115°	450.8	451.0	451.5	452.0	452.5	453.0	452.5	451.0	449.5	448.1	446.6
117.5°	511.6	512.2	513.6	515.0	516.3	517.8	517.5	515.5	513.5	511.5	509.5
120°	551.5	551.5	553.5	555.5	557.5	559.5	559.5	557.5	555.5	553.5	551.5
122.5°	593.7	594.3	595.7	597.2	598.6	599.9	599.4	597.0	594.7	592.3	589.9
125°	655.7	656.4	657.2	658.0	658.7	659.4	658.7	656.4	654.2	651.9	649.7
127.5°	715.8	716.7	717.6	718.5	719.5	720.3	719.4	716.5	713.7	710.8	708.0
130°	756.4	756.9	757.4	757.9	758.5	758.9	757.5	754.3	751.1	747.9	744.7
132.5°	796.9	798.0	797.9	797.8	797.7	797.6	796.3	793.6	791.0	788.3	785.7
135°	854.9	855.1	854.7	854.2	853.7	853.2	851.6	848.9	846.1	843.3	840.7
137.5°	911.3	911.5	910.8	910.2	909.5	908.9	907.4	905.2	902.9	900.7	898.5
140°	948.9	948.9	947.7	946.5	945.2	944.0	942.3	940.0	937.8	935.6	933.3
142.5°	983.1	982.9	982.1	981.2	980.3	979.5	978.0	975.8	973.5	971.3	969.1
145°	1035.2	1034.9	1033.5	1031.9	1030.4	1029.0	1027.3	1025.6	1023.9	1022.2	1020.4
147.5°	1080.6	1080.0	1079.0	1078.1	1077.0	1076.1	1074.5	1072.5	1070.3	1068.2	1066.2
150°	1109.3	1108.6	1107.6	1106.6	1105.6	1104.7	1103.4	1101.9	1100.4	1098.9	1097.4
152.5°	1138.2	1137.2	1136.0	1134.8	1133.6	1132.4	1131.1	1129.5	1128.1	1126.6	1125.2
155°	1174.6	1173.4	1172.6	1171.8	1171.1	1170.4	1169.7	1168.9	1168.1	1167.4	1166.7
157.5°	1208.1	1206.4	1205.9	1205.5	1205.1	1204.6	1204.1	1203.7	1203.2	1202.6	1202.1
160°	1228.4	1226.9	1226.7	1226.4	1226.2	1226.0	1225.5	1225.1	1224.6	1224.1	1223.6
162.5°	1246.5	1244.8	1244.6	1244.3	1244.1	1243.8	1243.6	1243.5	1243.5	1243.4	1243.2
165°	1270.0	1268.3	1268.3	1268.3	1268.3	1268.3	1268.3	1268.6	1268.9	1269.1	1269.4
167.5°	1289.4	1287.6	1287.7	1287.8	1287.8	1287.9	1288.2	1289.0	1289.8	1290.5	1291.2
170°	1300.1	1298.4	1298.6	1298.9	1299.2	1299.4	1299.9	1300.6	1301.4	1302.1	1302.9
172.5°	1308.2	1306.4	1306.7	1306.9	1307.2	1307.4	1307.9	1308.6	1309.4	1310.2	1310.9
175°	1316.9	1315.1	1315.6	1316.1	1316.6	1317.2	1317.8	1318.4	1319.2	1320.0	1320.7
177.5°	1321.5	1320.3	1320.7	1321.0	1321.5	1321.9	1322.3	1322.9	1323.5	1324.1	1324.7
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1149.6	1151.4	1157.0	1162.6	1169.0	1170.7	1173.5	1171.0	1170.4	1177.1	1182.0
5°	1152.9	1160.8	1176.2	1190.2	1202.1	1210.5	1219.3	1222.8	1229.3	1238.5	1250.0
7.5°	1149.2	1164.6	1188.8	1209.2	1231.6	1247.7	1260.2	1270.9	1283.9	1301.4	1320.5
10°	1145.0	1165.6	1195.1	1220.1	1247.3	1268.0	1285.2	1301.8	1321.2	1345.4	1370.5
12.5°	1137.2	1161.7	1198.6	1228.2	1263.2	1283.5	1306.7	1342.6	1363.4	1397.1	1432.4
15°	1121.7	1148.9	1200.3	1236.8	1276.3	1315.1	1357.7	1392.0	1426.2	1446.0	1495.7
17.5°	1098.5	1138.6	1195.5	1238.0	1288.3	1349.3	1397.1	1436.0	1475.6	1507.7	1532.6
20°	1080.0	1123.4	1188.4	1239.5	1299.2	1364.7	1419.7	1459.2	1493.5	1520.4	1535.7
22.5°	1056.4	1111.1	1174.4	1234.2	1310.5	1375.3	1433.0	1464.1	1492.8	1505.9	1511.8
25°	1019.3	1085.2	1156.8	1229.8	1316.0	1384.5	1437.3	1456.1	1464.5	1451.7	1430.6
27.5°	979.3	1052.7	1136.5	1221.5	1312.6	1378.5	1416.3	1413.3	1399.2	1358.0	1325.0
30°	949.3	1030.3	1120.3	1213.1	1304.5	1368.6	1390.7	1368.6	1336.6	1290.5	1243.5
32.5°	918.1	1001.8	1103.1	1201.1	1289.8	1346.2	1350.9	1313.1	1263.4	1211.0	1152.4
35°	870.7	961.2	1070.7	1174.4	1258.4	1294.0	1272.9	1206.1	1147.2	1075.6	995.5
37.5°	817.2	917.1	1026.9	1135.3	1211.3	1220.6	1168.3	1097.9	1014.9	930.7	836.5
40°	777.1	883.0	996.0	1105.4	1172.7	1163.0	1096.1	1018.8	919.9	817.1	729.6
42.5°	741.2	847.1	962.2	1069.5	1123.4	1096.9	1018.8	923.9	817.6	720.7	640.7
45°	679.1	788.1	905.9	1009.6	1040.3	992.5	889.2	783.7	679.1	598.2	534.9
47.5°	618.8	726.5	843.2	934.4	945.2	880.8	767.9	659.4	569.5	503.6	458.9
50°	574.5	682.6	798.1	879.5	876.0	798.1	682.2	578.9	503.7	450.5	420.6
52.5°	534.8	636.9	747.9	821.8	803.2	718.3	607.6	515.9	454.1	412.5	385.5
55°	472.9	567.4	672.9	732.3	697.9	603.9	510.3	436.4	390.7	359.6	338.5
57.5°	411.6	500.2	590.5	627.1	589.2	502.3	424.2	370.7	336.3	313.2	299.5
60°	373.6	451.0	531.4	563.0	517.7	440.4	378.8	331.0	303.2	284.4	272.1
62.5°	335.6	404.9	480.8	498.0	456.6	391.2	336.7	296.9	274.1	257.3	245.7
65°	284.0	340.6	398.2	409.7	371.4	320.9	277.8	251.8	231.6	219.3	210.1
67.5°	232.9	278.4	319.2	328.4	294.9	259.8	228.8	206.1	192.4	182.2	174.4
70°	202.6	238.7	272.1	279.6	252.7	221.5	197.8	179.8	167.5	158.7	151.2
72.5°	170.7	200.7	228.4	233.5	211.5	187.8	168.2	154.1	143.2	137.6	130.4
75°	130.5	148.1	169.6	171.0	156.4	142.0	127.0	117.8	112.1	105.0	101.5
77.5°	92.1	105.9	118.2	120.6	112.0	102.1	93.8	86.5	81.6	78.4	75.2
80°	70.3	81.3	86.6	89.6	83.5	76.5	71.6	66.8	63.7	61.6	59.3
82.5°	50.3	57.1	62.0	64.3	61.0	56.8	51.9	49.2	46.8	45.0	44.3
85°	25.5	28.6	31.7	32.5	31.7	29.9	27.2	27.2	25.9	25.5	25.5
87.5°	9.6	11.6	12.2	13.9	14.0	15.1	16.2	17.0	17.7	17.2	16.8
90°	4.1	7.1	10.1	13.0	17.2	22.7	28.2	33.6	39.1	38.6	38.1
92.5°	22.0	24.3	26.4	28.6	30.3	31.6	32.9	34.2	35.5	35.6	35.7
95°	60.5	63.0	65.5	68.0	69.5	70.0	70.4	70.9	71.5	71.5	71.5
97.5°	108.2	110.5	112.6	114.8	116.3	117.3	118.2	119.2	120.1	120.1	120.1
100°	143.8	145.8	147.7	149.7	151.1	151.8	152.6	153.3	154.0	154.0	154.0
102.5°	180.9	182.4	184.1	185.6	186.9	187.9	188.8	189.8	190.7	190.9	191.1
105°	240.7	241.5	242.3	243.0	243.7	244.1	244.6	245.1	245.6	246.1	246.6
107.5°	302.3	303.4	304.4	305.6	306.1	306.1	306.1	306.1	306.1	306.3	306.5
110°	342.0	343.5	345.0	346.5	347.2	347.2	347.2	347.2	347.2	347.2	347.2



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	384.9	386.3	387.9	389.3	389.9	389.8	389.6	389.3	389.2	388.6	388.0
115°	448.1	449.5	451.0	452.5	453.0	452.5	452.0	451.5	451.0	450.8	450.6
117.5°	511.5	513.5	515.5	517.5	517.8	516.3	515.0	513.6	512.2	511.6	511.0
120°	553.5	555.5	557.5	559.5	559.5	557.5	555.5	553.5	551.5	551.5	551.5
122.5°	592.3	594.7	597.0	599.4	599.9	598.6	597.2	595.7	594.3	593.7	593.2
125°	651.9	654.2	656.4	658.7	659.4	658.7	658.0	657.2	656.4	655.7	655.0
127.5°	710.8	713.7	716.5	719.4	720.3	719.5	718.5	717.6	716.7	715.8	715.0
130°	747.9	751.1	754.3	757.5	758.9	758.5	757.9	757.4	756.9	756.4	756.0
132.5°	788.3	791.0	793.6	796.3	797.6	797.7	797.8	797.9	798.0	796.9	795.8
135°	843.3	846.1	848.9	851.6	853.2	853.7	854.2	854.7	855.1	854.9	854.7
137.5°	900.7	902.9	905.2	907.4	908.9	909.5	910.2	910.8	911.5	911.3	911.0
140°	935.6	937.8	940.0	942.3	944.0	945.2	946.5	947.7	948.9	948.9	948.9
142.5°	971.3	973.5	975.8	978.0	979.5	980.3	981.2	982.1	982.9	983.1	983.3
145°	1022.2	1023.9	1025.6	1027.3	1029.0	1030.4	1031.9	1033.5	1034.9	1035.2	1035.4
147.5°	1068.2	1070.3	1072.5	1074.5	1076.1	1077.0	1078.1	1079.0	1080.0	1080.6	1081.1
150°	1098.9	1100.4	1101.9	1103.4	1104.7	1105.6	1106.6	1107.6	1108.6	1109.3	1110.1
152.5°	1126.6	1128.1	1129.5	1131.1	1132.4	1133.6	1134.8	1136.0	1137.2	1138.2	1139.1
155°	1167.4	1168.1	1168.9	1169.7	1170.4	1171.1	1171.8	1172.6	1173.4	1174.6	1175.9
157.5°	1202.6	1203.2	1203.7	1204.1	1204.6	1205.1	1205.5	1205.9	1206.4	1208.1	1209.8
160°	1224.1	1224.6	1225.1	1225.5	1226.0	1226.2	1226.4	1226.7	1226.9	1228.4	1229.9
162.5°	1243.4	1243.5	1243.5	1243.6	1243.8	1244.1	1244.3	1244.6	1244.8	1246.5	1248.2
165°	1269.1	1268.9	1268.6	1268.3	1268.3	1268.3	1268.3	1268.3	1268.3	1270.0	1271.7
167.5°	1290.5	1289.8	1289.0	1288.2	1287.9	1287.8	1287.8	1287.7	1287.6	1289.4	1291.2
170°	1302.1	1301.4	1300.6	1299.9	1299.4	1299.2	1298.9	1298.6	1298.4	1300.1	1301.8
172.5°	1310.2	1309.4	1308.6	1307.9	1307.4	1307.2	1306.9	1306.7	1306.4	1308.2	1309.9
175°	1320.0	1319.2	1318.4	1317.8	1317.2	1316.6	1316.1	1315.6	1315.1	1316.9	1318.6
177.5°	1324.1	1323.5	1322.9	1322.3	1321.9	1321.5	1321.0	1320.7	1320.3	1321.5	1322.7
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1186.2	1191.1	1191.1	1191.8	1197.5	1196.7	1196.4
5°	1262.3	1269.8	1270.7	1278.6	1283.8	1282.1	1277.3
7.5°	1334.1	1348.1	1358.6	1364.4	1371.4	1375.7	1373.8
10°	1391.1	1411.4	1423.7	1432.0	1442.1	1449.6	1446.9
12.5°	1442.8	1466.9	1483.8	1498.1	1499.4	1509.0	1502.4
15°	1523.4	1548.9	1551.5	1562.1	1570.5	1569.5	1569.9
17.5°	1550.1	1558.2	1559.9	1560.1	1560.2	1557.1	1550.5
20°	1540.5	1537.5	1530.0	1524.3	1514.2	1512.9	1504.1
22.5°	1495.6	1485.7	1467.1	1454.7	1438.9	1434.8	1432.4
25°	1407.0	1385.3	1355.5	1326.9	1319.1	1303.6	1308.0
27.5°	1285.4	1251.8	1219.4	1196.2	1175.2	1152.2	1158.7
30°	1199.9	1162.1	1116.4	1081.2	1058.9	1036.8	1032.9
32.5°	1097.9	1042.6	991.5	960.6	926.3	912.4	897.2
35°	922.1	868.1	817.5	774.0	749.0	729.6	712.0
37.5°	764.0	701.7	661.0	625.7	607.6	596.5	599.3
40°	665.9	611.4	581.5	554.7	538.0	530.0	531.8
42.5°	586.4	545.6	521.0	502.7	490.9	486.5	485.4
45°	496.2	473.4	453.1	442.6	436.9	432.0	429.0
47.5°	434.7	416.0	404.7	398.4	393.4	388.5	388.4
50°	397.8	385.5	377.5	370.9	367.0	363.5	366.5
52.5°	369.6	358.3	350.5	344.6	343.1	339.9	339.8
55°	327.9	319.1	313.4	308.1	305.5	303.7	301.5
57.5°	289.9	281.5	276.3	272.9	267.9	266.1	265.4
60°	262.9	256.2	251.0	246.6	244.4	240.8	240.8
62.5°	237.9	231.3	226.4	223.0	219.4	218.0	218.3
65°	201.7	196.5	191.7	188.1	187.3	184.6	185.5
67.5°	168.5	165.0	159.9	158.0	156.3	154.9	153.9
70°	146.4	142.8	140.2	137.6	136.2	136.2	136.2
72.5°	127.7	123.5	121.9	118.6	119.3	118.0	116.6
75°	98.9	96.3	95.0	93.6	91.4	91.4	91.4
77.5°	72.8	72.0	70.4	69.0	68.4	68.0	68.2
80°	56.2	55.8	54.9	54.9	54.1	53.6	52.8
82.5°	43.2	42.1	41.6	41.2	41.1	41.0	40.8
85°	24.6	23.8	23.8	24.2	23.3	23.3	23.8
87.5°	17.0	16.9	16.5	16.6	17.0	16.7	16.7
90°	37.6	37.1	36.9	37.2	37.5	37.7	38.0
92.5°	35.8	35.9	36.0	36.0	36.1	36.2	36.2
95°	71.5	71.5	71.2	70.7	70.2	69.7	69.2
97.5°	120.1	120.1	120.1	120.0	120.0	119.9	119.9
100°	154.0	154.0	153.9	153.7	153.4	153.2	152.9
102.5°	191.3	191.5	191.5	191.2	191.0	190.7	190.5
105°	247.1	247.6	247.9	247.9	247.9	247.9	247.9
107.5°	306.7	306.9	306.4	305.3	304.2	303.0	301.9
110°	347.2	347.2	346.8	346.1	345.3	344.6	343.9



TEST NUMBER: P331544-935

CATALOG NUMBER: S122DIW-S675D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	387.4	386.8	386.2	385.6	385.1	384.6	384.0
115°	450.3	450.0	449.5	448.8	448.1	447.3	446.6
117.5°	510.4	509.8	509.2	508.4	507.6	507.0	506.2
120°	551.5	551.5	551.1	550.4	549.7	548.9	548.2
122.5°	592.6	592.0	591.4	590.9	590.3	589.8	589.3
125°	654.2	653.5	653.0	652.7	652.5	652.2	651.9
127.5°	714.0	713.2	712.3	711.5	710.8	710.0	709.1
130°	755.4	754.9	754.2	753.2	752.3	751.2	750.2
132.5°	794.7	793.7	792.7	791.9	791.1	790.3	789.5
135°	854.5	854.2	853.7	852.9	852.2	851.4	850.7
137.5°	910.9	910.7	910.1	909.0	908.1	907.1	906.1
140°	948.9	948.9	948.5	947.4	946.5	945.5	944.5
142.5°	983.5	983.7	983.3	982.3	981.3	980.3	979.3
145°	1035.7	1035.9	1035.5	1034.6	1033.5	1032.6	1031.6
147.5°	1081.7	1082.2	1082.0	1081.1	1080.1	1079.2	1078.2
150°	1110.9	1111.6	1111.6	1110.9	1110.1	1109.3	1108.6
152.5°	1140.0	1140.9	1140.9	1140.0	1139.1	1138.2	1137.2
155°	1177.1	1178.3	1178.5	1177.8	1177.1	1176.3	1175.6
157.5°	1211.4	1213.1	1213.4	1212.2	1211.0	1209.8	1208.6
160°	1231.4	1232.9	1233.1	1232.2	1231.1	1230.2	1229.2
162.5°	1249.8	1251.5	1251.8	1250.6	1249.4	1248.2	1247.1
165°	1273.4	1275.2	1275.4	1274.2	1273.0	1271.7	1270.5
167.5°	1292.9	1294.6	1294.9	1293.6	1292.3	1291.0	1289.7
170°	1303.6	1305.4	1305.4	1304.0	1302.5	1301.0	1299.5
172.5°	1311.6	1313.4	1313.5	1312.0	1310.5	1309.1	1307.5
175°	1320.3	1322.1	1322.2	1320.7	1319.2	1317.8	1316.2
177.5°	1323.9	1325.0	1325.0	1323.9	1322.7	1321.5	1320.3
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9

(END OF REPORT)