

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331525-935

Luminaire Tested: **S122DIW-S675D435U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331525-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D435U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4014.8 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	76	70	69	67	61	60	59	54
2	93	86	80	75	87	81	75	71	71	67	64	62	59	57	54	52	50	46
3	85	76	69	63	80	71	65	60	63	58	54	56	52	49	49	46	44	40
4	78	68	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38	35
5	72	61	53	47	67	57	50	45	51	45	41	45	41	37	40	36	34	31
6	67	55	47	41	62	52	45	39	46	40	36	41	37	33	37	33	30	27
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	34	30	27	24
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24	22
9	54	42	34	29	50	40	33	28	36	30	26	32	27	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	18466	18466	18466	18466
5°	20702	18585	16470	18585
10°	23722	18433	14254	18433
15°	26242	18094	12593	18094
20°	25844	17732	11478	17732
25°	23302	17250	10774	17250
30°	19257	16479	10260	16479
35°	14034	15672	9895	15672
40°	11209	14720	9691	14720
45°	9796	13618	9412	13618
50°	9206	12552	9231	12552
55°	8487	11468	8982	11468
60°	7776	10317	8603	10317
65°	7087	9287	8225	9287
70°	6430	8280	7676	8280
75°	5702	7155	6800	7155
80°	4909	5923	5477	5923
85°	4409	4409	3260	4409



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.9	2.7
10°-20°	316.6	7.9
20°-30°	459.5	11.4
30°-40°	484.9	12.1
40°-50°	429.4	10.7
50°-60°	342.6	8.5
60°-70°	232.9	5.8
70°-80°	119.4	3.0
80°-90°	30.0	0.7
90°-100°	17.0	0.4
100°-110°	62.2	1.5
110°-120°	166.3	4.1
120°-130°	274.5	6.8
130°-140°	291.9	7.3
140°-150°	271.3	6.8
150°-160°	218.2	5.4
160°-170°	140.6	3.5
170°-180°	48.4	1.2
0°-30°	885.1	22.0
0°-40°	1370.0	34.1
0°-60°	2142.0	53.4
0°-90°	2524.4	62.9
90°-120°	245.5	6.1
90°-150°	1083.3	27.0
90°-180°	1490.0	37.1
0°-180°	4014.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1144	1144	1144	1144	1144	
5°	1277	1147	1016	1147	1277	128
15°	1570	1082	753	1082	1570	433
25°	1308	968	605	968	1308	591
35°	712	795	502	795	712	463
45°	429	596	412	596	429	337
55°	302	407	319	407	302	270
65°	186	243	215	243	186	184
75°	91	115	109	115	91	98
85°	24	24	18	24	24	26
90°	10	0	10	0	10	6
95°	16	24	16	24	16	15
105°	28	112	28	112	28	29
115°	30	212	30	212	30	76
125°	315	299	315	299	315	272
135°	382	370	382	370	382	295
145°	436	430	436	430	436	273
155°	473	473	473	473	473	218
165°	497	498	497	498	497	140
175°	507	510	507	510	507	48
180°	509	509	509	509	509	



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1196.4	1196.7	1197.5	1191.8	1191.1	1191.1	1186.2	1182.0	1177.1	1170.4	1171.0
5°	1277.3	1282.1	1283.8	1278.6	1270.7	1269.8	1262.3	1250.0	1238.5	1229.3	1222.8
7.5°	1373.8	1375.7	1371.4	1364.4	1358.6	1348.1	1334.1	1320.5	1301.4	1283.9	1270.9
10°	1446.9	1449.6	1442.1	1432.0	1423.7	1411.4	1391.1	1370.5	1345.4	1321.2	1301.8
12.5°	1502.4	1509.0	1499.4	1498.1	1483.8	1466.9	1442.8	1432.4	1397.1	1363.4	1342.6
15°	1569.9	1569.5	1570.5	1562.1	1551.5	1548.9	1523.4	1495.7	1446.0	1426.2	1392.0
17.5°	1550.5	1557.1	1560.2	1560.1	1559.9	1558.2	1550.1	1532.6	1507.7	1475.6	1436.0
20°	1504.1	1512.9	1514.2	1524.3	1530.0	1537.5	1540.5	1535.7	1520.4	1493.5	1459.2
22.5°	1432.4	1434.8	1438.9	1454.7	1467.1	1485.7	1495.6	1511.8	1505.9	1492.8	1464.1
25°	1308.0	1303.6	1319.1	1326.9	1355.5	1385.3	1407.0	1430.6	1451.7	1464.5	1456.1
27.5°	1158.7	1152.2	1175.2	1196.2	1219.4	1251.8	1285.4	1325.0	1358.0	1399.2	1413.3
30°	1032.9	1036.8	1058.9	1081.2	1116.4	1162.1	1199.9	1243.5	1290.5	1336.6	1368.6
32.5°	897.2	912.4	926.3	960.6	991.5	1042.6	1097.9	1152.4	1211.0	1263.4	1313.1
35°	712.0	729.6	749.0	774.0	817.5	868.1	922.1	995.5	1075.6	1147.2	1206.1
37.5°	599.3	596.5	607.6	625.7	661.0	701.7	764.0	836.5	930.7	1014.9	1097.9
40°	531.8	530.0	538.0	554.7	581.5	611.4	665.9	729.6	817.1	919.9	1018.8
42.5°	485.4	486.5	490.9	502.7	521.0	545.6	586.4	640.7	720.7	817.6	923.9
45°	429.0	432.0	436.9	442.6	453.1	473.4	496.2	534.9	598.2	679.1	783.7
47.5°	388.4	388.5	393.4	398.4	404.7	416.0	434.7	458.9	503.6	569.5	659.4
50°	366.5	363.5	367.0	370.9	377.5	385.5	397.8	420.6	450.5	503.7	578.9
52.5°	339.8	339.9	343.1	344.6	350.5	358.3	369.6	385.5	412.5	454.1	515.9
55°	301.5	303.7	305.5	308.1	313.4	319.1	327.9	338.5	359.6	390.7	436.4
57.5°	265.4	266.1	267.9	272.9	276.3	281.5	289.9	299.5	313.2	336.3	370.7
60°	240.8	240.8	244.4	246.6	251.0	256.2	262.9	272.1	284.4	303.2	331.0
62.5°	218.3	218.0	219.4	223.0	226.4	231.3	237.9	245.7	257.3	274.1	296.9
65°	185.5	184.6	187.3	188.1	191.7	196.5	201.7	210.1	219.3	231.6	251.8
67.5°	153.9	154.9	156.3	158.0	159.9	165.0	168.5	174.4	182.2	192.4	206.1
70°	136.2	136.2	136.2	137.6	140.2	142.8	146.4	151.2	158.7	167.5	179.8
72.5°	116.6	118.0	119.3	118.6	121.9	123.5	127.7	130.4	137.6	143.2	154.1
75°	91.4	91.4	91.4	93.6	95.0	96.3	98.9	101.5	105.0	112.1	117.8
77.5°	68.2	68.0	68.4	69.0	70.4	72.0	72.8	75.2	78.4	81.6	86.5
80°	52.8	53.6	54.1	54.9	54.9	55.8	56.2	59.3	61.6	63.7	66.8
82.5°	40.8	41.0	41.1	41.2	41.6	42.1	43.2	44.3	45.0	46.8	49.2
85°	23.8	23.3	23.3	24.2	23.8	23.8	24.6	25.5	25.5	25.9	27.2
87.5°	11.1	11.1	11.5	11.0	11.0	11.3	11.2	10.8	11.0	11.3	11.5
90°	9.9	9.8	9.6	9.5	9.3	9.0	8.6	8.2	7.7	7.3	6.7
92.5°	9.9	9.8	9.7	9.6	9.6	9.4	9.2	9.0	8.8	8.5	8.2
95°	15.8	15.9	16.0	16.1	16.2	16.0	15.6	15.2	14.7	14.4	13.8
97.5°	21.1	21.0	20.9	20.8	20.8	20.5	20.2	19.9	19.5	19.2	17.9
100°	24.6	24.5	24.4	24.2	24.0	23.6	22.9	22.3	21.6	21.0	19.5
102.5°	26.4	26.2	26.0	25.7	25.5	25.0	24.1	23.2	22.4	21.5	33.2
105°	28.0	27.6	27.3	26.9	26.7	26.1	25.1	24.3	23.3	22.5	44.8
107.5°	28.8	28.4	28.2	27.8	27.5	27.7	28.7	29.6	30.5	31.4	58.2
110°	29.1	28.8	28.4	28.1	27.7	31.7	39.9	48.0	56.2	64.4	88.0



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	29.4	29.1	28.8	28.6	28.3	43.1	72.9	102.8	132.6	162.5	168.2
115°	30.1	36.1	41.9	47.9	53.7	75.6	113.5	151.4	189.2	227.0	225.0
117.5°	123.2	142.6	161.9	181.2	200.6	214.8	224.0	233.2	242.4	251.5	250.1
120°	224.5	235.5	246.6	257.6	268.6	273.7	272.7	271.7	270.7	269.8	268.3
122.5°	280.1	282.2	284.4	286.5	288.7	289.5	288.9	288.3	287.7	287.1	285.5
125°	314.6	314.4	314.2	313.9	313.7	313.2	312.7	312.1	311.5	311.0	309.4
127.5°	336.4	336.4	336.3	336.3	336.2	335.8	334.9	334.2	333.3	332.4	331.3
130°	350.0	350.1	350.2	350.3	350.3	349.9	349.0	348.1	347.2	346.3	345.4
132.5°	363.3	363.3	363.3	363.4	363.5	363.2	362.4	361.7	360.9	360.2	359.2
135°	382.4	382.5	382.7	382.9	383.0	382.7	381.9	381.1	380.2	379.4	378.7
137.5°	399.8	400.1	400.4	400.6	400.9	400.6	399.8	399.1	398.2	397.4	396.6
140°	410.7	411.1	411.5	411.9	412.3	412.2	411.5	410.7	409.9	409.2	408.3
142.5°	421.3	421.7	422.1	422.5	422.9	422.8	422.1	421.5	420.8	420.1	419.0
145°	436.1	436.5	436.9	437.3	437.7	437.6	437.0	436.5	435.9	435.3	433.9
147.5°	449.1	449.4	449.8	450.1	450.5	450.5	450.0	449.6	449.2	448.8	447.4
150°	457.1	457.4	457.9	458.3	458.7	458.7	458.1	457.7	457.2	456.7	455.4
152.5°	463.8	464.3	464.9	465.5	466.0	466.1	465.5	465.0	464.5	464.1	462.8
155°	473.3	473.9	474.6	475.2	475.9	476.0	475.4	475.0	474.5	474.0	473.0
157.5°	481.9	482.5	483.1	483.8	484.4	484.5	483.9	483.4	482.8	482.2	481.6
160°	486.9	487.4	488.0	488.6	489.1	489.2	488.7	488.2	487.8	487.2	486.7
162.5°	491.0	491.7	492.4	493.1	493.8	493.9	493.4	492.8	492.2	491.6	491.2
165°	497.1	497.7	498.3	498.9	499.5	499.5	498.9	498.3	497.7	497.1	497.0
167.5°	501.1	501.8	502.6	503.3	504.0	504.1	503.5	503.0	502.4	501.8	501.6
170°	503.4	504.2	504.9	505.7	506.4	506.4	505.9	505.3	504.7	504.2	504.0
172.5°	505.2	505.9	506.7	507.4	508.2	508.2	507.6	507.0	506.5	505.9	505.8
175°	506.8	507.6	508.4	509.2	510.1	510.1	509.5	509.0	508.4	507.8	507.6
177.5°	507.7	508.2	508.9	509.5	510.1	510.1	509.6	509.2	508.8	508.2	508.2
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1173.5	1170.7	1169.0	1162.6	1157.0	1151.4	1149.6	1150.3	1142.6	1135.2	1132.0
5°	1219.3	1210.5	1202.1	1190.2	1176.2	1160.8	1152.9	1146.7	1131.4	1114.7	1105.0
7.5°	1260.2	1247.7	1231.6	1209.2	1188.8	1164.6	1149.2	1135.6	1113.0	1089.5	1075.0
10°	1285.2	1268.0	1247.3	1220.1	1195.1	1165.6	1145.0	1124.3	1097.9	1069.8	1052.2
12.5°	1306.7	1283.5	1263.2	1228.2	1198.6	1161.7	1137.2	1108.1	1080.4	1047.0	1029.8
15°	1357.7	1315.1	1276.3	1236.8	1200.3	1148.9	1121.7	1082.5	1046.0	1004.8	985.0
17.5°	1397.1	1349.3	1288.3	1238.0	1195.5	1138.6	1098.5	1051.7	1008.6	961.3	934.4
20°	1419.7	1364.7	1299.2	1239.5	1188.4	1123.4	1080.0	1032.0	981.5	928.2	899.2
22.5°	1433.0	1375.3	1310.5	1234.2	1174.4	1111.1	1056.4	1003.8	952.6	895.3	864.8
25°	1437.3	1384.5	1316.0	1229.8	1156.8	1085.2	1019.3	968.3	906.3	852.6	808.3
27.5°	1416.3	1378.5	1312.6	1221.5	1136.5	1052.7	979.3	921.5	856.1	797.9	753.3
30°	1390.7	1368.6	1304.5	1213.1	1120.3	1030.3	949.3	883.9	818.8	759.9	714.2
32.5°	1350.9	1346.2	1289.8	1201.1	1103.1	1001.8	918.1	851.9	779.8	721.9	678.4
35°	1272.9	1294.0	1258.4	1174.4	1070.7	961.2	870.7	795.1	720.4	665.0	624.1
37.5°	1168.3	1220.6	1211.3	1135.3	1026.9	917.1	817.2	738.1	666.9	611.1	570.9
40°	1096.1	1163.0	1172.7	1105.4	996.0	883.0	777.1	698.4	629.0	578.0	537.5
42.5°	1018.8	1096.9	1123.4	1069.5	962.2	847.1	741.2	659.7	591.0	541.4	505.6
45°	889.2	992.5	1040.3	1009.6	905.9	788.1	679.1	596.4	534.0	487.4	459.8
47.5°	767.9	880.8	945.2	934.4	843.2	726.5	618.8	539.5	478.7	441.5	416.7
50°	682.2	798.1	876.0	879.5	798.1	682.6	574.5	499.7	443.9	409.2	389.0
52.5°	607.6	718.3	803.2	821.8	747.9	636.9	534.8	460.4	411.2	379.3	361.2
55°	510.3	603.9	697.9	732.3	672.9	567.4	472.9	407.4	361.3	339.3	323.5
57.5°	424.2	502.3	589.2	627.1	590.5	500.2	411.6	354.7	317.3	298.0	285.9
60°	378.8	440.4	517.7	563.0	531.4	451.0	373.6	319.5	288.8	271.6	260.2
62.5°	336.7	391.2	456.6	498.0	480.8	404.9	335.6	287.9	261.3	245.2	237.0
65°	277.8	320.9	371.4	409.7	398.2	340.6	284.0	243.1	222.0	209.2	202.6
67.5°	228.8	259.8	294.9	328.4	319.2	278.4	232.9	201.0	185.3	174.4	170.4
70°	197.8	221.5	252.7	279.6	272.1	238.7	202.6	175.4	161.8	152.5	148.5
72.5°	168.2	187.8	211.5	233.5	228.4	200.7	170.7	150.1	139.6	131.0	127.8
75°	127.0	142.0	156.4	171.0	169.6	148.1	130.5	114.7	106.3	99.8	98.4
77.5°	93.8	102.1	112.0	120.6	118.2	105.9	92.1	83.1	76.9	72.5	71.8
80°	71.6	76.5	83.5	89.6	86.6	81.3	70.3	63.7	59.3	54.9	53.2
82.5°	51.9	56.8	61.0	64.3	62.0	57.1	50.3	45.8	43.1	40.2	39.4
85°	27.2	29.9	31.7	32.5	31.7	28.6	25.5	23.8	21.5	20.2	19.8
87.5°	11.8	11.6	11.5	12.1	10.8	10.6	9.0	7.8	7.7	7.5	7.0
90°	6.0	5.4	4.7	4.0	3.1	2.2	1.3	0.3	1.3	2.2	3.1
92.5°	7.9	7.6	7.2	7.1	7.1	7.2	7.3	7.4	7.3	7.2	7.1
95°	13.2	12.7	12.1	13.1	15.8	18.5	21.2	23.9	21.2	18.5	15.8
97.5°	16.5	15.2	13.9	17.0	24.6	32.3	39.9	47.4	39.9	32.3	24.6
100°	18.2	16.8	15.4	20.3	31.5	42.7	53.9	65.2	53.9	42.7	31.5
102.5°	44.9	56.5	68.1	75.1	77.5	79.8	82.2	84.6	82.2	79.8	77.5
105°	67.1	89.5	111.8	121.7	119.2	116.8	114.3	111.8	114.3	116.8	119.2
107.5°	85.0	111.8	138.5	150.9	149.0	147.0	145.0	143.0	145.0	147.0	149.0
110°	111.7	135.3	158.9	169.9	168.2	166.4	164.7	163.0	164.7	166.4	168.2



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	174.1	179.9	185.8	188.0	186.4	184.9	183.4	181.8	183.4	184.9	186.4
115°	223.0	220.9	218.9	217.1	215.8	214.4	213.0	211.6	213.0	214.4	215.8
117.5°	248.7	247.3	245.9	244.4	242.8	241.3	239.7	238.2	239.7	241.3	242.8
120°	266.8	265.4	263.9	262.5	261.3	260.0	258.8	257.6	258.8	260.0	261.3
122.5°	283.9	282.3	280.7	279.2	277.9	276.6	275.3	274.1	275.3	276.6	277.9
125°	307.9	306.3	304.7	303.4	302.4	301.4	300.2	299.2	300.2	301.4	302.4
127.5°	330.1	329.0	327.8	326.7	325.5	324.3	323.1	321.9	323.1	324.3	325.5
130°	344.5	343.6	342.7	341.6	340.3	339.0	337.7	336.4	337.7	339.0	340.3
132.5°	358.3	357.4	356.5	355.5	354.4	353.3	352.1	351.1	352.1	353.3	354.4
135°	378.0	377.2	376.4	375.5	374.1	372.8	371.5	370.2	371.5	372.8	374.1
137.5°	395.8	394.9	394.1	393.2	392.4	391.4	390.5	389.6	390.5	391.4	392.4
140°	407.4	406.6	405.6	404.8	404.2	403.6	402.9	402.3	402.9	403.6	404.2
142.5°	418.0	417.0	416.0	415.2	414.6	414.0	413.5	412.8	413.5	414.0	414.6
145°	432.6	431.2	429.8	429.1	429.2	429.3	429.4	429.5	429.4	429.3	429.2
147.5°	446.0	444.6	443.2	442.7	443.1	443.3	443.7	443.9	443.7	443.3	443.1
150°	454.1	452.8	451.4	451.1	451.7	452.2	452.8	453.4	452.8	452.2	451.7
152.5°	461.6	460.3	459.1	458.7	459.4	460.0	460.7	461.3	460.7	460.0	459.4
155°	472.0	471.1	470.1	469.9	470.7	471.4	472.2	472.9	472.2	471.4	470.7
157.5°	480.9	480.2	479.5	479.5	480.1	480.7	481.3	481.9	481.3	480.7	480.1
160°	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2	486.7	486.3	485.8
162.5°	490.8	490.3	490.0	490.0	490.5	490.9	491.5	492.0	491.5	490.9	490.5
165°	496.7	496.5	496.2	496.3	496.8	497.3	497.8	498.3	497.8	497.3	496.8
167.5°	501.4	501.1	500.9	501.0	501.5	502.0	502.5	503.0	502.5	502.0	501.5
170°	503.9	503.7	503.5	503.7	504.2	504.6	505.1	505.7	505.1	504.6	504.2
172.5°	505.6	505.4	505.3	505.4	505.9	506.4	507.0	507.4	507.0	506.4	505.9
175°	507.6	507.4	507.2	507.4	508.0	508.5	509.1	509.7	509.1	508.5	508.0
177.5°	508.2	508.1	508.0	508.2	508.7	509.1	509.6	510.1	509.6	509.1	508.7
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1128.5	1126.4	1119.0	1115.2	1108.8	1102.9	1099.0	1100.8	1102.2	1101.5	1100.4
5°	1096.1	1087.8	1075.0	1064.1	1056.2	1041.6	1035.5	1032.4	1029.8	1026.7	1023.6
7.5°	1057.7	1044.5	1026.2	1010.6	995.7	977.8	967.5	961.3	955.0	948.0	941.9
10°	1030.3	1011.8	992.5	970.4	952.9	936.6	922.1	912.5	903.7	895.4	889.2
12.5°	1001.4	980.2	956.2	926.2	906.8	883.6	881.3	864.3	850.6	845.4	838.2
15°	955.5	925.7	895.4	859.7	844.3	823.2	810.0	796.9	785.0	776.6	774.5
17.5°	903.4	864.7	834.6	809.0	783.8	762.2	750.0	739.4	729.7	718.5	717.0
20°	863.7	830.3	797.3	774.9	749.0	726.9	712.0	701.5	693.1	686.6	680.8
22.5°	826.0	789.5	759.3	734.8	709.2	691.5	679.7	669.5	662.5	655.2	649.9
25°	765.7	737.1	704.1	676.4	655.3	643.9	634.2	625.4	621.0	616.2	610.1
27.5°	712.8	681.1	650.2	628.8	610.3	600.1	593.2	587.3	583.2	580.3	576.9
30°	675.5	643.4	619.3	598.2	582.8	572.7	568.3	564.8	560.0	558.2	556.5
32.5°	639.7	610.8	590.1	571.8	557.2	550.5	546.5	543.4	539.6	537.8	534.3
35°	588.9	564.8	544.6	534.4	522.6	516.9	513.8	509.4	505.9	504.1	503.7
37.5°	541.2	520.2	507.0	494.0	489.0	485.4	481.2	478.2	477.2	476.9	476.5
40°	510.3	493.2	481.3	470.7	468.6	463.2	459.8	457.1	457.1	457.5	457.1
42.5°	482.2	466.7	456.3	447.2	444.6	441.4	437.9	437.7	438.5	440.0	438.5
45°	439.5	428.5	421.0	416.6	411.8	408.7	408.3	409.7	410.1	410.5	411.8
47.5°	400.3	393.0	386.2	381.4	379.3	378.8	378.2	380.6	382.6	383.4	385.5
50°	377.1	368.8	363.1	360.0	358.2	357.3	358.2	360.8	362.6	364.8	366.1
52.5°	351.1	345.2	341.2	338.9	338.2	338.7	338.9	341.9	344.7	345.4	346.1
55°	315.1	310.7	309.9	305.9	307.6	307.2	309.4	311.2	313.8	316.4	316.9
57.5°	279.3	275.8	273.4	273.7	274.2	276.2	278.0	281.1	284.0	286.7	287.0
60°	255.4	253.6	252.3	252.3	253.1	255.8	258.0	261.1	262.9	264.6	265.9
62.5°	233.6	231.8	230.5	231.2	233.5	235.1	237.6	239.3	241.0	242.8	243.4
65°	199.1	198.2	199.6	200.4	200.9	203.0	206.1	207.4	209.2	210.1	213.2
67.5°	167.4	167.6	167.4	168.6	171.2	171.7	174.6	177.6	178.0	179.7	181.7
70°	145.9	146.8	147.7	148.5	150.8	151.6	153.9	155.2	156.9	158.3	159.5
72.5°	126.2	126.4	127.3	127.1	129.0	130.9	132.8	134.1	135.8	137.5	138.8
75°	97.1	97.1	98.0	98.4	100.7	102.9	102.4	103.3	105.0	106.8	107.7
77.5°	70.9	70.0	70.9	71.4	72.1	74.0	74.3	75.5	77.5	76.9	77.9
80°	54.1	52.8	54.1	54.5	54.5	56.7	56.7	57.6	58.9	57.6	58.9
82.5°	38.6	38.0	38.9	39.0	39.7	39.8	40.6	40.7	42.0	41.4	42.0
85°	19.4	18.9	19.4	18.9	19.4	19.8	19.8	19.4	19.4	20.2	18.9
87.5°	6.8	6.5	6.4	6.5	6.3	6.0	5.8	5.9	5.9	5.3	5.3
90°	4.0	4.7	5.4	6.0	6.7	7.3	7.7	8.2	8.6	9.0	9.3
92.5°	7.1	7.2	7.6	7.9	8.2	8.5	8.8	9.0	9.2	9.4	9.6
95°	13.1	12.1	12.7	13.2	13.8	14.4	14.7	15.2	15.6	16.0	16.2
97.5°	17.0	13.9	15.2	16.5	17.9	19.2	19.5	19.9	20.2	20.5	20.8
100°	20.3	15.4	16.8	18.2	19.5	21.0	21.6	22.3	22.9	23.6	24.0
102.5°	75.1	68.1	56.5	44.9	33.2	21.5	22.4	23.2	24.1	25.0	25.5
105°	121.7	111.8	89.5	67.1	44.8	22.5	23.3	24.3	25.1	26.1	26.7
107.5°	150.9	138.5	111.8	85.0	58.2	31.4	30.5	29.6	28.7	27.7	27.5
110°	169.9	158.9	135.3	111.7	88.0	64.4	56.2	48.0	39.9	31.7	27.7



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	188.0	185.8	179.9	174.1	168.2	162.5	132.6	102.8	72.9	43.1	28.3
115°	217.1	218.9	220.9	223.0	225.0	227.0	189.2	151.4	113.5	75.6	53.7
117.5°	244.4	245.9	247.3	248.7	250.1	251.5	242.4	233.2	224.0	214.8	200.6
120°	262.5	263.9	265.4	266.8	268.3	269.8	270.7	271.7	272.7	273.7	268.6
122.5°	279.2	280.7	282.3	283.9	285.5	287.1	287.7	288.3	288.9	289.5	288.7
125°	303.4	304.7	306.3	307.9	309.4	311.0	311.5	312.1	312.7	313.2	313.7
127.5°	326.7	327.8	329.0	330.1	331.3	332.4	333.3	334.2	334.9	335.8	336.2
130°	341.6	342.7	343.6	344.5	345.4	346.3	347.2	348.1	349.0	349.9	350.3
132.5°	355.5	356.5	357.4	358.3	359.2	360.2	360.9	361.7	362.4	363.2	363.5
135°	375.5	376.4	377.2	378.0	378.7	379.4	380.2	381.1	381.9	382.7	383.0
137.5°	393.2	394.1	394.9	395.8	396.6	397.4	398.2	399.1	399.8	400.6	400.9
140°	404.8	405.6	406.6	407.4	408.3	409.2	409.9	410.7	411.5	412.2	412.3
142.5°	415.2	416.0	417.0	418.0	419.0	420.1	420.8	421.5	422.1	422.8	422.9
145°	429.1	429.8	431.2	432.6	433.9	435.3	435.9	436.5	437.0	437.6	437.7
147.5°	442.7	443.2	444.6	446.0	447.4	448.8	449.2	449.6	450.0	450.5	450.5
150°	451.1	451.4	452.8	454.1	455.4	456.7	457.2	457.7	458.1	458.7	458.7
152.5°	458.7	459.1	460.3	461.6	462.8	464.1	464.5	465.0	465.5	466.1	466.0
155°	469.9	470.1	471.1	472.0	473.0	474.0	474.5	475.0	475.4	476.0	475.9
157.5°	479.5	479.5	480.2	480.9	481.6	482.2	482.8	483.4	483.9	484.5	484.4
160°	485.3	485.3	485.8	486.3	486.7	487.2	487.8	488.2	488.7	489.2	489.1
162.5°	490.0	490.0	490.3	490.8	491.2	491.6	492.2	492.8	493.4	493.9	493.8
165°	496.3	496.2	496.5	496.7	497.0	497.1	497.7	498.3	498.9	499.5	499.5
167.5°	501.0	500.9	501.1	501.4	501.6	501.8	502.4	503.0	503.5	504.1	504.0
170°	503.7	503.5	503.7	503.9	504.0	504.2	504.7	505.3	505.9	506.4	506.4
172.5°	505.4	505.3	505.4	505.6	505.8	505.9	506.5	507.0	507.6	508.2	508.2
175°	507.4	507.2	507.4	507.6	507.6	507.8	508.4	509.0	509.5	510.1	510.1
177.5°	508.2	508.0	508.1	508.2	508.2	508.2	508.8	509.2	509.6	510.1	510.1
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1096.9	1096.1	1096.1	1093.0	1096.1	1096.1	1096.9	1100.4	1101.5	1102.2	1100.8
5°	1017.5	1016.2	1014.0	1016.2	1014.0	1016.2	1017.5	1023.6	1026.7	1029.8	1032.4
7.5°	939.0	933.8	933.0	927.7	933.0	933.8	939.0	941.9	948.0	955.0	961.3
10°	881.7	878.1	877.7	869.4	877.7	878.1	881.7	889.2	895.4	903.7	912.5
12.5°	838.1	829.7	831.3	826.5	831.3	829.7	838.1	838.2	845.4	850.6	864.3
15°	762.6	762.6	760.8	753.4	760.8	762.6	762.6	774.5	776.6	785.0	796.9
17.5°	708.3	707.5	703.3	705.3	703.3	707.5	708.3	717.0	718.5	729.7	739.4
20°	676.0	673.4	668.0	668.0	668.0	673.4	676.0	680.8	686.6	693.1	701.5
22.5°	645.4	645.2	639.6	641.4	639.6	645.2	645.4	649.9	655.2	662.5	669.5
25°	609.6	606.1	603.5	604.8	603.5	606.1	609.6	610.1	616.2	621.0	625.4
27.5°	575.7	573.8	573.6	570.0	573.6	573.8	575.7	576.9	580.3	583.2	587.3
30°	556.0	551.6	552.5	550.3	552.5	551.6	556.0	556.5	558.2	560.0	564.8
32.5°	533.5	531.9	531.1	529.2	531.1	531.9	533.5	534.3	537.8	539.6	543.4
35°	502.8	503.3	501.1	502.0	501.1	503.3	502.8	503.7	504.1	505.9	509.4
37.5°	476.0	477.4	476.4	476.6	476.4	477.4	476.0	476.5	476.9	477.2	478.2
40°	458.4	458.4	458.4	459.8	458.4	458.4	458.4	457.1	457.5	457.1	457.1
42.5°	441.5	440.8	440.1	440.1	440.1	440.8	441.5	438.5	440.0	438.5	437.7
45°	412.7	414.1	414.5	412.2	414.5	414.1	412.7	411.8	410.5	410.1	409.7
47.5°	386.6	386.8	386.6	388.6	386.6	386.8	386.6	385.5	383.4	382.6	380.6
50°	368.3	367.5	368.3	367.5	368.3	367.5	368.3	366.1	364.8	362.6	360.8
52.5°	349.0	349.1	348.6	348.4	348.6	349.1	349.0	346.1	345.4	344.7	341.9
55°	318.7	319.5	319.1	319.1	319.1	319.5	318.7	316.9	316.4	313.8	311.2
57.5°	287.3	288.1	288.7	286.7	288.7	288.1	287.3	287.0	286.7	284.0	281.1
60°	265.4	267.7	267.3	266.4	267.3	267.7	265.4	265.9	264.6	262.9	261.1
62.5°	245.5	246.2	246.2	246.0	246.2	246.2	245.5	243.4	242.8	241.0	239.3
65°	214.5	215.3	214.0	215.3	214.0	215.3	214.5	213.2	210.1	209.2	207.4
67.5°	181.2	181.4	182.4	183.0	182.4	181.4	181.2	181.7	179.7	178.0	177.6
70°	160.4	160.0	161.3	162.6	161.3	160.0	160.4	159.5	158.3	156.9	155.2
72.5°	138.6	139.6	139.1	140.1	139.1	139.6	138.6	138.8	137.5	135.8	134.1
75°	106.8	108.1	107.7	109.0	107.7	108.1	106.8	107.7	106.8	105.0	103.3
77.5°	77.1	77.3	77.1	77.9	77.1	77.3	77.1	77.9	76.9	77.5	75.5
80°	58.9	58.0	57.2	58.9	57.2	58.0	58.9	58.9	57.6	58.9	57.6
82.5°	41.0	41.5	40.6	40.6	40.6	41.5	41.0	42.0	41.4	42.0	40.7
85°	18.9	18.4	17.6	17.6	17.6	18.4	18.9	18.9	20.2	19.4	19.4
87.5°	5.4	5.1	5.1	4.8	5.1	5.1	5.4	5.3	5.3	5.9	5.9
90°	9.5	9.6	9.8	9.9	9.8	9.6	9.5	9.3	9.0	8.6	8.2
92.5°	9.6	9.7	9.8	9.9	9.8	9.7	9.6	9.6	9.4	9.2	9.0
95°	16.1	16.0	15.9	15.8	15.9	16.0	16.1	16.2	16.0	15.6	15.2
97.5°	20.8	20.9	21.0	21.1	21.0	20.9	20.8	20.8	20.5	20.2	19.9
100°	24.2	24.4	24.5	24.6	24.5	24.4	24.2	24.0	23.6	22.9	22.3
102.5°	25.7	26.0	26.2	26.4	26.2	26.0	25.7	25.5	25.0	24.1	23.2
105°	26.9	27.3	27.6	28.0	27.6	27.3	26.9	26.7	26.1	25.1	24.3
107.5°	27.8	28.2	28.4	28.8	28.4	28.2	27.8	27.5	27.7	28.7	29.6
110°	28.1	28.4	28.8	29.1	28.8	28.4	28.1	27.7	31.7	39.9	48.0



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	28.6	28.8	29.1	29.4	29.1	28.8	28.6	28.3	43.1	72.9	102.8
115°	47.9	41.9	36.1	30.1	36.1	41.9	47.9	53.7	75.6	113.5	151.4
117.5°	181.2	161.9	142.6	123.2	142.6	161.9	181.2	200.6	214.8	224.0	233.2
120°	257.6	246.6	235.5	224.5	235.5	246.6	257.6	268.6	273.7	272.7	271.7
122.5°	286.5	284.4	282.2	280.1	282.2	284.4	286.5	288.7	289.5	288.9	288.3
125°	313.9	314.2	314.4	314.6	314.4	314.2	313.9	313.7	313.2	312.7	312.1
127.5°	336.3	336.3	336.4	336.4	336.4	336.3	336.3	336.2	335.8	334.9	334.2
130°	350.3	350.2	350.1	350.0	350.1	350.2	350.3	350.3	349.9	349.0	348.1
132.5°	363.4	363.3	363.3	363.3	363.3	363.3	363.4	363.5	363.2	362.4	361.7
135°	382.9	382.7	382.5	382.4	382.5	382.7	382.9	383.0	382.7	381.9	381.1
137.5°	400.6	400.4	400.1	399.8	400.1	400.4	400.6	400.9	400.6	399.8	399.1
140°	411.9	411.5	411.1	410.7	411.1	411.5	411.9	412.3	412.2	411.5	410.7
142.5°	422.5	422.1	421.7	421.3	421.7	422.1	422.5	422.9	422.8	422.1	421.5
145°	437.3	436.9	436.5	436.1	436.5	436.9	437.3	437.7	437.6	437.0	436.5
147.5°	450.1	449.8	449.4	449.1	449.4	449.8	450.1	450.5	450.5	450.0	449.6
150°	458.3	457.9	457.4	457.1	457.4	457.9	458.3	458.7	458.7	458.1	457.7
152.5°	465.5	464.9	464.3	463.8	464.3	464.9	465.5	466.0	466.1	465.5	465.0
155°	475.2	474.6	473.9	473.3	473.9	474.6	475.2	475.9	476.0	475.4	475.0
157.5°	483.8	483.1	482.5	481.9	482.5	483.1	483.8	484.4	484.5	483.9	483.4
160°	488.6	488.0	487.4	486.9	487.4	488.0	488.6	489.1	489.2	488.7	488.2
162.5°	493.1	492.4	491.7	491.0	491.7	492.4	493.1	493.8	493.9	493.4	492.8
165°	498.9	498.3	497.7	497.1	497.7	498.3	498.9	499.5	499.5	498.9	498.3
167.5°	503.3	502.6	501.8	501.1	501.8	502.6	503.3	504.0	504.1	503.5	503.0
170°	505.7	504.9	504.2	503.4	504.2	504.9	505.7	506.4	506.4	505.9	505.3
172.5°	507.4	506.7	505.9	505.2	505.9	506.7	507.4	508.2	508.2	507.6	507.0
175°	509.2	508.4	507.6	506.8	507.6	508.4	509.2	510.1	510.1	509.5	509.0
177.5°	509.5	508.9	508.2	507.7	508.2	508.9	509.5	510.1	510.1	509.6	509.2
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1099.0	1102.9	1108.8	1115.2	1119.0	1126.4	1128.5	1132.0	1135.2	1142.6	1150.3
5°	1035.5	1041.6	1056.2	1064.1	1075.0	1087.8	1096.1	1105.0	1114.7	1131.4	1146.7
7.5°	967.5	977.8	995.7	1010.6	1026.2	1044.5	1057.7	1075.0	1089.5	1113.0	1135.6
10°	922.1	936.6	952.9	970.4	992.5	1011.8	1030.3	1052.2	1069.8	1097.9	1124.3
12.5°	881.3	883.6	906.8	926.2	956.2	980.2	1001.4	1029.8	1047.0	1080.4	1108.1
15°	810.0	823.2	844.3	859.7	895.4	925.7	955.5	985.0	1004.8	1046.0	1082.5
17.5°	750.0	762.2	783.8	809.0	834.6	864.7	903.4	934.4	961.3	1008.6	1051.7
20°	712.0	726.9	749.0	774.9	797.3	830.3	863.7	899.2	928.2	981.5	1032.0
22.5°	679.7	691.5	709.2	734.8	759.3	789.5	826.0	864.8	895.3	952.6	1003.8
25°	634.2	643.9	655.3	676.4	704.1	737.1	765.7	808.3	852.6	906.3	968.3
27.5°	593.2	600.1	610.3	628.8	650.2	681.1	712.8	753.3	797.9	856.1	921.5
30°	568.3	572.7	582.8	598.2	619.3	643.4	675.5	714.2	759.9	818.8	883.9
32.5°	546.5	550.5	557.2	571.8	590.1	610.8	639.7	678.4	721.9	779.8	851.9
35°	513.8	516.9	522.6	534.4	544.6	564.8	588.9	624.1	665.0	720.4	795.1
37.5°	481.2	485.4	489.0	494.0	507.0	520.2	541.2	570.9	611.1	666.9	738.1
40°	459.8	463.2	468.6	470.7	481.3	493.2	510.3	537.5	578.0	629.0	698.4
42.5°	437.9	441.4	444.6	447.2	456.3	466.7	482.2	505.6	541.4	591.0	659.7
45°	408.3	408.7	411.8	416.6	421.0	428.5	439.5	459.8	487.4	534.0	596.4
47.5°	378.2	378.8	379.3	381.4	386.2	393.0	400.3	416.7	441.5	478.7	539.5
50°	358.2	357.3	358.2	360.0	363.1	368.8	377.1	389.0	409.2	443.9	499.7
52.5°	338.9	338.7	338.2	338.9	341.2	345.2	351.1	361.2	379.3	411.2	460.4
55°	309.4	307.2	307.6	305.9	309.9	310.7	315.1	323.5	339.3	361.3	407.4
57.5°	278.0	276.2	274.2	273.7	273.4	275.8	279.3	285.9	298.0	317.3	354.7
60°	258.0	255.8	253.1	252.3	252.3	253.6	255.4	260.2	271.6	288.8	319.5
62.5°	237.6	235.1	233.5	231.2	230.5	231.8	233.6	237.0	245.2	261.3	287.9
65°	206.1	203.0	200.9	200.4	199.6	198.2	199.1	202.6	209.2	222.0	243.1
67.5°	174.6	171.7	171.2	168.6	167.4	167.6	167.4	170.4	174.4	185.3	201.0
70°	153.9	151.6	150.8	148.5	147.7	146.8	145.9	148.5	152.5	161.8	175.4
72.5°	132.8	130.9	129.0	127.1	127.3	126.4	126.2	127.8	131.0	139.6	150.1
75°	102.4	102.9	100.7	98.4	98.0	97.1	97.1	98.4	99.8	106.3	114.7
77.5°	74.3	74.0	72.1	71.4	70.9	70.0	70.9	71.8	72.5	76.9	83.1
80°	56.7	56.7	54.5	54.5	54.1	52.8	54.1	53.2	54.9	59.3	63.7
82.5°	40.6	39.8	39.7	39.0	38.9	38.0	38.6	39.4	40.2	43.1	45.8
85°	19.8	19.8	19.4	18.9	19.4	18.9	19.4	19.8	20.2	21.5	23.8
87.5°	5.8	6.0	6.3	6.5	6.4	6.5	6.8	7.0	7.5	7.7	7.8
90°	7.7	7.3	6.7	6.0	5.4	4.7	4.0	3.1	2.2	1.3	0.3
92.5°	8.8	8.5	8.2	7.9	7.6	7.2	7.1	7.1	7.2	7.3	7.4
95°	14.7	14.4	13.8	13.2	12.7	12.1	13.1	15.8	18.5	21.2	23.9
97.5°	19.5	19.2	17.9	16.5	15.2	13.9	17.0	24.6	32.3	39.9	47.4
100°	21.6	21.0	19.5	18.2	16.8	15.4	20.3	31.5	42.7	53.9	65.2
102.5°	22.4	21.5	33.2	44.9	56.5	68.1	75.1	77.5	79.8	82.2	84.6
105°	23.3	22.5	44.8	67.1	89.5	111.8	121.7	119.2	116.8	114.3	111.8
107.5°	30.5	31.4	58.2	85.0	111.8	138.5	150.9	149.0	147.0	145.0	143.0
110°	56.2	64.4	88.0	111.7	135.3	158.9	169.9	168.2	166.4	164.7	163.0



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	132.6	162.5	168.2	174.1	179.9	185.8	188.0	186.4	184.9	183.4	181.8
115°	189.2	227.0	225.0	223.0	220.9	218.9	217.1	215.8	214.4	213.0	211.6
117.5°	242.4	251.5	250.1	248.7	247.3	245.9	244.4	242.8	241.3	239.7	238.2
120°	270.7	269.8	268.3	266.8	265.4	263.9	262.5	261.3	260.0	258.8	257.6
122.5°	287.7	287.1	285.5	283.9	282.3	280.7	279.2	277.9	276.6	275.3	274.1
125°	311.5	311.0	309.4	307.9	306.3	304.7	303.4	302.4	301.4	300.2	299.2
127.5°	333.3	332.4	331.3	330.1	329.0	327.8	326.7	325.5	324.3	323.1	321.9
130°	347.2	346.3	345.4	344.5	343.6	342.7	341.6	340.3	339.0	337.7	336.4
132.5°	360.9	360.2	359.2	358.3	357.4	356.5	355.5	354.4	353.3	352.1	351.1
135°	380.2	379.4	378.7	378.0	377.2	376.4	375.5	374.1	372.8	371.5	370.2
137.5°	398.2	397.4	396.6	395.8	394.9	394.1	393.2	392.4	391.4	390.5	389.6
140°	409.9	409.2	408.3	407.4	406.6	405.6	404.8	404.2	403.6	402.9	402.3
142.5°	420.8	420.1	419.0	418.0	417.0	416.0	415.2	414.6	414.0	413.5	412.8
145°	435.9	435.3	433.9	432.6	431.2	429.8	429.1	429.2	429.3	429.4	429.5
147.5°	449.2	448.8	447.4	446.0	444.6	443.2	442.7	443.1	443.3	443.7	443.9
150°	457.2	456.7	455.4	454.1	452.8	451.4	451.1	451.7	452.2	452.8	453.4
152.5°	464.5	464.1	462.8	461.6	460.3	459.1	458.7	459.4	460.0	460.7	461.3
155°	474.5	474.0	473.0	472.0	471.1	470.1	469.9	470.7	471.4	472.2	472.9
157.5°	482.8	482.2	481.6	480.9	480.2	479.5	479.5	480.1	480.7	481.3	481.9
160°	487.8	487.2	486.7	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2
162.5°	492.2	491.6	491.2	490.8	490.3	490.0	490.0	490.5	490.9	491.5	492.0
165°	497.7	497.1	497.0	496.7	496.5	496.2	496.3	496.8	497.3	497.8	498.3
167.5°	502.4	501.8	501.6	501.4	501.1	500.9	501.0	501.5	502.0	502.5	503.0
170°	504.7	504.2	504.0	503.9	503.7	503.5	503.7	504.2	504.6	505.1	505.7
172.5°	506.5	505.9	505.8	505.6	505.4	505.3	505.4	505.9	506.4	507.0	507.4
175°	508.4	507.8	507.6	507.6	507.4	507.2	507.4	508.0	508.5	509.1	509.7
177.5°	508.8	508.2	508.2	508.2	508.1	508.0	508.2	508.7	509.1	509.6	510.1
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1149.6	1151.4	1157.0	1162.6	1169.0	1170.7	1173.5	1171.0	1170.4	1177.1	1182.0
5°	1152.9	1160.8	1176.2	1190.2	1202.1	1210.5	1219.3	1222.8	1229.3	1238.5	1250.0
7.5°	1149.2	1164.6	1188.8	1209.2	1231.6	1247.7	1260.2	1270.9	1283.9	1301.4	1320.5
10°	1145.0	1165.6	1195.1	1220.1	1247.3	1268.0	1285.2	1301.8	1321.2	1345.4	1370.5
12.5°	1137.2	1161.7	1198.6	1228.2	1263.2	1283.5	1306.7	1342.6	1363.4	1397.1	1432.4
15°	1121.7	1148.9	1200.3	1236.8	1276.3	1315.1	1357.7	1392.0	1426.2	1446.0	1495.7
17.5°	1098.5	1138.6	1195.5	1238.0	1288.3	1349.3	1397.1	1436.0	1475.6	1507.7	1532.6
20°	1080.0	1123.4	1188.4	1239.5	1299.2	1364.7	1419.7	1459.2	1493.5	1520.4	1535.7
22.5°	1056.4	1111.1	1174.4	1234.2	1310.5	1375.3	1433.0	1464.1	1492.8	1505.9	1511.8
25°	1019.3	1085.2	1156.8	1229.8	1316.0	1384.5	1437.3	1456.1	1464.5	1451.7	1430.6
27.5°	979.3	1052.7	1136.5	1221.5	1312.6	1378.5	1416.3	1413.3	1399.2	1358.0	1325.0
30°	949.3	1030.3	1120.3	1213.1	1304.5	1368.6	1390.7	1368.6	1336.6	1290.5	1243.5
32.5°	918.1	1001.8	1103.1	1201.1	1289.8	1346.2	1350.9	1313.1	1263.4	1211.0	1152.4
35°	870.7	961.2	1070.7	1174.4	1258.4	1294.0	1272.9	1206.1	1147.2	1075.6	995.5
37.5°	817.2	917.1	1026.9	1135.3	1211.3	1220.6	1168.3	1097.9	1014.9	930.7	836.5
40°	777.1	883.0	996.0	1105.4	1172.7	1163.0	1096.1	1018.8	919.9	817.1	729.6
42.5°	741.2	847.1	962.2	1069.5	1123.4	1096.9	1018.8	923.9	817.6	720.7	640.7
45°	679.1	788.1	905.9	1009.6	1040.3	992.5	889.2	783.7	679.1	598.2	534.9
47.5°	618.8	726.5	843.2	934.4	945.2	880.8	767.9	659.4	569.5	503.6	458.9
50°	574.5	682.6	798.1	879.5	876.0	798.1	682.2	578.9	503.7	450.5	420.6
52.5°	534.8	636.9	747.9	821.8	803.2	718.3	607.6	515.9	454.1	412.5	385.5
55°	472.9	567.4	672.9	732.3	697.9	603.9	510.3	436.4	390.7	359.6	338.5
57.5°	411.6	500.2	590.5	627.1	589.2	502.3	424.2	370.7	336.3	313.2	299.5
60°	373.6	451.0	531.4	563.0	517.7	440.4	378.8	331.0	303.2	284.4	272.1
62.5°	335.6	404.9	480.8	498.0	456.6	391.2	336.7	296.9	274.1	257.3	245.7
65°	284.0	340.6	398.2	409.7	371.4	320.9	277.8	251.8	231.6	219.3	210.1
67.5°	232.9	278.4	319.2	328.4	294.9	259.8	228.8	206.1	192.4	182.2	174.4
70°	202.6	238.7	272.1	279.6	252.7	221.5	197.8	179.8	167.5	158.7	151.2
72.5°	170.7	200.7	228.4	233.5	211.5	187.8	168.2	154.1	143.2	137.6	130.4
75°	130.5	148.1	169.6	171.0	156.4	142.0	127.0	117.8	112.1	105.0	101.5
77.5°	92.1	105.9	118.2	120.6	112.0	102.1	93.8	86.5	81.6	78.4	75.2
80°	70.3	81.3	86.6	89.6	83.5	76.5	71.6	66.8	63.7	61.6	59.3
82.5°	50.3	57.1	62.0	64.3	61.0	56.8	51.9	49.2	46.8	45.0	44.3
85°	25.5	28.6	31.7	32.5	31.7	29.9	27.2	27.2	25.9	25.5	25.5
87.5°	9.0	10.6	10.8	12.1	11.5	11.6	11.8	11.5	11.3	11.0	10.8
90°	1.3	2.2	3.1	4.0	4.7	5.4	6.0	6.7	7.3	7.7	8.2
92.5°	7.3	7.2	7.1	7.1	7.2	7.6	7.9	8.2	8.5	8.8	9.0
95°	21.2	18.5	15.8	13.1	12.1	12.7	13.2	13.8	14.4	14.7	15.2
97.5°	39.9	32.3	24.6	17.0	13.9	15.2	16.5	17.9	19.2	19.5	19.9
100°	53.9	42.7	31.5	20.3	15.4	16.8	18.2	19.5	21.0	21.6	22.3
102.5°	82.2	79.8	77.5	75.1	68.1	56.5	44.9	33.2	21.5	22.4	23.2
105°	114.3	116.8	119.2	121.7	111.8	89.5	67.1	44.8	22.5	23.3	24.3
107.5°	145.0	147.0	149.0	150.9	138.5	111.8	85.0	58.2	31.4	30.5	29.6
110°	164.7	166.4	168.2	169.9	158.9	135.3	111.7	88.0	64.4	56.2	48.0



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	183.4	184.9	186.4	188.0	185.8	179.9	174.1	168.2	162.5	132.6	102.8
115°	213.0	214.4	215.8	217.1	218.9	220.9	223.0	225.0	227.0	189.2	151.4
117.5°	239.7	241.3	242.8	244.4	245.9	247.3	248.7	250.1	251.5	242.4	233.2
120°	258.8	260.0	261.3	262.5	263.9	265.4	266.8	268.3	269.8	270.7	271.7
122.5°	275.3	276.6	277.9	279.2	280.7	282.3	283.9	285.5	287.1	287.7	288.3
125°	300.2	301.4	302.4	303.4	304.7	306.3	307.9	309.4	311.0	311.5	312.1
127.5°	323.1	324.3	325.5	326.7	327.8	329.0	330.1	331.3	332.4	333.3	334.2
130°	337.7	339.0	340.3	341.6	342.7	343.6	344.5	345.4	346.3	347.2	348.1
132.5°	352.1	353.3	354.4	355.5	356.5	357.4	358.3	359.2	360.2	360.9	361.7
135°	371.5	372.8	374.1	375.5	376.4	377.2	378.0	378.7	379.4	380.2	381.1
137.5°	390.5	391.4	392.4	393.2	394.1	394.9	395.8	396.6	397.4	398.2	399.1
140°	402.9	403.6	404.2	404.8	405.6	406.6	407.4	408.3	409.2	409.9	410.7
142.5°	413.5	414.0	414.6	415.2	416.0	417.0	418.0	419.0	420.1	420.8	421.5
145°	429.4	429.3	429.2	429.1	429.8	431.2	432.6	433.9	435.3	435.9	436.5
147.5°	443.7	443.3	443.1	442.7	443.2	444.6	446.0	447.4	448.8	449.2	449.6
150°	452.8	452.2	451.7	451.1	451.4	452.8	454.1	455.4	456.7	457.2	457.7
152.5°	460.7	460.0	459.4	458.7	459.1	460.3	461.6	462.8	464.1	464.5	465.0
155°	472.2	471.4	470.7	469.9	470.1	471.1	472.0	473.0	474.0	474.5	475.0
157.5°	481.3	480.7	480.1	479.5	479.5	480.2	480.9	481.6	482.2	482.8	483.4
160°	486.7	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2	487.8	488.2
162.5°	491.5	490.9	490.5	490.0	490.0	490.3	490.8	491.2	491.6	492.2	492.8
165°	497.8	497.3	496.8	496.3	496.2	496.5	496.7	497.0	497.1	497.7	498.3
167.5°	502.5	502.0	501.5	501.0	500.9	501.1	501.4	501.6	501.8	502.4	503.0
170°	505.1	504.6	504.2	503.7	503.5	503.7	503.9	504.0	504.2	504.7	505.3
172.5°	507.0	506.4	505.9	505.4	505.3	505.4	505.6	505.8	505.9	506.5	507.0
175°	509.1	508.5	508.0	507.4	507.2	507.4	507.6	507.6	507.8	508.4	509.0
177.5°	509.6	509.1	508.7	508.2	508.0	508.1	508.2	508.2	508.2	508.8	509.2
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1186.2	1191.1	1191.1	1191.8	1197.5	1196.7	1196.4
5°	1262.3	1269.8	1270.7	1278.6	1283.8	1282.1	1277.3
7.5°	1334.1	1348.1	1358.6	1364.4	1371.4	1375.7	1373.8
10°	1391.1	1411.4	1423.7	1432.0	1442.1	1449.6	1446.9
12.5°	1442.8	1466.9	1483.8	1498.1	1499.4	1509.0	1502.4
15°	1523.4	1548.9	1551.5	1562.1	1570.5	1569.5	1569.9
17.5°	1550.1	1558.2	1559.9	1560.1	1560.2	1557.1	1550.5
20°	1540.5	1537.5	1530.0	1524.3	1514.2	1512.9	1504.1
22.5°	1495.6	1485.7	1467.1	1454.7	1438.9	1434.8	1432.4
25°	1407.0	1385.3	1355.5	1326.9	1319.1	1303.6	1308.0
27.5°	1285.4	1251.8	1219.4	1196.2	1175.2	1152.2	1158.7
30°	1199.9	1162.1	1116.4	1081.2	1058.9	1036.8	1032.9
32.5°	1097.9	1042.6	991.5	960.6	926.3	912.4	897.2
35°	922.1	868.1	817.5	774.0	749.0	729.6	712.0
37.5°	764.0	701.7	661.0	625.7	607.6	596.5	599.3
40°	665.9	611.4	581.5	554.7	538.0	530.0	531.8
42.5°	586.4	545.6	521.0	502.7	490.9	486.5	485.4
45°	496.2	473.4	453.1	442.6	436.9	432.0	429.0
47.5°	434.7	416.0	404.7	398.4	393.4	388.5	388.4
50°	397.8	385.5	377.5	370.9	367.0	363.5	366.5
52.5°	369.6	358.3	350.5	344.6	343.1	339.9	339.8
55°	327.9	319.1	313.4	308.1	305.5	303.7	301.5
57.5°	289.9	281.5	276.3	272.9	267.9	266.1	265.4
60°	262.9	256.2	251.0	246.6	244.4	240.8	240.8
62.5°	237.9	231.3	226.4	223.0	219.4	218.0	218.3
65°	201.7	196.5	191.7	188.1	187.3	184.6	185.5
67.5°	168.5	165.0	159.9	158.0	156.3	154.9	153.9
70°	146.4	142.8	140.2	137.6	136.2	136.2	136.2
72.5°	127.7	123.5	121.9	118.6	119.3	118.0	116.6
75°	98.9	96.3	95.0	93.6	91.4	91.4	91.4
77.5°	72.8	72.0	70.4	69.0	68.4	68.0	68.2
80°	56.2	55.8	54.9	54.9	54.1	53.6	52.8
82.5°	43.2	42.1	41.6	41.2	41.1	41.0	40.8
85°	24.6	23.8	23.8	24.2	23.3	23.3	23.8
87.5°	11.2	11.3	11.0	11.0	11.5	11.1	11.1
90°	8.6	9.0	9.3	9.5	9.6	9.8	9.9
92.5°	9.2	9.4	9.6	9.6	9.7	9.8	9.9
95°	15.6	16.0	16.2	16.1	16.0	15.9	15.8
97.5°	20.2	20.5	20.8	20.8	20.9	21.0	21.1
100°	22.9	23.6	24.0	24.2	24.4	24.5	24.6
102.5°	24.1	25.0	25.5	25.7	26.0	26.2	26.4
105°	25.1	26.1	26.7	26.9	27.3	27.6	28.0
107.5°	28.7	27.7	27.5	27.8	28.2	28.4	28.8
110°	39.9	31.7	27.7	28.1	28.4	28.8	29.1



TEST NUMBER: P331525-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	72.9	43.1	28.3	28.6	28.8	29.1	29.4
115°	113.5	75.6	53.7	47.9	41.9	36.1	30.1
117.5°	224.0	214.8	200.6	181.2	161.9	142.6	123.2
120°	272.7	273.7	268.6	257.6	246.6	235.5	224.5
122.5°	288.9	289.5	288.7	286.5	284.4	282.2	280.1
125°	312.7	313.2	313.7	313.9	314.2	314.4	314.6
127.5°	334.9	335.8	336.2	336.3	336.3	336.4	336.4
130°	349.0	349.9	350.3	350.3	350.2	350.1	350.0
132.5°	362.4	363.2	363.5	363.4	363.3	363.3	363.3
135°	381.9	382.7	383.0	382.9	382.7	382.5	382.4
137.5°	399.8	400.6	400.9	400.6	400.4	400.1	399.8
140°	411.5	412.2	412.3	411.9	411.5	411.1	410.7
142.5°	422.1	422.8	422.9	422.5	422.1	421.7	421.3
145°	437.0	437.6	437.7	437.3	436.9	436.5	436.1
147.5°	450.0	450.5	450.5	450.1	449.8	449.4	449.1
150°	458.1	458.7	458.7	458.3	457.9	457.4	457.1
152.5°	465.5	466.1	466.0	465.5	464.9	464.3	463.8
155°	475.4	476.0	475.9	475.2	474.6	473.9	473.3
157.5°	483.9	484.5	484.4	483.8	483.1	482.5	481.9
160°	488.7	489.2	489.1	488.6	488.0	487.4	486.9
162.5°	493.4	493.9	493.8	493.1	492.4	491.7	491.0
165°	498.9	499.5	499.5	498.9	498.3	497.7	497.1
167.5°	503.5	504.1	504.0	503.3	502.6	501.8	501.1
170°	505.9	506.4	506.4	505.7	504.9	504.2	503.4
172.5°	507.6	508.2	508.2	507.4	506.7	505.9	505.2
175°	509.5	510.1	510.1	509.2	508.4	507.6	506.8
177.5°	509.6	510.1	510.1	509.5	508.9	508.2	507.7
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6

(END OF REPORT)