

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331800-940

Luminaire Tested: **S122RDIW-S485D1240U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331800-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1240U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5350.1 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331800-940

CATALOG NUMBER: S122RDIW-S485D1240U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331800-940

CATALOG NUMBER: S122RDIW-S485D1240U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	32	32	31
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23
4	71	61	53	48	63	55	49	44	44	39	36	33	30	28	23	21	20
5	65	54	47	41	58	49	42	37	39	34	31	30	27	24	21	19	17
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	16
7	56	44	36	31	50	40	33	29	32	27	24	24	21	19	18	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11880	11880	11880
5°	11925	11733	11797
10°	11835	11540	11442
15°	11699	11198	10877
20°	11510	10710	10172
25°	11318	10156	9492
30°	11050	9587	8617
35°	10789	8966	7849
40°	10526	8323	6962
45°	10218	7604	6158
50°	9902	6875	5368
55°	9579	6092	4611
60°	9203	5270	3827
65°	8779	4424	3484
70°	8266	3644	3205
75°	7642	3319	2994
80°	6750	2966	2724
85°	5298	2353	2353



TEST NUMBER: P331800-940

CATALOG NUMBER: S122RDIW-S485D1240U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.9	1.3
10°-20°	189.1	3.5
20°-30°	265.6	5.0
30°-40°	289.6	5.4
40°-50°	266.3	5.0
50°-60°	209.1	3.9
60°-70°	136.4	2.5
70°-80°	70.3	1.3
80°-90°	23.7	0.4
90°-100°	86.8	1.6
100°-110°	269.6	5.0
110°-120°	460.9	8.6
120°-130°	606.1	11.3
130°-140°	680.3	12.7
140°-150°	667.1	12.5
150°-160°	559.5	10.5
160°-170°	371.1	6.9
170°-180°	129.7	2.4
0°-30°	523.6	9.8
0°-40°	813.2	15.2
0°-60°	1288.6	24.1
0°-90°	1519.0	28.4
90°-120°	817.4	15.3
90°-150°	2770.9	51.8
90°-180°	3831.0	71.6
0°-180°	5350.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	736	736	736	736	736	
5°	736	732	724	729	728	70
15°	700	692	670	658	651	197
25°	635	613	570	544	533	292
35°	547	512	455	414	398	342
45°	448	402	333	287	270	345
55°	340	287	216	178	164	304
65°	230	176	116	94	91	228
75°	122	77	53	49	48	130
85°	29	15	13	13	13	34
90°	1	16	40	38	39	4
95°	60	71	74	74	72	69
105°	249	252	254	257	257	263
115°	462	469	467	466	462	457
125°	673	683	680	677	675	601
135°	871	883	886	884	881	672
145°	1057	1065	1072	1073	1068	660
155°	1208	1212	1215	1220	1218	556
165°	1315	1314	1314	1321	1316	371
175°	1368	1364	1362	1369	1363	130
180°	1370	1370	1370	1370	1370	



TEST NUMBER: P331800-940

CATALOG NUMBER: S122RDIW-S485D1240U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	738.5	738.0	737.4	736.7	736.2	735.2	734.0	732.6	731.3	730.0	731.2
5°	735.8	735.1	734.4	733.7	732.9	731.6	729.7	727.7	725.9	723.9	725.2
7.5°	728.3	727.4	726.5	725.5	724.6	723.0	720.8	718.5	716.3	714.1	714.4
10°	721.9	720.9	719.8	718.8	717.7	715.8	712.8	709.8	706.9	703.9	703.5
12.5°	713.9	712.7	711.3	710.1	708.8	706.3	702.5	698.7	694.9	691.2	690.4
15°	699.9	698.3	696.7	695.0	693.4	690.1	685.0	680.0	675.0	669.9	667.2
17.5°	682.8	680.3	677.8	675.3	672.8	668.3	661.9	655.4	649.0	642.5	639.2
20°	669.9	667.0	664.1	661.1	658.1	652.9	645.5	638.1	630.7	623.3	619.6
22.5°	656.1	652.8	649.4	646.1	642.8	637.0	628.7	620.3	612.0	603.6	598.9
25°	635.3	630.6	625.9	621.1	616.4	609.1	599.3	589.6	579.8	570.1	564.0
27.5°	610.3	605.1	599.9	594.9	589.7	581.6	570.6	559.5	548.6	537.5	530.5
30°	592.7	587.1	581.5	575.9	570.2	561.5	549.7	537.8	525.9	514.2	506.6
32.5°	575.7	569.1	562.5	556.0	549.4	540.0	528.0	515.9	503.8	491.8	483.1
35°	547.4	539.8	532.4	524.8	517.2	506.9	493.9	480.9	467.9	454.9	445.5
37.5°	519.2	510.9	502.6	494.3	486.1	474.9	461.1	447.2	433.3	419.5	409.1
40°	499.4	490.6	481.7	472.9	464.0	452.4	438.0	423.7	409.3	394.9	384.4
42.5°	479.2	469.8	460.5	451.2	441.8	429.7	414.9	400.0	385.2	370.4	359.5
45°	447.5	437.7	427.7	417.8	407.9	395.1	379.6	364.1	348.5	333.0	322.4
47.5°	416.6	406.1	395.7	385.1	374.6	361.3	345.3	329.2	313.2	297.1	286.7
50°	394.2	383.7	373.3	362.7	352.2	338.9	322.5	306.3	290.0	273.7	263.5
52.5°	372.4	361.4	350.4	339.5	328.5	315.0	299.1	283.2	267.2	251.4	241.5
55°	340.3	328.8	317.2	305.7	294.2	280.4	264.4	248.4	232.4	216.4	207.6
57.5°	307.4	295.6	283.7	271.9	260.0	246.5	231.1	215.7	200.4	185.0	176.8
60°	285.0	273.2	261.4	249.5	237.6	224.2	208.9	193.7	178.4	163.2	155.6
62.5°	263.1	251.4	239.5	227.7	215.8	202.7	188.2	173.6	159.1	144.5	137.3
65°	229.8	217.8	205.8	193.8	181.8	169.2	155.9	142.5	129.2	115.8	110.8
67.5°	197.5	185.7	173.7	161.8	149.9	137.9	126.0	114.0	102.0	90.1	87.7
70°	175.1	163.6	152.0	140.5	128.9	118.1	107.9	97.6	87.5	77.2	75.8
72.5°	153.8	142.8	131.7	120.6	109.6	100.0	91.8	83.6	75.3	67.1	65.9
75°	122.5	112.2	101.8	91.5	81.1	73.4	68.4	63.3	58.3	53.2	52.3
77.5°	91.8	82.7	73.6	64.5	55.5	49.7	47.3	44.9	42.4	39.9	39.3
80°	72.6	65.0	57.5	49.9	42.4	37.9	36.4	35.0	33.4	31.9	31.4
82.5°	55.0	49.1	43.2	37.4	31.5	28.0	27.0	25.9	25.0	24.0	23.6
85°	28.6	25.5	22.4	19.4	16.2	14.4	14.0	13.6	13.1	12.7	12.7
87.5°	8.7	8.4	8.1	7.8	7.4	7.8	9.0	10.1	11.2	12.4	12.1
90°	1.2	4.3	7.3	10.4	13.5	17.8	23.5	29.2	34.8	40.5	39.9
92.5°	20.6	22.8	25.1	27.4	29.6	31.4	32.7	34.1	35.4	36.7	36.8
95°	60.1	62.7	65.3	67.9	70.4	72.0	72.5	72.9	73.5	74.0	74.0
97.5°	109.9	112.1	114.4	116.6	118.9	120.5	121.5	122.4	123.4	124.4	124.4
100°	146.9	148.9	151.0	153.0	155.1	156.5	157.2	158.0	158.8	159.5	159.5
102.5°	185.7	187.3	189.0	190.6	192.3	193.6	194.6	195.6	196.5	197.5	197.7
105°	248.6	249.3	250.1	250.9	251.6	252.4	252.8	253.3	253.9	254.4	254.9
107.5°	311.9	313.1	314.2	315.3	316.5	317.0	317.0	317.0	317.0	317.0	317.3
110°	352.7	354.2	355.7	357.3	358.8	359.6	359.6	359.6	359.6	359.6	359.6



TEST NUMBER: P331800-940

CATALOG NUMBER: S122RDIW-S485D1240U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	397.1	398.6	400.1	401.7	403.2	403.9	403.7	403.5	403.2	403.1	402.4
115°	462.5	464.0	465.6	467.1	468.7	469.1	468.7	468.1	467.6	467.1	466.9
117.5°	527.7	529.8	531.8	533.9	535.9	536.3	534.8	533.3	531.9	530.5	529.9
120°	571.1	573.2	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1	571.1
122.5°	610.9	613.4	615.9	618.3	620.8	621.3	619.9	618.5	617.0	615.5	614.9
125°	672.9	675.2	677.5	679.8	682.2	683.0	682.2	681.4	680.6	679.8	679.1
127.5°	733.3	736.2	739.1	742.1	745.0	746.0	745.1	744.1	743.2	742.3	741.4
130°	771.2	774.5	777.9	781.2	784.5	786.0	785.5	785.0	784.4	783.9	783.4
132.5°	813.8	816.5	819.2	821.9	824.7	826.1	826.2	826.3	826.3	826.4	825.4
135°	870.7	873.4	876.3	879.1	882.0	883.6	884.1	884.7	885.2	885.6	885.4
137.5°	930.5	932.8	935.1	937.5	939.8	941.3	941.9	942.6	943.3	944.0	943.8
140°	966.6	968.9	971.3	973.6	975.9	977.7	978.9	980.3	981.5	982.8	982.8
142.5°	1003.6	1005.9	1008.3	1010.6	1012.9	1014.4	1015.3	1016.2	1017.1	1018.0	1018.2
145°	1056.8	1058.6	1060.4	1062.2	1064.0	1065.7	1067.2	1068.7	1070.3	1071.8	1072.1
147.5°	1104.2	1106.3	1108.5	1110.7	1112.9	1114.5	1115.4	1116.5	1117.5	1118.6	1119.1
150°	1136.6	1138.1	1139.7	1141.2	1142.7	1144.1	1145.0	1146.1	1147.1	1148.2	1148.9
152.5°	1165.3	1166.8	1168.3	1169.8	1171.4	1172.8	1174.0	1175.3	1176.5	1177.8	1178.8
155°	1208.3	1209.1	1209.8	1210.6	1211.4	1212.1	1212.9	1213.6	1214.4	1215.2	1216.5
157.5°	1245.0	1245.5	1246.1	1246.6	1247.1	1247.6	1248.0	1248.5	1248.9	1249.5	1251.2
160°	1267.2	1267.7	1268.3	1268.8	1269.3	1269.7	1269.9	1270.2	1270.4	1270.7	1272.2
162.5°	1287.5	1287.7	1287.8	1287.9	1288.0	1288.2	1288.4	1288.7	1289.0	1289.2	1290.9
165°	1314.6	1314.4	1314.1	1313.8	1313.6	1313.5	1313.5	1313.5	1313.5	1313.5	1315.3
167.5°	1337.3	1336.5	1335.8	1335.0	1334.2	1333.8	1333.7	1333.7	1333.6	1333.6	1335.4
170°	1349.3	1348.5	1347.8	1347.0	1346.2	1345.8	1345.5	1345.2	1345.0	1344.7	1346.5
172.5°	1357.6	1356.9	1356.1	1355.3	1354.6	1354.1	1353.8	1353.5	1353.3	1353.0	1354.9
175°	1367.8	1367.1	1366.3	1365.5	1364.8	1364.1	1363.6	1363.1	1362.5	1362.0	1363.9
177.5°	1372.0	1371.4	1370.7	1370.1	1369.5	1369.0	1368.6	1368.2	1367.8	1367.3	1368.6
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331800-940

CATALOG NUMBER: S122RDIW-S485D1240U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	732.4	733.6	734.8	735.2	735.0	734.8	734.5	734.3
5°	726.6	727.9	729.2	729.7	729.2	728.8	728.3	727.9
7.5°	714.8	715.2	715.6	715.4	714.6	713.8	713.1	712.3
10°	703.0	702.6	702.1	701.5	700.6	699.7	698.8	697.9
12.5°	689.6	688.8	688.0	686.8	685.3	683.9	682.3	680.9
15°	664.3	661.6	658.7	656.6	655.1	653.6	652.1	650.7
17.5°	635.8	632.5	629.1	626.2	623.7	621.1	618.6	616.0
20°	615.9	612.2	608.5	605.0	601.8	598.5	595.3	592.0
22.5°	594.1	589.3	584.6	580.9	578.5	576.1	573.7	571.2
25°	557.9	551.9	545.8	541.6	539.4	537.2	535.0	532.8
27.5°	523.4	516.3	509.3	504.0	500.4	497.0	493.4	489.9
30°	499.0	491.5	483.9	478.1	474.1	470.2	466.2	462.2
32.5°	474.5	465.9	457.3	451.1	447.4	443.6	439.8	436.0
35°	436.2	426.9	417.6	411.3	408.0	404.7	401.5	398.2
37.5°	398.9	388.6	378.4	371.3	367.7	363.9	360.2	356.4
40°	373.9	363.4	352.8	345.7	341.9	338.0	334.1	330.3
42.5°	348.7	337.8	327.0	319.7	315.9	312.2	308.4	304.7
45°	311.9	301.5	291.0	283.9	280.4	276.8	273.2	269.7
47.5°	276.3	265.8	255.4	248.5	245.3	242.1	238.8	235.6
50°	253.2	243.1	232.8	226.2	223.1	220.0	216.9	213.7
52.5°	231.6	221.8	211.9	205.5	202.7	199.8	196.9	194.0
55°	198.7	189.8	180.9	175.0	172.3	169.4	166.7	163.8
57.5°	168.7	160.6	152.5	147.2	144.8	142.5	140.1	137.7
60°	148.0	140.5	133.0	128.0	125.6	123.2	120.9	118.5
62.5°	130.1	123.0	115.7	111.5	110.0	108.6	107.2	105.8
65°	105.8	100.8	95.8	93.0	92.6	92.1	91.7	91.2
67.5°	85.4	83.1	80.8	79.5	78.9	78.5	78.0	77.5
70°	74.3	72.9	71.3	70.3	69.7	69.1	68.5	67.9
72.5°	64.6	63.4	62.2	61.3	61.0	60.6	60.3	59.9
75°	51.2	50.2	49.1	48.5	48.4	48.2	48.1	48.0
77.5°	38.8	38.2	37.6	37.2	36.9	36.7	36.5	36.2
80°	30.8	30.2	29.6	29.3	29.3	29.3	29.3	29.3
82.5°	23.3	22.9	22.6	22.4	22.4	22.4	22.4	22.4
85°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7
87.5°	11.9	11.7	11.5	11.4	11.4	11.5	11.5	11.6
90°	39.4	39.0	38.4	38.3	38.5	38.8	39.1	39.3
92.5°	37.0	37.1	37.2	37.3	37.3	37.4	37.5	37.5
95°	74.0	74.0	74.0	73.7	73.2	72.7	72.2	71.7
97.5°	124.4	124.4	124.4	124.4	124.3	124.3	124.2	124.2
100°	159.5	159.5	159.5	159.4	159.2	158.9	158.6	158.4
102.5°	197.9	198.1	198.3	198.3	198.0	197.8	197.5	197.2
105°	255.4	255.9	256.5	256.7	256.7	256.7	256.7	256.7
107.5°	317.4	317.6	317.9	317.4	316.2	315.0	313.8	312.6
110°	359.6	359.6	359.6	359.2	358.5	357.7	356.9	356.1



TEST NUMBER: P331800-940

CATALOG NUMBER: S122RDIW-S485D1240U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	401.8	401.2	400.6	400.0	399.4	398.9	398.3	397.7
115°	466.6	466.4	466.1	465.6	464.8	464.0	463.2	462.5
117.5°	529.2	528.6	528.0	527.4	526.6	525.8	525.0	524.2
120°	571.1	571.1	571.1	570.8	570.0	569.3	568.5	567.8
122.5°	614.4	613.8	613.1	612.5	612.0	611.4	610.8	610.3
125°	678.3	677.5	676.8	676.3	676.0	675.7	675.5	675.2
127.5°	740.5	739.5	738.6	737.7	736.9	736.1	735.3	734.4
130°	782.9	782.4	781.9	781.1	780.1	779.1	778.0	776.9
132.5°	824.2	823.0	822.0	821.0	820.2	819.3	818.5	817.7
135°	885.2	884.9	884.7	884.1	883.3	882.6	881.8	881.0
137.5°	943.5	943.3	943.2	942.5	941.5	940.5	939.4	938.4
140°	982.8	982.8	982.8	982.3	981.2	980.3	979.2	978.2
142.5°	1018.3	1018.6	1018.8	1018.3	1017.4	1016.3	1015.3	1014.2
145°	1072.4	1072.6	1072.8	1072.5	1071.5	1070.4	1069.4	1068.4
147.5°	1119.6	1120.3	1120.8	1120.6	1119.6	1118.7	1117.7	1116.7
150°	1149.7	1150.5	1151.2	1151.2	1150.5	1149.7	1148.9	1148.2
152.5°	1179.7	1180.6	1181.6	1181.6	1180.6	1179.7	1178.8	1177.8
155°	1217.8	1219.1	1220.3	1220.6	1219.9	1219.1	1218.3	1217.5
157.5°	1252.9	1254.6	1256.4	1256.7	1255.4	1254.2	1252.9	1251.7
160°	1273.8	1275.3	1276.8	1277.1	1276.1	1275.1	1274.1	1273.0
162.5°	1292.7	1294.4	1296.2	1296.5	1295.2	1294.0	1292.7	1291.6
165°	1317.1	1318.8	1320.7	1320.9	1319.6	1318.4	1317.1	1315.8
167.5°	1337.2	1339.0	1340.8	1341.0	1339.7	1338.4	1337.0	1335.7
170°	1348.3	1350.1	1351.9	1352.0	1350.5	1349.0	1347.4	1345.9
172.5°	1356.6	1358.4	1360.2	1360.3	1358.8	1357.3	1355.8	1354.2
175°	1365.7	1367.4	1369.2	1369.4	1367.8	1366.3	1364.8	1363.2
177.5°	1369.8	1371.1	1372.3	1372.3	1371.1	1369.8	1368.6	1367.3
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1

(END OF REPORT)