

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331531-935

Luminaire Tested: **S122DIW-S675D710U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331531-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S675D710U935-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4966.3 lumens  
Efficiency: N/A  
Efficacy: 110.4 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	46	44	42	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	23	28	24	21	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	18466	18466	18466	18466
5°	20702	18585	16470	18585
10°	23722	18433	14254	18433
15°	26242	18094	12593	18094
20°	25844	17732	11478	17732
25°	23302	17250	10774	17250
30°	19257	16479	10260	16479
35°	14034	15672	9895	15672
40°	11209	14720	9691	14720
45°	9796	13618	9412	13618
50°	9206	12552	9231	12552
55°	8487	11468	8982	11468
60°	7776	10317	8603	10317
65°	7087	9287	8225	9287
70°	6430	8280	7676	8280
75°	5702	7155	6800	7155
80°	4909	5923	5477	5923
85°	4409	4409	3260	4409



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.9	2.2
10°-20°	316.6	6.4
20°-30°	459.5	9.3
30°-40°	484.9	9.8
40°-50°	429.4	8.6
50°-60°	342.6	6.9
60°-70°	232.9	4.7
70°-80°	119.4	2.4
80°-90°	30.8	0.6
90°-100°	27.8	0.6
100°-110°	101.9	2.1
110°-120°	272.4	5.5
120°-130°	449.6	9.1
130°-140°	478.2	9.6
140°-150°	444.4	8.9
150°-160°	357.3	7.2
160°-170°	230.3	4.6
170°-180°	79.3	1.6
0°-30°	885.1	17.8
0°-40°	1370.0	27.6
0°-60°	2142.0	43.1
0°-90°	2525.2	50.8
90°-120°	402.1	8.1
90°-150°	1774.3	35.7
90°-180°	2441.0	49.2
0°-180°	4966.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1144	1144	1144	1144	1144	
5°	1277	1147	1016	1147	1277	128
15°	1570	1082	753	1082	1570	433
25°	1308	968	605	968	1308	591
35°	712	795	502	795	712	463
45°	429	596	412	596	429	337
55°	302	407	319	407	302	270
65°	186	243	215	243	186	184
75°	91	115	109	115	91	98
85°	24	24	18	24	24	26
90°	16	1	16	1	16	8
95°	26	39	26	39	26	24
105°	46	183	46	183	46	48
115°	49	347	49	347	49	124
125°	515	490	515	490	515	446
135°	626	606	626	606	626	483
145°	714	703	714	703	714	447
155°	775	775	775	775	775	358
165°	814	816	814	816	814	230
175°	830	835	830	835	830	79
180°	833	833	833	833	833	



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1196.4	1196.7	1197.5	1191.8	1191.1	1191.1	1186.2	1182.0	1177.1	1170.4	1171.0
5°	1277.3	1282.1	1283.8	1278.6	1270.7	1269.8	1262.3	1250.0	1238.5	1229.3	1222.8
7.5°	1373.8	1375.7	1371.4	1364.4	1358.6	1348.1	1334.1	1320.5	1301.4	1283.9	1270.9
10°	1446.9	1449.6	1442.1	1432.0	1423.7	1411.4	1391.1	1370.5	1345.4	1321.2	1301.8
12.5°	1502.4	1509.0	1499.4	1498.1	1483.8	1466.9	1442.8	1432.4	1397.1	1363.4	1342.6
15°	1569.9	1569.5	1570.5	1562.1	1551.5	1548.9	1523.4	1495.7	1446.0	1426.2	1392.0
17.5°	1550.5	1557.1	1560.2	1560.1	1559.9	1558.2	1550.1	1532.6	1507.7	1475.6	1436.0
20°	1504.1	1512.9	1514.2	1524.3	1530.0	1537.5	1540.5	1535.7	1520.4	1493.5	1459.2
22.5°	1432.4	1434.8	1438.9	1454.7	1467.1	1485.7	1495.6	1511.8	1505.9	1492.8	1464.1
25°	1308.0	1303.6	1319.1	1326.9	1355.5	1385.3	1407.0	1430.6	1451.7	1464.5	1456.1
27.5°	1158.7	1152.2	1175.2	1196.2	1219.4	1251.8	1285.4	1325.0	1358.0	1399.2	1413.3
30°	1032.9	1036.8	1058.9	1081.2	1116.4	1162.1	1199.9	1243.5	1290.5	1336.6	1368.6
32.5°	897.2	912.4	926.3	960.6	991.5	1042.6	1097.9	1152.4	1211.0	1263.4	1313.1
35°	712.0	729.6	749.0	774.0	817.5	868.1	922.1	995.5	1075.6	1147.2	1206.1
37.5°	599.3	596.5	607.6	625.7	661.0	701.7	764.0	836.5	930.7	1014.9	1097.9
40°	531.8	530.0	538.0	554.7	581.5	611.4	665.9	729.6	817.1	919.9	1018.8
42.5°	485.4	486.5	490.9	502.7	521.0	545.6	586.4	640.7	720.7	817.6	923.9
45°	429.0	432.0	436.9	442.6	453.1	473.4	496.2	534.9	598.2	679.1	783.7
47.5°	388.4	388.5	393.4	398.4	404.7	416.0	434.7	458.9	503.6	569.5	659.4
50°	366.5	363.5	367.0	370.9	377.5	385.5	397.8	420.6	450.5	503.7	578.9
52.5°	339.8	339.9	343.1	344.6	350.5	358.3	369.6	385.5	412.5	454.1	515.9
55°	301.5	303.7	305.5	308.1	313.4	319.1	327.9	338.5	359.6	390.7	436.4
57.5°	265.4	266.1	267.9	272.9	276.3	281.5	289.9	299.5	313.2	336.3	370.7
60°	240.8	240.8	244.4	246.6	251.0	256.2	262.9	272.1	284.4	303.2	331.0
62.5°	218.3	218.0	219.4	223.0	226.4	231.3	237.9	245.7	257.3	274.1	296.9
65°	185.5	184.6	187.3	188.1	191.7	196.5	201.7	210.1	219.3	231.6	251.8
67.5°	153.9	154.9	156.3	158.0	159.9	165.0	168.5	174.4	182.2	192.4	206.1
70°	136.2	136.2	136.2	137.6	140.2	142.8	146.4	151.2	158.7	167.5	179.8
72.5°	116.6	118.0	119.3	118.6	121.9	123.5	127.7	130.4	137.6	143.2	154.1
75°	91.4	91.4	91.4	93.6	95.0	96.3	98.9	101.5	105.0	112.1	117.8
77.5°	68.2	68.0	68.4	69.0	70.4	72.0	72.8	75.2	78.4	81.6	86.5
80°	52.8	53.6	54.1	54.9	54.9	55.8	56.2	59.3	61.6	63.7	66.8
82.5°	40.8	41.0	41.1	41.2	41.6	42.1	43.2	44.3	45.0	46.8	49.2
85°	23.8	23.3	23.3	24.2	23.8	23.8	24.6	25.5	25.5	25.9	27.2
87.5°	12.4	12.3	12.7	12.2	12.1	12.4	12.3	11.8	12.1	12.2	12.4
90°	16.3	16.0	15.8	15.5	15.2	14.7	14.0	13.4	12.7	12.1	11.0
92.5°	16.3	16.1	15.9	15.8	15.7	15.4	15.1	14.7	14.3	13.9	13.4
95°	25.9	26.1	26.2	26.3	26.4	26.2	25.5	24.9	24.2	23.5	22.6
97.5°	34.6	34.4	34.3	34.1	33.9	33.6	33.1	32.5	32.0	31.4	29.3
100°	40.4	40.1	39.9	39.6	39.3	38.7	37.5	36.5	35.4	34.4	32.1
102.5°	43.3	42.9	42.5	42.2	41.8	40.9	39.5	38.1	36.7	35.3	34.3
105°	45.8	45.3	44.8	44.2	43.7	42.6	41.2	39.7	38.2	36.8	35.4
107.5°	47.1	46.6	46.1	45.5	45.0	45.5	47.0	48.5	49.9	51.5	53.1
110°	47.6	47.1	46.6	46.0	45.5	51.9	65.3	78.7	92.1	105.5	144.2



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	48.1	47.7	47.3	46.8	46.4	70.6	119.5	168.3	217.2	266.0	275.6
115°	49.4	59.1	68.7	78.4	88.0	123.8	185.8	247.9	309.9	371.9	368.5
117.5°	201.8	233.5	265.2	296.9	328.6	351.9	366.9	381.9	396.9	411.9	409.6
120°	367.6	385.7	403.8	421.9	440.0	448.2	446.6	445.1	443.4	441.8	439.4
122.5°	458.8	462.4	465.8	469.3	472.9	474.2	473.1	472.2	471.2	470.3	467.6
125°	515.3	515.0	514.5	514.1	513.8	513.1	512.1	511.2	510.2	509.3	506.8
127.5°	551.0	551.0	550.9	550.8	550.7	550.0	548.6	547.3	545.9	544.5	542.6
130°	573.3	573.3	573.5	573.6	573.8	573.1	571.6	570.2	568.7	567.2	565.7
132.5°	595.0	595.0	595.2	595.3	595.5	594.9	593.7	592.4	591.1	589.9	588.4
135°	626.3	626.5	626.8	627.1	627.3	626.8	625.4	624.1	622.8	621.5	620.3
137.5°	654.8	655.3	655.7	656.2	656.7	656.3	654.9	653.6	652.3	651.0	649.6
140°	672.7	673.3	674.0	674.7	675.4	675.1	673.9	672.7	671.5	670.3	668.7
142.5°	690.0	690.7	691.4	692.1	692.7	692.5	691.4	690.3	689.2	688.1	686.4
145°	714.3	714.9	715.6	716.3	717.0	716.8	715.8	714.9	714.0	713.1	710.8
147.5°	735.6	736.2	736.8	737.3	737.9	737.8	737.1	736.4	735.7	734.9	732.7
150°	748.6	749.2	749.9	750.6	751.3	751.2	750.4	749.6	748.8	748.0	745.9
152.5°	759.7	760.6	761.5	762.3	763.3	763.3	762.5	761.6	760.9	760.1	758.0
155°	775.2	776.2	777.3	778.3	779.4	779.5	778.8	777.9	777.1	776.4	774.7
157.5°	789.2	790.3	791.3	792.4	793.4	793.5	792.6	791.7	790.7	789.8	788.7
160°	797.5	798.4	799.3	800.2	801.2	801.2	800.5	799.6	798.8	798.1	797.2
162.5°	804.2	805.3	806.5	807.6	808.8	808.9	808.0	807.1	806.2	805.3	804.6
165°	814.3	815.3	816.2	817.1	818.0	818.0	817.1	816.2	815.3	814.3	813.9
167.5°	820.7	821.9	823.1	824.3	825.5	825.6	824.8	823.8	822.9	821.9	821.6
170°	824.6	825.8	827.0	828.2	829.4	829.5	828.5	827.7	826.7	825.8	825.5
172.5°	827.4	828.6	829.8	831.0	832.2	832.4	831.5	830.5	829.6	828.6	828.4
175°	830.0	831.3	832.7	834.0	835.3	835.5	834.6	833.7	832.8	831.8	831.6
177.5°	831.6	832.5	833.4	834.5	835.4	835.5	834.7	834.1	833.3	832.5	832.4
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1173.5	1170.7	1169.0	1162.6	1157.0	1151.4	1149.6	1150.3	1142.6	1135.2	1132.0
5°	1219.3	1210.5	1202.1	1190.2	1176.2	1160.8	1152.9	1146.7	1131.4	1114.7	1105.0
7.5°	1260.2	1247.7	1231.6	1209.2	1188.8	1164.6	1149.2	1135.6	1113.0	1089.5	1075.0
10°	1285.2	1268.0	1247.3	1220.1	1195.1	1165.6	1145.0	1124.3	1097.9	1069.8	1052.2
12.5°	1306.7	1283.5	1263.2	1228.2	1198.6	1161.7	1137.2	1108.1	1080.4	1047.0	1029.8
15°	1357.7	1315.1	1276.3	1236.8	1200.3	1148.9	1121.7	1082.5	1046.0	1004.8	985.0
17.5°	1397.1	1349.3	1288.3	1238.0	1195.5	1138.6	1098.5	1051.7	1008.6	961.3	934.4
20°	1419.7	1364.7	1299.2	1239.5	1188.4	1123.4	1080.0	1032.0	981.5	928.2	899.2
22.5°	1433.0	1375.3	1310.5	1234.2	1174.4	1111.1	1056.4	1003.8	952.6	895.3	864.8
25°	1437.3	1384.5	1316.0	1229.8	1156.8	1085.2	1019.3	968.3	906.3	852.6	808.3
27.5°	1416.3	1378.5	1312.6	1221.5	1136.5	1052.7	979.3	921.5	856.1	797.9	753.3
30°	1390.7	1368.6	1304.5	1213.1	1120.3	1030.3	949.3	883.9	818.8	759.9	714.2
32.5°	1350.9	1346.2	1289.8	1201.1	1103.1	1001.8	918.1	851.9	779.8	721.9	678.4
35°	1272.9	1294.0	1258.4	1174.4	1070.7	961.2	870.7	795.1	720.4	665.0	624.1
37.5°	1168.3	1220.6	1211.3	1135.3	1026.9	917.1	817.2	738.1	666.9	611.1	570.9
40°	1096.1	1163.0	1172.7	1105.4	996.0	883.0	777.1	698.4	629.0	578.0	537.5
42.5°	1018.8	1096.9	1123.4	1069.5	962.2	847.1	741.2	659.7	591.0	541.4	505.6
45°	889.2	992.5	1040.3	1009.6	905.9	788.1	679.1	596.4	534.0	487.4	459.8
47.5°	767.9	880.8	945.2	934.4	843.2	726.5	618.8	539.5	478.7	441.5	416.7
50°	682.2	798.1	876.0	879.5	798.1	682.6	574.5	499.7	443.9	409.2	389.0
52.5°	607.6	718.3	803.2	821.8	747.9	636.9	534.8	460.4	411.2	379.3	361.2
55°	510.3	603.9	697.9	732.3	672.9	567.4	472.9	407.4	361.3	339.3	323.5
57.5°	424.2	502.3	589.2	627.1	590.5	500.2	411.6	354.7	317.3	298.0	285.9
60°	378.8	440.4	517.7	563.0	531.4	451.0	373.6	319.5	288.8	271.6	260.2
62.5°	336.7	391.2	456.6	498.0	480.8	404.9	335.6	287.9	261.3	245.2	237.0
65°	277.8	320.9	371.4	409.7	398.2	340.6	284.0	243.1	222.0	209.2	202.6
67.5°	228.8	259.8	294.9	328.4	319.2	278.4	232.9	201.0	185.3	174.4	170.4
70°	197.8	221.5	252.7	279.6	272.1	238.7	202.6	175.4	161.8	152.5	148.5
72.5°	168.2	187.8	211.5	233.5	228.4	200.7	170.7	150.1	139.6	131.0	127.8
75°	127.0	142.0	156.4	171.0	169.6	148.1	130.5	114.7	106.3	99.8	98.4
77.5°	93.8	102.1	112.0	120.6	118.2	105.9	92.1	83.1	76.9	72.5	71.8
80°	71.6	76.5	83.5	89.6	86.6	81.3	70.3	63.7	59.3	54.9	53.2
82.5°	51.9	56.8	61.0	64.3	62.0	57.1	50.3	45.8	43.1	40.2	39.4
85°	27.2	29.9	31.7	32.5	31.7	28.6	25.5	23.8	21.5	20.2	19.8
87.5°	12.6	12.3	12.1	12.6	11.2	10.9	9.2	7.8	7.8	7.7	7.3
90°	9.9	8.9	7.7	6.5	5.0	3.5	2.1	0.6	2.1	3.5	5.0
92.5°	12.9	12.4	11.9	11.6	11.8	11.9	12.1	12.1	12.1	11.9	11.8
95°	21.6	20.7	19.7	21.5	25.9	30.3	34.8	39.2	34.8	30.3	25.9
97.5°	27.1	25.0	22.8	27.9	40.4	52.9	65.3	77.7	65.3	52.9	40.4
100°	29.8	27.6	25.2	33.3	51.7	70.0	88.3	106.7	88.3	70.0	51.7
102.5°	73.4	92.5	111.5	123.0	126.8	130.7	134.7	138.5	134.7	130.7	126.8
105°	109.9	146.5	183.0	199.3	195.3	191.3	187.3	183.2	187.3	191.3	195.3
107.5°	139.2	183.0	226.9	247.2	243.9	240.7	237.5	234.2	237.5	240.7	243.9
110°	182.9	221.6	260.3	278.3	275.4	272.7	269.8	267.0	269.8	272.7	275.4





TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	285.2	294.7	304.3	307.8	305.3	302.9	300.4	297.9	300.4	302.9	305.3
115°	365.2	361.9	358.5	355.7	353.4	351.1	348.9	346.6	348.9	351.1	353.4
117.5°	407.3	405.0	402.7	400.3	397.7	395.2	392.6	390.1	392.6	395.2	397.7
120°	437.0	434.5	432.1	430.0	427.9	425.9	424.0	421.9	424.0	425.9	427.9
122.5°	465.0	462.4	459.8	457.4	455.3	453.1	451.1	448.9	451.1	453.1	455.3
125°	504.2	501.7	499.1	497.0	495.2	493.5	491.8	490.0	491.8	493.5	495.2
127.5°	540.7	538.8	536.9	535.0	533.0	531.2	529.2	527.3	529.2	531.2	533.0
130°	564.2	562.7	561.3	559.5	557.3	555.2	553.0	550.9	553.0	555.2	557.3
132.5°	586.9	585.4	583.9	582.3	580.5	578.7	576.9	575.1	576.9	578.7	580.5
135°	619.1	617.9	616.6	614.9	612.8	610.6	608.5	606.4	608.5	610.6	612.8
137.5°	648.2	646.9	645.5	644.0	642.6	641.1	639.6	638.1	639.6	641.1	642.6
140°	667.3	665.8	664.3	663.1	662.0	660.9	659.9	658.8	659.9	660.9	662.0
142.5°	684.8	683.0	681.3	680.0	679.1	678.1	677.1	676.1	677.1	678.1	679.1
145°	708.5	706.2	704.0	702.8	703.0	703.2	703.3	703.4	703.3	703.2	703.0
147.5°	730.5	728.2	726.0	725.1	725.7	726.2	726.7	727.1	726.7	726.2	725.7
150°	743.7	741.6	739.4	738.8	739.8	740.7	741.7	742.6	741.7	740.7	739.8
152.5°	756.0	754.0	751.9	751.4	752.4	753.5	754.6	755.6	754.6	753.5	752.4
155°	773.1	771.5	769.9	769.7	770.9	772.1	773.4	774.6	773.4	772.1	770.9
157.5°	787.6	786.4	785.3	785.3	786.3	787.3	788.3	789.4	788.3	787.3	786.3
160°	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1	797.2	796.4	795.7
162.5°	803.9	803.1	802.5	802.5	803.3	804.2	804.9	805.7	804.9	804.2	803.3
165°	813.5	813.1	812.7	812.9	813.7	814.5	815.3	816.1	815.3	814.5	813.7
167.5°	821.1	820.8	820.4	820.6	821.4	822.3	823.0	823.8	823.0	822.3	821.4
170°	825.3	824.9	824.7	824.9	825.8	826.6	827.3	828.2	827.3	826.6	825.8
172.5°	828.1	827.9	827.6	827.9	828.6	829.5	830.3	831.0	830.3	829.5	828.6
175°	831.3	831.0	830.7	831.0	832.0	832.9	833.9	834.8	833.9	832.9	832.0
177.5°	832.3	832.2	832.1	832.4	833.2	833.9	834.7	835.4	834.7	833.9	833.2
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1128.5	1126.4	1119.0	1115.2	1108.8	1102.9	1099.0	1100.8	1102.2	1101.5	1100.4
5°	1096.1	1087.8	1075.0	1064.1	1056.2	1041.6	1035.5	1032.4	1029.8	1026.7	1023.6
7.5°	1057.7	1044.5	1026.2	1010.6	995.7	977.8	967.5	961.3	955.0	948.0	941.9
10°	1030.3	1011.8	992.5	970.4	952.9	936.6	922.1	912.5	903.7	895.4	889.2
12.5°	1001.4	980.2	956.2	926.2	906.8	883.6	881.3	864.3	850.6	845.4	838.2
15°	955.5	925.7	895.4	859.7	844.3	823.2	810.0	796.9	785.0	776.6	774.5
17.5°	903.4	864.7	834.6	809.0	783.8	762.2	750.0	739.4	729.7	718.5	717.0
20°	863.7	830.3	797.3	774.9	749.0	726.9	712.0	701.5	693.1	686.6	680.8
22.5°	826.0	789.5	759.3	734.8	709.2	691.5	679.7	669.5	662.5	655.2	649.9
25°	765.7	737.1	704.1	676.4	655.3	643.9	634.2	625.4	621.0	616.2	610.1
27.5°	712.8	681.1	650.2	628.8	610.3	600.1	593.2	587.3	583.2	580.3	576.9
30°	675.5	643.4	619.3	598.2	582.8	572.7	568.3	564.8	560.0	558.2	556.5
32.5°	639.7	610.8	590.1	571.8	557.2	550.5	546.5	543.4	539.6	537.8	534.3
35°	588.9	564.8	544.6	534.4	522.6	516.9	513.8	509.4	505.9	504.1	503.7
37.5°	541.2	520.2	507.0	494.0	489.0	485.4	481.2	478.2	477.2	476.9	476.5
40°	510.3	493.2	481.3	470.7	468.6	463.2	459.8	457.1	457.1	457.5	457.1
42.5°	482.2	466.7	456.3	447.2	444.6	441.4	437.9	437.7	438.5	440.0	438.5
45°	439.5	428.5	421.0	416.6	411.8	408.7	408.3	409.7	410.1	410.5	411.8
47.5°	400.3	393.0	386.2	381.4	379.3	378.8	378.2	380.6	382.6	383.4	385.5
50°	377.1	368.8	363.1	360.0	358.2	357.3	358.2	360.8	362.6	364.8	366.1
52.5°	351.1	345.2	341.2	338.9	338.2	338.7	338.9	341.9	344.7	345.4	346.1
55°	315.1	310.7	309.9	305.9	307.6	307.2	309.4	311.2	313.8	316.4	316.9
57.5°	279.3	275.8	273.4	273.7	274.2	276.2	278.0	281.1	284.0	286.7	287.0
60°	255.4	253.6	252.3	252.3	253.1	255.8	258.0	261.1	262.9	264.6	265.9
62.5°	233.6	231.8	230.5	231.2	233.5	235.1	237.6	239.3	241.0	242.8	243.4
65°	199.1	198.2	199.6	200.4	200.9	203.0	206.1	207.4	209.2	210.1	213.2
67.5°	167.4	167.6	167.4	168.6	171.2	171.7	174.6	177.6	178.0	179.7	181.7
70°	145.9	146.8	147.7	148.5	150.8	151.6	153.9	155.2	156.9	158.3	159.5
72.5°	126.2	126.4	127.3	127.1	129.0	130.9	132.8	134.1	135.8	137.5	138.8
75°	97.1	97.1	98.0	98.4	100.7	102.9	102.4	103.3	105.0	106.8	107.7
77.5°	70.9	70.0	70.9	71.4	72.1	74.0	74.3	75.5	77.5	76.9	77.9
80°	54.1	52.8	54.1	54.5	54.5	56.7	56.7	57.6	58.9	57.6	58.9
82.5°	38.6	38.0	38.9	39.0	39.7	39.8	40.6	40.7	42.0	41.4	42.0
85°	19.4	18.9	19.4	18.9	19.4	19.8	19.8	19.4	19.4	20.2	18.9
87.5°	7.3	7.1	7.1	7.2	7.1	7.0	6.8	6.9	7.1	6.5	6.5
90°	6.5	7.7	8.9	9.9	11.0	12.1	12.7	13.4	14.0	14.7	15.2
92.5°	11.6	11.9	12.4	12.9	13.4	13.9	14.3	14.7	15.1	15.4	15.7
95°	21.5	19.7	20.7	21.6	22.6	23.5	24.2	24.9	25.5	26.2	26.4
97.5°	27.9	22.8	25.0	27.1	29.3	31.4	32.0	32.5	33.1	33.6	33.9
100°	33.3	25.2	27.6	29.8	32.1	34.4	35.4	36.5	37.5	38.7	39.3
102.5°	123.0	111.5	92.5	73.4	54.3	35.3	36.7	38.1	39.5	40.9	41.8
105°	199.3	183.0	146.5	109.9	73.4	36.8	38.2	39.7	41.2	42.6	43.7
107.5°	247.2	226.9	183.0	139.2	95.3	51.5	49.9	48.5	47.0	45.5	45.0
110°	278.3	260.3	221.6	182.9	144.2	105.5	92.1	78.7	65.3	51.9	45.5



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	307.8	304.3	294.7	285.2	275.6	266.0	217.2	168.3	119.5	70.6	46.4
115°	355.7	358.5	361.9	365.2	368.5	371.9	309.9	247.9	185.8	123.8	88.0
117.5°	400.3	402.7	405.0	407.3	409.6	411.9	396.9	381.9	366.9	351.9	328.6
120°	430.0	432.1	434.5	437.0	439.4	441.8	443.4	445.1	446.6	448.2	440.0
122.5°	457.4	459.8	462.4	465.0	467.6	470.3	471.2	472.2	473.1	474.2	472.9
125°	497.0	499.1	501.7	504.2	506.8	509.3	510.2	511.2	512.1	513.1	513.8
127.5°	535.0	536.9	538.8	540.7	542.6	544.5	545.9	547.3	548.6	550.0	550.7
130°	559.5	561.3	562.7	564.2	565.7	567.2	568.7	570.2	571.6	573.1	573.8
132.5°	582.3	583.9	585.4	586.9	588.4	589.9	591.1	592.4	593.7	594.9	595.5
135°	614.9	616.6	617.9	619.1	620.3	621.5	622.8	624.1	625.4	626.8	627.3
137.5°	644.0	645.5	646.9	648.2	649.6	651.0	652.3	653.6	654.9	656.3	656.7
140°	663.1	664.3	665.8	667.3	668.7	670.3	671.5	672.7	673.9	675.1	675.4
142.5°	680.0	681.3	683.0	684.8	686.4	688.1	689.2	690.3	691.4	692.5	692.7
145°	702.8	704.0	706.2	708.5	710.8	713.1	714.0	714.9	715.8	716.8	717.0
147.5°	725.1	726.0	728.2	730.5	732.7	734.9	735.7	736.4	737.1	737.8	737.9
150°	738.8	739.4	741.6	743.7	745.9	748.0	748.8	749.6	750.4	751.2	751.3
152.5°	751.4	751.9	754.0	756.0	758.0	760.1	760.9	761.6	762.5	763.3	763.3
155°	769.7	769.9	771.5	773.1	774.7	776.4	777.1	777.9	778.8	779.5	779.4
157.5°	785.3	785.3	786.4	787.6	788.7	789.8	790.7	791.7	792.6	793.5	793.4
160°	794.8	794.8	795.7	796.4	797.2	798.1	798.8	799.6	800.5	801.2	801.2
162.5°	802.5	802.5	803.1	803.9	804.6	805.3	806.2	807.1	808.0	808.9	808.8
165°	812.9	812.7	813.1	813.5	813.9	814.3	815.3	816.2	817.1	818.0	818.0
167.5°	820.6	820.4	820.8	821.1	821.6	821.9	822.9	823.8	824.8	825.6	825.5
170°	824.9	824.7	824.9	825.3	825.5	825.8	826.7	827.7	828.5	829.5	829.4
172.5°	827.9	827.6	827.9	828.1	828.4	828.6	829.6	830.5	831.5	832.4	832.2
175°	831.0	830.7	831.0	831.3	831.6	831.8	832.8	833.7	834.6	835.5	835.3
177.5°	832.4	832.1	832.2	832.3	832.4	832.5	833.3	834.1	834.7	835.5	835.4
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1096.9	1096.1	1096.1	1093.0	1096.1	1096.1	1096.9	1100.4	1101.5	1102.2	1100.8
5°	1017.5	1016.2	1014.0	1016.2	1014.0	1016.2	1017.5	1023.6	1026.7	1029.8	1032.4
7.5°	939.0	933.8	933.0	927.7	933.0	933.8	939.0	941.9	948.0	955.0	961.3
10°	881.7	878.1	877.7	869.4	877.7	878.1	881.7	889.2	895.4	903.7	912.5
12.5°	838.1	829.7	831.3	826.5	831.3	829.7	838.1	838.2	845.4	850.6	864.3
15°	762.6	762.6	760.8	753.4	760.8	762.6	762.6	774.5	776.6	785.0	796.9
17.5°	708.3	707.5	703.3	705.3	703.3	707.5	708.3	717.0	718.5	729.7	739.4
20°	676.0	673.4	668.0	668.0	668.0	673.4	676.0	680.8	686.6	693.1	701.5
22.5°	645.4	645.2	639.6	641.4	639.6	645.2	645.4	649.9	655.2	662.5	669.5
25°	609.6	606.1	603.5	604.8	603.5	606.1	609.6	610.1	616.2	621.0	625.4
27.5°	575.7	573.8	573.6	570.0	573.6	573.8	575.7	576.9	580.3	583.2	587.3
30°	556.0	551.6	552.5	550.3	552.5	551.6	556.0	556.5	558.2	560.0	564.8
32.5°	533.5	531.9	531.1	529.2	531.1	531.9	533.5	534.3	537.8	539.6	543.4
35°	502.8	503.3	501.1	502.0	501.1	503.3	502.8	503.7	504.1	505.9	509.4
37.5°	476.0	477.4	476.4	476.6	476.4	477.4	476.0	476.5	476.9	477.2	478.2
40°	458.4	458.4	458.4	459.8	458.4	458.4	458.4	457.1	457.5	457.1	457.1
42.5°	441.5	440.8	440.1	440.1	440.1	440.8	441.5	438.5	440.0	438.5	437.7
45°	412.7	414.1	414.5	412.2	414.5	414.1	412.7	411.8	410.5	410.1	409.7
47.5°	386.6	386.8	386.6	388.6	386.6	386.8	386.6	385.5	383.4	382.6	380.6
50°	368.3	367.5	368.3	367.5	368.3	367.5	368.3	366.1	364.8	362.6	360.8
52.5°	349.0	349.1	348.6	348.4	348.6	349.1	349.0	346.1	345.4	344.7	341.9
55°	318.7	319.5	319.1	319.1	319.1	319.5	318.7	316.9	316.4	313.8	311.2
57.5°	287.3	288.1	288.7	286.7	288.7	288.1	287.3	287.0	286.7	284.0	281.1
60°	265.4	267.7	267.3	266.4	267.3	267.7	265.4	265.9	264.6	262.9	261.1
62.5°	245.5	246.2	246.2	246.0	246.2	246.2	245.5	243.4	242.8	241.0	239.3
65°	214.5	215.3	214.0	215.3	214.0	215.3	214.5	213.2	210.1	209.2	207.4
67.5°	181.2	181.4	182.4	183.0	182.4	181.4	181.2	181.7	179.7	178.0	177.6
70°	160.4	160.0	161.3	162.6	161.3	160.0	160.4	159.5	158.3	156.9	155.2
72.5°	138.6	139.6	139.1	140.1	139.1	139.6	138.6	138.8	137.5	135.8	134.1
75°	106.8	108.1	107.7	109.0	107.7	108.1	106.8	107.7	106.8	105.0	103.3
77.5°	77.1	77.3	77.1	77.9	77.1	77.3	77.1	77.9	76.9	77.5	75.5
80°	58.9	58.0	57.2	58.9	57.2	58.0	58.9	58.9	57.6	58.9	57.6
82.5°	41.0	41.5	40.6	40.6	40.6	41.5	41.0	42.0	41.4	42.0	40.7
85°	18.9	18.4	17.6	17.6	17.6	18.4	18.9	18.9	20.2	19.4	19.4
87.5°	6.6	6.3	6.4	6.0	6.4	6.3	6.6	6.5	6.5	7.1	6.9
90°	15.5	15.8	16.0	16.3	16.0	15.8	15.5	15.2	14.7	14.0	13.4
92.5°	15.8	15.9	16.1	16.3	16.1	15.9	15.8	15.7	15.4	15.1	14.7
95°	26.3	26.2	26.1	25.9	26.1	26.2	26.3	26.4	26.2	25.5	24.9
97.5°	34.1	34.3	34.4	34.6	34.4	34.3	34.1	33.9	33.6	33.1	32.5
100°	39.6	39.9	40.1	40.4	40.1	39.9	39.6	39.3	38.7	37.5	36.5
102.5°	42.2	42.5	42.9	43.3	42.9	42.5	42.2	41.8	40.9	39.5	38.1
105°	44.2	44.8	45.3	45.8	45.3	44.8	44.2	43.7	42.6	41.2	39.7
107.5°	45.5	46.1	46.6	47.1	46.6	46.1	45.5	45.0	45.5	47.0	48.5
110°	46.0	46.6	47.1	47.6	47.1	46.6	46.0	45.5	51.9	65.3	78.7



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	46.8	47.3	47.7	48.1	47.7	47.3	46.8	46.4	70.6	119.5	168.3
115°	78.4	68.7	59.1	49.4	59.1	68.7	78.4	88.0	123.8	185.8	247.9
117.5°	296.9	265.2	233.5	201.8	233.5	265.2	296.9	328.6	351.9	366.9	381.9
120°	421.9	403.8	385.7	367.6	385.7	403.8	421.9	440.0	448.2	446.6	445.1
122.5°	469.3	465.8	462.4	458.8	462.4	465.8	469.3	472.9	474.2	473.1	472.2
125°	514.1	514.5	515.0	515.3	515.0	514.5	514.1	513.8	513.1	512.1	511.2
127.5°	550.8	550.9	551.0	551.0	551.0	550.9	550.8	550.7	550.0	548.6	547.3
130°	573.6	573.5	573.3	573.3	573.3	573.5	573.6	573.8	573.1	571.6	570.2
132.5°	595.3	595.2	595.0	595.0	595.0	595.2	595.3	595.5	594.9	593.7	592.4
135°	627.1	626.8	626.5	626.3	626.5	626.8	627.1	627.3	626.8	625.4	624.1
137.5°	656.2	655.7	655.3	654.8	655.3	655.7	656.2	656.7	656.3	654.9	653.6
140°	674.7	674.0	673.3	672.7	673.3	674.0	674.7	675.4	675.1	673.9	672.7
142.5°	692.1	691.4	690.7	690.0	690.7	691.4	692.1	692.7	692.5	691.4	690.3
145°	716.3	715.6	714.9	714.3	714.9	715.6	716.3	717.0	716.8	715.8	714.9
147.5°	737.3	736.8	736.2	735.6	736.2	736.8	737.3	737.9	737.8	737.1	736.4
150°	750.6	749.9	749.2	748.6	749.2	749.9	750.6	751.3	751.2	750.4	749.6
152.5°	762.3	761.5	760.6	759.7	760.6	761.5	762.3	763.3	763.3	762.5	761.6
155°	778.3	777.3	776.2	775.2	776.2	777.3	778.3	779.4	779.5	778.8	777.9
157.5°	792.4	791.3	790.3	789.2	790.3	791.3	792.4	793.4	793.5	792.6	791.7
160°	800.2	799.3	798.4	797.5	798.4	799.3	800.2	801.2	801.2	800.5	799.6
162.5°	807.6	806.5	805.3	804.2	805.3	806.5	807.6	808.8	808.9	808.0	807.1
165°	817.1	816.2	815.3	814.3	815.3	816.2	817.1	818.0	818.0	817.1	816.2
167.5°	824.3	823.1	821.9	820.7	821.9	823.1	824.3	825.5	825.6	824.8	823.8
170°	828.2	827.0	825.8	824.6	825.8	827.0	828.2	829.4	829.5	828.5	827.7
172.5°	831.0	829.8	828.6	827.4	828.6	829.8	831.0	832.2	832.4	831.5	830.5
175°	834.0	832.7	831.3	830.0	831.3	832.7	834.0	835.3	835.5	834.6	833.7
177.5°	834.5	833.4	832.5	831.6	832.5	833.4	834.5	835.4	835.5	834.7	834.1
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1099.0	1102.9	1108.8	1115.2	1119.0	1126.4	1128.5	1132.0	1135.2	1142.6	1150.3
5°	1035.5	1041.6	1056.2	1064.1	1075.0	1087.8	1096.1	1105.0	1114.7	1131.4	1146.7
7.5°	967.5	977.8	995.7	1010.6	1026.2	1044.5	1057.7	1075.0	1089.5	1113.0	1135.6
10°	922.1	936.6	952.9	970.4	992.5	1011.8	1030.3	1052.2	1069.8	1097.9	1124.3
12.5°	881.3	883.6	906.8	926.2	956.2	980.2	1001.4	1029.8	1047.0	1080.4	1108.1
15°	810.0	823.2	844.3	859.7	895.4	925.7	955.5	985.0	1004.8	1046.0	1082.5
17.5°	750.0	762.2	783.8	809.0	834.6	864.7	903.4	934.4	961.3	1008.6	1051.7
20°	712.0	726.9	749.0	774.9	797.3	830.3	863.7	899.2	928.2	981.5	1032.0
22.5°	679.7	691.5	709.2	734.8	759.3	789.5	826.0	864.8	895.3	952.6	1003.8
25°	634.2	643.9	655.3	676.4	704.1	737.1	765.7	808.3	852.6	906.3	968.3
27.5°	593.2	600.1	610.3	628.8	650.2	681.1	712.8	753.3	797.9	856.1	921.5
30°	568.3	572.7	582.8	598.2	619.3	643.4	675.5	714.2	759.9	818.8	883.9
32.5°	546.5	550.5	557.2	571.8	590.1	610.8	639.7	678.4	721.9	779.8	851.9
35°	513.8	516.9	522.6	534.4	544.6	564.8	588.9	624.1	665.0	720.4	795.1
37.5°	481.2	485.4	489.0	494.0	507.0	520.2	541.2	570.9	611.1	666.9	738.1
40°	459.8	463.2	468.6	470.7	481.3	493.2	510.3	537.5	578.0	629.0	698.4
42.5°	437.9	441.4	444.6	447.2	456.3	466.7	482.2	505.6	541.4	591.0	659.7
45°	408.3	408.7	411.8	416.6	421.0	428.5	439.5	459.8	487.4	534.0	596.4
47.5°	378.2	378.8	379.3	381.4	386.2	393.0	400.3	416.7	441.5	478.7	539.5
50°	358.2	357.3	358.2	360.0	363.1	368.8	377.1	389.0	409.2	443.9	499.7
52.5°	338.9	338.7	338.2	338.9	341.2	345.2	351.1	361.2	379.3	411.2	460.4
55°	309.4	307.2	307.6	305.9	309.9	310.7	315.1	323.5	339.3	361.3	407.4
57.5°	278.0	276.2	274.2	273.7	273.4	275.8	279.3	285.9	298.0	317.3	354.7
60°	258.0	255.8	253.1	252.3	252.3	253.6	255.4	260.2	271.6	288.8	319.5
62.5°	237.6	235.1	233.5	231.2	230.5	231.8	233.6	237.0	245.2	261.3	287.9
65°	206.1	203.0	200.9	200.4	199.6	198.2	199.1	202.6	209.2	222.0	243.1
67.5°	174.6	171.7	171.2	168.6	167.4	167.6	167.4	170.4	174.4	185.3	201.0
70°	153.9	151.6	150.8	148.5	147.7	146.8	145.9	148.5	152.5	161.8	175.4
72.5°	132.8	130.9	129.0	127.1	127.3	126.4	126.2	127.8	131.0	139.6	150.1
75°	102.4	102.9	100.7	98.4	98.0	97.1	97.1	98.4	99.8	106.3	114.7
77.5°	74.3	74.0	72.1	71.4	70.9	70.0	70.9	71.8	72.5	76.9	83.1
80°	56.7	56.7	54.5	54.5	54.1	52.8	54.1	53.2	54.9	59.3	63.7
82.5°	40.6	39.8	39.7	39.0	38.9	38.0	38.6	39.4	40.2	43.1	45.8
85°	19.8	19.8	19.4	18.9	19.4	18.9	19.4	19.8	20.2	21.5	23.8
87.5°	6.8	7.0	7.1	7.2	7.1	7.1	7.3	7.3	7.7	7.8	7.8
90°	12.7	12.1	11.0	9.9	8.9	7.7	6.5	5.0	3.5	2.1	0.6
92.5°	14.3	13.9	13.4	12.9	12.4	11.9	11.6	11.8	11.9	12.1	12.1
95°	24.2	23.5	22.6	21.6	20.7	19.7	21.5	25.9	30.3	34.8	39.2
97.5°	32.0	31.4	29.3	27.1	25.0	22.8	27.9	40.4	52.9	65.3	77.7
100°	35.4	34.4	32.1	29.8	27.6	25.2	33.3	51.7	70.0	88.3	106.7
102.5°	36.7	35.3	54.3	73.4	92.5	111.5	123.0	126.8	130.7	134.7	138.5
105°	38.2	36.8	73.4	109.9	146.5	183.0	199.3	195.3	191.3	187.3	183.2
107.5°	49.9	51.5	95.3	139.2	183.0	226.9	247.2	243.9	240.7	237.5	234.2
110°	92.1	105.5	144.2	182.9	221.6	260.3	278.3	275.4	272.7	269.8	267.0



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	217.2	266.0	275.6	285.2	294.7	304.3	307.8	305.3	302.9	300.4	297.9
115°	309.9	371.9	368.5	365.2	361.9	358.5	355.7	353.4	351.1	348.9	346.6
117.5°	396.9	411.9	409.6	407.3	405.0	402.7	400.3	397.7	395.2	392.6	390.1
120°	443.4	441.8	439.4	437.0	434.5	432.1	430.0	427.9	425.9	424.0	421.9
122.5°	471.2	470.3	467.6	465.0	462.4	459.8	457.4	455.3	453.1	451.1	448.9
125°	510.2	509.3	506.8	504.2	501.7	499.1	497.0	495.2	493.5	491.8	490.0
127.5°	545.9	544.5	542.6	540.7	538.8	536.9	535.0	533.0	531.2	529.2	527.3
130°	568.7	567.2	565.7	564.2	562.7	561.3	559.5	557.3	555.2	553.0	550.9
132.5°	591.1	589.9	588.4	586.9	585.4	583.9	582.3	580.5	578.7	576.9	575.1
135°	622.8	621.5	620.3	619.1	617.9	616.6	614.9	612.8	610.6	608.5	606.4
137.5°	652.3	651.0	649.6	648.2	646.9	645.5	644.0	642.6	641.1	639.6	638.1
140°	671.5	670.3	668.7	667.3	665.8	664.3	663.1	662.0	660.9	659.9	658.8
142.5°	689.2	688.1	686.4	684.8	683.0	681.3	680.0	679.1	678.1	677.1	676.1
145°	714.0	713.1	710.8	708.5	706.2	704.0	702.8	703.0	703.2	703.3	703.4
147.5°	735.7	734.9	732.7	730.5	728.2	726.0	725.1	725.7	726.2	726.7	727.1
150°	748.8	748.0	745.9	743.7	741.6	739.4	738.8	739.8	740.7	741.7	742.6
152.5°	760.9	760.1	758.0	756.0	754.0	751.9	751.4	752.4	753.5	754.6	755.6
155°	777.1	776.4	774.7	773.1	771.5	769.9	769.7	770.9	772.1	773.4	774.6
157.5°	790.7	789.8	788.7	787.6	786.4	785.3	785.3	786.3	787.3	788.3	789.4
160°	798.8	798.1	797.2	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1
162.5°	806.2	805.3	804.6	803.9	803.1	802.5	802.5	803.3	804.2	804.9	805.7
165°	815.3	814.3	813.9	813.5	813.1	812.7	812.9	813.7	814.5	815.3	816.1
167.5°	822.9	821.9	821.6	821.1	820.8	820.4	820.6	821.4	822.3	823.0	823.8
170°	826.7	825.8	825.5	825.3	824.9	824.7	824.9	825.8	826.6	827.3	828.2
172.5°	829.6	828.6	828.4	828.1	827.9	827.6	827.9	828.6	829.5	830.3	831.0
175°	832.8	831.8	831.6	831.3	831.0	830.7	831.0	832.0	832.9	833.9	834.8
177.5°	833.3	832.5	832.4	832.3	832.2	832.1	832.4	833.2	833.9	834.7	835.4
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1149.6	1151.4	1157.0	1162.6	1169.0	1170.7	1173.5	1171.0	1170.4	1177.1	1182.0
5°	1152.9	1160.8	1176.2	1190.2	1202.1	1210.5	1219.3	1222.8	1229.3	1238.5	1250.0
7.5°	1149.2	1164.6	1188.8	1209.2	1231.6	1247.7	1260.2	1270.9	1283.9	1301.4	1320.5
10°	1145.0	1165.6	1195.1	1220.1	1247.3	1268.0	1285.2	1301.8	1321.2	1345.4	1370.5
12.5°	1137.2	1161.7	1198.6	1228.2	1263.2	1283.5	1306.7	1342.6	1363.4	1397.1	1432.4
15°	1121.7	1148.9	1200.3	1236.8	1276.3	1315.1	1357.7	1392.0	1426.2	1446.0	1495.7
17.5°	1098.5	1138.6	1195.5	1238.0	1288.3	1349.3	1397.1	1436.0	1475.6	1507.7	1532.6
20°	1080.0	1123.4	1188.4	1239.5	1299.2	1364.7	1419.7	1459.2	1493.5	1520.4	1535.7
22.5°	1056.4	1111.1	1174.4	1234.2	1310.5	1375.3	1433.0	1464.1	1492.8	1505.9	1511.8
25°	1019.3	1085.2	1156.8	1229.8	1316.0	1384.5	1437.3	1456.1	1464.5	1451.7	1430.6
27.5°	979.3	1052.7	1136.5	1221.5	1312.6	1378.5	1416.3	1413.3	1399.2	1358.0	1325.0
30°	949.3	1030.3	1120.3	1213.1	1304.5	1368.6	1390.7	1368.6	1336.6	1290.5	1243.5
32.5°	918.1	1001.8	1103.1	1201.1	1289.8	1346.2	1350.9	1313.1	1263.4	1211.0	1152.4
35°	870.7	961.2	1070.7	1174.4	1258.4	1294.0	1272.9	1206.1	1147.2	1075.6	995.5
37.5°	817.2	917.1	1026.9	1135.3	1211.3	1220.6	1168.3	1097.9	1014.9	930.7	836.5
40°	777.1	883.0	996.0	1105.4	1172.7	1163.0	1096.1	1018.8	919.9	817.1	729.6
42.5°	741.2	847.1	962.2	1069.5	1123.4	1096.9	1018.8	923.9	817.6	720.7	640.7
45°	679.1	788.1	905.9	1009.6	1040.3	992.5	889.2	783.7	679.1	598.2	534.9
47.5°	618.8	726.5	843.2	934.4	945.2	880.8	767.9	659.4	569.5	503.6	458.9
50°	574.5	682.6	798.1	879.5	876.0	798.1	682.2	578.9	503.7	450.5	420.6
52.5°	534.8	636.9	747.9	821.8	803.2	718.3	607.6	515.9	454.1	412.5	385.5
55°	472.9	567.4	672.9	732.3	697.9	603.9	510.3	436.4	390.7	359.6	338.5
57.5°	411.6	500.2	590.5	627.1	589.2	502.3	424.2	370.7	336.3	313.2	299.5
60°	373.6	451.0	531.4	563.0	517.7	440.4	378.8	331.0	303.2	284.4	272.1
62.5°	335.6	404.9	480.8	498.0	456.6	391.2	336.7	296.9	274.1	257.3	245.7
65°	284.0	340.6	398.2	409.7	371.4	320.9	277.8	251.8	231.6	219.3	210.1
67.5°	232.9	278.4	319.2	328.4	294.9	259.8	228.8	206.1	192.4	182.2	174.4
70°	202.6	238.7	272.1	279.6	252.7	221.5	197.8	179.8	167.5	158.7	151.2
72.5°	170.7	200.7	228.4	233.5	211.5	187.8	168.2	154.1	143.2	137.6	130.4
75°	130.5	148.1	169.6	171.0	156.4	142.0	127.0	117.8	112.1	105.0	101.5
77.5°	92.1	105.9	118.2	120.6	112.0	102.1	93.8	86.5	81.6	78.4	75.2
80°	70.3	81.3	86.6	89.6	83.5	76.5	71.6	66.8	63.7	61.6	59.3
82.5°	50.3	57.1	62.0	64.3	61.0	56.8	51.9	49.2	46.8	45.0	44.3
85°	25.5	28.6	31.7	32.5	31.7	29.9	27.2	27.2	25.9	25.5	25.5
87.5°	9.2	10.9	11.2	12.6	12.1	12.3	12.6	12.4	12.2	12.1	11.8
90°	2.1	3.5	5.0	6.5	7.7	8.9	9.9	11.0	12.1	12.7	13.4
92.5°	12.1	11.9	11.8	11.6	11.9	12.4	12.9	13.4	13.9	14.3	14.7
95°	34.8	30.3	25.9	21.5	19.7	20.7	21.6	22.6	23.5	24.2	24.9
97.5°	65.3	52.9	40.4	27.9	22.8	25.0	27.1	29.3	31.4	32.0	32.5
100°	88.3	70.0	51.7	33.3	25.2	27.6	29.8	32.1	34.4	35.4	36.5
102.5°	134.7	130.7	126.8	123.0	111.5	92.5	73.4	54.3	35.3	36.7	38.1
105°	187.3	191.3	195.3	199.3	183.0	146.5	109.9	73.4	36.8	38.2	39.7
107.5°	237.5	240.7	243.9	247.2	226.9	183.0	139.2	95.3	51.5	49.9	48.5
110°	269.8	272.7	275.4	278.3	260.3	221.6	182.9	144.2	105.5	92.1	78.7





TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	300.4	302.9	305.3	307.8	304.3	294.7	285.2	275.6	266.0	217.2	168.3
115°	348.9	351.1	353.4	355.7	358.5	361.9	365.2	368.5	371.9	309.9	247.9
117.5°	392.6	395.2	397.7	400.3	402.7	405.0	407.3	409.6	411.9	396.9	381.9
120°	424.0	425.9	427.9	430.0	432.1	434.5	437.0	439.4	441.8	443.4	445.1
122.5°	451.1	453.1	455.3	457.4	459.8	462.4	465.0	467.6	470.3	471.2	472.2
125°	491.8	493.5	495.2	497.0	499.1	501.7	504.2	506.8	509.3	510.2	511.2
127.5°	529.2	531.2	533.0	535.0	536.9	538.8	540.7	542.6	544.5	545.9	547.3
130°	553.0	555.2	557.3	559.5	561.3	562.7	564.2	565.7	567.2	568.7	570.2
132.5°	576.9	578.7	580.5	582.3	583.9	585.4	586.9	588.4	589.9	591.1	592.4
135°	608.5	610.6	612.8	614.9	616.6	617.9	619.1	620.3	621.5	622.8	624.1
137.5°	639.6	641.1	642.6	644.0	645.5	646.9	648.2	649.6	651.0	652.3	653.6
140°	659.9	660.9	662.0	663.1	664.3	665.8	667.3	668.7	670.3	671.5	672.7
142.5°	677.1	678.1	679.1	680.0	681.3	683.0	684.8	686.4	688.1	689.2	690.3
145°	703.3	703.2	703.0	702.8	704.0	706.2	708.5	710.8	713.1	714.0	714.9
147.5°	726.7	726.2	725.7	725.1	726.0	728.2	730.5	732.7	734.9	735.7	736.4
150°	741.7	740.7	739.8	738.8	739.4	741.6	743.7	745.9	748.0	748.8	749.6
152.5°	754.6	753.5	752.4	751.4	751.9	754.0	756.0	758.0	760.1	760.9	761.6
155°	773.4	772.1	770.9	769.7	769.9	771.5	773.1	774.7	776.4	777.1	777.9
157.5°	788.3	787.3	786.3	785.3	785.3	786.4	787.6	788.7	789.8	790.7	791.7
160°	797.2	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1	798.8	799.6
162.5°	804.9	804.2	803.3	802.5	802.5	803.1	803.9	804.6	805.3	806.2	807.1
165°	815.3	814.5	813.7	812.9	812.7	813.1	813.5	813.9	814.3	815.3	816.2
167.5°	823.0	822.3	821.4	820.6	820.4	820.8	821.1	821.6	821.9	822.9	823.8
170°	827.3	826.6	825.8	824.9	824.7	824.9	825.3	825.5	825.8	826.7	827.7
172.5°	830.3	829.5	828.6	827.9	827.6	827.9	828.1	828.4	828.6	829.6	830.5
175°	833.9	832.9	832.0	831.0	830.7	831.0	831.3	831.6	831.8	832.8	833.7
177.5°	834.7	833.9	833.2	832.4	832.1	832.2	832.3	832.4	832.5	833.3	834.1
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1186.2	1191.1	1191.1	1191.8	1197.5	1196.7	1196.4
5°	1262.3	1269.8	1270.7	1278.6	1283.8	1282.1	1277.3
7.5°	1334.1	1348.1	1358.6	1364.4	1371.4	1375.7	1373.8
10°	1391.1	1411.4	1423.7	1432.0	1442.1	1449.6	1446.9
12.5°	1442.8	1466.9	1483.8	1498.1	1499.4	1509.0	1502.4
15°	1523.4	1548.9	1551.5	1562.1	1570.5	1569.5	1569.9
17.5°	1550.1	1558.2	1559.9	1560.1	1560.2	1557.1	1550.5
20°	1540.5	1537.5	1530.0	1524.3	1514.2	1512.9	1504.1
22.5°	1495.6	1485.7	1467.1	1454.7	1438.9	1434.8	1432.4
25°	1407.0	1385.3	1355.5	1326.9	1319.1	1303.6	1308.0
27.5°	1285.4	1251.8	1219.4	1196.2	1175.2	1152.2	1158.7
30°	1199.9	1162.1	1116.4	1081.2	1058.9	1036.8	1032.9
32.5°	1097.9	1042.6	991.5	960.6	926.3	912.4	897.2
35°	922.1	868.1	817.5	774.0	749.0	729.6	712.0
37.5°	764.0	701.7	661.0	625.7	607.6	596.5	599.3
40°	665.9	611.4	581.5	554.7	538.0	530.0	531.8
42.5°	586.4	545.6	521.0	502.7	490.9	486.5	485.4
45°	496.2	473.4	453.1	442.6	436.9	432.0	429.0
47.5°	434.7	416.0	404.7	398.4	393.4	388.5	388.4
50°	397.8	385.5	377.5	370.9	367.0	363.5	366.5
52.5°	369.6	358.3	350.5	344.6	343.1	339.9	339.8
55°	327.9	319.1	313.4	308.1	305.5	303.7	301.5
57.5°	289.9	281.5	276.3	272.9	267.9	266.1	265.4
60°	262.9	256.2	251.0	246.6	244.4	240.8	240.8
62.5°	237.9	231.3	226.4	223.0	219.4	218.0	218.3
65°	201.7	196.5	191.7	188.1	187.3	184.6	185.5
67.5°	168.5	165.0	159.9	158.0	156.3	154.9	153.9
70°	146.4	142.8	140.2	137.6	136.2	136.2	136.2
72.5°	127.7	123.5	121.9	118.6	119.3	118.0	116.6
75°	98.9	96.3	95.0	93.6	91.4	91.4	91.4
77.5°	72.8	72.0	70.4	69.0	68.4	68.0	68.2
80°	56.2	55.8	54.9	54.9	54.1	53.6	52.8
82.5°	43.2	42.1	41.6	41.2	41.1	41.0	40.8
85°	24.6	23.8	23.8	24.2	23.3	23.3	23.8
87.5°	12.3	12.4	12.1	12.2	12.7	12.3	12.4
90°	14.0	14.7	15.2	15.5	15.8	16.0	16.3
92.5°	15.1	15.4	15.7	15.8	15.9	16.1	16.3
95°	25.5	26.2	26.4	26.3	26.2	26.1	25.9
97.5°	33.1	33.6	33.9	34.1	34.3	34.4	34.6
100°	37.5	38.7	39.3	39.6	39.9	40.1	40.4
102.5°	39.5	40.9	41.8	42.2	42.5	42.9	43.3
105°	41.2	42.6	43.7	44.2	44.8	45.3	45.8
107.5°	47.0	45.5	45.0	45.5	46.1	46.6	47.1
110°	65.3	51.9	45.5	46.0	46.6	47.1	47.6



TEST NUMBER: P331531-935

CATALOG NUMBER: S122DIW-S675D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	119.5	70.6	46.4	46.8	47.3	47.7	48.1
115°	185.8	123.8	88.0	78.4	68.7	59.1	49.4
117.5°	366.9	351.9	328.6	296.9	265.2	233.5	201.8
120°	446.6	448.2	440.0	421.9	403.8	385.7	367.6
122.5°	473.1	474.2	472.9	469.3	465.8	462.4	458.8
125°	512.1	513.1	513.8	514.1	514.5	515.0	515.3
127.5°	548.6	550.0	550.7	550.8	550.9	551.0	551.0
130°	571.6	573.1	573.8	573.6	573.5	573.3	573.3
132.5°	593.7	594.9	595.5	595.3	595.2	595.0	595.0
135°	625.4	626.8	627.3	627.1	626.8	626.5	626.3
137.5°	654.9	656.3	656.7	656.2	655.7	655.3	654.8
140°	673.9	675.1	675.4	674.7	674.0	673.3	672.7
142.5°	691.4	692.5	692.7	692.1	691.4	690.7	690.0
145°	715.8	716.8	717.0	716.3	715.6	714.9	714.3
147.5°	737.1	737.8	737.9	737.3	736.8	736.2	735.6
150°	750.4	751.2	751.3	750.6	749.9	749.2	748.6
152.5°	762.5	763.3	763.3	762.3	761.5	760.6	759.7
155°	778.8	779.5	779.4	778.3	777.3	776.2	775.2
157.5°	792.6	793.5	793.4	792.4	791.3	790.3	789.2
160°	800.5	801.2	801.2	800.2	799.3	798.4	797.5
162.5°	808.0	808.9	808.8	807.6	806.5	805.3	804.2
165°	817.1	818.0	818.0	817.1	816.2	815.3	814.3
167.5°	824.8	825.6	825.5	824.3	823.1	821.9	820.7
170°	828.5	829.5	829.4	828.2	827.0	825.8	824.6
172.5°	831.5	832.4	832.2	831.0	829.8	828.6	827.4
175°	834.6	835.5	835.3	834.0	832.7	831.3	830.0
177.5°	834.7	835.5	835.4	834.5	833.4	832.5	831.6
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0

(END OF REPORT)