

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331801-940

Luminaire Tested: **S122RDIW-S485D1440U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331801-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S485D1440U940-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6796.9 lumens  
Efficiency: N/A  
Efficacy: 112.2 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24
1	92	88	85	82	82	79	76	73	61	59	57	44	43	42	29	29	28	21
2	84	78	72	67	75	69	65	61	54	51	48	40	38	36	26	25	24	18
3	77	68	62	56	69	61	56	51	48	44	41	35	33	31	24	22	21	16
4	71	61	53	48	63	55	48	44	43	38	35	32	29	27	21	20	19	14
5	65	54	47	41	58	49	42	37	38	34	30	29	26	23	19	18	16	13
6	60	49	41	36	53	44	37	33	35	30	27	26	23	21	18	16	15	11
7	55	44	37	31	49	40	33	29	31	27	23	24	21	18	16	15	13	10
8	51	40	33	28	46	36	30	25	29	24	21	22	19	16	15	13	12	9
9	48	36	29	25	43	33	27	23	26	22	19	20	17	15	14	12	11	9
10	45	33	27	22	40	30	24	20	24	20	17	18	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15474	15474	15474	15474
5°	17280	15571	13807	15571
10°	19174	15462	11968	15462
15°	20117	15234	9429	15234
20°	17438	14899	8158	14899
25°	11437	14439	7285	14439
30°	7700	13882	6594	13882
35°	6236	13180	5947	13180
40°	5545	12416	5503	12416
45°	5019	11520	4912	11520
50°	4567	10630	4549	10630
55°	4293	9647	4236	9647
60°	3591	8741	3549	8741
65°	3030	7939	3435	7939
70°	2799	7091	3238	7091
75°	2620	6170	2994	6170
80°	2408	5077	2659	5077
85°	2205	4020	2353	4020



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.8	1.3
10°-20°	253.1	3.7
20°-30°	326.2	4.8
30°-40°	310.0	4.6
40°-50°	265.6	3.9
50°-60°	202.2	3.0
60°-70°	127.8	1.9
70°-80°	63.8	0.9
80°-90°	20.9	0.3
90°-100°	58.5	0.9
100°-110°	214.4	3.2
110°-120°	573.1	8.4
120°-130°	946.0	13.9
130°-140°	1006.1	14.8
140°-150°	935.1	13.8
150°-160°	751.8	11.1
160°-170°	484.5	7.1
170°-180°	166.8	2.5
0°-30°	670.2	9.9
0°-40°	980.2	14.4
0°-60°	1448.0	21.3
0°-90°	1660.6	24.4
90°-120°	846.0	12.4
90°-150°	3733.2	54.9
90°-180°	5136.0	75.6
0°-180°	6796.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	958	958	958	958	958	
5°	1066	961	852	961	1066	105
15°	1204	911	564	911	1204	325
25°	642	810	409	810	642	305
35°	316	669	302	669	316	202
45°	220	504	215	504	220	170
55°	152	343	150	343	152	134
65°	79	208	90	208	79	81
75°	42	99	48	99	42	45
85°	12	22	13	22	12	14
90°	34	1	34	1	34	16
95°	55	82	55	82	55	51
105°	96	386	96	386	96	100
115°	104	729	104	729	104	260
125°	1084	1031	1084	1031	1084	938
135°	1318	1276	1318	1276	1318	1016
145°	1503	1480	1503	1480	1503	940
155°	1631	1630	1631	1630	1631	753
165°	1713	1717	1713	1717	1713	484
175°	1746	1756	1746	1756	1746	166
180°	1753	1753	1753	1753	1753	



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	997.3	998.1	998.9	997.0	997.0	995.4	991.9	989.3	981.8	980.7	980.7
5°	1066.2	1065.6	1066.9	1062.6	1056.6	1055.3	1048.9	1040.6	1032.0	1022.3	1020.3
7.5°	1134.9	1133.9	1131.2	1130.4	1125.9	1115.8	1105.6	1094.8	1080.4	1066.3	1059.3
10°	1169.5	1180.4	1173.8	1162.2	1164.5	1148.9	1140.5	1126.2	1114.2	1093.2	1088.6
12.5°	1203.5	1207.9	1205.8	1199.2	1196.2	1185.4	1174.1	1161.6	1139.5	1120.7	1104.3
15°	1203.5	1209.8	1211.5	1209.4	1211.1	1210.4	1204.4	1194.1	1174.8	1154.1	1136.2
17.5°	1114.6	1119.0	1129.9	1137.3	1146.7	1166.4	1176.1	1179.9	1177.0	1165.2	1152.5
20°	1014.9	1007.6	1038.3	1053.9	1067.3	1100.5	1129.2	1140.1	1157.8	1157.5	1154.1
22.5°	873.8	875.5	904.6	923.1	962.1	995.3	1028.0	1069.3	1103.5	1126.1	1139.2
25°	642.0	654.7	683.7	708.9	752.2	814.2	870.5	935.8	997.3	1046.0	1092.3
27.5°	482.1	483.1	506.0	529.5	555.2	605.9	676.8	754.7	842.6	915.0	998.4
30°	413.0	410.9	420.6	434.9	456.9	496.1	549.5	626.1	713.6	822.9	920.1
32.5°	363.9	364.0	371.3	381.9	400.1	426.6	463.2	525.3	608.1	715.5	829.5
35°	316.4	316.0	321.4	329.0	336.6	353.7	378.6	411.3	468.2	568.5	685.0
37.5°	282.2	283.7	286.3	291.1	299.5	309.0	324.0	345.9	386.5	445.8	543.7
40°	263.1	263.8	267.4	271.4	276.4	283.7	296.0	313.7	343.3	390.6	462.2
42.5°	245.5	246.1	248.8	252.4	256.4	263.8	273.9	289.2	313.3	350.1	409.2
45°	219.8	219.8	222.1	223.7	228.1	234.8	243.1	255.7	272.4	299.7	339.0
47.5°	195.6	195.7	197.2	200.1	202.9	208.0	216.2	226.6	238.7	259.8	293.4
50°	181.8	182.2	183.2	185.5	187.2	191.8	198.1	207.1	219.8	236.1	264.0
52.5°	170.6	170.4	171.7	172.7	173.8	177.2	181.9	189.8	201.2	215.3	238.5
55°	152.5	151.1	153.2	154.8	155.9	157.2	159.8	164.9	174.5	186.5	203.8
57.5°	129.8	129.3	130.7	132.2	135.4	139.0	141.2	144.5	149.5	158.0	175.2
60°	111.2	111.2	114.2	115.2	118.9	123.5	128.2	130.9	135.9	141.5	154.2
62.5°	94.7	95.0	96.4	97.4	99.4	105.1	111.7	117.5	122.3	127.7	136.1
65°	79.3	79.9	79.9	80.6	81.9	83.3	85.9	90.6	98.9	106.6	112.9
67.5°	67.2	67.5	67.7	68.3	68.7	70.1	71.2	73.3	75.2	82.5	90.3
70°	59.3	60.3	59.9	60.6	60.9	61.6	63.0	63.9	67.0	68.6	73.3
72.5°	51.8	52.5	52.5	52.9	53.8	53.9	54.9	55.9	57.9	59.3	61.8
75°	42.0	41.6	42.0	42.6	43.0	43.2	43.2	44.6	45.7	47.0	48.6
77.5°	32.4	32.7	32.6	32.7	32.7	33.3	33.3	33.9	34.9	35.6	36.4
80°	25.9	26.3	25.9	26.3	26.7	26.9	26.7	26.9	28.0	28.6	28.6
82.5°	20.2	20.2	20.4	20.4	20.5	20.6	21.0	21.1	21.8	21.7	21.9
85°	11.9	11.7	11.7	11.7	11.9	12.3	11.9	11.9	12.3	12.3	12.3
87.5°	11.1	11.2	11.1	11.1	11.0	10.7	10.4	10.4	9.9	9.9	9.2
90°	34.2	33.7	33.1	32.5	32.0	31.0	29.6	28.2	26.8	25.3	23.1
92.5°	34.2	33.9	33.5	33.3	32.9	32.4	31.7	30.9	30.1	29.4	28.3
95°	54.6	54.8	55.1	55.4	55.6	55.1	53.7	52.3	50.8	49.5	47.5
97.5°	72.8	72.5	72.1	71.8	71.4	70.7	69.6	68.5	67.3	66.2	61.6
100°	85.0	84.4	83.8	83.3	82.8	81.3	79.1	76.8	74.5	72.3	67.5
102.5°	91.0	90.2	89.4	88.7	87.9	86.1	83.1	80.2	77.2	74.3	114.4
105°	96.4	95.2	94.2	93.0	91.8	89.8	86.7	83.6	80.4	77.4	154.3
107.5°	99.2	98.1	96.9	95.8	94.7	95.7	98.8	102.0	105.1	108.3	200.5
110°	100.2	99.1	97.9	96.8	95.7	109.2	137.4	165.6	193.8	221.9	303.4



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	101.2	100.3	99.4	98.5	97.6	148.6	251.4	354.2	457.0	559.8	579.9
115°	104.0	124.3	144.5	164.9	185.1	260.6	391.0	521.6	652.0	782.5	775.4
117.5°	424.6	491.2	557.9	624.6	691.3	740.5	772.0	803.6	835.2	866.7	861.8
120°	773.6	811.6	849.7	887.8	925.8	943.2	939.8	936.4	933.0	929.6	924.5
122.5°	965.4	972.8	980.2	987.5	994.9	997.6	995.6	993.5	991.5	989.4	983.9
125°	1084.3	1083.5	1082.6	1081.8	1080.9	1079.5	1077.5	1075.6	1073.6	1071.7	1066.3
127.5°	1159.4	1159.2	1159.0	1158.9	1158.8	1157.2	1154.3	1151.5	1148.6	1145.8	1141.7
130°	1206.0	1206.4	1206.7	1206.9	1207.2	1205.8	1202.7	1199.6	1196.5	1193.4	1190.3
132.5°	1251.7	1252.1	1252.3	1252.6	1252.9	1251.7	1249.0	1246.3	1243.8	1241.1	1238.0
135°	1317.7	1318.2	1318.8	1319.4	1319.9	1318.8	1316.0	1313.1	1310.4	1307.5	1305.0
137.5°	1377.8	1378.8	1379.7	1380.6	1381.6	1380.7	1378.0	1375.2	1372.4	1369.7	1366.8
140°	1415.3	1416.8	1418.2	1419.6	1420.9	1420.4	1417.9	1415.3	1412.8	1410.2	1407.2
142.5°	1451.9	1453.3	1454.6	1456.1	1457.5	1457.1	1454.7	1452.4	1450.1	1447.8	1444.2
145°	1502.9	1504.2	1505.7	1507.1	1508.5	1508.2	1506.2	1504.2	1502.3	1500.3	1495.5
147.5°	1547.7	1548.9	1550.2	1551.3	1552.5	1552.4	1550.9	1549.4	1547.9	1546.5	1541.8
150°	1575.1	1576.5	1578.0	1579.4	1580.7	1580.6	1579.0	1577.3	1575.6	1573.9	1569.3
152.5°	1598.5	1600.4	1602.2	1604.0	1605.9	1606.0	1604.3	1602.6	1600.9	1599.2	1594.9
155°	1630.9	1633.2	1635.5	1637.7	1639.9	1640.2	1638.5	1636.8	1635.1	1633.4	1630.1
157.5°	1660.6	1662.8	1665.0	1667.2	1669.4	1669.6	1667.6	1665.7	1663.8	1661.9	1659.5
160°	1677.8	1679.8	1681.8	1683.8	1685.8	1685.9	1684.2	1682.5	1680.8	1679.1	1677.4
162.5°	1692.1	1694.5	1696.9	1699.3	1701.7	1702.0	1700.1	1698.2	1696.3	1694.3	1692.9
165°	1713.3	1715.4	1717.3	1719.3	1721.3	1721.3	1719.3	1717.3	1715.4	1713.3	1712.5
167.5°	1726.8	1729.4	1731.9	1734.5	1737.0	1737.2	1735.3	1733.3	1731.3	1729.4	1728.6
170°	1734.9	1737.5	1740.0	1742.6	1745.1	1745.3	1743.4	1741.4	1739.5	1737.5	1736.9
172.5°	1741.0	1743.6	1746.1	1748.6	1751.1	1751.4	1749.4	1747.5	1745.5	1743.6	1743.0
175°	1746.3	1749.2	1751.9	1754.8	1757.7	1758.0	1756.0	1754.1	1752.1	1750.2	1749.6
177.5°	1749.6	1751.7	1753.7	1755.7	1757.7	1758.0	1756.4	1754.8	1753.3	1751.7	1751.4
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	981.2	979.2	977.3	972.5	970.1	964.7	963.9	963.7	956.8	950.1	948.2
5°	1014.9	1009.7	1001.7	992.3	982.7	972.7	966.0	960.7	947.4	934.7	927.4
7.5°	1048.9	1037.5	1023.7	1006.0	991.3	974.8	962.6	951.5	932.6	914.5	902.3
10°	1074.2	1055.6	1037.3	1013.0	994.0	975.4	958.1	943.1	921.8	897.8	880.7
12.5°	1089.9	1069.4	1044.2	1020.5	995.9	972.1	949.0	929.7	904.7	879.9	859.7
15°	1111.3	1089.2	1058.6	1024.7	993.0	962.1	935.4	911.4	878.8	849.2	824.5
17.5°	1128.6	1098.3	1065.4	1026.2	989.5	950.2	915.9	885.2	848.9	813.2	784.2
20°	1134.2	1104.2	1066.2	1027.0	983.6	937.4	900.4	867.1	828.1	789.2	755.9
22.5°	1130.7	1107.4	1065.1	1018.2	973.8	925.4	883.7	845.0	801.8	762.1	723.4
25°	1107.2	1099.2	1059.3	1008.0	957.3	901.1	852.8	810.5	761.3	718.6	676.6
27.5°	1052.4	1069.7	1044.9	990.2	934.0	873.6	819.4	771.2	720.1	672.1	630.3
30°	999.7	1039.3	1028.6	978.0	915.1	855.8	794.9	744.6	690.0	640.7	599.4
32.5°	927.5	992.9	1003.4	961.0	895.9	830.7	766.9	716.8	659.9	607.9	567.7
35°	812.5	910.4	955.4	928.4	863.1	792.9	726.9	668.7	611.4	560.1	520.1
37.5°	675.4	808.7	883.7	885.6	825.6	752.6	680.8	622.9	564.3	514.0	470.7
40°	586.4	730.9	828.5	850.2	799.5	720.6	648.0	589.1	531.8	482.5	432.9
42.5°	506.5	650.5	770.4	808.1	767.9	689.5	616.6	555.0	499.3	452.6	402.0
45°	409.6	535.5	667.6	734.9	712.7	640.0	563.1	504.5	452.2	411.9	363.3
47.5°	345.5	434.3	562.1	653.2	652.7	586.5	510.9	454.7	406.2	368.5	329.0
50°	309.0	386.3	494.5	597.7	606.4	550.8	478.8	423.2	378.0	338.3	306.7
52.5°	276.3	339.9	437.2	536.2	560.8	512.6	442.9	391.6	347.6	311.1	284.0
55°	233.4	282.7	356.7	449.2	486.5	452.5	390.6	342.7	307.0	276.4	253.1
57.5°	197.4	234.4	293.7	368.3	411.7	390.3	339.3	300.3	269.8	242.1	223.7
60°	174.9	205.1	255.4	317.7	365.6	350.6	307.0	270.7	244.8	220.8	203.5
62.5°	153.6	179.6	222.7	273.2	317.2	310.9	275.4	244.9	222.1	200.3	185.7
65°	123.5	142.5	176.1	215.8	251.1	254.0	228.5	207.8	187.4	170.1	157.2
67.5°	98.4	110.8	134.5	167.8	194.3	203.8	188.1	172.3	156.1	142.8	131.5
70°	82.9	92.9	110.2	137.2	161.5	171.5	162.5	150.2	136.2	125.2	115.6
72.5°	67.2	77.0	89.7	109.5	130.4	141.2	138.0	129.1	117.8	108.7	99.6
75°	50.6	53.6	62.2	75.6	91.9	101.2	103.5	98.9	89.9	82.9	77.6
77.5°	37.5	39.2	43.3	50.4	61.0	69.3	72.8	72.2	66.0	62.0	57.0
80°	30.0	30.9	33.0	35.9	44.0	52.3	54.6	54.6	50.3	48.6	43.6
82.5°	22.7	23.5	24.7	26.4	30.1	37.4	39.9	40.5	37.7	35.6	31.7
85°	13.0	12.7	13.3	14.4	15.0	16.9	21.0	21.7	21.0	18.3	17.3
87.5°	8.7	8.5	8.0	7.2	6.9	6.6	7.2	7.9	7.5	7.3	7.4
90°	20.9	18.6	16.3	13.6	10.6	7.5	4.4	1.2	4.4	7.5	10.6
92.5°	27.2	26.0	24.9	24.5	24.8	25.1	25.3	25.6	25.3	25.1	24.8
95°	45.5	43.5	41.6	45.2	54.6	63.8	73.1	82.4	73.1	63.8	54.6
97.5°	57.1	52.5	48.0	58.8	85.0	111.2	137.4	163.6	137.4	111.2	85.0
100°	62.7	57.9	53.1	70.0	108.6	147.2	185.8	224.4	185.8	147.2	108.6
102.5°	154.4	194.6	234.6	258.8	266.9	275.1	283.3	291.4	283.3	275.1	266.9
105°	231.2	308.2	385.1	419.4	410.9	402.4	394.0	385.6	394.0	402.4	410.9
107.5°	292.8	385.1	477.4	520.1	513.3	506.5	499.6	492.8	499.6	506.5	513.3
110°	384.9	466.3	547.7	585.5	579.6	573.6	567.8	561.9	567.8	573.6	579.6





TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	600.0	620.2	640.2	647.7	642.5	637.2	632.0	626.8	632.0	637.2	642.5
115°	768.4	761.3	754.3	748.4	743.6	738.8	734.1	729.2	734.1	738.8	743.6
117.5°	857.0	852.1	847.3	842.2	836.9	831.5	826.2	820.8	826.2	831.5	836.9
120°	919.4	914.4	909.3	904.6	900.4	896.2	892.0	887.8	892.0	896.2	900.4
122.5°	978.4	972.9	967.4	962.4	958.0	953.5	949.0	944.6	949.0	953.5	958.0
125°	1061.0	1055.6	1050.3	1045.7	1042.1	1038.4	1034.7	1031.1	1034.7	1038.4	1042.1
127.5°	1137.7	1133.7	1129.7	1125.7	1121.6	1117.6	1113.5	1109.5	1113.5	1117.6	1121.6
130°	1187.2	1184.1	1181.0	1177.2	1172.7	1168.1	1163.7	1159.1	1163.7	1168.1	1172.7
132.5°	1234.8	1231.8	1228.7	1225.2	1221.4	1217.5	1213.7	1209.9	1213.7	1217.5	1221.4
135°	1302.4	1299.9	1297.4	1293.9	1289.3	1284.9	1280.3	1275.9	1280.3	1284.9	1289.3
137.5°	1364.0	1361.0	1358.2	1355.1	1352.0	1348.9	1345.7	1342.6	1345.7	1348.9	1352.0
140°	1404.1	1401.0	1397.8	1395.2	1392.9	1390.7	1388.4	1386.2	1388.4	1390.7	1392.9
142.5°	1440.7	1437.2	1433.6	1430.8	1428.8	1426.7	1424.7	1422.7	1424.7	1426.7	1428.8
145°	1490.8	1485.9	1481.1	1478.9	1479.2	1479.4	1479.7	1480.1	1479.7	1479.4	1479.2
147.5°	1537.0	1532.2	1527.5	1525.7	1526.8	1527.9	1528.9	1530.0	1528.9	1527.9	1526.8
150°	1564.9	1560.3	1555.9	1554.5	1556.6	1558.5	1560.5	1562.5	1560.5	1558.5	1556.6
152.5°	1590.6	1586.4	1582.1	1581.1	1583.2	1585.5	1587.7	1589.8	1587.7	1585.5	1583.2
155°	1626.7	1623.4	1620.0	1619.5	1622.0	1624.6	1627.1	1629.7	1627.1	1624.6	1622.0
157.5°	1657.2	1654.7	1652.4	1652.3	1654.5	1656.6	1658.8	1660.9	1658.8	1656.6	1654.5
160°	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1677.4	1675.8	1674.1
162.5°	1691.4	1690.0	1688.5	1688.6	1690.3	1692.0	1693.7	1695.3	1693.7	1692.0	1690.3
165°	1711.6	1710.8	1710.0	1710.4	1712.1	1713.8	1715.5	1717.2	1715.5	1713.8	1712.1
167.5°	1727.8	1727.0	1726.2	1726.6	1728.3	1730.0	1731.7	1733.4	1731.7	1730.0	1728.3
170°	1736.3	1735.8	1735.2	1735.8	1737.5	1739.2	1740.9	1742.6	1740.9	1739.2	1737.5
172.5°	1742.4	1741.9	1741.3	1741.9	1743.6	1745.3	1747.0	1748.6	1747.0	1745.3	1743.6
175°	1749.0	1748.5	1747.9	1748.6	1750.6	1752.6	1754.5	1756.5	1754.5	1752.6	1750.6
177.5°	1751.2	1751.0	1750.8	1751.4	1753.0	1754.6	1756.2	1757.7	1756.2	1754.6	1753.0
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	944.8	942.9	939.4	934.2	930.9	925.3	921.6	923.7	924.3	923.7	923.2
5°	919.4	912.4	902.8	893.4	884.8	875.5	870.1	867.8	863.1	860.5	859.2
7.5°	888.7	876.6	863.0	846.8	832.9	818.5	811.1	807.4	797.9	792.7	788.2
10°	865.8	846.8	833.1	811.8	798.9	779.9	766.9	767.2	754.2	746.9	741.5
12.5°	840.5	819.7	796.9	777.8	759.7	744.5	728.8	722.5	708.6	701.6	687.2
15°	798.5	774.2	750.3	724.2	706.0	682.3	659.7	632.0	609.8	590.4	585.1
17.5°	752.7	722.6	698.6	668.1	636.7	596.9	570.7	554.6	541.2	531.0	523.4
20°	721.3	690.6	665.0	619.0	576.8	549.7	530.5	518.2	504.2	493.2	487.1
22.5°	688.2	656.3	621.3	570.0	537.1	515.4	498.2	484.0	474.6	466.0	460.6
25°	641.3	606.4	548.8	513.4	486.9	464.2	452.2	443.5	433.5	421.9	416.6
27.5°	591.8	536.2	494.8	468.6	443.2	428.5	417.7	404.7	395.8	390.6	385.0
30°	554.7	499.2	466.9	438.2	420.3	403.9	391.3	384.0	375.3	366.3	362.7
32.5°	513.4	469.0	438.1	414.3	396.0	382.1	372.1	360.3	354.0	348.5	340.8
35°	462.2	428.6	400.3	380.9	363.6	352.3	340.6	333.7	322.4	317.7	314.7
37.5°	418.7	389.6	368.5	348.1	334.4	321.9	314.8	303.6	298.7	292.2	285.9
40°	394.2	365.6	345.4	328.7	313.3	304.0	295.1	286.1	278.7	275.7	268.0
42.5°	369.3	345.9	325.6	307.4	297.1	287.2	275.9	269.3	261.6	256.8	252.1
45°	334.7	314.1	296.7	281.7	270.4	260.1	252.7	241.7	237.5	227.7	223.7
47.5°	304.3	285.1	268.6	254.3	243.3	236.6	225.9	217.2	210.4	204.4	199.3
50°	282.7	266.7	250.7	238.1	228.1	218.5	207.5	203.1	192.4	189.5	186.5
52.5°	263.0	247.8	233.2	220.8	210.8	201.4	191.7	186.1	178.9	175.8	173.7
55°	235.4	220.8	206.8	195.8	185.8	176.1	170.1	163.2	159.8	157.5	154.8
57.5°	207.7	194.6	183.8	172.7	162.6	155.0	148.0	143.8	140.4	137.3	134.1
60°	190.1	177.5	167.8	157.5	147.2	140.9	135.5	130.5	126.5	121.9	120.6
62.5°	171.5	160.4	151.6	141.5	132.5	126.7	121.7	117.0	112.2	105.4	103.5
65°	145.9	137.2	127.9	119.6	111.6	105.9	98.5	93.3	91.2	90.6	90.2
67.5°	122.7	114.5	106.5	98.0	90.7	85.4	81.7	80.9	79.5	79.1	78.2
70°	107.2	99.6	91.6	83.6	76.6	75.6	74.3	72.9	71.2	70.6	69.9
72.5°	93.4	85.4	77.5	71.1	68.0	66.8	65.5	64.1	63.0	62.3	62.0
75°	71.6	64.3	58.9	56.6	54.9	53.9	52.0	50.9	50.3	49.3	49.0
77.5°	51.5	47.4	44.9	43.5	41.7	40.7	39.6	38.5	37.8	37.6	37.1
80°	39.3	37.3	35.7	33.6	33.0	31.7	31.3	30.3	30.7	29.6	29.6
82.5°	30.5	28.0	26.6	25.7	25.0	23.9	23.5	23.1	23.2	22.5	22.5
85°	15.7	15.0	14.4	13.6	13.6	12.7	13.0	12.7	12.7	11.9	11.7
87.5°	7.8	8.0	8.0	8.5	8.9	9.1	9.4	9.4	9.6	9.9	9.9
90°	13.6	16.3	18.6	20.9	23.1	25.3	26.8	28.2	29.6	31.0	32.0
92.5°	24.5	24.9	26.0	27.2	28.3	29.4	30.1	30.9	31.7	32.4	32.9
95°	45.2	41.6	43.5	45.5	47.5	49.5	50.8	52.3	53.7	55.1	55.6
97.5°	58.8	48.0	52.5	57.1	61.6	66.2	67.3	68.5	69.6	70.7	71.4
100°	70.0	53.1	57.9	62.7	67.5	72.3	74.5	76.8	79.1	81.3	82.8
102.5°	258.8	234.6	194.6	154.4	114.4	74.3	77.2	80.2	83.1	86.1	87.9
105°	419.4	385.1	308.2	231.2	154.3	77.4	80.4	83.6	86.7	89.8	91.8
107.5°	520.1	477.4	385.1	292.8	200.5	108.3	105.1	102.0	98.8	95.7	94.7
110°	585.5	547.7	466.3	384.9	303.4	221.9	193.8	165.6	137.4	109.2	95.7



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	647.7	640.2	620.2	600.0	579.9	559.8	457.0	354.2	251.4	148.6	97.6
115°	748.4	754.3	761.3	768.4	775.4	782.5	652.0	521.6	391.0	260.6	185.1
117.5°	842.2	847.3	852.1	857.0	861.8	866.7	835.2	803.6	772.0	740.5	691.3
120°	904.6	909.3	914.4	919.4	924.5	929.6	933.0	936.4	939.8	943.2	925.8
122.5°	962.4	967.4	972.9	978.4	983.9	989.4	991.5	993.5	995.6	997.6	994.9
125°	1045.7	1050.3	1055.6	1061.0	1066.3	1071.7	1073.6	1075.6	1077.5	1079.5	1080.9
127.5°	1125.7	1129.7	1133.7	1137.7	1141.7	1145.8	1148.6	1151.5	1154.3	1157.2	1158.8
130°	1177.2	1181.0	1184.1	1187.2	1190.3	1193.4	1196.5	1199.6	1202.7	1205.8	1207.2
132.5°	1225.2	1228.7	1231.8	1234.8	1238.0	1241.1	1243.8	1246.3	1249.0	1251.7	1252.9
135°	1293.9	1297.4	1299.9	1302.4	1305.0	1307.5	1310.4	1313.1	1316.0	1318.8	1319.9
137.5°	1355.1	1358.2	1361.0	1364.0	1366.8	1369.7	1372.4	1375.2	1378.0	1380.7	1381.6
140°	1395.2	1397.8	1401.0	1404.1	1407.2	1410.2	1412.8	1415.3	1417.9	1420.4	1420.9
142.5°	1430.8	1433.6	1437.2	1440.7	1444.2	1447.8	1450.1	1452.4	1454.7	1457.1	1457.5
145°	1478.9	1481.1	1485.9	1490.8	1495.5	1500.3	1502.3	1504.2	1506.2	1508.2	1508.5
147.5°	1525.7	1527.5	1532.2	1537.0	1541.8	1546.5	1547.9	1549.4	1550.9	1552.4	1552.5
150°	1554.5	1555.9	1560.3	1564.9	1569.3	1573.9	1575.6	1577.3	1579.0	1580.6	1580.7
152.5°	1581.1	1582.1	1586.4	1590.6	1594.9	1599.2	1600.9	1602.6	1604.3	1606.0	1605.9
155°	1619.5	1620.0	1623.4	1626.7	1630.1	1633.4	1635.1	1636.8	1638.5	1640.2	1639.9
157.5°	1652.3	1652.4	1654.7	1657.2	1659.5	1661.9	1663.8	1665.7	1667.6	1669.6	1669.4
160°	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1680.8	1682.5	1684.2	1685.9	1685.8
162.5°	1688.6	1688.5	1690.0	1691.4	1692.9	1694.3	1696.3	1698.2	1700.1	1702.0	1701.7
165°	1710.4	1710.0	1710.8	1711.6	1712.5	1713.3	1715.4	1717.3	1719.3	1721.3	1721.3
167.5°	1726.6	1726.2	1727.0	1727.8	1728.6	1729.4	1731.3	1733.3	1735.3	1737.2	1737.0
170°	1735.8	1735.2	1735.8	1736.3	1736.9	1737.5	1739.5	1741.4	1743.4	1745.3	1745.1
172.5°	1741.9	1741.3	1741.9	1742.4	1743.0	1743.6	1745.5	1747.5	1749.4	1751.4	1751.1
175°	1748.6	1747.9	1748.5	1749.0	1749.6	1750.2	1752.1	1754.1	1756.0	1758.0	1757.7
177.5°	1751.4	1750.8	1751.0	1751.2	1751.4	1751.7	1753.3	1754.8	1756.4	1758.0	1757.7
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	920.2	920.8	920.0	920.5	920.0	920.8	920.2	923.2	923.7	924.3	923.7
5°	857.5	853.5	852.8	851.9	852.8	853.5	857.5	859.2	860.5	863.1	867.8
7.5°	782.5	781.9	780.2	777.8	780.2	781.9	782.5	788.2	792.7	797.9	807.4
10°	734.2	732.6	732.3	730.0	732.3	732.6	734.2	741.5	746.9	754.2	767.2
12.5°	677.8	667.1	665.9	660.1	665.9	667.1	677.8	687.2	701.6	708.6	722.5
15°	577.1	575.1	568.5	564.1	568.5	575.1	577.1	585.1	590.4	609.8	632.0
17.5°	519.5	513.0	511.0	510.1	511.0	513.0	519.5	523.4	531.0	541.2	554.6
20°	482.5	476.5	475.5	474.8	475.5	476.5	482.5	487.1	493.2	504.2	518.2
22.5°	456.9	450.7	448.1	446.1	448.1	450.7	456.9	460.6	466.0	474.6	484.0
25°	413.2	410.9	409.6	408.9	409.6	410.9	413.2	416.6	421.9	433.5	443.5
27.5°	379.1	374.0	372.9	371.2	372.9	374.0	379.1	385.0	390.6	395.8	404.7
30°	359.6	357.9	355.6	353.7	355.6	357.9	359.6	362.7	366.3	375.3	384.0
32.5°	336.7	335.4	333.2	332.3	333.2	335.4	336.7	340.8	348.5	354.0	360.3
35°	311.4	306.7	304.7	301.7	304.7	306.7	311.4	314.7	317.7	322.4	333.7
37.5°	284.5	282.0	279.3	280.3	279.3	282.0	284.5	285.9	292.2	298.7	303.6
40°	263.8	262.1	261.4	261.1	261.4	262.1	263.8	268.0	275.7	278.7	286.1
42.5°	247.2	242.6	240.9	240.9	240.9	242.6	247.2	252.1	256.8	261.6	269.3
45°	222.1	217.8	214.8	215.1	214.8	217.8	222.1	223.7	227.7	237.5	241.7
47.5°	196.4	196.3	194.4	195.0	194.4	196.3	196.4	199.3	204.4	210.4	217.2
50°	184.1	182.2	180.8	181.1	180.8	182.2	184.1	186.5	189.5	192.4	203.1
52.5°	172.5	170.7	169.6	171.0	169.6	170.7	172.5	173.7	175.8	178.9	186.1
55°	153.2	151.1	150.9	150.5	150.9	151.1	153.2	154.8	157.5	159.8	163.2
57.5°	131.7	130.4	128.3	127.5	128.3	130.4	131.7	134.1	137.3	140.4	143.8
60°	116.2	113.5	110.2	109.9	110.2	113.5	116.2	120.6	121.9	126.5	130.5
62.5°	102.1	101.6	100.9	100.9	100.9	101.6	102.1	103.5	105.4	112.2	117.0
65°	89.6	89.3	89.6	89.9	89.6	89.3	89.6	90.2	90.6	91.2	93.3
67.5°	78.0	77.5	76.9	77.1	76.9	77.5	78.0	78.2	79.1	79.5	80.9
70°	69.3	68.9	68.6	68.6	68.6	68.9	69.3	69.9	70.6	71.2	72.9
72.5°	60.7	60.6	60.4	60.1	60.4	60.6	60.7	62.0	62.3	63.0	64.1
75°	48.6	48.0	48.0	48.0	48.0	48.0	48.6	49.0	49.3	50.3	50.9
77.5°	37.0	36.7	36.4	36.1	36.4	36.7	37.0	37.1	37.6	37.8	38.5
80°	29.3	29.0	28.6	28.6	28.6	29.0	29.3	29.6	29.6	30.7	30.3
82.5°	22.4	22.0	21.9	21.7	21.9	22.0	22.4	22.5	22.5	23.2	23.1
85°	11.9	12.3	11.9	12.7	11.9	12.3	11.9	11.7	11.9	12.7	12.7
87.5°	10.0	9.8	10.2	10.1	10.2	9.8	10.0	9.9	9.9	9.6	9.4
90°	32.5	33.1	33.7	34.2	33.7	33.1	32.5	32.0	31.0	29.6	28.2
92.5°	33.3	33.5	33.9	34.2	33.9	33.5	33.3	32.9	32.4	31.7	30.9
95°	55.4	55.1	54.8	54.6	54.8	55.1	55.4	55.6	55.1	53.7	52.3
97.5°	71.8	72.1	72.5	72.8	72.5	72.1	71.8	71.4	70.7	69.6	68.5
100°	83.3	83.8	84.4	85.0	84.4	83.8	83.3	82.8	81.3	79.1	76.8
102.5°	88.7	89.4	90.2	91.0	90.2	89.4	88.7	87.9	86.1	83.1	80.2
105°	93.0	94.2	95.2	96.4	95.2	94.2	93.0	91.8	89.8	86.7	83.6
107.5°	95.8	96.9	98.1	99.2	98.1	96.9	95.8	94.7	95.7	98.8	102.0
110°	96.8	97.9	99.1	100.2	99.1	97.9	96.8	95.7	109.2	137.4	165.6



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	98.5	99.4	100.3	101.2	100.3	99.4	98.5	97.6	148.6	251.4	354.2
115°	164.9	144.5	124.3	104.0	124.3	144.5	164.9	185.1	260.6	391.0	521.6
117.5°	624.6	557.9	491.2	424.6	491.2	557.9	624.6	691.3	740.5	772.0	803.6
120°	887.8	849.7	811.6	773.6	811.6	849.7	887.8	925.8	943.2	939.8	936.4
122.5°	987.5	980.2	972.8	965.4	972.8	980.2	987.5	994.9	997.6	995.6	993.5
125°	1081.8	1082.6	1083.5	1084.3	1083.5	1082.6	1081.8	1080.9	1079.5	1077.5	1075.6
127.5°	1158.9	1159.0	1159.2	1159.4	1159.2	1159.0	1158.9	1158.8	1157.2	1154.3	1151.5
130°	1206.9	1206.7	1206.4	1206.0	1206.4	1206.7	1206.9	1207.2	1205.8	1202.7	1199.6
132.5°	1252.6	1252.3	1252.1	1251.7	1252.1	1252.3	1252.6	1252.9	1251.7	1249.0	1246.3
135°	1319.4	1318.8	1318.2	1317.7	1318.2	1318.8	1319.4	1319.9	1318.8	1316.0	1313.1
137.5°	1380.6	1379.7	1378.8	1377.8	1378.8	1379.7	1380.6	1381.6	1380.7	1378.0	1375.2
140°	1419.6	1418.2	1416.8	1415.3	1416.8	1418.2	1419.6	1420.9	1420.4	1417.9	1415.3
142.5°	1456.1	1454.6	1453.3	1451.9	1453.3	1454.6	1456.1	1457.5	1457.1	1454.7	1452.4
145°	1507.1	1505.7	1504.2	1502.9	1504.2	1505.7	1507.1	1508.5	1508.2	1506.2	1504.2
147.5°	1551.3	1550.2	1548.9	1547.7	1548.9	1550.2	1551.3	1552.5	1552.4	1550.9	1549.4
150°	1579.4	1578.0	1576.5	1575.1	1576.5	1578.0	1579.4	1580.7	1580.6	1579.0	1577.3
152.5°	1604.0	1602.2	1600.4	1598.5	1600.4	1602.2	1604.0	1605.9	1606.0	1604.3	1602.6
155°	1637.7	1635.5	1633.2	1630.9	1633.2	1635.5	1637.7	1639.9	1640.2	1638.5	1636.8
157.5°	1667.2	1665.0	1662.8	1660.6	1662.8	1665.0	1667.2	1669.4	1669.6	1667.6	1665.7
160°	1683.8	1681.8	1679.8	1677.8	1679.8	1681.8	1683.8	1685.8	1685.9	1684.2	1682.5
162.5°	1699.3	1696.9	1694.5	1692.1	1694.5	1696.9	1699.3	1701.7	1702.0	1700.1	1698.2
165°	1719.3	1717.3	1715.4	1713.3	1715.4	1717.3	1719.3	1721.3	1721.3	1719.3	1717.3
167.5°	1734.5	1731.9	1729.4	1726.8	1729.4	1731.9	1734.5	1737.0	1737.2	1735.3	1733.3
170°	1742.6	1740.0	1737.5	1734.9	1737.5	1740.0	1742.6	1745.1	1745.3	1743.4	1741.4
172.5°	1748.6	1746.1	1743.6	1741.0	1743.6	1746.1	1748.6	1751.1	1751.4	1749.4	1747.5
175°	1754.8	1751.9	1749.2	1746.3	1749.2	1751.9	1754.8	1757.7	1758.0	1756.0	1754.1
177.5°	1755.7	1753.7	1751.7	1749.6	1751.7	1753.7	1755.7	1757.7	1758.0	1756.4	1754.8
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	921.6	925.3	930.9	934.2	939.4	942.9	944.8	948.2	950.1	956.8	963.7
5°	870.1	875.5	884.8	893.4	902.8	912.4	919.4	927.4	934.7	947.4	960.7
7.5°	811.1	818.5	832.9	846.8	863.0	876.6	888.7	902.3	914.5	932.6	951.5
10°	766.9	779.9	798.9	811.8	833.1	846.8	865.8	880.7	897.8	921.8	943.1
12.5°	728.8	744.5	759.7	777.8	796.9	819.7	840.5	859.7	879.9	904.7	929.7
15°	659.7	682.3	706.0	724.2	750.3	774.2	798.5	824.5	849.2	878.8	911.4
17.5°	570.7	596.9	636.7	668.1	698.6	722.6	752.7	784.2	813.2	848.9	885.2
20°	530.5	549.7	576.8	619.0	665.0	690.6	721.3	755.9	789.2	828.1	867.1
22.5°	498.2	515.4	537.1	570.0	621.3	656.3	688.2	723.4	762.1	801.8	845.0
25°	452.2	464.2	486.9	513.4	548.8	606.4	641.3	676.6	718.6	761.3	810.5
27.5°	417.7	428.5	443.2	468.6	494.8	536.2	591.8	630.3	672.1	720.1	771.2
30°	391.3	403.9	420.3	438.2	466.9	499.2	554.7	599.4	640.7	690.0	744.6
32.5°	372.1	382.1	396.0	414.3	438.1	469.0	513.4	567.7	607.9	659.9	716.8
35°	340.6	352.3	363.6	380.9	400.3	428.6	462.2	520.1	560.1	611.4	668.7
37.5°	314.8	321.9	334.4	348.1	368.5	389.6	418.7	470.7	514.0	564.3	622.9
40°	295.1	304.0	313.3	328.7	345.4	365.6	394.2	432.9	482.5	531.8	589.1
42.5°	275.9	287.2	297.1	307.4	325.6	345.9	369.3	402.0	452.6	499.3	555.0
45°	252.7	260.1	270.4	281.7	296.7	314.1	334.7	363.3	411.9	452.2	504.5
47.5°	225.9	236.6	243.3	254.3	268.6	285.1	304.3	329.0	368.5	406.2	454.7
50°	207.5	218.5	228.1	238.1	250.7	266.7	282.7	306.7	338.3	378.0	423.2
52.5°	191.7	201.4	210.8	220.8	233.2	247.8	263.0	284.0	311.1	347.6	391.6
55°	170.1	176.1	185.8	195.8	206.8	220.8	235.4	253.1	276.4	307.0	342.7
57.5°	148.0	155.0	162.6	172.7	183.8	194.6	207.7	223.7	242.1	269.8	300.3
60°	135.5	140.9	147.2	157.5	167.8	177.5	190.1	203.5	220.8	244.8	270.7
62.5°	121.7	126.7	132.5	141.5	151.6	160.4	171.5	185.7	200.3	222.1	244.9
65°	98.5	105.9	111.6	119.6	127.9	137.2	145.9	157.2	170.1	187.4	207.8
67.5°	81.7	85.4	90.7	98.0	106.5	114.5	122.7	131.5	142.8	156.1	172.3
70°	74.3	75.6	76.6	83.6	91.6	99.6	107.2	115.6	125.2	136.2	150.2
72.5°	65.5	66.8	68.0	71.1	77.5	85.4	93.4	99.6	108.7	117.8	129.1
75°	52.0	53.9	54.9	56.6	58.9	64.3	71.6	77.6	82.9	89.9	98.9
77.5°	39.6	40.7	41.7	43.5	44.9	47.4	51.5	57.0	62.0	66.0	72.2
80°	31.3	31.7	33.0	33.6	35.7	37.3	39.3	43.6	48.6	50.3	54.6
82.5°	23.5	23.9	25.0	25.7	26.6	28.0	30.5	31.7	35.6	37.7	40.5
85°	13.0	12.7	13.6	13.6	14.4	15.0	15.7	17.3	18.3	21.0	21.7
87.5°	9.4	9.1	8.9	8.5	8.0	8.0	7.8	7.4	7.3	7.5	7.9
90°	26.8	25.3	23.1	20.9	18.6	16.3	13.6	10.6	7.5	4.4	1.2
92.5°	30.1	29.4	28.3	27.2	26.0	24.9	24.5	24.8	25.1	25.3	25.6
95°	50.8	49.5	47.5	45.5	43.5	41.6	45.2	54.6	63.8	73.1	82.4
97.5°	67.3	66.2	61.6	57.1	52.5	48.0	58.8	85.0	111.2	137.4	163.6
100°	74.5	72.3	67.5	62.7	57.9	53.1	70.0	108.6	147.2	185.8	224.4
102.5°	77.2	74.3	114.4	154.4	194.6	234.6	258.8	266.9	275.1	283.3	291.4
105°	80.4	77.4	154.3	231.2	308.2	385.1	419.4	410.9	402.4	394.0	385.6
107.5°	105.1	108.3	200.5	292.8	385.1	477.4	520.1	513.3	506.5	499.6	492.8
110°	193.8	221.9	303.4	384.9	466.3	547.7	585.5	579.6	573.6	567.8	561.9



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	457.0	559.8	579.9	600.0	620.2	640.2	647.7	642.5	637.2	632.0	626.8
115°	652.0	782.5	775.4	768.4	761.3	754.3	748.4	743.6	738.8	734.1	729.2
117.5°	835.2	866.7	861.8	857.0	852.1	847.3	842.2	836.9	831.5	826.2	820.8
120°	933.0	929.6	924.5	919.4	914.4	909.3	904.6	900.4	896.2	892.0	887.8
122.5°	991.5	989.4	983.9	978.4	972.9	967.4	962.4	958.0	953.5	949.0	944.6
125°	1073.6	1071.7	1066.3	1061.0	1055.6	1050.3	1045.7	1042.1	1038.4	1034.7	1031.1
127.5°	1148.6	1145.8	1141.7	1137.7	1133.7	1129.7	1125.7	1121.6	1117.6	1113.5	1109.5
130°	1196.5	1193.4	1190.3	1187.2	1184.1	1181.0	1177.2	1172.7	1168.1	1163.7	1159.1
132.5°	1243.8	1241.1	1238.0	1234.8	1231.8	1228.7	1225.2	1221.4	1217.5	1213.7	1209.9
135°	1310.4	1307.5	1305.0	1302.4	1299.9	1297.4	1293.9	1289.3	1284.9	1280.3	1275.9
137.5°	1372.4	1369.7	1366.8	1364.0	1361.0	1358.2	1355.1	1352.0	1348.9	1345.7	1342.6
140°	1412.8	1410.2	1407.2	1404.1	1401.0	1397.8	1395.2	1392.9	1390.7	1388.4	1386.2
142.5°	1450.1	1447.8	1444.2	1440.7	1437.2	1433.6	1430.8	1428.8	1426.7	1424.7	1422.7
145°	1502.3	1500.3	1495.5	1490.8	1485.9	1481.1	1478.9	1479.2	1479.4	1479.7	1480.1
147.5°	1547.9	1546.5	1541.8	1537.0	1532.2	1527.5	1525.7	1526.8	1527.9	1528.9	1530.0
150°	1575.6	1573.9	1569.3	1564.9	1560.3	1555.9	1554.5	1556.6	1558.5	1560.5	1562.5
152.5°	1600.9	1599.2	1594.9	1590.6	1586.4	1582.1	1581.1	1583.2	1585.5	1587.7	1589.8
155°	1635.1	1633.4	1630.1	1626.7	1623.4	1620.0	1619.5	1622.0	1624.6	1627.1	1629.7
157.5°	1663.8	1661.9	1659.5	1657.2	1654.7	1652.4	1652.3	1654.5	1656.6	1658.8	1660.9
160°	1680.8	1679.1	1677.4	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1
162.5°	1696.3	1694.3	1692.9	1691.4	1690.0	1688.5	1688.6	1690.3	1692.0	1693.7	1695.3
165°	1715.4	1713.3	1712.5	1711.6	1710.8	1710.0	1710.4	1712.1	1713.8	1715.5	1717.2
167.5°	1731.3	1729.4	1728.6	1727.8	1727.0	1726.2	1726.6	1728.3	1730.0	1731.7	1733.4
170°	1739.5	1737.5	1736.9	1736.3	1735.8	1735.2	1735.8	1737.5	1739.2	1740.9	1742.6
172.5°	1745.5	1743.6	1743.0	1742.4	1741.9	1741.3	1741.9	1743.6	1745.3	1747.0	1748.6
175°	1752.1	1750.2	1749.6	1749.0	1748.5	1747.9	1748.6	1750.6	1752.6	1754.5	1756.5
177.5°	1753.3	1751.7	1751.4	1751.2	1751.0	1750.8	1751.4	1753.0	1754.6	1756.2	1757.7
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	963.9	964.7	970.1	972.5	977.3	979.2	981.2	980.7	980.7	981.8	989.3
5°	966.0	972.7	982.7	992.3	1001.7	1009.7	1014.9	1020.3	1022.3	1032.0	1040.6
7.5°	962.6	974.8	991.3	1006.0	1023.7	1037.5	1048.9	1059.3	1066.3	1080.4	1094.8
10°	958.1	975.4	994.0	1013.0	1037.3	1055.6	1074.2	1088.6	1093.2	1114.2	1126.2
12.5°	949.0	972.1	995.9	1020.5	1044.2	1069.4	1089.9	1104.3	1120.7	1139.5	1161.6
15°	935.4	962.1	993.0	1024.7	1058.6	1089.2	1111.3	1136.2	1154.1	1174.8	1194.1
17.5°	915.9	950.2	989.5	1026.2	1065.4	1098.3	1128.6	1152.5	1165.2	1177.0	1179.9
20°	900.4	937.4	983.6	1027.0	1066.2	1104.2	1134.2	1154.1	1157.5	1157.8	1140.1
22.5°	883.7	925.4	973.8	1018.2	1065.1	1107.4	1130.7	1139.2	1126.1	1103.5	1069.3
25°	852.8	901.1	957.3	1008.0	1059.3	1099.2	1107.2	1092.3	1046.0	997.3	935.8
27.5°	819.4	873.6	934.0	990.2	1044.9	1069.7	1052.4	998.4	915.0	842.6	754.7
30°	794.9	855.8	915.1	978.0	1028.6	1039.3	999.7	920.1	822.9	713.6	626.1
32.5°	766.9	830.7	895.9	961.0	1003.4	992.9	927.5	829.5	715.5	608.1	525.3
35°	726.9	792.9	863.1	928.4	955.4	910.4	812.5	685.0	568.5	468.2	411.3
37.5°	680.8	752.6	825.6	885.6	883.7	808.7	675.4	543.7	445.8	386.5	345.9
40°	648.0	720.6	799.5	850.2	828.5	730.9	586.4	462.2	390.6	343.3	313.7
42.5°	616.6	689.5	767.9	808.1	770.4	650.5	506.5	409.2	350.1	313.3	289.2
45°	563.1	640.0	712.7	734.9	667.6	535.5	409.6	339.0	299.7	272.4	255.7
47.5°	510.9	586.5	652.7	653.2	562.1	434.3	345.5	293.4	259.8	238.7	226.6
50°	478.8	550.8	606.4	597.7	494.5	386.3	309.0	264.0	236.1	219.8	207.1
52.5°	442.9	512.6	560.8	536.2	437.2	339.9	276.3	238.5	215.3	201.2	189.8
55°	390.6	452.5	486.5	449.2	356.7	282.7	233.4	203.8	186.5	174.5	164.9
57.5°	339.3	390.3	411.7	368.3	293.7	234.4	197.4	175.2	158.0	149.5	144.5
60°	307.0	350.6	365.6	317.7	255.4	205.1	174.9	154.2	141.5	135.9	130.9
62.5°	275.4	310.9	317.2	273.2	222.7	179.6	153.6	136.1	127.7	122.3	117.5
65°	228.5	254.0	251.1	215.8	176.1	142.5	123.5	112.9	106.6	98.9	90.6
67.5°	188.1	203.8	194.3	167.8	134.5	110.8	98.4	90.3	82.5	75.2	73.3
70°	162.5	171.5	161.5	137.2	110.2	92.9	82.9	73.3	68.6	67.0	63.9
72.5°	138.0	141.2	130.4	109.5	89.7	77.0	67.2	61.8	59.3	57.9	55.9
75°	103.5	101.2	91.9	75.6	62.2	53.6	50.6	48.6	47.0	45.7	44.6
77.5°	72.8	69.3	61.0	50.4	43.3	39.2	37.5	36.4	35.6	34.9	33.9
80°	54.6	52.3	44.0	35.9	33.0	30.9	30.0	28.6	28.6	28.0	26.9
82.5°	39.9	37.4	30.1	26.4	24.7	23.5	22.7	21.9	21.7	21.8	21.1
85°	21.0	16.9	15.0	14.4	13.3	12.7	13.0	12.3	12.3	12.3	11.9
87.5°	7.2	6.6	6.9	7.2	8.0	8.5	8.7	9.2	9.9	9.9	10.4
90°	4.4	7.5	10.6	13.6	16.3	18.6	20.9	23.1	25.3	26.8	28.2
92.5°	25.3	25.1	24.8	24.5	24.9	26.0	27.2	28.3	29.4	30.1	30.9
95°	73.1	63.8	54.6	45.2	41.6	43.5	45.5	47.5	49.5	50.8	52.3
97.5°	137.4	111.2	85.0	58.8	48.0	52.5	57.1	61.6	66.2	67.3	68.5
100°	185.8	147.2	108.6	70.0	53.1	57.9	62.7	67.5	72.3	74.5	76.8
102.5°	283.3	275.1	266.9	258.8	234.6	194.6	154.4	114.4	74.3	77.2	80.2
105°	394.0	402.4	410.9	419.4	385.1	308.2	231.2	154.3	77.4	80.4	83.6
107.5°	499.6	506.5	513.3	520.1	477.4	385.1	292.8	200.5	108.3	105.1	102.0
110°	567.8	573.6	579.6	585.5	547.7	466.3	384.9	303.4	221.9	193.8	165.6





TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	632.0	637.2	642.5	647.7	640.2	620.2	600.0	579.9	559.8	457.0	354.2
115°	734.1	738.8	743.6	748.4	754.3	761.3	768.4	775.4	782.5	652.0	521.6
117.5°	826.2	831.5	836.9	842.2	847.3	852.1	857.0	861.8	866.7	835.2	803.6
120°	892.0	896.2	900.4	904.6	909.3	914.4	919.4	924.5	929.6	933.0	936.4
122.5°	949.0	953.5	958.0	962.4	967.4	972.9	978.4	983.9	989.4	991.5	993.5
125°	1034.7	1038.4	1042.1	1045.7	1050.3	1055.6	1061.0	1066.3	1071.7	1073.6	1075.6
127.5°	1113.5	1117.6	1121.6	1125.7	1129.7	1133.7	1137.7	1141.7	1145.8	1148.6	1151.5
130°	1163.7	1168.1	1172.7	1177.2	1181.0	1184.1	1187.2	1190.3	1193.4	1196.5	1199.6
132.5°	1213.7	1217.5	1221.4	1225.2	1228.7	1231.8	1234.8	1238.0	1241.1	1243.8	1246.3
135°	1280.3	1284.9	1289.3	1293.9	1297.4	1299.9	1302.4	1305.0	1307.5	1310.4	1313.1
137.5°	1345.7	1348.9	1352.0	1355.1	1358.2	1361.0	1364.0	1366.8	1369.7	1372.4	1375.2
140°	1388.4	1390.7	1392.9	1395.2	1397.8	1401.0	1404.1	1407.2	1410.2	1412.8	1415.3
142.5°	1424.7	1426.7	1428.8	1430.8	1433.6	1437.2	1440.7	1444.2	1447.8	1450.1	1452.4
145°	1479.7	1479.4	1479.2	1478.9	1481.1	1485.9	1490.8	1495.5	1500.3	1502.3	1504.2
147.5°	1528.9	1527.9	1526.8	1525.7	1527.5	1532.2	1537.0	1541.8	1546.5	1547.9	1549.4
150°	1560.5	1558.5	1556.6	1554.5	1555.9	1560.3	1564.9	1569.3	1573.9	1575.6	1577.3
152.5°	1587.7	1585.5	1583.2	1581.1	1582.1	1586.4	1590.6	1594.9	1599.2	1600.9	1602.6
155°	1627.1	1624.6	1622.0	1619.5	1620.0	1623.4	1626.7	1630.1	1633.4	1635.1	1636.8
157.5°	1658.8	1656.6	1654.5	1652.3	1652.4	1654.7	1657.2	1659.5	1661.9	1663.8	1665.7
160°	1677.4	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1680.8	1682.5
162.5°	1693.7	1692.0	1690.3	1688.6	1688.5	1690.0	1691.4	1692.9	1694.3	1696.3	1698.2
165°	1715.5	1713.8	1712.1	1710.4	1710.0	1710.8	1711.6	1712.5	1713.3	1715.4	1717.3
167.5°	1731.7	1730.0	1728.3	1726.6	1726.2	1727.0	1727.8	1728.6	1729.4	1731.3	1733.3
170°	1740.9	1739.2	1737.5	1735.8	1735.2	1735.8	1736.3	1736.9	1737.5	1739.5	1741.4
172.5°	1747.0	1745.3	1743.6	1741.9	1741.3	1741.9	1742.4	1743.0	1743.6	1745.5	1747.5
175°	1754.5	1752.6	1750.6	1748.6	1747.9	1748.5	1749.0	1749.6	1750.2	1752.1	1754.1
177.5°	1756.2	1754.6	1753.0	1751.4	1750.8	1751.0	1751.2	1751.4	1751.7	1753.3	1754.8
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	991.9	995.4	997.0	997.0	998.9	998.1	997.3
5°	1048.9	1055.3	1056.6	1062.6	1066.9	1065.6	1066.2
7.5°	1105.6	1115.8	1125.9	1130.4	1131.2	1133.9	1134.9
10°	1140.5	1148.9	1164.5	1162.2	1173.8	1180.4	1169.5
12.5°	1174.1	1185.4	1196.2	1199.2	1205.8	1207.9	1203.5
15°	1204.4	1210.4	1211.1	1209.4	1211.5	1209.8	1203.5
17.5°	1176.1	1166.4	1146.7	1137.3	1129.9	1119.0	1114.6
20°	1129.2	1100.5	1067.3	1053.9	1038.3	1007.6	1014.9
22.5°	1028.0	995.3	962.1	923.1	904.6	875.5	873.8
25°	870.5	814.2	752.2	708.9	683.7	654.7	642.0
27.5°	676.8	605.9	555.2	529.5	506.0	483.1	482.1
30°	549.5	496.1	456.9	434.9	420.6	410.9	413.0
32.5°	463.2	426.6	400.1	381.9	371.3	364.0	363.9
35°	378.6	353.7	336.6	329.0	321.4	316.0	316.4
37.5°	324.0	309.0	299.5	291.1	286.3	283.7	282.2
40°	296.0	283.7	276.4	271.4	267.4	263.8	263.1
42.5°	273.9	263.8	256.4	252.4	248.8	246.1	245.5
45°	243.1	234.8	228.1	223.7	222.1	219.8	219.8
47.5°	216.2	208.0	202.9	200.1	197.2	195.7	195.6
50°	198.1	191.8	187.2	185.5	183.2	182.2	181.8
52.5°	181.9	177.2	173.8	172.7	171.7	170.4	170.6
55°	159.8	157.2	155.9	154.8	153.2	151.1	152.5
57.5°	141.2	139.0	135.4	132.2	130.7	129.3	129.8
60°	128.2	123.5	118.9	115.2	114.2	111.2	111.2
62.5°	111.7	105.1	99.4	97.4	96.4	95.0	94.7
65°	85.9	83.3	81.9	80.6	79.9	79.9	79.3
67.5°	71.2	70.1	68.7	68.3	67.7	67.5	67.2
70°	63.0	61.6	60.9	60.6	59.9	60.3	59.3
72.5°	54.9	53.9	53.8	52.9	52.5	52.5	51.8
75°	43.2	43.2	43.0	42.6	42.0	41.6	42.0
77.5°	33.3	33.3	32.7	32.7	32.6	32.7	32.4
80°	26.7	26.9	26.7	26.3	25.9	26.3	25.9
82.5°	21.0	20.6	20.5	20.4	20.4	20.2	20.2
85°	11.9	12.3	11.9	11.7	11.7	11.7	11.9
87.5°	10.4	10.7	11.0	11.1	11.1	11.2	11.1
90°	29.6	31.0	32.0	32.5	33.1	33.7	34.2
92.5°	31.7	32.4	32.9	33.3	33.5	33.9	34.2
95°	53.7	55.1	55.6	55.4	55.1	54.8	54.6
97.5°	69.6	70.7	71.4	71.8	72.1	72.5	72.8
100°	79.1	81.3	82.8	83.3	83.8	84.4	85.0
102.5°	83.1	86.1	87.9	88.7	89.4	90.2	91.0
105°	86.7	89.8	91.8	93.0	94.2	95.2	96.4
107.5°	98.8	95.7	94.7	95.8	96.9	98.1	99.2
110°	137.4	109.2	95.7	96.8	97.9	99.1	100.2



TEST NUMBER: P331801-940

CATALOG NUMBER: S122RDIW-S485D1440U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	251.4	148.6	97.6	98.5	99.4	100.3	101.2
115°	391.0	260.6	185.1	164.9	144.5	124.3	104.0
117.5°	772.0	740.5	691.3	624.6	557.9	491.2	424.6
120°	939.8	943.2	925.8	887.8	849.7	811.6	773.6
122.5°	995.6	997.6	994.9	987.5	980.2	972.8	965.4
125°	1077.5	1079.5	1080.9	1081.8	1082.6	1083.5	1084.3
127.5°	1154.3	1157.2	1158.8	1158.9	1159.0	1159.2	1159.4
130°	1202.7	1205.8	1207.2	1206.9	1206.7	1206.4	1206.0
132.5°	1249.0	1251.7	1252.9	1252.6	1252.3	1252.1	1251.7
135°	1316.0	1318.8	1319.9	1319.4	1318.8	1318.2	1317.7
137.5°	1378.0	1380.7	1381.6	1380.6	1379.7	1378.8	1377.8
140°	1417.9	1420.4	1420.9	1419.6	1418.2	1416.8	1415.3
142.5°	1454.7	1457.1	1457.5	1456.1	1454.6	1453.3	1451.9
145°	1506.2	1508.2	1508.5	1507.1	1505.7	1504.2	1502.9
147.5°	1550.9	1552.4	1552.5	1551.3	1550.2	1548.9	1547.7
150°	1579.0	1580.6	1580.7	1579.4	1578.0	1576.5	1575.1
152.5°	1604.3	1606.0	1605.9	1604.0	1602.2	1600.4	1598.5
155°	1638.5	1640.2	1639.9	1637.7	1635.5	1633.2	1630.9
157.5°	1667.6	1669.6	1669.4	1667.2	1665.0	1662.8	1660.6
160°	1684.2	1685.9	1685.8	1683.8	1681.8	1679.8	1677.8
162.5°	1700.1	1702.0	1701.7	1699.3	1696.9	1694.5	1692.1
165°	1719.3	1721.3	1721.3	1719.3	1717.3	1715.4	1713.3
167.5°	1735.3	1737.2	1737.0	1734.5	1731.9	1729.4	1726.8
170°	1743.4	1745.3	1745.1	1742.6	1740.0	1737.5	1734.9
172.5°	1749.4	1751.4	1751.1	1748.6	1746.1	1743.6	1741.0
175°	1756.0	1758.0	1757.7	1754.8	1751.9	1749.2	1746.3
177.5°	1756.4	1758.0	1757.7	1755.7	1753.7	1751.7	1749.6
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7

(END OF REPORT)