

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331787-940

Luminaire Tested: **S122RDIW-S485D435U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331787-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D435U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3058.4 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331787-940

CATALOG NUMBER: S122RDIW-S485D435U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331787-940

CATALOG NUMBER: S122RDIW-S485D435U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43
2	90	83	77	72	83	76	71	67	65	61	58	54	52	49	45	43	41	36
3	82	73	66	60	76	68	62	57	58	53	49	48	45	42	40	38	36	31
4	75	65	57	51	69	60	54	48	52	47	42	44	40	37	36	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	39	59	49	42	37	42	37	32	36	32	28	30	27	24	21
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22	19
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	51	39	32	27	48	37	30	26	32	27	23	28	23	20	23	20	18	16
10	48	36	29	25	44	34	28	23	30	25	21	26	22	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11880	11880	11880
5°	11925	11733	11797
10°	11835	11540	11442
15°	11699	11198	10877
20°	11510	10710	10172
25°	11318	10156	9492
30°	11050	9587	8617
35°	10789	8966	7849
40°	10526	8323	6962
45°	10218	7604	6158
50°	9902	6875	5368
55°	9579	6092	4611
60°	9203	5270	3827
65°	8779	4424	3484
70°	8266	3644	3205
75°	7642	3319	2994
80°	6750	2966	2724
85°	5298	2353	2353



TEST NUMBER: P331787-940

CATALOG NUMBER: S122RDIW-S485D435U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.9	2.3
10°-20°	189.1	6.2
20°-30°	265.6	8.7
30°-40°	289.6	9.5
40°-50°	266.3	8.7
50°-60°	209.1	6.8
60°-70°	136.4	4.5
70°-80°	70.3	2.3
80°-90°	19.5	0.6
90°-100°	17.6	0.6
100°-110°	64.4	2.1
110°-120°	172.2	5.6
120°-130°	284.3	9.3
130°-140°	302.4	9.9
140°-150°	281.0	9.2
150°-160°	225.9	7.4
160°-170°	145.6	4.8
170°-180°	50.1	1.6
0°-30°	523.6	17.1
0°-40°	813.2	26.6
0°-60°	1288.6	42.1
0°-90°	1514.8	49.5
90°-120°	254.2	8.3
90°-150°	1121.9	36.7
90°-180°	1544.0	50.5
0°-180°	3058.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	736	736	736	736	736	
5°	736	732	724	729	728	70
15°	700	692	670	658	651	197
25°	635	613	570	544	533	292
35°	547	512	455	414	398	342
45°	448	402	333	287	270	345
55°	340	287	216	178	164	304
65°	230	176	116	94	91	228
75°	122	77	53	49	48	130
85°	29	15	13	13	13	34
90°	0	4	8	9	10	2
95°	25	13	15	17	16	30
105°	116	121	23	27	29	124
115°	219	226	235	67	31	216
125°	310	315	322	325	326	276
135°	383	389	393	396	396	296
145°	445	445	451	453	452	278
155°	490	487	491	493	490	226
165°	516	514	515	517	515	146
175°	528	525	526	528	525	50
180°	527	527	527	527	527	



TEST NUMBER: P331787-940

CATALOG NUMBER: S122RDIW-S485D435U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	738.5	738.0	737.4	736.7	736.2	735.2	734.0	732.6	731.3	730.0	731.2
5°	735.8	735.1	734.4	733.7	732.9	731.6	729.7	727.7	725.9	723.9	725.2
7.5°	728.3	727.4	726.5	725.5	724.6	723.0	720.8	718.5	716.3	714.1	714.4
10°	721.9	720.9	719.8	718.8	717.7	715.8	712.8	709.8	706.9	703.9	703.5
12.5°	713.9	712.7	711.3	710.1	708.8	706.3	702.5	698.7	694.9	691.2	690.4
15°	699.9	698.3	696.7	695.0	693.4	690.1	685.0	680.0	675.0	669.9	667.2
17.5°	682.8	680.3	677.8	675.3	672.8	668.3	661.9	655.4	649.0	642.5	639.2
20°	669.9	667.0	664.1	661.1	658.1	652.9	645.5	638.1	630.7	623.3	619.6
22.5°	656.1	652.8	649.4	646.1	642.8	637.0	628.7	620.3	612.0	603.6	598.9
25°	635.3	630.6	625.9	621.1	616.4	609.1	599.3	589.6	579.8	570.1	564.0
27.5°	610.3	605.1	599.9	594.9	589.7	581.6	570.6	559.5	548.6	537.5	530.5
30°	592.7	587.1	581.5	575.9	570.2	561.5	549.7	537.8	525.9	514.2	506.6
32.5°	575.7	569.1	562.5	556.0	549.4	540.0	528.0	515.9	503.8	491.8	483.1
35°	547.4	539.8	532.4	524.8	517.2	506.9	493.9	480.9	467.9	454.9	445.5
37.5°	519.2	510.9	502.6	494.3	486.1	474.9	461.1	447.2	433.3	419.5	409.1
40°	499.4	490.6	481.7	472.9	464.0	452.4	438.0	423.7	409.3	394.9	384.4
42.5°	479.2	469.8	460.5	451.2	441.8	429.7	414.9	400.0	385.2	370.4	359.5
45°	447.5	437.7	427.7	417.8	407.9	395.1	379.6	364.1	348.5	333.0	322.4
47.5°	416.6	406.1	395.7	385.1	374.6	361.3	345.3	329.2	313.2	297.1	286.7
50°	394.2	383.7	373.3	362.7	352.2	338.9	322.5	306.3	290.0	273.7	263.5
52.5°	372.4	361.4	350.4	339.5	328.5	315.0	299.1	283.2	267.2	251.4	241.5
55°	340.3	328.8	317.2	305.7	294.2	280.4	264.4	248.4	232.4	216.4	207.6
57.5°	307.4	295.6	283.7	271.9	260.0	246.5	231.1	215.7	200.4	185.0	176.8
60°	285.0	273.2	261.4	249.5	237.6	224.2	208.9	193.7	178.4	163.2	155.6
62.5°	263.1	251.4	239.5	227.7	215.8	202.7	188.2	173.6	159.1	144.5	137.3
65°	229.8	217.8	205.8	193.8	181.8	169.2	155.9	142.5	129.2	115.8	110.8
67.5°	197.5	185.7	173.7	161.8	149.9	137.9	126.0	114.0	102.0	90.1	87.7
70°	175.1	163.6	152.0	140.5	128.9	118.1	107.9	97.6	87.5	77.2	75.8
72.5°	153.8	142.8	131.7	120.6	109.6	100.0	91.8	83.6	75.3	67.1	65.9
75°	122.5	112.2	101.8	91.5	81.1	73.4	68.4	63.3	58.3	53.2	52.3
77.5°	91.8	82.7	73.6	64.5	55.5	49.7	47.3	44.9	42.4	39.9	39.3
80°	72.6	65.0	57.5	49.9	42.4	37.9	36.4	35.0	33.4	31.9	31.4
82.5°	55.0	49.1	43.2	37.4	31.5	28.0	27.0	25.9	25.0	24.0	23.6
85°	28.6	25.5	22.4	19.4	16.2	14.4	14.0	13.6	13.1	12.7	12.7
87.5°	8.6	7.8	7.0	6.3	5.5	5.3	5.4	5.5	5.6	5.8	5.8
90°	0.4	1.3	2.2	3.2	4.1	4.9	5.6	6.2	7.0	7.6	8.0
92.5°	7.7	7.6	7.5	7.4	7.4	7.5	7.8	8.2	8.5	8.8	9.1
95°	24.8	21.9	19.2	16.4	13.6	12.5	13.1	13.6	14.3	14.9	15.2
97.5°	49.1	41.3	33.4	25.5	17.7	14.4	15.8	17.1	18.5	19.9	20.2
100°	67.5	55.8	44.2	32.6	21.0	16.0	17.4	18.8	20.2	21.8	22.4
102.5°	87.6	85.2	82.7	80.3	77.8	70.5	58.5	46.5	34.4	22.3	23.2
105°	115.8	118.4	120.9	123.5	126.0	115.7	92.6	69.5	46.4	23.3	24.2
107.5°	148.1	150.2	152.2	154.3	156.3	143.5	115.7	88.0	60.3	32.5	31.6
110°	168.8	170.6	172.4	174.2	175.9	164.6	140.1	115.7	91.1	66.7	58.2



TEST NUMBER: P331787-940

CATALOG NUMBER: S122RDIW-S485D435U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.3	189.9	191.5	193.1	194.7	192.4	186.4	180.3	174.2	168.3	137.3
115°	219.2	220.6	222.0	223.5	224.9	226.7	228.8	231.0	233.0	235.1	195.9
117.5°	246.6	248.3	249.9	251.5	253.1	254.7	256.1	257.5	259.0	260.5	251.0
120°	266.8	268.0	269.3	270.6	271.9	273.3	274.8	276.3	277.9	279.4	280.4
122.5°	283.8	285.2	286.5	287.8	289.2	290.7	292.4	294.0	295.7	297.4	298.0
125°	309.9	310.9	312.1	313.2	314.2	315.6	317.3	318.9	320.5	322.1	322.6
127.5°	333.4	334.7	335.8	337.1	338.3	339.5	340.7	341.9	343.1	344.3	345.2
130°	348.4	349.7	351.1	352.4	353.7	354.9	355.9	356.8	357.8	358.6	359.5
132.5°	363.6	364.7	365.9	367.0	368.2	369.3	370.1	371.1	372.0	373.0	373.8
135°	383.4	384.8	386.1	387.4	388.9	389.9	390.7	391.5	392.2	393.0	393.8
137.5°	403.5	404.4	405.4	406.4	407.2	408.1	409.0	409.9	410.7	411.6	412.4
140°	416.6	417.2	417.9	418.6	419.3	420.1	421.1	422.0	422.8	423.8	424.5
142.5°	427.6	428.2	428.7	429.4	430.0	430.9	431.9	432.9	434.0	435.1	435.8
145°	444.8	444.7	444.6	444.5	444.4	445.1	446.6	448.0	449.4	450.8	451.5
147.5°	459.8	459.5	459.1	458.9	458.5	459.1	460.5	461.9	463.3	464.8	465.2
150°	469.6	469.0	468.3	467.8	467.2	467.5	469.0	470.3	471.6	473.0	473.5
152.5°	477.8	477.2	476.4	475.8	475.1	475.5	476.7	478.0	479.3	480.6	481.1
155°	489.7	489.0	488.2	487.5	486.7	486.9	487.9	488.8	489.9	490.9	491.4
157.5°	499.1	498.5	497.8	497.2	496.6	496.6	497.3	498.0	498.7	499.4	500.0
160°	504.6	504.1	503.6	503.1	502.6	502.6	503.1	503.6	504.1	504.6	505.2
162.5°	509.5	509.0	508.5	508.0	507.5	507.5	507.8	508.3	508.7	509.2	509.8
165°	516.0	515.6	515.1	514.5	514.0	513.9	514.2	514.4	514.7	514.9	515.5
167.5°	520.9	520.4	520.0	519.4	518.9	518.8	519.0	519.2	519.5	519.7	520.3
170°	523.7	523.2	522.6	522.2	521.7	521.5	521.7	521.8	522.0	522.2	522.7
172.5°	525.5	525.0	524.5	524.0	523.4	523.3	523.4	523.6	523.8	524.0	524.6
175°	527.9	527.3	526.6	526.1	525.5	525.3	525.5	525.7	525.8	525.9	526.6
177.5°	528.2	527.8	527.3	526.8	526.4	526.1	526.2	526.3	526.4	526.4	526.9
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331787-940

CATALOG NUMBER: S122RDIW-S485D435U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	732.4	733.6	734.8	735.2	735.0	734.8	734.5	734.3
5°	726.6	727.9	729.2	729.7	729.2	728.8	728.3	727.9
7.5°	714.8	715.2	715.6	715.4	714.6	713.8	713.1	712.3
10°	703.0	702.6	702.1	701.5	700.6	699.7	698.8	697.9
12.5°	689.6	688.8	688.0	686.8	685.3	683.9	682.3	680.9
15°	664.3	661.6	658.7	656.6	655.1	653.6	652.1	650.7
17.5°	635.8	632.5	629.1	626.2	623.7	621.1	618.6	616.0
20°	615.9	612.2	608.5	605.0	601.8	598.5	595.3	592.0
22.5°	594.1	589.3	584.6	580.9	578.5	576.1	573.7	571.2
25°	557.9	551.9	545.8	541.6	539.4	537.2	535.0	532.8
27.5°	523.4	516.3	509.3	504.0	500.4	497.0	493.4	489.9
30°	499.0	491.5	483.9	478.1	474.1	470.2	466.2	462.2
32.5°	474.5	465.9	457.3	451.1	447.4	443.6	439.8	436.0
35°	436.2	426.9	417.6	411.3	408.0	404.7	401.5	398.2
37.5°	398.9	388.6	378.4	371.3	367.7	363.9	360.2	356.4
40°	373.9	363.4	352.8	345.7	341.9	338.0	334.1	330.3
42.5°	348.7	337.8	327.0	319.7	315.9	312.2	308.4	304.7
45°	311.9	301.5	291.0	283.9	280.4	276.8	273.2	269.7
47.5°	276.3	265.8	255.4	248.5	245.3	242.1	238.8	235.6
50°	253.2	243.1	232.8	226.2	223.1	220.0	216.9	213.7
52.5°	231.6	221.8	211.9	205.5	202.7	199.8	196.9	194.0
55°	198.7	189.8	180.9	175.0	172.3	169.4	166.7	163.8
57.5°	168.7	160.6	152.5	147.2	144.8	142.5	140.1	137.7
60°	148.0	140.5	133.0	128.0	125.6	123.2	120.9	118.5
62.5°	130.1	123.0	115.7	111.5	110.0	108.6	107.2	105.8
65°	105.8	100.8	95.8	93.0	92.6	92.1	91.7	91.2
67.5°	85.4	83.1	80.8	79.5	78.9	78.5	78.0	77.5
70°	74.3	72.9	71.3	70.3	69.7	69.1	68.5	67.9
72.5°	64.6	63.4	62.2	61.3	61.0	60.6	60.3	59.9
75°	51.2	50.2	49.1	48.5	48.4	48.2	48.1	48.0
77.5°	38.8	38.2	37.6	37.2	36.9	36.7	36.5	36.2
80°	30.8	30.2	29.6	29.3	29.3	29.3	29.3	29.3
82.5°	23.3	22.9	22.6	22.4	22.4	22.4	22.4	22.4
85°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7
87.5°	5.7	5.7	5.6	5.6	5.7	5.7	5.8	5.8
90°	8.5	8.9	9.3	9.6	9.8	10.0	10.2	10.3
92.5°	9.3	9.5	9.7	9.9	10.0	10.1	10.2	10.3
95°	15.7	16.1	16.6	16.8	16.7	16.6	16.5	16.4
97.5°	20.6	21.0	21.2	21.5	21.6	21.7	21.8	21.8
100°	23.1	23.7	24.4	24.9	25.1	25.2	25.3	25.5
102.5°	24.1	25.0	25.9	26.4	26.7	26.9	27.1	27.4
105°	25.1	26.0	27.0	27.6	27.9	28.3	28.6	29.0
107.5°	30.7	29.7	28.7	28.4	28.8	29.2	29.4	29.8
110°	49.8	41.3	32.8	28.7	29.1	29.4	29.8	30.1



TEST NUMBER: P331787-940

CATALOG NUMBER: S122RDIW-S485D435U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	106.5	75.5	44.7	29.3	29.6	29.9	30.1	30.4
115°	156.8	117.5	78.3	55.6	49.6	43.4	37.4	31.2
117.5°	241.5	232.0	222.5	207.8	187.7	167.6	147.7	127.6
120°	281.4	282.4	283.5	278.2	266.8	255.4	243.9	232.5
122.5°	298.5	299.2	299.8	299.0	296.8	294.5	292.3	290.1
125°	323.2	323.9	324.4	324.9	325.1	325.4	325.7	325.8
127.5°	346.1	346.9	347.8	348.2	348.3	348.3	348.4	348.4
130°	360.5	361.4	362.4	362.8	362.7	362.7	362.6	362.5
132.5°	374.6	375.3	376.1	376.5	376.4	376.3	376.3	376.2
135°	394.7	395.5	396.4	396.6	396.5	396.4	396.2	396.0
137.5°	413.3	414.1	414.9	415.2	414.9	414.6	414.4	414.0
140°	425.3	426.1	426.9	427.0	426.6	426.1	425.8	425.3
142.5°	436.5	437.2	437.9	438.0	437.6	437.2	436.8	436.3
145°	452.1	452.6	453.3	453.3	452.9	452.5	452.1	451.7
147.5°	465.7	466.1	466.5	466.5	466.2	465.8	465.5	465.1
150°	474.0	474.5	475.0	475.1	474.7	474.2	473.8	473.4
152.5°	481.6	482.1	482.7	482.6	482.1	481.5	480.9	480.4
155°	492.0	492.4	492.9	492.8	492.1	491.5	490.8	490.2
157.5°	500.6	501.1	501.8	501.7	501.1	500.3	499.7	499.1
160°	505.6	506.1	506.7	506.6	506.0	505.4	504.8	504.3
162.5°	510.3	511.0	511.5	511.4	510.7	510.0	509.3	508.5
165°	516.1	516.7	517.3	517.3	516.7	516.1	515.5	514.9
167.5°	520.9	521.5	522.1	522.0	521.2	520.5	519.7	519.0
170°	523.3	524.0	524.5	524.4	523.7	522.9	522.2	521.4
172.5°	525.1	525.8	526.4	526.3	525.5	524.8	524.0	523.3
175°	527.2	527.7	528.3	528.2	527.4	526.6	525.7	524.9
177.5°	527.4	527.8	528.3	528.2	527.6	527.0	526.4	525.8
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7

(END OF REPORT)