

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331573-935

Luminaire Tested: **S122DIW-S865D1240U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331573-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1240U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7548.8 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43																				
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37																				
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37	32																				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28																				
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24																				
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25	21																				
6	63	51	43	38	58	47	41	35	40	35	31	33	29	26	27	24	22	19																				
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17																				
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18	15																				
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14																				
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	24001	24001	24001	24001
5°	26909	24159	21409	24159
10°	30836	23961	18528	23961
15°	34111	23520	16368	23520
20°	33593	23048	14921	23048
25°	30289	22422	14004	22422
30°	25031	21420	13336	21420
35°	18242	20371	12861	20371
40°	14570	19134	12596	19134
45°	12732	17701	12237	17701
50°	11969	16317	11997	16317
55°	11032	14908	11674	14908
60°	10111	13411	11179	13411
65°	9211	12069	10693	12069
70°	8360	10763	9980	10763
75°	7411	9301	8840	9301
80°	6369	7699	7113	7699
85°	5706	5706	4224	5706



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.6	1.9
10°-20°	411.6	5.5
20°-30°	597.3	7.9
30°-40°	630.3	8.4
40°-50°	558.1	7.4
50°-60°	445.4	5.9
60°-70°	302.7	4.0
70°-80°	155.2	2.1
80°-90°	41.0	0.5
90°-100°	48.6	0.6
100°-110°	178.1	2.4
110°-120°	476.0	6.3
120°-130°	785.7	10.4
130°-140°	835.5	11.1
140°-150°	776.6	10.3
150°-160°	624.4	8.3
160°-170°	402.3	5.3
170°-180°	138.5	1.8
0°-30°	1150.5	15.2
0°-40°	1780.8	23.6
0°-60°	2784.3	36.9
0°-90°	3283.2	43.5
90°-120°	702.6	9.3
90°-150°	3100.4	41.1
90°-180°	4266.0	56.5
0°-180°	7548.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1486	1486	1486	1486	1486	
5°	1660	1491	1321	1491	1660	166
15°	2041	1407	979	1407	2041	563
25°	1700	1259	786	1259	1700	768
35°	926	1034	652	1034	926	602
45°	558	775	536	775	558	438
55°	392	530	415	530	392	351
65°	241	316	280	316	241	240
75°	119	149	142	149	119	127
85°	31	31	23	31	31	34
90°	28	1	28	1	28	14
95°	45	68	45	68	45	42
105°	80	320	80	320	80	83
115°	86	606	86	606	86	216
125°	900	856	900	856	900	779
135°	1094	1060	1094	1060	1094	843
145°	1248	1229	1248	1229	1248	781
155°	1354	1353	1354	1353	1354	625
165°	1423	1426	1423	1426	1423	402
175°	1450	1459	1450	1459	1450	138
180°	1456	1456	1456	1456	1456	



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1555.1	1555.6	1556.5	1549.2	1548.3	1548.3	1541.9	1536.4	1530.0	1521.3	1522.2
5°	1660.3	1666.6	1668.8	1662.0	1651.7	1650.5	1640.8	1624.8	1610.0	1597.9	1589.4
7.5°	1785.7	1788.2	1782.6	1773.6	1765.9	1752.2	1734.1	1716.5	1691.7	1669.0	1652.0
10°	1880.8	1884.2	1874.5	1861.3	1850.5	1834.4	1808.2	1781.3	1748.8	1717.4	1692.2
12.5°	1953.0	1961.4	1949.0	1947.2	1928.6	1906.7	1875.4	1861.8	1816.0	1772.2	1745.2
15°	2040.7	2040.1	2041.3	2030.4	2016.7	2013.3	1980.2	1944.2	1879.6	1853.9	1809.4
17.5°	2015.3	2024.0	2028.1	2027.9	2027.6	2025.4	2014.8	1992.1	1959.7	1918.0	1866.6
20°	1955.1	1966.4	1968.2	1981.3	1988.7	1998.5	2002.4	1996.1	1976.2	1941.3	1896.8
22.5°	1861.8	1865.0	1870.4	1890.8	1906.9	1931.3	1944.0	1965.1	1957.4	1940.4	1903.2
25°	1700.2	1694.5	1714.5	1724.8	1762.0	1800.8	1828.8	1859.6	1887.1	1903.6	1892.7
27.5°	1506.2	1497.6	1527.6	1554.9	1585.0	1627.1	1670.8	1722.3	1765.1	1818.7	1837.1
30°	1342.6	1347.7	1376.3	1405.4	1451.1	1510.5	1559.7	1616.3	1677.4	1737.3	1779.1
32.5°	1166.1	1185.9	1204.0	1248.6	1288.9	1355.1	1427.1	1497.9	1574.1	1642.3	1706.8
35°	925.5	948.4	973.5	1006.1	1062.6	1128.3	1198.6	1294.0	1398.0	1491.2	1567.7
37.5°	779.0	775.4	789.8	813.3	859.1	912.1	993.1	1087.4	1209.7	1319.1	1427.1
40°	691.3	689.0	699.3	721.0	755.9	794.7	865.6	948.4	1062.0	1195.8	1324.3
42.5°	630.9	632.3	638.0	653.3	677.3	709.2	762.2	832.8	936.9	1062.7	1200.9
45°	557.6	561.6	567.9	575.3	589.0	615.3	645.0	695.3	777.6	882.7	1018.6
47.5°	504.8	504.9	511.3	517.8	526.0	540.8	565.0	596.6	654.6	740.2	857.1
50°	476.5	472.5	477.1	482.2	490.8	501.0	517.0	546.7	585.6	654.7	752.4
52.5°	441.8	441.9	446.0	447.9	455.6	465.9	480.4	501.0	536.2	590.3	670.6
55°	391.9	394.8	397.1	400.5	407.3	414.7	426.2	439.9	467.4	507.9	567.3
57.5°	345.1	345.9	348.3	354.8	359.1	366.0	376.9	389.3	407.1	437.1	481.8
60°	313.1	313.1	317.6	320.5	326.2	333.0	341.6	353.6	369.6	394.2	430.2
62.5°	283.9	283.4	285.2	289.9	294.2	300.7	309.2	319.3	334.4	356.3	385.9
65°	241.1	240.0	243.4	244.5	249.1	255.4	262.3	273.1	285.1	301.1	327.4
67.5°	199.9	201.3	203.2	205.3	207.8	214.5	219.0	226.7	236.9	250.1	267.9
70°	177.1	177.1	177.1	178.8	182.3	185.7	190.3	196.6	206.2	217.7	233.7
72.5°	151.5	153.3	155.2	154.1	158.5	160.6	166.0	169.5	178.8	186.1	200.3
75°	118.8	118.8	118.8	121.7	123.4	125.1	128.5	132.0	136.6	145.7	153.1
77.5°	88.7	88.4	89.0	89.7	91.5	93.6	94.6	97.7	101.9	106.2	112.4
80°	68.5	69.7	70.3	71.4	71.4	72.6	73.1	77.1	80.0	82.8	86.9
82.5°	53.0	53.2	53.4	53.6	54.1	54.8	56.2	57.5	58.5	60.9	64.0
85°	30.8	30.3	30.3	31.4	30.8	30.8	32.0	33.1	33.1	33.7	35.4
87.5°	17.6	17.5	17.8	17.3	17.2	17.5	17.2	16.5	16.8	17.0	17.1
90°	28.4	28.0	27.5	27.0	26.6	25.7	24.5	23.4	22.2	21.1	19.2
92.5°	28.4	28.2	27.9	27.6	27.3	26.9	26.3	25.7	25.1	24.5	23.5
95°	45.3	45.5	45.7	46.0	46.2	45.7	44.6	43.4	42.3	41.1	39.4
97.5°	60.4	60.2	59.9	59.6	59.3	58.7	57.8	56.8	55.9	55.0	51.2
100°	70.6	70.1	69.7	69.1	68.7	67.5	65.6	63.8	61.9	60.0	56.1
102.5°	75.6	75.0	74.3	73.6	73.0	71.5	69.1	66.6	64.1	61.7	59.0
105°	80.1	79.1	78.2	77.2	76.3	74.6	72.0	69.4	66.8	64.2	61.1
107.5°	82.4	81.5	80.5	79.6	78.6	79.5	82.1	84.7	87.3	90.0	92.1
110°	83.2	82.3	81.4	80.4	79.5	90.7	114.1	137.5	160.9	184.3	251.9



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.0	83.3	82.6	81.8	81.0	123.4	208.8	294.1	379.5	464.9	481.6
115°	86.4	103.2	120.1	136.9	153.8	216.4	324.8	433.1	541.5	649.9	644.0
117.5°	352.6	408.0	463.4	518.8	574.1	614.9	641.1	667.4	693.5	719.8	715.7
120°	642.5	674.1	705.7	737.3	768.9	783.3	780.4	777.7	774.8	772.0	767.8
122.5°	801.7	807.9	814.0	820.1	826.2	828.5	826.8	825.1	823.4	821.7	817.2
125°	900.5	899.8	899.1	898.4	897.7	896.6	894.9	893.3	891.7	890.0	885.5
127.5°	962.9	962.7	962.6	962.4	962.3	961.0	958.6	956.2	953.9	951.5	948.1
130°	1001.6	1001.9	1002.1	1002.3	1002.5	1001.3	998.8	996.3	993.7	991.1	988.5
132.5°	1039.6	1039.7	1040.0	1040.3	1040.4	1039.5	1037.2	1035.1	1032.9	1030.7	1028.1
135°	1094.3	1094.8	1095.3	1095.7	1096.1	1095.3	1092.9	1090.5	1088.2	1085.9	1083.7
137.5°	1144.2	1145.0	1145.8	1146.6	1147.4	1146.7	1144.4	1142.0	1139.8	1137.5	1135.1
140°	1175.4	1176.6	1177.8	1178.9	1180.1	1179.7	1177.5	1175.4	1173.3	1171.2	1168.6
142.5°	1205.7	1206.9	1208.1	1209.3	1210.4	1210.0	1208.2	1206.2	1204.3	1202.4	1199.4
145°	1248.1	1249.2	1250.4	1251.5	1252.8	1252.5	1250.9	1249.2	1247.6	1246.0	1242.0
147.5°	1285.4	1286.3	1287.3	1288.3	1289.3	1289.2	1288.0	1286.8	1285.6	1284.3	1280.4
150°	1308.1	1309.2	1310.4	1311.6	1312.8	1312.7	1311.3	1309.8	1308.5	1307.1	1303.3
152.5°	1327.5	1329.0	1330.6	1332.1	1333.7	1333.8	1332.3	1330.9	1329.6	1328.1	1324.6
155°	1354.4	1356.3	1358.2	1360.0	1361.9	1362.2	1360.8	1359.3	1358.0	1356.6	1353.8
157.5°	1379.1	1381.0	1382.8	1384.6	1386.4	1386.6	1384.9	1383.4	1381.7	1380.2	1378.2
160°	1393.4	1395.1	1396.7	1398.4	1400.0	1400.1	1398.7	1397.3	1395.9	1394.5	1393.1
162.5°	1405.2	1407.2	1409.2	1411.3	1413.2	1413.5	1411.9	1410.3	1408.7	1407.1	1405.9
165°	1422.9	1424.5	1426.2	1427.8	1429.4	1429.4	1427.8	1426.2	1424.5	1422.9	1422.2
167.5°	1434.1	1436.1	1438.3	1440.4	1442.5	1442.7	1441.1	1439.4	1437.8	1436.1	1435.5
170°	1440.8	1442.9	1445.0	1447.2	1449.2	1449.5	1447.9	1446.2	1444.6	1442.9	1442.4
172.5°	1445.9	1447.9	1450.1	1452.2	1454.3	1454.5	1452.9	1451.2	1449.6	1447.9	1447.5
175°	1450.3	1452.6	1455.0	1457.3	1459.7	1460.0	1458.4	1456.7	1455.1	1453.5	1453.0
177.5°	1453.0	1454.7	1456.4	1458.1	1459.7	1460.0	1458.6	1457.3	1456.0	1454.7	1454.5
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1525.4	1521.7	1519.5	1511.2	1503.9	1496.6	1494.4	1495.2	1485.2	1475.6	1471.4
5°	1584.8	1573.4	1562.5	1547.1	1528.9	1508.8	1498.6	1490.6	1470.6	1448.9	1436.3
7.5°	1638.1	1621.7	1600.9	1571.8	1545.2	1513.7	1493.7	1476.0	1446.8	1416.2	1397.4
10°	1670.5	1648.2	1621.3	1586.0	1553.4	1515.1	1488.2	1461.5	1427.1	1390.6	1367.7
12.5°	1698.4	1668.4	1641.9	1596.5	1558.0	1510.1	1478.3	1440.4	1404.3	1360.9	1338.5
15°	1764.8	1709.3	1659.1	1607.7	1560.2	1493.4	1458.0	1407.1	1359.7	1306.1	1280.3
17.5°	1816.1	1753.9	1674.6	1609.3	1553.9	1480.0	1428.0	1367.0	1311.0	1249.6	1214.6
20°	1845.4	1773.9	1688.8	1611.1	1544.8	1460.3	1403.7	1341.4	1275.7	1206.6	1168.9
22.5°	1862.7	1787.6	1703.4	1604.2	1526.6	1444.2	1373.1	1304.8	1238.3	1163.6	1124.1
25°	1868.2	1799.7	1710.5	1598.5	1503.7	1410.6	1324.9	1258.6	1178.0	1108.4	1050.7
27.5°	1841.0	1791.8	1706.2	1587.8	1477.3	1368.4	1272.9	1197.8	1112.8	1037.2	979.1
30°	1807.7	1779.1	1695.7	1576.8	1456.3	1339.2	1234.1	1148.9	1064.4	987.8	928.4
32.5°	1756.0	1749.8	1676.5	1561.3	1433.9	1302.2	1193.3	1107.3	1013.7	938.4	881.8
35°	1654.5	1682.0	1635.6	1526.6	1391.7	1249.5	1131.8	1033.5	936.4	864.4	811.2
37.5°	1518.5	1586.7	1574.5	1475.7	1334.8	1192.1	1062.2	959.5	866.9	794.3	742.1
40°	1424.9	1511.7	1524.2	1436.8	1294.6	1147.8	1010.1	907.8	817.5	751.3	698.7
42.5°	1324.3	1425.7	1460.3	1390.3	1250.7	1101.1	963.5	857.6	768.2	703.8	657.1
45°	1155.8	1290.0	1352.3	1312.3	1177.5	1024.3	882.7	775.2	694.1	633.6	597.6
47.5°	998.2	1144.9	1228.6	1214.5	1096.0	944.3	804.3	701.2	622.2	573.9	541.7
50°	886.7	1037.5	1138.6	1143.2	1037.5	887.3	746.7	649.6	577.0	531.9	505.6
52.5°	789.8	933.8	1044.0	1068.2	972.2	827.9	695.1	598.4	534.5	493.0	469.5
55°	663.3	785.0	907.2	951.8	874.7	737.5	614.8	529.6	469.6	441.1	420.5
57.5°	551.5	652.9	765.8	815.0	767.5	650.1	534.9	461.1	412.3	387.4	371.6
60°	492.5	572.5	673.0	731.8	690.7	586.2	485.6	415.3	375.4	353.1	338.2
62.5°	437.6	508.5	593.5	647.3	624.9	526.3	436.3	374.2	339.7	318.8	308.1
65°	361.1	417.1	482.8	532.4	517.6	442.7	369.1	315.9	288.5	271.9	263.4
67.5°	297.3	337.8	383.3	426.9	414.9	361.9	302.6	261.3	240.9	226.6	221.4
70°	257.1	287.9	328.5	363.3	353.6	310.2	263.4	228.0	210.3	198.3	193.1
72.5°	218.7	244.1	275.0	303.5	297.0	260.9	221.8	195.0	181.4	170.4	166.2
75°	165.1	184.5	203.4	222.2	220.5	192.5	169.7	149.1	138.3	129.7	127.9
77.5°	121.9	132.8	145.6	156.8	153.7	137.7	119.8	108.0	100.0	94.3	93.3
80°	93.2	99.4	108.6	116.6	112.5	105.7	91.4	82.8	77.1	71.4	69.1
82.5°	67.5	73.8	79.3	83.6	80.6	74.1	65.3	59.5	56.1	52.2	51.3
85°	35.4	38.8	41.2	42.3	41.2	37.1	33.1	30.8	28.0	26.3	25.7
87.5°	17.1	16.8	16.4	16.9	15.0	14.5	12.1	10.2	10.3	10.4	10.0
90°	17.3	15.4	13.6	11.4	8.8	6.2	3.6	1.0	3.6	6.2	8.8
92.5°	22.6	21.6	20.7	20.3	20.6	20.8	21.0	21.3	21.0	20.8	20.6
95°	37.8	36.2	34.5	37.5	45.3	53.0	60.7	68.4	60.7	53.0	45.3
97.5°	47.4	43.6	39.8	48.8	70.6	92.3	114.1	135.9	114.1	92.3	70.6
100°	52.1	48.1	44.1	58.2	90.2	122.3	154.4	186.4	154.4	122.3	90.2
102.5°	128.3	161.5	194.8	214.9	221.7	228.4	235.2	242.0	235.2	228.4	221.7
105°	192.0	256.0	319.9	348.3	341.2	334.2	327.2	320.2	327.2	334.2	341.2
107.5°	243.2	319.9	396.5	432.0	426.3	420.6	414.9	409.3	414.9	420.6	426.3
110°	319.6	387.3	454.9	486.2	481.3	476.4	471.5	466.6	471.5	476.4	481.3



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	498.3	515.1	531.8	538.0	533.6	529.2	524.9	520.5	524.9	529.2	533.6
115°	638.2	632.3	626.5	621.6	617.5	613.5	609.6	605.6	609.6	613.5	617.5
117.5°	711.7	707.7	703.7	699.5	695.0	690.5	686.1	681.7	686.1	690.5	695.0
120°	763.6	759.4	755.2	751.3	747.8	744.2	740.8	737.3	740.8	744.2	747.8
122.5°	812.5	808.0	803.4	799.3	795.6	791.9	788.2	784.5	788.2	791.9	795.6
125°	881.1	876.7	872.2	868.4	865.4	862.4	859.3	856.3	859.3	862.4	865.4
127.5°	944.9	941.5	938.2	934.9	931.5	928.1	924.7	921.4	924.7	928.1	931.5
130°	985.9	983.3	980.8	977.7	973.9	970.2	966.4	962.7	966.4	970.2	973.9
132.5°	1025.5	1023.0	1020.4	1017.5	1014.3	1011.2	1008.0	1004.8	1008.0	1011.2	1014.3
135°	1081.7	1079.5	1077.5	1074.5	1070.7	1067.0	1063.2	1059.5	1063.2	1067.0	1070.7
137.5°	1132.7	1130.3	1127.9	1125.4	1122.8	1120.2	1117.6	1114.9	1117.6	1120.2	1122.8
140°	1166.1	1163.5	1160.9	1158.6	1156.8	1154.9	1153.1	1151.2	1153.1	1154.9	1156.8
142.5°	1196.4	1193.5	1190.6	1188.3	1186.5	1184.9	1183.2	1181.6	1183.2	1184.9	1186.5
145°	1238.0	1234.1	1230.0	1228.2	1228.4	1228.6	1228.9	1229.1	1228.9	1228.6	1228.4
147.5°	1276.4	1272.5	1268.6	1267.0	1267.9	1268.9	1269.7	1270.6	1269.7	1268.9	1267.9
150°	1299.6	1295.8	1292.1	1291.0	1292.6	1294.3	1296.0	1297.6	1296.0	1294.3	1292.6
152.5°	1321.0	1317.4	1313.9	1313.0	1314.8	1316.6	1318.5	1320.3	1318.5	1316.6	1314.8
155°	1350.9	1348.2	1345.3	1345.0	1347.0	1349.2	1351.3	1353.4	1351.3	1349.2	1347.0
157.5°	1376.2	1374.2	1372.3	1372.2	1374.0	1375.7	1377.5	1379.3	1377.5	1375.7	1374.0
160°	1391.6	1390.3	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5	1393.1	1391.6	1390.3
162.5°	1404.6	1403.4	1402.2	1402.3	1403.8	1405.2	1406.5	1408.0	1406.5	1405.2	1403.8
165°	1421.5	1420.8	1420.1	1420.5	1421.9	1423.2	1424.7	1426.1	1424.7	1423.2	1421.9
167.5°	1434.9	1434.3	1433.6	1433.9	1435.4	1436.8	1438.1	1439.6	1438.1	1436.8	1435.4
170°	1442.0	1441.5	1441.1	1441.5	1442.9	1444.3	1445.7	1447.2	1445.7	1444.3	1442.9
172.5°	1447.0	1446.6	1446.1	1446.6	1447.9	1449.4	1450.8	1452.2	1450.8	1449.4	1447.9
175°	1452.5	1452.1	1451.6	1452.2	1453.8	1455.4	1457.1	1458.7	1457.1	1455.4	1453.8
177.5°	1454.3	1454.1	1454.0	1454.5	1455.9	1457.2	1458.4	1459.7	1458.4	1457.2	1455.9
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1466.9	1464.1	1454.6	1449.6	1441.3	1433.6	1428.5	1430.8	1432.6	1431.7	1430.4
5°	1424.9	1414.0	1397.4	1383.1	1372.9	1354.0	1346.0	1342.0	1338.6	1334.6	1330.6
7.5°	1374.8	1357.7	1333.9	1313.5	1294.3	1270.9	1257.6	1249.6	1241.4	1232.3	1224.3
10°	1339.2	1315.2	1290.0	1261.5	1238.6	1217.5	1198.6	1186.0	1174.7	1163.7	1155.8
12.5°	1301.7	1274.0	1242.9	1203.9	1178.7	1148.5	1145.6	1123.4	1105.6	1098.9	1089.5
15°	1242.1	1203.2	1163.7	1117.5	1097.5	1070.1	1052.9	1035.8	1020.4	1009.5	1006.7
17.5°	1174.3	1124.0	1084.8	1051.5	1018.7	990.7	974.9	961.2	948.5	934.0	932.0
20°	1122.7	1079.2	1036.4	1007.2	973.5	944.9	925.5	911.8	901.0	892.4	884.9
22.5°	1073.8	1026.2	987.0	955.1	921.9	898.8	883.5	870.2	861.2	851.7	844.7
25°	995.2	958.1	915.2	879.3	851.8	837.0	824.4	813.0	807.3	801.0	793.0
27.5°	926.5	885.3	845.2	817.3	793.2	780.1	771.2	763.4	758.0	754.3	749.8
30°	878.1	836.4	804.9	777.6	757.6	744.4	738.7	734.2	727.9	725.6	723.3
32.5°	831.5	793.9	767.1	743.3	724.2	715.7	710.4	706.3	701.4	699.0	694.5
35°	765.6	734.2	707.8	694.7	679.3	671.8	667.9	662.2	657.5	655.3	654.7
37.5°	703.5	676.2	658.9	642.0	635.5	630.9	625.5	621.6	620.2	619.8	619.3
40°	663.3	641.0	625.6	611.9	609.0	602.2	597.6	594.2	594.2	594.8	594.2
42.5°	626.7	606.7	593.1	581.3	577.9	573.9	569.3	569.0	570.0	571.9	570.0
45°	571.3	557.1	547.3	541.6	535.3	531.3	530.7	532.4	533.0	533.6	535.3
47.5°	520.4	510.8	502.0	495.8	493.0	492.3	491.6	494.6	497.4	498.4	501.0
50°	490.2	479.3	471.9	467.9	465.6	464.5	465.6	469.1	471.3	474.2	475.9
52.5°	456.3	448.7	443.6	440.5	439.5	440.2	440.5	444.4	448.1	449.0	449.9
55°	409.7	403.9	402.8	397.6	399.9	399.3	402.2	404.5	407.9	411.4	411.9
57.5°	363.0	358.4	355.3	355.9	356.5	359.0	361.4	365.4	369.1	372.7	373.1
60°	331.9	329.7	328.0	328.0	329.1	332.5	335.4	339.3	341.6	344.0	345.6
62.5°	303.6	301.4	299.6	300.5	303.5	305.6	308.8	311.0	313.3	315.6	316.4
65°	258.8	257.7	259.4	260.5	261.1	264.0	267.9	269.7	271.9	273.1	277.1
67.5°	217.6	217.7	217.6	219.1	222.5	223.2	227.0	230.9	231.4	233.6	236.2
70°	189.7	190.8	192.0	193.1	196.0	197.1	199.9	201.6	204.0	205.7	207.4
72.5°	164.1	164.3	165.5	165.2	167.6	170.1	172.5	174.3	176.5	178.7	180.4
75°	126.2	126.2	127.4	127.9	130.9	133.7	133.1	134.2	136.6	138.8	140.0
77.5°	92.2	90.9	92.2	92.8	93.7	96.1	96.5	98.2	100.7	100.0	101.3
80°	70.3	68.5	70.3	70.9	70.9	73.7	73.7	74.8	76.5	74.8	76.5
82.5°	50.2	49.3	50.6	50.7	51.7	51.7	52.7	52.9	54.6	53.8	54.6
85°	25.1	24.5	25.1	24.5	25.1	25.7	25.7	25.1	25.1	26.3	24.5
87.5°	10.1	10.0	10.0	10.3	10.2	10.2	9.9	10.2	10.4	9.7	9.9
90°	11.4	13.6	15.4	17.3	19.2	21.1	22.2	23.4	24.5	25.7	26.6
92.5°	20.3	20.7	21.6	22.6	23.5	24.5	25.1	25.7	26.3	26.9	27.3
95°	37.5	34.5	36.2	37.8	39.4	41.1	42.3	43.4	44.6	45.7	46.2
97.5°	48.8	39.8	43.6	47.4	51.2	55.0	55.9	56.8	57.8	58.7	59.3
100°	58.2	44.1	48.1	52.1	56.1	60.0	61.9	63.8	65.6	67.5	68.7
102.5°	214.9	194.8	161.5	128.3	95.0	61.7	64.1	66.6	69.1	71.5	73.0
105°	348.3	319.9	256.0	192.0	128.1	64.2	66.8	69.4	72.0	74.6	76.3
107.5°	432.0	396.5	319.9	243.2	166.6	90.0	87.3	84.7	82.1	79.5	78.6
110°	486.2	454.9	387.3	319.6	251.9	184.3	160.9	137.5	114.1	90.7	79.5



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	538.0	531.8	515.1	498.3	481.6	464.9	379.5	294.1	208.8	123.4	81.0
115°	621.6	626.5	632.3	638.2	644.0	649.9	541.5	433.1	324.8	216.4	153.8
117.5°	699.5	703.7	707.7	711.7	715.7	719.8	693.5	667.4	641.1	614.9	574.1
120°	751.3	755.2	759.4	763.6	767.8	772.0	774.8	777.7	780.4	783.3	768.9
122.5°	799.3	803.4	808.0	812.5	817.2	821.7	823.4	825.1	826.8	828.5	826.2
125°	868.4	872.2	876.7	881.1	885.5	890.0	891.7	893.3	894.9	896.6	897.7
127.5°	934.9	938.2	941.5	944.9	948.1	951.5	953.9	956.2	958.6	961.0	962.3
130°	977.7	980.8	983.3	985.9	988.5	991.1	993.7	996.3	998.8	1001.3	1002.5
132.5°	1017.5	1020.4	1023.0	1025.5	1028.1	1030.7	1032.9	1035.1	1037.2	1039.5	1040.4
135°	1074.5	1077.5	1079.5	1081.7	1083.7	1085.9	1088.2	1090.5	1092.9	1095.3	1096.1
137.5°	1125.4	1127.9	1130.3	1132.7	1135.1	1137.5	1139.8	1142.0	1144.4	1146.7	1147.4
140°	1158.6	1160.9	1163.5	1166.1	1168.6	1171.2	1173.3	1175.4	1177.5	1179.7	1180.1
142.5°	1188.3	1190.6	1193.5	1196.4	1199.4	1202.4	1204.3	1206.2	1208.2	1210.0	1210.4
145°	1228.2	1230.0	1234.1	1238.0	1242.0	1246.0	1247.6	1249.2	1250.9	1252.5	1252.8
147.5°	1267.0	1268.6	1272.5	1276.4	1280.4	1284.3	1285.6	1286.8	1288.0	1289.2	1289.3
150°	1291.0	1292.1	1295.8	1299.6	1303.3	1307.1	1308.5	1309.8	1311.3	1312.7	1312.8
152.5°	1313.0	1313.9	1317.4	1321.0	1324.6	1328.1	1329.6	1330.9	1332.3	1333.8	1333.7
155°	1345.0	1345.3	1348.2	1350.9	1353.8	1356.6	1358.0	1359.3	1360.8	1362.2	1361.9
157.5°	1372.2	1372.3	1374.2	1376.2	1378.2	1380.2	1381.7	1383.4	1384.9	1386.6	1386.4
160°	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5	1395.9	1397.3	1398.7	1400.1	1400.0
162.5°	1402.3	1402.2	1403.4	1404.6	1405.9	1407.1	1408.7	1410.3	1411.9	1413.5	1413.2
165°	1420.5	1420.1	1420.8	1421.5	1422.2	1422.9	1424.5	1426.2	1427.8	1429.4	1429.4
167.5°	1433.9	1433.6	1434.3	1434.9	1435.5	1436.1	1437.8	1439.4	1441.1	1442.7	1442.5
170°	1441.5	1441.1	1441.5	1442.0	1442.4	1442.9	1444.6	1446.2	1447.9	1449.5	1449.2
172.5°	1446.6	1446.1	1446.6	1447.0	1447.5	1447.9	1449.6	1451.2	1452.9	1454.5	1454.3
175°	1452.2	1451.6	1452.1	1452.5	1453.0	1453.5	1455.1	1456.7	1458.4	1460.0	1459.7
177.5°	1454.5	1454.0	1454.1	1454.3	1454.5	1454.7	1456.0	1457.3	1458.6	1460.0	1459.7
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1425.7	1424.9	1424.9	1420.7	1424.9	1424.9	1425.7	1430.4	1431.7	1432.6	1430.8
5°	1322.6	1320.9	1318.0	1320.9	1318.0	1320.9	1322.6	1330.6	1334.6	1338.6	1342.0
7.5°	1220.6	1213.7	1212.6	1205.9	1212.6	1213.7	1220.6	1224.3	1232.3	1241.4	1249.6
10°	1146.1	1141.5	1140.9	1130.1	1140.9	1141.5	1146.1	1155.8	1163.7	1174.7	1186.0
12.5°	1089.4	1078.4	1080.6	1074.3	1080.6	1078.4	1089.4	1089.5	1098.9	1105.6	1123.4
15°	991.3	991.3	988.9	979.2	988.9	991.3	991.3	1006.7	1009.5	1020.4	1035.8
17.5°	920.8	919.5	914.1	916.9	914.1	919.5	920.8	932.0	934.0	948.5	961.2
20°	878.7	875.3	868.4	868.4	868.4	875.3	878.7	884.9	892.4	901.0	911.8
22.5°	839.0	838.7	831.4	833.6	831.4	838.7	839.0	844.7	851.7	861.2	870.2
25°	792.4	787.8	784.5	786.1	784.5	787.8	792.4	793.0	801.0	807.3	813.0
27.5°	748.3	745.8	745.5	740.9	745.5	745.8	748.3	749.8	754.3	758.0	763.4
30°	722.7	717.0	718.2	715.3	718.2	717.0	722.7	723.3	725.6	727.9	734.2
32.5°	693.4	691.4	690.3	687.9	690.3	691.4	693.4	694.5	699.0	701.4	706.3
35°	653.6	654.2	651.3	652.5	651.3	654.2	653.6	654.7	655.3	657.5	662.2
37.5°	618.7	620.5	619.2	619.6	619.2	620.5	618.7	619.3	619.8	620.2	621.6
40°	595.9	595.9	595.9	597.6	595.9	595.9	595.9	594.2	594.8	594.2	594.2
42.5°	573.9	573.0	572.1	572.0	572.1	573.0	573.9	570.0	571.9	570.0	569.0
45°	536.5	538.2	538.7	535.9	538.7	538.2	536.5	535.3	533.6	533.0	532.4
47.5°	502.6	502.7	502.6	505.1	502.6	502.7	502.6	501.0	498.4	497.4	494.6
50°	478.8	477.6	478.8	477.6	478.8	477.6	478.8	475.9	474.2	471.3	469.1
52.5°	453.7	453.8	453.1	453.0	453.1	453.8	453.7	449.9	449.0	448.1	444.4
55°	414.2	415.3	414.7	414.7	414.7	415.3	414.2	411.9	411.4	407.9	404.5
57.5°	373.4	374.4	375.2	372.7	375.2	374.4	373.4	373.1	372.7	369.1	365.4
60°	345.1	347.9	347.3	346.2	347.3	347.9	345.1	345.6	344.0	341.6	339.3
62.5°	319.0	320.0	319.9	319.7	319.9	320.0	319.0	316.4	315.6	313.3	311.0
65°	278.8	279.9	278.2	279.9	278.2	279.9	278.8	277.1	273.1	271.9	269.7
67.5°	235.5	235.8	237.1	237.9	237.1	235.8	235.5	236.2	233.6	231.4	230.9
70°	208.5	207.9	209.7	211.4	209.7	207.9	208.5	207.4	205.7	204.0	201.6
72.5°	180.2	181.4	180.9	182.1	180.9	181.4	180.2	180.4	178.7	176.5	174.3
75°	138.8	140.5	140.0	141.7	140.0	140.5	138.8	140.0	138.8	136.6	134.2
77.5°	100.3	100.6	100.3	101.3	100.3	100.6	100.3	101.3	100.0	100.7	98.2
80°	76.5	75.4	74.3	76.5	74.3	75.4	76.5	76.5	74.8	76.5	74.8
82.5°	53.2	53.9	52.8	52.8	52.8	53.9	53.2	54.6	53.8	54.6	52.9
85°	24.5	24.0	22.8	22.8	22.8	24.0	24.5	24.5	26.3	25.1	25.1
87.5°	10.0	9.6	9.7	9.4	9.7	9.6	10.0	9.9	9.7	10.4	10.2
90°	27.0	27.5	28.0	28.4	28.0	27.5	27.0	26.6	25.7	24.5	23.4
92.5°	27.6	27.9	28.2	28.4	28.2	27.9	27.6	27.3	26.9	26.3	25.7
95°	46.0	45.7	45.5	45.3	45.5	45.7	46.0	46.2	45.7	44.6	43.4
97.5°	59.6	59.9	60.2	60.4	60.2	59.9	59.6	59.3	58.7	57.8	56.8
100°	69.1	69.7	70.1	70.6	70.1	69.7	69.1	68.7	67.5	65.6	63.8
102.5°	73.6	74.3	75.0	75.6	75.0	74.3	73.6	73.0	71.5	69.1	66.6
105°	77.2	78.2	79.1	80.1	79.1	78.2	77.2	76.3	74.6	72.0	69.4
107.5°	79.6	80.5	81.5	82.4	81.5	80.5	79.6	78.6	79.5	82.1	84.7
110°	80.4	81.4	82.3	83.2	82.3	81.4	80.4	79.5	90.7	114.1	137.5



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	81.8	82.6	83.3	84.0	83.3	82.6	81.8	81.0	123.4	208.8	294.1
115°	136.9	120.1	103.2	86.4	103.2	120.1	136.9	153.8	216.4	324.8	433.1
117.5°	518.8	463.4	408.0	352.6	408.0	463.4	518.8	574.1	614.9	641.1	667.4
120°	737.3	705.7	674.1	642.5	674.1	705.7	737.3	768.9	783.3	780.4	777.7
122.5°	820.1	814.0	807.9	801.7	807.9	814.0	820.1	826.2	828.5	826.8	825.1
125°	898.4	899.1	899.8	900.5	899.8	899.1	898.4	897.7	896.6	894.9	893.3
127.5°	962.4	962.6	962.7	962.9	962.7	962.6	962.4	962.3	961.0	958.6	956.2
130°	1002.3	1002.1	1001.9	1001.6	1001.9	1002.1	1002.3	1002.5	1001.3	998.8	996.3
132.5°	1040.3	1040.0	1039.7	1039.6	1039.7	1040.0	1040.3	1040.4	1039.5	1037.2	1035.1
135°	1095.7	1095.3	1094.8	1094.3	1094.8	1095.3	1095.7	1096.1	1095.3	1092.9	1090.5
137.5°	1146.6	1145.8	1145.0	1144.2	1145.0	1145.8	1146.6	1147.4	1146.7	1144.4	1142.0
140°	1178.9	1177.8	1176.6	1175.4	1176.6	1177.8	1178.9	1180.1	1179.7	1177.5	1175.4
142.5°	1209.3	1208.1	1206.9	1205.7	1206.9	1208.1	1209.3	1210.4	1210.0	1208.2	1206.2
145°	1251.5	1250.4	1249.2	1248.1	1249.2	1250.4	1251.5	1252.8	1252.5	1250.9	1249.2
147.5°	1288.3	1287.3	1286.3	1285.4	1286.3	1287.3	1288.3	1289.3	1289.2	1288.0	1286.8
150°	1311.6	1310.4	1309.2	1308.1	1309.2	1310.4	1311.6	1312.8	1312.7	1311.3	1309.8
152.5°	1332.1	1330.6	1329.0	1327.5	1329.0	1330.6	1332.1	1333.7	1333.8	1332.3	1330.9
155°	1360.0	1358.2	1356.3	1354.4	1356.3	1358.2	1360.0	1361.9	1362.2	1360.8	1359.3
157.5°	1384.6	1382.8	1381.0	1379.1	1381.0	1382.8	1384.6	1386.4	1386.6	1384.9	1383.4
160°	1398.4	1396.7	1395.1	1393.4	1395.1	1396.7	1398.4	1400.0	1400.1	1398.7	1397.3
162.5°	1411.3	1409.2	1407.2	1405.2	1407.2	1409.2	1411.3	1413.2	1413.5	1411.9	1410.3
165°	1427.8	1426.2	1424.5	1422.9	1424.5	1426.2	1427.8	1429.4	1429.4	1427.8	1426.2
167.5°	1440.4	1438.3	1436.1	1434.1	1436.1	1438.3	1440.4	1442.5	1442.7	1441.1	1439.4
170°	1447.2	1445.0	1442.9	1440.8	1442.9	1445.0	1447.2	1449.2	1449.5	1447.9	1446.2
172.5°	1452.2	1450.1	1447.9	1445.9	1447.9	1450.1	1452.2	1454.3	1454.5	1452.9	1451.2
175°	1457.3	1455.0	1452.6	1450.3	1452.6	1455.0	1457.3	1459.7	1460.0	1458.4	1456.7
177.5°	1458.1	1456.4	1454.7	1453.0	1454.7	1456.4	1458.1	1459.7	1460.0	1458.6	1457.3
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1428.5	1433.6	1441.3	1449.6	1454.6	1464.1	1466.9	1471.4	1475.6	1485.2	1495.2
5°	1346.0	1354.0	1372.9	1383.1	1397.4	1414.0	1424.9	1436.3	1448.9	1470.6	1490.6
7.5°	1257.6	1270.9	1294.3	1313.5	1333.9	1357.7	1374.8	1397.4	1416.2	1446.8	1476.0
10°	1198.6	1217.5	1238.6	1261.5	1290.0	1315.2	1339.2	1367.7	1390.6	1427.1	1461.5
12.5°	1145.6	1148.5	1178.7	1203.9	1242.9	1274.0	1301.7	1338.5	1360.9	1404.3	1440.4
15°	1052.9	1070.1	1097.5	1117.5	1163.7	1203.2	1242.1	1280.3	1306.1	1359.7	1407.1
17.5°	974.9	990.7	1018.7	1051.5	1084.8	1124.0	1174.3	1214.6	1249.6	1311.0	1367.0
20°	925.5	944.9	973.5	1007.2	1036.4	1079.2	1122.7	1168.9	1206.6	1275.7	1341.4
22.5°	883.5	898.8	921.9	955.1	987.0	1026.2	1073.8	1124.1	1163.6	1238.3	1304.8
25°	824.4	837.0	851.8	879.3	915.2	958.1	995.2	1050.7	1108.4	1178.0	1258.6
27.5°	771.2	780.1	793.2	817.3	845.2	885.3	926.5	979.1	1037.2	1112.8	1197.8
30°	738.7	744.4	757.6	777.6	804.9	836.4	878.1	928.4	987.8	1064.4	1148.9
32.5°	710.4	715.7	724.2	743.3	767.1	793.9	831.5	881.8	938.4	1013.7	1107.3
35°	667.9	671.8	679.3	694.7	707.8	734.2	765.6	811.2	864.4	936.4	1033.5
37.5°	625.5	630.9	635.5	642.0	658.9	676.2	703.5	742.1	794.3	866.9	959.5
40°	597.6	602.2	609.0	611.9	625.6	641.0	663.3	698.7	751.3	817.5	907.8
42.5°	569.3	573.9	577.9	581.3	593.1	606.7	626.7	657.1	703.8	768.2	857.6
45°	530.7	531.3	535.3	541.6	547.3	557.1	571.3	597.6	633.6	694.1	775.2
47.5°	491.6	492.3	493.0	495.8	502.0	510.8	520.4	541.7	573.9	622.2	701.2
50°	465.6	464.5	465.6	467.9	471.9	479.3	490.2	505.6	531.9	577.0	649.6
52.5°	440.5	440.2	439.5	440.5	443.6	448.7	456.3	469.5	493.0	534.5	598.4
55°	402.2	399.3	399.9	397.6	402.8	403.9	409.7	420.5	441.1	469.6	529.6
57.5°	361.4	359.0	356.5	355.9	355.3	358.4	363.0	371.6	387.4	412.3	461.1
60°	335.4	332.5	329.1	328.0	328.0	329.7	331.9	338.2	353.1	375.4	415.3
62.5°	308.8	305.6	303.5	300.5	299.6	301.4	303.6	308.1	318.8	339.7	374.2
65°	267.9	264.0	261.1	260.5	259.4	257.7	258.8	263.4	271.9	288.5	315.9
67.5°	227.0	223.2	222.5	219.1	217.6	217.7	217.6	221.4	226.6	240.9	261.3
70°	199.9	197.1	196.0	193.1	192.0	190.8	189.7	193.1	198.3	210.3	228.0
72.5°	172.5	170.1	167.6	165.2	165.5	164.3	164.1	166.2	170.4	181.4	195.0
75°	133.1	133.7	130.9	127.9	127.4	126.2	126.2	127.9	129.7	138.3	149.1
77.5°	96.5	96.1	93.7	92.8	92.2	90.9	92.2	93.3	94.3	100.0	108.0
80°	73.7	73.7	70.9	70.9	70.3	68.5	70.3	69.1	71.4	77.1	82.8
82.5°	52.7	51.7	51.7	50.7	50.6	49.3	50.2	51.3	52.2	56.1	59.5
85°	25.7	25.7	25.1	24.5	25.1	24.5	25.1	25.7	26.3	28.0	30.8
87.5°	9.9	10.2	10.2	10.3	10.0	10.0	10.1	10.0	10.4	10.3	10.2
90°	22.2	21.1	19.2	17.3	15.4	13.6	11.4	8.8	6.2	3.6	1.0
92.5°	25.1	24.5	23.5	22.6	21.6	20.7	20.3	20.6	20.8	21.0	21.3
95°	42.3	41.1	39.4	37.8	36.2	34.5	37.5	45.3	53.0	60.7	68.4
97.5°	55.9	55.0	51.2	47.4	43.6	39.8	48.8	70.6	92.3	114.1	135.9
100°	61.9	60.0	56.1	52.1	48.1	44.1	58.2	90.2	122.3	154.4	186.4
102.5°	64.1	61.7	95.0	128.3	161.5	194.8	214.9	221.7	228.4	235.2	242.0
105°	66.8	64.2	128.1	192.0	256.0	319.9	348.3	341.2	334.2	327.2	320.2
107.5°	87.3	90.0	166.6	243.2	319.9	396.5	432.0	426.3	420.6	414.9	409.3
110°	160.9	184.3	251.9	319.6	387.3	454.9	486.2	481.3	476.4	471.5	466.6



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	379.5	464.9	481.6	498.3	515.1	531.8	538.0	533.6	529.2	524.9	520.5
115°	541.5	649.9	644.0	638.2	632.3	626.5	621.6	617.5	613.5	609.6	605.6
117.5°	693.5	719.8	715.7	711.7	707.7	703.7	699.5	695.0	690.5	686.1	681.7
120°	774.8	772.0	767.8	763.6	759.4	755.2	751.3	747.8	744.2	740.8	737.3
122.5°	823.4	821.7	817.2	812.5	808.0	803.4	799.3	795.6	791.9	788.2	784.5
125°	891.7	890.0	885.5	881.1	876.7	872.2	868.4	865.4	862.4	859.3	856.3
127.5°	953.9	951.5	948.1	944.9	941.5	938.2	934.9	931.5	928.1	924.7	921.4
130°	993.7	991.1	988.5	985.9	983.3	980.8	977.7	973.9	970.2	966.4	962.7
132.5°	1032.9	1030.7	1028.1	1025.5	1023.0	1020.4	1017.5	1014.3	1011.2	1008.0	1004.8
135°	1088.2	1085.9	1083.7	1081.7	1079.5	1077.5	1074.5	1070.7	1067.0	1063.2	1059.5
137.5°	1139.8	1137.5	1135.1	1132.7	1130.3	1127.9	1125.4	1122.8	1120.2	1117.6	1114.9
140°	1173.3	1171.2	1168.6	1166.1	1163.5	1160.9	1158.6	1156.8	1154.9	1153.1	1151.2
142.5°	1204.3	1202.4	1199.4	1196.4	1193.5	1190.6	1188.3	1186.5	1184.9	1183.2	1181.6
145°	1247.6	1246.0	1242.0	1238.0	1234.1	1230.0	1228.2	1228.4	1228.6	1228.9	1229.1
147.5°	1285.6	1284.3	1280.4	1276.4	1272.5	1268.6	1267.0	1267.9	1268.9	1269.7	1270.6
150°	1308.5	1307.1	1303.3	1299.6	1295.8	1292.1	1291.0	1292.6	1294.3	1296.0	1297.6
152.5°	1329.6	1328.1	1324.6	1321.0	1317.4	1313.9	1313.0	1314.8	1316.6	1318.5	1320.3
155°	1358.0	1356.6	1353.8	1350.9	1348.2	1345.3	1345.0	1347.0	1349.2	1351.3	1353.4
157.5°	1381.7	1380.2	1378.2	1376.2	1374.2	1372.3	1372.2	1374.0	1375.7	1377.5	1379.3
160°	1395.9	1394.5	1393.1	1391.6	1390.3	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5
162.5°	1408.7	1407.1	1405.9	1404.6	1403.4	1402.2	1402.3	1403.8	1405.2	1406.5	1408.0
165°	1424.5	1422.9	1422.2	1421.5	1420.8	1420.1	1420.5	1421.9	1423.2	1424.7	1426.1
167.5°	1437.8	1436.1	1435.5	1434.9	1434.3	1433.6	1433.9	1435.4	1436.8	1438.1	1439.6
170°	1444.6	1442.9	1442.4	1442.0	1441.5	1441.1	1441.5	1442.9	1444.3	1445.7	1447.2
172.5°	1449.6	1447.9	1447.5	1447.0	1446.6	1446.1	1446.6	1447.9	1449.4	1450.8	1452.2
175°	1455.1	1453.5	1453.0	1452.5	1452.1	1451.6	1452.2	1453.8	1455.4	1457.1	1458.7
177.5°	1456.0	1454.7	1454.5	1454.3	1454.1	1454.0	1454.5	1455.9	1457.2	1458.4	1459.7
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1494.4	1496.6	1503.9	1511.2	1519.5	1521.7	1525.4	1522.2	1521.3	1530.0	1536.4
5°	1498.6	1508.8	1528.9	1547.1	1562.5	1573.4	1584.8	1589.4	1597.9	1610.0	1624.8
7.5°	1493.7	1513.7	1545.2	1571.8	1600.9	1621.7	1638.1	1652.0	1669.0	1691.7	1716.5
10°	1488.2	1515.1	1553.4	1586.0	1621.3	1648.2	1670.5	1692.2	1717.4	1748.8	1781.3
12.5°	1478.3	1510.1	1558.0	1596.5	1641.9	1668.4	1698.4	1745.2	1772.2	1816.0	1861.8
15°	1458.0	1493.4	1560.2	1607.7	1659.1	1709.3	1764.8	1809.4	1853.9	1879.6	1944.2
17.5°	1428.0	1480.0	1553.9	1609.3	1674.6	1753.9	1816.1	1866.6	1918.0	1959.7	1992.1
20°	1403.7	1460.3	1544.8	1611.1	1688.8	1773.9	1845.4	1896.8	1941.3	1976.2	1996.1
22.5°	1373.1	1444.2	1526.6	1604.2	1703.4	1787.6	1862.7	1903.2	1940.4	1957.4	1965.1
25°	1324.9	1410.6	1503.7	1598.5	1710.5	1799.7	1868.2	1892.7	1903.6	1887.1	1859.6
27.5°	1272.9	1368.4	1477.3	1587.8	1706.2	1791.8	1841.0	1837.1	1818.7	1765.1	1722.3
30°	1234.1	1339.2	1456.3	1576.8	1695.7	1779.1	1807.7	1779.1	1737.3	1677.4	1616.3
32.5°	1193.3	1302.2	1433.9	1561.3	1676.5	1749.8	1756.0	1706.8	1642.3	1574.1	1497.9
35°	1131.8	1249.5	1391.7	1526.6	1635.6	1682.0	1654.5	1567.7	1491.2	1398.0	1294.0
37.5°	1062.2	1192.1	1334.8	1475.7	1574.5	1586.7	1518.5	1427.1	1319.1	1209.7	1087.4
40°	1010.1	1147.8	1294.6	1436.8	1524.2	1511.7	1424.9	1324.3	1195.8	1062.0	948.4
42.5°	963.5	1101.1	1250.7	1390.3	1460.3	1425.7	1324.3	1200.9	1062.7	936.9	832.8
45°	882.7	1024.3	1177.5	1312.3	1352.3	1290.0	1155.8	1018.6	882.7	777.6	695.3
47.5°	804.3	944.3	1096.0	1214.5	1228.6	1144.9	998.2	857.1	740.2	654.6	596.6
50°	746.7	887.3	1037.5	1143.2	1138.6	1037.5	886.7	752.4	654.7	585.6	546.7
52.5°	695.1	827.9	972.2	1068.2	1044.0	933.8	789.8	670.6	590.3	536.2	501.0
55°	614.8	737.5	874.7	951.8	907.2	785.0	663.3	567.3	507.9	467.4	439.9
57.5°	534.9	650.1	767.5	815.0	765.8	652.9	551.5	481.8	437.1	407.1	389.3
60°	485.6	586.2	690.7	731.8	673.0	572.5	492.5	430.2	394.2	369.6	353.6
62.5°	436.3	526.3	624.9	647.3	593.5	508.5	437.6	385.9	356.3	334.4	319.3
65°	369.1	442.7	517.6	532.4	482.8	417.1	361.1	327.4	301.1	285.1	273.1
67.5°	302.6	361.9	414.9	426.9	383.3	337.8	297.3	267.9	250.1	236.9	226.7
70°	263.4	310.2	353.6	363.3	328.5	287.9	257.1	233.7	217.7	206.2	196.6
72.5°	221.8	260.9	297.0	303.5	275.0	244.1	218.7	200.3	186.1	178.8	169.5
75°	169.7	192.5	220.5	222.2	203.4	184.5	165.1	153.1	145.7	136.6	132.0
77.5°	119.8	137.7	153.7	156.8	145.6	132.8	121.9	112.4	106.2	101.9	97.7
80°	91.4	105.7	112.5	116.6	108.6	99.4	93.2	86.9	82.8	80.0	77.1
82.5°	65.3	74.1	80.6	83.6	79.3	73.8	67.5	64.0	60.9	58.5	57.5
85°	33.1	37.1	41.2	42.3	41.2	38.8	35.4	35.4	33.7	33.1	33.1
87.5°	12.1	14.5	15.0	16.9	16.4	16.8	17.1	17.1	17.0	16.8	16.5
90°	3.6	6.2	8.8	11.4	13.6	15.4	17.3	19.2	21.1	22.2	23.4
92.5°	21.0	20.8	20.6	20.3	20.7	21.6	22.6	23.5	24.5	25.1	25.7
95°	60.7	53.0	45.3	37.5	34.5	36.2	37.8	39.4	41.1	42.3	43.4
97.5°	114.1	92.3	70.6	48.8	39.8	43.6	47.4	51.2	55.0	55.9	56.8
100°	154.4	122.3	90.2	58.2	44.1	48.1	52.1	56.1	60.0	61.9	63.8
102.5°	235.2	228.4	221.7	214.9	194.8	161.5	128.3	95.0	61.7	64.1	66.6
105°	327.2	334.2	341.2	348.3	319.9	256.0	192.0	128.1	64.2	66.8	69.4
107.5°	414.9	420.6	426.3	432.0	396.5	319.9	243.2	166.6	90.0	87.3	84.7
110°	471.5	476.4	481.3	486.2	454.9	387.3	319.6	251.9	184.3	160.9	137.5



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	524.9	529.2	533.6	538.0	531.8	515.1	498.3	481.6	464.9	379.5	294.1
115°	609.6	613.5	617.5	621.6	626.5	632.3	638.2	644.0	649.9	541.5	433.1
117.5°	686.1	690.5	695.0	699.5	703.7	707.7	711.7	715.7	719.8	693.5	667.4
120°	740.8	744.2	747.8	751.3	755.2	759.4	763.6	767.8	772.0	774.8	777.7
122.5°	788.2	791.9	795.6	799.3	803.4	808.0	812.5	817.2	821.7	823.4	825.1
125°	859.3	862.4	865.4	868.4	872.2	876.7	881.1	885.5	890.0	891.7	893.3
127.5°	924.7	928.1	931.5	934.9	938.2	941.5	944.9	948.1	951.5	953.9	956.2
130°	966.4	970.2	973.9	977.7	980.8	983.3	985.9	988.5	991.1	993.7	996.3
132.5°	1008.0	1011.2	1014.3	1017.5	1020.4	1023.0	1025.5	1028.1	1030.7	1032.9	1035.1
135°	1063.2	1067.0	1070.7	1074.5	1077.5	1079.5	1081.7	1083.7	1085.9	1088.2	1090.5
137.5°	1117.6	1120.2	1122.8	1125.4	1127.9	1130.3	1132.7	1135.1	1137.5	1139.8	1142.0
140°	1153.1	1154.9	1156.8	1158.6	1160.9	1163.5	1166.1	1168.6	1171.2	1173.3	1175.4
142.5°	1183.2	1184.9	1186.5	1188.3	1190.6	1193.5	1196.4	1199.4	1202.4	1204.3	1206.2
145°	1228.9	1228.6	1228.4	1228.2	1230.0	1234.1	1238.0	1242.0	1246.0	1247.6	1249.2
147.5°	1269.7	1268.9	1267.9	1267.0	1268.6	1272.5	1276.4	1280.4	1284.3	1285.6	1286.8
150°	1296.0	1294.3	1292.6	1291.0	1292.1	1295.8	1299.6	1303.3	1307.1	1308.5	1309.8
152.5°	1318.5	1316.6	1314.8	1313.0	1313.9	1317.4	1321.0	1324.6	1328.1	1329.6	1330.9
155°	1351.3	1349.2	1347.0	1345.0	1345.3	1348.2	1350.9	1353.8	1356.6	1358.0	1359.3
157.5°	1377.5	1375.7	1374.0	1372.2	1372.3	1374.2	1376.2	1378.2	1380.2	1381.7	1383.4
160°	1393.1	1391.6	1390.3	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5	1395.9	1397.3
162.5°	1406.5	1405.2	1403.8	1402.3	1402.2	1403.4	1404.6	1405.9	1407.1	1408.7	1410.3
165°	1424.7	1423.2	1421.9	1420.5	1420.1	1420.8	1421.5	1422.2	1422.9	1424.5	1426.2
167.5°	1438.1	1436.8	1435.4	1433.9	1433.6	1434.3	1434.9	1435.5	1436.1	1437.8	1439.4
170°	1445.7	1444.3	1442.9	1441.5	1441.1	1441.5	1442.0	1442.4	1442.9	1444.6	1446.2
172.5°	1450.8	1449.4	1447.9	1446.6	1446.1	1446.6	1447.0	1447.5	1447.9	1449.6	1451.2
175°	1457.1	1455.4	1453.8	1452.2	1451.6	1452.1	1452.5	1453.0	1453.5	1455.1	1456.7
177.5°	1458.4	1457.2	1455.9	1454.5	1454.0	1454.1	1454.3	1454.5	1454.7	1456.0	1457.3
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1541.9	1548.3	1548.3	1549.2	1556.5	1555.6	1555.1
5°	1640.8	1650.5	1651.7	1662.0	1668.8	1666.6	1660.3
7.5°	1734.1	1752.2	1765.9	1773.6	1782.6	1788.2	1785.7
10°	1808.2	1834.4	1850.5	1861.3	1874.5	1884.2	1880.8
12.5°	1875.4	1906.7	1928.6	1947.2	1949.0	1961.4	1953.0
15°	1980.2	2013.3	2016.7	2030.4	2041.3	2040.1	2040.7
17.5°	2014.8	2025.4	2027.6	2027.9	2028.1	2024.0	2015.3
20°	2002.4	1998.5	1988.7	1981.3	1968.2	1966.4	1955.1
22.5°	1944.0	1931.3	1906.9	1890.8	1870.4	1865.0	1861.8
25°	1828.8	1800.8	1762.0	1724.8	1714.5	1694.5	1700.2
27.5°	1670.8	1627.1	1585.0	1554.9	1527.6	1497.6	1506.2
30°	1559.7	1510.5	1451.1	1405.4	1376.3	1347.7	1342.6
32.5°	1427.1	1355.1	1288.9	1248.6	1204.0	1185.9	1166.1
35°	1198.6	1128.3	1062.6	1006.1	973.5	948.4	925.5
37.5°	993.1	912.1	859.1	813.3	789.8	775.4	779.0
40°	865.6	794.7	755.9	721.0	699.3	689.0	691.3
42.5°	762.2	709.2	677.3	653.3	638.0	632.3	630.9
45°	645.0	615.3	589.0	575.3	567.9	561.6	557.6
47.5°	565.0	540.8	526.0	517.8	511.3	504.9	504.8
50°	517.0	501.0	490.8	482.2	477.1	472.5	476.5
52.5°	480.4	465.9	455.6	447.9	446.0	441.9	441.8
55°	426.2	414.7	407.3	400.5	397.1	394.8	391.9
57.5°	376.9	366.0	359.1	354.8	348.3	345.9	345.1
60°	341.6	333.0	326.2	320.5	317.6	313.1	313.1
62.5°	309.2	300.7	294.2	289.9	285.2	283.4	283.9
65°	262.3	255.4	249.1	244.5	243.4	240.0	241.1
67.5°	219.0	214.5	207.8	205.3	203.2	201.3	199.9
70°	190.3	185.7	182.3	178.8	177.1	177.1	177.1
72.5°	166.0	160.6	158.5	154.1	155.2	153.3	151.5
75°	128.5	125.1	123.4	121.7	118.8	118.8	118.8
77.5°	94.6	93.6	91.5	89.7	89.0	88.4	88.7
80°	73.1	72.6	71.4	71.4	70.3	69.7	68.5
82.5°	56.2	54.8	54.1	53.6	53.4	53.2	53.0
85°	32.0	30.8	30.8	31.4	30.3	30.3	30.8
87.5°	17.2	17.5	17.2	17.3	17.8	17.5	17.6
90°	24.5	25.7	26.6	27.0	27.5	28.0	28.4
92.5°	26.3	26.9	27.3	27.6	27.9	28.2	28.4
95°	44.6	45.7	46.2	46.0	45.7	45.5	45.3
97.5°	57.8	58.7	59.3	59.6	59.9	60.2	60.4
100°	65.6	67.5	68.7	69.1	69.7	70.1	70.6
102.5°	69.1	71.5	73.0	73.6	74.3	75.0	75.6
105°	72.0	74.6	76.3	77.2	78.2	79.1	80.1
107.5°	82.1	79.5	78.6	79.6	80.5	81.5	82.4
110°	114.1	90.7	79.5	80.4	81.4	82.3	83.2



TEST NUMBER: P331573-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	208.8	123.4	81.0	81.8	82.6	83.3	84.0
115°	324.8	216.4	153.8	136.9	120.1	103.2	86.4
117.5°	641.1	614.9	574.1	518.8	463.4	408.0	352.6
120°	780.4	783.3	768.9	737.3	705.7	674.1	642.5
122.5°	826.8	828.5	826.2	820.1	814.0	807.9	801.7
125°	894.9	896.6	897.7	898.4	899.1	899.8	900.5
127.5°	958.6	961.0	962.3	962.4	962.6	962.7	962.9
130°	998.8	1001.3	1002.5	1002.3	1002.1	1001.9	1001.6
132.5°	1037.2	1039.5	1040.4	1040.3	1040.0	1039.7	1039.6
135°	1092.9	1095.3	1096.1	1095.7	1095.3	1094.8	1094.3
137.5°	1144.4	1146.7	1147.4	1146.6	1145.8	1145.0	1144.2
140°	1177.5	1179.7	1180.1	1178.9	1177.8	1176.6	1175.4
142.5°	1208.2	1210.0	1210.4	1209.3	1208.1	1206.9	1205.7
145°	1250.9	1252.5	1252.8	1251.5	1250.4	1249.2	1248.1
147.5°	1288.0	1289.2	1289.3	1288.3	1287.3	1286.3	1285.4
150°	1311.3	1312.7	1312.8	1311.6	1310.4	1309.2	1308.1
152.5°	1332.3	1333.8	1333.7	1332.1	1330.6	1329.0	1327.5
155°	1360.8	1362.2	1361.9	1360.0	1358.2	1356.3	1354.4
157.5°	1384.9	1386.6	1386.4	1384.6	1382.8	1381.0	1379.1
160°	1398.7	1400.1	1400.0	1398.4	1396.7	1395.1	1393.4
162.5°	1411.9	1413.5	1413.2	1411.3	1409.2	1407.2	1405.2
165°	1427.8	1429.4	1429.4	1427.8	1426.2	1424.5	1422.9
167.5°	1441.1	1442.7	1442.5	1440.4	1438.3	1436.1	1434.1
170°	1447.9	1449.5	1449.2	1447.2	1445.0	1442.9	1440.8
172.5°	1452.9	1454.5	1454.3	1452.2	1450.1	1447.9	1445.9
175°	1458.4	1460.0	1459.7	1457.3	1455.0	1452.6	1450.3
177.5°	1458.6	1460.0	1459.7	1458.1	1456.4	1454.7	1453.0
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5

(END OF REPORT)