

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331791-940

Luminaire Tested: **S122RDIW-S485D710U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331791-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D710U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4043.9 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331791-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331791-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33	28
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16	13
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11880	11880	11880
5°	11925	11733	11797
10°	11835	11540	11442
15°	11699	11198	10877
20°	11510	10710	10172
25°	11318	10156	9492
30°	11050	9587	8617
35°	10789	8966	7849
40°	10526	8323	6962
45°	10218	7604	6158
50°	9902	6875	5368
55°	9579	6092	4611
60°	9203	5270	3827
65°	8779	4424	3484
70°	8266	3644	3205
75°	7642	3319	2994
80°	6750	2966	2724
85°	5298	2353	2353



TEST NUMBER: P331791-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.9	1.7
10°-20°	189.1	4.7
20°-30°	265.6	6.6
30°-40°	289.6	7.2
40°-50°	266.3	6.6
50°-60°	209.1	5.2
60°-70°	136.4	3.4
70°-80°	70.3	1.7
80°-90°	20.4	0.5
90°-100°	28.8	0.7
100°-110°	105.5	2.6
110°-120°	282.1	7.0
120°-130°	465.6	11.5
130°-140°	495.2	12.2
140°-150°	460.3	11.4
150°-160°	370.1	9.2
160°-170°	238.5	5.9
170°-180°	82.1	2.0
0°-30°	523.6	12.9
0°-40°	813.2	20.1
0°-60°	1288.6	31.9
0°-90°	1515.7	37.5
90°-120°	416.4	10.3
90°-150°	1837.6	45.4
90°-180°	2528.0	62.5
0°-180°	4043.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	736	736	736	736	736	
5°	736	732	724	729	728	70
15°	700	692	670	658	651	197
25°	635	613	570	544	533	292
35°	547	512	455	414	398	342
45°	448	402	333	287	270	345
55°	340	287	216	178	164	304
65°	230	176	116	94	91	228
75°	122	77	53	49	48	130
85°	29	15	13	13	13	34
90°	1	7	12	16	17	3
95°	41	21	24	27	27	50
105°	190	198	38	45	47	203
115°	359	370	385	110	51	353
125°	508	516	527	532	534	452
135°	628	638	644	649	649	485
145°	728	728	738	742	740	455
155°	802	797	804	807	803	369
165°	845	842	843	847	843	239
175°	865	860	862	865	860	82
180°	863	863	863	863	863	



TEST NUMBER: P331791-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	738.5	738.0	737.4	736.7	736.2	735.2	734.0	732.6	731.3	730.0	731.2
5°	735.8	735.1	734.4	733.7	732.9	731.6	729.7	727.7	725.9	723.9	725.2
7.5°	728.3	727.4	726.5	725.5	724.6	723.0	720.8	718.5	716.3	714.1	714.4
10°	721.9	720.9	719.8	718.8	717.7	715.8	712.8	709.8	706.9	703.9	703.5
12.5°	713.9	712.7	711.3	710.1	708.8	706.3	702.5	698.7	694.9	691.2	690.4
15°	699.9	698.3	696.7	695.0	693.4	690.1	685.0	680.0	675.0	669.9	667.2
17.5°	682.8	680.3	677.8	675.3	672.8	668.3	661.9	655.4	649.0	642.5	639.2
20°	669.9	667.0	664.1	661.1	658.1	652.9	645.5	638.1	630.7	623.3	619.6
22.5°	656.1	652.8	649.4	646.1	642.8	637.0	628.7	620.3	612.0	603.6	598.9
25°	635.3	630.6	625.9	621.1	616.4	609.1	599.3	589.6	579.8	570.1	564.0
27.5°	610.3	605.1	599.9	594.9	589.7	581.6	570.6	559.5	548.6	537.5	530.5
30°	592.7	587.1	581.5	575.9	570.2	561.5	549.7	537.8	525.9	514.2	506.6
32.5°	575.7	569.1	562.5	556.0	549.4	540.0	528.0	515.9	503.8	491.8	483.1
35°	547.4	539.8	532.4	524.8	517.2	506.9	493.9	480.9	467.9	454.9	445.5
37.5°	519.2	510.9	502.6	494.3	486.1	474.9	461.1	447.2	433.3	419.5	409.1
40°	499.4	490.6	481.7	472.9	464.0	452.4	438.0	423.7	409.3	394.9	384.4
42.5°	479.2	469.8	460.5	451.2	441.8	429.7	414.9	400.0	385.2	370.4	359.5
45°	447.5	437.7	427.7	417.8	407.9	395.1	379.6	364.1	348.5	333.0	322.4
47.5°	416.6	406.1	395.7	385.1	374.6	361.3	345.3	329.2	313.2	297.1	286.7
50°	394.2	383.7	373.3	362.7	352.2	338.9	322.5	306.3	290.0	273.7	263.5
52.5°	372.4	361.4	350.4	339.5	328.5	315.0	299.1	283.2	267.2	251.4	241.5
55°	340.3	328.8	317.2	305.7	294.2	280.4	264.4	248.4	232.4	216.4	207.6
57.5°	307.4	295.6	283.7	271.9	260.0	246.5	231.1	215.7	200.4	185.0	176.8
60°	285.0	273.2	261.4	249.5	237.6	224.2	208.9	193.7	178.4	163.2	155.6
62.5°	263.1	251.4	239.5	227.7	215.8	202.7	188.2	173.6	159.1	144.5	137.3
65°	229.8	217.8	205.8	193.8	181.8	169.2	155.9	142.5	129.2	115.8	110.8
67.5°	197.5	185.7	173.7	161.8	149.9	137.9	126.0	114.0	102.0	90.1	87.7
70°	175.1	163.6	152.0	140.5	128.9	118.1	107.9	97.6	87.5	77.2	75.8
72.5°	153.8	142.8	131.7	120.6	109.6	100.0	91.8	83.6	75.3	67.1	65.9
75°	122.5	112.2	101.8	91.5	81.1	73.4	68.4	63.3	58.3	53.2	52.3
77.5°	91.8	82.7	73.6	64.5	55.5	49.7	47.3	44.9	42.4	39.9	39.3
80°	72.6	65.0	57.5	49.9	42.4	37.9	36.4	35.0	33.4	31.9	31.4
82.5°	55.0	49.1	43.2	37.4	31.5	28.0	27.0	25.9	25.0	24.0	23.6
85°	28.6	25.5	22.4	19.4	16.2	14.4	14.0	13.6	13.1	12.7	12.7
87.5°	8.6	8.0	7.4	6.7	6.1	5.9	6.1	6.3	6.5	6.8	6.8
90°	0.6	2.1	3.7	5.2	6.7	8.0	9.2	10.3	11.4	12.5	13.2
92.5°	12.6	12.5	12.3	12.2	12.0	12.3	12.8	13.4	13.9	14.4	14.8
95°	40.6	36.0	31.4	26.8	22.3	20.4	21.4	22.4	23.4	24.3	25.1
97.5°	80.5	67.6	54.8	41.8	28.9	23.6	25.9	28.1	30.3	32.5	33.2
100°	110.5	91.5	72.5	53.5	34.5	26.1	28.5	30.9	33.3	35.6	36.6
102.5°	143.5	139.5	135.4	131.3	127.3	115.5	95.8	76.1	56.3	36.6	38.0
105°	189.8	193.9	198.1	202.2	206.4	189.6	151.7	113.8	76.0	38.1	39.6
107.5°	242.5	245.9	249.3	252.6	256.0	235.0	189.6	144.2	98.7	53.3	51.7
110°	276.5	279.5	282.4	285.3	288.2	269.6	229.5	189.4	149.4	109.2	95.4



TEST NUMBER: P331791-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.5	311.1	313.7	316.2	318.8	315.1	305.2	295.3	285.4	275.5	225.0
115°	358.9	361.3	363.6	366.0	368.4	371.3	374.8	378.3	381.7	385.1	320.9
117.5°	404.0	406.6	409.3	411.9	414.6	417.1	419.5	421.9	424.2	426.6	411.1
120°	436.9	439.1	441.1	443.2	445.3	447.5	450.0	452.5	455.0	457.5	459.2
122.5°	464.9	467.2	469.3	471.5	473.7	476.2	478.8	481.6	484.3	487.1	488.0
125°	507.5	509.3	511.1	512.9	514.7	516.9	519.6	522.2	524.9	527.4	528.4
127.5°	546.1	548.0	550.1	552.1	554.1	556.1	558.0	560.0	562.0	563.9	565.3
130°	570.5	572.7	575.0	577.2	579.4	581.3	582.8	584.3	585.9	587.5	589.0
132.5°	595.6	597.4	599.3	601.2	603.1	604.8	606.3	607.8	609.4	610.9	612.2
135°	628.0	630.2	632.4	634.6	636.9	638.6	639.9	641.1	642.4	643.6	645.0
137.5°	660.8	662.4	664.0	665.5	667.0	668.5	669.9	671.4	672.8	674.2	675.6
140°	682.3	683.4	684.5	685.6	686.7	688.0	689.6	691.1	692.6	694.2	695.4
142.5°	700.3	701.2	702.3	703.3	704.3	705.6	707.4	709.2	710.9	712.7	713.8
145°	728.5	728.3	728.3	728.1	727.9	729.1	731.4	733.8	736.1	738.5	739.5
147.5°	753.0	752.6	752.1	751.5	751.0	751.9	754.2	756.5	758.8	761.2	762.0
150°	769.1	768.1	767.1	766.2	765.2	765.8	768.0	770.3	772.5	774.7	775.5
152.5°	782.6	781.5	780.4	779.3	778.2	778.7	780.9	782.9	785.1	787.2	788.0
155°	802.2	800.9	799.7	798.4	797.2	797.4	799.1	800.7	802.4	804.1	804.9
157.5°	817.5	816.5	815.4	814.3	813.3	813.3	814.5	815.6	816.8	818.0	818.9
160°	826.5	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	827.3
162.5°	834.5	833.7	832.9	832.0	831.2	831.1	831.8	832.6	833.3	834.0	834.9
165°	845.3	844.4	843.6	842.8	841.9	841.7	842.1	842.5	842.9	843.4	844.4
167.5°	853.2	852.4	851.6	850.7	849.9	849.7	850.1	850.4	850.9	851.2	852.2
170°	857.7	856.8	856.0	855.2	854.3	854.1	854.3	854.7	855.0	855.2	856.2
172.5°	860.7	859.9	859.1	858.2	857.4	857.1	857.4	857.6	857.9	858.2	859.2
175°	864.6	863.6	862.6	861.7	860.7	860.3	860.6	860.9	861.2	861.5	862.5
177.5°	865.2	864.4	863.6	862.9	862.1	861.7	861.8	862.0	862.1	862.2	863.0
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331791-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	732.4	733.6	734.8	735.2	735.0	734.8	734.5	734.3
5°	726.6	727.9	729.2	729.7	729.2	728.8	728.3	727.9
7.5°	714.8	715.2	715.6	715.4	714.6	713.8	713.1	712.3
10°	703.0	702.6	702.1	701.5	700.6	699.7	698.8	697.9
12.5°	689.6	688.8	688.0	686.8	685.3	683.9	682.3	680.9
15°	664.3	661.6	658.7	656.6	655.1	653.6	652.1	650.7
17.5°	635.8	632.5	629.1	626.2	623.7	621.1	618.6	616.0
20°	615.9	612.2	608.5	605.0	601.8	598.5	595.3	592.0
22.5°	594.1	589.3	584.6	580.9	578.5	576.1	573.7	571.2
25°	557.9	551.9	545.8	541.6	539.4	537.2	535.0	532.8
27.5°	523.4	516.3	509.3	504.0	500.4	497.0	493.4	489.9
30°	499.0	491.5	483.9	478.1	474.1	470.2	466.2	462.2
32.5°	474.5	465.9	457.3	451.1	447.4	443.6	439.8	436.0
35°	436.2	426.9	417.6	411.3	408.0	404.7	401.5	398.2
37.5°	398.9	388.6	378.4	371.3	367.7	363.9	360.2	356.4
40°	373.9	363.4	352.8	345.7	341.9	338.0	334.1	330.3
42.5°	348.7	337.8	327.0	319.7	315.9	312.2	308.4	304.7
45°	311.9	301.5	291.0	283.9	280.4	276.8	273.2	269.7
47.5°	276.3	265.8	255.4	248.5	245.3	242.1	238.8	235.6
50°	253.2	243.1	232.8	226.2	223.1	220.0	216.9	213.7
52.5°	231.6	221.8	211.9	205.5	202.7	199.8	196.9	194.0
55°	198.7	189.8	180.9	175.0	172.3	169.4	166.7	163.8
57.5°	168.7	160.6	152.5	147.2	144.8	142.5	140.1	137.7
60°	148.0	140.5	133.0	128.0	125.6	123.2	120.9	118.5
62.5°	130.1	123.0	115.7	111.5	110.0	108.6	107.2	105.8
65°	105.8	100.8	95.8	93.0	92.6	92.1	91.7	91.2
67.5°	85.4	83.1	80.8	79.5	78.9	78.5	78.0	77.5
70°	74.3	72.9	71.3	70.3	69.7	69.1	68.5	67.9
72.5°	64.6	63.4	62.2	61.3	61.0	60.6	60.3	59.9
75°	51.2	50.2	49.1	48.5	48.4	48.2	48.1	48.0
77.5°	38.8	38.2	37.6	37.2	36.9	36.7	36.5	36.2
80°	30.8	30.2	29.6	29.3	29.3	29.3	29.3	29.3
82.5°	23.3	22.9	22.6	22.4	22.4	22.4	22.4	22.4
85°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7
87.5°	6.8	6.8	6.9	6.9	7.0	7.0	7.0	7.1
90°	13.9	14.5	15.2	15.8	16.1	16.3	16.6	16.9
92.5°	15.2	15.6	16.0	16.2	16.3	16.5	16.7	16.9
95°	25.8	26.4	27.1	27.4	27.3	27.1	27.0	26.8
97.5°	33.7	34.2	34.8	35.1	35.3	35.5	35.7	35.8
100°	37.8	38.9	40.0	40.8	41.0	41.3	41.6	41.8
102.5°	39.5	40.9	42.4	43.2	43.7	44.1	44.4	44.9
105°	41.1	42.6	44.1	45.2	45.7	46.4	46.9	47.4
107.5°	50.2	48.7	47.1	46.6	47.2	47.7	48.2	48.8
110°	81.5	67.6	53.8	47.1	47.6	48.2	48.8	49.3



TEST NUMBER: P331791-940

CATALOG NUMBER: S122RDIW-S485D710U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	174.3	123.8	73.1	48.1	48.5	49.0	49.4	49.8
115°	256.7	192.4	128.2	91.1	81.1	71.2	61.2	51.2
117.5°	395.6	380.0	364.4	340.3	307.5	274.6	241.8	209.0
120°	460.9	462.5	464.2	455.7	436.9	418.2	399.5	380.8
122.5°	489.0	490.0	491.1	489.7	486.1	482.4	478.8	475.2
125°	529.4	530.4	531.4	532.1	532.4	532.9	533.3	533.7
127.5°	566.8	568.2	569.6	570.3	570.4	570.5	570.6	570.7
130°	590.5	592.0	593.5	594.2	594.1	594.0	593.8	593.7
132.5°	613.5	614.8	616.1	616.7	616.5	616.4	616.3	616.2
135°	646.4	647.7	649.2	649.7	649.4	649.2	648.9	648.6
137.5°	676.9	678.2	679.7	680.1	679.6	679.1	678.7	678.1
140°	696.7	697.9	699.2	699.5	698.7	698.0	697.3	696.7
142.5°	714.9	716.0	717.2	717.4	716.8	716.0	715.3	714.6
145°	740.4	741.4	742.3	742.5	741.8	741.1	740.4	739.8
147.5°	762.7	763.4	764.1	764.2	763.6	763.0	762.4	761.8
150°	776.3	777.2	778.0	778.1	777.4	776.7	776.0	775.3
152.5°	788.8	789.7	790.5	790.5	789.5	788.6	787.7	786.8
155°	805.7	806.6	807.4	807.2	806.1	805.0	803.9	802.8
157.5°	819.9	820.8	821.8	821.7	820.6	819.6	818.5	817.3
160°	828.1	829.0	829.8	829.7	828.8	827.8	826.9	825.9
162.5°	835.9	836.8	837.8	837.7	836.4	835.3	834.0	832.9
165°	845.3	846.2	847.2	847.2	846.2	845.3	844.4	843.4
167.5°	853.2	854.2	855.1	855.0	853.7	852.5	851.2	850.0
170°	857.2	858.1	859.1	859.0	857.7	856.5	855.2	854.0
172.5°	860.1	861.1	862.1	861.9	860.7	859.4	858.2	856.9
175°	863.4	864.3	865.3	865.1	863.7	862.4	860.9	859.6
177.5°	863.8	864.5	865.3	865.2	864.2	863.2	862.2	861.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7

(END OF REPORT)