

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331817-940

Luminaire Tested: **S122RDIW-S675D1240U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331817-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1240U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6685.4 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34								
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	37	37	36	30								
2	87	80	74	69	78	72	68	63	58	55	52	45	43	41	33	32	31	26								
3	79	71	64	58	72	64	58	54	52	48	44	41	38	36	30	29	27	22								
4	73	63	55	50	66	57	51	46	46	42	38	37	34	31	27	25	24	20								
5	67	56	49	43	60	51	45	40	42	37	33	33	30	27	25	23	21	18								
6	62	51	43	37	56	46	40	35	38	33	29	30	27	24	23	21	19	16								
7	57	46	38	33	52	42	35	31	34	30	26	28	24	22	21	19	17	14								
8	53	42	34	29	48	38	32	27	32	27	23	25	22	19	20	17	16	13								
9	50	38	31	26	45	35	29	24	29	24	21	23	20	18	18	16	14	12								
10	46	35	28	24	42	32	26	22	27	22	19	22	18	16	17	15	13	11								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21151	21151	21151	21151
5°	23622	21284	18870	21284
10°	26209	21135	16357	21135
15°	27497	20824	12889	20824
20°	23838	20366	11153	20366
25°	15634	19737	9957	19737
30°	10524	18975	9012	18975
35°	8523	18015	8129	18015
40°	7579	16971	7522	16971
45°	6859	15746	6715	15746
50°	6242	14531	6219	14531
55°	5869	13185	5790	13185
60°	4908	11951	4850	11951
65°	4138	10850	4695	10850
70°	3829	9692	4428	9692
75°	3575	8434	4086	8434
80°	3301	6936	3636	6936
85°	3038	5483	3205	5483



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.2	1.9
10°-20°	346.0	5.2
20°-30°	445.9	6.7
30°-40°	423.7	6.3
40°-50°	363.0	5.4
50°-60°	276.4	4.1
60°-70°	174.7	2.6
70°-80°	87.3	1.3
80°-90°	26.4	0.4
90°-100°	50.3	0.8
100°-110°	184.4	2.8
110°-120°	492.9	7.4
120°-130°	813.7	12.2
130°-140°	865.3	12.9
140°-150°	804.3	12.0
150°-160°	646.7	9.7
160°-170°	416.7	6.2
170°-180°	143.4	2.1
0°-30°	916.1	13.7
0°-40°	1339.8	20.0
0°-60°	1979.2	29.6
0°-90°	2267.7	33.9
90°-120°	727.6	10.9
90°-150°	3210.9	48.0
90°-180°	4418.0	66.1
0°-180°	6685.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1310	1310	1310	1310	1310	
5°	1458	1313	1164	1313	1458	144
15°	1645	1246	771	1246	1645	444
25°	878	1108	559	1108	878	416
35°	432	914	412	914	432	277
45°	300	690	294	690	300	232
55°	208	468	206	468	208	183
65°	108	284	123	284	108	110
75°	57	135	66	135	57	61
85°	16	30	17	30	16	18
90°	29	1	29	1	29	14
95°	47	71	47	71	47	44
105°	83	332	83	332	83	86
115°	89	627	89	627	89	224
125°	933	887	933	887	933	807
135°	1133	1097	1133	1097	1133	874
145°	1293	1273	1293	1273	1293	808
155°	1403	1402	1403	1402	1403	647
165°	1474	1477	1474	1477	1474	416
175°	1502	1511	1502	1511	1502	143
180°	1507	1507	1507	1507	1507	



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1363.2	1364.2	1365.4	1362.8	1362.8	1360.6	1355.8	1352.3	1342.0	1340.6	1340.6
5°	1457.5	1456.5	1458.4	1452.5	1444.3	1442.4	1433.8	1422.5	1410.6	1397.4	1394.6
7.5°	1551.2	1549.9	1546.2	1545.2	1538.9	1525.2	1511.3	1496.5	1476.8	1457.6	1448.0
10°	1598.6	1613.6	1604.5	1588.6	1591.8	1570.4	1559.0	1539.4	1523.0	1494.3	1488.0
12.5°	1645.2	1651.1	1648.2	1639.1	1635.0	1620.2	1604.9	1587.9	1557.6	1531.9	1509.5
15°	1645.0	1653.7	1655.9	1653.2	1655.5	1654.6	1646.4	1632.3	1605.9	1577.6	1553.1
17.5°	1523.6	1529.6	1544.5	1554.6	1567.4	1594.3	1607.6	1612.7	1608.8	1592.8	1575.5
20°	1387.4	1377.3	1419.2	1440.6	1458.8	1504.3	1543.5	1558.5	1582.6	1582.2	1577.6
22.5°	1194.4	1196.8	1236.4	1261.9	1315.0	1360.5	1405.2	1461.7	1508.3	1539.2	1557.3
25°	877.6	894.9	934.5	969.1	1028.2	1112.9	1189.8	1279.1	1363.2	1429.7	1493.0
27.5°	659.1	660.4	691.8	723.7	758.8	828.2	925.1	1031.6	1151.6	1250.7	1364.7
30°	564.5	561.7	574.9	594.5	624.5	678.2	751.0	855.8	975.4	1124.7	1257.7
32.5°	497.4	497.6	507.6	522.0	547.0	583.2	633.0	718.1	831.3	978.0	1133.8
35°	432.4	431.9	439.3	449.7	460.2	483.4	517.5	562.1	640.0	776.9	936.3
37.5°	385.8	387.8	391.4	397.9	409.5	422.4	442.9	472.9	528.2	609.3	743.2
40°	359.6	360.5	365.5	371.0	377.8	387.8	404.7	428.7	469.3	534.0	631.8
42.5°	335.6	336.4	340.0	345.1	350.4	360.5	374.4	395.3	428.1	478.6	559.3
45°	300.4	300.4	303.6	305.9	311.8	320.9	332.3	349.6	372.4	409.7	463.3
47.5°	267.4	267.5	269.7	273.6	277.3	284.4	295.6	309.7	326.3	355.2	401.0
50°	248.5	249.0	250.3	253.5	255.8	262.2	270.8	283.1	300.4	322.7	361.0
52.5°	233.3	232.9	234.7	236.0	237.6	242.2	248.6	259.5	274.9	294.4	326.0
55°	208.5	206.6	209.4	211.7	213.0	214.8	218.5	225.3	238.5	254.9	278.6
57.5°	177.5	176.8	178.7	180.8	185.1	190.0	193.1	197.4	204.3	216.1	239.5
60°	152.0	152.0	156.1	157.5	162.5	168.9	175.2	178.9	185.7	193.4	210.7
62.5°	129.5	129.8	131.7	133.1	135.9	143.7	152.7	160.7	167.1	174.5	186.0
65°	108.3	109.2	109.2	110.1	112.0	113.8	117.4	123.8	135.2	145.6	154.3
67.5°	91.9	92.2	92.5	93.4	93.9	95.9	97.3	100.1	102.8	112.7	123.4
70°	81.1	82.4	81.9	82.8	83.3	84.2	86.1	87.4	91.5	93.8	100.1
72.5°	70.8	71.8	71.7	72.3	73.5	73.7	75.1	76.5	79.1	81.1	84.4
75°	57.3	56.9	57.3	58.2	58.7	59.2	59.2	61.0	62.3	64.2	66.4
77.5°	44.2	44.7	44.6	44.7	44.8	45.6	45.5	46.4	47.7	48.6	49.7
80°	35.5	35.9	35.5	35.9	36.4	36.8	36.4	36.8	38.3	39.1	39.1
82.5°	27.5	27.6	27.8	27.9	28.0	28.1	28.8	28.9	29.9	29.7	30.1
85°	16.4	16.0	16.0	16.0	16.4	16.9	16.4	16.4	16.9	16.9	16.9
87.5°	11.7	11.9	11.9	11.8	11.7	11.5	11.3	11.4	10.8	10.9	10.2
90°	29.4	29.0	28.4	28.0	27.6	26.7	25.4	24.3	23.0	21.8	19.9
92.5°	29.4	29.2	28.9	28.5	28.3	27.8	27.2	26.6	25.9	25.3	24.3
95°	46.9	47.2	47.3	47.6	47.9	47.3	46.2	44.9	43.8	42.5	40.8
97.5°	62.6	62.3	62.1	61.7	61.4	60.8	59.8	58.9	57.9	57.0	53.1
100°	73.1	72.6	72.1	71.6	71.2	69.9	67.9	66.1	64.1	62.2	58.1
102.5°	78.3	77.7	77.0	76.2	75.6	74.0	71.5	68.9	66.4	63.9	58.4
105°	82.9	81.9	81.0	80.0	79.0	77.2	74.5	71.9	69.2	66.5	58.1
107.5°	85.3	84.4	83.4	82.4	81.4	82.3	85.0	87.7	90.4	93.2	172.5
110°	86.1	85.2	84.3	83.3	82.3	93.9	118.2	142.4	166.7	190.9	260.9



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	87.0	86.2	85.5	84.7	83.9	127.8	216.2	304.6	393.1	481.4	498.8
115°	89.4	106.9	124.4	141.8	159.3	224.1	336.4	448.5	560.8	673.1	667.0
117.5°	365.2	422.6	479.9	537.3	594.6	636.9	664.0	691.2	718.3	745.5	741.3
120°	665.4	698.1	730.8	763.6	796.3	811.2	808.2	805.4	802.5	799.5	795.2
122.5°	830.3	836.7	843.0	849.4	855.7	858.0	856.3	854.5	852.7	851.0	846.3
125°	932.6	931.9	931.2	930.4	929.7	928.5	926.8	925.1	923.5	921.8	917.1
127.5°	997.2	997.0	996.9	996.8	996.7	995.3	992.8	990.3	987.9	985.4	982.0
130°	1037.3	1037.6	1037.9	1038.0	1038.3	1037.1	1034.5	1031.8	1029.1	1026.4	1023.8
132.5°	1076.7	1076.8	1077.1	1077.4	1077.5	1076.6	1074.2	1072.0	1069.7	1067.5	1064.8
135°	1133.4	1133.8	1134.3	1134.8	1135.2	1134.3	1131.8	1129.4	1127.0	1124.6	1122.4
137.5°	1185.0	1185.9	1186.7	1187.5	1188.3	1187.6	1185.2	1182.8	1180.4	1178.0	1175.5
140°	1217.4	1218.5	1219.8	1220.9	1222.2	1221.7	1219.5	1217.4	1215.1	1213.0	1210.3
142.5°	1248.8	1249.9	1251.2	1252.4	1253.6	1253.2	1251.2	1249.2	1247.2	1245.3	1242.2
145°	1292.6	1293.8	1295.0	1296.2	1297.4	1297.2	1295.5	1293.8	1292.1	1290.4	1286.3
147.5°	1331.2	1332.2	1333.2	1334.3	1335.2	1335.2	1333.9	1332.7	1331.4	1330.1	1326.1
150°	1354.8	1355.9	1357.2	1358.4	1359.6	1359.5	1358.1	1356.6	1355.1	1353.7	1349.8
152.5°	1374.8	1376.4	1378.0	1379.7	1381.3	1381.3	1379.8	1378.4	1377.0	1375.5	1371.8
155°	1402.8	1404.7	1406.7	1408.5	1410.5	1410.8	1409.3	1407.8	1406.4	1405.0	1402.0
157.5°	1428.3	1430.2	1432.1	1434.0	1435.8	1436.0	1434.3	1432.7	1431.0	1429.4	1427.4
160°	1443.1	1444.8	1446.5	1448.2	1449.9	1450.0	1448.6	1447.2	1445.6	1444.2	1442.8
162.5°	1455.4	1457.4	1459.5	1461.6	1463.7	1463.9	1462.2	1460.6	1458.9	1457.3	1456.1
165°	1473.6	1475.3	1477.0	1478.7	1480.4	1480.4	1478.7	1477.0	1475.3	1473.6	1472.9
167.5°	1485.2	1487.4	1489.6	1491.7	1494.0	1494.2	1492.5	1490.8	1489.1	1487.4	1486.7
170°	1492.2	1494.4	1496.6	1498.8	1500.9	1501.2	1499.5	1497.8	1496.1	1494.4	1493.9
172.5°	1497.4	1499.6	1501.8	1504.0	1506.2	1506.4	1504.7	1503.0	1501.3	1499.6	1499.1
175°	1502.0	1504.4	1506.9	1509.3	1511.7	1512.1	1510.4	1508.7	1507.0	1505.3	1504.9
177.5°	1504.9	1506.6	1508.3	1510.1	1511.8	1512.1	1510.6	1509.3	1508.0	1506.6	1506.4
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1341.3	1338.4	1335.9	1329.3	1326.1	1318.8	1317.7	1317.3	1307.8	1298.7	1296.2
5°	1387.4	1380.1	1369.1	1356.4	1343.2	1329.5	1320.4	1313.2	1294.9	1277.6	1267.7
7.5°	1433.8	1418.2	1399.3	1375.2	1355.0	1332.5	1315.7	1300.7	1274.9	1250.1	1233.4
10°	1468.4	1442.9	1417.9	1384.6	1358.7	1333.2	1309.6	1289.1	1259.9	1227.2	1203.9
12.5°	1489.9	1461.9	1427.4	1394.8	1361.3	1328.8	1297.2	1270.9	1236.6	1202.7	1175.2
15°	1518.9	1488.9	1447.0	1400.6	1357.4	1315.0	1278.6	1245.8	1201.2	1160.7	1127.0
17.5°	1542.7	1501.4	1456.3	1402.7	1352.6	1298.8	1251.9	1210.1	1160.4	1111.5	1071.8
20°	1550.3	1509.4	1457.5	1403.7	1344.6	1281.3	1230.8	1185.3	1132.0	1078.8	1033.2
22.5°	1545.6	1513.8	1456.0	1391.8	1331.1	1264.9	1207.8	1155.0	1096.0	1041.6	988.8
25°	1513.5	1502.5	1448.0	1377.8	1308.7	1231.7	1165.7	1107.9	1040.5	982.3	924.9
27.5°	1438.5	1462.1	1428.3	1353.6	1276.7	1194.2	1120.0	1054.2	984.3	918.7	861.6
30°	1366.5	1420.6	1406.0	1336.9	1250.8	1169.8	1086.5	1017.8	943.2	875.7	819.3
32.5°	1267.7	1357.3	1371.5	1313.6	1224.6	1135.6	1048.3	979.9	902.0	831.0	776.0
35°	1110.6	1244.5	1305.9	1269.0	1179.8	1083.8	993.6	914.0	835.7	765.6	711.0
37.5°	923.2	1105.5	1207.8	1210.5	1128.5	1028.7	930.6	851.5	771.3	702.5	643.5
40°	801.6	999.1	1132.5	1162.1	1092.9	985.0	885.7	805.2	726.9	659.5	591.7
42.5°	692.3	889.1	1053.1	1104.6	1049.5	942.4	842.8	758.6	682.5	618.8	549.5
45°	559.9	731.9	912.7	1004.6	974.1	874.9	769.7	689.6	618.1	563.0	496.6
47.5°	472.3	593.5	768.4	892.8	892.2	801.6	698.2	621.5	555.3	503.6	449.8
50°	422.4	528.0	675.9	817.1	828.8	752.9	654.5	578.5	516.7	462.4	419.2
52.5°	377.6	464.7	597.6	732.9	766.6	700.8	605.4	535.2	475.1	425.3	388.3
55°	319.1	386.5	487.5	614.0	665.0	618.6	534.0	468.4	419.6	377.8	345.9
57.5°	269.9	320.5	401.5	503.5	562.8	533.6	463.7	410.5	368.8	330.9	305.8
60°	239.0	280.4	349.1	434.3	499.8	479.3	419.6	370.1	334.6	301.8	278.1
62.5°	209.8	245.4	304.3	373.4	433.5	425.1	376.3	334.7	303.6	273.8	253.7
65°	168.9	194.8	240.8	295.0	343.2	347.3	312.3	284.0	256.3	232.6	214.8
67.5°	134.5	151.4	183.8	229.4	265.6	278.5	257.1	235.5	213.5	195.2	179.8
70°	113.3	127.0	150.7	187.5	220.8	234.4	222.1	205.3	186.2	171.1	157.9
72.5°	91.8	105.1	122.6	149.6	178.2	192.9	188.6	176.6	161.0	148.6	136.1
75°	69.2	73.3	85.2	103.3	125.6	138.4	141.6	135.2	122.9	113.3	106.0
77.5°	51.2	53.6	59.3	68.8	83.4	94.8	99.4	98.7	90.2	84.6	77.8
80°	40.9	42.4	45.0	49.1	60.1	71.4	74.6	74.6	68.8	66.4	59.7
82.5°	31.1	32.1	33.8	36.0	41.1	51.1	54.7	55.4	51.6	48.6	43.2
85°	17.7	17.3	18.2	19.5	20.5	23.2	28.7	29.6	28.7	25.1	23.6
87.5°	9.8	9.7	9.4	8.6	8.4	8.2	9.5	10.8	9.9	9.3	9.1
90°	17.9	16.0	14.1	11.8	9.1	6.4	3.7	1.1	3.7	6.4	9.1
92.5°	23.4	22.4	21.4	21.0	21.3	21.6	21.8	22.0	21.8	21.6	21.3
95°	39.1	37.5	35.8	38.9	46.9	54.9	62.9	70.9	62.9	54.9	46.9
97.5°	49.0	45.1	41.2	50.6	73.1	95.6	118.2	140.7	118.2	95.6	73.1
100°	53.9	49.8	45.7	60.3	93.5	126.6	159.9	193.1	159.9	126.6	93.5
102.5°	132.9	167.3	201.8	222.6	229.6	236.6	243.6	250.7	243.6	236.6	229.6
105°	198.9	265.1	331.3	360.7	353.4	346.2	338.9	331.6	338.9	346.2	353.4
107.5°	251.9	331.3	410.6	447.4	441.5	435.6	429.7	423.9	429.7	435.6	441.5
110°	331.0	401.1	471.1	503.5	498.5	493.4	488.3	483.2	488.3	493.4	498.5



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	516.1	533.4	550.7	557.1	552.6	548.0	543.6	539.0	543.6	548.0	552.6
115°	660.9	654.9	648.8	643.7	639.5	635.4	631.3	627.2	631.3	635.4	639.5
117.5°	737.1	732.9	728.8	724.4	719.8	715.2	710.6	706.0	710.6	715.2	719.8
120°	790.9	786.5	782.1	778.1	774.5	770.8	767.2	763.6	767.2	770.8	774.5
122.5°	841.5	836.8	832.1	827.8	823.9	820.1	816.3	812.4	816.3	820.1	823.9
125°	912.5	907.9	903.3	899.4	896.3	893.1	889.9	886.8	889.9	893.1	896.3
127.5°	978.6	975.1	971.7	968.2	964.7	961.2	957.7	954.2	957.7	961.2	964.7
130°	1021.1	1018.4	1015.7	1012.5	1008.6	1004.8	1000.9	997.0	1000.9	1004.8	1008.6
132.5°	1062.1	1059.4	1056.8	1053.8	1050.5	1047.2	1043.9	1040.6	1043.9	1047.2	1050.5
135°	1120.3	1118.0	1115.9	1112.9	1108.9	1105.1	1101.2	1097.3	1101.2	1105.1	1108.9
137.5°	1173.1	1170.6	1168.1	1165.6	1162.9	1160.1	1157.4	1154.7	1157.4	1160.1	1162.9
140°	1207.6	1205.0	1202.3	1200.0	1198.0	1196.1	1194.2	1192.2	1194.2	1196.1	1198.0
142.5°	1239.1	1236.1	1233.1	1230.7	1228.9	1227.2	1225.4	1223.7	1225.4	1227.2	1228.9
145°	1282.2	1278.1	1273.9	1272.0	1272.2	1272.5	1272.7	1272.9	1272.7	1272.5	1272.2
147.5°	1322.0	1317.9	1313.8	1312.2	1313.1	1314.1	1315.0	1315.9	1315.0	1314.1	1313.1
150°	1345.9	1342.0	1338.2	1337.0	1338.7	1340.5	1342.2	1343.9	1342.2	1340.5	1338.7
152.5°	1368.2	1364.4	1360.8	1359.9	1361.7	1363.6	1365.6	1367.4	1365.6	1363.6	1361.7
155°	1399.1	1396.2	1393.3	1392.9	1395.1	1397.3	1399.5	1401.7	1399.5	1397.3	1395.1
157.5°	1425.3	1423.3	1421.2	1421.1	1423.0	1424.8	1426.6	1428.5	1426.6	1424.8	1423.0
160°	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1442.8	1441.3	1439.8
162.5°	1454.7	1453.5	1452.2	1452.3	1453.8	1455.3	1456.7	1458.2	1456.7	1455.3	1453.8
165°	1472.2	1471.5	1470.8	1471.1	1472.6	1474.0	1475.5	1476.9	1475.5	1474.0	1472.6
167.5°	1486.0	1485.4	1484.7	1485.1	1486.6	1488.0	1489.4	1490.9	1489.4	1488.0	1486.6
170°	1493.4	1492.9	1492.5	1492.9	1494.4	1495.8	1497.3	1498.8	1497.3	1495.8	1494.4
172.5°	1498.6	1498.2	1497.7	1498.2	1499.6	1501.1	1502.5	1504.0	1502.5	1501.1	1499.6
175°	1504.3	1503.9	1503.3	1504.0	1505.7	1507.3	1509.0	1510.7	1509.0	1507.3	1505.7
177.5°	1506.2	1506.0	1505.8	1506.4	1507.8	1509.1	1510.5	1511.8	1510.5	1509.1	1507.8
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1291.5	1288.9	1284.2	1276.8	1272.5	1264.8	1259.7	1262.7	1263.4	1262.7	1261.9
5°	1256.8	1247.1	1233.9	1221.2	1209.4	1196.7	1189.4	1186.2	1179.8	1176.2	1174.4
7.5°	1214.8	1198.3	1179.6	1157.4	1138.5	1118.8	1108.8	1103.7	1090.7	1083.6	1077.4
10°	1183.5	1157.5	1138.9	1109.7	1092.0	1066.0	1048.3	1048.7	1031.0	1020.9	1013.7
12.5°	1148.9	1120.3	1089.3	1063.1	1038.4	1017.6	996.2	987.6	968.7	959.0	939.4
15°	1091.5	1058.3	1025.6	990.0	965.0	932.6	901.7	863.9	833.4	807.0	799.8
17.5°	1028.9	987.7	954.8	913.2	870.3	815.9	780.1	758.1	739.8	725.9	715.4
20°	985.9	944.1	909.0	846.1	788.4	751.5	725.1	708.3	689.1	674.1	665.9
22.5°	940.8	897.1	849.3	779.2	734.1	704.5	681.0	661.6	648.7	636.9	629.5
25°	876.6	828.8	750.1	701.9	665.5	634.5	618.1	606.3	592.6	576.7	569.4
27.5°	809.0	732.9	676.4	640.5	605.7	585.6	570.9	553.2	541.0	533.9	526.3
30°	758.3	682.3	638.2	599.1	574.4	552.1	534.8	524.9	513.0	500.7	495.7
32.5°	701.9	641.1	598.9	566.2	541.3	522.3	508.6	492.4	483.8	476.3	465.8
35°	631.8	585.9	547.2	520.8	497.0	481.6	465.7	456.1	440.6	434.3	430.2
37.5°	572.4	532.5	503.7	475.8	457.1	440.0	430.3	415.0	408.3	399.5	390.8
40°	539.0	499.8	472.0	449.2	428.3	415.5	403.3	391.0	380.9	376.9	366.4
42.5°	504.7	472.9	445.1	420.1	406.1	392.6	377.1	368.1	357.7	351.1	344.6
45°	457.4	429.3	405.6	385.0	369.6	355.5	345.4	330.5	324.6	311.3	305.9
47.5°	416.0	389.7	367.1	347.7	332.5	323.3	308.7	296.9	287.5	279.4	272.4
50°	386.5	364.6	342.8	325.5	311.8	298.6	283.6	277.7	263.1	259.0	254.9
52.5°	359.5	338.8	318.7	301.8	288.1	275.3	262.1	254.3	244.5	240.4	237.5
55°	321.8	301.8	282.7	267.6	254.0	240.8	232.6	223.0	218.5	215.3	211.7
57.5°	283.9	265.9	251.3	236.0	222.3	211.9	202.3	196.6	191.9	187.7	183.3
60°	259.9	242.6	229.4	215.3	201.2	192.5	185.3	178.4	173.0	166.6	164.8
62.5°	234.4	219.3	207.2	193.4	181.2	173.3	166.3	159.9	153.3	144.0	141.4
65°	199.4	187.5	174.8	163.5	152.5	144.7	134.7	127.4	124.8	123.8	123.3
67.5°	167.7	156.5	145.5	133.9	123.9	116.8	111.7	110.6	108.7	108.2	106.9
70°	146.6	136.1	125.2	114.2	104.7	103.3	101.5	99.7	97.4	96.5	95.6
72.5°	127.6	116.8	105.8	97.1	93.0	91.3	89.5	87.7	86.1	85.2	84.6
75°	97.8	87.8	80.6	77.4	75.1	73.7	71.0	69.6	68.8	67.3	66.9
77.5°	70.4	64.8	61.4	59.5	57.1	55.6	54.0	52.7	51.7	51.5	50.7
80°	53.7	51.0	48.7	46.0	45.0	43.2	42.8	41.5	41.9	40.5	40.5
82.5°	41.7	38.3	36.3	35.0	34.2	32.7	32.2	31.6	31.7	30.7	30.7
85°	21.4	20.5	19.5	18.6	18.6	17.3	17.7	17.3	17.3	16.4	16.0
87.5°	9.3	9.4	9.0	9.5	9.8	9.8	10.1	10.0	10.2	10.4	10.3
90°	11.8	14.1	16.0	17.9	19.9	21.8	23.0	24.3	25.4	26.7	27.6
92.5°	21.0	21.4	22.4	23.4	24.3	25.3	25.9	26.6	27.2	27.8	28.3
95°	38.9	35.8	37.5	39.1	40.8	42.5	43.8	44.9	46.2	47.3	47.9
97.5°	50.6	41.2	45.1	49.0	53.1	57.0	57.9	58.9	59.8	60.8	61.4
100°	60.3	45.7	49.8	53.9	58.1	62.2	64.1	66.1	67.9	69.9	71.2
102.5°	222.6	201.8	167.3	132.9	98.4	63.9	66.4	68.9	71.5	74.0	75.6
105°	360.7	331.3	265.1	198.9	132.7	66.5	69.2	71.9	74.5	77.2	79.0
107.5°	447.4	410.6	331.3	251.9	172.5	93.2	90.4	87.7	85.0	82.3	81.4
110°	503.5	471.1	401.1	331.0	260.9	190.9	166.7	142.4	118.2	93.9	82.3



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	557.1	550.7	533.4	516.1	498.8	481.4	393.1	304.6	216.2	127.8	83.9
115°	643.7	648.8	654.9	660.9	667.0	673.1	560.8	448.5	336.4	224.1	159.3
117.5°	724.4	728.8	732.9	737.1	741.3	745.5	718.3	691.2	664.0	636.9	594.6
120°	778.1	782.1	786.5	790.9	795.2	799.5	802.5	805.4	808.2	811.2	796.3
122.5°	827.8	832.1	836.8	841.5	846.3	851.0	852.7	854.5	856.3	858.0	855.7
125°	899.4	903.3	907.9	912.5	917.1	921.8	923.5	925.1	926.8	928.5	929.7
127.5°	968.2	971.7	975.1	978.6	982.0	985.4	987.9	990.3	992.8	995.3	996.7
130°	1012.5	1015.7	1018.4	1021.1	1023.8	1026.4	1029.1	1031.8	1034.5	1037.1	1038.3
132.5°	1053.8	1056.8	1059.4	1062.1	1064.8	1067.5	1069.7	1072.0	1074.2	1076.6	1077.5
135°	1112.9	1115.9	1118.0	1120.3	1122.4	1124.6	1127.0	1129.4	1131.8	1134.3	1135.2
137.5°	1165.6	1168.1	1170.6	1173.1	1175.5	1178.0	1180.4	1182.8	1185.2	1187.6	1188.3
140°	1200.0	1202.3	1205.0	1207.6	1210.3	1213.0	1215.1	1217.4	1219.5	1221.7	1222.2
142.5°	1230.7	1233.1	1236.1	1239.1	1242.2	1245.3	1247.2	1249.2	1251.2	1253.2	1253.6
145°	1272.0	1273.9	1278.1	1282.2	1286.3	1290.4	1292.1	1293.8	1295.5	1297.2	1297.4
147.5°	1312.2	1313.8	1317.9	1322.0	1326.1	1330.1	1331.4	1332.7	1333.9	1335.2	1335.2
150°	1337.0	1338.2	1342.0	1345.9	1349.8	1353.7	1355.1	1356.6	1358.1	1359.5	1359.6
152.5°	1359.9	1360.8	1364.4	1368.2	1371.8	1375.5	1377.0	1378.4	1379.8	1381.3	1381.3
155°	1392.9	1393.3	1396.2	1399.1	1402.0	1405.0	1406.4	1407.8	1409.3	1410.8	1410.5
157.5°	1421.1	1421.2	1423.3	1425.3	1427.4	1429.4	1431.0	1432.7	1434.3	1436.0	1435.8
160°	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1445.6	1447.2	1448.6	1450.0	1449.9
162.5°	1452.3	1452.2	1453.5	1454.7	1456.1	1457.3	1458.9	1460.6	1462.2	1463.9	1463.7
165°	1471.1	1470.8	1471.5	1472.2	1472.9	1473.6	1475.3	1477.0	1478.7	1480.4	1480.4
167.5°	1485.1	1484.7	1485.4	1486.0	1486.7	1487.4	1489.1	1490.8	1492.5	1494.2	1494.0
170°	1492.9	1492.5	1492.9	1493.4	1493.9	1494.4	1496.1	1497.8	1499.5	1501.2	1500.9
172.5°	1498.2	1497.7	1498.2	1498.6	1499.1	1499.6	1501.3	1503.0	1504.7	1506.4	1506.2
175°	1504.0	1503.3	1503.9	1504.3	1504.9	1505.3	1507.0	1508.7	1510.4	1512.1	1511.7
177.5°	1506.4	1505.8	1506.0	1506.2	1506.4	1506.6	1508.0	1509.3	1510.6	1512.1	1511.8
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1257.9	1258.6	1257.6	1258.3	1257.6	1258.6	1257.9	1261.9	1262.7	1263.4	1262.7
5°	1172.1	1166.6	1165.7	1164.3	1165.7	1166.6	1172.1	1174.4	1176.2	1179.8	1186.2
7.5°	1069.6	1068.7	1066.5	1063.3	1066.5	1068.7	1069.6	1077.4	1083.6	1090.7	1103.7
10°	1003.6	1001.4	1000.9	997.7	1000.9	1001.4	1003.6	1013.7	1020.9	1031.0	1048.7
12.5°	926.5	911.8	910.3	902.3	910.3	911.8	926.5	939.4	959.0	968.7	987.6
15°	788.8	786.1	776.9	771.1	776.9	786.1	788.8	799.8	807.0	833.4	863.9
17.5°	710.2	701.2	698.4	697.1	698.4	701.2	710.2	715.4	725.9	739.8	758.1
20°	659.5	651.4	650.0	649.1	650.0	651.4	659.5	665.9	674.1	689.1	708.3
22.5°	624.6	616.0	612.5	609.8	612.5	616.0	624.6	629.5	636.9	648.7	661.6
25°	564.9	561.7	559.9	558.9	559.9	561.7	564.9	569.4	576.7	592.6	606.3
27.5°	518.2	511.1	509.8	507.5	509.8	511.1	518.2	526.3	533.9	541.0	553.2
30°	491.6	489.3	486.2	483.4	486.2	489.3	491.6	495.7	500.7	513.0	524.9
32.5°	460.3	458.3	455.6	454.2	455.6	458.3	460.3	465.8	476.3	483.8	492.4
35°	425.6	419.2	416.5	412.4	416.5	419.2	425.6	430.2	434.3	440.6	456.1
37.5°	388.9	385.6	381.7	383.1	381.7	385.6	388.9	390.8	399.5	408.3	415.0
40°	360.5	358.2	357.3	356.9	357.3	358.2	360.5	366.4	376.9	380.9	391.0
42.5°	338.0	331.6	329.3	329.2	329.3	331.6	338.0	344.6	351.1	357.7	368.1
45°	303.6	297.7	293.6	294.1	293.6	297.7	303.6	305.9	311.3	324.6	330.5
47.5°	268.5	268.3	265.7	266.5	265.7	268.3	268.5	272.4	279.4	287.5	296.9
50°	251.7	249.0	247.2	247.6	247.2	249.0	251.7	254.9	259.0	263.1	277.7
52.5°	235.7	233.4	231.8	233.8	231.8	233.4	235.7	237.5	240.4	244.5	254.3
55°	209.4	206.6	206.2	205.7	206.2	206.6	209.4	211.7	215.3	218.5	223.0
57.5°	179.9	178.2	175.4	174.2	175.4	178.2	179.9	183.3	187.7	191.9	196.6
60°	158.8	155.2	150.7	150.2	150.7	155.2	158.8	164.8	166.6	173.0	178.4
62.5°	139.6	138.8	137.9	137.9	137.9	138.8	139.6	141.4	144.0	153.3	159.9
65°	122.4	122.0	122.4	122.9	122.4	122.0	122.4	123.3	123.8	124.8	127.4
67.5°	106.7	105.8	105.0	105.4	105.0	105.8	106.7	106.9	108.2	108.7	110.6
70°	94.7	94.3	93.8	93.8	93.8	94.3	94.7	95.6	96.5	97.4	99.7
72.5°	83.0	82.9	82.5	82.1	82.5	82.9	83.0	84.6	85.2	86.1	87.7
75°	66.4	65.5	65.5	65.5	65.5	65.5	66.4	66.9	67.3	68.8	69.6
77.5°	50.6	50.2	49.7	49.3	49.7	50.2	50.6	50.7	51.5	51.7	52.7
80°	40.0	39.6	39.1	39.1	39.1	39.6	40.0	40.5	40.5	41.9	41.5
82.5°	30.6	30.1	30.1	29.7	30.1	30.1	30.6	30.7	30.7	31.7	31.6
85°	16.4	16.9	16.4	17.3	16.4	16.9	16.4	16.0	16.4	17.3	17.3
87.5°	10.3	10.1	10.5	10.3	10.5	10.1	10.3	10.3	10.4	10.2	10.0
90°	28.0	28.4	29.0	29.4	29.0	28.4	28.0	27.6	26.7	25.4	24.3
92.5°	28.5	28.9	29.2	29.4	29.2	28.9	28.5	28.3	27.8	27.2	26.6
95°	47.6	47.3	47.2	46.9	47.2	47.3	47.6	47.9	47.3	46.2	44.9
97.5°	61.7	62.1	62.3	62.6	62.3	62.1	61.7	61.4	60.8	59.8	58.9
100°	71.6	72.1	72.6	73.1	72.6	72.1	71.6	71.2	69.9	67.9	66.1
102.5°	76.2	77.0	77.7	78.3	77.7	77.0	76.2	75.6	74.0	71.5	68.9
105°	80.0	81.0	81.9	82.9	81.9	81.0	80.0	79.0	77.2	74.5	71.9
107.5°	82.4	83.4	84.4	85.3	84.4	83.4	82.4	81.4	82.3	85.0	87.7
110°	83.3	84.3	85.2	86.1	85.2	84.3	83.3	82.3	93.9	118.2	142.4



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	84.7	85.5	86.2	87.0	86.2	85.5	84.7	83.9	127.8	216.2	304.6
115°	141.8	124.4	106.9	89.4	106.9	124.4	141.8	159.3	224.1	336.4	448.5
117.5°	537.3	479.9	422.6	365.2	422.6	479.9	537.3	594.6	636.9	664.0	691.2
120°	763.6	730.8	698.1	665.4	698.1	730.8	763.6	796.3	811.2	808.2	805.4
122.5°	849.4	843.0	836.7	830.3	836.7	843.0	849.4	855.7	858.0	856.3	854.5
125°	930.4	931.2	931.9	932.6	931.9	931.2	930.4	929.7	928.5	926.8	925.1
127.5°	996.8	996.9	997.0	997.2	997.0	996.9	996.8	996.7	995.3	992.8	990.3
130°	1038.0	1037.9	1037.6	1037.3	1037.6	1037.9	1038.0	1038.3	1037.1	1034.5	1031.8
132.5°	1077.4	1077.1	1076.8	1076.7	1076.8	1077.1	1077.4	1077.5	1076.6	1074.2	1072.0
135°	1134.8	1134.3	1133.8	1133.4	1133.8	1134.3	1134.8	1135.2	1134.3	1131.8	1129.4
137.5°	1187.5	1186.7	1185.9	1185.0	1185.9	1186.7	1187.5	1188.3	1187.6	1185.2	1182.8
140°	1220.9	1219.8	1218.5	1217.4	1218.5	1219.8	1220.9	1222.2	1221.7	1219.5	1217.4
142.5°	1252.4	1251.2	1249.9	1248.8	1249.9	1251.2	1252.4	1253.6	1253.2	1251.2	1249.2
145°	1296.2	1295.0	1293.8	1292.6	1293.8	1295.0	1296.2	1297.4	1297.2	1295.5	1293.8
147.5°	1334.3	1333.2	1332.2	1331.2	1332.2	1333.2	1334.3	1335.2	1335.2	1333.9	1332.7
150°	1358.4	1357.2	1355.9	1354.8	1355.9	1357.2	1358.4	1359.6	1359.5	1358.1	1356.6
152.5°	1379.7	1378.0	1376.4	1374.8	1376.4	1378.0	1379.7	1381.3	1381.3	1379.8	1378.4
155°	1408.5	1406.7	1404.7	1402.8	1404.7	1406.7	1408.5	1410.5	1410.8	1409.3	1407.8
157.5°	1434.0	1432.1	1430.2	1428.3	1430.2	1432.1	1434.0	1435.8	1436.0	1434.3	1432.7
160°	1448.2	1446.5	1444.8	1443.1	1444.8	1446.5	1448.2	1449.9	1450.0	1448.6	1447.2
162.5°	1461.6	1459.5	1457.4	1455.4	1457.4	1459.5	1461.6	1463.7	1463.9	1462.2	1460.6
165°	1478.7	1477.0	1475.3	1473.6	1475.3	1477.0	1478.7	1480.4	1480.4	1478.7	1477.0
167.5°	1491.7	1489.6	1487.4	1485.2	1487.4	1489.6	1491.7	1494.0	1494.2	1492.5	1490.8
170°	1498.8	1496.6	1494.4	1492.2	1494.4	1496.6	1498.8	1500.9	1501.2	1499.5	1497.8
172.5°	1504.0	1501.8	1499.6	1497.4	1499.6	1501.8	1504.0	1506.2	1506.4	1504.7	1503.0
175°	1509.3	1506.9	1504.4	1502.0	1504.4	1506.9	1509.3	1511.7	1512.1	1510.4	1508.7
177.5°	1510.1	1508.3	1506.6	1504.9	1506.6	1508.3	1510.1	1511.8	1512.1	1510.6	1509.3
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1259.7	1264.8	1272.5	1276.8	1284.2	1288.9	1291.5	1296.2	1298.7	1307.8	1317.3
5°	1189.4	1196.7	1209.4	1221.2	1233.9	1247.1	1256.8	1267.7	1277.6	1294.9	1313.2
7.5°	1108.8	1118.8	1138.5	1157.4	1179.6	1198.3	1214.8	1233.4	1250.1	1274.9	1300.7
10°	1048.3	1066.0	1092.0	1109.7	1138.9	1157.5	1183.5	1203.9	1227.2	1259.9	1289.1
12.5°	996.2	1017.6	1038.4	1063.1	1089.3	1120.3	1148.9	1175.2	1202.7	1236.6	1270.9
15°	901.7	932.6	965.0	990.0	1025.6	1058.3	1091.5	1127.0	1160.7	1201.2	1245.8
17.5°	780.1	815.9	870.3	913.2	954.8	987.7	1028.9	1071.8	1111.5	1160.4	1210.1
20°	725.1	751.5	788.4	846.1	909.0	944.1	985.9	1033.2	1078.8	1132.0	1185.3
22.5°	681.0	704.5	734.1	779.2	849.3	897.1	940.8	988.8	1041.6	1096.0	1155.0
25°	618.1	634.5	665.5	701.9	750.1	828.8	876.6	924.9	982.3	1040.5	1107.9
27.5°	570.9	585.6	605.7	640.5	676.4	732.9	809.0	861.6	918.7	984.3	1054.2
30°	534.8	552.1	574.4	599.1	638.2	682.3	758.3	819.3	875.7	943.2	1017.8
32.5°	508.6	522.3	541.3	566.2	598.9	641.1	701.9	776.0	831.0	902.0	979.9
35°	465.7	481.6	497.0	520.8	547.2	585.9	631.8	711.0	765.6	835.7	914.0
37.5°	430.3	440.0	457.1	475.8	503.7	532.5	572.4	643.5	702.5	771.3	851.5
40°	403.3	415.5	428.3	449.2	472.0	499.8	539.0	591.7	659.5	726.9	805.2
42.5°	377.1	392.6	406.1	420.1	445.1	472.9	504.7	549.5	618.8	682.5	758.6
45°	345.4	355.5	369.6	385.0	405.6	429.3	457.4	496.6	563.0	618.1	689.6
47.5°	308.7	323.3	332.5	347.7	367.1	389.7	416.0	449.8	503.6	555.3	621.5
50°	283.6	298.6	311.8	325.5	342.8	364.6	386.5	419.2	462.4	516.7	578.5
52.5°	262.1	275.3	288.1	301.8	318.7	338.8	359.5	388.3	425.3	475.1	535.2
55°	232.6	240.8	254.0	267.6	282.7	301.8	321.8	345.9	377.8	419.6	468.4
57.5°	202.3	211.9	222.3	236.0	251.3	265.9	283.9	305.8	330.9	368.8	410.5
60°	185.3	192.5	201.2	215.3	229.4	242.6	259.9	278.1	301.8	334.6	370.1
62.5°	166.3	173.3	181.2	193.4	207.2	219.3	234.4	253.7	273.8	303.6	334.7
65°	134.7	144.7	152.5	163.5	174.8	187.5	199.4	214.8	232.6	256.3	284.0
67.5°	111.7	116.8	123.9	133.9	145.5	156.5	167.7	179.8	195.2	213.5	235.5
70°	101.5	103.3	104.7	114.2	125.2	136.1	146.6	157.9	171.1	186.2	205.3
72.5°	89.5	91.3	93.0	97.1	105.8	116.8	127.6	136.1	148.6	161.0	176.6
75°	71.0	73.7	75.1	77.4	80.6	87.8	97.8	106.0	113.3	122.9	135.2
77.5°	54.0	55.6	57.1	59.5	61.4	64.8	70.4	77.8	84.6	90.2	98.7
80°	42.8	43.2	45.0	46.0	48.7	51.0	53.7	59.7	66.4	68.8	74.6
82.5°	32.2	32.7	34.2	35.0	36.3	38.3	41.7	43.2	48.6	51.6	55.4
85°	17.7	17.3	18.6	18.6	19.5	20.5	21.4	23.6	25.1	28.7	29.6
87.5°	10.1	9.8	9.8	9.5	9.0	9.4	9.3	9.1	9.3	9.9	10.8
90°	23.0	21.8	19.9	17.9	16.0	14.1	11.8	9.1	6.4	3.7	1.1
92.5°	25.9	25.3	24.3	23.4	22.4	21.4	21.0	21.3	21.6	21.8	22.0
95°	43.8	42.5	40.8	39.1	37.5	35.8	38.9	46.9	54.9	62.9	70.9
97.5°	57.9	57.0	53.1	49.0	45.1	41.2	50.6	73.1	95.6	118.2	140.7
100°	64.1	62.2	58.1	53.9	49.8	45.7	60.3	93.5	126.6	159.9	193.1
102.5°	66.4	63.9	98.4	132.9	167.3	201.8	222.6	229.6	236.6	243.6	250.7
105°	69.2	66.5	132.7	198.9	265.1	331.3	360.7	353.4	346.2	338.9	331.6
107.5°	90.4	93.2	172.5	251.9	331.3	410.6	447.4	441.5	435.6	429.7	423.9
110°	166.7	190.9	260.9	331.0	401.1	471.1	503.5	498.5	493.4	488.3	483.2



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	393.1	481.4	498.8	516.1	533.4	550.7	557.1	552.6	548.0	543.6	539.0
115°	560.8	673.1	667.0	660.9	654.9	648.8	643.7	639.5	635.4	631.3	627.2
117.5°	718.3	745.5	741.3	737.1	732.9	728.8	724.4	719.8	715.2	710.6	706.0
120°	802.5	799.5	795.2	790.9	786.5	782.1	778.1	774.5	770.8	767.2	763.6
122.5°	852.7	851.0	846.3	841.5	836.8	832.1	827.8	823.9	820.1	816.3	812.4
125°	923.5	921.8	917.1	912.5	907.9	903.3	899.4	896.3	893.1	889.9	886.8
127.5°	987.9	985.4	982.0	978.6	975.1	971.7	968.2	964.7	961.2	957.7	954.2
130°	1029.1	1026.4	1023.8	1021.1	1018.4	1015.7	1012.5	1008.6	1004.8	1000.9	997.0
132.5°	1069.7	1067.5	1064.8	1062.1	1059.4	1056.8	1053.8	1050.5	1047.2	1043.9	1040.6
135°	1127.0	1124.6	1122.4	1120.3	1118.0	1115.9	1112.9	1108.9	1105.1	1101.2	1097.3
137.5°	1180.4	1178.0	1175.5	1173.1	1170.6	1168.1	1165.6	1162.9	1160.1	1157.4	1154.7
140°	1215.1	1213.0	1210.3	1207.6	1205.0	1202.3	1200.0	1198.0	1196.1	1194.2	1192.2
142.5°	1247.2	1245.3	1242.2	1239.1	1236.1	1233.1	1230.7	1228.9	1227.2	1225.4	1223.7
145°	1292.1	1290.4	1286.3	1282.2	1278.1	1273.9	1272.0	1272.2	1272.5	1272.7	1272.9
147.5°	1331.4	1330.1	1326.1	1322.0	1317.9	1313.8	1312.2	1313.1	1314.1	1315.0	1315.9
150°	1355.1	1353.7	1349.8	1345.9	1342.0	1338.2	1337.0	1338.7	1340.5	1342.2	1343.9
152.5°	1377.0	1375.5	1371.8	1368.2	1364.4	1360.8	1359.9	1361.7	1363.6	1365.6	1367.4
155°	1406.4	1405.0	1402.0	1399.1	1396.2	1393.3	1392.9	1395.1	1397.3	1399.5	1401.7
157.5°	1431.0	1429.4	1427.4	1425.3	1423.3	1421.2	1421.1	1423.0	1424.8	1426.6	1428.5
160°	1445.6	1444.2	1442.8	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2
162.5°	1458.9	1457.3	1456.1	1454.7	1453.5	1452.2	1452.3	1453.8	1455.3	1456.7	1458.2
165°	1475.3	1473.6	1472.9	1472.2	1471.5	1470.8	1471.1	1472.6	1474.0	1475.5	1476.9
167.5°	1489.1	1487.4	1486.7	1486.0	1485.4	1484.7	1485.1	1486.6	1488.0	1489.4	1490.9
170°	1496.1	1494.4	1493.9	1493.4	1492.9	1492.5	1492.9	1494.4	1495.8	1497.3	1498.8
172.5°	1501.3	1499.6	1499.1	1498.6	1498.2	1497.7	1498.2	1499.6	1501.1	1502.5	1504.0
175°	1507.0	1505.3	1504.9	1504.3	1503.9	1503.3	1504.0	1505.7	1507.3	1509.0	1510.7
177.5°	1508.0	1506.6	1506.4	1506.2	1506.0	1505.8	1506.4	1507.8	1509.1	1510.5	1511.8
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1317.7	1318.8	1326.1	1329.3	1335.9	1338.4	1341.3	1340.6	1340.6	1342.0	1352.3
5°	1320.4	1329.5	1343.2	1356.4	1369.1	1380.1	1387.4	1394.6	1397.4	1410.6	1422.5
7.5°	1315.7	1332.5	1355.0	1375.2	1399.3	1418.2	1433.8	1448.0	1457.6	1476.8	1496.5
10°	1309.6	1333.2	1358.7	1384.6	1417.9	1442.9	1468.4	1488.0	1494.3	1523.0	1539.4
12.5°	1297.2	1328.8	1361.3	1394.8	1427.4	1461.9	1489.9	1509.5	1531.9	1557.6	1587.9
15°	1278.6	1315.0	1357.4	1400.6	1447.0	1488.9	1518.9	1553.1	1577.6	1605.9	1632.3
17.5°	1251.9	1298.8	1352.6	1402.7	1456.3	1501.4	1542.7	1575.5	1592.8	1608.8	1612.7
20°	1230.8	1281.3	1344.6	1403.7	1457.5	1509.4	1550.3	1577.6	1582.2	1582.6	1558.5
22.5°	1207.8	1264.9	1331.1	1391.8	1456.0	1513.8	1545.6	1557.3	1539.2	1508.3	1461.7
25°	1165.7	1231.7	1308.7	1377.8	1448.0	1502.5	1513.5	1493.0	1429.7	1363.2	1279.1
27.5°	1120.0	1194.2	1276.7	1353.6	1428.3	1462.1	1438.5	1364.7	1250.7	1151.6	1031.6
30°	1086.5	1169.8	1250.8	1336.9	1406.0	1420.6	1366.5	1257.7	1124.7	975.4	855.8
32.5°	1048.3	1135.6	1224.6	1313.6	1371.5	1357.3	1267.7	1133.8	978.0	831.3	718.1
35°	993.6	1083.8	1179.8	1269.0	1305.9	1244.5	1110.6	936.3	776.9	640.0	562.1
37.5°	930.6	1028.7	1128.5	1210.5	1207.8	1105.5	923.2	743.2	609.3	528.2	472.9
40°	885.7	985.0	1092.9	1162.1	1132.5	999.1	801.6	631.8	534.0	469.3	428.7
42.5°	842.8	942.4	1049.5	1104.6	1053.1	889.1	692.3	559.3	478.6	428.1	395.3
45°	769.7	874.9	974.1	1004.6	912.7	731.9	559.9	463.3	409.7	372.4	349.6
47.5°	698.2	801.6	892.2	892.8	768.4	593.5	472.3	401.0	355.2	326.3	309.7
50°	654.5	752.9	828.8	817.1	675.9	528.0	422.4	361.0	322.7	300.4	283.1
52.5°	605.4	700.8	766.6	732.9	597.6	464.7	377.6	326.0	294.4	274.9	259.5
55°	534.0	618.6	665.0	614.0	487.5	386.5	319.1	278.6	254.9	238.5	225.3
57.5°	463.7	533.6	562.8	503.5	401.5	320.5	269.9	239.5	216.1	204.3	197.4
60°	419.6	479.3	499.8	434.3	349.1	280.4	239.0	210.7	193.4	185.7	178.9
62.5°	376.3	425.1	433.5	373.4	304.3	245.4	209.8	186.0	174.5	167.1	160.7
65°	312.3	347.3	343.2	295.0	240.8	194.8	168.9	154.3	145.6	135.2	123.8
67.5°	257.1	278.5	265.6	229.4	183.8	151.4	134.5	123.4	112.7	102.8	100.1
70°	222.1	234.4	220.8	187.5	150.7	127.0	113.3	100.1	93.8	91.5	87.4
72.5°	188.6	192.9	178.2	149.6	122.6	105.1	91.8	84.4	81.1	79.1	76.5
75°	141.6	138.4	125.6	103.3	85.2	73.3	69.2	66.4	64.2	62.3	61.0
77.5°	99.4	94.8	83.4	68.8	59.3	53.6	51.2	49.7	48.6	47.7	46.4
80°	74.6	71.4	60.1	49.1	45.0	42.4	40.9	39.1	39.1	38.3	36.8
82.5°	54.7	51.1	41.1	36.0	33.8	32.1	31.1	30.1	29.7	29.9	28.9
85°	28.7	23.2	20.5	19.5	18.2	17.3	17.7	16.9	16.9	16.9	16.4
87.5°	9.5	8.2	8.4	8.6	9.4	9.7	9.8	10.2	10.9	10.8	11.4
90°	3.7	6.4	9.1	11.8	14.1	16.0	17.9	19.9	21.8	23.0	24.3
92.5°	21.8	21.6	21.3	21.0	21.4	22.4	23.4	24.3	25.3	25.9	26.6
95°	62.9	54.9	46.9	38.9	35.8	37.5	39.1	40.8	42.5	43.8	44.9
97.5°	118.2	95.6	73.1	50.6	41.2	45.1	49.0	53.1	57.0	57.9	58.9
100°	159.9	126.6	93.5	60.3	45.7	49.8	53.9	58.1	62.2	64.1	66.1
102.5°	243.6	236.6	229.6	222.6	201.8	167.3	132.9	98.4	63.9	66.4	68.9
105°	338.9	346.2	353.4	360.7	331.3	265.1	198.9	132.7	66.5	69.2	71.9
107.5°	429.7	435.6	441.5	447.4	410.6	331.3	251.9	172.5	93.2	90.4	87.7
110°	488.3	493.4	498.5	503.5	471.1	401.1	331.0	260.9	190.9	166.7	142.4



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	543.6	548.0	552.6	557.1	550.7	533.4	516.1	498.8	481.4	393.1	304.6
115°	631.3	635.4	639.5	643.7	648.8	654.9	660.9	667.0	673.1	560.8	448.5
117.5°	710.6	715.2	719.8	724.4	728.8	732.9	737.1	741.3	745.5	718.3	691.2
120°	767.2	770.8	774.5	778.1	782.1	786.5	790.9	795.2	799.5	802.5	805.4
122.5°	816.3	820.1	823.9	827.8	832.1	836.8	841.5	846.3	851.0	852.7	854.5
125°	889.9	893.1	896.3	899.4	903.3	907.9	912.5	917.1	921.8	923.5	925.1
127.5°	957.7	961.2	964.7	968.2	971.7	975.1	978.6	982.0	985.4	987.9	990.3
130°	1000.9	1004.8	1008.6	1012.5	1015.7	1018.4	1021.1	1023.8	1026.4	1029.1	1031.8
132.5°	1043.9	1047.2	1050.5	1053.8	1056.8	1059.4	1062.1	1064.8	1067.5	1069.7	1072.0
135°	1101.2	1105.1	1108.9	1112.9	1115.9	1118.0	1120.3	1122.4	1124.6	1127.0	1129.4
137.5°	1157.4	1160.1	1162.9	1165.6	1168.1	1170.6	1173.1	1175.5	1178.0	1180.4	1182.8
140°	1194.2	1196.1	1198.0	1200.0	1202.3	1205.0	1207.6	1210.3	1213.0	1215.1	1217.4
142.5°	1225.4	1227.2	1228.9	1230.7	1233.1	1236.1	1239.1	1242.2	1245.3	1247.2	1249.2
145°	1272.7	1272.5	1272.2	1272.0	1273.9	1278.1	1282.2	1286.3	1290.4	1292.1	1293.8
147.5°	1315.0	1314.1	1313.1	1312.2	1313.8	1317.9	1322.0	1326.1	1330.1	1331.4	1332.7
150°	1342.2	1340.5	1338.7	1337.0	1338.2	1342.0	1345.9	1349.8	1353.7	1355.1	1356.6
152.5°	1365.6	1363.6	1361.7	1359.9	1360.8	1364.4	1368.2	1371.8	1375.5	1377.0	1378.4
155°	1399.5	1397.3	1395.1	1392.9	1393.3	1396.2	1399.1	1402.0	1405.0	1406.4	1407.8
157.5°	1426.6	1424.8	1423.0	1421.1	1421.2	1423.3	1425.3	1427.4	1429.4	1431.0	1432.7
160°	1442.8	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1445.6	1447.2
162.5°	1456.7	1455.3	1453.8	1452.3	1452.2	1453.5	1454.7	1456.1	1457.3	1458.9	1460.6
165°	1475.5	1474.0	1472.6	1471.1	1470.8	1471.5	1472.2	1472.9	1473.6	1475.3	1477.0
167.5°	1489.4	1488.0	1486.6	1485.1	1484.7	1485.4	1486.0	1486.7	1487.4	1489.1	1490.8
170°	1497.3	1495.8	1494.4	1492.9	1492.5	1492.9	1493.4	1493.9	1494.4	1496.1	1497.8
172.5°	1502.5	1501.1	1499.6	1498.2	1497.7	1498.2	1498.6	1499.1	1499.6	1501.3	1503.0
175°	1509.0	1507.3	1505.7	1504.0	1503.3	1503.9	1504.3	1504.9	1505.3	1507.0	1508.7
177.5°	1510.5	1509.1	1507.8	1506.4	1505.8	1506.0	1506.2	1506.4	1506.6	1508.0	1509.3
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1355.8	1360.6	1362.8	1362.8	1365.4	1364.2	1363.2
5°	1433.8	1442.4	1444.3	1452.5	1458.4	1456.5	1457.5
7.5°	1511.3	1525.2	1538.9	1545.2	1546.2	1549.9	1551.2
10°	1559.0	1570.4	1591.8	1588.6	1604.5	1613.6	1598.6
12.5°	1604.9	1620.2	1635.0	1639.1	1648.2	1651.1	1645.2
15°	1646.4	1654.6	1655.5	1653.2	1655.9	1653.7	1645.0
17.5°	1607.6	1594.3	1567.4	1554.6	1544.5	1529.6	1523.6
20°	1543.5	1504.3	1458.8	1440.6	1419.2	1377.3	1387.4
22.5°	1405.2	1360.5	1315.0	1261.9	1236.4	1196.8	1194.4
25°	1189.8	1112.9	1028.2	969.1	934.5	894.9	877.6
27.5°	925.1	828.2	758.8	723.7	691.8	660.4	659.1
30°	751.0	678.2	624.5	594.5	574.9	561.7	564.5
32.5°	633.0	583.2	547.0	522.0	507.6	497.6	497.4
35°	517.5	483.4	460.2	449.7	439.3	431.9	432.4
37.5°	442.9	422.4	409.5	397.9	391.4	387.8	385.8
40°	404.7	387.8	377.8	371.0	365.5	360.5	359.6
42.5°	374.4	360.5	350.4	345.1	340.0	336.4	335.6
45°	332.3	320.9	311.8	305.9	303.6	300.4	300.4
47.5°	295.6	284.4	277.3	273.6	269.7	267.5	267.4
50°	270.8	262.2	255.8	253.5	250.3	249.0	248.5
52.5°	248.6	242.2	237.6	236.0	234.7	232.9	233.3
55°	218.5	214.8	213.0	211.7	209.4	206.6	208.5
57.5°	193.1	190.0	185.1	180.8	178.7	176.8	177.5
60°	175.2	168.9	162.5	157.5	156.1	152.0	152.0
62.5°	152.7	143.7	135.9	133.1	131.7	129.8	129.5
65°	117.4	113.8	112.0	110.1	109.2	109.2	108.3
67.5°	97.3	95.9	93.9	93.4	92.5	92.2	91.9
70°	86.1	84.2	83.3	82.8	81.9	82.4	81.1
72.5°	75.1	73.7	73.5	72.3	71.7	71.8	70.8
75°	59.2	59.2	58.7	58.2	57.3	56.9	57.3
77.5°	45.5	45.6	44.8	44.7	44.6	44.7	44.2
80°	36.4	36.8	36.4	35.9	35.5	35.9	35.5
82.5°	28.8	28.1	28.0	27.9	27.8	27.6	27.5
85°	16.4	16.9	16.4	16.0	16.0	16.0	16.4
87.5°	11.3	11.5	11.7	11.8	11.9	11.9	11.7
90°	25.4	26.7	27.6	28.0	28.4	29.0	29.4
92.5°	27.2	27.8	28.3	28.5	28.9	29.2	29.4
95°	46.2	47.3	47.9	47.6	47.3	47.2	46.9
97.5°	59.8	60.8	61.4	61.7	62.1	62.3	62.6
100°	67.9	69.9	71.2	71.6	72.1	72.6	73.1
102.5°	71.5	74.0	75.6	76.2	77.0	77.7	78.3
105°	74.5	77.2	79.0	80.0	81.0	81.9	82.9
107.5°	85.0	82.3	81.4	82.4	83.4	84.4	85.3
110°	118.2	93.9	82.3	83.3	84.3	85.2	86.1



TEST NUMBER: P331817-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	216.2	127.8	83.9	84.7	85.5	86.2	87.0
115°	336.4	224.1	159.3	141.8	124.4	106.9	89.4
117.5°	664.0	636.9	594.6	537.3	479.9	422.6	365.2
120°	808.2	811.2	796.3	763.6	730.8	698.1	665.4
122.5°	856.3	858.0	855.7	849.4	843.0	836.7	830.3
125°	926.8	928.5	929.7	930.4	931.2	931.9	932.6
127.5°	992.8	995.3	996.7	996.8	996.9	997.0	997.2
130°	1034.5	1037.1	1038.3	1038.0	1037.9	1037.6	1037.3
132.5°	1074.2	1076.6	1077.5	1077.4	1077.1	1076.8	1076.7
135°	1131.8	1134.3	1135.2	1134.8	1134.3	1133.8	1133.4
137.5°	1185.2	1187.6	1188.3	1187.5	1186.7	1185.9	1185.0
140°	1219.5	1221.7	1222.2	1220.9	1219.8	1218.5	1217.4
142.5°	1251.2	1253.2	1253.6	1252.4	1251.2	1249.9	1248.8
145°	1295.5	1297.2	1297.4	1296.2	1295.0	1293.8	1292.6
147.5°	1333.9	1335.2	1335.2	1334.3	1333.2	1332.2	1331.2
150°	1358.1	1359.5	1359.6	1358.4	1357.2	1355.9	1354.8
152.5°	1379.8	1381.3	1381.3	1379.7	1378.0	1376.4	1374.8
155°	1409.3	1410.8	1410.5	1408.5	1406.7	1404.7	1402.8
157.5°	1434.3	1436.0	1435.8	1434.0	1432.1	1430.2	1428.3
160°	1448.6	1450.0	1449.9	1448.2	1446.5	1444.8	1443.1
162.5°	1462.2	1463.9	1463.7	1461.6	1459.5	1457.4	1455.4
165°	1478.7	1480.4	1480.4	1478.7	1477.0	1475.3	1473.6
167.5°	1492.5	1494.2	1494.0	1491.7	1489.6	1487.4	1485.2
170°	1499.5	1501.2	1500.9	1498.8	1496.6	1494.4	1492.2
172.5°	1504.7	1506.4	1506.2	1504.0	1501.8	1499.6	1497.4
175°	1510.4	1512.1	1511.7	1509.3	1506.9	1504.4	1502.0
177.5°	1510.6	1512.1	1511.8	1510.1	1508.3	1506.6	1504.9
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4

(END OF REPORT)