

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331566-935

Luminaire Tested: **S122DIW-S865D710U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331566-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D710U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5142.9 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331566-935

CATALOG NUMBER: S122DIW-S865D710U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331566-935

CATALOG NUMBER: S122DIW-S865D710U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	55	54	50
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	41
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19184	19184	19184
5°	19258	18979	19091
10°	19143	18787	18882
15°	18907	18544	18524
20°	18570	18179	18158
25°	18235	17728	17728
30°	17807	17316	17167
35°	17406	16821	16575
40°	16904	16326	16012
45°	16408	15835	15445
50°	15870	15325	14780
55°	15308	14728	14184
60°	14683	14018	13504
65°	14013	13310	12699
70°	13161	12458	11863
75°	11971	11472	11185
80°	10628	10302	9772
85°	8670	8262	7410



TEST NUMBER: P331566-935

CATALOG NUMBER: S122DIW-S865D710U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.7	2.2
10°-20°	314.4	6.1
20°-30°	462.1	9.0
30°-40°	536.8	10.4
40°-50°	536.2	10.4
50°-60°	467.6	9.1
60°-70°	345.7	6.7
70°-80°	195.8	3.8
80°-90°	55.7	1.1
90°-100°	48.0	0.9
100°-110°	149.0	2.9
110°-120°	254.7	5.0
120°-130°	334.9	6.5
130°-140°	375.9	7.3
140°-150°	368.6	7.2
150°-160°	309.2	6.0
160°-170°	205.1	4.0
170°-180°	71.7	1.4
0°-30°	888.2	17.3
0°-40°	1425.0	27.7
0°-60°	2428.7	47.2
0°-90°	3025.9	58.8
90°-120°	451.7	8.8
90°-150°	1531.1	29.8
90°-180°	2117.0	41.2
0°-180°	5142.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1188	1188	1188	1188	1188	
5°	1188	1183	1171	1180	1178	113
15°	1131	1124	1109	1113	1108	318
25°	1024	1014	995	997	995	471
35°	883	871	853	847	841	551
45°	719	710	694	681	676	554
55°	544	537	523	510	504	486
65°	367	360	348	338	332	363
75°	192	189	184	178	179	205
85°	47	46	45	41	40	54
90°	1	9	22	21	22	4
95°	33	39	41	41	40	38
105°	137	139	141	142	142	145
115°	256	259	258	257	256	253
125°	372	377	376	374	373	332
135°	481	488	489	489	487	372
145°	584	588	592	593	590	365
155°	668	670	672	674	673	307
165°	726	726	726	730	727	205
175°	756	754	753	757	753	72
180°	757	757	757	757	757	



TEST NUMBER: P331566-935

CATALOG NUMBER: S122DIW-S865D710U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1193.7	1192.7	1191.6	1190.7	1189.6	1188.0	1185.8	1183.5	1181.3	1179.1	1181.1
5°	1188.2	1187.1	1186.2	1185.2	1184.1	1182.2	1179.5	1176.6	1173.9	1171.0	1173.1
7.5°	1177.7	1176.1	1174.6	1172.9	1171.4	1169.2	1166.3	1163.5	1160.6	1157.8	1159.9
10°	1167.6	1165.9	1164.1	1162.3	1160.5	1158.1	1155.0	1152.0	1149.0	1145.9	1148.0
12.5°	1153.9	1152.4	1150.8	1149.2	1147.6	1145.3	1142.3	1139.2	1136.2	1133.2	1134.5
15°	1131.1	1129.5	1128.0	1126.5	1125.0	1122.6	1119.3	1115.9	1112.7	1109.4	1110.3
17.5°	1101.8	1100.3	1098.8	1097.3	1095.7	1093.3	1089.9	1086.6	1083.2	1079.9	1081.1
20°	1080.8	1079.3	1077.8	1076.2	1074.7	1072.2	1068.6	1065.1	1061.5	1058.0	1058.7
22.5°	1059.8	1057.7	1055.5	1053.3	1051.3	1048.5	1045.2	1041.8	1038.5	1035.1	1035.3
25°	1023.6	1021.7	1019.6	1017.6	1015.5	1012.4	1008.1	1003.8	999.4	995.1	995.7
27.5°	982.6	980.8	978.9	977.1	975.3	972.6	969.2	965.8	962.4	959.0	958.3
30°	955.1	953.1	951.1	949.1	947.0	944.1	940.3	936.5	932.6	928.8	928.1
32.5°	925.9	924.3	922.6	921.0	919.4	916.5	912.6	908.5	904.6	900.5	899.1
35°	883.1	880.6	878.0	875.6	873.0	869.7	865.6	861.6	857.5	853.4	852.0
37.5°	834.9	832.7	830.4	828.2	826.0	822.9	818.8	814.8	810.6	806.6	804.7
40°	802.0	800.0	798.0	795.9	793.9	790.8	786.8	782.7	778.7	774.6	772.3
42.5°	770.1	768.0	765.9	764.0	761.9	758.9	754.8	750.8	746.7	742.6	740.1
45°	718.6	716.9	715.1	713.3	711.5	708.7	704.9	701.1	697.3	693.5	690.7
47.5°	667.4	665.8	664.1	662.5	660.7	657.9	653.9	650.0	646.0	642.0	639.1
50°	631.8	630.5	629.3	628.0	626.7	624.3	620.8	617.2	613.6	610.1	606.6
52.5°	597.1	595.4	593.7	592.0	590.4	587.9	584.5	581.2	577.8	574.5	571.5
55°	543.8	542.3	540.8	539.2	537.7	535.5	532.4	529.3	526.3	523.2	520.2
57.5°	490.3	489.1	487.9	486.7	485.5	483.2	479.8	476.5	473.1	469.8	466.8
60°	454.7	453.7	452.7	451.7	450.6	448.4	444.8	441.3	437.7	434.1	431.4
62.5°	420.0	418.4	416.7	415.1	413.5	411.3	408.5	405.8	403.0	400.4	397.8
65°	366.8	365.2	363.7	362.1	360.7	358.6	356.1	353.5	351.0	348.4	346.2
67.5°	312.6	311.3	310.1	308.9	307.7	306.0	303.7	301.4	299.1	296.8	295.1
70°	278.8	277.8	276.7	275.7	274.7	273.0	270.8	268.5	266.2	263.9	262.2
72.5°	244.0	243.1	242.0	241.0	240.0	238.8	237.3	235.8	234.3	232.8	231.1
75°	191.9	191.4	190.9	190.5	189.9	189.0	187.8	186.5	185.2	183.9	182.4
77.5°	145.3	144.5	143.6	142.8	141.9	141.2	140.7	140.2	139.7	139.1	138.4
80°	114.3	114.0	113.7	113.5	113.2	112.9	112.4	111.8	111.3	110.8	110.0
82.5°	85.0	85.0	84.9	84.8	84.8	84.6	84.3	84.0	83.7	83.4	82.4
85°	46.8	46.6	46.3	46.1	45.8	45.5	45.3	45.0	44.8	44.6	43.8
87.5°	16.6	16.5	16.4	16.4	16.4	16.4	16.6	16.8	17.0	17.3	16.6
90°	0.6	2.3	4.0	5.8	7.5	9.9	13.0	16.1	19.2	22.4	22.0
92.5°	11.4	12.7	13.9	15.2	16.4	17.4	18.1	18.9	19.5	20.3	20.4
95°	33.2	34.6	36.1	37.5	38.9	39.8	40.0	40.3	40.6	40.9	40.9
97.5°	60.7	61.9	63.2	64.4	65.7	66.6	67.2	67.7	68.2	68.7	68.7
100°	81.1	82.3	83.4	84.6	85.7	86.4	86.9	87.3	87.7	88.2	88.2
102.5°	102.6	103.5	104.4	105.3	106.2	106.9	107.5	108.1	108.6	109.1	109.3
105°	137.3	137.8	138.2	138.6	139.1	139.4	139.7	140.0	140.3	140.6	140.9
107.5°	172.4	173.0	173.7	174.3	174.9	175.2	175.2	175.2	175.2	175.2	175.3
110°	194.8	195.7	196.6	197.4	198.3	198.7	198.7	198.7	198.7	198.7	198.7



TEST NUMBER: P331566-935

CATALOG NUMBER: S122DIW-S865D710U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.4	220.2	221.1	222.0	222.8	223.2	223.1	222.9	222.8	222.7	222.4
115°	255.5	256.4	257.3	258.1	259.0	259.2	259.0	258.6	258.4	258.1	258.0
117.5°	291.6	292.7	293.9	295.0	296.1	296.3	295.5	294.7	293.9	293.2	292.8
120°	315.6	316.8	317.9	319.0	320.1	320.1	319.0	317.9	316.8	315.6	315.6
122.5°	337.6	339.0	340.4	341.6	343.0	343.4	342.5	341.7	341.0	340.2	339.8
125°	371.9	373.2	374.4	375.7	376.9	377.4	376.9	376.5	376.1	375.7	375.2
127.5°	405.2	406.8	408.5	410.0	411.6	412.2	411.7	411.2	410.7	410.2	409.7
130°	426.1	428.0	429.8	431.7	433.5	434.3	434.0	433.8	433.4	433.2	432.9
132.5°	449.7	451.2	452.7	454.2	455.6	456.5	456.5	456.6	456.7	456.7	456.1
135°	481.1	482.7	484.2	485.8	487.3	488.3	488.5	488.9	489.1	489.4	489.2
137.5°	514.2	515.5	516.8	518.1	519.3	520.1	520.5	520.9	521.2	521.6	521.5
140°	534.2	535.4	536.7	538.0	539.2	540.2	541.0	541.7	542.3	543.0	543.0
142.5°	554.6	555.9	557.2	558.4	559.6	560.6	561.0	561.5	562.0	562.5	562.6
145°	583.9	585.0	585.9	586.9	588.0	588.8	589.7	590.6	591.4	592.3	592.4
147.5°	610.2	611.3	612.5	613.7	614.9	615.8	616.4	616.9	617.5	618.1	618.4
150°	628.0	628.9	629.7	630.6	631.5	632.1	632.7	633.3	633.9	634.5	634.9
152.5°	643.9	644.7	645.6	646.4	647.3	648.1	648.8	649.5	650.1	650.8	651.3
155°	667.6	668.0	668.5	668.9	669.3	669.8	670.2	670.6	671.1	671.5	672.2
157.5°	687.9	688.3	688.5	688.8	689.1	689.4	689.7	689.9	690.2	690.4	691.4
160°	700.3	700.5	700.8	701.1	701.4	701.6	701.7	701.9	702.0	702.1	703.0
162.5°	711.4	711.5	711.6	711.6	711.7	711.8	712.0	712.1	712.2	712.4	713.3
165°	726.4	726.3	726.2	726.0	725.9	725.8	725.8	725.8	725.8	725.8	726.8
167.5°	739.0	738.6	738.1	737.7	737.3	737.0	737.0	736.9	736.9	736.9	737.9
170°	745.6	745.2	744.8	744.3	743.9	743.6	743.5	743.3	743.2	743.0	744.1
172.5°	750.2	749.8	749.3	748.9	748.5	748.2	748.0	748.0	747.8	747.6	748.6
175°	755.8	755.4	755.0	754.6	754.1	753.8	753.5	753.2	752.9	752.6	753.6
177.5°	758.1	757.8	757.4	757.1	756.7	756.5	756.2	756.0	755.8	755.5	756.2
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331566-935

CATALOG NUMBER: S122DIW-S865D710U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1183.1	1185.2	1187.1	1188.0	1187.6	1187.1	1186.8	1186.4
5°	1175.1	1177.2	1179.2	1179.9	1179.5	1179.0	1178.5	1177.9
7.5°	1161.8	1163.9	1166.0	1166.7	1166.1	1165.5	1165.0	1164.4
10°	1150.0	1152.0	1154.1	1154.7	1153.9	1153.1	1152.4	1151.7
12.5°	1136.0	1137.4	1138.8	1139.3	1138.7	1138.2	1137.6	1137.0
15°	1111.4	1112.4	1113.4	1113.3	1112.1	1110.8	1109.5	1108.2
17.5°	1082.2	1083.4	1084.6	1084.5	1083.3	1082.1	1080.9	1079.7
20°	1059.5	1060.2	1061.0	1060.8	1059.9	1058.9	1057.8	1056.8
22.5°	1035.4	1035.5	1035.7	1035.5	1034.8	1034.2	1033.6	1033.0
25°	996.2	996.6	997.1	997.1	996.6	996.2	995.7	995.1
27.5°	957.5	956.7	956.0	955.0	953.7	952.5	951.3	950.1
30°	927.3	926.6	925.8	924.9	923.9	922.9	921.9	920.8
32.5°	897.8	896.4	895.0	893.8	892.9	891.8	890.8	889.8
35°	850.4	848.9	847.4	845.9	844.7	843.4	842.1	840.9
37.5°	802.9	801.0	799.1	797.5	796.3	795.1	793.9	792.6
40°	770.1	767.8	765.5	763.8	762.8	761.8	760.8	759.7
42.5°	737.6	735.1	732.7	730.7	729.3	727.9	726.4	725.0
45°	687.9	685.1	682.3	680.4	679.4	678.4	677.3	676.4
47.5°	636.2	633.3	630.3	628.1	626.6	625.2	623.7	622.2
50°	603.0	599.4	595.9	593.5	592.2	590.9	589.7	588.4
52.5°	568.5	565.6	562.7	560.3	558.7	557.0	555.3	553.6
55°	517.2	514.1	511.1	508.9	507.6	506.4	505.1	503.9
57.5°	463.8	460.8	457.8	455.8	454.9	453.9	453.0	451.9
60°	428.6	425.8	423.0	421.2	420.4	419.7	418.9	418.2
62.5°	395.1	392.5	389.9	388.2	387.2	386.2	385.3	384.4
65°	343.9	341.6	339.3	337.5	336.3	335.0	333.7	332.4
67.5°	293.3	291.4	289.7	288.3	287.3	286.3	285.2	284.2
70°	260.4	258.6	256.8	255.4	254.4	253.4	252.4	251.3
72.5°	229.3	227.5	225.8	224.5	223.6	222.8	222.0	221.2
75°	180.9	179.3	177.9	177.4	177.9	178.4	178.8	179.3
77.5°	137.7	136.9	136.1	135.3	134.7	134.0	133.3	132.5
80°	109.3	108.6	107.8	107.1	106.6	106.2	105.6	105.1
82.5°	81.5	80.5	79.6	79.0	78.9	78.8	78.7	78.6
85°	43.0	42.3	41.5	41.0	40.7	40.5	40.2	40.0
87.5°	15.9	15.2	14.6	14.2	14.0	13.9	13.7	13.5
90°	21.8	21.5	21.3	21.2	21.3	21.4	21.6	21.7
92.5°	20.4	20.5	20.6	20.6	20.6	20.7	20.7	20.7
95°	40.9	40.9	40.9	40.7	40.5	40.2	39.9	39.6
97.5°	68.7	68.7	68.7	68.7	68.7	68.7	68.6	68.6
100°	88.2	88.2	88.2	88.1	88.0	87.8	87.6	87.6
102.5°	109.3	109.4	109.6	109.6	109.4	109.3	109.2	109.0
105°	141.1	141.4	141.7	141.8	141.8	141.8	141.8	141.8
107.5°	175.4	175.6	175.6	175.4	174.7	174.1	173.4	172.8
110°	198.7	198.7	198.7	198.5	198.0	197.6	197.2	196.8



TEST NUMBER: P331566-935

CATALOG NUMBER: S122DIW-S865D710U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	222.1	221.7	221.4	221.0	220.8	220.4	220.1	219.8
115°	257.9	257.7	257.5	257.3	256.8	256.4	256.0	255.5
117.5°	292.5	292.1	291.8	291.4	290.9	290.5	290.1	289.6
120°	315.6	315.6	315.6	315.4	315.0	314.5	314.1	313.7
122.5°	339.5	339.1	338.8	338.5	338.1	337.9	337.5	337.3
125°	374.8	374.4	373.9	373.7	373.6	373.4	373.2	373.2
127.5°	409.1	408.6	408.1	407.7	407.2	406.7	406.3	405.9
130°	432.7	432.3	432.0	431.6	431.0	430.5	429.9	429.4
132.5°	455.5	454.8	454.2	453.7	453.2	452.7	452.3	451.9
135°	489.1	489.0	488.9	488.5	488.1	487.7	487.2	486.8
137.5°	521.3	521.2	521.2	520.8	520.2	519.7	519.1	518.5
140°	543.0	543.0	543.0	542.8	542.3	541.7	541.1	540.5
142.5°	562.7	562.8	562.9	562.7	562.1	561.5	561.0	560.4
145°	592.5	592.7	592.8	592.6	592.0	591.5	590.9	590.4
147.5°	618.7	619.0	619.3	619.2	618.7	618.1	617.6	617.1
150°	635.2	635.7	636.1	636.1	635.7	635.2	634.9	634.5
152.5°	651.9	652.4	653.0	653.0	652.4	651.9	651.3	650.8
155°	672.9	673.6	674.3	674.5	674.1	673.6	673.2	672.8
157.5°	692.3	693.3	694.2	694.4	693.7	693.0	692.3	691.6
160°	703.9	704.7	705.6	705.7	705.2	704.6	704.0	703.4
162.5°	714.3	715.3	716.3	716.4	715.7	715.1	714.4	713.7
165°	727.8	728.8	729.8	730.0	729.2	728.5	727.8	727.1
167.5°	738.9	739.9	740.9	741.0	740.3	739.5	738.8	738.0
170°	745.0	746.1	747.0	747.1	746.2	745.4	744.5	743.6
172.5°	749.7	750.6	751.7	751.7	750.9	750.0	749.2	748.3
175°	754.6	755.6	756.6	756.6	755.8	755.0	754.1	753.3
177.5°	756.9	757.6	758.3	758.3	757.6	756.9	756.2	755.5
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1

(END OF REPORT)