

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331819-940

Luminaire Tested: **S122RDIW-S675D1240U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331819-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1240U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6490.3 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331819-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331819-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32					32			
1	94	90	86	83	84	81	78	75	65	62	61	49	48	47	35	35	34	27					27			
2	86	79	73	68	77	71	66	62	57	54	51	44	41	40	31	30	29	24					24			
3	78	70	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20					20			
4	72	62	54	48	64	56	49	44	45	40	37	35	32	29	25	23	22	18					18			
5	66	55	47	42	59	50	43	38	40	35	32	31	28	25	23	21	19	16					16			
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14					14			
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	12					12			
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11					11			
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12	10					10			
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9					9			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16239	16239	16239
5°	16302	16037	16126
10°	16179	15775	15641
15°	15992	15308	14867
20°	15735	14639	13904
25°	15471	13881	12975
30°	15105	13103	11779
35°	14747	12254	10730
40°	14389	11377	9516
45°	13967	10392	8416
50°	13536	9399	7340
55°	13095	8329	6303
60°	12581	7201	5231
65°	12000	6052	4768
70°	11301	4985	4381
75°	10449	4548	4086
80°	9224	4063	3719
85°	7243	3205	3205



TEST NUMBER: P331819-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.2	1.5
10°-20°	258.5	4.0
20°-30°	363.0	5.6
30°-40°	395.9	6.1
40°-50°	364.0	5.6
50°-60°	285.9	4.4
60°-70°	186.4	2.9
70°-80°	96.1	1.5
80°-90°	28.6	0.4
90°-100°	50.3	0.8
100°-110°	184.4	2.8
110°-120°	492.9	7.6
120°-130°	813.7	12.5
130°-140°	865.3	13.3
140°-150°	804.3	12.4
150°-160°	646.7	10.0
160°-170°	416.7	6.4
170°-180°	143.4	2.2
0°-30°	715.7	11.0
0°-40°	1111.6	17.1
0°-60°	1761.4	27.1
0°-90°	2072.6	31.9
90°-120°	727.6	11.2
90°-150°	3210.9	49.5
90°-180°	4418.0	68.1
0°-180°	6490.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1006	1001	990	997	995	95
15°	957	946	916	899	889	269
25°	868	838	779	743	728	399
35°	748	700	622	566	544	468
45°	612	549	455	393	369	472
55°	465	393	296	243	224	416
65°	314	240	158	129	125	311
75°	168	106	73	67	66	177
85°	39	21	17	17	17	46
90°	1	13	22	27	29	5
95°	71	37	42	48	47	87
105°	332	346	66	78	83	354
115°	627	646	673	192	89	617
125°	887	901	922	929	933	790
135°	1097	1114	1125	1135	1133	847
145°	1273	1273	1290	1297	1293	796
155°	1402	1393	1405	1411	1403	646
165°	1477	1471	1474	1480	1474	417
175°	1511	1504	1505	1512	1502	144
180°	1507	1507	1507	1507	1507	



TEST NUMBER: P331819-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1009.5	1008.7	1007.9	1007.1	1006.3	1005.0	1003.2	1001.4	999.7	997.9	999.5
5°	1005.8	1004.9	1003.9	1002.8	1001.8	1000.1	997.4	994.8	992.1	989.5	991.3
7.5°	995.5	994.3	993.0	991.8	990.5	988.3	985.3	982.2	979.1	976.1	976.5
10°	986.8	985.3	983.9	982.5	981.1	978.4	974.3	970.3	966.3	962.2	961.6
12.5°	975.8	974.1	972.3	970.6	968.8	965.5	960.3	955.1	949.9	944.7	943.6
15°	956.7	954.5	952.3	950.0	947.8	943.3	936.4	929.5	922.7	915.8	912.0
17.5°	933.3	929.9	926.5	923.0	919.6	913.6	904.7	895.9	887.1	878.2	873.7
20°	915.8	911.7	907.7	903.7	899.6	892.5	882.3	872.3	862.2	852.0	846.9
22.5°	896.8	892.3	887.8	883.2	878.7	870.8	859.3	847.9	836.5	825.1	818.6
25°	868.4	861.9	855.5	849.0	842.6	832.6	819.3	805.9	792.6	779.2	770.9
27.5°	834.2	827.2	820.1	813.1	806.0	795.0	780.0	764.9	749.8	734.8	725.1
30°	810.2	802.5	794.8	787.1	779.4	767.5	751.3	735.1	718.9	702.8	692.4
32.5°	786.8	777.8	768.9	759.9	750.9	738.2	721.7	705.2	688.7	672.2	660.4
35°	748.2	738.0	727.6	717.3	707.0	692.9	675.1	657.4	639.5	621.7	608.9
37.5°	709.7	698.3	687.0	675.6	664.3	649.2	630.3	611.3	592.3	573.3	559.3
40°	682.7	670.6	658.4	646.3	634.2	618.3	598.7	579.1	559.5	539.8	525.5
42.5°	655.1	642.3	629.5	616.7	604.0	587.4	567.1	546.9	526.6	506.3	491.4
45°	611.7	598.2	584.6	571.1	557.5	540.1	518.9	497.7	476.4	455.1	440.8
47.5°	569.4	555.1	540.7	526.4	512.0	493.9	472.0	450.0	428.1	406.2	391.9
50°	538.9	524.5	510.1	495.8	481.4	463.2	440.9	418.7	396.4	374.2	360.2
52.5°	509.1	494.0	479.0	464.0	449.0	430.6	408.8	387.1	365.3	343.6	330.1
55°	465.2	449.4	433.6	417.9	402.1	383.3	361.4	339.6	317.7	295.9	283.7
57.5°	420.2	404.0	387.8	371.7	355.4	336.9	315.8	294.9	273.8	252.9	241.7
60°	389.6	373.4	357.2	341.1	324.9	306.4	285.5	264.7	243.9	223.0	212.7
62.5°	359.7	343.6	327.3	311.2	295.0	277.0	257.2	237.3	217.4	197.5	187.7
65°	314.1	297.7	281.2	264.9	248.5	231.2	213.0	194.8	176.6	158.4	151.5
67.5°	270.0	253.7	237.5	221.2	204.9	188.6	172.2	155.9	139.5	123.1	119.9
70°	239.4	223.6	207.9	192.1	176.3	161.4	147.5	133.5	119.6	105.6	103.5
72.5°	210.3	195.1	180.0	164.9	149.7	136.6	125.4	114.1	103.0	91.8	90.1
75°	167.5	153.4	139.2	125.0	110.8	100.3	93.5	86.6	79.7	72.9	71.4
77.5°	125.5	113.0	100.6	88.2	75.8	67.9	64.6	61.3	58.0	54.7	53.8
80°	99.2	88.9	78.6	68.3	58.0	51.8	49.8	47.7	45.7	43.7	42.9
82.5°	75.2	67.1	59.1	51.0	43.0	38.3	36.9	35.5	34.2	32.8	32.3
85°	39.1	34.9	30.7	26.4	22.1	19.7	19.1	18.5	17.9	17.3	17.3
87.5°	11.9	11.1	10.3	9.6	8.8	8.6	9.0	9.5	9.8	10.2	10.3
90°	1.1	3.7	6.4	9.1	11.8	14.1	16.0	17.9	19.9	21.8	23.0
92.5°	22.0	21.8	21.6	21.3	21.0	21.4	22.4	23.4	24.3	25.3	25.9
95°	70.9	62.9	54.9	46.9	38.9	35.8	37.5	39.1	40.8	42.5	43.8
97.5°	140.7	118.2	95.6	73.1	50.6	41.2	45.1	49.0	53.1	57.0	57.9
100°	193.1	159.9	126.6	93.5	60.3	45.7	49.8	53.9	58.1	62.2	64.1
102.5°	250.7	243.6	236.6	229.6	222.6	201.8	167.3	132.9	98.4	63.9	66.4
105°	331.6	338.9	346.2	353.4	360.7	331.3	265.1	198.9	132.7	66.5	69.2
107.5°	423.9	429.7	435.6	441.5	447.4	410.6	331.3	251.9	172.5	93.2	90.4
110°	483.2	488.3	493.4	498.5	503.5	471.1	401.1	331.0	260.9	190.9	166.7



TEST NUMBER: P331819-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	539.0	543.6	548.0	552.6	557.1	550.7	533.4	516.1	498.8	481.4	393.1
115°	627.2	631.3	635.4	639.5	643.7	648.8	654.9	660.9	667.0	673.1	560.8
117.5°	706.0	710.6	715.2	719.8	724.4	728.8	732.9	737.1	741.3	745.5	718.3
120°	763.6	767.2	770.8	774.5	778.1	782.1	786.5	790.9	795.2	799.5	802.5
122.5°	812.4	816.3	820.1	823.9	827.8	832.1	836.8	841.5	846.3	851.0	852.7
125°	886.8	889.9	893.1	896.3	899.4	903.3	907.9	912.5	917.1	921.8	923.5
127.5°	954.2	957.7	961.2	964.7	968.2	971.7	975.1	978.6	982.0	985.4	987.9
130°	997.0	1000.9	1004.8	1008.6	1012.5	1015.7	1018.4	1021.1	1023.8	1026.4	1029.1
132.5°	1040.6	1043.9	1047.2	1050.5	1053.8	1056.8	1059.4	1062.1	1064.8	1067.5	1069.7
135°	1097.3	1101.2	1105.1	1108.9	1112.9	1115.9	1118.0	1120.3	1122.4	1124.6	1127.0
137.5°	1154.7	1157.4	1160.1	1162.9	1165.6	1168.1	1170.6	1173.1	1175.5	1178.0	1180.4
140°	1192.2	1194.2	1196.1	1198.0	1200.0	1202.3	1205.0	1207.6	1210.3	1213.0	1215.1
142.5°	1223.7	1225.4	1227.2	1228.9	1230.7	1233.1	1236.1	1239.1	1242.2	1245.3	1247.2
145°	1272.9	1272.7	1272.5	1272.2	1272.0	1273.9	1278.1	1282.2	1286.3	1290.4	1292.1
147.5°	1315.9	1315.0	1314.1	1313.1	1312.2	1313.8	1317.9	1322.0	1326.1	1330.1	1331.4
150°	1343.9	1342.2	1340.5	1338.7	1337.0	1338.2	1342.0	1345.9	1349.8	1353.7	1355.1
152.5°	1367.4	1365.6	1363.6	1361.7	1359.9	1360.8	1364.4	1368.2	1371.8	1375.5	1377.0
155°	1401.7	1399.5	1397.3	1395.1	1392.9	1393.3	1396.2	1399.1	1402.0	1405.0	1406.4
157.5°	1428.5	1426.6	1424.8	1423.0	1421.1	1421.2	1423.3	1425.3	1427.4	1429.4	1431.0
160°	1444.2	1442.8	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1445.6
162.5°	1458.2	1456.7	1455.3	1453.8	1452.3	1452.2	1453.5	1454.7	1456.1	1457.3	1458.9
165°	1476.9	1475.5	1474.0	1472.6	1471.1	1470.8	1471.5	1472.2	1472.9	1473.6	1475.3
167.5°	1490.9	1489.4	1488.0	1486.6	1485.1	1484.7	1485.4	1486.0	1486.7	1487.4	1489.1
170°	1498.8	1497.3	1495.8	1494.4	1492.9	1492.5	1492.9	1493.4	1493.9	1494.4	1496.1
172.5°	1504.0	1502.5	1501.1	1499.6	1498.2	1497.7	1498.2	1498.6	1499.1	1499.6	1501.3
175°	1510.7	1509.0	1507.3	1505.7	1504.0	1503.3	1503.9	1504.3	1504.9	1505.3	1507.0
177.5°	1511.8	1510.5	1509.1	1507.8	1506.4	1505.8	1506.0	1506.2	1506.4	1506.6	1508.0
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331819-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1001.1	1002.7	1004.3	1005.0	1004.7	1004.3	1004.1	1003.7
5°	993.1	995.0	996.8	997.4	996.8	996.1	995.6	995.0
7.5°	977.0	977.6	978.1	977.9	976.8	975.8	974.7	973.7
10°	961.0	960.4	959.7	958.9	957.6	956.4	955.2	954.0
12.5°	942.5	941.5	940.3	938.8	936.7	934.8	932.7	930.7
15°	908.1	904.2	900.4	897.4	895.5	893.4	891.4	889.4
17.5°	869.2	864.5	860.0	856.0	852.5	849.0	845.5	842.0
20°	842.0	836.9	831.8	827.1	822.6	818.1	813.7	809.2
22.5°	812.1	805.6	799.1	794.2	790.8	787.5	784.2	780.9
25°	762.6	754.3	746.0	740.4	737.4	734.3	731.3	728.3
27.5°	715.4	705.8	696.2	688.8	684.0	679.2	674.4	669.6
30°	682.2	671.8	661.5	653.6	648.1	642.7	637.2	631.8
32.5°	648.6	636.9	625.1	616.6	611.4	606.4	601.2	596.1
35°	596.3	583.5	570.8	562.1	557.7	553.2	548.8	544.4
37.5°	545.2	531.2	517.2	507.6	502.5	497.4	492.3	487.2
40°	511.0	496.7	482.3	472.5	467.3	462.0	456.7	451.5
42.5°	476.6	461.7	446.9	436.9	431.9	426.8	421.7	416.5
45°	426.4	412.1	397.7	388.1	383.3	378.4	373.5	368.6
47.5°	377.6	363.4	349.0	339.7	335.3	330.9	326.5	322.1
50°	346.3	332.3	318.3	309.2	305.0	300.7	296.5	292.2
52.5°	316.6	303.1	289.6	281.0	277.1	273.1	269.2	265.3
55°	271.6	259.4	247.3	239.3	235.5	231.6	227.7	223.9
57.5°	230.6	219.5	208.4	201.2	198.0	194.7	191.5	188.2
60°	202.4	192.1	181.7	175.0	171.7	168.5	165.2	162.0
62.5°	177.9	168.0	158.2	152.3	150.3	148.5	146.5	144.5
65°	144.6	137.8	130.9	127.2	126.5	125.9	125.3	124.8
67.5°	116.7	113.6	110.5	108.5	107.9	107.3	106.6	105.9
70°	101.6	99.5	97.5	96.1	95.2	94.4	93.6	92.8
72.5°	88.4	86.7	85.0	83.9	83.4	82.9	82.4	81.9
75°	70.0	68.6	67.1	66.3	66.2	66.0	65.7	65.5
77.5°	53.0	52.2	51.4	50.8	50.5	50.2	49.8	49.5
80°	42.1	41.3	40.5	40.0	40.0	40.0	40.0	40.0
82.5°	31.8	31.3	30.9	30.6	30.6	30.6	30.6	30.6
85°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
87.5°	10.3	10.4	10.5	10.6	10.7	10.8	10.9	11.0
90°	24.3	25.4	26.7	27.6	28.0	28.4	29.0	29.4
92.5°	26.6	27.2	27.8	28.3	28.5	28.9	29.2	29.4
95°	44.9	46.2	47.3	47.9	47.6	47.3	47.2	46.9
97.5°	58.9	59.8	60.8	61.4	61.7	62.1	62.3	62.6
100°	66.1	67.9	69.9	71.2	71.6	72.1	72.6	73.1
102.5°	68.9	71.5	74.0	75.6	76.2	77.0	77.7	78.3
105°	71.9	74.5	77.2	79.0	80.0	81.0	81.9	82.9
107.5°	87.7	85.0	82.3	81.4	82.4	83.4	84.4	85.3
110°	142.4	118.2	93.9	82.3	83.3	84.3	85.2	86.1



TEST NUMBER: P331819-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	304.6	216.2	127.8	83.9	84.7	85.5	86.2	87.0
115°	448.5	336.4	224.1	159.3	141.8	124.4	106.9	89.4
117.5°	691.2	664.0	636.9	594.6	537.3	479.9	422.6	365.2
120°	805.4	808.2	811.2	796.3	763.6	730.8	698.1	665.4
122.5°	854.5	856.3	858.0	855.7	849.4	843.0	836.7	830.3
125°	925.1	926.8	928.5	929.7	930.4	931.2	931.9	932.6
127.5°	990.3	992.8	995.3	996.7	996.8	996.9	997.0	997.2
130°	1031.8	1034.5	1037.1	1038.3	1038.0	1037.9	1037.6	1037.3
132.5°	1072.0	1074.2	1076.6	1077.5	1077.4	1077.1	1076.8	1076.7
135°	1129.4	1131.8	1134.3	1135.2	1134.8	1134.3	1133.8	1133.4
137.5°	1182.8	1185.2	1187.6	1188.3	1187.5	1186.7	1185.9	1185.0
140°	1217.4	1219.5	1221.7	1222.2	1220.9	1219.8	1218.5	1217.4
142.5°	1249.2	1251.2	1253.2	1253.6	1252.4	1251.2	1249.9	1248.8
145°	1293.8	1295.5	1297.2	1297.4	1296.2	1295.0	1293.8	1292.6
147.5°	1332.7	1333.9	1335.2	1335.2	1334.3	1333.2	1332.2	1331.2
150°	1356.6	1358.1	1359.5	1359.6	1358.4	1357.2	1355.9	1354.8
152.5°	1378.4	1379.8	1381.3	1381.3	1379.7	1378.0	1376.4	1374.8
155°	1407.8	1409.3	1410.8	1410.5	1408.5	1406.7	1404.7	1402.8
157.5°	1432.7	1434.3	1436.0	1435.8	1434.0	1432.1	1430.2	1428.3
160°	1447.2	1448.6	1450.0	1449.9	1448.2	1446.5	1444.8	1443.1
162.5°	1460.6	1462.2	1463.9	1463.7	1461.6	1459.5	1457.4	1455.4
165°	1477.0	1478.7	1480.4	1480.4	1478.7	1477.0	1475.3	1473.6
167.5°	1490.8	1492.5	1494.2	1494.0	1491.7	1489.6	1487.4	1485.2
170°	1497.8	1499.5	1501.2	1500.9	1498.8	1496.6	1494.4	1492.2
172.5°	1503.0	1504.7	1506.4	1506.2	1504.0	1501.8	1499.6	1497.4
175°	1508.7	1510.4	1512.1	1511.7	1509.3	1506.9	1504.4	1502.0
177.5°	1509.3	1510.6	1512.1	1511.8	1510.1	1508.3	1506.6	1504.9
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4

(END OF REPORT)