

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331567-935

Luminaire Tested: **S122DIW-S865D970U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331567-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D970U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6614.4 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	45	43	41	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	32
4	75	65	57	52	69	60	54	48	52	47	43	44	40	37	36	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	39	59	49	42	37	42	37	33	36	32	28	30	27	24	22
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22	19
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	51	40	32	27	48	37	30	26	32	27	23	28	24	21	23	20	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	24001	24001	24001	24001
5°	26909	24159	21409	24159
10°	30836	23961	18528	23961
15°	34111	23520	16368	23520
20°	33593	23048	14921	23048
25°	30289	22422	14004	22422
30°	25031	21420	13336	21420
35°	18242	20371	12861	20371
40°	14570	19134	12596	19134
45°	12732	17701	12237	17701
50°	11969	16317	11997	16317
55°	11032	14908	11674	14908
60°	10111	13411	11179	13411
65°	9211	12069	10693	12069
70°	8360	10763	9980	10763
75°	7411	9301	8840	9301
80°	6369	7699	7113	7699
85°	5706	5706	4224	5706



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.6	2.1
10°-20°	411.6	6.2
20°-30°	597.3	9.0
30°-40°	630.3	9.5
40°-50°	558.1	8.4
50°-60°	445.4	6.7
60°-70°	302.7	4.6
70°-80°	155.2	2.3
80°-90°	40.2	0.6
90°-100°	37.9	0.6
100°-110°	139.1	2.1
110°-120°	371.8	5.6
120°-130°	613.7	9.3
130°-140°	652.7	9.9
140°-150°	606.6	9.2
150°-160°	487.7	7.4
160°-170°	314.3	4.8
170°-180°	108.2	1.6
0°-30°	1150.5	17.4
0°-40°	1780.8	26.9
0°-60°	2784.3	42.1
0°-90°	3282.4	49.6
90°-120°	548.8	8.3
90°-150°	2421.8	36.6
90°-180°	3332.0	50.4
0°-180°	6614.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1486	1486	1486	1486	1486	
5°	1660	1491	1321	1491	1660	166
15°	2041	1407	979	1407	2041	563
25°	1700	1259	786	1259	1700	768
35°	926	1034	652	1034	926	602
45°	558	775	536	775	558	438
55°	392	530	415	530	392	351
65°	241	316	280	316	241	240
75°	119	149	142	149	119	127
85°	31	31	23	31	31	34
90°	22	1	22	1	22	11
95°	35	54	35	54	35	33
105°	62	250	62	250	62	65
115°	68	473	68	473	68	169
125°	703	669	703	669	703	609
135°	855	828	855	828	855	659
145°	975	960	975	960	975	610
155°	1058	1057	1058	1057	1058	488
165°	1112	1114	1112	1114	1112	314
175°	1133	1139	1133	1139	1133	108
180°	1137	1137	1137	1137	1137	



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1555.1	1555.6	1556.5	1549.2	1548.3	1548.3	1541.9	1536.4	1530.0	1521.3	1522.2
5°	1660.3	1666.6	1668.8	1662.0	1651.7	1650.5	1640.8	1624.8	1610.0	1597.9	1589.4
7.5°	1785.7	1788.2	1782.6	1773.6	1765.9	1752.2	1734.1	1716.5	1691.7	1669.0	1652.0
10°	1880.8	1884.2	1874.5	1861.3	1850.5	1834.4	1808.2	1781.3	1748.8	1717.4	1692.2
12.5°	1953.0	1961.4	1949.0	1947.2	1928.6	1906.7	1875.4	1861.8	1816.0	1772.2	1745.2
15°	2040.7	2040.1	2041.3	2030.4	2016.7	2013.3	1980.2	1944.2	1879.6	1853.9	1809.4
17.5°	2015.3	2024.0	2028.1	2027.9	2027.6	2025.4	2014.8	1992.1	1959.7	1918.0	1866.6
20°	1955.1	1966.4	1968.2	1981.3	1988.7	1998.5	2002.4	1996.1	1976.2	1941.3	1896.8
22.5°	1861.8	1865.0	1870.4	1890.8	1906.9	1931.3	1944.0	1965.1	1957.4	1940.4	1903.2
25°	1700.2	1694.5	1714.5	1724.8	1762.0	1800.8	1828.8	1859.6	1887.1	1903.6	1892.7
27.5°	1506.2	1497.6	1527.6	1554.9	1585.0	1627.1	1670.8	1722.3	1765.1	1818.7	1837.1
30°	1342.6	1347.7	1376.3	1405.4	1451.1	1510.5	1559.7	1616.3	1677.4	1737.3	1779.1
32.5°	1166.1	1185.9	1204.0	1248.6	1288.9	1355.1	1427.1	1497.9	1574.1	1642.3	1706.8
35°	925.5	948.4	973.5	1006.1	1062.6	1128.3	1198.6	1294.0	1398.0	1491.2	1567.7
37.5°	779.0	775.4	789.8	813.3	859.1	912.1	993.1	1087.4	1209.7	1319.1	1427.1
40°	691.3	689.0	699.3	721.0	755.9	794.7	865.6	948.4	1062.0	1195.8	1324.3
42.5°	630.9	632.3	638.0	653.3	677.3	709.2	762.2	832.8	936.9	1062.7	1200.9
45°	557.6	561.6	567.9	575.3	589.0	615.3	645.0	695.3	777.6	882.7	1018.6
47.5°	504.8	504.9	511.3	517.8	526.0	540.8	565.0	596.6	654.6	740.2	857.1
50°	476.5	472.5	477.1	482.2	490.8	501.0	517.0	546.7	585.6	654.7	752.4
52.5°	441.8	441.9	446.0	447.9	455.6	465.9	480.4	501.0	536.2	590.3	670.6
55°	391.9	394.8	397.1	400.5	407.3	414.7	426.2	439.9	467.4	507.9	567.3
57.5°	345.1	345.9	348.3	354.8	359.1	366.0	376.9	389.3	407.1	437.1	481.8
60°	313.1	313.1	317.6	320.5	326.2	333.0	341.6	353.6	369.6	394.2	430.2
62.5°	283.9	283.4	285.2	289.9	294.2	300.7	309.2	319.3	334.4	356.3	385.9
65°	241.1	240.0	243.4	244.5	249.1	255.4	262.3	273.1	285.1	301.1	327.4
67.5°	199.9	201.3	203.2	205.3	207.8	214.5	219.0	226.7	236.9	250.1	267.9
70°	177.1	177.1	177.1	178.8	182.3	185.7	190.3	196.6	206.2	217.7	233.7
72.5°	151.5	153.3	155.2	154.1	158.5	160.6	166.0	169.5	178.8	186.1	200.3
75°	118.8	118.8	118.8	121.7	123.4	125.1	128.5	132.0	136.6	145.7	153.1
77.5°	88.7	88.4	89.0	89.7	91.5	93.6	94.6	97.7	101.9	106.2	112.4
80°	68.5	69.7	70.3	71.4	71.4	72.6	73.1	77.1	80.0	82.8	86.9
82.5°	53.0	53.2	53.4	53.6	54.1	54.8	56.2	57.5	58.5	60.9	64.0
85°	30.8	30.3	30.3	31.4	30.8	30.8	32.0	33.1	33.1	33.7	35.4
87.5°	16.4	16.3	16.6	16.1	16.0	16.4	16.2	15.5	15.8	16.1	16.3
90°	22.2	21.9	21.4	21.1	20.8	20.1	19.2	18.3	17.4	16.4	15.0
92.5°	22.2	22.0	21.8	21.5	21.4	21.0	20.5	20.1	19.5	19.1	18.3
95°	35.4	35.6	35.7	35.9	36.1	35.7	34.9	33.9	33.0	32.1	30.8
97.5°	47.2	47.0	46.8	46.6	46.3	45.9	45.1	44.4	43.7	43.0	40.0
100°	55.1	54.8	54.4	54.0	53.6	52.8	51.3	49.9	48.4	46.9	43.8
102.5°	59.1	58.5	58.0	57.5	57.0	55.8	53.9	52.0	50.1	48.2	44.2
105°	62.5	61.8	61.0	60.4	59.6	58.2	56.2	54.2	52.2	50.2	46.1
107.5°	64.3	63.6	62.9	62.2	61.4	62.1	64.1	66.1	68.2	70.3	74.1
110°	65.0	64.2	63.5	62.8	62.1	70.9	89.1	107.4	125.7	144.0	196.8



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	65.7	65.1	64.5	63.9	63.3	96.3	163.1	229.7	296.4	363.2	376.2
115°	67.5	80.6	93.8	106.9	120.1	169.0	253.7	338.3	422.9	507.6	503.1
117.5°	275.4	318.7	362.0	405.2	448.5	480.4	500.8	521.2	541.7	562.2	559.1
120°	501.9	526.5	551.2	575.9	600.5	611.8	609.6	607.4	605.3	603.0	599.8
122.5°	626.3	631.0	635.8	640.6	645.4	647.1	645.8	644.5	643.2	641.9	638.3
125°	703.4	702.8	702.3	701.8	701.2	700.3	699.0	697.8	696.5	695.2	691.7
127.5°	752.1	752.0	751.9	751.8	751.7	750.7	748.8	747.0	745.1	743.2	740.6
130°	782.4	782.6	782.7	782.9	783.2	782.2	780.2	778.2	776.2	774.2	772.1
132.5°	812.0	812.2	812.4	812.5	812.8	812.0	810.3	808.6	806.8	805.1	803.1
135°	854.8	855.1	855.5	855.9	856.3	855.5	853.7	851.9	850.1	848.3	846.5
137.5°	893.8	894.4	895.0	895.7	896.3	895.7	893.9	892.1	890.4	888.6	886.7
140°	918.2	919.0	920.0	920.9	921.8	921.4	919.8	918.2	916.5	914.9	912.8
142.5°	941.8	942.8	943.7	944.6	945.5	945.2	943.7	942.2	940.7	939.2	936.9
145°	974.9	975.9	976.7	977.7	978.6	978.4	977.1	975.9	974.6	973.3	970.2
147.5°	1004.0	1004.8	1005.6	1006.3	1007.1	1007.0	1006.1	1005.1	1004.2	1003.2	1000.1
150°	1021.8	1022.7	1023.6	1024.6	1025.5	1025.4	1024.2	1023.2	1022.1	1021.0	1018.0
152.5°	1037.0	1038.2	1039.4	1040.6	1041.8	1041.8	1040.7	1039.7	1038.5	1037.4	1034.7
155°	1058.0	1059.5	1060.9	1062.4	1063.9	1064.0	1062.9	1061.9	1060.8	1059.6	1057.5
157.5°	1077.3	1078.7	1080.1	1081.5	1083.0	1083.1	1081.8	1080.6	1079.3	1078.1	1076.5
160°	1088.5	1089.8	1091.0	1092.3	1093.6	1093.6	1092.5	1091.5	1090.4	1089.3	1088.2
162.5°	1097.7	1099.2	1100.8	1102.3	1104.0	1104.1	1102.9	1101.6	1100.4	1099.2	1098.2
165°	1111.5	1112.8	1114.0	1115.3	1116.6	1116.6	1115.3	1114.0	1112.8	1111.5	1110.9
167.5°	1120.2	1121.9	1123.5	1125.2	1126.8	1127.0	1125.7	1124.4	1123.1	1121.9	1121.4
170°	1125.5	1127.1	1128.8	1130.4	1132.0	1132.2	1130.9	1129.7	1128.4	1127.1	1126.8
172.5°	1129.5	1131.1	1132.7	1134.4	1136.0	1136.2	1134.9	1133.6	1132.4	1131.1	1130.7
175°	1132.9	1134.7	1136.5	1138.3	1140.2	1140.5	1139.2	1137.9	1136.6	1135.3	1135.0
177.5°	1135.1	1136.3	1137.6	1138.9	1140.3	1140.4	1139.4	1138.4	1137.4	1136.3	1136.2
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1525.4	1521.7	1519.5	1511.2	1503.9	1496.6	1494.4	1495.2	1485.2	1475.6	1471.4
5°	1584.8	1573.4	1562.5	1547.1	1528.9	1508.8	1498.6	1490.6	1470.6	1448.9	1436.3
7.5°	1638.1	1621.7	1600.9	1571.8	1545.2	1513.7	1493.7	1476.0	1446.8	1416.2	1397.4
10°	1670.5	1648.2	1621.3	1586.0	1553.4	1515.1	1488.2	1461.5	1427.1	1390.6	1367.7
12.5°	1698.4	1668.4	1641.9	1596.5	1558.0	1510.1	1478.3	1440.4	1404.3	1360.9	1338.5
15°	1764.8	1709.3	1659.1	1607.7	1560.2	1493.4	1458.0	1407.1	1359.7	1306.1	1280.3
17.5°	1816.1	1753.9	1674.6	1609.3	1553.9	1480.0	1428.0	1367.0	1311.0	1249.6	1214.6
20°	1845.4	1773.9	1688.8	1611.1	1544.8	1460.3	1403.7	1341.4	1275.7	1206.6	1168.9
22.5°	1862.7	1787.6	1703.4	1604.2	1526.6	1444.2	1373.1	1304.8	1238.3	1163.6	1124.1
25°	1868.2	1799.7	1710.5	1598.5	1503.7	1410.6	1324.9	1258.6	1178.0	1108.4	1050.7
27.5°	1841.0	1791.8	1706.2	1587.8	1477.3	1368.4	1272.9	1197.8	1112.8	1037.2	979.1
30°	1807.7	1779.1	1695.7	1576.8	1456.3	1339.2	1234.1	1148.9	1064.4	987.8	928.4
32.5°	1756.0	1749.8	1676.5	1561.3	1433.9	1302.2	1193.3	1107.3	1013.7	938.4	881.8
35°	1654.5	1682.0	1635.6	1526.6	1391.7	1249.5	1131.8	1033.5	936.4	864.4	811.2
37.5°	1518.5	1586.7	1574.5	1475.7	1334.8	1192.1	1062.2	959.5	866.9	794.3	742.1
40°	1424.9	1511.7	1524.2	1436.8	1294.6	1147.8	1010.1	907.8	817.5	751.3	698.7
42.5°	1324.3	1425.7	1460.3	1390.3	1250.7	1101.1	963.5	857.6	768.2	703.8	657.1
45°	1155.8	1290.0	1352.3	1312.3	1177.5	1024.3	882.7	775.2	694.1	633.6	597.6
47.5°	998.2	1144.9	1228.6	1214.5	1096.0	944.3	804.3	701.2	622.2	573.9	541.7
50°	886.7	1037.5	1138.6	1143.2	1037.5	887.3	746.7	649.6	577.0	531.9	505.6
52.5°	789.8	933.8	1044.0	1068.2	972.2	827.9	695.1	598.4	534.5	493.0	469.5
55°	663.3	785.0	907.2	951.8	874.7	737.5	614.8	529.6	469.6	441.1	420.5
57.5°	551.5	652.9	765.8	815.0	767.5	650.1	534.9	461.1	412.3	387.4	371.6
60°	492.5	572.5	673.0	731.8	690.7	586.2	485.6	415.3	375.4	353.1	338.2
62.5°	437.6	508.5	593.5	647.3	624.9	526.3	436.3	374.2	339.7	318.8	308.1
65°	361.1	417.1	482.8	532.4	517.6	442.7	369.1	315.9	288.5	271.9	263.4
67.5°	297.3	337.8	383.3	426.9	414.9	361.9	302.6	261.3	240.9	226.6	221.4
70°	257.1	287.9	328.5	363.3	353.6	310.2	263.4	228.0	210.3	198.3	193.1
72.5°	218.7	244.1	275.0	303.5	297.0	260.9	221.8	195.0	181.4	170.4	166.2
75°	165.1	184.5	203.4	222.2	220.5	192.5	169.7	149.1	138.3	129.7	127.9
77.5°	121.9	132.8	145.6	156.8	153.7	137.7	119.8	108.0	100.0	94.3	93.3
80°	93.2	99.4	108.6	116.6	112.5	105.7	91.4	82.8	77.1	71.4	69.1
82.5°	67.5	73.8	79.3	83.6	80.6	74.1	65.3	59.5	56.1	52.2	51.3
85°	35.4	38.8	41.2	42.3	41.2	37.1	33.1	30.8	28.0	26.3	25.7
87.5°	16.4	16.1	15.8	16.4	14.6	14.2	12.0	10.2	10.2	10.1	9.6
90°	13.5	12.1	10.6	8.9	6.9	4.8	2.8	0.9	2.8	4.8	6.9
92.5°	17.7	16.9	16.2	15.9	16.1	16.3	16.4	16.6	16.4	16.3	16.1
95°	29.5	28.2	26.9	29.4	35.4	41.4	47.4	53.5	47.4	41.4	35.4
97.5°	37.0	34.1	31.1	38.1	55.1	72.2	89.1	106.2	89.1	72.2	55.1
100°	40.6	37.5	34.4	45.5	70.5	95.5	120.5	145.6	120.5	95.5	70.5
102.5°	100.2	126.2	152.2	167.8	173.1	178.5	183.7	189.1	183.7	178.5	173.1
105°	150.0	199.9	249.9	272.1	266.6	261.1	255.6	250.1	255.6	261.1	266.6
107.5°	189.9	249.9	309.7	337.4	332.9	328.6	324.2	319.7	324.2	328.6	332.9
110°	249.7	302.5	355.3	379.8	376.0	372.1	368.3	364.5	368.3	372.1	376.0



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	389.3	402.3	415.3	420.2	416.8	413.4	410.0	406.6	410.0	413.4	416.8
115°	498.4	493.9	489.3	485.5	482.4	479.3	476.1	473.0	476.1	479.3	482.4
117.5°	555.9	552.8	549.7	546.4	542.9	539.4	536.0	532.4	536.0	539.4	542.9
120°	596.5	593.1	589.9	586.9	584.1	581.3	578.7	575.9	578.7	581.3	584.1
122.5°	634.7	631.1	627.6	624.3	621.4	618.5	615.6	612.8	615.6	618.5	621.4
125°	688.3	684.8	681.3	678.4	676.0	673.6	671.2	668.8	671.2	673.6	676.0
127.5°	738.0	735.5	732.9	730.2	727.6	725.0	722.4	719.7	722.4	725.0	727.6
130°	770.2	768.1	766.1	763.6	760.7	757.9	754.9	752.0	754.9	757.9	760.7
132.5°	801.1	799.1	797.0	794.8	792.3	789.9	787.4	784.9	787.4	789.9	792.3
135°	844.9	843.3	841.6	839.4	836.5	833.5	830.6	827.7	830.6	833.5	836.5
137.5°	884.8	883.0	881.1	879.1	877.1	875.0	873.0	870.9	873.0	875.0	877.1
140°	910.9	908.8	906.8	905.1	903.6	902.2	900.7	899.2	900.7	902.2	903.6
142.5°	934.6	932.3	930.0	928.2	926.9	925.6	924.2	922.9	924.2	925.6	926.9
145°	967.1	964.0	960.9	959.4	959.6	959.8	959.9	960.1	959.9	959.8	959.6
147.5°	997.0	994.0	990.9	989.7	990.4	991.1	991.8	992.6	991.8	991.1	990.4
150°	1015.1	1012.2	1009.3	1008.5	1009.8	1011.0	1012.3	1013.6	1012.3	1011.0	1009.8
152.5°	1031.9	1029.1	1026.3	1025.6	1027.1	1028.5	1029.9	1031.4	1029.9	1028.5	1027.1
155°	1055.2	1053.1	1050.9	1050.6	1052.2	1053.9	1055.5	1057.2	1055.5	1053.9	1052.2
157.5°	1075.0	1073.5	1071.9	1071.9	1073.2	1074.6	1076.1	1077.5	1076.1	1074.6	1073.2
160°	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1088.2	1087.1	1086.0
162.5°	1097.3	1096.3	1095.4	1095.5	1096.5	1097.6	1098.7	1099.8	1098.7	1097.6	1096.5
165°	1110.3	1109.8	1109.3	1109.6	1110.7	1111.7	1112.8	1114.0	1112.8	1111.7	1110.7
167.5°	1120.8	1120.3	1119.8	1120.1	1121.2	1122.3	1123.3	1124.5	1123.3	1122.3	1121.2
170°	1126.4	1126.0	1125.7	1126.0	1127.1	1128.3	1129.3	1130.4	1129.3	1128.3	1127.1
172.5°	1130.3	1130.0	1129.6	1130.0	1131.1	1132.1	1133.2	1134.4	1133.2	1132.1	1131.1
175°	1134.6	1134.3	1133.9	1134.4	1135.7	1136.9	1138.2	1139.4	1138.2	1136.9	1135.7
177.5°	1136.0	1135.9	1135.7	1136.2	1137.2	1138.2	1139.3	1140.3	1139.3	1138.2	1137.2
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1466.9	1464.1	1454.6	1449.6	1441.3	1433.6	1428.5	1430.8	1432.6	1431.7	1430.4
5°	1424.9	1414.0	1397.4	1383.1	1372.9	1354.0	1346.0	1342.0	1338.6	1334.6	1330.6
7.5°	1374.8	1357.7	1333.9	1313.5	1294.3	1270.9	1257.6	1249.6	1241.4	1232.3	1224.3
10°	1339.2	1315.2	1290.0	1261.5	1238.6	1217.5	1198.6	1186.0	1174.7	1163.7	1155.8
12.5°	1301.7	1274.0	1242.9	1203.9	1178.7	1148.5	1145.6	1123.4	1105.6	1098.9	1089.5
15°	1242.1	1203.2	1163.7	1117.5	1097.5	1070.1	1052.9	1035.8	1020.4	1009.5	1006.7
17.5°	1174.3	1124.0	1084.8	1051.5	1018.7	990.7	974.9	961.2	948.5	934.0	932.0
20°	1122.7	1079.2	1036.4	1007.2	973.5	944.9	925.5	911.8	901.0	892.4	884.9
22.5°	1073.8	1026.2	987.0	955.1	921.9	898.8	883.5	870.2	861.2	851.7	844.7
25°	995.2	958.1	915.2	879.3	851.8	837.0	824.4	813.0	807.3	801.0	793.0
27.5°	926.5	885.3	845.2	817.3	793.2	780.1	771.2	763.4	758.0	754.3	749.8
30°	878.1	836.4	804.9	777.6	757.6	744.4	738.7	734.2	727.9	725.6	723.3
32.5°	831.5	793.9	767.1	743.3	724.2	715.7	710.4	706.3	701.4	699.0	694.5
35°	765.6	734.2	707.8	694.7	679.3	671.8	667.9	662.2	657.5	655.3	654.7
37.5°	703.5	676.2	658.9	642.0	635.5	630.9	625.5	621.6	620.2	619.8	619.3
40°	663.3	641.0	625.6	611.9	609.0	602.2	597.6	594.2	594.2	594.8	594.2
42.5°	626.7	606.7	593.1	581.3	577.9	573.9	569.3	569.0	570.0	571.9	570.0
45°	571.3	557.1	547.3	541.6	535.3	531.3	530.7	532.4	533.0	533.6	535.3
47.5°	520.4	510.8	502.0	495.8	493.0	492.3	491.6	494.6	497.4	498.4	501.0
50°	490.2	479.3	471.9	467.9	465.6	464.5	465.6	469.1	471.3	474.2	475.9
52.5°	456.3	448.7	443.6	440.5	439.5	440.2	440.5	444.4	448.1	449.0	449.9
55°	409.7	403.9	402.8	397.6	399.9	399.3	402.2	404.5	407.9	411.4	411.9
57.5°	363.0	358.4	355.3	355.9	356.5	359.0	361.4	365.4	369.1	372.7	373.1
60°	331.9	329.7	328.0	328.0	329.1	332.5	335.4	339.3	341.6	344.0	345.6
62.5°	303.6	301.4	299.6	300.5	303.5	305.6	308.8	311.0	313.3	315.6	316.4
65°	258.8	257.7	259.4	260.5	261.1	264.0	267.9	269.7	271.9	273.1	277.1
67.5°	217.6	217.7	217.6	219.1	222.5	223.2	227.0	230.9	231.4	233.6	236.2
70°	189.7	190.8	192.0	193.1	196.0	197.1	199.9	201.6	204.0	205.7	207.4
72.5°	164.1	164.3	165.5	165.2	167.6	170.1	172.5	174.3	176.5	178.7	180.4
75°	126.2	126.2	127.4	127.9	130.9	133.7	133.1	134.2	136.6	138.8	140.0
77.5°	92.2	90.9	92.2	92.8	93.7	96.1	96.5	98.2	100.7	100.0	101.3
80°	70.3	68.5	70.3	70.9	70.9	73.7	73.7	74.8	76.5	74.8	76.5
82.5°	50.2	49.3	50.6	50.7	51.7	51.7	52.7	52.9	54.6	53.8	54.6
85°	25.1	24.5	25.1	24.5	25.1	25.7	25.7	25.1	25.1	26.3	24.5
87.5°	9.6	9.5	9.3	9.6	9.4	9.2	9.0	9.1	9.3	8.6	8.7
90°	8.9	10.6	12.1	13.5	15.0	16.4	17.4	18.3	19.2	20.1	20.8
92.5°	15.9	16.2	16.9	17.7	18.3	19.1	19.5	20.1	20.5	21.0	21.4
95°	29.4	26.9	28.2	29.5	30.8	32.1	33.0	33.9	34.9	35.7	36.1
97.5°	38.1	31.1	34.1	37.0	40.0	43.0	43.7	44.4	45.1	45.9	46.3
100°	45.5	34.4	37.5	40.6	43.8	46.9	48.4	49.9	51.3	52.8	53.6
102.5°	167.8	152.2	126.2	100.2	74.2	48.2	50.1	52.0	53.9	55.8	57.0
105°	272.1	249.9	199.9	150.0	100.1	50.2	52.2	54.2	56.2	58.2	59.6
107.5°	337.4	309.7	249.9	189.9	130.1	70.3	68.2	66.1	64.1	62.1	61.4
110°	379.8	355.3	302.5	249.7	196.8	144.0	125.7	107.4	89.1	70.9	62.1



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	420.2	415.3	402.3	389.3	376.2	363.2	296.4	229.7	163.1	96.3	63.3
115°	485.5	489.3	493.9	498.4	503.1	507.6	422.9	338.3	253.7	169.0	120.1
117.5°	546.4	549.7	552.8	555.9	559.1	562.2	541.7	521.2	500.8	480.4	448.5
120°	586.9	589.9	593.1	596.5	599.8	603.0	605.3	607.4	609.6	611.8	600.5
122.5°	624.3	627.6	631.1	634.7	638.3	641.9	643.2	644.5	645.8	647.1	645.4
125°	678.4	681.3	684.8	688.3	691.7	695.2	696.5	697.8	699.0	700.3	701.2
127.5°	730.2	732.9	735.5	738.0	740.6	743.2	745.1	747.0	748.8	750.7	751.7
130°	763.6	766.1	768.1	770.2	772.1	774.2	776.2	778.2	780.2	782.2	783.2
132.5°	794.8	797.0	799.1	801.1	803.1	805.1	806.8	808.6	810.3	812.0	812.8
135°	839.4	841.6	843.3	844.9	846.5	848.3	850.1	851.9	853.7	855.5	856.3
137.5°	879.1	881.1	883.0	884.8	886.7	888.6	890.4	892.1	893.9	895.7	896.3
140°	905.1	906.8	908.8	910.9	912.8	914.9	916.5	918.2	919.8	921.4	921.8
142.5°	928.2	930.0	932.3	934.6	936.9	939.2	940.7	942.2	943.7	945.2	945.5
145°	959.4	960.9	964.0	967.1	970.2	973.3	974.6	975.9	977.1	978.4	978.6
147.5°	989.7	990.9	994.0	997.0	1000.1	1003.2	1004.2	1005.1	1006.1	1007.0	1007.1
150°	1008.5	1009.3	1012.2	1015.1	1018.0	1021.0	1022.1	1023.2	1024.2	1025.4	1025.5
152.5°	1025.6	1026.3	1029.1	1031.9	1034.7	1037.4	1038.5	1039.7	1040.7	1041.8	1041.8
155°	1050.6	1050.9	1053.1	1055.2	1057.5	1059.6	1060.8	1061.9	1062.9	1064.0	1063.9
157.5°	1071.9	1071.9	1073.5	1075.0	1076.5	1078.1	1079.3	1080.6	1081.8	1083.1	1083.0
160°	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1090.4	1091.5	1092.5	1093.6	1093.6
162.5°	1095.5	1095.4	1096.3	1097.3	1098.2	1099.2	1100.4	1101.6	1102.9	1104.1	1104.0
165°	1109.6	1109.3	1109.8	1110.3	1110.9	1111.5	1112.8	1114.0	1115.3	1116.6	1116.6
167.5°	1120.1	1119.8	1120.3	1120.8	1121.4	1121.9	1123.1	1124.4	1125.7	1127.0	1126.8
170°	1126.0	1125.7	1126.0	1126.4	1126.8	1127.1	1128.4	1129.7	1130.9	1132.2	1132.0
172.5°	1130.0	1129.6	1130.0	1130.3	1130.7	1131.1	1132.4	1133.6	1134.9	1136.2	1136.0
175°	1134.4	1133.9	1134.3	1134.6	1135.0	1135.3	1136.6	1137.9	1139.2	1140.5	1140.2
177.5°	1136.2	1135.7	1135.9	1136.0	1136.2	1136.3	1137.4	1138.4	1139.4	1140.4	1140.3
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1425.7	1424.9	1424.9	1420.7	1424.9	1424.9	1425.7	1430.4	1431.7	1432.6	1430.8
5°	1322.6	1320.9	1318.0	1320.9	1318.0	1320.9	1322.6	1330.6	1334.6	1338.6	1342.0
7.5°	1220.6	1213.7	1212.6	1205.9	1212.6	1213.7	1220.6	1224.3	1232.3	1241.4	1249.6
10°	1146.1	1141.5	1140.9	1130.1	1140.9	1141.5	1146.1	1155.8	1163.7	1174.7	1186.0
12.5°	1089.4	1078.4	1080.6	1074.3	1080.6	1078.4	1089.4	1089.5	1098.9	1105.6	1123.4
15°	991.3	991.3	988.9	979.2	988.9	991.3	991.3	1006.7	1009.5	1020.4	1035.8
17.5°	920.8	919.5	914.1	916.9	914.1	919.5	920.8	932.0	934.0	948.5	961.2
20°	878.7	875.3	868.4	868.4	868.4	875.3	878.7	884.9	892.4	901.0	911.8
22.5°	839.0	838.7	831.4	833.6	831.4	838.7	839.0	844.7	851.7	861.2	870.2
25°	792.4	787.8	784.5	786.1	784.5	787.8	792.4	793.0	801.0	807.3	813.0
27.5°	748.3	745.8	745.5	740.9	745.5	745.8	748.3	749.8	754.3	758.0	763.4
30°	722.7	717.0	718.2	715.3	718.2	717.0	722.7	723.3	725.6	727.9	734.2
32.5°	693.4	691.4	690.3	687.9	690.3	691.4	693.4	694.5	699.0	701.4	706.3
35°	653.6	654.2	651.3	652.5	651.3	654.2	653.6	654.7	655.3	657.5	662.2
37.5°	618.7	620.5	619.2	619.6	619.2	620.5	618.7	619.3	619.8	620.2	621.6
40°	595.9	595.9	595.9	597.6	595.9	595.9	595.9	594.2	594.8	594.2	594.2
42.5°	573.9	573.0	572.1	572.0	572.1	573.0	573.9	570.0	571.9	570.0	569.0
45°	536.5	538.2	538.7	535.9	538.7	538.2	536.5	535.3	533.6	533.0	532.4
47.5°	502.6	502.7	502.6	505.1	502.6	502.7	502.6	501.0	498.4	497.4	494.6
50°	478.8	477.6	478.8	477.6	478.8	477.6	478.8	475.9	474.2	471.3	469.1
52.5°	453.7	453.8	453.1	453.0	453.1	453.8	453.7	449.9	449.0	448.1	444.4
55°	414.2	415.3	414.7	414.7	414.7	415.3	414.2	411.9	411.4	407.9	404.5
57.5°	373.4	374.4	375.2	372.7	375.2	374.4	373.4	373.1	372.7	369.1	365.4
60°	345.1	347.9	347.3	346.2	347.3	347.9	345.1	345.6	344.0	341.6	339.3
62.5°	319.0	320.0	319.9	319.7	319.9	320.0	319.0	316.4	315.6	313.3	311.0
65°	278.8	279.9	278.2	279.9	278.2	279.9	278.8	277.1	273.1	271.9	269.7
67.5°	235.5	235.8	237.1	237.9	237.1	235.8	235.5	236.2	233.6	231.4	230.9
70°	208.5	207.9	209.7	211.4	209.7	207.9	208.5	207.4	205.7	204.0	201.6
72.5°	180.2	181.4	180.9	182.1	180.9	181.4	180.2	180.4	178.7	176.5	174.3
75°	138.8	140.5	140.0	141.7	140.0	140.5	138.8	140.0	138.8	136.6	134.2
77.5°	100.3	100.6	100.3	101.3	100.3	100.6	100.3	101.3	100.0	100.7	98.2
80°	76.5	75.4	74.3	76.5	74.3	75.4	76.5	76.5	74.8	76.5	74.8
82.5°	53.2	53.9	52.8	52.8	52.8	53.9	53.2	54.6	53.8	54.6	52.9
85°	24.5	24.0	22.8	22.8	22.8	24.0	24.5	24.5	26.3	25.1	25.1
87.5°	8.8	8.4	8.5	8.1	8.5	8.4	8.8	8.7	8.6	9.3	9.1
90°	21.1	21.4	21.9	22.2	21.9	21.4	21.1	20.8	20.1	19.2	18.3
92.5°	21.5	21.8	22.0	22.2	22.0	21.8	21.5	21.4	21.0	20.5	20.1
95°	35.9	35.7	35.6	35.4	35.6	35.7	35.9	36.1	35.7	34.9	33.9
97.5°	46.6	46.8	47.0	47.2	47.0	46.8	46.6	46.3	45.9	45.1	44.4
100°	54.0	54.4	54.8	55.1	54.8	54.4	54.0	53.6	52.8	51.3	49.9
102.5°	57.5	58.0	58.5	59.1	58.5	58.0	57.5	57.0	55.8	53.9	52.0
105°	60.4	61.0	61.8	62.5	61.8	61.0	60.4	59.6	58.2	56.2	54.2
107.5°	62.2	62.9	63.6	64.3	63.6	62.9	62.2	61.4	62.1	64.1	66.1
110°	62.8	63.5	64.2	65.0	64.2	63.5	62.8	62.1	70.9	89.1	107.4



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	63.9	64.5	65.1	65.7	65.1	64.5	63.9	63.3	96.3	163.1	229.7
115°	106.9	93.8	80.6	67.5	80.6	93.8	106.9	120.1	169.0	253.7	338.3
117.5°	405.2	362.0	318.7	275.4	318.7	362.0	405.2	448.5	480.4	500.8	521.2
120°	575.9	551.2	526.5	501.9	526.5	551.2	575.9	600.5	611.8	609.6	607.4
122.5°	640.6	635.8	631.0	626.3	631.0	635.8	640.6	645.4	647.1	645.8	644.5
125°	701.8	702.3	702.8	703.4	702.8	702.3	701.8	701.2	700.3	699.0	697.8
127.5°	751.8	751.9	752.0	752.1	752.0	751.9	751.8	751.7	750.7	748.8	747.0
130°	782.9	782.7	782.6	782.4	782.6	782.7	782.9	783.2	782.2	780.2	778.2
132.5°	812.5	812.4	812.2	812.0	812.2	812.4	812.5	812.8	812.0	810.3	808.6
135°	855.9	855.5	855.1	854.8	855.1	855.5	855.9	856.3	855.5	853.7	851.9
137.5°	895.7	895.0	894.4	893.8	894.4	895.0	895.7	896.3	895.7	893.9	892.1
140°	920.9	920.0	919.0	918.2	919.0	920.0	920.9	921.8	921.4	919.8	918.2
142.5°	944.6	943.7	942.8	941.8	942.8	943.7	944.6	945.5	945.2	943.7	942.2
145°	977.7	976.7	975.9	974.9	975.9	976.7	977.7	978.6	978.4	977.1	975.9
147.5°	1006.3	1005.6	1004.8	1004.0	1004.8	1005.6	1006.3	1007.1	1007.0	1006.1	1005.1
150°	1024.6	1023.6	1022.7	1021.8	1022.7	1023.6	1024.6	1025.5	1025.4	1024.2	1023.2
152.5°	1040.6	1039.4	1038.2	1037.0	1038.2	1039.4	1040.6	1041.8	1041.8	1040.7	1039.7
155°	1062.4	1060.9	1059.5	1058.0	1059.5	1060.9	1062.4	1063.9	1064.0	1062.9	1061.9
157.5°	1081.5	1080.1	1078.7	1077.3	1078.7	1080.1	1081.5	1083.0	1083.1	1081.8	1080.6
160°	1092.3	1091.0	1089.8	1088.5	1089.8	1091.0	1092.3	1093.6	1093.6	1092.5	1091.5
162.5°	1102.3	1100.8	1099.2	1097.7	1099.2	1100.8	1102.3	1104.0	1104.1	1102.9	1101.6
165°	1115.3	1114.0	1112.8	1111.5	1112.8	1114.0	1115.3	1116.6	1116.6	1115.3	1114.0
167.5°	1125.2	1123.5	1121.9	1120.2	1121.9	1123.5	1125.2	1126.8	1127.0	1125.7	1124.4
170°	1130.4	1128.8	1127.1	1125.5	1127.1	1128.8	1130.4	1132.0	1132.2	1130.9	1129.7
172.5°	1134.4	1132.7	1131.1	1129.5	1131.1	1132.7	1134.4	1136.0	1136.2	1134.9	1133.6
175°	1138.3	1136.5	1134.7	1132.9	1134.7	1136.5	1138.3	1140.2	1140.5	1139.2	1137.9
177.5°	1138.9	1137.6	1136.3	1135.1	1136.3	1137.6	1138.9	1140.3	1140.4	1139.4	1138.4
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1428.5	1433.6	1441.3	1449.6	1454.6	1464.1	1466.9	1471.4	1475.6	1485.2	1495.2
5°	1346.0	1354.0	1372.9	1383.1	1397.4	1414.0	1424.9	1436.3	1448.9	1470.6	1490.6
7.5°	1257.6	1270.9	1294.3	1313.5	1333.9	1357.7	1374.8	1397.4	1416.2	1446.8	1476.0
10°	1198.6	1217.5	1238.6	1261.5	1290.0	1315.2	1339.2	1367.7	1390.6	1427.1	1461.5
12.5°	1145.6	1148.5	1178.7	1203.9	1242.9	1274.0	1301.7	1338.5	1360.9	1404.3	1440.4
15°	1052.9	1070.1	1097.5	1117.5	1163.7	1203.2	1242.1	1280.3	1306.1	1359.7	1407.1
17.5°	974.9	990.7	1018.7	1051.5	1084.8	1124.0	1174.3	1214.6	1249.6	1311.0	1367.0
20°	925.5	944.9	973.5	1007.2	1036.4	1079.2	1122.7	1168.9	1206.6	1275.7	1341.4
22.5°	883.5	898.8	921.9	955.1	987.0	1026.2	1073.8	1124.1	1163.6	1238.3	1304.8
25°	824.4	837.0	851.8	879.3	915.2	958.1	995.2	1050.7	1108.4	1178.0	1258.6
27.5°	771.2	780.1	793.2	817.3	845.2	885.3	926.5	979.1	1037.2	1112.8	1197.8
30°	738.7	744.4	757.6	777.6	804.9	836.4	878.1	928.4	987.8	1064.4	1148.9
32.5°	710.4	715.7	724.2	743.3	767.1	793.9	831.5	881.8	938.4	1013.7	1107.3
35°	667.9	671.8	679.3	694.7	707.8	734.2	765.6	811.2	864.4	936.4	1033.5
37.5°	625.5	630.9	635.5	642.0	658.9	676.2	703.5	742.1	794.3	866.9	959.5
40°	597.6	602.2	609.0	611.9	625.6	641.0	663.3	698.7	751.3	817.5	907.8
42.5°	569.3	573.9	577.9	581.3	593.1	606.7	626.7	657.1	703.8	768.2	857.6
45°	530.7	531.3	535.3	541.6	547.3	557.1	571.3	597.6	633.6	694.1	775.2
47.5°	491.6	492.3	493.0	495.8	502.0	510.8	520.4	541.7	573.9	622.2	701.2
50°	465.6	464.5	465.6	467.9	471.9	479.3	490.2	505.6	531.9	577.0	649.6
52.5°	440.5	440.2	439.5	440.5	443.6	448.7	456.3	469.5	493.0	534.5	598.4
55°	402.2	399.3	399.9	397.6	402.8	403.9	409.7	420.5	441.1	469.6	529.6
57.5°	361.4	359.0	356.5	355.9	355.3	358.4	363.0	371.6	387.4	412.3	461.1
60°	335.4	332.5	329.1	328.0	328.0	329.7	331.9	338.2	353.1	375.4	415.3
62.5°	308.8	305.6	303.5	300.5	299.6	301.4	303.6	308.1	318.8	339.7	374.2
65°	267.9	264.0	261.1	260.5	259.4	257.7	258.8	263.4	271.9	288.5	315.9
67.5°	227.0	223.2	222.5	219.1	217.6	217.7	217.6	221.4	226.6	240.9	261.3
70°	199.9	197.1	196.0	193.1	192.0	190.8	189.7	193.1	198.3	210.3	228.0
72.5°	172.5	170.1	167.6	165.2	165.5	164.3	164.1	166.2	170.4	181.4	195.0
75°	133.1	133.7	130.9	127.9	127.4	126.2	126.2	127.9	129.7	138.3	149.1
77.5°	96.5	96.1	93.7	92.8	92.2	90.9	92.2	93.3	94.3	100.0	108.0
80°	73.7	73.7	70.9	70.9	70.3	68.5	70.3	69.1	71.4	77.1	82.8
82.5°	52.7	51.7	51.7	50.7	50.6	49.3	50.2	51.3	52.2	56.1	59.5
85°	25.7	25.7	25.1	24.5	25.1	24.5	25.1	25.7	26.3	28.0	30.8
87.5°	9.0	9.2	9.4	9.6	9.3	9.5	9.6	9.6	10.1	10.2	10.2
90°	17.4	16.4	15.0	13.5	12.1	10.6	8.9	6.9	4.8	2.8	0.9
92.5°	19.5	19.1	18.3	17.7	16.9	16.2	15.9	16.1	16.3	16.4	16.6
95°	33.0	32.1	30.8	29.5	28.2	26.9	29.4	35.4	41.4	47.4	53.5
97.5°	43.7	43.0	40.0	37.0	34.1	31.1	38.1	55.1	72.2	89.1	106.2
100°	48.4	46.9	43.8	40.6	37.5	34.4	45.5	70.5	95.5	120.5	145.6
102.5°	50.1	48.2	74.2	100.2	126.2	152.2	167.8	173.1	178.5	183.7	189.1
105°	52.2	50.2	100.1	150.0	199.9	249.9	272.1	266.6	261.1	255.6	250.1
107.5°	68.2	70.3	130.1	189.9	249.9	309.7	337.4	332.9	328.6	324.2	319.7
110°	125.7	144.0	196.8	249.7	302.5	355.3	379.8	376.0	372.1	368.3	364.5



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	296.4	363.2	376.2	389.3	402.3	415.3	420.2	416.8	413.4	410.0	406.6
115°	422.9	507.6	503.1	498.4	493.9	489.3	485.5	482.4	479.3	476.1	473.0
117.5°	541.7	562.2	559.1	555.9	552.8	549.7	546.4	542.9	539.4	536.0	532.4
120°	605.3	603.0	599.8	596.5	593.1	589.9	586.9	584.1	581.3	578.7	575.9
122.5°	643.2	641.9	638.3	634.7	631.1	627.6	624.3	621.4	618.5	615.6	612.8
125°	696.5	695.2	691.7	688.3	684.8	681.3	678.4	676.0	673.6	671.2	668.8
127.5°	745.1	743.2	740.6	738.0	735.5	732.9	730.2	727.6	725.0	722.4	719.7
130°	776.2	774.2	772.1	770.2	768.1	766.1	763.6	760.7	757.9	754.9	752.0
132.5°	806.8	805.1	803.1	801.1	799.1	797.0	794.8	792.3	789.9	787.4	784.9
135°	850.1	848.3	846.5	844.9	843.3	841.6	839.4	836.5	833.5	830.6	827.7
137.5°	890.4	888.6	886.7	884.8	883.0	881.1	879.1	877.1	875.0	873.0	870.9
140°	916.5	914.9	912.8	910.9	908.8	906.8	905.1	903.6	902.2	900.7	899.2
142.5°	940.7	939.2	936.9	934.6	932.3	930.0	928.2	926.9	925.6	924.2	922.9
145°	974.6	973.3	970.2	967.1	964.0	960.9	959.4	959.6	959.8	959.9	960.1
147.5°	1004.2	1003.2	1000.1	997.0	994.0	990.9	989.7	990.4	991.1	991.8	992.6
150°	1022.1	1021.0	1018.0	1015.1	1012.2	1009.3	1008.5	1009.8	1011.0	1012.3	1013.6
152.5°	1038.5	1037.4	1034.7	1031.9	1029.1	1026.3	1025.6	1027.1	1028.5	1029.9	1031.4
155°	1060.8	1059.6	1057.5	1055.2	1053.1	1050.9	1050.6	1052.2	1053.9	1055.5	1057.2
157.5°	1079.3	1078.1	1076.5	1075.0	1073.5	1071.9	1071.9	1073.2	1074.6	1076.1	1077.5
160°	1090.4	1089.3	1088.2	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3
162.5°	1100.4	1099.2	1098.2	1097.3	1096.3	1095.4	1095.5	1096.5	1097.6	1098.7	1099.8
165°	1112.8	1111.5	1110.9	1110.3	1109.8	1109.3	1109.6	1110.7	1111.7	1112.8	1114.0
167.5°	1123.1	1121.9	1121.4	1120.8	1120.3	1119.8	1120.1	1121.2	1122.3	1123.3	1124.5
170°	1128.4	1127.1	1126.8	1126.4	1126.0	1125.7	1126.0	1127.1	1128.3	1129.3	1130.4
172.5°	1132.4	1131.1	1130.7	1130.3	1130.0	1129.6	1130.0	1131.1	1132.1	1133.2	1134.4
175°	1136.6	1135.3	1135.0	1134.6	1134.3	1133.9	1134.4	1135.7	1136.9	1138.2	1139.4
177.5°	1137.4	1136.3	1136.2	1136.0	1135.9	1135.7	1136.2	1137.2	1138.2	1139.3	1140.3
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1494.4	1496.6	1503.9	1511.2	1519.5	1521.7	1525.4	1522.2	1521.3	1530.0	1536.4
5°	1498.6	1508.8	1528.9	1547.1	1562.5	1573.4	1584.8	1589.4	1597.9	1610.0	1624.8
7.5°	1493.7	1513.7	1545.2	1571.8	1600.9	1621.7	1638.1	1652.0	1669.0	1691.7	1716.5
10°	1488.2	1515.1	1553.4	1586.0	1621.3	1648.2	1670.5	1692.2	1717.4	1748.8	1781.3
12.5°	1478.3	1510.1	1558.0	1596.5	1641.9	1668.4	1698.4	1745.2	1772.2	1816.0	1861.8
15°	1458.0	1493.4	1560.2	1607.7	1659.1	1709.3	1764.8	1809.4	1853.9	1879.6	1944.2
17.5°	1428.0	1480.0	1553.9	1609.3	1674.6	1753.9	1816.1	1866.6	1918.0	1959.7	1992.1
20°	1403.7	1460.3	1544.8	1611.1	1688.8	1773.9	1845.4	1896.8	1941.3	1976.2	1996.1
22.5°	1373.1	1444.2	1526.6	1604.2	1703.4	1787.6	1862.7	1903.2	1940.4	1957.4	1965.1
25°	1324.9	1410.6	1503.7	1598.5	1710.5	1799.7	1868.2	1892.7	1903.6	1887.1	1859.6
27.5°	1272.9	1368.4	1477.3	1587.8	1706.2	1791.8	1841.0	1837.1	1818.7	1765.1	1722.3
30°	1234.1	1339.2	1456.3	1576.8	1695.7	1779.1	1807.7	1779.1	1737.3	1677.4	1616.3
32.5°	1193.3	1302.2	1433.9	1561.3	1676.5	1749.8	1756.0	1706.8	1642.3	1574.1	1497.9
35°	1131.8	1249.5	1391.7	1526.6	1635.6	1682.0	1654.5	1567.7	1491.2	1398.0	1294.0
37.5°	1062.2	1192.1	1334.8	1475.7	1574.5	1586.7	1518.5	1427.1	1319.1	1209.7	1087.4
40°	1010.1	1147.8	1294.6	1436.8	1524.2	1511.7	1424.9	1324.3	1195.8	1062.0	948.4
42.5°	963.5	1101.1	1250.7	1390.3	1460.3	1425.7	1324.3	1200.9	1062.7	936.9	832.8
45°	882.7	1024.3	1177.5	1312.3	1352.3	1290.0	1155.8	1018.6	882.7	777.6	695.3
47.5°	804.3	944.3	1096.0	1214.5	1228.6	1144.9	998.2	857.1	740.2	654.6	596.6
50°	746.7	887.3	1037.5	1143.2	1138.6	1037.5	886.7	752.4	654.7	585.6	546.7
52.5°	695.1	827.9	972.2	1068.2	1044.0	933.8	789.8	670.6	590.3	536.2	501.0
55°	614.8	737.5	874.7	951.8	907.2	785.0	663.3	567.3	507.9	467.4	439.9
57.5°	534.9	650.1	767.5	815.0	765.8	652.9	551.5	481.8	437.1	407.1	389.3
60°	485.6	586.2	690.7	731.8	673.0	572.5	492.5	430.2	394.2	369.6	353.6
62.5°	436.3	526.3	624.9	647.3	593.5	508.5	437.6	385.9	356.3	334.4	319.3
65°	369.1	442.7	517.6	532.4	482.8	417.1	361.1	327.4	301.1	285.1	273.1
67.5°	302.6	361.9	414.9	426.9	383.3	337.8	297.3	267.9	250.1	236.9	226.7
70°	263.4	310.2	353.6	363.3	328.5	287.9	257.1	233.7	217.7	206.2	196.6
72.5°	221.8	260.9	297.0	303.5	275.0	244.1	218.7	200.3	186.1	178.8	169.5
75°	169.7	192.5	220.5	222.2	203.4	184.5	165.1	153.1	145.7	136.6	132.0
77.5°	119.8	137.7	153.7	156.8	145.6	132.8	121.9	112.4	106.2	101.9	97.7
80°	91.4	105.7	112.5	116.6	108.6	99.4	93.2	86.9	82.8	80.0	77.1
82.5°	65.3	74.1	80.6	83.6	79.3	73.8	67.5	64.0	60.9	58.5	57.5
85°	33.1	37.1	41.2	42.3	41.2	38.8	35.4	35.4	33.7	33.1	33.1
87.5°	12.0	14.2	14.6	16.4	15.8	16.1	16.4	16.3	16.1	15.8	15.5
90°	2.8	4.8	6.9	8.9	10.6	12.1	13.5	15.0	16.4	17.4	18.3
92.5°	16.4	16.3	16.1	15.9	16.2	16.9	17.7	18.3	19.1	19.5	20.1
95°	47.4	41.4	35.4	29.4	26.9	28.2	29.5	30.8	32.1	33.0	33.9
97.5°	89.1	72.2	55.1	38.1	31.1	34.1	37.0	40.0	43.0	43.7	44.4
100°	120.5	95.5	70.5	45.5	34.4	37.5	40.6	43.8	46.9	48.4	49.9
102.5°	183.7	178.5	173.1	167.8	152.2	126.2	100.2	74.2	48.2	50.1	52.0
105°	255.6	261.1	266.6	272.1	249.9	199.9	150.0	100.1	50.2	52.2	54.2
107.5°	324.2	328.6	332.9	337.4	309.7	249.9	189.9	130.1	70.3	68.2	66.1
110°	368.3	372.1	376.0	379.8	355.3	302.5	249.7	196.8	144.0	125.7	107.4



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	410.0	413.4	416.8	420.2	415.3	402.3	389.3	376.2	363.2	296.4	229.7
115°	476.1	479.3	482.4	485.5	489.3	493.9	498.4	503.1	507.6	422.9	338.3
117.5°	536.0	539.4	542.9	546.4	549.7	552.8	555.9	559.1	562.2	541.7	521.2
120°	578.7	581.3	584.1	586.9	589.9	593.1	596.5	599.8	603.0	605.3	607.4
122.5°	615.6	618.5	621.4	624.3	627.6	631.1	634.7	638.3	641.9	643.2	644.5
125°	671.2	673.6	676.0	678.4	681.3	684.8	688.3	691.7	695.2	696.5	697.8
127.5°	722.4	725.0	727.6	730.2	732.9	735.5	738.0	740.6	743.2	745.1	747.0
130°	754.9	757.9	760.7	763.6	766.1	768.1	770.2	772.1	774.2	776.2	778.2
132.5°	787.4	789.9	792.3	794.8	797.0	799.1	801.1	803.1	805.1	806.8	808.6
135°	830.6	833.5	836.5	839.4	841.6	843.3	844.9	846.5	848.3	850.1	851.9
137.5°	873.0	875.0	877.1	879.1	881.1	883.0	884.8	886.7	888.6	890.4	892.1
140°	900.7	902.2	903.6	905.1	906.8	908.8	910.9	912.8	914.9	916.5	918.2
142.5°	924.2	925.6	926.9	928.2	930.0	932.3	934.6	936.9	939.2	940.7	942.2
145°	959.9	959.8	959.6	959.4	960.9	964.0	967.1	970.2	973.3	974.6	975.9
147.5°	991.8	991.1	990.4	989.7	990.9	994.0	997.0	1000.1	1003.2	1004.2	1005.1
150°	1012.3	1011.0	1009.8	1008.5	1009.3	1012.2	1015.1	1018.0	1021.0	1022.1	1023.2
152.5°	1029.9	1028.5	1027.1	1025.6	1026.3	1029.1	1031.9	1034.7	1037.4	1038.5	1039.7
155°	1055.5	1053.9	1052.2	1050.6	1050.9	1053.1	1055.2	1057.5	1059.6	1060.8	1061.9
157.5°	1076.1	1074.6	1073.2	1071.9	1071.9	1073.5	1075.0	1076.5	1078.1	1079.3	1080.6
160°	1088.2	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1090.4	1091.5
162.5°	1098.7	1097.6	1096.5	1095.5	1095.4	1096.3	1097.3	1098.2	1099.2	1100.4	1101.6
165°	1112.8	1111.7	1110.7	1109.6	1109.3	1109.8	1110.3	1110.9	1111.5	1112.8	1114.0
167.5°	1123.3	1122.3	1121.2	1120.1	1119.8	1120.3	1120.8	1121.4	1121.9	1123.1	1124.4
170°	1129.3	1128.3	1127.1	1126.0	1125.7	1126.0	1126.4	1126.8	1127.1	1128.4	1129.7
172.5°	1133.2	1132.1	1131.1	1130.0	1129.6	1130.0	1130.3	1130.7	1131.1	1132.4	1133.6
175°	1138.2	1136.9	1135.7	1134.4	1133.9	1134.3	1134.6	1135.0	1135.3	1136.6	1137.9
177.5°	1139.3	1138.2	1137.2	1136.2	1135.7	1135.9	1136.0	1136.2	1136.3	1137.4	1138.4
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5	1486.5
2.5°	1541.9	1548.3	1548.3	1549.2	1556.5	1555.6	1555.1
5°	1640.8	1650.5	1651.7	1662.0	1668.8	1666.6	1660.3
7.5°	1734.1	1752.2	1765.9	1773.6	1782.6	1788.2	1785.7
10°	1808.2	1834.4	1850.5	1861.3	1874.5	1884.2	1880.8
12.5°	1875.4	1906.7	1928.6	1947.2	1949.0	1961.4	1953.0
15°	1980.2	2013.3	2016.7	2030.4	2041.3	2040.1	2040.7
17.5°	2014.8	2025.4	2027.6	2027.9	2028.1	2024.0	2015.3
20°	2002.4	1998.5	1988.7	1981.3	1968.2	1966.4	1955.1
22.5°	1944.0	1931.3	1906.9	1890.8	1870.4	1865.0	1861.8
25°	1828.8	1800.8	1762.0	1724.8	1714.5	1694.5	1700.2
27.5°	1670.8	1627.1	1585.0	1554.9	1527.6	1497.6	1506.2
30°	1559.7	1510.5	1451.1	1405.4	1376.3	1347.7	1342.6
32.5°	1427.1	1355.1	1288.9	1248.6	1204.0	1185.9	1166.1
35°	1198.6	1128.3	1062.6	1006.1	973.5	948.4	925.5
37.5°	993.1	912.1	859.1	813.3	789.8	775.4	779.0
40°	865.6	794.7	755.9	721.0	699.3	689.0	691.3
42.5°	762.2	709.2	677.3	653.3	638.0	632.3	630.9
45°	645.0	615.3	589.0	575.3	567.9	561.6	557.6
47.5°	565.0	540.8	526.0	517.8	511.3	504.9	504.8
50°	517.0	501.0	490.8	482.2	477.1	472.5	476.5
52.5°	480.4	465.9	455.6	447.9	446.0	441.9	441.8
55°	426.2	414.7	407.3	400.5	397.1	394.8	391.9
57.5°	376.9	366.0	359.1	354.8	348.3	345.9	345.1
60°	341.6	333.0	326.2	320.5	317.6	313.1	313.1
62.5°	309.2	300.7	294.2	289.9	285.2	283.4	283.9
65°	262.3	255.4	249.1	244.5	243.4	240.0	241.1
67.5°	219.0	214.5	207.8	205.3	203.2	201.3	199.9
70°	190.3	185.7	182.3	178.8	177.1	177.1	177.1
72.5°	166.0	160.6	158.5	154.1	155.2	153.3	151.5
75°	128.5	125.1	123.4	121.7	118.8	118.8	118.8
77.5°	94.6	93.6	91.5	89.7	89.0	88.4	88.7
80°	73.1	72.6	71.4	71.4	70.3	69.7	68.5
82.5°	56.2	54.8	54.1	53.6	53.4	53.2	53.0
85°	32.0	30.8	30.8	31.4	30.3	30.3	30.8
87.5°	16.2	16.4	16.0	16.1	16.6	16.3	16.4
90°	19.2	20.1	20.8	21.1	21.4	21.9	22.2
92.5°	20.5	21.0	21.4	21.5	21.8	22.0	22.2
95°	34.9	35.7	36.1	35.9	35.7	35.6	35.4
97.5°	45.1	45.9	46.3	46.6	46.8	47.0	47.2
100°	51.3	52.8	53.6	54.0	54.4	54.8	55.1
102.5°	53.9	55.8	57.0	57.5	58.0	58.5	59.1
105°	56.2	58.2	59.6	60.4	61.0	61.8	62.5
107.5°	64.1	62.1	61.4	62.2	62.9	63.6	64.3
110°	89.1	70.9	62.1	62.8	63.5	64.2	65.0



TEST NUMBER: P331567-935

CATALOG NUMBER: S122DIW-S865D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	163.1	96.3	63.3	63.9	64.5	65.1	65.7
115°	253.7	169.0	120.1	106.9	93.8	80.6	67.5
117.5°	500.8	480.4	448.5	405.2	362.0	318.7	275.4
120°	609.6	611.8	600.5	575.9	551.2	526.5	501.9
122.5°	645.8	647.1	645.4	640.6	635.8	631.0	626.3
125°	699.0	700.3	701.2	701.8	702.3	702.8	703.4
127.5°	748.8	750.7	751.7	751.8	751.9	752.0	752.1
130°	780.2	782.2	783.2	782.9	782.7	782.6	782.4
132.5°	810.3	812.0	812.8	812.5	812.4	812.2	812.0
135°	853.7	855.5	856.3	855.9	855.5	855.1	854.8
137.5°	893.9	895.7	896.3	895.7	895.0	894.4	893.8
140°	919.8	921.4	921.8	920.9	920.0	919.0	918.2
142.5°	943.7	945.2	945.5	944.6	943.7	942.8	941.8
145°	977.1	978.4	978.6	977.7	976.7	975.9	974.9
147.5°	1006.1	1007.0	1007.1	1006.3	1005.6	1004.8	1004.0
150°	1024.2	1025.4	1025.5	1024.6	1023.6	1022.7	1021.8
152.5°	1040.7	1041.8	1041.8	1040.6	1039.4	1038.2	1037.0
155°	1062.9	1064.0	1063.9	1062.4	1060.9	1059.5	1058.0
157.5°	1081.8	1083.1	1083.0	1081.5	1080.1	1078.7	1077.3
160°	1092.5	1093.6	1093.6	1092.3	1091.0	1089.8	1088.5
162.5°	1102.9	1104.1	1104.0	1102.3	1100.8	1099.2	1097.7
165°	1115.3	1116.6	1116.6	1115.3	1114.0	1112.8	1111.5
167.5°	1125.7	1127.0	1126.8	1125.2	1123.5	1121.9	1120.2
170°	1130.9	1132.2	1132.0	1130.4	1128.8	1127.1	1125.5
172.5°	1134.9	1136.2	1136.0	1134.4	1132.7	1131.1	1129.5
175°	1139.2	1140.5	1140.2	1138.3	1136.5	1134.7	1132.9
177.5°	1139.4	1140.4	1140.3	1138.9	1137.6	1136.3	1135.1
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0

(END OF REPORT)