

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331859-935

Luminaire Tested: **S122RDIW-S1005D1240U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331859-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1240U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7268.0 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331859-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331859-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31	26
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23
5	68	57	49	43	62	52	45	40	44	38	35	36	32	29	28	26	24	20
6	63	51	43	37	57	47	40	35	39	34	30	32	28	26	26	23	21	18
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	25	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23541	23541	23541
5°	23631	23246	23376
10°	23451	22866	22673
15°	23181	22188	21549
20°	22807	21220	20155
25°	22425	20122	18805
30°	21895	18990	17074
35°	21378	17763	15554
40°	20858	16493	13793
45°	20247	15066	12202
50°	19623	13622	10638
55°	18978	12073	9137
60°	18235	10440	7585
65°	17391	8772	6907
70°	16386	7227	6354
75°	15147	6588	5926
80°	13371	5895	5393
85°	10504	4650	4650



TEST NUMBER: P331859-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.5	1.9
10°-20°	374.7	5.2
20°-30°	526.2	7.2
30°-40°	573.8	7.9
40°-50°	527.6	7.3
50°-60°	414.4	5.7
60°-70°	270.2	3.7
70°-80°	139.3	1.9
80°-90°	39.7	0.5
90°-100°	48.6	0.7
100°-110°	178.1	2.4
110°-120°	476.0	6.5
120°-130°	785.7	10.8
130°-140°	835.5	11.5
140°-150°	776.6	10.7
150°-160°	624.4	8.6
160°-170°	402.3	5.5
170°-180°	138.5	1.9
0°-30°	1037.4	14.3
0°-40°	1611.3	22.2
0°-60°	2553.2	35.1
0°-90°	3002.4	41.3
90°-120°	702.6	9.7
90°-150°	3100.4	42.7
90°-180°	4266.0	58.7
0°-180°	7268.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1458	1458	1458	1458	1458	
5°	1458	1451	1434	1445	1442	138
15°	1387	1371	1327	1303	1289	390
25°	1259	1214	1130	1077	1056	579
35°	1085	1015	901	821	789	678
45°	887	796	660	570	534	684
55°	674	569	429	353	325	602
65°	455	348	230	187	181	451
75°	243	153	106	97	95	257
85°	57	30	25	25	25	67
90°	1	12	21	26	28	6
95°	68	36	41	46	45	84
105°	320	334	64	75	80	342
115°	606	624	650	185	86	596
125°	856	870	890	897	900	763
135°	1060	1076	1086	1096	1094	818
145°	1229	1229	1246	1253	1248	768
155°	1353	1345	1357	1362	1354	623
165°	1426	1420	1423	1429	1423	403
175°	1459	1452	1454	1460	1450	139
180°	1456	1456	1456	1456	1456	



TEST NUMBER: P331859-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0
2.5°	1463.4	1462.2	1460.9	1459.8	1458.6	1456.7	1454.1	1451.6	1449.1	1446.5	1448.8
5°	1458.0	1456.6	1455.1	1453.6	1452.2	1449.6	1445.7	1441.9	1438.1	1434.3	1436.9
7.5°	1443.0	1441.2	1439.4	1437.5	1435.7	1432.6	1428.1	1423.7	1419.3	1414.8	1415.6
10°	1430.4	1428.3	1426.2	1424.2	1422.1	1418.2	1412.3	1406.4	1400.6	1394.7	1393.9
12.5°	1414.5	1412.0	1409.5	1407.0	1404.5	1399.4	1391.9	1384.4	1376.9	1369.4	1367.8
15°	1386.8	1383.5	1380.4	1377.1	1373.9	1367.3	1357.4	1347.4	1337.4	1327.4	1321.9
17.5°	1352.7	1347.8	1342.9	1338.0	1333.1	1324.2	1311.4	1298.6	1285.8	1273.1	1266.4
20°	1327.4	1321.5	1315.7	1309.8	1304.0	1293.7	1279.0	1264.4	1249.7	1235.0	1227.7
22.5°	1299.9	1293.4	1286.9	1280.3	1273.7	1262.1	1245.6	1229.1	1212.5	1196.0	1186.5
25°	1258.8	1249.4	1240.0	1230.6	1221.2	1206.9	1187.6	1168.2	1148.8	1129.5	1117.5
27.5°	1209.2	1199.0	1188.8	1178.6	1168.4	1152.4	1130.6	1108.7	1086.9	1065.1	1051.1
30°	1174.4	1163.2	1152.1	1140.9	1129.8	1112.5	1089.0	1065.6	1042.2	1018.6	1003.7
32.5°	1140.6	1127.6	1114.6	1101.6	1088.5	1070.1	1046.1	1022.2	998.2	974.3	957.3
35°	1084.6	1069.7	1054.7	1039.7	1024.8	1004.4	978.6	952.9	927.0	901.2	882.8
37.5°	1028.7	1012.3	995.8	979.4	963.0	941.1	913.5	886.1	858.5	831.0	810.7
40°	989.6	972.1	954.4	936.9	919.3	896.2	867.8	839.4	810.9	782.5	761.6
42.5°	949.5	931.0	912.5	893.9	875.4	851.4	822.1	792.6	763.3	733.9	712.4
45°	886.7	867.0	847.4	827.8	808.1	782.9	752.1	721.3	690.5	659.8	638.9
47.5°	825.4	804.7	783.9	763.0	742.2	715.9	684.2	652.3	620.5	588.8	568.1
50°	781.2	760.3	739.5	718.7	697.8	671.3	639.1	606.8	574.5	542.3	522.1
52.5°	737.9	716.1	694.4	672.6	650.8	624.2	592.6	561.1	529.5	498.0	478.5
55°	674.2	651.4	628.5	605.6	582.8	555.5	523.8	492.1	460.5	428.9	411.2
57.5°	609.1	585.7	562.1	538.7	515.2	488.3	457.9	427.4	397.0	366.5	350.4
60°	564.7	541.3	517.8	494.4	470.9	444.1	413.9	383.7	353.4	323.3	308.3
62.5°	521.5	498.0	474.6	451.1	427.7	401.5	372.7	343.9	315.1	286.4	272.1
65°	455.2	431.4	407.8	384.0	360.2	335.2	308.8	282.4	256.0	229.6	219.6
67.5°	391.3	367.8	344.2	320.6	297.0	273.4	249.7	225.9	202.2	178.4	173.8
70°	347.1	324.2	301.3	278.4	255.5	234.0	213.8	193.6	173.3	153.1	150.2
72.5°	304.8	282.8	261.0	239.0	217.1	197.9	181.8	165.5	149.2	133.0	130.5
75°	242.8	222.2	201.7	181.2	160.7	145.4	135.4	125.5	115.5	105.6	103.5
77.5°	181.8	163.8	145.9	127.9	109.8	98.4	93.6	88.8	83.9	79.2	78.0
80°	143.8	128.9	113.9	98.9	84.0	75.1	72.2	69.2	66.3	63.4	62.2
82.5°	109.0	97.3	85.7	74.0	62.3	55.4	53.5	51.5	49.5	47.5	46.8
85°	56.7	50.5	44.4	38.2	32.1	28.6	27.7	26.9	25.9	25.1	25.1
87.5°	17.1	15.8	14.4	13.0	11.6	11.2	11.5	11.9	12.3	12.7	12.7
90°	1.0	3.6	6.2	8.8	11.4	13.6	15.4	17.3	19.2	21.1	22.2
92.5°	21.3	21.0	20.8	20.6	20.3	20.7	21.6	22.6	23.5	24.5	25.1
95°	68.4	60.7	53.0	45.3	37.5	34.5	36.2	37.8	39.4	41.1	42.3
97.5°	135.9	114.1	92.3	70.6	48.8	39.8	43.6	47.4	51.2	55.0	55.9
100°	186.4	154.4	122.3	90.2	58.2	44.1	48.1	52.1	56.1	60.0	61.9
102.5°	242.0	235.2	228.4	221.7	214.9	194.8	161.5	128.3	95.0	61.7	64.1
105°	320.2	327.2	334.2	341.2	348.3	319.9	256.0	192.0	128.1	64.2	66.8
107.5°	409.3	414.9	420.6	426.3	432.0	396.5	319.9	243.2	166.6	90.0	87.3
110°	466.6	471.5	476.4	481.3	486.2	454.9	387.3	319.6	251.9	184.3	160.9



TEST NUMBER: P331859-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	520.5	524.9	529.2	533.6	538.0	531.8	515.1	498.3	481.6	464.9	379.5
115°	605.6	609.6	613.5	617.5	621.6	626.5	632.3	638.2	644.0	649.9	541.5
117.5°	681.7	686.1	690.5	695.0	699.5	703.7	707.7	711.7	715.7	719.8	693.5
120°	737.3	740.8	744.2	747.8	751.3	755.2	759.4	763.6	767.8	772.0	774.8
122.5°	784.5	788.2	791.9	795.6	799.3	803.4	808.0	812.5	817.2	821.7	823.4
125°	856.3	859.3	862.4	865.4	868.4	872.2	876.7	881.1	885.5	890.0	891.7
127.5°	921.4	924.7	928.1	931.5	934.9	938.2	941.5	944.9	948.1	951.5	953.9
130°	962.7	966.4	970.2	973.9	977.7	980.8	983.3	985.9	988.5	991.1	993.7
132.5°	1004.8	1008.0	1011.2	1014.3	1017.5	1020.4	1023.0	1025.5	1028.1	1030.7	1032.9
135°	1059.5	1063.2	1067.0	1070.7	1074.5	1077.5	1079.5	1081.7	1083.7	1085.9	1088.2
137.5°	1114.9	1117.6	1120.2	1122.8	1125.4	1127.9	1130.3	1132.7	1135.1	1137.5	1139.8
140°	1151.2	1153.1	1154.9	1156.8	1158.6	1160.9	1163.5	1166.1	1168.6	1171.2	1173.3
142.5°	1181.6	1183.2	1184.9	1186.5	1188.3	1190.6	1193.5	1196.4	1199.4	1202.4	1204.3
145°	1229.1	1228.9	1228.6	1228.4	1228.2	1230.0	1234.1	1238.0	1242.0	1246.0	1247.6
147.5°	1270.6	1269.7	1268.9	1267.9	1267.0	1268.6	1272.5	1276.4	1280.4	1284.3	1285.6
150°	1297.6	1296.0	1294.3	1292.6	1291.0	1292.1	1295.8	1299.6	1303.3	1307.1	1308.5
152.5°	1320.3	1318.5	1316.6	1314.8	1313.0	1313.9	1317.4	1321.0	1324.6	1328.1	1329.6
155°	1353.4	1351.3	1349.2	1347.0	1345.0	1345.3	1348.2	1350.9	1353.8	1356.6	1358.0
157.5°	1379.3	1377.5	1375.7	1374.0	1372.2	1372.3	1374.2	1376.2	1378.2	1380.2	1381.7
160°	1394.5	1393.1	1391.6	1390.3	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5	1395.9
162.5°	1408.0	1406.5	1405.2	1403.8	1402.3	1402.2	1403.4	1404.6	1405.9	1407.1	1408.7
165°	1426.1	1424.7	1423.2	1421.9	1420.5	1420.1	1420.8	1421.5	1422.2	1422.9	1424.5
167.5°	1439.6	1438.1	1436.8	1435.4	1433.9	1433.6	1434.3	1434.9	1435.5	1436.1	1437.8
170°	1447.2	1445.7	1444.3	1442.9	1441.5	1441.1	1441.5	1442.0	1442.4	1442.9	1444.6
172.5°	1452.2	1450.8	1449.4	1447.9	1446.6	1446.1	1446.6	1447.0	1447.5	1447.9	1449.6
175°	1458.7	1457.1	1455.4	1453.8	1452.2	1451.6	1452.1	1452.5	1453.0	1453.5	1455.1
177.5°	1459.7	1458.4	1457.2	1455.9	1454.5	1454.0	1454.1	1454.3	1454.5	1454.7	1456.0
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331859-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0
2.5°	1451.1	1453.5	1455.9	1456.7	1456.3	1455.9	1455.3	1454.9
5°	1439.6	1442.3	1444.8	1445.7	1444.8	1444.0	1443.1	1442.3
7.5°	1416.3	1417.0	1417.8	1417.5	1415.9	1414.4	1412.9	1411.4
10°	1392.9	1392.1	1391.2	1389.9	1388.1	1386.4	1384.6	1382.9
12.5°	1366.2	1364.6	1363.0	1360.8	1357.9	1355.0	1352.0	1349.1
15°	1316.3	1310.7	1305.1	1300.9	1298.0	1295.0	1292.1	1289.2
17.5°	1259.8	1253.2	1246.6	1240.7	1235.7	1230.6	1225.5	1220.6
20°	1220.4	1213.1	1205.7	1198.9	1192.4	1185.9	1179.5	1173.0
22.5°	1177.2	1167.7	1158.2	1151.1	1146.3	1141.5	1136.7	1131.9
25°	1105.4	1093.5	1081.4	1073.2	1068.8	1064.4	1060.0	1055.6
27.5°	1037.1	1023.0	1009.0	998.5	991.5	984.6	977.6	970.6
30°	988.8	973.8	958.8	947.4	939.5	931.6	923.7	915.8
32.5°	940.2	923.2	906.0	893.8	886.4	878.9	871.4	864.0
35°	864.3	845.8	827.3	814.9	808.4	801.9	795.5	789.1
37.5°	790.3	770.0	749.6	735.7	728.4	721.0	713.6	706.2
40°	740.8	720.0	699.2	685.0	677.3	669.7	662.1	654.4
42.5°	690.9	669.3	647.8	633.4	625.9	618.5	611.2	603.8
45°	618.1	597.3	576.4	562.6	555.5	548.5	541.4	534.4
47.5°	547.3	526.7	505.9	492.4	486.0	479.7	473.2	466.8
50°	501.9	481.6	461.4	448.2	442.0	435.8	429.7	423.5
52.5°	458.9	439.4	419.9	407.3	401.6	395.9	390.2	384.5
55°	393.6	376.1	358.4	346.9	341.3	335.7	330.2	324.6
57.5°	334.3	318.1	302.0	291.6	287.0	282.2	277.6	272.9
60°	293.3	278.4	263.5	253.7	248.9	244.3	239.5	234.9
62.5°	257.9	243.6	229.4	220.8	218.0	215.2	212.3	209.6
65°	209.7	199.7	189.7	184.3	183.4	182.5	181.7	180.8
67.5°	169.3	164.7	160.1	157.3	156.4	155.5	154.5	153.6
70°	147.2	144.3	141.4	139.3	138.1	136.9	135.8	134.6
72.5°	128.1	125.6	123.1	121.6	120.9	120.2	119.4	118.7
75°	101.4	99.4	97.4	96.2	95.9	95.6	95.3	95.0
77.5°	76.8	75.7	74.5	73.6	73.2	72.8	72.2	71.8
80°	61.0	59.8	58.6	58.0	58.0	58.0	58.0	58.0
82.5°	46.1	45.4	44.7	44.3	44.3	44.3	44.3	44.3
85°	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1
87.5°	12.7	12.7	12.7	12.7	12.8	12.9	13.0	13.1
90°	23.4	24.5	25.7	26.6	27.0	27.5	28.0	28.4
92.5°	25.7	26.3	26.9	27.3	27.6	27.9	28.2	28.4
95°	43.4	44.6	45.7	46.2	46.0	45.7	45.5	45.3
97.5°	56.8	57.8	58.7	59.3	59.6	59.9	60.2	60.4
100°	63.8	65.6	67.5	68.7	69.1	69.7	70.1	70.6
102.5°	66.6	69.1	71.5	73.0	73.6	74.3	75.0	75.6
105°	69.4	72.0	74.6	76.3	77.2	78.2	79.1	80.1
107.5°	84.7	82.1	79.5	78.6	79.6	80.5	81.5	82.4
110°	137.5	114.1	90.7	79.5	80.4	81.4	82.3	83.2



TEST NUMBER: P331859-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	294.1	208.8	123.4	81.0	81.8	82.6	83.3	84.0
115°	433.1	324.8	216.4	153.8	136.9	120.1	103.2	86.4
117.5°	667.4	641.1	614.9	574.1	518.8	463.4	408.0	352.6
120°	777.7	780.4	783.3	768.9	737.3	705.7	674.1	642.5
122.5°	825.1	826.8	828.5	826.2	820.1	814.0	807.9	801.7
125°	893.3	894.9	896.6	897.7	898.4	899.1	899.8	900.5
127.5°	956.2	958.6	961.0	962.3	962.4	962.6	962.7	962.9
130°	996.3	998.8	1001.3	1002.5	1002.3	1002.1	1001.9	1001.6
132.5°	1035.1	1037.2	1039.5	1040.4	1040.3	1040.0	1039.7	1039.6
135°	1090.5	1092.9	1095.3	1096.1	1095.7	1095.3	1094.8	1094.3
137.5°	1142.0	1144.4	1146.7	1147.4	1146.6	1145.8	1145.0	1144.2
140°	1175.4	1177.5	1179.7	1180.1	1178.9	1177.8	1176.6	1175.4
142.5°	1206.2	1208.2	1210.0	1210.4	1209.3	1208.1	1206.9	1205.7
145°	1249.2	1250.9	1252.5	1252.8	1251.5	1250.4	1249.2	1248.1
147.5°	1286.8	1288.0	1289.2	1289.3	1288.3	1287.3	1286.3	1285.4
150°	1309.8	1311.3	1312.7	1312.8	1311.6	1310.4	1309.2	1308.1
152.5°	1330.9	1332.3	1333.8	1333.7	1332.1	1330.6	1329.0	1327.5
155°	1359.3	1360.8	1362.2	1361.9	1360.0	1358.2	1356.3	1354.4
157.5°	1383.4	1384.9	1386.6	1386.4	1384.6	1382.8	1381.0	1379.1
160°	1397.3	1398.7	1400.1	1400.0	1398.4	1396.7	1395.1	1393.4
162.5°	1410.3	1411.9	1413.5	1413.2	1411.3	1409.2	1407.2	1405.2
165°	1426.2	1427.8	1429.4	1429.4	1427.8	1426.2	1424.5	1422.9
167.5°	1439.4	1441.1	1442.7	1442.5	1440.4	1438.3	1436.1	1434.1
170°	1446.2	1447.9	1449.5	1449.2	1447.2	1445.0	1442.9	1440.8
172.5°	1451.2	1452.9	1454.5	1454.3	1452.2	1450.1	1447.9	1445.9
175°	1456.7	1458.4	1460.0	1459.7	1457.3	1455.0	1452.6	1450.3
177.5°	1457.3	1458.6	1460.0	1459.7	1458.1	1456.4	1454.7	1453.0
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5

(END OF REPORT)