

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331823-940

Luminaire Tested: **S122RDIW-S675D1440U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331823-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1440U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7209.5 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331823-940

CATALOG NUMBER: S122RDIW-S675D1440U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331823-940

CATALOG NUMBER: S122RDIW-S675D1440U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	68	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	57	69	62	56	51	49	45	42	37	34	32	26	24	23	18
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	22	20	16
5	65	54	47	41	58	49	43	38	39	34	31	30	27	24	21	19	18	14
6	60	49	41	36	54	44	37	33	35	30	27	27	24	21	19	17	16	12
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14	11
8	52	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16239	16239	16239
5°	16302	16037	16126
10°	16179	15775	15641
15°	15992	15308	14867
20°	15735	14639	13904
25°	15471	13881	12975
30°	15105	13103	11779
35°	14747	12254	10730
40°	14389	11377	9516
45°	13967	10392	8416
50°	13536	9399	7340
55°	13095	8329	6303
60°	12581	7201	5231
65°	12000	6052	4768
70°	11301	4985	4381
75°	10449	4548	4086
80°	9224	4063	3719
85°	7243	3205	3205



TEST NUMBER: P331823-940

CATALOG NUMBER: S122RDIW-S675D1440U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.2	1.3
10°-20°	258.5	3.6
20°-30°	363.0	5.0
30°-40°	395.9	5.5
40°-50°	364.0	5.0
50°-60°	285.9	4.0
60°-70°	186.4	2.6
70°-80°	96.1	1.3
80°-90°	29.2	0.4
90°-100°	58.5	0.8
100°-110°	214.4	3.0
110°-120°	573.1	7.9
120°-130°	946.0	13.1
130°-140°	1006.1	14.0
140°-150°	935.1	13.0
150°-160°	751.8	10.4
160°-170°	484.5	6.7
170°-180°	166.8	2.3
0°-30°	715.7	9.9
0°-40°	1111.6	15.4
0°-60°	1761.4	24.4
0°-90°	2073.2	28.8
90°-120°	846.0	11.7
90°-150°	3733.2	51.8
90°-180°	5136.0	71.2
0°-180°	7209.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1006	1001	990	997	995	95
15°	957	946	916	899	889	269
25°	868	838	779	743	728	399
35°	748	700	622	566	544	468
45°	612	549	455	393	369	472
55°	465	393	296	243	224	416
65°	314	240	158	129	125	311
75°	168	106	73	67	66	177
85°	39	21	17	17	17	46
90°	1	15	25	32	34	5
95°	82	43	50	55	55	101
105°	386	402	77	91	96	412
115°	729	751	782	223	104	718
125°	1031	1048	1072	1080	1084	919
135°	1276	1296	1308	1319	1318	985
145°	1480	1480	1500	1508	1503	925
155°	1630	1620	1633	1640	1631	751
165°	1717	1710	1713	1721	1713	485
175°	1756	1748	1750	1758	1746	167
180°	1753	1753	1753	1753	1753	



TEST NUMBER: P331823-940

CATALOG NUMBER: S122RDIW-S675D1440U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1009.5	1008.7	1007.9	1007.1	1006.3	1005.0	1003.2	1001.4	999.7	997.9	999.5
5°	1005.8	1004.9	1003.9	1002.8	1001.8	1000.1	997.4	994.8	992.1	989.5	991.3
7.5°	995.5	994.3	993.0	991.8	990.5	988.3	985.3	982.2	979.1	976.1	976.5
10°	986.8	985.3	983.9	982.5	981.1	978.4	974.3	970.3	966.3	962.2	961.6
12.5°	975.8	974.1	972.3	970.6	968.8	965.5	960.3	955.1	949.9	944.7	943.6
15°	956.7	954.5	952.3	950.0	947.8	943.3	936.4	929.5	922.7	915.8	912.0
17.5°	933.3	929.9	926.5	923.0	919.6	913.6	904.7	895.9	887.1	878.2	873.7
20°	915.8	911.7	907.7	903.7	899.6	892.5	882.3	872.3	862.2	852.0	846.9
22.5°	896.8	892.3	887.8	883.2	878.7	870.8	859.3	847.9	836.5	825.1	818.6
25°	868.4	861.9	855.5	849.0	842.6	832.6	819.3	805.9	792.6	779.2	770.9
27.5°	834.2	827.2	820.1	813.1	806.0	795.0	780.0	764.9	749.8	734.8	725.1
30°	810.2	802.5	794.8	787.1	779.4	767.5	751.3	735.1	718.9	702.8	692.4
32.5°	786.8	777.8	768.9	759.9	750.9	738.2	721.7	705.2	688.7	672.2	660.4
35°	748.2	738.0	727.6	717.3	707.0	692.9	675.1	657.4	639.5	621.7	608.9
37.5°	709.7	698.3	687.0	675.6	664.3	649.2	630.3	611.3	592.3	573.3	559.3
40°	682.7	670.6	658.4	646.3	634.2	618.3	598.7	579.1	559.5	539.8	525.5
42.5°	655.1	642.3	629.5	616.7	604.0	587.4	567.1	546.9	526.6	506.3	491.4
45°	611.7	598.2	584.6	571.1	557.5	540.1	518.9	497.7	476.4	455.1	440.8
47.5°	569.4	555.1	540.7	526.4	512.0	493.9	472.0	450.0	428.1	406.2	391.9
50°	538.9	524.5	510.1	495.8	481.4	463.2	440.9	418.7	396.4	374.2	360.2
52.5°	509.1	494.0	479.0	464.0	449.0	430.6	408.8	387.1	365.3	343.6	330.1
55°	465.2	449.4	433.6	417.9	402.1	383.3	361.4	339.6	317.7	295.9	283.7
57.5°	420.2	404.0	387.8	371.7	355.4	336.9	315.8	294.9	273.8	252.9	241.7
60°	389.6	373.4	357.2	341.1	324.9	306.4	285.5	264.7	243.9	223.0	212.7
62.5°	359.7	343.6	327.3	311.2	295.0	277.0	257.2	237.3	217.4	197.5	187.7
65°	314.1	297.7	281.2	264.9	248.5	231.2	213.0	194.8	176.6	158.4	151.5
67.5°	270.0	253.7	237.5	221.2	204.9	188.6	172.2	155.9	139.5	123.1	119.9
70°	239.4	223.6	207.9	192.1	176.3	161.4	147.5	133.5	119.6	105.6	103.5
72.5°	210.3	195.1	180.0	164.9	149.7	136.6	125.4	114.1	103.0	91.8	90.1
75°	167.5	153.4	139.2	125.0	110.8	100.3	93.5	86.6	79.7	72.9	71.4
77.5°	125.5	113.0	100.6	88.2	75.8	67.9	64.6	61.3	58.0	54.7	53.8
80°	99.2	88.9	78.6	68.3	58.0	51.8	49.8	47.7	45.7	43.7	42.9
82.5°	75.2	67.1	59.1	51.0	43.0	38.3	36.9	35.5	34.2	32.8	32.3
85°	39.1	34.9	30.7	26.4	22.1	19.7	19.1	18.5	17.9	17.3	17.3
87.5°	11.9	11.2	10.5	9.9	9.2	9.1	9.5	10.0	10.4	10.9	11.1
90°	1.2	4.4	7.5	10.6	13.6	16.3	18.6	20.9	23.1	25.3	26.8
92.5°	25.6	25.3	25.1	24.8	24.5	24.9	26.0	27.2	28.3	29.4	30.1
95°	82.4	73.1	63.8	54.6	45.2	41.6	43.5	45.5	47.5	49.5	50.8
97.5°	163.6	137.4	111.2	85.0	58.8	48.0	52.5	57.1	61.6	66.2	67.3
100°	224.4	185.8	147.2	108.6	70.0	53.1	57.9	62.7	67.5	72.3	74.5
102.5°	291.4	283.3	275.1	266.9	258.8	234.6	194.6	154.4	114.4	74.3	77.2
105°	385.6	394.0	402.4	410.9	419.4	385.1	308.2	231.2	154.3	77.4	80.4
107.5°	492.8	499.6	506.5	513.3	520.1	477.4	385.1	292.8	200.5	108.3	105.1
110°	561.9	567.8	573.6	579.6	585.5	547.7	466.3	384.9	303.4	221.9	193.8



TEST NUMBER: P331823-940

CATALOG NUMBER: S122RDIW-S675D1440U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	626.8	632.0	637.2	642.5	647.7	640.2	620.2	600.0	579.9	559.8	457.0
115°	729.2	734.1	738.8	743.6	748.4	754.3	761.3	768.4	775.4	782.5	652.0
117.5°	820.8	826.2	831.5	836.9	842.2	847.3	852.1	857.0	861.8	866.7	835.2
120°	887.8	892.0	896.2	900.4	904.6	909.3	914.4	919.4	924.5	929.6	933.0
122.5°	944.6	949.0	953.5	958.0	962.4	967.4	972.9	978.4	983.9	989.4	991.5
125°	1031.1	1034.7	1038.4	1042.1	1045.7	1050.3	1055.6	1061.0	1066.3	1071.7	1073.6
127.5°	1109.5	1113.5	1117.6	1121.6	1125.7	1129.7	1133.7	1137.7	1141.7	1145.8	1148.6
130°	1159.1	1163.7	1168.1	1172.7	1177.2	1181.0	1184.1	1187.2	1190.3	1193.4	1196.5
132.5°	1209.9	1213.7	1217.5	1221.4	1225.2	1228.7	1231.8	1234.8	1238.0	1241.1	1243.8
135°	1275.9	1280.3	1284.9	1289.3	1293.9	1297.4	1299.9	1302.4	1305.0	1307.5	1310.4
137.5°	1342.6	1345.7	1348.9	1352.0	1355.1	1358.2	1361.0	1364.0	1366.8	1369.7	1372.4
140°	1386.2	1388.4	1390.7	1392.9	1395.2	1397.8	1401.0	1404.1	1407.2	1410.2	1412.8
142.5°	1422.7	1424.7	1426.7	1428.8	1430.8	1433.6	1437.2	1440.7	1444.2	1447.8	1450.1
145°	1480.1	1479.7	1479.4	1479.2	1478.9	1481.1	1485.9	1490.8	1495.5	1500.3	1502.3
147.5°	1530.0	1528.9	1527.9	1526.8	1525.7	1527.5	1532.2	1537.0	1541.8	1546.5	1547.9
150°	1562.5	1560.5	1558.5	1556.6	1554.5	1555.9	1560.3	1564.9	1569.3	1573.9	1575.6
152.5°	1589.8	1587.7	1585.5	1583.2	1581.1	1582.1	1586.4	1590.6	1594.9	1599.2	1600.9
155°	1629.7	1627.1	1624.6	1622.0	1619.5	1620.0	1623.4	1626.7	1630.1	1633.4	1635.1
157.5°	1660.9	1658.8	1656.6	1654.5	1652.3	1652.4	1654.7	1657.2	1659.5	1661.9	1663.8
160°	1679.1	1677.4	1675.8	1674.1	1672.4	1672.4	1674.1	1675.8	1677.4	1679.1	1680.8
162.5°	1695.3	1693.7	1692.0	1690.3	1688.6	1688.5	1690.0	1691.4	1692.9	1694.3	1696.3
165°	1717.2	1715.5	1713.8	1712.1	1710.4	1710.0	1710.8	1711.6	1712.5	1713.3	1715.4
167.5°	1733.4	1731.7	1730.0	1728.3	1726.6	1726.2	1727.0	1727.8	1728.6	1729.4	1731.3
170°	1742.6	1740.9	1739.2	1737.5	1735.8	1735.2	1735.8	1736.3	1736.9	1737.5	1739.5
172.5°	1748.6	1747.0	1745.3	1743.6	1741.9	1741.3	1741.9	1742.4	1743.0	1743.6	1745.5
175°	1756.5	1754.5	1752.6	1750.6	1748.6	1747.9	1748.5	1749.0	1749.6	1750.2	1752.1
177.5°	1757.7	1756.2	1754.6	1753.0	1751.4	1750.8	1751.0	1751.2	1751.4	1751.7	1753.3
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7



TEST NUMBER: P331823-940

CATALOG NUMBER: S122RDIW-S675D1440U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1001.1	1002.7	1004.3	1005.0	1004.7	1004.3	1004.1	1003.7
5°	993.1	995.0	996.8	997.4	996.8	996.1	995.6	995.0
7.5°	977.0	977.6	978.1	977.9	976.8	975.8	974.7	973.7
10°	961.0	960.4	959.7	958.9	957.6	956.4	955.2	954.0
12.5°	942.5	941.5	940.3	938.8	936.7	934.8	932.7	930.7
15°	908.1	904.2	900.4	897.4	895.5	893.4	891.4	889.4
17.5°	869.2	864.5	860.0	856.0	852.5	849.0	845.5	842.0
20°	842.0	836.9	831.8	827.1	822.6	818.1	813.7	809.2
22.5°	812.1	805.6	799.1	794.2	790.8	787.5	784.2	780.9
25°	762.6	754.3	746.0	740.4	737.4	734.3	731.3	728.3
27.5°	715.4	705.8	696.2	688.8	684.0	679.2	674.4	669.6
30°	682.2	671.8	661.5	653.6	648.1	642.7	637.2	631.8
32.5°	648.6	636.9	625.1	616.6	611.4	606.4	601.2	596.1
35°	596.3	583.5	570.8	562.1	557.7	553.2	548.8	544.4
37.5°	545.2	531.2	517.2	507.6	502.5	497.4	492.3	487.2
40°	511.0	496.7	482.3	472.5	467.3	462.0	456.7	451.5
42.5°	476.6	461.7	446.9	436.9	431.9	426.8	421.7	416.5
45°	426.4	412.1	397.7	388.1	383.3	378.4	373.5	368.6
47.5°	377.6	363.4	349.0	339.7	335.3	330.9	326.5	322.1
50°	346.3	332.3	318.3	309.2	305.0	300.7	296.5	292.2
52.5°	316.6	303.1	289.6	281.0	277.1	273.1	269.2	265.3
55°	271.6	259.4	247.3	239.3	235.5	231.6	227.7	223.9
57.5°	230.6	219.5	208.4	201.2	198.0	194.7	191.5	188.2
60°	202.4	192.1	181.7	175.0	171.7	168.5	165.2	162.0
62.5°	177.9	168.0	158.2	152.3	150.3	148.5	146.5	144.5
65°	144.6	137.8	130.9	127.2	126.5	125.9	125.3	124.8
67.5°	116.7	113.6	110.5	108.5	107.9	107.3	106.6	105.9
70°	101.6	99.5	97.5	96.1	95.2	94.4	93.6	92.8
72.5°	88.4	86.7	85.0	83.9	83.4	82.9	82.4	81.9
75°	70.0	68.6	67.1	66.3	66.2	66.0	65.7	65.5
77.5°	53.0	52.2	51.4	50.8	50.5	50.2	49.8	49.5
80°	42.1	41.3	40.5	40.0	40.0	40.0	40.0	40.0
82.5°	31.8	31.3	30.9	30.6	30.6	30.6	30.6	30.6
85°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
87.5°	11.1	11.2	11.4	11.5	11.6	11.7	11.9	11.9
90°	28.2	29.6	31.0	32.0	32.5	33.1	33.7	34.2
92.5°	30.9	31.7	32.4	32.9	33.3	33.5	33.9	34.2
95°	52.3	53.7	55.1	55.6	55.4	55.1	54.8	54.6
97.5°	68.5	69.6	70.7	71.4	71.8	72.1	72.5	72.8
100°	76.8	79.1	81.3	82.8	83.3	83.8	84.4	85.0
102.5°	80.2	83.1	86.1	87.9	88.7	89.4	90.2	91.0
105°	83.6	86.7	89.8	91.8	93.0	94.2	95.2	96.4
107.5°	102.0	98.8	95.7	94.7	95.8	96.9	98.1	99.2
110°	165.6	137.4	109.2	95.7	96.8	97.9	99.1	100.2



TEST NUMBER: P331823-940

CATALOG NUMBER: S122RDIW-S675D1440U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	354.2	251.4	148.6	97.6	98.5	99.4	100.3	101.2
115°	521.6	391.0	260.6	185.1	164.9	144.5	124.3	104.0
117.5°	803.6	772.0	740.5	691.3	624.6	557.9	491.2	424.6
120°	936.4	939.8	943.2	925.8	887.8	849.7	811.6	773.6
122.5°	993.5	995.6	997.6	994.9	987.5	980.2	972.8	965.4
125°	1075.6	1077.5	1079.5	1080.9	1081.8	1082.6	1083.5	1084.3
127.5°	1151.5	1154.3	1157.2	1158.8	1158.9	1159.0	1159.2	1159.4
130°	1199.6	1202.7	1205.8	1207.2	1206.9	1206.7	1206.4	1206.0
132.5°	1246.3	1249.0	1251.7	1252.9	1252.6	1252.3	1252.1	1251.7
135°	1313.1	1316.0	1318.8	1319.9	1319.4	1318.8	1318.2	1317.7
137.5°	1375.2	1378.0	1380.7	1381.6	1380.6	1379.7	1378.8	1377.8
140°	1415.3	1417.9	1420.4	1420.9	1419.6	1418.2	1416.8	1415.3
142.5°	1452.4	1454.7	1457.1	1457.5	1456.1	1454.6	1453.3	1451.9
145°	1504.2	1506.2	1508.2	1508.5	1507.1	1505.7	1504.2	1502.9
147.5°	1549.4	1550.9	1552.4	1552.5	1551.3	1550.2	1548.9	1547.7
150°	1577.3	1579.0	1580.6	1580.7	1579.4	1578.0	1576.5	1575.1
152.5°	1602.6	1604.3	1606.0	1605.9	1604.0	1602.2	1600.4	1598.5
155°	1636.8	1638.5	1640.2	1639.9	1637.7	1635.5	1633.2	1630.9
157.5°	1665.7	1667.6	1669.6	1669.4	1667.2	1665.0	1662.8	1660.6
160°	1682.5	1684.2	1685.9	1685.8	1683.8	1681.8	1679.8	1677.8
162.5°	1698.2	1700.1	1702.0	1701.7	1699.3	1696.9	1694.5	1692.1
165°	1717.3	1719.3	1721.3	1721.3	1719.3	1717.3	1715.4	1713.3
167.5°	1733.3	1735.3	1737.2	1737.0	1734.5	1731.9	1729.4	1726.8
170°	1741.4	1743.4	1745.3	1745.1	1742.6	1740.0	1737.5	1734.9
172.5°	1747.5	1749.4	1751.4	1751.1	1748.6	1746.1	1743.6	1741.0
175°	1754.1	1756.0	1758.0	1757.7	1754.8	1751.9	1749.2	1746.3
177.5°	1754.8	1756.4	1758.0	1757.7	1755.7	1753.7	1751.7	1749.6
180°	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7	1752.7

(END OF REPORT)