

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331863-935

Luminaire Tested: **S122RDIW-S1005D1440U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331863-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1440U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7962.4 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331863-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331863-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38								
1	95	91	88	84	86	83	80	77	67	65	63	53	52	51	40	39	39	32								
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28								
3	80	71	64	58	72	64	59	54	53	49	45	42	39	37	32	30	28	24								
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21								
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18								
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16								
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15								
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13								
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12								
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23541	23541	23541
5°	23631	23246	23376
10°	23451	22866	22673
15°	23181	22188	21549
20°	22807	21220	20155
25°	22425	20122	18805
30°	21895	18990	17074
35°	21378	17763	15554
40°	20858	16493	13793
45°	20247	15066	12202
50°	19623	13622	10638
55°	18978	12073	9137
60°	18235	10440	7585
65°	17391	8772	6907
70°	16386	7227	6354
75°	15147	6588	5926
80°	13371	5895	5393
85°	10504	4650	4650



TEST NUMBER: P331863-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.5	1.7
10°-20°	374.7	4.7
20°-30°	526.2	6.6
30°-40°	573.8	7.2
40°-50°	527.6	6.6
50°-60°	414.4	5.2
60°-70°	270.2	3.4
70°-80°	139.3	1.7
80°-90°	40.3	0.5
90°-100°	56.5	0.7
100°-110°	207.0	2.6
110°-120°	553.4	6.9
120°-130°	913.5	11.5
130°-140°	971.4	12.2
140°-150°	902.9	11.3
150°-160°	726.0	9.1
160°-170°	467.8	5.9
170°-180°	161.0	2.0
0°-30°	1037.4	13.0
0°-40°	1611.3	20.2
0°-60°	2553.2	32.1
0°-90°	3003.0	37.7
90°-120°	816.8	10.3
90°-150°	3604.6	45.3
90°-180°	4959.0	62.3
0°-180°	7962.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1458	1458	1458	1458	1458	
5°	1458	1451	1434	1445	1442	138
15°	1387	1371	1327	1303	1289	390
25°	1259	1214	1130	1077	1056	579
35°	1085	1015	901	821	789	678
45°	887	796	660	570	534	684
55°	674	569	429	353	325	602
65°	455	348	230	187	181	451
75°	243	153	106	97	95	257
85°	57	30	25	25	25	67
90°	1	14	24	30	33	6
95°	80	42	48	53	53	97
105°	372	388	75	88	93	398
115°	704	725	756	215	100	693
125°	996	1012	1035	1043	1047	887
135°	1232	1251	1262	1274	1272	951
145°	1429	1429	1449	1456	1451	893
155°	1574	1564	1577	1584	1575	725
165°	1658	1651	1654	1662	1654	468
175°	1696	1688	1690	1697	1686	161
180°	1692	1692	1692	1692	1692	



TEST NUMBER: P331863-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0
2.5°	1463.4	1462.2	1460.9	1459.8	1458.6	1456.7	1454.1	1451.6	1449.1	1446.5	1448.8
5°	1458.0	1456.6	1455.1	1453.6	1452.2	1449.6	1445.7	1441.9	1438.1	1434.3	1436.9
7.5°	1443.0	1441.2	1439.4	1437.5	1435.7	1432.6	1428.1	1423.7	1419.3	1414.8	1415.6
10°	1430.4	1428.3	1426.2	1424.2	1422.1	1418.2	1412.3	1406.4	1400.6	1394.7	1393.9
12.5°	1414.5	1412.0	1409.5	1407.0	1404.5	1399.4	1391.9	1384.4	1376.9	1369.4	1367.8
15°	1386.8	1383.5	1380.4	1377.1	1373.9	1367.3	1357.4	1347.4	1337.4	1327.4	1321.9
17.5°	1352.7	1347.8	1342.9	1338.0	1333.1	1324.2	1311.4	1298.6	1285.8	1273.1	1266.4
20°	1327.4	1321.5	1315.7	1309.8	1304.0	1293.7	1279.0	1264.4	1249.7	1235.0	1227.7
22.5°	1299.9	1293.4	1286.9	1280.3	1273.7	1262.1	1245.6	1229.1	1212.5	1196.0	1186.5
25°	1258.8	1249.4	1240.0	1230.6	1221.2	1206.9	1187.6	1168.2	1148.8	1129.5	1117.5
27.5°	1209.2	1199.0	1188.8	1178.6	1168.4	1152.4	1130.6	1108.7	1086.9	1065.1	1051.1
30°	1174.4	1163.2	1152.1	1140.9	1129.8	1112.5	1089.0	1065.6	1042.2	1018.6	1003.7
32.5°	1140.6	1127.6	1114.6	1101.6	1088.5	1070.1	1046.1	1022.2	998.2	974.3	957.3
35°	1084.6	1069.7	1054.7	1039.7	1024.8	1004.4	978.6	952.9	927.0	901.2	882.8
37.5°	1028.7	1012.3	995.8	979.4	963.0	941.1	913.5	886.1	858.5	831.0	810.7
40°	989.6	972.1	954.4	936.9	919.3	896.2	867.8	839.4	810.9	782.5	761.6
42.5°	949.5	931.0	912.5	893.9	875.4	851.4	822.1	792.6	763.3	733.9	712.4
45°	886.7	867.0	847.4	827.8	808.1	782.9	752.1	721.3	690.5	659.8	638.9
47.5°	825.4	804.7	783.9	763.0	742.2	715.9	684.2	652.3	620.5	588.8	568.1
50°	781.2	760.3	739.5	718.7	697.8	671.3	639.1	606.8	574.5	542.3	522.1
52.5°	737.9	716.1	694.4	672.6	650.8	624.2	592.6	561.1	529.5	498.0	478.5
55°	674.2	651.4	628.5	605.6	582.8	555.5	523.8	492.1	460.5	428.9	411.2
57.5°	609.1	585.7	562.1	538.7	515.2	488.3	457.9	427.4	397.0	366.5	350.4
60°	564.7	541.3	517.8	494.4	470.9	444.1	413.9	383.7	353.4	323.3	308.3
62.5°	521.5	498.0	474.6	451.1	427.7	401.5	372.7	343.9	315.1	286.4	272.1
65°	455.2	431.4	407.8	384.0	360.2	335.2	308.8	282.4	256.0	229.6	219.6
67.5°	391.3	367.8	344.2	320.6	297.0	273.4	249.7	225.9	202.2	178.4	173.8
70°	347.1	324.2	301.3	278.4	255.5	234.0	213.8	193.6	173.3	153.1	150.2
72.5°	304.8	282.8	261.0	239.0	217.1	197.9	181.8	165.5	149.2	133.0	130.5
75°	242.8	222.2	201.7	181.2	160.7	145.4	135.4	125.5	115.5	105.6	103.5
77.5°	181.8	163.8	145.9	127.9	109.8	98.4	93.6	88.8	83.9	79.2	78.0
80°	143.8	128.9	113.9	98.9	84.0	75.1	72.2	69.2	66.3	63.4	62.2
82.5°	109.0	97.3	85.7	74.0	62.3	55.4	53.5	51.5	49.5	47.5	46.8
85°	56.7	50.5	44.4	38.2	32.1	28.6	27.7	26.9	25.9	25.1	25.1
87.5°	17.1	15.8	14.6	13.3	12.1	11.6	12.1	12.5	12.9	13.3	13.3
90°	1.2	4.2	7.2	10.2	13.2	15.8	18.0	20.1	22.3	24.5	25.8
92.5°	24.7	24.5	24.2	23.9	23.7	24.0	25.1	26.3	27.3	28.4	29.1
95°	79.6	70.6	61.6	52.7	43.7	40.1	42.0	43.9	45.9	47.8	49.1
97.5°	158.0	132.7	107.4	82.1	56.7	46.3	50.7	55.1	59.5	63.9	65.0
100°	216.7	179.4	142.2	104.9	67.6	51.3	55.9	60.5	65.2	69.8	72.0
102.5°	281.4	273.5	265.6	257.7	249.9	226.5	187.9	149.1	110.5	71.7	74.6
105°	372.3	380.4	388.6	396.7	404.9	371.9	297.6	223.3	149.0	74.7	77.7
107.5°	475.9	482.4	489.0	495.6	502.2	461.0	371.9	282.8	193.6	104.6	101.5
110°	542.5	548.2	553.9	559.6	565.3	528.8	450.2	371.6	292.9	214.3	187.1



TEST NUMBER: P331863-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	605.2	610.2	615.3	620.4	625.4	618.2	598.8	579.4	559.9	540.5	441.3
115°	704.1	708.8	713.3	718.0	722.6	728.3	735.1	741.9	748.7	755.5	629.6
117.5°	792.6	797.7	802.9	808.0	813.2	818.1	822.8	827.5	832.2	836.9	806.4
120°	857.2	861.3	865.3	869.4	873.5	878.0	882.9	887.8	892.7	897.6	900.9
122.5°	912.1	916.4	920.7	925.0	929.3	934.1	939.4	944.7	950.0	955.4	957.3
125°	995.6	999.1	1002.6	1006.2	1009.7	1014.1	1019.3	1024.4	1029.6	1034.7	1036.6
127.5°	1071.3	1075.1	1079.1	1083.0	1086.9	1090.8	1094.7	1098.5	1102.4	1106.3	1109.1
130°	1119.2	1123.6	1127.9	1132.3	1136.7	1140.3	1143.3	1146.3	1149.3	1152.3	1155.3
132.5°	1168.2	1171.9	1175.6	1179.3	1183.0	1186.4	1189.4	1192.3	1195.3	1198.3	1200.9
135°	1231.9	1236.2	1240.6	1244.9	1249.3	1252.7	1255.2	1257.6	1260.1	1262.5	1265.2
137.5°	1296.3	1299.3	1302.4	1305.4	1308.5	1311.4	1314.1	1317.0	1319.7	1322.5	1325.2
140°	1338.4	1340.6	1342.8	1345.0	1347.1	1349.7	1352.7	1355.7	1358.7	1361.7	1364.2
142.5°	1373.7	1375.6	1377.6	1379.6	1381.6	1384.2	1387.7	1391.1	1394.5	1397.9	1400.2
145°	1429.1	1428.7	1428.5	1428.2	1428.0	1430.1	1434.8	1439.4	1444.0	1448.6	1450.5
147.5°	1477.3	1476.3	1475.2	1474.2	1473.2	1474.9	1479.5	1484.1	1488.7	1493.2	1494.6
150°	1508.6	1506.8	1504.9	1503.0	1501.0	1502.3	1506.6	1511.0	1515.3	1519.7	1521.3
152.5°	1535.1	1533.0	1530.9	1528.7	1526.6	1527.6	1531.7	1535.9	1540.0	1544.1	1545.8
155°	1573.6	1571.1	1568.7	1566.2	1563.7	1564.2	1567.5	1570.7	1574.0	1577.2	1578.8
157.5°	1603.7	1601.6	1599.6	1597.5	1595.4	1595.5	1597.8	1600.1	1602.3	1604.6	1606.5
160°	1621.3	1619.6	1618.1	1616.4	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3	1622.9
162.5°	1636.9	1635.4	1633.7	1632.1	1630.5	1630.3	1631.8	1633.1	1634.6	1636.0	1637.9
165°	1658.0	1656.4	1654.8	1653.1	1651.5	1651.1	1651.9	1652.7	1653.6	1654.3	1656.3
167.5°	1673.7	1672.1	1670.4	1668.8	1667.2	1666.7	1667.5	1668.3	1669.0	1669.8	1671.7
170°	1682.6	1680.9	1679.3	1677.7	1676.0	1675.4	1676.0	1676.5	1677.1	1677.7	1679.6
172.5°	1688.4	1686.8	1685.1	1683.5	1681.9	1681.4	1681.9	1682.4	1683.0	1683.5	1685.4
175°	1696.0	1694.1	1692.2	1690.3	1688.4	1687.7	1688.2	1688.8	1689.4	1689.9	1691.8
177.5°	1697.2	1695.7	1694.2	1692.6	1691.1	1690.5	1690.7	1690.9	1691.1	1691.3	1692.9
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331863-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0
2.5°	1451.1	1453.5	1455.9	1456.7	1456.3	1455.9	1455.3	1454.9
5°	1439.6	1442.3	1444.8	1445.7	1444.8	1444.0	1443.1	1442.3
7.5°	1416.3	1417.0	1417.8	1417.5	1415.9	1414.4	1412.9	1411.4
10°	1392.9	1392.1	1391.2	1389.9	1388.1	1386.4	1384.6	1382.9
12.5°	1366.2	1364.6	1363.0	1360.8	1357.9	1355.0	1352.0	1349.1
15°	1316.3	1310.7	1305.1	1300.9	1298.0	1295.0	1292.1	1289.2
17.5°	1259.8	1253.2	1246.6	1240.7	1235.7	1230.6	1225.5	1220.6
20°	1220.4	1213.1	1205.7	1198.9	1192.4	1185.9	1179.5	1173.0
22.5°	1177.2	1167.7	1158.2	1151.1	1146.3	1141.5	1136.7	1131.9
25°	1105.4	1093.5	1081.4	1073.2	1068.8	1064.4	1060.0	1055.6
27.5°	1037.1	1023.0	1009.0	998.5	991.5	984.6	977.6	970.6
30°	988.8	973.8	958.8	947.4	939.5	931.6	923.7	915.8
32.5°	940.2	923.2	906.0	893.8	886.4	878.9	871.4	864.0
35°	864.3	845.8	827.3	814.9	808.4	801.9	795.5	789.1
37.5°	790.3	770.0	749.6	735.7	728.4	721.0	713.6	706.2
40°	740.8	720.0	699.2	685.0	677.3	669.7	662.1	654.4
42.5°	690.9	669.3	647.8	633.4	625.9	618.5	611.2	603.8
45°	618.1	597.3	576.4	562.6	555.5	548.5	541.4	534.4
47.5°	547.3	526.7	505.9	492.4	486.0	479.7	473.2	466.8
50°	501.9	481.6	461.4	448.2	442.0	435.8	429.7	423.5
52.5°	458.9	439.4	419.9	407.3	401.6	395.9	390.2	384.5
55°	393.6	376.1	358.4	346.9	341.3	335.7	330.2	324.6
57.5°	334.3	318.1	302.0	291.6	287.0	282.2	277.6	272.9
60°	293.3	278.4	263.5	253.7	248.9	244.3	239.5	234.9
62.5°	257.9	243.6	229.4	220.8	218.0	215.2	212.3	209.6
65°	209.7	199.7	189.7	184.3	183.4	182.5	181.7	180.8
67.5°	169.3	164.7	160.1	157.3	156.4	155.5	154.5	153.6
70°	147.2	144.3	141.4	139.3	138.1	136.9	135.8	134.6
72.5°	128.1	125.6	123.1	121.6	120.9	120.2	119.4	118.7
75°	101.4	99.4	97.4	96.2	95.9	95.6	95.3	95.0
77.5°	76.8	75.7	74.5	73.6	73.2	72.8	72.2	71.8
80°	61.0	59.8	58.6	58.0	58.0	58.0	58.0	58.0
82.5°	46.1	45.4	44.7	44.3	44.3	44.3	44.3	44.3
85°	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1
87.5°	13.4	13.4	13.5	13.6	13.7	13.8	13.9	14.0
90°	27.2	28.6	30.0	30.9	31.4	31.9	32.5	33.1
92.5°	29.8	30.6	31.3	31.8	32.1	32.4	32.7	33.1
95°	50.5	51.8	53.2	53.7	53.5	53.2	53.0	52.7
97.5°	66.1	67.2	68.3	69.0	69.3	69.7	70.0	70.3
100°	74.1	76.4	78.5	79.9	80.4	80.9	81.5	82.1
102.5°	77.4	80.2	83.1	84.9	85.7	86.4	87.1	87.9
105°	80.7	83.7	86.7	88.7	89.8	90.9	92.0	93.1
107.5°	98.5	95.4	92.4	91.4	92.5	93.6	94.7	95.7
110°	159.9	132.7	105.5	92.4	93.5	94.5	95.7	96.8



TEST NUMBER: P331863-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	342.0	242.7	143.4	94.2	95.1	96.0	96.9	97.7
115°	503.6	377.5	251.6	178.7	159.2	139.6	120.0	100.4
117.5°	775.9	745.5	715.0	667.5	603.1	538.7	474.3	410.0
120°	904.1	907.4	910.7	893.9	857.2	820.4	783.7	747.0
122.5°	959.3	961.3	963.2	960.6	953.5	946.4	939.3	932.1
125°	1038.5	1040.4	1042.3	1043.7	1044.6	1045.3	1046.2	1047.0
127.5°	1111.8	1114.6	1117.3	1118.9	1119.0	1119.1	1119.3	1119.5
130°	1158.3	1161.3	1164.2	1165.6	1165.4	1165.1	1164.8	1164.5
132.5°	1203.4	1206.0	1208.6	1209.7	1209.4	1209.2	1208.9	1208.6
135°	1267.9	1270.7	1273.4	1274.5	1273.9	1273.4	1272.8	1272.3
137.5°	1327.8	1330.5	1333.2	1334.0	1333.1	1332.2	1331.3	1330.3
140°	1366.6	1369.1	1371.5	1372.0	1370.7	1369.3	1368.0	1366.6
142.5°	1402.4	1404.6	1406.9	1407.3	1405.9	1404.5	1403.3	1401.9
145°	1452.4	1454.3	1456.3	1456.6	1455.2	1453.8	1452.4	1451.1
147.5°	1496.1	1497.5	1498.9	1499.0	1497.9	1496.8	1495.6	1494.4
150°	1522.9	1524.6	1526.2	1526.3	1525.0	1523.6	1522.2	1520.9
152.5°	1547.4	1549.0	1550.7	1550.6	1548.8	1547.0	1545.2	1543.4
155°	1580.5	1582.1	1583.7	1583.5	1581.3	1579.2	1576.9	1574.8
157.5°	1608.3	1610.2	1612.1	1611.9	1609.8	1607.7	1605.5	1603.4
160°	1624.5	1626.2	1627.8	1627.7	1625.8	1623.8	1622.0	1620.1
162.5°	1639.7	1641.6	1643.4	1643.1	1640.8	1638.5	1636.2	1633.8
165°	1658.2	1660.1	1662.0	1662.0	1660.1	1658.2	1656.3	1654.3
167.5°	1673.6	1675.5	1677.4	1677.1	1674.7	1672.2	1669.8	1667.3
170°	1681.4	1683.3	1685.2	1685.0	1682.6	1680.1	1677.7	1675.2
172.5°	1687.3	1689.2	1691.1	1690.8	1688.4	1685.9	1683.5	1681.0
175°	1693.7	1695.6	1697.5	1697.1	1694.4	1691.6	1688.9	1686.2
177.5°	1694.4	1695.9	1697.5	1697.2	1695.2	1693.3	1691.3	1689.4
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3

(END OF REPORT)