

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331807-940

Luminaire Tested: **S122RDIW-S675D435U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331807-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S675D435U940-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3613.7 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331807-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331807-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	46
3	84	75	67	62	78	70	64	59	61	56	52	53	49	46	45	42	40
4	77	66	59	53	72	62	55	50	55	49	45	47	43	40	41	38	35
5	71	60	52	46	66	56	49	44	49	44	39	43	38	35	37	34	31
6	66	54	46	40	61	50	43	38	45	39	35	39	34	31	34	30	28
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25
8	57	44	37	31	53	42	35	30	37	32	27	33	28	25	29	25	22
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16239	16239	16239
5°	16302	16037	16126
10°	16179	15775	15641
15°	15992	15308	14867
20°	15735	14639	13904
25°	15471	13881	12975
30°	15105	13103	11779
35°	14747	12254	10730
40°	14389	11377	9516
45°	13967	10392	8416
50°	13536	9399	7340
55°	13095	8329	6303
60°	12581	7201	5231
65°	12000	6052	4768
70°	11301	4985	4381
75°	10449	4548	4086
80°	9224	4063	3719
85°	7243	3205	3205



TEST NUMBER: P331807-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.2	2.6
10°-20°	258.5	7.2
20°-30°	363.0	10.0
30°-40°	395.9	11.0
40°-50°	364.0	10.1
50°-60°	285.9	7.9
60°-70°	186.4	5.2
70°-80°	96.1	2.7
80°-90°	26.2	0.7
90°-100°	17.6	0.5
100°-110°	64.4	1.8
110°-120°	172.2	4.8
120°-130°	284.3	7.9
130°-140°	302.4	8.4
140°-150°	281.0	7.8
150°-160°	225.9	6.3
160°-170°	145.6	4.0
170°-180°	50.1	1.4
0°-30°	715.7	19.8
0°-40°	1111.6	30.8
0°-60°	1761.4	48.7
0°-90°	2070.2	57.3
90°-120°	254.2	7.0
90°-150°	1121.9	31.0
90°-180°	1544.0	42.7
0°-180°	3613.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1006	1001	990	997	995	95
15°	957	946	916	899	889	269
25°	868	838	779	743	728	399
35°	748	700	622	566	544	468
45°	612	549	455	393	369	472
55°	465	393	296	243	224	416
65°	314	240	158	129	125	311
75°	168	106	73	67	66	177
85°	39	21	17	17	17	46
90°	0	4	8	9	10	3
95°	25	13	15	17	16	30
105°	116	121	23	27	29	124
115°	219	226	235	67	31	216
125°	310	315	322	325	326	276
135°	383	389	393	396	396	296
145°	445	445	451	453	452	278
155°	490	487	491	493	490	226
165°	516	514	515	517	515	146
175°	528	525	526	528	525	50
180°	527	527	527	527	527	



TEST NUMBER: P331807-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1009.5	1008.7	1007.9	1007.1	1006.3	1005.0	1003.2	1001.4	999.7	997.9	999.5
5°	1005.8	1004.9	1003.9	1002.8	1001.8	1000.1	997.4	994.8	992.1	989.5	991.3
7.5°	995.5	994.3	993.0	991.8	990.5	988.3	985.3	982.2	979.1	976.1	976.5
10°	986.8	985.3	983.9	982.5	981.1	978.4	974.3	970.3	966.3	962.2	961.6
12.5°	975.8	974.1	972.3	970.6	968.8	965.5	960.3	955.1	949.9	944.7	943.6
15°	956.7	954.5	952.3	950.0	947.8	943.3	936.4	929.5	922.7	915.8	912.0
17.5°	933.3	929.9	926.5	923.0	919.6	913.6	904.7	895.9	887.1	878.2	873.7
20°	915.8	911.7	907.7	903.7	899.6	892.5	882.3	872.3	862.2	852.0	846.9
22.5°	896.8	892.3	887.8	883.2	878.7	870.8	859.3	847.9	836.5	825.1	818.6
25°	868.4	861.9	855.5	849.0	842.6	832.6	819.3	805.9	792.6	779.2	770.9
27.5°	834.2	827.2	820.1	813.1	806.0	795.0	780.0	764.9	749.8	734.8	725.1
30°	810.2	802.5	794.8	787.1	779.4	767.5	751.3	735.1	718.9	702.8	692.4
32.5°	786.8	777.8	768.9	759.9	750.9	738.2	721.7	705.2	688.7	672.2	660.4
35°	748.2	738.0	727.6	717.3	707.0	692.9	675.1	657.4	639.5	621.7	608.9
37.5°	709.7	698.3	687.0	675.6	664.3	649.2	630.3	611.3	592.3	573.3	559.3
40°	682.7	670.6	658.4	646.3	634.2	618.3	598.7	579.1	559.5	539.8	525.5
42.5°	655.1	642.3	629.5	616.7	604.0	587.4	567.1	546.9	526.6	506.3	491.4
45°	611.7	598.2	584.6	571.1	557.5	540.1	518.9	497.7	476.4	455.1	440.8
47.5°	569.4	555.1	540.7	526.4	512.0	493.9	472.0	450.0	428.1	406.2	391.9
50°	538.9	524.5	510.1	495.8	481.4	463.2	440.9	418.7	396.4	374.2	360.2
52.5°	509.1	494.0	479.0	464.0	449.0	430.6	408.8	387.1	365.3	343.6	330.1
55°	465.2	449.4	433.6	417.9	402.1	383.3	361.4	339.6	317.7	295.9	283.7
57.5°	420.2	404.0	387.8	371.7	355.4	336.9	315.8	294.9	273.8	252.9	241.7
60°	389.6	373.4	357.2	341.1	324.9	306.4	285.5	264.7	243.9	223.0	212.7
62.5°	359.7	343.6	327.3	311.2	295.0	277.0	257.2	237.3	217.4	197.5	187.7
65°	314.1	297.7	281.2	264.9	248.5	231.2	213.0	194.8	176.6	158.4	151.5
67.5°	270.0	253.7	237.5	221.2	204.9	188.6	172.2	155.9	139.5	123.1	119.9
70°	239.4	223.6	207.9	192.1	176.3	161.4	147.5	133.5	119.6	105.6	103.5
72.5°	210.3	195.1	180.0	164.9	149.7	136.6	125.4	114.1	103.0	91.8	90.1
75°	167.5	153.4	139.2	125.0	110.8	100.3	93.5	86.6	79.7	72.9	71.4
77.5°	125.5	113.0	100.6	88.2	75.8	67.9	64.6	61.3	58.0	54.7	53.8
80°	99.2	88.9	78.6	68.3	58.0	51.8	49.8	47.7	45.7	43.7	42.9
82.5°	75.2	67.1	59.1	51.0	43.0	38.3	36.9	35.5	34.2	32.8	32.3
85°	39.1	34.9	30.7	26.4	22.1	19.7	19.1	18.5	17.9	17.3	17.3
87.5°	11.8	10.6	9.5	8.4	7.3	6.8	7.0	7.0	7.2	7.3	7.3
90°	0.4	1.3	2.2	3.2	4.1	4.9	5.6	6.2	7.0	7.6	8.0
92.5°	7.7	7.6	7.5	7.4	7.4	7.5	7.8	8.2	8.5	8.8	9.1
95°	24.8	21.9	19.2	16.4	13.6	12.5	13.1	13.6	14.3	14.9	15.2
97.5°	49.1	41.3	33.4	25.5	17.7	14.4	15.8	17.1	18.5	19.9	20.2
100°	67.5	55.8	44.2	32.6	21.0	16.0	17.4	18.8	20.2	21.8	22.4
102.5°	87.6	85.2	82.7	80.3	77.8	70.5	58.5	46.5	34.4	22.3	23.2
105°	115.8	118.4	120.9	123.5	126.0	115.7	92.6	69.5	46.4	23.3	24.2
107.5°	148.1	150.2	152.2	154.3	156.3	143.5	115.7	88.0	60.3	32.5	31.6
110°	168.8	170.6	172.4	174.2	175.9	164.6	140.1	115.7	91.1	66.7	58.2



TEST NUMBER: P331807-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.3	189.9	191.5	193.1	194.7	192.4	186.4	180.3	174.2	168.3	137.3
115°	219.2	220.6	222.0	223.5	224.9	226.7	228.8	231.0	233.0	235.1	195.9
117.5°	246.6	248.3	249.9	251.5	253.1	254.7	256.1	257.5	259.0	260.5	251.0
120°	266.8	268.0	269.3	270.6	271.9	273.3	274.8	276.3	277.9	279.4	280.4
122.5°	283.8	285.2	286.5	287.8	289.2	290.7	292.4	294.0	295.7	297.4	298.0
125°	309.9	310.9	312.1	313.2	314.2	315.6	317.3	318.9	320.5	322.1	322.6
127.5°	333.4	334.7	335.8	337.1	338.3	339.5	340.7	341.9	343.1	344.3	345.2
130°	348.4	349.7	351.1	352.4	353.7	354.9	355.9	356.8	357.8	358.6	359.5
132.5°	363.6	364.7	365.9	367.0	368.2	369.3	370.1	371.1	372.0	373.0	373.8
135°	383.4	384.8	386.1	387.4	388.9	389.9	390.7	391.5	392.2	393.0	393.8
137.5°	403.5	404.4	405.4	406.4	407.2	408.1	409.0	409.9	410.7	411.6	412.4
140°	416.6	417.2	417.9	418.6	419.3	420.1	421.1	422.0	422.8	423.8	424.5
142.5°	427.6	428.2	428.7	429.4	430.0	430.9	431.9	432.9	434.0	435.1	435.8
145°	444.8	444.7	444.6	444.5	444.4	445.1	446.6	448.0	449.4	450.8	451.5
147.5°	459.8	459.5	459.1	458.9	458.5	459.1	460.5	461.9	463.3	464.8	465.2
150°	469.6	469.0	468.3	467.8	467.2	467.5	469.0	470.3	471.6	473.0	473.5
152.5°	477.8	477.2	476.4	475.8	475.1	475.5	476.7	478.0	479.3	480.6	481.1
155°	489.7	489.0	488.2	487.5	486.7	486.9	487.9	488.8	489.9	490.9	491.4
157.5°	499.1	498.5	497.8	497.2	496.6	496.6	497.3	498.0	498.7	499.4	500.0
160°	504.6	504.1	503.6	503.1	502.6	502.6	503.1	503.6	504.1	504.6	505.2
162.5°	509.5	509.0	508.5	508.0	507.5	507.5	507.8	508.3	508.7	509.2	509.8
165°	516.0	515.6	515.1	514.5	514.0	513.9	514.2	514.4	514.7	514.9	515.5
167.5°	520.9	520.4	520.0	519.4	518.9	518.8	519.0	519.2	519.5	519.7	520.3
170°	523.7	523.2	522.6	522.2	521.7	521.5	521.7	521.8	522.0	522.2	522.7
172.5°	525.5	525.0	524.5	524.0	523.4	523.3	523.4	523.6	523.8	524.0	524.6
175°	527.9	527.3	526.6	526.1	525.5	525.3	525.5	525.7	525.8	525.9	526.6
177.5°	528.2	527.8	527.3	526.8	526.4	526.1	526.2	526.3	526.4	526.4	526.9
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7



TEST NUMBER: P331807-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1001.1	1002.7	1004.3	1005.0	1004.7	1004.3	1004.1	1003.7
5°	993.1	995.0	996.8	997.4	996.8	996.1	995.6	995.0
7.5°	977.0	977.6	978.1	977.9	976.8	975.8	974.7	973.7
10°	961.0	960.4	959.7	958.9	957.6	956.4	955.2	954.0
12.5°	942.5	941.5	940.3	938.8	936.7	934.8	932.7	930.7
15°	908.1	904.2	900.4	897.4	895.5	893.4	891.4	889.4
17.5°	869.2	864.5	860.0	856.0	852.5	849.0	845.5	842.0
20°	842.0	836.9	831.8	827.1	822.6	818.1	813.7	809.2
22.5°	812.1	805.6	799.1	794.2	790.8	787.5	784.2	780.9
25°	762.6	754.3	746.0	740.4	737.4	734.3	731.3	728.3
27.5°	715.4	705.8	696.2	688.8	684.0	679.2	674.4	669.6
30°	682.2	671.8	661.5	653.6	648.1	642.7	637.2	631.8
32.5°	648.6	636.9	625.1	616.6	611.4	606.4	601.2	596.1
35°	596.3	583.5	570.8	562.1	557.7	553.2	548.8	544.4
37.5°	545.2	531.2	517.2	507.6	502.5	497.4	492.3	487.2
40°	511.0	496.7	482.3	472.5	467.3	462.0	456.7	451.5
42.5°	476.6	461.7	446.9	436.9	431.9	426.8	421.7	416.5
45°	426.4	412.1	397.7	388.1	383.3	378.4	373.5	368.6
47.5°	377.6	363.4	349.0	339.7	335.3	330.9	326.5	322.1
50°	346.3	332.3	318.3	309.2	305.0	300.7	296.5	292.2
52.5°	316.6	303.1	289.6	281.0	277.1	273.1	269.2	265.3
55°	271.6	259.4	247.3	239.3	235.5	231.6	227.7	223.9
57.5°	230.6	219.5	208.4	201.2	198.0	194.7	191.5	188.2
60°	202.4	192.1	181.7	175.0	171.7	168.5	165.2	162.0
62.5°	177.9	168.0	158.2	152.3	150.3	148.5	146.5	144.5
65°	144.6	137.8	130.9	127.2	126.5	125.9	125.3	124.8
67.5°	116.7	113.6	110.5	108.5	107.9	107.3	106.6	105.9
70°	101.6	99.5	97.5	96.1	95.2	94.4	93.6	92.8
72.5°	88.4	86.7	85.0	83.9	83.4	82.9	82.4	81.9
75°	70.0	68.6	67.1	66.3	66.2	66.0	65.7	65.5
77.5°	53.0	52.2	51.4	50.8	50.5	50.2	49.8	49.5
80°	42.1	41.3	40.5	40.0	40.0	40.0	40.0	40.0
82.5°	31.8	31.3	30.9	30.6	30.6	30.6	30.6	30.6
85°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
87.5°	7.2	7.1	7.0	7.0	7.0	7.0	7.1	7.1
90°	8.5	8.9	9.3	9.6	9.8	10.0	10.2	10.3
92.5°	9.3	9.5	9.7	9.9	10.0	10.1	10.2	10.3
95°	15.7	16.1	16.6	16.8	16.7	16.6	16.5	16.4
97.5°	20.6	21.0	21.2	21.5	21.6	21.7	21.8	21.8
100°	23.1	23.7	24.4	24.9	25.1	25.2	25.3	25.5
102.5°	24.1	25.0	25.9	26.4	26.7	26.9	27.1	27.4
105°	25.1	26.0	27.0	27.6	27.9	28.3	28.6	29.0
107.5°	30.7	29.7	28.7	28.4	28.8	29.2	29.4	29.8
110°	49.8	41.3	32.8	28.7	29.1	29.4	29.8	30.1





TEST NUMBER: P331807-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	106.5	75.5	44.7	29.3	29.6	29.9	30.1	30.4
115°	156.8	117.5	78.3	55.6	49.6	43.4	37.4	31.2
117.5°	241.5	232.0	222.5	207.8	187.7	167.6	147.7	127.6
120°	281.4	282.4	283.5	278.2	266.8	255.4	243.9	232.5
122.5°	298.5	299.2	299.8	299.0	296.8	294.5	292.3	290.1
125°	323.2	323.9	324.4	324.9	325.1	325.4	325.7	325.8
127.5°	346.1	346.9	347.8	348.2	348.3	348.3	348.4	348.4
130°	360.5	361.4	362.4	362.8	362.7	362.7	362.6	362.5
132.5°	374.6	375.3	376.1	376.5	376.4	376.3	376.3	376.2
135°	394.7	395.5	396.4	396.6	396.5	396.4	396.2	396.0
137.5°	413.3	414.1	414.9	415.2	414.9	414.6	414.4	414.0
140°	425.3	426.1	426.9	427.0	426.6	426.1	425.8	425.3
142.5°	436.5	437.2	437.9	438.0	437.6	437.2	436.8	436.3
145°	452.1	452.6	453.3	453.3	452.9	452.5	452.1	451.7
147.5°	465.7	466.1	466.5	466.5	466.2	465.8	465.5	465.1
150°	474.0	474.5	475.0	475.1	474.7	474.2	473.8	473.4
152.5°	481.6	482.1	482.7	482.6	482.1	481.5	480.9	480.4
155°	492.0	492.4	492.9	492.8	492.1	491.5	490.8	490.2
157.5°	500.6	501.1	501.8	501.7	501.1	500.3	499.7	499.1
160°	505.6	506.1	506.7	506.6	506.0	505.4	504.8	504.3
162.5°	510.3	511.0	511.5	511.4	510.7	510.0	509.3	508.5
165°	516.1	516.7	517.3	517.3	516.7	516.1	515.5	514.9
167.5°	520.9	521.5	522.1	522.0	521.2	520.5	519.7	519.0
170°	523.3	524.0	524.5	524.4	523.7	522.9	522.2	521.4
172.5°	525.1	525.8	526.4	526.3	525.5	524.8	524.0	523.3
175°	527.2	527.7	528.3	528.2	527.4	526.6	525.7	524.9
177.5°	527.4	527.8	528.3	528.2	527.6	527.0	526.4	525.8
180°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7

(END OF REPORT)