

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331809-940

Luminaire Tested: **S122RDIW-S675D710U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331809-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D710U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4794.3 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	98	94	90	87	90	87	83	81	73	71	69	60	59	57	48	48	47	41
2	90	83	77	72	82	77	72	67	65	61	58	54	51	49	44	42	40	36
3	82	74	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35	31
4	76	66	58	53	70	61	54	49	52	47	43	44	40	37	36	33	31	28
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28	25
6	65	53	46	40	59	50	43	38	43	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	23	20
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21	18
9	52	41	33	29	48	38	31	27	33	28	24	28	24	22	24	21	19	17
10	49	37	30	26	45	35	29	25	31	26	22	26	22	20	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21151	21151	21151	21151
5°	23622	21284	18870	21284
10°	26209	21135	16357	21135
15°	27497	20824	12889	20824
20°	23838	20366	11153	20366
25°	15634	19737	9957	19737
30°	10524	18975	9012	18975
35°	8523	18015	8129	18015
40°	7579	16971	7522	16971
45°	6859	15746	6715	15746
50°	6242	14531	6219	14531
55°	5869	13185	5790	13185
60°	4908	11951	4850	11951
65°	4138	10850	4695	10850
70°	3829	9692	4428	9692
75°	3575	8434	4086	8434
80°	3301	6936	3636	6936
85°	3038	5483	3205	5483



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.2	2.6
10°-20°	346.0	7.2
20°-30°	445.9	9.3
30°-40°	423.7	8.8
40°-50°	363.0	7.6
50°-60°	276.4	5.8
60°-70°	174.7	3.6
70°-80°	87.3	1.8
80°-90°	24.8	0.5
90°-100°	28.8	0.6
100°-110°	105.5	2.2
110°-120°	282.1	5.9
120°-130°	465.6	9.7
130°-140°	495.2	10.3
140°-150°	460.3	9.6
150°-160°	370.1	7.7
160°-170°	238.5	5.0
170°-180°	82.1	1.7
0°-30°	916.1	19.1
0°-40°	1339.8	27.9
0°-60°	1979.2	41.3
0°-90°	2266.1	47.3
90°-120°	416.4	8.7
90°-150°	1837.6	38.3
90°-180°	2528.0	52.7
0°-180°	4794.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1310	1310	1310	1310	1310	
5°	1458	1313	1164	1313	1458	144
15°	1645	1246	771	1246	1645	444
25°	878	1108	559	1108	878	416
35°	432	914	412	914	432	277
45°	300	690	294	690	300	232
55°	208	468	206	468	208	183
65°	108	284	123	284	108	110
75°	57	135	66	135	57	61
85°	16	30	17	30	16	18
90°	17	1	17	1	17	8
95°	27	41	27	41	27	25
105°	47	190	47	190	47	49
115°	51	359	51	359	51	128
125°	534	508	534	508	534	462
135°	649	628	649	628	649	500
145°	740	728	740	728	740	463
155°	803	802	803	802	803	370
165°	843	845	843	845	843	238
175°	860	865	860	865	860	82
180°	863	863	863	863	863	



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1363.2	1364.2	1365.4	1362.8	1362.8	1360.6	1355.8	1352.3	1342.0	1340.6	1340.6
5°	1457.5	1456.5	1458.4	1452.5	1444.3	1442.4	1433.8	1422.5	1410.6	1397.4	1394.6
7.5°	1551.2	1549.9	1546.2	1545.2	1538.9	1525.2	1511.3	1496.5	1476.8	1457.6	1448.0
10°	1598.6	1613.6	1604.5	1588.6	1591.8	1570.4	1559.0	1539.4	1523.0	1494.3	1488.0
12.5°	1645.2	1651.1	1648.2	1639.1	1635.0	1620.2	1604.9	1587.9	1557.6	1531.9	1509.5
15°	1645.0	1653.7	1655.9	1653.2	1655.5	1654.6	1646.4	1632.3	1605.9	1577.6	1553.1
17.5°	1523.6	1529.6	1544.5	1554.6	1567.4	1594.3	1607.6	1612.7	1608.8	1592.8	1575.5
20°	1387.4	1377.3	1419.2	1440.6	1458.8	1504.3	1543.5	1558.5	1582.6	1582.2	1577.6
22.5°	1194.4	1196.8	1236.4	1261.9	1315.0	1360.5	1405.2	1461.7	1508.3	1539.2	1557.3
25°	877.6	894.9	934.5	969.1	1028.2	1112.9	1189.8	1279.1	1363.2	1429.7	1493.0
27.5°	659.1	660.4	691.8	723.7	758.8	828.2	925.1	1031.6	1151.6	1250.7	1364.7
30°	564.5	561.7	574.9	594.5	624.5	678.2	751.0	855.8	975.4	1124.7	1257.7
32.5°	497.4	497.6	507.6	522.0	547.0	583.2	633.0	718.1	831.3	978.0	1133.8
35°	432.4	431.9	439.3	449.7	460.2	483.4	517.5	562.1	640.0	776.9	936.3
37.5°	385.8	387.8	391.4	397.9	409.5	422.4	442.9	472.9	528.2	609.3	743.2
40°	359.6	360.5	365.5	371.0	377.8	387.8	404.7	428.7	469.3	534.0	631.8
42.5°	335.6	336.4	340.0	345.1	350.4	360.5	374.4	395.3	428.1	478.6	559.3
45°	300.4	300.4	303.6	305.9	311.8	320.9	332.3	349.6	372.4	409.7	463.3
47.5°	267.4	267.5	269.7	273.6	277.3	284.4	295.6	309.7	326.3	355.2	401.0
50°	248.5	249.0	250.3	253.5	255.8	262.2	270.8	283.1	300.4	322.7	361.0
52.5°	233.3	232.9	234.7	236.0	237.6	242.2	248.6	259.5	274.9	294.4	326.0
55°	208.5	206.6	209.4	211.7	213.0	214.8	218.5	225.3	238.5	254.9	278.6
57.5°	177.5	176.8	178.7	180.8	185.1	190.0	193.1	197.4	204.3	216.1	239.5
60°	152.0	152.0	156.1	157.5	162.5	168.9	175.2	178.9	185.7	193.4	210.7
62.5°	129.5	129.8	131.7	133.1	135.9	143.7	152.7	160.7	167.1	174.5	186.0
65°	108.3	109.2	109.2	110.1	112.0	113.8	117.4	123.8	135.2	145.6	154.3
67.5°	91.9	92.2	92.5	93.4	93.9	95.9	97.3	100.1	102.8	112.7	123.4
70°	81.1	82.4	81.9	82.8	83.3	84.2	86.1	87.4	91.5	93.8	100.1
72.5°	70.8	71.8	71.7	72.3	73.5	73.7	75.1	76.5	79.1	81.1	84.4
75°	57.3	56.9	57.3	58.2	58.7	59.2	59.2	61.0	62.3	64.2	66.4
77.5°	44.2	44.7	44.6	44.7	44.8	45.6	45.5	46.4	47.7	48.6	49.7
80°	35.5	35.9	35.5	35.9	36.4	36.8	36.4	36.8	38.3	39.1	39.1
82.5°	27.5	27.6	27.8	27.9	28.0	28.1	28.8	28.9	29.9	29.7	30.1
85°	16.4	16.0	16.0	16.0	16.4	16.9	16.4	16.4	16.9	16.9	16.9
87.5°	9.2	9.5	9.5	9.4	9.4	9.3	9.1	9.4	8.8	9.1	8.5
90°	16.9	16.6	16.3	16.1	15.8	15.2	14.5	13.9	13.2	12.5	11.4
92.5°	16.9	16.7	16.5	16.3	16.2	16.0	15.6	15.2	14.8	14.4	13.9
95°	26.8	27.0	27.1	27.3	27.4	27.1	26.4	25.8	25.1	24.3	23.4
97.5°	35.8	35.7	35.5	35.3	35.1	34.8	34.2	33.7	33.2	32.5	30.3
100°	41.8	41.6	41.3	41.0	40.8	40.0	38.9	37.8	36.6	35.6	33.3
102.5°	44.9	44.4	44.1	43.7	43.2	42.4	40.9	39.5	38.0	36.6	56.3
105°	47.4	46.9	46.4	45.7	45.2	44.1	42.6	41.1	39.6	38.1	76.0
107.5°	48.8	48.2	47.7	47.2	46.6	47.1	48.7	50.2	51.7	53.3	98.7
110°	49.3	48.8	48.2	47.6	47.1	53.8	67.6	81.5	95.4	109.2	149.4



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	49.8	49.4	49.0	48.5	48.1	73.1	123.8	174.3	225.0	275.5	285.4
115°	51.2	61.2	71.2	81.1	91.1	128.2	192.4	256.7	320.9	385.1	381.7
117.5°	209.0	241.8	274.6	307.5	340.3	364.4	380.0	395.6	411.1	426.6	424.2
120°	380.8	399.5	418.2	436.9	455.7	464.2	462.5	460.9	459.2	457.5	455.0
122.5°	475.2	478.8	482.4	486.1	489.7	491.1	490.0	489.0	488.0	487.1	484.3
125°	533.7	533.3	532.9	532.4	532.1	531.4	530.4	529.4	528.4	527.4	524.9
127.5°	570.7	570.6	570.5	570.4	570.3	569.6	568.2	566.8	565.3	563.9	562.0
130°	593.7	593.8	594.0	594.1	594.2	593.5	592.0	590.5	589.0	587.5	585.9
132.5°	616.2	616.3	616.4	616.5	616.7	616.1	614.8	613.5	612.2	610.9	609.4
135°	648.6	648.9	649.2	649.4	649.7	649.2	647.7	646.4	645.0	643.6	642.4
137.5°	678.1	678.7	679.1	679.6	680.1	679.7	678.2	676.9	675.6	674.2	672.8
140°	696.7	697.3	698.0	698.7	699.5	699.2	697.9	696.7	695.4	694.2	692.6
142.5°	714.6	715.3	716.0	716.8	717.4	717.2	716.0	714.9	713.8	712.7	710.9
145°	739.8	740.4	741.1	741.8	742.5	742.3	741.4	740.4	739.5	738.5	736.1
147.5°	761.8	762.4	763.0	763.6	764.2	764.1	763.4	762.7	762.0	761.2	758.8
150°	775.3	776.0	776.7	777.4	778.1	778.0	777.2	776.3	775.5	774.7	772.5
152.5°	786.8	787.7	788.6	789.5	790.5	790.5	789.7	788.8	788.0	787.2	785.1
155°	802.8	803.9	805.0	806.1	807.2	807.4	806.6	805.7	804.9	804.1	802.4
157.5°	817.3	818.5	819.6	820.6	821.7	821.8	820.8	819.9	818.9	818.0	816.8
160°	825.9	826.9	827.8	828.8	829.7	829.8	829.0	828.1	827.3	826.5	825.6
162.5°	832.9	834.0	835.3	836.4	837.7	837.8	836.8	835.9	834.9	834.0	833.3
165°	843.4	844.4	845.3	846.2	847.2	847.2	846.2	845.3	844.4	843.4	842.9
167.5°	850.0	851.2	852.5	853.7	855.0	855.1	854.2	853.2	852.2	851.2	850.9
170°	854.0	855.2	856.5	857.7	859.0	859.1	858.1	857.2	856.2	855.2	855.0
172.5°	856.9	858.2	859.4	860.7	861.9	862.1	861.1	860.1	859.2	858.2	857.9
175°	859.6	860.9	862.4	863.7	865.1	865.3	864.3	863.4	862.5	861.5	861.2
177.5°	861.2	862.2	863.2	864.2	865.2	865.3	864.5	863.8	863.0	862.2	862.1
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1341.3	1338.4	1335.9	1329.3	1326.1	1318.8	1317.7	1317.3	1307.8	1298.7	1296.2
5°	1387.4	1380.1	1369.1	1356.4	1343.2	1329.5	1320.4	1313.2	1294.9	1277.6	1267.7
7.5°	1433.8	1418.2	1399.3	1375.2	1355.0	1332.5	1315.7	1300.7	1274.9	1250.1	1233.4
10°	1468.4	1442.9	1417.9	1384.6	1358.7	1333.2	1309.6	1289.1	1259.9	1227.2	1203.9
12.5°	1489.9	1461.9	1427.4	1394.8	1361.3	1328.8	1297.2	1270.9	1236.6	1202.7	1175.2
15°	1518.9	1488.9	1447.0	1400.6	1357.4	1315.0	1278.6	1245.8	1201.2	1160.7	1127.0
17.5°	1542.7	1501.4	1456.3	1402.7	1352.6	1298.8	1251.9	1210.1	1160.4	1111.5	1071.8
20°	1550.3	1509.4	1457.5	1403.7	1344.6	1281.3	1230.8	1185.3	1132.0	1078.8	1033.2
22.5°	1545.6	1513.8	1456.0	1391.8	1331.1	1264.9	1207.8	1155.0	1096.0	1041.6	988.8
25°	1513.5	1502.5	1448.0	1377.8	1308.7	1231.7	1165.7	1107.9	1040.5	982.3	924.9
27.5°	1438.5	1462.1	1428.3	1353.6	1276.7	1194.2	1120.0	1054.2	984.3	918.7	861.6
30°	1366.5	1420.6	1406.0	1336.9	1250.8	1169.8	1086.5	1017.8	943.2	875.7	819.3
32.5°	1267.7	1357.3	1371.5	1313.6	1224.6	1135.6	1048.3	979.9	902.0	831.0	776.0
35°	1110.6	1244.5	1305.9	1269.0	1179.8	1083.8	993.6	914.0	835.7	765.6	711.0
37.5°	923.2	1105.5	1207.8	1210.5	1128.5	1028.7	930.6	851.5	771.3	702.5	643.5
40°	801.6	999.1	1132.5	1162.1	1092.9	985.0	885.7	805.2	726.9	659.5	591.7
42.5°	692.3	889.1	1053.1	1104.6	1049.5	942.4	842.8	758.6	682.5	618.8	549.5
45°	559.9	731.9	912.7	1004.6	974.1	874.9	769.7	689.6	618.1	563.0	496.6
47.5°	472.3	593.5	768.4	892.8	892.2	801.6	698.2	621.5	555.3	503.6	449.8
50°	422.4	528.0	675.9	817.1	828.8	752.9	654.5	578.5	516.7	462.4	419.2
52.5°	377.6	464.7	597.6	732.9	766.6	700.8	605.4	535.2	475.1	425.3	388.3
55°	319.1	386.5	487.5	614.0	665.0	618.6	534.0	468.4	419.6	377.8	345.9
57.5°	269.9	320.5	401.5	503.5	562.8	533.6	463.7	410.5	368.8	330.9	305.8
60°	239.0	280.4	349.1	434.3	499.8	479.3	419.6	370.1	334.6	301.8	278.1
62.5°	209.8	245.4	304.3	373.4	433.5	425.1	376.3	334.7	303.6	273.8	253.7
65°	168.9	194.8	240.8	295.0	343.2	347.3	312.3	284.0	256.3	232.6	214.8
67.5°	134.5	151.4	183.8	229.4	265.6	278.5	257.1	235.5	213.5	195.2	179.8
70°	113.3	127.0	150.7	187.5	220.8	234.4	222.1	205.3	186.2	171.1	157.9
72.5°	91.8	105.1	122.6	149.6	178.2	192.9	188.6	176.6	161.0	148.6	136.1
75°	69.2	73.3	85.2	103.3	125.6	138.4	141.6	135.2	122.9	113.3	106.0
77.5°	51.2	53.6	59.3	68.8	83.4	94.8	99.4	98.7	90.2	84.6	77.8
80°	40.9	42.4	45.0	49.1	60.1	71.4	74.6	74.6	68.8	66.4	59.7
82.5°	31.1	32.1	33.8	36.0	41.1	51.1	54.7	55.4	51.6	48.6	43.2
85°	17.7	17.3	18.2	19.5	20.5	23.2	28.7	29.6	28.7	25.1	23.6
87.5°	8.2	8.4	8.2	7.6	7.6	7.7	9.2	10.7	9.5	8.7	8.3
90°	10.3	9.2	8.0	6.7	5.2	3.7	2.1	0.6	2.1	3.7	5.2
92.5°	13.4	12.8	12.3	12.0	12.2	12.3	12.5	12.6	12.5	12.3	12.2
95°	22.4	21.4	20.4	22.3	26.8	31.4	36.0	40.6	36.0	31.4	26.8
97.5°	28.1	25.9	23.6	28.9	41.8	54.8	67.6	80.5	67.6	54.8	41.8
100°	30.9	28.5	26.1	34.5	53.5	72.5	91.5	110.5	91.5	72.5	53.5
102.5°	76.1	95.8	115.5	127.3	131.3	135.4	139.5	143.5	139.5	135.4	131.3
105°	113.8	151.7	189.6	206.4	202.2	198.1	193.9	189.8	193.9	198.1	202.2
107.5°	144.2	189.6	235.0	256.0	252.6	249.3	245.9	242.5	245.9	249.3	252.6
110°	189.4	229.5	269.6	288.2	285.3	282.4	279.5	276.5	279.5	282.4	285.3



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	295.3	305.2	315.1	318.8	316.2	313.7	311.1	308.5	311.1	313.7	316.2
115°	378.3	374.8	371.3	368.4	366.0	363.6	361.3	358.9	361.3	363.6	366.0
117.5°	421.9	419.5	417.1	414.6	411.9	409.3	406.6	404.0	406.6	409.3	411.9
120°	452.5	450.0	447.5	445.3	443.2	441.1	439.1	436.9	439.1	441.1	443.2
122.5°	481.6	478.8	476.2	473.7	471.5	469.3	467.2	464.9	467.2	469.3	471.5
125°	522.2	519.6	516.9	514.7	512.9	511.1	509.3	507.5	509.3	511.1	512.9
127.5°	560.0	558.0	556.1	554.1	552.1	550.1	548.0	546.1	548.0	550.1	552.1
130°	584.3	582.8	581.3	579.4	577.2	575.0	572.7	570.5	572.7	575.0	577.2
132.5°	607.8	606.3	604.8	603.1	601.2	599.3	597.4	595.6	597.4	599.3	601.2
135°	641.1	639.9	638.6	636.9	634.6	632.4	630.2	628.0	630.2	632.4	634.6
137.5°	671.4	669.9	668.5	667.0	665.5	664.0	662.4	660.8	662.4	664.0	665.5
140°	691.1	689.6	688.0	686.7	685.6	684.5	683.4	682.3	683.4	684.5	685.6
142.5°	709.2	707.4	705.6	704.3	703.3	702.3	701.2	700.3	701.2	702.3	703.3
145°	733.8	731.4	729.1	727.9	728.1	728.3	728.3	728.5	728.3	728.3	728.1
147.5°	756.5	754.2	751.9	751.0	751.5	752.1	752.6	753.0	752.6	752.1	751.5
150°	770.3	768.0	765.8	765.2	766.2	767.1	768.1	769.1	768.1	767.1	766.2
152.5°	782.9	780.9	778.7	778.2	779.3	780.4	781.5	782.6	781.5	780.4	779.3
155°	800.7	799.1	797.4	797.2	798.4	799.7	800.9	802.2	800.9	799.7	798.4
157.5°	815.6	814.5	813.3	813.3	814.3	815.4	816.5	817.5	816.5	815.4	814.3
160°	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	825.6	824.8	824.0
162.5°	832.6	831.8	831.1	831.2	832.0	832.9	833.7	834.5	833.7	832.9	832.0
165°	842.5	842.1	841.7	841.9	842.8	843.6	844.4	845.3	844.4	843.6	842.8
167.5°	850.4	850.1	849.7	849.9	850.7	851.6	852.4	853.2	852.4	851.6	850.7
170°	854.7	854.3	854.1	854.3	855.2	856.0	856.8	857.7	856.8	856.0	855.2
172.5°	857.6	857.4	857.1	857.4	858.2	859.1	859.9	860.7	859.9	859.1	858.2
175°	860.9	860.6	860.3	860.7	861.7	862.6	863.6	864.6	863.6	862.6	861.7
177.5°	862.0	861.8	861.7	862.1	862.9	863.6	864.4	865.2	864.4	863.6	862.9
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1291.5	1288.9	1284.2	1276.8	1272.5	1264.8	1259.7	1262.7	1263.4	1262.7	1261.9
5°	1256.8	1247.1	1233.9	1221.2	1209.4	1196.7	1189.4	1186.2	1179.8	1176.2	1174.4
7.5°	1214.8	1198.3	1179.6	1157.4	1138.5	1118.8	1108.8	1103.7	1090.7	1083.6	1077.4
10°	1183.5	1157.5	1138.9	1109.7	1092.0	1066.0	1048.3	1048.7	1031.0	1020.9	1013.7
12.5°	1148.9	1120.3	1089.3	1063.1	1038.4	1017.6	996.2	987.6	968.7	959.0	939.4
15°	1091.5	1058.3	1025.6	990.0	965.0	932.6	901.7	863.9	833.4	807.0	799.8
17.5°	1028.9	987.7	954.8	913.2	870.3	815.9	780.1	758.1	739.8	725.9	715.4
20°	985.9	944.1	909.0	846.1	788.4	751.5	725.1	708.3	689.1	674.1	665.9
22.5°	940.8	897.1	849.3	779.2	734.1	704.5	681.0	661.6	648.7	636.9	629.5
25°	876.6	828.8	750.1	701.9	665.5	634.5	618.1	606.3	592.6	576.7	569.4
27.5°	809.0	732.9	676.4	640.5	605.7	585.6	570.9	553.2	541.0	533.9	526.3
30°	758.3	682.3	638.2	599.1	574.4	552.1	534.8	524.9	513.0	500.7	495.7
32.5°	701.9	641.1	598.9	566.2	541.3	522.3	508.6	492.4	483.8	476.3	465.8
35°	631.8	585.9	547.2	520.8	497.0	481.6	465.7	456.1	440.6	434.3	430.2
37.5°	572.4	532.5	503.7	475.8	457.1	440.0	430.3	415.0	408.3	399.5	390.8
40°	539.0	499.8	472.0	449.2	428.3	415.5	403.3	391.0	380.9	376.9	366.4
42.5°	504.7	472.9	445.1	420.1	406.1	392.6	377.1	368.1	357.7	351.1	344.6
45°	457.4	429.3	405.6	385.0	369.6	355.5	345.4	330.5	324.6	311.3	305.9
47.5°	416.0	389.7	367.1	347.7	332.5	323.3	308.7	296.9	287.5	279.4	272.4
50°	386.5	364.6	342.8	325.5	311.8	298.6	283.6	277.7	263.1	259.0	254.9
52.5°	359.5	338.8	318.7	301.8	288.1	275.3	262.1	254.3	244.5	240.4	237.5
55°	321.8	301.8	282.7	267.6	254.0	240.8	232.6	223.0	218.5	215.3	211.7
57.5°	283.9	265.9	251.3	236.0	222.3	211.9	202.3	196.6	191.9	187.7	183.3
60°	259.9	242.6	229.4	215.3	201.2	192.5	185.3	178.4	173.0	166.6	164.8
62.5°	234.4	219.3	207.2	193.4	181.2	173.3	166.3	159.9	153.3	144.0	141.4
65°	199.4	187.5	174.8	163.5	152.5	144.7	134.7	127.4	124.8	123.8	123.3
67.5°	167.7	156.5	145.5	133.9	123.9	116.8	111.7	110.6	108.7	108.2	106.9
70°	146.6	136.1	125.2	114.2	104.7	103.3	101.5	99.7	97.4	96.5	95.6
72.5°	127.6	116.8	105.8	97.1	93.0	91.3	89.5	87.7	86.1	85.2	84.6
75°	97.8	87.8	80.6	77.4	75.1	73.7	71.0	69.6	68.8	67.3	66.9
77.5°	70.4	64.8	61.4	59.5	57.1	55.6	54.0	52.7	51.7	51.5	50.7
80°	53.7	51.0	48.7	46.0	45.0	43.2	42.8	41.5	41.9	40.5	40.5
82.5°	41.7	38.3	36.3	35.0	34.2	32.7	32.2	31.6	31.7	30.7	30.7
85°	21.4	20.5	19.5	18.6	18.6	17.3	17.7	17.3	17.3	16.4	16.0
87.5°	8.3	8.2	7.7	7.8	8.1	7.9	8.1	7.8	8.0	8.1	7.8
90°	6.7	8.0	9.2	10.3	11.4	12.5	13.2	13.9	14.5	15.2	15.8
92.5°	12.0	12.3	12.8	13.4	13.9	14.4	14.8	15.2	15.6	16.0	16.2
95°	22.3	20.4	21.4	22.4	23.4	24.3	25.1	25.8	26.4	27.1	27.4
97.5°	28.9	23.6	25.9	28.1	30.3	32.5	33.2	33.7	34.2	34.8	35.1
100°	34.5	26.1	28.5	30.9	33.3	35.6	36.6	37.8	38.9	40.0	40.8
102.5°	127.3	115.5	95.8	76.1	56.3	36.6	38.0	39.5	40.9	42.4	43.2
105°	206.4	189.6	151.7	113.8	76.0	38.1	39.6	41.1	42.6	44.1	45.2
107.5°	256.0	235.0	189.6	144.2	98.7	53.3	51.7	50.2	48.7	47.1	46.6
110°	288.2	269.6	229.5	189.4	149.4	109.2	95.4	81.5	67.6	53.8	47.1



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	318.8	315.1	305.2	295.3	285.4	275.5	225.0	174.3	123.8	73.1	48.1
115°	368.4	371.3	374.8	378.3	381.7	385.1	320.9	256.7	192.4	128.2	91.1
117.5°	414.6	417.1	419.5	421.9	424.2	426.6	411.1	395.6	380.0	364.4	340.3
120°	445.3	447.5	450.0	452.5	455.0	457.5	459.2	460.9	462.5	464.2	455.7
122.5°	473.7	476.2	478.8	481.6	484.3	487.1	488.0	489.0	490.0	491.1	489.7
125°	514.7	516.9	519.6	522.2	524.9	527.4	528.4	529.4	530.4	531.4	532.1
127.5°	554.1	556.1	558.0	560.0	562.0	563.9	565.3	566.8	568.2	569.6	570.3
130°	579.4	581.3	582.8	584.3	585.9	587.5	589.0	590.5	592.0	593.5	594.2
132.5°	603.1	604.8	606.3	607.8	609.4	610.9	612.2	613.5	614.8	616.1	616.7
135°	636.9	638.6	639.9	641.1	642.4	643.6	645.0	646.4	647.7	649.2	649.7
137.5°	667.0	668.5	669.9	671.4	672.8	674.2	675.6	676.9	678.2	679.7	680.1
140°	686.7	688.0	689.6	691.1	692.6	694.2	695.4	696.7	697.9	699.2	699.5
142.5°	704.3	705.6	707.4	709.2	710.9	712.7	713.8	714.9	716.0	717.2	717.4
145°	727.9	729.1	731.4	733.8	736.1	738.5	739.5	740.4	741.4	742.3	742.5
147.5°	751.0	751.9	754.2	756.5	758.8	761.2	762.0	762.7	763.4	764.1	764.2
150°	765.2	765.8	768.0	770.3	772.5	774.7	775.5	776.3	777.2	778.0	778.1
152.5°	778.2	778.7	780.9	782.9	785.1	787.2	788.0	788.8	789.7	790.5	790.5
155°	797.2	797.4	799.1	800.7	802.4	804.1	804.9	805.7	806.6	807.4	807.2
157.5°	813.3	813.3	814.5	815.6	816.8	818.0	818.9	819.9	820.8	821.8	821.7
160°	823.1	823.1	824.0	824.8	825.6	826.5	827.3	828.1	829.0	829.8	829.7
162.5°	831.2	831.1	831.8	832.6	833.3	834.0	834.9	835.9	836.8	837.8	837.7
165°	841.9	841.7	842.1	842.5	842.9	843.4	844.4	845.3	846.2	847.2	847.2
167.5°	849.9	849.7	850.1	850.4	850.9	851.2	852.2	853.2	854.2	855.1	855.0
170°	854.3	854.1	854.3	854.7	855.0	855.2	856.2	857.2	858.1	859.1	859.0
172.5°	857.4	857.1	857.4	857.6	857.9	858.2	859.2	860.1	861.1	862.1	861.9
175°	860.7	860.3	860.6	860.9	861.2	861.5	862.5	863.4	864.3	865.3	865.1
177.5°	862.1	861.7	861.8	862.0	862.1	862.2	863.0	863.8	864.5	865.3	865.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1257.9	1258.6	1257.6	1258.3	1257.6	1258.6	1257.9	1261.9	1262.7	1263.4	1262.7
5°	1172.1	1166.6	1165.7	1164.3	1165.7	1166.6	1172.1	1174.4	1176.2	1179.8	1186.2
7.5°	1069.6	1068.7	1066.5	1063.3	1066.5	1068.7	1069.6	1077.4	1083.6	1090.7	1103.7
10°	1003.6	1001.4	1000.9	997.7	1000.9	1001.4	1003.6	1013.7	1020.9	1031.0	1048.7
12.5°	926.5	911.8	910.3	902.3	910.3	911.8	926.5	939.4	959.0	968.7	987.6
15°	788.8	786.1	776.9	771.1	776.9	786.1	788.8	799.8	807.0	833.4	863.9
17.5°	710.2	701.2	698.4	697.1	698.4	701.2	710.2	715.4	725.9	739.8	758.1
20°	659.5	651.4	650.0	649.1	650.0	651.4	659.5	665.9	674.1	689.1	708.3
22.5°	624.6	616.0	612.5	609.8	612.5	616.0	624.6	629.5	636.9	648.7	661.6
25°	564.9	561.7	559.9	558.9	559.9	561.7	564.9	569.4	576.7	592.6	606.3
27.5°	518.2	511.1	509.8	507.5	509.8	511.1	518.2	526.3	533.9	541.0	553.2
30°	491.6	489.3	486.2	483.4	486.2	489.3	491.6	495.7	500.7	513.0	524.9
32.5°	460.3	458.3	455.6	454.2	455.6	458.3	460.3	465.8	476.3	483.8	492.4
35°	425.6	419.2	416.5	412.4	416.5	419.2	425.6	430.2	434.3	440.6	456.1
37.5°	388.9	385.6	381.7	383.1	381.7	385.6	388.9	390.8	399.5	408.3	415.0
40°	360.5	358.2	357.3	356.9	357.3	358.2	360.5	366.4	376.9	380.9	391.0
42.5°	338.0	331.6	329.3	329.2	329.3	331.6	338.0	344.6	351.1	357.7	368.1
45°	303.6	297.7	293.6	294.1	293.6	297.7	303.6	305.9	311.3	324.6	330.5
47.5°	268.5	268.3	265.7	266.5	265.7	268.3	268.5	272.4	279.4	287.5	296.9
50°	251.7	249.0	247.2	247.6	247.2	249.0	251.7	254.9	259.0	263.1	277.7
52.5°	235.7	233.4	231.8	233.8	231.8	233.4	235.7	237.5	240.4	244.5	254.3
55°	209.4	206.6	206.2	205.7	206.2	206.6	209.4	211.7	215.3	218.5	223.0
57.5°	179.9	178.2	175.4	174.2	175.4	178.2	179.9	183.3	187.7	191.9	196.6
60°	158.8	155.2	150.7	150.2	150.7	155.2	158.8	164.8	166.6	173.0	178.4
62.5°	139.6	138.8	137.9	137.9	137.9	138.8	139.6	141.4	144.0	153.3	159.9
65°	122.4	122.0	122.4	122.9	122.4	122.0	122.4	123.3	123.8	124.8	127.4
67.5°	106.7	105.8	105.0	105.4	105.0	105.8	106.7	106.9	108.2	108.7	110.6
70°	94.7	94.3	93.8	93.8	93.8	94.3	94.7	95.6	96.5	97.4	99.7
72.5°	83.0	82.9	82.5	82.1	82.5	82.9	83.0	84.6	85.2	86.1	87.7
75°	66.4	65.5	65.5	65.5	65.5	65.5	66.4	66.9	67.3	68.8	69.6
77.5°	50.6	50.2	49.7	49.3	49.7	50.2	50.6	50.7	51.5	51.7	52.7
80°	40.0	39.6	39.1	39.1	39.1	39.6	40.0	40.5	40.5	41.9	41.5
82.5°	30.6	30.1	30.1	29.7	30.1	30.1	30.6	30.7	30.7	31.7	31.6
85°	16.4	16.9	16.4	17.3	16.4	16.9	16.4	16.0	16.4	17.3	17.3
87.5°	7.9	7.7	8.0	7.8	8.0	7.7	7.9	7.8	8.1	8.0	7.8
90°	16.1	16.3	16.6	16.9	16.6	16.3	16.1	15.8	15.2	14.5	13.9
92.5°	16.3	16.5	16.7	16.9	16.7	16.5	16.3	16.2	16.0	15.6	15.2
95°	27.3	27.1	27.0	26.8	27.0	27.1	27.3	27.4	27.1	26.4	25.8
97.5°	35.3	35.5	35.7	35.8	35.7	35.5	35.3	35.1	34.8	34.2	33.7
100°	41.0	41.3	41.6	41.8	41.6	41.3	41.0	40.8	40.0	38.9	37.8
102.5°	43.7	44.1	44.4	44.9	44.4	44.1	43.7	43.2	42.4	40.9	39.5
105°	45.7	46.4	46.9	47.4	46.9	46.4	45.7	45.2	44.1	42.6	41.1
107.5°	47.2	47.7	48.2	48.8	48.2	47.7	47.2	46.6	47.1	48.7	50.2
110°	47.6	48.2	48.8	49.3	48.8	48.2	47.6	47.1	53.8	67.6	81.5



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	48.5	49.0	49.4	49.8	49.4	49.0	48.5	48.1	73.1	123.8	174.3
115°	81.1	71.2	61.2	51.2	61.2	71.2	81.1	91.1	128.2	192.4	256.7
117.5°	307.5	274.6	241.8	209.0	241.8	274.6	307.5	340.3	364.4	380.0	395.6
120°	436.9	418.2	399.5	380.8	399.5	418.2	436.9	455.7	464.2	462.5	460.9
122.5°	486.1	482.4	478.8	475.2	478.8	482.4	486.1	489.7	491.1	490.0	489.0
125°	532.4	532.9	533.3	533.7	533.3	532.9	532.4	532.1	531.4	530.4	529.4
127.5°	570.4	570.5	570.6	570.7	570.6	570.5	570.4	570.3	569.6	568.2	566.8
130°	594.1	594.0	593.8	593.7	593.8	594.0	594.1	594.2	593.5	592.0	590.5
132.5°	616.5	616.4	616.3	616.2	616.3	616.4	616.5	616.7	616.1	614.8	613.5
135°	649.4	649.2	648.9	648.6	648.9	649.2	649.4	649.7	649.2	647.7	646.4
137.5°	679.6	679.1	678.7	678.1	678.7	679.1	679.6	680.1	679.7	678.2	676.9
140°	698.7	698.0	697.3	696.7	697.3	698.0	698.7	699.5	699.2	697.9	696.7
142.5°	716.8	716.0	715.3	714.6	715.3	716.0	716.8	717.4	717.2	716.0	714.9
145°	741.8	741.1	740.4	739.8	740.4	741.1	741.8	742.5	742.3	741.4	740.4
147.5°	763.6	763.0	762.4	761.8	762.4	763.0	763.6	764.2	764.1	763.4	762.7
150°	777.4	776.7	776.0	775.3	776.0	776.7	777.4	778.1	778.0	777.2	776.3
152.5°	789.5	788.6	787.7	786.8	787.7	788.6	789.5	790.5	790.5	789.7	788.8
155°	806.1	805.0	803.9	802.8	803.9	805.0	806.1	807.2	807.4	806.6	805.7
157.5°	820.6	819.6	818.5	817.3	818.5	819.6	820.6	821.7	821.8	820.8	819.9
160°	828.8	827.8	826.9	825.9	826.9	827.8	828.8	829.7	829.8	829.0	828.1
162.5°	836.4	835.3	834.0	832.9	834.0	835.3	836.4	837.7	837.8	836.8	835.9
165°	846.2	845.3	844.4	843.4	844.4	845.3	846.2	847.2	847.2	846.2	845.3
167.5°	853.7	852.5	851.2	850.0	851.2	852.5	853.7	855.0	855.1	854.2	853.2
170°	857.7	856.5	855.2	854.0	855.2	856.5	857.7	859.0	859.1	858.1	857.2
172.5°	860.7	859.4	858.2	856.9	858.2	859.4	860.7	861.9	862.1	861.1	860.1
175°	863.7	862.4	860.9	859.6	860.9	862.4	863.7	865.1	865.3	864.3	863.4
177.5°	864.2	863.2	862.2	861.2	862.2	863.2	864.2	865.2	865.3	864.5	863.8
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1259.7	1264.8	1272.5	1276.8	1284.2	1288.9	1291.5	1296.2	1298.7	1307.8	1317.3
5°	1189.4	1196.7	1209.4	1221.2	1233.9	1247.1	1256.8	1267.7	1277.6	1294.9	1313.2
7.5°	1108.8	1118.8	1138.5	1157.4	1179.6	1198.3	1214.8	1233.4	1250.1	1274.9	1300.7
10°	1048.3	1066.0	1092.0	1109.7	1138.9	1157.5	1183.5	1203.9	1227.2	1259.9	1289.1
12.5°	996.2	1017.6	1038.4	1063.1	1089.3	1120.3	1148.9	1175.2	1202.7	1236.6	1270.9
15°	901.7	932.6	965.0	990.0	1025.6	1058.3	1091.5	1127.0	1160.7	1201.2	1245.8
17.5°	780.1	815.9	870.3	913.2	954.8	987.7	1028.9	1071.8	1111.5	1160.4	1210.1
20°	725.1	751.5	788.4	846.1	909.0	944.1	985.9	1033.2	1078.8	1132.0	1185.3
22.5°	681.0	704.5	734.1	779.2	849.3	897.1	940.8	988.8	1041.6	1096.0	1155.0
25°	618.1	634.5	665.5	701.9	750.1	828.8	876.6	924.9	982.3	1040.5	1107.9
27.5°	570.9	585.6	605.7	640.5	676.4	732.9	809.0	861.6	918.7	984.3	1054.2
30°	534.8	552.1	574.4	599.1	638.2	682.3	758.3	819.3	875.7	943.2	1017.8
32.5°	508.6	522.3	541.3	566.2	598.9	641.1	701.9	776.0	831.0	902.0	979.9
35°	465.7	481.6	497.0	520.8	547.2	585.9	631.8	711.0	765.6	835.7	914.0
37.5°	430.3	440.0	457.1	475.8	503.7	532.5	572.4	643.5	702.5	771.3	851.5
40°	403.3	415.5	428.3	449.2	472.0	499.8	539.0	591.7	659.5	726.9	805.2
42.5°	377.1	392.6	406.1	420.1	445.1	472.9	504.7	549.5	618.8	682.5	758.6
45°	345.4	355.5	369.6	385.0	405.6	429.3	457.4	496.6	563.0	618.1	689.6
47.5°	308.7	323.3	332.5	347.7	367.1	389.7	416.0	449.8	503.6	555.3	621.5
50°	283.6	298.6	311.8	325.5	342.8	364.6	386.5	419.2	462.4	516.7	578.5
52.5°	262.1	275.3	288.1	301.8	318.7	338.8	359.5	388.3	425.3	475.1	535.2
55°	232.6	240.8	254.0	267.6	282.7	301.8	321.8	345.9	377.8	419.6	468.4
57.5°	202.3	211.9	222.3	236.0	251.3	265.9	283.9	305.8	330.9	368.8	410.5
60°	185.3	192.5	201.2	215.3	229.4	242.6	259.9	278.1	301.8	334.6	370.1
62.5°	166.3	173.3	181.2	193.4	207.2	219.3	234.4	253.7	273.8	303.6	334.7
65°	134.7	144.7	152.5	163.5	174.8	187.5	199.4	214.8	232.6	256.3	284.0
67.5°	111.7	116.8	123.9	133.9	145.5	156.5	167.7	179.8	195.2	213.5	235.5
70°	101.5	103.3	104.7	114.2	125.2	136.1	146.6	157.9	171.1	186.2	205.3
72.5°	89.5	91.3	93.0	97.1	105.8	116.8	127.6	136.1	148.6	161.0	176.6
75°	71.0	73.7	75.1	77.4	80.6	87.8	97.8	106.0	113.3	122.9	135.2
77.5°	54.0	55.6	57.1	59.5	61.4	64.8	70.4	77.8	84.6	90.2	98.7
80°	42.8	43.2	45.0	46.0	48.7	51.0	53.7	59.7	66.4	68.8	74.6
82.5°	32.2	32.7	34.2	35.0	36.3	38.3	41.7	43.2	48.6	51.6	55.4
85°	17.7	17.3	18.6	18.6	19.5	20.5	21.4	23.6	25.1	28.7	29.6
87.5°	8.1	7.9	8.1	7.8	7.7	8.2	8.3	8.3	8.7	9.5	10.7
90°	13.2	12.5	11.4	10.3	9.2	8.0	6.7	5.2	3.7	2.1	0.6
92.5°	14.8	14.4	13.9	13.4	12.8	12.3	12.0	12.2	12.3	12.5	12.6
95°	25.1	24.3	23.4	22.4	21.4	20.4	22.3	26.8	31.4	36.0	40.6
97.5°	33.2	32.5	30.3	28.1	25.9	23.6	28.9	41.8	54.8	67.6	80.5
100°	36.6	35.6	33.3	30.9	28.5	26.1	34.5	53.5	72.5	91.5	110.5
102.5°	38.0	36.6	56.3	76.1	95.8	115.5	127.3	131.3	135.4	139.5	143.5
105°	39.6	38.1	76.0	113.8	151.7	189.6	206.4	202.2	198.1	193.9	189.8
107.5°	51.7	53.3	98.7	144.2	189.6	235.0	256.0	252.6	249.3	245.9	242.5
110°	95.4	109.2	149.4	189.4	229.5	269.6	288.2	285.3	282.4	279.5	276.5



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	225.0	275.5	285.4	295.3	305.2	315.1	318.8	316.2	313.7	311.1	308.5
115°	320.9	385.1	381.7	378.3	374.8	371.3	368.4	366.0	363.6	361.3	358.9
117.5°	411.1	426.6	424.2	421.9	419.5	417.1	414.6	411.9	409.3	406.6	404.0
120°	459.2	457.5	455.0	452.5	450.0	447.5	445.3	443.2	441.1	439.1	436.9
122.5°	488.0	487.1	484.3	481.6	478.8	476.2	473.7	471.5	469.3	467.2	464.9
125°	528.4	527.4	524.9	522.2	519.6	516.9	514.7	512.9	511.1	509.3	507.5
127.5°	565.3	563.9	562.0	560.0	558.0	556.1	554.1	552.1	550.1	548.0	546.1
130°	589.0	587.5	585.9	584.3	582.8	581.3	579.4	577.2	575.0	572.7	570.5
132.5°	612.2	610.9	609.4	607.8	606.3	604.8	603.1	601.2	599.3	597.4	595.6
135°	645.0	643.6	642.4	641.1	639.9	638.6	636.9	634.6	632.4	630.2	628.0
137.5°	675.6	674.2	672.8	671.4	669.9	668.5	667.0	665.5	664.0	662.4	660.8
140°	695.4	694.2	692.6	691.1	689.6	688.0	686.7	685.6	684.5	683.4	682.3
142.5°	713.8	712.7	710.9	709.2	707.4	705.6	704.3	703.3	702.3	701.2	700.3
145°	739.5	738.5	736.1	733.8	731.4	729.1	727.9	728.1	728.3	728.3	728.5
147.5°	762.0	761.2	758.8	756.5	754.2	751.9	751.0	751.5	752.1	752.6	753.0
150°	775.5	774.7	772.5	770.3	768.0	765.8	765.2	766.2	767.1	768.1	769.1
152.5°	788.0	787.2	785.1	782.9	780.9	778.7	778.2	779.3	780.4	781.5	782.6
155°	804.9	804.1	802.4	800.7	799.1	797.4	797.2	798.4	799.7	800.9	802.2
157.5°	818.9	818.0	816.8	815.6	814.5	813.3	813.3	814.3	815.4	816.5	817.5
160°	827.3	826.5	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5
162.5°	834.9	834.0	833.3	832.6	831.8	831.1	831.2	832.0	832.9	833.7	834.5
165°	844.4	843.4	842.9	842.5	842.1	841.7	841.9	842.8	843.6	844.4	845.3
167.5°	852.2	851.2	850.9	850.4	850.1	849.7	849.9	850.7	851.6	852.4	853.2
170°	856.2	855.2	855.0	854.7	854.3	854.1	854.3	855.2	856.0	856.8	857.7
172.5°	859.2	858.2	857.9	857.6	857.4	857.1	857.4	858.2	859.1	859.9	860.7
175°	862.5	861.5	861.2	860.9	860.6	860.3	860.7	861.7	862.6	863.6	864.6
177.5°	863.0	862.2	862.1	862.0	861.8	861.7	862.1	862.9	863.6	864.4	865.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1317.7	1318.8	1326.1	1329.3	1335.9	1338.4	1341.3	1340.6	1340.6	1342.0	1352.3
5°	1320.4	1329.5	1343.2	1356.4	1369.1	1380.1	1387.4	1394.6	1397.4	1410.6	1422.5
7.5°	1315.7	1332.5	1355.0	1375.2	1399.3	1418.2	1433.8	1448.0	1457.6	1476.8	1496.5
10°	1309.6	1333.2	1358.7	1384.6	1417.9	1442.9	1468.4	1488.0	1494.3	1523.0	1539.4
12.5°	1297.2	1328.8	1361.3	1394.8	1427.4	1461.9	1489.9	1509.5	1531.9	1557.6	1587.9
15°	1278.6	1315.0	1357.4	1400.6	1447.0	1488.9	1518.9	1553.1	1577.6	1605.9	1632.3
17.5°	1251.9	1298.8	1352.6	1402.7	1456.3	1501.4	1542.7	1575.5	1592.8	1608.8	1612.7
20°	1230.8	1281.3	1344.6	1403.7	1457.5	1509.4	1550.3	1577.6	1582.2	1582.6	1558.5
22.5°	1207.8	1264.9	1331.1	1391.8	1456.0	1513.8	1545.6	1557.3	1539.2	1508.3	1461.7
25°	1165.7	1231.7	1308.7	1377.8	1448.0	1502.5	1513.5	1493.0	1429.7	1363.2	1279.1
27.5°	1120.0	1194.2	1276.7	1353.6	1428.3	1462.1	1438.5	1364.7	1250.7	1151.6	1031.6
30°	1086.5	1169.8	1250.8	1336.9	1406.0	1420.6	1366.5	1257.7	1124.7	975.4	855.8
32.5°	1048.3	1135.6	1224.6	1313.6	1371.5	1357.3	1267.7	1133.8	978.0	831.3	718.1
35°	993.6	1083.8	1179.8	1269.0	1305.9	1244.5	1110.6	936.3	776.9	640.0	562.1
37.5°	930.6	1028.7	1128.5	1210.5	1207.8	1105.5	923.2	743.2	609.3	528.2	472.9
40°	885.7	985.0	1092.9	1162.1	1132.5	999.1	801.6	631.8	534.0	469.3	428.7
42.5°	842.8	942.4	1049.5	1104.6	1053.1	889.1	692.3	559.3	478.6	428.1	395.3
45°	769.7	874.9	974.1	1004.6	912.7	731.9	559.9	463.3	409.7	372.4	349.6
47.5°	698.2	801.6	892.2	892.8	768.4	593.5	472.3	401.0	355.2	326.3	309.7
50°	654.5	752.9	828.8	817.1	675.9	528.0	422.4	361.0	322.7	300.4	283.1
52.5°	605.4	700.8	766.6	732.9	597.6	464.7	377.6	326.0	294.4	274.9	259.5
55°	534.0	618.6	665.0	614.0	487.5	386.5	319.1	278.6	254.9	238.5	225.3
57.5°	463.7	533.6	562.8	503.5	401.5	320.5	269.9	239.5	216.1	204.3	197.4
60°	419.6	479.3	499.8	434.3	349.1	280.4	239.0	210.7	193.4	185.7	178.9
62.5°	376.3	425.1	433.5	373.4	304.3	245.4	209.8	186.0	174.5	167.1	160.7
65°	312.3	347.3	343.2	295.0	240.8	194.8	168.9	154.3	145.6	135.2	123.8
67.5°	257.1	278.5	265.6	229.4	183.8	151.4	134.5	123.4	112.7	102.8	100.1
70°	222.1	234.4	220.8	187.5	150.7	127.0	113.3	100.1	93.8	91.5	87.4
72.5°	188.6	192.9	178.2	149.6	122.6	105.1	91.8	84.4	81.1	79.1	76.5
75°	141.6	138.4	125.6	103.3	85.2	73.3	69.2	66.4	64.2	62.3	61.0
77.5°	99.4	94.8	83.4	68.8	59.3	53.6	51.2	49.7	48.6	47.7	46.4
80°	74.6	71.4	60.1	49.1	45.0	42.4	40.9	39.1	39.1	38.3	36.8
82.5°	54.7	51.1	41.1	36.0	33.8	32.1	31.1	30.1	29.7	29.9	28.9
85°	28.7	23.2	20.5	19.5	18.2	17.3	17.7	16.9	16.9	16.9	16.4
87.5°	9.2	7.7	7.6	7.6	8.2	8.4	8.2	8.5	9.1	8.8	9.4
90°	2.1	3.7	5.2	6.7	8.0	9.2	10.3	11.4	12.5	13.2	13.9
92.5°	12.5	12.3	12.2	12.0	12.3	12.8	13.4	13.9	14.4	14.8	15.2
95°	36.0	31.4	26.8	22.3	20.4	21.4	22.4	23.4	24.3	25.1	25.8
97.5°	67.6	54.8	41.8	28.9	23.6	25.9	28.1	30.3	32.5	33.2	33.7
100°	91.5	72.5	53.5	34.5	26.1	28.5	30.9	33.3	35.6	36.6	37.8
102.5°	139.5	135.4	131.3	127.3	115.5	95.8	76.1	56.3	36.6	38.0	39.5
105°	193.9	198.1	202.2	206.4	189.6	151.7	113.8	76.0	38.1	39.6	41.1
107.5°	245.9	249.3	252.6	256.0	235.0	189.6	144.2	98.7	53.3	51.7	50.2
110°	279.5	282.4	285.3	288.2	269.6	229.5	189.4	149.4	109.2	95.4	81.5



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	311.1	313.7	316.2	318.8	315.1	305.2	295.3	285.4	275.5	225.0	174.3
115°	361.3	363.6	366.0	368.4	371.3	374.8	378.3	381.7	385.1	320.9	256.7
117.5°	406.6	409.3	411.9	414.6	417.1	419.5	421.9	424.2	426.6	411.1	395.6
120°	439.1	441.1	443.2	445.3	447.5	450.0	452.5	455.0	457.5	459.2	460.9
122.5°	467.2	469.3	471.5	473.7	476.2	478.8	481.6	484.3	487.1	488.0	489.0
125°	509.3	511.1	512.9	514.7	516.9	519.6	522.2	524.9	527.4	528.4	529.4
127.5°	548.0	550.1	552.1	554.1	556.1	558.0	560.0	562.0	563.9	565.3	566.8
130°	572.7	575.0	577.2	579.4	581.3	582.8	584.3	585.9	587.5	589.0	590.5
132.5°	597.4	599.3	601.2	603.1	604.8	606.3	607.8	609.4	610.9	612.2	613.5
135°	630.2	632.4	634.6	636.9	638.6	639.9	641.1	642.4	643.6	645.0	646.4
137.5°	662.4	664.0	665.5	667.0	668.5	669.9	671.4	672.8	674.2	675.6	676.9
140°	683.4	684.5	685.6	686.7	688.0	689.6	691.1	692.6	694.2	695.4	696.7
142.5°	701.2	702.3	703.3	704.3	705.6	707.4	709.2	710.9	712.7	713.8	714.9
145°	728.3	728.3	728.1	727.9	729.1	731.4	733.8	736.1	738.5	739.5	740.4
147.5°	752.6	752.1	751.5	751.0	751.9	754.2	756.5	758.8	761.2	762.0	762.7
150°	768.1	767.1	766.2	765.2	765.8	768.0	770.3	772.5	774.7	775.5	776.3
152.5°	781.5	780.4	779.3	778.2	778.7	780.9	782.9	785.1	787.2	788.0	788.8
155°	800.9	799.7	798.4	797.2	797.4	799.1	800.7	802.4	804.1	804.9	805.7
157.5°	816.5	815.4	814.3	813.3	813.3	814.5	815.6	816.8	818.0	818.9	819.9
160°	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	827.3	828.1
162.5°	833.7	832.9	832.0	831.2	831.1	831.8	832.6	833.3	834.0	834.9	835.9
165°	844.4	843.6	842.8	841.9	841.7	842.1	842.5	842.9	843.4	844.4	845.3
167.5°	852.4	851.6	850.7	849.9	849.7	850.1	850.4	850.9	851.2	852.2	853.2
170°	856.8	856.0	855.2	854.3	854.1	854.3	854.7	855.0	855.2	856.2	857.2
172.5°	859.9	859.1	858.2	857.4	857.1	857.4	857.6	857.9	858.2	859.2	860.1
175°	863.6	862.6	861.7	860.7	860.3	860.6	860.9	861.2	861.5	862.5	863.4
177.5°	864.4	863.6	862.9	862.1	861.7	861.8	862.0	862.1	862.2	863.0	863.8
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1355.8	1360.6	1362.8	1362.8	1365.4	1364.2	1363.2
5°	1433.8	1442.4	1444.3	1452.5	1458.4	1456.5	1457.5
7.5°	1511.3	1525.2	1538.9	1545.2	1546.2	1549.9	1551.2
10°	1559.0	1570.4	1591.8	1588.6	1604.5	1613.6	1598.6
12.5°	1604.9	1620.2	1635.0	1639.1	1648.2	1651.1	1645.2
15°	1646.4	1654.6	1655.5	1653.2	1655.9	1653.7	1645.0
17.5°	1607.6	1594.3	1567.4	1554.6	1544.5	1529.6	1523.6
20°	1543.5	1504.3	1458.8	1440.6	1419.2	1377.3	1387.4
22.5°	1405.2	1360.5	1315.0	1261.9	1236.4	1196.8	1194.4
25°	1189.8	1112.9	1028.2	969.1	934.5	894.9	877.6
27.5°	925.1	828.2	758.8	723.7	691.8	660.4	659.1
30°	751.0	678.2	624.5	594.5	574.9	561.7	564.5
32.5°	633.0	583.2	547.0	522.0	507.6	497.6	497.4
35°	517.5	483.4	460.2	449.7	439.3	431.9	432.4
37.5°	442.9	422.4	409.5	397.9	391.4	387.8	385.8
40°	404.7	387.8	377.8	371.0	365.5	360.5	359.6
42.5°	374.4	360.5	350.4	345.1	340.0	336.4	335.6
45°	332.3	320.9	311.8	305.9	303.6	300.4	300.4
47.5°	295.6	284.4	277.3	273.6	269.7	267.5	267.4
50°	270.8	262.2	255.8	253.5	250.3	249.0	248.5
52.5°	248.6	242.2	237.6	236.0	234.7	232.9	233.3
55°	218.5	214.8	213.0	211.7	209.4	206.6	208.5
57.5°	193.1	190.0	185.1	180.8	178.7	176.8	177.5
60°	175.2	168.9	162.5	157.5	156.1	152.0	152.0
62.5°	152.7	143.7	135.9	133.1	131.7	129.8	129.5
65°	117.4	113.8	112.0	110.1	109.2	109.2	108.3
67.5°	97.3	95.9	93.9	93.4	92.5	92.2	91.9
70°	86.1	84.2	83.3	82.8	81.9	82.4	81.1
72.5°	75.1	73.7	73.5	72.3	71.7	71.8	70.8
75°	59.2	59.2	58.7	58.2	57.3	56.9	57.3
77.5°	45.5	45.6	44.8	44.7	44.6	44.7	44.2
80°	36.4	36.8	36.4	35.9	35.5	35.9	35.5
82.5°	28.8	28.1	28.0	27.9	27.8	27.6	27.5
85°	16.4	16.9	16.4	16.0	16.0	16.0	16.4
87.5°	9.1	9.3	9.4	9.4	9.5	9.5	9.2
90°	14.5	15.2	15.8	16.1	16.3	16.6	16.9
92.5°	15.6	16.0	16.2	16.3	16.5	16.7	16.9
95°	26.4	27.1	27.4	27.3	27.1	27.0	26.8
97.5°	34.2	34.8	35.1	35.3	35.5	35.7	35.8
100°	38.9	40.0	40.8	41.0	41.3	41.6	41.8
102.5°	40.9	42.4	43.2	43.7	44.1	44.4	44.9
105°	42.6	44.1	45.2	45.7	46.4	46.9	47.4
107.5°	48.7	47.1	46.6	47.2	47.7	48.2	48.8
110°	67.6	53.8	47.1	47.6	48.2	48.8	49.3



TEST NUMBER: P331809-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	123.8	73.1	48.1	48.5	49.0	49.4	49.8
115°	192.4	128.2	91.1	81.1	71.2	61.2	51.2
117.5°	380.0	364.4	340.3	307.5	274.6	241.8	209.0
120°	462.5	464.2	455.7	436.9	418.2	399.5	380.8
122.5°	490.0	491.1	489.7	486.1	482.4	478.8	475.2
125°	530.4	531.4	532.1	532.4	532.9	533.3	533.7
127.5°	568.2	569.6	570.3	570.4	570.5	570.6	570.7
130°	592.0	593.5	594.2	594.1	594.0	593.8	593.7
132.5°	614.8	616.1	616.7	616.5	616.4	616.3	616.2
135°	647.7	649.2	649.7	649.4	649.2	648.9	648.6
137.5°	678.2	679.7	680.1	679.6	679.1	678.7	678.1
140°	697.9	699.2	699.5	698.7	698.0	697.3	696.7
142.5°	716.0	717.2	717.4	716.8	716.0	715.3	714.6
145°	741.4	742.3	742.5	741.8	741.1	740.4	739.8
147.5°	763.4	764.1	764.2	763.6	763.0	762.4	761.8
150°	777.2	778.0	778.1	777.4	776.7	776.0	775.3
152.5°	789.7	790.5	790.5	789.5	788.6	787.7	786.8
155°	806.6	807.4	807.2	806.1	805.0	803.9	802.8
157.5°	820.8	821.8	821.7	820.6	819.6	818.5	817.3
160°	829.0	829.8	829.7	828.8	827.8	826.9	825.9
162.5°	836.8	837.8	837.7	836.4	835.3	834.0	832.9
165°	846.2	847.2	847.2	846.2	845.3	844.4	843.4
167.5°	854.2	855.1	855.0	853.7	852.5	851.2	850.0
170°	858.1	859.1	859.0	857.7	856.5	855.2	854.0
172.5°	861.1	862.1	861.9	860.7	859.4	858.2	856.9
175°	864.3	865.3	865.1	863.7	862.4	860.9	859.6
177.5°	864.5	865.3	865.2	864.2	863.2	862.2	861.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7

(END OF REPORT)