

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331811-940

Luminaire Tested: **S122RDIW-S675D710U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331811-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S675D710U940-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4599.2 lumens  
Efficiency: N/A  
Efficacy: 102.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331811-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331811-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33
3	81	72	65	60	74	66	60	56	56	51	48	46	43	40	37	35	33	29
4	74	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	22	19
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	16	14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16239	16239	16239
5°	16302	16037	16126
10°	16179	15775	15641
15°	15992	15308	14867
20°	15735	14639	13904
25°	15471	13881	12975
30°	15105	13103	11779
35°	14747	12254	10730
40°	14389	11377	9516
45°	13967	10392	8416
50°	13536	9399	7340
55°	13095	8329	6303
60°	12581	7201	5231
65°	12000	6052	4768
70°	11301	4985	4381
75°	10449	4548	4086
80°	9224	4063	3719
85°	7243	3205	3205



TEST NUMBER: P331811-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.2	2.0
10°-20°	258.5	5.6
20°-30°	363.0	7.9
30°-40°	395.9	8.6
40°-50°	364.0	7.9
50°-60°	285.9	6.2
60°-70°	186.4	4.1
70°-80°	96.1	2.1
80°-90°	27.1	0.6
90°-100°	28.8	0.6
100°-110°	105.5	2.3
110°-120°	282.1	6.1
120°-130°	465.6	10.1
130°-140°	495.2	10.8
140°-150°	460.3	10.0
150°-160°	370.1	8.0
160°-170°	238.5	5.2
170°-180°	82.1	1.8
0°-30°	715.7	15.6
0°-40°	1111.6	24.2
0°-60°	1761.4	38.3
0°-90°	2071.0	45.0
90°-120°	416.4	9.1
90°-150°	1837.6	40.0
90°-180°	2528.0	55.0
0°-180°	4599.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1006	1001	990	997	995	95
15°	957	946	916	899	889	269
25°	868	838	779	743	728	399
35°	748	700	622	566	544	468
45°	612	549	455	393	369	472
55°	465	393	296	243	224	416
65°	314	240	158	129	125	311
75°	168	106	73	67	66	177
85°	39	21	17	17	17	46
90°	1	7	12	16	17	4
95°	41	21	24	27	27	50
105°	190	198	38	45	47	203
115°	359	370	385	110	51	353
125°	508	516	527	532	534	452
135°	628	638	644	649	649	485
145°	728	728	738	742	740	455
155°	802	797	804	807	803	369
165°	845	842	843	847	843	239
175°	865	860	862	865	860	82
180°	863	863	863	863	863	



TEST NUMBER: P331811-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1009.5	1008.7	1007.9	1007.1	1006.3	1005.0	1003.2	1001.4	999.7	997.9	999.5
5°	1005.8	1004.9	1003.9	1002.8	1001.8	1000.1	997.4	994.8	992.1	989.5	991.3
7.5°	995.5	994.3	993.0	991.8	990.5	988.3	985.3	982.2	979.1	976.1	976.5
10°	986.8	985.3	983.9	982.5	981.1	978.4	974.3	970.3	966.3	962.2	961.6
12.5°	975.8	974.1	972.3	970.6	968.8	965.5	960.3	955.1	949.9	944.7	943.6
15°	956.7	954.5	952.3	950.0	947.8	943.3	936.4	929.5	922.7	915.8	912.0
17.5°	933.3	929.9	926.5	923.0	919.6	913.6	904.7	895.9	887.1	878.2	873.7
20°	915.8	911.7	907.7	903.7	899.6	892.5	882.3	872.3	862.2	852.0	846.9
22.5°	896.8	892.3	887.8	883.2	878.7	870.8	859.3	847.9	836.5	825.1	818.6
25°	868.4	861.9	855.5	849.0	842.6	832.6	819.3	805.9	792.6	779.2	770.9
27.5°	834.2	827.2	820.1	813.1	806.0	795.0	780.0	764.9	749.8	734.8	725.1
30°	810.2	802.5	794.8	787.1	779.4	767.5	751.3	735.1	718.9	702.8	692.4
32.5°	786.8	777.8	768.9	759.9	750.9	738.2	721.7	705.2	688.7	672.2	660.4
35°	748.2	738.0	727.6	717.3	707.0	692.9	675.1	657.4	639.5	621.7	608.9
37.5°	709.7	698.3	687.0	675.6	664.3	649.2	630.3	611.3	592.3	573.3	559.3
40°	682.7	670.6	658.4	646.3	634.2	618.3	598.7	579.1	559.5	539.8	525.5
42.5°	655.1	642.3	629.5	616.7	604.0	587.4	567.1	546.9	526.6	506.3	491.4
45°	611.7	598.2	584.6	571.1	557.5	540.1	518.9	497.7	476.4	455.1	440.8
47.5°	569.4	555.1	540.7	526.4	512.0	493.9	472.0	450.0	428.1	406.2	391.9
50°	538.9	524.5	510.1	495.8	481.4	463.2	440.9	418.7	396.4	374.2	360.2
52.5°	509.1	494.0	479.0	464.0	449.0	430.6	408.8	387.1	365.3	343.6	330.1
55°	465.2	449.4	433.6	417.9	402.1	383.3	361.4	339.6	317.7	295.9	283.7
57.5°	420.2	404.0	387.8	371.7	355.4	336.9	315.8	294.9	273.8	252.9	241.7
60°	389.6	373.4	357.2	341.1	324.9	306.4	285.5	264.7	243.9	223.0	212.7
62.5°	359.7	343.6	327.3	311.2	295.0	277.0	257.2	237.3	217.4	197.5	187.7
65°	314.1	297.7	281.2	264.9	248.5	231.2	213.0	194.8	176.6	158.4	151.5
67.5°	270.0	253.7	237.5	221.2	204.9	188.6	172.2	155.9	139.5	123.1	119.9
70°	239.4	223.6	207.9	192.1	176.3	161.4	147.5	133.5	119.6	105.6	103.5
72.5°	210.3	195.1	180.0	164.9	149.7	136.6	125.4	114.1	103.0	91.8	90.1
75°	167.5	153.4	139.2	125.0	110.8	100.3	93.5	86.6	79.7	72.9	71.4
77.5°	125.5	113.0	100.6	88.2	75.8	67.9	64.6	61.3	58.0	54.7	53.8
80°	99.2	88.9	78.6	68.3	58.0	51.8	49.8	47.7	45.7	43.7	42.9
82.5°	75.2	67.1	59.1	51.0	43.0	38.3	36.9	35.5	34.2	32.8	32.3
85°	39.1	34.9	30.7	26.4	22.1	19.7	19.1	18.5	17.9	17.3	17.3
87.5°	11.8	10.8	9.8	8.8	7.8	7.4	7.7	7.8	8.1	8.3	8.3
90°	0.6	2.1	3.7	5.2	6.7	8.0	9.2	10.3	11.4	12.5	13.2
92.5°	12.6	12.5	12.3	12.2	12.0	12.3	12.8	13.4	13.9	14.4	14.8
95°	40.6	36.0	31.4	26.8	22.3	20.4	21.4	22.4	23.4	24.3	25.1
97.5°	80.5	67.6	54.8	41.8	28.9	23.6	25.9	28.1	30.3	32.5	33.2
100°	110.5	91.5	72.5	53.5	34.5	26.1	28.5	30.9	33.3	35.6	36.6
102.5°	143.5	139.5	135.4	131.3	127.3	115.5	95.8	76.1	56.3	36.6	38.0
105°	189.8	193.9	198.1	202.2	206.4	189.6	151.7	113.8	76.0	38.1	39.6
107.5°	242.5	245.9	249.3	252.6	256.0	235.0	189.6	144.2	98.7	53.3	51.7
110°	276.5	279.5	282.4	285.3	288.2	269.6	229.5	189.4	149.4	109.2	95.4



TEST NUMBER: P331811-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.5	311.1	313.7	316.2	318.8	315.1	305.2	295.3	285.4	275.5	225.0
115°	358.9	361.3	363.6	366.0	368.4	371.3	374.8	378.3	381.7	385.1	320.9
117.5°	404.0	406.6	409.3	411.9	414.6	417.1	419.5	421.9	424.2	426.6	411.1
120°	436.9	439.1	441.1	443.2	445.3	447.5	450.0	452.5	455.0	457.5	459.2
122.5°	464.9	467.2	469.3	471.5	473.7	476.2	478.8	481.6	484.3	487.1	488.0
125°	507.5	509.3	511.1	512.9	514.7	516.9	519.6	522.2	524.9	527.4	528.4
127.5°	546.1	548.0	550.1	552.1	554.1	556.1	558.0	560.0	562.0	563.9	565.3
130°	570.5	572.7	575.0	577.2	579.4	581.3	582.8	584.3	585.9	587.5	589.0
132.5°	595.6	597.4	599.3	601.2	603.1	604.8	606.3	607.8	609.4	610.9	612.2
135°	628.0	630.2	632.4	634.6	636.9	638.6	639.9	641.1	642.4	643.6	645.0
137.5°	660.8	662.4	664.0	665.5	667.0	668.5	669.9	671.4	672.8	674.2	675.6
140°	682.3	683.4	684.5	685.6	686.7	688.0	689.6	691.1	692.6	694.2	695.4
142.5°	700.3	701.2	702.3	703.3	704.3	705.6	707.4	709.2	710.9	712.7	713.8
145°	728.5	728.3	728.3	728.1	727.9	729.1	731.4	733.8	736.1	738.5	739.5
147.5°	753.0	752.6	752.1	751.5	751.0	751.9	754.2	756.5	758.8	761.2	762.0
150°	769.1	768.1	767.1	766.2	765.2	765.8	768.0	770.3	772.5	774.7	775.5
152.5°	782.6	781.5	780.4	779.3	778.2	778.7	780.9	782.9	785.1	787.2	788.0
155°	802.2	800.9	799.7	798.4	797.2	797.4	799.1	800.7	802.4	804.1	804.9
157.5°	817.5	816.5	815.4	814.3	813.3	813.3	814.5	815.6	816.8	818.0	818.9
160°	826.5	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	827.3
162.5°	834.5	833.7	832.9	832.0	831.2	831.1	831.8	832.6	833.3	834.0	834.9
165°	845.3	844.4	843.6	842.8	841.9	841.7	842.1	842.5	842.9	843.4	844.4
167.5°	853.2	852.4	851.6	850.7	849.9	849.7	850.1	850.4	850.9	851.2	852.2
170°	857.7	856.8	856.0	855.2	854.3	854.1	854.3	854.7	855.0	855.2	856.2
172.5°	860.7	859.9	859.1	858.2	857.4	857.1	857.4	857.6	857.9	858.2	859.2
175°	864.6	863.6	862.6	861.7	860.7	860.3	860.6	860.9	861.2	861.5	862.5
177.5°	865.2	864.4	863.6	862.9	862.1	861.7	861.8	862.0	862.1	862.2	863.0
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331811-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1001.1	1002.7	1004.3	1005.0	1004.7	1004.3	1004.1	1003.7
5°	993.1	995.0	996.8	997.4	996.8	996.1	995.6	995.0
7.5°	977.0	977.6	978.1	977.9	976.8	975.8	974.7	973.7
10°	961.0	960.4	959.7	958.9	957.6	956.4	955.2	954.0
12.5°	942.5	941.5	940.3	938.8	936.7	934.8	932.7	930.7
15°	908.1	904.2	900.4	897.4	895.5	893.4	891.4	889.4
17.5°	869.2	864.5	860.0	856.0	852.5	849.0	845.5	842.0
20°	842.0	836.9	831.8	827.1	822.6	818.1	813.7	809.2
22.5°	812.1	805.6	799.1	794.2	790.8	787.5	784.2	780.9
25°	762.6	754.3	746.0	740.4	737.4	734.3	731.3	728.3
27.5°	715.4	705.8	696.2	688.8	684.0	679.2	674.4	669.6
30°	682.2	671.8	661.5	653.6	648.1	642.7	637.2	631.8
32.5°	648.6	636.9	625.1	616.6	611.4	606.4	601.2	596.1
35°	596.3	583.5	570.8	562.1	557.7	553.2	548.8	544.4
37.5°	545.2	531.2	517.2	507.6	502.5	497.4	492.3	487.2
40°	511.0	496.7	482.3	472.5	467.3	462.0	456.7	451.5
42.5°	476.6	461.7	446.9	436.9	431.9	426.8	421.7	416.5
45°	426.4	412.1	397.7	388.1	383.3	378.4	373.5	368.6
47.5°	377.6	363.4	349.0	339.7	335.3	330.9	326.5	322.1
50°	346.3	332.3	318.3	309.2	305.0	300.7	296.5	292.2
52.5°	316.6	303.1	289.6	281.0	277.1	273.1	269.2	265.3
55°	271.6	259.4	247.3	239.3	235.5	231.6	227.7	223.9
57.5°	230.6	219.5	208.4	201.2	198.0	194.7	191.5	188.2
60°	202.4	192.1	181.7	175.0	171.7	168.5	165.2	162.0
62.5°	177.9	168.0	158.2	152.3	150.3	148.5	146.5	144.5
65°	144.6	137.8	130.9	127.2	126.5	125.9	125.3	124.8
67.5°	116.7	113.6	110.5	108.5	107.9	107.3	106.6	105.9
70°	101.6	99.5	97.5	96.1	95.2	94.4	93.6	92.8
72.5°	88.4	86.7	85.0	83.9	83.4	82.9	82.4	81.9
75°	70.0	68.6	67.1	66.3	66.2	66.0	65.7	65.5
77.5°	53.0	52.2	51.4	50.8	50.5	50.2	49.8	49.5
80°	42.1	41.3	40.5	40.0	40.0	40.0	40.0	40.0
82.5°	31.8	31.3	30.9	30.6	30.6	30.6	30.6	30.6
85°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
87.5°	8.3	8.3	8.2	8.2	8.3	8.4	8.4	8.5
90°	13.9	14.5	15.2	15.8	16.1	16.3	16.6	16.9
92.5°	15.2	15.6	16.0	16.2	16.3	16.5	16.7	16.9
95°	25.8	26.4	27.1	27.4	27.3	27.1	27.0	26.8
97.5°	33.7	34.2	34.8	35.1	35.3	35.5	35.7	35.8
100°	37.8	38.9	40.0	40.8	41.0	41.3	41.6	41.8
102.5°	39.5	40.9	42.4	43.2	43.7	44.1	44.4	44.9
105°	41.1	42.6	44.1	45.2	45.7	46.4	46.9	47.4
107.5°	50.2	48.7	47.1	46.6	47.2	47.7	48.2	48.8
110°	81.5	67.6	53.8	47.1	47.6	48.2	48.8	49.3





TEST NUMBER: P331811-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	174.3	123.8	73.1	48.1	48.5	49.0	49.4	49.8
115°	256.7	192.4	128.2	91.1	81.1	71.2	61.2	51.2
117.5°	395.6	380.0	364.4	340.3	307.5	274.6	241.8	209.0
120°	460.9	462.5	464.2	455.7	436.9	418.2	399.5	380.8
122.5°	489.0	490.0	491.1	489.7	486.1	482.4	478.8	475.2
125°	529.4	530.4	531.4	532.1	532.4	532.9	533.3	533.7
127.5°	566.8	568.2	569.6	570.3	570.4	570.5	570.6	570.7
130°	590.5	592.0	593.5	594.2	594.1	594.0	593.8	593.7
132.5°	613.5	614.8	616.1	616.7	616.5	616.4	616.3	616.2
135°	646.4	647.7	649.2	649.7	649.4	649.2	648.9	648.6
137.5°	676.9	678.2	679.7	680.1	679.6	679.1	678.7	678.1
140°	696.7	697.9	699.2	699.5	698.7	698.0	697.3	696.7
142.5°	714.9	716.0	717.2	717.4	716.8	716.0	715.3	714.6
145°	740.4	741.4	742.3	742.5	741.8	741.1	740.4	739.8
147.5°	762.7	763.4	764.1	764.2	763.6	763.0	762.4	761.8
150°	776.3	777.2	778.0	778.1	777.4	776.7	776.0	775.3
152.5°	788.8	789.7	790.5	790.5	789.5	788.6	787.7	786.8
155°	805.7	806.6	807.4	807.2	806.1	805.0	803.9	802.8
157.5°	819.9	820.8	821.8	821.7	820.6	819.6	818.5	817.3
160°	828.1	829.0	829.8	829.7	828.8	827.8	826.9	825.9
162.5°	835.9	836.8	837.8	837.7	836.4	835.3	834.0	832.9
165°	845.3	846.2	847.2	847.2	846.2	845.3	844.4	843.4
167.5°	853.2	854.2	855.1	855.0	853.7	852.5	851.2	850.0
170°	857.2	858.1	859.1	859.0	857.7	856.5	855.2	854.0
172.5°	860.1	861.1	862.1	861.9	860.7	859.4	858.2	856.9
175°	863.4	864.3	865.3	865.1	863.7	862.4	860.9	859.6
177.5°	863.8	864.5	865.3	865.2	864.2	863.2	862.2	861.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7

(END OF REPORT)