

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331812-940

Luminaire Tested: **S122RDIW-S675D710U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331812-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D710U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4264.5 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331812-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331812-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	87	90	87	83	80	73	71	69	61	59	58	49	48	47	42
2	90	82	77	72	82	76	71	67	65	61	58	54	51	49	44	42	40	36
3	82	73	66	60	75	67	61	56	57	53	49	48	45	42	39	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24
6	64	52	44	39	59	49	42	36	42	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	29	32	28	25	27	24	21	19
8	55	43	35	30	51	40	33	29	35	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16239	16239	16239
5°	16302	16037	16126
10°	16179	15775	15641
15°	15992	15308	14867
20°	15735	14639	13904
25°	15471	13881	12975
30°	15105	13103	11779
35°	14747	12254	10730
40°	14389	11377	9516
45°	13967	10392	8416
50°	13536	9399	7340
55°	13095	8329	6303
60°	12581	7201	5231
65°	12000	6052	4768
70°	11301	4985	4381
75°	10449	4548	4086
80°	9224	4063	3719
85°	7243	3205	3205



TEST NUMBER: P331812-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.2	2.2
10°-20°	258.5	6.1
20°-30°	363.0	8.5
30°-40°	395.9	9.3
40°-50°	364.0	8.5
50°-60°	285.9	6.7
60°-70°	186.4	4.4
70°-80°	96.1	2.3
80°-90°	28.1	0.7
90°-100°	49.7	1.2
100°-110°	154.3	3.6
110°-120°	263.8	6.2
120°-130°	346.9	8.1
130°-140°	389.3	9.1
140°-150°	381.7	9.0
150°-160°	320.2	7.5
160°-170°	212.4	5.0
170°-180°	74.2	1.7
0°-30°	715.7	16.8
0°-40°	1111.6	26.1
0°-60°	1761.4	41.3
0°-90°	2072.0	48.6
90°-120°	467.8	11.0
90°-150°	1585.7	37.2
90°-180°	2193.0	51.4
0°-180°	4264.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1006	1001	990	997	995	95
15°	957	946	916	899	889	269
25°	868	838	779	743	728	399
35°	748	700	622	566	544	468
45°	612	549	455	393	369	472
55°	465	393	296	243	224	416
65°	314	240	158	129	125	311
75°	168	106	73	67	66	177
85°	39	21	17	17	17	46
90°	1	9	23	22	22	3
95°	34	41	42	42	41	39
105°	142	144	146	147	147	150
115°	265	268	267	267	265	262
125°	385	391	389	387	386	344
135°	498	505	507	506	504	385
145°	605	609	613	614	611	378
155°	691	693	695	698	697	318
165°	752	752	752	756	753	212
175°	783	781	779	784	780	74
180°	784	784	784	784	784	



TEST NUMBER: P331812-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1009.5	1008.7	1007.9	1007.1	1006.3	1005.0	1003.2	1001.4	999.7	997.9	999.5
5°	1005.8	1004.9	1003.9	1002.8	1001.8	1000.1	997.4	994.8	992.1	989.5	991.3
7.5°	995.5	994.3	993.0	991.8	990.5	988.3	985.3	982.2	979.1	976.1	976.5
10°	986.8	985.3	983.9	982.5	981.1	978.4	974.3	970.3	966.3	962.2	961.6
12.5°	975.8	974.1	972.3	970.6	968.8	965.5	960.3	955.1	949.9	944.7	943.6
15°	956.7	954.5	952.3	950.0	947.8	943.3	936.4	929.5	922.7	915.8	912.0
17.5°	933.3	929.9	926.5	923.0	919.6	913.6	904.7	895.9	887.1	878.2	873.7
20°	915.8	911.7	907.7	903.7	899.6	892.5	882.3	872.3	862.2	852.0	846.9
22.5°	896.8	892.3	887.8	883.2	878.7	870.8	859.3	847.9	836.5	825.1	818.6
25°	868.4	861.9	855.5	849.0	842.6	832.6	819.3	805.9	792.6	779.2	770.9
27.5°	834.2	827.2	820.1	813.1	806.0	795.0	780.0	764.9	749.8	734.8	725.1
30°	810.2	802.5	794.8	787.1	779.4	767.5	751.3	735.1	718.9	702.8	692.4
32.5°	786.8	777.8	768.9	759.9	750.9	738.2	721.7	705.2	688.7	672.2	660.4
35°	748.2	738.0	727.6	717.3	707.0	692.9	675.1	657.4	639.5	621.7	608.9
37.5°	709.7	698.3	687.0	675.6	664.3	649.2	630.3	611.3	592.3	573.3	559.3
40°	682.7	670.6	658.4	646.3	634.2	618.3	598.7	579.1	559.5	539.8	525.5
42.5°	655.1	642.3	629.5	616.7	604.0	587.4	567.1	546.9	526.6	506.3	491.4
45°	611.7	598.2	584.6	571.1	557.5	540.1	518.9	497.7	476.4	455.1	440.8
47.5°	569.4	555.1	540.7	526.4	512.0	493.9	472.0	450.0	428.1	406.2	391.9
50°	538.9	524.5	510.1	495.8	481.4	463.2	440.9	418.7	396.4	374.2	360.2
52.5°	509.1	494.0	479.0	464.0	449.0	430.6	408.8	387.1	365.3	343.6	330.1
55°	465.2	449.4	433.6	417.9	402.1	383.3	361.4	339.6	317.7	295.9	283.7
57.5°	420.2	404.0	387.8	371.7	355.4	336.9	315.8	294.9	273.8	252.9	241.7
60°	389.6	373.4	357.2	341.1	324.9	306.4	285.5	264.7	243.9	223.0	212.7
62.5°	359.7	343.6	327.3	311.2	295.0	277.0	257.2	237.3	217.4	197.5	187.7
65°	314.1	297.7	281.2	264.9	248.5	231.2	213.0	194.8	176.6	158.4	151.5
67.5°	270.0	253.7	237.5	221.2	204.9	188.6	172.2	155.9	139.5	123.1	119.9
70°	239.4	223.6	207.9	192.1	176.3	161.4	147.5	133.5	119.6	105.6	103.5
72.5°	210.3	195.1	180.0	164.9	149.7	136.6	125.4	114.1	103.0	91.8	90.1
75°	167.5	153.4	139.2	125.0	110.8	100.3	93.5	86.6	79.7	72.9	71.4
77.5°	125.5	113.0	100.6	88.2	75.8	67.9	64.6	61.3	58.0	54.7	53.8
80°	99.2	88.9	78.6	68.3	58.0	51.8	49.8	47.7	45.7	43.7	42.9
82.5°	75.2	67.1	59.1	51.0	43.0	38.3	36.9	35.5	34.2	32.8	32.3
85°	39.1	34.9	30.7	26.4	22.1	19.7	19.1	18.5	17.9	17.3	17.3
87.5°	11.8	10.9	9.9	8.9	8.0	7.8	8.6	9.2	9.8	10.4	10.3
90°	0.6	2.4	4.2	6.0	7.8	10.3	13.5	16.7	19.9	23.2	22.8
92.5°	11.8	13.1	14.4	15.7	16.9	18.0	18.7	19.5	20.2	21.0	21.1
95°	34.4	35.8	37.4	38.8	40.3	41.2	41.5	41.7	42.1	42.4	42.4
97.5°	62.9	64.1	65.5	66.7	68.0	68.9	69.6	70.1	70.6	71.2	71.2
100°	84.0	85.2	86.4	87.6	88.7	89.5	90.0	90.4	90.9	91.3	91.3
102.5°	106.3	107.2	108.2	109.1	110.0	110.8	111.4	111.9	112.4	113.0	113.2
105°	142.2	142.7	143.1	143.6	144.0	144.4	144.7	145.0	145.3	145.6	145.9
107.5°	178.5	179.1	179.9	180.5	181.1	181.5	181.5	181.5	181.5	181.5	181.6
110°	201.8	202.7	203.6	204.5	205.4	205.8	205.8	205.8	205.8	205.8	205.8



TEST NUMBER: P331812-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	227.2	228.1	229.0	229.9	230.8	231.1	231.0	230.9	230.8	230.7	230.3
115°	264.7	265.6	266.4	267.3	268.2	268.5	268.2	267.9	267.6	267.3	267.2
117.5°	302.0	303.2	304.3	305.5	306.7	306.8	306.0	305.2	304.4	303.6	303.3
120°	326.9	328.1	329.2	330.4	331.5	331.5	330.4	329.2	328.1	326.9	326.9
122.5°	349.6	351.1	352.5	353.8	355.3	355.6	354.7	353.9	353.1	352.3	352.0
125°	385.1	386.5	387.7	389.1	390.4	390.8	390.4	389.9	389.5	389.1	388.6
127.5°	419.6	421.3	423.0	424.6	426.3	427.0	426.4	425.9	425.3	424.8	424.3
130°	441.3	443.3	445.1	447.1	449.0	449.8	449.5	449.2	448.9	448.6	448.4
132.5°	465.7	467.3	468.9	470.4	471.9	472.8	472.8	472.9	473.0	473.0	472.3
135°	498.3	499.9	501.5	503.1	504.7	505.7	506.0	506.3	506.6	506.8	506.7
137.5°	532.5	533.9	535.2	536.5	537.8	538.7	539.0	539.5	539.8	540.2	540.1
140°	553.2	554.5	555.8	557.1	558.5	559.5	560.3	561.0	561.7	562.4	562.4
142.5°	574.4	575.7	577.0	578.4	579.6	580.6	581.0	581.6	582.0	582.6	582.6
145°	604.8	605.8	606.8	607.9	608.9	609.8	610.7	611.6	612.5	613.4	613.5
147.5°	632.0	633.1	634.4	635.6	636.9	637.8	638.4	638.9	639.5	640.2	640.4
150°	650.4	651.3	652.2	653.1	654.0	654.7	655.3	655.9	656.5	657.1	657.5
152.5°	666.8	667.7	668.6	669.5	670.4	671.2	671.9	672.6	673.3	674.0	674.6
155°	691.4	691.9	692.3	692.8	693.2	693.7	694.1	694.6	695.0	695.4	696.2
157.5°	712.5	712.8	713.1	713.4	713.7	714.0	714.3	714.5	714.8	715.1	716.0
160°	725.2	725.5	725.8	726.1	726.4	726.7	726.7	726.9	727.0	727.2	728.1
162.5°	736.8	736.9	737.0	737.0	737.1	737.2	737.4	737.5	737.6	737.8	738.8
165°	752.3	752.2	752.1	751.9	751.8	751.7	751.7	751.7	751.7	751.7	752.7
167.5°	765.4	764.9	764.5	764.0	763.6	763.3	763.3	763.2	763.2	763.2	764.2
170°	772.2	771.8	771.3	770.9	770.4	770.2	770.0	769.8	769.7	769.5	770.6
172.5°	776.9	776.5	776.1	775.6	775.2	774.9	774.7	774.6	774.5	774.3	775.3
175°	782.7	782.4	781.9	781.5	781.0	780.7	780.3	780.1	779.8	779.4	780.5
177.5°	785.2	784.8	784.4	784.1	783.7	783.5	783.2	783.0	782.7	782.5	783.2
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331812-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1001.1	1002.7	1004.3	1005.0	1004.7	1004.3	1004.1	1003.7
5°	993.1	995.0	996.8	997.4	996.8	996.1	995.6	995.0
7.5°	977.0	977.6	978.1	977.9	976.8	975.8	974.7	973.7
10°	961.0	960.4	959.7	958.9	957.6	956.4	955.2	954.0
12.5°	942.5	941.5	940.3	938.8	936.7	934.8	932.7	930.7
15°	908.1	904.2	900.4	897.4	895.5	893.4	891.4	889.4
17.5°	869.2	864.5	860.0	856.0	852.5	849.0	845.5	842.0
20°	842.0	836.9	831.8	827.1	822.6	818.1	813.7	809.2
22.5°	812.1	805.6	799.1	794.2	790.8	787.5	784.2	780.9
25°	762.6	754.3	746.0	740.4	737.4	734.3	731.3	728.3
27.5°	715.4	705.8	696.2	688.8	684.0	679.2	674.4	669.6
30°	682.2	671.8	661.5	653.6	648.1	642.7	637.2	631.8
32.5°	648.6	636.9	625.1	616.6	611.4	606.4	601.2	596.1
35°	596.3	583.5	570.8	562.1	557.7	553.2	548.8	544.4
37.5°	545.2	531.2	517.2	507.6	502.5	497.4	492.3	487.2
40°	511.0	496.7	482.3	472.5	467.3	462.0	456.7	451.5
42.5°	476.6	461.7	446.9	436.9	431.9	426.8	421.7	416.5
45°	426.4	412.1	397.7	388.1	383.3	378.4	373.5	368.6
47.5°	377.6	363.4	349.0	339.7	335.3	330.9	326.5	322.1
50°	346.3	332.3	318.3	309.2	305.0	300.7	296.5	292.2
52.5°	316.6	303.1	289.6	281.0	277.1	273.1	269.2	265.3
55°	271.6	259.4	247.3	239.3	235.5	231.6	227.7	223.9
57.5°	230.6	219.5	208.4	201.2	198.0	194.7	191.5	188.2
60°	202.4	192.1	181.7	175.0	171.7	168.5	165.2	162.0
62.5°	177.9	168.0	158.2	152.3	150.3	148.5	146.5	144.5
65°	144.6	137.8	130.9	127.2	126.5	125.9	125.3	124.8
67.5°	116.7	113.6	110.5	108.5	107.9	107.3	106.6	105.9
70°	101.6	99.5	97.5	96.1	95.2	94.4	93.6	92.8
72.5°	88.4	86.7	85.0	83.9	83.4	82.9	82.4	81.9
75°	70.0	68.6	67.1	66.3	66.2	66.0	65.7	65.5
77.5°	53.0	52.2	51.4	50.8	50.5	50.2	49.8	49.5
80°	42.1	41.3	40.5	40.0	40.0	40.0	40.0	40.0
82.5°	31.8	31.3	30.9	30.6	30.6	30.6	30.6	30.6
85°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
87.5°	10.0	9.8	9.5	9.5	9.5	9.5	9.5	9.6
90°	22.6	22.3	22.0	21.9	22.0	22.2	22.4	22.5
92.5°	21.1	21.2	21.3	21.3	21.3	21.4	21.4	21.4
95°	42.4	42.4	42.4	42.2	41.9	41.6	41.3	41.0
97.5°	71.2	71.2	71.2	71.2	71.2	71.2	71.1	71.1
100°	91.3	91.3	91.3	91.2	91.1	91.0	90.8	90.7
102.5°	113.2	113.3	113.5	113.5	113.3	113.2	113.1	112.9
105°	146.2	146.4	146.8	146.9	146.9	146.9	146.9	146.9
107.5°	181.6	181.8	181.9	181.6	180.9	180.3	179.6	179.0
110°	205.8	205.8	205.8	205.5	205.1	204.6	204.2	203.8



TEST NUMBER: P331812-940

CATALOG NUMBER: S122RDIW-S675D710U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	230.0	229.6	229.3	228.9	228.6	228.3	227.9	227.7
115°	267.1	266.9	266.7	266.4	266.0	265.6	265.1	264.7
117.5°	302.9	302.6	302.2	301.8	301.3	300.9	300.4	300.0
120°	326.9	326.9	326.9	326.6	326.2	325.7	325.3	324.9
122.5°	351.6	351.2	350.9	350.5	350.2	349.9	349.6	349.3
125°	388.2	387.7	387.3	387.0	386.9	386.7	386.6	386.5
127.5°	423.7	423.2	422.7	422.2	421.7	421.2	420.8	420.4
130°	448.1	447.7	447.5	447.0	446.4	445.9	445.2	444.7
132.5°	471.7	471.0	470.4	469.8	469.4	468.9	468.4	468.0
135°	506.6	506.4	506.3	506.0	505.5	505.1	504.6	504.2
137.5°	539.9	539.8	539.8	539.4	538.8	538.2	537.6	537.0
140°	562.4	562.4	562.4	562.1	561.6	561.0	560.4	559.8
142.5°	582.8	582.9	583.0	582.8	582.2	581.6	581.0	580.4
145°	613.7	613.9	613.9	613.8	613.1	612.6	612.0	611.4
147.5°	640.8	641.1	641.4	641.3	640.8	640.2	639.6	639.1
150°	657.9	658.4	658.8	658.8	658.4	657.9	657.5	657.1
152.5°	675.1	675.6	676.3	676.3	675.6	675.1	674.6	674.0
155°	696.9	697.7	698.4	698.6	698.1	697.7	697.2	696.8
157.5°	717.0	718.0	719.0	719.2	718.5	717.7	717.0	716.3
160°	729.0	729.9	730.8	730.8	730.3	729.7	729.2	728.5
162.5°	739.8	740.8	741.8	741.9	741.2	740.6	739.9	739.1
165°	753.8	754.7	755.8	756.0	755.2	754.5	753.8	753.0
167.5°	765.3	766.2	767.3	767.4	766.7	765.9	765.2	764.4
170°	771.6	772.7	773.6	773.7	772.8	772.0	771.1	770.2
172.5°	776.4	777.4	778.5	778.5	777.7	776.8	775.9	775.0
175°	781.5	782.6	783.6	783.6	782.7	781.9	781.0	780.2
177.5°	783.9	784.6	785.3	785.3	784.6	783.9	783.2	782.5
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1

(END OF REPORT)