

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331837-940

Luminaire Tested: **S122RDIW-S865D1240U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331837-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D1240U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7364.2 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	89	85	87	84	81	78	69	67	65	55	54	53	42	42	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	37	35	30
3	81	72	65	60	73	66	60	55	55	50	47	44	41	39	34	33	31	26
4	74	64	57	51	67	59	52	48	49	44	41	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	33	30	28	26	24	21
6	63	52	44	39	58	48	41	36	40	35	31	33	29	26	26	24	22	19
7	59	47	39	34	53	43	37	32	37	31	28	30	26	24	24	22	20	17
8	54	43	35	30	50	40	33	29	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	26	22	19	21	18	16	14
10	48	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27493	27493	27493	27493
5°	30705	27665	24530	27665
10°	34067	27471	21263	27471
15°	35741	27067	16754	27067
20°	30986	26472	14496	26472
25°	20322	25655	12944	25655
30°	13679	24664	11714	24664
35°	11077	23416	10565	23416
40°	9851	22059	9778	22059
45°	8917	20466	8727	20466
50°	8116	18889	8083	18889
55°	7628	17140	7527	17140
60°	6381	15532	6307	15532
65°	5379	14105	6101	14105
70°	4971	12595	5755	12595
75°	4648	10967	5315	10967
80°	4296	9019	4733	9019
85°	3946	7114	4168	7114



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.4	2.2
10°-20°	449.8	6.1
20°-30°	579.6	7.9
30°-40°	550.8	7.5
40°-50°	471.8	6.4
50°-60°	359.3	4.9
60°-70°	227.1	3.1
70°-80°	113.4	1.5
80°-90°	33.2	0.5
90°-100°	50.3	0.7
100°-110°	184.4	2.5
110°-120°	492.9	6.7
120°-130°	813.7	11.0
130°-140°	865.3	11.8
140°-150°	804.3	10.9
150°-160°	646.7	8.8
160°-170°	416.7	5.7
170°-180°	143.4	1.9
0°-30°	1190.8	16.2
0°-40°	1741.6	23.6
0°-60°	2572.7	34.9
0°-90°	2946.5	40.0
90°-120°	727.6	9.9
90°-150°	3210.9	43.6
90°-180°	4418.0	60.0
0°-180°	7364.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1703	1703	1703	1703	1703	
5°	1894	1707	1514	1707	1894	187
15°	2138	1619	1002	1619	2138	577
25°	1141	1440	727	1440	1141	541
35°	562	1188	536	1188	562	360
45°	390	896	382	896	390	302
55°	271	609	267	609	271	238
65°	141	369	160	369	141	143
75°	74	176	85	176	74	79
85°	21	38	22	38	21	24
90°	29	1	29	1	29	14
95°	47	71	47	71	47	44
105°	83	332	83	332	83	86
115°	89	627	89	627	89	224
125°	933	887	933	887	933	807
135°	1133	1097	1133	1097	1133	874
145°	1293	1273	1293	1273	1293	808
155°	1403	1402	1403	1402	1403	647
165°	1474	1477	1474	1477	1474	416
175°	1502	1511	1502	1511	1502	143
180°	1507	1507	1507	1507	1507	



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1771.9	1773.3	1774.8	1771.4	1771.4	1768.6	1762.5	1757.7	1744.5	1742.6	1742.6
5°	1894.5	1893.3	1895.7	1888.0	1877.3	1875.0	1863.8	1849.0	1833.5	1816.4	1812.8
7.5°	2016.3	2014.6	2009.8	2008.6	2000.4	1982.5	1964.4	1945.2	1919.6	1894.6	1882.0
10°	2077.9	2097.4	2085.6	2064.8	2069.0	2041.2	2026.4	2001.0	1979.7	1942.4	1934.1
12.5°	2138.5	2146.2	2142.4	2130.7	2125.4	2106.0	2086.1	2064.0	2024.6	1991.2	1962.0
15°	2138.2	2149.5	2152.4	2148.9	2151.9	2150.7	2140.0	2121.6	2087.4	2050.7	2018.7
17.5°	1980.4	1988.2	2007.6	2020.7	2037.3	2072.3	2089.6	2096.3	2091.2	2070.3	2047.8
20°	1803.4	1790.4	1844.8	1872.6	1896.2	1955.4	2006.3	2025.9	2057.2	2056.6	2050.7
22.5°	1552.5	1555.6	1607.2	1640.2	1709.3	1768.4	1826.5	1900.0	1960.6	2000.7	2024.2
25°	1140.7	1163.2	1214.7	1259.6	1336.6	1446.6	1546.6	1662.6	1772.0	1858.4	1940.6
27.5°	856.8	858.4	899.2	940.8	986.4	1076.6	1202.5	1341.0	1497.0	1625.8	1773.9
30°	733.7	730.1	747.3	772.7	811.7	881.5	976.2	1112.3	1267.9	1462.0	1634.8
32.5°	646.6	646.8	659.7	678.5	711.0	758.0	822.9	933.4	1080.5	1271.2	1473.8
35°	562.0	561.5	571.0	584.5	598.2	628.3	672.7	730.7	831.9	1010.0	1217.0
37.5°	501.5	504.1	508.7	517.2	532.3	549.0	575.7	614.7	686.7	792.0	966.1
40°	467.4	468.6	475.1	482.2	491.1	504.1	526.0	557.3	610.0	694.0	821.2
42.5°	436.1	437.4	441.9	448.6	455.6	468.6	486.7	513.8	556.5	622.1	727.0
45°	390.5	390.5	394.7	397.6	405.3	417.1	431.9	454.4	483.9	532.5	602.4
47.5°	347.7	347.8	350.5	355.6	360.4	369.7	384.2	402.6	424.1	461.6	521.3
50°	323.1	323.6	325.4	329.6	332.5	340.8	352.0	368.0	390.5	419.5	469.2
52.5°	303.2	302.8	305.1	306.8	308.9	314.8	323.2	337.2	357.4	382.5	423.7
55°	271.0	268.6	272.2	275.1	276.9	279.3	284.0	292.8	310.0	331.4	362.1
57.5°	230.8	229.8	232.3	235.0	240.6	246.9	251.0	256.6	265.6	280.8	311.3
60°	197.6	197.6	203.0	204.7	211.2	219.5	227.8	232.6	241.4	251.5	273.9
62.5°	168.3	168.7	171.2	173.0	176.6	186.8	198.4	208.8	217.2	226.9	241.7
65°	140.8	142.0	142.0	143.2	145.5	147.9	152.7	161.0	175.8	189.3	200.5
67.5°	119.5	119.8	120.2	121.5	122.0	124.6	126.5	130.2	133.6	146.5	160.4
70°	105.3	107.1	106.5	107.7	108.3	109.4	111.8	113.6	119.0	121.9	130.2
72.5°	92.0	93.4	93.3	94.0	95.5	95.8	97.6	99.4	102.8	105.3	109.8
75°	74.5	73.9	74.5	75.7	76.3	77.0	77.0	79.3	81.1	83.5	86.4
77.5°	57.5	58.1	58.0	58.1	58.2	59.3	59.2	60.2	62.0	63.2	64.6
80°	46.2	46.7	46.2	46.7	47.3	47.9	47.3	47.9	49.7	50.9	50.9
82.5°	35.8	35.8	36.2	36.3	36.5	36.6	37.4	37.5	38.8	38.6	39.1
85°	21.3	20.7	20.7	20.7	21.3	21.8	21.3	21.3	21.8	21.8	21.8
87.5°	13.5	13.8	13.7	13.6	13.6	13.4	13.1	13.4	12.7	12.8	12.0
90°	29.4	29.0	28.4	28.0	27.6	26.7	25.4	24.3	23.0	21.8	19.9
92.5°	29.4	29.2	28.9	28.5	28.3	27.8	27.2	26.6	25.9	25.3	24.3
95°	46.9	47.2	47.3	47.6	47.9	47.3	46.2	44.9	43.8	42.5	40.8
97.5°	62.6	62.3	62.1	61.7	61.4	60.8	59.8	58.9	57.9	57.0	53.1
100°	73.1	72.6	72.1	71.6	71.2	69.9	67.9	66.1	64.1	62.2	58.1
102.5°	78.3	77.7	77.0	76.2	75.6	74.0	71.5	68.9	66.4	63.9	98.4
105°	82.9	81.9	81.0	80.0	79.0	77.2	74.5	71.9	69.2	66.5	132.7
107.5°	85.3	84.4	83.4	82.4	81.4	82.3	85.0	87.7	90.4	93.2	172.5
110°	86.1	85.2	84.3	83.3	82.3	93.9	118.2	142.4	166.7	190.9	260.9



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	87.0	86.2	85.5	84.7	83.9	127.8	216.2	304.6	393.1	481.4	498.8
115°	89.4	106.9	124.4	141.8	159.3	224.1	336.4	448.5	560.8	673.1	667.0
117.5°	365.2	422.6	479.9	537.3	594.6	636.9	664.0	691.2	718.3	745.5	741.3
120°	665.4	698.1	730.8	763.6	796.3	811.2	808.2	805.4	802.5	799.5	795.2
122.5°	830.3	836.7	843.0	849.4	855.7	858.0	856.3	854.5	852.7	851.0	846.3
125°	932.6	931.9	931.2	930.4	929.7	928.5	926.8	925.1	923.5	921.8	917.1
127.5°	997.2	997.0	996.9	996.8	996.7	995.3	992.8	990.3	987.9	985.4	982.0
130°	1037.3	1037.6	1037.9	1038.0	1038.3	1037.1	1034.5	1031.8	1029.1	1026.4	1023.8
132.5°	1076.7	1076.8	1077.1	1077.4	1077.5	1076.6	1074.2	1072.0	1069.7	1067.5	1064.8
135°	1133.4	1133.8	1134.3	1134.8	1135.2	1134.3	1131.8	1129.4	1127.0	1124.6	1122.4
137.5°	1185.0	1185.9	1186.7	1187.5	1188.3	1187.6	1185.2	1182.8	1180.4	1178.0	1175.5
140°	1217.4	1218.5	1219.8	1220.9	1222.2	1221.7	1219.5	1217.4	1215.1	1213.0	1210.3
142.5°	1248.8	1249.9	1251.2	1252.4	1253.6	1253.2	1251.2	1249.2	1247.2	1245.3	1242.2
145°	1292.6	1293.8	1295.0	1296.2	1297.4	1297.2	1295.5	1293.8	1292.1	1290.4	1286.3
147.5°	1331.2	1332.2	1333.2	1334.3	1335.2	1335.2	1333.9	1332.7	1331.4	1330.1	1326.1
150°	1354.8	1355.9	1357.2	1358.4	1359.6	1359.5	1358.1	1356.6	1355.1	1353.7	1349.8
152.5°	1374.8	1376.4	1378.0	1379.7	1381.3	1381.3	1379.8	1378.4	1377.0	1375.5	1371.8
155°	1402.8	1404.7	1406.7	1408.5	1410.5	1410.8	1409.3	1407.8	1406.4	1405.0	1402.0
157.5°	1428.3	1430.2	1432.1	1434.0	1435.8	1436.0	1434.3	1432.7	1431.0	1429.4	1427.4
160°	1443.1	1444.8	1446.5	1448.2	1449.9	1450.0	1448.6	1447.2	1445.6	1444.2	1442.8
162.5°	1455.4	1457.4	1459.5	1461.6	1463.7	1463.9	1462.2	1460.6	1458.9	1457.3	1456.1
165°	1473.6	1475.3	1477.0	1478.7	1480.4	1480.4	1478.7	1477.0	1475.3	1473.6	1472.9
167.5°	1485.2	1487.4	1489.6	1491.7	1494.0	1494.2	1492.5	1490.8	1489.1	1487.4	1486.7
170°	1492.2	1494.4	1496.6	1498.8	1500.9	1501.2	1499.5	1497.8	1496.1	1494.4	1493.9
172.5°	1497.4	1499.6	1501.8	1504.0	1506.2	1506.4	1504.7	1503.0	1501.3	1499.6	1499.1
175°	1502.0	1504.4	1506.9	1509.3	1511.7	1512.1	1510.4	1508.7	1507.0	1505.3	1504.9
177.5°	1504.9	1506.6	1508.3	1510.1	1511.8	1512.1	1510.6	1509.3	1508.0	1506.6	1506.4
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1743.5	1739.7	1736.4	1727.9	1723.6	1714.1	1712.7	1712.3	1700.0	1688.1	1684.8
5°	1803.4	1793.9	1779.7	1763.2	1746.0	1728.2	1716.4	1706.9	1683.3	1660.8	1647.8
7.5°	1863.8	1843.3	1818.9	1787.5	1761.4	1732.1	1710.2	1690.7	1657.2	1625.0	1603.3
10°	1908.7	1875.5	1843.0	1799.8	1766.1	1733.0	1702.2	1675.6	1637.7	1595.1	1565.0
12.5°	1936.6	1900.1	1855.3	1813.1	1769.4	1727.2	1686.1	1651.9	1607.4	1563.4	1527.5
15°	1974.3	1935.3	1880.9	1820.5	1764.3	1709.3	1662.0	1619.3	1561.4	1508.7	1464.9
17.5°	2005.3	1951.5	1893.1	1823.3	1758.2	1688.3	1627.3	1572.9	1508.3	1444.8	1393.2
20°	2015.2	1961.9	1894.5	1824.7	1747.8	1665.5	1599.8	1540.7	1471.4	1402.2	1343.1
22.5°	2009.0	1967.6	1892.6	1809.0	1730.3	1644.2	1570.0	1501.4	1424.6	1354.0	1285.3
25°	1967.3	1953.0	1882.0	1790.9	1701.0	1601.1	1515.2	1440.1	1352.5	1276.8	1202.2
27.5°	1869.9	1900.5	1856.5	1759.4	1659.5	1552.3	1455.8	1370.3	1279.4	1194.2	1119.9
30°	1776.2	1846.6	1827.7	1737.7	1625.9	1520.5	1412.3	1322.9	1225.9	1138.4	1065.0
32.5°	1647.9	1764.2	1782.7	1707.4	1591.8	1476.0	1362.6	1273.7	1172.4	1080.1	1008.6
35°	1443.7	1617.6	1697.5	1649.6	1533.6	1408.7	1291.6	1188.0	1086.3	995.1	924.2
37.5°	1200.0	1436.9	1570.0	1573.4	1467.0	1337.1	1209.6	1106.8	1002.6	913.2	836.3
40°	1041.9	1298.7	1472.0	1510.5	1420.6	1280.3	1151.4	1046.6	944.9	857.3	769.2
42.5°	899.9	1155.7	1368.9	1435.7	1364.2	1224.9	1095.6	986.1	887.2	804.3	714.3
45°	727.7	951.4	1186.2	1305.8	1266.1	1137.2	1000.5	896.3	803.4	731.9	645.5
47.5°	613.9	771.5	998.8	1160.5	1159.8	1042.1	907.6	807.9	721.7	654.6	584.7
50°	549.0	686.3	878.6	1062.0	1077.4	978.6	850.8	752.0	671.5	601.1	544.9
52.5°	490.8	604.0	776.9	952.7	996.5	910.9	786.9	695.7	617.6	552.9	504.7
55°	414.7	502.3	633.6	798.2	864.4	804.1	694.0	608.9	545.5	491.1	449.7
57.5°	350.9	416.5	521.9	654.3	731.6	693.6	602.8	533.6	479.4	430.2	397.4
60°	310.6	364.4	453.8	564.5	649.6	623.0	545.5	481.0	434.9	392.3	361.5
62.5°	272.8	319.1	395.6	485.4	563.5	552.5	489.2	435.1	394.7	355.8	329.8
65°	219.5	253.2	313.0	383.4	446.1	451.5	405.9	369.2	333.1	302.4	279.3
67.5°	174.8	196.8	238.9	298.2	345.2	361.9	334.1	306.1	277.5	253.7	233.7
70°	147.3	165.1	195.8	243.8	287.0	304.7	288.7	266.8	242.0	222.5	205.3
72.5°	119.4	136.7	159.3	194.6	231.6	250.7	245.2	229.4	209.3	193.1	176.9
75°	90.0	95.2	110.7	134.3	163.3	179.9	184.0	175.8	159.7	147.3	137.9
77.5°	66.5	69.7	77.0	89.4	108.4	123.1	129.2	128.2	117.3	110.0	101.2
80°	53.2	55.0	58.6	63.9	78.1	92.9	97.0	97.0	89.3	86.4	77.5
82.5°	40.5	41.7	43.9	46.8	53.5	66.3	71.0	72.0	67.1	63.2	56.2
85°	23.1	22.5	23.6	25.4	26.7	30.1	37.3	38.4	37.3	32.5	30.8
87.5°	11.6	11.7	11.3	10.4	10.3	10.3	12.1	13.9	12.6	11.7	11.3
90°	17.9	16.0	14.1	11.8	9.1	6.4	3.7	1.1	3.7	6.4	9.1
92.5°	23.4	22.4	21.4	21.0	21.3	21.6	21.8	22.0	21.8	21.6	21.3
95°	39.1	37.5	35.8	38.9	46.9	54.9	62.9	70.9	62.9	54.9	46.9
97.5°	49.0	45.1	41.2	50.6	73.1	95.6	118.2	140.7	118.2	95.6	73.1
100°	53.9	49.8	45.7	60.3	93.5	126.6	159.9	193.1	159.9	126.6	93.5
102.5°	132.9	167.3	201.8	222.6	229.6	236.6	243.6	250.7	243.6	236.6	229.6
105°	198.9	265.1	331.3	360.7	353.4	346.2	338.9	331.6	338.9	346.2	353.4
107.5°	251.9	331.3	410.6	447.4	441.5	435.6	429.7	423.9	429.7	435.6	441.5
110°	331.0	401.1	471.1	503.5	498.5	493.4	488.3	483.2	488.3	493.4	498.5



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	516.1	533.4	550.7	557.1	552.6	548.0	543.6	539.0	543.6	548.0	552.6
115°	660.9	654.9	648.8	643.7	639.5	635.4	631.3	627.2	631.3	635.4	639.5
117.5°	737.1	732.9	728.8	724.4	719.8	715.2	710.6	706.0	710.6	715.2	719.8
120°	790.9	786.5	782.1	778.1	774.5	770.8	767.2	763.6	767.2	770.8	774.5
122.5°	841.5	836.8	832.1	827.8	823.9	820.1	816.3	812.4	816.3	820.1	823.9
125°	912.5	907.9	903.3	899.4	896.3	893.1	889.9	886.8	889.9	893.1	896.3
127.5°	978.6	975.1	971.7	968.2	964.7	961.2	957.7	954.2	957.7	961.2	964.7
130°	1021.1	1018.4	1015.7	1012.5	1008.6	1004.8	1000.9	997.0	1000.9	1004.8	1008.6
132.5°	1062.1	1059.4	1056.8	1053.8	1050.5	1047.2	1043.9	1040.6	1043.9	1047.2	1050.5
135°	1120.3	1118.0	1115.9	1112.9	1108.9	1105.1	1101.2	1097.3	1101.2	1105.1	1108.9
137.5°	1173.1	1170.6	1168.1	1165.6	1162.9	1160.1	1157.4	1154.7	1157.4	1160.1	1162.9
140°	1207.6	1205.0	1202.3	1200.0	1198.0	1196.1	1194.2	1192.2	1194.2	1196.1	1198.0
142.5°	1239.1	1236.1	1233.1	1230.7	1228.9	1227.2	1225.4	1223.7	1225.4	1227.2	1228.9
145°	1282.2	1278.1	1273.9	1272.0	1272.2	1272.5	1272.7	1272.9	1272.7	1272.5	1272.2
147.5°	1322.0	1317.9	1313.8	1312.2	1313.1	1314.1	1315.0	1315.9	1315.0	1314.1	1313.1
150°	1345.9	1342.0	1338.2	1337.0	1338.7	1340.5	1342.2	1343.9	1342.2	1340.5	1338.7
152.5°	1368.2	1364.4	1360.8	1359.9	1361.7	1363.6	1365.6	1367.4	1365.6	1363.6	1361.7
155°	1399.1	1396.2	1393.3	1392.9	1395.1	1397.3	1399.5	1401.7	1399.5	1397.3	1395.1
157.5°	1425.3	1423.3	1421.2	1421.1	1423.0	1424.8	1426.6	1428.5	1426.6	1424.8	1423.0
160°	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1442.8	1441.3	1439.8
162.5°	1454.7	1453.5	1452.2	1452.3	1453.8	1455.3	1456.7	1458.2	1456.7	1455.3	1453.8
165°	1472.2	1471.5	1470.8	1471.1	1472.6	1474.0	1475.5	1476.9	1475.5	1474.0	1472.6
167.5°	1486.0	1485.4	1484.7	1485.1	1486.6	1488.0	1489.4	1490.9	1489.4	1488.0	1486.6
170°	1493.4	1492.9	1492.5	1492.9	1494.4	1495.8	1497.3	1498.8	1497.3	1495.8	1494.4
172.5°	1498.6	1498.2	1497.7	1498.2	1499.6	1501.1	1502.5	1504.0	1502.5	1501.1	1499.6
175°	1504.3	1503.9	1503.3	1504.0	1505.7	1507.3	1509.0	1510.7	1509.0	1507.3	1505.7
177.5°	1506.2	1506.0	1505.8	1506.4	1507.8	1509.1	1510.5	1511.8	1510.5	1509.1	1507.8
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1678.6	1675.3	1669.2	1659.7	1654.0	1644.1	1637.4	1641.3	1642.2	1641.3	1640.3
5°	1633.5	1621.1	1604.0	1587.4	1572.0	1555.5	1546.0	1541.9	1533.6	1528.8	1526.5
7.5°	1579.0	1557.6	1533.3	1504.5	1480.0	1454.3	1441.2	1434.7	1417.7	1408.5	1400.4
10°	1538.3	1504.6	1480.3	1442.4	1419.4	1385.6	1362.6	1363.2	1340.1	1327.0	1317.6
12.5°	1493.3	1456.3	1415.9	1381.9	1349.8	1322.7	1294.9	1283.6	1259.2	1246.6	1221.0
15°	1418.8	1375.6	1333.0	1286.8	1254.3	1212.3	1172.1	1122.9	1083.3	1049.0	1039.6
17.5°	1337.4	1283.9	1241.2	1187.0	1131.2	1060.6	1014.0	985.4	961.5	943.4	930.0
20°	1281.6	1227.1	1181.5	1099.9	1024.8	976.9	942.5	920.6	895.8	876.3	865.6
22.5°	1222.8	1166.0	1103.9	1012.8	954.2	915.8	885.2	860.1	843.2	828.0	818.2
25°	1139.5	1077.4	975.1	912.3	865.0	824.7	803.4	788.1	770.3	749.7	740.1
27.5°	1051.5	952.7	879.2	832.6	787.4	761.3	742.1	719.1	703.2	693.9	684.0
30°	985.7	886.9	829.5	778.6	746.6	717.6	695.2	682.2	666.8	650.9	644.4
32.5°	912.3	833.4	778.4	736.0	703.6	678.9	661.1	640.1	628.9	619.1	605.5
35°	821.2	761.4	711.1	676.9	646.1	626.0	605.3	592.8	572.7	564.5	559.1
37.5°	744.0	692.2	654.7	618.5	594.1	571.9	559.2	539.5	530.7	519.2	508.0
40°	700.5	649.6	613.6	584.0	556.8	540.2	524.2	508.3	495.3	489.9	476.3
42.5°	656.0	614.7	578.5	546.1	527.9	510.3	490.2	478.4	464.9	456.3	447.9
45°	594.6	557.9	527.2	500.5	480.5	462.1	449.1	429.5	421.9	404.7	397.6
47.5°	540.6	506.6	477.2	451.9	432.3	420.4	401.3	386.0	373.7	363.2	354.0
50°	502.3	473.9	445.5	423.0	405.3	388.2	368.6	360.9	342.0	336.6	331.4
52.5°	467.3	440.3	414.3	392.3	374.5	357.8	340.6	330.6	317.8	312.5	308.6
55°	418.3	392.3	367.4	347.9	330.1	313.0	302.4	289.9	284.0	279.8	275.1
57.5°	369.1	345.6	326.6	306.8	289.0	275.4	263.1	255.6	249.4	244.0	238.4
60°	337.9	315.3	298.2	279.8	261.5	250.3	240.8	231.9	224.8	216.5	214.2
62.5°	304.7	285.1	269.3	251.5	235.5	225.2	216.2	207.8	199.3	187.2	183.9
65°	259.1	243.8	227.2	212.4	198.2	188.2	175.1	165.7	162.1	161.0	160.3
67.5°	217.9	203.4	189.2	174.1	161.1	151.9	145.2	143.7	141.2	140.5	138.9
70°	190.5	176.9	162.7	148.5	136.1	134.3	132.0	129.6	126.6	125.5	124.2
72.5°	165.9	151.9	137.6	126.3	120.9	118.7	116.3	114.0	111.9	110.8	110.0
75°	127.2	114.2	104.7	100.6	97.6	95.9	92.3	90.5	89.3	87.6	86.9
77.5°	91.6	84.3	79.9	77.3	74.2	72.3	70.3	68.5	67.2	66.9	65.9
80°	69.8	66.3	63.3	59.7	58.6	56.2	55.6	53.9	54.4	52.7	52.7
82.5°	54.2	49.7	47.2	45.6	44.4	42.4	41.9	41.0	41.2	39.9	39.9
85°	27.8	26.7	25.4	24.3	24.3	22.5	23.1	22.5	22.5	21.3	20.7
87.5°	11.3	11.3	10.8	11.1	11.6	11.5	11.7	11.5	11.7	11.9	11.7
90°	11.8	14.1	16.0	17.9	19.9	21.8	23.0	24.3	25.4	26.7	27.6
92.5°	21.0	21.4	22.4	23.4	24.3	25.3	25.9	26.6	27.2	27.8	28.3
95°	38.9	35.8	37.5	39.1	40.8	42.5	43.8	44.9	46.2	47.3	47.9
97.5°	50.6	41.2	45.1	49.0	53.1	57.0	57.9	58.9	59.8	60.8	61.4
100°	60.3	45.7	49.8	53.9	58.1	62.2	64.1	66.1	67.9	69.9	71.2
102.5°	222.6	201.8	167.3	132.9	98.4	63.9	66.4	68.9	71.5	74.0	75.6
105°	360.7	331.3	265.1	198.9	132.7	66.5	69.2	71.9	74.5	77.2	79.0
107.5°	447.4	410.6	331.3	251.9	172.5	93.2	90.4	87.7	85.0	82.3	81.4
110°	503.5	471.1	401.1	331.0	260.9	190.9	166.7	142.4	118.2	93.9	82.3



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	557.1	550.7	533.4	516.1	498.8	481.4	393.1	304.6	216.2	127.8	83.9
115°	643.7	648.8	654.9	660.9	667.0	673.1	560.8	448.5	336.4	224.1	159.3
117.5°	724.4	728.8	732.9	737.1	741.3	745.5	718.3	691.2	664.0	636.9	594.6
120°	778.1	782.1	786.5	790.9	795.2	799.5	802.5	805.4	808.2	811.2	796.3
122.5°	827.8	832.1	836.8	841.5	846.3	851.0	852.7	854.5	856.3	858.0	855.7
125°	899.4	903.3	907.9	912.5	917.1	921.8	923.5	925.1	926.8	928.5	929.7
127.5°	968.2	971.7	975.1	978.6	982.0	985.4	987.9	990.3	992.8	995.3	996.7
130°	1012.5	1015.7	1018.4	1021.1	1023.8	1026.4	1029.1	1031.8	1034.5	1037.1	1038.3
132.5°	1053.8	1056.8	1059.4	1062.1	1064.8	1067.5	1069.7	1072.0	1074.2	1076.6	1077.5
135°	1112.9	1115.9	1118.0	1120.3	1122.4	1124.6	1127.0	1129.4	1131.8	1134.3	1135.2
137.5°	1165.6	1168.1	1170.6	1173.1	1175.5	1178.0	1180.4	1182.8	1185.2	1187.6	1188.3
140°	1200.0	1202.3	1205.0	1207.6	1210.3	1213.0	1215.1	1217.4	1219.5	1221.7	1222.2
142.5°	1230.7	1233.1	1236.1	1239.1	1242.2	1245.3	1247.2	1249.2	1251.2	1253.2	1253.6
145°	1272.0	1273.9	1278.1	1282.2	1286.3	1290.4	1292.1	1293.8	1295.5	1297.2	1297.4
147.5°	1312.2	1313.8	1317.9	1322.0	1326.1	1330.1	1331.4	1332.7	1333.9	1335.2	1335.2
150°	1337.0	1338.2	1342.0	1345.9	1349.8	1353.7	1355.1	1356.6	1358.1	1359.5	1359.6
152.5°	1359.9	1360.8	1364.4	1368.2	1371.8	1375.5	1377.0	1378.4	1379.8	1381.3	1381.3
155°	1392.9	1393.3	1396.2	1399.1	1402.0	1405.0	1406.4	1407.8	1409.3	1410.8	1410.5
157.5°	1421.1	1421.2	1423.3	1425.3	1427.4	1429.4	1431.0	1432.7	1434.3	1436.0	1435.8
160°	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1445.6	1447.2	1448.6	1450.0	1449.9
162.5°	1452.3	1452.2	1453.5	1454.7	1456.1	1457.3	1458.9	1460.6	1462.2	1463.9	1463.7
165°	1471.1	1470.8	1471.5	1472.2	1472.9	1473.6	1475.3	1477.0	1478.7	1480.4	1480.4
167.5°	1485.1	1484.7	1485.4	1486.0	1486.7	1487.4	1489.1	1490.8	1492.5	1494.2	1494.0
170°	1492.9	1492.5	1492.9	1493.4	1493.9	1494.4	1496.1	1497.8	1499.5	1501.2	1500.9
172.5°	1498.2	1497.7	1498.2	1498.6	1499.1	1499.6	1501.3	1503.0	1504.7	1506.4	1506.2
175°	1504.0	1503.3	1503.9	1504.3	1504.9	1505.3	1507.0	1508.7	1510.4	1512.1	1511.7
177.5°	1506.4	1505.8	1506.0	1506.2	1506.4	1506.6	1508.0	1509.3	1510.6	1512.1	1511.8
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1635.1	1636.0	1634.6	1635.6	1634.6	1636.0	1635.1	1640.3	1641.3	1642.2	1641.3
5°	1523.5	1516.4	1515.2	1513.5	1515.2	1516.4	1523.5	1526.5	1528.8	1533.6	1541.9
7.5°	1390.3	1389.2	1386.3	1382.2	1386.3	1389.2	1390.3	1400.4	1408.5	1417.7	1434.7
10°	1304.6	1301.6	1301.1	1296.9	1301.1	1301.6	1304.6	1317.6	1327.0	1340.1	1363.2
12.5°	1204.3	1185.2	1183.2	1172.9	1183.2	1185.2	1204.3	1221.0	1246.6	1259.2	1283.6
15°	1025.4	1021.8	1010.0	1002.3	1010.0	1021.8	1025.4	1039.6	1049.0	1083.3	1122.9
17.5°	923.1	911.5	907.9	906.2	907.9	911.5	923.1	930.0	943.4	961.5	985.4
20°	857.3	846.7	844.9	843.7	844.9	846.7	857.3	865.6	876.3	895.8	920.6
22.5°	811.9	800.8	796.1	792.6	796.1	800.8	811.9	818.2	828.0	843.2	860.1
25°	734.2	730.1	727.7	726.6	727.7	730.1	734.2	740.1	749.7	770.3	788.1
27.5°	673.5	664.4	662.6	659.6	662.6	664.4	673.5	684.0	693.9	703.2	719.1
30°	639.0	636.1	631.9	628.3	631.9	636.1	639.0	644.4	650.9	666.8	682.2
32.5°	598.2	595.8	592.1	590.5	592.1	595.8	598.2	605.5	619.1	628.9	640.1
35°	553.2	544.9	541.4	536.0	541.4	544.9	553.2	559.1	564.5	572.7	592.8
37.5°	505.5	501.1	496.1	497.9	496.1	501.1	505.5	508.0	519.2	530.7	539.5
40°	468.6	465.7	464.5	463.9	464.5	465.7	468.6	476.3	489.9	495.3	508.3
42.5°	439.3	431.1	428.0	427.8	428.0	431.1	439.3	447.9	456.3	464.9	478.4
45°	394.7	386.9	381.7	382.2	381.7	386.9	394.7	397.6	404.7	421.9	429.5
47.5°	348.9	348.7	345.4	346.5	345.4	348.7	348.9	354.0	363.2	373.7	386.0
50°	327.2	323.6	321.3	321.8	321.3	323.6	327.2	331.4	336.6	342.0	360.9
52.5°	306.4	303.3	301.4	303.9	301.4	303.3	306.4	308.6	312.5	317.8	330.6
55°	272.2	268.6	268.0	267.4	268.0	268.6	272.2	275.1	279.8	284.0	289.9
57.5°	234.0	231.6	228.0	226.5	228.0	231.6	234.0	238.4	244.0	249.4	255.6
60°	206.5	201.8	195.8	195.3	195.8	201.8	206.5	214.2	216.5	224.8	231.9
62.5°	181.4	180.5	179.2	179.1	179.2	180.5	181.4	183.9	187.2	199.3	207.8
65°	159.2	158.5	159.2	159.7	159.2	158.5	159.2	160.3	161.0	162.1	165.7
67.5°	138.7	137.6	136.5	137.1	136.5	137.6	138.7	138.9	140.5	141.2	143.7
70°	123.1	122.4	121.9	121.9	121.9	122.4	123.1	124.2	125.5	126.6	129.6
72.5°	107.9	107.8	107.2	106.7	107.2	107.8	107.9	110.0	110.8	111.9	114.0
75°	86.4	85.2	85.2	85.2	85.2	85.2	86.4	86.9	87.6	89.3	90.5
77.5°	65.8	65.2	64.6	64.1	64.6	65.2	65.8	65.9	66.9	67.2	68.5
80°	52.1	51.5	50.9	50.9	50.9	51.5	52.1	52.7	52.7	54.4	53.9
82.5°	39.8	39.1	39.1	38.6	39.1	39.1	39.8	39.9	39.9	41.2	41.0
85°	21.3	21.8	21.3	22.5	21.3	21.8	21.3	20.7	21.3	22.5	22.5
87.5°	11.8	11.4	11.9	11.6	11.9	11.4	11.8	11.7	11.9	11.7	11.5
90°	28.0	28.4	29.0	29.4	29.0	28.4	28.0	27.6	26.7	25.4	24.3
92.5°	28.5	28.9	29.2	29.4	29.2	28.9	28.5	28.3	27.8	27.2	26.6
95°	47.6	47.3	47.2	46.9	47.2	47.3	47.6	47.9	47.3	46.2	44.9
97.5°	61.7	62.1	62.3	62.6	62.3	62.1	61.7	61.4	60.8	59.8	58.9
100°	71.6	72.1	72.6	73.1	72.6	72.1	71.6	71.2	69.9	67.9	66.1
102.5°	76.2	77.0	77.7	78.3	77.7	77.0	76.2	75.6	74.0	71.5	68.9
105°	80.0	81.0	81.9	82.9	81.9	81.0	80.0	79.0	77.2	74.5	71.9
107.5°	82.4	83.4	84.4	85.3	84.4	83.4	82.4	81.4	82.3	85.0	87.7
110°	83.3	84.3	85.2	86.1	85.2	84.3	83.3	82.3	93.9	118.2	142.4



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	84.7	85.5	86.2	87.0	86.2	85.5	84.7	83.9	127.8	216.2	304.6
115°	141.8	124.4	106.9	89.4	106.9	124.4	141.8	159.3	224.1	336.4	448.5
117.5°	537.3	479.9	422.6	365.2	422.6	479.9	537.3	594.6	636.9	664.0	691.2
120°	763.6	730.8	698.1	665.4	698.1	730.8	763.6	796.3	811.2	808.2	805.4
122.5°	849.4	843.0	836.7	830.3	836.7	843.0	849.4	855.7	858.0	856.3	854.5
125°	930.4	931.2	931.9	932.6	931.9	931.2	930.4	929.7	928.5	926.8	925.1
127.5°	996.8	996.9	997.0	997.2	997.0	996.9	996.8	996.7	995.3	992.8	990.3
130°	1038.0	1037.9	1037.6	1037.3	1037.6	1037.9	1038.0	1038.3	1037.1	1034.5	1031.8
132.5°	1077.4	1077.1	1076.8	1076.7	1076.8	1077.1	1077.4	1077.5	1076.6	1074.2	1072.0
135°	1134.8	1134.3	1133.8	1133.4	1133.8	1134.3	1134.8	1135.2	1134.3	1131.8	1129.4
137.5°	1187.5	1186.7	1185.9	1185.0	1185.9	1186.7	1187.5	1188.3	1187.6	1185.2	1182.8
140°	1220.9	1219.8	1218.5	1217.4	1218.5	1219.8	1220.9	1222.2	1221.7	1219.5	1217.4
142.5°	1252.4	1251.2	1249.9	1248.8	1249.9	1251.2	1252.4	1253.6	1253.2	1251.2	1249.2
145°	1296.2	1295.0	1293.8	1292.6	1293.8	1295.0	1296.2	1297.4	1297.2	1295.5	1293.8
147.5°	1334.3	1333.2	1332.2	1331.2	1332.2	1333.2	1334.3	1335.2	1335.2	1333.9	1332.7
150°	1358.4	1357.2	1355.9	1354.8	1355.9	1357.2	1358.4	1359.6	1359.5	1358.1	1356.6
152.5°	1379.7	1378.0	1376.4	1374.8	1376.4	1378.0	1379.7	1381.3	1381.3	1379.8	1378.4
155°	1408.5	1406.7	1404.7	1402.8	1404.7	1406.7	1408.5	1410.5	1410.8	1409.3	1407.8
157.5°	1434.0	1432.1	1430.2	1428.3	1430.2	1432.1	1434.0	1435.8	1436.0	1434.3	1432.7
160°	1448.2	1446.5	1444.8	1443.1	1444.8	1446.5	1448.2	1449.9	1450.0	1448.6	1447.2
162.5°	1461.6	1459.5	1457.4	1455.4	1457.4	1459.5	1461.6	1463.7	1463.9	1462.2	1460.6
165°	1478.7	1477.0	1475.3	1473.6	1475.3	1477.0	1478.7	1480.4	1480.4	1478.7	1477.0
167.5°	1491.7	1489.6	1487.4	1485.2	1487.4	1489.6	1491.7	1494.0	1494.2	1492.5	1490.8
170°	1498.8	1496.6	1494.4	1492.2	1494.4	1496.6	1498.8	1500.9	1501.2	1499.5	1497.8
172.5°	1504.0	1501.8	1499.6	1497.4	1499.6	1501.8	1504.0	1506.2	1506.4	1504.7	1503.0
175°	1509.3	1506.9	1504.4	1502.0	1504.4	1506.9	1509.3	1511.7	1512.1	1510.4	1508.7
177.5°	1510.1	1508.3	1506.6	1504.9	1506.6	1508.3	1510.1	1511.8	1512.1	1510.6	1509.3
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1637.4	1644.1	1654.0	1659.7	1669.2	1675.3	1678.6	1684.8	1688.1	1700.0	1712.3
5°	1546.0	1555.5	1572.0	1587.4	1604.0	1621.1	1633.5	1647.8	1660.8	1683.3	1706.9
7.5°	1441.2	1454.3	1480.0	1504.5	1533.3	1557.6	1579.0	1603.3	1625.0	1657.2	1690.7
10°	1362.6	1385.6	1419.4	1442.4	1480.3	1504.6	1538.3	1565.0	1595.1	1637.7	1675.6
12.5°	1294.9	1322.7	1349.8	1381.9	1415.9	1456.3	1493.3	1527.5	1563.4	1607.4	1651.9
15°	1172.1	1212.3	1254.3	1286.8	1333.0	1375.6	1418.8	1464.9	1508.7	1561.4	1619.3
17.5°	1014.0	1060.6	1131.2	1187.0	1241.2	1283.9	1337.4	1393.2	1444.8	1508.3	1572.9
20°	942.5	976.9	1024.8	1099.9	1181.5	1227.1	1281.6	1343.1	1402.2	1471.4	1540.7
22.5°	885.2	915.8	954.2	1012.8	1103.9	1166.0	1222.8	1285.3	1354.0	1424.6	1501.4
25°	803.4	824.7	865.0	912.3	975.1	1077.4	1139.5	1202.2	1276.8	1352.5	1440.1
27.5°	742.1	761.3	787.4	832.6	879.2	952.7	1051.5	1119.9	1194.2	1279.4	1370.3
30°	695.2	717.6	746.6	778.6	829.5	886.9	985.7	1065.0	1138.4	1225.9	1322.9
32.5°	661.1	678.9	703.6	736.0	778.4	833.4	912.3	1008.6	1080.1	1172.4	1273.7
35°	605.3	626.0	646.1	676.9	711.1	761.4	821.2	924.2	995.1	1086.3	1188.0
37.5°	559.2	571.9	594.1	618.5	654.7	692.2	744.0	836.3	913.2	1002.6	1106.8
40°	524.2	540.2	556.8	584.0	613.6	649.6	700.5	769.2	857.3	944.9	1046.6
42.5°	490.2	510.3	527.9	546.1	578.5	614.7	656.0	714.3	804.3	887.2	986.1
45°	449.1	462.1	480.5	500.5	527.2	557.9	594.6	645.5	731.9	803.4	896.3
47.5°	401.3	420.4	432.3	451.9	477.2	506.6	540.6	584.7	654.6	721.7	807.9
50°	368.6	388.2	405.3	423.0	445.5	473.9	502.3	544.9	601.1	671.5	752.0
52.5°	340.6	357.8	374.5	392.3	414.3	440.3	467.3	504.7	552.9	617.6	695.7
55°	302.4	313.0	330.1	347.9	367.4	392.3	418.3	449.7	491.1	545.5	608.9
57.5°	263.1	275.4	289.0	306.8	326.6	345.6	369.1	397.4	430.2	479.4	533.6
60°	240.8	250.3	261.5	279.8	298.2	315.3	337.9	361.5	392.3	434.9	481.0
62.5°	216.2	225.2	235.5	251.5	269.3	285.1	304.7	329.8	355.8	394.7	435.1
65°	175.1	188.2	198.2	212.4	227.2	243.8	259.1	279.3	302.4	333.1	369.2
67.5°	145.2	151.9	161.1	174.1	189.2	203.4	217.9	233.7	253.7	277.5	306.1
70°	132.0	134.3	136.1	148.5	162.7	176.9	190.5	205.3	222.5	242.0	266.8
72.5°	116.3	118.7	120.9	126.3	137.6	151.9	165.9	176.9	193.1	209.3	229.4
75°	92.3	95.9	97.6	100.6	104.7	114.2	127.2	137.9	147.3	159.7	175.8
77.5°	70.3	72.3	74.2	77.3	79.9	84.3	91.6	101.2	110.0	117.3	128.2
80°	55.6	56.2	58.6	59.7	63.3	66.3	69.8	77.5	86.4	89.3	97.0
82.5°	41.9	42.4	44.4	45.6	47.2	49.7	54.2	56.2	63.2	67.1	72.0
85°	23.1	22.5	24.3	24.3	25.4	26.7	27.8	30.8	32.5	37.3	38.4
87.5°	11.7	11.5	11.6	11.1	10.8	11.3	11.3	11.3	11.7	12.6	13.9
90°	23.0	21.8	19.9	17.9	16.0	14.1	11.8	9.1	6.4	3.7	1.1
92.5°	25.9	25.3	24.3	23.4	22.4	21.4	21.0	21.3	21.6	21.8	22.0
95°	43.8	42.5	40.8	39.1	37.5	35.8	38.9	46.9	54.9	62.9	70.9
97.5°	57.9	57.0	53.1	49.0	45.1	41.2	50.6	73.1	95.6	118.2	140.7
100°	64.1	62.2	58.1	53.9	49.8	45.7	60.3	93.5	126.6	159.9	193.1
102.5°	66.4	63.9	98.4	132.9	167.3	201.8	222.6	229.6	236.6	243.6	250.7
105°	69.2	66.5	132.7	198.9	265.1	331.3	360.7	353.4	346.2	338.9	331.6
107.5°	90.4	93.2	172.5	251.9	331.3	410.6	447.4	441.5	435.6	429.7	423.9
110°	166.7	190.9	260.9	331.0	401.1	471.1	503.5	498.5	493.4	488.3	483.2



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	393.1	481.4	498.8	516.1	533.4	550.7	557.1	552.6	548.0	543.6	539.0
115°	560.8	673.1	667.0	660.9	654.9	648.8	643.7	639.5	635.4	631.3	627.2
117.5°	718.3	745.5	741.3	737.1	732.9	728.8	724.4	719.8	715.2	710.6	706.0
120°	802.5	799.5	795.2	790.9	786.5	782.1	778.1	774.5	770.8	767.2	763.6
122.5°	852.7	851.0	846.3	841.5	836.8	832.1	827.8	823.9	820.1	816.3	812.4
125°	923.5	921.8	917.1	912.5	907.9	903.3	899.4	896.3	893.1	889.9	886.8
127.5°	987.9	985.4	982.0	978.6	975.1	971.7	968.2	964.7	961.2	957.7	954.2
130°	1029.1	1026.4	1023.8	1021.1	1018.4	1015.7	1012.5	1008.6	1004.8	1000.9	997.0
132.5°	1069.7	1067.5	1064.8	1062.1	1059.4	1056.8	1053.8	1050.5	1047.2	1043.9	1040.6
135°	1127.0	1124.6	1122.4	1120.3	1118.0	1115.9	1112.9	1108.9	1105.1	1101.2	1097.3
137.5°	1180.4	1178.0	1175.5	1173.1	1170.6	1168.1	1165.6	1162.9	1160.1	1157.4	1154.7
140°	1215.1	1213.0	1210.3	1207.6	1205.0	1202.3	1200.0	1198.0	1196.1	1194.2	1192.2
142.5°	1247.2	1245.3	1242.2	1239.1	1236.1	1233.1	1230.7	1228.9	1227.2	1225.4	1223.7
145°	1292.1	1290.4	1286.3	1282.2	1278.1	1273.9	1272.0	1272.2	1272.5	1272.7	1272.9
147.5°	1331.4	1330.1	1326.1	1322.0	1317.9	1313.8	1312.2	1313.1	1314.1	1315.0	1315.9
150°	1355.1	1353.7	1349.8	1345.9	1342.0	1338.2	1337.0	1338.7	1340.5	1342.2	1343.9
152.5°	1377.0	1375.5	1371.8	1368.2	1364.4	1360.8	1359.9	1361.7	1363.6	1365.6	1367.4
155°	1406.4	1405.0	1402.0	1399.1	1396.2	1393.3	1392.9	1395.1	1397.3	1399.5	1401.7
157.5°	1431.0	1429.4	1427.4	1425.3	1423.3	1421.2	1421.1	1423.0	1424.8	1426.6	1428.5
160°	1445.6	1444.2	1442.8	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2
162.5°	1458.9	1457.3	1456.1	1454.7	1453.5	1452.2	1452.3	1453.8	1455.3	1456.7	1458.2
165°	1475.3	1473.6	1472.9	1472.2	1471.5	1470.8	1471.1	1472.6	1474.0	1475.5	1476.9
167.5°	1489.1	1487.4	1486.7	1486.0	1485.4	1484.7	1485.1	1486.6	1488.0	1489.4	1490.9
170°	1496.1	1494.4	1493.9	1493.4	1492.9	1492.5	1492.9	1494.4	1495.8	1497.3	1498.8
172.5°	1501.3	1499.6	1499.1	1498.6	1498.2	1497.7	1498.2	1499.6	1501.1	1502.5	1504.0
175°	1507.0	1505.3	1504.9	1504.3	1503.9	1503.3	1504.0	1505.7	1507.3	1509.0	1510.7
177.5°	1508.0	1506.6	1506.4	1506.2	1506.0	1505.8	1506.4	1507.8	1509.1	1510.5	1511.8
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1712.7	1714.1	1723.6	1727.9	1736.4	1739.7	1743.5	1742.6	1742.6	1744.5	1757.7
5°	1716.4	1728.2	1746.0	1763.2	1779.7	1793.9	1803.4	1812.8	1816.4	1833.5	1849.0
7.5°	1710.2	1732.1	1761.4	1787.5	1818.9	1843.3	1863.8	1882.0	1894.6	1919.6	1945.2
10°	1702.2	1733.0	1766.1	1799.8	1843.0	1875.5	1908.7	1934.1	1942.4	1979.7	2001.0
12.5°	1686.1	1727.2	1769.4	1813.1	1855.3	1900.1	1936.6	1962.0	1991.2	2024.6	2064.0
15°	1662.0	1709.3	1764.3	1820.5	1880.9	1935.3	1974.3	2018.7	2050.7	2087.4	2121.6
17.5°	1627.3	1688.3	1758.2	1823.3	1893.1	1951.5	2005.3	2047.8	2070.3	2091.2	2096.3
20°	1599.8	1665.5	1747.8	1824.7	1894.5	1961.9	2015.2	2050.7	2056.6	2057.2	2025.9
22.5°	1570.0	1644.2	1730.3	1809.0	1892.6	1967.6	2009.0	2024.2	2000.7	1960.6	1900.0
25°	1515.2	1601.1	1701.0	1790.9	1882.0	1953.0	1967.3	1940.6	1858.4	1772.0	1662.6
27.5°	1455.8	1552.3	1659.5	1759.4	1856.5	1900.5	1869.9	1773.9	1625.8	1497.0	1341.0
30°	1412.3	1520.5	1625.9	1737.7	1827.7	1846.6	1776.2	1634.8	1462.0	1267.9	1112.3
32.5°	1362.6	1476.0	1591.8	1707.4	1782.7	1764.2	1647.9	1473.8	1271.2	1080.5	933.4
35°	1291.6	1408.7	1533.6	1649.6	1697.5	1617.6	1443.7	1217.0	1010.0	831.9	730.7
37.5°	1209.6	1337.1	1467.0	1573.4	1570.0	1436.9	1200.0	966.1	792.0	686.7	614.7
40°	1151.4	1280.3	1420.6	1510.5	1472.0	1298.7	1041.9	821.2	694.0	610.0	557.3
42.5°	1095.6	1224.9	1364.2	1435.7	1368.9	1155.7	899.9	727.0	622.1	556.5	513.8
45°	1000.5	1137.2	1266.1	1305.8	1186.2	951.4	727.7	602.4	532.5	483.9	454.4
47.5°	907.6	1042.1	1159.8	1160.5	998.8	771.5	613.9	521.3	461.6	424.1	402.6
50°	850.8	978.6	1077.4	1062.0	878.6	686.3	549.0	469.2	419.5	390.5	368.0
52.5°	786.9	910.9	996.5	952.7	776.9	604.0	490.8	423.7	382.5	357.4	337.2
55°	694.0	804.1	864.4	798.2	633.6	502.3	414.7	362.1	331.4	310.0	292.8
57.5°	602.8	693.6	731.6	654.3	521.9	416.5	350.9	311.3	280.8	265.6	256.6
60°	545.5	623.0	649.6	564.5	453.8	364.4	310.6	273.9	251.5	241.4	232.6
62.5°	489.2	552.5	563.5	485.4	395.6	319.1	272.8	241.7	226.9	217.2	208.8
65°	405.9	451.5	446.1	383.4	313.0	253.2	219.5	200.5	189.3	175.8	161.0
67.5°	334.1	361.9	345.2	298.2	238.9	196.8	174.8	160.4	146.5	133.6	130.2
70°	288.7	304.7	287.0	243.8	195.8	165.1	147.3	130.2	121.9	119.0	113.6
72.5°	245.2	250.7	231.6	194.6	159.3	136.7	119.4	109.8	105.3	102.8	99.4
75°	184.0	179.9	163.3	134.3	110.7	95.2	90.0	86.4	83.5	81.1	79.3
77.5°	129.2	123.1	108.4	89.4	77.0	69.7	66.5	64.6	63.2	62.0	60.2
80°	97.0	92.9	78.1	63.9	58.6	55.0	53.2	50.9	50.9	49.7	47.9
82.5°	71.0	66.3	53.5	46.8	43.9	41.7	40.5	39.1	38.6	38.8	37.5
85°	37.3	30.1	26.7	25.4	23.6	22.5	23.1	21.8	21.8	21.8	21.3
87.5°	12.1	10.3	10.3	10.4	11.3	11.7	11.6	12.0	12.8	12.7	13.4
90°	3.7	6.4	9.1	11.8	14.1	16.0	17.9	19.9	21.8	23.0	24.3
92.5°	21.8	21.6	21.3	21.0	21.4	22.4	23.4	24.3	25.3	25.9	26.6
95°	62.9	54.9	46.9	38.9	35.8	37.5	39.1	40.8	42.5	43.8	44.9
97.5°	118.2	95.6	73.1	50.6	41.2	45.1	49.0	53.1	57.0	57.9	58.9
100°	159.9	126.6	93.5	60.3	45.7	49.8	53.9	58.1	62.2	64.1	66.1
102.5°	243.6	236.6	229.6	222.6	201.8	167.3	132.9	98.4	63.9	66.4	68.9
105°	338.9	346.2	353.4	360.7	331.3	265.1	198.9	132.7	66.5	69.2	71.9
107.5°	429.7	435.6	441.5	447.4	410.6	331.3	251.9	172.5	93.2	90.4	87.7
110°	488.3	493.4	498.5	503.5	471.1	401.1	331.0	260.9	190.9	166.7	142.4



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	543.6	548.0	552.6	557.1	550.7	533.4	516.1	498.8	481.4	393.1	304.6
115°	631.3	635.4	639.5	643.7	648.8	654.9	660.9	667.0	673.1	560.8	448.5
117.5°	710.6	715.2	719.8	724.4	728.8	732.9	737.1	741.3	745.5	718.3	691.2
120°	767.2	770.8	774.5	778.1	782.1	786.5	790.9	795.2	799.5	802.5	805.4
122.5°	816.3	820.1	823.9	827.8	832.1	836.8	841.5	846.3	851.0	852.7	854.5
125°	889.9	893.1	896.3	899.4	903.3	907.9	912.5	917.1	921.8	923.5	925.1
127.5°	957.7	961.2	964.7	968.2	971.7	975.1	978.6	982.0	985.4	987.9	990.3
130°	1000.9	1004.8	1008.6	1012.5	1015.7	1018.4	1021.1	1023.8	1026.4	1029.1	1031.8
132.5°	1043.9	1047.2	1050.5	1053.8	1056.8	1059.4	1062.1	1064.8	1067.5	1069.7	1072.0
135°	1101.2	1105.1	1108.9	1112.9	1115.9	1118.0	1120.3	1122.4	1124.6	1127.0	1129.4
137.5°	1157.4	1160.1	1162.9	1165.6	1168.1	1170.6	1173.1	1175.5	1178.0	1180.4	1182.8
140°	1194.2	1196.1	1198.0	1200.0	1202.3	1205.0	1207.6	1210.3	1213.0	1215.1	1217.4
142.5°	1225.4	1227.2	1228.9	1230.7	1233.1	1236.1	1239.1	1242.2	1245.3	1247.2	1249.2
145°	1272.7	1272.5	1272.2	1272.0	1273.9	1278.1	1282.2	1286.3	1290.4	1292.1	1293.8
147.5°	1315.0	1314.1	1313.1	1312.2	1313.8	1317.9	1322.0	1326.1	1330.1	1331.4	1332.7
150°	1342.2	1340.5	1338.7	1337.0	1338.2	1342.0	1345.9	1349.8	1353.7	1355.1	1356.6
152.5°	1365.6	1363.6	1361.7	1359.9	1360.8	1364.4	1368.2	1371.8	1375.5	1377.0	1378.4
155°	1399.5	1397.3	1395.1	1392.9	1393.3	1396.2	1399.1	1402.0	1405.0	1406.4	1407.8
157.5°	1426.6	1424.8	1423.0	1421.1	1421.2	1423.3	1425.3	1427.4	1429.4	1431.0	1432.7
160°	1442.8	1441.3	1439.8	1438.4	1438.4	1439.8	1441.3	1442.8	1444.2	1445.6	1447.2
162.5°	1456.7	1455.3	1453.8	1452.3	1452.2	1453.5	1454.7	1456.1	1457.3	1458.9	1460.6
165°	1475.5	1474.0	1472.6	1471.1	1470.8	1471.5	1472.2	1472.9	1473.6	1475.3	1477.0
167.5°	1489.4	1488.0	1486.6	1485.1	1484.7	1485.4	1486.0	1486.7	1487.4	1489.1	1490.8
170°	1497.3	1495.8	1494.4	1492.9	1492.5	1492.9	1493.4	1493.9	1494.4	1496.1	1497.8
172.5°	1502.5	1501.1	1499.6	1498.2	1497.7	1498.2	1498.6	1499.1	1499.6	1501.3	1503.0
175°	1509.0	1507.3	1505.7	1504.0	1503.3	1503.9	1504.3	1504.9	1505.3	1507.0	1508.7
177.5°	1510.5	1509.1	1507.8	1506.4	1505.8	1506.0	1506.2	1506.4	1506.6	1508.0	1509.3
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1762.5	1768.6	1771.4	1771.4	1774.8	1773.3	1771.9
5°	1863.8	1875.0	1877.3	1888.0	1895.7	1893.3	1894.5
7.5°	1964.4	1982.5	2000.4	2008.6	2009.8	2014.6	2016.3
10°	2026.4	2041.2	2069.0	2064.8	2085.6	2097.4	2077.9
12.5°	2086.1	2106.0	2125.4	2130.7	2142.4	2146.2	2138.5
15°	2140.0	2150.7	2151.9	2148.9	2152.4	2149.5	2138.2
17.5°	2089.6	2072.3	2037.3	2020.7	2007.6	1988.2	1980.4
20°	2006.3	1955.4	1896.2	1872.6	1844.8	1790.4	1803.4
22.5°	1826.5	1768.4	1709.3	1640.2	1607.2	1555.6	1552.5
25°	1546.6	1446.6	1336.6	1259.6	1214.7	1163.2	1140.7
27.5°	1202.5	1076.6	986.4	940.8	899.2	858.4	856.8
30°	976.2	881.5	811.7	772.7	747.3	730.1	733.7
32.5°	822.9	758.0	711.0	678.5	659.7	646.8	646.6
35°	672.7	628.3	598.2	584.5	571.0	561.5	562.0
37.5°	575.7	549.0	532.3	517.2	508.7	504.1	501.5
40°	526.0	504.1	491.1	482.2	475.1	468.6	467.4
42.5°	486.7	468.6	455.6	448.6	441.9	437.4	436.1
45°	431.9	417.1	405.3	397.6	394.7	390.5	390.5
47.5°	384.2	369.7	360.4	355.6	350.5	347.8	347.7
50°	352.0	340.8	332.5	329.6	325.4	323.6	323.1
52.5°	323.2	314.8	308.9	306.8	305.1	302.8	303.2
55°	284.0	279.3	276.9	275.1	272.2	268.6	271.0
57.5°	251.0	246.9	240.6	235.0	232.3	229.8	230.8
60°	227.8	219.5	211.2	204.7	203.0	197.6	197.6
62.5°	198.4	186.8	176.6	173.0	171.2	168.7	168.3
65°	152.7	147.9	145.5	143.2	142.0	142.0	140.8
67.5°	126.5	124.6	122.0	121.5	120.2	119.8	119.5
70°	111.8	109.4	108.3	107.7	106.5	107.1	105.3
72.5°	97.6	95.8	95.5	94.0	93.3	93.4	92.0
75°	77.0	77.0	76.3	75.7	74.5	73.9	74.5
77.5°	59.2	59.3	58.2	58.1	58.0	58.1	57.5
80°	47.3	47.9	47.3	46.7	46.2	46.7	46.2
82.5°	37.4	36.6	36.5	36.3	36.2	35.8	35.8
85°	21.3	21.8	21.3	20.7	20.7	20.7	21.3
87.5°	13.1	13.4	13.6	13.6	13.7	13.8	13.5
90°	25.4	26.7	27.6	28.0	28.4	29.0	29.4
92.5°	27.2	27.8	28.3	28.5	28.9	29.2	29.4
95°	46.2	47.3	47.9	47.6	47.3	47.2	46.9
97.5°	59.8	60.8	61.4	61.7	62.1	62.3	62.6
100°	67.9	69.9	71.2	71.6	72.1	72.6	73.1
102.5°	71.5	74.0	75.6	76.2	77.0	77.7	78.3
105°	74.5	77.2	79.0	80.0	81.0	81.9	82.9
107.5°	85.0	82.3	81.4	82.4	83.4	84.4	85.3
110°	118.2	93.9	82.3	83.3	84.3	85.2	86.1



TEST NUMBER: P331837-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	216.2	127.8	83.9	84.7	85.5	86.2	87.0
115°	336.4	224.1	159.3	141.8	124.4	106.9	89.4
117.5°	664.0	636.9	594.6	537.3	479.9	422.6	365.2
120°	808.2	811.2	796.3	763.6	730.8	698.1	665.4
122.5°	856.3	858.0	855.7	849.4	843.0	836.7	830.3
125°	926.8	928.5	929.7	930.4	931.2	931.9	932.6
127.5°	992.8	995.3	996.7	996.8	996.9	997.0	997.2
130°	1034.5	1037.1	1038.3	1038.0	1037.9	1037.6	1037.3
132.5°	1074.2	1076.6	1077.5	1077.4	1077.1	1076.8	1076.7
135°	1131.8	1134.3	1135.2	1134.8	1134.3	1133.8	1133.4
137.5°	1185.2	1187.6	1188.3	1187.5	1186.7	1185.9	1185.0
140°	1219.5	1221.7	1222.2	1220.9	1219.8	1218.5	1217.4
142.5°	1251.2	1253.2	1253.6	1252.4	1251.2	1249.9	1248.8
145°	1295.5	1297.2	1297.4	1296.2	1295.0	1293.8	1292.6
147.5°	1333.9	1335.2	1335.2	1334.3	1333.2	1332.2	1331.2
150°	1358.1	1359.5	1359.6	1358.4	1357.2	1355.9	1354.8
152.5°	1379.8	1381.3	1381.3	1379.7	1378.0	1376.4	1374.8
155°	1409.3	1410.8	1410.5	1408.5	1406.7	1404.7	1402.8
157.5°	1434.3	1436.0	1435.8	1434.0	1432.1	1430.2	1428.3
160°	1448.6	1450.0	1449.9	1448.2	1446.5	1444.8	1443.1
162.5°	1462.2	1463.9	1463.7	1461.6	1459.5	1457.4	1455.4
165°	1478.7	1480.4	1480.4	1478.7	1477.0	1475.3	1473.6
167.5°	1492.5	1494.2	1494.0	1491.7	1489.6	1487.4	1485.2
170°	1499.5	1501.2	1500.9	1498.8	1496.6	1494.4	1492.2
172.5°	1504.7	1506.4	1506.2	1504.0	1501.8	1499.6	1497.4
175°	1510.4	1512.1	1511.7	1509.3	1506.9	1504.4	1502.0
177.5°	1510.6	1512.1	1511.8	1510.1	1508.3	1506.6	1504.9
180°	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4	1507.4

(END OF REPORT)