

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331838-940

Luminaire Tested: **S122RDIW-S865D1240U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331838-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D1240U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6779.4 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	82	73	66	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	65	57	52	68	60	53	48	50	46	42	42	38	35	33	31	29	25
5	69	58	50	45	63	54	47	42	45	40	37	38	34	31	30	28	26	23
6	64	52	45	39	58	49	42	37	41	36	32	34	31	28	28	25	23	20
7	59	48	40	35	54	44	37	33	38	33	29	32	28	25	26	23	21	18
8	55	43	36	31	51	40	34	29	35	29	26	29	25	22	24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27493	27493	27493	27493
5°	30705	27665	24530	27665
10°	34067	27471	21263	27471
15°	35741	27067	16754	27067
20°	30986	26472	14496	26472
25°	20322	25655	12944	25655
30°	13679	24664	11714	24664
35°	11077	23416	10565	23416
40°	9851	22059	9778	22059
45°	8917	20466	8727	20466
50°	8116	18889	8083	18889
55°	7628	17140	7527	17140
60°	6381	15532	6307	15532
65°	5379	14105	6101	14105
70°	4971	12595	5755	12595
75°	4648	10967	5315	10967
80°	4296	9019	4733	9019
85°	3946	7114	4168	7114



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.4	2.4
10°-20°	449.8	6.6
20°-30°	579.6	8.5
30°-40°	550.8	8.1
40°-50°	471.8	7.0
50°-60°	359.3	5.3
60°-70°	227.1	3.4
70°-80°	113.4	1.7
80°-90°	35.0	0.5
90°-100°	86.8	1.3
100°-110°	269.6	4.0
110°-120°	460.9	6.8
120°-130°	606.1	8.9
130°-140°	680.3	10.0
140°-150°	667.1	9.8
150°-160°	559.5	8.3
160°-170°	371.1	5.5
170°-180°	129.7	1.9
0°-30°	1190.8	17.6
0°-40°	1741.6	25.7
0°-60°	2572.7	37.9
0°-90°	2948.3	43.5
90°-120°	817.4	12.1
90°-150°	2770.9	40.9
90°-180°	3831.0	56.5
0°-180°	6779.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1703	1703	1703	1703	1703	
5°	1894	1707	1514	1707	1894	187
15°	2138	1619	1002	1619	2138	577
25°	1141	1440	727	1440	1141	541
35°	562	1188	536	1188	562	360
45°	390	896	382	896	390	302
55°	271	609	267	609	271	238
65°	141	369	160	369	141	143
75°	74	176	85	176	74	79
85°	21	38	22	38	21	24
90°	39	1	39	1	39	18
95°	72	60	72	60	72	80
105°	257	249	257	249	257	270
115°	462	462	462	462	462	457
125°	675	673	675	673	675	602
135°	881	871	881	871	881	678
145°	1068	1057	1068	1057	1068	667
155°	1218	1208	1218	1208	1218	560
165°	1316	1315	1316	1315	1316	371
175°	1363	1368	1363	1368	1363	130
180°	1370	1370	1370	1370	1370	



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1771.9	1773.3	1774.8	1771.4	1771.4	1768.6	1762.5	1757.7	1744.5	1742.6	1742.6
5°	1894.5	1893.3	1895.7	1888.0	1877.3	1875.0	1863.8	1849.0	1833.5	1816.4	1812.8
7.5°	2016.3	2014.6	2009.8	2008.6	2000.4	1982.5	1964.4	1945.2	1919.6	1894.6	1882.0
10°	2077.9	2097.4	2085.6	2064.8	2069.0	2041.2	2026.4	2001.0	1979.7	1942.4	1934.1
12.5°	2138.5	2146.2	2142.4	2130.7	2125.4	2106.0	2086.1	2064.0	2024.6	1991.2	1962.0
15°	2138.2	2149.5	2152.4	2148.9	2151.9	2150.7	2140.0	2121.6	2087.4	2050.7	2018.7
17.5°	1980.4	1988.2	2007.6	2020.7	2037.3	2072.3	2089.6	2096.3	2091.2	2070.3	2047.8
20°	1803.4	1790.4	1844.8	1872.6	1896.2	1955.4	2006.3	2025.9	2057.2	2056.6	2050.7
22.5°	1552.5	1555.6	1607.2	1640.2	1709.3	1768.4	1826.5	1900.0	1960.6	2000.7	2024.2
25°	1140.7	1163.2	1214.7	1259.6	1336.6	1446.6	1546.6	1662.6	1772.0	1858.4	1940.6
27.5°	856.8	858.4	899.2	940.8	986.4	1076.6	1202.5	1341.0	1497.0	1625.8	1773.9
30°	733.7	730.1	747.3	772.7	811.7	881.5	976.2	1112.3	1267.9	1462.0	1634.8
32.5°	646.6	646.8	659.7	678.5	711.0	758.0	822.9	933.4	1080.5	1271.2	1473.8
35°	562.0	561.5	571.0	584.5	598.2	628.3	672.7	730.7	831.9	1010.0	1217.0
37.5°	501.5	504.1	508.7	517.2	532.3	549.0	575.7	614.7	686.7	792.0	966.1
40°	467.4	468.6	475.1	482.2	491.1	504.1	526.0	557.3	610.0	694.0	821.2
42.5°	436.1	437.4	441.9	448.6	455.6	468.6	486.7	513.8	556.5	622.1	727.0
45°	390.5	390.5	394.7	397.6	405.3	417.1	431.9	454.4	483.9	532.5	602.4
47.5°	347.7	347.8	350.5	355.6	360.4	369.7	384.2	402.6	424.1	461.6	521.3
50°	323.1	323.6	325.4	329.6	332.5	340.8	352.0	368.0	390.5	419.5	469.2
52.5°	303.2	302.8	305.1	306.8	308.9	314.8	323.2	337.2	357.4	382.5	423.7
55°	271.0	268.6	272.2	275.1	276.9	279.3	284.0	292.8	310.0	331.4	362.1
57.5°	230.8	229.8	232.3	235.0	240.6	246.9	251.0	256.6	265.6	280.8	311.3
60°	197.6	197.6	203.0	204.7	211.2	219.5	227.8	232.6	241.4	251.5	273.9
62.5°	168.3	168.7	171.2	173.0	176.6	186.8	198.4	208.8	217.2	226.9	241.7
65°	140.8	142.0	142.0	143.2	145.5	147.9	152.7	161.0	175.8	189.3	200.5
67.5°	119.5	119.8	120.2	121.5	122.0	124.6	126.5	130.2	133.6	146.5	160.4
70°	105.3	107.1	106.5	107.7	108.3	109.4	111.8	113.6	119.0	121.9	130.2
72.5°	92.0	93.4	93.3	94.0	95.5	95.8	97.6	99.4	102.8	105.3	109.8
75°	74.5	73.9	74.5	75.7	76.3	77.0	77.0	79.3	81.1	83.5	86.4
77.5°	57.5	58.1	58.0	58.1	58.2	59.3	59.2	60.2	62.0	63.2	64.6
80°	46.2	46.7	46.2	46.7	47.3	47.9	47.3	47.9	49.7	50.9	50.9
82.5°	35.8	35.8	36.2	36.3	36.5	36.6	37.4	37.5	38.8	38.6	39.1
85°	21.3	20.7	20.7	20.7	21.3	21.8	21.3	21.3	21.8	21.8	21.8
87.5°	15.4	15.9	15.8	15.8	15.7	15.7	15.9	16.4	16.1	16.6	15.0
90°	39.3	39.1	38.8	38.5	38.3	38.4	39.0	39.4	39.9	40.5	34.8
92.5°	37.5	37.5	37.4	37.3	37.3	37.2	37.1	37.0	36.8	36.7	35.4
95°	71.7	72.2	72.7	73.2	73.7	74.0	74.0	74.0	74.0	74.0	73.5
97.5°	124.2	124.2	124.3	124.3	124.4	124.4	124.4	124.4	124.4	124.4	123.4
100°	158.4	158.6	158.9	159.2	159.4	159.5	159.5	159.5	159.5	159.5	158.8
102.5°	197.2	197.5	197.8	198.0	198.3	198.3	198.1	197.9	197.7	197.5	196.5
105°	256.7	256.7	256.7	256.7	256.7	256.5	255.9	255.4	254.9	254.4	253.9
107.5°	312.6	313.8	315.0	316.2	317.4	317.9	317.6	317.4	317.3	317.0	317.0
110°	356.1	356.9	357.7	358.5	359.2	359.6	359.6	359.6	359.6	359.6	359.6



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	397.7	398.3	398.9	399.4	400.0	400.6	401.2	401.8	402.4	403.1	403.2
115°	462.5	463.2	464.0	464.8	465.6	466.1	466.4	466.6	466.9	467.1	467.6
117.5°	524.2	525.0	525.8	526.6	527.4	528.0	528.6	529.2	529.9	530.5	531.9
120°	567.8	568.5	569.3	570.0	570.8	571.1	571.1	571.1	571.1	571.1	573.2
122.5°	610.3	610.8	611.4	612.0	612.5	613.1	613.8	614.4	614.9	615.5	617.0
125°	675.2	675.5	675.7	676.0	676.3	676.8	677.5	678.3	679.1	679.8	680.6
127.5°	734.4	735.3	736.1	736.9	737.7	738.6	739.5	740.5	741.4	742.3	743.2
130°	776.9	778.0	779.1	780.1	781.1	781.9	782.4	782.9	783.4	783.9	784.4
132.5°	817.7	818.5	819.3	820.2	821.0	822.0	823.0	824.2	825.4	826.4	826.3
135°	881.0	881.8	882.6	883.3	884.1	884.7	884.9	885.2	885.4	885.6	885.2
137.5°	938.4	939.4	940.5	941.5	942.5	943.2	943.3	943.5	943.8	944.0	943.3
140°	978.2	979.2	980.3	981.2	982.3	982.8	982.8	982.8	982.8	982.8	981.5
142.5°	1014.2	1015.3	1016.3	1017.4	1018.3	1018.8	1018.6	1018.3	1018.2	1018.0	1017.1
145°	1068.4	1069.4	1070.4	1071.5	1072.5	1072.8	1072.6	1072.4	1072.1	1071.8	1070.3
147.5°	1116.7	1117.7	1118.7	1119.6	1120.6	1120.8	1120.3	1119.6	1119.1	1118.6	1117.5
150°	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2	1150.5	1149.7	1148.9	1148.2	1147.1
152.5°	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6	1180.6	1179.7	1178.8	1177.8	1176.5
155°	1217.5	1218.3	1219.1	1219.9	1220.6	1220.3	1219.1	1217.8	1216.5	1215.2	1214.4
157.5°	1251.7	1252.9	1254.2	1255.4	1256.7	1256.4	1254.6	1252.9	1251.2	1249.5	1248.9
160°	1273.0	1274.1	1275.1	1276.1	1277.1	1276.8	1275.3	1273.8	1272.2	1270.7	1270.4
162.5°	1291.6	1292.7	1294.0	1295.2	1296.5	1296.2	1294.4	1292.7	1290.9	1289.2	1289.0
165°	1315.8	1317.1	1318.4	1319.6	1320.9	1320.7	1318.8	1317.1	1315.3	1313.5	1313.5
167.5°	1335.7	1337.0	1338.4	1339.7	1341.0	1340.8	1339.0	1337.2	1335.4	1333.6	1333.6
170°	1345.9	1347.4	1349.0	1350.5	1352.0	1351.9	1350.1	1348.3	1346.5	1344.7	1345.0
172.5°	1354.2	1355.8	1357.3	1358.8	1360.3	1360.2	1358.4	1356.6	1354.9	1353.0	1353.3
175°	1363.2	1364.8	1366.3	1367.8	1369.4	1369.2	1367.4	1365.7	1363.9	1362.0	1362.5
177.5°	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3	1371.1	1369.8	1368.6	1367.3	1367.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1743.5	1739.7	1736.4	1727.9	1723.6	1714.1	1712.7	1712.3	1700.0	1688.1	1684.8
5°	1803.4	1793.9	1779.7	1763.2	1746.0	1728.2	1716.4	1706.9	1683.3	1660.8	1647.8
7.5°	1863.8	1843.3	1818.9	1787.5	1761.4	1732.1	1710.2	1690.7	1657.2	1625.0	1603.3
10°	1908.7	1875.5	1843.0	1799.8	1766.1	1733.0	1702.2	1675.6	1637.7	1595.1	1565.0
12.5°	1936.6	1900.1	1855.3	1813.1	1769.4	1727.2	1686.1	1651.9	1607.4	1563.4	1527.5
15°	1974.3	1935.3	1880.9	1820.5	1764.3	1709.3	1662.0	1619.3	1561.4	1508.7	1464.9
17.5°	2005.3	1951.5	1893.1	1823.3	1758.2	1688.3	1627.3	1572.9	1508.3	1444.8	1393.2
20°	2015.2	1961.9	1894.5	1824.7	1747.8	1665.5	1599.8	1540.7	1471.4	1402.2	1343.1
22.5°	2009.0	1967.6	1892.6	1809.0	1730.3	1644.2	1570.0	1501.4	1424.6	1354.0	1285.3
25°	1967.3	1953.0	1882.0	1790.9	1701.0	1601.1	1515.2	1440.1	1352.5	1276.8	1202.2
27.5°	1869.9	1900.5	1856.5	1759.4	1659.5	1552.3	1455.8	1370.3	1279.4	1194.2	1119.9
30°	1776.2	1846.6	1827.7	1737.7	1625.9	1520.5	1412.3	1322.9	1225.9	1138.4	1065.0
32.5°	1647.9	1764.2	1782.7	1707.4	1591.8	1476.0	1362.6	1273.7	1172.4	1080.1	1008.6
35°	1443.7	1617.6	1697.5	1649.6	1533.6	1408.7	1291.6	1188.0	1086.3	995.1	924.2
37.5°	1200.0	1436.9	1570.0	1573.4	1467.0	1337.1	1209.6	1106.8	1002.6	913.2	836.3
40°	1041.9	1298.7	1472.0	1510.5	1420.6	1280.3	1151.4	1046.6	944.9	857.3	769.2
42.5°	899.9	1155.7	1368.9	1435.7	1364.2	1224.9	1095.6	986.1	887.2	804.3	714.3
45°	727.7	951.4	1186.2	1305.8	1266.1	1137.2	1000.5	896.3	803.4	731.9	645.5
47.5°	613.9	771.5	998.8	1160.5	1159.8	1042.1	907.6	807.9	721.7	654.6	584.7
50°	549.0	686.3	878.6	1062.0	1077.4	978.6	850.8	752.0	671.5	601.1	544.9
52.5°	490.8	604.0	776.9	952.7	996.5	910.9	786.9	695.7	617.6	552.9	504.7
55°	414.7	502.3	633.6	798.2	864.4	804.1	694.0	608.9	545.5	491.1	449.7
57.5°	350.9	416.5	521.9	654.3	731.6	693.6	602.8	533.6	479.4	430.2	397.4
60°	310.6	364.4	453.8	564.5	649.6	623.0	545.5	481.0	434.9	392.3	361.5
62.5°	272.8	319.1	395.6	485.4	563.5	552.5	489.2	435.1	394.7	355.8	329.8
65°	219.5	253.2	313.0	383.4	446.1	451.5	405.9	369.2	333.1	302.4	279.3
67.5°	174.8	196.8	238.9	298.2	345.2	361.9	334.1	306.1	277.5	253.7	233.7
70°	147.3	165.1	195.8	243.8	287.0	304.7	288.7	266.8	242.0	222.5	205.3
72.5°	119.4	136.7	159.3	194.6	231.6	250.7	245.2	229.4	209.3	193.1	176.9
75°	90.0	95.2	110.7	134.3	163.3	179.9	184.0	175.8	159.7	147.3	137.9
77.5°	66.5	69.7	77.0	89.4	108.4	123.1	129.2	128.2	117.3	110.0	101.2
80°	53.2	55.0	58.6	63.9	78.1	92.9	97.0	97.0	89.3	86.4	77.5
82.5°	40.5	41.7	43.9	46.8	53.5	66.3	71.0	72.0	67.1	63.2	56.2
85°	23.1	22.5	23.6	25.4	26.7	30.1	37.3	38.4	37.3	32.5	30.8
87.5°	13.9	13.2	12.1	10.7	10.6	10.4	12.2	14.0	12.7	11.9	11.6
90°	29.2	23.5	17.8	13.5	10.4	7.3	4.3	1.2	4.3	7.3	10.4
92.5°	34.1	32.7	31.4	29.6	27.4	25.1	22.8	20.6	22.8	25.1	27.4
95°	72.9	72.5	72.0	70.4	67.9	65.3	62.7	60.1	62.7	65.3	67.9
97.5°	122.4	121.5	120.5	118.9	116.6	114.4	112.1	109.9	112.1	114.4	116.6
100°	158.0	157.2	156.5	155.1	153.0	151.0	148.9	146.9	148.9	151.0	153.0
102.5°	195.6	194.6	193.6	192.3	190.6	189.0	187.3	185.7	187.3	189.0	190.6
105°	253.3	252.8	252.4	251.6	250.9	250.1	249.3	248.6	249.3	250.1	250.9
107.5°	317.0	317.0	317.0	316.5	315.3	314.2	313.1	311.9	313.1	314.2	315.3
110°	359.6	359.6	359.6	358.8	357.3	355.7	354.2	352.7	354.2	355.7	357.3



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	403.5	403.7	403.9	403.2	401.7	400.1	398.6	397.1	398.6	400.1	401.7
115°	468.1	468.7	469.1	468.7	467.1	465.6	464.0	462.5	464.0	465.6	467.1
117.5°	533.3	534.8	536.3	535.9	533.9	531.8	529.8	527.7	529.8	531.8	533.9
120°	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1	573.2	575.3	577.4
122.5°	618.5	619.9	621.3	620.8	618.3	615.9	613.4	610.9	613.4	615.9	618.3
125°	681.4	682.2	683.0	682.2	679.8	677.5	675.2	672.9	675.2	677.5	679.8
127.5°	744.1	745.1	746.0	745.0	742.1	739.1	736.2	733.3	736.2	739.1	742.1
130°	785.0	785.5	786.0	784.5	781.2	777.9	774.5	771.2	774.5	777.9	781.2
132.5°	826.3	826.2	826.1	824.7	821.9	819.2	816.5	813.8	816.5	819.2	821.9
135°	884.7	884.1	883.6	882.0	879.1	876.3	873.4	870.7	873.4	876.3	879.1
137.5°	942.6	941.9	941.3	939.8	937.5	935.1	932.8	930.5	932.8	935.1	937.5
140°	980.3	978.9	977.7	975.9	973.6	971.3	968.9	966.6	968.9	971.3	973.6
142.5°	1016.2	1015.3	1014.4	1012.9	1010.6	1008.3	1005.9	1003.6	1005.9	1008.3	1010.6
145°	1068.7	1067.2	1065.7	1064.0	1062.2	1060.4	1058.6	1056.8	1058.6	1060.4	1062.2
147.5°	1116.5	1115.4	1114.5	1112.9	1110.7	1108.5	1106.3	1104.2	1106.3	1108.5	1110.7
150°	1146.1	1145.0	1144.1	1142.7	1141.2	1139.7	1138.1	1136.6	1138.1	1139.7	1141.2
152.5°	1175.3	1174.0	1172.8	1171.4	1169.8	1168.3	1166.8	1165.3	1166.8	1168.3	1169.8
155°	1213.6	1212.9	1212.1	1211.4	1210.6	1209.8	1209.1	1208.3	1209.1	1209.8	1210.6
157.5°	1248.5	1248.0	1247.6	1247.1	1246.6	1246.1	1245.5	1245.0	1245.5	1246.1	1246.6
160°	1270.2	1269.9	1269.7	1269.3	1268.8	1268.3	1267.7	1267.2	1267.7	1268.3	1268.8
162.5°	1288.7	1288.4	1288.2	1288.0	1287.9	1287.8	1287.7	1287.5	1287.7	1287.8	1287.9
165°	1313.5	1313.5	1313.5	1313.6	1313.8	1314.1	1314.4	1314.6	1314.4	1314.1	1313.8
167.5°	1333.7	1333.7	1333.8	1334.2	1335.0	1335.8	1336.5	1337.3	1336.5	1335.8	1335.0
170°	1345.2	1345.5	1345.8	1346.2	1347.0	1347.8	1348.5	1349.3	1348.5	1347.8	1347.0
172.5°	1353.5	1353.8	1354.1	1354.6	1355.3	1356.1	1356.9	1357.6	1356.9	1356.1	1355.3
175°	1363.1	1363.6	1364.1	1364.8	1365.5	1366.3	1367.1	1367.8	1367.1	1366.3	1365.5
177.5°	1368.2	1368.6	1369.0	1369.5	1370.1	1370.7	1371.4	1372.0	1371.4	1370.7	1370.1
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1678.6	1675.3	1669.2	1659.7	1654.0	1644.1	1637.4	1641.3	1642.2	1641.3	1640.3
5°	1633.5	1621.1	1604.0	1587.4	1572.0	1555.5	1546.0	1541.9	1533.6	1528.8	1526.5
7.5°	1579.0	1557.6	1533.3	1504.5	1480.0	1454.3	1441.2	1434.7	1417.7	1408.5	1400.4
10°	1538.3	1504.6	1480.3	1442.4	1419.4	1385.6	1362.6	1363.2	1340.1	1327.0	1317.6
12.5°	1493.3	1456.3	1415.9	1381.9	1349.8	1322.7	1294.9	1283.6	1259.2	1246.6	1221.0
15°	1418.8	1375.6	1333.0	1286.8	1254.3	1212.3	1172.1	1122.9	1083.3	1049.0	1039.6
17.5°	1337.4	1283.9	1241.2	1187.0	1131.2	1060.6	1014.0	985.4	961.5	943.4	930.0
20°	1281.6	1227.1	1181.5	1099.9	1024.8	976.9	942.5	920.6	895.8	876.3	865.6
22.5°	1222.8	1166.0	1103.9	1012.8	954.2	915.8	885.2	860.1	843.2	828.0	818.2
25°	1139.5	1077.4	975.1	912.3	865.0	824.7	803.4	788.1	770.3	749.7	740.1
27.5°	1051.5	952.7	879.2	832.6	787.4	761.3	742.1	719.1	703.2	693.9	684.0
30°	985.7	886.9	829.5	778.6	746.6	717.6	695.2	682.2	666.8	650.9	644.4
32.5°	912.3	833.4	778.4	736.0	703.6	678.9	661.1	640.1	628.9	619.1	605.5
35°	821.2	761.4	711.1	676.9	646.1	626.0	605.3	592.8	572.7	564.5	559.1
37.5°	744.0	692.2	654.7	618.5	594.1	571.9	559.2	539.5	530.7	519.2	508.0
40°	700.5	649.6	613.6	584.0	556.8	540.2	524.2	508.3	495.3	489.9	476.3
42.5°	656.0	614.7	578.5	546.1	527.9	510.3	490.2	478.4	464.9	456.3	447.9
45°	594.6	557.9	527.2	500.5	480.5	462.1	449.1	429.5	421.9	404.7	397.6
47.5°	540.6	506.6	477.2	451.9	432.3	420.4	401.3	386.0	373.7	363.2	354.0
50°	502.3	473.9	445.5	423.0	405.3	388.2	368.6	360.9	342.0	336.6	331.4
52.5°	467.3	440.3	414.3	392.3	374.5	357.8	340.6	330.6	317.8	312.5	308.6
55°	418.3	392.3	367.4	347.9	330.1	313.0	302.4	289.9	284.0	279.8	275.1
57.5°	369.1	345.6	326.6	306.8	289.0	275.4	263.1	255.6	249.4	244.0	238.4
60°	337.9	315.3	298.2	279.8	261.5	250.3	240.8	231.9	224.8	216.5	214.2
62.5°	304.7	285.1	269.3	251.5	235.5	225.2	216.2	207.8	199.3	187.2	183.9
65°	259.1	243.8	227.2	212.4	198.2	188.2	175.1	165.7	162.1	161.0	160.3
67.5°	217.9	203.4	189.2	174.1	161.1	151.9	145.2	143.7	141.2	140.5	138.9
70°	190.5	176.9	162.7	148.5	136.1	134.3	132.0	129.6	126.6	125.5	124.2
72.5°	165.9	151.9	137.6	126.3	120.9	118.7	116.3	114.0	111.9	110.8	110.0
75°	127.2	114.2	104.7	100.6	97.6	95.9	92.3	90.5	89.3	87.6	86.9
77.5°	91.6	84.3	79.9	77.3	74.2	72.3	70.3	68.5	67.2	66.9	65.9
80°	69.8	66.3	63.3	59.7	58.6	56.2	55.6	53.9	54.4	52.7	52.7
82.5°	54.2	49.7	47.2	45.6	44.4	42.4	41.9	41.0	41.2	39.9	39.9
85°	27.8	26.7	25.4	24.3	24.3	22.5	23.1	22.5	22.5	21.3	20.7
87.5°	11.7	12.1	12.3	13.4	14.5	15.2	15.1	14.5	14.4	14.3	13.8
90°	13.5	17.8	23.5	29.2	34.8	40.5	39.9	39.4	39.0	38.4	38.3
92.5°	29.6	31.4	32.7	34.1	35.4	36.7	36.8	37.0	37.1	37.2	37.3
95°	70.4	72.0	72.5	72.9	73.5	74.0	74.0	74.0	74.0	74.0	73.7
97.5°	118.9	120.5	121.5	122.4	123.4	124.4	124.4	124.4	124.4	124.4	124.4
100°	155.1	156.5	157.2	158.0	158.8	159.5	159.5	159.5	159.5	159.5	159.4
102.5°	192.3	193.6	194.6	195.6	196.5	197.5	197.7	197.9	198.1	198.3	198.3
105°	251.6	252.4	252.8	253.3	253.9	254.4	254.9	255.4	255.9	256.5	256.7
107.5°	316.5	317.0	317.0	317.0	317.0	317.0	317.3	317.4	317.6	317.9	317.4
110°	358.8	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.2



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	403.2	403.9	403.7	403.5	403.2	403.1	402.4	401.8	401.2	400.6	400.0
115°	468.7	469.1	468.7	468.1	467.6	467.1	466.9	466.6	466.4	466.1	465.6
117.5°	535.9	536.3	534.8	533.3	531.9	530.5	529.9	529.2	528.6	528.0	527.4
120°	579.4	579.4	577.4	575.3	573.2	571.1	571.1	571.1	571.1	571.1	570.8
122.5°	620.8	621.3	619.9	618.5	617.0	615.5	614.9	614.4	613.8	613.1	612.5
125°	682.2	683.0	682.2	681.4	680.6	679.8	679.1	678.3	677.5	676.8	676.3
127.5°	745.0	746.0	745.1	744.1	743.2	742.3	741.4	740.5	739.5	738.6	737.7
130°	784.5	786.0	785.5	785.0	784.4	783.9	783.4	782.9	782.4	781.9	781.1
132.5°	824.7	826.1	826.2	826.3	826.3	826.4	825.4	824.2	823.0	822.0	821.0
135°	882.0	883.6	884.1	884.7	885.2	885.6	885.4	885.2	884.9	884.7	884.1
137.5°	939.8	941.3	941.9	942.6	943.3	944.0	943.8	943.5	943.3	943.2	942.5
140°	975.9	977.7	978.9	980.3	981.5	982.8	982.8	982.8	982.8	982.8	982.3
142.5°	1012.9	1014.4	1015.3	1016.2	1017.1	1018.0	1018.2	1018.3	1018.6	1018.8	1018.3
145°	1064.0	1065.7	1067.2	1068.7	1070.3	1071.8	1072.1	1072.4	1072.6	1072.8	1072.5
147.5°	1112.9	1114.5	1115.4	1116.5	1117.5	1118.6	1119.1	1119.6	1120.3	1120.8	1120.6
150°	1142.7	1144.1	1145.0	1146.1	1147.1	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2
152.5°	1171.4	1172.8	1174.0	1175.3	1176.5	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6
155°	1211.4	1212.1	1212.9	1213.6	1214.4	1215.2	1216.5	1217.8	1219.1	1220.3	1220.6
157.5°	1247.1	1247.6	1248.0	1248.5	1248.9	1249.5	1251.2	1252.9	1254.6	1256.4	1256.7
160°	1269.3	1269.7	1269.9	1270.2	1270.4	1270.7	1272.2	1273.8	1275.3	1276.8	1277.1
162.5°	1288.0	1288.2	1288.4	1288.7	1289.0	1289.2	1290.9	1292.7	1294.4	1296.2	1296.5
165°	1313.6	1313.5	1313.5	1313.5	1313.5	1313.5	1315.3	1317.1	1318.8	1320.7	1320.9
167.5°	1334.2	1333.8	1333.7	1333.7	1333.6	1333.6	1335.4	1337.2	1339.0	1340.8	1341.0
170°	1346.2	1345.8	1345.5	1345.2	1345.0	1344.7	1346.5	1348.3	1350.1	1351.9	1352.0
172.5°	1354.6	1354.1	1353.8	1353.5	1353.3	1353.0	1354.9	1356.6	1358.4	1360.2	1360.3
175°	1364.8	1364.1	1363.6	1363.1	1362.5	1362.0	1363.9	1365.7	1367.4	1369.2	1369.4
177.5°	1369.5	1369.0	1368.6	1368.2	1367.8	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1635.1	1636.0	1634.6	1635.6	1634.6	1636.0	1635.1	1640.3	1641.3	1642.2	1641.3
5°	1523.5	1516.4	1515.2	1513.5	1515.2	1516.4	1523.5	1526.5	1528.8	1533.6	1541.9
7.5°	1390.3	1389.2	1386.3	1382.2	1386.3	1389.2	1390.3	1400.4	1408.5	1417.7	1434.7
10°	1304.6	1301.6	1301.1	1296.9	1301.1	1301.6	1304.6	1317.6	1327.0	1340.1	1363.2
12.5°	1204.3	1185.2	1183.2	1172.9	1183.2	1185.2	1204.3	1221.0	1246.6	1259.2	1283.6
15°	1025.4	1021.8	1010.0	1002.3	1010.0	1021.8	1025.4	1039.6	1049.0	1083.3	1122.9
17.5°	923.1	911.5	907.9	906.2	907.9	911.5	923.1	930.0	943.4	961.5	985.4
20°	857.3	846.7	844.9	843.7	844.9	846.7	857.3	865.6	876.3	895.8	920.6
22.5°	811.9	800.8	796.1	792.6	796.1	800.8	811.9	818.2	828.0	843.2	860.1
25°	734.2	730.1	727.7	726.6	727.7	730.1	734.2	740.1	749.7	770.3	788.1
27.5°	673.5	664.4	662.6	659.6	662.6	664.4	673.5	684.0	693.9	703.2	719.1
30°	639.0	636.1	631.9	628.3	631.9	636.1	639.0	644.4	650.9	666.8	682.2
32.5°	598.2	595.8	592.1	590.5	592.1	595.8	598.2	605.5	619.1	628.9	640.1
35°	553.2	544.9	541.4	536.0	541.4	544.9	553.2	559.1	564.5	572.7	592.8
37.5°	505.5	501.1	496.1	497.9	496.1	501.1	505.5	508.0	519.2	530.7	539.5
40°	468.6	465.7	464.5	463.9	464.5	465.7	468.6	476.3	489.9	495.3	508.3
42.5°	439.3	431.1	428.0	427.8	428.0	431.1	439.3	447.9	456.3	464.9	478.4
45°	394.7	386.9	381.7	382.2	381.7	386.9	394.7	397.6	404.7	421.9	429.5
47.5°	348.9	348.7	345.4	346.5	345.4	348.7	348.9	354.0	363.2	373.7	386.0
50°	327.2	323.6	321.3	321.8	321.3	323.6	327.2	331.4	336.6	342.0	360.9
52.5°	306.4	303.3	301.4	303.9	301.4	303.3	306.4	308.6	312.5	317.8	330.6
55°	272.2	268.6	268.0	267.4	268.0	268.6	272.2	275.1	279.8	284.0	289.9
57.5°	234.0	231.6	228.0	226.5	228.0	231.6	234.0	238.4	244.0	249.4	255.6
60°	206.5	201.8	195.8	195.3	195.8	201.8	206.5	214.2	216.5	224.8	231.9
62.5°	181.4	180.5	179.2	179.1	179.2	180.5	181.4	183.9	187.2	199.3	207.8
65°	159.2	158.5	159.2	159.7	159.2	158.5	159.2	160.3	161.0	162.1	165.7
67.5°	138.7	137.6	136.5	137.1	136.5	137.6	138.7	138.9	140.5	141.2	143.7
70°	123.1	122.4	121.9	121.9	121.9	122.4	123.1	124.2	125.5	126.6	129.6
72.5°	107.9	107.8	107.2	106.7	107.2	107.8	107.9	110.0	110.8	111.9	114.0
75°	86.4	85.2	85.2	85.2	85.2	85.2	86.4	86.9	87.6	89.3	90.5
77.5°	65.8	65.2	64.6	64.1	64.6	65.2	65.8	65.9	66.9	67.2	68.5
80°	52.1	51.5	50.9	50.9	50.9	51.5	52.1	52.7	52.7	54.4	53.9
82.5°	39.8	39.1	39.1	38.6	39.1	39.1	39.8	39.9	39.9	41.2	41.0
85°	21.3	21.8	21.3	22.5	21.3	21.8	21.3	20.7	21.3	22.5	22.5
87.5°	13.8	13.5	14.0	13.6	14.0	13.5	13.8	13.8	14.3	14.4	14.5
90°	38.5	38.8	39.1	39.3	39.1	38.8	38.5	38.3	38.4	39.0	39.4
92.5°	37.3	37.4	37.5	37.5	37.5	37.4	37.3	37.3	37.2	37.1	37.0
95°	73.2	72.7	72.2	71.7	72.2	72.7	73.2	73.7	74.0	74.0	74.0
97.5°	124.3	124.3	124.2	124.2	124.2	124.3	124.3	124.4	124.4	124.4	124.4
100°	159.2	158.9	158.6	158.4	158.6	158.9	159.2	159.4	159.5	159.5	159.5
102.5°	198.0	197.8	197.5	197.2	197.5	197.8	198.0	198.3	198.3	198.1	197.9
105°	256.7	256.7	256.7	256.7	256.7	256.7	256.7	256.7	256.5	255.9	255.4
107.5°	316.2	315.0	313.8	312.6	313.8	315.0	316.2	317.4	317.9	317.6	317.4
110°	358.5	357.7	356.9	356.1	356.9	357.7	358.5	359.2	359.6	359.6	359.6



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	399.4	398.9	398.3	397.7	398.3	398.9	399.4	400.0	400.6	401.2	401.8
115°	464.8	464.0	463.2	462.5	463.2	464.0	464.8	465.6	466.1	466.4	466.6
117.5°	526.6	525.8	525.0	524.2	525.0	525.8	526.6	527.4	528.0	528.6	529.2
120°	570.0	569.3	568.5	567.8	568.5	569.3	570.0	570.8	571.1	571.1	571.1
122.5°	612.0	611.4	610.8	610.3	610.8	611.4	612.0	612.5	613.1	613.8	614.4
125°	676.0	675.7	675.5	675.2	675.5	675.7	676.0	676.3	676.8	677.5	678.3
127.5°	736.9	736.1	735.3	734.4	735.3	736.1	736.9	737.7	738.6	739.5	740.5
130°	780.1	779.1	778.0	776.9	778.0	779.1	780.1	781.1	781.9	782.4	782.9
132.5°	820.2	819.3	818.5	817.7	818.5	819.3	820.2	821.0	822.0	823.0	824.2
135°	883.3	882.6	881.8	881.0	881.8	882.6	883.3	884.1	884.7	884.9	885.2
137.5°	941.5	940.5	939.4	938.4	939.4	940.5	941.5	942.5	943.2	943.3	943.5
140°	981.2	980.3	979.2	978.2	979.2	980.3	981.2	982.3	982.8	982.8	982.8
142.5°	1017.4	1016.3	1015.3	1014.2	1015.3	1016.3	1017.4	1018.3	1018.8	1018.6	1018.3
145°	1071.5	1070.4	1069.4	1068.4	1069.4	1070.4	1071.5	1072.5	1072.8	1072.6	1072.4
147.5°	1119.6	1118.7	1117.7	1116.7	1117.7	1118.7	1119.6	1120.6	1120.8	1120.3	1119.6
150°	1150.5	1149.7	1148.9	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2	1150.5	1149.7
152.5°	1180.6	1179.7	1178.8	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6	1180.6	1179.7
155°	1219.9	1219.1	1218.3	1217.5	1218.3	1219.1	1219.9	1220.6	1220.3	1219.1	1217.8
157.5°	1255.4	1254.2	1252.9	1251.7	1252.9	1254.2	1255.4	1256.7	1256.4	1254.6	1252.9
160°	1276.1	1275.1	1274.1	1273.0	1274.1	1275.1	1276.1	1277.1	1276.8	1275.3	1273.8
162.5°	1295.2	1294.0	1292.7	1291.6	1292.7	1294.0	1295.2	1296.5	1296.2	1294.4	1292.7
165°	1319.6	1318.4	1317.1	1315.8	1317.1	1318.4	1319.6	1320.9	1320.7	1318.8	1317.1
167.5°	1339.7	1338.4	1337.0	1335.7	1337.0	1338.4	1339.7	1341.0	1340.8	1339.0	1337.2
170°	1350.5	1349.0	1347.4	1345.9	1347.4	1349.0	1350.5	1352.0	1351.9	1350.1	1348.3
172.5°	1358.8	1357.3	1355.8	1354.2	1355.8	1357.3	1358.8	1360.3	1360.2	1358.4	1356.6
175°	1367.8	1366.3	1364.8	1363.2	1364.8	1366.3	1367.8	1369.4	1369.2	1367.4	1365.7
177.5°	1371.1	1369.8	1368.6	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3	1371.1	1369.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1637.4	1644.1	1654.0	1659.7	1669.2	1675.3	1678.6	1684.8	1688.1	1700.0	1712.3
5°	1546.0	1555.5	1572.0	1587.4	1604.0	1621.1	1633.5	1647.8	1660.8	1683.3	1706.9
7.5°	1441.2	1454.3	1480.0	1504.5	1533.3	1557.6	1579.0	1603.3	1625.0	1657.2	1690.7
10°	1362.6	1385.6	1419.4	1442.4	1480.3	1504.6	1538.3	1565.0	1595.1	1637.7	1675.6
12.5°	1294.9	1322.7	1349.8	1381.9	1415.9	1456.3	1493.3	1527.5	1563.4	1607.4	1651.9
15°	1172.1	1212.3	1254.3	1286.8	1333.0	1375.6	1418.8	1464.9	1508.7	1561.4	1619.3
17.5°	1014.0	1060.6	1131.2	1187.0	1241.2	1283.9	1337.4	1393.2	1444.8	1508.3	1572.9
20°	942.5	976.9	1024.8	1099.9	1181.5	1227.1	1281.6	1343.1	1402.2	1471.4	1540.7
22.5°	885.2	915.8	954.2	1012.8	1103.9	1166.0	1222.8	1285.3	1354.0	1424.6	1501.4
25°	803.4	824.7	865.0	912.3	975.1	1077.4	1139.5	1202.2	1276.8	1352.5	1440.1
27.5°	742.1	761.3	787.4	832.6	879.2	952.7	1051.5	1119.9	1194.2	1279.4	1370.3
30°	695.2	717.6	746.6	778.6	829.5	886.9	985.7	1065.0	1138.4	1225.9	1322.9
32.5°	661.1	678.9	703.6	736.0	778.4	833.4	912.3	1008.6	1080.1	1172.4	1273.7
35°	605.3	626.0	646.1	676.9	711.1	761.4	821.2	924.2	995.1	1086.3	1188.0
37.5°	559.2	571.9	594.1	618.5	654.7	692.2	744.0	836.3	913.2	1002.6	1106.8
40°	524.2	540.2	556.8	584.0	613.6	649.6	700.5	769.2	857.3	944.9	1046.6
42.5°	490.2	510.3	527.9	546.1	578.5	614.7	656.0	714.3	804.3	887.2	986.1
45°	449.1	462.1	480.5	500.5	527.2	557.9	594.6	645.5	731.9	803.4	896.3
47.5°	401.3	420.4	432.3	451.9	477.2	506.6	540.6	584.7	654.6	721.7	807.9
50°	368.6	388.2	405.3	423.0	445.5	473.9	502.3	544.9	601.1	671.5	752.0
52.5°	340.6	357.8	374.5	392.3	414.3	440.3	467.3	504.7	552.9	617.6	695.7
55°	302.4	313.0	330.1	347.9	367.4	392.3	418.3	449.7	491.1	545.5	608.9
57.5°	263.1	275.4	289.0	306.8	326.6	345.6	369.1	397.4	430.2	479.4	533.6
60°	240.8	250.3	261.5	279.8	298.2	315.3	337.9	361.5	392.3	434.9	481.0
62.5°	216.2	225.2	235.5	251.5	269.3	285.1	304.7	329.8	355.8	394.7	435.1
65°	175.1	188.2	198.2	212.4	227.2	243.8	259.1	279.3	302.4	333.1	369.2
67.5°	145.2	151.9	161.1	174.1	189.2	203.4	217.9	233.7	253.7	277.5	306.1
70°	132.0	134.3	136.1	148.5	162.7	176.9	190.5	205.3	222.5	242.0	266.8
72.5°	116.3	118.7	120.9	126.3	137.6	151.9	165.9	176.9	193.1	209.3	229.4
75°	92.3	95.9	97.6	100.6	104.7	114.2	127.2	137.9	147.3	159.7	175.8
77.5°	70.3	72.3	74.2	77.3	79.9	84.3	91.6	101.2	110.0	117.3	128.2
80°	55.6	56.2	58.6	59.7	63.3	66.3	69.8	77.5	86.4	89.3	97.0
82.5°	41.9	42.4	44.4	45.6	47.2	49.7	54.2	56.2	63.2	67.1	72.0
85°	23.1	22.5	24.3	24.3	25.4	26.7	27.8	30.8	32.5	37.3	38.4
87.5°	15.1	15.2	14.5	13.4	12.3	12.1	11.7	11.6	11.9	12.7	14.0
90°	39.9	40.5	34.8	29.2	23.5	17.8	13.5	10.4	7.3	4.3	1.2
92.5°	36.8	36.7	35.4	34.1	32.7	31.4	29.6	27.4	25.1	22.8	20.6
95°	74.0	74.0	73.5	72.9	72.5	72.0	70.4	67.9	65.3	62.7	60.1
97.5°	124.4	124.4	123.4	122.4	121.5	120.5	118.9	116.6	114.4	112.1	109.9
100°	159.5	159.5	158.8	158.0	157.2	156.5	155.1	153.0	151.0	148.9	146.9
102.5°	197.7	197.5	196.5	195.6	194.6	193.6	192.3	190.6	189.0	187.3	185.7
105°	254.9	254.4	253.9	253.3	252.8	252.4	251.6	250.9	250.1	249.3	248.6
107.5°	317.3	317.0	317.0	317.0	317.0	317.0	316.5	315.3	314.2	313.1	311.9
110°	359.6	359.6	359.6	359.6	359.6	359.6	358.8	357.3	355.7	354.2	352.7



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	402.4	403.1	403.2	403.5	403.7	403.9	403.2	401.7	400.1	398.6	397.1
115°	466.9	467.1	467.6	468.1	468.7	469.1	468.7	467.1	465.6	464.0	462.5
117.5°	529.9	530.5	531.9	533.3	534.8	536.3	535.9	533.9	531.8	529.8	527.7
120°	571.1	571.1	573.2	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1
122.5°	614.9	615.5	617.0	618.5	619.9	621.3	620.8	618.3	615.9	613.4	610.9
125°	679.1	679.8	680.6	681.4	682.2	683.0	682.2	679.8	677.5	675.2	672.9
127.5°	741.4	742.3	743.2	744.1	745.1	746.0	745.0	742.1	739.1	736.2	733.3
130°	783.4	783.9	784.4	785.0	785.5	786.0	784.5	781.2	777.9	774.5	771.2
132.5°	825.4	826.4	826.3	826.3	826.2	826.1	824.7	821.9	819.2	816.5	813.8
135°	885.4	885.6	885.2	884.7	884.1	883.6	882.0	879.1	876.3	873.4	870.7
137.5°	943.8	944.0	943.3	942.6	941.9	941.3	939.8	937.5	935.1	932.8	930.5
140°	982.8	982.8	981.5	980.3	978.9	977.7	975.9	973.6	971.3	968.9	966.6
142.5°	1018.2	1018.0	1017.1	1016.2	1015.3	1014.4	1012.9	1010.6	1008.3	1005.9	1003.6
145°	1072.1	1071.8	1070.3	1068.7	1067.2	1065.7	1064.0	1062.2	1060.4	1058.6	1056.8
147.5°	1119.1	1118.6	1117.5	1116.5	1115.4	1114.5	1112.9	1110.7	1108.5	1106.3	1104.2
150°	1148.9	1148.2	1147.1	1146.1	1145.0	1144.1	1142.7	1141.2	1139.7	1138.1	1136.6
152.5°	1178.8	1177.8	1176.5	1175.3	1174.0	1172.8	1171.4	1169.8	1168.3	1166.8	1165.3
155°	1216.5	1215.2	1214.4	1213.6	1212.9	1212.1	1211.4	1210.6	1209.8	1209.1	1208.3
157.5°	1251.2	1249.5	1248.9	1248.5	1248.0	1247.6	1247.1	1246.6	1246.1	1245.5	1245.0
160°	1272.2	1270.7	1270.4	1270.2	1269.9	1269.7	1269.3	1268.8	1268.3	1267.7	1267.2
162.5°	1290.9	1289.2	1289.0	1288.7	1288.4	1288.2	1288.0	1287.9	1287.8	1287.7	1287.5
165°	1315.3	1313.5	1313.5	1313.5	1313.5	1313.5	1313.6	1313.8	1314.1	1314.4	1314.6
167.5°	1335.4	1333.6	1333.6	1333.7	1333.7	1333.8	1334.2	1335.0	1335.8	1336.5	1337.3
170°	1346.5	1344.7	1345.0	1345.2	1345.5	1345.8	1346.2	1347.0	1347.8	1348.5	1349.3
172.5°	1354.9	1353.0	1353.3	1353.5	1353.8	1354.1	1354.6	1355.3	1356.1	1356.9	1357.6
175°	1363.9	1362.0	1362.5	1363.1	1363.6	1364.1	1364.8	1365.5	1366.3	1367.1	1367.8
177.5°	1368.6	1367.3	1367.8	1368.2	1368.6	1369.0	1369.5	1370.1	1370.7	1371.4	1372.0
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1712.7	1714.1	1723.6	1727.9	1736.4	1739.7	1743.5	1742.6	1742.6	1744.5	1757.7
5°	1716.4	1728.2	1746.0	1763.2	1779.7	1793.9	1803.4	1812.8	1816.4	1833.5	1849.0
7.5°	1710.2	1732.1	1761.4	1787.5	1818.9	1843.3	1863.8	1882.0	1894.6	1919.6	1945.2
10°	1702.2	1733.0	1766.1	1799.8	1843.0	1875.5	1908.7	1934.1	1942.4	1979.7	2001.0
12.5°	1686.1	1727.2	1769.4	1813.1	1855.3	1900.1	1936.6	1962.0	1991.2	2024.6	2064.0
15°	1662.0	1709.3	1764.3	1820.5	1880.9	1935.3	1974.3	2018.7	2050.7	2087.4	2121.6
17.5°	1627.3	1688.3	1758.2	1823.3	1893.1	1951.5	2005.3	2047.8	2070.3	2091.2	2096.3
20°	1599.8	1665.5	1747.8	1824.7	1894.5	1961.9	2015.2	2050.7	2056.6	2057.2	2025.9
22.5°	1570.0	1644.2	1730.3	1809.0	1892.6	1967.6	2009.0	2024.2	2000.7	1960.6	1900.0
25°	1515.2	1601.1	1701.0	1790.9	1882.0	1953.0	1967.3	1940.6	1858.4	1772.0	1662.6
27.5°	1455.8	1552.3	1659.5	1759.4	1856.5	1900.5	1869.9	1773.9	1625.8	1497.0	1341.0
30°	1412.3	1520.5	1625.9	1737.7	1827.7	1846.6	1776.2	1634.8	1462.0	1267.9	1112.3
32.5°	1362.6	1476.0	1591.8	1707.4	1782.7	1764.2	1647.9	1473.8	1271.2	1080.5	933.4
35°	1291.6	1408.7	1533.6	1649.6	1697.5	1617.6	1443.7	1217.0	1010.0	831.9	730.7
37.5°	1209.6	1337.1	1467.0	1573.4	1570.0	1436.9	1200.0	966.1	792.0	686.7	614.7
40°	1151.4	1280.3	1420.6	1510.5	1472.0	1298.7	1041.9	821.2	694.0	610.0	557.3
42.5°	1095.6	1224.9	1364.2	1435.7	1368.9	1155.7	899.9	727.0	622.1	556.5	513.8
45°	1000.5	1137.2	1266.1	1305.8	1186.2	951.4	727.7	602.4	532.5	483.9	454.4
47.5°	907.6	1042.1	1159.8	1160.5	998.8	771.5	613.9	521.3	461.6	424.1	402.6
50°	850.8	978.6	1077.4	1062.0	878.6	686.3	549.0	469.2	419.5	390.5	368.0
52.5°	786.9	910.9	996.5	952.7	776.9	604.0	490.8	423.7	382.5	357.4	337.2
55°	694.0	804.1	864.4	798.2	633.6	502.3	414.7	362.1	331.4	310.0	292.8
57.5°	602.8	693.6	731.6	654.3	521.9	416.5	350.9	311.3	280.8	265.6	256.6
60°	545.5	623.0	649.6	564.5	453.8	364.4	310.6	273.9	251.5	241.4	232.6
62.5°	489.2	552.5	563.5	485.4	395.6	319.1	272.8	241.7	226.9	217.2	208.8
65°	405.9	451.5	446.1	383.4	313.0	253.2	219.5	200.5	189.3	175.8	161.0
67.5°	334.1	361.9	345.2	298.2	238.9	196.8	174.8	160.4	146.5	133.6	130.2
70°	288.7	304.7	287.0	243.8	195.8	165.1	147.3	130.2	121.9	119.0	113.6
72.5°	245.2	250.7	231.6	194.6	159.3	136.7	119.4	109.8	105.3	102.8	99.4
75°	184.0	179.9	163.3	134.3	110.7	95.2	90.0	86.4	83.5	81.1	79.3
77.5°	129.2	123.1	108.4	89.4	77.0	69.7	66.5	64.6	63.2	62.0	60.2
80°	97.0	92.9	78.1	63.9	58.6	55.0	53.2	50.9	50.9	49.7	47.9
82.5°	71.0	66.3	53.5	46.8	43.9	41.7	40.5	39.1	38.6	38.8	37.5
85°	37.3	30.1	26.7	25.4	23.6	22.5	23.1	21.8	21.8	21.8	21.3
87.5°	12.2	10.4	10.6	10.7	12.1	13.2	13.9	15.0	16.6	16.1	16.4
90°	4.3	7.3	10.4	13.5	17.8	23.5	29.2	34.8	40.5	39.9	39.4
92.5°	22.8	25.1	27.4	29.6	31.4	32.7	34.1	35.4	36.7	36.8	37.0
95°	62.7	65.3	67.9	70.4	72.0	72.5	72.9	73.5	74.0	74.0	74.0
97.5°	112.1	114.4	116.6	118.9	120.5	121.5	122.4	123.4	124.4	124.4	124.4
100°	148.9	151.0	153.0	155.1	156.5	157.2	158.0	158.8	159.5	159.5	159.5
102.5°	187.3	189.0	190.6	192.3	193.6	194.6	195.6	196.5	197.5	197.7	197.9
105°	249.3	250.1	250.9	251.6	252.4	252.8	253.3	253.9	254.4	254.9	255.4
107.5°	313.1	314.2	315.3	316.5	317.0	317.0	317.0	317.0	317.0	317.3	317.4
110°	354.2	355.7	357.3	358.8	359.6	359.6	359.6	359.6	359.6	359.6	359.6



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	398.6	400.1	401.7	403.2	403.9	403.7	403.5	403.2	403.1	402.4	401.8
115°	464.0	465.6	467.1	468.7	469.1	468.7	468.1	467.6	467.1	466.9	466.6
117.5°	529.8	531.8	533.9	535.9	536.3	534.8	533.3	531.9	530.5	529.9	529.2
120°	573.2	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1	571.1	571.1
122.5°	613.4	615.9	618.3	620.8	621.3	619.9	618.5	617.0	615.5	614.9	614.4
125°	675.2	677.5	679.8	682.2	683.0	682.2	681.4	680.6	679.8	679.1	678.3
127.5°	736.2	739.1	742.1	745.0	746.0	745.1	744.1	743.2	742.3	741.4	740.5
130°	774.5	777.9	781.2	784.5	786.0	785.5	785.0	784.4	783.9	783.4	782.9
132.5°	816.5	819.2	821.9	824.7	826.1	826.2	826.3	826.3	826.4	825.4	824.2
135°	873.4	876.3	879.1	882.0	883.6	884.1	884.7	885.2	885.6	885.4	885.2
137.5°	932.8	935.1	937.5	939.8	941.3	941.9	942.6	943.3	944.0	943.8	943.5
140°	968.9	971.3	973.6	975.9	977.7	978.9	980.3	981.5	982.8	982.8	982.8
142.5°	1005.9	1008.3	1010.6	1012.9	1014.4	1015.3	1016.2	1017.1	1018.0	1018.2	1018.3
145°	1058.6	1060.4	1062.2	1064.0	1065.7	1067.2	1068.7	1070.3	1071.8	1072.1	1072.4
147.5°	1106.3	1108.5	1110.7	1112.9	1114.5	1115.4	1116.5	1117.5	1118.6	1119.1	1119.6
150°	1138.1	1139.7	1141.2	1142.7	1144.1	1145.0	1146.1	1147.1	1148.2	1148.9	1149.7
152.5°	1166.8	1168.3	1169.8	1171.4	1172.8	1174.0	1175.3	1176.5	1177.8	1178.8	1179.7
155°	1209.1	1209.8	1210.6	1211.4	1212.1	1212.9	1213.6	1214.4	1215.2	1216.5	1217.8
157.5°	1245.5	1246.1	1246.6	1247.1	1247.6	1248.0	1248.5	1248.9	1249.5	1251.2	1252.9
160°	1267.7	1268.3	1268.8	1269.3	1269.7	1269.9	1270.2	1270.4	1270.7	1272.2	1273.8
162.5°	1287.7	1287.8	1287.9	1288.0	1288.2	1288.4	1288.7	1289.0	1289.2	1290.9	1292.7
165°	1314.4	1314.1	1313.8	1313.6	1313.5	1313.5	1313.5	1313.5	1313.5	1315.3	1317.1
167.5°	1336.5	1335.8	1335.0	1334.2	1333.8	1333.7	1333.7	1333.6	1333.6	1335.4	1337.2
170°	1348.5	1347.8	1347.0	1346.2	1345.8	1345.5	1345.2	1345.0	1344.7	1346.5	1348.3
172.5°	1356.9	1356.1	1355.3	1354.6	1354.1	1353.8	1353.5	1353.3	1353.0	1354.9	1356.6
175°	1367.1	1366.3	1365.5	1364.8	1364.1	1363.6	1363.1	1362.5	1362.0	1363.9	1365.7
177.5°	1371.4	1370.7	1370.1	1369.5	1369.0	1368.6	1368.2	1367.8	1367.3	1368.6	1369.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1762.5	1768.6	1771.4	1771.4	1774.8	1773.3	1771.9
5°	1863.8	1875.0	1877.3	1888.0	1895.7	1893.3	1894.5
7.5°	1964.4	1982.5	2000.4	2008.6	2009.8	2014.6	2016.3
10°	2026.4	2041.2	2069.0	2064.8	2085.6	2097.4	2077.9
12.5°	2086.1	2106.0	2125.4	2130.7	2142.4	2146.2	2138.5
15°	2140.0	2150.7	2151.9	2148.9	2152.4	2149.5	2138.2
17.5°	2089.6	2072.3	2037.3	2020.7	2007.6	1988.2	1980.4
20°	2006.3	1955.4	1896.2	1872.6	1844.8	1790.4	1803.4
22.5°	1826.5	1768.4	1709.3	1640.2	1607.2	1555.6	1552.5
25°	1546.6	1446.6	1336.6	1259.6	1214.7	1163.2	1140.7
27.5°	1202.5	1076.6	986.4	940.8	899.2	858.4	856.8
30°	976.2	881.5	811.7	772.7	747.3	730.1	733.7
32.5°	822.9	758.0	711.0	678.5	659.7	646.8	646.6
35°	672.7	628.3	598.2	584.5	571.0	561.5	562.0
37.5°	575.7	549.0	532.3	517.2	508.7	504.1	501.5
40°	526.0	504.1	491.1	482.2	475.1	468.6	467.4
42.5°	486.7	468.6	455.6	448.6	441.9	437.4	436.1
45°	431.9	417.1	405.3	397.6	394.7	390.5	390.5
47.5°	384.2	369.7	360.4	355.6	350.5	347.8	347.7
50°	352.0	340.8	332.5	329.6	325.4	323.6	323.1
52.5°	323.2	314.8	308.9	306.8	305.1	302.8	303.2
55°	284.0	279.3	276.9	275.1	272.2	268.6	271.0
57.5°	251.0	246.9	240.6	235.0	232.3	229.8	230.8
60°	227.8	219.5	211.2	204.7	203.0	197.6	197.6
62.5°	198.4	186.8	176.6	173.0	171.2	168.7	168.3
65°	152.7	147.9	145.5	143.2	142.0	142.0	140.8
67.5°	126.5	124.6	122.0	121.5	120.2	119.8	119.5
70°	111.8	109.4	108.3	107.7	106.5	107.1	105.3
72.5°	97.6	95.8	95.5	94.0	93.3	93.4	92.0
75°	77.0	77.0	76.3	75.7	74.5	73.9	74.5
77.5°	59.2	59.3	58.2	58.1	58.0	58.1	57.5
80°	47.3	47.9	47.3	46.7	46.2	46.7	46.2
82.5°	37.4	36.6	36.5	36.3	36.2	35.8	35.8
85°	21.3	21.8	21.3	20.7	20.7	20.7	21.3
87.5°	15.9	15.7	15.7	15.8	15.8	15.9	15.4
90°	39.0	38.4	38.3	38.5	38.8	39.1	39.3
92.5°	37.1	37.2	37.3	37.3	37.4	37.5	37.5
95°	74.0	74.0	73.7	73.2	72.7	72.2	71.7
97.5°	124.4	124.4	124.4	124.3	124.3	124.2	124.2
100°	159.5	159.5	159.4	159.2	158.9	158.6	158.4
102.5°	198.1	198.3	198.3	198.0	197.8	197.5	197.2
105°	255.9	256.5	256.7	256.7	256.7	256.7	256.7
107.5°	317.6	317.9	317.4	316.2	315.0	313.8	312.6
110°	359.6	359.6	359.2	358.5	357.7	356.9	356.1



TEST NUMBER: P331838-940

CATALOG NUMBER: S122RDIW-S865D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	401.2	400.6	400.0	399.4	398.9	398.3	397.7
115°	466.4	466.1	465.6	464.8	464.0	463.2	462.5
117.5°	528.6	528.0	527.4	526.6	525.8	525.0	524.2
120°	571.1	571.1	570.8	570.0	569.3	568.5	567.8
122.5°	613.8	613.1	612.5	612.0	611.4	610.8	610.3
125°	677.5	676.8	676.3	676.0	675.7	675.5	675.2
127.5°	739.5	738.6	737.7	736.9	736.1	735.3	734.4
130°	782.4	781.9	781.1	780.1	779.1	778.0	776.9
132.5°	823.0	822.0	821.0	820.2	819.3	818.5	817.7
135°	884.9	884.7	884.1	883.3	882.6	881.8	881.0
137.5°	943.3	943.2	942.5	941.5	940.5	939.4	938.4
140°	982.8	982.8	982.3	981.2	980.3	979.2	978.2
142.5°	1018.6	1018.8	1018.3	1017.4	1016.3	1015.3	1014.2
145°	1072.6	1072.8	1072.5	1071.5	1070.4	1069.4	1068.4
147.5°	1120.3	1120.8	1120.6	1119.6	1118.7	1117.7	1116.7
150°	1150.5	1151.2	1151.2	1150.5	1149.7	1148.9	1148.2
152.5°	1180.6	1181.6	1181.6	1180.6	1179.7	1178.8	1177.8
155°	1219.1	1220.3	1220.6	1219.9	1219.1	1218.3	1217.5
157.5°	1254.6	1256.4	1256.7	1255.4	1254.2	1252.9	1251.7
160°	1275.3	1276.8	1277.1	1276.1	1275.1	1274.1	1273.0
162.5°	1294.4	1296.2	1296.5	1295.2	1294.0	1292.7	1291.6
165°	1318.8	1320.7	1320.9	1319.6	1318.4	1317.1	1315.8
167.5°	1339.0	1340.8	1341.0	1339.7	1338.4	1337.0	1335.7
170°	1350.1	1351.9	1352.0	1350.5	1349.0	1347.4	1345.9
172.5°	1358.4	1360.2	1360.3	1358.8	1357.3	1355.8	1354.2
175°	1367.4	1369.2	1369.4	1367.8	1366.3	1364.8	1363.2
177.5°	1371.1	1372.3	1372.3	1371.1	1369.8	1368.6	1367.3
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1

(END OF REPORT)