

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331784-935

Luminaire Tested: **S122RDIW-S290D1440U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331784-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D1440U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5196.0 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331784-935

CATALOG NUMBER: S122RDIW-S290D1440U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331784-935

CATALOG NUMBER: S122RDIW-S290D1440U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	99	99	99	99	87	87	87	87	65	65	65	45	45	45	26	26	26	17																												
1	91	87	83	80	80	76	73	71	57	55	53	39	38	37	23	23	22	15																												
2	83	76	70	65	72	67	62	58	50	47	44	35	33	31	21	20	19	13																												
3	75	67	60	54	66	59	53	49	44	41	37	31	29	27	18	17	16	11																												
4	69	59	51	46	60	52	46	41	39	35	32	27	25	23	16	15	14	9																												
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	13	12	8																												
6	58	47	39	34	51	41	35	30	32	27	24	22	19	17	13	12	11	7																												
7	54	42	35	29	47	37	31	26	28	24	21	20	17	15	12	11	10	7																												
8	50	38	31	26	43	34	28	23	26	21	18	18	16	13	11	10	9	6																												
9	46	35	27	23	40	31	25	21	24	19	16	17	14	12	10	9	8	5																												
10	43	31	25	20	38	28	22	18	22	17	15	15	13	11	10	8	7	5																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6978	6978	6978
5°	7005	6891	6929
10°	6951	6779	6720
15°	6870	6578	6387
20°	6761	6290	5976
25°	6649	5964	5574
30°	6490	5630	5062
35°	6337	5267	4610
40°	6182	4890	4089
45°	6003	4464	3617
50°	5815	4037	3152
55°	5624	3578	2711
60°	5406	3094	2251
65°	5154	2598	2048
70°	4858	2143	1884
75°	4492	1953	1759
80°	3961	1748	1599
85°	3112	1371	1371



TEST NUMBER: P331784-935

CATALOG NUMBER: S122RDIW-S290D1440U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.5	0.8
10°-20°	111.1	2.1
20°-30°	156.0	3.0
30°-40°	170.1	3.3
40°-50°	156.4	3.0
50°-60°	122.8	2.4
60°-70°	80.1	1.5
70°-80°	41.3	0.8
80°-90°	16.8	0.3
90°-100°	97.5	1.9
100°-110°	302.7	5.8
110°-120°	517.4	10.0
120°-130°	680.4	13.1
130°-140°	763.7	14.7
140°-150°	748.8	14.4
150°-160°	628.1	12.1
160°-170°	416.6	8.0
170°-180°	145.6	2.8
0°-30°	307.5	5.9
0°-40°	477.6	9.2
0°-60°	756.8	14.6
0°-90°	895.1	17.2
90°-120°	917.6	17.7
90°-150°	3110.6	59.9
90°-180°	4301.0	82.8
0°-180°	5196.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	432	432	432	432	432	
5°	432	430	425	428	428	41
15°	411	406	394	386	382	116
25°	373	360	335	319	313	172
35°	322	301	267	243	234	201
45°	263	236	196	169	158	203
55°	200	169	127	104	96	179
65°	135	103	68	55	54	134
75°	72	45	31	29	28	76
85°	17	9	7	7	7	20
90°	1	18	46	43	44	4
95°	68	80	83	83	80	77
105°	279	283	286	288	288	295
115°	519	526	524	523	519	513
125°	755	766	763	759	758	675
135°	977	991	994	993	989	755
145°	1186	1195	1203	1204	1199	741
155°	1356	1360	1364	1370	1367	624
165°	1476	1475	1474	1483	1477	416
175°	1536	1532	1529	1537	1530	146
180°	1538	1538	1538	1538	1538	



TEST NUMBER: P331784-935

CATALOG NUMBER: S122RDIW-S290D1440U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	433.8	433.4	433.1	432.7	432.4	431.8	431.0	430.3	429.6	428.8	429.5
5°	432.2	431.8	431.4	430.9	430.5	429.6	428.5	427.4	426.3	425.2	425.9
7.5°	427.7	427.2	426.6	426.1	425.6	424.6	423.4	422.0	420.7	419.4	419.6
10°	424.0	423.4	422.8	422.1	421.5	420.3	418.6	416.9	415.2	413.5	413.2
12.5°	419.3	418.5	417.8	417.1	416.3	414.8	412.6	410.4	408.1	405.9	405.4
15°	411.0	410.1	409.1	408.2	407.3	405.3	402.3	399.4	396.4	393.5	391.8
17.5°	401.0	399.5	398.0	396.6	395.1	392.5	388.7	385.0	381.2	377.4	375.4
20°	393.5	391.8	390.0	388.2	386.5	383.5	379.1	374.8	370.5	366.1	363.9
22.5°	385.4	383.4	381.4	379.5	377.5	374.1	369.2	364.3	359.5	354.6	351.7
25°	373.2	370.3	367.6	364.8	362.1	357.7	352.0	346.3	340.5	334.8	331.2
27.5°	358.4	355.4	352.4	349.4	346.3	341.6	335.1	328.6	322.2	315.7	311.6
30°	348.1	344.8	341.5	338.2	334.9	329.8	322.8	315.9	308.9	302.0	297.6
32.5°	338.1	334.2	330.4	326.5	322.6	317.2	310.1	303.0	295.9	288.8	283.8
35°	321.5	317.1	312.6	308.2	303.8	297.7	290.1	282.4	274.8	267.2	261.7
37.5°	305.0	300.1	295.2	290.3	285.4	279.0	270.8	262.6	254.5	246.3	240.3
40°	293.3	288.2	282.9	277.7	272.5	265.7	257.3	248.8	240.4	232.0	225.8
42.5°	281.5	276.0	270.4	265.0	259.5	252.4	243.7	235.0	226.3	217.6	211.2
45°	262.9	257.0	251.2	245.4	239.5	232.0	222.9	213.8	204.7	195.5	189.4
47.5°	244.7	238.5	232.4	226.2	220.0	212.2	202.8	193.4	183.9	174.5	168.4
50°	231.5	225.4	219.2	213.0	206.9	199.0	189.4	179.9	170.3	160.7	154.7
52.5°	218.7	212.2	205.9	199.4	193.0	185.0	175.6	166.3	157.0	147.6	141.8
55°	199.8	193.1	186.3	179.5	172.7	164.7	155.2	145.9	136.5	127.1	121.9
57.5°	180.6	173.6	166.6	159.7	152.7	144.7	135.7	126.7	117.7	108.7	103.8
60°	167.4	160.5	153.5	146.5	139.6	131.6	122.7	113.7	104.8	95.8	91.4
62.5°	154.5	147.7	140.7	133.7	126.7	119.0	110.5	101.9	93.4	84.9	80.7
65°	134.9	127.9	120.9	113.8	106.8	99.4	91.5	83.7	75.9	68.0	65.1
67.5°	116.0	109.0	102.0	95.1	88.1	81.0	74.0	67.0	59.9	52.9	51.5
70°	102.9	96.1	89.3	82.6	75.8	69.4	63.4	57.3	51.4	45.4	44.5
72.5°	90.3	83.9	77.3	70.9	64.3	58.7	53.9	49.1	44.3	39.4	38.7
75°	72.0	65.9	59.8	53.7	47.6	43.1	40.1	37.2	34.3	31.3	30.7
77.5°	53.9	48.6	43.2	37.9	32.5	29.2	27.7	26.3	24.9	23.5	23.2
80°	42.6	38.2	33.8	29.4	24.9	22.2	21.4	20.5	19.6	18.8	18.4
82.5°	32.3	28.8	25.4	22.0	18.5	16.4	15.8	15.2	14.6	14.1	13.9
85°	16.8	15.0	13.2	11.4	9.6	8.4	8.2	7.9	7.7	7.4	7.4
87.5°	5.3	5.4	5.5	5.7	5.8	6.5	7.7	9.0	10.3	11.6	11.4
90°	1.3	4.7	8.2	11.7	15.2	20.1	26.4	32.7	39.1	45.5	44.9
92.5°	23.1	25.7	28.2	30.7	33.2	35.3	36.8	38.3	39.8	41.2	41.4
95°	67.5	70.3	73.3	76.1	79.0	80.8	81.4	81.9	82.5	83.1	83.1
97.5°	123.3	125.9	128.4	131.0	133.5	135.3	136.4	137.5	138.5	139.7	139.7
100°	164.9	167.1	169.4	171.8	174.1	175.6	176.5	177.4	178.2	179.1	179.1
102.5°	208.4	210.3	212.2	214.0	215.9	217.3	218.4	219.5	220.6	221.7	222.0
105°	279.1	279.9	280.8	281.6	282.5	283.3	283.9	284.4	285.0	285.6	286.1
107.5°	350.2	351.5	352.8	354.0	355.2	355.9	355.9	355.9	355.9	355.9	356.1
110°	395.9	397.6	399.3	401.1	402.8	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P331784-935

CATALOG NUMBER: S122RDIW-S290D1440U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	445.7	447.5	449.2	450.9	452.6	453.4	453.1	453.0	452.7	452.5	451.8
115°	519.2	520.9	522.6	524.4	526.2	526.7	526.2	525.6	525.0	524.4	524.1
117.5°	592.5	594.7	597.0	599.3	601.7	602.0	600.4	598.7	597.1	595.6	594.9
120°	641.2	643.5	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2	641.2
122.5°	685.9	688.6	691.4	694.1	697.0	697.5	695.9	694.3	692.7	691.0	690.3
125°	755.4	758.0	760.6	763.2	765.9	766.7	765.9	765.0	764.1	763.2	762.3
127.5°	823.2	826.5	829.7	833.1	836.4	837.5	836.5	835.4	834.4	833.4	832.2
130°	865.7	869.5	873.3	877.0	880.8	882.4	881.8	881.2	880.6	880.0	879.5
132.5°	913.5	916.6	919.6	922.7	925.7	927.4	927.5	927.6	927.7	927.8	926.5
135°	977.4	980.6	983.8	986.9	990.1	992.0	992.6	993.2	993.7	994.3	994.0
137.5°	1044.7	1047.2	1049.8	1052.4	1055.0	1056.7	1057.5	1058.2	1058.9	1059.7	1059.5
140°	1085.1	1087.7	1090.4	1093.0	1095.5	1097.5	1099.0	1100.4	1101.9	1103.3	1103.3
142.5°	1126.7	1129.3	1131.9	1134.5	1137.0	1138.8	1139.8	1140.8	1141.8	1142.8	1143.0
145°	1186.4	1188.4	1190.4	1192.4	1194.5	1196.4	1198.1	1199.8	1201.5	1203.2	1203.5
147.5°	1239.6	1242.0	1244.4	1246.9	1249.3	1251.1	1252.2	1253.4	1254.6	1255.7	1256.4
150°	1275.9	1277.6	1279.4	1281.2	1282.9	1284.3	1285.5	1286.6	1287.8	1288.9	1289.8
152.5°	1308.1	1309.8	1311.6	1313.3	1315.1	1316.6	1318.0	1319.4	1320.8	1322.2	1323.3
155°	1356.4	1357.3	1358.1	1359.0	1359.9	1360.7	1361.6	1362.4	1363.3	1364.2	1365.6
157.5°	1397.7	1398.3	1398.9	1399.5	1400.0	1400.6	1401.1	1401.6	1402.1	1402.7	1404.5
160°	1422.6	1423.2	1423.7	1424.4	1425.0	1425.4	1425.6	1425.9	1426.2	1426.5	1428.2
162.5°	1445.4	1445.6	1445.7	1445.8	1446.0	1446.1	1446.4	1446.7	1447.0	1447.3	1449.2
165°	1475.8	1475.6	1475.2	1475.0	1474.7	1474.5	1474.5	1474.5	1474.5	1474.5	1476.5
167.5°	1501.2	1500.4	1499.5	1498.7	1497.8	1497.4	1497.3	1497.3	1497.2	1497.1	1499.2
170°	1514.8	1513.9	1513.0	1512.2	1511.3	1510.7	1510.5	1510.2	1509.8	1509.6	1511.6
172.5°	1524.1	1523.3	1522.4	1521.6	1520.7	1520.1	1519.8	1519.5	1519.2	1518.9	1521.0
175°	1535.5	1534.6	1533.8	1532.9	1532.1	1531.4	1530.8	1530.2	1529.7	1529.0	1531.1
177.5°	1540.2	1539.6	1538.9	1538.2	1537.5	1536.9	1536.4	1535.9	1535.5	1535.0	1536.4
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331784-935

CATALOG NUMBER: S122RDIW-S290D1440U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	430.2	430.8	431.5	431.8	431.7	431.5	431.4	431.3
5°	426.7	427.5	428.3	428.5	428.3	428.0	427.7	427.5
7.5°	419.8	420.1	420.3	420.2	419.7	419.2	418.8	418.4
10°	412.9	412.7	412.4	412.0	411.5	411.0	410.4	409.9
12.5°	405.0	404.5	404.1	403.4	402.5	401.7	400.8	399.9
15°	390.2	388.5	386.8	385.6	384.8	383.8	383.0	382.1
17.5°	373.4	371.4	369.5	367.8	366.3	364.8	363.3	361.8
20°	361.8	359.6	357.4	355.3	353.4	351.5	349.7	347.8
22.5°	349.0	346.1	343.4	341.2	339.8	338.4	336.9	335.5
25°	327.7	324.1	320.6	318.1	316.8	315.5	314.2	312.9
27.5°	307.4	303.2	299.1	296.0	293.9	291.9	289.8	287.7
30°	293.1	288.7	284.2	280.9	278.4	276.1	273.8	271.5
32.5°	278.7	273.6	268.5	264.9	262.8	260.5	258.3	256.1
35°	256.2	250.7	245.2	241.5	239.6	237.7	235.8	233.9
37.5°	234.3	228.3	222.2	218.1	215.9	213.7	211.5	209.3
40°	219.6	213.4	207.2	203.0	200.8	198.5	196.2	194.0
42.5°	204.7	198.4	192.0	187.8	185.5	183.4	181.2	179.0
45°	183.2	177.0	170.9	166.8	164.7	162.6	160.5	158.4
47.5°	162.2	156.1	150.0	145.9	144.0	142.2	140.3	138.4
50°	148.8	142.8	136.7	132.9	131.0	129.2	127.3	125.5
52.5°	136.0	130.3	124.5	120.7	119.1	117.4	115.6	114.0
55°	116.7	111.5	106.2	102.8	101.2	99.5	97.9	96.3
57.5°	99.1	94.3	89.5	86.4	85.1	83.7	82.3	80.8
60°	87.0	82.6	78.1	75.2	73.8	72.4	71.0	69.7
62.5°	76.5	72.2	68.0	65.4	64.6	63.8	62.9	62.1
65°	62.2	59.2	56.2	54.6	54.3	54.1	53.8	53.6
67.5°	50.2	48.8	47.4	46.7	46.3	46.1	45.8	45.5
70°	43.7	42.8	41.9	41.3	40.9	40.6	40.2	39.9
72.5°	38.0	37.2	36.5	36.1	35.8	35.6	35.4	35.2
75°	30.0	29.4	28.8	28.5	28.4	28.3	28.2	28.2
77.5°	22.7	22.4	22.0	21.9	21.7	21.5	21.4	21.3
80°	18.1	17.7	17.4	17.2	17.2	17.2	17.2	17.2
82.5°	13.7	13.4	13.3	13.2	13.2	13.2	13.2	13.2
85°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
87.5°	11.2	11.0	10.8	10.8	10.8	10.9	10.9	11.0
90°	44.3	43.7	43.1	43.0	43.3	43.6	43.8	44.2
92.5°	41.5	41.6	41.8	41.8	41.8	41.9	42.0	42.0
95°	83.1	83.1	83.1	82.7	82.2	81.6	81.0	80.5
97.5°	139.7	139.7	139.7	139.7	139.6	139.5	139.5	139.4
100°	179.1	179.1	179.1	179.0	178.7	178.4	178.1	177.8
102.5°	222.1	222.4	222.7	222.6	222.3	222.1	221.7	221.4
105°	286.7	287.3	287.8	288.2	288.2	288.2	288.2	288.2
107.5°	356.4	356.6	356.8	356.3	355.0	353.6	352.3	350.9
110°	403.7	403.7	403.7	403.2	402.3	401.5	400.6	399.8



TEST NUMBER: P331784-935

CATALOG NUMBER: S122RDIW-S290D1440U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	451.1	450.4	449.7	449.0	448.4	447.8	447.1	446.5
115°	523.8	523.5	523.2	522.6	521.8	520.9	520.0	519.2
117.5°	594.2	593.5	592.8	591.9	591.1	590.2	589.4	588.5
120°	641.2	641.2	641.2	640.8	639.9	639.0	638.2	637.3
122.5°	689.7	689.0	688.3	687.6	687.0	686.4	685.7	685.1
125°	761.5	760.6	759.7	759.2	758.9	758.6	758.4	758.0
127.5°	831.2	830.2	829.1	828.2	827.2	826.3	825.4	824.5
130°	878.9	878.3	877.7	876.8	875.7	874.6	873.4	872.3
132.5°	925.3	924.0	922.7	921.6	920.8	919.8	918.9	917.9
135°	993.7	993.4	993.2	992.6	991.7	990.8	990.0	989.1
137.5°	1059.2	1059.0	1058.8	1058.1	1057.0	1055.8	1054.6	1053.4
140°	1103.3	1103.3	1103.3	1102.8	1101.6	1100.4	1099.2	1098.1
142.5°	1143.2	1143.5	1143.7	1143.2	1142.1	1140.9	1139.8	1138.6
145°	1203.9	1204.1	1204.4	1203.9	1202.8	1201.7	1200.5	1199.4
147.5°	1257.0	1257.6	1258.3	1258.0	1256.9	1255.8	1254.7	1253.6
150°	1290.6	1291.5	1292.4	1292.4	1291.5	1290.6	1289.8	1288.9
152.5°	1324.3	1325.4	1326.5	1326.5	1325.4	1324.3	1323.3	1322.2
155°	1367.1	1368.6	1369.9	1370.3	1369.4	1368.6	1367.7	1366.8
157.5°	1406.5	1408.5	1410.5	1410.7	1409.4	1408.0	1406.6	1405.2
160°	1429.9	1431.7	1433.4	1433.7	1432.5	1431.4	1430.3	1429.1
162.5°	1451.2	1453.2	1455.1	1455.4	1454.1	1452.7	1451.3	1449.8
165°	1478.6	1480.6	1482.6	1482.9	1481.4	1480.1	1478.6	1477.1
167.5°	1501.2	1503.2	1505.2	1505.5	1504.0	1502.4	1501.0	1499.4
170°	1513.6	1515.6	1517.7	1517.8	1516.0	1514.3	1512.6	1510.9
172.5°	1522.9	1525.0	1527.0	1527.2	1525.4	1523.7	1522.0	1520.3
175°	1533.1	1535.1	1537.1	1537.3	1535.5	1533.8	1532.1	1530.3
177.5°	1537.8	1539.2	1540.6	1540.6	1539.2	1537.8	1536.4	1535.0
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2

(END OF REPORT)