

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331768-935

Luminaire Tested: **S122RDIW-S290D435U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331768-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D435U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2183.3 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331768-935

CATALOG NUMBER: S122RDIW-S290D435U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331768-935

CATALOG NUMBER: S122RDIW-S290D435U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35	30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26	23
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	18	16
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	23	19	23	19	17	18	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6978	6978	6978
5°	7005	6891	6929
10°	6951	6779	6720
15°	6870	6578	6387
20°	6761	6290	5976
25°	6649	5964	5574
30°	6490	5630	5062
35°	6337	5267	4610
40°	6182	4890	4089
45°	6003	4464	3617
50°	5815	4037	3152
55°	5624	3578	2711
60°	5406	3094	2251
65°	5154	2598	2048
70°	4858	2143	1884
75°	4492	1953	1759
80°	3961	1748	1599
85°	3112	1371	1371



TEST NUMBER: P331768-935

CATALOG NUMBER: S122RDIW-S290D435U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.5	1.9
10°-20°	111.1	5.1
20°-30°	156.0	7.1
30°-40°	170.1	7.8
40°-50°	156.4	7.2
50°-60°	122.8	5.6
60°-70°	80.1	3.7
70°-80°	41.3	1.9
80°-90°	12.6	0.6
90°-100°	29.3	1.3
100°-110°	91.0	4.2
110°-120°	155.5	7.1
120°-130°	204.5	9.4
130°-140°	229.5	10.5
140°-150°	225.0	10.3
150°-160°	188.8	8.6
160°-170°	125.2	5.7
170°-180°	43.8	2.0
0°-30°	307.5	14.1
0°-40°	477.6	21.9
0°-60°	756.8	34.7
0°-90°	890.8	40.8
90°-120°	275.7	12.6
90°-150°	934.8	42.8
90°-180°	1293.0	59.2
0°-180°	2183.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	432	432	432	432	432	
5°	432	430	425	428	428	41
15°	411	406	394	386	382	116
25°	373	360	335	319	313	172
35°	322	301	267	243	234	201
45°	263	236	196	169	158	203
55°	200	169	127	104	96	179
65°	135	103	68	55	54	134
75°	72	45	31	29	28	76
85°	17	9	7	7	7	20
90°	0	5	14	13	13	2
95°	20	24	25	25	24	23
105°	84	85	86	87	87	89
115°	156	158	158	157	156	154
125°	227	230	229	228	228	203
135°	294	298	299	298	297	227
145°	356	359	362	362	360	223
155°	408	409	410	412	411	188
165°	444	443	443	446	444	125
175°	462	460	460	462	460	44
180°	462	462	462	462	462	



TEST NUMBER: P331768-935

CATALOG NUMBER: S122RDIW-S290D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	433.8	433.4	433.1	432.7	432.4	431.8	431.0	430.3	429.6	428.8	429.5
5°	432.2	431.8	431.4	430.9	430.5	429.6	428.5	427.4	426.3	425.2	425.9
7.5°	427.7	427.2	426.6	426.1	425.6	424.6	423.4	422.0	420.7	419.4	419.6
10°	424.0	423.4	422.8	422.1	421.5	420.3	418.6	416.9	415.2	413.5	413.2
12.5°	419.3	418.5	417.8	417.1	416.3	414.8	412.6	410.4	408.1	405.9	405.4
15°	411.0	410.1	409.1	408.2	407.3	405.3	402.3	399.4	396.4	393.5	391.8
17.5°	401.0	399.5	398.0	396.6	395.1	392.5	388.7	385.0	381.2	377.4	375.4
20°	393.5	391.8	390.0	388.2	386.5	383.5	379.1	374.8	370.5	366.1	363.9
22.5°	385.4	383.4	381.4	379.5	377.5	374.1	369.2	364.3	359.5	354.6	351.7
25°	373.2	370.3	367.6	364.8	362.1	357.7	352.0	346.3	340.5	334.8	331.2
27.5°	358.4	355.4	352.4	349.4	346.3	341.6	335.1	328.6	322.2	315.7	311.6
30°	348.1	344.8	341.5	338.2	334.9	329.8	322.8	315.9	308.9	302.0	297.6
32.5°	338.1	334.2	330.4	326.5	322.6	317.2	310.1	303.0	295.9	288.8	283.8
35°	321.5	317.1	312.6	308.2	303.8	297.7	290.1	282.4	274.8	267.2	261.7
37.5°	305.0	300.1	295.2	290.3	285.4	279.0	270.8	262.6	254.5	246.3	240.3
40°	293.3	288.2	282.9	277.7	272.5	265.7	257.3	248.8	240.4	232.0	225.8
42.5°	281.5	276.0	270.4	265.0	259.5	252.4	243.7	235.0	226.3	217.6	211.2
45°	262.9	257.0	251.2	245.4	239.5	232.0	222.9	213.8	204.7	195.5	189.4
47.5°	244.7	238.5	232.4	226.2	220.0	212.2	202.8	193.4	183.9	174.5	168.4
50°	231.5	225.4	219.2	213.0	206.9	199.0	189.4	179.9	170.3	160.7	154.7
52.5°	218.7	212.2	205.9	199.4	193.0	185.0	175.6	166.3	157.0	147.6	141.8
55°	199.8	193.1	186.3	179.5	172.7	164.7	155.2	145.9	136.5	127.1	121.9
57.5°	180.6	173.6	166.6	159.7	152.7	144.7	135.7	126.7	117.7	108.7	103.8
60°	167.4	160.5	153.5	146.5	139.6	131.6	122.7	113.7	104.8	95.8	91.4
62.5°	154.5	147.7	140.7	133.7	126.7	119.0	110.5	101.9	93.4	84.9	80.7
65°	134.9	127.9	120.9	113.8	106.8	99.4	91.5	83.7	75.9	68.0	65.1
67.5°	116.0	109.0	102.0	95.1	88.1	81.0	74.0	67.0	59.9	52.9	51.5
70°	102.9	96.1	89.3	82.6	75.8	69.4	63.4	57.3	51.4	45.4	44.5
72.5°	90.3	83.9	77.3	70.9	64.3	58.7	53.9	49.1	44.3	39.4	38.7
75°	72.0	65.9	59.8	53.7	47.6	43.1	40.1	37.2	34.3	31.3	30.7
77.5°	53.9	48.6	43.2	37.9	32.5	29.2	27.7	26.3	24.9	23.5	23.2
80°	42.6	38.2	33.8	29.4	24.9	22.2	21.4	20.5	19.6	18.8	18.4
82.5°	32.3	28.8	25.4	22.0	18.5	16.4	15.8	15.2	14.6	14.1	13.9
85°	16.8	15.0	13.2	11.4	9.6	8.4	8.2	7.9	7.7	7.4	7.4
87.5°	5.1	4.7	4.4	4.0	3.7	3.7	4.0	4.5	4.8	5.3	5.2
90°	0.4	1.5	2.5	3.5	4.6	6.0	7.9	9.8	11.7	13.7	13.5
92.5°	7.0	7.7	8.4	9.2	10.0	10.6	11.0	11.5	12.0	12.4	12.4
95°	20.3	21.2	22.0	22.9	23.8	24.3	24.5	24.6	24.8	25.0	25.0
97.5°	37.0	37.8	38.6	39.3	40.1	40.6	41.0	41.3	41.7	41.9	41.9
100°	49.5	50.2	50.9	51.7	52.3	52.8	53.0	53.3	53.6	53.8	53.8
102.5°	62.7	63.2	63.7	64.3	64.8	65.3	65.6	66.0	66.3	66.6	66.7
105°	83.9	84.1	84.4	84.6	84.9	85.2	85.3	85.5	85.7	85.8	86.0
107.5°	105.2	105.6	106.0	106.4	106.8	106.9	106.9	106.9	106.9	106.9	107.0
110°	119.0	119.5	120.0	120.5	121.1	121.3	121.3	121.3	121.3	121.3	121.3



TEST NUMBER: P331768-935

CATALOG NUMBER: S122RDIW-S290D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.0	134.5	135.0	135.5	136.0	136.3	136.2	136.1	136.0	136.0	135.8
115°	156.0	156.5	157.0	157.6	158.1	158.3	158.1	157.9	157.7	157.6	157.5
117.5°	178.1	178.7	179.4	180.1	180.8	180.9	180.5	179.9	179.4	179.0	178.7
120°	192.7	193.4	194.1	194.8	195.4	195.4	194.8	194.1	193.4	192.7	192.7
122.5°	206.1	207.0	207.8	208.6	209.5	209.7	209.1	208.6	208.2	207.7	207.5
125°	227.0	227.8	228.6	229.4	230.1	230.4	230.1	229.9	229.6	229.4	229.1
127.5°	247.4	248.4	249.3	250.4	251.3	251.7	251.4	251.1	250.7	250.5	250.1
130°	260.2	261.3	262.4	263.6	264.7	265.2	265.0	264.8	264.7	264.5	264.3
132.5°	274.6	275.4	276.4	277.3	278.2	278.7	278.7	278.8	278.8	278.8	278.4
135°	293.8	294.7	295.7	296.6	297.6	298.1	298.3	298.4	298.6	298.8	298.7
137.5°	313.9	314.7	315.5	316.2	317.0	317.5	317.8	318.1	318.2	318.5	318.4
140°	326.1	326.9	327.7	328.5	329.2	329.8	330.3	330.7	331.1	331.6	331.6
142.5°	338.6	339.4	340.2	341.0	341.7	342.2	342.5	342.9	343.1	343.5	343.5
145°	356.5	357.1	357.7	358.3	359.0	359.6	360.1	360.6	361.1	361.6	361.7
147.5°	372.6	373.2	374.0	374.7	375.5	376.0	376.3	376.7	377.0	377.4	377.5
150°	383.5	384.0	384.5	385.0	385.6	386.0	386.3	386.7	387.0	387.4	387.6
152.5°	393.1	393.6	394.2	394.7	395.2	395.7	396.1	396.5	396.9	397.4	397.7
155°	407.6	407.9	408.1	408.5	408.7	409.0	409.2	409.5	409.7	410.0	410.4
157.5°	420.1	420.3	420.4	420.6	420.8	420.9	421.0	421.2	421.4	421.5	422.1
160°	427.6	427.7	427.9	428.1	428.3	428.3	428.4	428.5	428.6	428.7	429.2
162.5°	434.4	434.5	434.5	434.5	434.5	434.6	434.7	434.8	434.9	435.0	435.5
165°	443.5	443.4	443.3	443.2	443.2	443.2	443.2	443.2	443.2	443.2	443.8
167.5°	451.2	450.9	450.6	450.4	450.1	450.0	450.0	450.0	450.0	450.0	450.6
170°	455.2	455.0	454.7	454.4	454.2	454.0	453.9	453.8	453.7	453.7	454.3
172.5°	458.1	457.8	457.5	457.3	457.0	456.8	456.8	456.7	456.6	456.5	457.1
175°	461.5	461.2	461.0	460.7	460.5	460.2	460.0	459.9	459.7	459.5	460.1
177.5°	462.9	462.7	462.4	462.3	462.0	461.8	461.8	461.6	461.4	461.3	461.8
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331768-935

CATALOG NUMBER: S122RDIW-S290D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	430.2	430.8	431.5	431.8	431.7	431.5	431.4	431.3
5°	426.7	427.5	428.3	428.5	428.3	428.0	427.7	427.5
7.5°	419.8	420.1	420.3	420.2	419.7	419.2	418.8	418.4
10°	412.9	412.7	412.4	412.0	411.5	411.0	410.4	409.9
12.5°	405.0	404.5	404.1	403.4	402.5	401.7	400.8	399.9
15°	390.2	388.5	386.8	385.6	384.8	383.8	383.0	382.1
17.5°	373.4	371.4	369.5	367.8	366.3	364.8	363.3	361.8
20°	361.8	359.6	357.4	355.3	353.4	351.5	349.7	347.8
22.5°	349.0	346.1	343.4	341.2	339.8	338.4	336.9	335.5
25°	327.7	324.1	320.6	318.1	316.8	315.5	314.2	312.9
27.5°	307.4	303.2	299.1	296.0	293.9	291.9	289.8	287.7
30°	293.1	288.7	284.2	280.9	278.4	276.1	273.8	271.5
32.5°	278.7	273.6	268.5	264.9	262.8	260.5	258.3	256.1
35°	256.2	250.7	245.2	241.5	239.6	237.7	235.8	233.9
37.5°	234.3	228.3	222.2	218.1	215.9	213.7	211.5	209.3
40°	219.6	213.4	207.2	203.0	200.8	198.5	196.2	194.0
42.5°	204.7	198.4	192.0	187.8	185.5	183.4	181.2	179.0
45°	183.2	177.0	170.9	166.8	164.7	162.6	160.5	158.4
47.5°	162.2	156.1	150.0	145.9	144.0	142.2	140.3	138.4
50°	148.8	142.8	136.7	132.9	131.0	129.2	127.3	125.5
52.5°	136.0	130.3	124.5	120.7	119.1	117.4	115.6	114.0
55°	116.7	111.5	106.2	102.8	101.2	99.5	97.9	96.3
57.5°	99.1	94.3	89.5	86.4	85.1	83.7	82.3	80.8
60°	87.0	82.6	78.1	75.2	73.8	72.4	71.0	69.7
62.5°	76.5	72.2	68.0	65.4	64.6	63.8	62.9	62.1
65°	62.2	59.2	56.2	54.6	54.3	54.1	53.8	53.6
67.5°	50.2	48.8	47.4	46.7	46.3	46.1	45.8	45.5
70°	43.7	42.8	41.9	41.3	40.9	40.6	40.2	39.9
72.5°	38.0	37.2	36.5	36.1	35.8	35.6	35.4	35.2
75°	30.0	29.4	28.8	28.5	28.4	28.3	28.2	28.2
77.5°	22.7	22.4	22.0	21.9	21.7	21.5	21.4	21.3
80°	18.1	17.7	17.4	17.2	17.2	17.2	17.2	17.2
82.5°	13.7	13.4	13.3	13.2	13.2	13.2	13.2	13.2
85°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
87.5°	5.0	4.9	4.8	4.7	4.8	4.8	4.8	4.8
90°	13.3	13.2	13.0	12.9	13.0	13.1	13.2	13.3
92.5°	12.5	12.5	12.6	12.6	12.6	12.6	12.7	12.7
95°	25.0	25.0	25.0	24.9	24.7	24.5	24.4	24.2
97.5°	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9
100°	53.8	53.8	53.8	53.8	53.7	53.6	53.6	53.5
102.5°	66.7	66.8	66.9	66.9	66.8	66.7	66.6	66.6
105°	86.2	86.4	86.5	86.6	86.6	86.6	86.6	86.6
107.5°	107.1	107.2	107.3	107.1	106.7	106.2	105.9	105.5
110°	121.3	121.3	121.3	121.1	120.9	120.6	120.4	120.1



TEST NUMBER: P331768-935

CATALOG NUMBER: S122RDIW-S290D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	135.6	135.3	135.2	134.9	134.7	134.6	134.4	134.2
115°	157.4	157.3	157.2	157.0	156.8	156.5	156.3	156.0
117.5°	178.6	178.3	178.1	177.9	177.6	177.4	177.1	176.8
120°	192.7	192.7	192.7	192.6	192.3	192.1	191.8	191.6
122.5°	207.2	207.1	206.8	206.6	206.5	206.3	206.0	205.9
125°	228.9	228.6	228.3	228.2	228.1	228.0	227.9	227.8
127.5°	249.8	249.5	249.2	248.9	248.6	248.3	248.1	247.8
130°	264.2	264.0	263.8	263.6	263.2	262.9	262.5	262.2
132.5°	278.1	277.7	277.3	277.0	276.7	276.4	276.1	275.9
135°	298.6	298.5	298.4	298.3	298.0	297.7	297.5	297.2
137.5°	318.3	318.2	318.2	318.0	317.6	317.3	316.9	316.6
140°	331.6	331.6	331.6	331.4	331.1	330.7	330.4	330.0
142.5°	343.5	343.6	343.7	343.5	343.2	342.9	342.5	342.2
145°	361.8	361.9	362.0	361.8	361.4	361.1	360.8	360.4
147.5°	377.7	378.0	378.2	378.1	377.7	377.4	377.0	376.8
150°	387.9	388.1	388.4	388.4	388.1	387.9	387.6	387.4
152.5°	398.0	398.3	398.6	398.6	398.3	398.0	397.7	397.4
155°	410.9	411.3	411.7	411.8	411.6	411.3	411.0	410.8
157.5°	422.7	423.3	423.9	424.0	423.5	423.1	422.8	422.3
160°	429.7	430.2	430.8	430.8	430.5	430.2	429.8	429.5
162.5°	436.1	436.7	437.3	437.4	437.0	436.5	436.1	435.8
165°	444.4	445.0	445.6	445.7	445.2	444.8	444.4	443.9
167.5°	451.2	451.8	452.4	452.5	451.9	451.5	451.1	450.6
170°	454.9	455.5	456.1	456.2	455.6	455.1	454.6	454.1
172.5°	457.7	458.3	458.9	458.9	458.4	457.9	457.4	456.8
175°	460.7	461.3	461.9	462.0	461.5	461.0	460.5	459.9
177.5°	462.2	462.5	463.0	463.0	462.5	462.2	461.8	461.3
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3

(END OF REPORT)