

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331804-935

Luminaire Tested: **S122RDIW-S485D1440U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331804-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1440U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5768.5 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331804-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331804-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	21	20	18	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16	12
6	60	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	11	9
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11472	11472	11472
5°	11515	11329	11391
10°	11429	11144	11049
15°	11296	10813	10502
20°	11115	10340	9821
25°	10929	9805	9164
30°	10670	9257	8321
35°	10419	8657	7579
40°	10163	8037	6721
45°	9866	7341	5948
50°	9560	6636	5184
55°	9250	5883	4453
60°	8887	5089	3694
65°	8478	4271	3366
70°	7983	3522	3097
75°	7380	3206	2888
80°	6518	2864	2631
85°	5113	2260	2260



TEST NUMBER: P331804-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	1.2
10°-20°	182.6	3.2
20°-30°	256.4	4.4
30°-40°	279.6	4.8
40°-50°	257.1	4.5
50°-60°	201.9	3.5
60°-70°	131.7	2.3
70°-80°	67.9	1.2
80°-90°	23.7	0.4
90°-100°	97.5	1.7
100°-110°	302.7	5.2
110°-120°	517.4	9.0
120°-130°	680.4	11.8
130°-140°	763.7	13.2
140°-150°	748.8	13.0
150°-160°	628.1	10.9
160°-170°	416.6	7.2
170°-180°	145.6	2.5
0°-30°	505.6	8.8
0°-40°	785.2	13.6
0°-60°	1244.3	21.6
0°-90°	1467.6	25.4
90°-120°	917.6	15.9
90°-150°	3110.6	53.9
90°-180°	4301.0	74.6
0°-180°	5768.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	710	710	710	710	710	
5°	710	707	699	704	703	67
15°	676	668	647	635	628	190
25°	614	592	550	525	514	282
35°	529	494	439	400	384	331
45°	432	388	322	278	260	334
55°	329	277	209	172	158	293
65°	222	169	112	91	88	220
75°	118	75	51	47	46	125
85°	28	15	12	12	12	33
90°	1	18	46	43	44	5
95°	68	80	83	83	80	77
105°	279	283	286	288	288	295
115°	519	526	524	523	519	513
125°	755	766	763	759	758	675
135°	977	991	994	993	989	755
145°	1186	1195	1203	1204	1199	741
155°	1356	1360	1364	1370	1367	624
165°	1476	1475	1474	1483	1477	416
175°	1536	1532	1529	1537	1530	146
180°	1538	1538	1538	1538	1538	



TEST NUMBER: P331804-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	713.1	712.6	712.0	711.4	710.8	709.9	708.7	707.4	706.1	704.9	706.0
5°	710.5	709.8	709.1	708.4	707.7	706.4	704.6	702.7	700.9	699.0	700.3
7.5°	703.2	702.3	701.5	700.5	699.6	698.1	695.9	693.8	691.6	689.5	689.8
10°	697.1	696.0	695.0	694.1	693.0	691.1	688.3	685.4	682.5	679.7	679.2
12.5°	689.3	688.1	686.8	685.6	684.4	682.0	678.3	674.7	671.0	667.4	666.6
15°	675.8	674.2	672.7	671.1	669.5	666.3	661.4	656.6	651.8	646.9	644.2
17.5°	659.3	656.9	654.4	652.0	649.6	645.3	639.1	632.8	626.6	620.4	617.2
20°	646.9	644.0	641.2	638.3	635.4	630.4	623.3	616.1	609.0	601.8	598.3
22.5°	633.5	630.3	627.1	623.9	620.7	615.1	607.0	598.9	590.9	582.8	578.2
25°	613.5	608.9	604.3	599.7	595.1	588.1	578.7	569.3	559.8	550.4	544.6
27.5°	589.3	584.3	579.3	574.4	569.4	561.5	551.0	540.3	529.7	519.0	512.2
30°	572.3	566.9	561.5	556.0	550.6	542.2	530.7	519.3	507.8	496.5	489.1
32.5°	555.9	549.5	543.1	536.8	530.5	521.4	509.8	498.1	486.5	474.8	466.5
35°	528.6	521.2	514.0	506.7	499.4	489.5	476.9	464.3	451.8	439.2	430.2
37.5°	501.3	493.3	485.3	477.3	469.3	458.6	445.2	431.8	418.4	405.0	395.0
40°	482.2	473.7	465.1	456.6	448.0	436.8	422.9	409.1	395.2	381.3	371.2
42.5°	462.7	453.7	444.6	435.7	426.6	414.9	400.6	386.2	372.0	357.7	347.2
45°	432.1	422.6	412.9	403.4	393.8	381.5	366.5	351.5	336.5	321.5	311.3
47.5°	402.3	392.1	382.0	371.9	361.7	348.9	333.4	317.9	302.4	286.9	276.8
50°	380.6	370.5	360.4	350.3	340.1	327.2	311.4	295.8	280.0	264.2	254.4
52.5°	359.6	349.0	338.4	327.8	317.2	304.2	288.8	273.5	258.0	242.7	233.2
55°	328.6	317.5	306.3	295.2	284.0	270.7	255.3	239.9	224.4	209.0	200.4
57.5°	296.8	285.4	274.0	262.5	251.1	238.0	223.2	208.3	193.5	178.7	170.7
60°	275.2	263.8	252.4	240.9	229.5	216.5	201.7	187.0	172.3	157.6	150.2
62.5°	254.1	242.7	231.3	219.8	208.4	195.7	181.7	167.6	153.6	139.6	132.6
65°	221.9	210.3	198.7	187.1	175.6	163.3	150.5	137.6	124.8	111.8	107.0
67.5°	190.7	179.3	167.7	156.3	144.7	133.2	121.7	110.1	98.5	87.0	84.7
70°	169.1	158.0	146.8	135.7	124.5	114.0	104.2	94.3	84.5	74.6	73.2
72.5°	148.5	137.8	127.2	116.5	105.8	96.5	88.6	80.7	72.8	64.8	63.6
75°	118.3	108.3	98.3	88.3	78.3	70.9	66.0	61.1	56.3	51.4	50.5
77.5°	88.6	79.8	71.0	62.3	53.6	48.0	45.6	43.3	40.9	38.6	38.0
80°	70.1	62.8	55.5	48.2	40.9	36.6	35.1	33.8	32.3	30.8	30.3
82.5°	53.1	47.4	41.8	36.1	30.4	27.0	26.1	25.1	24.1	23.2	22.8
85°	27.6	24.6	21.6	18.7	15.7	13.9	13.5	13.1	12.7	12.2	12.2
87.5°	8.5	8.3	8.0	7.8	7.6	8.1	9.4	10.7	12.0	13.2	13.0
90°	1.3	4.7	8.2	11.7	15.2	20.1	26.4	32.7	39.1	45.5	44.9
92.5°	23.1	25.7	28.2	30.7	33.2	35.3	36.8	38.3	39.8	41.2	41.4
95°	67.5	70.3	73.3	76.1	79.0	80.8	81.4	81.9	82.5	83.1	83.1
97.5°	123.3	125.9	128.4	131.0	133.5	135.3	136.4	137.5	138.5	139.7	139.7
100°	164.9	167.1	169.4	171.8	174.1	175.6	176.5	177.4	178.2	179.1	179.1
102.5°	208.4	210.3	212.2	214.0	215.9	217.3	218.4	219.5	220.6	221.7	222.0
105°	279.1	279.9	280.8	281.6	282.5	283.3	283.9	284.4	285.0	285.6	286.1
107.5°	350.2	351.5	352.8	354.0	355.2	355.9	355.9	355.9	355.9	355.9	356.1
110°	395.9	397.6	399.3	401.1	402.8	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P331804-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	445.7	447.5	449.2	450.9	452.6	453.4	453.1	453.0	452.7	452.5	451.8
115°	519.2	520.9	522.6	524.4	526.2	526.7	526.2	525.6	525.0	524.4	524.1
117.5°	592.5	594.7	597.0	599.3	601.7	602.0	600.4	598.7	597.1	595.6	594.9
120°	641.2	643.5	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2	641.2
122.5°	685.9	688.6	691.4	694.1	697.0	697.5	695.9	694.3	692.7	691.0	690.3
125°	755.4	758.0	760.6	763.2	765.9	766.7	765.9	765.0	764.1	763.2	762.3
127.5°	823.2	826.5	829.7	833.1	836.4	837.5	836.5	835.4	834.4	833.4	832.2
130°	865.7	869.5	873.3	877.0	880.8	882.4	881.8	881.2	880.6	880.0	879.5
132.5°	913.5	916.6	919.6	922.7	925.7	927.4	927.5	927.6	927.7	927.8	926.5
135°	977.4	980.6	983.8	986.9	990.1	992.0	992.6	993.2	993.7	994.3	994.0
137.5°	1044.7	1047.2	1049.8	1052.4	1055.0	1056.7	1057.5	1058.2	1058.9	1059.7	1059.5
140°	1085.1	1087.7	1090.4	1093.0	1095.5	1097.5	1099.0	1100.4	1101.9	1103.3	1103.3
142.5°	1126.7	1129.3	1131.9	1134.5	1137.0	1138.8	1139.8	1140.8	1141.8	1142.8	1143.0
145°	1186.4	1188.4	1190.4	1192.4	1194.5	1196.4	1198.1	1199.8	1201.5	1203.2	1203.5
147.5°	1239.6	1242.0	1244.4	1246.9	1249.3	1251.1	1252.2	1253.4	1254.6	1255.7	1256.4
150°	1275.9	1277.6	1279.4	1281.2	1282.9	1284.3	1285.5	1286.6	1287.8	1288.9	1289.8
152.5°	1308.1	1309.8	1311.6	1313.3	1315.1	1316.6	1318.0	1319.4	1320.8	1322.2	1323.3
155°	1356.4	1357.3	1358.1	1359.0	1359.9	1360.7	1361.6	1362.4	1363.3	1364.2	1365.6
157.5°	1397.7	1398.3	1398.9	1399.5	1400.0	1400.6	1401.1	1401.6	1402.1	1402.7	1404.5
160°	1422.6	1423.2	1423.7	1424.4	1425.0	1425.4	1425.6	1425.9	1426.2	1426.5	1428.2
162.5°	1445.4	1445.6	1445.7	1445.8	1446.0	1446.1	1446.4	1446.7	1447.0	1447.3	1449.2
165°	1475.8	1475.6	1475.2	1475.0	1474.7	1474.5	1474.5	1474.5	1474.5	1474.5	1476.5
167.5°	1501.2	1500.4	1499.5	1498.7	1497.8	1497.4	1497.3	1497.3	1497.2	1497.1	1499.2
170°	1514.8	1513.9	1513.0	1512.2	1511.3	1510.7	1510.5	1510.2	1509.8	1509.6	1511.6
172.5°	1524.1	1523.3	1522.4	1521.6	1520.7	1520.1	1519.8	1519.5	1519.2	1518.9	1521.0
175°	1535.5	1534.6	1533.8	1532.9	1532.1	1531.4	1530.8	1530.2	1529.7	1529.0	1531.1
177.5°	1540.2	1539.6	1538.9	1538.2	1537.5	1536.9	1536.4	1535.9	1535.5	1535.0	1536.4
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331804-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	707.1	708.3	709.5	709.9	709.7	709.5	709.2	709.0
5°	701.5	702.8	704.1	704.6	704.1	703.7	703.3	702.8
7.5°	690.2	690.5	691.0	690.8	690.0	689.2	688.5	687.8
10°	678.8	678.4	678.0	677.3	676.5	675.6	674.8	673.9
12.5°	665.8	665.0	664.3	663.1	661.7	660.3	658.8	657.5
15°	641.4	638.8	636.0	634.0	632.5	631.1	629.6	628.3
17.5°	613.9	610.7	607.4	604.6	602.2	599.7	597.3	594.8
20°	594.7	591.2	587.5	584.2	581.1	577.9	574.8	571.6
22.5°	573.6	569.0	564.5	560.9	558.6	556.3	554.0	551.6
25°	538.7	532.9	527.0	523.0	520.8	518.7	516.6	514.4
27.5°	505.4	498.5	491.7	486.6	483.2	479.8	476.4	473.0
30°	481.8	474.6	467.3	461.7	457.8	454.0	450.1	446.3
32.5°	458.1	449.9	441.5	435.6	432.0	428.3	424.6	421.0
35°	421.2	412.2	403.2	397.1	394.0	390.8	387.7	384.5
37.5°	385.1	375.2	365.3	358.5	355.0	351.4	347.8	344.1
40°	361.0	350.9	340.7	333.8	330.1	326.4	322.6	318.9
42.5°	336.7	326.1	315.7	308.7	305.1	301.4	297.8	294.2
45°	301.2	291.1	280.9	274.1	270.7	267.3	263.8	260.5
47.5°	266.7	256.7	246.6	240.0	236.9	233.8	230.6	227.5
50°	244.5	234.7	224.8	218.4	215.4	212.4	209.4	206.4
52.5°	223.6	214.1	204.6	198.5	195.7	193.0	190.1	187.4
55°	191.8	183.2	174.7	169.0	166.3	163.6	160.9	158.2
57.5°	162.9	155.1	147.2	142.2	139.8	137.6	135.3	132.9
60°	142.9	135.7	128.4	123.6	121.3	119.0	116.8	114.4
62.5°	125.6	118.7	111.8	107.6	106.2	104.9	103.5	102.1
65°	102.2	97.3	92.5	89.8	89.4	88.9	88.5	88.1
67.5°	82.5	80.2	78.0	76.7	76.2	75.8	75.3	74.8
70°	71.7	70.3	68.9	67.8	67.3	66.7	66.1	65.6
72.5°	62.4	61.2	60.0	59.2	58.9	58.5	58.2	57.9
75°	49.4	48.5	47.4	46.8	46.8	46.6	46.4	46.3
77.5°	37.5	36.9	36.3	35.9	35.6	35.5	35.2	35.0
80°	29.7	29.2	28.6	28.3	28.3	28.3	28.3	28.3
82.5°	22.5	22.1	21.8	21.6	21.6	21.6	21.6	21.6
85°	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
87.5°	12.7	12.5	12.3	12.2	12.2	12.3	12.4	12.4
90°	44.3	43.7	43.1	43.0	43.3	43.6	43.8	44.2
92.5°	41.5	41.6	41.8	41.8	41.8	41.9	42.0	42.0
95°	83.1	83.1	83.1	82.7	82.2	81.6	81.0	80.5
97.5°	139.7	139.7	139.7	139.7	139.6	139.5	139.5	139.4
100°	179.1	179.1	179.1	179.0	178.7	178.4	178.1	177.8
102.5°	222.1	222.4	222.7	222.6	222.3	222.1	221.7	221.4
105°	286.7	287.3	287.8	288.2	288.2	288.2	288.2	288.2
107.5°	356.4	356.6	356.8	356.3	355.0	353.6	352.3	350.9
110°	403.7	403.7	403.7	403.2	402.3	401.5	400.6	399.8



TEST NUMBER: P331804-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	451.1	450.4	449.7	449.0	448.4	447.8	447.1	446.5
115°	523.8	523.5	523.2	522.6	521.8	520.9	520.0	519.2
117.5°	594.2	593.5	592.8	591.9	591.1	590.2	589.4	588.5
120°	641.2	641.2	641.2	640.8	639.9	639.0	638.2	637.3
122.5°	689.7	689.0	688.3	687.6	687.0	686.4	685.7	685.1
125°	761.5	760.6	759.7	759.2	758.9	758.6	758.4	758.0
127.5°	831.2	830.2	829.1	828.2	827.2	826.3	825.4	824.5
130°	878.9	878.3	877.7	876.8	875.7	874.6	873.4	872.3
132.5°	925.3	924.0	922.7	921.6	920.8	919.8	918.9	917.9
135°	993.7	993.4	993.2	992.6	991.7	990.8	990.0	989.1
137.5°	1059.2	1059.0	1058.8	1058.1	1057.0	1055.8	1054.6	1053.4
140°	1103.3	1103.3	1103.3	1102.8	1101.6	1100.4	1099.2	1098.1
142.5°	1143.2	1143.5	1143.7	1143.2	1142.1	1140.9	1139.8	1138.6
145°	1203.9	1204.1	1204.4	1203.9	1202.8	1201.7	1200.5	1199.4
147.5°	1257.0	1257.6	1258.3	1258.0	1256.9	1255.8	1254.7	1253.6
150°	1290.6	1291.5	1292.4	1292.4	1291.5	1290.6	1289.8	1288.9
152.5°	1324.3	1325.4	1326.5	1326.5	1325.4	1324.3	1323.3	1322.2
155°	1367.1	1368.6	1369.9	1370.3	1369.4	1368.6	1367.7	1366.8
157.5°	1406.5	1408.5	1410.5	1410.7	1409.4	1408.0	1406.6	1405.2
160°	1429.9	1431.7	1433.4	1433.7	1432.5	1431.4	1430.3	1429.1
162.5°	1451.2	1453.2	1455.1	1455.4	1454.1	1452.7	1451.3	1449.8
165°	1478.6	1480.6	1482.6	1482.9	1481.4	1480.1	1478.6	1477.1
167.5°	1501.2	1503.2	1505.2	1505.5	1504.0	1502.4	1501.0	1499.4
170°	1513.6	1515.6	1517.7	1517.8	1516.0	1514.3	1512.6	1510.9
172.5°	1522.9	1525.0	1527.0	1527.2	1525.4	1523.7	1522.0	1520.3
175°	1533.1	1535.1	1537.1	1537.3	1535.5	1533.8	1532.1	1530.3
177.5°	1537.8	1539.2	1540.6	1540.6	1539.2	1537.8	1536.4	1535.0
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2

(END OF REPORT)