

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331785-935

Luminaire Tested: **S122RDIW-S485D435U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331785-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D435U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3090.9 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84		70	70	70		58	58	58	52
1	99	95	91	88	91	88	85	82	75	73	71		63	62	60		52	51	50	45
2	91	84	78	73	84	78	73	69	67	63	60		57	54	52		47	45	44	39
3	83	75	68	62	77	69	63	59	60	55	52		51	48	45		42	40	38	34
4	77	67	59	53	71	62	56	51	54	49	45		46	42	39		39	36	34	30
5	71	60	52	46	66	56	49	44	49	43	39		42	38	35		35	32	30	27
6	66	54	46	41	61	51	44	39	44	39	35		38	34	31		32	29	27	24
7	61	49	42	36	56	46	39	35	40	35	31		35	31	28		30	27	24	22
8	57	45	38	32	53	42	36	31	37	32	28		32	28	25		28	25	22	20
9	53	41	34	29	49	39	32	28	34	29	25		30	26	23		26	23	20	18
10	50	38	31	27	46	36	30	25	32	27	23		28	24	21		24	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14941	14941	14941	14941
5°	16686	15034	13331	15034
10°	18513	14929	11555	14929
15°	19423	14710	9105	14710
20°	16838	14385	7878	14385
25°	11043	13942	7035	13942
30°	7433	13403	6367	13403
35°	6022	12727	5742	12727
40°	5354	11989	5313	11989
45°	4845	11125	4743	11125
50°	4411	10263	4393	10263
55°	4144	9315	4090	9315
60°	3468	8441	3426	8441
65°	2923	7664	3316	7664
70°	2705	6845	3125	6845
75°	2533	5958	2888	5958
80°	2334	4900	2566	4900
85°	2130	3872	2260	3872



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	2.8
10°-20°	244.4	7.9
20°-30°	315.0	10.2
30°-40°	299.3	9.7
40°-50°	256.4	8.3
50°-60°	195.3	6.3
60°-70°	123.4	4.0
70°-80°	61.6	2.0
80°-90°	17.3	0.6
90°-100°	17.0	0.5
100°-110°	62.2	2.0
110°-120°	166.3	5.4
120°-130°	274.5	8.9
130°-140°	291.9	9.4
140°-150°	271.3	8.8
150°-160°	218.2	7.1
160°-170°	140.6	4.5
170°-180°	48.4	1.6
0°-30°	647.1	20.9
0°-40°	946.4	30.6
0°-60°	1398.1	45.2
0°-90°	1600.5	51.8
90°-120°	245.5	7.9
90°-150°	1083.3	35.0
90°-180°	1490.0	48.2
0°-180°	3090.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	925	925	925	925	925	
5°	1030	928	822	928	1030	102
15°	1162	880	545	880	1162	313
25°	620	783	395	783	620	294
35°	306	646	291	646	306	195
45°	212	487	208	487	212	164
55°	147	331	145	331	147	129
65°	76	201	87	201	76	78
75°	41	96	46	96	41	43
85°	12	21	12	21	12	13
90°	10	0	10	0	10	5
95°	16	24	16	24	16	15
105°	28	112	28	112	28	29
115°	30	212	30	212	30	76
125°	315	299	315	299	315	272
135°	382	370	382	370	382	295
145°	436	430	436	430	436	273
155°	473	473	473	473	473	218
165°	497	498	497	498	497	140
175°	507	510	507	510	507	48
180°	509	509	509	509	509	



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	962.9	963.7	964.5	962.7	962.7	961.1	957.8	955.2	948.0	946.9	946.9
5°	1029.5	1028.9	1030.2	1026.0	1020.2	1018.9	1012.8	1004.8	996.4	987.1	985.2
7.5°	1095.8	1094.8	1092.3	1091.5	1087.1	1077.4	1067.6	1057.0	1043.2	1029.6	1022.8
10°	1129.2	1139.8	1133.4	1122.1	1124.4	1109.3	1101.2	1087.4	1075.8	1055.6	1051.1
12.5°	1162.1	1166.3	1164.2	1157.9	1155.0	1144.5	1133.7	1121.6	1100.3	1082.1	1066.3
15°	1162.0	1168.1	1169.8	1167.8	1169.4	1168.7	1163.0	1153.0	1134.4	1114.4	1097.1
17.5°	1076.2	1080.5	1091.0	1098.1	1107.2	1126.2	1135.6	1139.3	1136.4	1125.1	1112.8
20°	980.0	972.9	1002.5	1017.6	1030.5	1062.6	1090.3	1100.9	1117.9	1117.7	1114.4
22.5°	843.7	845.3	873.4	891.3	928.9	961.0	992.6	1032.5	1065.5	1087.3	1100.0
25°	619.9	632.1	660.1	684.5	726.3	786.2	840.5	903.5	962.9	1010.0	1054.6
27.5°	465.5	466.5	488.6	511.3	536.1	585.0	653.5	728.8	813.6	883.5	964.0
30°	398.7	396.7	406.1	419.9	441.2	479.1	530.5	604.5	689.1	794.5	888.4
32.5°	351.4	351.5	358.5	368.8	386.3	411.9	447.2	507.2	587.2	690.9	800.9
35°	305.5	305.1	310.3	317.7	325.0	341.5	365.6	397.1	452.1	548.9	661.4
37.5°	272.5	274.0	276.5	281.1	289.2	298.3	312.9	334.0	373.2	430.4	525.0
40°	254.0	254.7	258.2	262.1	266.9	274.0	285.9	302.9	331.5	377.1	446.3
42.5°	237.0	237.6	240.2	243.7	247.5	254.7	264.5	279.2	302.5	338.0	395.1
45°	212.2	212.2	214.5	216.0	220.2	226.7	234.7	246.9	263.0	289.4	327.4
47.5°	188.9	189.0	190.5	193.2	195.9	200.9	208.8	218.8	230.5	250.9	283.3
50°	175.6	175.9	176.8	179.1	180.7	185.2	191.3	200.0	212.2	228.0	254.9
52.5°	164.7	164.5	165.7	166.8	167.8	171.1	175.6	183.3	194.2	207.9	230.3
55°	147.2	145.9	147.9	149.5	150.5	151.8	154.3	159.2	168.5	180.0	196.7
57.5°	125.4	124.8	126.2	127.7	130.7	134.2	136.4	139.5	144.3	152.6	169.2
60°	107.4	107.4	110.3	111.2	114.8	119.2	123.8	126.4	131.2	136.6	148.9
62.5°	91.4	91.7	93.1	94.0	96.0	101.5	107.9	113.5	118.0	123.3	131.4
65°	76.5	77.1	77.1	77.8	79.1	80.4	82.9	87.5	95.5	102.9	109.0
67.5°	64.9	65.2	65.3	66.0	66.3	67.7	68.7	70.8	72.6	79.6	87.2
70°	57.3	58.2	57.9	58.5	58.8	59.5	60.8	61.7	64.7	66.2	70.8
72.5°	50.0	50.7	50.7	51.1	51.9	52.0	53.0	54.0	55.9	57.3	59.7
75°	40.6	40.2	40.6	41.2	41.5	41.8	41.8	43.0	44.1	45.4	46.9
77.5°	31.3	31.6	31.5	31.6	31.6	32.2	32.1	32.7	33.7	34.4	35.1
80°	25.1	25.4	25.1	25.4	25.7	26.0	25.7	26.0	27.0	27.6	27.6
82.5°	19.5	19.5	19.7	19.7	19.8	19.9	20.3	20.4	21.1	20.9	21.2
85°	11.5	11.3	11.3	11.3	11.5	11.9	11.5	11.5	11.9	11.9	11.9
87.5°	6.1	6.3	6.3	6.3	6.2	6.2	6.1	6.3	5.9	6.1	5.7
90°	9.9	9.8	9.6	9.5	9.3	9.0	8.6	8.2	7.7	7.3	6.7
92.5°	9.9	9.8	9.7	9.6	9.6	9.4	9.2	9.0	8.8	8.5	8.2
95°	15.8	15.9	16.0	16.1	16.2	16.0	15.6	15.2	14.7	14.4	13.8
97.5°	21.1	21.0	20.9	20.8	20.8	20.5	20.2	19.9	19.5	19.2	17.9
100°	24.6	24.5	24.4	24.2	24.0	23.6	22.9	22.3	21.6	21.0	19.5
102.5°	26.4	26.2	26.0	25.7	25.5	25.0	24.1	23.2	22.4	21.5	33.2
105°	28.0	27.6	27.3	26.9	26.7	26.1	25.1	24.3	23.3	22.5	44.8
107.5°	28.8	28.4	28.2	27.8	27.5	27.7	28.7	29.6	30.5	31.4	58.2
110°	29.1	28.8	28.4	28.1	27.7	31.7	39.9	48.0	56.2	64.4	88.0



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	29.4	29.1	28.8	28.6	28.3	43.1	72.9	102.8	132.6	162.5	168.2
115°	30.1	36.1	41.9	47.9	53.7	75.6	113.5	151.4	189.2	227.0	225.0
117.5°	123.2	142.6	161.9	181.2	200.6	214.8	224.0	233.2	242.4	251.5	250.1
120°	224.5	235.5	246.6	257.6	268.6	273.7	272.7	271.7	270.7	269.8	268.3
122.5°	280.1	282.2	284.4	286.5	288.7	289.5	288.9	288.3	287.7	287.1	285.5
125°	314.6	314.4	314.2	313.9	313.7	313.2	312.7	312.1	311.5	311.0	309.4
127.5°	336.4	336.4	336.3	336.3	336.2	335.8	334.9	334.2	333.3	332.4	331.3
130°	350.0	350.1	350.2	350.3	350.3	349.9	349.0	348.1	347.2	346.3	345.4
132.5°	363.3	363.3	363.3	363.4	363.5	363.2	362.4	361.7	360.9	360.2	359.2
135°	382.4	382.5	382.7	382.9	383.0	382.7	381.9	381.1	380.2	379.4	378.7
137.5°	399.8	400.1	400.4	400.6	400.9	400.6	399.8	399.1	398.2	397.4	396.6
140°	410.7	411.1	411.5	411.9	412.3	412.2	411.5	410.7	409.9	409.2	408.3
142.5°	421.3	421.7	422.1	422.5	422.9	422.8	422.1	421.5	420.8	420.1	419.0
145°	436.1	436.5	436.9	437.3	437.7	437.6	437.0	436.5	435.9	435.3	433.9
147.5°	449.1	449.4	449.8	450.1	450.5	450.5	450.0	449.6	449.2	448.8	447.4
150°	457.1	457.4	457.9	458.3	458.7	458.7	458.1	457.7	457.2	456.7	455.4
152.5°	463.8	464.3	464.9	465.5	466.0	466.1	465.5	465.0	464.5	464.1	462.8
155°	473.3	473.9	474.6	475.2	475.9	476.0	475.4	475.0	474.5	474.0	473.0
157.5°	481.9	482.5	483.1	483.8	484.4	484.5	483.9	483.4	482.8	482.2	481.6
160°	486.9	487.4	488.0	488.6	489.1	489.2	488.7	488.2	487.8	487.2	486.7
162.5°	491.0	491.7	492.4	493.1	493.8	493.9	493.4	492.8	492.2	491.6	491.2
165°	497.1	497.7	498.3	498.9	499.5	499.5	498.9	498.3	497.7	497.1	497.0
167.5°	501.1	501.8	502.6	503.3	504.0	504.1	503.5	503.0	502.4	501.8	501.6
170°	503.4	504.2	504.9	505.7	506.4	506.4	505.9	505.3	504.7	504.2	504.0
172.5°	505.2	505.9	506.7	507.4	508.2	508.2	507.6	507.0	506.5	505.9	505.8
175°	506.8	507.6	508.4	509.2	510.1	510.1	509.5	509.0	508.4	507.8	507.6
177.5°	507.7	508.2	508.9	509.5	510.1	510.1	509.6	509.2	508.8	508.2	508.2
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	947.4	945.5	943.7	939.0	936.7	931.5	930.7	930.5	923.9	917.4	915.6
5°	980.0	974.9	967.2	958.1	948.8	939.2	932.7	927.6	914.7	902.5	895.4
7.5°	1012.8	1001.8	988.4	971.4	957.2	941.2	929.4	918.8	900.5	883.0	871.2
10°	1037.2	1019.3	1001.6	978.1	959.8	941.8	925.1	910.6	890.0	866.9	850.4
12.5°	1052.4	1032.6	1008.2	985.3	961.6	938.7	916.3	897.7	873.6	849.6	830.1
15°	1073.0	1051.7	1022.2	989.4	958.8	928.9	903.2	880.0	848.5	819.9	796.1
17.5°	1089.8	1060.5	1028.7	990.8	955.5	917.5	884.3	854.7	819.7	785.1	757.2
20°	1095.1	1066.2	1029.5	991.6	949.8	905.1	869.4	837.2	799.6	762.0	729.9
22.5°	1091.7	1069.3	1028.5	983.1	940.3	893.5	853.3	815.9	774.2	735.8	698.5
25°	1069.1	1061.4	1022.8	973.3	924.4	870.0	823.5	782.6	735.0	693.9	653.3
27.5°	1016.2	1032.9	1008.9	956.1	901.8	843.5	791.2	744.7	695.3	648.9	608.6
30°	965.3	1003.5	993.2	944.3	883.6	826.3	767.5	718.9	666.2	618.6	578.8
32.5°	895.5	958.7	968.8	927.9	865.0	802.1	740.5	692.2	637.1	586.9	548.1
35°	784.5	879.1	922.5	896.4	833.4	765.6	701.9	645.7	590.3	540.8	502.2
37.5°	652.1	780.8	853.3	855.1	797.2	726.7	657.4	601.5	544.8	496.3	454.5
40°	566.2	705.8	800.0	820.9	772.0	695.8	625.7	568.8	513.5	465.9	418.0
42.5°	489.0	628.1	743.9	780.2	741.4	665.7	595.4	535.9	482.1	437.0	388.1
45°	395.5	517.0	644.6	709.6	688.1	617.9	543.7	487.2	436.6	397.7	350.8
47.5°	333.6	419.3	542.8	630.7	630.3	566.3	493.3	439.0	392.2	355.8	317.7
50°	298.3	373.0	477.5	577.1	585.5	531.8	462.4	408.6	365.0	326.7	296.1
52.5°	266.7	328.2	422.1	517.7	541.5	495.0	427.7	378.1	335.6	300.4	274.2
55°	225.4	272.9	344.4	433.8	469.8	437.0	377.1	330.9	296.4	266.9	244.4
57.5°	190.6	226.4	283.6	355.6	397.5	376.9	327.6	290.0	260.5	233.8	216.0
60°	168.8	198.0	246.6	306.8	353.0	338.5	296.4	261.4	236.3	213.2	196.5
62.5°	148.3	173.4	215.0	263.8	306.3	300.2	265.9	236.4	214.5	193.4	179.3
65°	119.2	137.6	170.0	208.4	242.5	245.3	220.6	200.6	181.0	164.3	151.8
67.5°	95.0	106.9	129.8	162.0	187.6	196.7	181.6	166.3	150.8	137.8	127.0
70°	80.1	89.7	106.4	132.5	155.9	165.6	156.9	145.0	131.5	120.9	111.6
72.5°	64.9	74.3	86.6	105.7	125.9	136.3	133.3	124.7	113.7	105.0	96.2
75°	48.9	51.7	60.1	73.0	88.8	97.7	100.0	95.5	86.8	80.1	74.9
77.5°	36.2	37.9	41.8	48.6	58.9	66.9	70.3	69.7	63.7	59.8	55.0
80°	28.9	29.9	31.9	34.7	42.4	50.5	52.7	52.7	48.6	46.9	42.1
82.5°	22.0	22.7	23.8	25.5	29.1	36.1	38.6	39.1	36.4	34.4	30.6
85°	12.6	12.2	12.8	13.9	14.5	16.4	20.2	20.9	20.2	17.7	16.7
87.5°	5.6	5.7	5.6	5.2	5.3	5.3	6.5	7.5	6.7	6.1	5.8
90°	6.0	5.4	4.7	4.0	3.1	2.2	1.3	0.3	1.3	2.2	3.1
92.5°	7.9	7.6	7.2	7.1	7.1	7.2	7.3	7.4	7.3	7.2	7.1
95°	13.2	12.7	12.1	13.1	15.8	18.5	21.2	23.9	21.2	18.5	15.8
97.5°	16.5	15.2	13.9	17.0	24.6	32.3	39.9	47.4	39.9	32.3	24.6
100°	18.2	16.8	15.4	20.3	31.5	42.7	53.9	65.2	53.9	42.7	31.5
102.5°	44.9	56.5	68.1	75.1	77.5	79.8	82.2	84.6	82.2	79.8	77.5
105°	67.1	89.5	111.8	121.7	119.2	116.8	114.3	111.8	114.3	116.8	119.2
107.5°	85.0	111.8	138.5	150.9	149.0	147.0	145.0	143.0	145.0	147.0	149.0
110°	111.7	135.3	158.9	169.9	168.2	166.4	164.7	163.0	164.7	166.4	168.2



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	174.1	179.9	185.8	188.0	186.4	184.9	183.4	181.8	183.4	184.9	186.4
115°	223.0	220.9	218.9	217.1	215.8	214.4	213.0	211.6	213.0	214.4	215.8
117.5°	248.7	247.3	245.9	244.4	242.8	241.3	239.7	238.2	239.7	241.3	242.8
120°	266.8	265.4	263.9	262.5	261.3	260.0	258.8	257.6	258.8	260.0	261.3
122.5°	283.9	282.3	280.7	279.2	277.9	276.6	275.3	274.1	275.3	276.6	277.9
125°	307.9	306.3	304.7	303.4	302.4	301.4	300.2	299.2	300.2	301.4	302.4
127.5°	330.1	329.0	327.8	326.7	325.5	324.3	323.1	321.9	323.1	324.3	325.5
130°	344.5	343.6	342.7	341.6	340.3	339.0	337.7	336.4	337.7	339.0	340.3
132.5°	358.3	357.4	356.5	355.5	354.4	353.3	352.1	351.1	352.1	353.3	354.4
135°	378.0	377.2	376.4	375.5	374.1	372.8	371.5	370.2	371.5	372.8	374.1
137.5°	395.8	394.9	394.1	393.2	392.4	391.4	390.5	389.6	390.5	391.4	392.4
140°	407.4	406.6	405.6	404.8	404.2	403.6	402.9	402.3	402.9	403.6	404.2
142.5°	418.0	417.0	416.0	415.2	414.6	414.0	413.5	412.8	413.5	414.0	414.6
145°	432.6	431.2	429.8	429.1	429.2	429.3	429.4	429.5	429.4	429.3	429.2
147.5°	446.0	444.6	443.2	442.7	443.1	443.3	443.7	443.9	443.7	443.3	443.1
150°	454.1	452.8	451.4	451.1	451.7	452.2	452.8	453.4	452.8	452.2	451.7
152.5°	461.6	460.3	459.1	458.7	459.4	460.0	460.7	461.3	460.7	460.0	459.4
155°	472.0	471.1	470.1	469.9	470.7	471.4	472.2	472.9	472.2	471.4	470.7
157.5°	480.9	480.2	479.5	479.5	480.1	480.7	481.3	481.9	481.3	480.7	480.1
160°	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2	486.7	486.3	485.8
162.5°	490.8	490.3	490.0	490.0	490.5	490.9	491.5	492.0	491.5	490.9	490.5
165°	496.7	496.5	496.2	496.3	496.8	497.3	497.8	498.3	497.8	497.3	496.8
167.5°	501.4	501.1	500.9	501.0	501.5	502.0	502.5	503.0	502.5	502.0	501.5
170°	503.9	503.7	503.5	503.7	504.2	504.6	505.1	505.7	505.1	504.6	504.2
172.5°	505.6	505.4	505.3	505.4	505.9	506.4	507.0	507.4	507.0	506.4	505.9
175°	507.6	507.4	507.2	507.4	508.0	508.5	509.1	509.7	509.1	508.5	508.0
177.5°	508.2	508.1	508.0	508.2	508.7	509.1	509.6	510.1	509.6	509.1	508.7
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	912.2	910.4	907.1	902.0	898.9	893.5	889.8	891.9	892.4	891.9	891.4
5°	887.8	881.0	871.7	862.6	854.3	845.3	840.2	837.9	833.4	830.9	829.6
7.5°	858.1	846.4	833.3	817.6	804.3	790.3	783.2	779.6	770.4	765.4	761.0
10°	835.9	817.6	804.4	783.9	771.4	753.0	740.5	740.8	728.2	721.2	716.0
12.5°	811.6	791.4	769.5	751.0	733.6	718.8	703.7	697.6	684.2	677.4	663.6
15°	771.0	747.5	724.4	699.3	681.7	658.8	637.0	610.3	588.8	570.1	564.9
17.5°	726.8	697.8	674.5	645.1	614.8	576.4	551.0	535.5	522.5	512.7	505.4
20°	696.5	666.8	642.1	597.7	556.9	530.8	512.2	500.3	486.8	476.2	470.4
22.5°	664.5	633.7	599.9	550.4	518.6	497.7	481.0	467.4	458.2	450.0	444.7
25°	619.2	585.5	529.9	495.8	470.1	448.2	436.6	428.3	418.6	407.3	402.3
27.5°	571.4	517.7	477.8	452.5	427.9	413.7	403.3	390.8	382.2	377.1	371.8
30°	535.6	482.0	450.8	423.1	405.8	390.0	377.8	370.7	362.4	353.7	350.2
32.5°	495.8	452.9	423.0	400.0	382.4	368.9	359.3	347.8	341.8	336.5	329.1
35°	446.3	413.8	386.5	367.8	351.1	340.2	328.9	322.2	311.3	306.8	303.8
37.5°	404.3	376.2	355.8	336.1	322.9	310.8	303.9	293.2	288.4	282.1	276.0
40°	380.6	353.0	333.5	317.4	302.6	293.5	284.9	276.2	269.1	266.2	258.8
42.5°	356.5	334.0	314.4	296.8	286.9	277.3	266.4	260.0	252.6	248.0	243.4
45°	323.1	303.2	286.5	272.0	261.1	251.2	244.0	233.4	229.3	219.9	216.0
47.5°	293.8	275.3	259.3	245.6	234.9	228.4	218.1	209.7	203.1	197.3	192.4
50°	272.9	257.5	242.1	229.9	220.2	210.9	200.4	196.1	185.8	183.0	180.0
52.5°	253.9	239.3	225.2	213.2	203.5	194.5	185.1	179.7	172.7	169.8	167.7
55°	227.3	213.2	199.7	189.1	179.4	170.0	164.3	157.6	154.3	152.1	149.5
57.5°	200.5	187.9	177.5	166.8	157.0	149.6	142.9	138.9	135.5	132.6	129.5
60°	183.6	171.3	162.0	152.1	142.2	136.0	130.9	126.1	122.2	117.7	116.4
62.5°	165.6	154.9	146.4	136.6	127.9	122.3	117.5	113.0	108.3	101.8	100.0
65°	140.9	132.5	123.5	115.5	107.7	102.3	95.1	90.1	88.1	87.5	87.1
67.5°	118.5	110.6	102.8	94.6	87.6	82.5	78.9	78.1	76.8	76.4	75.5
70°	103.5	96.2	88.4	80.7	74.0	73.0	71.7	70.4	68.8	68.2	67.5
72.5°	90.1	82.5	74.8	68.6	65.7	64.5	63.2	61.9	60.9	60.2	59.8
75°	69.1	62.1	56.9	54.7	53.0	52.1	50.2	49.2	48.6	47.6	47.3
77.5°	49.8	45.8	43.4	42.0	40.3	39.3	38.2	37.2	36.5	36.3	35.8
80°	38.0	36.0	34.4	32.5	31.9	30.6	30.2	29.3	29.6	28.6	28.6
82.5°	29.4	27.0	25.7	24.8	24.1	23.1	22.7	22.3	22.4	21.7	21.7
85°	15.2	14.5	13.9	13.2	13.2	12.2	12.6	12.2	12.2	11.5	11.3
87.5°	5.7	5.6	5.2	5.3	5.4	5.3	5.4	5.3	5.3	5.4	5.2
90°	4.0	4.7	5.4	6.0	6.7	7.3	7.7	8.2	8.6	9.0	9.3
92.5°	7.1	7.2	7.6	7.9	8.2	8.5	8.8	9.0	9.2	9.4	9.6
95°	13.1	12.1	12.7	13.2	13.8	14.4	14.7	15.2	15.6	16.0	16.2
97.5°	17.0	13.9	15.2	16.5	17.9	19.2	19.5	19.9	20.2	20.5	20.8
100°	20.3	15.4	16.8	18.2	19.5	21.0	21.6	22.3	22.9	23.6	24.0
102.5°	75.1	68.1	56.5	44.9	33.2	21.5	22.4	23.2	24.1	25.0	25.5
105°	121.7	111.8	89.5	67.1	44.8	22.5	23.3	24.3	25.1	26.1	26.7
107.5°	150.9	138.5	111.8	85.0	58.2	31.4	30.5	29.6	28.7	27.7	27.5
110°	169.9	158.9	135.3	111.7	88.0	64.4	56.2	48.0	39.9	31.7	27.7



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	188.0	185.8	179.9	174.1	168.2	162.5	132.6	102.8	72.9	43.1	28.3
115°	217.1	218.9	220.9	223.0	225.0	227.0	189.2	151.4	113.5	75.6	53.7
117.5°	244.4	245.9	247.3	248.7	250.1	251.5	242.4	233.2	224.0	214.8	200.6
120°	262.5	263.9	265.4	266.8	268.3	269.8	270.7	271.7	272.7	273.7	268.6
122.5°	279.2	280.7	282.3	283.9	285.5	287.1	287.7	288.3	288.9	289.5	288.7
125°	303.4	304.7	306.3	307.9	309.4	311.0	311.5	312.1	312.7	313.2	313.7
127.5°	326.7	327.8	329.0	330.1	331.3	332.4	333.3	334.2	334.9	335.8	336.2
130°	341.6	342.7	343.6	344.5	345.4	346.3	347.2	348.1	349.0	349.9	350.3
132.5°	355.5	356.5	357.4	358.3	359.2	360.2	360.9	361.7	362.4	363.2	363.5
135°	375.5	376.4	377.2	378.0	378.7	379.4	380.2	381.1	381.9	382.7	383.0
137.5°	393.2	394.1	394.9	395.8	396.6	397.4	398.2	399.1	399.8	400.6	400.9
140°	404.8	405.6	406.6	407.4	408.3	409.2	409.9	410.7	411.5	412.2	412.3
142.5°	415.2	416.0	417.0	418.0	419.0	420.1	420.8	421.5	422.1	422.8	422.9
145°	429.1	429.8	431.2	432.6	433.9	435.3	435.9	436.5	437.0	437.6	437.7
147.5°	442.7	443.2	444.6	446.0	447.4	448.8	449.2	449.6	450.0	450.5	450.5
150°	451.1	451.4	452.8	454.1	455.4	456.7	457.2	457.7	458.1	458.7	458.7
152.5°	458.7	459.1	460.3	461.6	462.8	464.1	464.5	465.0	465.5	466.1	466.0
155°	469.9	470.1	471.1	472.0	473.0	474.0	474.5	475.0	475.4	476.0	475.9
157.5°	479.5	479.5	480.2	480.9	481.6	482.2	482.8	483.4	483.9	484.5	484.4
160°	485.3	485.3	485.8	486.3	486.7	487.2	487.8	488.2	488.7	489.2	489.1
162.5°	490.0	490.0	490.3	490.8	491.2	491.6	492.2	492.8	493.4	493.9	493.8
165°	496.3	496.2	496.5	496.7	497.0	497.1	497.7	498.3	498.9	499.5	499.5
167.5°	501.0	500.9	501.1	501.4	501.6	501.8	502.4	503.0	503.5	504.1	504.0
170°	503.7	503.5	503.7	503.9	504.0	504.2	504.7	505.3	505.9	506.4	506.4
172.5°	505.4	505.3	505.4	505.6	505.8	505.9	506.5	507.0	507.6	508.2	508.2
175°	507.4	507.2	507.4	507.6	507.6	507.8	508.4	509.0	509.5	510.1	510.1
177.5°	508.2	508.0	508.1	508.2	508.2	508.2	508.8	509.2	509.6	510.1	510.1
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	888.6	889.1	888.3	888.8	888.3	889.1	888.6	891.4	891.9	892.4	891.9
5°	827.9	824.1	823.5	822.5	823.5	824.1	827.9	829.6	830.9	833.4	837.9
7.5°	755.5	754.9	753.4	751.1	753.4	754.9	755.5	761.0	765.4	770.4	779.6
10°	708.9	707.4	707.1	704.8	707.1	707.4	708.9	716.0	721.2	728.2	740.8
12.5°	654.4	644.1	643.0	637.4	643.0	644.1	654.4	663.6	677.4	684.2	697.6
15°	557.2	555.3	548.9	544.7	548.9	555.3	557.2	564.9	570.1	588.8	610.3
17.5°	501.6	495.3	493.4	492.5	493.4	495.3	501.6	505.4	512.7	522.5	535.5
20°	465.9	460.1	459.2	458.5	459.2	460.1	465.9	470.4	476.2	486.8	500.3
22.5°	441.2	435.1	432.7	430.8	432.7	435.1	441.2	444.7	450.0	458.2	467.4
25°	399.0	396.7	395.5	394.9	395.5	396.7	399.0	402.3	407.3	418.6	428.3
27.5°	366.0	361.1	360.1	358.4	360.1	361.1	366.0	371.8	377.1	382.2	390.8
30°	347.2	345.6	343.4	341.5	343.4	345.6	347.2	350.2	353.7	362.4	370.7
32.5°	325.1	323.8	321.8	320.9	321.8	323.8	325.1	329.1	336.5	341.8	347.8
35°	300.7	296.1	294.2	291.3	294.2	296.1	300.7	303.8	306.8	311.3	322.2
37.5°	274.7	272.3	269.7	270.6	269.7	272.3	274.7	276.0	282.1	288.4	293.2
40°	254.7	253.0	252.4	252.1	252.4	253.0	254.7	258.8	266.2	269.1	276.2
42.5°	238.7	234.3	232.6	232.6	232.6	234.3	238.7	243.4	248.0	252.6	260.0
45°	214.5	210.3	207.4	207.7	207.4	210.3	214.5	216.0	219.9	229.3	233.4
47.5°	189.7	189.5	187.7	188.3	187.7	189.5	189.7	192.4	197.3	203.1	209.7
50°	177.8	175.9	174.6	174.9	174.6	175.9	177.8	180.0	183.0	185.8	196.1
52.5°	166.5	164.8	163.8	165.1	163.8	164.8	166.5	167.7	169.8	172.7	179.7
55°	147.9	145.9	145.7	145.3	145.7	145.9	147.9	149.5	152.1	154.3	157.6
57.5°	127.2	125.9	123.9	123.1	123.9	125.9	127.2	129.5	132.6	135.5	138.9
60°	112.2	109.6	106.4	106.1	106.4	109.6	112.2	116.4	117.7	122.2	126.1
62.5°	98.6	98.1	97.5	97.4	97.5	98.1	98.6	100.0	101.8	108.3	113.0
65°	86.5	86.2	86.5	86.8	86.5	86.2	86.5	87.1	87.5	88.1	90.1
67.5°	75.3	74.8	74.2	74.5	74.2	74.8	75.3	75.5	76.4	76.8	78.1
70°	66.9	66.6	66.2	66.2	66.2	66.6	66.9	67.5	68.2	68.8	70.4
72.5°	58.6	58.5	58.3	58.0	58.3	58.5	58.6	59.8	60.2	60.9	61.9
75°	46.9	46.3	46.3	46.3	46.3	46.3	46.9	47.3	47.6	48.6	49.2
77.5°	35.7	35.5	35.1	34.9	35.1	35.5	35.7	35.8	36.3	36.5	37.2
80°	28.3	28.0	27.6	27.6	27.6	28.0	28.3	28.6	28.6	29.6	29.3
82.5°	21.6	21.3	21.2	20.9	21.2	21.3	21.6	21.7	21.7	22.4	22.3
85°	11.5	11.9	11.5	12.2	11.5	11.9	11.5	11.3	11.5	12.2	12.2
87.5°	5.3	5.0	5.3	5.1	5.3	5.0	5.3	5.2	5.4	5.3	5.3
90°	9.5	9.6	9.8	9.9	9.8	9.6	9.5	9.3	9.0	8.6	8.2
92.5°	9.6	9.7	9.8	9.9	9.8	9.7	9.6	9.6	9.4	9.2	9.0
95°	16.1	16.0	15.9	15.8	15.9	16.0	16.1	16.2	16.0	15.6	15.2
97.5°	20.8	20.9	21.0	21.1	21.0	20.9	20.8	20.8	20.5	20.2	19.9
100°	24.2	24.4	24.5	24.6	24.5	24.4	24.2	24.0	23.6	22.9	22.3
102.5°	25.7	26.0	26.2	26.4	26.2	26.0	25.7	25.5	25.0	24.1	23.2
105°	26.9	27.3	27.6	28.0	27.6	27.3	26.9	26.7	26.1	25.1	24.3
107.5°	27.8	28.2	28.4	28.8	28.4	28.2	27.8	27.5	27.7	28.7	29.6
110°	28.1	28.4	28.8	29.1	28.8	28.4	28.1	27.7	31.7	39.9	48.0



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	28.6	28.8	29.1	29.4	29.1	28.8	28.6	28.3	43.1	72.9	102.8
115°	47.9	41.9	36.1	30.1	36.1	41.9	47.9	53.7	75.6	113.5	151.4
117.5°	181.2	161.9	142.6	123.2	142.6	161.9	181.2	200.6	214.8	224.0	233.2
120°	257.6	246.6	235.5	224.5	235.5	246.6	257.6	268.6	273.7	272.7	271.7
122.5°	286.5	284.4	282.2	280.1	282.2	284.4	286.5	288.7	289.5	288.9	288.3
125°	313.9	314.2	314.4	314.6	314.4	314.2	313.9	313.7	313.2	312.7	312.1
127.5°	336.3	336.3	336.4	336.4	336.4	336.3	336.3	336.2	335.8	334.9	334.2
130°	350.3	350.2	350.1	350.0	350.1	350.2	350.3	350.3	349.9	349.0	348.1
132.5°	363.4	363.3	363.3	363.3	363.3	363.3	363.4	363.5	363.2	362.4	361.7
135°	382.9	382.7	382.5	382.4	382.5	382.7	382.9	383.0	382.7	381.9	381.1
137.5°	400.6	400.4	400.1	399.8	400.1	400.4	400.6	400.9	400.6	399.8	399.1
140°	411.9	411.5	411.1	410.7	411.1	411.5	411.9	412.3	412.2	411.5	410.7
142.5°	422.5	422.1	421.7	421.3	421.7	422.1	422.5	422.9	422.8	422.1	421.5
145°	437.3	436.9	436.5	436.1	436.5	436.9	437.3	437.7	437.6	437.0	436.5
147.5°	450.1	449.8	449.4	449.1	449.4	449.8	450.1	450.5	450.5	450.0	449.6
150°	458.3	457.9	457.4	457.1	457.4	457.9	458.3	458.7	458.7	458.1	457.7
152.5°	465.5	464.9	464.3	463.8	464.3	464.9	465.5	466.0	466.1	465.5	465.0
155°	475.2	474.6	473.9	473.3	473.9	474.6	475.2	475.9	476.0	475.4	475.0
157.5°	483.8	483.1	482.5	481.9	482.5	483.1	483.8	484.4	484.5	483.9	483.4
160°	488.6	488.0	487.4	486.9	487.4	488.0	488.6	489.1	489.2	488.7	488.2
162.5°	493.1	492.4	491.7	491.0	491.7	492.4	493.1	493.8	493.9	493.4	492.8
165°	498.9	498.3	497.7	497.1	497.7	498.3	498.9	499.5	499.5	498.9	498.3
167.5°	503.3	502.6	501.8	501.1	501.8	502.6	503.3	504.0	504.1	503.5	503.0
170°	505.7	504.9	504.2	503.4	504.2	504.9	505.7	506.4	506.4	505.9	505.3
172.5°	507.4	506.7	505.9	505.2	505.9	506.7	507.4	508.2	508.2	507.6	507.0
175°	509.2	508.4	507.6	506.8	507.6	508.4	509.2	510.1	510.1	509.5	509.0
177.5°	509.5	508.9	508.2	507.7	508.2	508.9	509.5	510.1	510.1	509.6	509.2
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	889.8	893.5	898.9	902.0	907.1	910.4	912.2	915.6	917.4	923.9	930.5
5°	840.2	845.3	854.3	862.6	871.7	881.0	887.8	895.4	902.5	914.7	927.6
7.5°	783.2	790.3	804.3	817.6	833.3	846.4	858.1	871.2	883.0	900.5	918.8
10°	740.5	753.0	771.4	783.9	804.4	817.6	835.9	850.4	866.9	890.0	910.6
12.5°	703.7	718.8	733.6	751.0	769.5	791.4	811.6	830.1	849.6	873.6	897.7
15°	637.0	658.8	681.7	699.3	724.4	747.5	771.0	796.1	819.9	848.5	880.0
17.5°	551.0	576.4	614.8	645.1	674.5	697.8	726.8	757.2	785.1	819.7	854.7
20°	512.2	530.8	556.9	597.7	642.1	666.8	696.5	729.9	762.0	799.6	837.2
22.5°	481.0	497.7	518.6	550.4	599.9	633.7	664.5	698.5	735.8	774.2	815.9
25°	436.6	448.2	470.1	495.8	529.9	585.5	619.2	653.3	693.9	735.0	782.6
27.5°	403.3	413.7	427.9	452.5	477.8	517.7	571.4	608.6	648.9	695.3	744.7
30°	377.8	390.0	405.8	423.1	450.8	482.0	535.6	578.8	618.6	666.2	718.9
32.5°	359.3	368.9	382.4	400.0	423.0	452.9	495.8	548.1	586.9	637.1	692.2
35°	328.9	340.2	351.1	367.8	386.5	413.8	446.3	502.2	540.8	590.3	645.7
37.5°	303.9	310.8	322.9	336.1	355.8	376.2	404.3	454.5	496.3	544.8	601.5
40°	284.9	293.5	302.6	317.4	333.5	353.0	380.6	418.0	465.9	513.5	568.8
42.5°	266.4	277.3	286.9	296.8	314.4	334.0	356.5	388.1	437.0	482.1	535.9
45°	244.0	251.2	261.1	272.0	286.5	303.2	323.1	350.8	397.7	436.6	487.2
47.5°	218.1	228.4	234.9	245.6	259.3	275.3	293.8	317.7	355.8	392.2	439.0
50°	200.4	210.9	220.2	229.9	242.1	257.5	272.9	296.1	326.7	365.0	408.6
52.5°	185.1	194.5	203.5	213.2	225.2	239.3	253.9	274.2	300.4	335.6	378.1
55°	164.3	170.0	179.4	189.1	199.7	213.2	227.3	244.4	266.9	296.4	330.9
57.5°	142.9	149.6	157.0	166.8	177.5	187.9	200.5	216.0	233.8	260.5	290.0
60°	130.9	136.0	142.2	152.1	162.0	171.3	183.6	196.5	213.2	236.3	261.4
62.5°	117.5	122.3	127.9	136.6	146.4	154.9	165.6	179.3	193.4	214.5	236.4
65°	95.1	102.3	107.7	115.5	123.5	132.5	140.9	151.8	164.3	181.0	200.6
67.5°	78.9	82.5	87.6	94.6	102.8	110.6	118.5	127.0	137.8	150.8	166.3
70°	71.7	73.0	74.0	80.7	88.4	96.2	103.5	111.6	120.9	131.5	145.0
72.5°	63.2	64.5	65.7	68.6	74.8	82.5	90.1	96.2	105.0	113.7	124.7
75°	50.2	52.1	53.0	54.7	56.9	62.1	69.1	74.9	80.1	86.8	95.5
77.5°	38.2	39.3	40.3	42.0	43.4	45.8	49.8	55.0	59.8	63.7	69.7
80°	30.2	30.6	31.9	32.5	34.4	36.0	38.0	42.1	46.9	48.6	52.7
82.5°	22.7	23.1	24.1	24.8	25.7	27.0	29.4	30.6	34.4	36.4	39.1
85°	12.6	12.2	13.2	13.2	13.9	14.5	15.2	16.7	17.7	20.2	20.9
87.5°	5.4	5.3	5.4	5.3	5.2	5.6	5.7	5.8	6.1	6.7	7.5
90°	7.7	7.3	6.7	6.0	5.4	4.7	4.0	3.1	2.2	1.3	0.3
92.5°	8.8	8.5	8.2	7.9	7.6	7.2	7.1	7.1	7.2	7.3	7.4
95°	14.7	14.4	13.8	13.2	12.7	12.1	13.1	15.8	18.5	21.2	23.9
97.5°	19.5	19.2	17.9	16.5	15.2	13.9	17.0	24.6	32.3	39.9	47.4
100°	21.6	21.0	19.5	18.2	16.8	15.4	20.3	31.5	42.7	53.9	65.2
102.5°	22.4	21.5	33.2	44.9	56.5	68.1	75.1	77.5	79.8	82.2	84.6
105°	23.3	22.5	44.8	67.1	89.5	111.8	121.7	119.2	116.8	114.3	111.8
107.5°	30.5	31.4	58.2	85.0	111.8	138.5	150.9	149.0	147.0	145.0	143.0
110°	56.2	64.4	88.0	111.7	135.3	158.9	169.9	168.2	166.4	164.7	163.0



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	132.6	162.5	168.2	174.1	179.9	185.8	188.0	186.4	184.9	183.4	181.8
115°	189.2	227.0	225.0	223.0	220.9	218.9	217.1	215.8	214.4	213.0	211.6
117.5°	242.4	251.5	250.1	248.7	247.3	245.9	244.4	242.8	241.3	239.7	238.2
120°	270.7	269.8	268.3	266.8	265.4	263.9	262.5	261.3	260.0	258.8	257.6
122.5°	287.7	287.1	285.5	283.9	282.3	280.7	279.2	277.9	276.6	275.3	274.1
125°	311.5	311.0	309.4	307.9	306.3	304.7	303.4	302.4	301.4	300.2	299.2
127.5°	333.3	332.4	331.3	330.1	329.0	327.8	326.7	325.5	324.3	323.1	321.9
130°	347.2	346.3	345.4	344.5	343.6	342.7	341.6	340.3	339.0	337.7	336.4
132.5°	360.9	360.2	359.2	358.3	357.4	356.5	355.5	354.4	353.3	352.1	351.1
135°	380.2	379.4	378.7	378.0	377.2	376.4	375.5	374.1	372.8	371.5	370.2
137.5°	398.2	397.4	396.6	395.8	394.9	394.1	393.2	392.4	391.4	390.5	389.6
140°	409.9	409.2	408.3	407.4	406.6	405.6	404.8	404.2	403.6	402.9	402.3
142.5°	420.8	420.1	419.0	418.0	417.0	416.0	415.2	414.6	414.0	413.5	412.8
145°	435.9	435.3	433.9	432.6	431.2	429.8	429.1	429.2	429.3	429.4	429.5
147.5°	449.2	448.8	447.4	446.0	444.6	443.2	442.7	443.1	443.3	443.7	443.9
150°	457.2	456.7	455.4	454.1	452.8	451.4	451.1	451.7	452.2	452.8	453.4
152.5°	464.5	464.1	462.8	461.6	460.3	459.1	458.7	459.4	460.0	460.7	461.3
155°	474.5	474.0	473.0	472.0	471.1	470.1	469.9	470.7	471.4	472.2	472.9
157.5°	482.8	482.2	481.6	480.9	480.2	479.5	479.5	480.1	480.7	481.3	481.9
160°	487.8	487.2	486.7	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2
162.5°	492.2	491.6	491.2	490.8	490.3	490.0	490.0	490.5	490.9	491.5	492.0
165°	497.7	497.1	497.0	496.7	496.5	496.2	496.3	496.8	497.3	497.8	498.3
167.5°	502.4	501.8	501.6	501.4	501.1	500.9	501.0	501.5	502.0	502.5	503.0
170°	504.7	504.2	504.0	503.9	503.7	503.5	503.7	504.2	504.6	505.1	505.7
172.5°	506.5	505.9	505.8	505.6	505.4	505.3	505.4	505.9	506.4	507.0	507.4
175°	508.4	507.8	507.6	507.6	507.4	507.2	507.4	508.0	508.5	509.1	509.7
177.5°	508.8	508.2	508.2	508.2	508.1	508.0	508.2	508.7	509.1	509.6	510.1
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	930.7	931.5	936.7	939.0	943.7	945.5	947.4	946.9	946.9	948.0	955.2
5°	932.7	939.2	948.8	958.1	967.2	974.9	980.0	985.2	987.1	996.4	1004.8
7.5°	929.4	941.2	957.2	971.4	988.4	1001.8	1012.8	1022.8	1029.6	1043.2	1057.0
10°	925.1	941.8	959.8	978.1	1001.6	1019.3	1037.2	1051.1	1055.6	1075.8	1087.4
12.5°	916.3	938.7	961.6	985.3	1008.2	1032.6	1052.4	1066.3	1082.1	1100.3	1121.6
15°	903.2	928.9	958.8	989.4	1022.2	1051.7	1073.0	1097.1	1114.4	1134.4	1153.0
17.5°	884.3	917.5	955.5	990.8	1028.7	1060.5	1089.8	1112.8	1125.1	1136.4	1139.3
20°	869.4	905.1	949.8	991.6	1029.5	1066.2	1095.1	1114.4	1117.7	1117.9	1100.9
22.5°	853.3	893.5	940.3	983.1	1028.5	1069.3	1091.7	1100.0	1087.3	1065.5	1032.5
25°	823.5	870.0	924.4	973.3	1022.8	1061.4	1069.1	1054.6	1010.0	962.9	903.5
27.5°	791.2	843.5	901.8	956.1	1008.9	1032.9	1016.2	964.0	883.5	813.6	728.8
30°	767.5	826.3	883.6	944.3	993.2	1003.5	965.3	888.4	794.5	689.1	604.5
32.5°	740.5	802.1	865.0	927.9	968.8	958.7	895.5	800.9	690.9	587.2	507.2
35°	701.9	765.6	833.4	896.4	922.5	879.1	784.5	661.4	548.9	452.1	397.1
37.5°	657.4	726.7	797.2	855.1	853.3	780.8	652.1	525.0	430.4	373.2	334.0
40°	625.7	695.8	772.0	820.9	800.0	705.8	566.2	446.3	377.1	331.5	302.9
42.5°	595.4	665.7	741.4	780.2	743.9	628.1	489.0	395.1	338.0	302.5	279.2
45°	543.7	617.9	688.1	709.6	644.6	517.0	395.5	327.4	289.4	263.0	246.9
47.5°	493.3	566.3	630.3	630.7	542.8	419.3	333.6	283.3	250.9	230.5	218.8
50°	462.4	531.8	585.5	577.1	477.5	373.0	298.3	254.9	228.0	212.2	200.0
52.5°	427.7	495.0	541.5	517.7	422.1	328.2	266.7	230.3	207.9	194.2	183.3
55°	377.1	437.0	469.8	433.8	344.4	272.9	225.4	196.7	180.0	168.5	159.2
57.5°	327.6	376.9	397.5	355.6	283.6	226.4	190.6	169.2	152.6	144.3	139.5
60°	296.4	338.5	353.0	306.8	246.6	198.0	168.8	148.9	136.6	131.2	126.4
62.5°	265.9	300.2	306.3	263.8	215.0	173.4	148.3	131.4	123.3	118.0	113.5
65°	220.6	245.3	242.5	208.4	170.0	137.6	119.2	109.0	102.9	95.5	87.5
67.5°	181.6	196.7	187.6	162.0	129.8	106.9	95.0	87.2	79.6	72.6	70.8
70°	156.9	165.6	155.9	132.5	106.4	89.7	80.1	70.8	66.2	64.7	61.7
72.5°	133.3	136.3	125.9	105.7	86.6	74.3	64.9	59.7	57.3	55.9	54.0
75°	100.0	97.7	88.8	73.0	60.1	51.7	48.9	46.9	45.4	44.1	43.0
77.5°	70.3	66.9	58.9	48.6	41.8	37.9	36.2	35.1	34.4	33.7	32.7
80°	52.7	50.5	42.4	34.7	31.9	29.9	28.9	27.6	27.6	27.0	26.0
82.5°	38.6	36.1	29.1	25.5	23.8	22.7	22.0	21.2	20.9	21.1	20.4
85°	20.2	16.4	14.5	13.9	12.8	12.2	12.6	11.9	11.9	11.9	11.5
87.5°	6.5	5.3	5.3	5.2	5.6	5.7	5.6	5.7	6.1	5.9	6.3
90°	1.3	2.2	3.1	4.0	4.7	5.4	6.0	6.7	7.3	7.7	8.2
92.5°	7.3	7.2	7.1	7.1	7.2	7.6	7.9	8.2	8.5	8.8	9.0
95°	21.2	18.5	15.8	13.1	12.1	12.7	13.2	13.8	14.4	14.7	15.2
97.5°	39.9	32.3	24.6	17.0	13.9	15.2	16.5	17.9	19.2	19.5	19.9
100°	53.9	42.7	31.5	20.3	15.4	16.8	18.2	19.5	21.0	21.6	22.3
102.5°	82.2	79.8	77.5	75.1	68.1	56.5	44.9	33.2	21.5	22.4	23.2
105°	114.3	116.8	119.2	121.7	111.8	89.5	67.1	44.8	22.5	23.3	24.3
107.5°	145.0	147.0	149.0	150.9	138.5	111.8	85.0	58.2	31.4	30.5	29.6
110°	164.7	166.4	168.2	169.9	158.9	135.3	111.7	88.0	64.4	56.2	48.0



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	183.4	184.9	186.4	188.0	185.8	179.9	174.1	168.2	162.5	132.6	102.8
115°	213.0	214.4	215.8	217.1	218.9	220.9	223.0	225.0	227.0	189.2	151.4
117.5°	239.7	241.3	242.8	244.4	245.9	247.3	248.7	250.1	251.5	242.4	233.2
120°	258.8	260.0	261.3	262.5	263.9	265.4	266.8	268.3	269.8	270.7	271.7
122.5°	275.3	276.6	277.9	279.2	280.7	282.3	283.9	285.5	287.1	287.7	288.3
125°	300.2	301.4	302.4	303.4	304.7	306.3	307.9	309.4	311.0	311.5	312.1
127.5°	323.1	324.3	325.5	326.7	327.8	329.0	330.1	331.3	332.4	333.3	334.2
130°	337.7	339.0	340.3	341.6	342.7	343.6	344.5	345.4	346.3	347.2	348.1
132.5°	352.1	353.3	354.4	355.5	356.5	357.4	358.3	359.2	360.2	360.9	361.7
135°	371.5	372.8	374.1	375.5	376.4	377.2	378.0	378.7	379.4	380.2	381.1
137.5°	390.5	391.4	392.4	393.2	394.1	394.9	395.8	396.6	397.4	398.2	399.1
140°	402.9	403.6	404.2	404.8	405.6	406.6	407.4	408.3	409.2	409.9	410.7
142.5°	413.5	414.0	414.6	415.2	416.0	417.0	418.0	419.0	420.1	420.8	421.5
145°	429.4	429.3	429.2	429.1	429.8	431.2	432.6	433.9	435.3	435.9	436.5
147.5°	443.7	443.3	443.1	442.7	443.2	444.6	446.0	447.4	448.8	449.2	449.6
150°	452.8	452.2	451.7	451.1	451.4	452.8	454.1	455.4	456.7	457.2	457.7
152.5°	460.7	460.0	459.4	458.7	459.1	460.3	461.6	462.8	464.1	464.5	465.0
155°	472.2	471.4	470.7	469.9	470.1	471.1	472.0	473.0	474.0	474.5	475.0
157.5°	481.3	480.7	480.1	479.5	479.5	480.2	480.9	481.6	482.2	482.8	483.4
160°	486.7	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2	487.8	488.2
162.5°	491.5	490.9	490.5	490.0	490.0	490.3	490.8	491.2	491.6	492.2	492.8
165°	497.8	497.3	496.8	496.3	496.2	496.5	496.7	497.0	497.1	497.7	498.3
167.5°	502.5	502.0	501.5	501.0	500.9	501.1	501.4	501.6	501.8	502.4	503.0
170°	505.1	504.6	504.2	503.7	503.5	503.7	503.9	504.0	504.2	504.7	505.3
172.5°	507.0	506.4	505.9	505.4	505.3	505.4	505.6	505.8	505.9	506.5	507.0
175°	509.1	508.5	508.0	507.4	507.2	507.4	507.6	507.6	507.8	508.4	509.0
177.5°	509.6	509.1	508.7	508.2	508.0	508.1	508.2	508.2	508.2	508.8	509.2
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	957.8	961.1	962.7	962.7	964.5	963.7	962.9
5°	1012.8	1018.9	1020.2	1026.0	1030.2	1028.9	1029.5
7.5°	1067.6	1077.4	1087.1	1091.5	1092.3	1094.8	1095.8
10°	1101.2	1109.3	1124.4	1122.1	1133.4	1139.8	1129.2
12.5°	1133.7	1144.5	1155.0	1157.9	1164.2	1166.3	1162.1
15°	1163.0	1168.7	1169.4	1167.8	1169.8	1168.1	1162.0
17.5°	1135.6	1126.2	1107.2	1098.1	1091.0	1080.5	1076.2
20°	1090.3	1062.6	1030.5	1017.6	1002.5	972.9	980.0
22.5°	992.6	961.0	928.9	891.3	873.4	845.3	843.7
25°	840.5	786.2	726.3	684.5	660.1	632.1	619.9
27.5°	653.5	585.0	536.1	511.3	488.6	466.5	465.5
30°	530.5	479.1	441.2	419.9	406.1	396.7	398.7
32.5°	447.2	411.9	386.3	368.8	358.5	351.5	351.4
35°	365.6	341.5	325.0	317.7	310.3	305.1	305.5
37.5°	312.9	298.3	289.2	281.1	276.5	274.0	272.5
40°	285.9	274.0	266.9	262.1	258.2	254.7	254.0
42.5°	264.5	254.7	247.5	243.7	240.2	237.6	237.0
45°	234.7	226.7	220.2	216.0	214.5	212.2	212.2
47.5°	208.8	200.9	195.9	193.2	190.5	189.0	188.9
50°	191.3	185.2	180.7	179.1	176.8	175.9	175.6
52.5°	175.6	171.1	167.8	166.8	165.7	164.5	164.7
55°	154.3	151.8	150.5	149.5	147.9	145.9	147.2
57.5°	136.4	134.2	130.7	127.7	126.2	124.8	125.4
60°	123.8	119.2	114.8	111.2	110.3	107.4	107.4
62.5°	107.9	101.5	96.0	94.0	93.1	91.7	91.4
65°	82.9	80.4	79.1	77.8	77.1	77.1	76.5
67.5°	68.7	67.7	66.3	66.0	65.3	65.2	64.9
70°	60.8	59.5	58.8	58.5	57.9	58.2	57.3
72.5°	53.0	52.0	51.9	51.1	50.7	50.7	50.0
75°	41.8	41.8	41.5	41.2	40.6	40.2	40.6
77.5°	32.1	32.2	31.6	31.6	31.5	31.6	31.3
80°	25.7	26.0	25.7	25.4	25.1	25.4	25.1
82.5°	20.3	19.9	19.8	19.7	19.7	19.5	19.5
85°	11.5	11.9	11.5	11.3	11.3	11.3	11.5
87.5°	6.1	6.2	6.2	6.3	6.3	6.3	6.1
90°	8.6	9.0	9.3	9.5	9.6	9.8	9.9
92.5°	9.2	9.4	9.6	9.6	9.7	9.8	9.9
95°	15.6	16.0	16.2	16.1	16.0	15.9	15.8
97.5°	20.2	20.5	20.8	20.8	20.9	21.0	21.1
100°	22.9	23.6	24.0	24.2	24.4	24.5	24.6
102.5°	24.1	25.0	25.5	25.7	26.0	26.2	26.4
105°	25.1	26.1	26.7	26.9	27.3	27.6	28.0
107.5°	28.7	27.7	27.5	27.8	28.2	28.4	28.8
110°	39.9	31.7	27.7	28.1	28.4	28.8	29.1



TEST NUMBER: P331785-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	72.9	43.1	28.3	28.6	28.8	29.1	29.4
115°	113.5	75.6	53.7	47.9	41.9	36.1	30.1
117.5°	224.0	214.8	200.6	181.2	161.9	142.6	123.2
120°	272.7	273.7	268.6	257.6	246.6	235.5	224.5
122.5°	288.9	289.5	288.7	286.5	284.4	282.2	280.1
125°	312.7	313.2	313.7	313.9	314.2	314.4	314.6
127.5°	334.9	335.8	336.2	336.3	336.3	336.4	336.4
130°	349.0	349.9	350.3	350.3	350.2	350.1	350.0
132.5°	362.4	363.2	363.5	363.4	363.3	363.3	363.3
135°	381.9	382.7	383.0	382.9	382.7	382.5	382.4
137.5°	399.8	400.6	400.9	400.6	400.4	400.1	399.8
140°	411.5	412.2	412.3	411.9	411.5	411.1	410.7
142.5°	422.1	422.8	422.9	422.5	422.1	421.7	421.3
145°	437.0	437.6	437.7	437.3	436.9	436.5	436.1
147.5°	450.0	450.5	450.5	450.1	449.8	449.4	449.1
150°	458.1	458.7	458.7	458.3	457.9	457.4	457.1
152.5°	465.5	466.1	466.0	465.5	464.9	464.3	463.8
155°	475.4	476.0	475.9	475.2	474.6	473.9	473.3
157.5°	483.9	484.5	484.4	483.8	483.1	482.5	481.9
160°	488.7	489.2	489.1	488.6	488.0	487.4	486.9
162.5°	493.4	493.9	493.8	493.1	492.4	491.7	491.0
165°	498.9	499.5	499.5	498.9	498.3	497.7	497.1
167.5°	503.5	504.1	504.0	503.3	502.6	501.8	501.1
170°	505.9	506.4	506.4	505.7	504.9	504.2	503.4
172.5°	507.6	508.2	508.2	507.4	506.7	505.9	505.2
175°	509.5	510.1	510.1	509.2	508.4	507.6	506.8
177.5°	509.6	510.1	510.1	509.5	508.9	508.2	507.7
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6

(END OF REPORT)