

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331789-935

Luminaire Tested: **S122RDIW-S485D710U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331789-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S485D710U935-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4042.4 lumens  
Efficiency: N/A  
Efficacy: 107.5 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	40	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	18
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14941	14941	14941	14941
5°	16686	15034	13331	15034
10°	18513	14929	11555	14929
15°	19423	14710	9105	14710
20°	16838	14385	7878	14385
25°	11043	13942	7035	13942
30°	7433	13403	6367	13403
35°	6022	12727	5742	12727
40°	5354	11989	5313	11989
45°	4845	11125	4743	11125
50°	4411	10263	4393	10263
55°	4144	9315	4090	9315
60°	3468	8441	3426	8441
65°	2923	7664	3316	7664
70°	2705	6845	3125	6845
75°	2533	5958	2888	5958
80°	2334	4900	2566	4900
85°	2130	3872	2260	3872



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.7	2.2
10°-20°	244.4	6.0
20°-30°	315.0	7.8
30°-40°	299.3	7.4
40°-50°	256.4	6.3
50°-60°	195.3	4.8
60°-70°	123.4	3.1
70°-80°	61.6	1.5
80°-90°	18.1	0.4
90°-100°	27.8	0.7
100°-110°	101.9	2.5
110°-120°	272.4	6.7
120°-130°	449.6	11.1
130°-140°	478.2	11.8
140°-150°	444.4	11.0
150°-160°	357.3	8.8
160°-170°	230.3	5.7
170°-180°	79.3	2.0
0°-30°	647.1	16.0
0°-40°	946.4	23.4
0°-60°	1398.1	34.6
0°-90°	1601.3	39.6
90°-120°	402.1	9.9
90°-150°	1774.3	43.9
90°-180°	2441.0	60.4
0°-180°	4042.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	925	925	925	925	925	
5°	1030	928	822	928	1030	102
15°	1162	880	545	880	1162	313
25°	620	783	395	783	620	294
35°	306	646	291	646	306	195
45°	212	487	208	487	212	164
55°	147	331	145	331	147	129
65°	76	201	87	201	76	78
75°	41	96	46	96	41	43
85°	12	21	12	21	12	13
90°	16	1	16	1	16	8
95°	26	39	26	39	26	24
105°	46	183	46	183	46	48
115°	49	347	49	347	49	124
125°	515	490	515	490	515	446
135°	626	606	626	606	626	483
145°	714	703	714	703	714	447
155°	775	775	775	775	775	358
165°	814	816	814	816	814	230
175°	830	835	830	835	830	79
180°	833	833	833	833	833	



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	962.9	963.7	964.5	962.7	962.7	961.1	957.8	955.2	948.0	946.9	946.9
5°	1029.5	1028.9	1030.2	1026.0	1020.2	1018.9	1012.8	1004.8	996.4	987.1	985.2
7.5°	1095.8	1094.8	1092.3	1091.5	1087.1	1077.4	1067.6	1057.0	1043.2	1029.6	1022.8
10°	1129.2	1139.8	1133.4	1122.1	1124.4	1109.3	1101.2	1087.4	1075.8	1055.6	1051.1
12.5°	1162.1	1166.3	1164.2	1157.9	1155.0	1144.5	1133.7	1121.6	1100.3	1082.1	1066.3
15°	1162.0	1168.1	1169.8	1167.8	1169.4	1168.7	1163.0	1153.0	1134.4	1114.4	1097.1
17.5°	1076.2	1080.5	1091.0	1098.1	1107.2	1126.2	1135.6	1139.3	1136.4	1125.1	1112.8
20°	980.0	972.9	1002.5	1017.6	1030.5	1062.6	1090.3	1100.9	1117.9	1117.7	1114.4
22.5°	843.7	845.3	873.4	891.3	928.9	961.0	992.6	1032.5	1065.5	1087.3	1100.0
25°	619.9	632.1	660.1	684.5	726.3	786.2	840.5	903.5	962.9	1010.0	1054.6
27.5°	465.5	466.5	488.6	511.3	536.1	585.0	653.5	728.8	813.6	883.5	964.0
30°	398.7	396.7	406.1	419.9	441.2	479.1	530.5	604.5	689.1	794.5	888.4
32.5°	351.4	351.5	358.5	368.8	386.3	411.9	447.2	507.2	587.2	690.9	800.9
35°	305.5	305.1	310.3	317.7	325.0	341.5	365.6	397.1	452.1	548.9	661.4
37.5°	272.5	274.0	276.5	281.1	289.2	298.3	312.9	334.0	373.2	430.4	525.0
40°	254.0	254.7	258.2	262.1	266.9	274.0	285.9	302.9	331.5	377.1	446.3
42.5°	237.0	237.6	240.2	243.7	247.5	254.7	264.5	279.2	302.5	338.0	395.1
45°	212.2	212.2	214.5	216.0	220.2	226.7	234.7	246.9	263.0	289.4	327.4
47.5°	188.9	189.0	190.5	193.2	195.9	200.9	208.8	218.8	230.5	250.9	283.3
50°	175.6	175.9	176.8	179.1	180.7	185.2	191.3	200.0	212.2	228.0	254.9
52.5°	164.7	164.5	165.7	166.8	167.8	171.1	175.6	183.3	194.2	207.9	230.3
55°	147.2	145.9	147.9	149.5	150.5	151.8	154.3	159.2	168.5	180.0	196.7
57.5°	125.4	124.8	126.2	127.7	130.7	134.2	136.4	139.5	144.3	152.6	169.2
60°	107.4	107.4	110.3	111.2	114.8	119.2	123.8	126.4	131.2	136.6	148.9
62.5°	91.4	91.7	93.1	94.0	96.0	101.5	107.9	113.5	118.0	123.3	131.4
65°	76.5	77.1	77.1	77.8	79.1	80.4	82.9	87.5	95.5	102.9	109.0
67.5°	64.9	65.2	65.3	66.0	66.3	67.7	68.7	70.8	72.6	79.6	87.2
70°	57.3	58.2	57.9	58.5	58.8	59.5	60.8	61.7	64.7	66.2	70.8
72.5°	50.0	50.7	50.7	51.1	51.9	52.0	53.0	54.0	55.9	57.3	59.7
75°	40.6	40.2	40.6	41.2	41.5	41.8	41.8	43.0	44.1	45.4	46.9
77.5°	31.3	31.6	31.5	31.6	31.6	32.2	32.1	32.7	33.7	34.4	35.1
80°	25.1	25.4	25.1	25.4	25.7	26.0	25.7	26.0	27.0	27.6	27.6
82.5°	19.5	19.5	19.7	19.7	19.8	19.9	20.3	20.4	21.1	20.9	21.2
85°	11.5	11.3	11.3	11.3	11.5	11.9	11.5	11.5	11.9	11.9	11.9
87.5°	7.4	7.6	7.5	7.5	7.4	7.3	7.1	7.3	6.9	7.1	6.5
90°	16.3	16.0	15.8	15.5	15.2	14.7	14.0	13.4	12.7	12.1	11.0
92.5°	16.3	16.1	15.9	15.8	15.7	15.4	15.1	14.7	14.3	13.9	13.4
95°	25.9	26.1	26.2	26.3	26.4	26.2	25.5	24.9	24.2	23.5	22.6
97.5°	34.6	34.4	34.3	34.1	33.9	33.6	33.1	32.5	32.0	31.4	29.3
100°	40.4	40.1	39.9	39.6	39.3	38.7	37.5	36.5	35.4	34.4	32.1
102.5°	43.3	42.9	42.5	42.2	41.8	40.9	39.5	38.1	36.7	35.3	54.3
105°	45.8	45.3	44.8	44.2	43.7	42.6	41.2	39.7	38.2	36.8	73.4
107.5°	47.1	46.6	46.1	45.5	45.0	45.5	47.0	48.5	49.9	51.5	95.3
110°	47.6	47.1	46.6	46.0	45.5	51.9	65.3	78.7	92.1	105.5	144.2



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	48.1	47.7	47.3	46.8	46.4	70.6	119.5	168.3	217.2	266.0	275.6
115°	49.4	59.1	68.7	78.4	88.0	123.8	185.8	247.9	309.9	371.9	368.5
117.5°	201.8	233.5	265.2	296.9	328.6	351.9	366.9	381.9	396.9	411.9	409.6
120°	367.6	385.7	403.8	421.9	440.0	448.2	446.6	445.1	443.4	441.8	439.4
122.5°	458.8	462.4	465.8	469.3	472.9	474.2	473.1	472.2	471.2	470.3	467.6
125°	515.3	515.0	514.5	514.1	513.8	513.1	512.1	511.2	510.2	509.3	506.8
127.5°	551.0	551.0	550.9	550.8	550.7	550.0	548.6	547.3	545.9	544.5	542.6
130°	573.3	573.3	573.5	573.6	573.8	573.1	571.6	570.2	568.7	567.2	565.7
132.5°	595.0	595.0	595.2	595.3	595.5	594.9	593.7	592.4	591.1	589.9	588.4
135°	626.3	626.5	626.8	627.1	627.3	626.8	625.4	624.1	622.8	621.5	620.3
137.5°	654.8	655.3	655.7	656.2	656.7	656.3	654.9	653.6	652.3	651.0	649.6
140°	672.7	673.3	674.0	674.7	675.4	675.1	673.9	672.7	671.5	670.3	668.7
142.5°	690.0	690.7	691.4	692.1	692.7	692.5	691.4	690.3	689.2	688.1	686.4
145°	714.3	714.9	715.6	716.3	717.0	716.8	715.8	714.9	714.0	713.1	710.8
147.5°	735.6	736.2	736.8	737.3	737.9	737.8	737.1	736.4	735.7	734.9	732.7
150°	748.6	749.2	749.9	750.6	751.3	751.2	750.4	749.6	748.8	748.0	745.9
152.5°	759.7	760.6	761.5	762.3	763.3	763.3	762.5	761.6	760.9	760.1	758.0
155°	775.2	776.2	777.3	778.3	779.4	779.5	778.8	777.9	777.1	776.4	774.7
157.5°	789.2	790.3	791.3	792.4	793.4	793.5	792.6	791.7	790.7	789.8	788.7
160°	797.5	798.4	799.3	800.2	801.2	801.2	800.5	799.6	798.8	798.1	797.2
162.5°	804.2	805.3	806.5	807.6	808.8	808.9	808.0	807.1	806.2	805.3	804.6
165°	814.3	815.3	816.2	817.1	818.0	818.0	817.1	816.2	815.3	814.3	813.9
167.5°	820.7	821.9	823.1	824.3	825.5	825.6	824.8	823.8	822.9	821.9	821.6
170°	824.6	825.8	827.0	828.2	829.4	829.5	828.5	827.7	826.7	825.8	825.5
172.5°	827.4	828.6	829.8	831.0	832.2	832.4	831.5	830.5	829.6	828.6	828.4
175°	830.0	831.3	832.7	834.0	835.3	835.5	834.6	833.7	832.8	831.8	831.6
177.5°	831.6	832.5	833.4	834.5	835.4	835.5	834.7	834.1	833.3	832.5	832.4
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	947.4	945.5	943.7	939.0	936.7	931.5	930.7	930.5	923.9	917.4	915.6
5°	980.0	974.9	967.2	958.1	948.8	939.2	932.7	927.6	914.7	902.5	895.4
7.5°	1012.8	1001.8	988.4	971.4	957.2	941.2	929.4	918.8	900.5	883.0	871.2
10°	1037.2	1019.3	1001.6	978.1	959.8	941.8	925.1	910.6	890.0	866.9	850.4
12.5°	1052.4	1032.6	1008.2	985.3	961.6	938.7	916.3	897.7	873.6	849.6	830.1
15°	1073.0	1051.7	1022.2	989.4	958.8	928.9	903.2	880.0	848.5	819.9	796.1
17.5°	1089.8	1060.5	1028.7	990.8	955.5	917.5	884.3	854.7	819.7	785.1	757.2
20°	1095.1	1066.2	1029.5	991.6	949.8	905.1	869.4	837.2	799.6	762.0	729.9
22.5°	1091.7	1069.3	1028.5	983.1	940.3	893.5	853.3	815.9	774.2	735.8	698.5
25°	1069.1	1061.4	1022.8	973.3	924.4	870.0	823.5	782.6	735.0	693.9	653.3
27.5°	1016.2	1032.9	1008.9	956.1	901.8	843.5	791.2	744.7	695.3	648.9	608.6
30°	965.3	1003.5	993.2	944.3	883.6	826.3	767.5	718.9	666.2	618.6	578.8
32.5°	895.5	958.7	968.8	927.9	865.0	802.1	740.5	692.2	637.1	586.9	548.1
35°	784.5	879.1	922.5	896.4	833.4	765.6	701.9	645.7	590.3	540.8	502.2
37.5°	652.1	780.8	853.3	855.1	797.2	726.7	657.4	601.5	544.8	496.3	454.5
40°	566.2	705.8	800.0	820.9	772.0	695.8	625.7	568.8	513.5	465.9	418.0
42.5°	489.0	628.1	743.9	780.2	741.4	665.7	595.4	535.9	482.1	437.0	388.1
45°	395.5	517.0	644.6	709.6	688.1	617.9	543.7	487.2	436.6	397.7	350.8
47.5°	333.6	419.3	542.8	630.7	630.3	566.3	493.3	439.0	392.2	355.8	317.7
50°	298.3	373.0	477.5	577.1	585.5	531.8	462.4	408.6	365.0	326.7	296.1
52.5°	266.7	328.2	422.1	517.7	541.5	495.0	427.7	378.1	335.6	300.4	274.2
55°	225.4	272.9	344.4	433.8	469.8	437.0	377.1	330.9	296.4	266.9	244.4
57.5°	190.6	226.4	283.6	355.6	397.5	376.9	327.6	290.0	260.5	233.8	216.0
60°	168.8	198.0	246.6	306.8	353.0	338.5	296.4	261.4	236.3	213.2	196.5
62.5°	148.3	173.4	215.0	263.8	306.3	300.2	265.9	236.4	214.5	193.4	179.3
65°	119.2	137.6	170.0	208.4	242.5	245.3	220.6	200.6	181.0	164.3	151.8
67.5°	95.0	106.9	129.8	162.0	187.6	196.7	181.6	166.3	150.8	137.8	127.0
70°	80.1	89.7	106.4	132.5	155.9	165.6	156.9	145.0	131.5	120.9	111.6
72.5°	64.9	74.3	86.6	105.7	125.9	136.3	133.3	124.7	113.7	105.0	96.2
75°	48.9	51.7	60.1	73.0	88.8	97.7	100.0	95.5	86.8	80.1	74.9
77.5°	36.2	37.9	41.8	48.6	58.9	66.9	70.3	69.7	63.7	59.8	55.0
80°	28.9	29.9	31.9	34.7	42.4	50.5	52.7	52.7	48.6	46.9	42.1
82.5°	22.0	22.7	23.8	25.5	29.1	36.1	38.6	39.1	36.4	34.4	30.6
85°	12.6	12.2	12.8	13.9	14.5	16.4	20.2	20.9	20.2	17.7	16.7
87.5°	6.4	6.4	6.2	5.7	5.6	5.6	6.6	7.6	6.9	6.4	6.1
90°	9.9	8.9	7.7	6.5	5.0	3.5	2.1	0.6	2.1	3.5	5.0
92.5°	12.9	12.4	11.9	11.6	11.8	11.9	12.1	12.1	12.1	11.9	11.8
95°	21.6	20.7	19.7	21.5	25.9	30.3	34.8	39.2	34.8	30.3	25.9
97.5°	27.1	25.0	22.8	27.9	40.4	52.9	65.3	77.7	65.3	52.9	40.4
100°	29.8	27.6	25.2	33.3	51.7	70.0	88.3	106.7	88.3	70.0	51.7
102.5°	73.4	92.5	111.5	123.0	126.8	130.7	134.7	138.5	134.7	130.7	126.8
105°	109.9	146.5	183.0	199.3	195.3	191.3	187.3	183.2	187.3	191.3	195.3
107.5°	139.2	183.0	226.9	247.2	243.9	240.7	237.5	234.2	237.5	240.7	243.9
110°	182.9	221.6	260.3	278.3	275.4	272.7	269.8	267.0	269.8	272.7	275.4





TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	285.2	294.7	304.3	307.8	305.3	302.9	300.4	297.9	300.4	302.9	305.3
115°	365.2	361.9	358.5	355.7	353.4	351.1	348.9	346.6	348.9	351.1	353.4
117.5°	407.3	405.0	402.7	400.3	397.7	395.2	392.6	390.1	392.6	395.2	397.7
120°	437.0	434.5	432.1	430.0	427.9	425.9	424.0	421.9	424.0	425.9	427.9
122.5°	465.0	462.4	459.8	457.4	455.3	453.1	451.1	448.9	451.1	453.1	455.3
125°	504.2	501.7	499.1	497.0	495.2	493.5	491.8	490.0	491.8	493.5	495.2
127.5°	540.7	538.8	536.9	535.0	533.0	531.2	529.2	527.3	529.2	531.2	533.0
130°	564.2	562.7	561.3	559.5	557.3	555.2	553.0	550.9	553.0	555.2	557.3
132.5°	586.9	585.4	583.9	582.3	580.5	578.7	576.9	575.1	576.9	578.7	580.5
135°	619.1	617.9	616.6	614.9	612.8	610.6	608.5	606.4	608.5	610.6	612.8
137.5°	648.2	646.9	645.5	644.0	642.6	641.1	639.6	638.1	639.6	641.1	642.6
140°	667.3	665.8	664.3	663.1	662.0	660.9	659.9	658.8	659.9	660.9	662.0
142.5°	684.8	683.0	681.3	680.0	679.1	678.1	677.1	676.1	677.1	678.1	679.1
145°	708.5	706.2	704.0	702.8	703.0	703.2	703.3	703.4	703.3	703.2	703.0
147.5°	730.5	728.2	726.0	725.1	725.7	726.2	726.7	727.1	726.7	726.2	725.7
150°	743.7	741.6	739.4	738.8	739.8	740.7	741.7	742.6	741.7	740.7	739.8
152.5°	756.0	754.0	751.9	751.4	752.4	753.5	754.6	755.6	754.6	753.5	752.4
155°	773.1	771.5	769.9	769.7	770.9	772.1	773.4	774.6	773.4	772.1	770.9
157.5°	787.6	786.4	785.3	785.3	786.3	787.3	788.3	789.4	788.3	787.3	786.3
160°	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1	797.2	796.4	795.7
162.5°	803.9	803.1	802.5	802.5	803.3	804.2	804.9	805.7	804.9	804.2	803.3
165°	813.5	813.1	812.7	812.9	813.7	814.5	815.3	816.1	815.3	814.5	813.7
167.5°	821.1	820.8	820.4	820.6	821.4	822.3	823.0	823.8	823.0	822.3	821.4
170°	825.3	824.9	824.7	824.9	825.8	826.6	827.3	828.2	827.3	826.6	825.8
172.5°	828.1	827.9	827.6	827.9	828.6	829.5	830.3	831.0	830.3	829.5	828.6
175°	831.3	831.0	830.7	831.0	832.0	832.9	833.9	834.8	833.9	832.9	832.0
177.5°	832.3	832.2	832.1	832.4	833.2	833.9	834.7	835.4	834.7	833.9	833.2
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	912.2	910.4	907.1	902.0	898.9	893.5	889.8	891.9	892.4	891.9	891.4
5°	887.8	881.0	871.7	862.6	854.3	845.3	840.2	837.9	833.4	830.9	829.6
7.5°	858.1	846.4	833.3	817.6	804.3	790.3	783.2	779.6	770.4	765.4	761.0
10°	835.9	817.6	804.4	783.9	771.4	753.0	740.5	740.8	728.2	721.2	716.0
12.5°	811.6	791.4	769.5	751.0	733.6	718.8	703.7	697.6	684.2	677.4	663.6
15°	771.0	747.5	724.4	699.3	681.7	658.8	637.0	610.3	588.8	570.1	564.9
17.5°	726.8	697.8	674.5	645.1	614.8	576.4	551.0	535.5	522.5	512.7	505.4
20°	696.5	666.8	642.1	597.7	556.9	530.8	512.2	500.3	486.8	476.2	470.4
22.5°	664.5	633.7	599.9	550.4	518.6	497.7	481.0	467.4	458.2	450.0	444.7
25°	619.2	585.5	529.9	495.8	470.1	448.2	436.6	428.3	418.6	407.3	402.3
27.5°	571.4	517.7	477.8	452.5	427.9	413.7	403.3	390.8	382.2	377.1	371.8
30°	535.6	482.0	450.8	423.1	405.8	390.0	377.8	370.7	362.4	353.7	350.2
32.5°	495.8	452.9	423.0	400.0	382.4	368.9	359.3	347.8	341.8	336.5	329.1
35°	446.3	413.8	386.5	367.8	351.1	340.2	328.9	322.2	311.3	306.8	303.8
37.5°	404.3	376.2	355.8	336.1	322.9	310.8	303.9	293.2	288.4	282.1	276.0
40°	380.6	353.0	333.5	317.4	302.6	293.5	284.9	276.2	269.1	266.2	258.8
42.5°	356.5	334.0	314.4	296.8	286.9	277.3	266.4	260.0	252.6	248.0	243.4
45°	323.1	303.2	286.5	272.0	261.1	251.2	244.0	233.4	229.3	219.9	216.0
47.5°	293.8	275.3	259.3	245.6	234.9	228.4	218.1	209.7	203.1	197.3	192.4
50°	272.9	257.5	242.1	229.9	220.2	210.9	200.4	196.1	185.8	183.0	180.0
52.5°	253.9	239.3	225.2	213.2	203.5	194.5	185.1	179.7	172.7	169.8	167.7
55°	227.3	213.2	199.7	189.1	179.4	170.0	164.3	157.6	154.3	152.1	149.5
57.5°	200.5	187.9	177.5	166.8	157.0	149.6	142.9	138.9	135.5	132.6	129.5
60°	183.6	171.3	162.0	152.1	142.2	136.0	130.9	126.1	122.2	117.7	116.4
62.5°	165.6	154.9	146.4	136.6	127.9	122.3	117.5	113.0	108.3	101.8	100.0
65°	140.9	132.5	123.5	115.5	107.7	102.3	95.1	90.1	88.1	87.5	87.1
67.5°	118.5	110.6	102.8	94.6	87.6	82.5	78.9	78.1	76.8	76.4	75.5
70°	103.5	96.2	88.4	80.7	74.0	73.0	71.7	70.4	68.8	68.2	67.5
72.5°	90.1	82.5	74.8	68.6	65.7	64.5	63.2	61.9	60.9	60.2	59.8
75°	69.1	62.1	56.9	54.7	53.0	52.1	50.2	49.2	48.6	47.6	47.3
77.5°	49.8	45.8	43.4	42.0	40.3	39.3	38.2	37.2	36.5	36.3	35.8
80°	38.0	36.0	34.4	32.5	31.9	30.6	30.2	29.3	29.6	28.6	28.6
82.5°	29.4	27.0	25.7	24.8	24.1	23.1	22.7	22.3	22.4	21.7	21.7
85°	15.2	14.5	13.9	13.2	13.2	12.2	12.6	12.2	12.2	11.5	11.3
87.5°	6.2	6.2	5.9	6.1	6.3	6.3	6.4	6.3	6.4	6.5	6.4
90°	6.5	7.7	8.9	9.9	11.0	12.1	12.7	13.4	14.0	14.7	15.2
92.5°	11.6	11.9	12.4	12.9	13.4	13.9	14.3	14.7	15.1	15.4	15.7
95°	21.5	19.7	20.7	21.6	22.6	23.5	24.2	24.9	25.5	26.2	26.4
97.5°	27.9	22.8	25.0	27.1	29.3	31.4	32.0	32.5	33.1	33.6	33.9
100°	33.3	25.2	27.6	29.8	32.1	34.4	35.4	36.5	37.5	38.7	39.3
102.5°	123.0	111.5	92.5	73.4	54.3	35.3	36.7	38.1	39.5	40.9	41.8
105°	199.3	183.0	146.5	109.9	73.4	36.8	38.2	39.7	41.2	42.6	43.7
107.5°	247.2	226.9	183.0	139.2	95.3	51.5	49.9	48.5	47.0	45.5	45.0
110°	278.3	260.3	221.6	182.9	144.2	105.5	92.1	78.7	65.3	51.9	45.5



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	307.8	304.3	294.7	285.2	275.6	266.0	217.2	168.3	119.5	70.6	46.4
115°	355.7	358.5	361.9	365.2	368.5	371.9	309.9	247.9	185.8	123.8	88.0
117.5°	400.3	402.7	405.0	407.3	409.6	411.9	396.9	381.9	366.9	351.9	328.6
120°	430.0	432.1	434.5	437.0	439.4	441.8	443.4	445.1	446.6	448.2	440.0
122.5°	457.4	459.8	462.4	465.0	467.6	470.3	471.2	472.2	473.1	474.2	472.9
125°	497.0	499.1	501.7	504.2	506.8	509.3	510.2	511.2	512.1	513.1	513.8
127.5°	535.0	536.9	538.8	540.7	542.6	544.5	545.9	547.3	548.6	550.0	550.7
130°	559.5	561.3	562.7	564.2	565.7	567.2	568.7	570.2	571.6	573.1	573.8
132.5°	582.3	583.9	585.4	586.9	588.4	589.9	591.1	592.4	593.7	594.9	595.5
135°	614.9	616.6	617.9	619.1	620.3	621.5	622.8	624.1	625.4	626.8	627.3
137.5°	644.0	645.5	646.9	648.2	649.6	651.0	652.3	653.6	654.9	656.3	656.7
140°	663.1	664.3	665.8	667.3	668.7	670.3	671.5	672.7	673.9	675.1	675.4
142.5°	680.0	681.3	683.0	684.8	686.4	688.1	689.2	690.3	691.4	692.5	692.7
145°	702.8	704.0	706.2	708.5	710.8	713.1	714.0	714.9	715.8	716.8	717.0
147.5°	725.1	726.0	728.2	730.5	732.7	734.9	735.7	736.4	737.1	737.8	737.9
150°	738.8	739.4	741.6	743.7	745.9	748.0	748.8	749.6	750.4	751.2	751.3
152.5°	751.4	751.9	754.0	756.0	758.0	760.1	760.9	761.6	762.5	763.3	763.3
155°	769.7	769.9	771.5	773.1	774.7	776.4	777.1	777.9	778.8	779.5	779.4
157.5°	785.3	785.3	786.4	787.6	788.7	789.8	790.7	791.7	792.6	793.5	793.4
160°	794.8	794.8	795.7	796.4	797.2	798.1	798.8	799.6	800.5	801.2	801.2
162.5°	802.5	802.5	803.1	803.9	804.6	805.3	806.2	807.1	808.0	808.9	808.8
165°	812.9	812.7	813.1	813.5	813.9	814.3	815.3	816.2	817.1	818.0	818.0
167.5°	820.6	820.4	820.8	821.1	821.6	821.9	822.9	823.8	824.8	825.6	825.5
170°	824.9	824.7	824.9	825.3	825.5	825.8	826.7	827.7	828.5	829.5	829.4
172.5°	827.9	827.6	827.9	828.1	828.4	828.6	829.6	830.5	831.5	832.4	832.2
175°	831.0	830.7	831.0	831.3	831.6	831.8	832.8	833.7	834.6	835.5	835.3
177.5°	832.4	832.1	832.2	832.3	832.4	832.5	833.3	834.1	834.7	835.5	835.4
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	888.6	889.1	888.3	888.8	888.3	889.1	888.6	891.4	891.9	892.4	891.9
5°	827.9	824.1	823.5	822.5	823.5	824.1	827.9	829.6	830.9	833.4	837.9
7.5°	755.5	754.9	753.4	751.1	753.4	754.9	755.5	761.0	765.4	770.4	779.6
10°	708.9	707.4	707.1	704.8	707.1	707.4	708.9	716.0	721.2	728.2	740.8
12.5°	654.4	644.1	643.0	637.4	643.0	644.1	654.4	663.6	677.4	684.2	697.6
15°	557.2	555.3	548.9	544.7	548.9	555.3	557.2	564.9	570.1	588.8	610.3
17.5°	501.6	495.3	493.4	492.5	493.4	495.3	501.6	505.4	512.7	522.5	535.5
20°	465.9	460.1	459.2	458.5	459.2	460.1	465.9	470.4	476.2	486.8	500.3
22.5°	441.2	435.1	432.7	430.8	432.7	435.1	441.2	444.7	450.0	458.2	467.4
25°	399.0	396.7	395.5	394.9	395.5	396.7	399.0	402.3	407.3	418.6	428.3
27.5°	366.0	361.1	360.1	358.4	360.1	361.1	366.0	371.8	377.1	382.2	390.8
30°	347.2	345.6	343.4	341.5	343.4	345.6	347.2	350.2	353.7	362.4	370.7
32.5°	325.1	323.8	321.8	320.9	321.8	323.8	325.1	329.1	336.5	341.8	347.8
35°	300.7	296.1	294.2	291.3	294.2	296.1	300.7	303.8	306.8	311.3	322.2
37.5°	274.7	272.3	269.7	270.6	269.7	272.3	274.7	276.0	282.1	288.4	293.2
40°	254.7	253.0	252.4	252.1	252.4	253.0	254.7	258.8	266.2	269.1	276.2
42.5°	238.7	234.3	232.6	232.6	232.6	234.3	238.7	243.4	248.0	252.6	260.0
45°	214.5	210.3	207.4	207.7	207.4	210.3	214.5	216.0	219.9	229.3	233.4
47.5°	189.7	189.5	187.7	188.3	187.7	189.5	189.7	192.4	197.3	203.1	209.7
50°	177.8	175.9	174.6	174.9	174.6	175.9	177.8	180.0	183.0	185.8	196.1
52.5°	166.5	164.8	163.8	165.1	163.8	164.8	166.5	167.7	169.8	172.7	179.7
55°	147.9	145.9	145.7	145.3	145.7	145.9	147.9	149.5	152.1	154.3	157.6
57.5°	127.2	125.9	123.9	123.1	123.9	125.9	127.2	129.5	132.6	135.5	138.9
60°	112.2	109.6	106.4	106.1	106.4	109.6	112.2	116.4	117.7	122.2	126.1
62.5°	98.6	98.1	97.5	97.4	97.5	98.1	98.6	100.0	101.8	108.3	113.0
65°	86.5	86.2	86.5	86.8	86.5	86.2	86.5	87.1	87.5	88.1	90.1
67.5°	75.3	74.8	74.2	74.5	74.2	74.8	75.3	75.5	76.4	76.8	78.1
70°	66.9	66.6	66.2	66.2	66.2	66.6	66.9	67.5	68.2	68.8	70.4
72.5°	58.6	58.5	58.3	58.0	58.3	58.5	58.6	59.8	60.2	60.9	61.9
75°	46.9	46.3	46.3	46.3	46.3	46.3	46.9	47.3	47.6	48.6	49.2
77.5°	35.7	35.5	35.1	34.9	35.1	35.5	35.7	35.8	36.3	36.5	37.2
80°	28.3	28.0	27.6	27.6	27.6	28.0	28.3	28.6	28.6	29.6	29.3
82.5°	21.6	21.3	21.2	20.9	21.2	21.3	21.6	21.7	21.7	22.4	22.3
85°	11.5	11.9	11.5	12.2	11.5	11.9	11.5	11.3	11.5	12.2	12.2
87.5°	6.5	6.2	6.5	6.4	6.5	6.2	6.5	6.4	6.5	6.4	6.3
90°	15.5	15.8	16.0	16.3	16.0	15.8	15.5	15.2	14.7	14.0	13.4
92.5°	15.8	15.9	16.1	16.3	16.1	15.9	15.8	15.7	15.4	15.1	14.7
95°	26.3	26.2	26.1	25.9	26.1	26.2	26.3	26.4	26.2	25.5	24.9
97.5°	34.1	34.3	34.4	34.6	34.4	34.3	34.1	33.9	33.6	33.1	32.5
100°	39.6	39.9	40.1	40.4	40.1	39.9	39.6	39.3	38.7	37.5	36.5
102.5°	42.2	42.5	42.9	43.3	42.9	42.5	42.2	41.8	40.9	39.5	38.1
105°	44.2	44.8	45.3	45.8	45.3	44.8	44.2	43.7	42.6	41.2	39.7
107.5°	45.5	46.1	46.6	47.1	46.6	46.1	45.5	45.0	45.5	47.0	48.5
110°	46.0	46.6	47.1	47.6	47.1	46.6	46.0	45.5	51.9	65.3	78.7



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	46.8	47.3	47.7	48.1	47.7	47.3	46.8	46.4	70.6	119.5	168.3
115°	78.4	68.7	59.1	49.4	59.1	68.7	78.4	88.0	123.8	185.8	247.9
117.5°	296.9	265.2	233.5	201.8	233.5	265.2	296.9	328.6	351.9	366.9	381.9
120°	421.9	403.8	385.7	367.6	385.7	403.8	421.9	440.0	448.2	446.6	445.1
122.5°	469.3	465.8	462.4	458.8	462.4	465.8	469.3	472.9	474.2	473.1	472.2
125°	514.1	514.5	515.0	515.3	515.0	514.5	514.1	513.8	513.1	512.1	511.2
127.5°	550.8	550.9	551.0	551.0	551.0	550.9	550.8	550.7	550.0	548.6	547.3
130°	573.6	573.5	573.3	573.3	573.3	573.5	573.6	573.8	573.1	571.6	570.2
132.5°	595.3	595.2	595.0	595.0	595.0	595.2	595.3	595.5	594.9	593.7	592.4
135°	627.1	626.8	626.5	626.3	626.5	626.8	627.1	627.3	626.8	625.4	624.1
137.5°	656.2	655.7	655.3	654.8	655.3	655.7	656.2	656.7	656.3	654.9	653.6
140°	674.7	674.0	673.3	672.7	673.3	674.0	674.7	675.4	675.1	673.9	672.7
142.5°	692.1	691.4	690.7	690.0	690.7	691.4	692.1	692.7	692.5	691.4	690.3
145°	716.3	715.6	714.9	714.3	714.9	715.6	716.3	717.0	716.8	715.8	714.9
147.5°	737.3	736.8	736.2	735.6	736.2	736.8	737.3	737.9	737.8	737.1	736.4
150°	750.6	749.9	749.2	748.6	749.2	749.9	750.6	751.3	751.2	750.4	749.6
152.5°	762.3	761.5	760.6	759.7	760.6	761.5	762.3	763.3	763.3	762.5	761.6
155°	778.3	777.3	776.2	775.2	776.2	777.3	778.3	779.4	779.5	778.8	777.9
157.5°	792.4	791.3	790.3	789.2	790.3	791.3	792.4	793.4	793.5	792.6	791.7
160°	800.2	799.3	798.4	797.5	798.4	799.3	800.2	801.2	801.2	800.5	799.6
162.5°	807.6	806.5	805.3	804.2	805.3	806.5	807.6	808.8	808.9	808.0	807.1
165°	817.1	816.2	815.3	814.3	815.3	816.2	817.1	818.0	818.0	817.1	816.2
167.5°	824.3	823.1	821.9	820.7	821.9	823.1	824.3	825.5	825.6	824.8	823.8
170°	828.2	827.0	825.8	824.6	825.8	827.0	828.2	829.4	829.5	828.5	827.7
172.5°	831.0	829.8	828.6	827.4	828.6	829.8	831.0	832.2	832.4	831.5	830.5
175°	834.0	832.7	831.3	830.0	831.3	832.7	834.0	835.3	835.5	834.6	833.7
177.5°	834.5	833.4	832.5	831.6	832.5	833.4	834.5	835.4	835.5	834.7	834.1
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	889.8	893.5	898.9	902.0	907.1	910.4	912.2	915.6	917.4	923.9	930.5
5°	840.2	845.3	854.3	862.6	871.7	881.0	887.8	895.4	902.5	914.7	927.6
7.5°	783.2	790.3	804.3	817.6	833.3	846.4	858.1	871.2	883.0	900.5	918.8
10°	740.5	753.0	771.4	783.9	804.4	817.6	835.9	850.4	866.9	890.0	910.6
12.5°	703.7	718.8	733.6	751.0	769.5	791.4	811.6	830.1	849.6	873.6	897.7
15°	637.0	658.8	681.7	699.3	724.4	747.5	771.0	796.1	819.9	848.5	880.0
17.5°	551.0	576.4	614.8	645.1	674.5	697.8	726.8	757.2	785.1	819.7	854.7
20°	512.2	530.8	556.9	597.7	642.1	666.8	696.5	729.9	762.0	799.6	837.2
22.5°	481.0	497.7	518.6	550.4	599.9	633.7	664.5	698.5	735.8	774.2	815.9
25°	436.6	448.2	470.1	495.8	529.9	585.5	619.2	653.3	693.9	735.0	782.6
27.5°	403.3	413.7	427.9	452.5	477.8	517.7	571.4	608.6	648.9	695.3	744.7
30°	377.8	390.0	405.8	423.1	450.8	482.0	535.6	578.8	618.6	666.2	718.9
32.5°	359.3	368.9	382.4	400.0	423.0	452.9	495.8	548.1	586.9	637.1	692.2
35°	328.9	340.2	351.1	367.8	386.5	413.8	446.3	502.2	540.8	590.3	645.7
37.5°	303.9	310.8	322.9	336.1	355.8	376.2	404.3	454.5	496.3	544.8	601.5
40°	284.9	293.5	302.6	317.4	333.5	353.0	380.6	418.0	465.9	513.5	568.8
42.5°	266.4	277.3	286.9	296.8	314.4	334.0	356.5	388.1	437.0	482.1	535.9
45°	244.0	251.2	261.1	272.0	286.5	303.2	323.1	350.8	397.7	436.6	487.2
47.5°	218.1	228.4	234.9	245.6	259.3	275.3	293.8	317.7	355.8	392.2	439.0
50°	200.4	210.9	220.2	229.9	242.1	257.5	272.9	296.1	326.7	365.0	408.6
52.5°	185.1	194.5	203.5	213.2	225.2	239.3	253.9	274.2	300.4	335.6	378.1
55°	164.3	170.0	179.4	189.1	199.7	213.2	227.3	244.4	266.9	296.4	330.9
57.5°	142.9	149.6	157.0	166.8	177.5	187.9	200.5	216.0	233.8	260.5	290.0
60°	130.9	136.0	142.2	152.1	162.0	171.3	183.6	196.5	213.2	236.3	261.4
62.5°	117.5	122.3	127.9	136.6	146.4	154.9	165.6	179.3	193.4	214.5	236.4
65°	95.1	102.3	107.7	115.5	123.5	132.5	140.9	151.8	164.3	181.0	200.6
67.5°	78.9	82.5	87.6	94.6	102.8	110.6	118.5	127.0	137.8	150.8	166.3
70°	71.7	73.0	74.0	80.7	88.4	96.2	103.5	111.6	120.9	131.5	145.0
72.5°	63.2	64.5	65.7	68.6	74.8	82.5	90.1	96.2	105.0	113.7	124.7
75°	50.2	52.1	53.0	54.7	56.9	62.1	69.1	74.9	80.1	86.8	95.5
77.5°	38.2	39.3	40.3	42.0	43.4	45.8	49.8	55.0	59.8	63.7	69.7
80°	30.2	30.6	31.9	32.5	34.4	36.0	38.0	42.1	46.9	48.6	52.7
82.5°	22.7	23.1	24.1	24.8	25.7	27.0	29.4	30.6	34.4	36.4	39.1
85°	12.6	12.2	13.2	13.2	13.9	14.5	15.2	16.7	17.7	20.2	20.9
87.5°	6.4	6.3	6.3	6.1	5.9	6.2	6.2	6.1	6.4	6.9	7.6
90°	12.7	12.1	11.0	9.9	8.9	7.7	6.5	5.0	3.5	2.1	0.6
92.5°	14.3	13.9	13.4	12.9	12.4	11.9	11.6	11.8	11.9	12.1	12.1
95°	24.2	23.5	22.6	21.6	20.7	19.7	21.5	25.9	30.3	34.8	39.2
97.5°	32.0	31.4	29.3	27.1	25.0	22.8	27.9	40.4	52.9	65.3	77.7
100°	35.4	34.4	32.1	29.8	27.6	25.2	33.3	51.7	70.0	88.3	106.7
102.5°	36.7	35.3	54.3	73.4	92.5	111.5	123.0	126.8	130.7	134.7	138.5
105°	38.2	36.8	73.4	109.9	146.5	183.0	199.3	195.3	191.3	187.3	183.2
107.5°	49.9	51.5	95.3	139.2	183.0	226.9	247.2	243.9	240.7	237.5	234.2
110°	92.1	105.5	144.2	182.9	221.6	260.3	278.3	275.4	272.7	269.8	267.0



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	217.2	266.0	275.6	285.2	294.7	304.3	307.8	305.3	302.9	300.4	297.9
115°	309.9	371.9	368.5	365.2	361.9	358.5	355.7	353.4	351.1	348.9	346.6
117.5°	396.9	411.9	409.6	407.3	405.0	402.7	400.3	397.7	395.2	392.6	390.1
120°	443.4	441.8	439.4	437.0	434.5	432.1	430.0	427.9	425.9	424.0	421.9
122.5°	471.2	470.3	467.6	465.0	462.4	459.8	457.4	455.3	453.1	451.1	448.9
125°	510.2	509.3	506.8	504.2	501.7	499.1	497.0	495.2	493.5	491.8	490.0
127.5°	545.9	544.5	542.6	540.7	538.8	536.9	535.0	533.0	531.2	529.2	527.3
130°	568.7	567.2	565.7	564.2	562.7	561.3	559.5	557.3	555.2	553.0	550.9
132.5°	591.1	589.9	588.4	586.9	585.4	583.9	582.3	580.5	578.7	576.9	575.1
135°	622.8	621.5	620.3	619.1	617.9	616.6	614.9	612.8	610.6	608.5	606.4
137.5°	652.3	651.0	649.6	648.2	646.9	645.5	644.0	642.6	641.1	639.6	638.1
140°	671.5	670.3	668.7	667.3	665.8	664.3	663.1	662.0	660.9	659.9	658.8
142.5°	689.2	688.1	686.4	684.8	683.0	681.3	680.0	679.1	678.1	677.1	676.1
145°	714.0	713.1	710.8	708.5	706.2	704.0	702.8	703.0	703.2	703.3	703.4
147.5°	735.7	734.9	732.7	730.5	728.2	726.0	725.1	725.7	726.2	726.7	727.1
150°	748.8	748.0	745.9	743.7	741.6	739.4	738.8	739.8	740.7	741.7	742.6
152.5°	760.9	760.1	758.0	756.0	754.0	751.9	751.4	752.4	753.5	754.6	755.6
155°	777.1	776.4	774.7	773.1	771.5	769.9	769.7	770.9	772.1	773.4	774.6
157.5°	790.7	789.8	788.7	787.6	786.4	785.3	785.3	786.3	787.3	788.3	789.4
160°	798.8	798.1	797.2	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1
162.5°	806.2	805.3	804.6	803.9	803.1	802.5	802.5	803.3	804.2	804.9	805.7
165°	815.3	814.3	813.9	813.5	813.1	812.7	812.9	813.7	814.5	815.3	816.1
167.5°	822.9	821.9	821.6	821.1	820.8	820.4	820.6	821.4	822.3	823.0	823.8
170°	826.7	825.8	825.5	825.3	824.9	824.7	824.9	825.8	826.6	827.3	828.2
172.5°	829.6	828.6	828.4	828.1	827.9	827.6	827.9	828.6	829.5	830.3	831.0
175°	832.8	831.8	831.6	831.3	831.0	830.7	831.0	832.0	832.9	833.9	834.8
177.5°	833.3	832.5	832.4	832.3	832.2	832.1	832.4	833.2	833.9	834.7	835.4
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	930.7	931.5	936.7	939.0	943.7	945.5	947.4	946.9	946.9	948.0	955.2
5°	932.7	939.2	948.8	958.1	967.2	974.9	980.0	985.2	987.1	996.4	1004.8
7.5°	929.4	941.2	957.2	971.4	988.4	1001.8	1012.8	1022.8	1029.6	1043.2	1057.0
10°	925.1	941.8	959.8	978.1	1001.6	1019.3	1037.2	1051.1	1055.6	1075.8	1087.4
12.5°	916.3	938.7	961.6	985.3	1008.2	1032.6	1052.4	1066.3	1082.1	1100.3	1121.6
15°	903.2	928.9	958.8	989.4	1022.2	1051.7	1073.0	1097.1	1114.4	1134.4	1153.0
17.5°	884.3	917.5	955.5	990.8	1028.7	1060.5	1089.8	1112.8	1125.1	1136.4	1139.3
20°	869.4	905.1	949.8	991.6	1029.5	1066.2	1095.1	1114.4	1117.7	1117.9	1100.9
22.5°	853.3	893.5	940.3	983.1	1028.5	1069.3	1091.7	1100.0	1087.3	1065.5	1032.5
25°	823.5	870.0	924.4	973.3	1022.8	1061.4	1069.1	1054.6	1010.0	962.9	903.5
27.5°	791.2	843.5	901.8	956.1	1008.9	1032.9	1016.2	964.0	883.5	813.6	728.8
30°	767.5	826.3	883.6	944.3	993.2	1003.5	965.3	888.4	794.5	689.1	604.5
32.5°	740.5	802.1	865.0	927.9	968.8	958.7	895.5	800.9	690.9	587.2	507.2
35°	701.9	765.6	833.4	896.4	922.5	879.1	784.5	661.4	548.9	452.1	397.1
37.5°	657.4	726.7	797.2	855.1	853.3	780.8	652.1	525.0	430.4	373.2	334.0
40°	625.7	695.8	772.0	820.9	800.0	705.8	566.2	446.3	377.1	331.5	302.9
42.5°	595.4	665.7	741.4	780.2	743.9	628.1	489.0	395.1	338.0	302.5	279.2
45°	543.7	617.9	688.1	709.6	644.6	517.0	395.5	327.4	289.4	263.0	246.9
47.5°	493.3	566.3	630.3	630.7	542.8	419.3	333.6	283.3	250.9	230.5	218.8
50°	462.4	531.8	585.5	577.1	477.5	373.0	298.3	254.9	228.0	212.2	200.0
52.5°	427.7	495.0	541.5	517.7	422.1	328.2	266.7	230.3	207.9	194.2	183.3
55°	377.1	437.0	469.8	433.8	344.4	272.9	225.4	196.7	180.0	168.5	159.2
57.5°	327.6	376.9	397.5	355.6	283.6	226.4	190.6	169.2	152.6	144.3	139.5
60°	296.4	338.5	353.0	306.8	246.6	198.0	168.8	148.9	136.6	131.2	126.4
62.5°	265.9	300.2	306.3	263.8	215.0	173.4	148.3	131.4	123.3	118.0	113.5
65°	220.6	245.3	242.5	208.4	170.0	137.6	119.2	109.0	102.9	95.5	87.5
67.5°	181.6	196.7	187.6	162.0	129.8	106.9	95.0	87.2	79.6	72.6	70.8
70°	156.9	165.6	155.9	132.5	106.4	89.7	80.1	70.8	66.2	64.7	61.7
72.5°	133.3	136.3	125.9	105.7	86.6	74.3	64.9	59.7	57.3	55.9	54.0
75°	100.0	97.7	88.8	73.0	60.1	51.7	48.9	46.9	45.4	44.1	43.0
77.5°	70.3	66.9	58.9	48.6	41.8	37.9	36.2	35.1	34.4	33.7	32.7
80°	52.7	50.5	42.4	34.7	31.9	29.9	28.9	27.6	27.6	27.0	26.0
82.5°	38.6	36.1	29.1	25.5	23.8	22.7	22.0	21.2	20.9	21.1	20.4
85°	20.2	16.4	14.5	13.9	12.8	12.2	12.6	11.9	11.9	11.9	11.5
87.5°	6.6	5.6	5.6	5.7	6.2	6.4	6.4	6.5	7.1	6.9	7.3
90°	2.1	3.5	5.0	6.5	7.7	8.9	9.9	11.0	12.1	12.7	13.4
92.5°	12.1	11.9	11.8	11.6	11.9	12.4	12.9	13.4	13.9	14.3	14.7
95°	34.8	30.3	25.9	21.5	19.7	20.7	21.6	22.6	23.5	24.2	24.9
97.5°	65.3	52.9	40.4	27.9	22.8	25.0	27.1	29.3	31.4	32.0	32.5
100°	88.3	70.0	51.7	33.3	25.2	27.6	29.8	32.1	34.4	35.4	36.5
102.5°	134.7	130.7	126.8	123.0	111.5	92.5	73.4	54.3	35.3	36.7	38.1
105°	187.3	191.3	195.3	199.3	183.0	146.5	109.9	73.4	36.8	38.2	39.7
107.5°	237.5	240.7	243.9	247.2	226.9	183.0	139.2	95.3	51.5	49.9	48.5
110°	269.8	272.7	275.4	278.3	260.3	221.6	182.9	144.2	105.5	92.1	78.7





TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	300.4	302.9	305.3	307.8	304.3	294.7	285.2	275.6	266.0	217.2	168.3
115°	348.9	351.1	353.4	355.7	358.5	361.9	365.2	368.5	371.9	309.9	247.9
117.5°	392.6	395.2	397.7	400.3	402.7	405.0	407.3	409.6	411.9	396.9	381.9
120°	424.0	425.9	427.9	430.0	432.1	434.5	437.0	439.4	441.8	443.4	445.1
122.5°	451.1	453.1	455.3	457.4	459.8	462.4	465.0	467.6	470.3	471.2	472.2
125°	491.8	493.5	495.2	497.0	499.1	501.7	504.2	506.8	509.3	510.2	511.2
127.5°	529.2	531.2	533.0	535.0	536.9	538.8	540.7	542.6	544.5	545.9	547.3
130°	553.0	555.2	557.3	559.5	561.3	562.7	564.2	565.7	567.2	568.7	570.2
132.5°	576.9	578.7	580.5	582.3	583.9	585.4	586.9	588.4	589.9	591.1	592.4
135°	608.5	610.6	612.8	614.9	616.6	617.9	619.1	620.3	621.5	622.8	624.1
137.5°	639.6	641.1	642.6	644.0	645.5	646.9	648.2	649.6	651.0	652.3	653.6
140°	659.9	660.9	662.0	663.1	664.3	665.8	667.3	668.7	670.3	671.5	672.7
142.5°	677.1	678.1	679.1	680.0	681.3	683.0	684.8	686.4	688.1	689.2	690.3
145°	703.3	703.2	703.0	702.8	704.0	706.2	708.5	710.8	713.1	714.0	714.9
147.5°	726.7	726.2	725.7	725.1	726.0	728.2	730.5	732.7	734.9	735.7	736.4
150°	741.7	740.7	739.8	738.8	739.4	741.6	743.7	745.9	748.0	748.8	749.6
152.5°	754.6	753.5	752.4	751.4	751.9	754.0	756.0	758.0	760.1	760.9	761.6
155°	773.4	772.1	770.9	769.7	769.9	771.5	773.1	774.7	776.4	777.1	777.9
157.5°	788.3	787.3	786.3	785.3	785.3	786.4	787.6	788.7	789.8	790.7	791.7
160°	797.2	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1	798.8	799.6
162.5°	804.9	804.2	803.3	802.5	802.5	803.1	803.9	804.6	805.3	806.2	807.1
165°	815.3	814.5	813.7	812.9	812.7	813.1	813.5	813.9	814.3	815.3	816.2
167.5°	823.0	822.3	821.4	820.6	820.4	820.8	821.1	821.6	821.9	822.9	823.8
170°	827.3	826.6	825.8	824.9	824.7	824.9	825.3	825.5	825.8	826.7	827.7
172.5°	830.3	829.5	828.6	827.9	827.6	827.9	828.1	828.4	828.6	829.6	830.5
175°	833.9	832.9	832.0	831.0	830.7	831.0	831.3	831.6	831.8	832.8	833.7
177.5°	834.7	833.9	833.2	832.4	832.1	832.2	832.3	832.4	832.5	833.3	834.1
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	957.8	961.1	962.7	962.7	964.5	963.7	962.9
5°	1012.8	1018.9	1020.2	1026.0	1030.2	1028.9	1029.5
7.5°	1067.6	1077.4	1087.1	1091.5	1092.3	1094.8	1095.8
10°	1101.2	1109.3	1124.4	1122.1	1133.4	1139.8	1129.2
12.5°	1133.7	1144.5	1155.0	1157.9	1164.2	1166.3	1162.1
15°	1163.0	1168.7	1169.4	1167.8	1169.8	1168.1	1162.0
17.5°	1135.6	1126.2	1107.2	1098.1	1091.0	1080.5	1076.2
20°	1090.3	1062.6	1030.5	1017.6	1002.5	972.9	980.0
22.5°	992.6	961.0	928.9	891.3	873.4	845.3	843.7
25°	840.5	786.2	726.3	684.5	660.1	632.1	619.9
27.5°	653.5	585.0	536.1	511.3	488.6	466.5	465.5
30°	530.5	479.1	441.2	419.9	406.1	396.7	398.7
32.5°	447.2	411.9	386.3	368.8	358.5	351.5	351.4
35°	365.6	341.5	325.0	317.7	310.3	305.1	305.5
37.5°	312.9	298.3	289.2	281.1	276.5	274.0	272.5
40°	285.9	274.0	266.9	262.1	258.2	254.7	254.0
42.5°	264.5	254.7	247.5	243.7	240.2	237.6	237.0
45°	234.7	226.7	220.2	216.0	214.5	212.2	212.2
47.5°	208.8	200.9	195.9	193.2	190.5	189.0	188.9
50°	191.3	185.2	180.7	179.1	176.8	175.9	175.6
52.5°	175.6	171.1	167.8	166.8	165.7	164.5	164.7
55°	154.3	151.8	150.5	149.5	147.9	145.9	147.2
57.5°	136.4	134.2	130.7	127.7	126.2	124.8	125.4
60°	123.8	119.2	114.8	111.2	110.3	107.4	107.4
62.5°	107.9	101.5	96.0	94.0	93.1	91.7	91.4
65°	82.9	80.4	79.1	77.8	77.1	77.1	76.5
67.5°	68.7	67.7	66.3	66.0	65.3	65.2	64.9
70°	60.8	59.5	58.8	58.5	57.9	58.2	57.3
72.5°	53.0	52.0	51.9	51.1	50.7	50.7	50.0
75°	41.8	41.8	41.5	41.2	40.6	40.2	40.6
77.5°	32.1	32.2	31.6	31.6	31.5	31.6	31.3
80°	25.7	26.0	25.7	25.4	25.1	25.4	25.1
82.5°	20.3	19.9	19.8	19.7	19.7	19.5	19.5
85°	11.5	11.9	11.5	11.3	11.3	11.3	11.5
87.5°	7.1	7.3	7.4	7.5	7.5	7.6	7.4
90°	14.0	14.7	15.2	15.5	15.8	16.0	16.3
92.5°	15.1	15.4	15.7	15.8	15.9	16.1	16.3
95°	25.5	26.2	26.4	26.3	26.2	26.1	25.9
97.5°	33.1	33.6	33.9	34.1	34.3	34.4	34.6
100°	37.5	38.7	39.3	39.6	39.9	40.1	40.4
102.5°	39.5	40.9	41.8	42.2	42.5	42.9	43.3
105°	41.2	42.6	43.7	44.2	44.8	45.3	45.8
107.5°	47.0	45.5	45.0	45.5	46.1	46.6	47.1
110°	65.3	51.9	45.5	46.0	46.6	47.1	47.6



TEST NUMBER: P331789-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	119.5	70.6	46.4	46.8	47.3	47.7	48.1
115°	185.8	123.8	88.0	78.4	68.7	59.1	49.4
117.5°	366.9	351.9	328.6	296.9	265.2	233.5	201.8
120°	446.6	448.2	440.0	421.9	403.8	385.7	367.6
122.5°	473.1	474.2	472.9	469.3	465.8	462.4	458.8
125°	512.1	513.1	513.8	514.1	514.5	515.0	515.3
127.5°	548.6	550.0	550.7	550.8	550.9	551.0	551.0
130°	571.6	573.1	573.8	573.6	573.5	573.3	573.3
132.5°	593.7	594.9	595.5	595.3	595.2	595.0	595.0
135°	625.4	626.8	627.3	627.1	626.8	626.5	626.3
137.5°	654.9	656.3	656.7	656.2	655.7	655.3	654.8
140°	673.9	675.1	675.4	674.7	674.0	673.3	672.7
142.5°	691.4	692.5	692.7	692.1	691.4	690.7	690.0
145°	715.8	716.8	717.0	716.3	715.6	714.9	714.3
147.5°	737.1	737.8	737.9	737.3	736.8	736.2	735.6
150°	750.4	751.2	751.3	750.6	749.9	749.2	748.6
152.5°	762.5	763.3	763.3	762.3	761.5	760.6	759.7
155°	778.8	779.5	779.4	778.3	777.3	776.2	775.2
157.5°	792.6	793.5	793.4	792.4	791.3	790.3	789.2
160°	800.5	801.2	801.2	800.2	799.3	798.4	797.5
162.5°	808.0	808.9	808.8	807.6	806.5	805.3	804.2
165°	817.1	818.0	818.0	817.1	816.2	815.3	814.3
167.5°	824.8	825.6	825.5	824.3	823.1	821.9	820.7
170°	828.5	829.5	829.4	828.2	827.0	825.8	824.6
172.5°	831.5	832.4	832.2	831.0	829.8	828.6	827.4
175°	834.6	835.5	835.3	834.0	832.7	831.3	830.0
177.5°	834.7	835.5	835.4	834.5	833.4	832.5	831.6
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0

(END OF REPORT)