

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331791-935

Luminaire Tested: **S122RDIW-S485D710U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331791-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D710U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3904.6 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331791-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331791-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37				
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32				
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33	28				
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24				
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18				
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16				
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15				
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16	13				
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12				
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11472	11472	11472
5°	11515	11329	11391
10°	11429	11144	11049
15°	11296	10813	10502
20°	11115	10340	9821
25°	10929	9805	9164
30°	10670	9257	8321
35°	10419	8657	7579
40°	10163	8037	6721
45°	9866	7341	5948
50°	9560	6636	5184
55°	9250	5883	4453
60°	8887	5089	3694
65°	8478	4271	3366
70°	7983	3522	3097
75°	7380	3206	2888
80°	6518	2864	2631
85°	5113	2260	2260



TEST NUMBER: P331791-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	1.7
10°-20°	182.6	4.7
20°-30°	256.4	6.6
30°-40°	279.6	7.2
40°-50°	257.1	6.6
50°-60°	201.9	5.2
60°-70°	131.7	3.4
70°-80°	67.9	1.7
80°-90°	19.7	0.5
90°-100°	27.8	0.7
100°-110°	101.9	2.6
110°-120°	272.4	7.0
120°-130°	449.6	11.5
130°-140°	478.2	12.2
140°-150°	444.4	11.4
150°-160°	357.3	9.2
160°-170°	230.3	5.9
170°-180°	79.3	2.0
0°-30°	505.6	12.9
0°-40°	785.2	20.1
0°-60°	1244.3	31.9
0°-90°	1463.5	37.5
90°-120°	402.1	10.3
90°-150°	1774.3	45.4
90°-180°	2441.0	62.5
0°-180°	3904.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	710	710	710	710	710	
5°	710	707	699	704	703	67
15°	676	668	647	635	628	190
25°	614	592	550	525	514	282
35°	529	494	439	400	384	331
45°	432	388	322	278	260	334
55°	329	277	209	172	158	293
65°	222	169	112	91	88	220
75°	118	75	51	47	46	125
85°	28	15	12	12	12	33
90°	1	7	12	15	16	3
95°	39	21	24	26	26	48
105°	183	191	37	43	46	196
115°	347	357	372	106	49	341
125°	490	498	509	513	515	437
135°	606	616	622	627	626	468
145°	703	703	713	717	714	440
155°	775	770	776	779	775	357
165°	816	813	814	818	814	230
175°	835	831	832	835	830	79
180°	833	833	833	833	833	



TEST NUMBER: P331791-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	713.1	712.6	712.0	711.4	710.8	709.9	708.7	707.4	706.1	704.9	706.0
5°	710.5	709.8	709.1	708.4	707.7	706.4	704.6	702.7	700.9	699.0	700.3
7.5°	703.2	702.3	701.5	700.5	699.6	698.1	695.9	693.8	691.6	689.5	689.8
10°	697.1	696.0	695.0	694.1	693.0	691.1	688.3	685.4	682.5	679.7	679.2
12.5°	689.3	688.1	686.8	685.6	684.4	682.0	678.3	674.7	671.0	667.4	666.6
15°	675.8	674.2	672.7	671.1	669.5	666.3	661.4	656.6	651.8	646.9	644.2
17.5°	659.3	656.9	654.4	652.0	649.6	645.3	639.1	632.8	626.6	620.4	617.2
20°	646.9	644.0	641.2	638.3	635.4	630.4	623.3	616.1	609.0	601.8	598.3
22.5°	633.5	630.3	627.1	623.9	620.7	615.1	607.0	598.9	590.9	582.8	578.2
25°	613.5	608.9	604.3	599.7	595.1	588.1	578.7	569.3	559.8	550.4	544.6
27.5°	589.3	584.3	579.3	574.4	569.4	561.5	551.0	540.3	529.7	519.0	512.2
30°	572.3	566.9	561.5	556.0	550.6	542.2	530.7	519.3	507.8	496.5	489.1
32.5°	555.9	549.5	543.1	536.8	530.5	521.4	509.8	498.1	486.5	474.8	466.5
35°	528.6	521.2	514.0	506.7	499.4	489.5	476.9	464.3	451.8	439.2	430.2
37.5°	501.3	493.3	485.3	477.3	469.3	458.6	445.2	431.8	418.4	405.0	395.0
40°	482.2	473.7	465.1	456.6	448.0	436.8	422.9	409.1	395.2	381.3	371.2
42.5°	462.7	453.7	444.6	435.7	426.6	414.9	400.6	386.2	372.0	357.7	347.2
45°	432.1	422.6	412.9	403.4	393.8	381.5	366.5	351.5	336.5	321.5	311.3
47.5°	402.3	392.1	382.0	371.9	361.7	348.9	333.4	317.9	302.4	286.9	276.8
50°	380.6	370.5	360.4	350.3	340.1	327.2	311.4	295.8	280.0	264.2	254.4
52.5°	359.6	349.0	338.4	327.8	317.2	304.2	288.8	273.5	258.0	242.7	233.2
55°	328.6	317.5	306.3	295.2	284.0	270.7	255.3	239.9	224.4	209.0	200.4
57.5°	296.8	285.4	274.0	262.5	251.1	238.0	223.2	208.3	193.5	178.7	170.7
60°	275.2	263.8	252.4	240.9	229.5	216.5	201.7	187.0	172.3	157.6	150.2
62.5°	254.1	242.7	231.3	219.8	208.4	195.7	181.7	167.6	153.6	139.6	132.6
65°	221.9	210.3	198.7	187.1	175.6	163.3	150.5	137.6	124.8	111.8	107.0
67.5°	190.7	179.3	167.7	156.3	144.7	133.2	121.7	110.1	98.5	87.0	84.7
70°	169.1	158.0	146.8	135.7	124.5	114.0	104.2	94.3	84.5	74.6	73.2
72.5°	148.5	137.8	127.2	116.5	105.8	96.5	88.6	80.7	72.8	64.8	63.6
75°	118.3	108.3	98.3	88.3	78.3	70.9	66.0	61.1	56.3	51.4	50.5
77.5°	88.6	79.8	71.0	62.3	53.6	48.0	45.6	43.3	40.9	38.6	38.0
80°	70.1	62.8	55.5	48.2	40.9	36.6	35.1	33.8	32.3	30.8	30.3
82.5°	53.1	47.4	41.8	36.1	30.4	27.0	26.1	25.1	24.1	23.2	22.8
85°	27.6	24.6	21.6	18.7	15.7	13.9	13.5	13.1	12.7	12.2	12.2
87.5°	8.4	7.7	7.1	6.5	5.9	5.7	5.9	6.1	6.3	6.5	6.5
90°	0.6	2.1	3.5	5.0	6.5	7.7	8.9	9.9	11.0	12.1	12.7
92.5°	12.1	12.1	11.9	11.8	11.6	11.9	12.4	12.9	13.4	13.9	14.3
95°	39.2	34.8	30.3	25.9	21.5	19.7	20.7	21.6	22.6	23.5	24.2
97.5°	77.7	65.3	52.9	40.4	27.9	22.8	25.0	27.1	29.3	31.4	32.0
100°	106.7	88.3	70.0	51.7	33.3	25.2	27.6	29.8	32.1	34.4	35.4
102.5°	138.5	134.7	130.7	126.8	123.0	111.5	92.5	73.4	54.3	35.3	36.7
105°	183.2	187.3	191.3	195.3	199.3	183.0	146.5	109.9	73.4	36.8	38.2
107.5°	234.2	237.5	240.7	243.9	247.2	226.9	183.0	139.2	95.3	51.5	49.9
110°	267.0	269.8	272.7	275.4	278.3	260.3	221.6	182.9	144.2	105.5	92.1



TEST NUMBER: P331791-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	297.9	300.4	302.9	305.3	307.8	304.3	294.7	285.2	275.6	266.0	217.2
115°	346.6	348.9	351.1	353.4	355.7	358.5	361.9	365.2	368.5	371.9	309.9
117.5°	390.1	392.6	395.2	397.7	400.3	402.7	405.0	407.3	409.6	411.9	396.9
120°	421.9	424.0	425.9	427.9	430.0	432.1	434.5	437.0	439.4	441.8	443.4
122.5°	448.9	451.1	453.1	455.3	457.4	459.8	462.4	465.0	467.6	470.3	471.2
125°	490.0	491.8	493.5	495.2	497.0	499.1	501.7	504.2	506.8	509.3	510.2
127.5°	527.3	529.2	531.2	533.0	535.0	536.9	538.8	540.7	542.6	544.5	545.9
130°	550.9	553.0	555.2	557.3	559.5	561.3	562.7	564.2	565.7	567.2	568.7
132.5°	575.1	576.9	578.7	580.5	582.3	583.9	585.4	586.9	588.4	589.9	591.1
135°	606.4	608.5	610.6	612.8	614.9	616.6	617.9	619.1	620.3	621.5	622.8
137.5°	638.1	639.6	641.1	642.6	644.0	645.5	646.9	648.2	649.6	651.0	652.3
140°	658.8	659.9	660.9	662.0	663.1	664.3	665.8	667.3	668.7	670.3	671.5
142.5°	676.1	677.1	678.1	679.1	680.0	681.3	683.0	684.8	686.4	688.1	689.2
145°	703.4	703.3	703.2	703.0	702.8	704.0	706.2	708.5	710.8	713.1	714.0
147.5°	727.1	726.7	726.2	725.7	725.1	726.0	728.2	730.5	732.7	734.9	735.7
150°	742.6	741.7	740.7	739.8	738.8	739.4	741.6	743.7	745.9	748.0	748.8
152.5°	755.6	754.6	753.5	752.4	751.4	751.9	754.0	756.0	758.0	760.1	760.9
155°	774.6	773.4	772.1	770.9	769.7	769.9	771.5	773.1	774.7	776.4	777.1
157.5°	789.4	788.3	787.3	786.3	785.3	785.3	786.4	787.6	788.7	789.8	790.7
160°	798.1	797.2	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1	798.8
162.5°	805.7	804.9	804.2	803.3	802.5	802.5	803.1	803.9	804.6	805.3	806.2
165°	816.1	815.3	814.5	813.7	812.9	812.7	813.1	813.5	813.9	814.3	815.3
167.5°	823.8	823.0	822.3	821.4	820.6	820.4	820.8	821.1	821.6	821.9	822.9
170°	828.2	827.3	826.6	825.8	824.9	824.7	824.9	825.3	825.5	825.8	826.7
172.5°	831.0	830.3	829.5	828.6	827.9	827.6	827.9	828.1	828.4	828.6	829.6
175°	834.8	833.9	832.9	832.0	831.0	830.7	831.0	831.3	831.6	831.8	832.8
177.5°	835.4	834.7	833.9	833.2	832.4	832.1	832.2	832.3	832.4	832.5	833.3
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331791-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	707.1	708.3	709.5	709.9	709.7	709.5	709.2	709.0
5°	701.5	702.8	704.1	704.6	704.1	703.7	703.3	702.8
7.5°	690.2	690.5	691.0	690.8	690.0	689.2	688.5	687.8
10°	678.8	678.4	678.0	677.3	676.5	675.6	674.8	673.9
12.5°	665.8	665.0	664.3	663.1	661.7	660.3	658.8	657.5
15°	641.4	638.8	636.0	634.0	632.5	631.1	629.6	628.3
17.5°	613.9	610.7	607.4	604.6	602.2	599.7	597.3	594.8
20°	594.7	591.2	587.5	584.2	581.1	577.9	574.8	571.6
22.5°	573.6	569.0	564.5	560.9	558.6	556.3	554.0	551.6
25°	538.7	532.9	527.0	523.0	520.8	518.7	516.6	514.4
27.5°	505.4	498.5	491.7	486.6	483.2	479.8	476.4	473.0
30°	481.8	474.6	467.3	461.7	457.8	454.0	450.1	446.3
32.5°	458.1	449.9	441.5	435.6	432.0	428.3	424.6	421.0
35°	421.2	412.2	403.2	397.1	394.0	390.8	387.7	384.5
37.5°	385.1	375.2	365.3	358.5	355.0	351.4	347.8	344.1
40°	361.0	350.9	340.7	333.8	330.1	326.4	322.6	318.9
42.5°	336.7	326.1	315.7	308.7	305.1	301.4	297.8	294.2
45°	301.2	291.1	280.9	274.1	270.7	267.3	263.8	260.5
47.5°	266.7	256.7	246.6	240.0	236.9	233.8	230.6	227.5
50°	244.5	234.7	224.8	218.4	215.4	212.4	209.4	206.4
52.5°	223.6	214.1	204.6	198.5	195.7	193.0	190.1	187.4
55°	191.8	183.2	174.7	169.0	166.3	163.6	160.9	158.2
57.5°	162.9	155.1	147.2	142.2	139.8	137.6	135.3	132.9
60°	142.9	135.7	128.4	123.6	121.3	119.0	116.8	114.4
62.5°	125.6	118.7	111.8	107.6	106.2	104.9	103.5	102.1
65°	102.2	97.3	92.5	89.8	89.4	88.9	88.5	88.1
67.5°	82.5	80.2	78.0	76.7	76.2	75.8	75.3	74.8
70°	71.7	70.3	68.9	67.8	67.3	66.7	66.1	65.6
72.5°	62.4	61.2	60.0	59.2	58.9	58.5	58.2	57.9
75°	49.4	48.5	47.4	46.8	46.8	46.6	46.4	46.3
77.5°	37.5	36.9	36.3	35.9	35.6	35.5	35.2	35.0
80°	29.7	29.2	28.6	28.3	28.3	28.3	28.3	28.3
82.5°	22.5	22.1	21.8	21.6	21.6	21.6	21.6	21.6
85°	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
87.5°	6.5	6.5	6.6	6.6	6.7	6.7	6.8	6.9
90°	13.4	14.0	14.7	15.2	15.5	15.8	16.0	16.3
92.5°	14.7	15.1	15.4	15.7	15.8	15.9	16.1	16.3
95°	24.9	25.5	26.2	26.4	26.3	26.2	26.1	25.9
97.5°	32.5	33.1	33.6	33.9	34.1	34.3	34.4	34.6
100°	36.5	37.5	38.7	39.3	39.6	39.9	40.1	40.4
102.5°	38.1	39.5	40.9	41.8	42.2	42.5	42.9	43.3
105°	39.7	41.2	42.6	43.7	44.2	44.8	45.3	45.8
107.5°	48.5	47.0	45.5	45.0	45.5	46.1	46.6	47.1
110°	78.7	65.3	51.9	45.5	46.0	46.6	47.1	47.6



TEST NUMBER: P331791-935

CATALOG NUMBER: S122RDIW-S485D710U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.3	119.5	70.6	46.4	46.8	47.3	47.7	48.1
115°	247.9	185.8	123.8	88.0	78.4	68.7	59.1	49.4
117.5°	381.9	366.9	351.9	328.6	296.9	265.2	233.5	201.8
120°	445.1	446.6	448.2	440.0	421.9	403.8	385.7	367.6
122.5°	472.2	473.1	474.2	472.9	469.3	465.8	462.4	458.8
125°	511.2	512.1	513.1	513.8	514.1	514.5	515.0	515.3
127.5°	547.3	548.6	550.0	550.7	550.8	550.9	551.0	551.0
130°	570.2	571.6	573.1	573.8	573.6	573.5	573.3	573.3
132.5°	592.4	593.7	594.9	595.5	595.3	595.2	595.0	595.0
135°	624.1	625.4	626.8	627.3	627.1	626.8	626.5	626.3
137.5°	653.6	654.9	656.3	656.7	656.2	655.7	655.3	654.8
140°	672.7	673.9	675.1	675.4	674.7	674.0	673.3	672.7
142.5°	690.3	691.4	692.5	692.7	692.1	691.4	690.7	690.0
145°	714.9	715.8	716.8	717.0	716.3	715.6	714.9	714.3
147.5°	736.4	737.1	737.8	737.9	737.3	736.8	736.2	735.6
150°	749.6	750.4	751.2	751.3	750.6	749.9	749.2	748.6
152.5°	761.6	762.5	763.3	763.3	762.3	761.5	760.6	759.7
155°	777.9	778.8	779.5	779.4	778.3	777.3	776.2	775.2
157.5°	791.7	792.6	793.5	793.4	792.4	791.3	790.3	789.2
160°	799.6	800.5	801.2	801.2	800.2	799.3	798.4	797.5
162.5°	807.1	808.0	808.9	808.8	807.6	806.5	805.3	804.2
165°	816.2	817.1	818.0	818.0	817.1	816.2	815.3	814.3
167.5°	823.8	824.8	825.6	825.5	824.3	823.1	821.9	820.7
170°	827.7	828.5	829.5	829.4	828.2	827.0	825.8	824.6
172.5°	830.5	831.5	832.4	832.2	831.0	829.8	828.6	827.4
175°	833.7	834.6	835.5	835.3	834.0	832.7	831.3	830.0
177.5°	834.1	834.7	835.5	835.4	834.5	833.4	832.5	831.6
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0

(END OF REPORT)