

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331796-935

Luminaire Tested: **S122RDIW-S485D970U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331796-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D970U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4355.1 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331796-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331796-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74		57	57	57		41	41	41	34
1	94	90	87	83	85	82	79	76	65	63	61		50	49	48		37	36	35	29
2	86	79	73	69	78	72	67	63	58	54	51		45	42	40		33	31	30	25
3	79	70	63	57	71	63	57	53	51	47	43		40	37	35		29	28	26	21
4	72	62	54	49	65	56	50	45	46	41	37		36	32	30		26	24	23	19
5	66	55	48	42	60	50	44	39	41	36	32		32	29	26		24	22	20	16
6	61	50	42	36	55	45	38	34	37	32	28		29	26	23		22	19	18	15
7	56	45	37	32	51	41	34	29	33	28	25		26	23	20		20	18	16	13
8	52	41	33	28	47	37	31	26	30	26	22		24	21	18		18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20		22	19	16		17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18		21	17	15		16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11472	11472	11472
5°	11515	11329	11391
10°	11429	11144	11049
15°	11296	10813	10502
20°	11115	10340	9821
25°	10929	9805	9164
30°	10670	9257	8321
35°	10419	8657	7579
40°	10163	8037	6721
45°	9866	7341	5948
50°	9560	6636	5184
55°	9250	5883	4453
60°	8887	5089	3694
65°	8478	4271	3366
70°	7983	3522	3097
75°	7380	3206	2888
80°	6518	2864	2631
85°	5113	2260	2260



TEST NUMBER: P331796-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	1.5
10°-20°	182.6	4.2
20°-30°	256.4	5.9
30°-40°	279.6	6.4
40°-50°	257.1	5.9
50°-60°	201.9	4.6
60°-70°	131.7	3.0
70°-80°	67.9	1.6
80°-90°	21.7	0.5
90°-100°	65.5	1.5
100°-110°	203.4	4.7
110°-120°	347.6	8.0
120°-130°	457.2	10.5
130°-140°	513.1	11.8
140°-150°	503.1	11.6
150°-160°	422.0	9.7
160°-170°	279.9	6.4
170°-180°	97.8	2.2
0°-30°	505.6	11.6
0°-40°	785.2	18.0
0°-60°	1244.3	28.6
0°-90°	1465.5	33.7
90°-120°	616.5	14.2
90°-150°	2089.9	48.0
90°-180°	2890.0	66.4
0°-180°	4355.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	710	710	710	710	710	
5°	710	707	699	704	703	67
15°	676	668	647	635	628	190
25°	614	592	550	525	514	282
35°	529	494	439	400	384	331
45°	432	388	322	278	260	334
55°	329	277	209	172	158	293
65°	222	169	112	91	88	220
75°	118	75	51	47	46	125
85°	28	15	12	12	12	33
90°	1	12	30	29	30	4
95°	45	54	56	56	54	52
105°	188	190	192	194	194	198
115°	349	354	352	351	349	345
125°	508	515	513	510	509	453
135°	657	666	668	667	664	507
145°	797	803	808	809	806	498
155°	911	914	916	920	918	419
165°	992	991	991	996	992	280
175°	1032	1029	1027	1033	1028	98
180°	1033	1033	1033	1033	1033	



TEST NUMBER: P331796-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	713.1	712.6	712.0	711.4	710.8	709.9	708.7	707.4	706.1	704.9	706.0
5°	710.5	709.8	709.1	708.4	707.7	706.4	704.6	702.7	700.9	699.0	700.3
7.5°	703.2	702.3	701.5	700.5	699.6	698.1	695.9	693.8	691.6	689.5	689.8
10°	697.1	696.0	695.0	694.1	693.0	691.1	688.3	685.4	682.5	679.7	679.2
12.5°	689.3	688.1	686.8	685.6	684.4	682.0	678.3	674.7	671.0	667.4	666.6
15°	675.8	674.2	672.7	671.1	669.5	666.3	661.4	656.6	651.8	646.9	644.2
17.5°	659.3	656.9	654.4	652.0	649.6	645.3	639.1	632.8	626.6	620.4	617.2
20°	646.9	644.0	641.2	638.3	635.4	630.4	623.3	616.1	609.0	601.8	598.3
22.5°	633.5	630.3	627.1	623.9	620.7	615.1	607.0	598.9	590.9	582.8	578.2
25°	613.5	608.9	604.3	599.7	595.1	588.1	578.7	569.3	559.8	550.4	544.6
27.5°	589.3	584.3	579.3	574.4	569.4	561.5	551.0	540.3	529.7	519.0	512.2
30°	572.3	566.9	561.5	556.0	550.6	542.2	530.7	519.3	507.8	496.5	489.1
32.5°	555.9	549.5	543.1	536.8	530.5	521.4	509.8	498.1	486.5	474.8	466.5
35°	528.6	521.2	514.0	506.7	499.4	489.5	476.9	464.3	451.8	439.2	430.2
37.5°	501.3	493.3	485.3	477.3	469.3	458.6	445.2	431.8	418.4	405.0	395.0
40°	482.2	473.7	465.1	456.6	448.0	436.8	422.9	409.1	395.2	381.3	371.2
42.5°	462.7	453.7	444.6	435.7	426.6	414.9	400.6	386.2	372.0	357.7	347.2
45°	432.1	422.6	412.9	403.4	393.8	381.5	366.5	351.5	336.5	321.5	311.3
47.5°	402.3	392.1	382.0	371.9	361.7	348.9	333.4	317.9	302.4	286.9	276.8
50°	380.6	370.5	360.4	350.3	340.1	327.2	311.4	295.8	280.0	264.2	254.4
52.5°	359.6	349.0	338.4	327.8	317.2	304.2	288.8	273.5	258.0	242.7	233.2
55°	328.6	317.5	306.3	295.2	284.0	270.7	255.3	239.9	224.4	209.0	200.4
57.5°	296.8	285.4	274.0	262.5	251.1	238.0	223.2	208.3	193.5	178.7	170.7
60°	275.2	263.8	252.4	240.9	229.5	216.5	201.7	187.0	172.3	157.6	150.2
62.5°	254.1	242.7	231.3	219.8	208.4	195.7	181.7	167.6	153.6	139.6	132.6
65°	221.9	210.3	198.7	187.1	175.6	163.3	150.5	137.6	124.8	111.8	107.0
67.5°	190.7	179.3	167.7	156.3	144.7	133.2	121.7	110.1	98.5	87.0	84.7
70°	169.1	158.0	146.8	135.7	124.5	114.0	104.2	94.3	84.5	74.6	73.2
72.5°	148.5	137.8	127.2	116.5	105.8	96.5	88.6	80.7	72.8	64.8	63.6
75°	118.3	108.3	98.3	88.3	78.3	70.9	66.0	61.1	56.3	51.4	50.5
77.5°	88.6	79.8	71.0	62.3	53.6	48.0	45.6	43.3	40.9	38.6	38.0
80°	70.1	62.8	55.5	48.2	40.9	36.6	35.1	33.8	32.3	30.8	30.3
82.5°	53.1	47.4	41.8	36.1	30.4	27.0	26.1	25.1	24.1	23.2	22.8
85°	27.6	24.6	21.6	18.7	15.7	13.9	13.5	13.1	12.7	12.2	12.2
87.5°	8.4	7.9	7.5	7.1	6.6	6.8	7.7	8.5	9.4	10.2	10.0
90°	0.9	3.2	5.5	7.8	10.2	13.4	17.7	22.0	26.3	30.5	30.1
92.5°	15.5	17.2	18.9	20.7	22.4	23.7	24.7	25.7	26.7	27.7	27.8
95°	45.4	47.3	49.2	51.1	53.1	54.2	54.7	55.0	55.4	55.8	55.8
97.5°	82.8	84.6	86.3	88.0	89.6	90.9	91.6	92.4	93.1	93.8	93.8
100°	110.7	112.3	113.8	115.4	116.9	118.0	118.6	119.2	119.8	120.4	120.4
102.5°	140.1	141.3	142.5	143.8	145.0	146.0	146.7	147.5	148.2	149.0	149.1
105°	187.5	188.0	188.6	189.2	189.9	190.3	190.7	191.1	191.5	191.8	192.3
107.5°	235.3	236.2	236.9	237.8	238.7	239.1	239.1	239.1	239.1	239.1	239.3
110°	266.0	267.2	268.3	269.5	270.6	271.2	271.2	271.2	271.2	271.2	271.2



TEST NUMBER: P331796-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	299.5	300.7	301.8	303.0	304.1	304.6	304.4	304.3	304.2	304.0	303.5
115°	348.8	350.0	351.1	352.3	353.4	353.9	353.4	353.1	352.7	352.3	352.1
117.5°	398.0	399.6	401.1	402.7	404.2	404.4	403.4	402.3	401.2	400.1	399.7
120°	430.8	432.4	433.9	435.5	437.0	437.0	435.5	433.9	432.4	430.8	430.8
122.5°	460.8	462.7	464.5	466.4	468.2	468.6	467.5	466.5	465.4	464.3	463.8
125°	507.6	509.3	511.0	512.8	514.5	515.1	514.5	513.9	513.3	512.8	512.2
127.5°	553.1	555.3	557.5	559.7	561.9	562.7	562.0	561.3	560.6	559.9	559.1
130°	581.7	584.2	586.7	589.3	591.8	592.8	592.5	592.0	591.7	591.2	590.9
132.5°	613.7	615.8	617.9	619.9	622.0	623.0	623.1	623.2	623.3	623.4	622.5
135°	656.7	658.8	660.9	663.1	665.2	666.4	666.8	667.2	667.6	668.0	667.8
137.5°	701.8	703.6	705.3	707.1	708.8	710.0	710.4	710.9	711.4	712.0	711.8
140°	729.0	730.8	732.5	734.3	736.0	737.4	738.4	739.3	740.3	741.2	741.2
142.5°	757.0	758.7	760.4	762.2	764.0	765.2	765.8	766.5	767.2	767.8	767.9
145°	797.0	798.4	799.8	801.2	802.5	803.7	804.9	806.1	807.3	808.4	808.6
147.5°	832.8	834.5	836.1	837.7	839.3	840.5	841.3	842.1	842.8	843.6	844.0
150°	857.2	858.4	859.5	860.7	861.9	862.9	863.7	864.4	865.2	866.0	866.5
152.5°	878.9	880.0	881.2	882.4	883.6	884.6	885.5	886.4	887.3	888.3	889.0
155°	911.3	911.9	912.5	913.1	913.6	914.2	914.8	915.4	915.9	916.5	917.5
157.5°	939.0	939.4	939.8	940.2	940.6	941.0	941.3	941.7	942.0	942.4	943.7
160°	955.8	956.1	956.6	956.9	957.3	957.6	957.9	958.0	958.2	958.4	959.6
162.5°	971.1	971.2	971.3	971.4	971.5	971.6	971.8	972.0	972.2	972.3	973.7
165°	991.5	991.4	991.2	990.9	990.8	990.7	990.7	990.7	990.7	990.7	992.0
167.5°	1008.7	1008.1	1007.5	1006.9	1006.3	1006.0	1006.0	1005.9	1005.9	1005.8	1007.2
170°	1017.7	1017.1	1016.6	1016.0	1015.4	1015.0	1014.8	1014.6	1014.4	1014.3	1015.5
172.5°	1024.0	1023.4	1022.8	1022.3	1021.7	1021.2	1021.1	1020.9	1020.7	1020.5	1021.8
175°	1031.7	1031.0	1030.5	1029.9	1029.3	1028.8	1028.5	1028.0	1027.7	1027.3	1028.6
177.5°	1034.8	1034.3	1033.9	1033.4	1032.9	1032.5	1032.3	1031.9	1031.7	1031.3	1032.3
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331796-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	707.1	708.3	709.5	709.9	709.7	709.5	709.2	709.0
5°	701.5	702.8	704.1	704.6	704.1	703.7	703.3	702.8
7.5°	690.2	690.5	691.0	690.8	690.0	689.2	688.5	687.8
10°	678.8	678.4	678.0	677.3	676.5	675.6	674.8	673.9
12.5°	665.8	665.0	664.3	663.1	661.7	660.3	658.8	657.5
15°	641.4	638.8	636.0	634.0	632.5	631.1	629.6	628.3
17.5°	613.9	610.7	607.4	604.6	602.2	599.7	597.3	594.8
20°	594.7	591.2	587.5	584.2	581.1	577.9	574.8	571.6
22.5°	573.6	569.0	564.5	560.9	558.6	556.3	554.0	551.6
25°	538.7	532.9	527.0	523.0	520.8	518.7	516.6	514.4
27.5°	505.4	498.5	491.7	486.6	483.2	479.8	476.4	473.0
30°	481.8	474.6	467.3	461.7	457.8	454.0	450.1	446.3
32.5°	458.1	449.9	441.5	435.6	432.0	428.3	424.6	421.0
35°	421.2	412.2	403.2	397.1	394.0	390.8	387.7	384.5
37.5°	385.1	375.2	365.3	358.5	355.0	351.4	347.8	344.1
40°	361.0	350.9	340.7	333.8	330.1	326.4	322.6	318.9
42.5°	336.7	326.1	315.7	308.7	305.1	301.4	297.8	294.2
45°	301.2	291.1	280.9	274.1	270.7	267.3	263.8	260.5
47.5°	266.7	256.7	246.6	240.0	236.9	233.8	230.6	227.5
50°	244.5	234.7	224.8	218.4	215.4	212.4	209.4	206.4
52.5°	223.6	214.1	204.6	198.5	195.7	193.0	190.1	187.4
55°	191.8	183.2	174.7	169.0	166.3	163.6	160.9	158.2
57.5°	162.9	155.1	147.2	142.2	139.8	137.6	135.3	132.9
60°	142.9	135.7	128.4	123.6	121.3	119.0	116.8	114.4
62.5°	125.6	118.7	111.8	107.6	106.2	104.9	103.5	102.1
65°	102.2	97.3	92.5	89.8	89.4	88.9	88.5	88.1
67.5°	82.5	80.2	78.0	76.7	76.2	75.8	75.3	74.8
70°	71.7	70.3	68.9	67.8	67.3	66.7	66.1	65.6
72.5°	62.4	61.2	60.0	59.2	58.9	58.5	58.2	57.9
75°	49.4	48.5	47.4	46.8	46.8	46.6	46.4	46.3
77.5°	37.5	36.9	36.3	35.9	35.6	35.5	35.2	35.0
80°	29.7	29.2	28.6	28.3	28.3	28.3	28.3	28.3
82.5°	22.5	22.1	21.8	21.6	21.6	21.6	21.6	21.6
85°	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
87.5°	9.8	9.6	9.5	9.4	9.4	9.5	9.5	9.6
90°	29.7	29.4	28.9	28.8	29.1	29.3	29.4	29.6
92.5°	27.9	28.0	28.1	28.1	28.2	28.2	28.2	28.2
95°	55.8	55.8	55.8	55.6	55.2	54.8	54.4	54.1
97.5°	93.8	93.8	93.8	93.8	93.8	93.8	93.7	93.7
100°	120.4	120.4	120.4	120.3	120.0	119.9	119.7	119.5
102.5°	149.3	149.4	149.6	149.6	149.4	149.1	149.0	148.8
105°	192.6	193.0	193.4	193.6	193.6	193.6	193.6	193.6
107.5°	239.4	239.6	239.7	239.4	238.5	237.5	236.7	235.8
110°	271.2	271.2	271.2	271.0	270.4	269.8	269.1	268.6



TEST NUMBER: P331796-935

CATALOG NUMBER: S122RDIW-S485D970U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	303.1	302.6	302.1	301.7	301.3	300.8	300.4	300.0
115°	351.9	351.7	351.5	351.1	350.6	350.0	349.4	348.8
117.5°	399.2	398.7	398.2	397.7	397.2	396.6	396.0	395.4
120°	430.8	430.8	430.8	430.5	429.9	429.4	428.8	428.2
122.5°	463.4	462.9	462.4	462.0	461.6	461.2	460.7	460.3
125°	511.6	511.0	510.5	510.1	509.9	509.7	509.5	509.3
127.5°	558.4	557.8	557.1	556.4	555.8	555.2	554.6	554.0
130°	590.5	590.1	589.7	589.1	588.3	587.5	586.8	586.0
132.5°	621.6	620.8	619.9	619.2	618.6	617.9	617.3	616.7
135°	667.6	667.4	667.2	666.8	666.2	665.6	665.1	664.5
137.5°	711.6	711.5	711.4	710.8	710.1	709.3	708.5	707.7
140°	741.2	741.2	741.2	740.9	740.1	739.3	738.6	737.8
142.5°	768.1	768.3	768.4	768.1	767.3	766.5	765.8	765.0
145°	808.8	809.0	809.2	808.9	808.1	807.4	806.6	805.8
147.5°	844.5	844.9	845.3	845.2	844.5	843.7	843.0	842.2
150°	867.1	867.7	868.3	868.3	867.7	867.1	866.5	866.0
152.5°	889.8	890.5	891.2	891.2	890.5	889.8	889.0	888.3
155°	918.5	919.5	920.4	920.6	920.1	919.5	918.9	918.3
157.5°	945.0	946.3	947.6	947.8	946.9	946.0	945.0	944.1
160°	960.7	961.9	963.0	963.3	962.5	961.7	961.0	960.2
162.5°	975.0	976.3	977.7	977.8	976.9	975.9	975.0	974.1
165°	993.4	994.7	996.1	996.3	995.3	994.4	993.4	992.4
167.5°	1008.6	1010.0	1011.2	1011.4	1010.5	1009.4	1008.4	1007.5
170°	1016.9	1018.3	1019.7	1019.8	1018.6	1017.4	1016.2	1015.1
172.5°	1023.2	1024.6	1025.9	1026.1	1024.8	1023.7	1022.5	1021.4
175°	1030.0	1031.4	1032.7	1032.9	1031.7	1030.5	1029.3	1028.2
177.5°	1033.2	1034.1	1035.0	1035.0	1034.1	1033.2	1032.3	1031.3
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4

(END OF REPORT)