

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332192-927

Luminaire Tested: **S123DIW-S1000D1030U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332192-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1030U927-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6627.2 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	51	50	49	43
2	90	82	76	71	83	76	71	67	65	61	58	55	52	49	45	43	41	37
3	82	73	65	60	75	67	61	56	58	53	49	48	45	42	40	37	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27
5	69	57	49	44	63	53	46	41	46	40	36	39	35	31	32	29	27	24
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	33	54	43	36	31	38	32	28	32	28	24	27	24	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11976	11976	11976	11976
5°	14282	12028	10659	12028
10°	17876	11967	9627	11967
15°	21926	11870	8963	11870
20°	26120	11720	8534	11720
25°	27736	11537	8438	11537
30°	23772	11404	8483	11404
35°	16533	11213	8571	11213
40°	12452	10991	8545	10991
45°	10339	10660	8435	10660
50°	9262	9984	8359	9984
55°	8659	9256	8255	9256
60°	8122	8495	8170	8495
65°	7636	7743	7908	7743
70°	7160	6889	7531	6889
75°	6413	6030	6904	6030
80°	5610	4947	5945	4947
85°	4397	3594	3989	3594



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.6	1.7
10°-20°	351.5	5.3
20°-30°	589.8	8.9
30°-40°	667.9	10.1
40°-50°	598.9	9.0
50°-60°	483.3	7.3
60°-70°	336.8	5.1
70°-80°	177.0	2.7
80°-90°	46.3	0.7
90°-100°	38.9	0.6
100°-110°	185.6	2.8
110°-120°	445.8	6.7
120°-130°	567.6	8.6
130°-140°	606.5	9.2
140°-150°	567.1	8.6
150°-160°	457.5	6.9
160°-170°	295.2	4.5
170°-180°	101.8	1.5
0°-30°	1050.9	15.9
0°-40°	1718.8	25.9
0°-60°	2801.1	42.3
0°-90°	3361.2	50.7
90°-120°	670.3	10.1
90°-150°	2411.5	36.4
90°-180°	3266.0	49.3
0°-180°	6627.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1113	1113	1113	1113	1113	
5°	1322	1113	986	1113	1322	137
15°	1968	1065	804	1065	1968	568
25°	2335	971	710	971	2335	1024
35°	1258	853	652	853	1258	817
45°	679	700	554	700	679	537
55°	461	493	440	493	461	414
65°	300	304	310	304	300	298
75°	154	145	166	145	154	165
85°	36	29	32	29	36	43
90°	24	1	24	1	24	13
95°	30	49	30	49	30	25
105°	35	237	35	237	35	80
115°	468	445	468	445	468	432
125°	640	627	640	627	640	571
135°	788	780	788	780	788	608
145°	909	901	909	901	909	568
155°	991	992	991	992	991	457
165°	1044	1046	1044	1046	1044	295
175°	1067	1071	1067	1071	1067	102
180°	1071	1071	1071	1071	1071	



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1180.7	1180.0	1177.7	1179.5	1176.1	1171.3	1170.8	1166.6	1154.1	1153.2	1149.8
5°	1321.8	1317.5	1316.9	1316.4	1308.8	1298.6	1279.2	1277.6	1251.7	1238.8	1223.1
7.5°	1504.4	1506.7	1498.8	1491.9	1468.9	1453.7	1432.8	1406.2	1374.4	1342.2	1320.7
10°	1635.5	1653.4	1631.3	1616.1	1602.1	1575.7	1545.0	1506.7	1468.5	1423.7	1389.7
12.5°	1776.2	1784.9	1780.4	1766.2	1744.5	1704.2	1649.8	1607.7	1572.4	1497.9	1467.8
15°	1967.6	2000.5	1979.5	1930.9	1932.1	1893.8	1822.6	1744.5	1703.0	1637.7	1548.8
17.5°	2171.6	2175.7	2166.8	2126.3	2099.4	2046.8	1981.1	1906.1	1822.1	1743.1	1648.8
20°	2280.3	2277.0	2258.2	2237.1	2190.8	2149.8	2078.1	1994.6	1886.7	1809.1	1706.2
22.5°	2340.7	2335.3	2326.3	2308.7	2270.2	2226.2	2161.8	2070.4	1967.9	1860.9	1741.9
25°	2335.3	2342.2	2343.4	2338.5	2325.1	2298.6	2247.9	2175.2	2072.7	1935.3	1811.3
27.5°	2123.9	2133.9	2162.7	2188.2	2216.8	2245.9	2242.0	2205.9	2130.1	2011.4	1859.8
30°	1912.6	1891.1	1944.4	2011.8	2057.6	2138.5	2183.8	2186.5	2143.9	2042.0	1894.3
32.5°	1619.4	1643.1	1666.7	1749.6	1849.7	1940.5	2030.7	2103.2	2111.6	2043.8	1914.5
35°	1258.2	1287.9	1330.9	1374.1	1481.9	1574.6	1733.1	1871.1	1981.1	1995.7	1916.4
37.5°	1013.9	1028.6	1055.8	1099.1	1169.6	1279.5	1402.2	1576.6	1735.9	1854.4	1859.6
40°	886.2	890.6	921.3	954.2	1011.3	1101.8	1212.4	1366.5	1557.4	1722.9	1791.9
42.5°	790.5	799.9	813.0	844.6	890.1	958.2	1061.0	1188.4	1363.3	1553.8	1688.8
45°	679.2	690.0	698.1	719.1	751.5	797.3	869.0	985.4	1118.6	1315.3	1497.0
47.5°	605.7	606.6	612.6	628.4	650.5	684.8	735.5	810.3	932.6	1092.2	1278.7
50°	553.1	561.7	563.9	576.2	593.5	618.9	660.9	724.5	824.8	965.0	1136.4
52.5°	516.0	518.6	524.7	533.6	548.7	568.4	604.8	654.7	733.3	852.8	1010.4
55°	461.4	461.4	467.4	474.4	483.0	500.8	525.1	561.7	621.5	714.3	844.7
57.5°	411.0	413.7	417.9	420.0	427.4	439.1	459.4	487.2	531.9	603.2	706.9
60°	377.3	382.2	381.7	386.0	392.4	401.6	418.8	441.5	481.4	538.5	625.9
62.5°	348.0	347.7	347.6	352.8	359.3	368.0	379.2	398.8	432.7	483.3	557.7
65°	299.8	298.7	302.5	305.6	307.8	314.3	322.9	340.2	362.8	400.5	458.2
67.5°	256.8	253.7	255.7	256.8	260.5	265.5	273.6	284.3	302.3	332.6	376.0
70°	227.5	224.8	224.3	225.3	228.5	232.3	238.3	248.5	265.2	289.5	321.3
72.5°	197.3	195.4	195.4	197.7	199.2	201.7	205.9	215.3	228.5	246.8	276.5
75°	154.2	154.2	154.2	154.7	156.3	158.5	161.7	166.6	176.8	189.7	209.7
77.5°	115.6	115.5	114.8	114.7	117.1	118.0	118.8	123.3	129.0	137.8	152.3
80°	90.5	87.9	89.0	90.5	91.7	92.2	93.8	94.9	99.7	104.6	114.8
82.5°	67.3	65.0	65.2	67.7	67.9	68.4	70.1	71.6	73.4	77.9	83.3
85°	35.6	35.6	36.1	36.1	36.7	36.1	37.7	38.3	38.3	41.0	44.2
87.5°	17.7	16.8	17.1	17.5	17.0	17.3	17.6	17.9	18.2	18.5	18.5
90°	23.8	23.5	23.1	22.8	22.4	21.9	21.2	20.5	19.8	19.1	16.8
92.5°	26.4	26.2	26.0	25.7	25.6	24.9	23.8	22.7	21.5	20.4	18.6
95°	30.3	30.3	30.3	30.3	30.3	29.6	28.4	27.2	25.9	24.6	22.7
97.5°	32.8	32.6	32.4	32.2	32.1	31.3	29.9	28.4	27.0	25.6	38.3
100°	33.4	33.3	33.0	32.9	32.7	31.9	30.5	29.1	27.6	26.2	53.9
102.5°	34.1	33.7	33.4	33.1	32.8	34.8	39.2	43.6	48.0	52.4	82.5
105°	35.0	34.6	34.3	34.0	33.6	49.0	80.3	111.7	143.0	174.3	190.2
107.5°	110.0	133.6	157.2	180.7	204.3	227.6	250.6	273.5	296.4	319.4	316.9
110°	218.8	244.1	269.3	294.7	320.0	335.5	341.4	347.2	353.0	358.9	356.9



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	375.4	380.7	386.1	391.4	396.7	399.3	399.3	399.2	399.0	398.9	397.0
115°	467.9	467.1	466.4	465.7	465.0	463.8	462.0	460.3	458.5	456.7	455.1
117.5°	519.8	519.6	519.4	519.3	519.2	518.4	517.0	515.6	514.1	512.7	511.9
120°	555.4	555.4	555.4	555.4	555.4	554.7	553.3	551.8	550.4	549.0	548.5
122.5°	590.4	590.3	590.1	589.9	589.9	589.2	588.3	587.2	586.3	585.3	584.6
125°	639.7	639.4	639.0	638.7	638.3	637.9	637.6	637.2	636.9	636.5	635.8
127.5°	687.1	687.5	687.9	688.2	688.6	688.5	687.9	687.3	686.7	686.2	685.3
130°	717.7	718.0	718.4	718.7	719.1	718.9	718.2	717.6	716.8	716.1	715.4
132.5°	745.7	746.2	746.7	747.2	747.7	747.6	746.9	746.2	745.4	744.7	744.2
135°	788.5	789.0	789.6	790.1	790.6	790.6	790.1	789.6	789.0	788.5	787.8
137.5°	828.8	829.1	829.5	829.8	830.2	830.0	829.1	828.2	827.4	826.6	826.2
140°	852.9	853.3	853.7	854.1	854.4	854.2	853.5	852.8	852.1	851.4	850.8
142.5°	875.2	875.8	876.2	876.7	877.2	877.2	876.6	876.1	875.5	874.9	874.4
145°	909.4	909.4	909.4	909.4	909.4	909.3	908.9	908.6	908.2	907.8	907.5
147.5°	934.9	935.7	936.5	937.4	938.2	938.4	938.0	937.7	937.3	937.0	936.6
150°	954.0	954.6	955.1	955.6	956.2	956.2	955.8	955.5	955.1	954.8	954.4
152.5°	969.3	970.1	970.9	971.7	972.6	972.6	972.0	971.4	970.7	970.1	969.9
155°	990.6	991.7	992.8	993.8	994.8	995.0	994.0	993.2	992.3	991.4	991.3
157.5°	1008.6	1010.0	1011.4	1012.7	1014.1	1014.2	1013.2	1012.2	1011.1	1010.0	1010.2
160°	1020.0	1021.3	1022.5	1023.7	1025.0	1025.1	1024.1	1022.9	1021.9	1020.9	1021.0
162.5°	1030.9	1032.0	1033.1	1034.2	1035.2	1035.2	1034.0	1032.8	1031.6	1030.4	1030.5
165°	1043.9	1045.1	1046.4	1047.7	1048.8	1048.8	1047.3	1045.9	1044.6	1043.1	1043.3
167.5°	1053.3	1054.7	1056.1	1057.6	1059.0	1059.0	1057.6	1056.1	1054.7	1053.3	1053.3
170°	1059.1	1060.4	1061.8	1063.3	1064.7	1064.7	1063.3	1061.8	1060.4	1059.1	1059.1
172.5°	1062.2	1063.7	1065.3	1066.9	1068.4	1068.5	1067.1	1065.7	1064.3	1062.9	1062.7
175°	1067.0	1068.4	1069.8	1071.3	1072.7	1072.8	1071.5	1070.2	1069.1	1067.8	1067.6
177.5°	1068.4	1069.8	1071.3	1072.7	1074.1	1074.2	1073.1	1072.0	1070.9	1069.7	1069.5
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1147.2	1143.7	1140.3	1134.2	1129.0	1121.7	1119.5	1117.0	1109.2	1102.3	1097.1
5°	1217.2	1204.3	1185.4	1168.2	1154.1	1135.3	1124.5	1113.2	1097.0	1082.4	1070.6
7.5°	1290.5	1265.1	1235.8	1204.0	1174.6	1146.1	1123.1	1102.6	1080.0	1058.5	1041.8
10°	1348.8	1312.1	1271.1	1226.9	1189.2	1152.5	1121.8	1094.9	1065.7	1040.4	1019.4
12.5°	1415.2	1360.8	1304.3	1250.6	1206.0	1155.2	1117.9	1083.6	1050.7	1020.2	996.6
15°	1493.7	1424.7	1358.0	1284.0	1216.2	1152.5	1108.3	1065.2	1026.9	995.7	965.5
17.5°	1565.4	1487.2	1399.1	1309.3	1227.3	1151.9	1090.0	1041.2	993.4	955.1	925.0
20°	1605.9	1516.9	1417.2	1324.0	1233.4	1149.3	1081.4	1023.2	971.4	931.0	897.0
22.5°	1640.8	1536.8	1433.6	1333.9	1233.0	1142.4	1065.4	1005.5	949.4	909.8	873.7
25°	1677.0	1552.5	1449.1	1332.1	1219.4	1125.6	1039.3	971.4	915.4	869.0	831.8
27.5°	1708.1	1551.5	1428.6	1302.8	1198.0	1104.0	1011.9	939.1	879.6	829.2	791.5
30°	1728.8	1553.6	1407.5	1283.0	1177.3	1080.3	990.8	917.5	855.0	803.7	768.2
32.5°	1741.8	1552.3	1388.1	1255.4	1144.5	1058.8	968.0	892.1	827.8	777.4	743.1
35°	1749.3	1542.9	1354.7	1198.3	1091.6	1008.1	932.1	853.3	786.0	739.1	700.3
37.5°	1734.2	1522.9	1315.9	1143.4	1026.5	944.2	880.3	813.3	748.8	697.1	663.7
40°	1710.5	1510.0	1285.7	1104.5	981.7	902.4	848.0	782.2	718.6	669.6	638.3
42.5°	1665.2	1483.6	1252.5	1061.4	935.1	855.8	805.7	750.8	690.5	644.5	613.2
45°	1554.7	1426.4	1202.7	996.7	866.3	784.3	740.1	700.3	645.8	601.0	574.1
47.5°	1401.4	1340.2	1130.7	928.5	794.5	715.7	669.7	637.6	597.9	561.7	535.8
50°	1294.8	1269.6	1081.9	881.9	746.6	669.6	625.3	596.2	567.7	531.6	507.8
52.5°	1172.0	1187.6	1025.0	833.6	697.9	622.1	580.5	557.4	531.4	501.8	481.1
55°	998.9	1055.5	926.7	752.6	625.3	553.1	513.7	493.2	478.2	456.1	438.2
57.5°	836.9	908.9	820.4	669.0	554.1	491.7	454.0	431.7	422.0	410.4	396.4
60°	740.7	811.8	744.5	612.9	506.2	446.9	413.4	394.6	384.9	376.8	365.0
62.5°	654.9	726.9	670.3	556.0	459.1	404.2	375.1	356.6	349.1	344.9	334.8
65°	536.9	598.9	561.2	467.4	391.9	343.4	317.0	304.0	297.1	295.4	288.9
67.5°	437.0	484.2	456.7	387.7	328.3	286.4	264.0	252.9	247.6	247.0	242.2
70°	371.5	415.7	394.6	332.1	280.8	248.0	228.5	218.9	215.6	215.1	212.4
72.5°	320.5	351.3	334.6	282.5	242.9	213.0	198.8	188.7	185.0	185.8	183.9
75°	237.2	260.4	250.6	214.5	182.8	163.3	151.5	145.0	141.8	143.4	141.2
77.5°	170.6	185.4	176.6	151.6	132.0	118.0	109.2	105.2	102.3	102.2	101.2
80°	128.8	137.4	132.6	117.5	101.3	89.5	82.5	79.8	78.2	77.6	77.1
82.5°	91.7	99.1	93.4	83.0	72.0	64.9	60.9	57.4	56.2	56.5	55.9
85°	46.3	49.0	46.9	40.4	36.1	32.9	30.7	29.1	28.0	28.6	27.5
87.5°	18.9	18.9	17.1	15.0	13.7	12.0	11.7	10.5	10.0	10.4	10.3
90°	14.5	12.2	9.9	7.8	6.1	4.4	2.5	0.8	2.5	4.4	6.1
92.5°	16.9	15.2	13.5	12.8	13.3	13.8	14.3	14.8	14.3	13.8	13.3
95°	20.8	18.9	16.9	19.6	26.8	34.1	41.3	48.6	41.3	34.1	26.8
97.5°	51.1	63.8	76.5	84.5	87.8	91.0	94.3	97.5	94.3	91.0	87.8
100°	81.4	109.0	136.6	148.6	145.0	141.6	138.0	134.4	138.0	141.6	145.0
102.5°	112.6	142.8	172.9	186.6	184.1	181.6	179.0	176.5	179.0	181.6	184.1
105°	206.0	222.0	237.9	244.9	243.0	241.0	239.1	237.1	239.1	241.0	243.0
107.5°	314.3	311.9	309.3	307.3	305.8	304.2	302.6	301.1	302.6	304.2	305.8
110°	355.0	353.0	351.1	349.4	348.0	346.6	345.2	343.7	345.2	346.6	348.0



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	395.1	393.1	391.2	389.6	388.3	387.0	385.7	384.4	385.7	387.0	388.3
115°	453.5	451.9	450.4	449.0	448.0	446.9	445.8	444.8	445.8	446.9	448.0
117.5°	511.1	510.3	509.5	508.4	507.1	505.8	504.5	503.2	504.5	505.8	507.1
120°	548.0	547.4	546.9	545.8	544.2	542.6	541.1	539.5	541.1	542.6	544.2
122.5°	583.9	583.3	582.6	581.6	580.3	579.0	577.7	576.4	577.7	579.0	580.3
125°	635.1	634.4	633.7	632.6	631.2	629.8	628.4	627.0	628.4	629.8	631.2
127.5°	684.5	683.7	682.8	681.7	680.2	678.8	677.4	676.0	677.4	678.8	680.2
130°	714.7	714.0	713.3	712.3	710.8	709.4	708.0	706.5	708.0	709.4	710.8
132.5°	743.6	743.1	742.5	741.5	740.1	738.6	737.3	735.9	737.3	738.6	740.1
135°	787.1	786.4	785.7	784.8	783.7	782.7	781.6	780.5	781.6	782.7	783.7
137.5°	825.8	825.4	825.0	824.1	822.8	821.4	820.1	818.7	820.1	821.4	822.8
140°	850.3	849.8	849.2	848.4	847.4	846.4	845.3	844.2	845.3	846.4	847.4
142.5°	873.9	873.3	872.8	872.0	870.9	869.9	868.8	867.8	868.8	869.9	870.9
145°	907.1	906.8	906.4	905.6	904.4	903.2	901.9	900.7	901.9	903.2	904.4
147.5°	936.3	935.9	935.6	935.0	934.1	933.3	932.6	931.8	932.6	933.3	934.1
150°	954.1	953.7	953.4	952.9	952.4	951.9	951.3	950.9	951.3	951.9	952.4
152.5°	969.6	969.5	969.2	969.0	968.8	968.5	968.3	968.0	968.3	968.5	968.8
155°	991.0	990.9	990.7	990.8	991.2	991.5	991.8	992.2	991.8	991.5	991.2
157.5°	1010.3	1010.6	1010.7	1010.8	1010.9	1010.9	1011.0	1011.0	1011.0	1010.9	1010.9
160°	1021.2	1021.4	1021.5	1021.8	1021.9	1022.1	1022.2	1022.5	1022.2	1022.1	1021.9
162.5°	1030.8	1030.9	1031.1	1031.4	1031.9	1032.4	1032.8	1033.2	1032.8	1032.4	1031.9
165°	1043.5	1043.6	1043.9	1044.2	1044.7	1045.3	1045.8	1046.3	1045.8	1045.3	1044.7
167.5°	1053.3	1053.3	1053.3	1053.7	1054.4	1055.1	1055.8	1056.5	1055.8	1055.1	1054.4
170°	1059.1	1059.1	1059.1	1059.4	1060.1	1060.8	1061.5	1062.2	1061.5	1060.8	1060.1
172.5°	1062.6	1062.4	1062.3	1062.6	1063.5	1064.4	1065.2	1066.0	1065.2	1064.4	1063.5
175°	1067.5	1067.2	1067.1	1067.5	1068.3	1069.2	1070.1	1071.0	1070.1	1069.2	1068.3
177.5°	1069.4	1069.3	1069.1	1069.4	1070.2	1070.9	1071.5	1072.2	1071.5	1070.9	1070.2
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1094.1	1091.1	1086.8	1080.3	1075.1	1066.9	1066.9	1068.3	1068.3	1067.8	1066.9
5°	1060.9	1052.8	1043.1	1031.8	1019.9	1008.1	1005.9	1001.6	998.4	996.2	993.5
7.5°	1025.9	1011.5	997.4	981.5	967.1	955.1	946.8	939.9	935.5	930.7	927.3
10°	1002.1	984.4	967.7	950.9	932.6	918.1	908.9	902.4	897.5	893.3	891.1
12.5°	974.1	953.7	935.3	919.4	899.4	884.4	875.7	872.7	867.0	857.9	853.1
15°	933.1	914.3	892.2	867.9	858.2	839.9	829.7	824.8	821.6	814.5	812.4
17.5°	898.1	873.4	848.6	830.5	812.5	797.6	791.9	785.8	781.6	775.9	774.1
20°	870.1	848.0	825.3	805.9	787.0	770.9	766.0	761.7	757.4	754.7	752.6
22.5°	841.6	819.5	800.7	782.6	762.5	751.9	746.6	741.9	738.9	737.0	734.8
25°	801.6	782.2	761.2	745.0	728.8	721.8	718.6	715.9	713.8	711.1	710.5
27.5°	765.8	744.7	727.6	712.6	700.9	695.1	692.0	690.6	691.1	692.1	692.7
30°	739.1	719.7	705.7	692.7	681.9	676.5	676.0	676.0	678.2	678.7	679.8
32.5°	714.5	698.5	684.5	672.0	663.8	660.1	662.2	662.2	663.9	665.4	667.3
35°	678.7	664.6	653.9	643.1	636.1	637.7	638.8	639.8	642.5	645.8	648.0
37.5°	644.5	632.3	621.2	612.7	609.5	612.4	615.0	617.3	620.4	622.8	625.0
40°	620.0	610.8	600.0	592.5	593.5	595.2	597.3	600.0	602.7	604.3	606.5
42.5°	597.1	587.5	579.3	573.1	574.6	576.6	577.9	579.3	582.4	585.3	586.6
45°	562.3	554.7	547.2	543.4	544.5	545.6	546.6	548.3	551.0	553.1	553.7
47.5°	523.1	517.8	512.8	509.1	510.8	510.4	511.8	515.2	516.1	517.4	520.4
50°	498.1	493.2	487.4	486.2	486.2	486.2	486.8	491.1	491.1	493.2	495.4
52.5°	470.5	467.4	463.6	461.7	460.8	460.8	463.0	465.2	466.1	469.1	471.3
55°	429.7	426.4	423.2	421.5	420.5	421.5	425.9	426.9	429.7	431.3	432.8
57.5°	387.1	384.6	382.0	381.1	380.9	382.3	384.7	387.9	388.6	393.6	396.0
60°	359.0	355.2	353.1	353.1	352.0	356.9	355.8	361.2	362.3	365.5	369.2
62.5°	330.1	325.0	324.2	324.2	325.7	327.1	328.6	331.0	333.8	337.9	340.8
65°	283.5	280.8	284.6	284.1	283.0	286.2	286.2	288.9	292.2	296.0	301.9
67.5°	239.5	238.1	238.4	238.4	240.0	241.9	243.4	245.7	249.6	253.6	257.5
70°	209.7	211.4	208.7	210.8	212.4	212.9	214.0	217.2	221.6	224.3	228.5
72.5°	180.8	180.7	181.0	181.9	183.5	184.5	185.5	189.3	193.9	196.2	199.7
75°	139.1	138.6	140.1	140.1	142.8	143.9	145.0	146.6	150.9	154.2	156.9
77.5°	101.6	102.2	101.9	103.7	103.0	103.1	106.5	108.1	108.6	114.9	116.4
80°	76.5	77.6	78.2	78.7	79.2	78.2	81.9	83.6	83.6	87.3	90.0
82.5°	55.0	55.6	57.0	57.6	57.7	58.8	59.1	60.3	61.6	63.2	66.7
85°	27.5	29.1	29.6	29.1	29.6	28.6	30.2	30.7	31.3	31.3	31.3
87.5°	10.2	11.0	11.1	12.0	12.0	12.9	13.0	12.3	12.4	13.9	12.3
90°	7.8	9.9	12.2	14.5	16.8	19.1	19.8	20.5	21.2	21.9	22.4
92.5°	12.8	13.5	15.2	16.9	18.6	20.4	21.5	22.7	23.8	24.9	25.6
95°	19.6	16.9	18.9	20.8	22.7	24.6	25.9	27.2	28.4	29.6	30.3
97.5°	84.5	76.5	63.8	51.1	38.3	25.6	27.0	28.4	29.9	31.3	32.1
100°	148.6	136.6	109.0	81.4	53.9	26.2	27.6	29.1	30.5	31.9	32.7
102.5°	186.6	172.9	142.8	112.6	82.5	52.4	48.0	43.6	39.2	34.8	32.8
105°	244.9	237.9	222.0	206.0	190.2	174.3	143.0	111.7	80.3	49.0	33.6
107.5°	307.3	309.3	311.9	314.3	316.9	319.4	296.4	273.5	250.6	227.6	204.3
110°	349.4	351.1	353.0	355.0	356.9	358.9	353.0	347.2	341.4	335.5	320.0



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	389.6	391.2	393.1	395.1	397.0	398.9	399.0	399.2	399.3	399.3	396.7
115°	449.0	450.4	451.9	453.5	455.1	456.7	458.5	460.3	462.0	463.8	465.0
117.5°	508.4	509.5	510.3	511.1	511.9	512.7	514.1	515.6	517.0	518.4	519.2
120°	545.8	546.9	547.4	548.0	548.5	549.0	550.4	551.8	553.3	554.7	555.4
122.5°	581.6	582.6	583.3	583.9	584.6	585.3	586.3	587.2	588.3	589.2	589.9
125°	632.6	633.7	634.4	635.1	635.8	636.5	636.9	637.2	637.6	637.9	638.3
127.5°	681.7	682.8	683.7	684.5	685.3	686.2	686.7	687.3	687.9	688.5	688.6
130°	712.3	713.3	714.0	714.7	715.4	716.1	716.8	717.6	718.2	718.9	719.1
132.5°	741.5	742.5	743.1	743.6	744.2	744.7	745.4	746.2	746.9	747.6	747.7
135°	784.8	785.7	786.4	787.1	787.8	788.5	789.0	789.6	790.1	790.6	790.6
137.5°	824.1	825.0	825.4	825.8	826.2	826.6	827.4	828.2	829.1	830.0	830.2
140°	848.4	849.2	849.8	850.3	850.8	851.4	852.1	852.8	853.5	854.2	854.4
142.5°	872.0	872.8	873.3	873.9	874.4	874.9	875.5	876.1	876.6	877.2	877.2
145°	905.6	906.4	906.8	907.1	907.5	907.8	908.2	908.6	908.9	909.3	909.4
147.5°	935.0	935.6	935.9	936.3	936.6	937.0	937.3	937.7	938.0	938.4	938.2
150°	952.9	953.4	953.7	954.1	954.4	954.8	955.1	955.5	955.8	956.2	956.2
152.5°	969.0	969.2	969.5	969.6	969.9	970.1	970.7	971.4	972.0	972.6	972.6
155°	990.8	990.7	990.9	991.0	991.3	991.4	992.3	993.2	994.0	995.0	994.8
157.5°	1010.8	1010.7	1010.6	1010.3	1010.2	1010.0	1011.1	1012.2	1013.2	1014.2	1014.1
160°	1021.8	1021.5	1021.4	1021.2	1021.0	1020.9	1021.9	1022.9	1024.1	1025.1	1025.0
162.5°	1031.4	1031.1	1030.9	1030.8	1030.5	1030.4	1031.6	1032.8	1034.0	1035.2	1035.2
165°	1044.2	1043.9	1043.6	1043.5	1043.3	1043.1	1044.6	1045.9	1047.3	1048.8	1048.8
167.5°	1053.7	1053.3	1053.3	1053.3	1053.3	1053.3	1054.7	1056.1	1057.6	1059.0	1059.0
170°	1059.4	1059.1	1059.1	1059.1	1059.1	1059.1	1060.4	1061.8	1063.3	1064.7	1064.7
172.5°	1062.6	1062.3	1062.4	1062.6	1062.7	1062.9	1064.3	1065.7	1067.1	1068.5	1068.4
175°	1067.5	1067.1	1067.2	1067.5	1067.6	1067.8	1069.1	1070.2	1071.5	1072.8	1072.7
177.5°	1069.4	1069.1	1069.3	1069.4	1069.5	1069.7	1070.9	1072.0	1073.1	1074.2	1074.1
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1063.9	1063.5	1066.5	1064.4	1066.5	1063.5	1063.9	1066.9	1067.8	1068.3	1068.3
5°	990.3	991.9	986.5	986.5	986.5	991.9	990.3	993.5	996.2	998.4	1001.6
7.5°	924.7	922.3	922.6	919.6	922.6	922.3	924.7	927.3	930.7	935.5	939.9
10°	884.6	881.4	880.3	880.8	880.3	881.4	884.6	891.1	893.3	897.5	902.4
12.5°	851.4	850.8	843.7	843.8	843.7	850.8	851.4	853.1	857.9	867.0	872.7
15°	812.4	802.2	801.1	804.3	801.1	802.2	812.4	812.4	814.5	821.6	824.8
17.5°	773.2	767.9	768.2	766.6	768.2	767.9	773.2	774.1	775.9	781.6	785.8
20°	752.6	749.3	748.8	745.0	748.8	749.3	752.6	752.6	754.7	757.4	761.7
22.5°	733.6	732.5	732.8	728.6	732.8	732.5	733.6	734.8	737.0	738.9	741.9
25°	710.0	712.6	710.5	710.5	710.5	712.6	710.0	710.5	711.1	713.8	715.9
27.5°	694.0	693.9	692.8	692.8	692.8	693.9	694.0	692.7	692.1	691.1	690.6
30°	681.9	681.4	682.5	682.5	682.5	681.4	681.9	679.8	678.7	678.2	676.0
32.5°	669.9	670.6	670.8	671.2	670.8	670.6	669.9	667.3	665.4	663.9	662.2
35°	651.2	651.7	653.4	652.3	653.4	651.7	651.2	648.0	645.8	642.5	639.8
37.5°	626.0	628.4	627.9	628.8	627.9	628.4	626.0	625.0	622.8	620.4	617.3
40°	607.0	608.6	608.1	608.1	608.1	608.6	607.0	606.5	604.3	602.7	600.0
42.5°	587.6	588.7	587.4	586.5	587.4	588.7	587.6	586.6	585.3	582.4	579.3
45°	555.8	554.7	556.3	554.1	556.3	554.7	555.8	553.7	553.1	551.0	548.3
47.5°	520.2	521.3	521.7	523.3	521.7	521.3	520.2	520.4	517.4	516.1	515.2
50°	496.5	499.7	499.7	499.2	499.7	499.7	496.5	495.4	493.2	491.1	491.1
52.5°	473.2	474.7	476.9	476.7	476.9	474.7	473.2	471.3	469.1	466.1	465.2
55°	437.2	438.2	439.3	439.9	439.3	438.2	437.2	432.8	431.3	429.7	426.9
57.5°	399.9	399.4	402.0	402.8	402.0	399.4	399.9	396.0	393.6	388.6	387.9
60°	373.6	373.6	377.9	379.5	377.9	373.6	373.6	369.2	365.5	362.3	361.2
62.5°	345.5	347.3	351.6	349.4	351.6	347.3	345.5	340.8	337.9	333.8	331.0
65°	304.6	308.9	308.3	310.5	308.3	308.9	304.6	301.9	296.0	292.2	288.9
67.5°	261.7	264.4	268.3	268.7	268.3	264.4	261.7	257.5	253.6	249.6	245.7
70°	232.9	235.6	237.7	239.3	237.7	235.6	232.9	228.5	224.3	221.6	217.2
72.5°	204.9	206.3	211.4	209.1	211.4	206.3	204.9	199.7	196.2	193.9	189.3
75°	160.7	164.4	167.6	166.0	167.6	164.4	160.7	156.9	154.2	150.9	146.6
77.5°	118.8	122.6	124.1	122.7	124.1	122.6	118.8	116.4	114.9	108.6	108.1
80°	93.8	93.2	96.5	95.9	96.5	93.2	93.8	90.0	87.3	83.6	83.6
82.5°	68.8	68.3	69.8	70.1	69.8	68.3	68.8	66.7	63.2	61.6	60.3
85°	33.4	35.0	32.9	32.3	32.9	35.0	33.4	31.3	31.3	31.3	30.7
87.5°	12.4	12.4	12.0	11.6	12.0	12.4	12.4	12.3	13.9	12.4	12.3
90°	22.8	23.1	23.5	23.8	23.5	23.1	22.8	22.4	21.9	21.2	20.5
92.5°	25.7	26.0	26.2	26.4	26.2	26.0	25.7	25.6	24.9	23.8	22.7
95°	30.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3	29.6	28.4	27.2
97.5°	32.2	32.4	32.6	32.8	32.6	32.4	32.2	32.1	31.3	29.9	28.4
100°	32.9	33.0	33.3	33.4	33.3	33.0	32.9	32.7	31.9	30.5	29.1
102.5°	33.1	33.4	33.7	34.1	33.7	33.4	33.1	32.8	34.8	39.2	43.6
105°	34.0	34.3	34.6	35.0	34.6	34.3	34.0	33.6	49.0	80.3	111.7
107.5°	180.7	157.2	133.6	110.0	133.6	157.2	180.7	204.3	227.6	250.6	273.5
110°	294.7	269.3	244.1	218.8	244.1	269.3	294.7	320.0	335.5	341.4	347.2



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	391.4	386.1	380.7	375.4	380.7	386.1	391.4	396.7	399.3	399.3	399.2
115°	465.7	466.4	467.1	467.9	467.1	466.4	465.7	465.0	463.8	462.0	460.3
117.5°	519.3	519.4	519.6	519.8	519.6	519.4	519.3	519.2	518.4	517.0	515.6
120°	555.4	555.4	555.4	555.4	555.4	555.4	555.4	555.4	554.7	553.3	551.8
122.5°	589.9	590.1	590.3	590.4	590.3	590.1	589.9	589.9	589.2	588.3	587.2
125°	638.7	639.0	639.4	639.7	639.4	639.0	638.7	638.3	637.9	637.6	637.2
127.5°	688.2	687.9	687.5	687.1	687.5	687.9	688.2	688.6	688.5	687.9	687.3
130°	718.7	718.4	718.0	717.7	718.0	718.4	718.7	719.1	718.9	718.2	717.6
132.5°	747.2	746.7	746.2	745.7	746.2	746.7	747.2	747.7	747.6	746.9	746.2
135°	790.1	789.6	789.0	788.5	789.0	789.6	790.1	790.6	790.6	790.1	789.6
137.5°	829.8	829.5	829.1	828.8	829.1	829.5	829.8	830.2	830.0	829.1	828.2
140°	854.1	853.7	853.3	852.9	853.3	853.7	854.1	854.4	854.2	853.5	852.8
142.5°	876.7	876.2	875.8	875.2	875.8	876.2	876.7	877.2	877.2	876.6	876.1
145°	909.4	909.4	909.4	909.4	909.4	909.4	909.4	909.4	909.3	908.9	908.6
147.5°	937.4	936.5	935.7	934.9	935.7	936.5	937.4	938.2	938.4	938.0	937.7
150°	955.6	955.1	954.6	954.0	954.6	955.1	955.6	956.2	956.2	955.8	955.5
152.5°	971.7	970.9	970.1	969.3	970.1	970.9	971.7	972.6	972.6	972.0	971.4
155°	993.8	992.8	991.7	990.6	991.7	992.8	993.8	994.8	995.0	994.0	993.2
157.5°	1012.7	1011.4	1010.0	1008.6	1010.0	1011.4	1012.7	1014.1	1014.2	1013.2	1012.2
160°	1023.7	1022.5	1021.3	1020.0	1021.3	1022.5	1023.7	1025.0	1025.1	1024.1	1022.9
162.5°	1034.2	1033.1	1032.0	1030.9	1032.0	1033.1	1034.2	1035.2	1035.2	1034.0	1032.8
165°	1047.7	1046.4	1045.1	1043.9	1045.1	1046.4	1047.7	1048.8	1048.8	1047.3	1045.9
167.5°	1057.6	1056.1	1054.7	1053.3	1054.7	1056.1	1057.6	1059.0	1059.0	1057.6	1056.1
170°	1063.3	1061.8	1060.4	1059.1	1060.4	1061.8	1063.3	1064.7	1064.7	1063.3	1061.8
172.5°	1066.9	1065.3	1063.7	1062.2	1063.7	1065.3	1066.9	1068.4	1068.5	1067.1	1065.7
175°	1071.3	1069.8	1068.4	1067.0	1068.4	1069.8	1071.3	1072.7	1072.8	1071.5	1070.2
177.5°	1072.7	1071.3	1069.8	1068.4	1069.8	1071.3	1072.7	1074.1	1074.2	1073.1	1072.0
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1066.9	1066.9	1075.1	1080.3	1086.8	1091.1	1094.1	1097.1	1102.3	1109.2	1117.0
5°	1005.9	1008.1	1019.9	1031.8	1043.1	1052.8	1060.9	1070.6	1082.4	1097.0	1113.2
7.5°	946.8	955.1	967.1	981.5	997.4	1011.5	1025.9	1041.8	1058.5	1080.0	1102.6
10°	908.9	918.1	932.6	950.9	967.7	984.4	1002.1	1019.4	1040.4	1065.7	1094.9
12.5°	875.7	884.4	899.4	919.4	935.3	953.7	974.1	996.6	1020.2	1050.7	1083.6
15°	829.7	839.9	858.2	867.9	892.2	914.3	933.1	965.5	995.7	1026.9	1065.2
17.5°	791.9	797.6	812.5	830.5	848.6	873.4	898.1	925.0	955.1	993.4	1041.2
20°	766.0	770.9	787.0	805.9	825.3	848.0	870.1	897.0	931.0	971.4	1023.2
22.5°	746.6	751.9	762.5	782.6	800.7	819.5	841.6	873.7	909.8	949.4	1005.5
25°	718.6	721.8	728.8	745.0	761.2	782.2	801.6	831.8	869.0	915.4	971.4
27.5°	692.0	695.1	700.9	712.6	727.6	744.7	765.8	791.5	829.2	879.6	939.1
30°	676.0	676.5	681.9	692.7	705.7	719.7	739.1	768.2	803.7	855.0	917.5
32.5°	662.2	660.1	663.8	672.0	684.5	698.5	714.5	743.1	777.4	827.8	892.1
35°	638.8	637.7	636.1	643.1	653.9	664.6	678.7	700.3	739.1	786.0	853.3
37.5°	615.0	612.4	609.5	612.7	621.2	632.3	644.5	663.7	697.1	748.8	813.3
40°	597.3	595.2	593.5	592.5	600.0	610.8	620.0	638.3	669.6	718.6	782.2
42.5°	577.9	576.6	574.6	573.1	579.3	587.5	597.1	613.2	644.5	690.5	750.8
45°	546.6	545.6	544.5	543.4	547.2	554.7	562.3	574.1	601.0	645.8	700.3
47.5°	511.8	510.4	510.8	509.1	512.8	517.8	523.1	535.8	561.7	597.9	637.6
50°	486.8	486.2	486.2	486.2	487.4	493.2	498.1	507.8	531.6	567.7	596.2
52.5°	463.0	460.8	460.8	461.7	463.6	467.4	470.5	481.1	501.8	531.4	557.4
55°	425.9	421.5	420.5	421.5	423.2	426.4	429.7	438.2	456.1	478.2	493.2
57.5°	384.7	382.3	380.9	381.1	382.0	384.6	387.1	396.4	410.4	422.0	431.7
60°	355.8	356.9	352.0	353.1	353.1	355.2	359.0	365.0	376.8	384.9	394.6
62.5°	328.6	327.1	325.7	324.2	324.2	325.0	330.1	334.8	344.9	349.1	356.6
65°	286.2	286.2	283.0	284.1	284.6	280.8	283.5	288.9	295.4	297.1	304.0
67.5°	243.4	241.9	240.0	238.4	238.4	238.1	239.5	242.2	247.0	247.6	252.9
70°	214.0	212.9	212.4	210.8	208.7	211.4	209.7	212.4	215.1	215.6	218.9
72.5°	185.5	184.5	183.5	181.9	181.0	180.7	180.8	183.9	185.8	185.0	188.7
75°	145.0	143.9	142.8	140.1	140.1	138.6	139.1	141.2	143.4	141.8	145.0
77.5°	106.5	103.1	103.0	103.7	101.9	102.2	101.6	101.2	102.2	102.3	105.2
80°	81.9	78.2	79.2	78.7	78.2	77.6	76.5	77.1	77.6	78.2	79.8
82.5°	59.1	58.8	57.7	57.6	57.0	55.6	55.0	55.9	56.5	56.2	57.4
85°	30.2	28.6	29.6	29.1	29.6	29.1	27.5	27.5	28.6	28.0	29.1
87.5°	13.0	12.9	12.0	12.0	11.1	11.0	10.2	10.3	10.4	10.0	10.5
90°	19.8	19.1	16.8	14.5	12.2	9.9	7.8	6.1	4.4	2.5	0.8
92.5°	21.5	20.4	18.6	16.9	15.2	13.5	12.8	13.3	13.8	14.3	14.8
95°	25.9	24.6	22.7	20.8	18.9	16.9	19.6	26.8	34.1	41.3	48.6
97.5°	27.0	25.6	38.3	51.1	63.8	76.5	84.5	87.8	91.0	94.3	97.5
100°	27.6	26.2	53.9	81.4	109.0	136.6	148.6	145.0	141.6	138.0	134.4
102.5°	48.0	52.4	82.5	112.6	142.8	172.9	186.6	184.1	181.6	179.0	176.5
105°	143.0	174.3	190.2	206.0	222.0	237.9	244.9	243.0	241.0	239.1	237.1
107.5°	296.4	319.4	316.9	314.3	311.9	309.3	307.3	305.8	304.2	302.6	301.1
110°	353.0	358.9	356.9	355.0	353.0	351.1	349.4	348.0	346.6	345.2	343.7



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	399.0	398.9	397.0	395.1	393.1	391.2	389.6	388.3	387.0	385.7	384.4
115°	458.5	456.7	455.1	453.5	451.9	450.4	449.0	448.0	446.9	445.8	444.8
117.5°	514.1	512.7	511.9	511.1	510.3	509.5	508.4	507.1	505.8	504.5	503.2
120°	550.4	549.0	548.5	548.0	547.4	546.9	545.8	544.2	542.6	541.1	539.5
122.5°	586.3	585.3	584.6	583.9	583.3	582.6	581.6	580.3	579.0	577.7	576.4
125°	636.9	636.5	635.8	635.1	634.4	633.7	632.6	631.2	629.8	628.4	627.0
127.5°	686.7	686.2	685.3	684.5	683.7	682.8	681.7	680.2	678.8	677.4	676.0
130°	716.8	716.1	715.4	714.7	714.0	713.3	712.3	710.8	709.4	708.0	706.5
132.5°	745.4	744.7	744.2	743.6	743.1	742.5	741.5	740.1	738.6	737.3	735.9
135°	789.0	788.5	787.8	787.1	786.4	785.7	784.8	783.7	782.7	781.6	780.5
137.5°	827.4	826.6	826.2	825.8	825.4	825.0	824.1	822.8	821.4	820.1	818.7
140°	852.1	851.4	850.8	850.3	849.8	849.2	848.4	847.4	846.4	845.3	844.2
142.5°	875.5	874.9	874.4	873.9	873.3	872.8	872.0	870.9	869.9	868.8	867.8
145°	908.2	907.8	907.5	907.1	906.8	906.4	905.6	904.4	903.2	901.9	900.7
147.5°	937.3	937.0	936.6	936.3	935.9	935.6	935.0	934.1	933.3	932.6	931.8
150°	955.1	954.8	954.4	954.1	953.7	953.4	952.9	952.4	951.9	951.3	950.9
152.5°	970.7	970.1	969.9	969.6	969.5	969.2	969.0	968.8	968.5	968.3	968.0
155°	992.3	991.4	991.3	991.0	990.9	990.7	990.8	991.2	991.5	991.8	992.2
157.5°	1011.1	1010.0	1010.2	1010.3	1010.6	1010.7	1010.8	1010.9	1010.9	1011.0	1011.0
160°	1021.9	1020.9	1021.0	1021.2	1021.4	1021.5	1021.8	1021.9	1022.1	1022.2	1022.5
162.5°	1031.6	1030.4	1030.5	1030.8	1030.9	1031.1	1031.4	1031.9	1032.4	1032.8	1033.2
165°	1044.6	1043.1	1043.3	1043.5	1043.6	1043.9	1044.2	1044.7	1045.3	1045.8	1046.3
167.5°	1054.7	1053.3	1053.3	1053.3	1053.3	1053.3	1053.7	1054.4	1055.1	1055.8	1056.5
170°	1060.4	1059.1	1059.1	1059.1	1059.1	1059.1	1059.4	1060.1	1060.8	1061.5	1062.2
172.5°	1064.3	1062.9	1062.7	1062.6	1062.4	1062.3	1062.6	1063.5	1064.4	1065.2	1066.0
175°	1069.1	1067.8	1067.6	1067.5	1067.2	1067.1	1067.5	1068.3	1069.2	1070.1	1071.0
177.5°	1070.9	1069.7	1069.5	1069.4	1069.3	1069.1	1069.4	1070.2	1070.9	1071.5	1072.2
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1119.5	1121.7	1129.0	1134.2	1140.3	1143.7	1147.2	1149.8	1153.2	1154.1	1166.6
5°	1124.5	1135.3	1154.1	1168.2	1185.4	1204.3	1217.2	1223.1	1238.8	1251.7	1277.6
7.5°	1123.1	1146.1	1174.6	1204.0	1235.8	1265.1	1290.5	1320.7	1342.2	1374.4	1406.2
10°	1121.8	1152.5	1189.2	1226.9	1271.1	1312.1	1348.8	1389.7	1423.7	1468.5	1506.7
12.5°	1117.9	1155.2	1206.0	1250.6	1304.3	1360.8	1415.2	1467.8	1497.9	1572.4	1607.7
15°	1108.3	1152.5	1216.2	1284.0	1358.0	1424.7	1493.7	1548.8	1637.7	1703.0	1744.5
17.5°	1090.0	1151.9	1227.3	1309.3	1399.1	1487.2	1565.4	1648.8	1743.1	1822.1	1906.1
20°	1081.4	1149.3	1233.4	1324.0	1417.2	1516.9	1605.9	1706.2	1809.1	1886.7	1994.6
22.5°	1065.4	1142.4	1233.0	1333.9	1433.6	1536.8	1640.8	1741.9	1860.9	1967.9	2070.4
25°	1039.3	1125.6	1219.4	1332.1	1449.1	1552.5	1677.0	1811.3	1935.3	2072.7	2175.2
27.5°	1011.9	1104.0	1198.0	1302.8	1428.6	1551.5	1708.1	1859.8	2011.4	2130.1	2205.9
30°	990.8	1080.3	1177.3	1283.0	1407.5	1553.6	1728.8	1894.3	2042.0	2143.9	2186.5
32.5°	968.0	1058.8	1144.5	1255.4	1388.1	1552.3	1741.8	1914.5	2043.8	2111.6	2103.2
35°	932.1	1008.1	1091.6	1198.3	1354.7	1542.9	1749.3	1916.4	1995.7	1981.1	1871.1
37.5°	880.3	944.2	1026.5	1143.4	1315.9	1522.9	1734.2	1859.6	1854.4	1735.9	1576.6
40°	848.0	902.4	981.7	1104.5	1285.7	1510.0	1710.5	1791.9	1722.9	1557.4	1366.5
42.5°	805.7	855.8	935.1	1061.4	1252.5	1483.6	1665.2	1688.8	1553.8	1363.3	1188.4
45°	740.1	784.3	866.3	996.7	1202.7	1426.4	1554.7	1497.0	1315.3	1118.6	985.4
47.5°	669.7	715.7	794.5	928.5	1130.7	1340.2	1401.4	1278.7	1092.2	932.6	810.3
50°	625.3	669.6	746.6	881.9	1081.9	1269.6	1294.8	1136.4	965.0	824.8	724.5
52.5°	580.5	622.1	697.9	833.6	1025.0	1187.6	1172.0	1010.4	852.8	733.3	654.7
55°	513.7	553.1	625.3	752.6	926.7	1055.5	998.9	844.7	714.3	621.5	561.7
57.5°	454.0	491.7	554.1	669.0	820.4	908.9	836.9	706.9	603.2	531.9	487.2
60°	413.4	446.9	506.2	612.9	744.5	811.8	740.7	625.9	538.5	481.4	441.5
62.5°	375.1	404.2	459.1	556.0	670.3	726.9	654.9	557.7	483.3	432.7	398.8
65°	317.0	343.4	391.9	467.4	561.2	598.9	536.9	458.2	400.5	362.8	340.2
67.5°	264.0	286.4	328.3	387.7	456.7	484.2	437.0	376.0	332.6	302.3	284.3
70°	228.5	248.0	280.8	332.1	394.6	415.7	371.5	321.3	289.5	265.2	248.5
72.5°	198.8	213.0	242.9	282.5	334.6	351.3	320.5	276.5	246.8	228.5	215.3
75°	151.5	163.3	182.8	214.5	250.6	260.4	237.2	209.7	189.7	176.8	166.6
77.5°	109.2	118.0	132.0	151.6	176.6	185.4	170.6	152.3	137.8	129.0	123.3
80°	82.5	89.5	101.3	117.5	132.6	137.4	128.8	114.8	104.6	99.7	94.9
82.5°	60.9	64.9	72.0	83.0	93.4	99.1	91.7	83.3	77.9	73.4	71.6
85°	30.7	32.9	36.1	40.4	46.9	49.0	46.3	44.2	41.0	38.3	38.3
87.5°	11.7	12.0	13.7	15.0	17.1	18.9	18.9	18.5	18.5	18.2	17.9
90°	2.5	4.4	6.1	7.8	9.9	12.2	14.5	16.8	19.1	19.8	20.5
92.5°	14.3	13.8	13.3	12.8	13.5	15.2	16.9	18.6	20.4	21.5	22.7
95°	41.3	34.1	26.8	19.6	16.9	18.9	20.8	22.7	24.6	25.9	27.2
97.5°	94.3	91.0	87.8	84.5	76.5	63.8	51.1	38.3	25.6	27.0	28.4
100°	138.0	141.6	145.0	148.6	136.6	109.0	81.4	53.9	26.2	27.6	29.1
102.5°	179.0	181.6	184.1	186.6	172.9	142.8	112.6	82.5	52.4	48.0	43.6
105°	239.1	241.0	243.0	244.9	237.9	222.0	206.0	190.2	174.3	143.0	111.7
107.5°	302.6	304.2	305.8	307.3	309.3	311.9	314.3	316.9	319.4	296.4	273.5
110°	345.2	346.6	348.0	349.4	351.1	353.0	355.0	356.9	358.9	353.0	347.2



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	385.7	387.0	388.3	389.6	391.2	393.1	395.1	397.0	398.9	399.0	399.2
115°	445.8	446.9	448.0	449.0	450.4	451.9	453.5	455.1	456.7	458.5	460.3
117.5°	504.5	505.8	507.1	508.4	509.5	510.3	511.1	511.9	512.7	514.1	515.6
120°	541.1	542.6	544.2	545.8	546.9	547.4	548.0	548.5	549.0	550.4	551.8
122.5°	577.7	579.0	580.3	581.6	582.6	583.3	583.9	584.6	585.3	586.3	587.2
125°	628.4	629.8	631.2	632.6	633.7	634.4	635.1	635.8	636.5	636.9	637.2
127.5°	677.4	678.8	680.2	681.7	682.8	683.7	684.5	685.3	686.2	686.7	687.3
130°	708.0	709.4	710.8	712.3	713.3	714.0	714.7	715.4	716.1	716.8	717.6
132.5°	737.3	738.6	740.1	741.5	742.5	743.1	743.6	744.2	744.7	745.4	746.2
135°	781.6	782.7	783.7	784.8	785.7	786.4	787.1	787.8	788.5	789.0	789.6
137.5°	820.1	821.4	822.8	824.1	825.0	825.4	825.8	826.2	826.6	827.4	828.2
140°	845.3	846.4	847.4	848.4	849.2	849.8	850.3	850.8	851.4	852.1	852.8
142.5°	868.8	869.9	870.9	872.0	872.8	873.3	873.9	874.4	874.9	875.5	876.1
145°	901.9	903.2	904.4	905.6	906.4	906.8	907.1	907.5	907.8	908.2	908.6
147.5°	932.6	933.3	934.1	935.0	935.6	935.9	936.3	936.6	937.0	937.3	937.7
150°	951.3	951.9	952.4	952.9	953.4	953.7	954.1	954.4	954.8	955.1	955.5
152.5°	968.3	968.5	968.8	969.0	969.2	969.5	969.6	969.9	970.1	970.7	971.4
155°	991.8	991.5	991.2	990.8	990.7	990.9	991.0	991.3	991.4	992.3	993.2
157.5°	1011.0	1010.9	1010.9	1010.8	1010.7	1010.6	1010.3	1010.2	1010.0	1011.1	1012.2
160°	1022.2	1022.1	1021.9	1021.8	1021.5	1021.4	1021.2	1021.0	1020.9	1021.9	1022.9
162.5°	1032.8	1032.4	1031.9	1031.4	1031.1	1030.9	1030.8	1030.5	1030.4	1031.6	1032.8
165°	1045.8	1045.3	1044.7	1044.2	1043.9	1043.6	1043.5	1043.3	1043.1	1044.6	1045.9
167.5°	1055.8	1055.1	1054.4	1053.7	1053.3	1053.3	1053.3	1053.3	1053.3	1054.7	1056.1
170°	1061.5	1060.8	1060.1	1059.4	1059.1	1059.1	1059.1	1059.1	1059.1	1060.4	1061.8
172.5°	1065.2	1064.4	1063.5	1062.6	1062.3	1062.4	1062.6	1062.7	1062.9	1064.3	1065.7
175°	1070.1	1069.2	1068.3	1067.5	1067.1	1067.2	1067.5	1067.6	1067.8	1069.1	1070.2
177.5°	1071.5	1070.9	1070.2	1069.4	1069.1	1069.3	1069.4	1069.5	1069.7	1070.9	1072.0
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1170.8	1171.3	1176.1	1179.5	1177.7	1180.0	1180.7
5°	1279.2	1298.6	1308.8	1316.4	1316.9	1317.5	1321.8
7.5°	1432.8	1453.7	1468.9	1491.9	1498.8	1506.7	1504.4
10°	1545.0	1575.7	1602.1	1616.1	1631.3	1653.4	1635.5
12.5°	1649.8	1704.2	1744.5	1766.2	1780.4	1784.9	1776.2
15°	1822.6	1893.8	1932.1	1930.9	1979.5	2000.5	1967.6
17.5°	1981.1	2046.8	2099.4	2126.3	2166.8	2175.7	2171.6
20°	2078.1	2149.8	2190.8	2237.1	2258.2	2277.0	2280.3
22.5°	2161.8	2226.2	2270.2	2308.7	2326.3	2335.3	2340.7
25°	2247.9	2298.6	2325.1	2338.5	2343.4	2342.2	2335.3
27.5°	2242.0	2245.9	2216.8	2188.2	2162.7	2133.9	2123.9
30°	2183.8	2138.5	2057.6	2011.8	1944.4	1891.1	1912.6
32.5°	2030.7	1940.5	1849.7	1749.6	1666.7	1643.1	1619.4
35°	1733.1	1574.6	1481.9	1374.1	1330.9	1287.9	1258.2
37.5°	1402.2	1279.5	1169.6	1099.1	1055.8	1028.6	1013.9
40°	1212.4	1101.8	1011.3	954.2	921.3	890.6	886.2
42.5°	1061.0	958.2	890.1	844.6	813.0	799.9	790.5
45°	869.0	797.3	751.5	719.1	698.1	690.0	679.2
47.5°	735.5	684.8	650.5	628.4	612.6	606.6	605.7
50°	660.9	618.9	593.5	576.2	563.9	561.7	553.1
52.5°	604.8	568.4	548.7	533.6	524.7	518.6	516.0
55°	525.1	500.8	483.0	474.4	467.4	461.4	461.4
57.5°	459.4	439.1	427.4	420.0	417.9	413.7	411.0
60°	418.8	401.6	392.4	386.0	381.7	382.2	377.3
62.5°	379.2	368.0	359.3	352.8	347.6	347.7	348.0
65°	322.9	314.3	307.8	305.6	302.5	298.7	299.8
67.5°	273.6	265.5	260.5	256.8	255.7	253.7	256.8
70°	238.3	232.3	228.5	225.3	224.3	224.8	227.5
72.5°	205.9	201.7	199.2	197.7	195.4	195.4	197.3
75°	161.7	158.5	156.3	154.7	154.2	154.2	154.2
77.5°	118.8	118.0	117.1	114.7	114.8	115.5	115.6
80°	93.8	92.2	91.7	90.5	89.0	87.9	90.5
82.5°	70.1	68.4	67.9	67.7	65.2	65.0	67.3
85°	37.7	36.1	36.7	36.1	36.1	35.6	35.6
87.5°	17.6	17.3	17.0	17.5	17.1	16.8	17.7
90°	21.2	21.9	22.4	22.8	23.1	23.5	23.8
92.5°	23.8	24.9	25.6	25.7	26.0	26.2	26.4
95°	28.4	29.6	30.3	30.3	30.3	30.3	30.3
97.5°	29.9	31.3	32.1	32.2	32.4	32.6	32.8
100°	30.5	31.9	32.7	32.9	33.0	33.3	33.4
102.5°	39.2	34.8	32.8	33.1	33.4	33.7	34.1
105°	80.3	49.0	33.6	34.0	34.3	34.6	35.0
107.5°	250.6	227.6	204.3	180.7	157.2	133.6	110.0
110°	341.4	335.5	320.0	294.7	269.3	244.1	218.8



TEST NUMBER: P332192-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	399.3	399.3	396.7	391.4	386.1	380.7	375.4
115°	462.0	463.8	465.0	465.7	466.4	467.1	467.9
117.5°	517.0	518.4	519.2	519.3	519.4	519.6	519.8
120°	553.3	554.7	555.4	555.4	555.4	555.4	555.4
122.5°	588.3	589.2	589.9	589.9	590.1	590.3	590.4
125°	637.6	637.9	638.3	638.7	639.0	639.4	639.7
127.5°	687.9	688.5	688.6	688.2	687.9	687.5	687.1
130°	718.2	718.9	719.1	718.7	718.4	718.0	717.7
132.5°	746.9	747.6	747.7	747.2	746.7	746.2	745.7
135°	790.1	790.6	790.6	790.1	789.6	789.0	788.5
137.5°	829.1	830.0	830.2	829.8	829.5	829.1	828.8
140°	853.5	854.2	854.4	854.1	853.7	853.3	852.9
142.5°	876.6	877.2	877.2	876.7	876.2	875.8	875.2
145°	908.9	909.3	909.4	909.4	909.4	909.4	909.4
147.5°	938.0	938.4	938.2	937.4	936.5	935.7	934.9
150°	955.8	956.2	956.2	955.6	955.1	954.6	954.0
152.5°	972.0	972.6	972.6	971.7	970.9	970.1	969.3
155°	994.0	995.0	994.8	993.8	992.8	991.7	990.6
157.5°	1013.2	1014.2	1014.1	1012.7	1011.4	1010.0	1008.6
160°	1024.1	1025.1	1025.0	1023.7	1022.5	1021.3	1020.0
162.5°	1034.0	1035.2	1035.2	1034.2	1033.1	1032.0	1030.9
165°	1047.3	1048.8	1048.8	1047.7	1046.4	1045.1	1043.9
167.5°	1057.6	1059.0	1059.0	1057.6	1056.1	1054.7	1053.3
170°	1063.3	1064.7	1064.7	1063.3	1061.8	1060.4	1059.1
172.5°	1067.1	1068.5	1068.4	1066.9	1065.3	1063.7	1062.2
175°	1071.5	1072.8	1072.7	1071.3	1069.8	1068.4	1067.0
177.5°	1073.1	1074.2	1074.1	1072.7	1071.3	1069.8	1068.4
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0

(END OF REPORT)