

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331841-935

Luminaire Tested: **S122RDIW-S865D1440U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331841-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S865D1440U935-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7805.0 lumens  
Efficiency: N/A  
Efficacy: 101.9 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	88	84	86	83	80	77	67	65	63	53	51	50	39	39	38	32
2	87	80	75	70	79	73	68	64	60	56	53	47	45	43	35	34	33	28
3	80	71	64	59	72	65	59	54	53	49	45	42	39	37	32	30	29	24
4	73	63	56	50	66	58	52	47	48	43	39	38	35	32	29	27	25	21
5	68	57	49	43	61	52	45	40	43	38	34	34	31	28	26	24	22	19
6	62	51	43	38	57	47	40	35	39	34	30	31	28	25	24	22	20	17
7	58	46	39	33	52	42	36	31	35	30	27	29	25	22	22	20	18	15
8	54	42	35	30	49	39	32	28	32	27	24	26	23	20	21	18	16	14
9	50	39	31	27	46	36	29	25	30	25	22	24	21	18	19	17	15	13
10	47	35	29	24	43	33	27	23	27	23	20	23	19	17	18	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	26547	26547	26547	26547
5°	29648	26712	23686	26712
10°	32893	26525	20530	26525
15°	34511	26136	16177	26136
20°	29919	25560	13998	25560
25°	19621	24772	12497	24772
30°	13207	23815	11311	23815
35°	10697	22610	10200	22610
40°	9512	21300	9440	21300
45°	8608	19763	8426	19763
50°	7834	18239	7804	18239
55°	7367	16549	7268	16549
60°	6161	14996	6090	14996
65°	5196	13620	5891	13620
70°	4801	12161	5556	12161
75°	4492	10586	5128	10586
80°	4147	8712	4575	8712
85°	3816	6873	4020	6873



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.9	2.0
10°-20°	434.3	5.6
20°-30°	559.6	7.2
30°-40°	531.8	6.8
40°-50°	455.6	5.8
50°-60°	346.9	4.4
60°-70°	219.3	2.8
70°-80°	109.5	1.4
80°-90°	32.7	0.4
90°-100°	56.5	0.7
100°-110°	207.0	2.7
110°-120°	553.4	7.1
120°-130°	913.5	11.7
130°-140°	971.4	12.4
140°-150°	902.9	11.6
150°-160°	726.0	9.3
160°-170°	467.8	6.0
170°-180°	161.0	2.1
0°-30°	1149.8	14.7
0°-40°	1681.6	21.5
0°-60°	2484.1	31.8
0°-90°	2845.6	36.5
90°-120°	816.8	10.5
90°-150°	3604.6	46.2
90°-180°	4959.0	63.5
0°-180°	7805.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1829	1648	1461	1648	1829	181
15°	2065	1564	968	1564	2065	557
25°	1101	1390	702	1390	1101	523
35°	543	1147	518	1147	543	347
45°	377	866	369	866	377	292
55°	262	588	258	588	262	230
65°	136	356	154	356	136	138
75°	72	170	82	170	72	76
85°	21	37	22	37	21	23
90°	33	1	33	1	33	16
95°	53	80	53	80	53	49
105°	93	372	93	372	93	97
115°	100	704	100	704	100	251
125°	1047	996	1047	996	1047	906
135°	1272	1232	1272	1232	1272	981
145°	1451	1429	1451	1429	1451	907
155°	1575	1574	1575	1574	1575	727
165°	1654	1658	1654	1658	1654	467
175°	1686	1696	1686	1696	1686	161
180°	1692	1692	1692	1692	1692	



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1710.9	1712.3	1713.6	1710.4	1710.4	1707.7	1701.8	1697.2	1684.4	1682.6	1682.6
5°	1829.3	1828.1	1830.4	1823.0	1812.7	1810.4	1799.6	1785.3	1770.4	1753.9	1750.4
7.5°	1946.9	1945.2	1940.6	1939.4	1931.5	1914.3	1896.8	1878.2	1853.5	1829.4	1817.2
10°	2006.3	2025.2	2013.8	1993.7	1997.8	1970.9	1956.6	1932.1	1911.5	1875.5	1867.5
12.5°	2064.9	2072.3	2068.6	2057.3	2052.2	2033.5	2014.2	1992.9	1954.9	1922.6	1894.5
15°	2064.6	2075.4	2078.3	2074.9	2077.8	2076.6	2066.3	2048.6	2015.5	1980.0	1949.2
17.5°	1912.2	1919.8	1938.5	1951.1	1967.1	2001.0	2017.7	2024.1	2019.2	1999.0	1977.3
20°	1741.3	1728.7	1781.2	1808.1	1830.9	1888.1	1937.2	1956.1	1986.3	1985.8	1980.0
22.5°	1499.0	1502.0	1551.9	1583.7	1650.5	1707.5	1763.6	1834.5	1893.1	1931.8	1954.5
25°	1101.4	1123.2	1172.9	1216.2	1290.6	1396.8	1493.3	1605.3	1711.0	1794.4	1873.8
27.5°	827.2	828.8	868.2	908.4	952.4	1039.5	1161.1	1294.8	1445.4	1569.8	1712.8
30°	708.4	705.0	721.5	746.1	783.8	851.2	942.6	1074.0	1224.3	1411.6	1578.5
32.5°	624.3	624.5	637.0	655.1	686.5	731.9	794.5	901.3	1043.3	1227.4	1423.1
35°	542.7	542.2	551.3	564.4	577.6	606.7	649.5	705.5	803.2	975.2	1175.1
37.5°	484.2	486.7	491.2	499.4	513.9	530.1	555.9	593.5	663.1	764.7	932.8
40°	451.3	452.5	458.7	465.6	474.2	486.7	507.9	538.1	589.0	670.1	792.9
42.5°	421.1	422.3	426.7	433.2	439.9	452.5	469.9	496.1	537.4	600.6	702.0
45°	377.0	377.0	381.1	383.9	391.3	402.8	417.1	438.8	467.3	514.2	581.6
47.5°	335.7	335.8	338.5	343.4	348.0	357.0	371.0	388.7	409.5	445.7	503.3
50°	311.9	312.5	314.2	318.2	321.1	329.1	339.9	355.3	377.0	405.0	453.1
52.5°	292.7	292.4	294.5	296.3	298.3	303.9	312.0	325.6	345.1	369.4	409.1
55°	261.7	259.3	262.8	265.6	267.3	269.7	274.2	282.8	299.4	319.9	349.7
57.5°	222.8	221.9	224.3	226.9	232.3	238.4	242.4	247.8	256.4	271.1	300.6
60°	190.8	190.8	196.0	197.7	204.0	212.0	220.0	224.5	233.1	242.8	264.5
62.5°	162.5	162.9	165.3	167.0	170.6	180.4	191.6	201.6	209.7	219.0	233.4
65°	136.0	137.1	137.1	138.3	140.5	142.8	147.4	155.4	169.7	182.8	193.6
67.5°	115.4	115.7	116.1	117.3	117.8	120.3	122.2	125.7	129.0	141.5	154.9
70°	101.7	103.4	102.8	104.0	104.5	105.6	108.0	109.7	114.9	117.7	125.7
72.5°	88.9	90.1	90.1	90.7	92.2	92.5	94.3	96.0	99.3	101.7	106.0
75°	72.0	71.4	72.0	73.1	73.7	74.3	74.3	76.5	78.3	80.6	83.4
77.5°	55.5	56.1	56.0	56.1	56.2	57.3	57.2	58.1	59.8	61.0	62.4
80°	44.6	45.1	44.6	45.1	45.7	46.2	45.7	46.2	48.0	49.2	49.2
82.5°	34.5	34.6	35.0	35.0	35.2	35.3	36.1	36.2	37.5	37.3	37.7
85°	20.6	20.0	20.0	20.0	20.6	21.1	20.6	20.6	21.1	21.1	21.1
87.5°	13.9	14.3	14.2	14.0	13.9	13.8	13.5	13.7	12.9	13.1	12.2
90°	33.1	32.5	31.9	31.4	30.9	30.0	28.6	27.2	25.8	24.5	22.3
92.5°	33.1	32.7	32.4	32.1	31.8	31.3	30.6	29.8	29.1	28.4	27.3
95°	52.7	53.0	53.2	53.5	53.7	53.2	51.8	50.5	49.1	47.8	45.9
97.5°	70.3	70.0	69.7	69.3	69.0	68.3	67.2	66.1	65.0	63.9	59.5
100°	82.1	81.5	80.9	80.4	79.9	78.5	76.4	74.1	72.0	69.8	65.2
102.5°	87.9	87.1	86.4	85.7	84.9	83.1	80.2	77.4	74.6	71.7	110.5
105°	93.1	92.0	90.9	89.8	88.7	86.7	83.7	80.7	77.7	74.7	149.0
107.5°	95.7	94.7	93.6	92.5	91.4	92.4	95.4	98.5	101.5	104.6	193.6
110°	96.8	95.7	94.5	93.5	92.4	105.5	132.7	159.9	187.1	214.3	292.9



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	97.7	96.9	96.0	95.1	94.2	143.4	242.7	342.0	441.3	540.5	559.9
115°	100.4	120.0	139.6	159.2	178.7	251.6	377.5	503.6	629.6	755.5	748.7
117.5°	410.0	474.3	538.7	603.1	667.5	715.0	745.5	775.9	806.4	836.9	832.2
120°	747.0	783.7	820.4	857.2	893.9	910.7	907.4	904.1	900.9	897.6	892.7
122.5°	932.1	939.3	946.4	953.5	960.6	963.2	961.3	959.3	957.3	955.4	950.0
125°	1047.0	1046.2	1045.3	1044.6	1043.7	1042.3	1040.4	1038.5	1036.6	1034.7	1029.6
127.5°	1119.5	1119.3	1119.1	1119.0	1118.9	1117.3	1114.6	1111.8	1109.1	1106.3	1102.4
130°	1164.5	1164.8	1165.1	1165.4	1165.6	1164.2	1161.3	1158.3	1155.3	1152.3	1149.3
132.5°	1208.6	1208.9	1209.2	1209.4	1209.7	1208.6	1206.0	1203.4	1200.9	1198.3	1195.3
135°	1272.3	1272.8	1273.4	1273.9	1274.5	1273.4	1270.7	1267.9	1265.2	1262.5	1260.1
137.5°	1330.3	1331.3	1332.2	1333.1	1334.0	1333.2	1330.5	1327.8	1325.2	1322.5	1319.7
140°	1366.6	1368.0	1369.3	1370.7	1372.0	1371.5	1369.1	1366.6	1364.2	1361.7	1358.7
142.5°	1401.9	1403.3	1404.5	1405.9	1407.3	1406.9	1404.6	1402.4	1400.2	1397.9	1394.5
145°	1451.1	1452.4	1453.8	1455.2	1456.6	1456.3	1454.3	1452.4	1450.5	1448.6	1444.0
147.5°	1494.4	1495.6	1496.8	1497.9	1499.0	1498.9	1497.5	1496.1	1494.6	1493.2	1488.7
150°	1520.9	1522.2	1523.6	1525.0	1526.3	1526.2	1524.6	1522.9	1521.3	1519.7	1515.3
152.5°	1543.4	1545.2	1547.0	1548.8	1550.6	1550.7	1549.0	1547.4	1545.8	1544.1	1540.0
155°	1574.8	1576.9	1579.2	1581.3	1583.5	1583.7	1582.1	1580.5	1578.8	1577.2	1574.0
157.5°	1603.4	1605.5	1607.7	1609.8	1611.9	1612.1	1610.2	1608.3	1606.5	1604.6	1602.3
160°	1620.1	1622.0	1623.8	1625.8	1627.7	1627.8	1626.2	1624.5	1622.9	1621.3	1619.6
162.5°	1633.8	1636.2	1638.5	1640.8	1643.1	1643.4	1641.6	1639.7	1637.9	1636.0	1634.6
165°	1654.3	1656.3	1658.2	1660.1	1662.0	1662.0	1660.1	1658.2	1656.3	1654.3	1653.6
167.5°	1667.3	1669.8	1672.2	1674.7	1677.1	1677.4	1675.5	1673.6	1671.7	1669.8	1669.0
170°	1675.2	1677.7	1680.1	1682.6	1685.0	1685.2	1683.3	1681.4	1679.6	1677.7	1677.1
172.5°	1681.0	1683.5	1685.9	1688.4	1690.8	1691.1	1689.2	1687.3	1685.4	1683.5	1683.0
175°	1686.2	1688.9	1691.6	1694.4	1697.1	1697.5	1695.6	1693.7	1691.8	1689.9	1689.4
177.5°	1689.4	1691.3	1693.3	1695.2	1697.2	1697.5	1695.9	1694.4	1692.9	1691.3	1691.1
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1683.4	1679.8	1676.6	1668.4	1664.2	1655.1	1653.7	1653.3	1641.4	1630.0	1626.8
5°	1741.3	1732.2	1718.4	1702.5	1685.8	1668.7	1657.3	1648.1	1625.3	1603.6	1591.0
7.5°	1799.6	1779.9	1756.3	1726.0	1700.7	1672.4	1651.3	1632.5	1600.1	1569.0	1548.1
10°	1843.0	1810.9	1779.5	1737.8	1705.3	1673.3	1643.6	1617.9	1581.3	1540.2	1511.1
12.5°	1869.9	1834.7	1791.4	1750.7	1708.5	1667.8	1628.1	1595.0	1552.0	1509.6	1474.9
15°	1906.3	1868.6	1816.1	1757.8	1703.6	1650.5	1604.7	1563.6	1507.6	1456.7	1414.5
17.5°	1936.2	1884.3	1827.9	1760.5	1697.6	1630.1	1571.2	1518.7	1456.4	1395.1	1345.2
20°	1945.8	1894.4	1829.3	1761.9	1687.6	1608.2	1544.7	1487.6	1420.7	1353.9	1296.8
22.5°	1939.8	1899.9	1827.4	1746.7	1670.7	1587.6	1516.0	1449.7	1375.5	1307.3	1241.0
25°	1899.5	1885.8	1817.2	1729.2	1642.4	1545.9	1463.0	1390.5	1306.0	1232.9	1160.8
27.5°	1805.5	1835.0	1792.6	1698.8	1602.3	1498.8	1405.7	1323.1	1235.4	1153.1	1081.3
30°	1715.0	1783.0	1764.7	1677.8	1569.9	1468.2	1363.7	1277.4	1183.7	1099.2	1028.3
32.5°	1591.1	1703.4	1721.3	1648.6	1537.0	1425.2	1315.7	1229.9	1132.0	1042.9	973.9
35°	1394.0	1561.9	1639.0	1592.8	1480.7	1360.2	1247.1	1147.1	1048.9	960.9	892.3
37.5°	1158.6	1387.4	1516.0	1519.2	1416.4	1291.1	1167.9	1068.7	968.1	881.8	807.5
40°	1006.0	1254.0	1421.3	1458.4	1371.7	1236.2	1111.7	1010.6	912.3	827.8	742.7
42.5°	868.9	1115.9	1321.7	1386.3	1317.2	1182.8	1057.8	952.1	856.6	776.6	689.7
45°	702.7	918.6	1145.4	1260.8	1222.5	1098.0	966.0	865.5	775.8	706.7	623.3
47.5°	592.8	744.9	964.4	1120.5	1119.8	1006.2	876.3	780.1	696.8	632.1	564.6
50°	530.1	662.7	848.3	1025.5	1040.3	944.9	821.5	726.1	648.4	580.4	526.2
52.5°	473.9	583.2	750.1	919.9	962.2	879.5	759.8	671.8	596.3	533.8	487.3
55°	400.5	485.0	611.8	770.7	834.7	776.4	670.1	587.9	526.8	474.2	434.2
57.5°	338.8	402.2	503.9	631.8	706.4	669.7	582.0	515.2	462.9	415.3	383.7
60°	299.9	351.9	438.2	545.0	627.2	601.6	526.8	464.4	419.9	378.8	349.0
62.5°	263.4	308.1	381.9	468.6	544.1	533.5	472.3	420.1	381.1	343.5	318.4
65°	212.0	244.5	302.2	370.2	430.8	435.9	391.9	356.5	321.7	292.0	269.7
67.5°	168.8	190.0	230.7	287.9	333.3	349.5	322.6	295.6	267.9	245.0	225.7
70°	142.2	159.4	189.1	235.4	277.1	294.2	278.8	257.6	233.7	214.8	198.2
72.5°	115.3	132.0	153.9	187.9	223.6	242.1	236.8	221.5	202.1	186.5	170.8
75°	86.9	92.0	106.9	129.7	157.6	173.7	177.7	169.7	154.2	142.2	133.1
77.5°	64.2	67.3	74.4	86.4	104.7	118.9	124.8	123.8	113.2	106.2	97.7
80°	51.4	53.1	56.6	61.7	75.4	89.7	93.7	93.7	86.3	83.4	74.8
82.5°	39.1	40.3	42.4	45.2	51.7	64.1	68.5	69.5	64.7	61.0	54.2
85°	22.3	21.7	22.8	24.5	25.7	29.1	36.0	37.1	36.0	31.4	29.7
87.5°	11.8	11.8	11.4	10.4	10.2	10.2	11.8	13.5	12.2	11.5	11.2
90°	20.1	18.0	15.8	13.2	10.2	7.2	4.2	1.2	4.2	7.2	10.2
92.5°	26.3	25.1	24.0	23.7	23.9	24.2	24.5	24.7	24.5	24.2	23.9
95°	43.9	42.0	40.1	43.7	52.7	61.6	70.6	79.6	70.6	61.6	52.7
97.5°	55.1	50.7	46.3	56.7	82.1	107.4	132.7	158.0	132.7	107.4	82.1
100°	60.5	55.9	51.3	67.6	104.9	142.2	179.4	216.7	179.4	142.2	104.9
102.5°	149.1	187.9	226.5	249.9	257.7	265.6	273.5	281.4	273.5	265.6	257.7
105°	223.3	297.6	371.9	404.9	396.7	388.6	380.4	372.3	380.4	388.6	396.7
107.5°	282.8	371.9	461.0	502.2	495.6	489.0	482.4	475.9	482.4	489.0	495.6
110°	371.6	450.2	528.8	565.3	559.6	553.9	548.2	542.5	548.2	553.9	559.6





TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	579.4	598.8	618.2	625.4	620.4	615.3	610.2	605.2	610.2	615.3	620.4
115°	741.9	735.1	728.3	722.6	718.0	713.3	708.8	704.1	708.8	713.3	718.0
117.5°	827.5	822.8	818.1	813.2	808.0	802.9	797.7	792.6	797.7	802.9	808.0
120°	887.8	882.9	878.0	873.5	869.4	865.3	861.3	857.2	861.3	865.3	869.4
122.5°	944.7	939.4	934.1	929.3	925.0	920.7	916.4	912.1	916.4	920.7	925.0
125°	1024.4	1019.3	1014.1	1009.7	1006.2	1002.6	999.1	995.6	999.1	1002.6	1006.2
127.5°	1098.5	1094.7	1090.8	1086.9	1083.0	1079.1	1075.1	1071.3	1075.1	1079.1	1083.0
130°	1146.3	1143.3	1140.3	1136.7	1132.3	1127.9	1123.6	1119.2	1123.6	1127.9	1132.3
132.5°	1192.3	1189.4	1186.4	1183.0	1179.3	1175.6	1171.9	1168.2	1171.9	1175.6	1179.3
135°	1257.6	1255.2	1252.7	1249.3	1244.9	1240.6	1236.2	1231.9	1236.2	1240.6	1244.9
137.5°	1317.0	1314.1	1311.4	1308.5	1305.4	1302.4	1299.3	1296.3	1299.3	1302.4	1305.4
140°	1355.7	1352.7	1349.7	1347.1	1345.0	1342.8	1340.6	1338.4	1340.6	1342.8	1345.0
142.5°	1391.1	1387.7	1384.2	1381.6	1379.6	1377.6	1375.6	1373.7	1375.6	1377.6	1379.6
145°	1439.4	1434.8	1430.1	1428.0	1428.2	1428.5	1428.7	1429.1	1428.7	1428.5	1428.2
147.5°	1484.1	1479.5	1474.9	1473.2	1474.2	1475.2	1476.3	1477.3	1476.3	1475.2	1474.2
150°	1511.0	1506.6	1502.3	1501.0	1503.0	1504.9	1506.8	1508.6	1506.8	1504.9	1503.0
152.5°	1535.9	1531.7	1527.6	1526.6	1528.7	1530.9	1533.0	1535.1	1533.0	1530.9	1528.7
155°	1570.7	1567.5	1564.2	1563.7	1566.2	1568.7	1571.1	1573.6	1571.1	1568.7	1566.2
157.5°	1600.1	1597.8	1595.5	1595.4	1597.5	1599.6	1601.6	1603.7	1601.6	1599.6	1597.5
160°	1618.1	1616.4	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3	1619.6	1618.1	1616.4
162.5°	1633.1	1631.8	1630.3	1630.5	1632.1	1633.7	1635.4	1636.9	1635.4	1633.7	1632.1
165°	1652.7	1651.9	1651.1	1651.5	1653.1	1654.8	1656.4	1658.0	1656.4	1654.8	1653.1
167.5°	1668.3	1667.5	1666.7	1667.2	1668.8	1670.4	1672.1	1673.7	1672.1	1670.4	1668.8
170°	1676.5	1676.0	1675.4	1676.0	1677.7	1679.3	1680.9	1682.6	1680.9	1679.3	1677.7
172.5°	1682.4	1681.9	1681.4	1681.9	1683.5	1685.1	1686.8	1688.4	1686.8	1685.1	1683.5
175°	1688.8	1688.2	1687.7	1688.4	1690.3	1692.2	1694.1	1696.0	1694.1	1692.2	1690.3
177.5°	1690.9	1690.7	1690.5	1691.1	1692.6	1694.2	1695.7	1697.2	1695.7	1694.2	1692.6
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1620.8	1617.6	1611.7	1602.6	1597.1	1587.5	1581.1	1584.8	1585.6	1584.8	1583.8
5°	1577.3	1565.3	1548.8	1532.8	1517.9	1501.9	1492.7	1488.8	1480.7	1476.2	1473.9
7.5°	1524.7	1504.0	1480.5	1452.7	1429.0	1404.2	1391.5	1385.3	1368.9	1359.9	1352.2
10°	1485.3	1452.8	1429.3	1392.8	1370.5	1337.9	1315.7	1316.2	1293.9	1281.3	1272.2
12.5°	1441.9	1406.2	1367.2	1334.3	1303.3	1277.1	1250.3	1239.4	1215.8	1203.7	1179.0
15°	1369.9	1328.3	1287.1	1242.5	1211.1	1170.5	1131.7	1084.3	1046.0	1012.9	1003.8
17.5°	1291.3	1239.7	1198.4	1146.1	1092.3	1024.1	979.0	951.5	928.4	910.9	897.9
20°	1237.4	1184.8	1140.8	1062.0	989.5	943.2	910.1	888.9	865.0	846.1	835.8
22.5°	1180.7	1125.8	1065.9	977.9	921.4	884.2	854.7	830.4	814.2	799.4	790.1
25°	1100.3	1040.3	941.5	880.9	835.2	796.3	775.8	761.0	743.8	723.8	714.6
27.5°	1015.3	919.9	848.9	803.9	760.3	735.0	716.5	694.3	679.0	670.0	660.5
30°	951.7	856.4	800.9	751.8	720.9	692.9	671.2	658.7	643.9	628.4	622.2
32.5°	880.9	804.7	751.6	710.7	679.3	655.5	638.3	618.0	607.3	597.8	584.6
35°	792.9	735.2	686.6	653.6	623.9	604.4	584.4	572.4	553.0	545.0	539.8
37.5°	718.4	668.4	632.1	597.2	573.7	552.2	539.9	520.9	512.5	501.4	490.5
40°	676.4	627.2	592.5	563.9	537.6	521.6	506.2	490.8	478.2	473.0	459.9
42.5°	633.4	593.5	558.6	527.3	509.7	492.8	473.3	461.9	448.9	440.6	432.5
45°	574.1	538.7	509.0	483.3	463.9	446.2	433.6	414.7	407.3	390.7	383.9
47.5°	522.0	489.1	460.8	436.4	417.4	405.9	387.4	372.7	360.8	350.7	341.8
50°	485.0	457.6	430.2	408.5	391.3	374.8	355.9	348.4	330.2	325.0	319.9
52.5°	451.2	425.2	400.0	378.8	361.6	345.5	328.9	319.3	306.9	301.8	298.0
55°	403.9	378.8	354.7	335.9	318.7	302.2	292.0	279.9	274.2	270.2	265.6
57.5°	356.4	333.7	315.4	296.3	279.1	265.9	254.0	246.8	240.8	235.6	230.1
60°	326.2	304.4	287.9	270.2	252.5	241.7	232.5	223.9	217.1	209.1	206.8
62.5°	294.2	275.3	260.0	242.8	227.4	217.4	208.7	200.6	192.4	180.7	177.5
65°	250.2	235.4	219.4	205.1	191.4	181.7	169.1	160.0	156.5	155.4	154.8
67.5°	210.4	196.4	182.7	168.1	155.6	146.6	140.2	138.8	136.4	135.7	134.1
70°	183.9	170.8	157.1	143.4	131.4	129.7	127.4	125.1	122.3	121.1	119.9
72.5°	160.1	146.6	132.9	121.9	116.8	114.6	112.3	110.0	108.1	106.9	106.2
75°	122.9	110.3	101.1	97.1	94.3	92.6	89.1	87.4	86.3	84.6	83.9
77.5°	88.4	81.4	77.1	74.6	71.6	69.8	67.8	66.1	64.9	64.6	63.6
80°	67.4	64.0	61.1	57.7	56.6	54.2	53.7	52.0	52.5	50.9	50.9
82.5°	52.3	48.0	45.5	44.0	42.9	41.0	40.5	39.6	39.8	38.5	38.5
85°	26.9	25.7	24.5	23.4	23.4	21.7	22.3	21.7	21.7	20.6	20.0
87.5°	11.4	11.4	10.9	11.4	11.8	11.8	12.1	11.9	12.1	12.4	12.1
90°	13.2	15.8	18.0	20.1	22.3	24.5	25.8	27.2	28.6	30.0	30.9
92.5°	23.7	24.0	25.1	26.3	27.3	28.4	29.1	29.8	30.6	31.3	31.8
95°	43.7	40.1	42.0	43.9	45.9	47.8	49.1	50.5	51.8	53.2	53.7
97.5°	56.7	46.3	50.7	55.1	59.5	63.9	65.0	66.1	67.2	68.3	69.0
100°	67.6	51.3	55.9	60.5	65.2	69.8	72.0	74.1	76.4	78.5	79.9
102.5°	249.9	226.5	187.9	149.1	110.5	71.7	74.6	77.4	80.2	83.1	84.9
105°	404.9	371.9	297.6	223.3	149.0	74.7	77.7	80.7	83.7	86.7	88.7
107.5°	502.2	461.0	371.9	282.8	193.6	104.6	101.5	98.5	95.4	92.4	91.4
110°	565.3	528.8	450.2	371.6	292.9	214.3	187.1	159.9	132.7	105.5	92.4



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	625.4	618.2	598.8	579.4	559.9	540.5	441.3	342.0	242.7	143.4	94.2
115°	722.6	728.3	735.1	741.9	748.7	755.5	629.6	503.6	377.5	251.6	178.7
117.5°	813.2	818.1	822.8	827.5	832.2	836.9	806.4	775.9	745.5	715.0	667.5
120°	873.5	878.0	882.9	887.8	892.7	897.6	900.9	904.1	907.4	910.7	893.9
122.5°	929.3	934.1	939.4	944.7	950.0	955.4	957.3	959.3	961.3	963.2	960.6
125°	1009.7	1014.1	1019.3	1024.4	1029.6	1034.7	1036.6	1038.5	1040.4	1042.3	1043.7
127.5°	1086.9	1090.8	1094.7	1098.5	1102.4	1106.3	1109.1	1111.8	1114.6	1117.3	1118.9
130°	1136.7	1140.3	1143.3	1146.3	1149.3	1152.3	1155.3	1158.3	1161.3	1164.2	1165.6
132.5°	1183.0	1186.4	1189.4	1192.3	1195.3	1198.3	1200.9	1203.4	1206.0	1208.6	1209.7
135°	1249.3	1252.7	1255.2	1257.6	1260.1	1262.5	1265.2	1267.9	1270.7	1273.4	1274.5
137.5°	1308.5	1311.4	1314.1	1317.0	1319.7	1322.5	1325.2	1327.8	1330.5	1333.2	1334.0
140°	1347.1	1349.7	1352.7	1355.7	1358.7	1361.7	1364.2	1366.6	1369.1	1371.5	1372.0
142.5°	1381.6	1384.2	1387.7	1391.1	1394.5	1397.9	1400.2	1402.4	1404.6	1406.9	1407.3
145°	1428.0	1430.1	1434.8	1439.4	1444.0	1448.6	1450.5	1452.4	1454.3	1456.3	1456.6
147.5°	1473.2	1474.9	1479.5	1484.1	1488.7	1493.2	1494.6	1496.1	1497.5	1498.9	1499.0
150°	1501.0	1502.3	1506.6	1511.0	1515.3	1519.7	1521.3	1522.9	1524.6	1526.2	1526.3
152.5°	1526.6	1527.6	1531.7	1535.9	1540.0	1544.1	1545.8	1547.4	1549.0	1550.7	1550.6
155°	1563.7	1564.2	1567.5	1570.7	1574.0	1577.2	1578.8	1580.5	1582.1	1583.7	1583.5
157.5°	1595.4	1595.5	1597.8	1600.1	1602.3	1604.6	1606.5	1608.3	1610.2	1612.1	1611.9
160°	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3	1622.9	1624.5	1626.2	1627.8	1627.7
162.5°	1630.5	1630.3	1631.8	1633.1	1634.6	1636.0	1637.9	1639.7	1641.6	1643.4	1643.1
165°	1651.5	1651.1	1651.9	1652.7	1653.6	1654.3	1656.3	1658.2	1660.1	1662.0	1662.0
167.5°	1667.2	1666.7	1667.5	1668.3	1669.0	1669.8	1671.7	1673.6	1675.5	1677.4	1677.1
170°	1676.0	1675.4	1676.0	1676.5	1677.1	1677.7	1679.6	1681.4	1683.3	1685.2	1685.0
172.5°	1681.9	1681.4	1681.9	1682.4	1683.0	1683.5	1685.4	1687.3	1689.2	1691.1	1690.8
175°	1688.4	1687.7	1688.2	1688.8	1689.4	1689.9	1691.8	1693.7	1695.6	1697.5	1697.1
177.5°	1691.1	1690.5	1690.7	1690.9	1691.1	1691.3	1692.9	1694.4	1695.9	1697.5	1697.2
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1578.8	1579.7	1578.3	1579.2	1578.3	1579.7	1578.8	1583.8	1584.8	1585.6	1584.8
5°	1471.0	1464.2	1463.0	1461.4	1463.0	1464.2	1471.0	1473.9	1476.2	1480.7	1488.8
7.5°	1342.4	1341.4	1338.5	1334.6	1338.5	1341.4	1342.4	1352.2	1359.9	1368.9	1385.3
10°	1259.6	1256.8	1256.3	1252.2	1256.3	1256.8	1259.6	1272.2	1281.3	1293.9	1316.2
12.5°	1162.8	1144.4	1142.5	1132.5	1142.5	1144.4	1162.8	1179.0	1203.7	1215.8	1239.4
15°	990.1	986.6	975.2	967.8	975.2	986.6	990.1	1003.8	1012.9	1046.0	1084.3
17.5°	891.3	880.1	876.6	874.9	876.6	880.1	891.3	897.9	910.9	928.4	951.5
20°	827.8	817.5	815.8	814.7	815.8	817.5	827.8	835.8	846.1	865.0	888.9
22.5°	783.9	773.2	768.7	765.3	768.7	773.2	783.9	790.1	799.4	814.2	830.4
25°	708.9	705.0	702.7	701.5	702.7	705.0	708.9	714.6	723.8	743.8	761.0
27.5°	650.3	641.5	639.8	636.9	639.8	641.5	650.3	660.5	670.0	679.0	694.3
30°	617.0	614.2	610.1	606.7	610.1	614.2	617.0	622.2	628.4	643.9	658.7
32.5°	577.6	575.3	571.7	570.2	571.7	575.3	577.6	584.6	597.8	607.3	618.0
35°	534.2	526.2	522.7	517.5	522.7	526.2	534.2	539.8	545.0	553.0	572.4
37.5°	488.1	483.9	479.1	480.8	479.1	483.9	488.1	490.5	501.4	512.5	520.9
40°	452.5	449.6	448.5	447.9	448.5	449.6	452.5	459.9	473.0	478.2	490.8
42.5°	424.1	416.2	413.3	413.1	413.3	416.2	424.1	432.5	440.6	448.9	461.9
45°	381.1	373.6	368.5	369.0	368.5	373.6	381.1	383.9	390.7	407.3	414.7
47.5°	336.9	336.7	333.6	334.6	333.6	336.7	336.9	341.8	350.7	360.8	372.7
50°	315.9	312.5	310.2	310.7	310.2	312.5	315.9	319.9	325.0	330.2	348.4
52.5°	295.8	292.8	291.0	293.4	291.0	292.8	295.8	298.0	301.8	306.9	319.3
55°	262.8	259.3	258.8	258.2	258.8	259.3	262.8	265.6	270.2	274.2	279.9
57.5°	225.9	223.6	220.2	218.7	220.2	223.6	225.9	230.1	235.6	240.8	246.8
60°	199.4	194.8	189.1	188.6	189.1	194.8	199.4	206.8	209.1	217.1	223.9
62.5°	175.1	174.3	173.1	173.0	173.1	174.3	175.1	177.5	180.7	192.4	200.6
65°	153.7	153.1	153.7	154.2	153.7	153.1	153.7	154.8	155.4	156.5	160.0
67.5°	133.9	132.9	131.8	132.3	131.8	132.9	133.9	134.1	135.7	136.4	138.8
70°	118.8	118.2	117.7	117.7	117.7	118.2	118.8	119.9	121.1	122.3	125.1
72.5°	104.2	104.1	103.5	103.1	103.5	104.1	104.2	106.2	106.9	108.1	110.0
75°	83.4	82.2	82.2	82.2	82.2	82.2	83.4	83.9	84.6	86.3	87.4
77.5°	63.5	62.9	62.4	61.9	62.4	62.9	63.5	63.6	64.6	64.9	66.1
80°	50.3	49.7	49.2	49.2	49.2	49.7	50.3	50.9	50.9	52.5	52.0
82.5°	38.4	37.8	37.7	37.3	37.7	37.8	38.4	38.5	38.5	39.8	39.6
85°	20.6	21.1	20.6	21.7	20.6	21.1	20.6	20.0	20.6	21.7	21.7
87.5°	12.2	11.9	12.5	12.1	12.5	11.9	12.2	12.1	12.4	12.1	11.9
90°	31.4	31.9	32.5	33.1	32.5	31.9	31.4	30.9	30.0	28.6	27.2
92.5°	32.1	32.4	32.7	33.1	32.7	32.4	32.1	31.8	31.3	30.6	29.8
95°	53.5	53.2	53.0	52.7	53.0	53.2	53.5	53.7	53.2	51.8	50.5
97.5°	69.3	69.7	70.0	70.3	70.0	69.7	69.3	69.0	68.3	67.2	66.1
100°	80.4	80.9	81.5	82.1	81.5	80.9	80.4	79.9	78.5	76.4	74.1
102.5°	85.7	86.4	87.1	87.9	87.1	86.4	85.7	84.9	83.1	80.2	77.4
105°	89.8	90.9	92.0	93.1	92.0	90.9	89.8	88.7	86.7	83.7	80.7
107.5°	92.5	93.6	94.7	95.7	94.7	93.6	92.5	91.4	92.4	95.4	98.5
110°	93.5	94.5	95.7	96.8	95.7	94.5	93.5	92.4	105.5	132.7	159.9



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	95.1	96.0	96.9	97.7	96.9	96.0	95.1	94.2	143.4	242.7	342.0
115°	159.2	139.6	120.0	100.4	120.0	139.6	159.2	178.7	251.6	377.5	503.6
117.5°	603.1	538.7	474.3	410.0	474.3	538.7	603.1	667.5	715.0	745.5	775.9
120°	857.2	820.4	783.7	747.0	783.7	820.4	857.2	893.9	910.7	907.4	904.1
122.5°	953.5	946.4	939.3	932.1	939.3	946.4	953.5	960.6	963.2	961.3	959.3
125°	1044.6	1045.3	1046.2	1047.0	1046.2	1045.3	1044.6	1043.7	1042.3	1040.4	1038.5
127.5°	1119.0	1119.1	1119.3	1119.5	1119.3	1119.1	1119.0	1118.9	1117.3	1114.6	1111.8
130°	1165.4	1165.1	1164.8	1164.5	1164.8	1165.1	1165.4	1165.6	1164.2	1161.3	1158.3
132.5°	1209.4	1209.2	1208.9	1208.6	1208.9	1209.2	1209.4	1209.7	1208.6	1206.0	1203.4
135°	1273.9	1273.4	1272.8	1272.3	1272.8	1273.4	1273.9	1274.5	1273.4	1270.7	1267.9
137.5°	1333.1	1332.2	1331.3	1330.3	1331.3	1332.2	1333.1	1334.0	1333.2	1330.5	1327.8
140°	1370.7	1369.3	1368.0	1366.6	1368.0	1369.3	1370.7	1372.0	1371.5	1369.1	1366.6
142.5°	1405.9	1404.5	1403.3	1401.9	1403.3	1404.5	1405.9	1407.3	1406.9	1404.6	1402.4
145°	1455.2	1453.8	1452.4	1451.1	1452.4	1453.8	1455.2	1456.6	1456.3	1454.3	1452.4
147.5°	1497.9	1496.8	1495.6	1494.4	1495.6	1496.8	1497.9	1499.0	1498.9	1497.5	1496.1
150°	1525.0	1523.6	1522.2	1520.9	1522.2	1523.6	1525.0	1526.3	1526.2	1524.6	1522.9
152.5°	1548.8	1547.0	1545.2	1543.4	1545.2	1547.0	1548.8	1550.6	1550.7	1549.0	1547.4
155°	1581.3	1579.2	1576.9	1574.8	1576.9	1579.2	1581.3	1583.5	1583.7	1582.1	1580.5
157.5°	1609.8	1607.7	1605.5	1603.4	1605.5	1607.7	1609.8	1611.9	1612.1	1610.2	1608.3
160°	1625.8	1623.8	1622.0	1620.1	1622.0	1623.8	1625.8	1627.7	1627.8	1626.2	1624.5
162.5°	1640.8	1638.5	1636.2	1633.8	1636.2	1638.5	1640.8	1643.1	1643.4	1641.6	1639.7
165°	1660.1	1658.2	1656.3	1654.3	1656.3	1658.2	1660.1	1662.0	1662.0	1660.1	1658.2
167.5°	1674.7	1672.2	1669.8	1667.3	1669.8	1672.2	1674.7	1677.1	1677.4	1675.5	1673.6
170°	1682.6	1680.1	1677.7	1675.2	1677.7	1680.1	1682.6	1685.0	1685.2	1683.3	1681.4
172.5°	1688.4	1685.9	1683.5	1681.0	1683.5	1685.9	1688.4	1690.8	1691.1	1689.2	1687.3
175°	1694.4	1691.6	1688.9	1686.2	1688.9	1691.6	1694.4	1697.1	1697.5	1695.6	1693.7
177.5°	1695.2	1693.3	1691.3	1689.4	1691.3	1693.3	1695.2	1697.2	1697.5	1695.9	1694.4
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1581.1	1587.5	1597.1	1602.6	1611.7	1617.6	1620.8	1626.8	1630.0	1641.4	1653.3
5°	1492.7	1501.9	1517.9	1532.8	1548.8	1565.3	1577.3	1591.0	1603.6	1625.3	1648.1
7.5°	1391.5	1404.2	1429.0	1452.7	1480.5	1504.0	1524.7	1548.1	1569.0	1600.1	1632.5
10°	1315.7	1337.9	1370.5	1392.8	1429.3	1452.8	1485.3	1511.1	1540.2	1581.3	1617.9
12.5°	1250.3	1277.1	1303.3	1334.3	1367.2	1406.2	1441.9	1474.9	1509.6	1552.0	1595.0
15°	1131.7	1170.5	1211.1	1242.5	1287.1	1328.3	1369.9	1414.5	1456.7	1507.6	1563.6
17.5°	979.0	1024.1	1092.3	1146.1	1198.4	1239.7	1291.3	1345.2	1395.1	1456.4	1518.7
20°	910.1	943.2	989.5	1062.0	1140.8	1184.8	1237.4	1296.8	1353.9	1420.7	1487.6
22.5°	854.7	884.2	921.4	977.9	1065.9	1125.8	1180.7	1241.0	1307.3	1375.5	1449.7
25°	775.8	796.3	835.2	880.9	941.5	1040.3	1100.3	1160.8	1232.9	1306.0	1390.5
27.5°	716.5	735.0	760.3	803.9	848.9	919.9	1015.3	1081.3	1153.1	1235.4	1323.1
30°	671.2	692.9	720.9	751.8	800.9	856.4	951.7	1028.3	1099.2	1183.7	1277.4
32.5°	638.3	655.5	679.3	710.7	751.6	804.7	880.9	973.9	1042.9	1132.0	1229.9
35°	584.4	604.4	623.9	653.6	686.6	735.2	792.9	892.3	960.9	1048.9	1147.1
37.5°	539.9	552.2	573.7	597.2	632.1	668.4	718.4	807.5	881.8	968.1	1068.7
40°	506.2	521.6	537.6	563.9	592.5	627.2	676.4	742.7	827.8	912.3	1010.6
42.5°	473.3	492.8	509.7	527.3	558.6	593.5	633.4	689.7	776.6	856.6	952.1
45°	433.6	446.2	463.9	483.3	509.0	538.7	574.1	623.3	706.7	775.8	865.5
47.5°	387.4	405.9	417.4	436.4	460.8	489.1	522.0	564.6	632.1	696.8	780.1
50°	355.9	374.8	391.3	408.5	430.2	457.6	485.0	526.2	580.4	648.4	726.1
52.5°	328.9	345.5	361.6	378.8	400.0	425.2	451.2	487.3	533.8	596.3	671.8
55°	292.0	302.2	318.7	335.9	354.7	378.8	403.9	434.2	474.2	526.8	587.9
57.5°	254.0	265.9	279.1	296.3	315.4	333.7	356.4	383.7	415.3	462.9	515.2
60°	232.5	241.7	252.5	270.2	287.9	304.4	326.2	349.0	378.8	419.9	464.4
62.5°	208.7	217.4	227.4	242.8	260.0	275.3	294.2	318.4	343.5	381.1	420.1
65°	169.1	181.7	191.4	205.1	219.4	235.4	250.2	269.7	292.0	321.7	356.5
67.5°	140.2	146.6	155.6	168.1	182.7	196.4	210.4	225.7	245.0	267.9	295.6
70°	127.4	129.7	131.4	143.4	157.1	170.8	183.9	198.2	214.8	233.7	257.6
72.5°	112.3	114.6	116.8	121.9	132.9	146.6	160.1	170.8	186.5	202.1	221.5
75°	89.1	92.6	94.3	97.1	101.1	110.3	122.9	133.1	142.2	154.2	169.7
77.5°	67.8	69.8	71.6	74.6	77.1	81.4	88.4	97.7	106.2	113.2	123.8
80°	53.7	54.2	56.6	57.7	61.1	64.0	67.4	74.8	83.4	86.3	93.7
82.5°	40.5	41.0	42.9	44.0	45.5	48.0	52.3	54.2	61.0	64.7	69.5
85°	22.3	21.7	23.4	23.4	24.5	25.7	26.9	29.7	31.4	36.0	37.1
87.5°	12.1	11.8	11.8	11.4	10.9	11.4	11.4	11.2	11.5	12.2	13.5
90°	25.8	24.5	22.3	20.1	18.0	15.8	13.2	10.2	7.2	4.2	1.2
92.5°	29.1	28.4	27.3	26.3	25.1	24.0	23.7	23.9	24.2	24.5	24.7
95°	49.1	47.8	45.9	43.9	42.0	40.1	43.7	52.7	61.6	70.6	79.6
97.5°	65.0	63.9	59.5	55.1	50.7	46.3	56.7	82.1	107.4	132.7	158.0
100°	72.0	69.8	65.2	60.5	55.9	51.3	67.6	104.9	142.2	179.4	216.7
102.5°	74.6	71.7	110.5	149.1	187.9	226.5	249.9	257.7	265.6	273.5	281.4
105°	77.7	74.7	149.0	223.3	297.6	371.9	404.9	396.7	388.6	380.4	372.3
107.5°	101.5	104.6	193.6	282.8	371.9	461.0	502.2	495.6	489.0	482.4	475.9
110°	187.1	214.3	292.9	371.6	450.2	528.8	565.3	559.6	553.9	548.2	542.5



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	441.3	540.5	559.9	579.4	598.8	618.2	625.4	620.4	615.3	610.2	605.2
115°	629.6	755.5	748.7	741.9	735.1	728.3	722.6	718.0	713.3	708.8	704.1
117.5°	806.4	836.9	832.2	827.5	822.8	818.1	813.2	808.0	802.9	797.7	792.6
120°	900.9	897.6	892.7	887.8	882.9	878.0	873.5	869.4	865.3	861.3	857.2
122.5°	957.3	955.4	950.0	944.7	939.4	934.1	929.3	925.0	920.7	916.4	912.1
125°	1036.6	1034.7	1029.6	1024.4	1019.3	1014.1	1009.7	1006.2	1002.6	999.1	995.6
127.5°	1109.1	1106.3	1102.4	1098.5	1094.7	1090.8	1086.9	1083.0	1079.1	1075.1	1071.3
130°	1155.3	1152.3	1149.3	1146.3	1143.3	1140.3	1136.7	1132.3	1127.9	1123.6	1119.2
132.5°	1200.9	1198.3	1195.3	1192.3	1189.4	1186.4	1183.0	1179.3	1175.6	1171.9	1168.2
135°	1265.2	1262.5	1260.1	1257.6	1255.2	1252.7	1249.3	1244.9	1240.6	1236.2	1231.9
137.5°	1325.2	1322.5	1319.7	1317.0	1314.1	1311.4	1308.5	1305.4	1302.4	1299.3	1296.3
140°	1364.2	1361.7	1358.7	1355.7	1352.7	1349.7	1347.1	1345.0	1342.8	1340.6	1338.4
142.5°	1400.2	1397.9	1394.5	1391.1	1387.7	1384.2	1381.6	1379.6	1377.6	1375.6	1373.7
145°	1450.5	1448.6	1444.0	1439.4	1434.8	1430.1	1428.0	1428.2	1428.5	1428.7	1429.1
147.5°	1494.6	1493.2	1488.7	1484.1	1479.5	1474.9	1473.2	1474.2	1475.2	1476.3	1477.3
150°	1521.3	1519.7	1515.3	1511.0	1506.6	1502.3	1501.0	1503.0	1504.9	1506.8	1508.6
152.5°	1545.8	1544.1	1540.0	1535.9	1531.7	1527.6	1526.6	1528.7	1530.9	1533.0	1535.1
155°	1578.8	1577.2	1574.0	1570.7	1567.5	1564.2	1563.7	1566.2	1568.7	1571.1	1573.6
157.5°	1606.5	1604.6	1602.3	1600.1	1597.8	1595.5	1595.4	1597.5	1599.6	1601.6	1603.7
160°	1622.9	1621.3	1619.6	1618.1	1616.4	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3
162.5°	1637.9	1636.0	1634.6	1633.1	1631.8	1630.3	1630.5	1632.1	1633.7	1635.4	1636.9
165°	1656.3	1654.3	1653.6	1652.7	1651.9	1651.1	1651.5	1653.1	1654.8	1656.4	1658.0
167.5°	1671.7	1669.8	1669.0	1668.3	1667.5	1666.7	1667.2	1668.8	1670.4	1672.1	1673.7
170°	1679.6	1677.7	1677.1	1676.5	1676.0	1675.4	1676.0	1677.7	1679.3	1680.9	1682.6
172.5°	1685.4	1683.5	1683.0	1682.4	1681.9	1681.4	1681.9	1683.5	1685.1	1686.8	1688.4
175°	1691.8	1689.9	1689.4	1688.8	1688.2	1687.7	1688.4	1690.3	1692.2	1694.1	1696.0
177.5°	1692.9	1691.3	1691.1	1690.9	1690.7	1690.5	1691.1	1692.6	1694.2	1695.7	1697.2
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1653.7	1655.1	1664.2	1668.4	1676.6	1679.8	1683.4	1682.6	1682.6	1684.4	1697.2
5°	1657.3	1668.7	1685.8	1702.5	1718.4	1732.2	1741.3	1750.4	1753.9	1770.4	1785.3
7.5°	1651.3	1672.4	1700.7	1726.0	1756.3	1779.9	1799.6	1817.2	1829.4	1853.5	1878.2
10°	1643.6	1673.3	1705.3	1737.8	1779.5	1810.9	1843.0	1867.5	1875.5	1911.5	1932.1
12.5°	1628.1	1667.8	1708.5	1750.7	1791.4	1834.7	1869.9	1894.5	1922.6	1954.9	1992.9
15°	1604.7	1650.5	1703.6	1757.8	1816.1	1868.6	1906.3	1949.2	1980.0	2015.5	2048.6
17.5°	1571.2	1630.1	1697.6	1760.5	1827.9	1884.3	1936.2	1977.3	1999.0	2019.2	2024.1
20°	1544.7	1608.2	1687.6	1761.9	1829.3	1894.4	1945.8	1980.0	1985.8	1986.3	1956.1
22.5°	1516.0	1587.6	1670.7	1746.7	1827.4	1899.9	1939.8	1954.5	1931.8	1893.1	1834.5
25°	1463.0	1545.9	1642.4	1729.2	1817.2	1885.8	1899.5	1873.8	1794.4	1711.0	1605.3
27.5°	1405.7	1498.8	1602.3	1698.8	1792.6	1835.0	1805.5	1712.8	1569.8	1445.4	1294.8
30°	1363.7	1468.2	1569.9	1677.8	1764.7	1783.0	1715.0	1578.5	1411.6	1224.3	1074.0
32.5°	1315.7	1425.2	1537.0	1648.6	1721.3	1703.4	1591.1	1423.1	1227.4	1043.3	901.3
35°	1247.1	1360.2	1480.7	1592.8	1639.0	1561.9	1394.0	1175.1	975.2	803.2	705.5
37.5°	1167.9	1291.1	1416.4	1519.2	1516.0	1387.4	1158.6	932.8	764.7	663.1	593.5
40°	1111.7	1236.2	1371.7	1458.4	1421.3	1254.0	1006.0	792.9	670.1	589.0	538.1
42.5°	1057.8	1182.8	1317.2	1386.3	1321.7	1115.9	868.9	702.0	600.6	537.4	496.1
45°	966.0	1098.0	1222.5	1260.8	1145.4	918.6	702.7	581.6	514.2	467.3	438.8
47.5°	876.3	1006.2	1119.8	1120.5	964.4	744.9	592.8	503.3	445.7	409.5	388.7
50°	821.5	944.9	1040.3	1025.5	848.3	662.7	530.1	453.1	405.0	377.0	355.3
52.5°	759.8	879.5	962.2	919.9	750.1	583.2	473.9	409.1	369.4	345.1	325.6
55°	670.1	776.4	834.7	770.7	611.8	485.0	400.5	349.7	319.9	299.4	282.8
57.5°	582.0	669.7	706.4	631.8	503.9	402.2	338.8	300.6	271.1	256.4	247.8
60°	526.8	601.6	627.2	545.0	438.2	351.9	299.9	264.5	242.8	233.1	224.5
62.5°	472.3	533.5	544.1	468.6	381.9	308.1	263.4	233.4	219.0	209.7	201.6
65°	391.9	435.9	430.8	370.2	302.2	244.5	212.0	193.6	182.8	169.7	155.4
67.5°	322.6	349.5	333.3	287.9	230.7	190.0	168.8	154.9	141.5	129.0	125.7
70°	278.8	294.2	277.1	235.4	189.1	159.4	142.2	125.7	117.7	114.9	109.7
72.5°	236.8	242.1	223.6	187.9	153.9	132.0	115.3	106.0	101.7	99.3	96.0
75°	177.7	173.7	157.6	129.7	106.9	92.0	86.9	83.4	80.6	78.3	76.5
77.5°	124.8	118.9	104.7	86.4	74.4	67.3	64.2	62.4	61.0	59.8	58.1
80°	93.7	89.7	75.4	61.7	56.6	53.1	51.4	49.2	49.2	48.0	46.2
82.5°	68.5	64.1	51.7	45.2	42.4	40.3	39.1	37.7	37.3	37.5	36.2
85°	36.0	29.1	25.7	24.5	22.8	21.7	22.3	21.1	21.1	21.1	20.6
87.5°	11.8	10.2	10.2	10.4	11.4	11.8	11.8	12.2	13.1	12.9	13.7
90°	4.2	7.2	10.2	13.2	15.8	18.0	20.1	22.3	24.5	25.8	27.2
92.5°	24.5	24.2	23.9	23.7	24.0	25.1	26.3	27.3	28.4	29.1	29.8
95°	70.6	61.6	52.7	43.7	40.1	42.0	43.9	45.9	47.8	49.1	50.5
97.5°	132.7	107.4	82.1	56.7	46.3	50.7	55.1	59.5	63.9	65.0	66.1
100°	179.4	142.2	104.9	67.6	51.3	55.9	60.5	65.2	69.8	72.0	74.1
102.5°	273.5	265.6	257.7	249.9	226.5	187.9	149.1	110.5	71.7	74.6	77.4
105°	380.4	388.6	396.7	404.9	371.9	297.6	223.3	149.0	74.7	77.7	80.7
107.5°	482.4	489.0	495.6	502.2	461.0	371.9	282.8	193.6	104.6	101.5	98.5
110°	548.2	553.9	559.6	565.3	528.8	450.2	371.6	292.9	214.3	187.1	159.9





TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	610.2	615.3	620.4	625.4	618.2	598.8	579.4	559.9	540.5	441.3	342.0
115°	708.8	713.3	718.0	722.6	728.3	735.1	741.9	748.7	755.5	629.6	503.6
117.5°	797.7	802.9	808.0	813.2	818.1	822.8	827.5	832.2	836.9	806.4	775.9
120°	861.3	865.3	869.4	873.5	878.0	882.9	887.8	892.7	897.6	900.9	904.1
122.5°	916.4	920.7	925.0	929.3	934.1	939.4	944.7	950.0	955.4	957.3	959.3
125°	999.1	1002.6	1006.2	1009.7	1014.1	1019.3	1024.4	1029.6	1034.7	1036.6	1038.5
127.5°	1075.1	1079.1	1083.0	1086.9	1090.8	1094.7	1098.5	1102.4	1106.3	1109.1	1111.8
130°	1123.6	1127.9	1132.3	1136.7	1140.3	1143.3	1146.3	1149.3	1152.3	1155.3	1158.3
132.5°	1171.9	1175.6	1179.3	1183.0	1186.4	1189.4	1192.3	1195.3	1198.3	1200.9	1203.4
135°	1236.2	1240.6	1244.9	1249.3	1252.7	1255.2	1257.6	1260.1	1262.5	1265.2	1267.9
137.5°	1299.3	1302.4	1305.4	1308.5	1311.4	1314.1	1317.0	1319.7	1322.5	1325.2	1327.8
140°	1340.6	1342.8	1345.0	1347.1	1349.7	1352.7	1355.7	1358.7	1361.7	1364.2	1366.6
142.5°	1375.6	1377.6	1379.6	1381.6	1384.2	1387.7	1391.1	1394.5	1397.9	1400.2	1402.4
145°	1428.7	1428.5	1428.2	1428.0	1430.1	1434.8	1439.4	1444.0	1448.6	1450.5	1452.4
147.5°	1476.3	1475.2	1474.2	1473.2	1474.9	1479.5	1484.1	1488.7	1493.2	1494.6	1496.1
150°	1506.8	1504.9	1503.0	1501.0	1502.3	1506.6	1511.0	1515.3	1519.7	1521.3	1522.9
152.5°	1533.0	1530.9	1528.7	1526.6	1527.6	1531.7	1535.9	1540.0	1544.1	1545.8	1547.4
155°	1571.1	1568.7	1566.2	1563.7	1564.2	1567.5	1570.7	1574.0	1577.2	1578.8	1580.5
157.5°	1601.6	1599.6	1597.5	1595.4	1595.5	1597.8	1600.1	1602.3	1604.6	1606.5	1608.3
160°	1619.6	1618.1	1616.4	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3	1622.9	1624.5
162.5°	1635.4	1633.7	1632.1	1630.5	1630.3	1631.8	1633.1	1634.6	1636.0	1637.9	1639.7
165°	1656.4	1654.8	1653.1	1651.5	1651.1	1651.9	1652.7	1653.6	1654.3	1656.3	1658.2
167.5°	1672.1	1670.4	1668.8	1667.2	1666.7	1667.5	1668.3	1669.0	1669.8	1671.7	1673.6
170°	1680.9	1679.3	1677.7	1676.0	1675.4	1676.0	1676.5	1677.1	1677.7	1679.6	1681.4
172.5°	1686.8	1685.1	1683.5	1681.9	1681.4	1681.9	1682.4	1683.0	1683.5	1685.4	1687.3
175°	1694.1	1692.2	1690.3	1688.4	1687.7	1688.2	1688.8	1689.4	1689.9	1691.8	1693.7
177.5°	1695.7	1694.2	1692.6	1691.1	1690.5	1690.7	1690.9	1691.1	1691.3	1692.9	1694.4
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1701.8	1707.7	1710.4	1710.4	1713.6	1712.3	1710.9
5°	1799.6	1810.4	1812.7	1823.0	1830.4	1828.1	1829.3
7.5°	1896.8	1914.3	1931.5	1939.4	1940.6	1945.2	1946.9
10°	1956.6	1970.9	1997.8	1993.7	2013.8	2025.2	2006.3
12.5°	2014.2	2033.5	2052.2	2057.3	2068.6	2072.3	2064.9
15°	2066.3	2076.6	2077.8	2074.9	2078.3	2075.4	2064.6
17.5°	2017.7	2001.0	1967.1	1951.1	1938.5	1919.8	1912.2
20°	1937.2	1888.1	1830.9	1808.1	1781.2	1728.7	1741.3
22.5°	1763.6	1707.5	1650.5	1583.7	1551.9	1502.0	1499.0
25°	1493.3	1396.8	1290.6	1216.2	1172.9	1123.2	1101.4
27.5°	1161.1	1039.5	952.4	908.4	868.2	828.8	827.2
30°	942.6	851.2	783.8	746.1	721.5	705.0	708.4
32.5°	794.5	731.9	686.5	655.1	637.0	624.5	624.3
35°	649.5	606.7	577.6	564.4	551.3	542.2	542.7
37.5°	555.9	530.1	513.9	499.4	491.2	486.7	484.2
40°	507.9	486.7	474.2	465.6	458.7	452.5	451.3
42.5°	469.9	452.5	439.9	433.2	426.7	422.3	421.1
45°	417.1	402.8	391.3	383.9	381.1	377.0	377.0
47.5°	371.0	357.0	348.0	343.4	338.5	335.8	335.7
50°	339.9	329.1	321.1	318.2	314.2	312.5	311.9
52.5°	312.0	303.9	298.3	296.3	294.5	292.4	292.7
55°	274.2	269.7	267.3	265.6	262.8	259.3	261.7
57.5°	242.4	238.4	232.3	226.9	224.3	221.9	222.8
60°	220.0	212.0	204.0	197.7	196.0	190.8	190.8
62.5°	191.6	180.4	170.6	167.0	165.3	162.9	162.5
65°	147.4	142.8	140.5	138.3	137.1	137.1	136.0
67.5°	122.2	120.3	117.8	117.3	116.1	115.7	115.4
70°	108.0	105.6	104.5	104.0	102.8	103.4	101.7
72.5°	94.3	92.5	92.2	90.7	90.1	90.1	88.9
75°	74.3	74.3	73.7	73.1	72.0	71.4	72.0
77.5°	57.2	57.3	56.2	56.1	56.0	56.1	55.5
80°	45.7	46.2	45.7	45.1	44.6	45.1	44.6
82.5°	36.1	35.3	35.2	35.0	35.0	34.6	34.5
85°	20.6	21.1	20.6	20.0	20.0	20.0	20.6
87.5°	13.5	13.8	13.9	14.0	14.2	14.3	13.9
90°	28.6	30.0	30.9	31.4	31.9	32.5	33.1
92.5°	30.6	31.3	31.8	32.1	32.4	32.7	33.1
95°	51.8	53.2	53.7	53.5	53.2	53.0	52.7
97.5°	67.2	68.3	69.0	69.3	69.7	70.0	70.3
100°	76.4	78.5	79.9	80.4	80.9	81.5	82.1
102.5°	80.2	83.1	84.9	85.7	86.4	87.1	87.9
105°	83.7	86.7	88.7	89.8	90.9	92.0	93.1
107.5°	95.4	92.4	91.4	92.5	93.6	94.7	95.7
110°	132.7	105.5	92.4	93.5	94.5	95.7	96.8



TEST NUMBER: P331841-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	242.7	143.4	94.2	95.1	96.0	96.9	97.7
115°	377.5	251.6	178.7	159.2	139.6	120.0	100.4
117.5°	745.5	715.0	667.5	603.1	538.7	474.3	410.0
120°	907.4	910.7	893.9	857.2	820.4	783.7	747.0
122.5°	961.3	963.2	960.6	953.5	946.4	939.3	932.1
125°	1040.4	1042.3	1043.7	1044.6	1045.3	1046.2	1047.0
127.5°	1114.6	1117.3	1118.9	1119.0	1119.1	1119.3	1119.5
130°	1161.3	1164.2	1165.6	1165.4	1165.1	1164.8	1164.5
132.5°	1206.0	1208.6	1209.7	1209.4	1209.2	1208.9	1208.6
135°	1270.7	1273.4	1274.5	1273.9	1273.4	1272.8	1272.3
137.5°	1330.5	1333.2	1334.0	1333.1	1332.2	1331.3	1330.3
140°	1369.1	1371.5	1372.0	1370.7	1369.3	1368.0	1366.6
142.5°	1404.6	1406.9	1407.3	1405.9	1404.5	1403.3	1401.9
145°	1454.3	1456.3	1456.6	1455.2	1453.8	1452.4	1451.1
147.5°	1497.5	1498.9	1499.0	1497.9	1496.8	1495.6	1494.4
150°	1524.6	1526.2	1526.3	1525.0	1523.6	1522.2	1520.9
152.5°	1549.0	1550.7	1550.6	1548.8	1547.0	1545.2	1543.4
155°	1582.1	1583.7	1583.5	1581.3	1579.2	1576.9	1574.8
157.5°	1610.2	1612.1	1611.9	1609.8	1607.7	1605.5	1603.4
160°	1626.2	1627.8	1627.7	1625.8	1623.8	1622.0	1620.1
162.5°	1641.6	1643.4	1643.1	1640.8	1638.5	1636.2	1633.8
165°	1660.1	1662.0	1662.0	1660.1	1658.2	1656.3	1654.3
167.5°	1675.5	1677.4	1677.1	1674.7	1672.2	1669.8	1667.3
170°	1683.3	1685.2	1685.0	1682.6	1680.1	1677.7	1675.2
172.5°	1689.2	1691.1	1690.8	1688.4	1685.9	1683.5	1681.0
175°	1695.6	1697.5	1697.1	1694.4	1691.6	1688.9	1686.2
177.5°	1695.9	1697.5	1697.2	1695.2	1693.3	1691.3	1689.4
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3

(END OF REPORT)