

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332197-927

Luminaire Tested: **S123DIW-S1000D1030U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332197-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1000D1030U927-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6096.6 lumens  
Efficiency: N/A  
Efficacy: 99.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332197-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332197-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	44	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	32	54	43	36	31	37	32	27	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13497	13497	13497
5°	13560	13374	13467
10°	13470	13258	13340
15°	13312	13108	13133
20°	13128	12893	12906
25°	12883	12638	12613
30°	12609	12356	12261
35°	12326	12056	11901
40°	12029	11726	11545
45°	11702	11423	11144
50°	11375	11050	10742
55°	10946	10663	10340
60°	10514	10213	9888
65°	10132	9722	9419
70°	9567	9161	8752
75°	8742	8430	8072
80°	7885	7550	7482
85°	6928	6657	6385



TEST NUMBER: P332197-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.1	1.9
10°-20°	333.5	5.5
20°-30°	492.7	8.1
30°-40°	575.5	9.4
40°-50°	578.6	9.5
50°-60°	508.2	8.3
60°-70°	378.6	6.2
70°-80°	215.7	3.5
80°-90°	64.9	1.1
90°-100°	66.6	1.1
100°-110°	199.2	3.3
110°-120°	338.8	5.6
120°-130°	445.7	7.3
130°-140°	500.9	8.2
140°-150°	492.4	8.1
150°-160°	414.5	6.8
160°-170°	275.9	4.5
170°-180°	96.6	1.6
0°-30°	944.3	15.5
0°-40°	1519.8	24.9
0°-60°	2606.6	42.8
0°-90°	3265.9	53.6
90°-120°	604.6	9.9
90°-150°	2043.6	33.5
90°-180°	2831.0	46.4
0°-180°	6096.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1254	1254	1254	1254	1254	
5°	1255	1249	1238	1248	1246	119
15°	1195	1190	1176	1184	1178	337
25°	1085	1078	1064	1065	1062	499
35°	938	931	918	911	906	587
45°	769	764	750	738	732	593
55°	583	582	568	557	551	522
65°	398	392	382	373	370	392
75°	210	206	203	197	194	225
85°	56	54	54	52	52	62
90°	1	9	19	22	24	6
95°	47	53	59	62	63	53
105°	181	182	189	190	191	193
115°	341	343	342	343	342	337
125°	499	501	500	497	494	445
135°	648	652	652	649	647	499
145°	786	787	790	789	786	491
155°	900	900	900	903	898	414
165°	980	978	978	982	977	276
175°	1019	1016	1016	1020	1015	97
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P332197-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1258.2	1257.5	1256.7	1255.9	1255.2	1253.7	1251.6	1249.5	1247.4	1245.3	1247.2
5°	1255.0	1253.8	1252.6	1251.4	1250.2	1248.3	1245.7	1243.0	1240.4	1237.8	1240.2
7.5°	1242.7	1241.5	1240.3	1239.1	1237.9	1236.0	1233.3	1230.5	1227.8	1225.0	1227.2
10°	1232.4	1231.2	1229.9	1228.8	1227.6	1225.4	1222.3	1219.2	1216.1	1213.0	1215.1
12.5°	1218.5	1217.6	1216.6	1215.5	1214.6	1212.6	1209.7	1206.7	1203.8	1200.9	1202.5
15°	1194.6	1193.7	1192.7	1191.8	1190.8	1188.7	1185.7	1182.6	1179.4	1176.3	1178.2
17.5°	1166.8	1165.5	1164.3	1163.1	1161.8	1159.7	1156.5	1153.4	1150.3	1147.2	1148.5
20°	1146.1	1144.7	1143.3	1141.8	1140.3	1138.0	1135.0	1131.9	1128.8	1125.6	1126.6
22.5°	1122.8	1121.4	1120.0	1118.5	1117.1	1114.8	1111.7	1108.6	1105.5	1102.3	1103.1
25°	1084.7	1083.2	1081.8	1080.4	1078.9	1076.7	1073.5	1070.4	1067.3	1064.1	1064.4
27.5°	1043.9	1042.5	1041.1	1039.7	1038.3	1035.9	1032.6	1029.3	1025.9	1022.5	1022.7
30°	1014.5	1013.4	1012.2	1011.0	1009.8	1007.5	1004.2	1000.8	997.4	994.1	994.1
32.5°	985.2	983.7	982.1	980.5	978.9	976.8	974.2	971.7	969.1	966.5	965.1
35°	938.0	936.6	935.2	933.7	932.2	930.0	926.9	923.8	920.7	917.5	916.1
37.5°	889.7	887.9	886.1	884.2	882.4	880.0	876.8	873.6	870.4	867.3	865.5
40°	856.1	854.6	853.2	851.8	850.3	848.0	844.5	841.2	837.9	834.5	832.6
42.5°	822.4	820.8	819.2	817.5	815.9	813.4	810.1	806.8	803.4	800.0	798.1
45°	768.7	767.8	766.8	765.9	764.9	762.9	759.8	756.6	753.5	750.4	747.6
47.5°	715.5	714.1	712.7	711.3	710.0	707.7	704.9	702.0	699.0	696.1	693.2
50°	679.3	678.0	676.8	675.7	674.5	672.3	669.2	666.1	663.0	659.9	657.2
52.5°	641.3	640.5	639.7	638.9	638.0	636.0	632.7	629.4	626.1	622.7	620.5
55°	583.3	583.0	582.8	582.6	582.3	580.7	577.6	574.4	571.3	568.2	565.5
57.5°	528.1	527.3	526.5	525.7	524.8	523.2	520.7	518.2	515.7	513.3	510.9
60°	488.4	488.1	487.9	487.7	487.4	485.9	483.0	480.1	477.3	474.4	472.2
62.5°	453.0	452.4	451.8	451.1	450.6	448.9	445.9	443.1	440.2	437.3	435.1
65°	397.8	396.6	395.5	394.3	393.1	391.3	388.9	386.5	384.0	381.7	379.8
67.5°	339.5	338.3	337.3	336.3	335.2	333.7	331.9	330.1	328.3	326.5	324.8
70°	304.0	302.6	301.2	299.8	298.3	296.8	295.4	294.0	292.6	291.1	289.5
72.5°	267.0	265.9	264.8	263.8	262.8	261.4	259.8	258.2	256.5	254.8	253.4
75°	210.2	209.3	208.3	207.4	206.4	205.6	204.9	204.1	203.4	202.7	201.5
77.5°	160.0	159.5	158.9	158.4	157.9	157.2	156.4	155.5	154.6	153.8	153.0
80°	127.2	126.5	125.8	125.1	124.4	123.7	123.3	122.8	122.3	121.8	121.6
82.5°	95.3	95.1	95.1	94.9	94.7	94.6	94.5	94.4	94.3	94.3	93.8
85°	56.1	55.6	55.1	54.7	54.2	53.9	53.9	53.9	53.9	53.9	53.4
87.5°	22.6	22.3	22.2	21.9	21.7	21.7	22.0	22.3	22.6	22.8	22.8
90°	0.8	2.6	4.4	6.2	7.9	10.0	12.3	14.7	17.0	19.3	20.0
92.5°	19.4	20.6	21.9	23.1	24.2	25.5	26.9	28.2	29.5	30.8	31.4
95°	47.4	48.6	49.8	51.1	52.4	53.7	55.1	56.6	58.0	59.4	60.1
97.5°	84.1	85.0	86.0	86.9	87.9	88.8	89.8	90.9	91.9	92.9	93.8
100°	109.2	110.2	111.3	112.3	113.4	114.4	115.3	116.2	117.1	118.0	118.5
102.5°	138.1	138.7	139.3	140.0	140.6	141.5	142.7	143.9	145.0	146.2	146.8
105°	180.6	180.9	181.3	181.6	182.0	183.0	184.6	186.2	187.8	189.4	189.4
107.5°	230.0	230.2	230.4	230.7	230.8	231.3	232.0	232.6	233.2	233.9	234.4
110°	260.9	261.2	261.6	261.9	262.3	262.6	263.0	263.3	263.7	264.0	264.7



TEST NUMBER: P332197-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.9	293.2	293.3	293.6	293.8	293.9	294.0	294.1	294.1	294.2	295.1
115°	341.1	341.6	342.1	342.7	343.3	343.3	342.9	342.6	342.2	341.9	342.1
117.5°	389.6	389.9	390.3	390.6	391.0	390.9	390.5	390.0	389.5	389.1	389.0
120°	419.8	420.8	421.9	422.9	424.1	424.1	423.2	422.3	421.4	420.6	420.3
122.5°	451.2	452.0	452.8	453.5	454.3	454.5	454.1	453.6	453.1	452.7	452.2
125°	499.2	499.7	500.3	500.8	501.4	501.5	501.1	500.7	500.3	500.0	499.3
127.5°	543.5	544.6	545.8	546.9	548.0	548.4	548.0	547.6	547.2	546.8	545.9
130°	573.1	574.5	575.9	577.3	578.8	579.2	578.7	578.1	577.6	577.0	576.3
132.5°	602.5	604.0	605.4	606.9	608.3	608.8	608.4	608.0	607.6	607.2	606.3
135°	647.7	648.7	649.8	650.9	652.0	652.4	652.2	652.0	651.9	651.6	650.9
137.5°	689.4	690.3	691.2	692.1	693.0	693.6	694.1	694.6	695.1	695.5	694.7
140°	718.3	719.2	720.1	721.0	721.8	722.4	722.5	722.8	722.9	723.1	722.9
142.5°	744.7	745.5	746.4	747.3	748.2	748.8	749.1	749.4	749.8	750.1	749.9
145°	785.7	786.1	786.4	786.8	787.1	787.6	788.1	788.7	789.2	789.7	789.6
147.5°	821.7	822.3	822.9	823.6	824.3	824.8	825.3	825.9	826.3	826.8	826.8
150°	846.7	847.1	847.4	847.8	848.1	848.5	848.8	849.2	849.5	849.9	849.9
152.5°	867.3	867.8	868.2	868.8	869.3	869.6	869.8	870.1	870.3	870.4	870.8
155°	899.7	899.7	899.7	899.7	899.7	899.8	899.9	900.2	900.3	900.5	901.2
157.5°	927.3	927.1	926.9	926.6	926.5	926.4	926.5	926.7	926.9	926.9	927.7
160°	944.6	944.3	943.9	943.6	943.2	943.0	943.0	943.0	943.0	943.0	943.9
162.5°	960.0	959.6	959.0	958.5	958.1	957.8	958.0	958.1	958.3	958.5	959.3
165°	979.9	979.4	978.9	978.3	977.8	977.6	977.6	977.6	977.6	977.6	978.6
167.5°	995.9	995.1	994.4	993.7	993.0	992.7	992.8	993.0	993.2	993.2	994.3
170°	1004.8	1004.1	1003.4	1002.7	1002.0	1001.6	1001.6	1001.6	1001.6	1001.6	1002.8
172.5°	1011.9	1011.1	1010.4	1009.7	1009.0	1008.7	1008.7	1008.7	1008.7	1008.7	1009.8
175°	1019.3	1018.6	1017.9	1017.2	1016.4	1016.1	1016.1	1016.1	1016.1	1016.1	1017.2
177.5°	1022.3	1021.8	1021.2	1020.6	1020.0	1019.8	1019.8	1019.8	1019.8	1019.8	1020.6
180°	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7



TEST NUMBER: P332197-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1249.1	1251.1	1253.0	1253.9	1253.6	1253.5	1253.2	1253.1
5°	1242.5	1244.9	1247.4	1248.3	1247.8	1247.4	1246.9	1246.4
7.5°	1229.4	1231.5	1233.7	1234.6	1234.3	1234.1	1233.7	1233.4
10°	1217.3	1219.4	1221.6	1222.4	1221.9	1221.5	1221.0	1220.5
12.5°	1204.0	1205.6	1207.2	1207.8	1207.6	1207.3	1207.0	1206.7
15°	1180.1	1182.0	1184.0	1184.2	1182.8	1181.3	1179.9	1178.5
17.5°	1149.9	1151.2	1152.5	1152.9	1152.5	1151.9	1151.4	1150.9
20°	1127.5	1128.5	1129.5	1129.6	1128.9	1128.1	1127.4	1126.7
22.5°	1103.9	1104.6	1105.4	1105.3	1104.5	1103.5	1102.6	1101.7
25°	1064.6	1064.9	1065.2	1064.9	1064.1	1063.4	1062.7	1062.0
27.5°	1022.9	1023.1	1023.3	1022.9	1022.1	1021.1	1020.3	1019.3
30°	994.1	994.1	994.1	993.2	991.6	989.9	988.2	986.5
32.5°	963.8	962.5	961.2	960.0	959.1	958.1	957.3	956.3
35°	914.7	913.2	911.8	910.5	909.3	908.1	906.9	905.7
37.5°	863.9	862.1	860.4	859.1	858.4	857.6	856.8	856.1
40°	830.7	828.8	826.9	825.4	824.4	823.5	822.5	821.6
42.5°	796.1	794.2	792.3	790.9	790.0	789.0	788.1	787.1
45°	744.7	741.8	738.9	736.9	735.7	734.5	733.3	732.1
47.5°	690.4	687.6	684.8	682.9	681.8	680.7	679.7	678.6
50°	654.6	652.0	649.3	647.3	645.9	644.4	642.9	641.5
52.5°	618.2	616.0	613.8	611.9	610.5	609.0	607.6	606.2
55°	562.9	560.3	557.7	555.7	554.5	553.3	552.2	551.0
57.5°	508.5	506.2	503.8	501.9	500.6	499.2	497.8	496.4
60°	470.1	467.9	465.8	464.1	462.9	461.7	460.5	459.3
62.5°	433.0	430.9	428.6	427.2	426.4	425.6	424.8	424.0
65°	377.9	375.9	374.0	372.7	372.0	371.3	370.5	369.8
67.5°	323.1	321.5	319.8	318.5	317.4	316.4	315.4	314.4
70°	287.7	286.1	284.4	283.0	281.8	280.6	279.4	278.1
72.5°	251.9	250.4	248.9	247.9	247.2	246.6	246.1	245.4
75°	200.3	199.1	197.9	196.9	196.2	195.5	194.8	194.1
77.5°	152.1	151.3	150.5	150.1	150.1	150.1	150.1	150.1
80°	121.4	121.1	120.9	120.7	120.7	120.7	120.7	120.7
82.5°	93.4	92.9	92.5	92.2	92.0	91.8	91.7	91.4
85°	52.9	52.4	52.0	51.7	51.7	51.7	51.7	51.7
87.5°	22.7	22.7	22.7	22.7	22.7	22.8	22.9	22.9
90°	20.7	21.4	22.1	22.7	23.0	23.4	23.7	24.1
92.5°	31.9	32.6	33.1	33.3	33.0	32.9	32.6	32.4
95°	60.8	61.6	62.3	62.6	62.6	62.6	62.6	62.6
97.5°	94.6	95.4	96.3	96.6	96.5	96.5	96.4	96.3
100°	119.1	119.6	120.1	120.6	120.9	121.3	121.6	122.0
102.5°	147.3	147.8	148.4	148.6	148.5	148.5	148.4	148.3
105°	189.4	189.4	189.4	189.6	190.0	190.3	190.7	191.0
107.5°	235.0	235.6	236.1	236.3	236.1	235.9	235.7	235.4
110°	265.5	266.2	266.9	267.0	266.7	266.3	266.0	265.6





TEST NUMBER: P332197-927

CATALOG NUMBER: S123DIW-S1000D1030U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	296.0	296.8	297.6	298.0	297.9	297.9	297.9	297.8
115°	342.2	342.5	342.6	342.6	342.5	342.2	342.1	341.9
117.5°	389.0	389.0	389.0	388.6	388.2	387.7	387.1	386.7
120°	420.2	420.0	419.9	419.5	419.2	418.8	418.5	418.1
122.5°	451.7	451.2	450.8	450.3	449.8	449.3	448.9	448.3
125°	498.6	497.9	497.2	496.5	495.7	495.0	494.3	493.6
127.5°	544.9	543.9	542.9	541.9	541.1	540.3	539.5	538.7
130°	575.6	574.9	574.2	573.2	572.0	570.7	569.5	568.2
132.5°	605.5	604.7	603.8	602.9	601.9	600.9	600.0	599.0
135°	650.2	649.5	648.8	648.3	647.9	647.6	647.2	646.9
137.5°	694.0	693.2	692.5	691.8	691.1	690.5	689.8	689.1
140°	722.8	722.5	722.4	721.7	720.4	719.2	718.0	716.7
142.5°	749.7	749.6	749.4	748.8	747.8	746.9	745.9	745.0
145°	789.4	789.2	789.0	788.5	787.8	787.1	786.4	785.7
147.5°	826.8	826.8	826.8	826.2	825.2	824.1	823.1	822.0
150°	849.9	849.9	849.9	849.4	848.3	847.2	846.2	845.1
152.5°	871.0	871.3	871.6	871.3	870.4	869.4	868.5	867.6
155°	901.9	902.6	903.3	903.1	901.8	900.6	899.4	898.1
157.5°	928.4	929.2	929.9	929.9	928.8	927.9	926.9	925.8
160°	944.8	945.7	946.6	946.7	945.9	945.2	944.5	943.8
162.5°	960.2	961.1	962.0	961.9	960.8	959.6	958.5	957.3
165°	979.7	980.7	981.8	981.8	980.5	979.2	977.9	976.8
167.5°	995.5	996.6	997.7	997.7	996.6	995.5	994.3	993.2
170°	1004.1	1005.4	1006.6	1006.6	1005.4	1004.1	1002.8	1001.6
172.5°	1010.9	1012.0	1013.1	1013.0	1011.8	1010.5	1009.2	1008.1
175°	1018.2	1019.3	1020.3	1020.3	1019.0	1017.7	1016.5	1015.3
177.5°	1021.4	1022.3	1023.2	1023.1	1022.1	1021.1	1020.1	1019.1
180°	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7

(END OF REPORT)