

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332202-927

Luminaire Tested: **S123DIW-S1000D1320U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332202-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1320U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7447.7 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332202-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332202-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80		65	65	65		50	50	50	44
1	96	92	88	85	88	84	81	78	70	68	65		57	55	54		45	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54		50	47	45		39	37	36	31
3	80	71	63	57	73	65	58	53	54	49	45		44	41	38		35	32	30	26
4	73	62	55	49	67	57	51	45	48	43	39		39	35	32		31	28	26	22
5	67	56	47	42	61	51	44	39	43	37	33		35	31	28		28	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29		32	28	24		25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25		29	25	22		23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23		26	22	19		21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20		24	20	17		20	17	14	12
10	46	34	27	22	42	32	25	21	27	22	18		22	18	16		18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13497	13497	13497
5°	13560	13374	13467
10°	13470	13258	13340
15°	13312	13108	13133
20°	13128	12893	12906
25°	12883	12638	12613
30°	12609	12356	12261
35°	12326	12056	11901
40°	12029	11726	11545
45°	11702	11423	11144
50°	11375	11050	10742
55°	10946	10663	10340
60°	10514	10213	9888
65°	10132	9722	9419
70°	9567	9161	8752
75°	8742	8430	8072
80°	7885	7550	7482
85°	6928	6657	6385



TEST NUMBER: P332202-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.1	1.6
10°-20°	333.5	4.5
20°-30°	492.7	6.6
30°-40°	575.5	7.7
40°-50°	578.6	7.8
50°-60°	508.2	6.8
60°-70°	378.6	5.1
70°-80°	215.7	2.9
80°-90°	65.7	0.9
90°-100°	49.8	0.7
100°-110°	237.6	3.2
110°-120°	570.6	7.7
120°-130°	726.7	9.8
130°-140°	776.4	10.4
140°-150°	726.0	9.7
150°-160°	585.6	7.9
160°-170°	378.0	5.1
170°-180°	130.3	1.7
0°-30°	944.3	12.7
0°-40°	1519.8	20.4
0°-60°	2606.6	35.0
0°-90°	3266.7	43.9
90°-120°	858.1	11.5
90°-150°	3087.2	41.5
90°-180°	4181.0	56.1
0°-180°	7447.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1254	1254	1254	1254	1254	
5°	1255	1249	1238	1248	1246	119
15°	1195	1190	1176	1184	1178	337
25°	1085	1078	1064	1065	1062	499
35°	938	931	918	911	906	587
45°	769	764	750	738	732	593
55°	583	582	568	557	551	522
65°	398	392	382	373	370	392
75°	210	206	203	197	194	225
85°	56	54	54	52	52	62
90°	1	11	24	28	31	6
95°	62	23	32	38	39	77
105°	304	309	223	53	45	322
115°	569	576	585	594	599	562
125°	803	811	815	817	819	717
135°	999	1005	1010	1012	1010	769
145°	1153	1160	1162	1164	1164	722
155°	1270	1268	1269	1274	1268	585
165°	1340	1336	1335	1343	1336	378
175°	1371	1366	1367	1373	1366	130
180°	1371	1371	1371	1371	1371	



TEST NUMBER: P332202-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1258.2	1257.5	1256.7	1255.9	1255.2	1253.7	1251.6	1249.5	1247.4	1245.3	1247.2
5°	1255.0	1253.8	1252.6	1251.4	1250.2	1248.3	1245.7	1243.0	1240.4	1237.8	1240.2
7.5°	1242.7	1241.5	1240.3	1239.1	1237.9	1236.0	1233.3	1230.5	1227.8	1225.0	1227.2
10°	1232.4	1231.2	1229.9	1228.8	1227.6	1225.4	1222.3	1219.2	1216.1	1213.0	1215.1
12.5°	1218.5	1217.6	1216.6	1215.5	1214.6	1212.6	1209.7	1206.7	1203.8	1200.9	1202.5
15°	1194.6	1193.7	1192.7	1191.8	1190.8	1188.7	1185.7	1182.6	1179.4	1176.3	1178.2
17.5°	1166.8	1165.5	1164.3	1163.1	1161.8	1159.7	1156.5	1153.4	1150.3	1147.2	1148.5
20°	1146.1	1144.7	1143.3	1141.8	1140.3	1138.0	1135.0	1131.9	1128.8	1125.6	1126.6
22.5°	1122.8	1121.4	1120.0	1118.5	1117.1	1114.8	1111.7	1108.6	1105.5	1102.3	1103.1
25°	1084.7	1083.2	1081.8	1080.4	1078.9	1076.7	1073.5	1070.4	1067.3	1064.1	1064.4
27.5°	1043.9	1042.5	1041.1	1039.7	1038.3	1035.9	1032.6	1029.3	1025.9	1022.5	1022.7
30°	1014.5	1013.4	1012.2	1011.0	1009.8	1007.5	1004.2	1000.8	997.4	994.1	994.1
32.5°	985.2	983.7	982.1	980.5	978.9	976.8	974.2	971.7	969.1	966.5	965.1
35°	938.0	936.6	935.2	933.7	932.2	930.0	926.9	923.8	920.7	917.5	916.1
37.5°	889.7	887.9	886.1	884.2	882.4	880.0	876.8	873.6	870.4	867.3	865.5
40°	856.1	854.6	853.2	851.8	850.3	848.0	844.5	841.2	837.9	834.5	832.6
42.5°	822.4	820.8	819.2	817.5	815.9	813.4	810.1	806.8	803.4	800.0	798.1
45°	768.7	767.8	766.8	765.9	764.9	762.9	759.8	756.6	753.5	750.4	747.6
47.5°	715.5	714.1	712.7	711.3	710.0	707.7	704.9	702.0	699.0	696.1	693.2
50°	679.3	678.0	676.8	675.7	674.5	672.3	669.2	666.1	663.0	659.9	657.2
52.5°	641.3	640.5	639.7	638.9	638.0	636.0	632.7	629.4	626.1	622.7	620.5
55°	583.3	583.0	582.8	582.6	582.3	580.7	577.6	574.4	571.3	568.2	565.5
57.5°	528.1	527.3	526.5	525.7	524.8	523.2	520.7	518.2	515.7	513.3	510.9
60°	488.4	488.1	487.9	487.7	487.4	485.9	483.0	480.1	477.3	474.4	472.2
62.5°	453.0	452.4	451.8	451.1	450.6	448.9	445.9	443.1	440.2	437.3	435.1
65°	397.8	396.6	395.5	394.3	393.1	391.3	388.9	386.5	384.0	381.7	379.8
67.5°	339.5	338.3	337.3	336.3	335.2	333.7	331.9	330.1	328.3	326.5	324.8
70°	304.0	302.6	301.2	299.8	298.3	296.8	295.4	294.0	292.6	291.1	289.5
72.5°	267.0	265.9	264.8	263.8	262.8	261.4	259.8	258.2	256.5	254.8	253.4
75°	210.2	209.3	208.3	207.4	206.4	205.6	204.9	204.1	203.4	202.7	201.5
77.5°	160.0	159.5	158.9	158.4	157.9	157.2	156.4	155.5	154.6	153.8	153.0
80°	127.2	126.5	125.8	125.1	124.4	123.7	123.3	122.8	122.3	121.8	121.6
82.5°	95.3	95.1	95.1	94.9	94.7	94.6	94.5	94.4	94.3	94.3	93.8
85°	56.1	55.6	55.1	54.7	54.2	53.9	53.9	53.9	53.9	53.9	53.4
87.5°	22.7	22.5	22.4	22.3	22.1	22.3	22.7	23.1	23.4	23.8	23.8
90°	1.0	3.2	5.5	7.8	10.1	12.7	15.6	18.5	21.5	24.5	25.3
92.5°	18.9	18.3	17.7	17.0	16.4	17.2	19.4	21.6	23.8	26.1	27.5
95°	62.1	52.8	43.6	34.3	25.0	21.6	24.1	26.6	29.1	31.6	33.2
97.5°	124.8	120.7	116.5	112.4	108.2	98.0	81.7	65.4	49.1	32.8	34.6
100°	172.1	176.7	181.2	185.7	190.3	174.8	139.6	104.3	68.9	33.6	35.4
102.5°	225.9	229.2	232.4	235.7	239.0	221.3	182.8	144.2	105.6	67.0	61.4
105°	303.6	306.0	308.6	311.0	313.5	304.6	284.2	263.8	243.4	223.1	183.0
107.5°	385.5	387.5	389.4	391.4	393.4	396.0	399.3	402.4	405.7	408.8	379.5
110°	440.1	441.9	443.6	445.4	447.3	449.4	451.9	454.4	456.9	459.4	451.9



TEST NUMBER: P332202-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	492.2	493.8	495.4	497.1	498.7	500.7	503.3	505.7	508.3	510.7	510.9
115°	569.4	570.8	572.1	573.5	574.8	576.6	578.5	580.6	582.7	584.7	586.9
117.5°	644.2	645.9	647.5	649.2	650.9	652.2	653.2	654.3	655.4	656.4	658.2
120°	690.6	692.7	694.7	696.7	698.8	700.1	700.8	701.5	702.2	702.8	704.6
122.5°	737.9	739.6	741.2	742.9	744.6	745.8	746.7	747.6	748.5	749.3	750.6
125°	802.6	804.5	806.3	808.1	809.9	811.3	812.1	813.1	814.0	814.9	815.3
127.5°	865.4	867.2	869.0	870.8	872.7	874.1	875.2	876.3	877.3	878.5	879.2
130°	904.5	906.3	908.2	910.0	911.8	913.1	914.0	915.0	915.8	916.7	917.7
132.5°	942.0	943.8	945.6	947.5	949.3	950.5	951.3	952.0	952.7	953.4	954.3
135°	999.3	1000.6	1002.0	1003.3	1004.7	1005.8	1006.7	1007.7	1008.5	1009.5	1010.1
137.5°	1048.1	1049.9	1051.6	1053.3	1055.0	1056.1	1056.6	1057.2	1057.6	1058.1	1059.2
140°	1080.8	1082.1	1083.5	1084.8	1086.2	1087.2	1087.9	1088.5	1089.3	1089.9	1090.8
142.5°	1110.9	1112.2	1113.6	1115.0	1116.3	1117.4	1118.0	1118.7	1119.4	1120.1	1120.8
145°	1153.1	1154.7	1156.3	1157.9	1159.4	1160.4	1160.9	1161.3	1161.8	1162.2	1162.7
147.5°	1192.8	1193.8	1194.8	1195.9	1197.0	1197.7	1198.2	1198.6	1199.0	1199.5	1200.0
150°	1217.3	1217.9	1218.6	1219.2	1220.0	1220.5	1221.0	1221.4	1221.9	1222.3	1222.8
152.5°	1239.2	1239.5	1239.8	1240.2	1240.5	1240.8	1241.1	1241.3	1241.6	1241.9	1242.7
155°	1270.2	1269.8	1269.3	1268.8	1268.4	1268.3	1268.5	1268.8	1269.0	1269.2	1270.3
157.5°	1294.3	1294.2	1294.2	1294.1	1294.0	1294.0	1293.7	1293.5	1293.2	1293.0	1294.3
160°	1308.9	1308.7	1308.4	1308.2	1308.0	1307.8	1307.6	1307.3	1307.1	1306.9	1308.2
162.5°	1322.8	1322.2	1321.6	1321.0	1320.4	1320.0	1319.8	1319.5	1319.3	1319.1	1320.6
165°	1339.5	1338.8	1338.1	1337.4	1336.7	1336.3	1336.1	1335.9	1335.6	1335.4	1337.2
167.5°	1352.5	1351.6	1350.7	1349.8	1348.8	1348.5	1348.5	1348.5	1348.5	1348.5	1350.3
170°	1359.9	1358.9	1358.0	1357.2	1356.2	1355.7	1355.7	1355.7	1355.7	1355.7	1357.6
172.5°	1364.8	1363.7	1362.6	1361.4	1360.4	1359.9	1360.1	1360.3	1360.5	1360.7	1362.5
175°	1371.0	1369.9	1368.8	1367.6	1366.5	1366.0	1366.3	1366.5	1366.8	1367.0	1368.6
177.5°	1372.7	1371.7	1370.9	1370.0	1369.0	1368.7	1368.9	1369.0	1369.2	1369.4	1370.9
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332202-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1249.1	1251.1	1253.0	1253.9	1253.6	1253.5	1253.2	1253.1
5°	1242.5	1244.9	1247.4	1248.3	1247.8	1247.4	1246.9	1246.4
7.5°	1229.4	1231.5	1233.7	1234.6	1234.3	1234.1	1233.7	1233.4
10°	1217.3	1219.4	1221.6	1222.4	1221.9	1221.5	1221.0	1220.5
12.5°	1204.0	1205.6	1207.2	1207.8	1207.6	1207.3	1207.0	1206.7
15°	1180.1	1182.0	1184.0	1184.2	1182.8	1181.3	1179.9	1178.5
17.5°	1149.9	1151.2	1152.5	1152.9	1152.5	1151.9	1151.4	1150.9
20°	1127.5	1128.5	1129.5	1129.6	1128.9	1128.1	1127.4	1126.7
22.5°	1103.9	1104.6	1105.4	1105.3	1104.5	1103.5	1102.6	1101.7
25°	1064.6	1064.9	1065.2	1064.9	1064.1	1063.4	1062.7	1062.0
27.5°	1022.9	1023.1	1023.3	1022.9	1022.1	1021.1	1020.3	1019.3
30°	994.1	994.1	994.1	993.2	991.6	989.9	988.2	986.5
32.5°	963.8	962.5	961.2	960.0	959.1	958.1	957.3	956.3
35°	914.7	913.2	911.8	910.5	909.3	908.1	906.9	905.7
37.5°	863.9	862.1	860.4	859.1	858.4	857.6	856.8	856.1
40°	830.7	828.8	826.9	825.4	824.4	823.5	822.5	821.6
42.5°	796.1	794.2	792.3	790.9	790.0	789.0	788.1	787.1
45°	744.7	741.8	738.9	736.9	735.7	734.5	733.3	732.1
47.5°	690.4	687.6	684.8	682.9	681.8	680.7	679.7	678.6
50°	654.6	652.0	649.3	647.3	645.9	644.4	642.9	641.5
52.5°	618.2	616.0	613.8	611.9	610.5	609.0	607.6	606.2
55°	562.9	560.3	557.7	555.7	554.5	553.3	552.2	551.0
57.5°	508.5	506.2	503.8	501.9	500.6	499.2	497.8	496.4
60°	470.1	467.9	465.8	464.1	462.9	461.7	460.5	459.3
62.5°	433.0	430.9	428.6	427.2	426.4	425.6	424.8	424.0
65°	377.9	375.9	374.0	372.7	372.0	371.3	370.5	369.8
67.5°	323.1	321.5	319.8	318.5	317.4	316.4	315.4	314.4
70°	287.7	286.1	284.4	283.0	281.8	280.6	279.4	278.1
72.5°	251.9	250.4	248.9	247.9	247.2	246.6	246.1	245.4
75°	200.3	199.1	197.9	196.9	196.2	195.5	194.8	194.1
77.5°	152.1	151.3	150.5	150.1	150.1	150.1	150.1	150.1
80°	121.4	121.1	120.9	120.7	120.7	120.7	120.7	120.7
82.5°	93.4	92.9	92.5	92.2	92.0	91.8	91.7	91.4
85°	52.9	52.4	52.0	51.7	51.7	51.7	51.7	51.7
87.5°	23.8	23.8	23.8	23.8	23.9	24.1	24.2	24.2
90°	26.2	27.2	28.0	28.8	29.2	29.6	30.1	30.6
92.5°	29.0	30.4	31.8	32.7	33.0	33.3	33.5	33.8
95°	34.8	36.4	37.9	38.7	38.7	38.7	38.7	38.7
97.5°	36.4	38.3	40.0	41.0	41.3	41.5	41.7	42.0
100°	37.2	39.1	40.9	41.9	42.1	42.3	42.5	42.8
102.5°	55.8	50.1	44.6	42.0	42.4	42.8	43.2	43.6
105°	142.9	102.9	62.8	43.0	43.5	43.9	44.4	44.8
107.5°	350.1	320.8	291.4	261.6	231.4	201.1	171.0	140.8
110°	444.4	437.0	429.5	409.6	377.2	344.8	312.5	280.1



TEST NUMBER: P332202-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	511.0	511.1	511.3	507.9	501.1	494.2	487.4	480.6
115°	589.2	591.4	593.7	595.3	596.2	597.1	598.0	599.0
117.5°	660.0	661.8	663.6	664.6	664.8	665.0	665.2	665.4
120°	706.5	708.3	710.1	711.0	711.0	711.0	711.0	711.0
122.5°	751.9	753.1	754.4	755.1	755.3	755.4	755.7	755.8
125°	815.8	816.3	816.7	817.1	817.6	818.1	818.5	819.0
127.5°	879.9	880.6	881.4	881.5	881.1	880.6	880.1	879.6
130°	918.5	919.5	920.4	920.6	920.1	919.7	919.2	918.8
132.5°	955.2	956.2	957.0	957.2	956.6	955.9	955.3	954.7
135°	1010.8	1011.5	1012.2	1012.2	1011.5	1010.8	1010.1	1009.5
137.5°	1060.3	1061.4	1062.5	1062.8	1062.3	1061.9	1061.4	1061.0
140°	1091.7	1092.7	1093.5	1093.8	1093.3	1092.8	1092.4	1091.9
142.5°	1121.5	1122.2	1123.0	1123.0	1122.4	1121.7	1121.1	1120.5
145°	1163.2	1163.6	1164.0	1164.3	1164.3	1164.3	1164.3	1164.3
147.5°	1200.4	1200.9	1201.3	1201.0	1200.0	1199.0	1197.9	1196.8
150°	1223.2	1223.7	1224.2	1224.0	1223.4	1222.7	1222.0	1221.3
152.5°	1243.5	1244.4	1245.2	1245.1	1244.0	1242.9	1241.9	1240.9
155°	1271.5	1272.6	1273.7	1273.6	1272.2	1270.9	1269.6	1268.2
157.5°	1295.8	1297.1	1298.5	1298.2	1296.5	1294.7	1292.9	1291.2
160°	1309.6	1311.0	1312.3	1312.2	1310.6	1309.0	1307.4	1305.8
162.5°	1322.2	1323.7	1325.2	1325.3	1323.9	1322.5	1321.1	1319.7
165°	1339.0	1340.8	1342.7	1342.7	1341.2	1339.6	1338.0	1336.4
167.5°	1352.1	1353.8	1355.7	1355.7	1353.8	1352.1	1350.3	1348.5
170°	1359.4	1361.2	1363.0	1363.0	1361.2	1359.4	1357.6	1355.7
172.5°	1364.3	1366.1	1367.9	1367.8	1365.8	1363.8	1361.8	1359.9
175°	1370.2	1371.7	1373.3	1373.2	1371.4	1369.6	1367.8	1366.0
177.5°	1372.3	1373.8	1375.2	1375.1	1373.2	1371.4	1369.6	1367.8
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0

(END OF REPORT)