

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331843-935

Luminaire Tested: **S122RDIW-S865D1440U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331843-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S865D1440U935-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7560.2 lumens  
Efficiency: N/A  
Efficacy: 98.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331843-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331843-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	34				
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	37	36	30				
2	86	79	74	69	78	72	67	63	58	55	52	45	43	41	33	32	31	25				
3	79	70	63	58	71	64	58	53	51	47	44	40	37	35	30	28	26	22				
4	72	62	55	49	65	56	50	45	46	41	38	36	33	30	27	25	23	19				
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	17				
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18	15				
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	20	18	16	13				
8	53	41	33	28	47	37	31	26	31	26	22	25	21	18	19	16	15	12				
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	17	15	13	11				
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20384	20384	20384
5°	20462	20128	20238
10°	20305	19799	19630
15°	20072	19211	18658
20°	19747	18374	17452
25°	19417	17423	16283
30°	18957	16444	14783
35°	18510	15380	13466
40°	18061	14280	11944
45°	17532	13045	10565
50°	16990	11796	9211
55°	16434	10452	7910
60°	15791	9038	6568
65°	15060	7595	5979
70°	14186	6255	5500
75°	13119	5702	5128
80°	11576	5095	4677
85°	9114	4020	4020



TEST NUMBER: P331843-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.2	1.6
10°-20°	324.5	4.3
20°-30°	455.6	6.0
30°-40°	496.8	6.6
40°-50°	456.8	6.0
50°-60°	358.8	4.7
60°-70°	233.9	3.1
70°-80°	120.6	1.6
80°-90°	35.5	0.5
90°-100°	56.5	0.7
100°-110°	207.0	2.7
110°-120°	553.4	7.3
120°-130°	913.5	12.1
130°-140°	971.4	12.8
140°-150°	902.9	11.9
150°-160°	726.0	9.6
160°-170°	467.8	6.2
170°-180°	161.0	2.1
0°-30°	898.3	11.9
0°-40°	1395.1	18.5
0°-60°	2210.7	29.2
0°-90°	2600.7	34.4
90°-120°	816.8	10.8
90°-150°	3604.6	47.7
90°-180°	4959.0	65.6
0°-180°	7560.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1262	1262	1262	1262	1262	
5°	1262	1256	1242	1251	1249	120
15°	1201	1187	1149	1128	1116	338
25°	1090	1051	978	933	914	501
35°	939	878	780	711	683	587
45°	768	689	571	493	463	593
55°	584	493	371	305	281	521
65°	394	301	199	162	156	391
75°	210	133	91	84	82	223
85°	49	26	22	22	22	58
90°	1	14	24	30	33	6
95°	80	42	48	53	53	97
105°	372	388	75	88	93	398
115°	704	725	756	215	100	693
125°	996	1012	1035	1043	1047	887
135°	1232	1251	1262	1274	1272	951
145°	1429	1429	1449	1456	1451	893
155°	1574	1564	1577	1584	1575	725
165°	1658	1651	1654	1662	1654	468
175°	1696	1688	1690	1697	1686	161
180°	1692	1692	1692	1692	1692	



TEST NUMBER: P331843-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1267.0	1266.0	1265.0	1263.9	1263.0	1261.4	1259.1	1256.9	1254.6	1252.4	1254.5
5°	1262.5	1261.2	1259.9	1258.6	1257.4	1255.1	1251.8	1248.5	1245.2	1241.9	1244.1
7.5°	1249.4	1247.8	1246.3	1244.7	1243.1	1240.4	1236.6	1232.7	1228.8	1224.9	1225.6
10°	1238.5	1236.7	1234.9	1233.1	1231.3	1228.0	1222.9	1217.8	1212.7	1207.6	1206.9
12.5°	1224.8	1222.5	1220.4	1218.2	1216.0	1211.7	1205.1	1198.7	1192.1	1185.7	1184.3
15°	1200.8	1198.0	1195.2	1192.4	1189.6	1183.9	1175.3	1166.7	1158.0	1149.3	1144.5
17.5°	1171.3	1167.0	1162.8	1158.5	1154.3	1146.6	1135.5	1124.4	1113.4	1102.3	1096.6
20°	1149.3	1144.3	1139.2	1134.1	1129.0	1120.2	1107.4	1094.8	1082.1	1069.4	1063.0
22.5°	1125.6	1119.9	1114.2	1108.5	1102.9	1092.9	1078.5	1064.2	1049.9	1035.5	1027.3
25°	1089.9	1081.8	1073.7	1065.6	1057.5	1045.0	1028.2	1011.5	994.7	978.0	967.6
27.5°	1047.0	1038.1	1029.3	1020.5	1011.7	997.8	978.9	960.0	941.1	922.2	910.1
30°	1016.8	1007.2	997.6	987.9	978.3	963.3	943.0	922.6	902.3	882.0	869.1
32.5°	987.6	976.3	965.0	953.7	942.5	926.5	905.8	885.0	864.4	843.6	828.9
35°	939.1	926.2	913.3	900.3	887.3	869.7	847.3	825.0	802.7	780.3	764.3
37.5°	890.7	876.5	862.3	848.0	833.8	814.8	791.0	767.2	743.4	719.5	701.9
40°	856.9	841.6	826.4	811.1	795.9	776.0	751.4	726.8	702.1	677.5	659.4
42.5°	822.2	806.1	790.1	774.0	757.9	737.2	711.8	686.3	660.9	635.4	616.8
45°	767.8	750.7	733.7	716.7	699.7	677.9	651.3	624.6	597.9	571.3	553.2
47.5°	714.7	696.7	678.7	660.6	642.7	619.8	592.4	564.8	537.3	509.8	491.9
50°	676.4	658.3	640.3	622.2	604.2	581.3	553.4	525.4	497.5	469.6	452.0
52.5°	638.9	620.0	601.2	582.4	563.5	540.4	513.2	485.8	458.5	431.2	414.2
55°	583.8	564.0	544.2	524.4	504.6	481.0	453.6	426.1	398.7	371.3	356.1
57.5°	527.4	507.0	486.7	466.4	446.2	422.8	396.4	370.1	343.7	317.4	303.4
60°	489.0	468.6	448.4	428.1	407.8	384.5	358.3	332.2	306.1	279.9	267.0
62.5°	451.5	431.2	410.9	390.5	370.2	347.7	322.7	297.8	272.9	247.9	235.6
65°	394.2	373.6	353.0	332.4	311.9	290.2	267.3	244.5	221.6	198.8	190.2
67.5°	338.9	318.5	298.1	277.6	257.2	236.7	216.2	195.6	175.0	154.5	150.5
70°	300.5	280.7	260.9	241.1	221.3	202.6	185.1	167.6	150.1	132.5	130.0
72.5°	263.9	245.0	225.9	207.0	188.0	171.4	157.4	143.3	129.2	115.2	113.0
75°	210.3	192.4	174.7	156.9	139.1	126.0	117.3	108.7	100.0	91.4	89.6
77.5°	157.5	141.8	126.2	110.6	95.1	85.2	81.0	76.9	72.8	68.5	67.5
80°	124.5	111.6	98.7	85.7	72.8	65.0	62.4	59.9	57.3	54.8	53.8
82.5°	94.4	84.3	74.1	64.1	54.0	48.0	46.3	44.6	42.9	41.2	40.6
85°	49.2	43.8	38.5	33.1	27.8	24.8	24.0	23.2	22.5	21.7	21.7
87.5°	14.9	13.9	12.8	11.8	10.8	10.5	10.9	11.4	11.8	12.2	12.3
90°	1.2	4.2	7.2	10.2	13.2	15.8	18.0	20.1	22.3	24.5	25.8
92.5°	24.7	24.5	24.2	23.9	23.7	24.0	25.1	26.3	27.3	28.4	29.1
95°	79.6	70.6	61.6	52.7	43.7	40.1	42.0	43.9	45.9	47.8	49.1
97.5°	158.0	132.7	107.4	82.1	56.7	46.3	50.7	55.1	59.5	63.9	65.0
100°	216.7	179.4	142.2	104.9	67.6	51.3	55.9	60.5	65.2	69.8	72.0
102.5°	281.4	273.5	265.6	257.7	249.9	226.5	187.9	149.1	110.5	71.7	74.6
105°	372.3	380.4	388.6	396.7	404.9	371.9	297.6	223.3	149.0	74.7	77.7
107.5°	475.9	482.4	489.0	495.6	502.2	461.0	371.9	282.8	193.6	104.6	101.5
110°	542.5	548.2	553.9	559.6	565.3	528.8	450.2	371.6	292.9	214.3	187.1



TEST NUMBER: P331843-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	605.2	610.2	615.3	620.4	625.4	618.2	598.8	579.4	559.9	540.5	441.3
115°	704.1	708.8	713.3	718.0	722.6	728.3	735.1	741.9	748.7	755.5	629.6
117.5°	792.6	797.7	802.9	808.0	813.2	818.1	822.8	827.5	832.2	836.9	806.4
120°	857.2	861.3	865.3	869.4	873.5	878.0	882.9	887.8	892.7	897.6	900.9
122.5°	912.1	916.4	920.7	925.0	929.3	934.1	939.4	944.7	950.0	955.4	957.3
125°	995.6	999.1	1002.6	1006.2	1009.7	1014.1	1019.3	1024.4	1029.6	1034.7	1036.6
127.5°	1071.3	1075.1	1079.1	1083.0	1086.9	1090.8	1094.7	1098.5	1102.4	1106.3	1109.1
130°	1119.2	1123.6	1127.9	1132.3	1136.7	1140.3	1143.3	1146.3	1149.3	1152.3	1155.3
132.5°	1168.2	1171.9	1175.6	1179.3	1183.0	1186.4	1189.4	1192.3	1195.3	1198.3	1200.9
135°	1231.9	1236.2	1240.6	1244.9	1249.3	1252.7	1255.2	1257.6	1260.1	1262.5	1265.2
137.5°	1296.3	1299.3	1302.4	1305.4	1308.5	1311.4	1314.1	1317.0	1319.7	1322.5	1325.2
140°	1338.4	1340.6	1342.8	1345.0	1347.1	1349.7	1352.7	1355.7	1358.7	1361.7	1364.2
142.5°	1373.7	1375.6	1377.6	1379.6	1381.6	1384.2	1387.7	1391.1	1394.5	1397.9	1400.2
145°	1429.1	1428.7	1428.5	1428.2	1428.0	1430.1	1434.8	1439.4	1444.0	1448.6	1450.5
147.5°	1477.3	1476.3	1475.2	1474.2	1473.2	1474.9	1479.5	1484.1	1488.7	1493.2	1494.6
150°	1508.6	1506.8	1504.9	1503.0	1501.0	1502.3	1506.6	1511.0	1515.3	1519.7	1521.3
152.5°	1535.1	1533.0	1530.9	1528.7	1526.6	1527.6	1531.7	1535.9	1540.0	1544.1	1545.8
155°	1573.6	1571.1	1568.7	1566.2	1563.7	1564.2	1567.5	1570.7	1574.0	1577.2	1578.8
157.5°	1603.7	1601.6	1599.6	1597.5	1595.4	1595.5	1597.8	1600.1	1602.3	1604.6	1606.5
160°	1621.3	1619.6	1618.1	1616.4	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3	1622.9
162.5°	1636.9	1635.4	1633.7	1632.1	1630.5	1630.3	1631.8	1633.1	1634.6	1636.0	1637.9
165°	1658.0	1656.4	1654.8	1653.1	1651.5	1651.1	1651.9	1652.7	1653.6	1654.3	1656.3
167.5°	1673.7	1672.1	1670.4	1668.8	1667.2	1666.7	1667.5	1668.3	1669.0	1669.8	1671.7
170°	1682.6	1680.9	1679.3	1677.7	1676.0	1675.4	1676.0	1676.5	1677.1	1677.7	1679.6
172.5°	1688.4	1686.8	1685.1	1683.5	1681.9	1681.4	1681.9	1682.4	1683.0	1683.5	1685.4
175°	1696.0	1694.1	1692.2	1690.3	1688.4	1687.7	1688.2	1688.8	1689.4	1689.9	1691.8
177.5°	1697.2	1695.7	1694.2	1692.6	1691.1	1690.5	1690.7	1690.9	1691.1	1691.3	1692.9
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331843-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1256.5	1258.5	1260.5	1261.4	1260.9	1260.5	1260.2	1259.7
5°	1246.5	1248.7	1251.0	1251.8	1251.0	1250.3	1249.5	1248.7
7.5°	1226.3	1226.9	1227.6	1227.3	1226.0	1224.7	1223.3	1222.0
10°	1206.1	1205.3	1204.5	1203.4	1201.9	1200.4	1198.9	1197.3
12.5°	1182.9	1181.6	1180.2	1178.3	1175.7	1173.2	1170.6	1168.1
15°	1139.7	1134.9	1130.1	1126.4	1123.9	1121.3	1118.8	1116.2
17.5°	1090.8	1085.0	1079.3	1074.3	1069.9	1065.6	1061.2	1056.8
20°	1056.7	1050.3	1044.0	1038.0	1032.4	1026.8	1021.2	1015.7
22.5°	1019.3	1011.1	1002.9	996.7	992.6	988.3	984.2	980.1
25°	957.2	946.8	936.3	929.2	925.4	921.6	917.8	914.0
27.5°	897.9	885.8	873.7	864.6	858.6	852.5	846.4	840.4
30°	856.1	843.2	830.2	820.3	813.5	806.6	799.8	792.9
32.5°	814.1	799.3	784.5	773.9	767.5	761.0	754.6	748.1
35°	748.3	732.4	716.4	705.6	700.0	694.4	688.8	683.2
37.5°	684.3	666.7	649.1	637.1	630.7	624.2	617.9	611.5
40°	641.4	623.5	605.4	593.1	586.5	579.9	573.3	566.7
42.5°	598.2	579.5	560.9	548.4	542.0	535.6	529.2	522.8
45°	535.2	517.2	499.1	487.1	481.0	474.9	468.8	462.7
47.5°	473.9	456.0	438.1	426.4	420.9	415.3	409.7	404.2
50°	434.5	417.0	399.5	388.1	382.7	377.4	372.0	366.7
52.5°	397.4	380.5	363.5	352.7	347.7	342.8	337.9	332.9
55°	340.9	325.6	310.4	300.3	295.5	290.7	285.9	281.0
57.5°	289.5	275.5	261.6	252.5	248.5	244.4	240.3	236.3
60°	254.0	241.1	228.1	219.6	215.5	211.5	207.4	203.4
62.5°	223.3	210.9	198.5	191.1	188.7	186.3	183.8	181.4
65°	181.5	172.9	164.3	159.5	158.8	158.1	157.3	156.5
67.5°	146.5	142.6	138.6	136.2	135.4	134.6	133.8	133.0
70°	127.4	124.9	122.3	120.6	119.6	118.6	117.5	116.5
72.5°	110.9	108.7	106.6	105.3	104.6	104.0	103.4	102.8
75°	87.8	86.1	84.3	83.3	83.0	82.7	82.5	82.2
77.5°	66.6	65.5	64.5	63.8	63.4	62.9	62.6	62.2
80°	52.8	51.8	50.8	50.3	50.3	50.3	50.3	50.3
82.5°	40.0	39.3	38.7	38.4	38.4	38.4	38.4	38.4
85°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7
87.5°	12.3	12.4	12.5	12.6	12.7	12.8	12.9	13.0
90°	27.2	28.6	30.0	30.9	31.4	31.9	32.5	33.1
92.5°	29.8	30.6	31.3	31.8	32.1	32.4	32.7	33.1
95°	50.5	51.8	53.2	53.7	53.5	53.2	53.0	52.7
97.5°	66.1	67.2	68.3	69.0	69.3	69.7	70.0	70.3
100°	74.1	76.4	78.5	79.9	80.4	80.9	81.5	82.1
102.5°	77.4	80.2	83.1	84.9	85.7	86.4	87.1	87.9
105°	80.7	83.7	86.7	88.7	89.8	90.9	92.0	93.1
107.5°	98.5	95.4	92.4	91.4	92.5	93.6	94.7	95.7
110°	159.9	132.7	105.5	92.4	93.5	94.5	95.7	96.8





TEST NUMBER: P331843-935

CATALOG NUMBER: S122RDIW-S865D1440U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	342.0	242.7	143.4	94.2	95.1	96.0	96.9	97.7
115°	503.6	377.5	251.6	178.7	159.2	139.6	120.0	100.4
117.5°	775.9	745.5	715.0	667.5	603.1	538.7	474.3	410.0
120°	904.1	907.4	910.7	893.9	857.2	820.4	783.7	747.0
122.5°	959.3	961.3	963.2	960.6	953.5	946.4	939.3	932.1
125°	1038.5	1040.4	1042.3	1043.7	1044.6	1045.3	1046.2	1047.0
127.5°	1111.8	1114.6	1117.3	1118.9	1119.0	1119.1	1119.3	1119.5
130°	1158.3	1161.3	1164.2	1165.6	1165.4	1165.1	1164.8	1164.5
132.5°	1203.4	1206.0	1208.6	1209.7	1209.4	1209.2	1208.9	1208.6
135°	1267.9	1270.7	1273.4	1274.5	1273.9	1273.4	1272.8	1272.3
137.5°	1327.8	1330.5	1333.2	1334.0	1333.1	1332.2	1331.3	1330.3
140°	1366.6	1369.1	1371.5	1372.0	1370.7	1369.3	1368.0	1366.6
142.5°	1402.4	1404.6	1406.9	1407.3	1405.9	1404.5	1403.3	1401.9
145°	1452.4	1454.3	1456.3	1456.6	1455.2	1453.8	1452.4	1451.1
147.5°	1496.1	1497.5	1498.9	1499.0	1497.9	1496.8	1495.6	1494.4
150°	1522.9	1524.6	1526.2	1526.3	1525.0	1523.6	1522.2	1520.9
152.5°	1547.4	1549.0	1550.7	1550.6	1548.8	1547.0	1545.2	1543.4
155°	1580.5	1582.1	1583.7	1583.5	1581.3	1579.2	1576.9	1574.8
157.5°	1608.3	1610.2	1612.1	1611.9	1609.8	1607.7	1605.5	1603.4
160°	1624.5	1626.2	1627.8	1627.7	1625.8	1623.8	1622.0	1620.1
162.5°	1639.7	1641.6	1643.4	1643.1	1640.8	1638.5	1636.2	1633.8
165°	1658.2	1660.1	1662.0	1662.0	1660.1	1658.2	1656.3	1654.3
167.5°	1673.6	1675.5	1677.4	1677.1	1674.7	1672.2	1669.8	1667.3
170°	1681.4	1683.3	1685.2	1685.0	1682.6	1680.1	1677.7	1675.2
172.5°	1687.3	1689.2	1691.1	1690.8	1688.4	1685.9	1683.5	1681.0
175°	1693.7	1695.6	1697.5	1697.1	1694.4	1691.6	1688.9	1686.2
177.5°	1694.4	1695.9	1697.5	1697.2	1695.2	1693.3	1691.3	1689.4
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3

(END OF REPORT)