

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332208-927

Luminaire Tested: **S123DIW-S1000D1535U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332208-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1535U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8128.5 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332208-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332208-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	42	41	40	34
2	87	80	74	68	79	73	67	63	60	56	53	48	45	43	37	35	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	34	30	27	26	23	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	24	21	19	16
7	56	44	37	31	51	41	34	29	34	29	25	28	24	21	21	19	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13497	13497	13497
5°	13560	13374	13467
10°	13470	13258	13340
15°	13312	13108	13133
20°	13128	12893	12906
25°	12883	12638	12613
30°	12609	12356	12261
35°	12326	12056	11901
40°	12029	11726	11545
45°	11702	11423	11144
50°	11375	11050	10742
55°	10946	10663	10340
60°	10514	10213	9888
65°	10132	9722	9419
70°	9567	9161	8752
75°	8742	8430	8072
80°	7885	7550	7482
85°	6928	6657	6385



TEST NUMBER: P332208-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.1	1.5
10°-20°	333.5	4.1
20°-30°	492.7	6.1
30°-40°	575.5	7.1
40°-50°	578.6	7.1
50°-60°	508.2	6.3
60°-70°	378.6	4.7
70°-80°	215.7	2.7
80°-90°	66.4	0.8
90°-100°	58.0	0.7
100°-110°	276.2	3.4
110°-120°	663.5	8.2
120°-130°	844.9	10.4
130°-140°	902.7	11.1
140°-150°	844.1	10.4
150°-160°	680.9	8.4
160°-170°	439.5	5.4
170°-180°	151.5	1.9
0°-30°	944.3	11.6
0°-40°	1519.8	18.7
0°-60°	2606.6	32.1
0°-90°	3267.3	40.2
90°-120°	997.6	12.3
90°-150°	3589.3	44.2
90°-180°	4861.0	59.8
0°-180°	8128.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1254	1254	1254	1254	1254	
5°	1255	1249	1238	1248	1246	119
15°	1195	1190	1176	1184	1178	337
25°	1085	1078	1064	1065	1062	499
35°	938	931	918	911	906	587
45°	769	764	750	738	732	593
55°	583	582	568	557	551	522
65°	398	392	382	373	370	392
75°	210	206	203	197	194	225
85°	56	54	54	52	52	62
90°	1	13	28	33	36	6
95°	72	27	37	44	45	89
105°	353	359	259	62	52	374
115°	662	669	680	691	696	653
125°	933	942	948	950	952	833
135°	1162	1169	1174	1177	1174	894
145°	1341	1349	1351	1354	1354	839
155°	1477	1475	1476	1481	1474	680
165°	1557	1554	1553	1561	1554	440
175°	1594	1588	1589	1597	1588	152
180°	1594	1594	1594	1594	1594	



TEST NUMBER: P332208-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1258.2	1257.5	1256.7	1255.9	1255.2	1253.7	1251.6	1249.5	1247.4	1245.3	1247.2
5°	1255.0	1253.8	1252.6	1251.4	1250.2	1248.3	1245.7	1243.0	1240.4	1237.8	1240.2
7.5°	1242.7	1241.5	1240.3	1239.1	1237.9	1236.0	1233.3	1230.5	1227.8	1225.0	1227.2
10°	1232.4	1231.2	1229.9	1228.8	1227.6	1225.4	1222.3	1219.2	1216.1	1213.0	1215.1
12.5°	1218.5	1217.6	1216.6	1215.5	1214.6	1212.6	1209.7	1206.7	1203.8	1200.9	1202.5
15°	1194.6	1193.7	1192.7	1191.8	1190.8	1188.7	1185.7	1182.6	1179.4	1176.3	1178.2
17.5°	1166.8	1165.5	1164.3	1163.1	1161.8	1159.7	1156.5	1153.4	1150.3	1147.2	1148.5
20°	1146.1	1144.7	1143.3	1141.8	1140.3	1138.0	1135.0	1131.9	1128.8	1125.6	1126.6
22.5°	1122.8	1121.4	1120.0	1118.5	1117.1	1114.8	1111.7	1108.6	1105.5	1102.3	1103.1
25°	1084.7	1083.2	1081.8	1080.4	1078.9	1076.7	1073.5	1070.4	1067.3	1064.1	1064.4
27.5°	1043.9	1042.5	1041.1	1039.7	1038.3	1035.9	1032.6	1029.3	1025.9	1022.5	1022.7
30°	1014.5	1013.4	1012.2	1011.0	1009.8	1007.5	1004.2	1000.8	997.4	994.1	994.1
32.5°	985.2	983.7	982.1	980.5	978.9	976.8	974.2	971.7	969.1	966.5	965.1
35°	938.0	936.6	935.2	933.7	932.2	930.0	926.9	923.8	920.7	917.5	916.1
37.5°	889.7	887.9	886.1	884.2	882.4	880.0	876.8	873.6	870.4	867.3	865.5
40°	856.1	854.6	853.2	851.8	850.3	848.0	844.5	841.2	837.9	834.5	832.6
42.5°	822.4	820.8	819.2	817.5	815.9	813.4	810.1	806.8	803.4	800.0	798.1
45°	768.7	767.8	766.8	765.9	764.9	762.9	759.8	756.6	753.5	750.4	747.6
47.5°	715.5	714.1	712.7	711.3	710.0	707.7	704.9	702.0	699.0	696.1	693.2
50°	679.3	678.0	676.8	675.7	674.5	672.3	669.2	666.1	663.0	659.9	657.2
52.5°	641.3	640.5	639.7	638.9	638.0	636.0	632.7	629.4	626.1	622.7	620.5
55°	583.3	583.0	582.8	582.6	582.3	580.7	577.6	574.4	571.3	568.2	565.5
57.5°	528.1	527.3	526.5	525.7	524.8	523.2	520.7	518.2	515.7	513.3	510.9
60°	488.4	488.1	487.9	487.7	487.4	485.9	483.0	480.1	477.3	474.4	472.2
62.5°	453.0	452.4	451.8	451.1	450.6	448.9	445.9	443.1	440.2	437.3	435.1
65°	397.8	396.6	395.5	394.3	393.1	391.3	388.9	386.5	384.0	381.7	379.8
67.5°	339.5	338.3	337.3	336.3	335.2	333.7	331.9	330.1	328.3	326.5	324.8
70°	304.0	302.6	301.2	299.8	298.3	296.8	295.4	294.0	292.6	291.1	289.5
72.5°	267.0	265.9	264.8	263.8	262.8	261.4	259.8	258.2	256.5	254.8	253.4
75°	210.2	209.3	208.3	207.4	206.4	205.6	204.9	204.1	203.4	202.7	201.5
77.5°	160.0	159.5	158.9	158.4	157.9	157.2	156.4	155.5	154.6	153.8	153.0
80°	127.2	126.5	125.8	125.1	124.4	123.7	123.3	122.8	122.3	121.8	121.6
82.5°	95.3	95.1	95.1	94.9	94.7	94.6	94.5	94.4	94.3	94.3	93.8
85°	56.1	55.6	55.1	54.7	54.2	53.9	53.9	53.9	53.9	53.9	53.4
87.5°	22.7	22.6	22.6	22.5	22.5	22.7	23.2	23.7	24.2	24.6	24.7
90°	1.2	3.8	6.4	9.1	11.7	14.7	18.1	21.5	25.0	28.4	29.5
92.5°	22.0	21.3	20.5	19.8	19.1	20.0	22.6	25.2	27.7	30.3	32.0
95°	72.2	61.5	50.7	39.8	29.1	25.1	28.0	30.9	33.8	36.7	38.6
97.5°	145.2	140.4	135.5	130.6	125.8	113.9	95.0	76.0	57.1	38.1	40.2
100°	200.2	205.4	210.6	215.9	221.2	203.3	162.2	121.2	80.2	39.1	41.2
102.5°	262.7	266.5	270.3	274.0	277.8	257.3	212.5	167.6	122.8	78.0	71.4
105°	352.9	355.8	358.7	361.6	364.5	354.1	330.4	306.7	283.0	259.4	212.8
107.5°	448.1	450.4	452.7	455.1	457.4	460.4	464.1	467.9	471.7	475.4	441.2
110°	511.6	513.7	515.8	517.9	520.1	522.5	525.5	528.3	531.2	534.1	525.5



TEST NUMBER: P332208-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	572.3	574.2	576.1	578.0	579.8	582.3	585.1	588.0	590.9	593.8	594.0
115°	662.0	663.6	665.2	666.8	668.4	670.3	672.7	675.0	677.4	679.8	682.4
117.5°	748.9	750.9	752.8	754.8	756.8	758.4	759.5	760.7	761.9	763.2	765.2
120°	803.0	805.3	807.7	810.1	812.5	814.0	814.8	815.6	816.3	817.1	819.3
122.5°	857.9	859.8	861.8	863.7	865.7	867.2	868.2	869.2	870.1	871.2	872.7
125°	933.2	935.3	937.5	939.5	941.7	943.3	944.3	945.3	946.4	947.5	948.0
127.5°	1006.2	1008.3	1010.4	1012.5	1014.6	1016.3	1017.6	1018.8	1020.1	1021.4	1022.2
130°	1051.6	1053.8	1055.9	1058.0	1060.1	1061.7	1062.7	1063.7	1064.9	1065.9	1066.9
132.5°	1095.3	1097.3	1099.5	1101.5	1103.7	1105.2	1106.0	1106.8	1107.6	1108.5	1109.5
135°	1161.8	1163.4	1165.0	1166.6	1168.2	1169.4	1170.4	1171.6	1172.6	1173.6	1174.4
137.5°	1218.6	1220.7	1222.7	1224.6	1226.6	1228.0	1228.5	1229.1	1229.7	1230.3	1231.5
140°	1256.6	1258.1	1259.7	1261.3	1262.9	1264.0	1264.8	1265.6	1266.4	1267.2	1268.3
142.5°	1291.6	1293.2	1294.7	1296.3	1297.9	1299.1	1299.9	1300.7	1301.5	1302.3	1303.1
145°	1340.6	1342.4	1344.3	1346.2	1348.0	1349.2	1349.7	1350.2	1350.8	1351.3	1351.8
147.5°	1386.8	1388.1	1389.3	1390.4	1391.6	1392.5	1393.1	1393.6	1394.1	1394.6	1395.2
150°	1415.2	1416.0	1416.8	1417.6	1418.4	1419.0	1419.6	1420.1	1420.6	1421.2	1421.7
152.5°	1440.8	1441.2	1441.5	1441.9	1442.3	1442.6	1443.0	1443.3	1443.6	1443.9	1444.9
155°	1476.8	1476.3	1475.8	1475.3	1474.7	1474.6	1474.9	1475.1	1475.4	1475.6	1476.9
157.5°	1504.8	1504.8	1504.7	1504.6	1504.6	1504.4	1504.1	1503.9	1503.6	1503.3	1504.9
160°	1521.9	1521.5	1521.3	1521.1	1520.8	1520.5	1520.3	1520.0	1519.7	1519.5	1521.1
162.5°	1537.9	1537.2	1536.6	1535.9	1535.2	1534.7	1534.5	1534.2	1533.9	1533.7	1535.5
165°	1557.4	1556.6	1555.8	1555.0	1554.2	1553.7	1553.4	1553.2	1552.9	1552.6	1554.7
167.5°	1572.5	1571.5	1570.4	1569.4	1568.3	1567.8	1567.8	1567.8	1567.8	1567.8	1569.9
170°	1581.0	1580.0	1578.9	1577.9	1576.8	1576.3	1576.3	1576.3	1576.3	1576.3	1578.4
172.5°	1586.7	1585.5	1584.2	1582.9	1581.7	1581.1	1581.4	1581.6	1581.8	1582.0	1584.1
175°	1594.0	1592.8	1591.4	1590.1	1588.8	1588.2	1588.6	1588.8	1589.0	1589.4	1591.2
177.5°	1595.9	1594.9	1593.9	1592.8	1591.7	1591.3	1591.6	1591.7	1592.0	1592.2	1593.9
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332208-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1249.1	1251.1	1253.0	1253.9	1253.6	1253.5	1253.2	1253.1
5°	1242.5	1244.9	1247.4	1248.3	1247.8	1247.4	1246.9	1246.4
7.5°	1229.4	1231.5	1233.7	1234.6	1234.3	1234.1	1233.7	1233.4
10°	1217.3	1219.4	1221.6	1222.4	1221.9	1221.5	1221.0	1220.5
12.5°	1204.0	1205.6	1207.2	1207.8	1207.6	1207.3	1207.0	1206.7
15°	1180.1	1182.0	1184.0	1184.2	1182.8	1181.3	1179.9	1178.5
17.5°	1149.9	1151.2	1152.5	1152.9	1152.5	1151.9	1151.4	1150.9
20°	1127.5	1128.5	1129.5	1129.6	1128.9	1128.1	1127.4	1126.7
22.5°	1103.9	1104.6	1105.4	1105.3	1104.5	1103.5	1102.6	1101.7
25°	1064.6	1064.9	1065.2	1064.9	1064.1	1063.4	1062.7	1062.0
27.5°	1022.9	1023.1	1023.3	1022.9	1022.1	1021.1	1020.3	1019.3
30°	994.1	994.1	994.1	993.2	991.6	989.9	988.2	986.5
32.5°	963.8	962.5	961.2	960.0	959.1	958.1	957.3	956.3
35°	914.7	913.2	911.8	910.5	909.3	908.1	906.9	905.7
37.5°	863.9	862.1	860.4	859.1	858.4	857.6	856.8	856.1
40°	830.7	828.8	826.9	825.4	824.4	823.5	822.5	821.6
42.5°	796.1	794.2	792.3	790.9	790.0	789.0	788.1	787.1
45°	744.7	741.8	738.9	736.9	735.7	734.5	733.3	732.1
47.5°	690.4	687.6	684.8	682.9	681.8	680.7	679.7	678.6
50°	654.6	652.0	649.3	647.3	645.9	644.4	642.9	641.5
52.5°	618.2	616.0	613.8	611.9	610.5	609.0	607.6	606.2
55°	562.9	560.3	557.7	555.7	554.5	553.3	552.2	551.0
57.5°	508.5	506.2	503.8	501.9	500.6	499.2	497.8	496.4
60°	470.1	467.9	465.8	464.1	462.9	461.7	460.5	459.3
62.5°	433.0	430.9	428.6	427.2	426.4	425.6	424.8	424.0
65°	377.9	375.9	374.0	372.7	372.0	371.3	370.5	369.8
67.5°	323.1	321.5	319.8	318.5	317.4	316.4	315.4	314.4
70°	287.7	286.1	284.4	283.0	281.8	280.6	279.4	278.1
72.5°	251.9	250.4	248.9	247.9	247.2	246.6	246.1	245.4
75°	200.3	199.1	197.9	196.9	196.2	195.5	194.8	194.1
77.5°	152.1	151.3	150.5	150.1	150.1	150.1	150.1	150.1
80°	121.4	121.1	120.9	120.7	120.7	120.7	120.7	120.7
82.5°	93.4	92.9	92.5	92.2	92.0	91.8	91.7	91.4
85°	52.9	52.4	52.0	51.7	51.7	51.7	51.7	51.7
87.5°	24.7	24.7	24.7	24.8	24.9	25.0	25.1	25.2
90°	30.5	31.6	32.6	33.4	34.0	34.5	35.0	35.5
92.5°	33.7	35.4	37.1	38.0	38.3	38.7	39.0	39.3
95°	40.4	42.2	44.0	45.0	45.0	45.0	45.0	45.0
97.5°	42.4	44.4	46.6	47.8	48.0	48.2	48.6	48.8
100°	43.3	45.4	47.5	48.7	49.0	49.2	49.5	49.7
102.5°	64.9	58.4	51.8	48.8	49.3	49.7	50.2	50.7
105°	166.2	119.6	73.0	50.0	50.5	51.1	51.6	52.1
107.5°	407.0	372.9	338.7	304.1	269.0	233.9	198.8	163.7
110°	516.7	508.0	499.4	476.2	438.6	400.9	363.3	325.7



TEST NUMBER: P332208-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	594.1	594.3	594.5	590.6	582.6	574.6	566.7	558.7
115°	685.1	687.7	690.3	692.1	693.2	694.3	695.3	696.4
117.5°	767.4	769.4	771.6	772.8	772.9	773.2	773.4	773.6
120°	821.4	823.5	825.6	826.6	826.6	826.6	826.6	826.6
122.5°	874.1	875.6	877.1	877.9	878.1	878.3	878.5	878.8
125°	948.5	949.0	949.5	950.1	950.6	951.1	951.6	952.2
127.5°	1023.0	1023.9	1024.7	1024.8	1024.4	1023.8	1023.3	1022.8
130°	1067.9	1069.1	1070.1	1070.3	1069.8	1069.3	1068.7	1068.3
132.5°	1110.6	1111.7	1112.7	1112.9	1112.1	1111.4	1110.6	1109.9
135°	1175.2	1176.0	1176.8	1176.8	1176.0	1175.2	1174.4	1173.6
137.5°	1232.8	1234.1	1235.3	1235.6	1235.2	1234.6	1234.1	1233.6
140°	1269.3	1270.3	1271.4	1271.7	1271.1	1270.7	1270.1	1269.6
142.5°	1303.9	1304.8	1305.6	1305.7	1305.0	1304.2	1303.5	1302.7
145°	1352.3	1352.9	1353.4	1353.7	1353.7	1353.7	1353.7	1353.7
147.5°	1395.7	1396.2	1396.8	1396.4	1395.2	1394.0	1392.7	1391.5
150°	1422.2	1422.8	1423.2	1423.2	1422.4	1421.6	1420.8	1420.0
152.5°	1445.8	1446.8	1447.7	1447.6	1446.4	1445.1	1443.9	1442.7
155°	1478.3	1479.6	1480.9	1480.7	1479.2	1477.6	1476.0	1474.5
157.5°	1506.5	1508.1	1509.7	1509.4	1507.4	1505.3	1503.2	1501.2
160°	1522.7	1524.2	1525.7	1525.7	1523.8	1521.9	1520.1	1518.3
162.5°	1537.2	1539.1	1540.8	1540.9	1539.3	1537.6	1536.0	1534.4
165°	1556.8	1558.9	1561.1	1561.2	1559.3	1557.5	1555.6	1553.8
167.5°	1572.0	1574.1	1576.2	1576.2	1574.1	1572.0	1569.9	1567.8
170°	1580.5	1582.6	1584.8	1584.8	1582.6	1580.5	1578.4	1576.3
172.5°	1586.2	1588.3	1590.4	1590.3	1588.0	1585.7	1583.3	1581.0
175°	1593.0	1594.8	1596.7	1596.6	1594.4	1592.4	1590.2	1588.2
177.5°	1595.5	1597.2	1598.9	1598.7	1596.6	1594.5	1592.4	1590.3
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0

(END OF REPORT)