

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332209-927

Luminaire Tested: **S123DIW-S1000D1535U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332209-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1535U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7480.6 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332209-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332209-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80		64	64	64		50	50	50	44
1	96	92	88	85	88	84	81	78	70	67	65		57	55	53		44	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54		50	47	45		39	37	36	31
3	80	71	63	57	73	65	58	53	54	49	45		44	41	38		35	32	30	26
4	73	62	55	49	67	57	50	45	48	43	39		39	35	32		31	28	26	22
5	67	55	47	41	61	51	44	39	43	37	33		35	31	28		28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29		32	28	24		25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25		29	25	22		23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23		26	22	19		21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20		24	20	17		19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18		22	18	16		18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13497	13497	13497
5°	13560	13374	13467
10°	13470	13258	13340
15°	13312	13108	13133
20°	13128	12893	12906
25°	12883	12638	12613
30°	12609	12356	12261
35°	12326	12056	11901
40°	12029	11726	11545
45°	11702	11423	11144
50°	11375	11050	10742
55°	10946	10663	10340
60°	10514	10213	9888
65°	10132	9722	9419
70°	9567	9161	8752
75°	8742	8430	8072
80°	7885	7550	7482
85°	6928	6657	6385



TEST NUMBER: P332209-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.1	1.6
10°-20°	333.5	4.5
20°-30°	492.7	6.6
30°-40°	575.5	7.7
40°-50°	578.6	7.7
50°-60°	508.2	6.8
60°-70°	378.6	5.1
70°-80°	215.7	2.9
80°-90°	66.4	0.9
90°-100°	99.1	1.3
100°-110°	296.5	4.0
110°-120°	504.3	6.7
120°-130°	663.4	8.9
130°-140°	745.6	10.0
140°-150°	732.9	9.8
150°-160°	617.0	8.2
160°-170°	410.7	5.5
170°-180°	143.8	1.9
0°-30°	944.3	12.6
0°-40°	1519.8	20.3
0°-60°	2606.6	34.8
0°-90°	3267.3	43.7
90°-120°	899.9	12.0
90°-150°	3041.8	40.7
90°-180°	4213.0	56.3
0°-180°	7480.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1254	1254	1254	1254	1254	
5°	1255	1249	1238	1248	1246	119
15°	1195	1190	1176	1184	1178	337
25°	1085	1078	1064	1065	1062	499
35°	938	931	918	911	906	587
45°	769	764	750	738	732	593
55°	583	582	568	557	551	522
65°	398	392	382	373	370	392
75°	210	206	203	197	194	225
85°	56	54	54	52	52	62
90°	1	13	29	33	36	7
95°	70	79	88	93	93	79
105°	269	272	282	282	284	288
115°	508	511	509	510	509	502
125°	743	746	744	739	735	662
135°	964	971	970	965	963	743
145°	1170	1172	1175	1174	1170	730
155°	1339	1339	1340	1344	1337	616
165°	1459	1455	1455	1461	1454	411
175°	1517	1513	1512	1519	1511	144
180°	1521	1521	1521	1521	1521	



TEST NUMBER: P332209-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1258.2	1257.5	1256.7	1255.9	1255.2	1253.7	1251.6	1249.5	1247.4	1245.3	1247.2
5°	1255.0	1253.8	1252.6	1251.4	1250.2	1248.3	1245.7	1243.0	1240.4	1237.8	1240.2
7.5°	1242.7	1241.5	1240.3	1239.1	1237.9	1236.0	1233.3	1230.5	1227.8	1225.0	1227.2
10°	1232.4	1231.2	1229.9	1228.8	1227.6	1225.4	1222.3	1219.2	1216.1	1213.0	1215.1
12.5°	1218.5	1217.6	1216.6	1215.5	1214.6	1212.6	1209.7	1206.7	1203.8	1200.9	1202.5
15°	1194.6	1193.7	1192.7	1191.8	1190.8	1188.7	1185.7	1182.6	1179.4	1176.3	1178.2
17.5°	1166.8	1165.5	1164.3	1163.1	1161.8	1159.7	1156.5	1153.4	1150.3	1147.2	1148.5
20°	1146.1	1144.7	1143.3	1141.8	1140.3	1138.0	1135.0	1131.9	1128.8	1125.6	1126.6
22.5°	1122.8	1121.4	1120.0	1118.5	1117.1	1114.8	1111.7	1108.6	1105.5	1102.3	1103.1
25°	1084.7	1083.2	1081.8	1080.4	1078.9	1076.7	1073.5	1070.4	1067.3	1064.1	1064.4
27.5°	1043.9	1042.5	1041.1	1039.7	1038.3	1035.9	1032.6	1029.3	1025.9	1022.5	1022.7
30°	1014.5	1013.4	1012.2	1011.0	1009.8	1007.5	1004.2	1000.8	997.4	994.1	994.1
32.5°	985.2	983.7	982.1	980.5	978.9	976.8	974.2	971.7	969.1	966.5	965.1
35°	938.0	936.6	935.2	933.7	932.2	930.0	926.9	923.8	920.7	917.5	916.1
37.5°	889.7	887.9	886.1	884.2	882.4	880.0	876.8	873.6	870.4	867.3	865.5
40°	856.1	854.6	853.2	851.8	850.3	848.0	844.5	841.2	837.9	834.5	832.6
42.5°	822.4	820.8	819.2	817.5	815.9	813.4	810.1	806.8	803.4	800.0	798.1
45°	768.7	767.8	766.8	765.9	764.9	762.9	759.8	756.6	753.5	750.4	747.6
47.5°	715.5	714.1	712.7	711.3	710.0	707.7	704.9	702.0	699.0	696.1	693.2
50°	679.3	678.0	676.8	675.7	674.5	672.3	669.2	666.1	663.0	659.9	657.2
52.5°	641.3	640.5	639.7	638.9	638.0	636.0	632.7	629.4	626.1	622.7	620.5
55°	583.3	583.0	582.8	582.6	582.3	580.7	577.6	574.4	571.3	568.2	565.5
57.5°	528.1	527.3	526.5	525.7	524.8	523.2	520.7	518.2	515.7	513.3	510.9
60°	488.4	488.1	487.9	487.7	487.4	485.9	483.0	480.1	477.3	474.4	472.2
62.5°	453.0	452.4	451.8	451.1	450.6	448.9	445.9	443.1	440.2	437.3	435.1
65°	397.8	396.6	395.5	394.3	393.1	391.3	388.9	386.5	384.0	381.7	379.8
67.5°	339.5	338.3	337.3	336.3	335.2	333.7	331.9	330.1	328.3	326.5	324.8
70°	304.0	302.6	301.2	299.8	298.3	296.8	295.4	294.0	292.6	291.1	289.5
72.5°	267.0	265.9	264.8	263.8	262.8	261.4	259.8	258.2	256.5	254.8	253.4
75°	210.2	209.3	208.3	207.4	206.4	205.6	204.9	204.1	203.4	202.7	201.5
77.5°	160.0	159.5	158.9	158.4	157.9	157.2	156.4	155.5	154.6	153.8	153.0
80°	127.2	126.5	125.8	125.1	124.4	123.7	123.3	122.8	122.3	121.8	121.6
82.5°	95.3	95.1	95.1	94.9	94.7	94.6	94.5	94.4	94.3	94.3	93.8
85°	56.1	55.6	55.1	54.7	54.2	53.9	53.9	53.9	53.9	53.9	53.4
87.5°	22.7	22.7	22.6	22.5	22.5	22.7	23.2	23.7	24.2	24.7	24.7
90°	1.2	3.9	6.5	9.2	11.8	14.9	18.3	21.8	25.2	28.7	29.7
92.5°	28.9	30.7	32.5	34.3	36.1	38.0	40.0	41.9	43.9	45.9	46.7
95°	70.5	72.3	74.2	76.0	78.0	79.9	82.0	84.1	86.3	88.4	89.4
97.5°	125.2	126.6	127.9	129.4	130.7	132.1	133.7	135.2	136.8	138.3	139.6
100°	162.5	164.1	165.6	167.2	168.8	170.3	171.6	172.9	174.3	175.6	176.4
102.5°	205.5	206.4	207.4	208.3	209.3	210.6	212.4	214.1	215.9	217.6	218.5
105°	268.8	269.3	269.8	270.4	270.9	272.4	274.7	277.1	279.6	281.9	281.9
107.5°	342.4	342.7	343.0	343.3	343.6	344.3	345.2	346.2	347.1	348.1	349.0
110°	388.2	388.8	389.3	389.8	390.4	390.9	391.4	392.0	392.4	393.0	394.1



TEST NUMBER: P332209-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	436.0	436.3	436.7	437.0	437.3	437.5	437.6	437.7	437.8	437.9	439.2
115°	507.7	508.5	509.3	510.1	510.9	511.0	510.5	509.9	509.5	508.9	509.1
117.5°	579.9	580.4	580.9	581.5	581.9	581.9	581.2	580.5	579.8	579.2	579.1
120°	624.8	626.4	628.0	629.5	631.1	631.3	629.9	628.6	627.2	626.0	625.7
122.5°	671.6	672.7	673.9	675.1	676.3	676.5	675.8	675.1	674.5	673.8	673.0
125°	743.0	743.8	744.7	745.4	746.2	746.3	745.8	745.3	744.7	744.3	743.1
127.5°	809.0	810.6	812.4	814.0	815.8	816.3	815.7	815.2	814.6	814.0	812.5
130°	852.9	855.1	857.1	859.3	861.4	862.1	861.3	860.5	859.7	858.9	857.9
132.5°	896.9	899.0	901.1	903.2	905.4	906.2	905.5	905.0	904.4	903.8	902.5
135°	964.0	965.6	967.2	968.8	970.4	971.1	970.8	970.5	970.3	970.0	968.9
137.5°	1026.1	1027.5	1028.8	1030.2	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1
140°	1069.1	1070.5	1071.8	1073.1	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0
142.5°	1108.3	1109.6	1111.0	1112.3	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2
145°	1169.5	1170.1	1170.5	1171.1	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2
147.5°	1223.0	1223.9	1224.9	1225.9	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7
150°	1260.3	1260.8	1261.3	1261.9	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0
152.5°	1290.9	1291.6	1292.4	1293.1	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1
155°	1339.1	1339.1	1339.1	1339.1	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4
157.5°	1380.2	1379.9	1379.6	1379.3	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9
160°	1406.0	1405.5	1404.9	1404.4	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9
162.5°	1428.9	1428.2	1427.4	1426.7	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9
165°	1458.6	1457.8	1457.0	1456.2	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6
167.5°	1482.3	1481.1	1480.1	1479.0	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0
170°	1495.6	1494.5	1493.5	1492.4	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7
172.5°	1506.1	1505.1	1504.0	1502.9	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0
175°	1517.1	1516.1	1515.0	1513.9	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9
177.5°	1521.6	1520.8	1520.0	1519.1	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332209-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1249.1	1251.1	1253.0	1253.9	1253.6	1253.5	1253.2	1253.1
5°	1242.5	1244.9	1247.4	1248.3	1247.8	1247.4	1246.9	1246.4
7.5°	1229.4	1231.5	1233.7	1234.6	1234.3	1234.1	1233.7	1233.4
10°	1217.3	1219.4	1221.6	1222.4	1221.9	1221.5	1221.0	1220.5
12.5°	1204.0	1205.6	1207.2	1207.8	1207.6	1207.3	1207.0	1206.7
15°	1180.1	1182.0	1184.0	1184.2	1182.8	1181.3	1179.9	1178.5
17.5°	1149.9	1151.2	1152.5	1152.9	1152.5	1151.9	1151.4	1150.9
20°	1127.5	1128.5	1129.5	1129.6	1128.9	1128.1	1127.4	1126.7
22.5°	1103.9	1104.6	1105.4	1105.3	1104.5	1103.5	1102.6	1101.7
25°	1064.6	1064.9	1065.2	1064.9	1064.1	1063.4	1062.7	1062.0
27.5°	1022.9	1023.1	1023.3	1022.9	1022.1	1021.1	1020.3	1019.3
30°	994.1	994.1	994.1	993.2	991.6	989.9	988.2	986.5
32.5°	963.8	962.5	961.2	960.0	959.1	958.1	957.3	956.3
35°	914.7	913.2	911.8	910.5	909.3	908.1	906.9	905.7
37.5°	863.9	862.1	860.4	859.1	858.4	857.6	856.8	856.1
40°	830.7	828.8	826.9	825.4	824.4	823.5	822.5	821.6
42.5°	796.1	794.2	792.3	790.9	790.0	789.0	788.1	787.1
45°	744.7	741.8	738.9	736.9	735.7	734.5	733.3	732.1
47.5°	690.4	687.6	684.8	682.9	681.8	680.7	679.7	678.6
50°	654.6	652.0	649.3	647.3	645.9	644.4	642.9	641.5
52.5°	618.2	616.0	613.8	611.9	610.5	609.0	607.6	606.2
55°	562.9	560.3	557.7	555.7	554.5	553.3	552.2	551.0
57.5°	508.5	506.2	503.8	501.9	500.6	499.2	497.8	496.4
60°	470.1	467.9	465.8	464.1	462.9	461.7	460.5	459.3
62.5°	433.0	430.9	428.6	427.2	426.4	425.6	424.8	424.0
65°	377.9	375.9	374.0	372.7	372.0	371.3	370.5	369.8
67.5°	323.1	321.5	319.8	318.5	317.4	316.4	315.4	314.4
70°	287.7	286.1	284.4	283.0	281.8	280.6	279.4	278.1
72.5°	251.9	250.4	248.9	247.9	247.2	246.6	246.1	245.4
75°	200.3	199.1	197.9	196.9	196.2	195.5	194.8	194.1
77.5°	152.1	151.3	150.5	150.1	150.1	150.1	150.1	150.1
80°	121.4	121.1	120.9	120.7	120.7	120.7	120.7	120.7
82.5°	93.4	92.9	92.5	92.2	92.0	91.8	91.7	91.4
85°	52.9	52.4	52.0	51.7	51.7	51.7	51.7	51.7
87.5°	24.7	24.8	24.8	24.9	25.0	25.0	25.2	25.3
90°	30.8	31.8	33.0	33.7	34.2	34.8	35.3	35.8
92.5°	47.5	48.4	49.3	49.5	49.2	48.9	48.6	48.2
95°	90.5	91.6	92.6	93.2	93.2	93.2	93.2	93.2
97.5°	140.8	142.0	143.2	143.8	143.7	143.5	143.5	143.4
100°	177.2	178.0	178.8	179.4	180.0	180.5	181.0	181.6
102.5°	219.3	220.1	220.9	221.2	221.1	220.9	220.9	220.8
105°	281.9	281.9	281.9	282.2	282.7	283.3	283.8	284.3
107.5°	349.8	350.6	351.5	351.7	351.4	351.1	350.8	350.5
110°	395.1	396.2	397.3	397.5	397.0	396.5	395.9	395.4



TEST NUMBER: P332209-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	440.5	441.7	443.0	443.6	443.5	443.4	443.3	443.1
115°	509.5	509.7	509.9	509.9	509.7	509.5	509.1	508.9
117.5°	579.0	579.0	578.9	578.5	577.7	577.0	576.3	575.5
120°	625.4	625.2	624.9	624.5	624.0	623.4	622.9	622.3
122.5°	672.3	671.7	671.0	670.3	669.6	668.8	668.0	667.3
125°	742.1	741.0	740.0	738.9	737.8	736.8	735.7	734.7
127.5°	811.0	809.5	808.0	806.7	805.5	804.2	803.0	801.8
130°	856.7	855.7	854.7	853.2	851.4	849.5	847.6	845.7
132.5°	901.3	900.0	898.7	897.4	896.0	894.5	893.0	891.6
135°	967.9	966.8	965.7	965.0	964.4	963.8	963.4	962.8
137.5°	1033.0	1031.9	1030.8	1029.7	1028.6	1027.7	1026.7	1025.6
140°	1075.8	1075.5	1075.2	1074.2	1072.3	1070.5	1068.6	1066.8
142.5°	1115.9	1115.6	1115.4	1114.5	1113.1	1111.7	1110.2	1108.8
145°	1174.9	1174.6	1174.4	1173.7	1172.7	1171.6	1170.5	1169.5
147.5°	1230.7	1230.7	1230.7	1229.9	1228.3	1226.7	1225.0	1223.4
150°	1265.0	1265.0	1265.0	1264.2	1262.7	1261.1	1259.5	1257.9
152.5°	1296.5	1296.9	1297.4	1296.9	1295.5	1294.1	1292.7	1291.3
155°	1342.4	1343.5	1344.6	1344.2	1342.3	1340.5	1338.6	1336.7
157.5°	1382.0	1383.1	1384.2	1384.0	1382.5	1381.0	1379.5	1378.1
160°	1406.3	1407.6	1408.9	1409.1	1408.0	1406.9	1405.9	1404.8
162.5°	1429.2	1430.5	1431.9	1431.7	1430.0	1428.3	1426.6	1424.9
165°	1458.2	1459.8	1461.3	1461.3	1459.4	1457.5	1455.6	1453.8
167.5°	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4
170°	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8
172.5°	1504.6	1506.3	1507.9	1507.8	1505.9	1504.1	1502.2	1500.4
175°	1515.5	1517.1	1518.7	1518.5	1516.7	1514.8	1513.0	1511.2
177.5°	1520.4	1521.6	1522.9	1522.8	1521.3	1519.8	1518.4	1516.9
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7

(END OF REPORT)