

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331828-935

Luminaire Tested: **S122RDIW-S865D435U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331828-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S865D435U935-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3890.9 lumens  
Efficiency: N/A  
Efficacy: 84.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331828-935

CATALOG NUMBER: S122RDIW-S865D435U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331828-935

CATALOG NUMBER: S122RDIW-S865D435U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				
1	102	98	94	91	96	93	89	86	82	80	78	73	71	69	64	63	62	58				
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49				
3	86	77	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46	42				
4	79	68	60	54	74	65	58	52	58	53	48	52	48	44	46	43	40	37				
5	73	61	53	47	68	58	51	45	52	47	42	47	42	39	42	38	35	33				
6	67	55	47	41	63	53	45	40	48	42	37	43	38	34	38	35	31	29				
7	62	50	42	37	59	48	41	35	43	37	33	39	34	31	35	31	28	26				
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	23				
9	54	42	35	30	51	40	33	29	37	31	27	33	29	25	30	26	23	21				
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20384	20384	20384
5°	20462	20128	20238
10°	20305	19799	19630
15°	20072	19211	18658
20°	19747	18374	17452
25°	19417	17423	16283
30°	18957	16444	14783
35°	18510	15380	13466
40°	18061	14280	11944
45°	17532	13045	10565
50°	16990	11796	9211
55°	16434	10452	7910
60°	15791	9038	6568
65°	15060	7595	5979
70°	14186	6255	5500
75°	13119	5702	5128
80°	11576	5095	4677
85°	9114	4020	4020



TEST NUMBER: P331828-935

CATALOG NUMBER: S122RDIW-S865D435U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.2	3.0
10°-20°	324.5	8.3
20°-30°	455.6	11.7
30°-40°	496.8	12.8
40°-50°	456.8	11.7
50°-60°	358.8	9.2
60°-70°	233.9	6.0
70°-80°	120.6	3.1
80°-90°	33.1	0.9
90°-100°	29.3	0.8
100°-110°	91.0	2.3
110°-120°	155.5	4.0
120°-130°	204.5	5.3
130°-140°	229.5	5.9
140°-150°	225.0	5.8
150°-160°	188.8	4.9
160°-170°	125.2	3.2
170°-180°	43.8	1.1
0°-30°	898.3	23.1
0°-40°	1395.1	35.9
0°-60°	2210.7	56.8
0°-90°	2598.4	66.8
90°-120°	275.7	7.1
90°-150°	934.8	24.0
90°-180°	1293.0	33.2
0°-180°	3890.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1262	1262	1262	1262	1262	
5°	1262	1256	1242	1251	1249	120
15°	1201	1187	1149	1128	1116	338
25°	1090	1051	978	933	914	501
35°	939	878	780	711	683	587
45°	768	689	571	493	463	593
55°	584	493	371	305	281	521
65°	394	301	199	162	156	391
75°	210	133	91	84	82	223
85°	49	26	22	22	22	58
90°	0	5	14	13	13	3
95°	20	24	25	25	24	23
105°	84	85	86	87	87	89
115°	156	158	158	157	156	154
125°	227	230	229	228	228	203
135°	294	298	299	298	297	227
145°	356	359	362	362	360	223
155°	408	409	410	412	411	188
165°	444	443	443	446	444	125
175°	462	460	460	462	460	44
180°	462	462	462	462	462	



TEST NUMBER: P331828-935

CATALOG NUMBER: S122RDIW-S865D435U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1267.0	1266.0	1265.0	1263.9	1263.0	1261.4	1259.1	1256.9	1254.6	1252.4	1254.5
5°	1262.5	1261.2	1259.9	1258.6	1257.4	1255.1	1251.8	1248.5	1245.2	1241.9	1244.1
7.5°	1249.4	1247.8	1246.3	1244.7	1243.1	1240.4	1236.6	1232.7	1228.8	1224.9	1225.6
10°	1238.5	1236.7	1234.9	1233.1	1231.3	1228.0	1222.9	1217.8	1212.7	1207.6	1206.9
12.5°	1224.8	1222.5	1220.4	1218.2	1216.0	1211.7	1205.1	1198.7	1192.1	1185.7	1184.3
15°	1200.8	1198.0	1195.2	1192.4	1189.6	1183.9	1175.3	1166.7	1158.0	1149.3	1144.5
17.5°	1171.3	1167.0	1162.8	1158.5	1154.3	1146.6	1135.5	1124.4	1113.4	1102.3	1096.6
20°	1149.3	1144.3	1139.2	1134.1	1129.0	1120.2	1107.4	1094.8	1082.1	1069.4	1063.0
22.5°	1125.6	1119.9	1114.2	1108.5	1102.9	1092.9	1078.5	1064.2	1049.9	1035.5	1027.3
25°	1089.9	1081.8	1073.7	1065.6	1057.5	1045.0	1028.2	1011.5	994.7	978.0	967.6
27.5°	1047.0	1038.1	1029.3	1020.5	1011.7	997.8	978.9	960.0	941.1	922.2	910.1
30°	1016.8	1007.2	997.6	987.9	978.3	963.3	943.0	922.6	902.3	882.0	869.1
32.5°	987.6	976.3	965.0	953.7	942.5	926.5	905.8	885.0	864.4	843.6	828.9
35°	939.1	926.2	913.3	900.3	887.3	869.7	847.3	825.0	802.7	780.3	764.3
37.5°	890.7	876.5	862.3	848.0	833.8	814.8	791.0	767.2	743.4	719.5	701.9
40°	856.9	841.6	826.4	811.1	795.9	776.0	751.4	726.8	702.1	677.5	659.4
42.5°	822.2	806.1	790.1	774.0	757.9	737.2	711.8	686.3	660.9	635.4	616.8
45°	767.8	750.7	733.7	716.7	699.7	677.9	651.3	624.6	597.9	571.3	553.2
47.5°	714.7	696.7	678.7	660.6	642.7	619.8	592.4	564.8	537.3	509.8	491.9
50°	676.4	658.3	640.3	622.2	604.2	581.3	553.4	525.4	497.5	469.6	452.0
52.5°	638.9	620.0	601.2	582.4	563.5	540.4	513.2	485.8	458.5	431.2	414.2
55°	583.8	564.0	544.2	524.4	504.6	481.0	453.6	426.1	398.7	371.3	356.1
57.5°	527.4	507.0	486.7	466.4	446.2	422.8	396.4	370.1	343.7	317.4	303.4
60°	489.0	468.6	448.4	428.1	407.8	384.5	358.3	332.2	306.1	279.9	267.0
62.5°	451.5	431.2	410.9	390.5	370.2	347.7	322.7	297.8	272.9	247.9	235.6
65°	394.2	373.6	353.0	332.4	311.9	290.2	267.3	244.5	221.6	198.8	190.2
67.5°	338.9	318.5	298.1	277.6	257.2	236.7	216.2	195.6	175.0	154.5	150.5
70°	300.5	280.7	260.9	241.1	221.3	202.6	185.1	167.6	150.1	132.5	130.0
72.5°	263.9	245.0	225.9	207.0	188.0	171.4	157.4	143.3	129.2	115.2	113.0
75°	210.3	192.4	174.7	156.9	139.1	126.0	117.3	108.7	100.0	91.4	89.6
77.5°	157.5	141.8	126.2	110.6	95.1	85.2	81.0	76.9	72.8	68.5	67.5
80°	124.5	111.6	98.7	85.7	72.8	65.0	62.4	59.9	57.3	54.8	53.8
82.5°	94.4	84.3	74.1	64.1	54.0	48.0	46.3	44.6	42.9	41.2	40.6
85°	49.2	43.8	38.5	33.1	27.8	24.8	24.0	23.2	22.5	21.7	21.7
87.5°	14.7	13.3	11.9	10.4	9.0	8.5	8.9	9.3	9.6	10.1	9.8
90°	0.4	1.5	2.5	3.5	4.6	6.0	7.9	9.8	11.7	13.7	13.5
92.5°	7.0	7.7	8.4	9.2	10.0	10.6	11.0	11.5	12.0	12.4	12.4
95°	20.3	21.2	22.0	22.9	23.8	24.3	24.5	24.6	24.8	25.0	25.0
97.5°	37.0	37.8	38.6	39.3	40.1	40.6	41.0	41.3	41.7	41.9	41.9
100°	49.5	50.2	50.9	51.7	52.3	52.8	53.0	53.3	53.6	53.8	53.8
102.5°	62.7	63.2	63.7	64.3	64.8	65.3	65.6	66.0	66.3	66.6	66.7
105°	83.9	84.1	84.4	84.6	84.9	85.2	85.3	85.5	85.7	85.8	86.0
107.5°	105.2	105.6	106.0	106.4	106.8	106.9	106.9	106.9	106.9	106.9	107.0
110°	119.0	119.5	120.0	120.5	121.1	121.3	121.3	121.3	121.3	121.3	121.3



TEST NUMBER: P331828-935

CATALOG NUMBER: S122RDIW-S865D435U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.0	134.5	135.0	135.5	136.0	136.3	136.2	136.1	136.0	136.0	135.8
115°	156.0	156.5	157.0	157.6	158.1	158.3	158.1	157.9	157.7	157.6	157.5
117.5°	178.1	178.7	179.4	180.1	180.8	180.9	180.5	179.9	179.4	179.0	178.7
120°	192.7	193.4	194.1	194.8	195.4	195.4	194.8	194.1	193.4	192.7	192.7
122.5°	206.1	207.0	207.8	208.6	209.5	209.7	209.1	208.6	208.2	207.7	207.5
125°	227.0	227.8	228.6	229.4	230.1	230.4	230.1	229.9	229.6	229.4	229.1
127.5°	247.4	248.4	249.3	250.4	251.3	251.7	251.4	251.1	250.7	250.5	250.1
130°	260.2	261.3	262.4	263.6	264.7	265.2	265.0	264.8	264.7	264.5	264.3
132.5°	274.6	275.4	276.4	277.3	278.2	278.7	278.7	278.8	278.8	278.8	278.4
135°	293.8	294.7	295.7	296.6	297.6	298.1	298.3	298.4	298.6	298.8	298.7
137.5°	313.9	314.7	315.5	316.2	317.0	317.5	317.8	318.1	318.2	318.5	318.4
140°	326.1	326.9	327.7	328.5	329.2	329.8	330.3	330.7	331.1	331.6	331.6
142.5°	338.6	339.4	340.2	341.0	341.7	342.2	342.5	342.9	343.1	343.5	343.5
145°	356.5	357.1	357.7	358.3	359.0	359.6	360.1	360.6	361.1	361.6	361.7
147.5°	372.6	373.2	374.0	374.7	375.5	376.0	376.3	376.7	377.0	377.4	377.5
150°	383.5	384.0	384.5	385.0	385.6	386.0	386.3	386.7	387.0	387.4	387.6
152.5°	393.1	393.6	394.2	394.7	395.2	395.7	396.1	396.5	396.9	397.4	397.7
155°	407.6	407.9	408.1	408.5	408.7	409.0	409.2	409.5	409.7	410.0	410.4
157.5°	420.1	420.3	420.4	420.6	420.8	420.9	421.0	421.2	421.4	421.5	422.1
160°	427.6	427.7	427.9	428.1	428.3	428.3	428.4	428.5	428.6	428.7	429.2
162.5°	434.4	434.5	434.5	434.5	434.5	434.6	434.7	434.8	434.9	435.0	435.5
165°	443.5	443.4	443.3	443.2	443.2	443.2	443.2	443.2	443.2	443.2	443.8
167.5°	451.2	450.9	450.6	450.4	450.1	450.0	450.0	450.0	450.0	450.0	450.6
170°	455.2	455.0	454.7	454.4	454.2	454.0	453.9	453.8	453.7	453.7	454.3
172.5°	458.1	457.8	457.5	457.3	457.0	456.8	456.8	456.7	456.6	456.5	457.1
175°	461.5	461.2	461.0	460.7	460.5	460.2	460.0	459.9	459.7	459.5	460.1
177.5°	462.9	462.7	462.4	462.3	462.0	461.8	461.8	461.6	461.4	461.3	461.8
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331828-935

CATALOG NUMBER: S122RDIW-S865D435U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1256.5	1258.5	1260.5	1261.4	1260.9	1260.5	1260.2	1259.7
5°	1246.5	1248.7	1251.0	1251.8	1251.0	1250.3	1249.5	1248.7
7.5°	1226.3	1226.9	1227.6	1227.3	1226.0	1224.7	1223.3	1222.0
10°	1206.1	1205.3	1204.5	1203.4	1201.9	1200.4	1198.9	1197.3
12.5°	1182.9	1181.6	1180.2	1178.3	1175.7	1173.2	1170.6	1168.1
15°	1139.7	1134.9	1130.1	1126.4	1123.9	1121.3	1118.8	1116.2
17.5°	1090.8	1085.0	1079.3	1074.3	1069.9	1065.6	1061.2	1056.8
20°	1056.7	1050.3	1044.0	1038.0	1032.4	1026.8	1021.2	1015.7
22.5°	1019.3	1011.1	1002.9	996.7	992.6	988.3	984.2	980.1
25°	957.2	946.8	936.3	929.2	925.4	921.6	917.8	914.0
27.5°	897.9	885.8	873.7	864.6	858.6	852.5	846.4	840.4
30°	856.1	843.2	830.2	820.3	813.5	806.6	799.8	792.9
32.5°	814.1	799.3	784.5	773.9	767.5	761.0	754.6	748.1
35°	748.3	732.4	716.4	705.6	700.0	694.4	688.8	683.2
37.5°	684.3	666.7	649.1	637.1	630.7	624.2	617.9	611.5
40°	641.4	623.5	605.4	593.1	586.5	579.9	573.3	566.7
42.5°	598.2	579.5	560.9	548.4	542.0	535.6	529.2	522.8
45°	535.2	517.2	499.1	487.1	481.0	474.9	468.8	462.7
47.5°	473.9	456.0	438.1	426.4	420.9	415.3	409.7	404.2
50°	434.5	417.0	399.5	388.1	382.7	377.4	372.0	366.7
52.5°	397.4	380.5	363.5	352.7	347.7	342.8	337.9	332.9
55°	340.9	325.6	310.4	300.3	295.5	290.7	285.9	281.0
57.5°	289.5	275.5	261.6	252.5	248.5	244.4	240.3	236.3
60°	254.0	241.1	228.1	219.6	215.5	211.5	207.4	203.4
62.5°	223.3	210.9	198.5	191.1	188.7	186.3	183.8	181.4
65°	181.5	172.9	164.3	159.5	158.8	158.1	157.3	156.5
67.5°	146.5	142.6	138.6	136.2	135.4	134.6	133.8	133.0
70°	127.4	124.9	122.3	120.6	119.6	118.6	117.5	116.5
72.5°	110.9	108.7	106.6	105.3	104.6	104.0	103.4	102.8
75°	87.8	86.1	84.3	83.3	83.0	82.7	82.5	82.2
77.5°	66.6	65.5	64.5	63.8	63.4	62.9	62.6	62.2
80°	52.8	51.8	50.8	50.3	50.3	50.3	50.3	50.3
82.5°	40.0	39.3	38.7	38.4	38.4	38.4	38.4	38.4
85°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7
87.5°	9.6	9.3	9.1	9.0	9.0	9.0	9.0	9.0
90°	13.3	13.2	13.0	12.9	13.0	13.1	13.2	13.3
92.5°	12.5	12.5	12.6	12.6	12.6	12.6	12.7	12.7
95°	25.0	25.0	25.0	24.9	24.7	24.5	24.4	24.2
97.5°	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9
100°	53.8	53.8	53.8	53.8	53.7	53.6	53.6	53.5
102.5°	66.7	66.8	66.9	66.9	66.8	66.7	66.6	66.6
105°	86.2	86.4	86.5	86.6	86.6	86.6	86.6	86.6
107.5°	107.1	107.2	107.3	107.1	106.7	106.2	105.9	105.5
110°	121.3	121.3	121.3	121.1	120.9	120.6	120.4	120.1





TEST NUMBER: P331828-935

CATALOG NUMBER: S122RDIW-S865D435U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	135.6	135.3	135.2	134.9	134.7	134.6	134.4	134.2
115°	157.4	157.3	157.2	157.0	156.8	156.5	156.3	156.0
117.5°	178.6	178.3	178.1	177.9	177.6	177.4	177.1	176.8
120°	192.7	192.7	192.7	192.6	192.3	192.1	191.8	191.6
122.5°	207.2	207.1	206.8	206.6	206.5	206.3	206.0	205.9
125°	228.9	228.6	228.3	228.2	228.1	228.0	227.9	227.8
127.5°	249.8	249.5	249.2	248.9	248.6	248.3	248.1	247.8
130°	264.2	264.0	263.8	263.6	263.2	262.9	262.5	262.2
132.5°	278.1	277.7	277.3	277.0	276.7	276.4	276.1	275.9
135°	298.6	298.5	298.4	298.3	298.0	297.7	297.5	297.2
137.5°	318.3	318.2	318.2	318.0	317.6	317.3	316.9	316.6
140°	331.6	331.6	331.6	331.4	331.1	330.7	330.4	330.0
142.5°	343.5	343.6	343.7	343.5	343.2	342.9	342.5	342.2
145°	361.8	361.9	362.0	361.8	361.4	361.1	360.8	360.4
147.5°	377.7	378.0	378.2	378.1	377.7	377.4	377.0	376.8
150°	387.9	388.1	388.4	388.4	388.1	387.9	387.6	387.4
152.5°	398.0	398.3	398.6	398.6	398.3	398.0	397.7	397.4
155°	410.9	411.3	411.7	411.8	411.6	411.3	411.0	410.8
157.5°	422.7	423.3	423.9	424.0	423.5	423.1	422.8	422.3
160°	429.7	430.2	430.8	430.8	430.5	430.2	429.8	429.5
162.5°	436.1	436.7	437.3	437.4	437.0	436.5	436.1	435.8
165°	444.4	445.0	445.6	445.7	445.2	444.8	444.4	443.9
167.5°	451.2	451.8	452.4	452.5	451.9	451.5	451.1	450.6
170°	454.9	455.5	456.1	456.2	455.6	455.1	454.6	454.1
172.5°	457.7	458.3	458.9	458.9	458.4	457.9	457.4	456.8
175°	460.7	461.3	461.9	462.0	461.5	461.0	460.5	459.9
177.5°	462.2	462.5	463.0	463.0	462.5	462.2	461.8	461.3
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3

(END OF REPORT)