

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332184-927

Luminaire Tested: **S123DIW-S1000D460U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332184-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1000D460U927-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 460 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4725.1 lumens  
Efficiency: N/A  
Efficacy: 102.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332184-927

CATALOG NUMBER: S123DIW-S1000D460U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332184-927

CATALOG NUMBER: S123DIW-S1000D460U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	74	74	74	69
1	102	97	93	90	96	92	89	85	82	80	77	73	71	69	65	63	62	58
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	55	52	49
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	47	44	41
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	45	41	38	35
5	71	59	51	45	67	56	49	43	51	44	40	46	40	36	41	37	33	31
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27
7	61	48	40	34	57	46	38	33	42	35	31	38	32	28	34	29	26	24
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	27	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13497	13497	13497
5°	13560	13374	13467
10°	13470	13258	13340
15°	13312	13108	13133
20°	13128	12893	12906
25°	12883	12638	12613
30°	12609	12356	12261
35°	12326	12056	11901
40°	12029	11726	11545
45°	11702	11423	11144
50°	11375	11050	10742
55°	10946	10663	10340
60°	10514	10213	9888
65°	10132	9722	9419
70°	9567	9161	8752
75°	8742	8430	8072
80°	7885	7550	7482
85°	6928	6657	6385



TEST NUMBER: P332184-927

CATALOG NUMBER: S123DIW-S1000D460U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.1	2.5
10°-20°	333.5	7.1
20°-30°	492.7	10.4
30°-40°	575.5	12.2
40°-50°	578.6	12.2
50°-60°	508.2	10.8
60°-70°	378.6	8.0
70°-80°	215.7	4.6
80°-90°	63.3	1.3
90°-100°	17.4	0.4
100°-110°	83.0	1.8
110°-120°	199.4	4.2
120°-130°	253.9	5.4
130°-140°	271.3	5.7
140°-150°	253.7	5.4
150°-160°	204.6	4.3
160°-170°	132.1	2.8
170°-180°	45.5	1.0
0°-30°	944.3	20.0
0°-40°	1519.8	32.2
0°-60°	2606.6	55.2
0°-90°	3264.2	69.1
90°-120°	299.8	6.3
90°-150°	1078.7	22.8
90°-180°	1461.0	30.9
0°-180°	4725.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1254	1254	1254	1254	1254	
5°	1255	1249	1238	1248	1246	119
15°	1195	1190	1176	1184	1178	337
25°	1085	1078	1064	1065	1062	499
35°	938	931	918	911	906	587
45°	769	764	750	738	732	593
55°	583	582	568	557	551	522
65°	398	392	382	373	370	392
75°	210	206	203	197	194	225
85°	56	54	54	52	52	62
90°	0	4	9	10	11	4
95°	22	8	11	13	14	27
105°	106	108	78	18	16	112
115°	199	201	204	208	209	196
125°	280	283	285	285	286	250
135°	349	351	353	354	353	269
145°	403	405	406	407	407	252
155°	444	443	444	445	443	204
165°	468	467	467	469	467	132
175°	479	477	478	480	477	46
180°	479	479	479	479	479	



TEST NUMBER: P332184-927

CATALOG NUMBER: S123DIW-S1000D460U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1258.2	1257.5	1256.7	1255.9	1255.2	1253.7	1251.6	1249.5	1247.4	1245.3	1247.2
5°	1255.0	1253.8	1252.6	1251.4	1250.2	1248.3	1245.7	1243.0	1240.4	1237.8	1240.2
7.5°	1242.7	1241.5	1240.3	1239.1	1237.9	1236.0	1233.3	1230.5	1227.8	1225.0	1227.2
10°	1232.4	1231.2	1229.9	1228.8	1227.6	1225.4	1222.3	1219.2	1216.1	1213.0	1215.1
12.5°	1218.5	1217.6	1216.6	1215.5	1214.6	1212.6	1209.7	1206.7	1203.8	1200.9	1202.5
15°	1194.6	1193.7	1192.7	1191.8	1190.8	1188.7	1185.7	1182.6	1179.4	1176.3	1178.2
17.5°	1166.8	1165.5	1164.3	1163.1	1161.8	1159.7	1156.5	1153.4	1150.3	1147.2	1148.5
20°	1146.1	1144.7	1143.3	1141.8	1140.3	1138.0	1135.0	1131.9	1128.8	1125.6	1126.6
22.5°	1122.8	1121.4	1120.0	1118.5	1117.1	1114.8	1111.7	1108.6	1105.5	1102.3	1103.1
25°	1084.7	1083.2	1081.8	1080.4	1078.9	1076.7	1073.5	1070.4	1067.3	1064.1	1064.4
27.5°	1043.9	1042.5	1041.1	1039.7	1038.3	1035.9	1032.6	1029.3	1025.9	1022.5	1022.7
30°	1014.5	1013.4	1012.2	1011.0	1009.8	1007.5	1004.2	1000.8	997.4	994.1	994.1
32.5°	985.2	983.7	982.1	980.5	978.9	976.8	974.2	971.7	969.1	966.5	965.1
35°	938.0	936.6	935.2	933.7	932.2	930.0	926.9	923.8	920.7	917.5	916.1
37.5°	889.7	887.9	886.1	884.2	882.4	880.0	876.8	873.6	870.4	867.3	865.5
40°	856.1	854.6	853.2	851.8	850.3	848.0	844.5	841.2	837.9	834.5	832.6
42.5°	822.4	820.8	819.2	817.5	815.9	813.4	810.1	806.8	803.4	800.0	798.1
45°	768.7	767.8	766.8	765.9	764.9	762.9	759.8	756.6	753.5	750.4	747.6
47.5°	715.5	714.1	712.7	711.3	710.0	707.7	704.9	702.0	699.0	696.1	693.2
50°	679.3	678.0	676.8	675.7	674.5	672.3	669.2	666.1	663.0	659.9	657.2
52.5°	641.3	640.5	639.7	638.9	638.0	636.0	632.7	629.4	626.1	622.7	620.5
55°	583.3	583.0	582.8	582.6	582.3	580.7	577.6	574.4	571.3	568.2	565.5
57.5°	528.1	527.3	526.5	525.7	524.8	523.2	520.7	518.2	515.7	513.3	510.9
60°	488.4	488.1	487.9	487.7	487.4	485.9	483.0	480.1	477.3	474.4	472.2
62.5°	453.0	452.4	451.8	451.1	450.6	448.9	445.9	443.1	440.2	437.3	435.1
65°	397.8	396.6	395.5	394.3	393.1	391.3	388.9	386.5	384.0	381.7	379.8
67.5°	339.5	338.3	337.3	336.3	335.2	333.7	331.9	330.1	328.3	326.5	324.8
70°	304.0	302.6	301.2	299.8	298.3	296.8	295.4	294.0	292.6	291.1	289.5
72.5°	267.0	265.9	264.8	263.8	262.8	261.4	259.8	258.2	256.5	254.8	253.4
75°	210.2	209.3	208.3	207.4	206.4	205.6	204.9	204.1	203.4	202.7	201.5
77.5°	160.0	159.5	158.9	158.4	157.9	157.2	156.4	155.5	154.6	153.8	153.0
80°	127.2	126.5	125.8	125.1	124.4	123.7	123.3	122.8	122.3	121.8	121.6
82.5°	95.3	95.1	95.1	94.9	94.7	94.6	94.5	94.4	94.3	94.3	93.8
85°	56.1	55.6	55.1	54.7	54.2	53.9	53.9	53.9	53.9	53.9	53.4
87.5°	22.5	22.1	21.6	21.2	20.8	20.6	20.7	20.7	20.7	20.7	20.5
90°	0.3	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.5	8.6	8.9
92.5°	6.7	6.4	6.2	5.9	5.7	6.0	6.8	7.5	8.3	9.1	9.6
95°	21.7	18.5	15.2	12.0	8.7	7.5	8.4	9.3	10.1	11.0	11.6
97.5°	43.6	42.1	40.7	39.3	37.8	34.2	28.5	22.8	17.2	11.5	12.1
100°	60.1	61.7	63.3	64.9	66.5	61.1	48.8	36.4	24.1	11.7	12.4
102.5°	78.9	80.1	81.2	82.4	83.5	77.3	63.8	50.4	36.9	23.4	21.5
105°	106.1	106.9	107.8	108.7	109.6	106.4	99.3	92.2	85.1	78.0	63.9
107.5°	134.7	135.4	136.1	136.7	137.4	138.4	139.5	140.6	141.7	142.8	132.6
110°	153.8	154.4	155.0	155.7	156.3	157.0	157.9	158.8	159.6	160.5	157.9



TEST NUMBER: P332184-927

CATALOG NUMBER: S123DIW-S1000D460U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.0	172.5	173.1	173.6	174.3	175.0	175.9	176.7	177.6	178.5	178.5
115°	198.9	199.4	199.9	200.3	200.8	201.5	202.2	202.9	203.6	204.3	205.1
117.5°	225.1	225.7	226.2	226.8	227.4	227.9	228.2	228.6	229.0	229.3	230.0
120°	241.3	242.0	242.7	243.4	244.2	244.6	244.9	245.1	245.3	245.6	246.2
122.5°	257.9	258.4	259.0	259.6	260.2	260.6	260.9	261.2	261.5	261.8	262.2
125°	280.4	281.1	281.7	282.3	283.0	283.4	283.8	284.1	284.4	284.7	284.9
127.5°	302.4	303.0	303.6	304.3	304.9	305.4	305.8	306.2	306.6	307.0	307.2
130°	316.1	316.7	317.3	318.0	318.6	319.1	319.4	319.7	320.0	320.3	320.6
132.5°	329.2	329.8	330.4	331.1	331.7	332.1	332.4	332.6	332.9	333.1	333.4
135°	349.1	349.6	350.1	350.5	351.0	351.4	351.7	352.0	352.4	352.7	352.9
137.5°	366.2	366.9	367.4	368.0	368.6	369.0	369.2	369.4	369.6	369.7	370.1
140°	377.6	378.1	378.6	379.1	379.5	379.9	380.1	380.3	380.6	380.8	381.1
142.5°	388.2	388.6	389.1	389.6	390.1	390.4	390.6	390.9	391.1	391.3	391.6
145°	402.9	403.5	404.0	404.6	405.1	405.4	405.6	405.8	405.9	406.1	406.2
147.5°	416.8	417.2	417.5	417.9	418.2	418.5	418.7	418.8	419.0	419.1	419.3
150°	425.3	425.6	425.8	426.0	426.3	426.4	426.6	426.7	426.9	427.1	427.2
152.5°	433.0	433.1	433.2	433.3	433.5	433.6	433.6	433.7	433.8	434.0	434.2
155°	443.8	443.6	443.5	443.4	443.2	443.1	443.2	443.3	443.4	443.5	443.9
157.5°	452.3	452.2	452.2	452.2	452.2	452.1	452.0	451.9	451.9	451.8	452.3
160°	457.3	457.2	457.2	457.1	457.0	456.9	456.9	456.8	456.7	456.6	457.1
162.5°	462.2	462.0	461.8	461.6	461.4	461.2	461.1	461.1	461.0	460.9	461.4
165°	468.0	467.8	467.5	467.3	467.1	466.9	466.8	466.8	466.7	466.6	467.2
167.5°	472.6	472.3	472.0	471.7	471.3	471.2	471.2	471.2	471.2	471.2	471.8
170°	475.2	474.8	474.5	474.2	473.9	473.7	473.7	473.7	473.7	473.7	474.4
172.5°	476.8	476.5	476.1	475.7	475.3	475.2	475.2	475.3	475.4	475.4	476.0
175°	479.0	478.6	478.2	477.8	477.4	477.3	477.4	477.4	477.5	477.6	478.2
177.5°	479.6	479.3	479.0	478.6	478.3	478.2	478.3	478.3	478.4	478.5	479.0
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332184-927

CATALOG NUMBER: S123DIW-S1000D460U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1249.1	1251.1	1253.0	1253.9	1253.6	1253.5	1253.2	1253.1
5°	1242.5	1244.9	1247.4	1248.3	1247.8	1247.4	1246.9	1246.4
7.5°	1229.4	1231.5	1233.7	1234.6	1234.3	1234.1	1233.7	1233.4
10°	1217.3	1219.4	1221.6	1222.4	1221.9	1221.5	1221.0	1220.5
12.5°	1204.0	1205.6	1207.2	1207.8	1207.6	1207.3	1207.0	1206.7
15°	1180.1	1182.0	1184.0	1184.2	1182.8	1181.3	1179.9	1178.5
17.5°	1149.9	1151.2	1152.5	1152.9	1152.5	1151.9	1151.4	1150.9
20°	1127.5	1128.5	1129.5	1129.6	1128.9	1128.1	1127.4	1126.7
22.5°	1103.9	1104.6	1105.4	1105.3	1104.5	1103.5	1102.6	1101.7
25°	1064.6	1064.9	1065.2	1064.9	1064.1	1063.4	1062.7	1062.0
27.5°	1022.9	1023.1	1023.3	1022.9	1022.1	1021.1	1020.3	1019.3
30°	994.1	994.1	994.1	993.2	991.6	989.9	988.2	986.5
32.5°	963.8	962.5	961.2	960.0	959.1	958.1	957.3	956.3
35°	914.7	913.2	911.8	910.5	909.3	908.1	906.9	905.7
37.5°	863.9	862.1	860.4	859.1	858.4	857.6	856.8	856.1
40°	830.7	828.8	826.9	825.4	824.4	823.5	822.5	821.6
42.5°	796.1	794.2	792.3	790.9	790.0	789.0	788.1	787.1
45°	744.7	741.8	738.9	736.9	735.7	734.5	733.3	732.1
47.5°	690.4	687.6	684.8	682.9	681.8	680.7	679.7	678.6
50°	654.6	652.0	649.3	647.3	645.9	644.4	642.9	641.5
52.5°	618.2	616.0	613.8	611.9	610.5	609.0	607.6	606.2
55°	562.9	560.3	557.7	555.7	554.5	553.3	552.2	551.0
57.5°	508.5	506.2	503.8	501.9	500.6	499.2	497.8	496.4
60°	470.1	467.9	465.8	464.1	462.9	461.7	460.5	459.3
62.5°	433.0	430.9	428.6	427.2	426.4	425.6	424.8	424.0
65°	377.9	375.9	374.0	372.7	372.0	371.3	370.5	369.8
67.5°	323.1	321.5	319.8	318.5	317.4	316.4	315.4	314.4
70°	287.7	286.1	284.4	283.0	281.8	280.6	279.4	278.1
72.5°	251.9	250.4	248.9	247.9	247.2	246.6	246.1	245.4
75°	200.3	199.1	197.9	196.9	196.2	195.5	194.8	194.1
77.5°	152.1	151.3	150.5	150.1	150.1	150.1	150.1	150.1
80°	121.4	121.1	120.9	120.7	120.7	120.7	120.7	120.7
82.5°	93.4	92.9	92.5	92.2	92.0	91.8	91.7	91.4
85°	52.9	52.4	52.0	51.7	51.7	51.7	51.7	51.7
87.5°	20.4	20.3	20.2	20.1	20.1	20.2	20.2	20.3
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.1	10.6	11.2	11.4	11.6	11.6	11.7	11.8
95°	12.1	12.7	13.2	13.5	13.5	13.5	13.5	13.5
97.5°	12.8	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.0	13.6	14.3	14.7	14.7	14.8	14.9	15.0
102.5°	19.5	17.5	15.6	14.7	14.8	15.0	15.1	15.2
105°	49.9	36.0	21.9	15.1	15.2	15.4	15.5	15.7
107.5°	122.3	112.1	101.8	91.4	80.8	70.3	59.7	49.2
110°	155.3	152.7	150.0	143.1	131.8	120.5	109.2	97.9





TEST NUMBER: P332184-927

CATALOG NUMBER: S123DIW-S1000D460U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	178.6	178.6	178.6	177.4	175.1	172.7	170.3	167.9
115°	205.9	206.7	207.5	208.0	208.3	208.7	209.0	209.3
117.5°	230.6	231.2	231.9	232.2	232.3	232.3	232.4	232.5
120°	246.8	247.5	248.1	248.4	248.4	248.4	248.4	248.4
122.5°	262.7	263.2	263.6	263.8	263.9	264.0	264.0	264.1
125°	285.0	285.2	285.3	285.5	285.7	285.8	286.0	286.1
127.5°	307.4	307.7	307.9	308.0	307.8	307.7	307.5	307.4
130°	320.9	321.2	321.5	321.6	321.5	321.3	321.2	321.0
132.5°	333.7	334.1	334.4	334.5	334.2	334.0	333.7	333.6
135°	353.2	353.4	353.6	353.6	353.4	353.2	352.9	352.7
137.5°	370.5	370.8	371.2	371.4	371.2	371.1	370.9	370.7
140°	381.4	381.8	382.1	382.1	382.0	381.8	381.7	381.5
142.5°	391.9	392.1	392.4	392.4	392.1	392.0	391.7	391.5
145°	406.4	406.5	406.7	406.8	406.8	406.8	406.8	406.8
147.5°	419.5	419.6	419.8	419.6	419.3	418.9	418.6	418.2
150°	427.4	427.5	427.7	427.7	427.5	427.2	427.0	426.7
152.5°	434.5	434.7	435.1	435.0	434.7	434.3	434.0	433.6
155°	444.3	444.7	445.0	445.0	444.5	444.0	443.5	443.1
157.5°	452.7	453.2	453.7	453.6	453.0	452.4	451.8	451.1
160°	457.6	458.0	458.5	458.5	458.0	457.4	456.9	456.3
162.5°	462.0	462.6	463.0	463.1	462.6	462.1	461.6	461.1
165°	467.9	468.5	469.1	469.1	468.6	468.1	467.5	467.0
167.5°	472.5	473.0	473.6	473.6	473.0	472.5	471.8	471.2
170°	475.0	475.6	476.3	476.3	475.6	475.0	474.4	473.7
172.5°	476.7	477.3	477.9	477.9	477.2	476.5	475.9	475.2
175°	478.7	479.3	479.8	479.8	479.2	478.6	477.9	477.3
177.5°	479.5	480.0	480.5	480.5	479.8	479.2	478.6	477.9
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0

(END OF REPORT)