

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332187-927

Luminaire Tested: **S123DIW-S1000D755U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332187-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D755U927-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5434.3 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	60	58	57	53
2	92	85	79	73	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	67	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	42	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	35	38	35	32	29
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25	23
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11976	11976	11976	11976
5°	14282	12028	10659	12028
10°	17876	11967	9627	11967
15°	21926	11870	8963	11870
20°	26120	11720	8534	11720
25°	27736	11537	8438	11537
30°	23772	11404	8483	11404
35°	16533	11213	8571	11213
40°	12452	10991	8545	10991
45°	10339	10660	8435	10660
50°	9262	9984	8359	9984
55°	8659	9256	8255	9256
60°	8122	8495	8170	8495
65°	7636	7743	7908	7743
70°	7160	6889	7531	6889
75°	6413	6030	6904	6030
80°	5610	4947	5945	4947
85°	4397	3594	3989	3594



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.6	2.0
10°-20°	351.5	6.5
20°-30°	589.8	10.9
30°-40°	667.9	12.3
40°-50°	598.9	11.0
50°-60°	483.3	8.9
60°-70°	336.8	6.2
70°-80°	177.0	3.3
80°-90°	45.5	0.8
90°-100°	48.8	0.9
100°-110°	145.9	2.7
110°-120°	248.2	4.6
120°-130°	326.5	6.0
130°-140°	367.0	6.8
140°-150°	360.7	6.6
150°-160°	303.7	5.6
160°-170°	202.2	3.7
170°-180°	70.8	1.3
0°-30°	1050.9	19.3
0°-40°	1718.8	31.6
0°-60°	2801.1	51.5
0°-90°	3360.4	61.8
90°-120°	442.9	8.2
90°-150°	1497.2	27.6
90°-180°	2074.0	38.2
0°-180°	5434.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1113	1113	1113	1113	1113	
5°	1322	1113	986	1113	1322	137
15°	1968	1065	804	1065	1968	568
25°	2335	971	710	971	2335	1024
35°	1258	853	652	853	1258	817
45°	679	700	554	700	679	537
55°	461	493	440	493	461	414
65°	300	304	310	304	300	298
75°	154	145	166	145	154	165
85°	36	29	32	29	36	43
90°	18	1	18	1	18	10
95°	46	35	46	35	46	47
105°	140	132	140	132	140	149
115°	250	250	250	250	250	248
125°	362	366	362	366	362	323
135°	474	474	474	474	474	364
145°	576	576	576	576	576	359
155°	658	659	658	659	658	303
165°	716	718	716	718	716	202
175°	744	747	744	747	744	71
180°	748	748	748	748	748	



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1180.7	1180.0	1177.7	1179.5	1176.1	1171.3	1170.8	1166.6	1154.1	1153.2	1149.8
5°	1321.8	1317.5	1316.9	1316.4	1308.8	1298.6	1279.2	1277.6	1251.7	1238.8	1223.1
7.5°	1504.4	1506.7	1498.8	1491.9	1468.9	1453.7	1432.8	1406.2	1374.4	1342.2	1320.7
10°	1635.5	1653.4	1631.3	1616.1	1602.1	1575.7	1545.0	1506.7	1468.5	1423.7	1389.7
12.5°	1776.2	1784.9	1780.4	1766.2	1744.5	1704.2	1649.8	1607.7	1572.4	1497.9	1467.8
15°	1967.6	2000.5	1979.5	1930.9	1932.1	1893.8	1822.6	1744.5	1703.0	1637.7	1548.8
17.5°	2171.6	2175.7	2166.8	2126.3	2099.4	2046.8	1981.1	1906.1	1822.1	1743.1	1648.8
20°	2280.3	2277.0	2258.2	2237.1	2190.8	2149.8	2078.1	1994.6	1886.7	1809.1	1706.2
22.5°	2340.7	2335.3	2326.3	2308.7	2270.2	2226.2	2161.8	2070.4	1967.9	1860.9	1741.9
25°	2335.3	2342.2	2343.4	2338.5	2325.1	2298.6	2247.9	2175.2	2072.7	1935.3	1811.3
27.5°	2123.9	2133.9	2162.7	2188.2	2216.8	2245.9	2242.0	2205.9	2130.1	2011.4	1859.8
30°	1912.6	1891.1	1944.4	2011.8	2057.6	2138.5	2183.8	2186.5	2143.9	2042.0	1894.3
32.5°	1619.4	1643.1	1666.7	1749.6	1849.7	1940.5	2030.7	2103.2	2111.6	2043.8	1914.5
35°	1258.2	1287.9	1330.9	1374.1	1481.9	1574.6	1733.1	1871.1	1981.1	1995.7	1916.4
37.5°	1013.9	1028.6	1055.8	1099.1	1169.6	1279.5	1402.2	1576.6	1735.9	1854.4	1859.6
40°	886.2	890.6	921.3	954.2	1011.3	1101.8	1212.4	1366.5	1557.4	1722.9	1791.9
42.5°	790.5	799.9	813.0	844.6	890.1	958.2	1061.0	1188.4	1363.3	1553.8	1688.8
45°	679.2	690.0	698.1	719.1	751.5	797.3	869.0	985.4	1118.6	1315.3	1497.0
47.5°	605.7	606.6	612.6	628.4	650.5	684.8	735.5	810.3	932.6	1092.2	1278.7
50°	553.1	561.7	563.9	576.2	593.5	618.9	660.9	724.5	824.8	965.0	1136.4
52.5°	516.0	518.6	524.7	533.6	548.7	568.4	604.8	654.7	733.3	852.8	1010.4
55°	461.4	461.4	467.4	474.4	483.0	500.8	525.1	561.7	621.5	714.3	844.7
57.5°	411.0	413.7	417.9	420.0	427.4	439.1	459.4	487.2	531.9	603.2	706.9
60°	377.3	382.2	381.7	386.0	392.4	401.6	418.8	441.5	481.4	538.5	625.9
62.5°	348.0	347.7	347.6	352.8	359.3	368.0	379.2	398.8	432.7	483.3	557.7
65°	299.8	298.7	302.5	305.6	307.8	314.3	322.9	340.2	362.8	400.5	458.2
67.5°	256.8	253.7	255.7	256.8	260.5	265.5	273.6	284.3	302.3	332.6	376.0
70°	227.5	224.8	224.3	225.3	228.5	232.3	238.3	248.5	265.2	289.5	321.3
72.5°	197.3	195.4	195.4	197.7	199.2	201.7	205.9	215.3	228.5	246.8	276.5
75°	154.2	154.2	154.2	154.7	156.3	158.5	161.7	166.6	176.8	189.7	209.7
77.5°	115.6	115.5	114.8	114.7	117.1	118.0	118.8	123.3	129.0	137.8	152.3
80°	90.5	87.9	89.0	90.5	91.7	92.2	93.8	94.9	99.7	104.6	114.8
82.5°	67.3	65.0	65.2	67.7	67.9	68.4	70.1	71.6	73.4	77.9	83.3
85°	35.6	35.6	36.1	36.1	36.7	36.1	37.7	38.3	38.3	41.0	44.2
87.5°	16.5	15.5	15.9	16.3	15.8	16.2	16.5	16.8	17.2	17.5	17.6
90°	17.7	17.3	17.1	16.9	16.6	16.2	15.7	15.1	14.7	14.1	12.4
92.5°	23.8	23.9	24.1	24.2	24.4	24.2	23.8	23.4	23.0	22.6	21.6
95°	45.9	45.9	45.9	45.9	45.9	45.6	45.1	44.5	44.0	43.5	42.5
97.5°	70.6	70.6	70.7	70.7	70.7	70.5	69.9	69.3	68.7	68.1	67.3
100°	89.4	89.1	88.9	88.6	88.3	88.0	87.6	87.2	86.8	86.4	85.8
102.5°	108.7	108.7	108.8	108.8	108.8	108.7	108.3	107.9	107.5	107.1	106.2
105°	140.0	139.7	139.4	139.2	138.9	138.8	138.8	138.8	138.8	138.8	137.6
107.5°	172.5	172.7	172.9	173.0	173.2	173.0	172.6	172.1	171.7	171.3	170.9
110°	194.6	194.9	195.1	195.4	195.7	195.5	195.0	194.5	194.0	193.5	193.2



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.2	218.2	218.2	218.3	218.3	218.1	217.5	216.8	216.2	215.6	215.5
115°	250.5	250.6	250.7	250.9	251.0	251.0	250.9	250.7	250.6	250.5	250.7
117.5°	283.3	283.7	284.0	284.4	284.8	284.9	284.9	285.0	285.0	285.0	285.4
120°	306.3	306.6	306.9	307.1	307.4	307.6	307.7	307.8	308.0	308.1	308.8
122.5°	328.4	328.8	329.2	329.5	329.9	330.3	330.6	331.0	331.3	331.6	332.0
125°	361.6	362.1	362.7	363.2	363.7	364.2	364.7	365.3	365.8	366.3	366.5
127.5°	394.7	395.3	395.9	396.5	397.0	397.8	398.5	399.2	399.9	400.7	400.9
130°	416.3	417.2	418.1	419.1	419.9	420.6	421.2	421.8	422.2	422.8	423.2
132.5°	438.9	439.6	440.3	441.0	441.7	442.4	443.0	443.6	444.3	444.9	445.1
135°	473.9	474.2	474.4	474.7	475.0	475.4	475.9	476.4	476.9	477.4	477.6
137.5°	504.9	505.3	505.8	506.4	506.8	507.4	507.9	508.4	509.0	509.5	509.2
140°	525.1	526.0	526.9	527.8	528.7	529.3	529.4	529.5	529.7	529.8	529.7
142.5°	545.7	546.4	547.2	547.9	548.6	549.0	549.1	549.3	549.4	549.5	549.3
145°	575.7	576.2	576.7	577.2	577.7	578.1	578.2	578.3	578.5	578.6	578.2
147.5°	602.2	603.0	603.8	604.6	605.4	605.8	605.8	605.8	605.8	605.8	605.4
150°	619.2	620.0	620.8	621.5	622.3	622.7	622.7	622.7	622.7	622.7	622.4
152.5°	635.6	636.3	637.0	637.6	638.3	638.6	638.3	638.2	637.9	637.7	637.5
155°	658.0	658.9	659.8	660.7	661.6	661.8	661.3	660.8	660.3	659.7	659.6
157.5°	678.3	679.1	679.8	680.5	681.2	681.4	680.8	680.2	679.7	679.1	679.1
160°	691.5	692.0	692.5	693.1	693.6	693.5	692.8	692.2	691.6	690.9	690.9
162.5°	701.3	702.2	703.1	703.9	704.7	704.8	704.2	703.5	702.8	702.2	702.1
165°	715.6	716.5	717.4	718.4	719.2	719.3	718.5	717.7	716.9	716.1	716.1
167.5°	727.7	728.5	729.3	730.2	730.9	730.9	730.2	729.3	728.5	727.7	727.6
170°	733.8	734.7	735.6	736.6	737.4	737.4	736.6	735.6	734.7	733.8	733.8
172.5°	738.6	739.4	740.4	741.2	742.2	742.2	741.4	740.6	739.8	738.9	738.9
175°	743.8	744.7	745.6	746.6	747.5	747.5	746.7	746.0	745.2	744.4	744.4
177.5°	746.6	747.3	748.1	748.8	749.6	749.6	749.0	748.4	747.7	747.1	747.1
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1147.2	1143.7	1140.3	1134.2	1129.0	1121.7	1119.5	1117.0	1109.2	1102.3	1097.1
5°	1217.2	1204.3	1185.4	1168.2	1154.1	1135.3	1124.5	1113.2	1097.0	1082.4	1070.6
7.5°	1290.5	1265.1	1235.8	1204.0	1174.6	1146.1	1123.1	1102.6	1080.0	1058.5	1041.8
10°	1348.8	1312.1	1271.1	1226.9	1189.2	1152.5	1121.8	1094.9	1065.7	1040.4	1019.4
12.5°	1415.2	1360.8	1304.3	1250.6	1206.0	1155.2	1117.9	1083.6	1050.7	1020.2	996.6
15°	1493.7	1424.7	1358.0	1284.0	1216.2	1152.5	1108.3	1065.2	1026.9	995.7	965.5
17.5°	1565.4	1487.2	1399.1	1309.3	1227.3	1151.9	1090.0	1041.2	993.4	955.1	925.0
20°	1605.9	1516.9	1417.2	1324.0	1233.4	1149.3	1081.4	1023.2	971.4	931.0	897.0
22.5°	1640.8	1536.8	1433.6	1333.9	1233.0	1142.4	1065.4	1005.5	949.4	909.8	873.7
25°	1677.0	1552.5	1449.1	1332.1	1219.4	1125.6	1039.3	971.4	915.4	869.0	831.8
27.5°	1708.1	1551.5	1428.6	1302.8	1198.0	1104.0	1011.9	939.1	879.6	829.2	791.5
30°	1728.8	1553.6	1407.5	1283.0	1177.3	1080.3	990.8	917.5	855.0	803.7	768.2
32.5°	1741.8	1552.3	1388.1	1255.4	1144.5	1058.8	968.0	892.1	827.8	777.4	743.1
35°	1749.3	1542.9	1354.7	1198.3	1091.6	1008.1	932.1	853.3	786.0	739.1	700.3
37.5°	1734.2	1522.9	1315.9	1143.4	1026.5	944.2	880.3	813.3	748.8	697.1	663.7
40°	1710.5	1510.0	1285.7	1104.5	981.7	902.4	848.0	782.2	718.6	669.6	638.3
42.5°	1665.2	1483.6	1252.5	1061.4	935.1	855.8	805.7	750.8	690.5	644.5	613.2
45°	1554.7	1426.4	1202.7	996.7	866.3	784.3	740.1	700.3	645.8	601.0	574.1
47.5°	1401.4	1340.2	1130.7	928.5	794.5	715.7	669.7	637.6	597.9	561.7	535.8
50°	1294.8	1269.6	1081.9	881.9	746.6	669.6	625.3	596.2	567.7	531.6	507.8
52.5°	1172.0	1187.6	1025.0	833.6	697.9	622.1	580.5	557.4	531.4	501.8	481.1
55°	998.9	1055.5	926.7	752.6	625.3	553.1	513.7	493.2	478.2	456.1	438.2
57.5°	836.9	908.9	820.4	669.0	554.1	491.7	454.0	431.7	422.0	410.4	396.4
60°	740.7	811.8	744.5	612.9	506.2	446.9	413.4	394.6	384.9	376.8	365.0
62.5°	654.9	726.9	670.3	556.0	459.1	404.2	375.1	356.6	349.1	344.9	334.8
65°	536.9	598.9	561.2	467.4	391.9	343.4	317.0	304.0	297.1	295.4	288.9
67.5°	437.0	484.2	456.7	387.7	328.3	286.4	264.0	252.9	247.6	247.0	242.2
70°	371.5	415.7	394.6	332.1	280.8	248.0	228.5	218.9	215.6	215.1	212.4
72.5°	320.5	351.3	334.6	282.5	242.9	213.0	198.8	188.7	185.0	185.8	183.9
75°	237.2	260.4	250.6	214.5	182.8	163.3	151.5	145.0	141.8	143.4	141.2
77.5°	170.6	185.4	176.6	151.6	132.0	118.0	109.2	105.2	102.3	102.2	101.2
80°	128.8	137.4	132.6	117.5	101.3	89.5	82.5	79.8	78.2	77.6	77.1
82.5°	91.7	99.1	93.4	83.0	72.0	64.9	60.9	57.4	56.2	56.5	55.9
85°	46.3	49.0	46.9	40.4	36.1	32.9	30.7	29.1	28.0	28.6	27.5
87.5°	18.1	18.2	16.6	14.5	13.4	11.9	11.6	10.5	9.9	10.1	10.0
90°	10.7	9.0	7.3	5.8	4.5	3.2	1.9	0.6	1.9	3.2	4.5
92.5°	20.7	19.6	18.7	17.7	16.9	16.0	15.1	14.3	15.1	16.0	16.9
95°	41.4	40.4	39.3	38.3	37.5	36.5	35.6	34.7	35.6	36.5	37.5
97.5°	66.5	65.8	65.0	64.3	63.7	63.0	62.3	61.6	62.3	63.0	63.7
100°	85.2	84.4	83.8	83.1	82.3	81.5	80.7	79.9	80.7	81.5	82.3
102.5°	105.4	104.6	103.7	103.0	102.5	102.1	101.6	101.2	101.6	102.1	102.5
105°	136.4	135.2	134.0	133.3	133.1	132.8	132.5	132.3	132.5	132.8	133.1
107.5°	170.4	169.9	169.4	169.1	169.0	168.8	168.7	168.5	168.7	168.8	169.0
110°	192.9	192.7	192.4	192.1	191.9	191.6	191.4	191.1	191.4	191.6	191.9



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	215.5	215.4	215.3	215.2	215.1	214.9	214.8	214.6	214.8	214.9	215.1
115°	251.0	251.3	251.5	251.4	251.0	250.6	250.3	249.9	250.3	250.6	251.0
117.5°	285.7	286.1	286.5	286.5	286.2	285.9	285.7	285.4	285.7	285.9	286.2
120°	309.4	310.1	310.7	310.7	309.9	309.1	308.3	307.5	308.3	309.1	309.9
122.5°	332.3	332.6	333.0	332.9	332.3	331.7	331.1	330.6	331.1	331.7	332.3
125°	366.9	367.1	367.3	367.3	366.9	366.5	366.1	365.8	366.1	366.5	366.9
127.5°	401.2	401.6	401.8	401.6	400.7	399.9	399.0	398.2	399.0	399.9	400.7
130°	423.6	424.0	424.4	424.0	422.9	421.9	420.9	419.9	420.9	421.9	422.9
132.5°	445.4	445.8	446.0	445.7	444.6	443.5	442.5	441.5	442.5	443.5	444.6
135°	477.7	477.8	478.0	477.6	476.9	476.1	475.3	474.5	475.3	476.1	476.9
137.5°	508.9	508.5	508.2	507.7	507.1	506.4	505.7	505.1	505.7	506.4	507.1
140°	529.5	529.4	529.3	528.9	528.2	527.6	526.9	526.2	526.9	527.6	528.2
142.5°	549.1	548.8	548.6	548.1	547.5	546.8	546.2	545.6	546.2	546.8	547.5
145°	577.8	577.4	577.0	576.7	576.4	576.2	575.9	575.7	575.9	576.2	576.4
147.5°	605.0	604.7	604.3	603.9	603.4	602.9	602.5	602.0	602.5	602.9	603.4
150°	622.2	621.9	621.6	621.4	621.2	620.8	620.6	620.4	620.6	620.8	621.2
152.5°	637.4	637.2	637.1	636.8	636.5	636.1	635.7	635.4	635.7	636.1	636.5
155°	659.5	659.3	659.2	659.2	659.2	659.2	659.2	659.2	659.2	659.2	659.2
157.5°	678.9	678.8	678.7	678.7	678.9	679.1	679.2	679.4	679.2	679.1	678.9
160°	690.9	690.9	690.9	691.0	691.3	691.6	691.8	692.1	691.8	691.6	691.3
162.5°	702.0	701.9	701.8	701.9	702.3	702.6	703.0	703.4	703.0	702.6	702.3
165°	716.1	716.1	716.1	716.4	716.8	717.2	717.6	718.0	717.6	717.2	716.8
167.5°	727.5	727.4	727.3	727.5	728.0	728.6	729.0	729.6	729.0	728.6	728.0
170°	733.8	733.8	733.8	734.0	734.6	735.1	735.6	736.2	735.6	735.1	734.6
172.5°	738.9	738.9	738.9	739.3	739.7	740.3	740.8	741.3	740.8	740.3	739.7
175°	744.4	744.4	744.4	744.7	745.2	745.7	746.2	746.7	746.2	745.7	745.2
177.5°	747.1	747.1	747.1	747.3	747.7	748.1	748.5	749.0	748.5	748.1	747.7
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1094.1	1091.1	1086.8	1080.3	1075.1	1066.9	1066.9	1068.3	1068.3	1067.8	1066.9
5°	1060.9	1052.8	1043.1	1031.8	1019.9	1008.1	1005.9	1001.6	998.4	996.2	993.5
7.5°	1025.9	1011.5	997.4	981.5	967.1	955.1	946.8	939.9	935.5	930.7	927.3
10°	1002.1	984.4	967.7	950.9	932.6	918.1	908.9	902.4	897.5	893.3	891.1
12.5°	974.1	953.7	935.3	919.4	899.4	884.4	875.7	872.7	867.0	857.9	853.1
15°	933.1	914.3	892.2	867.9	858.2	839.9	829.7	824.8	821.6	814.5	812.4
17.5°	898.1	873.4	848.6	830.5	812.5	797.6	791.9	785.8	781.6	775.9	774.1
20°	870.1	848.0	825.3	805.9	787.0	770.9	766.0	761.7	757.4	754.7	752.6
22.5°	841.6	819.5	800.7	782.6	762.5	751.9	746.6	741.9	738.9	737.0	734.8
25°	801.6	782.2	761.2	745.0	728.8	721.8	718.6	715.9	713.8	711.1	710.5
27.5°	765.8	744.7	727.6	712.6	700.9	695.1	692.0	690.6	691.1	692.1	692.7
30°	739.1	719.7	705.7	692.7	681.9	676.5	676.0	676.0	678.2	678.7	679.8
32.5°	714.5	698.5	684.5	672.0	663.8	660.1	662.2	662.2	663.9	665.4	667.3
35°	678.7	664.6	653.9	643.1	636.1	637.7	638.8	639.8	642.5	645.8	648.0
37.5°	644.5	632.3	621.2	612.7	609.5	612.4	615.0	617.3	620.4	622.8	625.0
40°	620.0	610.8	600.0	592.5	593.5	595.2	597.3	600.0	602.7	604.3	606.5
42.5°	597.1	587.5	579.3	573.1	574.6	576.6	577.9	579.3	582.4	585.3	586.6
45°	562.3	554.7	547.2	543.4	544.5	545.6	546.6	548.3	551.0	553.1	553.7
47.5°	523.1	517.8	512.8	509.1	510.8	510.4	511.8	515.2	516.1	517.4	520.4
50°	498.1	493.2	487.4	486.2	486.2	486.2	486.8	491.1	491.1	493.2	495.4
52.5°	470.5	467.4	463.6	461.7	460.8	460.8	463.0	465.2	466.1	469.1	471.3
55°	429.7	426.4	423.2	421.5	420.5	421.5	425.9	426.9	429.7	431.3	432.8
57.5°	387.1	384.6	382.0	381.1	380.9	382.3	384.7	387.9	388.6	393.6	396.0
60°	359.0	355.2	353.1	353.1	352.0	356.9	355.8	361.2	362.3	365.5	369.2
62.5°	330.1	325.0	324.2	324.2	325.7	327.1	328.6	331.0	333.8	337.9	340.8
65°	283.5	280.8	284.6	284.1	283.0	286.2	286.2	288.9	292.2	296.0	301.9
67.5°	239.5	238.1	238.4	238.4	240.0	241.9	243.4	245.7	249.6	253.6	257.5
70°	209.7	211.4	208.7	210.8	212.4	212.9	214.0	217.2	221.6	224.3	228.5
72.5°	180.8	180.7	181.0	181.9	183.5	184.5	185.5	189.3	193.9	196.2	199.7
75°	139.1	138.6	140.1	140.1	142.8	143.9	145.0	146.6	150.9	154.2	156.9
77.5°	101.6	102.2	101.9	103.7	103.0	103.1	106.5	108.1	108.6	114.9	116.4
80°	76.5	77.6	78.2	78.7	79.2	78.2	81.9	83.6	83.6	87.3	90.0
82.5°	55.0	55.6	57.0	57.6	57.7	58.8	59.1	60.3	61.6	63.2	66.7
85°	27.5	29.1	29.6	29.1	29.6	28.6	30.2	30.7	31.3	31.3	31.3
87.5°	9.8	10.5	10.5	11.2	11.1	11.9	12.0	11.2	11.3	12.8	11.1
90°	5.8	7.3	9.0	10.7	12.4	14.1	14.7	15.1	15.7	16.2	16.6
92.5°	17.7	18.7	19.6	20.7	21.6	22.6	23.0	23.4	23.8	24.2	24.4
95°	38.3	39.3	40.4	41.4	42.5	43.5	44.0	44.5	45.1	45.6	45.9
97.5°	64.3	65.0	65.8	66.5	67.3	68.1	68.7	69.3	69.9	70.5	70.7
100°	83.1	83.8	84.4	85.2	85.8	86.4	86.8	87.2	87.6	88.0	88.3
102.5°	103.0	103.7	104.6	105.4	106.2	107.1	107.5	107.9	108.3	108.7	108.8
105°	133.3	134.0	135.2	136.4	137.6	138.8	138.8	138.8	138.8	138.8	138.9
107.5°	169.1	169.4	169.9	170.4	170.9	171.3	171.7	172.1	172.6	173.0	173.2
110°	192.1	192.4	192.7	192.9	193.2	193.5	194.0	194.5	195.0	195.5	195.7



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	215.2	215.3	215.4	215.5	215.5	215.6	216.2	216.8	217.5	218.1	218.3
115°	251.4	251.5	251.3	251.0	250.7	250.5	250.6	250.7	250.9	251.0	251.0
117.5°	286.5	286.5	286.1	285.7	285.4	285.0	285.0	285.0	284.9	284.9	284.8
120°	310.7	310.7	310.1	309.4	308.8	308.1	308.0	307.8	307.7	307.6	307.4
122.5°	332.9	333.0	332.6	332.3	332.0	331.6	331.3	331.0	330.6	330.3	329.9
125°	367.3	367.3	367.1	366.9	366.5	366.3	365.8	365.3	364.7	364.2	363.7
127.5°	401.6	401.8	401.6	401.2	400.9	400.7	399.9	399.2	398.5	397.8	397.0
130°	424.0	424.4	424.0	423.6	423.2	422.8	422.2	421.8	421.2	420.6	419.9
132.5°	445.7	446.0	445.8	445.4	445.1	444.9	444.3	443.6	443.0	442.4	441.7
135°	477.6	478.0	477.8	477.7	477.6	477.4	476.9	476.4	475.9	475.4	475.0
137.5°	507.7	508.2	508.5	508.9	509.2	509.5	509.0	508.4	507.9	507.4	506.8
140°	528.9	529.3	529.4	529.5	529.7	529.8	529.7	529.5	529.4	529.3	528.7
142.5°	548.1	548.6	548.8	549.1	549.3	549.5	549.4	549.3	549.1	549.0	548.6
145°	576.7	577.0	577.4	577.8	578.2	578.6	578.5	578.3	578.2	578.1	577.7
147.5°	603.9	604.3	604.7	605.0	605.4	605.8	605.8	605.8	605.8	605.8	605.4
150°	621.4	621.6	621.9	622.2	622.4	622.7	622.7	622.7	622.7	622.7	622.3
152.5°	636.8	637.1	637.2	637.4	637.5	637.7	637.9	638.2	638.3	638.6	638.3
155°	659.2	659.2	659.3	659.5	659.6	659.7	660.3	660.8	661.3	661.8	661.6
157.5°	678.7	678.7	678.8	678.9	679.1	679.1	679.7	680.2	680.8	681.4	681.2
160°	691.0	690.9	690.9	690.9	690.9	690.9	691.6	692.2	692.8	693.5	693.6
162.5°	701.9	701.8	701.9	702.0	702.1	702.2	702.8	703.5	704.2	704.8	704.7
165°	716.4	716.1	716.1	716.1	716.1	716.1	716.9	717.7	718.5	719.3	719.2
167.5°	727.5	727.3	727.4	727.5	727.6	727.7	728.5	729.3	730.2	730.9	730.9
170°	734.0	733.8	733.8	733.8	733.8	733.8	734.7	735.6	736.6	737.4	737.4
172.5°	739.3	738.9	738.9	738.9	738.9	738.9	739.8	740.6	741.4	742.2	742.2
175°	744.7	744.4	744.4	744.4	744.4	744.4	745.2	746.0	746.7	747.5	747.5
177.5°	747.3	747.1	747.1	747.1	747.1	747.1	747.7	748.4	749.0	749.6	749.6
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1063.9	1063.5	1066.5	1064.4	1066.5	1063.5	1063.9	1066.9	1067.8	1068.3	1068.3
5°	990.3	991.9	986.5	986.5	986.5	991.9	990.3	993.5	996.2	998.4	1001.6
7.5°	924.7	922.3	922.6	919.6	922.6	922.3	924.7	927.3	930.7	935.5	939.9
10°	884.6	881.4	880.3	880.8	880.3	881.4	884.6	891.1	893.3	897.5	902.4
12.5°	851.4	850.8	843.7	843.8	843.7	850.8	851.4	853.1	857.9	867.0	872.7
15°	812.4	802.2	801.1	804.3	801.1	802.2	812.4	812.4	814.5	821.6	824.8
17.5°	773.2	767.9	768.2	766.6	768.2	767.9	773.2	774.1	775.9	781.6	785.8
20°	752.6	749.3	748.8	745.0	748.8	749.3	752.6	752.6	754.7	757.4	761.7
22.5°	733.6	732.5	732.8	728.6	732.8	732.5	733.6	734.8	737.0	738.9	741.9
25°	710.0	712.6	710.5	710.5	710.5	712.6	710.0	710.5	711.1	713.8	715.9
27.5°	694.0	693.9	692.8	692.8	692.8	693.9	694.0	692.7	692.1	691.1	690.6
30°	681.9	681.4	682.5	682.5	682.5	681.4	681.9	679.8	678.7	678.2	676.0
32.5°	669.9	670.6	670.8	671.2	670.8	670.6	669.9	667.3	665.4	663.9	662.2
35°	651.2	651.7	653.4	652.3	653.4	651.7	651.2	648.0	645.8	642.5	639.8
37.5°	626.0	628.4	627.9	628.8	627.9	628.4	626.0	625.0	622.8	620.4	617.3
40°	607.0	608.6	608.1	608.1	608.1	608.6	607.0	606.5	604.3	602.7	600.0
42.5°	587.6	588.7	587.4	586.5	587.4	588.7	587.6	586.6	585.3	582.4	579.3
45°	555.8	554.7	556.3	554.1	556.3	554.7	555.8	553.7	553.1	551.0	548.3
47.5°	520.2	521.3	521.7	523.3	521.7	521.3	520.2	520.4	517.4	516.1	515.2
50°	496.5	499.7	499.7	499.2	499.7	499.7	496.5	495.4	493.2	491.1	491.1
52.5°	473.2	474.7	476.9	476.7	476.9	474.7	473.2	471.3	469.1	466.1	465.2
55°	437.2	438.2	439.3	439.9	439.3	438.2	437.2	432.8	431.3	429.7	426.9
57.5°	399.9	399.4	402.0	402.8	402.0	399.4	399.9	396.0	393.6	388.6	387.9
60°	373.6	373.6	377.9	379.5	377.9	373.6	373.6	369.2	365.5	362.3	361.2
62.5°	345.5	347.3	351.6	349.4	351.6	347.3	345.5	340.8	337.9	333.8	331.0
65°	304.6	308.9	308.3	310.5	308.3	308.9	304.6	301.9	296.0	292.2	288.9
67.5°	261.7	264.4	268.3	268.7	268.3	264.4	261.7	257.5	253.6	249.6	245.7
70°	232.9	235.6	237.7	239.3	237.7	235.6	232.9	228.5	224.3	221.6	217.2
72.5°	204.9	206.3	211.4	209.1	211.4	206.3	204.9	199.7	196.2	193.9	189.3
75°	160.7	164.4	167.6	166.0	167.6	164.4	160.7	156.9	154.2	150.9	146.6
77.5°	118.8	122.6	124.1	122.7	124.1	122.6	118.8	116.4	114.9	108.6	108.1
80°	93.8	93.2	96.5	95.9	96.5	93.2	93.8	90.0	87.3	83.6	83.6
82.5°	68.8	68.3	69.8	70.1	69.8	68.3	68.8	66.7	63.2	61.6	60.3
85°	33.4	35.0	32.9	32.3	32.9	35.0	33.4	31.3	31.3	31.3	30.7
87.5°	11.2	11.2	10.8	10.5	10.8	11.2	11.2	11.1	12.8	11.3	11.2
90°	16.9	17.1	17.3	17.7	17.3	17.1	16.9	16.6	16.2	15.7	15.1
92.5°	24.2	24.1	23.9	23.8	23.9	24.1	24.2	24.4	24.2	23.8	23.4
95°	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.6	45.1	44.5
97.5°	70.7	70.7	70.6	70.6	70.6	70.7	70.7	70.7	70.5	69.9	69.3
100°	88.6	88.9	89.1	89.4	89.1	88.9	88.6	88.3	88.0	87.6	87.2
102.5°	108.8	108.8	108.7	108.7	108.7	108.8	108.8	108.8	108.7	108.3	107.9
105°	139.2	139.4	139.7	140.0	139.7	139.4	139.2	138.9	138.8	138.8	138.8
107.5°	173.0	172.9	172.7	172.5	172.7	172.9	173.0	173.2	173.0	172.6	172.1
110°	195.4	195.1	194.9	194.6	194.9	195.1	195.4	195.7	195.5	195.0	194.5



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	218.3	218.2	218.2	218.2	218.2	218.2	218.3	218.3	218.1	217.5	216.8
115°	250.9	250.7	250.6	250.5	250.6	250.7	250.9	251.0	251.0	250.9	250.7
117.5°	284.4	284.0	283.7	283.3	283.7	284.0	284.4	284.8	284.9	284.9	285.0
120°	307.1	306.9	306.6	306.3	306.6	306.9	307.1	307.4	307.6	307.7	307.8
122.5°	329.5	329.2	328.8	328.4	328.8	329.2	329.5	329.9	330.3	330.6	331.0
125°	363.2	362.7	362.1	361.6	362.1	362.7	363.2	363.7	364.2	364.7	365.3
127.5°	396.5	395.9	395.3	394.7	395.3	395.9	396.5	397.0	397.8	398.5	399.2
130°	419.1	418.1	417.2	416.3	417.2	418.1	419.1	419.9	420.6	421.2	421.8
132.5°	441.0	440.3	439.6	438.9	439.6	440.3	441.0	441.7	442.4	443.0	443.6
135°	474.7	474.4	474.2	473.9	474.2	474.4	474.7	475.0	475.4	475.9	476.4
137.5°	506.4	505.8	505.3	504.9	505.3	505.8	506.4	506.8	507.4	507.9	508.4
140°	527.8	526.9	526.0	525.1	526.0	526.9	527.8	528.7	529.3	529.4	529.5
142.5°	547.9	547.2	546.4	545.7	546.4	547.2	547.9	548.6	549.0	549.1	549.3
145°	577.2	576.7	576.2	575.7	576.2	576.7	577.2	577.7	578.1	578.2	578.3
147.5°	604.6	603.8	603.0	602.2	603.0	603.8	604.6	605.4	605.8	605.8	605.8
150°	621.5	620.8	620.0	619.2	620.0	620.8	621.5	622.3	622.7	622.7	622.7
152.5°	637.6	637.0	636.3	635.6	636.3	637.0	637.6	638.3	638.6	638.3	638.2
155°	660.7	659.8	658.9	658.0	658.9	659.8	660.7	661.6	661.8	661.3	660.8
157.5°	680.5	679.8	679.1	678.3	679.1	679.8	680.5	681.2	681.4	680.8	680.2
160°	693.1	692.5	692.0	691.5	692.0	692.5	693.1	693.6	693.5	692.8	692.2
162.5°	703.9	703.1	702.2	701.3	702.2	703.1	703.9	704.7	704.8	704.2	703.5
165°	718.4	717.4	716.5	715.6	716.5	717.4	718.4	719.2	719.3	718.5	717.7
167.5°	730.2	729.3	728.5	727.7	728.5	729.3	730.2	730.9	730.9	730.2	729.3
170°	736.6	735.6	734.7	733.8	734.7	735.6	736.6	737.4	737.4	736.6	735.6
172.5°	741.2	740.4	739.4	738.6	739.4	740.4	741.2	742.2	742.2	741.4	740.6
175°	746.6	745.6	744.7	743.8	744.7	745.6	746.6	747.5	747.5	746.7	746.0
177.5°	748.8	748.1	747.3	746.6	747.3	748.1	748.8	749.6	749.6	749.0	748.4
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1066.9	1066.9	1075.1	1080.3	1086.8	1091.1	1094.1	1097.1	1102.3	1109.2	1117.0
5°	1005.9	1008.1	1019.9	1031.8	1043.1	1052.8	1060.9	1070.6	1082.4	1097.0	1113.2
7.5°	946.8	955.1	967.1	981.5	997.4	1011.5	1025.9	1041.8	1058.5	1080.0	1102.6
10°	908.9	918.1	932.6	950.9	967.7	984.4	1002.1	1019.4	1040.4	1065.7	1094.9
12.5°	875.7	884.4	899.4	919.4	935.3	953.7	974.1	996.6	1020.2	1050.7	1083.6
15°	829.7	839.9	858.2	867.9	892.2	914.3	933.1	965.5	995.7	1026.9	1065.2
17.5°	791.9	797.6	812.5	830.5	848.6	873.4	898.1	925.0	955.1	993.4	1041.2
20°	766.0	770.9	787.0	805.9	825.3	848.0	870.1	897.0	931.0	971.4	1023.2
22.5°	746.6	751.9	762.5	782.6	800.7	819.5	841.6	873.7	909.8	949.4	1005.5
25°	718.6	721.8	728.8	745.0	761.2	782.2	801.6	831.8	869.0	915.4	971.4
27.5°	692.0	695.1	700.9	712.6	727.6	744.7	765.8	791.5	829.2	879.6	939.1
30°	676.0	676.5	681.9	692.7	705.7	719.7	739.1	768.2	803.7	855.0	917.5
32.5°	662.2	660.1	663.8	672.0	684.5	698.5	714.5	743.1	777.4	827.8	892.1
35°	638.8	637.7	636.1	643.1	653.9	664.6	678.7	700.3	739.1	786.0	853.3
37.5°	615.0	612.4	609.5	612.7	621.2	632.3	644.5	663.7	697.1	748.8	813.3
40°	597.3	595.2	593.5	592.5	600.0	610.8	620.0	638.3	669.6	718.6	782.2
42.5°	577.9	576.6	574.6	573.1	579.3	587.5	597.1	613.2	644.5	690.5	750.8
45°	546.6	545.6	544.5	543.4	547.2	554.7	562.3	574.1	601.0	645.8	700.3
47.5°	511.8	510.4	510.8	509.1	512.8	517.8	523.1	535.8	561.7	597.9	637.6
50°	486.8	486.2	486.2	486.2	487.4	493.2	498.1	507.8	531.6	567.7	596.2
52.5°	463.0	460.8	460.8	461.7	463.6	467.4	470.5	481.1	501.8	531.4	557.4
55°	425.9	421.5	420.5	421.5	423.2	426.4	429.7	438.2	456.1	478.2	493.2
57.5°	384.7	382.3	380.9	381.1	382.0	384.6	387.1	396.4	410.4	422.0	431.7
60°	355.8	356.9	352.0	353.1	353.1	355.2	359.0	365.0	376.8	384.9	394.6
62.5°	328.6	327.1	325.7	324.2	324.2	325.0	330.1	334.8	344.9	349.1	356.6
65°	286.2	286.2	283.0	284.1	284.6	280.8	283.5	288.9	295.4	297.1	304.0
67.5°	243.4	241.9	240.0	238.4	238.4	238.1	239.5	242.2	247.0	247.6	252.9
70°	214.0	212.9	212.4	210.8	208.7	211.4	209.7	212.4	215.1	215.6	218.9
72.5°	185.5	184.5	183.5	181.9	181.0	180.7	180.8	183.9	185.8	185.0	188.7
75°	145.0	143.9	142.8	140.1	140.1	138.6	139.1	141.2	143.4	141.8	145.0
77.5°	106.5	103.1	103.0	103.7	101.9	102.2	101.6	101.2	102.2	102.3	105.2
80°	81.9	78.2	79.2	78.7	78.2	77.6	76.5	77.1	77.6	78.2	79.8
82.5°	59.1	58.8	57.7	57.6	57.0	55.6	55.0	55.9	56.5	56.2	57.4
85°	30.2	28.6	29.6	29.1	29.6	29.1	27.5	27.5	28.6	28.0	29.1
87.5°	12.0	11.9	11.1	11.2	10.5	10.5	9.8	10.0	10.1	9.9	10.5
90°	14.7	14.1	12.4	10.7	9.0	7.3	5.8	4.5	3.2	1.9	0.6
92.5°	23.0	22.6	21.6	20.7	19.6	18.7	17.7	16.9	16.0	15.1	14.3
95°	44.0	43.5	42.5	41.4	40.4	39.3	38.3	37.5	36.5	35.6	34.7
97.5°	68.7	68.1	67.3	66.5	65.8	65.0	64.3	63.7	63.0	62.3	61.6
100°	86.8	86.4	85.8	85.2	84.4	83.8	83.1	82.3	81.5	80.7	79.9
102.5°	107.5	107.1	106.2	105.4	104.6	103.7	103.0	102.5	102.1	101.6	101.2
105°	138.8	138.8	137.6	136.4	135.2	134.0	133.3	133.1	132.8	132.5	132.3
107.5°	171.7	171.3	170.9	170.4	169.9	169.4	169.1	169.0	168.8	168.7	168.5
110°	194.0	193.5	193.2	192.9	192.7	192.4	192.1	191.9	191.6	191.4	191.1



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	216.2	215.6	215.5	215.5	215.4	215.3	215.2	215.1	214.9	214.8	214.6
115°	250.6	250.5	250.7	251.0	251.3	251.5	251.4	251.0	250.6	250.3	249.9
117.5°	285.0	285.0	285.4	285.7	286.1	286.5	286.5	286.2	285.9	285.7	285.4
120°	308.0	308.1	308.8	309.4	310.1	310.7	310.7	309.9	309.1	308.3	307.5
122.5°	331.3	331.6	332.0	332.3	332.6	333.0	332.9	332.3	331.7	331.1	330.6
125°	365.8	366.3	366.5	366.9	367.1	367.3	367.3	366.9	366.5	366.1	365.8
127.5°	399.9	400.7	400.9	401.2	401.6	401.8	401.6	400.7	399.9	399.0	398.2
130°	422.2	422.8	423.2	423.6	424.0	424.4	424.0	422.9	421.9	420.9	419.9
132.5°	444.3	444.9	445.1	445.4	445.8	446.0	445.7	444.6	443.5	442.5	441.5
135°	476.9	477.4	477.6	477.7	477.8	478.0	477.6	476.9	476.1	475.3	474.5
137.5°	509.0	509.5	509.2	508.9	508.5	508.2	507.7	507.1	506.4	505.7	505.1
140°	529.7	529.8	529.7	529.5	529.4	529.3	528.9	528.2	527.6	526.9	526.2
142.5°	549.4	549.5	549.3	549.1	548.8	548.6	548.1	547.5	546.8	546.2	545.6
145°	578.5	578.6	578.2	577.8	577.4	577.0	576.7	576.4	576.2	575.9	575.7
147.5°	605.8	605.8	605.4	605.0	604.7	604.3	603.9	603.4	602.9	602.5	602.0
150°	622.7	622.7	622.4	622.2	621.9	621.6	621.4	621.2	620.8	620.6	620.4
152.5°	637.9	637.7	637.5	637.4	637.2	637.1	636.8	636.5	636.1	635.7	635.4
155°	660.3	659.7	659.6	659.5	659.3	659.2	659.2	659.2	659.2	659.2	659.2
157.5°	679.7	679.1	679.1	678.9	678.8	678.7	678.7	678.9	679.1	679.2	679.4
160°	691.6	690.9	690.9	690.9	690.9	690.9	691.0	691.3	691.6	691.8	692.1
162.5°	702.8	702.2	702.1	702.0	701.9	701.8	701.9	702.3	702.6	703.0	703.4
165°	716.9	716.1	716.1	716.1	716.1	716.1	716.4	716.8	717.2	717.6	718.0
167.5°	728.5	727.7	727.6	727.5	727.4	727.3	727.5	728.0	728.6	729.0	729.6
170°	734.7	733.8	733.8	733.8	733.8	733.8	734.0	734.6	735.1	735.6	736.2
172.5°	739.8	738.9	738.9	738.9	738.9	738.9	739.3	739.7	740.3	740.8	741.3
175°	745.2	744.4	744.4	744.4	744.4	744.4	744.7	745.2	745.7	746.2	746.7
177.5°	747.7	747.1	747.1	747.1	747.1	747.1	747.3	747.7	748.1	748.5	749.0
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1119.5	1121.7	1129.0	1134.2	1140.3	1143.7	1147.2	1149.8	1153.2	1154.1	1166.6
5°	1124.5	1135.3	1154.1	1168.2	1185.4	1204.3	1217.2	1223.1	1238.8	1251.7	1277.6
7.5°	1123.1	1146.1	1174.6	1204.0	1235.8	1265.1	1290.5	1320.7	1342.2	1374.4	1406.2
10°	1121.8	1152.5	1189.2	1226.9	1271.1	1312.1	1348.8	1389.7	1423.7	1468.5	1506.7
12.5°	1117.9	1155.2	1206.0	1250.6	1304.3	1360.8	1415.2	1467.8	1497.9	1572.4	1607.7
15°	1108.3	1152.5	1216.2	1284.0	1358.0	1424.7	1493.7	1548.8	1637.7	1703.0	1744.5
17.5°	1090.0	1151.9	1227.3	1309.3	1399.1	1487.2	1565.4	1648.8	1743.1	1822.1	1906.1
20°	1081.4	1149.3	1233.4	1324.0	1417.2	1516.9	1605.9	1706.2	1809.1	1886.7	1994.6
22.5°	1065.4	1142.4	1233.0	1333.9	1433.6	1536.8	1640.8	1741.9	1860.9	1967.9	2070.4
25°	1039.3	1125.6	1219.4	1332.1	1449.1	1552.5	1677.0	1811.3	1935.3	2072.7	2175.2
27.5°	1011.9	1104.0	1198.0	1302.8	1428.6	1551.5	1708.1	1859.8	2011.4	2130.1	2205.9
30°	990.8	1080.3	1177.3	1283.0	1407.5	1553.6	1728.8	1894.3	2042.0	2143.9	2186.5
32.5°	968.0	1058.8	1144.5	1255.4	1388.1	1552.3	1741.8	1914.5	2043.8	2111.6	2103.2
35°	932.1	1008.1	1091.6	1198.3	1354.7	1542.9	1749.3	1916.4	1995.7	1981.1	1871.1
37.5°	880.3	944.2	1026.5	1143.4	1315.9	1522.9	1734.2	1859.6	1854.4	1735.9	1576.6
40°	848.0	902.4	981.7	1104.5	1285.7	1510.0	1710.5	1791.9	1722.9	1557.4	1366.5
42.5°	805.7	855.8	935.1	1061.4	1252.5	1483.6	1665.2	1688.8	1553.8	1363.3	1188.4
45°	740.1	784.3	866.3	996.7	1202.7	1426.4	1554.7	1497.0	1315.3	1118.6	985.4
47.5°	669.7	715.7	794.5	928.5	1130.7	1340.2	1401.4	1278.7	1092.2	932.6	810.3
50°	625.3	669.6	746.6	881.9	1081.9	1269.6	1294.8	1136.4	965.0	824.8	724.5
52.5°	580.5	622.1	697.9	833.6	1025.0	1187.6	1172.0	1010.4	852.8	733.3	654.7
55°	513.7	553.1	625.3	752.6	926.7	1055.5	998.9	844.7	714.3	621.5	561.7
57.5°	454.0	491.7	554.1	669.0	820.4	908.9	836.9	706.9	603.2	531.9	487.2
60°	413.4	446.9	506.2	612.9	744.5	811.8	740.7	625.9	538.5	481.4	441.5
62.5°	375.1	404.2	459.1	556.0	670.3	726.9	654.9	557.7	483.3	432.7	398.8
65°	317.0	343.4	391.9	467.4	561.2	598.9	536.9	458.2	400.5	362.8	340.2
67.5°	264.0	286.4	328.3	387.7	456.7	484.2	437.0	376.0	332.6	302.3	284.3
70°	228.5	248.0	280.8	332.1	394.6	415.7	371.5	321.3	289.5	265.2	248.5
72.5°	198.8	213.0	242.9	282.5	334.6	351.3	320.5	276.5	246.8	228.5	215.3
75°	151.5	163.3	182.8	214.5	250.6	260.4	237.2	209.7	189.7	176.8	166.6
77.5°	109.2	118.0	132.0	151.6	176.6	185.4	170.6	152.3	137.8	129.0	123.3
80°	82.5	89.5	101.3	117.5	132.6	137.4	128.8	114.8	104.6	99.7	94.9
82.5°	60.9	64.9	72.0	83.0	93.4	99.1	91.7	83.3	77.9	73.4	71.6
85°	30.7	32.9	36.1	40.4	46.9	49.0	46.3	44.2	41.0	38.3	38.3
87.5°	11.6	11.9	13.4	14.5	16.6	18.2	18.1	17.6	17.5	17.2	16.8
90°	1.9	3.2	4.5	5.8	7.3	9.0	10.7	12.4	14.1	14.7	15.1
92.5°	15.1	16.0	16.9	17.7	18.7	19.6	20.7	21.6	22.6	23.0	23.4
95°	35.6	36.5	37.5	38.3	39.3	40.4	41.4	42.5	43.5	44.0	44.5
97.5°	62.3	63.0	63.7	64.3	65.0	65.8	66.5	67.3	68.1	68.7	69.3
100°	80.7	81.5	82.3	83.1	83.8	84.4	85.2	85.8	86.4	86.8	87.2
102.5°	101.6	102.1	102.5	103.0	103.7	104.6	105.4	106.2	107.1	107.5	107.9
105°	132.5	132.8	133.1	133.3	134.0	135.2	136.4	137.6	138.8	138.8	138.8
107.5°	168.7	168.8	169.0	169.1	169.4	169.9	170.4	170.9	171.3	171.7	172.1
110°	191.4	191.6	191.9	192.1	192.4	192.7	192.9	193.2	193.5	194.0	194.5



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	214.8	214.9	215.1	215.2	215.3	215.4	215.5	215.5	215.6	216.2	216.8
115°	250.3	250.6	251.0	251.4	251.5	251.3	251.0	250.7	250.5	250.6	250.7
117.5°	285.7	285.9	286.2	286.5	286.5	286.1	285.7	285.4	285.0	285.0	285.0
120°	308.3	309.1	309.9	310.7	310.7	310.1	309.4	308.8	308.1	308.0	307.8
122.5°	331.1	331.7	332.3	332.9	333.0	332.6	332.3	332.0	331.6	331.3	331.0
125°	366.1	366.5	366.9	367.3	367.3	367.1	366.9	366.5	366.3	365.8	365.3
127.5°	399.0	399.9	400.7	401.6	401.8	401.6	401.2	400.9	400.7	399.9	399.2
130°	420.9	421.9	422.9	424.0	424.4	424.0	423.6	423.2	422.8	422.2	421.8
132.5°	442.5	443.5	444.6	445.7	446.0	445.8	445.4	445.1	444.9	444.3	443.6
135°	475.3	476.1	476.9	477.6	478.0	477.8	477.7	477.6	477.4	476.9	476.4
137.5°	505.7	506.4	507.1	507.7	508.2	508.5	508.9	509.2	509.5	509.0	508.4
140°	526.9	527.6	528.2	528.9	529.3	529.4	529.5	529.7	529.8	529.7	529.5
142.5°	546.2	546.8	547.5	548.1	548.6	548.8	549.1	549.3	549.5	549.4	549.3
145°	575.9	576.2	576.4	576.7	577.0	577.4	577.8	578.2	578.6	578.5	578.3
147.5°	602.5	602.9	603.4	603.9	604.3	604.7	605.0	605.4	605.8	605.8	605.8
150°	620.6	620.8	621.2	621.4	621.6	621.9	622.2	622.4	622.7	622.7	622.7
152.5°	635.7	636.1	636.5	636.8	637.1	637.2	637.4	637.5	637.7	637.9	638.2
155°	659.2	659.2	659.2	659.2	659.2	659.3	659.5	659.6	659.7	660.3	660.8
157.5°	679.2	679.1	678.9	678.7	678.7	678.8	678.9	679.1	679.1	679.7	680.2
160°	691.8	691.6	691.3	691.0	690.9	690.9	690.9	690.9	690.9	691.6	692.2
162.5°	703.0	702.6	702.3	701.9	701.8	701.9	702.0	702.1	702.2	702.8	703.5
165°	717.6	717.2	716.8	716.4	716.1	716.1	716.1	716.1	716.1	716.9	717.7
167.5°	729.0	728.6	728.0	727.5	727.3	727.4	727.5	727.6	727.7	728.5	729.3
170°	735.6	735.1	734.6	734.0	733.8	733.8	733.8	733.8	733.8	734.7	735.6
172.5°	740.8	740.3	739.7	739.3	738.9	738.9	738.9	738.9	738.9	739.8	740.6
175°	746.2	745.7	745.2	744.7	744.4	744.4	744.4	744.4	744.4	745.2	746.0
177.5°	748.5	748.1	747.7	747.3	747.1	747.1	747.1	747.1	747.1	747.7	748.4
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1170.8	1171.3	1176.1	1179.5	1177.7	1180.0	1180.7
5°	1279.2	1298.6	1308.8	1316.4	1316.9	1317.5	1321.8
7.5°	1432.8	1453.7	1468.9	1491.9	1498.8	1506.7	1504.4
10°	1545.0	1575.7	1602.1	1616.1	1631.3	1653.4	1635.5
12.5°	1649.8	1704.2	1744.5	1766.2	1780.4	1784.9	1776.2
15°	1822.6	1893.8	1932.1	1930.9	1979.5	2000.5	1967.6
17.5°	1981.1	2046.8	2099.4	2126.3	2166.8	2175.7	2171.6
20°	2078.1	2149.8	2190.8	2237.1	2258.2	2277.0	2280.3
22.5°	2161.8	2226.2	2270.2	2308.7	2326.3	2335.3	2340.7
25°	2247.9	2298.6	2325.1	2338.5	2343.4	2342.2	2335.3
27.5°	2242.0	2245.9	2216.8	2188.2	2162.7	2133.9	2123.9
30°	2183.8	2138.5	2057.6	2011.8	1944.4	1891.1	1912.6
32.5°	2030.7	1940.5	1849.7	1749.6	1666.7	1643.1	1619.4
35°	1733.1	1574.6	1481.9	1374.1	1330.9	1287.9	1258.2
37.5°	1402.2	1279.5	1169.6	1099.1	1055.8	1028.6	1013.9
40°	1212.4	1101.8	1011.3	954.2	921.3	890.6	886.2
42.5°	1061.0	958.2	890.1	844.6	813.0	799.9	790.5
45°	869.0	797.3	751.5	719.1	698.1	690.0	679.2
47.5°	735.5	684.8	650.5	628.4	612.6	606.6	605.7
50°	660.9	618.9	593.5	576.2	563.9	561.7	553.1
52.5°	604.8	568.4	548.7	533.6	524.7	518.6	516.0
55°	525.1	500.8	483.0	474.4	467.4	461.4	461.4
57.5°	459.4	439.1	427.4	420.0	417.9	413.7	411.0
60°	418.8	401.6	392.4	386.0	381.7	382.2	377.3
62.5°	379.2	368.0	359.3	352.8	347.6	347.7	348.0
65°	322.9	314.3	307.8	305.6	302.5	298.7	299.8
67.5°	273.6	265.5	260.5	256.8	255.7	253.7	256.8
70°	238.3	232.3	228.5	225.3	224.3	224.8	227.5
72.5°	205.9	201.7	199.2	197.7	195.4	195.4	197.3
75°	161.7	158.5	156.3	154.7	154.2	154.2	154.2
77.5°	118.8	118.0	117.1	114.7	114.8	115.5	115.6
80°	93.8	92.2	91.7	90.5	89.0	87.9	90.5
82.5°	70.1	68.4	67.9	67.7	65.2	65.0	67.3
85°	37.7	36.1	36.7	36.1	36.1	35.6	35.6
87.5°	16.5	16.2	15.8	16.3	15.9	15.5	16.5
90°	15.7	16.2	16.6	16.9	17.1	17.3	17.7
92.5°	23.8	24.2	24.4	24.2	24.1	23.9	23.8
95°	45.1	45.6	45.9	45.9	45.9	45.9	45.9
97.5°	69.9	70.5	70.7	70.7	70.7	70.6	70.6
100°	87.6	88.0	88.3	88.6	88.9	89.1	89.4
102.5°	108.3	108.7	108.8	108.8	108.8	108.7	108.7
105°	138.8	138.8	138.9	139.2	139.4	139.7	140.0
107.5°	172.6	173.0	173.2	173.0	172.9	172.7	172.5
110°	195.0	195.5	195.7	195.4	195.1	194.9	194.6



TEST NUMBER: P332187-927

CATALOG NUMBER: S123DIW-S1000D755U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	217.5	218.1	218.3	218.3	218.2	218.2	218.2
115°	250.9	251.0	251.0	250.9	250.7	250.6	250.5
117.5°	284.9	284.9	284.8	284.4	284.0	283.7	283.3
120°	307.7	307.6	307.4	307.1	306.9	306.6	306.3
122.5°	330.6	330.3	329.9	329.5	329.2	328.8	328.4
125°	364.7	364.2	363.7	363.2	362.7	362.1	361.6
127.5°	398.5	397.8	397.0	396.5	395.9	395.3	394.7
130°	421.2	420.6	419.9	419.1	418.1	417.2	416.3
132.5°	443.0	442.4	441.7	441.0	440.3	439.6	438.9
135°	475.9	475.4	475.0	474.7	474.4	474.2	473.9
137.5°	507.9	507.4	506.8	506.4	505.8	505.3	504.9
140°	529.4	529.3	528.7	527.8	526.9	526.0	525.1
142.5°	549.1	549.0	548.6	547.9	547.2	546.4	545.7
145°	578.2	578.1	577.7	577.2	576.7	576.2	575.7
147.5°	605.8	605.8	605.4	604.6	603.8	603.0	602.2
150°	622.7	622.7	622.3	621.5	620.8	620.0	619.2
152.5°	638.3	638.6	638.3	637.6	637.0	636.3	635.6
155°	661.3	661.8	661.6	660.7	659.8	658.9	658.0
157.5°	680.8	681.4	681.2	680.5	679.8	679.1	678.3
160°	692.8	693.5	693.6	693.1	692.5	692.0	691.5
162.5°	704.2	704.8	704.7	703.9	703.1	702.2	701.3
165°	718.5	719.3	719.2	718.4	717.4	716.5	715.6
167.5°	730.2	730.9	730.9	730.2	729.3	728.5	727.7
170°	736.6	737.4	737.4	736.6	735.6	734.7	733.8
172.5°	741.4	742.2	742.2	741.2	740.4	739.4	738.6
175°	746.7	747.5	747.5	746.6	745.6	744.7	743.8
177.5°	749.0	749.6	749.6	748.8	748.1	747.3	746.6
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5

(END OF REPORT)