

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332229-927

Luminaire Tested: **S123DIW-S1165D1320U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332229-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1320U927-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7506.2 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	71	67	65	62	58	55	52	50	46	44	42	37
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	41	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	34	31	28
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	42	35	29	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13832	13832	13832	13832
5°	16495	13891	12310	13891
10°	20647	13821	11119	13821
15°	25324	13710	10351	13710
20°	30166	13536	9856	13536
25°	32033	13324	9745	13324
30°	27455	13170	9797	13170
35°	19094	12951	9900	12951
40°	14383	12694	9868	12694
45°	11942	12310	9742	12310
50°	10697	11531	9656	11531
55°	10001	10691	9533	10691
60°	9382	9810	9436	9810
65°	8818	8945	9133	8945
70°	8271	7956	8699	7956
75°	7407	6966	7977	6966
80°	6484	5709	6868	5709
85°	5076	4150	4619	4150



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.6	1.7
10°-20°	405.9	5.4
20°-30°	681.2	9.1
30°-40°	771.4	10.3
40°-50°	691.7	9.2
50°-60°	558.2	7.4
60°-70°	389.0	5.2
70°-80°	204.5	2.7
80°-90°	53.9	0.7
90°-100°	85.2	1.1
100°-110°	255.0	3.4
110°-120°	433.8	5.8
120°-130°	570.5	7.6
130°-140°	641.3	8.5
140°-150°	630.4	8.4
150°-160°	530.7	7.1
160°-170°	353.3	4.7
170°-180°	123.7	1.6
0°-30°	1213.7	16.2
0°-40°	1985.1	26.4
0°-60°	3235.0	43.1
0°-90°	3882.4	51.7
90°-120°	774.0	10.3
90°-150°	2616.2	34.9
90°-180°	3624.0	48.3
0°-180°	7506.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1285	1285	1285	1285	1285	
5°	1527	1286	1139	1286	1527	158
15°	2272	1230	929	1230	2272	656
25°	2697	1122	820	1122	2697	1183
35°	1453	986	753	986	1453	944
45°	784	809	640	809	784	621
55°	533	570	508	570	533	478
65°	346	351	359	351	346	345
75°	178	168	192	168	178	191
85°	41	34	37	34	41	49
90°	31	1	31	1	31	17
95°	80	61	80	61	80	82
105°	244	231	244	231	244	259
115°	438	437	438	437	438	433
125°	632	639	632	639	632	565
135°	828	829	828	829	828	637
145°	1006	1006	1006	1006	1006	628
155°	1150	1152	1150	1152	1150	529
165°	1250	1254	1250	1254	1250	353
175°	1300	1305	1300	1305	1300	123
180°	1308	1308	1308	1308	1308	



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1363.7	1362.7	1360.3	1362.2	1358.3	1352.7	1352.3	1347.3	1332.8	1331.8	1327.9
5°	1526.6	1521.6	1521.0	1520.4	1511.6	1499.8	1477.4	1475.5	1445.7	1430.7	1412.7
7.5°	1737.5	1740.1	1731.1	1723.1	1696.5	1678.9	1654.9	1624.1	1587.4	1550.1	1525.3
10°	1889.0	1909.5	1884.0	1866.5	1850.4	1819.8	1784.4	1740.1	1695.9	1644.3	1605.0
12.5°	2051.4	2061.4	2056.3	2039.9	2014.7	1968.3	1905.4	1856.7	1816.0	1730.0	1695.2
15°	2272.5	2310.5	2286.2	2230.2	2231.3	2187.1	2105.0	2014.7	1966.8	1891.4	1788.7
17.5°	2508.0	2512.8	2502.4	2455.8	2424.6	2363.9	2288.1	2201.5	2104.4	2013.3	1904.2
20°	2633.5	2629.8	2608.0	2583.8	2530.2	2482.9	2400.1	2303.6	2179.1	2089.5	1970.5
22.5°	2703.3	2697.1	2686.8	2666.4	2621.9	2571.0	2496.7	2391.3	2272.7	2149.2	2011.8
25°	2697.1	2705.1	2706.4	2700.8	2685.3	2654.8	2596.2	2512.2	2393.9	2235.1	2091.9
27.5°	2453.0	2464.5	2497.8	2527.2	2560.3	2593.8	2589.3	2547.7	2460.1	2323.0	2147.9
30°	2208.9	2184.0	2245.7	2323.5	2376.5	2469.8	2522.1	2525.2	2476.0	2358.4	2187.8
32.5°	1870.3	1897.7	1924.9	2020.7	2136.4	2241.2	2345.3	2429.1	2438.7	2360.4	2211.2
35°	1453.1	1487.4	1537.2	1587.0	1711.5	1818.6	2001.6	2161.0	2288.1	2304.9	2213.3
37.5°	1171.0	1187.9	1219.4	1269.3	1350.8	1477.8	1619.4	1820.8	2004.9	2141.7	2147.7
40°	1023.6	1028.5	1064.0	1102.0	1168.0	1272.6	1400.2	1578.3	1798.6	1989.8	2069.5
42.5°	913.0	923.9	939.0	975.5	1028.0	1106.8	1225.4	1372.5	1574.5	1794.5	1950.4
45°	784.5	796.9	806.3	830.5	867.9	920.8	1003.6	1138.1	1291.9	1519.1	1728.9
47.5°	699.6	700.5	707.5	725.8	751.2	790.9	849.5	935.9	1077.1	1261.4	1476.8
50°	638.8	648.7	651.3	665.5	685.5	714.7	763.3	836.8	952.6	1114.4	1312.4
52.5°	596.0	599.0	605.9	616.2	633.7	656.5	698.5	756.1	847.0	984.9	1167.0
55°	532.9	532.9	539.8	547.9	557.9	578.4	606.4	648.7	717.9	824.9	975.6
57.5°	474.7	477.8	482.6	485.1	493.6	507.2	530.6	562.7	614.3	696.6	816.5
60°	435.8	441.4	440.8	445.8	453.3	463.8	483.8	509.9	556.0	621.9	722.9
62.5°	402.0	401.6	401.5	407.4	414.9	425.0	437.9	460.6	499.7	558.3	644.1
65°	346.2	344.9	349.3	353.0	355.5	363.0	373.0	392.8	419.0	462.6	529.2
67.5°	296.6	293.0	295.3	296.6	300.9	306.7	316.0	328.4	349.1	384.1	434.4
70°	262.8	259.6	259.0	260.2	264.0	268.3	275.2	287.0	306.3	334.3	371.1
72.5°	227.8	225.8	225.6	228.4	230.1	233.0	237.8	248.7	264.0	285.0	319.2
75°	178.1	178.1	178.1	178.7	180.5	183.1	186.8	192.3	204.2	219.1	242.2
77.5°	133.5	133.3	132.6	132.5	135.2	136.3	137.2	142.4	149.0	159.1	175.9
80°	104.6	101.5	102.7	104.6	105.8	106.5	108.4	109.6	115.2	120.8	132.6
82.5°	77.7	75.1	75.3	78.2	78.4	79.1	81.0	82.7	84.8	89.9	96.3
85°	41.1	41.1	41.7	41.7	42.3	41.7	43.6	44.2	44.2	47.3	51.0
87.5°	21.1	20.0	20.4	20.8	20.3	20.6	20.9	21.2	21.5	21.9	21.8
90°	30.8	30.3	29.9	29.5	29.0	28.3	27.4	26.5	25.6	24.6	21.7
92.5°	41.5	41.7	42.1	42.3	42.6	42.4	41.7	40.9	40.2	39.5	37.8
95°	80.2	80.2	80.2	80.2	80.2	79.7	78.7	77.9	76.9	76.0	74.2
97.5°	123.3	123.4	123.5	123.6	123.7	123.2	122.2	121.0	120.0	119.0	117.6
100°	156.1	155.7	155.3	154.8	154.3	153.8	153.0	152.4	151.7	151.1	149.9
102.5°	189.9	190.0	190.0	190.1	190.2	190.0	189.3	188.5	187.9	187.2	185.7
105°	244.5	244.1	243.6	243.2	242.7	242.5	242.5	242.5	242.5	242.5	240.4
107.5°	301.4	301.7	302.0	302.3	302.5	302.3	301.6	300.9	300.2	299.4	298.6
110°	340.1	340.6	341.0	341.4	341.9	341.7	340.8	339.8	339.0	338.0	337.5



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	381.2	381.3	381.4	381.4	381.5	381.0	379.9	378.8	377.8	376.7	376.6
115°	437.7	437.9	438.2	438.4	438.6	438.6	438.4	438.2	437.9	437.7	438.2
117.5°	495.0	495.7	496.3	496.9	497.6	497.9	498.0	498.0	498.0	498.1	498.7
120°	535.3	535.8	536.2	536.7	537.1	537.5	537.7	537.9	538.1	538.4	539.6
122.5°	573.9	574.6	575.2	575.8	576.5	577.1	577.7	578.3	578.8	579.5	580.0
125°	631.8	632.8	633.7	634.6	635.6	636.4	637.4	638.3	639.2	640.1	640.6
127.5°	689.6	690.7	691.7	692.8	693.8	695.0	696.2	697.5	698.8	700.1	700.6
130°	727.5	729.0	730.6	732.2	733.8	735.1	736.0	736.9	737.8	738.7	739.4
132.5°	766.9	768.1	769.4	770.6	771.8	773.0	774.0	775.2	776.3	777.4	777.8
135°	828.1	828.5	829.0	829.5	830.0	830.6	831.6	832.4	833.4	834.2	834.5
137.5°	882.2	883.0	883.9	884.8	885.7	886.5	887.5	888.4	889.4	890.4	889.8
140°	917.5	919.1	920.7	922.3	923.9	924.8	925.0	925.3	925.5	925.7	925.5
142.5°	953.7	954.9	956.2	957.4	958.6	959.3	959.6	959.8	960.0	960.3	959.8
145°	1005.8	1006.8	1007.7	1008.6	1009.6	1010.1	1010.3	1010.5	1010.7	1011.0	1010.3
147.5°	1052.3	1053.7	1055.0	1056.5	1057.8	1058.4	1058.4	1058.4	1058.4	1058.4	1057.8
150°	1081.9	1083.2	1084.7	1086.0	1087.3	1088.1	1088.1	1088.1	1088.1	1088.1	1087.6
152.5°	1110.6	1111.8	1113.0	1114.2	1115.4	1115.8	1115.5	1115.1	1114.8	1114.4	1114.1
155°	1149.7	1151.3	1152.9	1154.5	1156.1	1156.4	1155.6	1154.6	1153.7	1152.8	1152.5
157.5°	1185.3	1186.5	1187.8	1189.1	1190.3	1190.6	1189.5	1188.6	1187.6	1186.7	1186.5
160°	1208.2	1209.2	1210.1	1211.0	1212.0	1211.8	1210.7	1209.5	1208.4	1207.2	1207.2
162.5°	1225.5	1227.0	1228.4	1229.9	1231.4	1231.5	1230.4	1229.2	1228.1	1226.9	1226.8
165°	1250.4	1252.0	1253.6	1255.2	1256.8	1256.9	1255.5	1254.2	1252.8	1251.4	1251.4
167.5°	1271.5	1273.0	1274.4	1275.8	1277.2	1277.2	1275.8	1274.4	1273.0	1271.5	1271.4
170°	1282.2	1283.8	1285.5	1287.1	1288.6	1288.6	1287.1	1285.5	1283.8	1282.2	1282.2
172.5°	1290.5	1292.0	1293.6	1295.3	1296.9	1297.0	1295.5	1294.1	1292.7	1291.3	1291.3
175°	1299.7	1301.3	1302.9	1304.5	1306.1	1306.2	1304.9	1303.5	1302.1	1300.8	1300.8
177.5°	1304.6	1305.9	1307.2	1308.4	1309.8	1309.9	1308.8	1307.7	1306.5	1305.4	1305.4
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1324.8	1320.9	1316.9	1310.0	1303.9	1295.5	1293.0	1290.0	1281.0	1273.1	1267.1
5°	1405.8	1390.8	1369.0	1349.2	1333.0	1311.2	1298.7	1285.6	1266.9	1250.1	1236.4
7.5°	1490.5	1461.1	1427.2	1390.6	1356.5	1323.7	1297.1	1273.4	1247.3	1222.5	1203.2
10°	1557.7	1515.4	1468.1	1417.1	1373.4	1331.1	1295.6	1264.5	1230.9	1201.6	1177.3
12.5°	1634.4	1571.7	1506.4	1444.4	1392.9	1334.1	1291.1	1251.6	1213.5	1178.2	1151.0
15°	1725.2	1645.5	1568.3	1483.0	1404.5	1331.1	1280.1	1230.3	1186.1	1149.9	1115.1
17.5°	1807.9	1717.6	1615.9	1512.1	1417.5	1330.4	1258.9	1202.6	1147.3	1103.1	1068.3
20°	1854.7	1752.0	1636.8	1529.1	1424.5	1327.4	1249.0	1181.7	1121.9	1075.2	1036.0
22.5°	1895.1	1774.9	1655.7	1540.6	1424.0	1319.4	1230.5	1161.3	1096.5	1050.8	1009.1
25°	1936.9	1793.1	1673.6	1538.4	1408.3	1300.0	1200.4	1121.9	1057.2	1003.6	960.7
27.5°	1972.8	1791.8	1650.0	1504.7	1383.6	1275.1	1168.7	1084.6	1015.8	957.7	914.1
30°	1996.6	1794.3	1625.6	1481.8	1359.8	1247.7	1144.3	1059.6	987.5	928.3	887.2
32.5°	2011.6	1792.8	1603.1	1449.9	1321.9	1222.7	1117.9	1030.2	956.1	897.9	858.3
35°	2020.3	1781.9	1564.6	1384.0	1260.8	1164.3	1076.5	985.6	907.8	853.6	808.7
37.5°	2002.9	1758.8	1519.7	1320.5	1185.6	1090.5	1016.7	939.2	864.7	805.2	766.5
40°	1975.5	1743.9	1484.9	1275.7	1133.8	1042.2	979.4	903.4	829.9	773.2	737.1
42.5°	1923.2	1713.5	1446.5	1225.9	1080.0	988.4	930.5	867.0	797.6	744.3	708.3
45°	1795.6	1647.3	1389.0	1151.2	1000.5	905.9	854.8	808.7	745.8	694.2	663.1
47.5°	1618.5	1547.9	1305.8	1072.4	917.6	826.6	773.5	736.4	690.5	648.7	618.9
50°	1495.5	1466.2	1249.5	1018.6	862.3	773.2	722.2	688.6	655.6	613.9	586.5
52.5°	1353.5	1371.6	1183.8	962.7	806.0	718.5	670.4	643.7	613.8	579.5	555.6
55°	1153.7	1219.0	1070.2	869.1	722.2	638.8	593.3	569.7	552.2	526.7	506.2
57.5°	966.5	1049.7	947.5	772.6	639.9	567.9	524.3	498.6	487.4	474.0	457.9
60°	855.5	937.6	859.8	707.9	584.6	516.1	477.5	455.7	444.5	435.2	421.5
62.5°	756.3	839.5	774.1	642.1	530.3	466.8	433.2	411.9	403.2	398.3	386.7
65°	620.1	691.7	648.1	539.8	452.7	396.6	366.1	351.2	343.0	341.2	333.7
67.5°	504.7	559.2	527.4	447.7	379.1	330.7	304.8	292.2	285.9	285.3	279.6
70°	429.0	480.0	455.7	383.5	324.4	286.4	264.0	252.8	249.1	248.4	245.3
72.5°	370.2	405.8	386.5	326.2	280.5	246.1	229.6	217.9	213.7	214.5	212.5
75°	273.9	300.7	289.5	247.8	211.0	188.6	174.9	167.5	163.7	165.6	163.1
77.5°	197.1	214.0	204.0	175.1	152.4	136.3	126.1	121.5	118.2	118.0	116.9
80°	148.8	158.8	153.1	135.7	117.1	103.4	95.2	92.1	90.3	89.7	89.0
82.5°	106.0	114.5	107.8	95.9	83.2	74.9	70.3	66.2	64.9	65.3	64.6
85°	53.6	56.6	54.2	46.7	41.7	37.9	35.5	33.6	32.4	33.0	31.8
87.5°	22.2	22.1	20.0	17.5	16.0	14.1	13.6	12.1	11.6	12.0	12.0
90°	18.7	15.8	12.8	10.1	7.8	5.6	3.3	1.0	3.3	5.6	7.8
92.5°	36.0	34.4	32.7	31.1	29.5	28.0	26.4	24.9	26.4	28.0	29.5
95°	72.4	70.6	68.8	67.0	65.4	63.8	62.2	60.6	62.2	63.8	65.4
97.5°	116.3	115.0	113.7	112.4	111.2	110.0	108.8	107.7	108.8	110.0	111.2
100°	148.8	147.6	146.5	145.2	143.9	142.4	141.1	139.7	141.1	142.4	143.9
102.5°	184.2	182.7	181.2	180.0	179.2	178.4	177.5	176.7	177.5	178.4	179.2
105°	238.4	236.3	234.2	233.0	232.5	232.1	231.6	231.2	231.6	232.1	232.5
107.5°	297.8	296.9	296.1	295.6	295.3	295.0	294.8	294.5	294.8	295.0	295.3
110°	337.2	336.7	336.2	335.7	335.3	334.9	334.4	333.9	334.4	334.9	335.3



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	376.4	376.4	376.3	376.1	375.8	375.6	375.3	375.0	375.3	375.6	375.8
115°	438.6	439.0	439.5	439.4	438.7	438.0	437.4	436.7	437.4	438.0	438.7
117.5°	499.3	499.9	500.5	500.6	500.1	499.6	499.2	498.8	499.2	499.6	500.1
120°	540.7	541.8	543.0	542.8	541.5	540.1	538.7	537.3	538.7	540.1	541.5
122.5°	580.7	581.2	581.9	581.6	580.7	579.6	578.6	577.7	578.6	579.6	580.7
125°	641.0	641.4	641.9	641.8	641.1	640.4	639.8	639.1	639.8	640.4	641.1
127.5°	701.1	701.6	702.1	701.6	700.1	698.7	697.3	695.8	697.3	698.7	700.1
130°	740.1	740.8	741.5	740.9	739.1	737.3	735.4	733.6	735.4	737.3	739.1
132.5°	778.4	778.9	779.3	778.7	776.9	775.1	773.2	771.4	773.2	775.1	776.9
135°	834.7	835.0	835.2	834.6	833.2	831.9	830.5	829.2	830.5	831.9	833.2
137.5°	889.2	888.6	888.0	887.2	886.0	884.9	883.7	882.6	883.7	884.9	886.0
140°	925.3	925.0	924.8	924.2	923.0	921.9	920.7	919.6	920.7	921.9	923.0
142.5°	959.4	959.0	958.6	957.8	956.7	955.5	954.4	953.2	954.4	955.5	956.7
145°	1009.6	1008.9	1008.3	1007.7	1007.3	1006.8	1006.3	1005.8	1006.3	1006.8	1007.3
147.5°	1057.2	1056.5	1055.9	1055.2	1054.4	1053.5	1052.7	1051.9	1052.7	1053.5	1054.4
150°	1087.1	1086.7	1086.2	1085.8	1085.3	1084.9	1084.4	1083.9	1084.4	1084.9	1085.3
152.5°	1113.8	1113.6	1113.3	1112.8	1112.1	1111.5	1110.9	1110.2	1110.9	1111.5	1112.1
155°	1152.3	1152.1	1151.9	1151.8	1151.8	1151.8	1151.8	1151.8	1151.8	1151.8	1151.8
157.5°	1186.3	1186.1	1186.0	1186.0	1186.3	1186.5	1186.8	1187.1	1186.8	1186.5	1186.3
160°	1207.2	1207.2	1207.2	1207.4	1207.9	1208.4	1208.9	1209.3	1208.9	1208.4	1207.9
162.5°	1226.6	1226.5	1226.2	1226.5	1227.1	1227.7	1228.4	1229.0	1228.4	1227.7	1227.1
165°	1251.4	1251.4	1251.4	1251.8	1252.4	1253.2	1253.8	1254.5	1253.8	1253.2	1252.4
167.5°	1271.2	1271.0	1270.8	1271.2	1272.1	1273.0	1273.9	1274.9	1273.9	1273.0	1272.1
170°	1282.2	1282.2	1282.2	1282.7	1283.7	1284.5	1285.5	1286.3	1285.5	1284.5	1283.7
172.5°	1291.3	1291.3	1291.3	1291.7	1292.7	1293.6	1294.5	1295.4	1294.5	1293.6	1292.7
175°	1300.8	1300.8	1300.8	1301.2	1302.1	1303.1	1303.9	1304.9	1303.9	1303.1	1302.1
177.5°	1305.4	1305.4	1305.4	1305.8	1306.5	1307.3	1308.1	1308.8	1308.1	1307.3	1306.5
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1263.6	1260.1	1255.1	1247.7	1241.7	1232.2	1232.2	1233.7	1233.7	1233.3	1232.2
5°	1225.3	1215.9	1204.8	1191.7	1178.0	1164.3	1161.7	1156.7	1153.0	1150.6	1147.5
7.5°	1184.8	1168.2	1151.9	1133.6	1116.9	1103.1	1093.5	1085.5	1080.5	1075.0	1071.0
10°	1157.4	1136.9	1117.5	1098.3	1077.1	1060.3	1049.7	1042.2	1036.6	1031.7	1029.1
12.5°	1125.1	1101.5	1080.2	1061.9	1038.7	1021.4	1011.4	1007.8	1001.2	990.8	985.3
15°	1077.7	1055.9	1030.4	1002.3	991.2	970.0	958.1	952.6	948.8	940.7	938.3
17.5°	1037.2	1008.7	980.1	959.2	938.3	921.1	914.6	907.6	902.6	896.0	894.1
20°	1004.9	979.4	953.2	930.8	908.9	890.3	884.7	879.7	874.7	871.6	869.1
22.5°	972.0	946.5	924.8	903.9	880.6	868.4	862.3	856.8	853.3	851.2	848.7
25°	925.8	903.4	879.1	860.4	841.8	833.6	829.9	826.8	824.3	821.2	820.5
27.5°	884.5	860.1	840.3	822.9	809.5	802.8	799.2	797.6	798.2	799.3	800.0
30°	853.6	831.2	815.0	800.0	787.6	781.3	780.7	780.7	783.2	783.9	785.1
32.5°	825.2	806.8	790.6	776.1	766.7	762.4	764.8	764.8	766.8	768.4	770.6
35°	783.9	767.6	755.2	742.8	734.7	736.5	737.8	739.0	742.1	745.8	748.4
37.5°	744.3	730.3	717.3	707.7	703.9	707.3	710.3	712.9	716.4	719.4	721.8
40°	716.0	705.4	692.9	684.2	685.5	687.4	689.8	692.9	696.1	697.9	700.4
42.5°	689.6	678.5	669.1	661.8	663.5	665.9	667.4	669.1	672.6	676.0	677.5
45°	649.4	640.6	631.9	627.6	628.8	630.1	631.3	633.2	636.3	638.8	639.4
47.5°	604.2	598.1	592.2	588.0	589.9	589.5	591.1	595.1	596.0	597.5	601.0
50°	575.3	569.7	562.8	561.6	561.6	561.6	562.2	567.2	567.2	569.7	572.2
52.5°	543.4	539.8	535.4	533.2	532.2	532.2	534.8	537.3	538.3	541.8	544.3
55°	496.2	492.5	488.7	486.9	485.6	486.9	491.9	493.1	496.2	498.0	499.9
57.5°	447.0	444.2	441.2	440.1	439.9	441.6	444.3	448.0	448.8	454.5	457.3
60°	414.6	410.3	407.8	407.8	406.5	412.2	410.9	417.2	418.4	422.2	426.5
62.5°	381.3	375.4	374.5	374.5	376.2	377.8	379.5	382.3	385.5	390.2	393.6
65°	327.5	324.4	328.8	328.1	326.9	330.6	330.6	333.7	337.5	341.8	348.6
67.5°	276.6	275.0	275.3	275.3	277.2	279.3	281.1	283.8	288.3	292.9	297.4
70°	242.2	244.1	241.0	243.4	245.3	245.9	247.2	250.9	255.9	259.0	264.0
72.5°	208.8	208.7	209.1	210.1	211.9	213.0	214.3	218.6	224.0	226.6	230.6
75°	160.7	160.0	161.8	161.8	165.0	166.2	167.5	169.4	174.4	178.1	181.2
77.5°	117.3	118.0	117.6	119.8	118.9	119.1	123.0	124.9	125.4	132.8	134.4
80°	88.4	89.7	90.3	90.9	91.5	90.3	94.7	96.5	96.5	100.8	103.9
82.5°	63.5	64.2	65.9	66.5	66.6	67.9	68.2	69.6	71.1	73.0	77.1
85°	31.8	33.6	34.2	33.6	34.2	33.0	34.9	35.5	36.1	36.1	36.1
87.5°	12.0	13.0	13.2	14.2	14.3	15.4	15.6	14.7	15.0	16.6	14.7
90°	10.1	12.8	15.8	18.7	21.7	24.6	25.6	26.5	27.4	28.3	29.0
92.5°	31.1	32.7	34.4	36.0	37.8	39.5	40.2	40.9	41.7	42.4	42.6
95°	67.0	68.8	70.6	72.4	74.2	76.0	76.9	77.9	78.7	79.7	80.2
97.5°	112.4	113.7	115.0	116.3	117.6	119.0	120.0	121.0	122.2	123.2	123.7
100°	145.2	146.5	147.6	148.8	149.9	151.1	151.7	152.4	153.0	153.8	154.3
102.5°	180.0	181.2	182.7	184.2	185.7	187.2	187.9	188.5	189.3	190.0	190.2
105°	233.0	234.2	236.3	238.4	240.4	242.5	242.5	242.5	242.5	242.5	242.7
107.5°	295.6	296.1	296.9	297.8	298.6	299.4	300.2	300.9	301.6	302.3	302.5
110°	335.7	336.2	336.7	337.2	337.5	338.0	339.0	339.8	340.8	341.7	341.9



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	376.1	376.3	376.4	376.4	376.6	376.7	377.8	378.8	379.9	381.0	381.5
115°	439.4	439.5	439.0	438.6	438.2	437.7	437.9	438.2	438.4	438.6	438.6
117.5°	500.6	500.5	499.9	499.3	498.7	498.1	498.0	498.0	498.0	497.9	497.6
120°	542.8	543.0	541.8	540.7	539.6	538.4	538.1	537.9	537.7	537.5	537.1
122.5°	581.6	581.9	581.2	580.7	580.0	579.5	578.8	578.3	577.7	577.1	576.5
125°	641.8	641.9	641.4	641.0	640.6	640.1	639.2	638.3	637.4	636.4	635.6
127.5°	701.6	702.1	701.6	701.1	700.6	700.1	698.8	697.5	696.2	695.0	693.8
130°	740.9	741.5	740.8	740.1	739.4	738.7	737.8	736.9	736.0	735.1	733.8
132.5°	778.7	779.3	778.9	778.4	777.8	777.4	776.3	775.2	774.0	773.0	771.8
135°	834.6	835.2	835.0	834.7	834.5	834.2	833.4	832.4	831.6	830.6	830.0
137.5°	887.2	888.0	888.6	889.2	889.8	890.4	889.4	888.4	887.5	886.5	885.7
140°	924.2	924.8	925.0	925.3	925.5	925.7	925.5	925.3	925.0	924.8	923.9
142.5°	957.8	958.6	959.0	959.4	959.8	960.3	960.0	959.8	959.6	959.3	958.6
145°	1007.7	1008.3	1008.9	1009.6	1010.3	1011.0	1010.7	1010.5	1010.3	1010.1	1009.6
147.5°	1055.2	1055.9	1056.5	1057.2	1057.8	1058.4	1058.4	1058.4	1058.4	1058.4	1057.8
150°	1085.8	1086.2	1086.7	1087.1	1087.6	1088.1	1088.1	1088.1	1088.1	1088.1	1087.3
152.5°	1112.8	1113.3	1113.6	1113.8	1114.1	1114.4	1114.8	1115.1	1115.5	1115.8	1115.4
155°	1151.8	1151.9	1152.1	1152.3	1152.5	1152.8	1153.7	1154.6	1155.6	1156.4	1156.1
157.5°	1186.0	1186.0	1186.1	1186.3	1186.5	1186.7	1187.6	1188.6	1189.5	1190.6	1190.3
160°	1207.4	1207.2	1207.2	1207.2	1207.2	1207.2	1208.4	1209.5	1210.7	1211.8	1212.0
162.5°	1226.5	1226.2	1226.5	1226.6	1226.8	1226.9	1228.1	1229.2	1230.4	1231.5	1231.4
165°	1251.8	1251.4	1251.4	1251.4	1251.4	1251.4	1252.8	1254.2	1255.5	1256.9	1256.8
167.5°	1271.2	1270.8	1271.0	1271.2	1271.4	1271.5	1273.0	1274.4	1275.8	1277.2	1277.2
170°	1282.7	1282.2	1282.2	1282.2	1282.2	1282.2	1283.8	1285.5	1287.1	1288.6	1288.6
172.5°	1291.7	1291.3	1291.3	1291.3	1291.3	1291.3	1292.7	1294.1	1295.5	1297.0	1296.9
175°	1301.2	1300.8	1300.8	1300.8	1300.8	1300.8	1302.1	1303.5	1304.9	1306.2	1306.1
177.5°	1305.8	1305.4	1305.4	1305.4	1305.4	1305.4	1306.5	1307.7	1308.8	1309.9	1309.8
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1228.8	1228.3	1231.8	1229.2	1231.8	1228.3	1228.8	1232.2	1233.3	1233.7	1233.7
5°	1143.7	1145.6	1139.3	1139.3	1139.3	1145.6	1143.7	1147.5	1150.6	1153.0	1156.7
7.5°	1068.0	1065.2	1065.5	1062.2	1065.5	1065.2	1068.0	1071.0	1075.0	1080.5	1085.5
10°	1021.7	1018.0	1016.7	1017.3	1016.7	1018.0	1021.7	1029.1	1031.7	1036.6	1042.2
12.5°	983.3	982.5	974.4	974.5	974.4	982.5	983.3	985.3	990.8	1001.2	1007.8
15°	938.3	926.5	925.2	928.9	925.2	926.5	938.3	938.3	940.7	948.8	952.6
17.5°	893.0	886.8	887.2	885.3	887.2	886.8	893.0	894.1	896.0	902.6	907.6
20°	869.1	865.4	864.7	860.4	864.7	865.4	869.1	869.1	871.6	874.7	879.7
22.5°	847.2	846.0	846.4	841.5	846.4	846.0	847.2	848.7	851.2	853.3	856.8
25°	820.0	823.1	820.5	820.5	820.5	823.1	820.0	820.5	821.2	824.3	826.8
27.5°	801.5	801.4	800.2	800.2	800.2	801.4	801.5	800.0	799.3	798.2	797.6
30°	787.6	787.0	788.2	788.2	788.2	787.0	787.6	785.1	783.9	783.2	780.7
32.5°	773.6	774.5	774.8	775.2	774.8	774.5	773.6	770.6	768.4	766.8	764.8
35°	752.1	752.7	754.6	753.4	754.6	752.7	752.1	748.4	745.8	742.1	739.0
37.5°	722.9	725.8	725.2	726.2	725.2	725.8	722.9	721.8	719.4	716.4	712.9
40°	701.0	702.9	702.3	702.3	702.3	702.9	701.0	700.4	697.9	696.1	692.9
42.5°	678.7	680.0	678.3	677.4	678.3	680.0	678.7	677.5	676.0	672.6	669.1
45°	641.9	640.6	642.5	640.0	642.5	640.6	641.9	639.4	638.8	636.3	633.2
47.5°	600.8	602.1	602.5	604.4	602.5	602.1	600.8	601.0	597.5	596.0	595.1
50°	573.4	577.1	577.1	576.6	577.1	577.1	573.4	572.2	569.7	567.2	567.2
52.5°	546.5	548.3	550.7	550.6	550.7	548.3	546.5	544.3	541.8	538.3	537.3
55°	504.9	506.2	507.4	508.0	507.4	506.2	504.9	499.9	498.0	496.2	493.1
57.5°	461.8	461.4	464.3	465.2	464.3	461.4	461.8	457.3	454.5	448.8	448.0
60°	431.4	431.4	436.4	438.3	436.4	431.4	431.4	426.5	422.2	418.4	417.2
62.5°	399.1	401.1	406.1	403.5	406.1	401.1	399.1	393.6	390.2	385.5	382.3
65°	351.7	356.7	356.1	358.6	356.1	356.7	351.7	348.6	341.8	337.5	333.7
67.5°	302.3	305.5	309.9	310.3	309.9	305.5	302.3	297.4	292.9	288.3	283.8
70°	268.9	272.0	274.6	276.4	274.6	272.0	268.9	264.0	259.0	255.9	250.9
72.5°	236.6	238.2	244.2	241.5	244.2	238.2	236.6	230.6	226.6	224.0	218.6
75°	185.5	189.9	193.6	191.8	193.6	189.9	185.5	181.2	178.1	174.4	169.4
77.5°	137.2	141.6	143.3	141.7	143.3	141.6	137.2	134.4	132.8	125.4	124.9
80°	108.4	107.7	111.5	110.8	111.5	107.7	108.4	103.9	100.8	96.5	96.5
82.5°	79.5	78.8	80.6	81.0	80.6	78.8	79.5	77.1	73.0	71.1	69.6
85°	38.6	40.5	37.9	37.4	37.9	40.5	38.6	36.1	36.1	36.1	35.5
87.5°	14.9	15.0	14.6	14.1	14.6	15.0	14.9	14.7	16.6	15.0	14.7
90°	29.5	29.9	30.3	30.8	30.3	29.9	29.5	29.0	28.3	27.4	26.5
92.5°	42.3	42.1	41.7	41.5	41.7	42.1	42.3	42.6	42.4	41.7	40.9
95°	80.2	80.2	80.2	80.2	80.2	80.2	80.2	80.2	79.7	78.7	77.9
97.5°	123.6	123.5	123.4	123.3	123.4	123.5	123.6	123.7	123.2	122.2	121.0
100°	154.8	155.3	155.7	156.1	155.7	155.3	154.8	154.3	153.8	153.0	152.4
102.5°	190.1	190.0	190.0	189.9	190.0	190.0	190.1	190.2	190.0	189.3	188.5
105°	243.2	243.6	244.1	244.5	244.1	243.6	243.2	242.7	242.5	242.5	242.5
107.5°	302.3	302.0	301.7	301.4	301.7	302.0	302.3	302.5	302.3	301.6	300.9
110°	341.4	341.0	340.6	340.1	340.6	341.0	341.4	341.9	341.7	340.8	339.8



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	381.4	381.4	381.3	381.2	381.3	381.4	381.4	381.5	381.0	379.9	378.8
115°	438.4	438.2	437.9	437.7	437.9	438.2	438.4	438.6	438.6	438.4	438.2
117.5°	496.9	496.3	495.7	495.0	495.7	496.3	496.9	497.6	497.9	498.0	498.0
120°	536.7	536.2	535.8	535.3	535.8	536.2	536.7	537.1	537.5	537.7	537.9
122.5°	575.8	575.2	574.6	573.9	574.6	575.2	575.8	576.5	577.1	577.7	578.3
125°	634.6	633.7	632.8	631.8	632.8	633.7	634.6	635.6	636.4	637.4	638.3
127.5°	692.8	691.7	690.7	689.6	690.7	691.7	692.8	693.8	695.0	696.2	697.5
130°	732.2	730.6	729.0	727.5	729.0	730.6	732.2	733.8	735.1	736.0	736.9
132.5°	770.6	769.4	768.1	766.9	768.1	769.4	770.6	771.8	773.0	774.0	775.2
135°	829.5	829.0	828.5	828.1	828.5	829.0	829.5	830.0	830.6	831.6	832.4
137.5°	884.8	883.9	883.0	882.2	883.0	883.9	884.8	885.7	886.5	887.5	888.4
140°	922.3	920.7	919.1	917.5	919.1	920.7	922.3	923.9	924.8	925.0	925.3
142.5°	957.4	956.2	954.9	953.7	954.9	956.2	957.4	958.6	959.3	959.6	959.8
145°	1008.6	1007.7	1006.8	1005.8	1006.8	1007.7	1008.6	1009.6	1010.1	1010.3	1010.5
147.5°	1056.5	1055.0	1053.7	1052.3	1053.7	1055.0	1056.5	1057.8	1058.4	1058.4	1058.4
150°	1086.0	1084.7	1083.2	1081.9	1083.2	1084.7	1086.0	1087.3	1088.1	1088.1	1088.1
152.5°	1114.2	1113.0	1111.8	1110.6	1111.8	1113.0	1114.2	1115.4	1115.8	1115.5	1115.1
155°	1154.5	1152.9	1151.3	1149.7	1151.3	1152.9	1154.5	1156.1	1156.4	1155.6	1154.6
157.5°	1189.1	1187.8	1186.5	1185.3	1186.5	1187.8	1189.1	1190.3	1190.6	1189.5	1188.6
160°	1211.0	1210.1	1209.2	1208.2	1209.2	1210.1	1211.0	1212.0	1211.8	1210.7	1209.5
162.5°	1229.9	1228.4	1227.0	1225.5	1227.0	1228.4	1229.9	1231.4	1231.5	1230.4	1229.2
165°	1255.2	1253.6	1252.0	1250.4	1252.0	1253.6	1255.2	1256.8	1256.9	1255.5	1254.2
167.5°	1275.8	1274.4	1273.0	1271.5	1273.0	1274.4	1275.8	1277.2	1277.2	1275.8	1274.4
170°	1287.1	1285.5	1283.8	1282.2	1283.8	1285.5	1287.1	1288.6	1288.6	1287.1	1285.5
172.5°	1295.3	1293.6	1292.0	1290.5	1292.0	1293.6	1295.3	1296.9	1297.0	1295.5	1294.1
175°	1304.5	1302.9	1301.3	1299.7	1301.3	1302.9	1304.5	1306.1	1306.2	1304.9	1303.5
177.5°	1308.4	1307.2	1305.9	1304.6	1305.9	1307.2	1308.4	1309.8	1309.9	1308.8	1307.7
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1232.2	1232.2	1241.7	1247.7	1255.1	1260.1	1263.6	1267.1	1273.1	1281.0	1290.0
5°	1161.7	1164.3	1178.0	1191.7	1204.8	1215.9	1225.3	1236.4	1250.1	1266.9	1285.6
7.5°	1093.5	1103.1	1116.9	1133.6	1151.9	1168.2	1184.8	1203.2	1222.5	1247.3	1273.4
10°	1049.7	1060.3	1077.1	1098.3	1117.5	1136.9	1157.4	1177.3	1201.6	1230.9	1264.5
12.5°	1011.4	1021.4	1038.7	1061.9	1080.2	1101.5	1125.1	1151.0	1178.2	1213.5	1251.6
15°	958.1	970.0	991.2	1002.3	1030.4	1055.9	1077.7	1115.1	1149.9	1186.1	1230.3
17.5°	914.6	921.1	938.3	959.2	980.1	1008.7	1037.2	1068.3	1103.1	1147.3	1202.6
20°	884.7	890.3	908.9	930.8	953.2	979.4	1004.9	1036.0	1075.2	1121.9	1181.7
22.5°	862.3	868.4	880.6	903.9	924.8	946.5	972.0	1009.1	1050.8	1096.5	1161.3
25°	829.9	833.6	841.8	860.4	879.1	903.4	925.8	960.7	1003.6	1057.2	1121.9
27.5°	799.2	802.8	809.5	822.9	840.3	860.1	884.5	914.1	957.7	1015.8	1084.6
30°	780.7	781.3	787.6	800.0	815.0	831.2	853.6	887.2	928.3	987.5	1059.6
32.5°	764.8	762.4	766.7	776.1	790.6	806.8	825.2	858.3	897.9	956.1	1030.2
35°	737.8	736.5	734.7	742.8	755.2	767.6	783.9	808.7	853.6	907.8	985.6
37.5°	710.3	707.3	703.9	707.7	717.3	730.3	744.3	766.5	805.2	864.7	939.2
40°	689.8	687.4	685.5	684.2	692.9	705.4	716.0	737.1	773.2	829.9	903.4
42.5°	667.4	665.9	663.5	661.8	669.1	678.5	689.6	708.3	744.3	797.6	867.0
45°	631.3	630.1	628.8	627.6	631.9	640.6	649.4	663.1	694.2	745.8	808.7
47.5°	591.1	589.5	589.9	588.0	592.2	598.1	604.2	618.9	648.7	690.5	736.4
50°	562.2	561.6	561.6	561.6	562.8	569.7	575.3	586.5	613.9	655.6	688.6
52.5°	534.8	532.2	532.2	533.2	535.4	539.8	543.4	555.6	579.5	613.8	643.7
55°	491.9	486.9	485.6	486.9	488.7	492.5	496.2	506.2	526.7	552.2	569.7
57.5°	444.3	441.6	439.9	440.1	441.2	444.2	447.0	457.9	474.0	487.4	498.6
60°	410.9	412.2	406.5	407.8	407.8	410.3	414.6	421.5	435.2	444.5	455.7
62.5°	379.5	377.8	376.2	374.5	374.5	375.4	381.3	386.7	398.3	403.2	411.9
65°	330.6	330.6	326.9	328.1	328.8	324.4	327.5	333.7	341.2	343.0	351.2
67.5°	281.1	279.3	277.2	275.3	275.3	275.0	276.6	279.6	285.3	285.9	292.2
70°	247.2	245.9	245.3	243.4	241.0	244.1	242.2	245.3	248.4	249.1	252.8
72.5°	214.3	213.0	211.9	210.1	209.1	208.7	208.8	212.5	214.5	213.7	217.9
75°	167.5	166.2	165.0	161.8	161.8	160.0	160.7	163.1	165.6	163.7	167.5
77.5°	123.0	119.1	118.9	119.8	117.6	118.0	117.3	116.9	118.0	118.2	121.5
80°	94.7	90.3	91.5	90.9	90.3	89.7	88.4	89.0	89.7	90.3	92.1
82.5°	68.2	67.9	66.6	66.5	65.9	64.2	63.5	64.6	65.3	64.9	66.2
85°	34.9	33.0	34.2	33.6	34.2	33.6	31.8	31.8	33.0	32.4	33.6
87.5°	15.6	15.4	14.3	14.2	13.2	13.0	12.0	12.0	12.0	11.6	12.1
90°	25.6	24.6	21.7	18.7	15.8	12.8	10.1	7.8	5.6	3.3	1.0
92.5°	40.2	39.5	37.8	36.0	34.4	32.7	31.1	29.5	28.0	26.4	24.9
95°	76.9	76.0	74.2	72.4	70.6	68.8	67.0	65.4	63.8	62.2	60.6
97.5°	120.0	119.0	117.6	116.3	115.0	113.7	112.4	111.2	110.0	108.8	107.7
100°	151.7	151.1	149.9	148.8	147.6	146.5	145.2	143.9	142.4	141.1	139.7
102.5°	187.9	187.2	185.7	184.2	182.7	181.2	180.0	179.2	178.4	177.5	176.7
105°	242.5	242.5	240.4	238.4	236.3	234.2	233.0	232.5	232.1	231.6	231.2
107.5°	300.2	299.4	298.6	297.8	296.9	296.1	295.6	295.3	295.0	294.8	294.5
110°	339.0	338.0	337.5	337.2	336.7	336.2	335.7	335.3	334.9	334.4	333.9



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	377.8	376.7	376.6	376.4	376.4	376.3	376.1	375.8	375.6	375.3	375.0
115°	437.9	437.7	438.2	438.6	439.0	439.5	439.4	438.7	438.0	437.4	436.7
117.5°	498.0	498.1	498.7	499.3	499.9	500.5	500.6	500.1	499.6	499.2	498.8
120°	538.1	538.4	539.6	540.7	541.8	543.0	542.8	541.5	540.1	538.7	537.3
122.5°	578.8	579.5	580.0	580.7	581.2	581.9	581.6	580.7	579.6	578.6	577.7
125°	639.2	640.1	640.6	641.0	641.4	641.9	641.8	641.1	640.4	639.8	639.1
127.5°	698.8	700.1	700.6	701.1	701.6	702.1	701.6	700.1	698.7	697.3	695.8
130°	737.8	738.7	739.4	740.1	740.8	741.5	740.9	739.1	737.3	735.4	733.6
132.5°	776.3	777.4	777.8	778.4	778.9	779.3	778.7	776.9	775.1	773.2	771.4
135°	833.4	834.2	834.5	834.7	835.0	835.2	834.6	833.2	831.9	830.5	829.2
137.5°	889.4	890.4	889.8	889.2	888.6	888.0	887.2	886.0	884.9	883.7	882.6
140°	925.5	925.7	925.5	925.3	925.0	924.8	924.2	923.0	921.9	920.7	919.6
142.5°	960.0	960.3	959.8	959.4	959.0	958.6	957.8	956.7	955.5	954.4	953.2
145°	1010.7	1011.0	1010.3	1009.6	1008.9	1008.3	1007.7	1007.3	1006.8	1006.3	1005.8
147.5°	1058.4	1058.4	1057.8	1057.2	1056.5	1055.9	1055.2	1054.4	1053.5	1052.7	1051.9
150°	1088.1	1088.1	1087.6	1087.1	1086.7	1086.2	1085.8	1085.3	1084.9	1084.4	1083.9
152.5°	1114.8	1114.4	1114.1	1113.8	1113.6	1113.3	1112.8	1112.1	1111.5	1110.9	1110.2
155°	1153.7	1152.8	1152.5	1152.3	1152.1	1151.9	1151.8	1151.8	1151.8	1151.8	1151.8
157.5°	1187.6	1186.7	1186.5	1186.3	1186.1	1186.0	1186.0	1186.3	1186.5	1186.8	1187.1
160°	1208.4	1207.2	1207.2	1207.2	1207.2	1207.2	1207.4	1207.9	1208.4	1208.9	1209.3
162.5°	1228.1	1226.9	1226.8	1226.6	1226.5	1226.2	1226.5	1227.1	1227.7	1228.4	1229.0
165°	1252.8	1251.4	1251.4	1251.4	1251.4	1251.4	1251.8	1252.4	1253.2	1253.8	1254.5
167.5°	1273.0	1271.5	1271.4	1271.2	1271.0	1270.8	1271.2	1272.1	1273.0	1273.9	1274.9
170°	1283.8	1282.2	1282.2	1282.2	1282.2	1282.2	1282.7	1283.7	1284.5	1285.5	1286.3
172.5°	1292.7	1291.3	1291.3	1291.3	1291.3	1291.3	1291.7	1292.7	1293.6	1294.5	1295.4
175°	1302.1	1300.8	1300.8	1300.8	1300.8	1300.8	1301.2	1302.1	1303.1	1303.9	1304.9
177.5°	1306.5	1305.4	1305.4	1305.4	1305.4	1305.4	1305.8	1306.5	1307.3	1308.1	1308.8
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1293.0	1295.5	1303.9	1310.0	1316.9	1320.9	1324.8	1327.9	1331.8	1332.8	1347.3
5°	1298.7	1311.2	1333.0	1349.2	1369.0	1390.8	1405.8	1412.7	1430.7	1445.7	1475.5
7.5°	1297.1	1323.7	1356.5	1390.6	1427.2	1461.1	1490.5	1525.3	1550.1	1587.4	1624.1
10°	1295.6	1331.1	1373.4	1417.1	1468.1	1515.4	1557.7	1605.0	1644.3	1695.9	1740.1
12.5°	1291.1	1334.1	1392.9	1444.4	1506.4	1571.7	1634.4	1695.2	1730.0	1816.0	1856.7
15°	1280.1	1331.1	1404.5	1483.0	1568.3	1645.5	1725.2	1788.7	1891.4	1966.8	2014.7
17.5°	1258.9	1330.4	1417.5	1512.1	1615.9	1717.6	1807.9	1904.2	2013.3	2104.4	2201.5
20°	1249.0	1327.4	1424.5	1529.1	1636.8	1752.0	1854.7	1970.5	2089.5	2179.1	2303.6
22.5°	1230.5	1319.4	1424.0	1540.6	1655.7	1774.9	1895.1	2011.8	2149.2	2272.7	2391.3
25°	1200.4	1300.0	1408.3	1538.4	1673.6	1793.1	1936.9	2091.9	2235.1	2393.9	2512.2
27.5°	1168.7	1275.1	1383.6	1504.7	1650.0	1791.8	1972.8	2147.9	2323.0	2460.1	2547.7
30°	1144.3	1247.7	1359.8	1481.8	1625.6	1794.3	1996.6	2187.8	2358.4	2476.0	2525.2
32.5°	1117.9	1222.7	1321.9	1449.9	1603.1	1792.8	2011.6	2211.2	2360.4	2438.7	2429.1
35°	1076.5	1164.3	1260.8	1384.0	1564.6	1781.9	2020.3	2213.3	2304.9	2288.1	2161.0
37.5°	1016.7	1090.5	1185.6	1320.5	1519.7	1758.8	2002.9	2147.7	2141.7	2004.9	1820.8
40°	979.4	1042.2	1133.8	1275.7	1484.9	1743.9	1975.5	2069.5	1989.8	1798.6	1578.3
42.5°	930.5	988.4	1080.0	1225.9	1446.5	1713.5	1923.2	1950.4	1794.5	1574.5	1372.5
45°	854.8	905.9	1000.5	1151.2	1389.0	1647.3	1795.6	1728.9	1519.1	1291.9	1138.1
47.5°	773.5	826.6	917.6	1072.4	1305.8	1547.9	1618.5	1476.8	1261.4	1077.1	935.9
50°	722.2	773.2	862.3	1018.6	1249.5	1466.2	1495.5	1312.4	1114.4	952.6	836.8
52.5°	670.4	718.5	806.0	962.7	1183.8	1371.6	1353.5	1167.0	984.9	847.0	756.1
55°	593.3	638.8	722.2	869.1	1070.2	1219.0	1153.7	975.6	824.9	717.9	648.7
57.5°	524.3	567.9	639.9	772.6	947.5	1049.7	966.5	816.5	696.6	614.3	562.7
60°	477.5	516.1	584.6	707.9	859.8	937.6	855.5	722.9	621.9	556.0	509.9
62.5°	433.2	466.8	530.3	642.1	774.1	839.5	756.3	644.1	558.3	499.7	460.6
65°	366.1	396.6	452.7	539.8	648.1	691.7	620.1	529.2	462.6	419.0	392.8
67.5°	304.8	330.7	379.1	447.7	527.4	559.2	504.7	434.4	384.1	349.1	328.4
70°	264.0	286.4	324.4	383.5	455.7	480.0	429.0	371.1	334.3	306.3	287.0
72.5°	229.6	246.1	280.5	326.2	386.5	405.8	370.2	319.2	285.0	264.0	248.7
75°	174.9	188.6	211.0	247.8	289.5	300.7	273.9	242.2	219.1	204.2	192.3
77.5°	126.1	136.3	152.4	175.1	204.0	214.0	197.1	175.9	159.1	149.0	142.4
80°	95.2	103.4	117.1	135.7	153.1	158.8	148.8	132.6	120.8	115.2	109.6
82.5°	70.3	74.9	83.2	95.9	107.8	114.5	106.0	96.3	89.9	84.8	82.7
85°	35.5	37.9	41.7	46.7	54.2	56.6	53.6	51.0	47.3	44.2	44.2
87.5°	13.6	14.1	16.0	17.5	20.0	22.1	22.2	21.8	21.9	21.5	21.2
90°	3.3	5.6	7.8	10.1	12.8	15.8	18.7	21.7	24.6	25.6	26.5
92.5°	26.4	28.0	29.5	31.1	32.7	34.4	36.0	37.8	39.5	40.2	40.9
95°	62.2	63.8	65.4	67.0	68.8	70.6	72.4	74.2	76.0	76.9	77.9
97.5°	108.8	110.0	111.2	112.4	113.7	115.0	116.3	117.6	119.0	120.0	121.0
100°	141.1	142.4	143.9	145.2	146.5	147.6	148.8	149.9	151.1	151.7	152.4
102.5°	177.5	178.4	179.2	180.0	181.2	182.7	184.2	185.7	187.2	187.9	188.5
105°	231.6	232.1	232.5	233.0	234.2	236.3	238.4	240.4	242.5	242.5	242.5
107.5°	294.8	295.0	295.3	295.6	296.1	296.9	297.8	298.6	299.4	300.2	300.9
110°	334.4	334.9	335.3	335.7	336.2	336.7	337.2	337.5	338.0	339.0	339.8



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	375.3	375.6	375.8	376.1	376.3	376.4	376.4	376.6	376.7	377.8	378.8
115°	437.4	438.0	438.7	439.4	439.5	439.0	438.6	438.2	437.7	437.9	438.2
117.5°	499.2	499.6	500.1	500.6	500.5	499.9	499.3	498.7	498.1	498.0	498.0
120°	538.7	540.1	541.5	542.8	543.0	541.8	540.7	539.6	538.4	538.1	537.9
122.5°	578.6	579.6	580.7	581.6	581.9	581.2	580.7	580.0	579.5	578.8	578.3
125°	639.8	640.4	641.1	641.8	641.9	641.4	641.0	640.6	640.1	639.2	638.3
127.5°	697.3	698.7	700.1	701.6	702.1	701.6	701.1	700.6	700.1	698.8	697.5
130°	735.4	737.3	739.1	740.9	741.5	740.8	740.1	739.4	738.7	737.8	736.9
132.5°	773.2	775.1	776.9	778.7	779.3	778.9	778.4	777.8	777.4	776.3	775.2
135°	830.5	831.9	833.2	834.6	835.2	835.0	834.7	834.5	834.2	833.4	832.4
137.5°	883.7	884.9	886.0	887.2	888.0	888.6	889.2	889.8	890.4	889.4	888.4
140°	920.7	921.9	923.0	924.2	924.8	925.0	925.3	925.5	925.7	925.5	925.3
142.5°	954.4	955.5	956.7	957.8	958.6	959.0	959.4	959.8	960.3	960.0	959.8
145°	1006.3	1006.8	1007.3	1007.7	1008.3	1008.9	1009.6	1010.3	1011.0	1010.7	1010.5
147.5°	1052.7	1053.5	1054.4	1055.2	1055.9	1056.5	1057.2	1057.8	1058.4	1058.4	1058.4
150°	1084.4	1084.9	1085.3	1085.8	1086.2	1086.7	1087.1	1087.6	1088.1	1088.1	1088.1
152.5°	1110.9	1111.5	1112.1	1112.8	1113.3	1113.6	1113.8	1114.1	1114.4	1114.8	1115.1
155°	1151.8	1151.8	1151.8	1151.8	1151.9	1152.1	1152.3	1152.5	1152.8	1153.7	1154.6
157.5°	1186.8	1186.5	1186.3	1186.0	1186.0	1186.1	1186.3	1186.5	1186.7	1187.6	1188.6
160°	1208.9	1208.4	1207.9	1207.4	1207.2	1207.2	1207.2	1207.2	1207.2	1208.4	1209.5
162.5°	1228.4	1227.7	1227.1	1226.5	1226.2	1226.5	1226.6	1226.8	1226.9	1228.1	1229.2
165°	1253.8	1253.2	1252.4	1251.8	1251.4	1251.4	1251.4	1251.4	1251.4	1252.8	1254.2
167.5°	1273.9	1273.0	1272.1	1271.2	1270.8	1271.0	1271.2	1271.4	1271.5	1273.0	1274.4
170°	1285.5	1284.5	1283.7	1282.7	1282.2	1282.2	1282.2	1282.2	1282.2	1283.8	1285.5
172.5°	1294.5	1293.6	1292.7	1291.7	1291.3	1291.3	1291.3	1291.3	1291.3	1292.7	1294.1
175°	1303.9	1303.1	1302.1	1301.2	1300.8	1300.8	1300.8	1300.8	1300.8	1302.1	1303.5
177.5°	1308.1	1307.3	1306.5	1305.8	1305.4	1305.4	1305.4	1305.4	1305.4	1306.5	1307.7
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1352.3	1352.7	1358.3	1362.2	1360.3	1362.7	1363.7
5°	1477.4	1499.8	1511.6	1520.4	1521.0	1521.6	1526.6
7.5°	1654.9	1678.9	1696.5	1723.1	1731.1	1740.1	1737.5
10°	1784.4	1819.8	1850.4	1866.5	1884.0	1909.5	1889.0
12.5°	1905.4	1968.3	2014.7	2039.9	2056.3	2061.4	2051.4
15°	2105.0	2187.1	2231.3	2230.2	2286.2	2310.5	2272.5
17.5°	2288.1	2363.9	2424.6	2455.8	2502.4	2512.8	2508.0
20°	2400.1	2482.9	2530.2	2583.8	2608.0	2629.8	2633.5
22.5°	2496.7	2571.0	2621.9	2666.4	2686.8	2697.1	2703.3
25°	2596.2	2654.8	2685.3	2700.8	2706.4	2705.1	2697.1
27.5°	2589.3	2593.8	2560.3	2527.2	2497.8	2464.5	2453.0
30°	2522.1	2469.8	2376.5	2323.5	2245.7	2184.0	2208.9
32.5°	2345.3	2241.2	2136.4	2020.7	1924.9	1897.7	1870.3
35°	2001.6	1818.6	1711.5	1587.0	1537.2	1487.4	1453.1
37.5°	1619.4	1477.8	1350.8	1269.3	1219.4	1187.9	1171.0
40°	1400.2	1272.6	1168.0	1102.0	1064.0	1028.5	1023.6
42.5°	1225.4	1106.8	1028.0	975.5	939.0	923.9	913.0
45°	1003.6	920.8	867.9	830.5	806.3	796.9	784.5
47.5°	849.5	790.9	751.2	725.8	707.5	700.5	699.6
50°	763.3	714.7	685.5	665.5	651.3	648.7	638.8
52.5°	698.5	656.5	633.7	616.2	605.9	599.0	596.0
55°	606.4	578.4	557.9	547.9	539.8	532.9	532.9
57.5°	530.6	507.2	493.6	485.1	482.6	477.8	474.7
60°	483.8	463.8	453.3	445.8	440.8	441.4	435.8
62.5°	437.9	425.0	414.9	407.4	401.5	401.6	402.0
65°	373.0	363.0	355.5	353.0	349.3	344.9	346.2
67.5°	316.0	306.7	300.9	296.6	295.3	293.0	296.6
70°	275.2	268.3	264.0	260.2	259.0	259.6	262.8
72.5°	237.8	233.0	230.1	228.4	225.6	225.8	227.8
75°	186.8	183.1	180.5	178.7	178.1	178.1	178.1
77.5°	137.2	136.3	135.2	132.5	132.6	133.3	133.5
80°	108.4	106.5	105.8	104.6	102.7	101.5	104.6
82.5°	81.0	79.1	78.4	78.2	75.3	75.1	77.7
85°	43.6	41.7	42.3	41.7	41.7	41.1	41.1
87.5°	20.9	20.6	20.3	20.8	20.4	20.0	21.1
90°	27.4	28.3	29.0	29.5	29.9	30.3	30.8
92.5°	41.7	42.4	42.6	42.3	42.1	41.7	41.5
95°	78.7	79.7	80.2	80.2	80.2	80.2	80.2
97.5°	122.2	123.2	123.7	123.6	123.5	123.4	123.3
100°	153.0	153.8	154.3	154.8	155.3	155.7	156.1
102.5°	189.3	190.0	190.2	190.1	190.0	190.0	189.9
105°	242.5	242.5	242.7	243.2	243.6	244.1	244.5
107.5°	301.6	302.3	302.5	302.3	302.0	301.7	301.4
110°	340.8	341.7	341.9	341.4	341.0	340.6	340.1



TEST NUMBER: P332229-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	379.9	381.0	381.5	381.4	381.4	381.3	381.2
115°	438.4	438.6	438.6	438.4	438.2	437.9	437.7
117.5°	498.0	497.9	497.6	496.9	496.3	495.7	495.0
120°	537.7	537.5	537.1	536.7	536.2	535.8	535.3
122.5°	577.7	577.1	576.5	575.8	575.2	574.6	573.9
125°	637.4	636.4	635.6	634.6	633.7	632.8	631.8
127.5°	696.2	695.0	693.8	692.8	691.7	690.7	689.6
130°	736.0	735.1	733.8	732.2	730.6	729.0	727.5
132.5°	774.0	773.0	771.8	770.6	769.4	768.1	766.9
135°	831.6	830.6	830.0	829.5	829.0	828.5	828.1
137.5°	887.5	886.5	885.7	884.8	883.9	883.0	882.2
140°	925.0	924.8	923.9	922.3	920.7	919.1	917.5
142.5°	959.6	959.3	958.6	957.4	956.2	954.9	953.7
145°	1010.3	1010.1	1009.6	1008.6	1007.7	1006.8	1005.8
147.5°	1058.4	1058.4	1057.8	1056.5	1055.0	1053.7	1052.3
150°	1088.1	1088.1	1087.3	1086.0	1084.7	1083.2	1081.9
152.5°	1115.5	1115.8	1115.4	1114.2	1113.0	1111.8	1110.6
155°	1155.6	1156.4	1156.1	1154.5	1152.9	1151.3	1149.7
157.5°	1189.5	1190.6	1190.3	1189.1	1187.8	1186.5	1185.3
160°	1210.7	1211.8	1212.0	1211.0	1210.1	1209.2	1208.2
162.5°	1230.4	1231.5	1231.4	1229.9	1228.4	1227.0	1225.5
165°	1255.5	1256.9	1256.8	1255.2	1253.6	1252.0	1250.4
167.5°	1275.8	1277.2	1277.2	1275.8	1274.4	1273.0	1271.5
170°	1287.1	1288.6	1288.6	1287.1	1285.5	1283.8	1282.2
172.5°	1295.5	1297.0	1296.9	1295.3	1293.6	1292.0	1290.5
175°	1304.9	1306.2	1306.1	1304.5	1302.9	1301.3	1299.7
177.5°	1308.8	1309.9	1309.8	1308.4	1307.2	1305.9	1304.6
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0

(END OF REPORT)