

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332214-927

Luminaire Tested: **S123DIW-S1165D460U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332214-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1165D460U927-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 460 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5230.6 lumens  
Efficiency: N/A  
Efficacy: 99.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332214-927

CATALOG NUMBER: S123DIW-S1165D460U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332214-927

CATALOG NUMBER: S123DIW-S1165D460U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72
1	103	98	94	90	97	93	90	86	84	81	79	75	73	71	67	66	64	61
2	93	86	79	74	88	81	76	71	73	69	65	66	63	59	59	57	54	51
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	53	49	46	43
4	78	67	58	52	74	64	56	50	58	52	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	42	37	42	38	35	32
6	66	54	45	39	63	51	43	38	47	40	35	42	37	33	38	34	30	28
7	61	49	40	34	58	46	39	33	42	36	31	39	33	29	35	31	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	40	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15588	15588	15588
5°	15662	15446	15554
10°	15557	15312	15407
15°	15375	15139	15166
20°	15163	14892	14905
25°	14878	14598	14567
30°	14564	14270	14162
35°	14236	13925	13745
40°	13893	13543	13333
45°	13516	13192	12871
50°	13137	12762	12407
55°	12643	12314	11941
60°	12144	11795	11418
65°	11703	11227	10878
70°	11053	10581	10112
75°	10098	9736	9320
80°	9106	8722	8647
85°	7991	7694	7385



TEST NUMBER: P332214-927

CATALOG NUMBER: S123DIW-S1165D460U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.4	2.6
10°-20°	385.2	7.4
20°-30°	569.0	10.9
30°-40°	664.6	12.7
40°-50°	668.2	12.8
50°-60°	587.0	11.2
60°-70°	437.3	8.4
70°-80°	249.1	4.8
80°-90°	72.9	1.4
90°-100°	17.4	0.3
100°-110°	83.0	1.6
110°-120°	199.4	3.8
120°-130°	253.9	4.9
130°-140°	271.3	5.2
140°-150°	253.7	4.8
150°-160°	204.6	3.9
160°-170°	132.1	2.5
170°-180°	45.5	0.9
0°-30°	1090.6	20.9
0°-40°	1755.3	33.6
0°-60°	3010.4	57.6
0°-90°	3769.7	72.1
90°-120°	299.8	5.7
90°-150°	1078.7	20.6
90°-180°	1461.0	27.9
0°-180°	5230.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1448	1448	1448	1448	1448	
5°	1450	1443	1430	1441	1440	137
15°	1380	1374	1358	1368	1361	389
25°	1253	1245	1229	1230	1226	577
35°	1083	1075	1060	1052	1046	677
45°	888	882	867	852	846	685
55°	674	672	656	643	636	603
65°	460	453	441	431	427	453
75°	243	238	234	228	224	260
85°	65	62	62	60	60	71
90°	0	4	9	10	11	5
95°	22	8	11	13	14	27
105°	106	108	78	18	16	112
115°	199	201	204	208	209	196
125°	280	283	285	285	286	250
135°	349	351	353	354	353	269
145°	403	405	406	407	407	252
155°	444	443	444	445	443	204
165°	468	467	467	469	467	132
175°	479	477	478	480	477	46
180°	479	479	479	479	479	



TEST NUMBER: P332214-927

CATALOG NUMBER: S123DIW-S1165D460U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1453.2	1452.3	1451.4	1450.6	1449.6	1448.0	1445.6	1443.1	1440.7	1438.2	1440.4
5°	1449.5	1448.1	1446.7	1445.3	1443.9	1441.7	1438.7	1435.6	1432.6	1429.5	1432.3
7.5°	1435.3	1433.8	1432.5	1431.1	1429.7	1427.4	1424.3	1421.2	1418.0	1414.8	1417.3
10°	1423.3	1421.9	1420.5	1419.1	1417.8	1415.3	1411.7	1408.1	1404.5	1400.9	1403.4
12.5°	1407.4	1406.2	1405.0	1403.9	1402.7	1400.4	1397.1	1393.7	1390.3	1387.0	1388.8
15°	1379.7	1378.6	1377.5	1376.4	1375.3	1372.9	1369.4	1365.7	1362.2	1358.5	1360.7
17.5°	1347.6	1346.2	1344.7	1343.3	1341.8	1339.3	1335.7	1332.1	1328.5	1324.9	1326.5
20°	1323.7	1322.0	1320.3	1318.7	1317.1	1314.4	1310.8	1307.3	1303.6	1300.1	1301.2
22.5°	1296.8	1295.1	1293.5	1291.8	1290.1	1287.5	1283.9	1280.3	1276.8	1273.1	1274.0
25°	1252.7	1251.0	1249.4	1247.7	1246.1	1243.4	1239.8	1236.3	1232.6	1229.1	1229.3
27.5°	1205.6	1204.0	1202.5	1200.8	1199.2	1196.5	1192.6	1188.7	1184.9	1181.0	1181.2
30°	1171.8	1170.4	1169.0	1167.6	1166.3	1163.6	1159.8	1155.9	1152.0	1148.1	1148.1
32.5°	1137.9	1136.1	1134.2	1132.4	1130.6	1128.1	1125.2	1122.2	1119.2	1116.3	1114.7
35°	1083.4	1081.7	1080.1	1078.4	1076.7	1074.1	1070.5	1066.9	1063.3	1059.7	1058.0
37.5°	1027.5	1025.5	1023.3	1021.3	1019.1	1016.3	1012.6	1009.0	1005.4	1001.6	999.7
40°	988.7	987.1	985.4	983.7	982.1	979.3	975.4	971.5	967.7	963.8	961.6
42.5°	949.8	948.0	946.1	944.2	942.3	939.4	935.6	931.7	927.8	924.0	921.8
45°	887.9	886.8	885.7	884.6	883.4	881.1	877.5	873.9	870.3	866.6	863.4
47.5°	826.3	824.7	823.2	821.5	819.9	817.5	814.0	810.6	807.3	803.9	800.7
50°	784.5	783.2	781.7	780.4	779.0	776.5	772.9	769.3	765.6	762.1	759.1
52.5°	740.7	739.7	738.8	737.8	736.9	734.5	730.7	726.9	723.1	719.2	716.6
55°	673.7	673.4	673.1	672.9	672.6	670.7	667.0	663.5	659.8	656.2	653.2
57.5°	609.9	609.0	608.0	607.1	606.2	604.3	601.3	598.5	595.6	592.7	590.0
60°	564.1	563.8	563.6	563.2	563.0	561.2	557.9	554.5	551.2	547.9	545.4
62.5°	523.2	522.5	521.8	521.1	520.4	518.3	515.0	511.7	508.4	505.1	502.6
65°	459.5	458.1	456.7	455.3	453.9	451.9	449.1	446.3	443.5	440.8	438.6
67.5°	392.0	390.8	389.6	388.3	387.1	385.5	383.3	381.3	379.1	377.1	375.1
70°	351.2	349.5	347.8	346.2	344.5	342.9	341.2	339.5	337.9	336.2	334.3
72.5°	308.3	307.1	305.9	304.7	303.5	301.9	300.0	298.1	296.3	294.4	292.6
75°	242.8	241.7	240.6	239.5	238.4	237.4	236.6	235.8	235.0	234.1	232.7
77.5°	184.8	184.2	183.5	183.0	182.4	181.6	180.5	179.6	178.6	177.6	176.7
80°	146.9	146.1	145.3	144.4	143.6	142.9	142.4	141.8	141.2	140.7	140.5
82.5°	110.1	109.9	109.7	109.6	109.4	109.2	109.2	109.1	108.9	108.8	108.4
85°	64.7	64.2	63.6	63.1	62.5	62.3	62.3	62.3	62.3	62.3	61.7
87.5°	26.0	25.4	25.0	24.5	23.9	23.7	23.7	23.7	23.6	23.6	23.4
90°	0.3	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.5	8.6	8.9
92.5°	6.7	6.4	6.2	5.9	5.7	6.0	6.8	7.5	8.3	9.1	9.6
95°	21.7	18.5	15.2	12.0	8.7	7.5	8.4	9.3	10.1	11.0	11.6
97.5°	43.6	42.1	40.7	39.3	37.8	34.2	28.5	22.8	17.2	11.5	12.1
100°	60.1	61.7	63.3	64.9	66.5	61.1	48.8	36.4	24.1	11.7	12.4
102.5°	78.9	80.1	81.2	82.4	83.5	77.3	63.8	50.4	36.9	23.4	21.5
105°	106.1	106.9	107.8	108.7	109.6	106.4	99.3	92.2	85.1	78.0	63.9
107.5°	134.7	135.4	136.1	136.7	137.4	138.4	139.5	140.6	141.7	142.8	132.6
110°	153.8	154.4	155.0	155.7	156.3	157.0	157.9	158.8	159.6	160.5	157.9



TEST NUMBER: P332214-927

CATALOG NUMBER: S123DIW-S1165D460U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.0	172.5	173.1	173.6	174.3	175.0	175.9	176.7	177.6	178.5	178.5
115°	198.9	199.4	199.9	200.3	200.8	201.5	202.2	202.9	203.6	204.3	205.1
117.5°	225.1	225.7	226.2	226.8	227.4	227.9	228.2	228.6	229.0	229.3	230.0
120°	241.3	242.0	242.7	243.4	244.2	244.6	244.9	245.1	245.3	245.6	246.2
122.5°	257.9	258.4	259.0	259.6	260.2	260.6	260.9	261.2	261.5	261.8	262.2
125°	280.4	281.1	281.7	282.3	283.0	283.4	283.8	284.1	284.4	284.7	284.9
127.5°	302.4	303.0	303.6	304.3	304.9	305.4	305.8	306.2	306.6	307.0	307.2
130°	316.1	316.7	317.3	318.0	318.6	319.1	319.4	319.7	320.0	320.3	320.6
132.5°	329.2	329.8	330.4	331.1	331.7	332.1	332.4	332.6	332.9	333.1	333.4
135°	349.1	349.6	350.1	350.5	351.0	351.4	351.7	352.0	352.4	352.7	352.9
137.5°	366.2	366.9	367.4	368.0	368.6	369.0	369.2	369.4	369.6	369.7	370.1
140°	377.6	378.1	378.6	379.1	379.5	379.9	380.1	380.3	380.6	380.8	381.1
142.5°	388.2	388.6	389.1	389.6	390.1	390.4	390.6	390.9	391.1	391.3	391.6
145°	402.9	403.5	404.0	404.6	405.1	405.4	405.6	405.8	405.9	406.1	406.2
147.5°	416.8	417.2	417.5	417.9	418.2	418.5	418.7	418.8	419.0	419.1	419.3
150°	425.3	425.6	425.8	426.0	426.3	426.4	426.6	426.7	426.9	427.1	427.2
152.5°	433.0	433.1	433.2	433.3	433.5	433.6	433.6	433.7	433.8	434.0	434.2
155°	443.8	443.6	443.5	443.4	443.2	443.1	443.2	443.3	443.4	443.5	443.9
157.5°	452.3	452.2	452.2	452.2	452.2	452.1	452.0	451.9	451.9	451.8	452.3
160°	457.3	457.2	457.2	457.1	457.0	456.9	456.9	456.8	456.7	456.6	457.1
162.5°	462.2	462.0	461.8	461.6	461.4	461.2	461.1	461.1	461.0	460.9	461.4
165°	468.0	467.8	467.5	467.3	467.1	466.9	466.8	466.8	466.7	466.6	467.2
167.5°	472.6	472.3	472.0	471.7	471.3	471.2	471.2	471.2	471.2	471.2	471.8
170°	475.2	474.8	474.5	474.2	473.9	473.7	473.7	473.7	473.7	473.7	474.4
172.5°	476.8	476.5	476.1	475.7	475.3	475.2	475.2	475.3	475.4	475.4	476.0
175°	479.0	478.6	478.2	477.8	477.4	477.3	477.4	477.4	477.5	477.6	478.2
177.5°	479.6	479.3	479.0	478.6	478.3	478.2	478.3	478.3	478.4	478.5	479.0
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332214-927

CATALOG NUMBER: S123DIW-S1165D460U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1442.6	1444.9	1447.1	1448.1	1447.9	1447.6	1447.4	1447.2
5°	1435.0	1437.8	1440.6	1441.7	1441.1	1440.6	1440.0	1439.5
7.5°	1419.8	1422.3	1424.8	1425.8	1425.5	1425.2	1424.9	1424.6
10°	1405.9	1408.3	1410.9	1411.8	1411.3	1410.7	1410.2	1409.6
12.5°	1390.6	1392.4	1394.2	1395.0	1394.6	1394.3	1394.0	1393.7
15°	1362.9	1365.2	1367.4	1367.7	1366.0	1364.4	1362.7	1361.0
17.5°	1328.0	1329.6	1331.1	1331.6	1331.0	1330.4	1329.8	1329.2
20°	1302.3	1303.4	1304.5	1304.6	1303.8	1302.9	1302.1	1301.2
22.5°	1274.9	1275.8	1276.7	1276.6	1275.6	1274.5	1273.4	1272.4
25°	1229.6	1229.9	1230.2	1229.9	1229.1	1228.2	1227.4	1226.5
27.5°	1181.5	1181.6	1181.9	1181.5	1180.4	1179.3	1178.3	1177.3
30°	1148.1	1148.1	1148.1	1147.2	1145.2	1143.3	1141.3	1139.4
32.5°	1113.1	1111.6	1110.0	1108.7	1107.7	1106.6	1105.6	1104.5
35°	1056.4	1054.7	1053.0	1051.5	1050.1	1048.8	1047.3	1046.0
37.5°	997.7	995.7	993.7	992.3	991.3	990.5	989.6	988.7
40°	959.4	957.2	955.0	953.3	952.2	951.1	950.0	948.9
42.5°	919.6	917.3	915.1	913.5	912.4	911.2	910.1	909.0
45°	860.1	856.7	853.4	851.0	849.7	848.3	846.9	845.5
47.5°	797.4	794.2	790.8	788.6	787.4	786.2	785.0	783.8
50°	756.0	753.0	749.9	747.6	745.9	744.3	742.6	740.9
52.5°	714.1	711.5	708.8	706.7	705.0	703.4	701.7	700.1
55°	650.1	647.1	644.0	641.8	640.5	639.1	637.7	636.3
57.5°	587.3	584.6	581.9	579.7	578.1	576.6	574.9	573.3
60°	543.0	540.4	538.0	536.0	534.6	533.2	531.9	530.4
62.5°	500.1	497.6	495.1	493.4	492.4	491.5	490.6	489.6
65°	436.4	434.2	432.0	430.5	429.6	428.8	427.9	427.1
67.5°	373.2	371.2	369.3	367.7	366.6	365.4	364.2	363.1
70°	332.3	330.4	328.4	326.8	325.4	324.0	322.7	321.3
72.5°	291.0	289.2	287.5	286.3	285.6	284.9	284.2	283.4
75°	231.3	230.0	228.5	227.4	226.6	225.8	225.0	224.1
77.5°	175.7	174.8	173.8	173.3	173.3	173.3	173.3	173.3
80°	140.1	139.9	139.6	139.5	139.5	139.5	139.5	139.5
82.5°	107.8	107.3	106.9	106.5	106.2	106.1	105.8	105.6
85°	61.2	60.6	60.0	59.8	59.8	59.8	59.8	59.8
87.5°	23.3	23.1	23.0	22.9	23.0	23.0	23.1	23.1
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.1	10.6	11.2	11.4	11.6	11.6	11.7	11.8
95°	12.1	12.7	13.2	13.5	13.5	13.5	13.5	13.5
97.5°	12.8	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.0	13.6	14.3	14.7	14.7	14.8	14.9	15.0
102.5°	19.5	17.5	15.6	14.7	14.8	15.0	15.1	15.2
105°	49.9	36.0	21.9	15.1	15.2	15.4	15.5	15.7
107.5°	122.3	112.1	101.8	91.4	80.8	70.3	59.7	49.2
110°	155.3	152.7	150.0	143.1	131.8	120.5	109.2	97.9





TEST NUMBER: P332214-927

CATALOG NUMBER: S123DIW-S1165D460U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	178.6	178.6	178.6	177.4	175.1	172.7	170.3	167.9
115°	205.9	206.7	207.5	208.0	208.3	208.7	209.0	209.3
117.5°	230.6	231.2	231.9	232.2	232.3	232.3	232.4	232.5
120°	246.8	247.5	248.1	248.4	248.4	248.4	248.4	248.4
122.5°	262.7	263.2	263.6	263.8	263.9	264.0	264.0	264.1
125°	285.0	285.2	285.3	285.5	285.7	285.8	286.0	286.1
127.5°	307.4	307.7	307.9	308.0	307.8	307.7	307.5	307.4
130°	320.9	321.2	321.5	321.6	321.5	321.3	321.2	321.0
132.5°	333.7	334.1	334.4	334.5	334.2	334.0	333.7	333.6
135°	353.2	353.4	353.6	353.6	353.4	353.2	352.9	352.7
137.5°	370.5	370.8	371.2	371.4	371.2	371.1	370.9	370.7
140°	381.4	381.8	382.1	382.1	382.0	381.8	381.7	381.5
142.5°	391.9	392.1	392.4	392.4	392.1	392.0	391.7	391.5
145°	406.4	406.5	406.7	406.8	406.8	406.8	406.8	406.8
147.5°	419.5	419.6	419.8	419.6	419.3	418.9	418.6	418.2
150°	427.4	427.5	427.7	427.7	427.5	427.2	427.0	426.7
152.5°	434.5	434.7	435.1	435.0	434.7	434.3	434.0	433.6
155°	444.3	444.7	445.0	445.0	444.5	444.0	443.5	443.1
157.5°	452.7	453.2	453.7	453.6	453.0	452.4	451.8	451.1
160°	457.6	458.0	458.5	458.5	458.0	457.4	456.9	456.3
162.5°	462.0	462.6	463.0	463.1	462.6	462.1	461.6	461.1
165°	467.9	468.5	469.1	469.1	468.6	468.1	467.5	467.0
167.5°	472.5	473.0	473.6	473.6	473.0	472.5	471.8	471.2
170°	475.0	475.6	476.3	476.3	475.6	475.0	474.4	473.7
172.5°	476.7	477.3	477.9	477.9	477.2	476.5	475.9	475.2
175°	478.7	479.3	479.8	479.8	479.2	478.6	477.9	477.3
177.5°	479.5	480.0	480.5	480.5	479.8	479.2	478.6	477.9
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0

(END OF REPORT)