

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332216-927

Luminaire Tested: **S123DIW-S1165D755U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332216-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D755U927-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6273.5 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	60	59	57	53
2	92	85	79	73	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	67	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	42	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	35	38	35	32	29
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25	23
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13832	13832	13832	13832
5°	16495	13891	12310	13891
10°	20647	13821	11119	13821
15°	25324	13710	10351	13710
20°	30166	13536	9856	13536
25°	32033	13324	9745	13324
30°	27455	13170	9797	13170
35°	19094	12951	9900	12951
40°	14383	12694	9868	12694
45°	11942	12310	9742	12310
50°	10697	11531	9656	11531
55°	10001	10691	9533	10691
60°	9382	9810	9436	9810
65°	8818	8945	9133	8945
70°	8271	7956	8699	7956
75°	7407	6966	7977	6966
80°	6484	5709	6868	5709
85°	5076	4150	4619	4150



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.6	2.0
10°-20°	405.9	6.5
20°-30°	681.2	10.9
30°-40°	771.4	12.3
40°-50°	691.7	11.0
50°-60°	558.2	8.9
60°-70°	389.0	6.2
70°-80°	204.5	3.3
80°-90°	52.2	0.8
90°-100°	28.5	0.5
100°-110°	136.0	2.2
110°-120°	326.6	5.2
120°-130°	415.9	6.6
130°-140°	444.3	7.1
140°-150°	415.5	6.6
150°-160°	335.2	5.3
160°-170°	216.3	3.4
170°-180°	74.5	1.2
0°-30°	1213.7	19.3
0°-40°	1985.1	31.6
0°-60°	3235.0	51.6
0°-90°	3880.7	61.9
90°-120°	491.1	7.8
90°-150°	1766.8	28.2
90°-180°	2393.0	38.1
0°-180°	6273.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1285	1285	1285	1285	1285	
5°	1527	1286	1139	1286	1527	158
15°	2272	1230	929	1230	2272	656
25°	2697	1122	820	1122	2697	1183
35°	1453	986	753	986	1453	944
45°	784	809	640	809	784	621
55°	533	570	508	570	533	478
65°	346	351	359	351	346	345
75°	178	168	192	168	178	191
85°	41	34	37	34	41	49
90°	18	1	18	1	18	10
95°	22	36	22	36	22	19
105°	26	174	26	174	26	59
115°	343	326	343	326	343	317
125°	469	459	469	459	469	419
135°	578	572	578	572	578	445
145°	666	660	666	660	666	416
155°	726	727	726	727	726	335
165°	765	767	765	767	765	216
175°	782	785	782	785	782	74
180°	785	785	785	785	785	



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1363.7	1362.7	1360.3	1362.2	1358.3	1352.7	1352.3	1347.3	1332.8	1331.8	1327.9
5°	1526.6	1521.6	1521.0	1520.4	1511.6	1499.8	1477.4	1475.5	1445.7	1430.7	1412.7
7.5°	1737.5	1740.1	1731.1	1723.1	1696.5	1678.9	1654.9	1624.1	1587.4	1550.1	1525.3
10°	1889.0	1909.5	1884.0	1866.5	1850.4	1819.8	1784.4	1740.1	1695.9	1644.3	1605.0
12.5°	2051.4	2061.4	2056.3	2039.9	2014.7	1968.3	1905.4	1856.7	1816.0	1730.0	1695.2
15°	2272.5	2310.5	2286.2	2230.2	2231.3	2187.1	2105.0	2014.7	1966.8	1891.4	1788.7
17.5°	2508.0	2512.8	2502.4	2455.8	2424.6	2363.9	2288.1	2201.5	2104.4	2013.3	1904.2
20°	2633.5	2629.8	2608.0	2583.8	2530.2	2482.9	2400.1	2303.6	2179.1	2089.5	1970.5
22.5°	2703.3	2697.1	2686.8	2666.4	2621.9	2571.0	2496.7	2391.3	2272.7	2149.2	2011.8
25°	2697.1	2705.1	2706.4	2700.8	2685.3	2654.8	2596.2	2512.2	2393.9	2235.1	2091.9
27.5°	2453.0	2464.5	2497.8	2527.2	2560.3	2593.8	2589.3	2547.7	2460.1	2323.0	2147.9
30°	2208.9	2184.0	2245.7	2323.5	2376.5	2469.8	2522.1	2525.2	2476.0	2358.4	2187.8
32.5°	1870.3	1897.7	1924.9	2020.7	2136.4	2241.2	2345.3	2429.1	2438.7	2360.4	2211.2
35°	1453.1	1487.4	1537.2	1587.0	1711.5	1818.6	2001.6	2161.0	2288.1	2304.9	2213.3
37.5°	1171.0	1187.9	1219.4	1269.3	1350.8	1477.8	1619.4	1820.8	2004.9	2141.7	2147.7
40°	1023.6	1028.5	1064.0	1102.0	1168.0	1272.6	1400.2	1578.3	1798.6	1989.8	2069.5
42.5°	913.0	923.9	939.0	975.5	1028.0	1106.8	1225.4	1372.5	1574.5	1794.5	1950.4
45°	784.5	796.9	806.3	830.5	867.9	920.8	1003.6	1138.1	1291.9	1519.1	1728.9
47.5°	699.6	700.5	707.5	725.8	751.2	790.9	849.5	935.9	1077.1	1261.4	1476.8
50°	638.8	648.7	651.3	665.5	685.5	714.7	763.3	836.8	952.6	1114.4	1312.4
52.5°	596.0	599.0	605.9	616.2	633.7	656.5	698.5	756.1	847.0	984.9	1167.0
55°	532.9	532.9	539.8	547.9	557.9	578.4	606.4	648.7	717.9	824.9	975.6
57.5°	474.7	477.8	482.6	485.1	493.6	507.2	530.6	562.7	614.3	696.6	816.5
60°	435.8	441.4	440.8	445.8	453.3	463.8	483.8	509.9	556.0	621.9	722.9
62.5°	402.0	401.6	401.5	407.4	414.9	425.0	437.9	460.6	499.7	558.3	644.1
65°	346.2	344.9	349.3	353.0	355.5	363.0	373.0	392.8	419.0	462.6	529.2
67.5°	296.6	293.0	295.3	296.6	300.9	306.7	316.0	328.4	349.1	384.1	434.4
70°	262.8	259.6	259.0	260.2	264.0	268.3	275.2	287.0	306.3	334.3	371.1
72.5°	227.8	225.8	225.6	228.4	230.1	233.0	237.8	248.7	264.0	285.0	319.2
75°	178.1	178.1	178.1	178.7	180.5	183.1	186.8	192.3	204.2	219.1	242.2
77.5°	133.5	133.3	132.6	132.5	135.2	136.3	137.2	142.4	149.0	159.1	175.9
80°	104.6	101.5	102.7	104.6	105.8	106.5	108.4	109.6	115.2	120.8	132.6
82.5°	77.7	75.1	75.3	78.2	78.4	79.1	81.0	82.7	84.8	89.9	96.3
85°	41.1	41.1	41.7	41.7	42.3	41.7	43.6	44.2	44.2	47.3	51.0
87.5°	18.5	17.4	17.8	18.3	17.7	18.1	18.5	18.9	19.3	19.7	19.9
90°	17.5	17.2	17.0	16.7	16.5	16.1	15.5	15.1	14.5	14.0	12.3
92.5°	19.3	19.2	19.0	18.9	18.7	18.2	17.4	16.6	15.8	14.9	13.6
95°	22.2	22.2	22.2	22.2	22.2	21.7	20.8	19.9	19.0	18.1	16.6
97.5°	24.0	23.9	23.8	23.6	23.5	22.9	21.9	20.8	19.8	18.8	28.1
100°	24.5	24.3	24.2	24.1	24.0	23.4	22.3	21.3	20.3	19.3	39.5
102.5°	25.0	24.7	24.5	24.2	24.0	25.5	28.8	31.9	35.2	38.3	60.4
105°	25.7	25.4	25.1	24.9	24.6	36.0	58.9	81.8	104.7	127.7	139.3
107.5°	80.6	97.8	115.1	132.4	149.7	166.8	183.5	200.3	217.1	234.0	232.2
110°	160.3	178.8	197.3	215.9	234.4	245.8	250.1	254.4	258.6	262.9	261.5



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.0	278.9	282.9	286.8	290.7	292.6	292.6	292.5	292.4	292.3	290.9
115°	342.8	342.2	341.7	341.2	340.7	339.8	338.5	337.2	335.9	334.6	333.4
117.5°	380.8	380.6	380.6	380.5	380.3	379.8	378.7	377.7	376.7	375.7	375.0
120°	406.9	406.9	406.9	406.9	406.9	406.4	405.4	404.3	403.3	402.2	401.9
122.5°	432.5	432.5	432.3	432.2	432.1	431.7	430.9	430.2	429.5	428.8	428.3
125°	468.7	468.4	468.2	467.9	467.6	467.4	467.1	466.8	466.6	466.4	465.8
127.5°	503.4	503.7	503.9	504.2	504.5	504.4	504.0	503.6	503.1	502.7	502.1
130°	525.8	526.1	526.3	526.6	526.9	526.7	526.2	525.7	525.1	524.7	524.1
132.5°	546.3	546.7	547.1	547.4	547.8	547.7	547.2	546.7	546.1	545.7	545.2
135°	577.7	578.1	578.5	578.8	579.2	579.2	578.8	578.5	578.1	577.7	577.2
137.5°	607.2	607.4	607.7	608.0	608.2	608.1	607.4	606.8	606.2	605.5	605.3
140°	624.9	625.2	625.4	625.7	626.0	625.8	625.3	624.8	624.2	623.8	623.4
142.5°	641.2	641.6	642.0	642.3	642.7	642.6	642.2	641.8	641.4	641.0	640.6
145°	666.3	666.3	666.3	666.3	666.3	666.1	665.9	665.7	665.4	665.1	664.9
147.5°	684.9	685.6	686.1	686.7	687.3	687.5	687.2	687.0	686.7	686.4	686.2
150°	698.9	699.3	699.7	700.1	700.5	700.5	700.3	700.1	699.8	699.5	699.3
152.5°	710.1	710.7	711.3	711.9	712.5	712.6	712.1	711.6	711.1	710.7	710.6
155°	725.7	726.5	727.3	728.1	728.9	729.0	728.3	727.6	727.0	726.4	726.2
157.5°	738.9	740.0	740.9	742.0	743.0	743.1	742.3	741.6	740.8	740.0	740.1
160°	747.3	748.2	749.2	750.0	751.0	751.0	750.3	749.5	748.7	747.9	748.1
162.5°	755.3	756.1	756.9	757.6	758.4	758.4	757.6	756.7	755.8	754.9	755.0
165°	764.8	765.7	766.6	767.5	768.4	768.3	767.3	766.3	765.2	764.2	764.4
167.5°	771.7	772.7	773.7	774.8	775.9	775.9	774.8	773.7	772.7	771.7	771.7
170°	775.9	776.9	777.9	779.0	780.1	780.1	779.0	777.9	776.9	775.9	775.9
172.5°	778.2	779.3	780.5	781.6	782.8	782.8	781.8	780.8	779.7	778.7	778.6
175°	781.7	782.8	783.8	784.8	785.8	785.9	785.1	784.1	783.2	782.3	782.2
177.5°	782.8	783.8	784.8	785.8	786.9	787.0	786.2	785.4	784.5	783.7	783.6
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1324.8	1320.9	1316.9	1310.0	1303.9	1295.5	1293.0	1290.0	1281.0	1273.1	1267.1
5°	1405.8	1390.8	1369.0	1349.2	1333.0	1311.2	1298.7	1285.6	1266.9	1250.1	1236.4
7.5°	1490.5	1461.1	1427.2	1390.6	1356.5	1323.7	1297.1	1273.4	1247.3	1222.5	1203.2
10°	1557.7	1515.4	1468.1	1417.1	1373.4	1331.1	1295.6	1264.5	1230.9	1201.6	1177.3
12.5°	1634.4	1571.7	1506.4	1444.4	1392.9	1334.1	1291.1	1251.6	1213.5	1178.2	1151.0
15°	1725.2	1645.5	1568.3	1483.0	1404.5	1331.1	1280.1	1230.3	1186.1	1149.9	1115.1
17.5°	1807.9	1717.6	1615.9	1512.1	1417.5	1330.4	1258.9	1202.6	1147.3	1103.1	1068.3
20°	1854.7	1752.0	1636.8	1529.1	1424.5	1327.4	1249.0	1181.7	1121.9	1075.2	1036.0
22.5°	1895.1	1774.9	1655.7	1540.6	1424.0	1319.4	1230.5	1161.3	1096.5	1050.8	1009.1
25°	1936.9	1793.1	1673.6	1538.4	1408.3	1300.0	1200.4	1121.9	1057.2	1003.6	960.7
27.5°	1972.8	1791.8	1650.0	1504.7	1383.6	1275.1	1168.7	1084.6	1015.8	957.7	914.1
30°	1996.6	1794.3	1625.6	1481.8	1359.8	1247.7	1144.3	1059.6	987.5	928.3	887.2
32.5°	2011.6	1792.8	1603.1	1449.9	1321.9	1222.7	1117.9	1030.2	956.1	897.9	858.3
35°	2020.3	1781.9	1564.6	1384.0	1260.8	1164.3	1076.5	985.6	907.8	853.6	808.7
37.5°	2002.9	1758.8	1519.7	1320.5	1185.6	1090.5	1016.7	939.2	864.7	805.2	766.5
40°	1975.5	1743.9	1484.9	1275.7	1133.8	1042.2	979.4	903.4	829.9	773.2	737.1
42.5°	1923.2	1713.5	1446.5	1225.9	1080.0	988.4	930.5	867.0	797.6	744.3	708.3
45°	1795.6	1647.3	1389.0	1151.2	1000.5	905.9	854.8	808.7	745.8	694.2	663.1
47.5°	1618.5	1547.9	1305.8	1072.4	917.6	826.6	773.5	736.4	690.5	648.7	618.9
50°	1495.5	1466.2	1249.5	1018.6	862.3	773.2	722.2	688.6	655.6	613.9	586.5
52.5°	1353.5	1371.6	1183.8	962.7	806.0	718.5	670.4	643.7	613.8	579.5	555.6
55°	1153.7	1219.0	1070.2	869.1	722.2	638.8	593.3	569.7	552.2	526.7	506.2
57.5°	966.5	1049.7	947.5	772.6	639.9	567.9	524.3	498.6	487.4	474.0	457.9
60°	855.5	937.6	859.8	707.9	584.6	516.1	477.5	455.7	444.5	435.2	421.5
62.5°	756.3	839.5	774.1	642.1	530.3	466.8	433.2	411.9	403.2	398.3	386.7
65°	620.1	691.7	648.1	539.8	452.7	396.6	366.1	351.2	343.0	341.2	333.7
67.5°	504.7	559.2	527.4	447.7	379.1	330.7	304.8	292.2	285.9	285.3	279.6
70°	429.0	480.0	455.7	383.5	324.4	286.4	264.0	252.8	249.1	248.4	245.3
72.5°	370.2	405.8	386.5	326.2	280.5	246.1	229.6	217.9	213.7	214.5	212.5
75°	273.9	300.7	289.5	247.8	211.0	188.6	174.9	167.5	163.7	165.6	163.1
77.5°	197.1	214.0	204.0	175.1	152.4	136.3	126.1	121.5	118.2	118.0	116.9
80°	148.8	158.8	153.1	135.7	117.1	103.4	95.2	92.1	90.3	89.7	89.0
82.5°	106.0	114.5	107.8	95.9	83.2	74.9	70.3	66.2	64.9	65.3	64.6
85°	53.6	56.6	54.2	46.7	41.7	37.9	35.5	33.6	32.4	33.0	31.8
87.5°	20.5	20.7	18.9	16.6	15.4	13.5	13.3	12.0	11.3	11.6	11.3
90°	10.6	9.0	7.3	5.8	4.4	3.2	1.9	0.6	1.9	3.2	4.4
92.5°	12.4	11.1	9.8	9.4	9.7	10.1	10.5	10.9	10.5	10.1	9.7
95°	15.2	13.8	12.4	14.3	19.6	25.0	30.3	35.6	30.3	25.0	19.6
97.5°	37.4	46.7	56.1	61.9	64.3	66.7	69.1	71.5	69.1	66.7	64.3
100°	59.7	79.9	100.1	108.8	106.3	103.7	101.1	98.5	101.1	103.7	106.3
102.5°	82.5	104.6	126.7	136.7	134.9	133.0	131.2	129.3	131.2	133.0	134.9
105°	151.0	162.6	174.3	179.4	178.0	176.6	175.2	173.7	175.2	176.6	178.0
107.5°	230.3	228.5	226.6	225.1	224.0	222.8	221.7	220.5	221.7	222.8	224.0
110°	260.1	258.6	257.2	256.0	254.9	253.9	252.9	251.8	252.9	253.9	254.9



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	289.5	288.0	286.6	285.4	284.5	283.5	282.6	281.7	282.6	283.5	284.5
115°	332.2	331.1	329.9	329.0	328.2	327.4	326.6	325.8	326.6	327.4	328.2
117.5°	374.5	373.8	373.3	372.5	371.5	370.6	369.6	368.7	369.6	370.6	371.5
120°	401.5	401.1	400.7	399.9	398.7	397.6	396.4	395.2	396.4	397.6	398.7
122.5°	427.9	427.3	426.8	426.1	425.2	424.2	423.3	422.3	423.3	424.2	425.2
125°	465.3	464.8	464.3	463.5	462.5	461.4	460.4	459.4	460.4	461.4	462.5
127.5°	501.5	500.9	500.3	499.4	498.4	497.3	496.3	495.3	496.3	497.3	498.4
130°	523.6	523.1	522.6	521.8	520.8	519.8	518.7	517.6	518.7	519.8	520.8
132.5°	544.8	544.4	544.0	543.3	542.2	541.1	540.1	539.1	540.1	541.1	542.2
135°	576.6	576.2	575.6	575.0	574.2	573.4	572.7	571.9	572.7	573.4	574.2
137.5°	605.0	604.7	604.4	603.8	602.8	601.8	600.8	599.8	600.8	601.8	602.8
140°	623.0	622.6	622.2	621.6	620.8	620.0	619.2	618.5	619.2	620.0	620.8
142.5°	640.2	639.8	639.4	638.9	638.1	637.3	636.5	635.7	636.5	637.3	638.1
145°	664.6	664.3	664.1	663.5	662.6	661.7	660.8	659.9	660.8	661.7	662.6
147.5°	686.0	685.7	685.4	685.0	684.4	683.8	683.2	682.6	683.2	683.8	684.4
150°	699.0	698.8	698.5	698.2	697.8	697.4	697.0	696.6	697.0	697.4	697.8
152.5°	710.4	710.3	710.1	710.0	709.7	709.6	709.4	709.2	709.4	709.6	709.7
155°	726.1	726.0	725.8	725.9	726.1	726.4	726.7	726.9	726.7	726.4	726.1
157.5°	740.2	740.4	740.5	740.6	740.6	740.6	740.7	740.7	740.7	740.6	740.6
160°	748.1	748.3	748.5	748.5	748.7	748.8	748.9	749.1	748.9	748.8	748.7
162.5°	755.2	755.3	755.4	755.7	756.0	756.3	756.7	757.0	756.7	756.3	756.0
165°	764.5	764.6	764.8	765.0	765.4	765.8	766.2	766.6	766.2	765.8	765.4
167.5°	771.7	771.7	771.7	772.0	772.5	773.0	773.5	774.0	773.5	773.0	772.5
170°	775.9	775.9	775.9	776.2	776.7	777.2	777.7	778.2	777.7	777.2	776.7
172.5°	778.5	778.4	778.2	778.6	779.2	779.7	780.4	781.0	780.4	779.7	779.2
175°	782.0	781.9	781.8	782.0	782.7	783.3	783.9	784.7	783.9	783.3	782.7
177.5°	783.5	783.4	783.3	783.5	784.0	784.5	785.1	785.5	785.1	784.5	784.0
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1263.6	1260.1	1255.1	1247.7	1241.7	1232.2	1232.2	1233.7	1233.7	1233.3	1232.2
5°	1225.3	1215.9	1204.8	1191.7	1178.0	1164.3	1161.7	1156.7	1153.0	1150.6	1147.5
7.5°	1184.8	1168.2	1151.9	1133.6	1116.9	1103.1	1093.5	1085.5	1080.5	1075.0	1071.0
10°	1157.4	1136.9	1117.5	1098.3	1077.1	1060.3	1049.7	1042.2	1036.6	1031.7	1029.1
12.5°	1125.1	1101.5	1080.2	1061.9	1038.7	1021.4	1011.4	1007.8	1001.2	990.8	985.3
15°	1077.7	1055.9	1030.4	1002.3	991.2	970.0	958.1	952.6	948.8	940.7	938.3
17.5°	1037.2	1008.7	980.1	959.2	938.3	921.1	914.6	907.6	902.6	896.0	894.1
20°	1004.9	979.4	953.2	930.8	908.9	890.3	884.7	879.7	874.7	871.6	869.1
22.5°	972.0	946.5	924.8	903.9	880.6	868.4	862.3	856.8	853.3	851.2	848.7
25°	925.8	903.4	879.1	860.4	841.8	833.6	829.9	826.8	824.3	821.2	820.5
27.5°	884.5	860.1	840.3	822.9	809.5	802.8	799.2	797.6	798.2	799.3	800.0
30°	853.6	831.2	815.0	800.0	787.6	781.3	780.7	780.7	783.2	783.9	785.1
32.5°	825.2	806.8	790.6	776.1	766.7	762.4	764.8	764.8	766.8	768.4	770.6
35°	783.9	767.6	755.2	742.8	734.7	736.5	737.8	739.0	742.1	745.8	748.4
37.5°	744.3	730.3	717.3	707.7	703.9	707.3	710.3	712.9	716.4	719.4	721.8
40°	716.0	705.4	692.9	684.2	685.5	687.4	689.8	692.9	696.1	697.9	700.4
42.5°	689.6	678.5	669.1	661.8	663.5	665.9	667.4	669.1	672.6	676.0	677.5
45°	649.4	640.6	631.9	627.6	628.8	630.1	631.3	633.2	636.3	638.8	639.4
47.5°	604.2	598.1	592.2	588.0	589.9	589.5	591.1	595.1	596.0	597.5	601.0
50°	575.3	569.7	562.8	561.6	561.6	561.6	562.2	567.2	567.2	569.7	572.2
52.5°	543.4	539.8	535.4	533.2	532.2	532.2	534.8	537.3	538.3	541.8	544.3
55°	496.2	492.5	488.7	486.9	485.6	486.9	491.9	493.1	496.2	498.0	499.9
57.5°	447.0	444.2	441.2	440.1	439.9	441.6	444.3	448.0	448.8	454.5	457.3
60°	414.6	410.3	407.8	407.8	406.5	412.2	410.9	417.2	418.4	422.2	426.5
62.5°	381.3	375.4	374.5	374.5	376.2	377.8	379.5	382.3	385.5	390.2	393.6
65°	327.5	324.4	328.8	328.1	326.9	330.6	330.6	333.7	337.5	341.8	348.6
67.5°	276.6	275.0	275.3	275.3	277.2	279.3	281.1	283.8	288.3	292.9	297.4
70°	242.2	244.1	241.0	243.4	245.3	245.9	247.2	250.9	255.9	259.0	264.0
72.5°	208.8	208.7	209.1	210.1	211.9	213.0	214.3	218.6	224.0	226.6	230.6
75°	160.7	160.0	161.8	161.8	165.0	166.2	167.5	169.4	174.4	178.1	181.2
77.5°	117.3	118.0	117.6	119.8	118.9	119.1	123.0	124.9	125.4	132.8	134.4
80°	88.4	89.7	90.3	90.9	91.5	90.3	94.7	96.5	96.5	100.8	103.9
82.5°	63.5	64.2	65.9	66.5	66.6	67.9	68.2	69.6	71.1	73.0	77.1
85°	31.8	33.6	34.2	33.6	34.2	33.0	34.9	35.5	36.1	36.1	36.1
87.5°	11.1	11.9	11.7	12.6	12.4	13.2	13.4	12.4	12.6	14.2	12.3
90°	5.8	7.3	9.0	10.6	12.3	14.0	14.5	15.1	15.5	16.1	16.5
92.5°	9.4	9.8	11.1	12.4	13.6	14.9	15.8	16.6	17.4	18.2	18.7
95°	14.3	12.4	13.8	15.2	16.6	18.1	19.0	19.9	20.8	21.7	22.2
97.5°	61.9	56.1	46.7	37.4	28.1	18.8	19.8	20.8	21.9	22.9	23.5
100°	108.8	100.1	79.9	59.7	39.5	19.3	20.3	21.3	22.3	23.4	24.0
102.5°	136.7	126.7	104.6	82.5	60.4	38.3	35.2	31.9	28.8	25.5	24.0
105°	179.4	174.3	162.6	151.0	139.3	127.7	104.7	81.8	58.9	36.0	24.6
107.5°	225.1	226.6	228.5	230.3	232.2	234.0	217.1	200.3	183.5	166.8	149.7
110°	256.0	257.2	258.6	260.1	261.5	262.9	258.6	254.4	250.1	245.8	234.4



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	285.4	286.6	288.0	289.5	290.9	292.3	292.4	292.5	292.6	292.6	290.7
115°	329.0	329.9	331.1	332.2	333.4	334.6	335.9	337.2	338.5	339.8	340.7
117.5°	372.5	373.3	373.8	374.5	375.0	375.7	376.7	377.7	378.7	379.8	380.3
120°	399.9	400.7	401.1	401.5	401.9	402.2	403.3	404.3	405.4	406.4	406.9
122.5°	426.1	426.8	427.3	427.9	428.3	428.8	429.5	430.2	430.9	431.7	432.1
125°	463.5	464.3	464.8	465.3	465.8	466.4	466.6	466.8	467.1	467.4	467.6
127.5°	499.4	500.3	500.9	501.5	502.1	502.7	503.1	503.6	504.0	504.4	504.5
130°	521.8	522.6	523.1	523.6	524.1	524.7	525.1	525.7	526.2	526.7	526.9
132.5°	543.3	544.0	544.4	544.8	545.2	545.7	546.1	546.7	547.2	547.7	547.8
135°	575.0	575.6	576.2	576.6	577.2	577.7	578.1	578.5	578.8	579.2	579.2
137.5°	603.8	604.4	604.7	605.0	605.3	605.5	606.2	606.8	607.4	608.1	608.2
140°	621.6	622.2	622.6	623.0	623.4	623.8	624.2	624.8	625.3	625.8	626.0
142.5°	638.9	639.4	639.8	640.2	640.6	641.0	641.4	641.8	642.2	642.6	642.7
145°	663.5	664.1	664.3	664.6	664.9	665.1	665.4	665.7	665.9	666.1	666.3
147.5°	685.0	685.4	685.7	686.0	686.2	686.4	686.7	687.0	687.2	687.5	687.3
150°	698.2	698.5	698.8	699.0	699.3	699.5	699.8	700.1	700.3	700.5	700.5
152.5°	710.0	710.1	710.3	710.4	710.6	710.7	711.1	711.6	712.1	712.6	712.5
155°	725.9	725.8	726.0	726.1	726.2	726.4	727.0	727.6	728.3	729.0	728.9
157.5°	740.6	740.5	740.4	740.2	740.1	740.0	740.8	741.6	742.3	743.1	743.0
160°	748.5	748.5	748.3	748.1	748.1	747.9	748.7	749.5	750.3	751.0	751.0
162.5°	755.7	755.4	755.3	755.2	755.0	754.9	755.8	756.7	757.6	758.4	758.4
165°	765.0	764.8	764.6	764.5	764.4	764.2	765.2	766.3	767.3	768.3	768.4
167.5°	772.0	771.7	771.7	771.7	771.7	771.7	772.7	773.7	774.8	775.9	775.9
170°	776.2	775.9	775.9	775.9	775.9	775.9	776.9	777.9	779.0	780.1	780.1
172.5°	778.6	778.2	778.4	778.5	778.6	778.7	779.7	780.8	781.8	782.8	782.8
175°	782.0	781.8	781.9	782.0	782.2	782.3	783.2	784.1	785.1	785.9	785.8
177.5°	783.5	783.3	783.4	783.5	783.6	783.7	784.5	785.4	786.2	787.0	786.9
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1228.8	1228.3	1231.8	1229.2	1231.8	1228.3	1228.8	1232.2	1233.3	1233.7	1233.7
5°	1143.7	1145.6	1139.3	1139.3	1139.3	1145.6	1143.7	1147.5	1150.6	1153.0	1156.7
7.5°	1068.0	1065.2	1065.5	1062.2	1065.5	1065.2	1068.0	1071.0	1075.0	1080.5	1085.5
10°	1021.7	1018.0	1016.7	1017.3	1016.7	1018.0	1021.7	1029.1	1031.7	1036.6	1042.2
12.5°	983.3	982.5	974.4	974.5	974.4	982.5	983.3	985.3	990.8	1001.2	1007.8
15°	938.3	926.5	925.2	928.9	925.2	926.5	938.3	938.3	940.7	948.8	952.6
17.5°	893.0	886.8	887.2	885.3	887.2	886.8	893.0	894.1	896.0	902.6	907.6
20°	869.1	865.4	864.7	860.4	864.7	865.4	869.1	869.1	871.6	874.7	879.7
22.5°	847.2	846.0	846.4	841.5	846.4	846.0	847.2	848.7	851.2	853.3	856.8
25°	820.0	823.1	820.5	820.5	820.5	823.1	820.0	820.5	821.2	824.3	826.8
27.5°	801.5	801.4	800.2	800.2	800.2	801.4	801.5	800.0	799.3	798.2	797.6
30°	787.6	787.0	788.2	788.2	788.2	787.0	787.6	785.1	783.9	783.2	780.7
32.5°	773.6	774.5	774.8	775.2	774.8	774.5	773.6	770.6	768.4	766.8	764.8
35°	752.1	752.7	754.6	753.4	754.6	752.7	752.1	748.4	745.8	742.1	739.0
37.5°	722.9	725.8	725.2	726.2	725.2	725.8	722.9	721.8	719.4	716.4	712.9
40°	701.0	702.9	702.3	702.3	702.3	702.9	701.0	700.4	697.9	696.1	692.9
42.5°	678.7	680.0	678.3	677.4	678.3	680.0	678.7	677.5	676.0	672.6	669.1
45°	641.9	640.6	642.5	640.0	642.5	640.6	641.9	639.4	638.8	636.3	633.2
47.5°	600.8	602.1	602.5	604.4	602.5	602.1	600.8	601.0	597.5	596.0	595.1
50°	573.4	577.1	577.1	576.6	577.1	577.1	573.4	572.2	569.7	567.2	567.2
52.5°	546.5	548.3	550.7	550.6	550.7	548.3	546.5	544.3	541.8	538.3	537.3
55°	504.9	506.2	507.4	508.0	507.4	506.2	504.9	499.9	498.0	496.2	493.1
57.5°	461.8	461.4	464.3	465.2	464.3	461.4	461.8	457.3	454.5	448.8	448.0
60°	431.4	431.4	436.4	438.3	436.4	431.4	431.4	426.5	422.2	418.4	417.2
62.5°	399.1	401.1	406.1	403.5	406.1	401.1	399.1	393.6	390.2	385.5	382.3
65°	351.7	356.7	356.1	358.6	356.1	356.7	351.7	348.6	341.8	337.5	333.7
67.5°	302.3	305.5	309.9	310.3	309.9	305.5	302.3	297.4	292.9	288.3	283.8
70°	268.9	272.0	274.6	276.4	274.6	272.0	268.9	264.0	259.0	255.9	250.9
72.5°	236.6	238.2	244.2	241.5	244.2	238.2	236.6	230.6	226.6	224.0	218.6
75°	185.5	189.9	193.6	191.8	193.6	189.9	185.5	181.2	178.1	174.4	169.4
77.5°	137.2	141.6	143.3	141.7	143.3	141.6	137.2	134.4	132.8	125.4	124.9
80°	108.4	107.7	111.5	110.8	111.5	107.7	108.4	103.9	100.8	96.5	96.5
82.5°	79.5	78.8	80.6	81.0	80.6	78.8	79.5	77.1	73.0	71.1	69.6
85°	38.6	40.5	37.9	37.4	37.9	40.5	38.6	36.1	36.1	36.1	35.5
87.5°	12.3	12.4	11.9	11.5	11.9	12.4	12.3	12.3	14.2	12.6	12.4
90°	16.7	17.0	17.2	17.5	17.2	17.0	16.7	16.5	16.1	15.5	15.1
92.5°	18.9	19.0	19.2	19.3	19.2	19.0	18.9	18.7	18.2	17.4	16.6
95°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	21.7	20.8	19.9
97.5°	23.6	23.8	23.9	24.0	23.9	23.8	23.6	23.5	22.9	21.9	20.8
100°	24.1	24.2	24.3	24.5	24.3	24.2	24.1	24.0	23.4	22.3	21.3
102.5°	24.2	24.5	24.7	25.0	24.7	24.5	24.2	24.0	25.5	28.8	31.9
105°	24.9	25.1	25.4	25.7	25.4	25.1	24.9	24.6	36.0	58.9	81.8
107.5°	132.4	115.1	97.8	80.6	97.8	115.1	132.4	149.7	166.8	183.5	200.3
110°	215.9	197.3	178.8	160.3	178.8	197.3	215.9	234.4	245.8	250.1	254.4



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	286.8	282.9	278.9	275.0	278.9	282.9	286.8	290.7	292.6	292.6	292.5
115°	341.2	341.7	342.2	342.8	342.2	341.7	341.2	340.7	339.8	338.5	337.2
117.5°	380.5	380.6	380.6	380.8	380.6	380.6	380.5	380.3	379.8	378.7	377.7
120°	406.9	406.9	406.9	406.9	406.9	406.9	406.9	406.9	406.4	405.4	404.3
122.5°	432.2	432.3	432.5	432.5	432.5	432.3	432.2	432.1	431.7	430.9	430.2
125°	467.9	468.2	468.4	468.7	468.4	468.2	467.9	467.6	467.4	467.1	466.8
127.5°	504.2	503.9	503.7	503.4	503.7	503.9	504.2	504.5	504.4	504.0	503.6
130°	526.6	526.3	526.1	525.8	526.1	526.3	526.6	526.9	526.7	526.2	525.7
132.5°	547.4	547.1	546.7	546.3	546.7	547.1	547.4	547.8	547.7	547.2	546.7
135°	578.8	578.5	578.1	577.7	578.1	578.5	578.8	579.2	579.2	578.8	578.5
137.5°	608.0	607.7	607.4	607.2	607.4	607.7	608.0	608.2	608.1	607.4	606.8
140°	625.7	625.4	625.2	624.9	625.2	625.4	625.7	626.0	625.8	625.3	624.8
142.5°	642.3	642.0	641.6	641.2	641.6	642.0	642.3	642.7	642.6	642.2	641.8
145°	666.3	666.3	666.3	666.3	666.3	666.3	666.3	666.3	666.1	665.9	665.7
147.5°	686.7	686.1	685.6	684.9	685.6	686.1	686.7	687.3	687.5	687.2	687.0
150°	700.1	699.7	699.3	698.9	699.3	699.7	700.1	700.5	700.5	700.3	700.1
152.5°	711.9	711.3	710.7	710.1	710.7	711.3	711.9	712.5	712.6	712.1	711.6
155°	728.1	727.3	726.5	725.7	726.5	727.3	728.1	728.9	729.0	728.3	727.6
157.5°	742.0	740.9	740.0	738.9	740.0	740.9	742.0	743.0	743.1	742.3	741.6
160°	750.0	749.2	748.2	747.3	748.2	749.2	750.0	751.0	751.0	750.3	749.5
162.5°	757.6	756.9	756.1	755.3	756.1	756.9	757.6	758.4	758.4	757.6	756.7
165°	767.5	766.6	765.7	764.8	765.7	766.6	767.5	768.4	768.3	767.3	766.3
167.5°	774.8	773.7	772.7	771.7	772.7	773.7	774.8	775.9	775.9	774.8	773.7
170°	779.0	777.9	776.9	775.9	776.9	777.9	779.0	780.1	780.1	779.0	777.9
172.5°	781.6	780.5	779.3	778.2	779.3	780.5	781.6	782.8	782.8	781.8	780.8
175°	784.8	783.8	782.8	781.7	782.8	783.8	784.8	785.8	785.9	785.1	784.1
177.5°	785.8	784.8	783.8	782.8	783.8	784.8	785.8	786.9	787.0	786.2	785.4
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1232.2	1232.2	1241.7	1247.7	1255.1	1260.1	1263.6	1267.1	1273.1	1281.0	1290.0
5°	1161.7	1164.3	1178.0	1191.7	1204.8	1215.9	1225.3	1236.4	1250.1	1266.9	1285.6
7.5°	1093.5	1103.1	1116.9	1133.6	1151.9	1168.2	1184.8	1203.2	1222.5	1247.3	1273.4
10°	1049.7	1060.3	1077.1	1098.3	1117.5	1136.9	1157.4	1177.3	1201.6	1230.9	1264.5
12.5°	1011.4	1021.4	1038.7	1061.9	1080.2	1101.5	1125.1	1151.0	1178.2	1213.5	1251.6
15°	958.1	970.0	991.2	1002.3	1030.4	1055.9	1077.7	1115.1	1149.9	1186.1	1230.3
17.5°	914.6	921.1	938.3	959.2	980.1	1008.7	1037.2	1068.3	1103.1	1147.3	1202.6
20°	884.7	890.3	908.9	930.8	953.2	979.4	1004.9	1036.0	1075.2	1121.9	1181.7
22.5°	862.3	868.4	880.6	903.9	924.8	946.5	972.0	1009.1	1050.8	1096.5	1161.3
25°	829.9	833.6	841.8	860.4	879.1	903.4	925.8	960.7	1003.6	1057.2	1121.9
27.5°	799.2	802.8	809.5	822.9	840.3	860.1	884.5	914.1	957.7	1015.8	1084.6
30°	780.7	781.3	787.6	800.0	815.0	831.2	853.6	887.2	928.3	987.5	1059.6
32.5°	764.8	762.4	766.7	776.1	790.6	806.8	825.2	858.3	897.9	956.1	1030.2
35°	737.8	736.5	734.7	742.8	755.2	767.6	783.9	808.7	853.6	907.8	985.6
37.5°	710.3	707.3	703.9	707.7	717.3	730.3	744.3	766.5	805.2	864.7	939.2
40°	689.8	687.4	685.5	684.2	692.9	705.4	716.0	737.1	773.2	829.9	903.4
42.5°	667.4	665.9	663.5	661.8	669.1	678.5	689.6	708.3	744.3	797.6	867.0
45°	631.3	630.1	628.8	627.6	631.9	640.6	649.4	663.1	694.2	745.8	808.7
47.5°	591.1	589.5	589.9	588.0	592.2	598.1	604.2	618.9	648.7	690.5	736.4
50°	562.2	561.6	561.6	561.6	562.8	569.7	575.3	586.5	613.9	655.6	688.6
52.5°	534.8	532.2	532.2	533.2	535.4	539.8	543.4	555.6	579.5	613.8	643.7
55°	491.9	486.9	485.6	486.9	488.7	492.5	496.2	506.2	526.7	552.2	569.7
57.5°	444.3	441.6	439.9	440.1	441.2	444.2	447.0	457.9	474.0	487.4	498.6
60°	410.9	412.2	406.5	407.8	407.8	410.3	414.6	421.5	435.2	444.5	455.7
62.5°	379.5	377.8	376.2	374.5	374.5	375.4	381.3	386.7	398.3	403.2	411.9
65°	330.6	330.6	326.9	328.1	328.8	324.4	327.5	333.7	341.2	343.0	351.2
67.5°	281.1	279.3	277.2	275.3	275.3	275.0	276.6	279.6	285.3	285.9	292.2
70°	247.2	245.9	245.3	243.4	241.0	244.1	242.2	245.3	248.4	249.1	252.8
72.5°	214.3	213.0	211.9	210.1	209.1	208.7	208.8	212.5	214.5	213.7	217.9
75°	167.5	166.2	165.0	161.8	161.8	160.0	160.7	163.1	165.6	163.7	167.5
77.5°	123.0	119.1	118.9	119.8	117.6	118.0	117.3	116.9	118.0	118.2	121.5
80°	94.7	90.3	91.5	90.9	90.3	89.7	88.4	89.0	89.7	90.3	92.1
82.5°	68.2	67.9	66.6	66.5	65.9	64.2	63.5	64.6	65.3	64.9	66.2
85°	34.9	33.0	34.2	33.6	34.2	33.6	31.8	31.8	33.0	32.4	33.6
87.5°	13.4	13.2	12.4	12.6	11.7	11.9	11.1	11.3	11.6	11.3	12.0
90°	14.5	14.0	12.3	10.6	9.0	7.3	5.8	4.4	3.2	1.9	0.6
92.5°	15.8	14.9	13.6	12.4	11.1	9.8	9.4	9.7	10.1	10.5	10.9
95°	19.0	18.1	16.6	15.2	13.8	12.4	14.3	19.6	25.0	30.3	35.6
97.5°	19.8	18.8	28.1	37.4	46.7	56.1	61.9	64.3	66.7	69.1	71.5
100°	20.3	19.3	39.5	59.7	79.9	100.1	108.8	106.3	103.7	101.1	98.5
102.5°	35.2	38.3	60.4	82.5	104.6	126.7	136.7	134.9	133.0	131.2	129.3
105°	104.7	127.7	139.3	151.0	162.6	174.3	179.4	178.0	176.6	175.2	173.7
107.5°	217.1	234.0	232.2	230.3	228.5	226.6	225.1	224.0	222.8	221.7	220.5
110°	258.6	262.9	261.5	260.1	258.6	257.2	256.0	254.9	253.9	252.9	251.8



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	292.4	292.3	290.9	289.5	288.0	286.6	285.4	284.5	283.5	282.6	281.7
115°	335.9	334.6	333.4	332.2	331.1	329.9	329.0	328.2	327.4	326.6	325.8
117.5°	376.7	375.7	375.0	374.5	373.8	373.3	372.5	371.5	370.6	369.6	368.7
120°	403.3	402.2	401.9	401.5	401.1	400.7	399.9	398.7	397.6	396.4	395.2
122.5°	429.5	428.8	428.3	427.9	427.3	426.8	426.1	425.2	424.2	423.3	422.3
125°	466.6	466.4	465.8	465.3	464.8	464.3	463.5	462.5	461.4	460.4	459.4
127.5°	503.1	502.7	502.1	501.5	500.9	500.3	499.4	498.4	497.3	496.3	495.3
130°	525.1	524.7	524.1	523.6	523.1	522.6	521.8	520.8	519.8	518.7	517.6
132.5°	546.1	545.7	545.2	544.8	544.4	544.0	543.3	542.2	541.1	540.1	539.1
135°	578.1	577.7	577.2	576.6	576.2	575.6	575.0	574.2	573.4	572.7	571.9
137.5°	606.2	605.5	605.3	605.0	604.7	604.4	603.8	602.8	601.8	600.8	599.8
140°	624.2	623.8	623.4	623.0	622.6	622.2	621.6	620.8	620.0	619.2	618.5
142.5°	641.4	641.0	640.6	640.2	639.8	639.4	638.9	638.1	637.3	636.5	635.7
145°	665.4	665.1	664.9	664.6	664.3	664.1	663.5	662.6	661.7	660.8	659.9
147.5°	686.7	686.4	686.2	686.0	685.7	685.4	685.0	684.4	683.8	683.2	682.6
150°	699.8	699.5	699.3	699.0	698.8	698.5	698.2	697.8	697.4	697.0	696.6
152.5°	711.1	710.7	710.6	710.4	710.3	710.1	710.0	709.7	709.6	709.4	709.2
155°	727.0	726.4	726.2	726.1	726.0	725.8	725.9	726.1	726.4	726.7	726.9
157.5°	740.8	740.0	740.1	740.2	740.4	740.5	740.6	740.6	740.6	740.7	740.7
160°	748.7	747.9	748.1	748.1	748.3	748.5	748.5	748.7	748.8	748.9	749.1
162.5°	755.8	754.9	755.0	755.2	755.3	755.4	755.7	756.0	756.3	756.7	757.0
165°	765.2	764.2	764.4	764.5	764.6	764.8	765.0	765.4	765.8	766.2	766.6
167.5°	772.7	771.7	771.7	771.7	771.7	771.7	772.0	772.5	773.0	773.5	774.0
170°	776.9	775.9	775.9	775.9	775.9	775.9	776.2	776.7	777.2	777.7	778.2
172.5°	779.7	778.7	778.6	778.5	778.4	778.2	778.6	779.2	779.7	780.4	781.0
175°	783.2	782.3	782.2	782.0	781.9	781.8	782.0	782.7	783.3	783.9	784.7
177.5°	784.5	783.7	783.6	783.5	783.4	783.3	783.5	784.0	784.5	785.1	785.5
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1293.0	1295.5	1303.9	1310.0	1316.9	1320.9	1324.8	1327.9	1331.8	1332.8	1347.3
5°	1298.7	1311.2	1333.0	1349.2	1369.0	1390.8	1405.8	1412.7	1430.7	1445.7	1475.5
7.5°	1297.1	1323.7	1356.5	1390.6	1427.2	1461.1	1490.5	1525.3	1550.1	1587.4	1624.1
10°	1295.6	1331.1	1373.4	1417.1	1468.1	1515.4	1557.7	1605.0	1644.3	1695.9	1740.1
12.5°	1291.1	1334.1	1392.9	1444.4	1506.4	1571.7	1634.4	1695.2	1730.0	1816.0	1856.7
15°	1280.1	1331.1	1404.5	1483.0	1568.3	1645.5	1725.2	1788.7	1891.4	1966.8	2014.7
17.5°	1258.9	1330.4	1417.5	1512.1	1615.9	1717.6	1807.9	1904.2	2013.3	2104.4	2201.5
20°	1249.0	1327.4	1424.5	1529.1	1636.8	1752.0	1854.7	1970.5	2089.5	2179.1	2303.6
22.5°	1230.5	1319.4	1424.0	1540.6	1655.7	1774.9	1895.1	2011.8	2149.2	2272.7	2391.3
25°	1200.4	1300.0	1408.3	1538.4	1673.6	1793.1	1936.9	2091.9	2235.1	2393.9	2512.2
27.5°	1168.7	1275.1	1383.6	1504.7	1650.0	1791.8	1972.8	2147.9	2323.0	2460.1	2547.7
30°	1144.3	1247.7	1359.8	1481.8	1625.6	1794.3	1996.6	2187.8	2358.4	2476.0	2525.2
32.5°	1117.9	1222.7	1321.9	1449.9	1603.1	1792.8	2011.6	2211.2	2360.4	2438.7	2429.1
35°	1076.5	1164.3	1260.8	1384.0	1564.6	1781.9	2020.3	2213.3	2304.9	2288.1	2161.0
37.5°	1016.7	1090.5	1185.6	1320.5	1519.7	1758.8	2002.9	2147.7	2141.7	2004.9	1820.8
40°	979.4	1042.2	1133.8	1275.7	1484.9	1743.9	1975.5	2069.5	1989.8	1798.6	1578.3
42.5°	930.5	988.4	1080.0	1225.9	1446.5	1713.5	1923.2	1950.4	1794.5	1574.5	1372.5
45°	854.8	905.9	1000.5	1151.2	1389.0	1647.3	1795.6	1728.9	1519.1	1291.9	1138.1
47.5°	773.5	826.6	917.6	1072.4	1305.8	1547.9	1618.5	1476.8	1261.4	1077.1	935.9
50°	722.2	773.2	862.3	1018.6	1249.5	1466.2	1495.5	1312.4	1114.4	952.6	836.8
52.5°	670.4	718.5	806.0	962.7	1183.8	1371.6	1353.5	1167.0	984.9	847.0	756.1
55°	593.3	638.8	722.2	869.1	1070.2	1219.0	1153.7	975.6	824.9	717.9	648.7
57.5°	524.3	567.9	639.9	772.6	947.5	1049.7	966.5	816.5	696.6	614.3	562.7
60°	477.5	516.1	584.6	707.9	859.8	937.6	855.5	722.9	621.9	556.0	509.9
62.5°	433.2	466.8	530.3	642.1	774.1	839.5	756.3	644.1	558.3	499.7	460.6
65°	366.1	396.6	452.7	539.8	648.1	691.7	620.1	529.2	462.6	419.0	392.8
67.5°	304.8	330.7	379.1	447.7	527.4	559.2	504.7	434.4	384.1	349.1	328.4
70°	264.0	286.4	324.4	383.5	455.7	480.0	429.0	371.1	334.3	306.3	287.0
72.5°	229.6	246.1	280.5	326.2	386.5	405.8	370.2	319.2	285.0	264.0	248.7
75°	174.9	188.6	211.0	247.8	289.5	300.7	273.9	242.2	219.1	204.2	192.3
77.5°	126.1	136.3	152.4	175.1	204.0	214.0	197.1	175.9	159.1	149.0	142.4
80°	95.2	103.4	117.1	135.7	153.1	158.8	148.8	132.6	120.8	115.2	109.6
82.5°	70.3	74.9	83.2	95.9	107.8	114.5	106.0	96.3	89.9	84.8	82.7
85°	35.5	37.9	41.7	46.7	54.2	56.6	53.6	51.0	47.3	44.2	44.2
87.5°	13.3	13.5	15.4	16.6	18.9	20.7	20.5	19.9	19.7	19.3	18.9
90°	1.9	3.2	4.4	5.8	7.3	9.0	10.6	12.3	14.0	14.5	15.1
92.5°	10.5	10.1	9.7	9.4	9.8	11.1	12.4	13.6	14.9	15.8	16.6
95°	30.3	25.0	19.6	14.3	12.4	13.8	15.2	16.6	18.1	19.0	19.9
97.5°	69.1	66.7	64.3	61.9	56.1	46.7	37.4	28.1	18.8	19.8	20.8
100°	101.1	103.7	106.3	108.8	100.1	79.9	59.7	39.5	19.3	20.3	21.3
102.5°	131.2	133.0	134.9	136.7	126.7	104.6	82.5	60.4	38.3	35.2	31.9
105°	175.2	176.6	178.0	179.4	174.3	162.6	151.0	139.3	127.7	104.7	81.8
107.5°	221.7	222.8	224.0	225.1	226.6	228.5	230.3	232.2	234.0	217.1	200.3
110°	252.9	253.9	254.9	256.0	257.2	258.6	260.1	261.5	262.9	258.6	254.4



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	282.6	283.5	284.5	285.4	286.6	288.0	289.5	290.9	292.3	292.4	292.5
115°	326.6	327.4	328.2	329.0	329.9	331.1	332.2	333.4	334.6	335.9	337.2
117.5°	369.6	370.6	371.5	372.5	373.3	373.8	374.5	375.0	375.7	376.7	377.7
120°	396.4	397.6	398.7	399.9	400.7	401.1	401.5	401.9	402.2	403.3	404.3
122.5°	423.3	424.2	425.2	426.1	426.8	427.3	427.9	428.3	428.8	429.5	430.2
125°	460.4	461.4	462.5	463.5	464.3	464.8	465.3	465.8	466.4	466.6	466.8
127.5°	496.3	497.3	498.4	499.4	500.3	500.9	501.5	502.1	502.7	503.1	503.6
130°	518.7	519.8	520.8	521.8	522.6	523.1	523.6	524.1	524.7	525.1	525.7
132.5°	540.1	541.1	542.2	543.3	544.0	544.4	544.8	545.2	545.7	546.1	546.7
135°	572.7	573.4	574.2	575.0	575.6	576.2	576.6	577.2	577.7	578.1	578.5
137.5°	600.8	601.8	602.8	603.8	604.4	604.7	605.0	605.3	605.5	606.2	606.8
140°	619.2	620.0	620.8	621.6	622.2	622.6	623.0	623.4	623.8	624.2	624.8
142.5°	636.5	637.3	638.1	638.9	639.4	639.8	640.2	640.6	641.0	641.4	641.8
145°	660.8	661.7	662.6	663.5	664.1	664.3	664.6	664.9	665.1	665.4	665.7
147.5°	683.2	683.8	684.4	685.0	685.4	685.7	686.0	686.2	686.4	686.7	687.0
150°	697.0	697.4	697.8	698.2	698.5	698.8	699.0	699.3	699.5	699.8	700.1
152.5°	709.4	709.6	709.7	710.0	710.1	710.3	710.4	710.6	710.7	711.1	711.6
155°	726.7	726.4	726.1	725.9	725.8	726.0	726.1	726.2	726.4	727.0	727.6
157.5°	740.7	740.6	740.6	740.6	740.5	740.4	740.2	740.1	740.0	740.8	741.6
160°	748.9	748.8	748.7	748.5	748.5	748.3	748.1	748.1	747.9	748.7	749.5
162.5°	756.7	756.3	756.0	755.7	755.4	755.3	755.2	755.0	754.9	755.8	756.7
165°	766.2	765.8	765.4	765.0	764.8	764.6	764.5	764.4	764.2	765.2	766.3
167.5°	773.5	773.0	772.5	772.0	771.7	771.7	771.7	771.7	771.7	772.7	773.7
170°	777.7	777.2	776.7	776.2	775.9	775.9	775.9	775.9	775.9	776.9	777.9
172.5°	780.4	779.7	779.2	778.6	778.2	778.4	778.5	778.6	778.7	779.7	780.8
175°	783.9	783.3	782.7	782.0	781.8	781.9	782.0	782.2	782.3	783.2	784.1
177.5°	785.1	784.5	784.0	783.5	783.3	783.4	783.5	783.6	783.7	784.5	785.4
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1352.3	1352.7	1358.3	1362.2	1360.3	1362.7	1363.7
5°	1477.4	1499.8	1511.6	1520.4	1521.0	1521.6	1526.6
7.5°	1654.9	1678.9	1696.5	1723.1	1731.1	1740.1	1737.5
10°	1784.4	1819.8	1850.4	1866.5	1884.0	1909.5	1889.0
12.5°	1905.4	1968.3	2014.7	2039.9	2056.3	2061.4	2051.4
15°	2105.0	2187.1	2231.3	2230.2	2286.2	2310.5	2272.5
17.5°	2288.1	2363.9	2424.6	2455.8	2502.4	2512.8	2508.0
20°	2400.1	2482.9	2530.2	2583.8	2608.0	2629.8	2633.5
22.5°	2496.7	2571.0	2621.9	2666.4	2686.8	2697.1	2703.3
25°	2596.2	2654.8	2685.3	2700.8	2706.4	2705.1	2697.1
27.5°	2589.3	2593.8	2560.3	2527.2	2497.8	2464.5	2453.0
30°	2522.1	2469.8	2376.5	2323.5	2245.7	2184.0	2208.9
32.5°	2345.3	2241.2	2136.4	2020.7	1924.9	1897.7	1870.3
35°	2001.6	1818.6	1711.5	1587.0	1537.2	1487.4	1453.1
37.5°	1619.4	1477.8	1350.8	1269.3	1219.4	1187.9	1171.0
40°	1400.2	1272.6	1168.0	1102.0	1064.0	1028.5	1023.6
42.5°	1225.4	1106.8	1028.0	975.5	939.0	923.9	913.0
45°	1003.6	920.8	867.9	830.5	806.3	796.9	784.5
47.5°	849.5	790.9	751.2	725.8	707.5	700.5	699.6
50°	763.3	714.7	685.5	665.5	651.3	648.7	638.8
52.5°	698.5	656.5	633.7	616.2	605.9	599.0	596.0
55°	606.4	578.4	557.9	547.9	539.8	532.9	532.9
57.5°	530.6	507.2	493.6	485.1	482.6	477.8	474.7
60°	483.8	463.8	453.3	445.8	440.8	441.4	435.8
62.5°	437.9	425.0	414.9	407.4	401.5	401.6	402.0
65°	373.0	363.0	355.5	353.0	349.3	344.9	346.2
67.5°	316.0	306.7	300.9	296.6	295.3	293.0	296.6
70°	275.2	268.3	264.0	260.2	259.0	259.6	262.8
72.5°	237.8	233.0	230.1	228.4	225.6	225.8	227.8
75°	186.8	183.1	180.5	178.7	178.1	178.1	178.1
77.5°	137.2	136.3	135.2	132.5	132.6	133.3	133.5
80°	108.4	106.5	105.8	104.6	102.7	101.5	104.6
82.5°	81.0	79.1	78.4	78.2	75.3	75.1	77.7
85°	43.6	41.7	42.3	41.7	41.7	41.1	41.1
87.5°	18.5	18.1	17.7	18.3	17.8	17.4	18.5
90°	15.5	16.1	16.5	16.7	17.0	17.2	17.5
92.5°	17.4	18.2	18.7	18.9	19.0	19.2	19.3
95°	20.8	21.7	22.2	22.2	22.2	22.2	22.2
97.5°	21.9	22.9	23.5	23.6	23.8	23.9	24.0
100°	22.3	23.4	24.0	24.1	24.2	24.3	24.5
102.5°	28.8	25.5	24.0	24.2	24.5	24.7	25.0
105°	58.9	36.0	24.6	24.9	25.1	25.4	25.7
107.5°	183.5	166.8	149.7	132.4	115.1	97.8	80.6
110°	250.1	245.8	234.4	215.9	197.3	178.8	160.3



TEST NUMBER: P332216-927

CATALOG NUMBER: S123DIW-S1165D755U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	292.6	292.6	290.7	286.8	282.9	278.9	275.0
115°	338.5	339.8	340.7	341.2	341.7	342.2	342.8
117.5°	378.7	379.8	380.3	380.5	380.6	380.6	380.8
120°	405.4	406.4	406.9	406.9	406.9	406.9	406.9
122.5°	430.9	431.7	432.1	432.2	432.3	432.5	432.5
125°	467.1	467.4	467.6	467.9	468.2	468.4	468.7
127.5°	504.0	504.4	504.5	504.2	503.9	503.7	503.4
130°	526.2	526.7	526.9	526.6	526.3	526.1	525.8
132.5°	547.2	547.7	547.8	547.4	547.1	546.7	546.3
135°	578.8	579.2	579.2	578.8	578.5	578.1	577.7
137.5°	607.4	608.1	608.2	608.0	607.7	607.4	607.2
140°	625.3	625.8	626.0	625.7	625.4	625.2	624.9
142.5°	642.2	642.6	642.7	642.3	642.0	641.6	641.2
145°	665.9	666.1	666.3	666.3	666.3	666.3	666.3
147.5°	687.2	687.5	687.3	686.7	686.1	685.6	684.9
150°	700.3	700.5	700.5	700.1	699.7	699.3	698.9
152.5°	712.1	712.6	712.5	711.9	711.3	710.7	710.1
155°	728.3	729.0	728.9	728.1	727.3	726.5	725.7
157.5°	742.3	743.1	743.0	742.0	740.9	740.0	738.9
160°	750.3	751.0	751.0	750.0	749.2	748.2	747.3
162.5°	757.6	758.4	758.4	757.6	756.9	756.1	755.3
165°	767.3	768.3	768.4	767.5	766.6	765.7	764.8
167.5°	774.8	775.9	775.9	774.8	773.7	772.7	771.7
170°	779.0	780.1	780.1	779.0	777.9	776.9	775.9
172.5°	781.8	782.8	782.8	781.6	780.5	779.3	778.2
175°	785.1	785.9	785.8	784.8	783.8	782.8	781.7
177.5°	786.2	787.0	786.9	785.8	784.8	783.8	782.8
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7

(END OF REPORT)