

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331595-840

Luminaire Tested: **S122DIW-S1005D710U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331595-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D710U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6960.5 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331595-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331595-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34	30
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25987	25987	25987
5°	26086	25710	25861
10°	25932	25450	25576
15°	25611	25120	25095
20°	25156	24624	24598
25°	24704	24015	24015
30°	24121	23457	23256
35°	23580	22787	22450
40°	22898	22118	21692
45°	22229	21450	20922
50°	21499	20760	20022
55°	20738	19952	19212
60°	19888	18991	18290
65°	18980	18032	17207
70°	17825	16877	16074
75°	16220	15540	15159
80°	14393	13966	13240
85°	11745	11189	10022



TEST NUMBER: P331595-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	2.2
10°-20°	425.9	6.1
20°-30°	626.0	9.0
30°-40°	727.1	10.4
40°-50°	726.3	10.4
50°-60°	633.4	9.1
60°-70°	468.3	6.7
70°-80°	265.3	3.8
80°-90°	73.7	1.1
90°-100°	32.6	0.5
100°-110°	119.5	1.7
110°-120°	319.5	4.6
120°-130°	527.3	7.6
130°-140°	560.8	8.1
140°-150°	521.3	7.5
150°-160°	419.1	6.0
160°-170°	270.1	3.9
170°-180°	93.0	1.3
0°-30°	1203.2	17.3
0°-40°	1930.3	27.7
0°-60°	3290.0	47.3
0°-90°	4097.4	58.9
90°-120°	471.6	6.8
90°-150°	2081.0	29.9
90°-180°	2863.0	41.1
0°-180°	6960.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1610	1603	1586	1598	1596	153
15°	1532	1522	1503	1508	1501	431
25°	1387	1374	1348	1351	1348	638
35°	1196	1180	1156	1147	1139	747
45°	974	962	939	923	916	751
55°	737	727	709	691	682	658
65°	497	487	472	458	450	491
75°	260	257	249	241	243	278
85°	63	62	60	56	54	73
90°	1	8	14	18	19	5
95°	46	24	28	31	30	56
105°	215	224	43	51	54	230
115°	406	419	436	124	58	400
125°	575	584	597	602	604	512
135°	711	722	729	736	735	549
145°	825	825	836	841	838	516
155°	908	903	911	914	909	418
165°	957	953	955	960	955	270
175°	979	974	976	980	974	93
180°	977	977	977	977	977	



TEST NUMBER: P331595-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1617.0	1615.6	1614.3	1612.9	1611.4	1609.3	1606.3	1603.3	1600.2	1597.2	1599.9
5°	1609.5	1608.2	1606.8	1605.4	1604.1	1601.4	1597.7	1593.9	1590.1	1586.3	1589.1
7.5°	1595.3	1593.2	1591.0	1588.9	1586.8	1583.8	1579.9	1576.1	1572.3	1568.4	1571.1
10°	1581.7	1579.3	1576.9	1574.5	1572.1	1568.8	1564.7	1560.5	1556.4	1552.3	1555.1
12.5°	1563.2	1560.9	1558.8	1556.7	1554.6	1551.5	1547.3	1543.2	1539.1	1535.0	1536.9
15°	1532.2	1530.1	1528.0	1526.0	1523.9	1520.7	1516.2	1511.7	1507.2	1502.8	1504.2
17.5°	1492.6	1490.5	1488.4	1486.3	1484.3	1481.0	1476.4	1471.9	1467.3	1462.9	1464.4
20°	1464.1	1462.0	1460.0	1457.8	1455.8	1452.4	1447.5	1442.8	1437.9	1433.1	1434.1
22.5°	1435.6	1432.7	1429.9	1426.9	1424.0	1420.4	1415.8	1411.3	1406.7	1402.2	1402.4
25°	1386.7	1383.9	1381.2	1378.5	1375.7	1371.4	1365.5	1359.7	1353.8	1348.0	1348.7
27.5°	1331.0	1328.5	1326.1	1323.5	1321.1	1317.6	1312.9	1308.3	1303.7	1299.1	1298.1
30°	1293.8	1291.1	1288.3	1285.6	1282.8	1278.9	1273.7	1268.6	1263.4	1258.2	1257.2
32.5°	1254.3	1252.0	1249.8	1247.6	1245.4	1241.6	1236.2	1230.7	1225.3	1219.8	1218.0
35°	1196.3	1192.9	1189.4	1186.0	1182.6	1178.1	1172.6	1167.1	1161.6	1156.1	1154.1
37.5°	1131.0	1128.0	1125.0	1122.0	1118.9	1114.7	1109.1	1103.7	1098.1	1092.7	1090.0
40°	1086.4	1083.7	1081.0	1078.2	1075.4	1071.4	1065.8	1060.4	1054.8	1049.4	1046.2
42.5°	1043.1	1040.4	1037.6	1034.9	1032.1	1027.9	1022.5	1016.9	1011.5	1005.9	1002.6
45°	973.5	971.1	968.7	966.2	963.8	960.1	954.9	949.8	944.6	939.4	935.6
47.5°	904.1	901.9	899.6	897.4	895.0	891.2	885.9	880.5	875.1	869.8	865.8
50°	855.9	854.1	852.4	850.7	849.0	845.7	840.9	836.1	831.2	826.5	821.6
52.5°	808.8	806.6	804.3	802.0	799.7	796.3	791.7	787.2	782.7	778.2	774.2
55°	736.7	734.6	732.6	730.5	728.4	725.3	721.2	717.1	713.0	708.8	704.7
57.5°	664.3	662.6	661.0	659.3	657.6	654.6	650.1	645.5	641.0	636.4	632.4
60°	615.9	614.6	613.2	611.9	610.5	607.3	602.6	597.7	592.9	588.1	584.3
62.5°	569.0	566.7	564.5	562.3	560.1	557.1	553.4	549.8	546.0	542.3	538.8
65°	496.8	494.7	492.7	490.6	488.6	485.7	482.3	478.9	475.4	472.0	469.0
67.5°	423.4	421.8	420.1	418.5	416.9	414.4	411.3	408.3	405.2	402.1	399.7
70°	377.6	376.3	374.9	373.5	372.1	369.9	366.8	363.7	360.6	357.5	355.1
72.5°	330.5	329.2	327.8	326.5	325.1	323.4	321.4	319.4	317.4	315.4	313.0
75°	260.0	259.3	258.6	257.9	257.2	256.0	254.3	252.6	250.9	249.1	247.1
77.5°	196.8	195.7	194.5	193.4	192.2	191.3	190.6	189.9	189.1	188.5	187.4
80°	154.8	154.4	154.1	153.7	153.4	152.9	152.2	151.5	150.8	150.2	149.1
82.5°	115.1	115.1	115.0	114.9	114.8	114.6	114.2	113.8	113.4	113.0	111.7
85°	63.4	63.1	62.8	62.4	62.1	61.7	61.4	61.0	60.7	60.4	59.3
87.5°	22.4	22.2	22.0	21.8	21.6	21.3	21.1	20.8	20.5	20.2	19.5
90°	0.7	2.4	4.1	5.9	7.6	9.1	10.4	11.6	12.9	14.1	14.9
92.5°	14.2	14.1	13.9	13.8	13.6	13.9	14.5	15.1	15.8	16.4	16.8
95°	45.9	40.8	35.5	30.4	25.2	23.1	24.2	25.3	26.5	27.6	28.4
97.5°	91.2	76.5	62.0	47.4	32.7	26.8	29.3	31.8	34.3	36.9	37.6
100°	125.1	103.6	82.1	60.6	39.1	29.6	32.3	34.9	37.7	40.3	41.5
102.5°	162.5	157.9	153.3	148.8	144.2	130.8	108.5	86.1	63.7	41.4	43.0
105°	214.9	219.6	224.4	229.0	233.8	214.7	171.8	128.9	86.0	43.1	44.8
107.5°	274.7	278.5	282.4	286.1	289.9	266.1	214.7	163.3	111.8	60.4	58.6
110°	313.2	316.5	319.8	323.1	326.4	305.3	259.9	214.5	169.2	123.7	108.1



TEST NUMBER: P331595-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	349.4	352.3	355.3	358.1	361.0	356.9	345.7	334.5	323.3	312.0	254.8
115°	406.5	409.2	411.8	414.5	417.2	420.5	424.4	428.4	432.2	436.2	363.5
117.5°	457.6	460.5	463.5	466.5	469.5	472.3	475.0	477.8	480.4	483.1	465.5
120°	494.8	497.3	499.6	501.9	504.3	506.9	509.7	512.5	515.3	518.2	520.1
122.5°	526.5	529.1	531.5	534.0	536.4	539.3	542.3	545.4	548.5	551.6	552.7
125°	574.7	576.8	578.9	580.9	582.9	585.4	588.4	591.4	594.4	597.3	598.4
127.5°	618.4	620.7	623.0	625.2	627.5	629.8	632.0	634.2	636.4	638.6	640.3
130°	646.1	648.6	651.2	653.7	656.2	658.3	660.0	661.8	663.5	665.3	667.0
132.5°	674.5	676.6	678.7	680.9	683.0	684.9	686.6	688.3	690.1	691.9	693.3
135°	711.2	713.7	716.2	718.7	721.2	723.3	724.7	726.1	727.5	728.9	730.4
137.5°	748.4	750.1	751.9	753.7	755.4	757.1	758.7	760.3	761.9	763.6	765.1
140°	772.7	774.0	775.2	776.5	777.7	779.2	780.9	782.6	784.4	786.2	787.6
142.5°	793.0	794.2	795.4	796.5	797.6	799.1	801.1	803.1	805.1	807.1	808.4
145°	825.1	824.9	824.8	824.6	824.4	825.7	828.3	831.0	833.6	836.4	837.5
147.5°	852.8	852.3	851.7	851.1	850.5	851.5	854.1	856.8	859.4	862.0	862.9
150°	871.0	869.9	868.8	867.7	866.6	867.3	869.8	872.3	874.8	877.4	878.3
152.5°	886.3	885.0	883.8	882.5	881.3	881.9	884.3	886.7	889.1	891.5	892.4
155°	908.5	907.1	905.6	904.2	902.8	903.0	904.9	906.8	908.7	910.6	911.5
157.5°	925.8	924.6	923.4	922.2	921.1	921.1	922.4	923.7	925.0	926.3	927.5
160°	936.0	935.0	934.1	933.2	932.2	932.2	933.2	934.1	935.0	936.0	937.0
162.5°	945.0	944.1	943.2	942.2	941.3	941.2	942.0	942.9	943.7	944.5	945.5
165°	957.3	956.2	955.3	954.4	953.4	953.2	953.7	954.1	954.6	955.1	956.2
167.5°	966.2	965.3	964.4	963.4	962.5	962.3	962.7	963.1	963.6	964.0	965.1
170°	971.4	970.4	969.5	968.6	967.6	967.2	967.6	968.0	968.3	968.6	969.7
172.5°	974.7	973.8	972.9	971.9	971.0	970.7	971.0	971.3	971.6	971.9	973.0
175°	979.2	978.1	976.9	975.8	974.7	974.3	974.6	975.0	975.3	975.6	976.7
177.5°	979.9	979.0	978.1	977.2	976.3	975.9	976.0	976.2	976.3	976.4	977.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331595-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1602.7	1605.4	1608.2	1609.3	1608.7	1608.2	1607.6	1607.1
5°	1591.9	1594.6	1597.3	1598.4	1597.7	1597.0	1596.3	1595.6
7.5°	1573.9	1576.6	1579.4	1580.4	1579.6	1578.9	1578.1	1577.4
10°	1557.8	1560.5	1563.3	1564.2	1563.2	1562.1	1561.0	1560.0
12.5°	1538.8	1540.8	1542.7	1543.3	1542.5	1541.8	1541.0	1540.2
15°	1505.5	1506.9	1508.2	1508.1	1506.4	1504.7	1503.0	1501.3
17.5°	1466.0	1467.6	1469.2	1469.2	1467.4	1465.8	1464.2	1462.5
20°	1435.2	1436.2	1437.2	1437.0	1435.7	1434.3	1433.0	1431.6
22.5°	1402.6	1402.8	1403.0	1402.7	1401.9	1401.1	1400.2	1399.4
25°	1349.4	1350.1	1350.8	1350.8	1350.1	1349.4	1348.7	1348.0
27.5°	1297.1	1296.0	1294.9	1293.6	1292.0	1290.3	1288.7	1287.1
30°	1256.2	1255.2	1254.2	1252.9	1251.5	1250.1	1248.8	1247.4
32.5°	1216.2	1214.3	1212.4	1210.8	1209.4	1208.1	1206.7	1205.3
35°	1152.0	1149.9	1147.8	1146.0	1144.3	1142.6	1140.7	1139.0
37.5°	1087.5	1085.0	1082.5	1080.4	1078.7	1077.0	1075.4	1073.8
40°	1043.1	1040.1	1036.9	1034.7	1033.3	1032.0	1030.6	1029.2
42.5°	999.3	995.8	992.5	989.9	988.0	986.0	984.1	982.1
45°	931.9	928.1	924.3	921.7	920.3	919.0	917.6	916.3
47.5°	861.8	857.8	853.8	850.8	848.8	846.9	844.9	842.8
50°	816.8	812.0	807.2	804.0	802.2	800.5	798.8	797.1
52.5°	770.2	766.2	762.2	759.1	756.8	754.6	752.2	750.0
55°	700.5	696.4	692.4	689.4	687.7	686.0	684.3	682.5
57.5°	628.2	624.2	620.2	617.4	616.2	614.9	613.6	612.3
60°	580.6	576.7	573.0	570.6	569.6	568.6	567.4	566.4
62.5°	535.3	531.8	528.3	525.8	524.5	523.2	521.9	520.6
65°	465.9	462.7	459.7	457.3	455.6	453.8	452.1	450.4
67.5°	397.3	394.9	392.4	390.5	389.2	387.8	386.5	385.1
70°	352.6	350.3	347.9	346.0	344.6	343.3	341.8	340.5
72.5°	310.6	308.2	305.8	304.1	303.0	301.8	300.7	299.6
75°	245.1	243.0	241.0	240.2	241.0	241.6	242.3	243.0
77.5°	186.4	185.4	184.4	183.4	182.4	181.5	180.5	179.6
80°	148.0	147.0	146.0	145.1	144.4	143.8	143.1	142.4
82.5°	110.4	109.1	107.8	107.0	106.8	106.7	106.6	106.4
85°	58.3	57.3	56.2	55.5	55.2	54.8	54.5	54.1
87.5°	18.8	18.2	17.5	17.1	16.9	16.7	16.5	16.2
90°	15.8	16.5	17.3	17.9	18.2	18.5	18.8	19.1
92.5°	17.3	17.7	18.1	18.4	18.5	18.7	18.9	19.1
95°	29.2	29.9	30.7	31.0	30.9	30.7	30.6	30.4
97.5°	38.2	38.8	39.4	39.8	40.0	40.2	40.4	40.6
100°	42.8	44.0	45.3	46.2	46.5	46.8	47.1	47.4
102.5°	44.7	46.4	48.0	49.0	49.5	49.9	50.3	50.8
105°	46.6	48.3	50.0	51.2	51.8	52.5	53.1	53.7
107.5°	56.9	55.1	53.3	52.8	53.4	54.0	54.6	55.2
110°	92.3	76.5	60.9	53.3	53.9	54.6	55.2	55.8



TEST NUMBER: P331595-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	197.4	140.2	82.8	54.4	54.9	55.4	55.9	56.5
115°	290.7	217.9	145.2	103.2	91.9	80.6	69.3	58.0
117.5°	448.0	430.3	412.7	385.4	348.2	311.0	273.9	236.7
120°	522.0	523.8	525.7	516.0	494.8	473.6	452.4	431.2
122.5°	553.8	554.9	556.1	554.6	550.5	546.3	542.3	538.2
125°	599.6	600.7	601.8	602.6	603.0	603.5	604.0	604.4
127.5°	641.9	643.5	645.1	645.9	646.0	646.1	646.2	646.3
130°	668.7	670.4	672.2	673.0	672.8	672.7	672.5	672.4
132.5°	694.8	696.3	697.7	698.4	698.2	698.1	697.9	697.8
135°	732.1	733.6	735.2	735.8	735.5	735.2	734.9	734.6
137.5°	766.6	768.1	769.7	770.2	769.6	769.1	768.6	768.0
140°	789.0	790.4	791.8	792.1	791.3	790.5	789.7	789.0
142.5°	809.6	810.9	812.2	812.4	811.7	810.9	810.1	809.3
145°	838.5	839.6	840.7	840.9	840.1	839.3	838.5	837.8
147.5°	863.7	864.5	865.4	865.5	864.7	864.1	863.4	862.7
150°	879.2	880.2	881.1	881.2	880.4	879.6	878.8	878.1
152.5°	893.3	894.3	895.2	895.2	894.1	893.1	892.1	891.0
155°	912.4	913.4	914.3	914.1	912.9	911.7	910.4	909.2
157.5°	928.6	929.6	930.7	930.6	929.4	928.2	927.0	925.6
160°	937.9	938.9	939.8	939.7	938.6	937.5	936.4	935.3
162.5°	946.6	947.7	948.8	948.7	947.3	945.9	944.5	943.2
165°	957.4	958.4	959.5	959.5	958.4	957.4	956.2	955.1
167.5°	966.2	967.3	968.4	968.3	966.8	965.4	964.0	962.6
170°	970.8	971.8	972.9	972.8	971.4	970.0	968.6	967.1
172.5°	974.1	975.2	976.3	976.1	974.7	973.3	971.9	970.5
175°	977.9	978.9	980.0	979.8	978.2	976.6	975.0	973.5
177.5°	978.3	979.1	980.0	979.9	978.8	977.5	976.4	975.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0

(END OF REPORT)