

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331596-840

Luminaire Tested: **S122DIW-S1005D710U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331596-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D710U840-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6581.5 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331596-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331596-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	52
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	52	50	48	44
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	32	28	24	29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20	17
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25987	25987	25987
5°	26086	25710	25861
10°	25932	25450	25576
15°	25611	25120	25095
20°	25156	24624	24598
25°	24704	24015	24015
30°	24121	23457	23256
35°	23580	22787	22450
40°	22898	22118	21692
45°	22229	21450	20922
50°	21499	20760	20022
55°	20738	19952	19212
60°	19888	18991	18290
65°	18980	18032	17207
70°	17825	16877	16074
75°	16220	15540	15159
80°	14393	13966	13240
85°	11745	11189	10022



TEST NUMBER: P331596-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	151.3	2.3
10°-20°	425.9	6.5
20°-30°	626.0	9.5
30°-40°	727.1	11.0
40°-50°	726.3	11.0
50°-60°	633.4	9.6
60°-70°	468.3	7.1
70°-80°	265.3	4.0
80°-90°	74.9	1.1
90°-100°	56.3	0.9
100°-110°	174.8	2.7
110°-120°	298.7	4.5
120°-130°	392.8	6.0
130°-140°	440.9	6.7
140°-150°	432.3	6.6
150°-160°	362.6	5.5
160°-170°	240.5	3.7
170°-180°	84.1	1.3
0°-30°	1203.2	18.3
0°-40°	1930.3	29.3
0°-60°	3290.0	50.0
0°-90°	4098.5	62.3
90°-120°	529.8	8.0
90°-150°	1795.8	27.3
90°-180°	2483.0	37.7
0°-180°	6581.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1610	1603	1586	1598	1596	153
15°	1532	1522	1503	1508	1501	431
25°	1387	1374	1348	1351	1348	638
35°	1196	1180	1156	1147	1139	747
45°	974	962	939	923	916	751
55°	737	727	709	691	682	658
65°	497	487	472	458	450	491
75°	260	257	249	241	243	278
85°	63	62	60	56	54	73
90°	1	10	26	25	25	5
95°	39	46	48	48	46	45
105°	161	163	165	166	166	170
115°	300	304	303	302	300	296
125°	436	442	441	438	438	390
135°	564	572	574	573	571	436
145°	685	690	695	695	692	428
155°	783	785	788	791	789	360
165°	852	851	851	856	853	240
175°	886	884	883	888	884	84
180°	888	888	888	888	888	



TEST NUMBER: P331596-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1617.0	1615.6	1614.3	1612.9	1611.4	1609.3	1606.3	1603.3	1600.2	1597.2	1599.9
5°	1609.5	1608.2	1606.8	1605.4	1604.1	1601.4	1597.7	1593.9	1590.1	1586.3	1589.1
7.5°	1595.3	1593.2	1591.0	1588.9	1586.8	1583.8	1579.9	1576.1	1572.3	1568.4	1571.1
10°	1581.7	1579.3	1576.9	1574.5	1572.1	1568.8	1564.7	1560.5	1556.4	1552.3	1555.1
12.5°	1563.2	1560.9	1558.8	1556.7	1554.6	1551.5	1547.3	1543.2	1539.1	1535.0	1536.9
15°	1532.2	1530.1	1528.0	1526.0	1523.9	1520.7	1516.2	1511.7	1507.2	1502.8	1504.2
17.5°	1492.6	1490.5	1488.4	1486.3	1484.3	1481.0	1476.4	1471.9	1467.3	1462.9	1464.4
20°	1464.1	1462.0	1460.0	1457.8	1455.8	1452.4	1447.5	1442.8	1437.9	1433.1	1434.1
22.5°	1435.6	1432.7	1429.9	1426.9	1424.0	1420.4	1415.8	1411.3	1406.7	1402.2	1402.4
25°	1386.7	1383.9	1381.2	1378.5	1375.7	1371.4	1365.5	1359.7	1353.8	1348.0	1348.7
27.5°	1331.0	1328.5	1326.1	1323.5	1321.1	1317.6	1312.9	1308.3	1303.7	1299.1	1298.1
30°	1293.8	1291.1	1288.3	1285.6	1282.8	1278.9	1273.7	1268.6	1263.4	1258.2	1257.2
32.5°	1254.3	1252.0	1249.8	1247.6	1245.4	1241.6	1236.2	1230.7	1225.3	1219.8	1218.0
35°	1196.3	1192.9	1189.4	1186.0	1182.6	1178.1	1172.6	1167.1	1161.6	1156.1	1154.1
37.5°	1131.0	1128.0	1125.0	1122.0	1118.9	1114.7	1109.1	1103.7	1098.1	1092.7	1090.0
40°	1086.4	1083.7	1081.0	1078.2	1075.4	1071.4	1065.8	1060.4	1054.8	1049.4	1046.2
42.5°	1043.1	1040.4	1037.6	1034.9	1032.1	1027.9	1022.5	1016.9	1011.5	1005.9	1002.6
45°	973.5	971.1	968.7	966.2	963.8	960.1	954.9	949.8	944.6	939.4	935.6
47.5°	904.1	901.9	899.6	897.4	895.0	891.2	885.9	880.5	875.1	869.8	865.8
50°	855.9	854.1	852.4	850.7	849.0	845.7	840.9	836.1	831.2	826.5	821.6
52.5°	808.8	806.6	804.3	802.0	799.7	796.3	791.7	787.2	782.7	778.2	774.2
55°	736.7	734.6	732.6	730.5	728.4	725.3	721.2	717.1	713.0	708.8	704.7
57.5°	664.3	662.6	661.0	659.3	657.6	654.6	650.1	645.5	641.0	636.4	632.4
60°	615.9	614.6	613.2	611.9	610.5	607.3	602.6	597.7	592.9	588.1	584.3
62.5°	569.0	566.7	564.5	562.3	560.1	557.1	553.4	549.8	546.0	542.3	538.8
65°	496.8	494.7	492.7	490.6	488.6	485.7	482.3	478.9	475.4	472.0	469.0
67.5°	423.4	421.8	420.1	418.5	416.9	414.4	411.3	408.3	405.2	402.1	399.7
70°	377.6	376.3	374.9	373.5	372.1	369.9	366.8	363.7	360.6	357.5	355.1
72.5°	330.5	329.2	327.8	326.5	325.1	323.4	321.4	319.4	317.4	315.4	313.0
75°	260.0	259.3	258.6	257.9	257.2	256.0	254.3	252.6	250.9	249.1	247.1
77.5°	196.8	195.7	194.5	193.4	192.2	191.3	190.6	189.9	189.1	188.5	187.4
80°	154.8	154.4	154.1	153.7	153.4	152.9	152.2	151.5	150.8	150.2	149.1
82.5°	115.1	115.1	115.0	114.9	114.8	114.6	114.2	113.8	113.4	113.0	111.7
85°	63.4	63.1	62.8	62.4	62.1	61.7	61.4	61.0	60.7	60.4	59.3
87.5°	22.4	22.3	22.1	22.0	21.8	21.8	22.0	22.2	22.4	22.6	21.7
90°	0.7	2.7	4.7	6.8	8.8	11.6	15.2	18.9	22.5	26.3	25.9
92.5°	13.3	14.8	16.3	17.8	19.2	20.4	21.2	22.1	22.9	23.8	23.9
95°	39.0	40.6	42.3	43.9	45.6	46.7	47.0	47.3	47.7	48.0	48.0
97.5°	71.2	72.6	74.1	75.5	77.1	78.1	78.8	79.4	80.0	80.6	80.6
100°	95.1	96.5	97.9	99.2	100.5	101.4	101.9	102.4	102.9	103.4	103.4
102.5°	120.4	121.4	122.5	123.5	124.6	125.4	126.1	126.7	127.3	127.9	128.2
105°	161.1	161.6	162.1	162.6	163.1	163.5	163.9	164.2	164.5	164.9	165.2
107.5°	202.2	202.9	203.7	204.4	205.1	205.5	205.5	205.5	205.5	205.5	205.6
110°	228.5	229.5	230.6	231.6	232.6	233.1	233.1	233.1	233.1	233.1	233.1



TEST NUMBER: P331596-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	257.3	258.3	259.3	260.3	261.4	261.8	261.7	261.5	261.4	261.3	260.8
115°	299.7	300.7	301.7	302.8	303.8	304.1	303.8	303.4	303.1	302.8	302.6
117.5°	342.0	343.4	344.7	346.0	347.3	347.5	346.6	345.7	344.8	343.9	343.5
120°	370.2	371.5	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2	370.2
122.5°	396.0	397.6	399.2	400.7	402.3	402.7	401.7	400.8	399.9	399.0	398.6
125°	436.2	437.7	439.1	440.6	442.1	442.6	442.1	441.6	441.1	440.6	440.1
127.5°	475.2	477.2	479.1	480.9	482.8	483.5	482.9	482.3	481.7	481.1	480.5
130°	499.8	502.0	504.1	506.3	508.5	509.4	509.1	508.8	508.4	508.1	507.8
132.5°	527.5	529.2	531.0	532.7	534.4	535.4	535.4	535.5	535.6	535.6	534.9
135°	564.3	566.1	567.9	569.8	571.6	572.7	573.0	573.4	573.7	574.0	573.8
137.5°	603.1	604.6	606.1	607.6	609.0	610.1	610.5	611.0	611.4	611.8	611.7
140°	626.5	627.9	629.4	631.0	632.5	633.6	634.5	635.3	636.1	636.9	636.9
142.5°	650.5	652.0	653.5	655.0	656.4	657.5	658.0	658.6	659.1	659.7	659.8
145°	684.9	686.1	687.2	688.4	689.6	690.6	691.7	692.7	693.7	694.7	694.8
147.5°	715.7	717.0	718.4	719.8	721.2	722.3	723.0	723.6	724.3	725.0	725.3
150°	736.6	737.6	738.6	739.6	740.6	741.4	742.1	742.8	743.5	744.2	744.7
152.5°	755.2	756.2	757.2	758.2	759.2	760.1	760.9	761.7	762.5	763.4	764.0
155°	783.0	783.6	784.1	784.6	785.1	785.6	786.1	786.6	787.1	787.6	788.4
157.5°	806.9	807.3	807.6	807.9	808.3	808.6	808.9	809.2	809.5	809.8	810.9
160°	821.3	821.6	821.9	822.3	822.6	822.9	823.0	823.2	823.3	823.5	824.6
162.5°	834.5	834.6	834.7	834.7	834.8	834.9	835.1	835.3	835.4	835.6	836.7
165°	852.0	851.8	851.7	851.5	851.4	851.3	851.3	851.3	851.3	851.3	852.4
167.5°	866.8	866.3	865.8	865.3	864.7	864.4	864.4	864.3	864.3	864.3	865.5
170°	874.5	874.0	873.5	873.0	872.5	872.2	872.0	871.8	871.7	871.5	872.7
172.5°	879.9	879.4	878.9	878.4	877.9	877.6	877.4	877.3	877.1	876.9	878.1
175°	886.5	886.1	885.6	885.0	884.5	884.1	883.7	883.4	883.1	882.7	883.9
177.5°	889.2	888.8	888.4	888.0	887.6	887.3	887.0	886.8	886.5	886.2	887.0
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331596-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1602.7	1605.4	1608.2	1609.3	1608.7	1608.2	1607.6	1607.1
5°	1591.9	1594.6	1597.3	1598.4	1597.7	1597.0	1596.3	1595.6
7.5°	1573.9	1576.6	1579.4	1580.4	1579.6	1578.9	1578.1	1577.4
10°	1557.8	1560.5	1563.3	1564.2	1563.2	1562.1	1561.0	1560.0
12.5°	1538.8	1540.8	1542.7	1543.3	1542.5	1541.8	1541.0	1540.2
15°	1505.5	1506.9	1508.2	1508.1	1506.4	1504.7	1503.0	1501.3
17.5°	1466.0	1467.6	1469.2	1469.2	1467.4	1465.8	1464.2	1462.5
20°	1435.2	1436.2	1437.2	1437.0	1435.7	1434.3	1433.0	1431.6
22.5°	1402.6	1402.8	1403.0	1402.7	1401.9	1401.1	1400.2	1399.4
25°	1349.4	1350.1	1350.8	1350.8	1350.1	1349.4	1348.7	1348.0
27.5°	1297.1	1296.0	1294.9	1293.6	1292.0	1290.3	1288.7	1287.1
30°	1256.2	1255.2	1254.2	1252.9	1251.5	1250.1	1248.8	1247.4
32.5°	1216.2	1214.3	1212.4	1210.8	1209.4	1208.1	1206.7	1205.3
35°	1152.0	1149.9	1147.8	1146.0	1144.3	1142.6	1140.7	1139.0
37.5°	1087.5	1085.0	1082.5	1080.4	1078.7	1077.0	1075.4	1073.8
40°	1043.1	1040.1	1036.9	1034.7	1033.3	1032.0	1030.6	1029.2
42.5°	999.3	995.8	992.5	989.9	988.0	986.0	984.1	982.1
45°	931.9	928.1	924.3	921.7	920.3	919.0	917.6	916.3
47.5°	861.8	857.8	853.8	850.8	848.8	846.9	844.9	842.8
50°	816.8	812.0	807.2	804.0	802.2	800.5	798.8	797.1
52.5°	770.2	766.2	762.2	759.1	756.8	754.6	752.2	750.0
55°	700.5	696.4	692.4	689.4	687.7	686.0	684.3	682.5
57.5°	628.2	624.2	620.2	617.4	616.2	614.9	613.6	612.3
60°	580.6	576.7	573.0	570.6	569.6	568.6	567.4	566.4
62.5°	535.3	531.8	528.3	525.8	524.5	523.2	521.9	520.6
65°	465.9	462.7	459.7	457.3	455.6	453.8	452.1	450.4
67.5°	397.3	394.9	392.4	390.5	389.2	387.8	386.5	385.1
70°	352.6	350.3	347.9	346.0	344.6	343.3	341.8	340.5
72.5°	310.6	308.2	305.8	304.1	303.0	301.8	300.7	299.6
75°	245.1	243.0	241.0	240.2	241.0	241.6	242.3	243.0
77.5°	186.4	185.4	184.4	183.4	182.4	181.5	180.5	179.6
80°	148.0	147.0	146.0	145.1	144.4	143.8	143.1	142.4
82.5°	110.4	109.1	107.8	107.0	106.8	106.7	106.6	106.4
85°	58.3	57.3	56.2	55.5	55.2	54.8	54.5	54.1
87.5°	20.8	19.9	19.0	18.5	18.2	18.0	17.7	17.5
90°	25.5	25.2	24.9	24.8	24.9	25.1	25.3	25.4
92.5°	23.9	24.0	24.1	24.1	24.1	24.2	24.2	24.2
95°	48.0	48.0	48.0	47.8	47.5	47.2	46.8	46.5
97.5°	80.6	80.6	80.6	80.6	80.6	80.6	80.5	80.5
100°	103.4	103.4	103.4	103.3	103.2	103.0	102.8	102.7
102.5°	128.3	128.4	128.6	128.6	128.4	128.2	128.1	127.8
105°	165.5	165.8	166.2	166.3	166.3	166.3	166.3	166.3
107.5°	205.7	205.9	206.0	205.7	204.9	204.2	203.4	202.7
110°	233.1	233.1	233.1	232.8	232.3	231.8	231.3	230.9





TEST NUMBER: P331596-840

CATALOG NUMBER: S122DIW-S1005D710U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	260.4	260.0	259.6	259.2	258.9	258.5	258.1	257.8
115°	302.5	302.3	302.1	301.7	301.2	300.7	300.2	299.7
117.5°	343.1	342.6	342.2	341.7	341.2	340.7	340.2	339.7
120°	370.2	370.2	370.2	369.9	369.4	368.9	368.4	367.9
122.5°	398.2	397.8	397.4	397.0	396.6	396.3	395.9	395.6
125°	439.6	439.1	438.6	438.3	438.2	438.0	437.8	437.7
127.5°	479.9	479.3	478.7	478.2	477.6	477.1	476.6	476.1
130°	507.5	507.1	506.8	506.2	505.5	504.9	504.2	503.6
132.5°	534.2	533.4	532.7	532.1	531.6	531.0	530.5	530.0
135°	573.7	573.5	573.4	573.0	572.5	572.0	571.5	571.0
137.5°	611.5	611.4	611.3	610.9	610.2	609.6	608.8	608.1
140°	636.9	636.9	636.9	636.6	636.0	635.3	634.6	634.0
142.5°	660.0	660.1	660.2	660.0	659.3	658.6	658.0	657.3
145°	695.0	695.2	695.3	695.1	694.4	693.8	693.1	692.5
147.5°	725.7	726.0	726.4	726.3	725.7	725.0	724.4	723.8
150°	745.1	745.6	746.1	746.1	745.6	745.1	744.7	744.2
152.5°	764.6	765.2	765.9	765.9	765.2	764.6	764.0	763.4
155°	789.2	790.1	790.9	791.1	790.6	790.1	789.6	789.1
157.5°	812.0	813.1	814.3	814.5	813.6	812.8	812.0	811.2
160°	825.6	826.6	827.6	827.7	827.1	826.4	825.8	825.1
162.5°	837.8	839.0	840.1	840.2	839.4	838.7	837.9	837.1
165°	853.6	854.7	856.0	856.2	855.3	854.4	853.6	852.8
167.5°	866.7	867.8	869.0	869.1	868.3	867.4	866.6	865.7
170°	873.8	875.0	876.2	876.3	875.3	874.2	873.2	872.2
172.5°	879.3	880.4	881.6	881.6	880.7	879.7	878.7	877.7
175°	885.0	886.3	887.5	887.5	886.5	885.6	884.5	883.5
177.5°	887.8	888.6	889.4	889.4	888.6	887.8	887.0	886.2
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0

(END OF REPORT)