

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331599-840

Luminaire Tested: **S122DIW-S1005D970U840-4F0-1E-UDD-D**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331599-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D970U840-4F0-1E-UDD-D
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7985.4 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331599-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P331599-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	95	90	86	82	87	83	79	76	69	66	63	56	54	52	44	42	41	35				
2	86	78	72	66	79	72	66	61	59	55	51	48	45	42	38	35	34	29				
3	78	68	61	54	71	63	56	50	52	47	43	42	38	35	33	30	28	24				
4	71	60	52	45	65	55	48	42	46	40	36	37	33	30	29	26	24	20				
5	65	53	45	39	60	49	42	36	41	35	31	33	29	25	26	23	20	17				
6	60	48	39	33	55	44	36	31	37	31	27	30	25	22	24	20	18	15				
7	56	43	35	29	51	40	32	27	33	27	23	27	23	19	21	18	16	13				
8	51	39	31	25	47	36	29	24	30	24	20	25	20	17	20	16	14	11				
9	48	35	28	23	44	33	26	21	28	22	18	23	18	15	18	15	13	10				
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	14	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17241	17241	17241
5°	17327	16597	16534
10°	17217	16106	15925
15°	16980	15587	15284
20°	16681	15031	14669
25°	16384	14494	14107
30°	15966	13945	13546
35°	15544	13412	13150
40°	15099	12958	12754
45°	14678	12551	12415
50°	14226	12185	12082
55°	13750	11789	11742
60°	13168	11380	11382
65°	12566	10901	10957
70°	11886	10385	10497
75°	11021	9881	10071
80°	9646	9362	9643
85°	8334	8915	9308



TEST NUMBER: P331599-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.2	1.3
10°-20°	290.2	3.6
20°-30°	439.7	5.5
30°-40°	535.6	6.7
40°-50°	576.2	7.2
50°-60°	559.5	7.0
60°-70°	488.6	6.1
70°-80°	376.1	4.7
80°-90°	255.7	3.2
90°-100°	218.4	2.7
100°-110°	290.1	3.6
110°-120°	519.9	6.5
120°-130°	766.6	9.6
130°-140°	785.1	9.8
140°-150°	714.9	9.0
150°-160°	572.1	7.2
160°-170°	368.6	4.6
170°-180°	126.9	1.6
0°-30°	831.1	10.4
0°-40°	1366.6	17.1
0°-60°	2502.3	31.3
0°-90°	3622.7	45.4
90°-120°	1028.4	12.9
90°-150°	3295.1	41.3
90°-180°	4363.0	54.6
0°-180°	7985.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1068	1068	1068	1068	1068	
5°	1071	1066	1057	1066	1065	102
15°	1022	1024	1024	1038	1037	288
25°	929	940	953	971	976	427
35°	800	827	856	889	901	500
45°	656	699	752	798	816	506
55°	503	560	639	693	715	450
65°	344	420	511	572	594	341
75°	190	278	376	440	463	201
85°	56	152	251	313	337	60
90°	16	117	224	288	311	13
95°	75	119	216	277	297	86
105°	301	361	192	254	278	322
115°	561	598	688	307	235	552
125°	788	803	868	915	933	703
135°	972	988	1012	1052	1064	751
145°	1126	1126	1142	1157	1160	704
155°	1240	1232	1243	1248	1241	571
165°	1307	1301	1304	1310	1304	369
175°	1336	1330	1332	1338	1329	127
180°	1334	1334	1334	1334	1334	



TEST NUMBER: P331599-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8
2.5°	1074.1	1073.3	1072.4	1071.6	1070.8	1069.3	1067.4	1065.5	1063.6	1061.7	1063.1
5°	1071.0	1070.0	1068.9	1067.8	1066.8	1065.3	1063.3	1061.2	1059.1	1057.0	1059.1
7.5°	1061.4	1060.7	1060.0	1059.3	1058.6	1057.5	1055.9	1054.3	1052.8	1051.2	1053.6
10°	1054.0	1053.3	1052.6	1051.9	1051.2	1050.4	1049.4	1048.2	1047.2	1046.2	1048.9
12.5°	1041.6	1041.7	1041.9	1042.0	1042.1	1041.8	1041.1	1040.3	1039.6	1038.7	1041.6
15°	1021.5	1022.2	1022.8	1023.5	1024.2	1024.5	1024.5	1024.5	1024.5	1024.5	1027.6
17.5°	995.4	996.9	998.4	999.8	1001.2	1002.5	1003.6	1004.7	1005.8	1006.9	1010.2
20°	978.2	979.9	981.6	983.3	985.0	986.5	988.0	989.3	990.7	992.1	995.8
22.5°	959.6	961.5	963.5	965.5	967.6	969.5	971.4	973.3	975.2	977.1	981.0
25°	928.6	931.0	933.4	935.8	938.3	941.0	944.0	947.2	950.3	953.3	957.5
27.5°	891.4	895.3	899.3	903.2	907.2	910.9	914.5	918.2	921.8	925.5	930.7
30°	866.7	871.1	875.7	880.1	884.5	889.1	893.5	898.0	902.4	907.0	912.4
32.5°	839.4	844.4	849.5	854.5	859.5	864.6	870.0	875.3	880.6	885.9	892.2
35°	800.1	806.0	811.8	817.7	823.5	829.7	836.3	842.7	849.3	855.9	863.4
37.5°	757.4	764.2	770.9	777.6	784.4	791.9	800.4	808.9	817.4	825.9	834.2
40°	728.9	736.5	744.1	751.6	759.2	767.6	776.9	786.2	795.5	804.8	813.7
42.5°	701.8	709.2	716.8	724.4	732.0	741.0	751.7	762.4	773.1	783.8	793.5
45°	656.2	665.5	674.8	684.1	693.4	704.0	716.1	728.1	740.1	752.1	762.9
47.5°	611.4	621.5	631.6	641.7	651.8	663.9	678.0	692.1	706.2	720.2	731.4
50°	580.4	591.1	601.7	612.4	623.0	636.1	651.6	667.0	682.5	698.0	709.7
52.5°	550.7	561.9	573.1	584.3	595.5	609.3	625.5	641.9	658.1	674.5	686.4
55°	503.0	515.3	527.8	540.2	552.5	567.6	585.5	603.4	621.3	639.1	651.6
57.5°	456.0	469.9	483.8	497.9	511.8	527.9	546.1	564.3	582.6	600.8	614.1
60°	422.5	437.3	452.1	466.9	481.7	498.9	518.5	538.1	557.6	577.2	590.4
62.5°	392.8	408.1	423.4	438.8	454.1	471.6	491.2	510.8	530.5	550.1	563.9
65°	343.6	360.4	377.3	394.2	411.0	429.6	449.9	470.1	490.4	510.7	524.8
67.5°	298.4	316.0	333.6	351.2	368.8	388.0	408.8	429.6	450.3	471.1	485.3
70°	266.2	284.1	301.9	319.8	337.7	357.3	378.7	400.0	421.3	442.6	457.4
72.5°	236.5	254.9	273.4	291.8	310.2	330.2	351.8	373.4	395.1	416.7	431.1
75°	190.4	209.6	228.8	248.1	267.4	288.0	310.0	332.0	354.1	376.1	390.8
77.5°	145.8	165.9	186.1	206.2	226.4	247.6	270.0	292.4	314.7	337.1	351.8
80°	116.0	137.0	158.0	179.0	200.0	221.7	244.0	266.4	288.7	311.0	325.5
82.5°	91.3	112.0	132.7	153.4	174.1	195.8	218.4	241.1	263.7	286.3	300.7
85°	55.7	77.1	98.4	119.7	141.0	162.7	184.7	206.7	228.7	250.7	265.2
87.5°	30.5	51.5	72.5	93.4	114.4	136.0	158.4	180.8	203.1	225.5	239.7
90°	16.5	38.8	61.1	83.3	105.6	128.7	152.4	176.1	199.9	223.6	238.4
92.5°	33.7	52.1	70.5	88.8	107.1	127.3	149.4	171.5	193.5	215.5	229.5
95°	75.1	84.2	93.3	102.4	111.5	127.0	149.2	171.4	193.5	215.6	229.7
97.5°	135.3	129.8	124.2	118.7	113.0	121.9	145.2	168.4	191.8	215.0	228.6
100°	181.7	165.0	148.3	131.7	115.0	118.2	141.1	164.0	186.8	209.7	224.2
102.5°	231.4	236.7	242.2	247.5	253.0	249.7	238.0	226.2	214.4	202.7	217.3
105°	301.0	317.5	333.9	350.3	366.7	354.6	314.0	273.3	232.6	192.0	206.3
107.5°	382.4	395.6	408.8	421.9	435.0	415.2	362.0	309.0	255.9	202.8	212.0
110°	433.6	445.0	456.5	467.8	479.2	462.3	417.2	372.1	327.0	281.9	271.5



TEST NUMBER: P331599-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.1	492.8	502.6	512.4	522.1	527.4	528.1	528.8	529.6	530.3	463.0
115°	561.1	568.5	575.9	583.3	590.8	604.9	625.7	646.5	667.4	688.2	599.3
117.5°	629.1	635.7	642.3	648.8	655.4	667.6	685.6	703.7	721.6	739.6	725.8
120°	680.1	684.7	689.3	693.9	698.5	709.6	727.2	744.8	762.4	780.0	792.2
122.5°	723.4	727.3	731.2	735.2	739.1	749.6	766.8	783.9	801.0	818.2	829.1
125°	787.6	790.4	793.1	796.0	798.8	807.7	822.7	837.9	852.9	868.0	878.8
127.5°	847.3	850.0	852.7	855.5	858.2	865.6	877.5	889.4	901.3	913.2	923.9
130°	885.0	888.2	891.2	894.3	897.4	903.7	913.3	922.9	932.5	942.1	952.7
132.5°	923.6	926.2	928.8	931.4	933.9	939.2	947.2	955.0	963.0	970.9	980.9
135°	972.3	975.7	979.2	982.6	986.0	990.4	995.8	1001.2	1006.5	1011.9	1021.3
137.5°	1023.1	1025.4	1027.7	1030.1	1032.4	1035.4	1039.2	1042.8	1046.5	1050.2	1058.6
140°	1056.2	1057.6	1058.9	1060.4	1061.8	1063.9	1067.0	1070.1	1073.1	1076.1	1083.6
142.5°	1084.0	1085.2	1086.4	1087.6	1088.8	1090.9	1093.7	1096.5	1099.3	1102.2	1108.3
145°	1126.1	1125.9	1125.7	1125.5	1125.3	1127.0	1130.6	1134.3	1137.9	1141.6	1145.1
147.5°	1164.2	1163.3	1162.5	1161.6	1160.8	1162.3	1165.9	1169.4	1173.1	1176.7	1178.1
150°	1188.8	1187.3	1185.8	1184.4	1182.9	1183.8	1187.2	1190.6	1194.1	1197.5	1198.8
152.5°	1209.7	1208.0	1206.3	1204.7	1203.0	1203.8	1207.0	1210.3	1213.6	1216.8	1218.1
155°	1240.0	1238.0	1236.1	1234.2	1232.2	1232.5	1235.2	1237.7	1240.3	1242.8	1244.2
157.5°	1263.7	1262.1	1260.4	1258.8	1257.2	1257.3	1259.1	1260.9	1262.6	1264.5	1266.0
160°	1277.6	1276.4	1275.1	1273.7	1272.4	1272.4	1273.7	1275.1	1276.4	1277.6	1278.9
162.5°	1290.0	1288.7	1287.4	1286.1	1284.9	1284.8	1285.9	1287.0	1288.1	1289.2	1290.6
165°	1306.6	1305.3	1303.9	1302.7	1301.4	1301.1	1301.7	1302.3	1303.0	1303.6	1305.1
167.5°	1318.9	1317.6	1316.4	1315.0	1313.7	1313.4	1314.0	1314.6	1315.2	1315.9	1317.3
170°	1325.9	1324.5	1323.3	1322.0	1320.7	1320.3	1320.7	1321.1	1321.6	1322.0	1323.5
172.5°	1330.5	1329.2	1327.9	1326.7	1325.3	1324.9	1325.3	1325.8	1326.2	1326.7	1328.2
175°	1336.5	1334.9	1333.4	1332.0	1330.5	1329.9	1330.4	1330.8	1331.2	1331.6	1333.1
177.5°	1337.5	1336.3	1335.0	1333.8	1332.6	1332.1	1332.3	1332.4	1332.6	1332.8	1334.0
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5



TEST NUMBER: P331599-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8	1067.8
2.5°	1064.4	1065.8	1067.2	1067.6	1067.0	1066.5	1065.9	1065.4
5°	1061.2	1063.3	1065.3	1066.1	1065.8	1065.5	1065.1	1064.8
7.5°	1056.1	1058.6	1061.1	1062.2	1061.8	1061.5	1061.1	1060.8
10°	1051.7	1054.5	1057.2	1058.4	1058.0	1057.7	1057.4	1057.0
12.5°	1044.3	1047.0	1049.8	1051.0	1050.7	1050.3	1050.0	1049.7
15°	1030.8	1033.8	1036.9	1038.3	1037.9	1037.6	1037.2	1036.9
17.5°	1013.4	1016.6	1019.9	1021.5	1021.5	1021.5	1021.5	1021.5
20°	999.6	1003.4	1007.1	1009.1	1009.1	1009.1	1009.1	1009.1
22.5°	984.7	988.6	992.3	994.5	995.0	995.6	996.1	996.7
25°	961.6	965.7	969.9	972.4	973.5	974.5	975.5	976.5
27.5°	935.9	941.2	946.4	949.4	950.2	950.9	951.7	952.4
30°	918.0	923.4	929.0	932.2	933.2	934.2	935.3	936.3
32.5°	898.6	904.8	911.2	915.2	917.2	919.0	920.9	922.7
35°	871.0	878.6	886.2	891.1	893.5	896.0	898.4	900.7
37.5°	842.6	851.0	859.4	864.8	867.4	870.0	872.5	875.0
40°	822.6	831.6	840.5	846.6	849.7	852.7	855.9	859.0
42.5°	803.2	813.0	822.8	829.2	832.3	835.5	838.5	841.6
45°	773.5	784.2	794.8	801.8	805.3	808.7	812.1	815.6
47.5°	742.6	753.7	764.9	772.3	776.1	779.9	783.7	787.5
50°	721.3	733.1	744.8	752.6	756.3	760.0	763.9	767.6
52.5°	698.4	710.3	722.4	730.3	734.4	738.5	742.6	746.6
55°	664.0	676.3	688.7	697.1	701.6	706.1	710.5	715.0
57.5°	627.5	640.9	654.2	663.1	667.6	672.2	676.7	681.3
60°	603.4	616.5	629.5	638.5	643.3	648.1	653.0	657.7
62.5°	577.8	591.7	605.6	614.8	619.4	623.9	628.4	633.0
65°	539.0	553.0	567.1	576.4	580.9	585.3	589.9	594.3
67.5°	499.6	513.8	528.1	537.6	542.2	546.8	551.6	556.2
70°	472.2	487.0	501.8	511.2	515.3	519.5	523.6	527.8
72.5°	445.7	460.2	474.6	484.4	489.4	494.3	499.3	504.2
75°	405.7	420.4	435.3	444.8	449.3	453.8	458.3	462.7
77.5°	366.5	381.2	396.0	405.8	410.5	415.4	420.2	425.0
80°	339.9	354.5	368.9	378.5	383.3	388.1	392.9	397.8
82.5°	315.2	329.6	344.1	353.6	358.1	362.6	367.2	371.7
85°	279.6	294.1	308.5	318.1	323.0	327.8	332.5	337.4
87.5°	254.0	268.2	282.5	291.9	296.3	300.8	305.3	309.8
90°	253.3	268.1	282.9	292.6	297.2	301.7	306.3	310.8
92.5°	243.6	257.6	271.7	280.9	285.3	289.6	294.1	298.4
95°	243.9	258.0	272.2	281.2	285.1	289.0	293.0	296.9
97.5°	242.2	255.8	269.3	278.3	282.7	286.9	291.2	295.6
100°	238.6	253.1	267.5	276.9	281.0	285.3	289.5	293.7
102.5°	232.0	246.7	261.4	270.9	275.3	279.6	284.1	288.4
105°	220.8	235.2	249.5	259.0	263.7	268.3	273.0	277.6
107.5°	221.2	230.2	239.4	246.3	251.0	255.6	260.2	264.9
110°	260.9	250.5	240.0	237.2	241.9	246.5	251.2	255.8



TEST NUMBER: P331599-840

CATALOG NUMBER: S122DIW-S1005D970U840-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	395.8	328.6	261.4	229.9	234.5	238.9	243.4	247.8
115°	510.3	421.3	332.3	282.1	270.4	258.7	247.1	235.4
117.5°	712.0	698.1	684.3	653.8	606.5	559.3	512.1	464.8
120°	804.5	816.7	828.9	822.4	797.2	772.0	746.9	721.8
122.5°	840.0	850.9	861.7	866.1	863.6	861.2	858.9	856.5
125°	889.6	900.4	911.2	918.4	922.2	925.9	929.7	933.4
127.5°	934.6	945.3	956.0	963.0	966.1	969.4	972.5	975.6
130°	963.3	973.9	984.5	991.1	993.6	996.1	998.8	1001.3
132.5°	990.9	1000.9	1010.9	1017.1	1019.7	1022.3	1024.8	1027.3
135°	1030.7	1040.0	1049.4	1055.2	1057.5	1059.9	1062.2	1064.5
137.5°	1067.0	1075.5	1083.9	1088.9	1090.6	1092.2	1093.8	1095.4
140°	1091.0	1098.4	1105.9	1110.0	1111.1	1112.1	1113.1	1114.1
142.5°	1114.5	1120.6	1126.8	1130.3	1131.0	1131.8	1132.5	1133.2
145°	1148.7	1152.3	1155.8	1157.9	1158.5	1159.2	1159.8	1160.5
147.5°	1179.4	1180.8	1182.2	1182.9	1182.9	1182.8	1182.7	1182.6
150°	1200.1	1201.3	1202.6	1202.7	1201.7	1200.6	1199.5	1198.5
152.5°	1219.4	1220.6	1221.9	1221.9	1220.5	1219.1	1217.7	1216.3
155°	1245.5	1246.7	1248.0	1247.8	1246.1	1244.4	1242.6	1240.9
157.5°	1267.4	1268.9	1270.3	1270.2	1268.5	1266.9	1265.2	1263.5
160°	1280.2	1281.4	1282.7	1282.6	1281.1	1279.6	1278.2	1276.7
162.5°	1292.1	1293.5	1295.1	1294.8	1292.9	1291.1	1289.3	1287.5
165°	1306.7	1308.2	1309.7	1309.7	1308.2	1306.7	1305.1	1303.6
167.5°	1318.8	1320.3	1321.8	1321.6	1319.7	1317.8	1315.9	1313.9
170°	1325.0	1326.5	1328.0	1327.8	1325.9	1323.9	1322.0	1320.1
172.5°	1329.6	1331.1	1332.6	1332.4	1330.5	1328.6	1326.7	1324.7
175°	1334.6	1336.2	1337.7	1337.4	1335.1	1333.0	1330.9	1328.8
177.5°	1335.2	1336.4	1337.6	1337.5	1335.8	1334.3	1332.8	1331.3
180°	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5	1333.5

(END OF REPORT)