

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332112-927

Luminaire Tested: **S123DIW-S340D1320U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332112-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S340D1320U927-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1320 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5301.9 lumens  
Efficiency: N/A  
Efficacy: 113.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332112-927

CATALOG NUMBER: S123DIW-S340D1320U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332112-927

CATALOG NUMBER: S123DIW-S340D1320U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	91	87	83	80	81	77	74	71	59	57	55	42	41	39	26	25	25	18
2	83	76	70	65	73	67	63	58	51	48	45	37	35	33	23	22	21	15
3	76	67	60	54	67	59	53	49	45	41	38	32	30	28	20	19	18	13
4	69	59	51	46	61	52	46	41	40	36	32	29	26	24	18	17	15	11
5	63	52	45	39	56	47	40	35	36	31	28	26	23	20	16	15	13	9
6	58	47	39	33	51	42	35	30	32	27	24	23	20	18	15	13	12	8
7	54	42	34	29	47	37	31	26	29	24	21	21	18	16	13	12	10	7
8	50	38	31	25	44	34	27	23	26	22	18	19	16	14	12	10	9	6
9	46	34	27	22	41	31	25	20	24	19	16	17	14	12	11	9	8	6
10	43	31	25	20	38	28	22	18	22	18	15	16	13	11	10	9	7	5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4621	4621	4621
5°	4643	4578	4611
10°	4611	4539	4568
15°	4558	4488	4496
20°	4495	4415	4418
25°	4410	4327	4318
30°	4318	4230	4197
35°	4221	4127	4075
40°	4118	4014	3953
45°	4007	3911	3815
50°	3893	3783	3677
55°	3748	3652	3539
60°	3599	3496	3384
65°	3469	3326	3224
70°	3276	3138	2996
75°	2994	2886	2766
80°	2703	2585	2566
85°	2371	2285	2186



TEST NUMBER: P332112-927

CATALOG NUMBER: S123DIW-S340D1320U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.4	0.8
10°-20°	114.2	2.2
20°-30°	168.7	3.2
30°-40°	197.0	3.7
40°-50°	198.1	3.7
50°-60°	174.0	3.3
60°-70°	129.6	2.4
70°-80°	73.8	1.4
80°-90°	25.0	0.5
90°-100°	49.8	0.9
100°-110°	237.6	4.5
110°-120°	570.6	10.8
120°-130°	726.7	13.7
130°-140°	776.4	14.6
140°-150°	726.0	13.7
150°-160°	585.6	11.0
160°-170°	378.0	7.1
170°-180°	130.3	2.5
0°-30°	323.3	6.1
0°-40°	520.3	9.8
0°-60°	892.4	16.8
0°-90°	1120.9	21.1
90°-120°	858.1	16.2
90°-150°	3087.2	58.2
90°-180°	4181.0	78.9
0°-180°	5301.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	429	429	429	429	429	
5°	430	428	424	427	427	41
15°	409	407	403	405	404	115
25°	371	369	364	365	364	171
35°	321	319	314	312	310	201
45°	263	262	257	253	251	203
55°	200	199	195	191	189	179
65°	136	134	131	128	127	134
75°	72	70	69	68	66	77
85°	19	18	18	18	18	21
90°	1	11	24	28	31	4
95°	62	23	32	38	39	77
105°	304	309	223	53	45	322
115°	569	576	585	594	599	562
125°	803	811	815	817	819	717
135°	999	1005	1010	1012	1010	769
145°	1153	1160	1162	1164	1164	722
155°	1270	1268	1269	1274	1268	585
165°	1340	1336	1335	1343	1336	378
175°	1371	1366	1367	1373	1366	130
180°	1371	1371	1371	1371	1371	



TEST NUMBER: P332112-927

CATALOG NUMBER: S123DIW-S340D1320U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	430.8	430.5	430.2	430.0	429.7	429.2	428.5	427.8	427.1	426.4	427.0
5°	429.7	429.2	428.8	428.4	428.0	427.4	426.4	425.6	424.6	423.7	424.5
7.5°	425.5	425.0	424.6	424.2	423.8	423.1	422.2	421.3	420.3	419.4	420.1
10°	421.9	421.5	421.0	420.6	420.3	419.5	418.4	417.4	416.3	415.3	416.0
12.5°	417.2	416.8	416.5	416.1	415.8	415.1	414.2	413.1	412.1	411.1	411.7
15°	409.0	408.7	408.3	408.0	407.7	406.9	405.9	404.8	403.8	402.7	403.4
17.5°	399.4	399.0	398.6	398.2	397.8	397.0	395.9	394.9	393.8	392.8	393.2
20°	392.4	391.9	391.4	390.9	390.4	389.6	388.6	387.5	386.4	385.4	385.7
22.5°	384.4	383.9	383.4	382.9	382.5	381.7	380.6	379.5	378.4	377.4	377.6
25°	371.3	370.8	370.3	369.9	369.4	368.6	367.5	366.5	365.4	364.3	364.4
27.5°	357.4	356.9	356.4	355.9	355.5	354.7	353.6	352.4	351.3	350.1	350.1
30°	347.4	346.9	346.5	346.1	345.7	344.9	343.8	342.6	341.5	340.3	340.3
32.5°	337.3	336.8	336.2	335.6	335.2	334.4	333.5	332.6	331.8	330.9	330.4
35°	321.2	320.7	320.1	319.6	319.2	318.4	317.3	316.2	315.2	314.1	313.6
37.5°	304.6	304.0	303.3	302.7	302.1	301.3	300.2	299.0	298.0	296.9	296.4
40°	293.1	292.6	292.1	291.6	291.1	290.3	289.1	288.0	286.8	285.7	285.0
42.5°	281.5	281.0	280.4	279.9	279.3	278.5	277.3	276.2	275.0	273.9	273.2
45°	263.2	262.8	262.5	262.2	261.9	261.2	260.1	259.0	257.9	256.9	256.0
47.5°	244.9	244.5	244.0	243.5	243.0	242.3	241.3	240.3	239.3	238.3	237.3
50°	232.5	232.1	231.7	231.3	230.9	230.1	229.1	228.1	227.0	225.9	225.0
52.5°	219.5	219.3	219.0	218.7	218.4	217.7	216.6	215.5	214.4	213.2	212.5
55°	199.7	199.6	199.6	199.5	199.4	198.8	197.7	196.6	195.6	194.6	193.6
57.5°	180.8	180.5	180.2	180.0	179.7	179.1	178.2	177.4	176.6	175.7	174.9
60°	167.2	167.2	167.1	167.0	166.9	166.4	165.3	164.4	163.4	162.4	161.7
62.5°	155.1	154.9	154.7	154.5	154.2	153.7	152.7	151.7	150.7	149.7	149.0
65°	136.2	135.8	135.4	135.0	134.6	134.0	133.2	132.3	131.5	130.6	130.0
67.5°	116.2	115.8	115.5	115.1	114.8	114.2	113.7	113.0	112.4	111.8	111.2
70°	104.1	103.6	103.1	102.6	102.1	101.6	101.2	100.6	100.1	99.7	99.1
72.5°	91.4	91.0	90.7	90.3	89.9	89.5	89.0	88.4	87.9	87.3	86.7
75°	72.0	71.6	71.3	71.0	70.7	70.3	70.1	69.9	69.6	69.4	69.0
77.5°	54.7	54.6	54.4	54.3	54.0	53.8	53.6	53.2	52.9	52.6	52.4
80°	43.6	43.3	43.1	42.9	42.5	42.4	42.2	42.1	41.9	41.7	41.6
82.5°	32.6	32.6	32.6	32.5	32.4	32.4	32.3	32.3	32.3	32.2	32.1
85°	19.2	19.0	18.9	18.7	18.5	18.5	18.5	18.5	18.5	18.5	18.3
87.5°	7.8	8.2	8.4	8.6	8.9	9.3	9.8	10.4	10.9	11.4	11.5
90°	1.0	3.2	5.5	7.8	10.1	12.7	15.6	18.5	21.5	24.5	25.3
92.5°	18.9	18.3	17.7	17.0	16.4	17.2	19.4	21.6	23.8	26.1	27.5
95°	62.1	52.8	43.6	34.3	25.0	21.6	24.1	26.6	29.1	31.6	33.2
97.5°	124.8	120.7	116.5	112.4	108.2	98.0	81.7	65.4	49.1	32.8	34.6
100°	172.1	176.7	181.2	185.7	190.3	174.8	139.6	104.3	68.9	33.6	35.4
102.5°	225.9	229.2	232.4	235.7	239.0	221.3	182.8	144.2	105.6	67.0	61.4
105°	303.6	306.0	308.6	311.0	313.5	304.6	284.2	263.8	243.4	223.1	183.0
107.5°	385.5	387.5	389.4	391.4	393.4	396.0	399.3	402.4	405.7	408.8	379.5
110°	440.1	441.9	443.6	445.4	447.3	449.4	451.9	454.4	456.9	459.4	451.9



TEST NUMBER: P332112-927

CATALOG NUMBER: S123DIW-S340D1320U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	492.2	493.8	495.4	497.1	498.7	500.7	503.3	505.7	508.3	510.7	510.9
115°	569.4	570.8	572.1	573.5	574.8	576.6	578.5	580.6	582.7	584.7	586.9
117.5°	644.2	645.9	647.5	649.2	650.9	652.2	653.2	654.3	655.4	656.4	658.2
120°	690.6	692.7	694.7	696.7	698.8	700.1	700.8	701.5	702.2	702.8	704.6
122.5°	737.9	739.6	741.2	742.9	744.6	745.8	746.7	747.6	748.5	749.3	750.6
125°	802.6	804.5	806.3	808.1	809.9	811.3	812.1	813.1	814.0	814.9	815.3
127.5°	865.4	867.2	869.0	870.8	872.7	874.1	875.2	876.3	877.3	878.5	879.2
130°	904.5	906.3	908.2	910.0	911.8	913.1	914.0	915.0	915.8	916.7	917.7
132.5°	942.0	943.8	945.6	947.5	949.3	950.5	951.3	952.0	952.7	953.4	954.3
135°	999.3	1000.6	1002.0	1003.3	1004.7	1005.8	1006.7	1007.7	1008.5	1009.5	1010.1
137.5°	1048.1	1049.9	1051.6	1053.3	1055.0	1056.1	1056.6	1057.2	1057.6	1058.1	1059.2
140°	1080.8	1082.1	1083.5	1084.8	1086.2	1087.2	1087.9	1088.5	1089.3	1089.9	1090.8
142.5°	1110.9	1112.2	1113.6	1115.0	1116.3	1117.4	1118.0	1118.7	1119.4	1120.1	1120.8
145°	1153.1	1154.7	1156.3	1157.9	1159.4	1160.4	1160.9	1161.3	1161.8	1162.2	1162.7
147.5°	1192.8	1193.8	1194.8	1195.9	1197.0	1197.7	1198.2	1198.6	1199.0	1199.5	1200.0
150°	1217.3	1217.9	1218.6	1219.2	1220.0	1220.5	1221.0	1221.4	1221.9	1222.3	1222.8
152.5°	1239.2	1239.5	1239.8	1240.2	1240.5	1240.8	1241.1	1241.3	1241.6	1241.9	1242.7
155°	1270.2	1269.8	1269.3	1268.8	1268.4	1268.3	1268.5	1268.8	1269.0	1269.2	1270.3
157.5°	1294.3	1294.2	1294.2	1294.1	1294.0	1294.0	1293.7	1293.5	1293.2	1293.0	1294.3
160°	1308.9	1308.7	1308.4	1308.2	1308.0	1307.8	1307.6	1307.3	1307.1	1306.9	1308.2
162.5°	1322.8	1322.2	1321.6	1321.0	1320.4	1320.0	1319.8	1319.5	1319.3	1319.1	1320.6
165°	1339.5	1338.8	1338.1	1337.4	1336.7	1336.3	1336.1	1335.9	1335.6	1335.4	1337.2
167.5°	1352.5	1351.6	1350.7	1349.8	1348.8	1348.5	1348.5	1348.5	1348.5	1348.5	1350.3
170°	1359.9	1358.9	1358.0	1357.2	1356.2	1355.7	1355.7	1355.7	1355.7	1355.7	1357.6
172.5°	1364.8	1363.7	1362.6	1361.4	1360.4	1359.9	1360.1	1360.3	1360.5	1360.7	1362.5
175°	1371.0	1369.9	1368.8	1367.6	1366.5	1366.0	1366.3	1366.5	1366.8	1367.0	1368.6
177.5°	1372.7	1371.7	1370.9	1370.0	1369.0	1368.7	1368.9	1369.0	1369.2	1369.4	1370.9
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332112-927

CATALOG NUMBER: S123DIW-S340D1320U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	427.6	428.3	429.0	429.3	429.2	429.1	429.0	429.0
5°	425.4	426.2	427.1	427.4	427.2	427.1	426.8	426.7
7.5°	420.9	421.6	422.3	422.6	422.6	422.5	422.4	422.2
10°	416.8	417.5	418.2	418.5	418.4	418.2	418.0	417.9
12.5°	412.2	412.7	413.3	413.5	413.4	413.3	413.2	413.1
15°	404.0	404.6	405.4	405.4	404.9	404.4	403.9	403.5
17.5°	393.6	394.1	394.6	394.7	394.5	394.3	394.2	394.0
20°	386.0	386.3	386.7	386.7	386.4	386.2	386.0	385.7
22.5°	377.9	378.2	378.4	378.4	378.1	377.8	377.5	377.2
25°	364.5	364.6	364.6	364.6	364.3	364.1	363.8	363.6
27.5°	350.2	350.3	350.3	350.2	349.9	349.6	349.3	349.0
30°	340.3	340.3	340.3	340.0	339.5	338.9	338.3	337.7
32.5°	329.9	329.5	329.1	328.7	328.4	328.0	327.7	327.4
35°	313.1	312.7	312.1	311.7	311.3	310.9	310.5	310.1
37.5°	295.7	295.2	294.5	294.1	293.9	293.6	293.3	293.1
40°	284.4	283.8	283.0	282.6	282.3	281.9	281.6	281.3
42.5°	272.6	271.9	271.2	270.8	270.5	270.1	269.8	269.4
45°	254.9	254.0	252.9	252.3	251.8	251.4	251.0	250.6
47.5°	236.4	235.4	234.4	233.8	233.4	233.1	232.7	232.3
50°	224.1	223.2	222.3	221.6	221.1	220.6	220.1	219.6
52.5°	211.7	210.9	210.1	209.5	209.0	208.5	208.0	207.6
55°	192.7	191.8	190.9	190.3	189.9	189.4	189.0	188.6
57.5°	174.1	173.3	172.5	171.8	171.3	170.9	170.4	169.9
60°	161.0	160.2	159.5	158.9	158.4	158.0	157.6	157.2
62.5°	148.2	147.5	146.8	146.2	146.0	145.7	145.4	145.1
65°	129.4	128.7	128.0	127.6	127.4	127.1	126.8	126.6
67.5°	110.6	110.0	109.5	109.0	108.7	108.3	108.0	107.7
70°	98.5	97.9	97.4	96.9	96.5	96.1	95.6	95.2
72.5°	86.3	85.7	85.2	84.8	84.7	84.4	84.2	84.0
75°	68.6	68.1	67.7	67.4	67.2	66.9	66.7	66.5
77.5°	52.0	51.8	51.5	51.4	51.4	51.4	51.4	51.4
80°	41.5	41.4	41.4	41.4	41.4	41.4	41.4	41.4
82.5°	32.0	31.8	31.7	31.5	31.5	31.4	31.4	31.3
85°	18.1	18.0	17.8	17.7	17.7	17.7	17.7	17.7
87.5°	11.6	11.7	11.9	12.0	12.0	12.1	12.2	12.3
90°	26.2	27.2	28.0	28.8	29.2	29.6	30.1	30.6
92.5°	29.0	30.4	31.8	32.7	33.0	33.3	33.5	33.8
95°	34.8	36.4	37.9	38.7	38.7	38.7	38.7	38.7
97.5°	36.4	38.3	40.0	41.0	41.3	41.5	41.7	42.0
100°	37.2	39.1	40.9	41.9	42.1	42.3	42.5	42.8
102.5°	55.8	50.1	44.6	42.0	42.4	42.8	43.2	43.6
105°	142.9	102.9	62.8	43.0	43.5	43.9	44.4	44.8
107.5°	350.1	320.8	291.4	261.6	231.4	201.1	171.0	140.8
110°	444.4	437.0	429.5	409.6	377.2	344.8	312.5	280.1





TEST NUMBER: P332112-927

CATALOG NUMBER: S123DIW-S340D1320U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	511.0	511.1	511.3	507.9	501.1	494.2	487.4	480.6
115°	589.2	591.4	593.7	595.3	596.2	597.1	598.0	599.0
117.5°	660.0	661.8	663.6	664.6	664.8	665.0	665.2	665.4
120°	706.5	708.3	710.1	711.0	711.0	711.0	711.0	711.0
122.5°	751.9	753.1	754.4	755.1	755.3	755.4	755.7	755.8
125°	815.8	816.3	816.7	817.1	817.6	818.1	818.5	819.0
127.5°	879.9	880.6	881.4	881.5	881.1	880.6	880.1	879.6
130°	918.5	919.5	920.4	920.6	920.1	919.7	919.2	918.8
132.5°	955.2	956.2	957.0	957.2	956.6	955.9	955.3	954.7
135°	1010.8	1011.5	1012.2	1012.2	1011.5	1010.8	1010.1	1009.5
137.5°	1060.3	1061.4	1062.5	1062.8	1062.3	1061.9	1061.4	1061.0
140°	1091.7	1092.7	1093.5	1093.8	1093.3	1092.8	1092.4	1091.9
142.5°	1121.5	1122.2	1123.0	1123.0	1122.4	1121.7	1121.1	1120.5
145°	1163.2	1163.6	1164.0	1164.3	1164.3	1164.3	1164.3	1164.3
147.5°	1200.4	1200.9	1201.3	1201.0	1200.0	1199.0	1197.9	1196.8
150°	1223.2	1223.7	1224.2	1224.0	1223.4	1222.7	1222.0	1221.3
152.5°	1243.5	1244.4	1245.2	1245.1	1244.0	1242.9	1241.9	1240.9
155°	1271.5	1272.6	1273.7	1273.6	1272.2	1270.9	1269.6	1268.2
157.5°	1295.8	1297.1	1298.5	1298.2	1296.5	1294.7	1292.9	1291.2
160°	1309.6	1311.0	1312.3	1312.2	1310.6	1309.0	1307.4	1305.8
162.5°	1322.2	1323.7	1325.2	1325.3	1323.9	1322.5	1321.1	1319.7
165°	1339.0	1340.8	1342.7	1342.7	1341.2	1339.6	1338.0	1336.4
167.5°	1352.1	1353.8	1355.7	1355.7	1353.8	1352.1	1350.3	1348.5
170°	1359.4	1361.2	1363.0	1363.0	1361.2	1359.4	1357.6	1355.7
172.5°	1364.3	1366.1	1367.9	1367.8	1365.8	1363.8	1361.8	1359.9
175°	1370.2	1371.7	1373.3	1373.2	1371.4	1369.6	1367.8	1366.0
177.5°	1372.3	1373.8	1375.2	1375.1	1373.2	1371.4	1369.6	1367.8
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0

(END OF REPORT)